

Ceiling Installation Instructions:

AUDIMUTE ACOUSTIC CEILING BAFFLES

AUDIMUTE ACOUSTIC CEILING CLOUDS

Acoustic Ceiling Baffles:



Acoustic Ceiling Clouds (3'x3' and Smaller):



Instructions:

To ensure proper installation, follow the instructions below and check building codes.

1. Start screwing in the included Eye Hooks into the pre-drilled locations by hand, then use a 9/16" socket to finish screwing them in. ****IMPORTANT**** Be sure not to over-tighten.
2. Hang the Baffle or Cloud using hardware with load ratings twice that of the product's weight.

Ceiling Installation Instructions:

AUDIMUTE ACOUSTIC CEILING BAFFLES

AUDIMUTE ACOUSTIC CEILING CLOUDS

Acoustic Ceiling Clouds (3'x4' and Larger):



Tools Required:

- Power Drill w/ Adjustable Torque
- 3/8" Socket Drive
- 3/8" Socket

Included:

- Acoustic Cloud w/ Rigid Substrates
- 3/8" Drive Self-Tapping Screws
- Steel Perforated Angles

Instructions:

To ensure proper installation, follow the instructions below and check building codes.

1. Chuck the 3/8" socket and drive into drill. Set torque setting to middle of torque range.
2. Align and center Steel Perforated Angle with the locating notches in the structural backers.
3. Insert self-tapping screws through the Steel Perforated Angle using the power drill. ****DO NOT**** over-torque the screws; if over-torquing occurs, remove the screw and insert into a new location. ****IMPORTANT**** Set the torque setting to the middle of the torque range.
4. Hang the Cloud using hardware with load ratings twice that of the Cloud's weight.