

AXOR UNO FORM FOLLOWS PERFECTION





AXOR UNO


PURISM.
IN PERFECTION.

Simplicity of forms. The aesthetics of construction. The original purists let things speak for themselves. AXOR Uno perfects purism. With pipes, the most elemental means of transporting water. Simplest design. Perfectly executed. Subtly raised to the golden ratio. This

ascetic form exudes a unique radiance. At the wash basin. In the shower. At the bathtub. Radically functional. Radically purist. In perfection.

Design: Phoenix Design

AXOR Uno DESIGN






Purist design at its best: from radical to gently curved. Style-defining, striking proportions. Clear-cut. With precise contours.

AXOR Uno DESIGN

A clear design principle: two cylinders. A marriage of precision. At right angles. Consistent in construction. Radically purist.





Maximum ergonomics, minimal design. The loop-handle.

Or the Select button. The purist form of operation. Outstanding.

In form. And function.





Operation reduced to the bare minimum: on and off.
Separate from the temperature handle. As with the single-lever basin mixer. With the operating button on the spout at the front. Purity in its finest form.

The elevation of purism. The floor-standing basin mixer – sculptured to perfection. Refined with the exclusive Polished Brass surface: elevation one step further.





14







Purism in its most fascinating form: from spout to handle design. From gently rounded to clear right angles. Perfect examples: three-hole mixers.









Purism in perfection. Including shower design. The pipe another tribute to the original form of transporting water.





AXOR Showerpipe in traditional pipe appearance. The perfect complement to AXOR Uno - even extending to the shower design. Excellence across the board. In its purist design. As in its functionality. Two buttons, an intuitive and spacious - the mirror glass shelf. The depiction of top quality and indivi-

Each individual product an expression of precision. The well-proportioned AXOR overhead shower. For the first time combined and perfectly in tune with the AXOR thermostat for exposed concealed installation and hand shower. Here not visibly connected with the overhead shower. A tribute to the traditional pipe look. Therefore the ideal composition for an AXOR Uno bathroom.


Opening the overhead shower reveals the latest innovation in spray design: PowderRain and its gently enveloping drops. A highlight in the shower. Perfection in form and function.


A further combination option with the overhead shower: the single-lever shower mixer for concealed installation.

22



AXOR Uno BATHTUB






Ergonomic perfection in the bathtub. Like the AXOR Uno three-hole rim-mounted mixer with loop-handle. Gently curved from the handle to the hand shower.





AXOR Uno BATHTUB





Single lever basin mixer 110, zero handle, with pop-up waste set # 45001, -000, -820, -930

without pull-rod # 45002, -000, -820, -930 (not shown)

Single lever basin mixer 80, zero handle, without pull-rod # 45005, -000, -820, -930 (not shown)



3-hole basin mixer 200, zero handle, with pop-up waste set # 45133, -000, -820, -930



Single lever basin mixer 200, zero handle, without pull-rod # 45003, -000, -820, -930



Single lever basin mixer 260, zero handle, without pull-rod # 45004, -000, -820, -930



Single lever basin mixer floor-standing, zero handle, without waste set # 45037, -000, -820, -930

Basic set # 10452180

WASH BASIN SELECT



Select basin mixer 110 with pop-up waste set # 45010, -000, -820, -930

without pull-rod # 45012, -000, -820, -930 (not shown)

Select basin mixer 80 without pull-rod # 45015, -000, -820, -930 (not shown)



Select basin mixer 220 with pop-up waste set # 45016, -000, -820, -930



Pillar tap 70

without waste set

38130, -000, -820, -930

Select basin mixer 200 without pull-rod # 45013, -000, -820, -930



Select basin mixer 260 without pull-rod # 45014, -000, -820, -930



Select basin mixer 220 for concealed installation, wall-mounted # 45113, -000, -820, -930

Select basin mixer 165, for concealed installation, wall-mounted # 45112, -000, -820, -930 (not shown)

Basic set #13622180



Select pillar tap 80 without waste set # 45130, -000, -820, -930 Single lever basin mixer 100, loop handle, with pop-up waste set # 38023, -000, -820, -930

without pull-rod # 38026, -000, -820, -930 (not shown)

Single lever basin mixer 70, loop handle, without pull-rod # 38021, -000, -820, -930 (not shown)



Single lever basin mixer 240, loop handle, with pop-up waste set # 38036, -000, -820, -930



Single lever basin mixer 190, loop handle, without pull-rod # 38032, -000, -820, -930



Single lever basin mixer 220 for concealed installation, loop handle, wall-mounted # 38122, -000, -820, -930

Single lever basin mixer 250,

loop handle, without pull-rod

38034, -000, -820, -930

Single lever basin mixer 165 for concealed installation, loop handle, wall-mounted # 38121, -000, -820, -930 (not shown)

Basic set # 13622180



Single lever basin mixer, floor-standing, loop handle, without waste set # 38037, -000, -820, -930

Basic set # 10452180

WASH BASIN ELECTRONIC



Electronic basin mixer 220 for concealed installation, wall-mounted # 38120, -000, -820, -930

Electronic basin mixer 165 for concealed installation, wall-mounted # 38119, -000, -820, -930 (not shown)

Basic set # 16180180



Electronic basin mixer # 38010, -000, -820, -930

3-hole basin mixer 200, loop handle, with pop-up waste set

38054, -000, -820, -930

Basic set # 16182180



Electronic basin mixer 220 for concealed installation, wall-mounted # 45111, -000, -820, -930

Electronic basin mixer 160 for concealed installation, wall-mounted # 45110, -000, -820, -930 (not shown)

Basic set # 16180180

BIDET



Single lever bidet mixer, zero handle, with pop-up waste set # 45200, -000, -820, -930



Select bidet mixer with pop-up waste set # 45210, -000, -820, -930



Single lever bidet mixer, loop handle, with pop-up waste set # 38211, -000, -820, -930

Chrome surface (-000), brushed nickel (-820), polished brass (-930) More AXOR finishes: axor-design.com 33

4-hole rim mounted bath mixer, zero handle # 45444, -000, -820, -930

Basic set # 13444180



Single lever bath mixer for concealed installation, zero handle # 45405, -000, -820, -930

with integrated security combination # 45407, -000, -820, -930 (not shown)

Basic set iBox universal # 01800180



Thermostatic bath mixer 1200 for exposed installation # 45421, -000, -820, -930

Thermostatic bath mixer 800 for exposed installation # 45420, -000, -820, -930 (not shown)



Bath spout straight # 45410, -000, -820, -930



Single lever bath mixer, floor-standing, zero handle

45416, -000, -820, -930

Basic set # 10452180



Bath spout, floor-standing, straight # 45412, -000, -820, -930

Basic set # 10452180

34

BATHTUB LOOP HANDLE



3-hole rim mounted bath mixer, loop handle # 38436, -000, -820, -930

Basic set # 13437180



4-hole rim mounted bath mixer, loop handle # 38445, -000, -820, -930

Basic set # 13444180



Single lever bath mixer for exposed installation, loop handle # 38421, -000, -820, -930



Single lever bath mixer for concealed installation, loop handle # 38426, -000, -820, -930

with integrated security combination # 38428, -000, -820, -930 (not shown)

Basic set iBox universal # 01800180



Single lever bath mixer, floor-standing, loop handle # 38442, -000, -820, -930

Basic set # 10452180



Bath spout, floor-standing, curved # 38412, -000, -820, -930

Basic set # 10452180



Bath spout, curved # 38411, -000, -820, -930

This is a selection from the AXOR Uno range. All products in the collection and all complementary products can be found on axor-design.com

Single lever shower mixer for concealed installation, zero handle # 45605, -000, -820, -930

Basic set iBox universal # 01800180



Single lever shower mixer for exposed installation, zero handle # 45600, -000, -820, -930



Single lever shower mixer for exposed installation, loop handle # 38621, -000, -820, -930



Single lever shower mixer for concealed installation, loop handle # 38626, -000, -820, -930

Basic set iBox universal # 01800180

FURTHER SHOWER PRODUCTS



ShowerSelect Round thermostatic mixer highflow for concealed installation # 36721, -000, -820, -930

Basic set iBox universal # 01800180



ShowerSelect Round thermostatic mixer highflow for concealed installation for 1 outlet and additional outlet # 36726, -000, -820, -930

Basic set iBox universal # 01800180



ShowerSelect Round valve for concealed installation for 3 outlets # 36727, -000, -820, -930

Basic set iBox universal # 01800180



ShowerSelect Round thermostatic mixer for concealed installation for 1 outlet # 36722, -000, -820, -930

Basic set iBox universal # 01800180



ShowerSelect Round thermostatic mixer for concealed installation for 2 outlet # 36723, -000, -820, -930

Basic set iBox universal # 01800180



Theromstatic mixer 800 for exposed / concealed installation # 45440, -000, -820, -930



Shower Set with hand shower 120 3jet, wall bar 0,90 m and shower hose # 27987, -000, -820, -930



Showerpipe 800 with thermostatic mixer, overhead shower 350 1jet, baton hand shower and shower hose # 27984, -000, -820, -930



Overhead shower 350 1jet with shower arm # 26034, -000, -820, -930

Overhead shower 350 1jet with ceiling connector 100 mm # 26035, -000, -820, -930



FixFit Porter, round # 36733, -000, -820, -930

Chrome surface (-000), brushed nickel (-820), polished brass (-930) More AXOR finishes: axor-design.com

Argentina – Hansgrohe S.A. / Av. del Libertador 14.323 / Martínez / B1640APB / Buenos Aires Tel. +54 11 4733 2400 / Fax +54 11 4733 2499 / info@hansgrohe.com.ar / hansgrohe.com.ar

Australia - Hansgrohe Pty Ltd. / Level 1 / 123 Camberwell Rd / East Hawthorn / Victoria 3123 Tel. +61 3 9811 9971 / info@hansgrohe.com.au / hansgrohe.com.au

China – Hansgrohe Sanitary (Shanghai) Products Co. Ltd / No. 2999 Shenggang Road / 201611 Shanghai Tel. +86 21 3774 2200 / Fax +86 21 3774 2202 / info@hansgrohe.com / hansgrohe.com.cn

Croatia - Hansgrohe d.o.o. / Horvatova 82 / HR-10010 Zagreb
Tel. +385-1-56-30-800 / Fax +385-1-56-30-899 / info@hansgrohe.hr / hansgrohe.hr

Cyprus - Hansgrohe Middle East & Africa Ltd. / Pentadaktilou Street 2 / Office 104 / 7101 Larnaca (Aradippou) Tel. +357 22 441 370 / Fax +357 22 441 374 / me.support@hansgrohe.com / hansgrohe-middleeast.com

Dubai – Hansgrohe SE DMCC Branch / Swiss Tower, Cluster Y / Jumeirah Lakes Towers, Office 1904 / PO Box 34216 Tel. +971 4 448 0200 / Fax +971 4 448 0299 / me.support@hansgrohe.com / hansgrohe-middleeast.com

Estonia - Hansgrohe Eesti / Mäealuse 2/1 / 12618 Tallinn Tel. +372 6826829 / info@hansgrohe.ee / hansgrohe.ee

Finland - Hansgrohe SE / Helsinki Branch Office / Kavallinmäki 15 / 02710 Espoo Tel. +358 (0) 207 931 340 / Fax +358 (0) 207 931 349 / info@hansgrohe.fi / hansgrohe.fi

Hungary – Hansgrohe Kft. / Forgách utca 11-13 / 1139 Budapest Tel. +36 1 2369090 / info@hansgrohe.hu / hansgrohe.hu

India – Hansgrohe India (pvt.) Ltd. / Office Nos. 601-604 / Sky Station / Viman Nagar / $411\,016$ Pune / Maharashtra Tel. +91 20 $6625\,9500$ / info@hansgrohe.in

Japan – Hansgrohe Japan K.K. / Tennozu First Tower 2F / 2-2-4 Higashi Shinagawa / Shinagawa-ku / Tokyo 140-0002 Tel. +81 3 5715-3073 / Fax +81 3 5715-3088 / info@hansgrohe.co.jp / hansgrohe.co.jp

Latvia – Hansgrohe Latvijas pārstāvniecība / SIA Aqua Studio / Raiņa iela 14 / 3913 Iecava Tel. +371 9229029 / info@hansgrohe.lv / hansgrohe.lv

Lithuania – Hansgrohe atstovybė / Santoza / Ulonų g. 5 / 08240 Vilnius Tel. +370 5 2043291 / info@hansgrohe.lt / hansgrohe.lt

Mexico - Hansgrohe / S. de R.L. de C.V. / German Center 0-2-02 / Av. Santa Fe No. 170 / Col. Lomas de Santa Fe / 01210 Ciudad de México Tel. +52 55 5861 4170 / Fax +52 55 5261 4199 / info@hansgrohe.com.mx / hansgrohe.com.mx

Panama - Centroamérica & el Caribe - Hansgrohe SE Regional Office / Obarrio Calle 58 PH Office One No. 803 / República de Panamá Tel. +507 263 1343 / marketing.cca@hansgrohe.com / hansgrohe-la.com

South Africa - Hansgrohe South Africa (pty) Ltd. / 30 Archimedes Street / Kramerville / Johannesburg 2090 Tel. +27 11 445 0000 / Fax +27 11 445 0199 / sales@hansgrohe.co.za / hansgrohe.co.za

Singapore - Hansgrohe Pte. Ltd. / 69 Mohamed Sultan Road / Singapore 239015 Tel. +65 6884 5060 / Fax +65 6884 5071 / info@hansgrohe.com.sg / hansgrohe.com.sg

Sweden - Hansgrohe AB / Svangatan 2B / 416 68 Göteborg Tel. +46-31 21 66 00 / Fax +46-31 19 01 03 / info@hansgrohe.se / hansgrohe.se

United Kingdom - Hansgrohe Limited / Units D1 and D2 / Sandown Park Trading Estate / Royal Mills / KT10 8BL Esher Surrey Tel. +44 (0) 1372 472 001 / Fax +44 (0) 1372 470 670 / customerservice@hansgrohe.co.uk / pro.hansgrohe.co.uk





EN-AXOR Uno 2017 / Subject to change in the interest of technical advancement. Form No. 84090421 / 03/17/20.0 / Printed in Germany. / Printed on 100% chlorine free bleached paper.

AXOR / Hansgrohe SE Auestrasse 5-9 77757 Schiltach Germany

info@axor-design.com axor-design.com