



VISIT CENDREX.COM
TO SEE OUR LEED V4
COMPLIANT PRODUCTS.



cendrex

Gives you access

...to all types and dimensions of
access doors in record time!

MULTIPURPOSE

AHD



Flush Universal Access Door

AHD-00 | Exposed Flange
AHD-GYP-00 | Drywall Bead Flange
AHD-GYP-SS-00 | Stainless Steel, Drywall Bead Flange
AHD-PLY-00 | Plaster Bead Flange
AHD-SS-00 | Stainless Steel, Exposed Flange

CTR



Flush Universal Access Door with Pantograph Hinge

CTR-00 | Hidden Flange
CTR-MAG-00 | CONTOUR - Magnetic Closing
CTR-SS-00 | Stainless Steel, Hidden Flange

FLE



FLEXISNAP® - Flush Universal Access Door with Adjustable Frame and Magnetic Closing

FLE-00 | No Hinge, Folding Tabs

GFRG



Fiberglass Reinforced Gypsum Access Door

GFRG-PUR-00 | Removable Door, Rounded Corners
GFRG-PUS-00 | Removable Door, Square Corners
GFRG-POR-00 | Removable door, Pop-Out Round
GFRG-HIR-00 | European Type Hinge, Rounded Corners
GFRG-HIS-00 | European Type Hinge, Square Corners

EDG-GYP



Flush Removable Access Door with Drywall Bead Flange

EDG-GYP-00
Concealed Push Latch

RPL



Flush Universal Removable Plastic Access Door with Exposed Flange

RPL-00 | Snap Friction Latch

SFM



Flush Universal Surface Mounted Access Door with Exposed Flange

SFM-00 | Surface Mounted

RMD



Flush Universal Removable Access Door with Hidden Flange

RMD-00 | Hidden Flange Design, with Removable Panel

FIRE-RATED

PFI



Fire-rated Insulated Access Door

PFI-00 | Exposed Flange
PFI-GYP-00 | Drywall Bead Flange
PFI-HS-00 | High Security with Exposed Flange
PFI-PLY-00 | Plaster Bead Flange
PFI-SS-00 | Stainless Steel, Exposed Flange

PFN



Fire-rated Uninsulated Access Door

PFN-00 | Exposed Flange
PFN-GYP-00 | Drywall Bead Flange
PFN-PLY-00 | Plaster Bead Flange
PFN-SS-00 | Stainless Steel, Exposed Flange

PFU



Fire-rated Insulated Upward Opening Access Door with Exposed Flange

PFU-00 | Hex Head Slam Latch and Ring-Key Operated Slam Latch

SPECIALITY

DRD



Draft Stop Access Door for Attic Application with Exposed Flange

DRD-00 | Self-Locking and Closing Mechanism

PAL



Flush Universal Aluminium Insulated Access Door with Exposed Flange

PAL-00 | Neoprene Gasket and Fiberglass Wool Insulation

BTA



Valve Box with Pantograph Hinge

BTA-00 | Hidden Flange
BTA-SS-00 | Stainless Steel, with Hidden Flange

HHD-110



Heavy Duty Access Door For Large Openings

HHD-110 | Exposed Flange
HHD-GYP-110 | Drywall Bead Flange
HHD-PLY-110 | Plaster Bead Flange

HVAC door

HHD-180



Heavy Duty Double Leaf Access Door for Large Openings with Exposed Flange

HHD-180 | Exposed Flange, Double Leaf Access Door

BTV



Valve Box with Plexiglass Window

BTV-00 | Hidden Flange
BTV-SS-00 | Stainless Steel, Hidden Flange

Registered Trademark of Les industries Cendrex Inc.

All the models, dimensions and options
you want. Design your access door!

514-493-1489 | 1-800-479-1489 | info@cendrex.com | cendrex.com

SECURITY

MDS



Medium-Security Flush Universal Access Door with Exposed Flange

MDS-00 | Key-Operated Cylinder Cam Latch, Galvaneel Steel
MDS-SS-00 | Key-Operated Cylinder Cam Latch, Stainless Steel

ALN-GYP



Anti-ligature Door with Drywall Bead Flange

ALN-GYP-00 | Piano Hinge, Gasket, Key-operated cylinder cam latches

PHS-40



High-Security Flush Universal Access Door with Exposed Flange, made in 10-gauge cold-rolled steel

PHS-40 | Mortise Deadbolt Lock with Cylinder
PHS-40C | Mortise Deadbolt Lock with Cylinder, Keyed Differently
PHS-40CKA | Mortise Deadbolt lock with Cylinder, Keyed Alike

RECESSED

AHA



Recessed Access Door

AHA-00 | Without Flange
AHA-GYP-00 | Drywall Bead Flange
AHA-PLY-00 | Plaster Bead Flange
AHA-SS-00 | Stainless Steel without Flange

RAL



ALUMI - Recessed 1/2" or 5/8" Aluminum Access Door with Hidden Flange

RAL-00
 Push Latch, Free Pivot Hinge

OPTIONS

Customize Cendrex's standard products by choosing the size, materials and other options that are right for you.

LOW SECURITY LOCKING MECHANISM



35
 Screwdriver operated cam latch



220
 Screwdriver operated cylinder Cam latch



80
 Ring/tool key operated slam latch



55
 Hex head slam latch and ring key operated slam latch



30
 Slide latch



50
 Allen hex head cam latch

HANDLES



25
 WITH KEY - 4" handle and key operated cam latch



100K
 Key-operated recessed handle cam latch with cap over key path



20
 WITHOUT KEY - 4" handle operated cam latch



22
 WITHOUT KEY - 4" handle operated slam latch



21
 WITHOUT KEY Fixed 4" handle



26
 WITHOUT KEY - L handle

MEDIUM SECURITY LOCKING MECHANISM



10
 Key-operated cylinder cam latch



15
 Mortise cam latch preparation

15C
 Mortise cam latch preparation, keyed differently

15CKA
 Mortise cam latch preparation, keyed alike



85
 Mortise slam latch



85C
 Mortise slam latch with cylinder
85CKA
 Mortise slam latch cylinder keyed alike



90
 Pinned hex head cam latch



C
 Cylinder cam latch, keyed differently

CKA
 Cylinder cam latch, keyed alike

MATERIALS



GS
 Galvaneel steel



AL
 Aluminum



SS
 Stainless steel



CR
 Cold rolled steel

HIGH SECURITY LOCKING MECHANISM



40
 Mortise deadbolt lock



40C
 Mortise Deadbolt Lock with Cylinder, keyed differently

40CKA
 Mortise deadbolt lock with cylinder, keyed alike



99
 Inside release thumbturn for mortise deadbolt lock



45
 Mortise preparation for detention deadbolt lock



46
 Detention deadbolt lock



47
 Detention deadbolt Key

OTHERS



60
 Gasket



160
 Holding cable



240
 Masonry anchors

Design your
 access door
 in no time!