

The latest innovations from Versatex®

Elevate your exterior design with the beauty of premium hardwood and the engineered performance of Versatex® cellular PVC. Enjoy rich, realistic woodgrain options without the endless cycle of fading, scraping, and staining.



New! Nickel Gap for the Canvas Series®

Smart profile, consistent results

The precise tongue-and-groove profile of Nickel Gap leaves a space about as wide as a nickel without extra measuring or spacers for a clean, modern aesthetic.

Hidden fastening compatible

The VZClip system uses the board groove to ensure a secure lock and an unblemished, authentic wood finish without exposed nails or screws.

Engineered for outdoors

The Canvas Series resists moisture, sun, and pests to deliver long life, low maintenance, and enduring good looks, backed by a Lifetime Limited Product Warranty and 12-year limited film laminate warranty.

High-style, low-maintenance woodgrain finishes

Offered in a wide variety of lightly textured, low-gloss finishes, the Canvas Series is the solution to any project's porch ceiling, soffit, wainscotting, and other exterior applications.



Canvas Series colors




VERSATEX™

New! Install Canvas Series® WP4 as cladding

Superior to wood
Canvas Series WP4 replaces fragile cedar and costly tropical hardwoods with no waste from knots, checking, or warping.

Near-zero maintenance
No staining, sealing, or painting is required. Bonded high-tech woodgrain laminate stands up to moisture and UV.

Strength & durability
VZClip attaches cladding securely and invisibly: Stays rot free from ground contact, rooflines, and weather.



New! 6" Stealth Trim for seamless, clean transitions

Custom built for the Canvas Series
Integrates flawlessly with Canvas Series profiles, ensuring an exact color match and woodgrain consistency. Matching screw and plug kits secure trim invisibly.

Deep 1-1/2" pocket
Built-in routing easily conceals the cut ends of the Canvas Series or other brand siding boards, eliminating the need for tedious field routing.

Enhanced width & scale
The new 6" wide profile delivers a prominent, upscale architectural band around windows, doors, corners, and frieze transitions.



Product specifications

PRODUCT DESCRIPTION	DIMENSIONS	APPLICATIONS
Canvas Nickel Gap	3/4" x 5-1/2" (6" nominal) 18' lengths	Porch ceilings, accent walls, wainscoting Not approved for use as cladding
Canvas WP4	3/4" x 5-1/2" (6" nominal) 18' lengths	Exterior cladding (horizontal/vertical), porch ceilings, accent walls
Canvas 6" Stealth Trim	5/4" x 5-1/2" (6" nominal) with 1-1/2" pocket 18' lengths	Accent wall trim, capturing edge cuts for natural expansion and contraction of cladding
Canvas Series Pro Plug® System	Available in all nine Canvas Series colors, 250 lin ft or 750 lin ft packs, 2-3/4" epoxy coated screws, Canvas plugs & installation bit	Fastening Canvas Stealth Trim and Trim Boards