



EI1 120

WINLOCK
FIRE DOORS

WINLOCK

Fire resistance

CE marking in accordance with EN 16034 & EN 13241



EI1 120

Our Winlock EI1 120 fire resistant sectional shutters provide 120 minutes of reliable fire protection, fully compliant with European standards. They are designed for industrial and commercial applications where fire compartmentation is crucial for safety and operational continuity.

Each shutter is custom-built to specification and combines durability with user-friendly operation, available in both manual and automatic versions. A wide range of finishes and colours ensures seamless integration with any architectural style.

Winlock fire resistant sectional shutters are suitable for a wide range of sectors, including industrial production facilities, logistics and distribution centres, commercial and retail environments, and public buildings or critical infrastructure where strict fire safety standards apply.

In addition to fire resistance, our shutters can be equipped with multiple optional features such as Safe Lock (burglary resistance), Smoke Lock (smoke control), Noise Lock (sound insulation), Liquid Lock (liquid barrier), and Food Lock (food-safe configuration).

Manufactured to the highest quality standards, Winlock fire resistant sectional shutters ensure reliable performance, long-lasting durability, and maximum safety - even under intensive daily use in demanding environments.



Technical specifications

Fire resistance classes:	EI1 120, EI2 120, EW 120, E 120
Fire test standard:	EN 1363-1, EN 1363-2, EN 1634-1
Classification standard:	EN 13501-2
Maximum width:	7,440 mm
Maximum height:	7,227 mm
Maximum surface area:	35.85 m²

WINLOCK

WINLOCK

FIRE DOORS

Multiple add-ons
Endless possibilities



winlockfiredoors.com
info@winlockfiredoors.com

