



Surface, Stair & Cleat Brackets

SURFACE MOUNTED FLAT BRACKET

- A simple, strong and attractive alternative for floating shelves
- Black and White powder coated metal
- ½" thick material with ¼" mounting holes
- 4 sizes available: 6" 9" 12" and 15"
- Also available is Stainless steel and Aluminum, both brushed with clear finish

Formica color matches:

- Black 909-58
 White 933-58



Surface Mounted Flat Brackets - Imported

Bracket Size	Pcs/Wgt/Box	Load to Deformation (lbf)
SF6	2 pcs/7 lbs	2000/pr
SF9	2 pcs/10 lbs	1600/pr
SF12	2 pcs/14 lbs	1200/pr
SF15	2 pcs/17 lbs	900/pr
SF6 SS	2 pcs/7 lbs	2000/pr
SF9 SS	2 pcs/10 lbs	1600/pr
SF12 SS	2 pcs/14 lbs	1200/pr
SF15 SS	2 pcs/17 lbs	900/pr
SF6 AL	2 pcs/3 lbs	1100/pr
SF9 AL	2 pcs/4 lbs	800/pr
SF12 AL	2 pcs/5 lbs	600/pr
SF15 AL	2 pcs/7 lbs	500/pr

STAIR TREAD BRACKET

- Black powder coated metal
- Heavy duty support for industrial style design treads
- Can be mounted either direction
- 10 inch by 2 inch support, ¼" thick, ¼" mounting holes



Stair Tread Brackets - Imported

Bracket Size	Pcs/Wgt/Box	Load to Deformation (lbf)
ST10	6 pcs/14 lbs	10,000/pr

Formica color matches:

- Black 909-58

CLEAT SUPPORT BRACKET

- Black Powder coated metal
- Countertop support for side walls and along back edge
- Countertop attachment holes offset with wall holes at 8 inch intervals
- ¼" thick, ¼" mounting holes
- 3 sizes available, 28" 44" and 90"

Formica color matches:

- Black 909-58

Cleat Support Brackets Imported

Bracket Size	Pcs/Wgt/Box
CLT28	2 pcs/13 lbs
CLT44	2 pcs/21 lbs
CLT90	2 pcs/43 lbs



A&M HARDWARE, INC.

Call To Order (888) 647-0200

1165 Strickler Road, Mount Joy, PA 17552 | Fax: (717) 653-5874

www.AandMhardware.com