Specialized Equipment for Specialty Healthcare

ADA COMPLIANT

MADE IN USA


Product Specifications


840

Stretcher Bed



	Model Number	840
	Product Number	**840-003-XX**
Functional & Performance	Base Style	Mobile
	Country of Origin	USA
	Patient Weight Capacity	725 lb
	Power Functions	Lift, Back, Tilt, Foot, & Foot Extension
	Swivel Rotation	0°
	Entry Height Highest point of uncompressed upholstery	18.75”
	Maximum Seat Height	37”
	Programmable Buttons	4
	Programmable Home	✓
	Seat Tilt Range Relative to floor	0-30°
	Foot Section Range Relative to seat angle	0-90°
	Foot Section Extension	7”
Features	Standard Controls	Hand Control
	Optional Controls	Foot Control
	Arms	Optional Slide Back Removable
	Standard Headrest Articulating	Deep Oval or Ophthalmic
Dimensions & Weight	Product Weight	294 lb
	Shipping Weight With upholstery installed	381 lb
	Shipping Weight Without upholstery installed	361 lb
	Shipping Size	80 × 38 × 32”
Electrical	Voltage (V)	100-240 V
	Hertz (Hz)	47-63 Hz
	Current Rating (A)	7 amp
	Plug Type	NEMA type 5–15P
	Battery	28.8V 2.7Ah Lithium Ion
Regulatory & Compliance	Listed to UL 60601-1 & 60601-2	✓
	Listed to CAN/CSA-C22.2 No. 60601-1	✓
	Compliant with 2024 DOJ & HSS Final Rules	✓
	Compliant with 2017 36 CFR Part 1195 Standards for Accessible Medical Diagnostic Equipment	✓
	Compliant with 2010 ADA Standards for Accessible Design	✓





NOTES:

1. THE HEADREST EXTENSION ADDS UP TO 7.0in [17.8cm].
2. OPTIONAL 3 FOOT POWER CORD WITH 90° PLUG AVAILABLE.
3. UPHOLSTERY RELATED DIMENSIONS MAY VARY FROM THOSE SHOWN UP TO .25in [.6cm].
4. INDICATED DIMENSIONS INCLUDE 7.0in [17.8cm] OF POWERED EXTENSION.
5. CASTER LOCKS SHOWN IN STEERING POSITION.
6. MTI RESERVES THE RIGHT TO MAKE ANY PRODUCT CHANGES WITHOUT NOTICE.

© MTI, Inc.
www.mti.net

Specialized Equipment
for Specialty Healthcare

3655 W. Ninigret Drive • Salt Lake City, Utah, 84104-6572
800-924-4655 • 801-875-4999 (Call/text)
customer.service@mti.net