Specialized Equipment for Specialty Healthcare

ADA COMPLIANT

MADE IN USA

Product Specifications

829


Procedure Chair









	Model Number	829	829-SB	829-MB
	Product Number	**829-001-80**	**829-002-80**	**829-003-22**
Functional & Performance	Base Style	Standard	Swivel	Mobile
	Country of Origin	USA	USA	USA
	Patient Weight Capacity	725 lb	725 lb	725 lb
	Power Functions	Lift, Back, Tilt, Foot, & Foot Extension	Lift, Back, Tilt, Foot, & Foot Extension	Lift, Back, Tilt, Foot, & Foot Extension
	Swivel Rotation	0°	333°	0°
	Entry Height Highest point of uncompressed upholstery	18.75”	18.75”	18.75”
	Maximum Seat Height	39”	37”	37”
	Programmable Buttons	4	4	4
	Programmable Home	✓	✓	✓
	Seat Tilt Range Relative to floor	0-30°	0-30°	0-30°
	Foot Section Range Relative to seat angle	0-90°	0-90°	0-90°
	Foot Section Extension	7”	7”	7”
Features	Standard Controls	Foot & Hand Control	Foot & Hand Control	Foot & Hand Control
	Arms	Optional Slide Back Removable	Optional Slide Back Removable	Optional Slide Back Removable
	Standard Headrest Articulating	Oval or Deep Oval	Oval or Deep Oval	Oval or Deep Oval
Dimensions & Weight	Product Weight	292 lb	354 lb	285 lb
	Shipping Weight With upholstery installed	372 lb	434 lb	368 lb
	Shipping Weight Without upholstery installed	355 lb	417 lb	351 lb
	Shipping Size	80 × 32 × 32”	80 × 32 × 32”	80 × 38 × 32”
Electrical	Voltage (V)	100-240 V	100-240 V	100-240 V
	Hertz (Hz)	47-63 Hz	47-63 Hz	47-63 Hz
	Current Rating (A)	7 amp	7 amp	7 amp
	Plug Type	NEMA type 5–15P	NEMA type 5–15P	NEMA type 5–15P
Regulatory & Compliance	Listed to UL 60601-1 & 60601-2	✓	✓	✓
	Listed to CAN/CSA-C22.2 No. 60601-1	✓	✓	✓
	Compliant with 2024 DOJ & HSS Final Rules	✓	✓	✓
	Compliant with 2017 36 CFR Part 1195 Standards for Accessible Medical Diagnostic Equipment	✓	✓	✓
	Compliant with 2010 ADA Standards for Accessible Design	✓	✓	✓






NOTES:


1. THE HEADREST EXTENSION ADDS UP TO 7.0in [17.8cm].
2. OPTIONAL 3 FOOT POWER CORD WITH 90° PLUG AVAILABLE.
3. UPHOLSTERY RELATED DIMENSIONS MAY VARY FROM THOSE SHOWN UP TO .25in [.6cm].
4. INDICATED DIMENSIONS INCLUDE 7.0in [17.8cm] OF POWERED EXTENSION.
5. A PLUSH UPHOLSTERY KIT ADDS UP TO 1.5in [3.8cm] TO THE INDICATED DIMENSION.
6. MTI RESERVES THE RIGHT TO MAKE ANY PRODUCT CHANGES WITHOUT NOTICE.






NOTES:

1. THE HEADREST EXTENSION ADDS UP TO 7.0in [17.8cm].
2. OPTIONAL 3 FOOT POWER CORD WITH 90° PLUG AVAILABLE.
3. UPHOLSTERY RELATED DIMENSIONS MAY VARY FROM THOSE SHOWN UP TO .25in [.6cm].
4. INDICATED DIMENSIONS INCLUDE 7.0in [17.8cm] OF POWERED EXTENSION.
5. A PLUSH UPHOLSTERY KIT ADDS UP TO 1.5in [3.8cm] TO THE INDICATED DIMENSION.
6. MTI RESERVES THE RIGHT TO MAKE ANY PRODUCT CHANGES WITHOUT NOTICE.





NOTES:

1. THE HEADREST EXTENSION ADDS UP TO 7.0in [17.8cm].
2. OPTIONAL 3 FOOT POWER CORD WITH 90° PLUG AVAILABLE.
3. UPHOLSTERY RELATED DIMENSIONS MAY VARY FROM THOSE SHOWN UP TO .25in [.6cm].
4. INDICATED DIMENSIONS INCLUDE 7.0in [17.8cm] OF POWERED EXTENSION.
5. A PLUSH UPHOLSTERY KIT ADDS UP TO 1.5in [3.8cm] TO THE INDICATED DIMENSION.
6. CASTER LOCKS SHOWN IN STEERING POSITION.
7. MTI RESERVES THE RIGHT TO MAKE ANY PRODUCT CHANGES WITHOUT NOTICE.

© MTI, Inc.
www.mti.net

Specialized Equipment for Specialty Healthcare

3655 W. Ninigret Drive • Salt Lake City, Utah, 84104-6572
800-924-4655 • 801-875-4999 (Call/text)
customer.service@mti.net