



Exceeding your expectations with innovative solutions.

Peerless-AV® continues to be a pioneer and market leader in the digital signage arena. We consistently raise the bar, providing innovative, award-winning solutions for interactive displays, out-of-home advertising, in-store displays, POS solutions, and much more. We have creative, compelling solutions for just about any environment.

Our standard products encompass a wide range of digital signage solutions, from dvLED video wall mounting systems to integrated kiosks. As the industry leader in custom solutions for high volume projects, we offer true innovation and technical expertise, all housed within our state-of-the-art facility, to take projects from concept to successful completion. Our dedicated team ensures we're staying ahead of industry trends, providing you with innovative products backed by the Peerless-AV quality you trust.

COMPLETE LINE OF DIGITAL SIGNAGE SOLUTIONS



Outdoor Displays & Accessories pg# 4-5



Outdoor Kiosks pg# 6-7



Indoor Kiosks pg# 8-9



dvLED Video Wall Mounting Systems pg# 10-11















Digital Menu Board Mounts pg# 14



Window Display Mounts pg# 15



Modular Solutions pg# 16-17



Trolleys & Stands pg# 18



Media Storage & Back-to-Back Mounts pg# 19



reerless-AV XtremeTM High Bright Outdoor Displays

The unique, fully-sealed design of the Peerless-AV® Xtreme™ High Bright Outdoor Display is perfect for any professional, digital signage application. These daylight readable displays are an ideal solution for commercial installations including stadiums, theme parks, quick serve restaurants, mass transit and more.

Visit **peerless-av.com/XtremeHB** to learn more.





Xtreme[™] High Bright Outdoor Displays

XHB554-EUK		XHB653-EUK		XHB754-EUK	
Display Size 55" Class (54.6" Diagonal)		Display Size 65" Class (64.5" Diagonal)		Display Size 75" Class (74.5" Diagonal)	
Inputs CVBS, YPbPr, HDMI, DisplayPort, USB, HDBaseT, LAN		Inputs CVBS, HDMI, DisplayPort, USB, LAN		Inputs CVBS, YPbPr, HDMI DisplayPort, USB, HDBaseT, LAN	
Resolution 1920 x 1080	Brightness 2,500cd/m ²	Resolution 1920 x 1080	Brightness 2,500cd/m ²	Resolution 3840 x 2160	Brightness 3,000cd/m²

Viewing Angle

178° Vertical/Horizontal

• Daylight readable displays offer high bright output for a clear, crisp picture, even in direct sunlight

Operating Temperature

-35°C to 60°C

- IP66 rated design prevents the ingress of foreign materials, such as water, dust, moisture and insects, from entering the display
- Patented thermal exhaust system keeps internal components properly cooled in extreme heat


Refresh Rate

60Hz

• Remote and Local monitoring, supported via IP addressable user interface, for temperature, humidity, and power draw diagnostics of the display

Display Orientation

Landscape, Portrait



OUTDOOR ACCESSORIES



Outdoor Universal Tilt Wall Mount. For 32" to 75" Landscape Displays.

model number:

EPT650



Outdoor Flat Wall Mount, Landscape for the XHB754-EUK.

model numbers:

ESF675



Outdoor Universal Flat Wall Mount, for 42" to 80" Portrait Displays.

model numbers:

ESF655P



Outdoor Universal Tilt Wall Mount, for 42" to 80" Portrait Displays.

model numbers: **EST655P**



Outdoor Articulating Wall Mount. For 42" to 75" Landscape Displays.

model number:

EPA762PU



Outdoor Articulating Wall Mount, Landscape for the XHB554-EUK.

model number: **ESA763PU**

Visit peerless-av.com to learn more about Peerless-AV's complete line of outdoor solutions.



peerless-AV Outdoor Kiosks

Replace static signage with Peerless-AV® outdoor kiosks for greater public engagement and seamless updates of digital content whenever, wherever. With a focus on functionality and aesthetics, these outdoor kiosks are designed to be modern, approachable, practical, and endure the rigours of everyday use. Peerless-AV's all-weather rated kiosks are ideal for sharing community information, travel, and weather details, as well as wayfinding, advertising, entertainment, and more.







Display's Operating Temperature Range: -35°C to 60°C

Smart City Kiosks

Includes 55" Xtreme™ High Bright Outdoor Display (XHB554-EUK)

Single Sided: KOP55XHB-(S)-EUK | KOP55XHB-(S)A-EUK Dual Sided: KOP55XHB2-(S)-EUK | KOP55XHB2-(S)A-EUK

> **Display Size** 55" Class



Wind tested up to 135 mph







Display: RoHS FC CE IP W LK



Create an interactive kiosk by adding the IRTO55-XHB4, which can detect up to 10 touch points

- All stainless steel and aluminium body combined with an outdoor rated paint finish to provide the ultimate in corrosion resistance
- Installation is easy without the need for cranes or forklifts
- IP55 rated media cabinet provides a dedicated, spacious area for storing AV components, and the integrated fans provide active cooling
- Available in black or silver and with or without speakers to ensure your product needs are met









Outdoor Digital Signage Boards

Supports 55" Peerless-AV® Xtreme XHB554-EUK, LG 55XE4F-M & Samsung OH55F/OH55A-S Outdoor Displays*

*All Displays Must Be Ordered Separately

Peerless Xtreme: KOF555-1-XHB-EUK, KOF555-2-XHB-EUK, KOF555-3-XHB-EUK LG Electronics: KOF555-1-LGE-EUK, KOF555-2-LGE-EUK, KOF555-3-LGE-EUK Samsung: KOF555-1-SAM-EUK, KOF555-2-SAM-EUK, KOF555-3-SAM-EUK



Display Size 55" Class

SAMSUNG





CREATE A FULLY INTEGRATED DRIVE-THRU SOLUTION WITH A VARIETY OF OPTIONS:



Speaker/ Microphone Kit (KOF-OPT-SPK)



Media Storage Fan (KOF-OPT-FAN)



Internal Media Player Shelf (KOF-OPT-SHELF)

- Available as a single, dual or triple display unit, to ensure your product needs are met
- Modular design allows displays to be installed from the front, without disturbing the adjacent units
- Pedestal base allows for mounting to existing footing, thus eliminating the need for pouring new concrete**





Indoor Kiosks

Choose from a versatile array of sleek, slim and attractive standard kiosk enclosures or create a completely unique kiosk solution fit for any indoor application and market – corporate, education, quick serve restaurants, hospitality, stadiums, retail and more. Our kiosks are customizable to fit your needs – from the choice of technology to custom paint and vinyl wraps. If you can envision it, we can make it happen.

Visit peerless-av.com see the our full line of indoor kiosk solutions.





COOLING FANS

help maintain an ideal operating temperature

TOOL-LESS MICRO ADJUSTMENT

at 8-points for flush display alignment in kiosk window

UNIVERSAL MOUNTING PATTERN

Scalable compatibility from VESA® 200 x 200mm up to 800 x 400mm

HEAVY DUTY BASE

with cable management cut-outs can be bolted to floor for added security



LOCKABLE FRONT & REAR DOOR

allows convenient access for quick installation and simple maintenance

UNIVERSAL WINDOW SIZE

to accommodate all standard 40", 42", 43", 46", 47", 48", 49", 50" 55" or 65" panels

POWDER COATED & CURED

for a durable and long lasting finish ideal for high traffic public areas

MEDIA PLAYER STORAGE

area included within body of the kiosk





KIPC25 models

Floor Standing Portrait Kiosks, Single Sided

For 40"-65" displays

Also available as Back-to-Back dual display model - KIPC25B



KIP522-EUK

Free Standing Landscape & Portrait Kiosk

For 15", 22" or 32" displays



KILH5 models

Floor Standing Landscape Kiosks

For 40"-55" displays

- A wide range of custom aesthetic options also available; options include custom colour finishes, vinyl logos, wraps, etc.
- Internal micro-adjustments allow for quick positioning of display within the kiosk window for flush alignment
- Made in the UK, for quicker lead times



SEAMLESS dvLED Video Wall Mounting Systems


With over 80 years of audio visual experience, our commitment to the creation of cutting-edge technology and standard-setting solutions has elevated us to the status of the industry's most innovative leader. Our Dedicated SEAMLESS dvLED Solutions Team sets the bar for high quality design, while achieving the pinnacle of aesthetic results. Our dynamic group of dvLED professionals include structural and mechanical engineers, product managers, project managers, installers, as well as sales and service personnel. The entire Peerless-AV® dvLED Solutions Team is there every step of the way to ensure every customer receives SEAMLESS product support & service.

Choose between our SEAMLESS Kitted or Bespoke Series dvLED Mounting Systems to fit your specific needs.

SEAMLESS KITTED


Standard, Dedicated & Universal dvLED Mounting Systems

The SEAMLESS Kitted Series dvLED Mounting Systems offer slim, space-saving & aesthetically appealing designs that can be adapted to support all of your dvLED video wall needs.



Standard Slim Flat dvLED Mounting Systems

DS-LEDFS



SAMSUNG

Dedicated Flat dvLED Mounting Systems

DS-LEDIER models




Universal dvLED Mounting Systems - for latching cabinets

DS-LEDUNV models



Accessory: Universal Trim Kit for dvLED Video Walls 90mm to 150mm deep (DS-LEDTK)

This sleek accessory is designed to cover the unsightly sides of dvLED displays and give the video wall a completely finished appearance.



SEAMLESS BESPOKE

Custom dvLED Mounting Systems

Peerless-AV® provides an innovative approach to all our services - both indoors & out. Specializing in custom dvLED solutions, we strive to stay on the cutting edge of what the industry has to offer. We are equipped to work in a variety of markets & environments, giving our customers endless design options (flat, corner or curved configurations).

No dvLED array is too small or too large for our team. We specialise in a wide variety of applications:

Columns | Curved | Corners | Tickers | Floor | Floor-to-wall | Ceiling | + More







Corner Mount Ticker Mount Curved Mount

For full details of our dvLED installs visit www.peerless-av.com/pages/case-studies



SmartMount® Full Service Video Wall Mounts

The SmartMount® video wall series is a comprehensive line of mounts that provide solutions for any environment. Limitless configurations are possible with the ability to accommodate displays in both landscape and portrait orientations. With features such as the tool-less micro-adjustment and the quick release pop out mechanism, we give you the tools you need to create the perfect video wall.

Visit **peerless-av.com** see the full line of award-winning mounting solutions.

RoHS



Supreme Full Service Video Wall Mount with Quick Release



Full Service Thin Video Wall Mount with Quick Release



c (Jus os pd

Full Service Video Wall Mount Landscape with Quick Release

Manual Release Model Available:



Full Service Video Wall Mount with Quick Release

Landscape & Portrait	Landscape & Portrait	Landscape Only	Landscape & Portrait
Orientation	Orientation	Orientation	Orientation
VESA® Pattern 200 x 200 up to 600 x 400mm	VESA® Pattern 200 x 200 up to 400 x 400mm (600 x 400mm with required accessory)	VESA® Pattern In 100mm increments, from 200 x 200 up to 700 x 400mm	VESA® Pattern 200 x 200 up to 600 x 600mm
Max Load 125lb (56.8kg)	Max Load 80lb (36.4kg)	Max Load 125lb (56.8kg)	Max Load 225lb (102kg)
Display Size 46" to 60"	Display Size 46" to 65"	Display Size 46" to 65"	Display Size 65" to 95"
DS-VW775-QR	DS-VW755S	DS-VW765-LQR	DS-VW795-QR
Manual Release Model: DS-VW775	With Quick Helease	DS-VW765-LAND	With Guior Holoase

- Tool-less microadjustment on the x, y and z axis
- ADA compliant when paired with displays ≤ 2" deep and 8-point tool-less micro-adjustment
- Tool-less micro-adjustments at 8 points allows the mount to overcome uneven walls and creates a seamless video wall display
- Quick release pop out mechanism provides convenient display access in recessed applications







ADDITIONAL MOUNTING SOLUTIONS



2x2 Flat Video Wall Mount



3x3 Video Wall Cart & Pedestal Mount

Other Configurations Available



Accessories

Multi-Display Ceiling Mount with Four Telescoping Arms

Other Configurations Available

DS-VW655-2X2	DS-C555-3X3 DS-S555-3X3	DST975-4
Display Size	Display Size	Display Size
46" to 55"	46" to 55"	37" to 75"
Max Load 600lb (272kg)	Max Load 900lb (409kg) 100lb (45kg) per display	Max Load 500lb (227kg) 125lb (57kg) per display
Mounting Pattern	VESA® Pattern	Mounting Pattern
1886 x 1137mm	200 x 200 up to	730 x 405mm
(74.25"W x 44.75"H)	600 x 400mm	(28.75"W x 15.95"H)
Orientation	Orientation	Orientation
Landscape Only	Landscape Only	Landscape Only

 Horizontal adjustment makes mounting and aligning displays quick and easy

- Tool-less micro-adjustment at 8 points seamlessly aligns the displays
- Arms telescope to allow for the desired display spacing
- 0°-20° of till and 360° of swivel

peerless-AV

SmartMount® Digital Menu Board Mounts

Peerless-AV® offers menu board solutions for both wall and ceiling applications to fit all environments. The SmartMount® Digital Menu Board Mounts are perfect for Quick Service Restaurants, Cafeterias, Bars and more. With a one-to-one ordering process and functionality features that reduce installation time and costs, these digital menu board mounts are the perfect solution for your digital signage needs.

RoHS





Landscape configuration

for three displays

M

Landscape



Digital Menu Board Wall Mount with Height & Depth Adjustment

Digital Menu Board Ceiling Mount with Height & Depth Adjustment - Landscape

Landscape	Landscape	Portrait	2x1 Configuration	2x1 Configuration	3x1 Configuration	3x1 Configuration
DS-MBZ642L	DS-MBZ647L	DS-MBZ647P	DS-MBZ942L-2X1	DS-MBZ947L-2X1	DS-MBZ942L-3X1	DS-MBZ947L-3X1
Display Size	Display Size	Display Size 42" to 48"	Display Size	Display Size	Display Size	Display Size
40" to 42"	46" to 65"		40" to 42"	46" to 48"	40" to 42"	46" to 48"
Max Load	Max Load	Max Load	Max Load	Max Load	Max Load	Max Load
100lb (45.5kg)	100lb (45.5kg)	100lb (45.5kg)	200lb (90.9kg)	200lb (90.9kg)	300lb (136kg)	300lb (136kg)
Mounting Pattern	Mounting Pattern	Mounting Pattern	Mounting Pattern	Mounting Pattern	Mounting Pattern	Mounting Pattern
880 x 400mm	975 x 400mm	550 x 400mm	1769 x 400mm	1960 x 400mm	2658 x 400mm	2944 x 400mm

- Tool-less height adjustment and four-corner depth adjustment to alleviate issues with wall imperfections and fine-tuning
- Uses a one-to-one ordering process for an effortless digital signage solution
- Connecting wall plates create a continuous mounting surface for ease of display alignment
- Vertical adjustment on each bracket for post-installation leveling and height adjustment fine tuning
- Quick connect latch automatically engages the wall plate when mounting the display for a speedy set-up and peace of mind





Floor & Ceiling Window Display Mounts

Peerless-AV's unique mounting solutions are ideal for retail applications to showcase eye-catching, digital signage content in store windows. Choose between double-sided or single-sided mounts.

RoHS



Ceiling Window Display Mounts

For Samsung OM55N-D Double-Sided Displays



Floor Window Display Mounts

For Samsung OM55N-D Double-Sided Displays



Floor to Ceiling Cable Mount

Landscape/Portrait

DS-OM55ND-CEIL	DS-OM55ND-FLOOR	DSF265L / DSF265P
Display Size 55" Samsung Double-Sided Display	Display Size 55" Samsung Double-Sided Display	Display Size 46" to 65"
Max Load 100lb (45.4kg)	Max Load 100lb (45.4kg)	Max Load 65lb (29.5kg)
Center of Display	Center of Display	Mounting Pattern
Ceiling Mounted:	Floor Mounted:	600 x 400mm
53" (1350mm)	65" (1650mm)	

- Both floor and ceiling models have a minimal footprint, which allows for installation right up to the window
- Concealed cable management for a sleek and professional appearance
- Mounting solution that attaches at any point along the cable making it ideal for store windows



Modular Series

The Modular Series features connectable components to meet virtually any application, making them the most versatile and easy to install products available. Choose from a variety of kits including ceiling, floor-to-ceiling, and free standing in either single or dual poles, or create your own video wall configuration for your unique installation. The modular series provides a complete digital signage solution for a wide range of applications.

To "build your own" solution, contact Peerless-AV® Customer Care.

Modular Series poles

can be cut to length

on the jobsite


RoHS

• Additional displays can be

stacked on the dual poles

for added versatility to the

installation



Securely mounts to wood

or concrete ceilings and

floors to accommodate

many environments

• Includes simple hook-on

feature, with +20° to -5°

tilt and locks at every 5°

increment














3x3 LANDSCAPE VIDEO WALL Shown in Modular Series Dual Pole Floor-to-Ceiling configuration (SmartMount® Full Service Video Wall Mount with Quick Release.



1 x MOD-CPF2 : Flat Ceiling/Floor Plate
1 x MOD-WP2 : Wall Mount Attachment
2 x MOD-P300 : 3m Pole
1 x MOD-ASC2 : Screen Stacking Clamp
1 x MOD-FPMS2 : Single Display Bracket
1 x MOD-UNL2 : Screen Adaptor

Display Size 46" to 90"

Max Load

211lb (96kg) per display
For multi screen applications the max system
load is 411lb (192kg) with a maximum of 3
displays positioned on one side of the poles
using MOD-ASC2 and MOD-FPMS2 accessories.

VESA® Pattern up to 600 x 400mm

Twin Pole Free Standing Example

1 x MOD-FPP2 : Floor Pedestal Plate 2 x MOD-P200 : 2m Pole 1 x MOD-ASC2 : Screen Stacking Clamp 1 x MOD-FPMS2 : Single Display Bracket 1 x MOD-UNL2 : Screen Adaptor

Display Size 46" to 90"

Max Load

211lb (96kg) per display
For multi screen applications the max system
load is 411lb (192kg) with a maximum of 2
displays positioned on one side of the poles or
4 displays back to back using MOD-ASC2 and
MOD-FPMS2 or MOD-FPMD2 accessories.

VESA® Pattern

up to 600 x 400mm

MOD-AWM2

Modular Series Dual-Pole

Wall Mount Interface & Flat Mount

Display Size 46" to 90"*

Max Load

211lb (96kg) per display when used as a display mount*

*Reference mount specifications when used with optional Flat, Tilt or Video Wall Mounts

VESA® Pattern

200, 300 & 400mm when used as a display mount*

 Display can be positioned at any point along the height of the pole for maximum versatility Integrated cable management runs through poles with open access at both ends for ease of use Provides compatibility with Peerless-AV Flat, Tilt and Video Wall mounts onto the Modular Series Dual Pole configurations



3x2 PORTRAIT VIDEO WALL Shown in Modular Series Dual Pole Floor-to-Wall configuration (SmartMount® Full Service Video Wall Mount with Quick Release, DS-VW765-PQR, required)

Trolleys & Stands

Peerless-AV® trolleys and stands are compatible with a wide range of display sizes, and are perfect for portability or when mounting to a wall is not an option. These solutions provide a safe and secure mounting platform for displaying digital content in public areas like conference rooms, lobbies or convention centers.





RoHS









Flat Panel Floor Stand	Motorised Trolley	Flat Panel Cart	Flat Panel Cart
SS560F	PR598-M	SR560M	SR598*
Display Size	Display Size	Display Size	Display Size
32" to 75"	50" to 98"	32" to 75"	55" to 98"
Max Load 150lb (68.2kg) display 10lb (4.55kg) shelf	Max Load 130kg (286lb) display 4kg (8.8lb) shelf	Max Load 150lb (68.2kg) display 10lb (4.55kg) shelf	Max Load 300lb (136.1kg)
VESA® Pattern 200 x 200 up to 600 x 400mm	VESA® Pattern up to 800 x 600mm	Mounting Pattern 200 x 200 up to 600 x 400mm	VESA® Pattern 200 x 200 up to 900 x 600mm

- Display and optional component shelf can be located anywhere along the column for perfect component placement & viewing height
- Height adjustment at the touch of a button. Trolley offers 500mm of travel, from 1m up to 1.5m
- Display and component shelf can be located anywhere along the column for perfect component placement & viewing height
- Pre-assembled base provides rigidity, stability and quick assembly

* Also available in white: SR598W







SmartMount® Media Storage & Back-to-Back Mounts

Media device storage is simple and effective with the SmartMount® Media Storage Mounts. Available solutions include flat/tilt wall and ceiling mounts and back-to-back ceiling mounts.

RoHS









Flat/Tilt Wall Mount with Media Device Storage

Flat/Tilt Wall Mount with Media Device Storage

Flat/Tilt Ceiling Mount with Media Device Storage

Back-to-Back Ceiling Mount with Media Device Storage

DS508	DST660	DST995	DST965
Display Size 25" to 60"	Display Size 40" to 60"	Display Size 40" to 95"	Display Size 40" to 65"
Internal Storage 378 x 229 x 51mm	Internal Storage 305 x 330 x 61mm	Internal Storage 406 x 279 x 83mm	Max Load 300lb (136kg)
VESA® Pattern Up to 200 x 200mm	VESA® Pattern 200 x 100 up to 400 x 400mm	VESA® Pattern In 100mm increments, starting at 200 x 200 up to 400 x 400mm	Mounting Pattern 730 x 405mm (28.75"W x 15.95"H)

- Ratchet or fixed tilt capabilty for perfect viewing angle (excl DST965)
- Displays can be mounted in portrait & landscape orientation (excl DST965)
- Security hardware to deter tampering and theft
- Easy access to media player for maintenance or repair



For over 80 years, passion and innovation continue to drive Peerless-AV forward.

We proudly design and manufacture the highest quality products, including outdoor displays and TVs, dvLED and LCD video wall systems, complete integrated kiosks, professional carts and stands, and more. Whether a full-scale global deployment or high volume custom project, Peerless-AV develops meaningful relationships and delivers world-class service.

In partnership with Peerless-AV, you are trusting an award-winning team of experts who will support your business every step of the way. For more information, visit peerless-av.com.

