WESTGATE

America's Most **Dependable** Lighting



Season 2 - 2026

PRODUCTSHEET

@WESTGATEMFG

OUTDOOR
Commrcial & Architectural

Page 6

Wall Packs | Floods & Area | Garage & Canopy | Sign & Street | Solar | Security | Bollards

INDOOR
Commrcial & Architectural

Page 186

Panels | Troffers | Linear & Strip | Suspended | Commercial Recessed | T8 Lamps | Cylinders | Vanities

INDUSTRIAL

Page 313

UFO & Linear High Bays | Vapor | Hazardous | Loading Docks | Corn Lamps

RESIDENTIAL

Page 346

Trims | Fans & Lights | Flush Mounts | Disk | Recessed Trims | Pendants | Lamps & String

LAMPS

Page 418

Corn | Retrofit | T8 | T5 | String | Residential | Landscape

UNDER CABINET



Page 445

Linears | Receptacles | USB Ports | Puck | Accessories

RIBBON

Page 459

Tapes | Sheets | 12 Volt | 24 Volt | Accessories

LANDSCAPE

Page 476

Directional | Step | Well | Underwater | Path | Flood | Transformers | Accessories

EXIT & EMERGENCY

Page 530

Combo Signs | Wet Location Signs | Edge-Lit Signs | Thermoplastic Signs | Decorative Signs | Lamp Heads Vandal Shields

ELECTRICAL

Page 554

Weatherproof Boxes & Covers | Conduit Bodies | Ground Clamps | EV Chargers

See controls on each section: motion sensors, photocell, EM, smart app control.

Check out our social media @westgatemfg for more info!

POLICIES

Transactions are subject to terms and conditions. Visit **www.westgatemfg.com/terms-and-conditions** for details.
Valid 06/01/2026 until further notice.

New Arrivals

LW360-PSR Series

WMDL Series

LFXMAX-FLEX Series



BKR-36W Series

SFP Series

FLD4X Series

SFX-G10 Series

LCSB Series



LRP-HL Series

LRT-HL Series

SCRR Series

TRM Series

VLM Series

VLA Series

RLB Series

LLB Series



LIH Series

UHT Series

LVTT Series

FDLO Series



UCLB Series

COMMERCIAL OUTDOOR

WPMX SERIES

WPMAX SERIES

LWPX SERIES

WPCX SERIES

WPX SERIES

WHCX SERIES


LWPMAX SERIES

WAX SERIES

LWAX SERIES

LW360 SERIES

WMXMAX SERIES

WMXPRO SERIES

WMX SERIES


WML-HL

WML2 SERIES


WMXE SERIES

WPAX SERIES

WPFX SERIES

LTW SERIES

LSWX SERIES

WMDL SERIES

WMV SERIES

LESW SERIES


BKH SERIES

BKR SERIES

BKRD SERIES

DLW SERIES

WMS SERIES

LAX SERIES

LFXMAX SERIES

LFX-MD SERIES

LFXPRO SERIES

LFX SERIES

LFXE SERIES

GPX SERIES

LRXB SERIES

LRX SERIES

HML SERIES

SFP SERIES

LF4MAX SERIES

LF4PRO SERIES

LF4 SERIES

LFE SERIES

FLDF SERIES

FLDX SERIES

FLDXPRO SERIES

FLD4X SERIES

FLD3 SERIES

Search for the series name @WESTGATEMFG.COM

FLD2 SERIES

FLVX SERIES

FLVXPRO SERIES

GL SERIES

TC-GL SERIES



TC-FL SERIES

CDX SERIES

CDLX SERIES

CXER SERIES

CGL SERIES

CXU SERIES

CAX SERIES

GPX-GCP SERIES

GSX SERIES

SL SERIES

SLX SERIES

SL-CAM SERIES

FLS SERIES

FLH SERIES



STP SERIES



CIGL SERIES



IGLC SERIES



STL4 SERIES

SOLN SERIES



SOLA SERIES

SOLF SERIES

SOLH SERIES

SOLS SERIES

SOLW SERIES

DAB SERIES

BOL-G4 SERIES

BOL-G5 SERIES



SOLR SERIES

SOLB SERIES

SFX SERIES

SFX-G10 SERIES



SFX-G11 SERIES

LOHB SERIES

TSR SERIES

CL-CONST SERIES

WL SERIES

ACCESSORIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

WALL PACKS

WPMX-24-40W-MCTPB

WPMX-24-40W-MCTPB-BK



WPMX-24-40W-MCTPB-SIL



WPMX-24-40W-MCTPB-WH

HALF-MOON WALL PACK- **BEAM** & POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WPMX-24-40W-MCTPB	24W/32W/40W	160LM/W	30K/40K/50K - Bronze	1
WPMX-24-40W-MCTPB-BK	24W/32W/40W	160LM/W	30K/40K/50K -Black	1
WPMX-24-40W-MCTPB-WH	24W/32W/40W	160LM/W	30K/40K/50K - White	1
WPMX-24-40W-MCTPB-SIL	24W/32W/40W	160LM/W	30K/40K/50K - Silver	1
WPMX-48-80W-MCTPB	48W/64W/80W	160LM/W	30K/40K/50K - Bronze	1
WPMX-48-80W-MCTPB-BK	48W/64W/80W	160LM/W	30K/40K/50K -Black	1
WPMX-48-80W-MCTPB-WH	48W/64W/80W	160LM/W	30K/40K/50K - White	1
WPMX-48-80W-MCTPB-SIL	48W/64W/80W	160LM/W	30K/40K/50K - Silver	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	480 V OPTION	DESCRIPTION
WPMX-24W	OPT-EM-WPMX-24	INTERNAL	OPT-WP-480V	CHANGE VOLTAGE
WPMX-48W	OPT-EM-WPMX-48	INTERNAL		
VANDAL RES.	DESCRIPTION		**SENSOR**	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw		OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE
POWDER COATING			OPT-SEN-NLS-WPMX	WG NETWORK SENSOR
OPT-CLR-85(BK/GR/SR/WH)			OPT-SEN-KEILTON-WPMX	KEILTON NETWORK SENSOR
OPT-CLR-MC (390 SET UP FEE PER PROJECT)			WEC-8RC	REMOTE CONTROL

WPMX-BR

WPMX-BK

WPMX-WH



WPMX-SIL

HALF-MOON WALL PACK WITH PHOTOCELL TYPE 3 LENS POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WPMX-24-40W-MCTP-SR	24W/32W/40W	135LM/W	30K/40K/50K - Bronze	1
WPMX-24-40W-MCTP-BK	24W/32W/40W	135LM/W	30K/40K/50K - Black	1
WPMX-24-40W-MCTP-WH	24W/32W/40W	135LM/W	30K/40K/50K - White	1
WPMX-24-40W-MCTP-SIL	24W/32W/40W	135LM/W	30K/40K/50K - Silver	1
WPMX-48-80W-MCTP-SR	48W/64W/80W	135LM/W	30K/40K/50K - Bronze	1
WPMX-48-80W-MCTP-BK	48W/64W/80W	135LM/W	30K/40K/50K - Black	1
WPMX-48-80W-MCTP-WH	48W/64W/80W	135LM/W	30K/40K/50K - White	1
WPMX-48-80W-MCTP-SIL	48W/64W/80W	135LM/W	30K/40K/50K - Silver	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	480 V OPTION	DESCRIPTION
WPMX-24W	OPT-EM-WPMX-24	INTERNAL	OPT-WP-480V	CHANGE VOLTAGE
WPMX-48W	OPT-EM-WPMX-48	INTERNAL		
VANDAL RES.	DESCRIPTION		**SENSOR**	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw		OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE
POWDER COATING			OPT-SEN-NLS-WPMX	WG NETWORK SENSOR
OPT-CLR-85(BK/GR/SR/WH)			OPT-SEN-KEILTON-WPMX	KEILTON NETWORK SENSOR
OPT-CLR-MC (390 SET UP FEE PER PROJECT)			WEC-8RC	REMOTE CONTROL

WPMAX-25-40W-BR
WPMAX-40-60W-BR

WPMAX-24-45W-VC-BR


WPMAX-60-100W-BR

WPMAX-90-150W-MCTP

WPMAX-25-40W-BK
WPMAX-40-60W-BK

WPMAX-24-45W-VC-BK


WPMAX-60-100W-BK

WPMAX-90-150W-MCTP-BK

WPMAX-25-40W-SIL
WPMAX-40-60W-SIL

WPMAX-24-45W-VC-SIL


WPMAX-60-100W-SIL

WPMAX-90-150W-MCTP-SIL

MAX-FEATURE WALL PACK, VISUAL COMFORT OR LENS TYPE SELECTABLE TYPE 2, 3, 4

ADJUSTABLE CCT, WATTS, PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
WPMAX-27-45W-MCT-VC	27W/36W/45W	135LM/W	30K/40K/50K - Bronze, Visual Comfort Tech.	1
WPMAX-27-45W-MCT-VC-BK	27W/36W/45W	135LM/W	30K/40K/50K - Black, Visual Comfort Tech.	1
WPMAX-27-45W-MCT-VC-SIL	27W/36W/45W	135LM/W	30K/40K/50K - Silver, Visual Comfort Tech.	1
WPMAX-25-40W-MCTP	25W/30W/40W	135LM/W	30K/40K/50K - Bronze	1
WPMAX-25-40W-MCTP-BK	25W/30W/40W	135LM/W	30K/40K/50K - Black	1
WPMAX-25-40W-MCTP-SIL	25W/30W/40W	135LM/W	30K/40K/50K - Silver	1
WPMAX-40-60W-MCTP	40W/50W/60W	135LM/W	30K/40K/50K - Bronze	1
WPMAX-40-60W-MCTP-BK	40W/50W/60W	135LM/W	30K/40K/50K - Black	1
WPMAX-40-60W-MCTP-SIL	40W/50W/60W	135LM/W	30K/40K/50K - Silver	1
WPMAX-60-100W-MCTP	60W/80W/100W	135LM/W	30K/40K/50K - Bronze	1
WPMAX-60-100W-MCTP-BK	60W/80W/100W	135LM/W	30K/40K/50K - Black	1
WPMAX-60-100W-MCTP-SIL	60W/80W/100W	135LM/W	30K/40K/50K - Silver	1
WPMAX-90-150W-MCTP	90W/120W/150W	135LM/W	30K/40K/50K - Bronze	1
WPMAX-90-150W-MCTP-BK	90W/120W/150W	135LM/W	30K/40K/50K - Black	1
WPMAX-90-150W-MCTP-SIL	90W/120W/150W	135LM/W	30K/40K/50K - Silver	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
40W	OPT-EM-WPMAX-40	INTERNAL	OPT-PC-B	BUTTON
60W	OPT-EM-WPMAX-60	INTERNAL	SENSOR	DESCRIPTION
100W	OPT-EM-WPMAX-100	INTERNAL	OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE
VANDAL RES.	DESCRIPTION		OPT-SEN-NLS-WPMAX	WG NETWORK SENSOR
OPT-TRS-T20	Tamper Resistant Screw		OPT-SEN-KEILTON-WPMAX	KEILTON NETWORK SENSOR
	POWDER COATING		WEC-8RC	REMOTE CONTROL
	OPT-CLR-85(BK/GR/SR/WH)		480 V OPTION	DESCRIPTION
	OPT-CLR-MC (390 SET UP FEE PER PROJECT)		OPT-WP-480V	CHANGE VOLTAGE

LWPX-BR

LWPX-BK

LED CUTOFF WALL PACK, **120-277V**, 14" (W) x 9 1/4" (H) x 8 1/4" (D) TYPE 2 LENS

CATALOG NO.	DESCRIPTION			PCK QTY
MCTP POWER & CCT-ADJUSTABLE VERSION				
LWPX-30-80W-MCTP	30W/40W/60W/80W	125LM/W	30K/40K/50K/57K - Bronze	1
LWPX-30-80W-MCTP-BK	30W/40W/60W/80W	125LM/W	30K/40K/50K/57K - Black	1
LED SINGLE POWER & CCT VERSION				
LWPX-50W-30K	50W	6600LM	3000K	1
LWPX-50W-40K	50W	6600LM	4000K	1
LWPX-50W-50K	50W	6600LM	5000K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

WATTS	EM OPTION	DESCRIPTION
50W	OPT-EM-LWPX-50	INTERNAL
80W	OPT-EM-LWPX-80	INTERNAL

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE
OPT-SEN-NLS-LWPX	WG NETWORK SENSOR
OPT-SEN-KEILTON-LWPX	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

VANDAL RES.	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw

480 V OPTION	DESCRIPTION
OPT-WP-480V	CHANGE VOLTAGE

WPCX-21-35W-MCTPB

WPCX-21-35W-MCTPB-BK

WPCX-21-35W-MCTPB-SIL

FULL CUT-OFF WALL PACK, BEAM & POWER & CCT ADJUSTABLE /W PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
WPCX-21-35W-MCTPB	21W/28W/35W	160LM/W	30K/40K/50K - Bronze	1
WPCX-36-60W-MCTPB	36W/48W/60W	160LM/W	30K/40K/50K - Bronze	1
WPCX-60-100W-MCTPB	60W/80W/100W	160LM/W	30K/40K/50K - Bronze	1
WPCX-21-35W-MCTPB-BK	21W/28W/35W	160LM/W	30K/40K/50K -Black	1
WPCX-36-60W-MCTPB-BK	36W/48W/60W	160LM/W	30K/40K/50K -Black	1
WPCX-60-100W-MCTPB-BK	60W/80W/100W	160LM/W	30K/40K/50K -Black	1
WPCX-21-35W-MCTPB-SIL	21W/28W/35W	160LM/W	30K/40K/50K - Silver	1
WPCX-36-60W-MCTPB-SIL	36W/48W/60W	160LM/W	30K/40K/50K - Silver	1
WPCX-60-100W-MCTPB-SIL	60W/80W/100W	160LM/W	30K/40K/50K - Silver	1

WPCX-MCTP

FULL CUT-OFF WALL PACK /W PHOTOCELL POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WPCX-21-35W-MCTP	21W/28W/35W	135LM/W	30K/40K/50K	1
WPCX-36-60W-MCTP	36W/48W/60W	135LM/W	30K/40K/50K	1
WPCX-60-100W-MCTP	60W/80W/100W	135LM/W	30K/40K/50K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	480 V OPTION	DESCRIPTION
60W	OPT-EM-WPCX-60	INTERNAL	OPT-WP-480V	CHANGE VOLTAGE
100W	OPT-EM-WPCX-100	INTERNAL	SENSOR	DESCRIPTION
VANDAL RES.	DESCRIPTION		OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE
OPT-WPCX-TYPEII	TYPE II		OPT-SEN-NLS-WPCX	WG NETWORK SENSOR
OPT-WPCX-TYPEIV	TYPE IV		OPT-SEN-KEILTON-WPCX	KEILTON NETWORK SENSOR
POWDER COATING			WEC-8RC	REMOTE CONTROL
OPT-CLR-85(BK/GR/SR/WH)			VANDAL RES.	DESCRIPTION
OPT-CLR-MC (390 SET UP FEE PER PROJECT)			OPT-TRS-T20	Tamper Resistant Screw

WPX-24W-BR


WPX-42W-BR

WPX-80W-BR

WPX-120W-BR

WPX-24W-BK

WPX-42W-BK

WPX-80W-BK

WPX-120W-BK

WPX-24W-SIL

WPX-42W-SIL

WPX-80W-SIL

WPX-120W-SIL

SPEC SERIES X-GEN CUT-OFF WALL PACK POWER & COLOR TEMPERATURE TUNABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WPX-24W-MCTP	12W/18W/24W	135LM/W	30K/40K/50K - 8"W Bronze	4
WPX-24W-MCTP-BK	12W/18W/24W	135LM/W	30K/40K/50K - 8"W Black	4
WPX-24W-MCTP-SIL	12W/18W/24W	135LM/W	30K/40K/50K - 8"W Silver	4
WPX-42W-MCTP	11W/21W/32W/42W	135LM/W	30K/40K/50K - 10"W Bronze	4
WPX-42W-MCTP-BK	11W/21W/32W/42W	135LM/W	30K/40K/50K - 10"W Black	4
WPX-42W-MCTP-SIL	11W/21W/32W/42W	135LM/W	30K/40K/50K - 10"W Silver	4
WPX-80W-MCTP	20W/40W/60W/80W	135LM/W	30K/40K/50K - 12"W Bronze	2
WPX-80W-MCTP-BK	20W/40W/60W/80W	135LM/W	30K/40K/50K - 12"W Black	2
WPX-80W-MCTP-SIL	20W/40W/60W/80W	135LM/W	30K/40K/50K - 12"W Silver	2
WPX-120W-MCTP	80W/100W/120W	135LM/W	30K/40K/50K - 16"W Bronze	1
WPX-120W-MCTP-BK	80W/100W/120W	135LM/W	30K/40K/50K - 16"W Black	1
WPX-120W-MCTP-SIL	80W/100W/120W	135LM/W	30K/40K/50K - 16"W Silver	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

WATTS	EM OPTION	DESCRIPTION
24W	OPT-EM-WPX-24	INTERNAL
42W	OPT-EM-WPX-42	INTERNAL
80W	OPT-EM-WPX-80	INTERNAL
120W	OPT-EM-WPX-120	INTERNAL

VANDAL RES.	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw

POWDER COATING
OPT-CLR-85(BK/GR/SR/WH)
OPT-CLR-MC (390 SET UP FEE PER PROJECT)

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE
OPT-SEN-NLS-WPX	WG NETWORK SENSOR
OPT-SEN-KEILTON-WPX	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

480 V OPTION	DESCRIPTION
OPT-WP-480V	CHANGE VOLTAGE

WHCX-24-40W-MCTPB

WHCX-24-40W-MCTPB-BK

WHCX-24-40W-MCTPB-WH

WHCX-24-40W-MCTPB-SIL

CYLINDER WALL PACK, **BEAM** & POWER & CCT ADJUSTABLE WITH CONTROLLED UP/DOWN LIGHTING

CATALOG NO.	DESCRIPTION			PCK QTY
WHCX-24-40W-MCTPB	24W/32W/40W	160LM/W	30K/40K/50K - Bronze	1
WHCX-24-40W-MCTPB-BK	24W/32W/40W	160LM/W	30K/40K/50K -Black	1
WHCX-24-40W-MCTPB-WH	24W/32W/40W	160LM/W	30K/40K/50K - White	1
WHCX-24-40W-MCTPB-SIL	24W/32W/40W	160LM/W	30K/40K/50K - Silver	1
WHCX-48-80W-MCTPB	48W/64W/80W	160LM/W	30K/40K/50K - Bronze	1
WHCX-48-80W-MCTPB-BK	48W/64W/80W	160LM/W	30K/40K/50K -Black	1
WHCX-48-80W-MCTPB-WH	48W/64W/80W	160LM/W	30K/40K/50K - White	1
WHCX-48-80W-MCTPB-SIL	48W/64W/80W	160LM/W	30K/40K/50K - Silver	1


WHCX-BR

WHCX-BK

WHCX-WH

WHCX-SIL

HALF-CYLINDER WALL PACK WITH PHOTOCELL TYPE 3 LENS WITH CONTROLLED UP/DOWN LIGHTING POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WHCX-24-40W-MCTP	24W/32W/40W	145LM/W	30K/40K/50K - Bronze	1
WHCX-24-40W-MCTP-BK	24W/32W/40W	145LM/W	30K/40K/50K - Black	1
WHCX-24-40W-MCTP-WH	24W/32W/40W	145LM/W	30K/40K/50K - White	1
WHCX-24-40W-MCTP-SIL	24W/32W/40W	145LM/W	30K/40K/50K - Silver	1
WHCX-48-80W-MCTP	48W/64W/80W	145LM/W	30K/40K/50K - Bronze	1
WHCX-48-80W-MCTP-BK	48W/64W/80W	145LM/W	30K/40K/50K - Black	1
WHCX-48-80W-MCTP-WH	48W/64W/80W	145LM/W	30K/40K/50K - White	1
WHCX-48-80W-MCTP-SIL	48W/64W/80W	145LM/W	30K/40K/50K - Silver	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	480 V OPTION	DESCRIPTION
WHCX-40W	OPT-EM-WHCX-40W	INTERNAL	OPT-WP-480V	CHANGE VOLTAGE
WHCX-80W	OPT-EM-WHCX-80W	INTERNAL		
VANDAL RES.	DESCRIPTION		**SENSOR**	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw		OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE
POWDER COATING			OPT-SEN-NLS-WHCX	WG NETWORK SENSOR
OPT-CLR-85(BK/GR/SR/WH)			OPT-SEN-KEILTON-WHCX	KEILTON NETWORK SENSOR
OPT-CLR-MC (390 SET UP FEE PER PROJECT)			WEC-8RC	REMOTE CONTROL

LWPMAX-BR

LWPMAX-BK

LWPMAX-SIL

SPEC SERIES MAX-FEATURE CUT-OFF WALL PACK, LENS TYPE SELECTABLE TYPE 3, 4

ADJUSTABLE CCT, WATTS, PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
LWPMAX-SM-20-40W-MCTPB-P	20W/30W/40W	135LM/W	30K/40K/50K - Bronze	1
LWPMAX-SM-20-40W-MCTPB-P-BK	20W/30W/40W	135LM/W	30K/40K/50K - Black	1
LWPMAX-SM-20-40W-MCTPB-P-SIL	20W/30W/40W	135LM/W	30K/40K/50K - Silver	1
LWPMAX-MD-40-80W-MCTPB-P	40W/60W/80W	135LM/W	30K/40K/50K - Bronze	1
LWPMAX-MD-40-80W-MCTPB-P-BK	40W/60W/80W	135LM/W	30K/40K/50K - Black	1
LWPMAX-MD-40-80W-MCTPB-P-SIL	40W/60W/80W	135LM/W	30K/40K/50K - Silver	1
LWPMAX-MD-80-120W-MCTPB-P	80W/100W/120W	135LM/W	30K/40K/50K - Bronze	1
LWPMAX-MD-80-120W-MCTPB-P-BK	80W/100W/120W	135LM/W	30K/40K/50K - Black	1
LWPMAX-MD-80-120W-MCTPB-P-SIL	80W/100W/120W	135LM/W	30K/40K/50K - Silver	1
LWPMAX-LG-100-150W-MCTPB-P	100W/120W/150W	135LM/W	30K/40K/50K - Bronze	1
LWPMAX-LG-100-150W-MCTPB-P-BK	100W/120W/150W	135LM/W	30K/40K/50K - Black	1
LWPMAX-LG-100-150W-MCTPB-P-SIL	100W/120W/150W	135LM/W	30K/40K/50K - Silver	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

WATTS	EM OPTION	DESCRIPTION
50W	OPT-EM-LWPX-50	INTERNAL
80W	OPT-EM-LWPX-80	INTERNAL

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE
OPT-SEN-NLS-LWPX	WG NETWORK SENSOR
OPT-SEN-KEILTON-LWPX	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

VANDAL RES.	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw

480 V OPTION	DESCRIPTION
OPT-WP-480V	CHANGE VOLTAGE

WAX-MCTP-BR

WAX-MCTP-BK

WAX-MCTP with adjusted lens

WAX-MCTP-WH

WAX-MCTP-SIL

Shown Installed as Indirect Light

SPEC SERIES MODERN ADJUSTABLE WALL PACK FOR DOWN OR UP LIGHTING INSTALLATION WITH PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
WAX-20-40W-MCTP	20W/30W/40W	140LM/W	30K/40K/50K - Bronze	1
WAX-20-40W-MCTP-WH	20W/30W/40W	140LM/W	30K/40K/50K - White	1
WAX-20-40W-MCTP-BK	20W/30W/40W	140LM/W	30K/40K/50K - Black	1
WAX-20-40W-MCTP-SIL	20W/30W/40W	140LM/W	30K/40K/50K - Silver	1
WAX-50-80W-MCTP	50W/65W/80W	140LM/W	30K/40K/50K - Bronze	1
WAX-50-80W-MCTP-WH	50W/65W/80W	140LM/W	30K/40K/50K - White	1
WAX-50-80W-MCTP-BK	50W/65W/80W	140LM/W	30K/40K/50K - Black	1
WAX-50-80W-MCTP-SIL	50W/65W/80W	140LM/W	30K/40K/50K - Silver	1
WAX-90-120W-MCTP	90W/105W/120W	140LM/W	30K/40K/50K - Bronze	1
WAX-90-120W-MCTP-WH	90W/105W/120W	140LM/W	30K/40K/50K - White	1
WAX-90-120W-MCTP-BK	90W/105W/120W	140LM/W	30K/40K/50K - Black	1
WAX-90-120W-MCTP-SIL	90W/105W/120W	140LM/W	30K/40K/50K - Silver	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

WATTS	EM OPTION	DESCRIPTION	480 V OPTION	DESCRIPTION
40W	**OPT-EM-WAX-40**	INTERNAL	**OPT-WP-480V**	CHANGE VOLTAGE
80W	**OPT-EM-WAX-80**	INTERNAL		
120W	**OPT-EM-WAX-120**	INTERNAL		

VANDAL RES.	DESCRIPTION	SENSOR	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw	**OPT-SEN-3MRLV-5**	PROGRAMMABLE MICROWAVE
POWDER COATING		**OPT-SEN-NLS-WAX**	WG NETWORK SENSOR
OPT-CLR-85(BK/GR/SR/WH)		**OPT-SEN-KEILTON-WAX**	KEILTON NETWORK SENSOR
OPT-CLR-MC (390 SET UP FEE PER PROJECT)		**WEC-8RC**	REMOTE CONTROL

LWAX-BR

LWAX-BK

LWAX-WH

Shown with Shroud

Mounting Options Shown with LWAX-12W

GEN. 2 ADJUSTABLE WALL PACK, WATTAGE & CCT SELECT, WITH PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
LWAX-SM-12W-30K-P	12W	1500LM	30K	12
LWAX-SM-12W-30K-P-WH	12W	1500LM	30K	12
LWAX-SM-12W-40K-P	12W	1500LM	40K	12
LWAX-SM-12W-50K-P	12W	1500LM	50K	12
LWAX-SM-12W-50K-P-WH	12W	1500LM	50K	12
LWAX-MD-30W-30K-P	30W	3900LM	30K	4
LWAX-MD-30W-40K-P	30W	3900LM	40K	4
LWAX-MD-30W-50K-P	30W	3900LM	50K	4
LWAX-MD-15-50W-MCTP-P	15W/20W/30W/50W	125LM/W	30K/40K/50K/57K	4
LWAX-MD-15-50W-MCTP-P-BK	15W/20W/30W/50W	125LM/W	30K/40K/50K/57K	4
LWAX-MD-15-50W-MCTP-P-WH	15W/20W/30W/50W	125LM/W	30K/40K/50K/57K	4
LWAX-LG-50-120W-MCTP-P	50W/80W/120W	130LM/W	30K/40K/50K/57K	2
LWAX-LG-50-120W-MCTP-P-BK	50W/80W/120W	130LM/W	30K/40K/50K/57K	2
LWAX-LG-50-120W-MCTP-P-WH	50W/80W/120W	130LM/W	30K/40K/50K/57K	2
LWA-SH1	Shroud For LWAX SM, Bronze			
LWA-SH2	Shroud For LWAX MD, Bronze			
LWA-SH3	Shroud For LWAX LG, Bronze			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

SIZE	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
SM	OPT-EM-LWAX-SM	EXTERNAL BACK BOX	OPT-TRS-T20	Tamper Resistant Screw
MD	OPT-EM-LWAX-MD	INTERNAL	SENSOR	DESCRIPTION
LG	OPT-EM-LWAX-LG	INTERNAL	OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE (BI-LEVEL)
	POWDER COATING		OPT-SEN-NLS-LWAX	WG NETWORK SENSOR
	OPT-CLR-85(BK/GR/SR/WH)		OPT-SEN-KEILTON-LWAX	KEILTON NETWORK SENSOR
	OPT-CLR-MC (390 SET UP FEE PER PROJECT)		WEC-8RC	OPTIONAL REMOTE

LWAX-SM-BR

LWAX-MD-BR

LWAX-LG-BR



Mounting Options Shown with LWAX-12W

LWAX-SM-WH

Shown with Shroud

WHILE SUPPLIES LAST

CUTOFF WALL PACK 120-277V TYPE 2 LENS POWER & CCT-ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LWAX-SM-12W-50K	12W	1500LM	5000K	12
LWAX-MD-30W-30K	30W	3900LM	3000K	4
LWAX-MD-30W-50K	30W	3900LM	5000K	4
LWAX-SM-12W-30K-WH	12W	1500LM	3000K	12
LWA-SH1	Shroud For LWAX SM, Bronze			
LWA-SH2	Shroud For LWAX MD, Bronze			
LWA-SH3	Shroud For LWAX LG, Bronze			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

SIZE	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
SM	OPT-EM-LWAX-SM	EXTERNAL BACK BOX	OPT-TRS-T20	Tamper Resistant Screw
MD	OPT-EM-LWAX-MD	INTERNAL	**SENSOR**	DESCRIPTION
LG	OPT-EM-LWAX-LG	INTERNAL	OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE (BI-LEVEL)
	POWDER COATING		OPT-SEN-NLS-LWAX	WG NETWORK SENSOR
	OPT-CLR-85(BK/GR/SR/WH)		OPT-SEN-KEILTON-LWAX	KEILTON NETWORK SENSOR
	OPT-CLR-MC (390 SET UP FEE PER PROJECT)		WEC-8RC	OPTIONAL REMOTE

LW360-15-40W-MCTP-PSR

LW360-15-40W-MCTP-PSR-BK

LW360-15-40W-MCTP-PSR-SIL

LW360-15-40W-MCTP-PSR-WH

LW360-60-120W-MCTP-PSR

LW360-60-120W-MCTP-PSR-BK

LW360-60-120W-MCTP-PSR-SIL

LW360-60-120W-MCTP-PSR-WH

LED 360° ROTATABLE WALL PACK, PHOTOCELL, SENSOR-READY

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
LW360-15-40W-MCTP-PSR	15W/25W/30W/40W	150LM/W	30K/40K/50K - Bronze	1
LW360-60-120W-MCTP-PSR	60W/80W/100W/120W	150LM/W	30K/40K/50K - Bronze	1
LW360-15-40W-MCTP-PSR-WH	15W/25W/30W/40W	150LM/W	30K/40K/50K -White	1
LW360-60-120W-MCTP-PSR-WH	60W/80W/100W/120W	150LM/W	30K/40K/50K - White	1
LW360-15-40W-MCTP-PSR-SIL	15W/25W/30W/40W	150LM/W	30K/40K/50K - Silver	1
LW360-60-120W-MCTP-PSR-SIL	60W/80W/100W/120W	150LM/W	30K/40K/50K - Silver	1
LW360-15-40W-MCTP-PSR-BK	15W/25W/30W/40W	150LM/W	30K/40K/50K - Black	1
LW360-60-120W-MCTP-PSR-BK	60W/80W/100W/120W	150LM/W	30K/40K/50K - Black	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
25W, 40W, 60W	OPT-EM-LW360	INTERNAL
80W	OPT-EM-LW360-LG	INTERNAL

POWDER COATING
OPT-CLR-85(BK/GR/SR/WH)
OPT-CLR-95(BK/GR/SR/WH)
OPT-CLR-35-SHR (BK/GR/SR/WH)
OPT-CLR-MC (390 SET UP FEE PER PROJECT)

PHOTOCELL	DESCRIPTION
OPT-LW360-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-LW360-3MRLV-5	PROGRAMMABLE MICROWAVE
OPT-SEN-NLS-LW360	WG NETWORK SENSOR
OPT-SEN-KEILTON-LW360	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

LW360-40W-BR
LW360-60W-BR
LW360-80W-BR
LW360-120W-BR

LW360-25W-BR

LW360-60W-MCTP-G2-BK

LW360-25W-MCT-G2-WH

LW360-25W-BK

LW360-25W-WH

Shown with Extended EM Box & Shroud

LED 360° ROTATABLE WALL PACK 120-277V G2 SERIES OFFERS A LARGE, HINGED BACK BOX

CATALOG NO.	DESCRIPTION			PCK QTY
LW360-25W-30K-G2	25W	3250LM	3000K - Bronze	4
LW360-25W-40K-G2	25W	3250LM	4000K - Bronze	4
LW360-25W-50K-G2	25W	3250LM	5000K - Bronze	4
LW360-40W-30K-G2	40W	5200LM	3000K - Bronze	4
LW360-40W-40K-G2	40W	5200LM	4000K - Bronze	4
LW360-40W-50K-G2	40W	5200LM	5000K - Bronze	4
LW360-60W-30K-G2	60W	7800LM	3000K - Bronze	2
LW360-60W-40K-G2	60W	7800LM	4000K - Bronze	2
LW360-60W-50K-G2	60W	7800LM	5000K - Bronze	2
LW360-80W-30K-G2	80W	10400LM	3000K - Bronze	2
LW360-80W-40K-G2	80W	10400LM	4000K - Bronze	2
LW360-80W-50K-G2	80W	10400LM	5000K - Bronze	2
LW360-120W-30K-G2	120W	15600LM	3000K - Bronze	2
LW360-120W-40K-G2	120W	15600LM	4000K - Bronze	2
LW360-120W-50K-G2	120W	15600LM	5000K - Bronze	2

MCT CCT-ADJUSTABLE LED 360° ROTATABLE WALL PACK, 120-277V

LW360-25W-MCT-G2	25W	3250LM	30K/40K/50K - Bronze	4
LW360-60W-MCT-G2	60W	7800LM	30K/40K/50K - Bronze	2

MCTP POWER & CCT-ADJUSTABLE LED 360° ROTATABLE WALL PACK, 120-277V

LW360-60W-MCTP-G2	25W/40W/60W	130LM/W	30K/40K/50K - Bronze	2
LW360-60W-MCTP-WH-G2	25W/40W/60W	130LM/W	30K/40K/50K - White	2
LW360-60W-MCTP-BK-G2	25W/40W/60W	130LM/W	30K/40K/50K - Black	2
LW360-SH1	Shroud For LW360 Series, Bronze Finish			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
25W, 40W, 60W	OPT-EM-LW360	INTERNAL	OPT-LW360-PC-B	BUTTON
80W	OPT-EM-LW360-LG	INTERNAL		

SENSOR	DESCRIPTION	POWDER COATING
OPT-SEN-LW360-3MRLV-5	PROGRAMMABLE MICROWAVE	OPT-CLR-85(BK/GR/SR/WH)
OPT-SEN-NLS-LW360	WG NETWORK SENSOR	OPT-CLR-95(BK/GR/SR/WH)
OPT-SEN-KEILTON-LW360	KEILTON NETWORK SENSOR	OPT-CLR-35-SHR (BK/GR/SR/WH)
WEC-8RC	REMOTE CONTROL	OPT-CLR-MC (390 SET UP FEE PER PROJECT)

LW360-25W-30K-WH

LW360-60W-30K
LW360-80W-30K

WHILE SUPPLIES LAST

LED ROTATABLE WALL PACK, 120-277V DARK BRONZE & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
LW360-60W-30K	60W	8100LM	3000K	2
LW360-80W-30K	80W	10800LM	3000K	2
LW360-80W-40K	80W	10800LM	4000K	2
LW360-25W-30K-WH	25W	3375LM	3000K	4
LW360-SH1	Shroud For LW360 Series, Bronze Finish			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
25W, 40W, 60W	OPT-EM-LW360	INTERNAL	OPT-LW360-PC-B	BUTTON
80W	OPT-EM-LW360-LG	INTERNAL		

SENSOR	DESCRIPTION	POWDER COATING
OPT-SEN-LW360-3MRLV-5	PROGRAMMABLE MICROWAVE	OPT-CLR-85(BK/GR/SR/WH)
OPT-SEN-NLS-LW360	WG NETWORK SENSOR	OPT-CLR-95(BK/GR/SR/WH)
OPT-SEN-KEILTON-LW360	KEILTON NETWORK SENSOR	OPT-CLR-35-SHR (BK/GR/SR/WH)
WEC-8RC	REMOTE CONTROL	OPT-CLR-MC (390 SET UP FEE PER PROJECT)

WMXMAX

Narrow

Wide



WMXMAX FULL CONTROL OF BEAM ANGLE, CCT, WATTS, PHOTOCELL

CATALOG NO.	DESCRIPTION		
WMXMAX-40-60W-MCTPB	40W/50W/60W	135LM/W	30K/40K/50K
WMXMAX-50-80W-MCTPB	50W/60W/80W	135LM/W	30K/40K/50K
WMXMAX-80-120W-MCTPB	80W/100W/120W	135LM/W	30K/40K/50K

Shown with Shroud

WMXPRO-SM DARK BRONZE

WMXPRO-MD DARK BRONZE

WMXPRO-LG DARK BRONZE

SPEC SERIES TRADITIONAL WALL PACK, GLASS LENS 480V OPTION POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WMXPRO-SM-15-30W-MCTP	15W/20W/25W/30W	130LM/W	30K/40K/50K/57K	4
WMXPRO-MD-20-60W-MCTP	20W/30W/50W/60W	130LM/W	30K/40K/50K/57K	2
WMXPRO-MD-20-80W-MCTP	20W/40W/60W/80W	130LM/W	30K/40K/50K/57K	2
WMXPRO-LG-50-120W-MCTP	50W/80W/100W/120W	130LM/W	30K/40K/50K/57K	1

Shown with Shroud

WMX-SM DARK BRONZE

WMX-MD DARK BRONZE

WMX-LG DARK BRONZE

SPEC SERIES TRADITIONAL WALL PACK, GLASS LENS 480V OPTION POWER ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WMX-SM-15-30W-30K	15W/20W/25W/30W	130LM/W	3000K	4
WMX-SM-15-30W-40K	15W/20W/25W/30W	130LM/W	4000K	4
WMX-SM-15-30W-50K	15W/20W/25W/30W	130LM/W	5000K	4
WMX-MD-20-50W-30K	20W/30W/40W/50W	130LM/W	3000K	2
WMX-MD-20-50W-40K	20W/30W/40W/50W	130LM/W	4000K	2
WMX-MD-20-50W-50K	20W/30W/40W/50W	130LM/W	5000K	2
WMX-MD-20-80W-30K	20W/40W/60W/80W	130LM/W	3000K	2
WMX-MD-20-80W-40K	20W/40W/60W/80W	130LM/W	4000K	2
WMX-MD-20-80W-50K	20W/40W/60W/80W	130LM/W	5000K	2
WMX-LG-50-120W-30K	50W/80W/100W/120W	130LM/W	3000K	1
WMX-LG-50-120W-40K	50W/80W/100W/120W	130LM/W	4000K	1
WMX-LG-50-120W-50K	50W/80W/100W/120W	130LM/W	5000K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

SIZE	EM OPTION	DESCRIPTION
SM	OPT-EM-WMX-SM	EXTERNAL BOX
MD	OPT-EM-WMX-MD	INTERNAL
LG	OPT-EM-WMX-LG	INTERNAL

VANDAL RES.	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw

POWDER COATING
OPT-CLR-85(BK/GR/SR/WH)
OPT-CLR-95(BK/GR/SR/WH)
OPT-CLR-MC (390 SET UP FEE PER PROJECT)

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-WMXPRO	WG NETWORK SENSOR
OPT-SEN-KEILTON-WMXPRO	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

480 V OPTION	DESCRIPTION
OPT-WP-480V	CHANGE VOLTAGE

WML2-28W-50K-HL-SM

WHILE SUPPLIES LAST

LED NON-CUTOFF WALL PACK WITH DIRECTIONAL OPTIC LENS 120-277V TYPE 3 LENS

CATALOG NO.	DESCRIPTION		
WML2-28W-50K-HL-SM	28W	3780LM	5000K
WML2-50W-50K-SM-D	50W	6000LM	5000K
WML2-50W-30K-SM	50W	5500LM	3000K
WML2-50W-30K-HL	48W	6000LM	3000K

WML-HL-30W

WML-HL-60W/80W/100W

WHILE SUPPLIES LAST

LED NON-CUTOFF WALL PACK 120-277V DARK BRONZE

CATALOG NO.	DESCRIPTION		
WML-HL-30W-30K	30W	4200LM	3000K
WML-HL-60W-30K	60W	8700LM	3000K
WML-HL-80W-30K	80W	11600LM	3000K
WML-HL-100W-30K	100W	14800LM	3000K

WMXE-65W/85W/120W-BR

WMXE-65W/85W/120W-BK



WMXE-150W-BR

WMXE-150W-BK

BUILDER SERIES TRADITIONAL GLASS LENS WALL PACK WITH PHOTOCELL **480V** OPTION, PHOTOCELL DISCONNECT SWITCH

CATALOG NO.	DESCRIPTION			PCK QTY
MP	**POWER ADJUSTABLE BUILDER SERIES TRADITIONAL WALL PACK**			
WMXE-MD-25-65W-50K-P	25W/45W/65W	140LM/W	5000K - Bronze	2
WMXE-MD-45-85W-50K-P	45W/65W/85W	140LM/W	5000K - Bronze	2
WMXE-MD-80-120W-50K-P	80W/100W/120W	140LM/W	5000K - Bronze	2
MCTP	**POWER & 3CCT ADJUSTABLE BUILDER SERIES TRADITIONAL WALL PACK**			
WMXE-MD-25-65W-MCTP-P	25W/45W/65W	140LM/W	3000K/4000K/5000K - Bronze	2
WMXE-MD-45-85W-MCTP-P	45W/65W/85W	140LM/W	3000K/4000K/5000K - Bronze	2
WMXE-MD-80-120W-MCTP-P	80W/100W/120W	140LM/W	3000K/4000K/5000K - Bronze	2
WMXE-LG-100-150W-MCTP-P	100W/120W/150W	140LM/W	3000K/4000K/5000K - Bronze	1
WMXE-MD-45-85W-MCTP-P-BK	45W/65W/85W	140LM/W	3000K/4000K/5000K - Black	2
WMXE-LG-100-150W-MCTP-P-BK	100W/120W/150W	140LM/W	3000K/4000K/5000K - Black	1
MCTP	**POWER & 3CCT ADJUSTABLE BUILDER SERIES TRADITIONAL WALL PACK WITH EMERGENCY BACKUP**			
WMXE-MD-25-65W-MCTP-P-EM	25W/45W/65W	140LM/W	30K/40K/50K - Bronze	2
QUICK SHIP WMXE-MD-45-85W-MCTP-P-EM	45W/65W/85W	140LM/W	30K/40K/50K - Bronze	2
WMXE-MD-80-120W-MCTP-P-EM	80W/100W/120W	140LM/W	30K/40K/50K - Bronze	2
WMXE-LG-100-150W-MCTP-P-EM	100W/120W/150W	140LM/W	30K/40K/50K - Bronze	1

FOR COLD-WEATHER EM OPTION SEE PAGE 527

Shield For WMX Series

Shown with Shroud

WMX-SM DARK BRONZE

WMX-MD DARK BRONZE

WMX-LG DARK BRONZE

SPEC SERIES TRADITIONAL WALL PACK, GLASS LENS 480V OPTION

POWER & COLOR TEMPERATURE TUNABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WMX-MCTP-D	80W Max	9000LM Max	3000K~5700K	2
WMX-MCTP-D-WH	80W Max	9000LM Max	3000K~5700K	2
MCTP-RC1	Remote Control for Multi-Color Temp. & Power Outdoor Fixture (One per projects)			
WML-SH2	Shield For WML 50W, 60W, 80W, 100W, WMX			
WML-SH3	Shield For WML 120W			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

SIZE	EM OPTION	DESCRIPTION
SM	OPT-EM-WMX-SM	EXTERNAL BOX
MD	OPT-EM-WMX-MD	INTERNAL
LG	OPT-EM-WMX-LG	INTERNAL

VANDAL RES.	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw

POWDER COATING
OPT-CLR-85(BK/GR/SR/WH)
OPT-CLR-95(BK/GR/SR/WH)
OPT-CLR-MC (390 SET UP FEE PER PROJECT)

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-WMXPRO	WG NETWORK SENSOR
OPT-SEN-KEILTON-WMXPRO	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

480 V OPTION	DESCRIPTION
OPT-WP-480V	CHANGE VOLTAGE

WPAX-100W-MCTP

SPEC SERIES MODERN CUT-OFF WALL PACK WITH 20% FRONT LIGHT & PHOTOCELL

POWER & CCT ADJUSTABLE, 20% NON-CUTOFF AMBIENT LIGHT, 80% FULL-CUTOFF LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
WPAX-100W-MCTP	60W/80W/100W	130LM/W	30K/40K/50K	2

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

WATTS	EM OPTION	DESCRIPTION
All	OPT-EM-WPAX	INTERNAL

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

480 V OPTION	DESCRIPTION
OPT-WP-480V	CHANGE VOLTAGE

POWDER COATING
OPT-CLR-85(BK/GR/SR/WH)
OPT-CLR-MC (390 SET UP FEE PER PROJECT)

SENSOR	DESCRIPTION
OPT-SEN-3MRLV-5	EXTERNAL MICROWAVE
OPT-SEN-NLS-WPAX	WG NETWORK SENSOR
OPT-SEN-KEILTON-WPAX	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

VANDAL RES.	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw

WPFX-SM

WPFX-MD

WPFX-LG

BUILDER SERIES FLAT WALL PACK WITH PHOTOCELL GLASS LENS AND VANDAL SCREWS

CATALOG NO.	DESCRIPTION			PCK QTY
WPFX-SM-15-40W-MCTP-P	15W/25W/40W	130LM/W	30K/40K/50K	1
WPFX-MD-20-40W-MCTP-P	20W/30W/40W	130LM/W	30K/40K/50K	1
WPFX-MD-40-80W-MCTP-P	40W/60W/80W	130LM/W	30K/40K/50K	1
WPFX-LG-80-120W-MCTP-P	80W/100W/120W	130LM/W	30K/40K/50K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR COLD-WEATHER EM OPTION SEE PAGE 527

SIZE	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
SM	OPT-EM-WPFX-SM	INTERNAL	OPT-PC-B	BUTTON
MD	OPT-EM-WPFX-MD	INTERNAL	SENSOR	DESCRIPTION
LG	OPT-EM-WPFX-LG	INTERNAL	OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE
480 V OPTION	DESCRIPTION		OPT-SEN-NLS-WPFX	WG NETWORK SENSOR
OPT-WP-480V	CHANGE VOLTAGE		OPT-SEN-KEILTON-WPFX	KEILTON NETWORK SENSOR
POWDER COATING			WEC-8RC	REMOTE CONTROL
OPT-CLR-85(BK/GR/SR/WH)			VANDAL RES.	DESCRIPTION
OPT-CLR-MC (390 SET UP FEE PER PROJECT)			OPT-TRS-T20	Tamper Resistant Screw

LTW-50NW

LED SEMI-CUTOFF VANDAL-PROOF WALL PACK 120-277V DARK BRONZE

CATALOG NO.	DESCRIPTION			PCK QTY
LTW-50NW	50W	4400LM	4000K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL	OPT-EM-LTW	INTERNAL	OPT-PC-B	BUTTON
480 V OPTION	DESCRIPTION		SENSOR	DESCRIPTION
OPT-WP-480V	CHANGE VOLTAGE		OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE BI-LEVEL
VANDAL RES.	DESCRIPTION		OPT-SEN-NLS-LTW	WG NETWORK SENSOR
OPT-TRS-T20	Tamper Resistant Screw		OPT-SEN-KEILTON-LTW	KEILTON NETWORK SENSOR
POWDER COATING			WEC-8RC	REMOTE CONTROL
N/A				

LSWX-BR

LSWX-BK

LSWX-WH

11" LED SMALL WALL PACK WITH PHOTOCELL **120-277V** TYPE 2 LENS

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
MCTP	**POWER & CCT-ADJUSTABLE SMALL WALL PACK WITH PHOTOCELL**			
LSWX-13-26W-MCTP-PC	13W/20W/26W	4231LM	30K/40K/50K - Bronze	4
LSWX-13-26W-MCTP-PC-BK	13W/20W/26W	4231LM	30K/40K/50K - Black	4
LSWX-13-26W-MCTP-PC-WH	13W/20W/26W	4231LM	30K/40K/50K - White	4
SINGLE POWER AND CCT SMALL WALL PACK WITH PHOTOCELL				
LSWX-20W-30K-PC	20W	2450LM	3000K - Bronze	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL	OPT-EM-LSWX	INTERNAL	OPT-NOPC	REMOVE PHOTOCELL
VANDAL RES.	DESCRIPTION		SENSOR	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw		OPT-SEN-SLPIR	EXTERNAL, SECURITY LIGHT TYPE
POWDER COATING			OPT-SEN-NLS-LSWX	WG NETWORK SENSOR
N/A			OPT-SEN-KEILTON-LSWX	KEILTON NETWORK SENSOR

WMDL-15-25W-MCTP5-D-P-WH

WMDL-15-25W-MCTP5-D-P

WMDL-15-25W-MCTP5-D-P-BK

14” DUAL-LENS VANDAL-PROOF WALL LIGHT - W/ PHOTOCELL - 120-277V

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
WMDL-15-25W-MCTP5-D-P-WH	15W/20W/25W	110LM/W	27K/30K/35K/40K/50K - White	6
WMDL-15-25W-MCTP5-D-P-BK	15W/20W/25W	110LM/W	27K/30K/35K/40K/50K - Black	6
WMDL-15-25W-MCTP5-D-P	15W/20W/25W	110LM/W	27K/30K/35K/40K/50K - Bronze	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
WMDL	OPT-EM-WMDL	INTERNAL	OPT-PC-B	BUTTON
	VANDAL RES.	DESCRIPTION	SENSOR	DESCRIPTION
	OPT-TRS-T20	Tamper Resistant Screw	OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE BI-LEVEL
	POWDER COATING		OPT-SEN-NLS-WMDL	WG NETWORK SENSOR
	OPT-CLR-70(BK/GR/SR/WH)		OPT-SEN-KEILTON-WMDL	KEILTON NETWORK SENSOR
	OPT-CLR-MC (390 SET UP FEE PER PROJECT)		WEC-8RC	REMOTE CONTROL

WMV-20W-30K/40K/50K

LED VERSATILE WALL OR CEILING LIGHT **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
WMV-20W-50K	20W	2000LM	5000K	6
WMV-20W-40K	20W	1900LM	4000K	6
WMV-20W-30K	20W	1800LM	3000K	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL	OPT-EM-WMV	INTERNAL	OPT-PC-B	BUTTON
VANDAL RES.	DESCRIPTION		SENSOR	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw		OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE BI-LEVEL
	POWDER COATING		OPT-SEN-NLS-WMV	WG NETWORK SENSOR
	OPT-CLR-70(BK/GR/SR/WH)		OPT-SEN-KEILTON-WMV	KEILTON NETWORK SENSOR
	OPT-CLR-MC (390 SET UP FEE PER PROJECT)		WEC-8RC	REMOTE CONTROL

LESW-WH

LESW-EM

LESW-EM-WH

8.5" MODERN LED SMALL WALL PACK WITH PHOTOCELL 120~277V DARK BRONZE & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
SINGLE POWER & CCT LED SMALL NON-CUTOFF WALL PACK WITH PHOTOCELL				
LESW-15W-30K-P	15W	1675LM	3000K - Bronze	10
LESW-15W-50K-P	15W	1875LM	5000K - Bronze	10
LESW-20W-30K-P	20W	2300LM	3000K - Bronze	10
LESW-20W-50K-P	20W	2500LM	5000K - Bronze	10
LESW-15W-30K-P-WH	15W	1675LM	3000K - White	10
LESW-15W-50K-P-WH	15W	1875LM	5000K - White	10
LESW-20W-30K-P-WH	20W	2300LM	3000K - White	10
LESW-20W-50K-P-WH	20W	2500LM	5000K - White	10
MCTP **POWER & CCT - ADJUSTABLE LED SMALL NON-CUTOFF WALL PACK WITH PHOTOCELL**				
LESW-8-15W-MCTP-P	8W/12W/15W	135LM/W	30K/40K/50K - Bronze	
LESW-8-15W-MCTP-P-WH	8W/12W/15W	135LM/W	30K/40K/50K - White	
LESW-15-30W-MCTP-P	15W/20W/30W	135LM/W	3000K/4000K/5000K - Bronze	10
LESW-15-30W-MCTP-P-WH	15W/20W/30W	135LM/W	3000K/4000K/5000K - White	10

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	SENSOR	DESCRIPTION
ALL	OPT-EM-LESW	INTERNAL	OPT-SEN-3MRLV-6	PROGRAMMABLE MICROWAVE BI-LEVEL
VANDAL RES.	DESCRIPTION		OPT-SEN-NLS-LESW	WG NETWORK SENSOR
OPT-TRS-T20	Tamper Resistant Screw		OPT-SEN-KEILTON-LESW	KEILTON NETWORK SENSOR
POWDER COATING			WEC-3RC	REMOTE CONTROL
N/A				

BKH

BKH-BR

BKH-WH

BKH-EM

TRADITIONAL BULKHEAD WITH PHOTOCELL POWER & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
BKH-10W-MCTP-BK-P	6W/8W/10W	85LM/W	30K/40K/50K - Black, 2.45" X 8.29" X 4.80"	8
BKH-10W-MCTP-BR-P	6W/8W/10W	85LM/W	30K/40K/50K - Bronze, 2.45" X 8.29" X 4.80"	8
BKH-10W-MCTP-WH-P	6W/8W/10W	85LM/W	30K/40K/50K - White, 2.45" X 8.29" X 4.80"	8
BKH-20W-MCTP-BK-P	12W/18W/20W	85LM/W	30K/40K/50K - Black, 3.24" X 9.64" X 5.83"	6
BKH-20W-MCTP-BR-P	12W/18W/20W	85LM/W	30K/40K/50K - Bronze, 3.24" X 9.64" X 5.83"	6
BKH-20W-MCTP-WH-P	12W/18W/20W	85LM/W	30K/40K/50K - White, 3.24" X 9.64" X 5.83"	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
20W	OPT-EM-BKH	INTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

BKR-36W-MCTP-60W-P-BK

BKR-36W-MCTP-60W-P-BR

BKR-36W-MCTP-60W-P-WH

Shown with TRIM1

Shown with TRIM2

Shown with TRIM3

14" ROUND FLAT BULKHEAD WITH PHOTOCELL POWER & CCT SELECTABLE

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
BKR-36W-MCTP-60W-P-BR	36W/48W/60W	106LM/W	30K/40K/50K - Bronze	3
BKR-36W-MCTP-60W-P-BK	36W/48W/60W	106LM/W	30K/40K/50K - Black	3
BKR-36W-MCTP-60W-P-WH	36W/48W/60W	106LM/W	30K/40K/50K - White	3
BKR-36W-TRIM1-60W-BR	BKR 14in Field-Replaced Trim - Cross - Bronze			
BKR-36W-TRIM1-60W-BK	BKR 14in Field-Replaced Trim - Cross - Black			
BKR-36W-TRIM1-60W-WH	BKR 14in Field-Replaced Trim - Cross - White			
BKR-36W-TRIM2-60W-BR	BKR 14in Field-Replaced Trim - Eyelid - Bronze			
BKR-36W-TRIM2-60W-BK	BKR 14in Field-Replaced Trim - Eyelid - Black			
BKR-36W-TRIM2-60W-WH	BKR 14in Field-Replaced Trim - Eyelid - White			
BKR-36W-TRIM3-60W-BR	BKR 14in Field-Replaced Trim - Cage - Bronze			
BKR-36W-TRIM3-60W-BK	BKR 14in Field-Replaced Trim - Cage - Black			
BKR-36W-TRIM3-60W-WH	BKR 14in Field-Replaced Trim - Cage - White			

BKRN-15W-MCTP-BK-P

BKRN-15W-MCTP-BR-P

BKRN-15W-MCTP-WH-P

BKRD-15W-MCTP-BK-P


BKRD-15W-MCTP-BR-P

BKRD-15W-MCTP-WH-P

BKRF-15W-MCTP-BK-P


BKRF-15W-MCTP-BR-P

BKRF-15W-MCTP-WH-P

ROUND BULKHEAD WITH PHOTOCELL POWER & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
BKRD-15W-MCTP-BK-P	9W/12W/15W	85LM/W	30K/40K/50K - Black	8
BKRD-15W-MCTP-BR-P	9W/12W/15W	85LM/W	30K/40K/50K - Bronze	8
BKRD-15W-MCTP-WH-P	9W/12W/15W	85LM/W	30K/40K/50K - Whtie	8
BKRF-15W-MCTP-BK-P	9W/12W/15W	85LM/W	30K/40K/50K - Black	8
BKRF-15W-MCTP-BR-P	9W/12W/15W	85LM/W	30K/40K/50K - Bronze	8
BKRF-15W-MCTP-WH-P	9W/12W/15W	85LM/W	30K/40K/50K - Whtie	8
BKRN-15W-MCTP-BK-P	9W/12W/15W	85LM/W	30K/40K/50K - Black	8
BKRN-15W-MCTP-BR-P	9W/12W/15W	85LM/W	30K/40K/50K - Bronze	8
BKRN-15W-MCTP-WH-P	9W/12W/15W	85LM/W	30K/40K/50K - Whtie	8

DLW-15W-MCT-BK

DLW-15W-MCT-BR

DLW-15W-MCT-WH

MODERN WALL PACK, 3CCT WITH PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
DLW-15W-MCT-BK	15W	120LM/W	35K/40K/50K - Black	10
DLW-15W-MCT-BR	15W	120LM/W	35K/40K/50K - Bronze	10
DLW-15W-MCT-WH	15W	120LM/W	35K/40K/50K - White	10

FOR EM OPTION SEE PAGE 550

WPV-12W-MCT-DT

VANDAL-PROOF OUTDOOR WALL LIGHT, 3CCT

CATALOG NO.	DESCRIPTION			PCK QTY
WPV-12W-MCT-DT	12W	80LM/W	30K/40K/50K	6

WMS-R | WMS-R-WH | WMS-S | WMS-S-WH | WMS-R-With-EM | WMS-S-With-EM

LED WALL/STEP LIGHT **120~277V** 5”X5” DARK BRONZE & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
WMS-S-50K-BR	6W	660LM	5000K - Bronze	24
WMS-S-30K-BR	6W	630LM	3000K - Bronze	24
WMS-R-50K-BR	6W	660LM	5000K - Bronze	24
WMS-R-30K-BR	6W	630LM	3000K - Bronze	24
WMS-S-50K-WH	6W	660LM	5000K - White	24
WMS-S-30K-WH	6W	630LM	3000K - White	24
WMS-R-50K-WH	6W	660LM	5000K - White	24
WMS-R-30K-WH	6W	630LM	3000K - White	24

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR BOLLARD SETTINGS SEE PAGE 133

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL	**OPT-EM-WMS**	EXTERNAL BACK BOX	**N/A**	N/A
	OPT-EM-WMS-WH	EXTERNAL BACK BOX	**SENSOR**	DESCRIPTION
POST ALL MODELS	**OPT-EM-WMS-POST**	POST MOUNT	**OPT-SEN-LMW**	PROGRAMMABLE MICROWAVE BI-LEVEL (ONLY 2" & 3")
	POWDER COATING		**OPT-SEN-NLS-LMW**	WG NETWORK SENSOR
	OPT-CLR-65(BK/GR/SR/WH)		**OPT-SEN-KEILTON-LMW**	KEILTON NETWORK SENSOR
			OPT-SEN-LMW-WH	PROGRAMMABLE MICROWAVE BI-LEVEL, WHITE (ONLY 2"&3")

AREA LIGHTS

SENSOR-READY PLUG & PLAY

WEC-3RC

WEC-3PR-78-AJ-WH
WEC-3PBT-78-AJ-WH

LAX-LG-90-150W-MCTPD-PSR

LAX-XL-180-300W-MCTPD-PSR

Shown with Shield

LAX-LG-90-150W-MCTPD-PSR-BK

LAX-XL-180-300W-MCTPD-PSR-BK

LAX-PRA

DYNAMIC BEAM-ADJ AREA LIGHT 4-TYPES 7-PIN NEMA SOCKET, SENSOR-READY WESTGATE SIGNATURE - T2, T3, T4, T5 DISTRIBUTIONS

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
LAX-LG-90-150W-MCTPD-PSR	90W/120W/150W	170LM/W	30K/40K/50K - Bronze	1
LAX-LG-90-150W-MCTPD-PSR-BK	90W/120W/150W	170LM/W	30K/40K/50K - Black	1
LAX-LG-90-150W-MCTPD-PSR-480V	90W/120W/150W	170LM/W	30K/40K/50K - Bronze	1
LAX-XL-180-300W-MCTPD-PSR	180W/240W/300W	170LM/W	30K/40K/50K - Bronze	1
LAX-XL-180-300W-MCTPD-PSR-BK	180W/240W/300W	170LM/W	30K/40K/50K - Black	1
LAX-XL-180-300W-MCTPD-PSR-480V	180W/240W/300W	170LM/W	30K/40K/50K - Bronze	1
LAX-XL-240-400W-50K-PDPSR-480V	240W/320W/400W	170LM/W	5000K	1
LAX-SH1	LAX LG Glare Shield			
LAX-SH2	LAX XL Glare Shield			
LAX-SH1-BK	LAX LG Glare Shield Black			
LAX-SH2-BK	LAX XL Glare Shield Black			
LAX-RPA	LAX Series Round-Pole Adapter			

SENSOR-READY PLUG & PLAY

PC-TWIST
PC-TWIST-480V

WEC-3RC

WEC-3PR-78-AJ-WH
WEC-3PBT-78-AJ-WH

LFXMAX-BR

LFXMAX-BK

Field Changeable Lens



Shown with Half Shroud

LFXMAX SPEC SIGNATURE MAXIMUM-FEATURE AREA LIGHT, SENSOR & PHOTOCELL READY, ROTATABLE LENS - TYPE 3 STANDARD

CATALOG NO.	DESCRIPTION			PCK QTY
LFXMAX SPEC SIGNATURE MAXIMUM-FEATURE AREA LIGHT, WATTAGE & CCT SELECTABLE				
LFXMAX-LG-70-150W-MCTP-PSR	70W/100W/150W	145LM/W	30K/40K/50K	1
LFXMAX-XL-200-300W-MCTP-PSR	200W/250W/300W	145LM/W	30K/40K/50K	1
LFXMAX-XXL-250-450W-MCTP-PSR	250W/350W/450W	145LM/W	30K/40K/50K	1
LFXMAX-LG-70-150W-MCTP-PSR-480V	70W/100W/150W	145LM/W	30K/40K/50K	1
LFXMAX-XL-200-300W-MCTP-PSR-480V	200W/250W/300W	145LM/W	30K/40K/50K	1
LFXMAX-XXL-250-450W-MCTP-480V	250W/350W/450W	145LM/W	30K/40K/50K	1
LFXMAX SPEC SIGNATURE MAXIMUM-FEATURE AREA LIGHT, WATTAGE & CCT & BEAM ANGLE SELECTABLE				
LFXMAX-LG-70-150W-MCTPB-PSR	70W/100W/150W	145LM/W	30K/40K/50K	1
LFXMAX-XL-200-300W-MCTPB-PSR	200W/250W/300W	145LM/W	30K/40K/50K	1
LFXMAX-TR-A	LFXMAX-LG TR U-Shaped Mounting Bracket			
LFXMAX-LG-SHROUD-H	LFXMAX-LG Half Shroud			
LFXMAX-XL-SHROUD-H	LFXMAX-XL Half Shroud			
LFXMAX-LG-LENS-T1S	LFXMAX-LG Type T1S Lens			
LFXMAX-LG-LENS-T2M	LFXMAX-LG Type T2M Lens			
LFXMAX-LG-LENS-T4M	LFXMAX-LG Type T4M Lens			
LFXMAX-LG-LENS-T5M	LFXMAX-LG Type T5M Lens			
LFXMAX-LG-LENS-TFTM	LFXMAX-LG Type TFTM Lens			
LFXMAX-LG-LENS-AFR	LFXMAX-LG Type AFR Lens			
LFXMAX-LG-LENS-T5W	LFXMAX-LG Type T5W Lens			

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION
LFXMAX-XL-LENS-T1S	LFXMAX-XL Type T1S Lens
LFXMAX-XL-LENS-T2M	LFXMAX-XL Type T2M Lens
LFXMAX-XL-LENS-T4M	LFXMAX-XL Type T4M Lens
LFXMAX-XL-LENS-T5M	LFXMAX-XL Type T5M Lens
LFXMAX-XL-LENS-TFTM	LFXMAX-XL Type TFTM Lens
LFXMAX-XL-LENS-AFR	LFXMAX-XL Type AFR Lens
LFXMAX-XL-LENS-T5W	LFXMAX-XL Type T5W Lens
LFXMAX-XXL-LENS-T4	LFXMAX-XXL Type T4 Lens
LFXMAX-XXL-LENS-T5	LFXMAX-XXL Type T5 Lens
PC-TWIST	Twist Lock Photocell 1800W Tungeston 120-277V Ac /1800W
PC-TWIST-480V	Twist Lock Photocell 1800W Tungeston 490V
WEC-3PR-78-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level & RC (Optional RC WEC-3RC)
WEC-3PBT-78-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level Bluetooth App Ready

FOR COLD-WEATHER EM OPTION SEE PAGE 527

FOR MOUNTING OPTIONS SEE PAGE 37

FOR OPT OPTION SEE PAGE 34

LFXMAX-FLEX-70-150W

LFXMAX-FLEX-70-150W-BK



LFXMAX-FLEX-200-300W

LFXMAX-FLEX-200-300W-BK

CONTRACTOR PACK AREA LIGHT FLEXIBLE CCT/WATTS/BEAM/SENSORS/MOUNTING WITH REMOTE CONTROL

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
LFXMAX-FLEX-70-150W	70-150W	150LM/W	30K/40K/50K - Bronze	1
LFXMAX-FLEX-200-300W	200-300W	150LM/W	30K/40K/50K - Bronze	1
LFXMAX-FLEX-70-150W-BK	70-150W	150LM/W	30K/40K/50K - Black	1
LFXMAX-FLEX-200-300W-BK	200-300W	150LM/W	30K/40K/50K - Black	1

c UL us LISTED | DLC LISTED PREMIUM | DIMMING 0-10V | WET LOCATIONS | EM CAPABLE | SENSOR OPTION

SENSOR-READY PLUG & PLAY

PC-TWIST
PC-TWIST-480V

WEC-3RC

WEC-3PR-78-AJ-WH
WEC-3PBT-78-AJ-WH

LFX-XXL

LFX-XL

LFX-LG

SPEC SERIES AREA LIGHT, PHOTOCELL READY, TYPE 3 LENS POWER-ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
MP SPEC SERIES POWER-ADJUSTABLE FLOOD/AREA LIGHT, PHOTOCELL READY, 120~277V				
LFX-LG-50-150W-30K-SC	50W/80W/100W/150W	140LM/W	3000K	1
LFX-LG-50-150W-40K-SC	50W/80W/100W/150W	140LM/W	4000K	1
LFX-LG-50-150W-50K-SC	50W/80W/100W/150W	140LM/W	5000K	1
LFX-XL-150-300W-30K-SC	150W/200W/240W/300W	145LM/W	3000K	1
LFX-XL-150-300W-40K-SC	150W/200W/240W/300W	145LM/W	4000K	1
LFX-XL-150-300W-50K-SC	150W/200W/240W/300W	145LM/W	5000K	1
LFX-XXL-400-600W-50K-SC	400W/500W/600W	160LM/W	5000K	1
SPEC SERIES POWER-ADJUSTABLE FLOOD/AREA LIGHT, PHOTOCELL READY, 480V				
MCTP LFX-LG-80-150W-MCTP-480V-SC	80W/100W/150W	145LM/W	30K/40K/50K	1
MCTP LFX-XL-200-300W-MCTP-480V-SC	200W/240W/300W	145LM/W	30K/40K/50K	1
MP LFX-XXL-400-600W-50K-SC-480V	400W/500W/600W	160LM/W	5000K	1
SPEC SERIES POWER-ADJUSTABLE FLOOD/AREA LIGHT, SENSOR READY, 120-277V				
LFX-LG-80-150W-MCTP-PSR	80W/100W/150W	150LM/W	30K/40K/50K - Black	1
LFX-LG-80-150W-MCTP-PSR-BK	80W/100W/150W	150LM/W	30K/40K/50K - Black	1
LFX-XL-200-300W-MCTP-PSR	200W/240W/300W	155LM/W	30K/40K/50K - Black	1
LFX-XL-200-300W-MCTP-PSR-BK	200W/240W/300W	155LM/W	30K/40K/50K - Black	1
LFX-LG-80-150W-MCTP-PSR-480V	80W/100W/150W	150LM/W	30K/40K/50K - Black	1
LFX-XL-200-300W-MCTP-PSR-480V	200W/240W/300W	155LM/W	30K/40K/50K - Black	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
LFX-LG	OPT-EM-LFX-LG	EXTERNAL
LFX-XL	OPT-EM-LFX-XL	EXTERNAL BOX

LENS OPTION	DESCRIPTION
OPT-LFX-LG-TYPEIV	TYPE IV
OPT-LFX-XL-TYPEIV	TYPE IV
OPT-LFX-LG-TYPEV	TYPE V
OPT-LFX-XL-TYPEV	TYPE V

POWDER COATING
OPT-CLR-95(BK/GR/SR/WH)
OPT-CLR-MC (390 SET UP FEE PER PROJECT)

PHOTOCELL	DESCRIPTION
OPT-3MPC	ELECTRONIC
OPT-LF3-PCK	TWIST-LOCK
OPT-LF3-PCK-480V	TWIST-LOCK

SENSOR	DESCRIPTION
OPT-SEN-3MR-3	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-LFX	WG NETWORK SENSOR
OPT-SEN-KEILTON-LFX	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

WIRES PULLED OUT	DESCRIPTION
OPT-010WPO	0-10V Dim. Wires Pulled Out

LFXPRO-LG-50-150W-MCTP-BK

LFXPRO-LG-50-150W-MCTP

LFXPRO-LG-50-150W-MCTP-WH

LFXPRO-XL-150-300W-MCTP-BK

LFXPRO-XL-150-300W-MCTP

LFXPRO-XL-150-300W-MCTP-WH

SPEC PLUS AREA LIGHT 120-277V TYPE 3 LENS POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LFXPRO-LG-50-150W-MCTP	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K	1
LFXPRO-LG-50-150W-MCTP-WH	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K	1
LFXPRO-LG-50-150W-MCTP-BK	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K	1
LFXPRO-XL-150-300W-MCTP	150W/200W/240W/300W	125LM/W	30K/40K/50K/57K	1
LFXPRO-XL-150-300W-MCTP-WH	150W/200W/240W/300W	125LM/W	30K/40K/50K/57K	1
LFXPRO-XL-150-300W-MCTP-BK	150W/200W/240W/300W	125LM/W	30K/40K/50K/57K	1

FOR COLD-WEATHER EM OPTION SEE PAGE 527

FOR MOUNTING OPTIONS SEE PAGE 37 (LFX MOUNTING OPTIONS COMPATIBLE WITH LFXE-LG & LFXE-XL, LFXPRO, LFX, LF4PRO, LFXMAX, LF4MAX)

FOR OPT OPTION SEE PAGE 34

LFX-LG-50-150W

LFX-XL-150-300W

LFX-XXL-300-600W

WHILE SUPPLIES LAST

SPEC SERIES AREA LIGHT TYPE 3 LENS POWER-ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
SPEC SERIES POWER-ADJUSTABLE FLOOD/AREA LIGHT, 120~277V				
LFX-LG-50-150W-30K	50W/80W/100W/150W	140LM/W	3000K	1
LFX-LG-50-150W-40K	50W/80W/100W/150W	140LM/W	4000K	1
LFX-XL-150-300W-30K	150W/200W/240W/300W	145LM/W	3000K	1
LFX-XL-150-300W-40K	150W/200W/240W/300W	145LM/W	4000K	1
LFX-XXL-300-600W-50K	300W/400W/500W/600W	140LM/W	5000K	1
SPEC SERIES POWER-ADJUSTABLE FLOOD/AREA LIGHT, 480V				
LFX-XXL-300-600W-50K-480V	300W/400W/500W/600W	140LM/W	5000K	1

FOR COLD-WEATHER EM OPTION SEE PAGE 527

FOR MOUNTING OPTIONS SEE PAGE 37 (LFX MOUNTING OPTIONS COMPATIBLE WITH LFXE-LG & LFXE-XL, LFXPRO, LFX, LF4PRO, LFXMAX, LF4MAX)

FOR OPT OPTION SEE PAGE 34

LFXE-LG



LFXE-XL

LFXE-MD-KN

LFXE-MD-KN-BK

LFXE-MD-KN-WH

LFXE-MD-TR

Can be used as BILBOARDSIGN LIGHT
Shown with ACC-WMA-30-BR

BUILDER SERIES FLOOD/AREA LIGHT, WITH PHOTOCELL, TYPE 3 LENS PHOTOCELL DISCONNECT SWITCH

CATALOG NO.	DESCRIPTION			PCK QTY
POWER & CCT ADJUSTABLE BUILDER SERIES FLOOD/AREA LIGHTS WITH PHOTOCELL				
LFXE-MD-50-100W-MCTP-KN-P	50W/80W/100W	135LM/W	30K/40K/50K - Dark Bronze	4
LFXE-MD-50-100W-MCTP-KN-P-BK	50W/80W/100W	135LM/W	30K/40K/50K - Black	4
LFXE-MD-50-100W-MCTP-KN-P-WH	50W/80W/100W	135LM/W	30K/40K/50K - White	4
LFXE-MD-50-100W-MCTP-TR-P	50W/80W/100W	135LM/W	30K/40K/50K - Dark Bronze	4
POWER & 3CCT ADJUSTABLE BUILDER SERIES FLOOD/AREA LIGHTS WITH PHOTOCELL (COMPATIBLE WITH LFX MOUNTING OPTIONS)				
MP LFXE-LG-80-150W-50K-P	80W/100W/150W	135LM/W	5000K - Dark Bronze	1
MCTP LFXE-LG-80-150W-MCTP-P	80W/100W/150W	135LM/W	30K/40K/50K - Dark Bronze	1
POWER & 3CCT ADJUSTABLE BUILDER SERIES FLOOD/AREA LIGHTS WITH PHOTOCELL (COMPATIBLE WITH LFX MOUNTING OPTIONS)				
MP LFXE-XL-200-300W-50K-P	200W/240W/300W	135LM/W	5000K - Dark Bronze	1
MCTP LFXE-XL-200-300W-MCTP-P	200W/240W/300W	135LM/W	30K/40K/50K - Dark Bronze	1

FOR COLD-WEATHER EM OPTION SEE PAGE 527

FOR MOUNTING OPTIONS SEE PAGE 37 (LFX MOUNTING OPTIONS COMPATIBLE WITH LFXE-LG & LFXE-XL, LFXPRO, LFX, LF4PRO, LFXMAX, LF4MAX)

LFX-EXT

LFX-ASA



LFX-AWB

LFX-YK

LFX-TR-A

LFX-TR-B

LFX-PASF

Microwave Photocell

MOUNTING OPTIONS FOR LFX, LFXPRO, LF4PRO, LFXE, LFXMAX SERIES

CATALOG NO.	DESCRIPTION
LFX-SF	Slip Fitter for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, Bronze
LFX-SF-WH	Slip Fitter for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, White
LFX-SF-BK	Slip Fitter for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, Black
LFX-EXT	Straight Arm for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, Bronze
LFX-EXT-WH	Straight Arm for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, White
LFX-EXT-BK	Straight Arm for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, Black
LFX-ASA	Adjustable Straight Arm for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, Bronze
LFX-ASA-WH	Adjustable Straight Arm for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, White
LFX-ASA-BK	Adjustable Straight Arm for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, Black
LFX-AWB	Adjustable Wall Junction Box for LFX & LFX-XXL & LFXMAX & LFXPRO & LF4PRO & LFXE Series, Bronze
LFX-AWB-WH	Adjustable Wall Junction Box for LFX & LFX-XXL & LFXMAX & LFXPRO & LF4PRO & LFXE Series, White
LFX-AWB-BK	Adjustable Wall Junction Box for LFX & LFX-XXL & LFXMAX & LFXPRO & LF4PRO & LFXE Series, Black
LFX-YK	Yoke for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, Bronze
LFX-YK-WH	Yoke for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, White
LFX-YK-BK	Yoke for LFX & LFX-XXL & LFXPRO & LFXMAX & LF4PRO & LFXE Series, Black
LFX-TR-A	U Bracket for LFX & LFXPRO “LG“ & LF4PRO & LFXE Series, Bronze
LFX-TR-A-WH	U Bracket for LFX & LFXPRO “LG“ & LF4PRO & LFXE Series, White
LFX-TR-A-BK	U Bracket for LFX & LFXPRO “LG“ & LF4PRO & LFXE Series, Black
LFX-TR-B	U Bracket for LFX “XL“ & LFX-XXL & LFXPRO “XL“ & LFXE Series, Bronze
LFX-TR-B-WH	U Bracket for LFX “XL“ & LFX-XXL & LFXPRO “XL“ & LFXE Series, White
LFX-TR-B-BK	U Bracket for LFX “XL“ & LFX-XXL & LFXPRO “XL“ & LFXE Series, Black
LFX-PASF	Pole Adapter for Slip Fitter for LFX & LFX-XXL & LFXMAX & LFXPRO & LF4PRO & LFXE Series, Bronze
LFX-PASF-WH	Pole Adapter for Slip Fitter for LFX & LFX-XXL & LFXMAX & LFXPRO & LF4PRO & LFXE Series, White
LFX-PASF-BK	Pole Adapter for Slip Fitter for LFX & LFX-XXL & LFXMAX & LFXPRO & LF4PRO & LFXE Series, Black

OPT-3MPC
MICROWAVE PHOTOCELL

OPT-LF3-PCK
OPT-LF3-PCK-480V
TWIST-LOCK PHOTOCELL KIT

PHOTOCELL FOR LFX SERIES

CATALOG NO.	DESCRIPTION
OPT-3MPC	
OPT-LF3-PCK	
OPT-LF3-PCK-480V	



OPT-3MPC
COMPATIBLE WITH EXT, ASA, SF MOUNTING

PHOTOCELL FOR LFXE SERIES

CATALOG NO.	DESCRIPTION
OPT-3MPC	

OPT-TLSOC7P
SMART CONTROL RECEIVER SOCKET

7-PIN SOCKET FOR SMART CONTROL RECEIVERS

CATALOG NO.	DESCRIPTION
OPT-TLSOC7P	

LF-SHROUD-A

LF-SHROUD-B



LF-SHROUD-D



LF-SHROUD-E

LF-SHROUD-F

LF-SHROUD-G

LFX-WG-A
LFX-WG-B
LFXPRO-WG-A
LFXPRO-WG-B

SHROUD & WIRE GUARD FOR LFX, LFX PRO, LF4 PRO SERIES

CATALOG NO.	DESCRIPTION
LF-SHROUD-A	Half Shroud for LFX & LFXPRO "LG" & LF4PRO Series, Reversible (Back or Front)
LF-SHROUD-B	Half Shroud for LFX & LFXPRO "XL" Series, Reversible (Back or Front)
LF-SHROUD-F	Half Shroud for LFX "XXL" Series
LF-SHROUD-D	Full Shroud for LFX & LFXPRO "LG" & LF4PRO Series
LF-SHROUD-E	Full Shroud for LFX & LFXPRO "XL" Series
LF-SHROUD-G	Full Shroud for LFX "XXL" Series
LFX-WG-A	Wire Guard for LFX "LG" Series
LFX-WG-B	Wire Guard for LFX "XL" Series
LFXPRO-WG-A	Wire Guard for LFXPRO "LG" Series
LFXPRO-WG-B	Wire Guard for LFXPRO "XL" Series

GPX-18-60W-MCTP-CM

GPX-CM
Back Side

SPEC SERIES AREA/FLOOD LIGHT **120~277V**, TYPE 5 LENS (TYPE 2 & TYPE 3 LENS ALSO AVAILABLE) MADE TO ORDER POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GPX-18-60W-MCTP-CM	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-22-75W-MCTP-CM	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1
GPX-90-150W-MCTP-CM	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL	OPT-EM-GPX	INTERNAL	OPT-3MPC	ELECTRONIC
	LENS OPTION	DESCRIPTION	SENSOR	DESCRIPTION
	OPT-GPX-LENS-TYPE2S	TYPE 2S	OPT-SEN-3MR-3	BI-LEVEL MICROWAVE
	OPT-GPX-LENS-TYPE3S	TYPE3S	OPT-SEN-NLS-GPX	WG NETWORK SENSOR
	OPT-GPX-150W-LENS-TYPE3S	TYPE3S	OPT-SEN-KEILTON-GPX	KEILTON NETWORK SENSOR
	OPT-GPX-LENS-FL	FROSTED GLASS LENS	WEC-8RC	REMOTE CONTROL
	OPT-GPX-LENS-TYPE4	TYPE4		
	POWDER COATING		480V OPTION	DESCRIPTION
	OPT-CLR-95(BK/GR/SR/WH)		OPT-WP-480V	CHANGE VOLTAGE

LRXB-40W-50K-P

RESIDENTIAL BARN LIGHT W/ PHOTOCELL, **120V**, 5000K

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
LRXB-40W-50K-P	40W	5000LM	5000K	10

LRX-36-60W-MCTP-P

LRX-72-120W-MCTP-TL

SHOWN WITH ARM INCLUDED

BUILDER SERIES DUSK-TO-DAWN BARN/AREA LIGHT **120-277V** (PHOTOCELL & ARM INCLUDED) POWER & COLOR-TEMPERATURE SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LRX-36-60W-MCTP-P	36W/42W/60W	130LM/W	3000K/4000K/5000K	4
LRX-72-120W-MCTP-TL	72W/96W/120W	130LM/W	3000K/4000K/5000K	4

LRX-20-50W-MCTP

LR-ECO-ARM

SPEC SERIES POWER & CCT DUSK-TO-DAWN BARN/AREA LIGHT **120-277V** NEMA PHOTOCELL & ARM INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
LRX-20-50W-MCTP	20W/30W/40W/50W	130LM/W	30K/40K/50K/57K	2
LRX-50-120W-MCTP	50W/80W/100W/120W	130LM/W	30K/40K/50K/57K	1

HML-BK
Shown With Shroud

HIGH-LUMEN HIGH-MAST ROADWAY LIGHT, 90 DAYS LEAD TIME

CATALOG NO.	DESCRIPTION
HML-60-200W-XXK-CLR	High-Mast 60W To 200W, 120-277V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-90-300W-XXK-CLR	High-Mast 90W To 300W, 120-277V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-135-450W-XXK-CLR	High-Mast 135W To 450W, 120-277V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-150-500W-XXK-CLR	High-Mast 150W To 500W, 120-277V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-180-600W-XXK-CLR	High-Mast 180W To 600W, 120-277V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-225-750W-XXK-CLR	High-Mast 225W To 750W, 120-277V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-60-200W-XXK-CLR-480V	High-Mast 60W To 200W, 277-480V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-90-300W-XXK-CLR-480V	High-Mast 90W To 300W, 277-480V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-135-450W-XXK-CLR-480V	High-Mast 135W To 450W, 277-480V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-150-500W-XXK-CLR-480V	High-Mast 150W To 500W, 277-480V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-180-600W-XXK-CLR-480V	High-Mast 180W To 600W, 277-480V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-225-750W-XXK-CLR-480V	High-Mast 225W To 750W, 277-480V, Specify 3 Watt Stops, Specify CCT, Specify Bk Or Gy
HML-SH1-CLR	HML High-Mast Glare Shield For Up To 750W Version, Specify Bk Or Gy
HML-SCK	HML High-Mast NEMA Socket And Shorting Cap Pre-Installed

c UL us LISTED

WET LOCATIONS

SFP-240W-50K

Shown with SFP-SF

SFP-320W-50K

PICKLEBALL COURT LIGHT

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
SFP-240W-50K	240W	41594LM		5000K	1
SFP-320W-50K	320W	57135LM		5000K	1
SFP-SF	SFP Series Slip-Fitter Pole Adapter				

FLOOD LIGHTS

LF4MAX-LG Bronze

LF4MAX-LG Black

LF4MAX-LG White

LF4MAX
Shown with Slip Fitter

LF4MAX-XL Bronze

LF4MAX-XL Black

LF4MAX-XL White

LF4MAX SPEC SIGNATURE MAXIMUM-FEATURE ROUND-BACK FLOOD LIGHT FULL CONTROL OF BEAM ANGLE, CCT, WATTS, PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
SPEC SIGNATURE MAXIMUM-FEATURE ROUND-BACK FLOOD LIGHT 120-277V				
LF4MAX-LG-75-150W-MCTPB-P	75W/100W/150W	140LM/W	30K/40K/50K - Bronze	1
LF4MAX-LG-75-150W-MCTPB-P-BK	75W/100W/150W	140LM/W	30K/40K/50K - Black	1
LF4MAX-LG-75-150W-MCTPB-P-WH	75W/100W/150W	140LM/W	30K/40K/50K - White	1
LF4MAX-XL-200-300W-MCTPB-P	200W/240W/300W	140LM/W	30K/40K/50K - Bronze	1
LF4MAX-XL-200-300W-MCTPB-P-BK	200W/240W/300W	140LM/W	30K/40K/50K - Black	1
LF4MAX-XL-200-300W-MCTPB-P-WH	200W/240W/300W	140LM/W	30K/40K/50K - White	1
SPEC SIGNATURE MAXIMUM-FEATURE ROUND-BACK FLOOD LIGHT 480V				
LF4MAX-LG-150W-MCTPB-P-480V	75W/100W/150W	140LM/W	30K/40K/50K - White	1
LF4MAX-XL-300W-MCTPB-P-480V	200W/240W/300W	140LM/W	30K/40K/50K - White	1

FOR COLD-WEATHER EM OPTION SEE PAGE 527

FOR MOUNTING OPTIONS SEE PAGE 37 (LFX MOUNTING OPTIONS COMPATIBLE WITH LFXE-LG & LFXE-XL, LFXPRO, LFX, LF4PRO, LFXMAX, LF4MAX)

FOR OPT OPTION SEE PAGE 34



LF4PRO-50-150W-MCTP



Shown with LFX-SF Slip Fitter

SPEC SERIES ARCHITECTURAL ROUND-BACK FLOOD LIGHT 120-277V

POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LF4PRO-50-150W-MCTP	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K	1

FOR COLD-WEATHER EM OPTION SEE PAGE 527

FOR MOUNTING OPTIONS SEE PAGE 37 (LFX MOUNTING OPTIONS COMPATIBLE WITH LFXE-LG & LFXE-XL, LFXPRO, LFX, LF4PRO, LFXMAX, LF4MAX)

FOR OPT OPTION SEE PAGE 34

LF4MAX-MD

LF4MAX-LG

LF4MAX SPEC SIGNATURE MAXIMUM-FEATURE ROUND-BACK FLOOD LIGHT WITH U BRACKET FULL CONTROL OF BEAM ANGLE, CCT, WATTS, PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
SPEC SIGNATURE MAXIMUM-FEATURE ROUND-BACK FLOOD LIGHT WITH U BRACKET 120-277V				
LF4MAX-SM-15-35W-MCTPB-TR-P	15W/25W/35W	140LM/W	30K/40K/50K - Bronze	1
LF4MAX-MD-20-50W-MCTPB-TR-P	20W/30W/50W	140LM/W	30K/40K/50K - Bronze	1
LF4MAX-MD-45-80W-MCTPB-TR-P	45W/60W/80W	140LM/W	30K/40K/50K - Bronze	1
LF4MAX-LG-75-150W-MCTPB-TR-P	75W/100W/150W	140LM/W	30K/40K/50K - Bronze	1
LF4MAX-XL-200-300W-MCTPB-TR-P	200W/240W/300W	140LM/W	30K/40K/50K - Bronze	1
SPEC SIGNATURE MAXIMUM-FEATURE ROUND-BACK FLOOD LIGHT WITH U BRACKET 480V				
LF4MAX-LG-150W-MCTPB-TR-P-480V	75W/100W/150W	140LM/W	30K/40K/50K - Bronze	1
LF4MAX-XL-300W-MCTPB-TR-P-480V	200W/240W/300W	140LM/W	30K/40K/50K - Bronze	1

LF4MAX-KN

LF4MAX-KN-BK
Black

LF4MAX-KN-WH
White

Architectural Round-Back Design

LF4MAX SPEC SIGNATURE MAXIMUM-FEATURE ROUND-BACK FLOOD LIGHT WITH KNUCKLE FULL CONTROL OF BEAM ANGLE, CCT, WATTS, PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
LF4MAX-SM-15-35W-MCTPB-KN-P	15W/25W/35W	140LM/W	30K/40K/50K - Bronze	1
LF4MAX-SM-15-35W-MCTPB-KN-P-BK	15W/25W/35W	140LM/W	30K/40K/50K - Black	1
LF4MAX-SM-15-35W-MCTPB-KN-P-WH	15W/25W/35W	140LM/W	30K/40K/50K - White	1
LF4MAX-MD-20-50W-MCTPB-KN-P	20W/30W/50W	140LM/W	30K/40K/50K - Bronze	1
LF4MAX-MD-20-50W-MCTPB-KN-P-BK	20W/30W/50W	140LM/W	30K/40K/50K - Black	1
LF4MAX-MD-20-50W-MCTPB-KN-P-WH	20W/30W/50W	140LM/W	30K/40K/50K - White	1
LF4MAX-MD-45-80W-MCTPB-KN-P	45W/60W/80W	140LM/W	30K/40K/50K - Bronze	1
LF4MAX-MD-45-80W-MCTPB-KN-P-BK	45W/60W/80W	140LM/W	30K/40K/50K - Black	1
LF4MAX-MD-45-80W-MCTPB-KN-P-WH	45W/60W/80W	140LM/W	30K/40K/50K - White	1

LFX-SM-10-30W-KN

LFX-SM-10-30W-KN-WH

LFX-MD-15-50W-KN

LFX-MD-15-50W-KN-WH

SPEC SERIES X-GEN. FLOOD LIGHT 0-10V DIMMING, INCLUDED MULTI POWER & MULTI POWER + 3CCT (WITH KNUCKLE) 120-277V

CATALOG NO.	DESCRIPTION			PCK QTY
MP POWER-ADJUSTABLE SMALL FLOOD LIGHT				
LFX-SM-10-30W-30K-KN	10W/15W/20W/30W	130LM/W	3000K	10
LFX-SM-10-30W-40K-KN	10W/15W/20W/30W	130LM/W	4000K	10
LFX-SM-10-30W-50K-KN	10W/15W/20W/30W	130LM/W	5000K	10
LFX-MD-15-50W-30K-KN	15W/20W/30W/50W	130LM/W	3000K	6
LFX-MD-15-50W-40K-KN	15W/20W/30W/50W	130LM/W	4000K	6
LFX-MD-15-50W-50K-KN	15W/20W/30W/50W	130LM/W	5000K	6
MCTP POWER & CCT-ADJUSTABLE SMALL FLOOD LIGHT				
LFX-SM-10-30W-MCTP-KN	10W/15W/20W/30W	130LM/W	30K/40K/50K/57K	6
LFX-SM-10-30W-MCTP-KN-WH	10W/15W/20W/30W	130LM/W	30K/40K/50K/57K	6
LFX-SM-10-30W-MCTP-KN-BK	10W/15W/20W/30W	130LM/W	30K/40K/50K/57K	6
LFX-SM-10-30W-MCTP-KN-SV	10W/15W/20W/30W	130LM/W	30K/40K/50K/57K	6
LFX-MD-15-50W-MCTP-KN	15W/20W/30W/50W	130LM/W	30K/40K/50K/57K	6
LFX-MD-15-50W-MCTP-KN-WH	15W/20W/30W/50W	130LM/W	30K/40K/50K/57K	6
LFX-MD-15-50W-MCTP-KN-BK	15W/20W/30W/50W	130LM/W	30K/40K/50K/57K	6
LFX-MD-15-50W-MCTP-KN-SV	15W/20W/30W/50W	130LM/W	30K/40K/50K/57K	6
MCTP POWER & CCT-ADJUSTABLE SMALL FLOOD LIGHT WITH PHOTOCELL				
LFX-SM-10-30W-MCTP-KN-P	10W/20W/30W	130LM/W	30K/40K/50K	6
LFX-SM-10-30W-MCTP-KN-WH-P	10W/20W/30W	130LM/W	30K/40K/50K	6
LFX-SM-10-30W-MCTP-KN-BK-P	10W/20W/30W	130LM/W	30K/40K/50K	6
LFX-SM-10-30W-MCTP-KN-SV-P	10W/20W/30W	130LM/W	30K/40K/50K	6
LFX-MD-30-50W-MCTP-KN-P	30W/40W/50W	130LM/W	30K/40K/50K	6
LFX-MD-30-50W-MCTP-KN-WH-P	30W/40W/50W	130LM/W	30K/40K/50K	6
LFX-MD-30-50W-MCTP-KN-BK-P	30W/40W/50W	130LM/W	30K/40K/50K	6
LFX-MD-30-50W-MCTP-KN-SV-P	30W/40W/50W	130LM/W	30K/40K/50K	6

LFX-SM-10-30W-TR

LFX-MD-15-50W-TR

SPEC SERIES X-GEN. FLOOD LIGHT 0-10V DIMMING, INCLUDED MULTI POWER & MULTI POWER + 3CCT (WITH U BRACKET) **120-277V** BUILT-IN PC SWITCH

CATALOG NO.	DESCRIPTION			PCK QTY
MP	**POWER-ADJUSTABLE SMALL FLOOD LIGHT**			
LFX-SM-10-30W-30K-TR	10W/15W/20W/30W	130LM/W	3000K	10
LFX-SM-10-30W-50K-TR	10W/15W/20W/30W	130LM/W	5000K	10
LFX-MD-15-50W-30K-TR	15W/20W/30W/50W	130LM/W	3000K	10
LFX-MD-15-50W-50K-TR	15W/20W/30W/50W	130LM/W	5000K	10
MCTP	**POWER & CCT-ADJUSTABLE SMALL FLOOD LIGHT**			
LFX-SM-10-30W-MCTP-TR	10W/15W/20W/30W	130LM/W	30K/40K/50K/57K	6
LFX-MD-15-50W-MCTP-TR	15W/20W/30W/50W	130LM/W	30K/40K/50K/57K	6
MCTP	**POWER & CCT-ADJUSTABLE SMALL FLOOD LIGHT WITH PHOTOCELL**			
LFX-SM-10-30W-MCTP-TR-P	10W/20W/30W	130LM/W	30K/40K/50K	6
LFX-MD-30-50W-MCTP-TR-P	30W/40W/50W	130LM/W	30K/40K/50K	6

LFX-XS-15W-KN

LFX-XS-15W-WH-KN

SPEC SERIES X-GEN. EXTRA SMALL FLOOD LIGHT 0-10V DIMMING, INCLUDED MULTI POWER & MULTI POWER + 3CCT (WITH KNUCKLE) **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
LFX-XS-15W-30K-KN	15W	1950LM	3000K	18
LFX-XS-15W-40K-KN	15W	1950LM	4000K	18
LFX-XS-15W-50K-KN	15W	1950LM	5000K	18

LFX-XS-15W-TR

SPEC SERIES X-GEN. EXTRA SMALL FLOOD LIGHT 0-10V DIMMING, INCLUDED MULTI POWER & MULTI POWER + 3CCT (WITH KNUCKLE) **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
LFX-XS-15W-30K-TR	15W	1950LM	3000K	18
LFX-XS-15W-40K-TR	15W	1950LM	4000K	18
LFX-XS-15W-50K-TR	15W	1950LM	5000K	18

LF4-30W-KN

LF4-50W-KN

LF4-15W-KN

SPEC SERIES LED ARCHITECTURAL ROUND-BACK FLOOD LIGHTS 0-10V DIMMING **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
LF4-15W-50K-KN	15W	1900LM	5000K	12
LF4-15W-30K-KN	15W	1900LM	3000K	12
LF4-30W-50K-D-KN	30W	4050LM	5000K	6
LF4-30W-30K-D-KN	30W	4050LM	3000K	6
LF4-50W-50K-D-KN	50W	6750LM	5000K	6
LF4-50W-30K-D-KN	50W	6750LM	3000K	6

c UL us LISTED

WET LOCATIONS

LF4-12CW-KN

WHILE SUPPLIES LAST

LED ARCHITECTURAL ROUND-BACK FLOOD LIGHT **120V-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
LF4-12CW-KN	12W	1300LM	5000K	12

LF4 with Half Shroud

LF3-HL with Half Shroud

LF4 with Full-Glare Shroud

LF3-HL with Full-Glare Shroud

OUTDOOR SHROUD

CATALOG NO.	DESCRIPTION
LF4-SH1	Fits LF4-12W & 15W, LF4-12V-6W & 12W (Polycarbonate)
LF4-SH2	Fits LF4-30W, LF4-12V-24W & 30W (Polycarbonate)
LF4-SH3	Fits LF4-50W, LF4-12V-50W (Polycarbonate)
LF4-SH4	Fits LF4-80W & 100W, (Aluminum)
LF4-SH5	Fits LF4-150W (Aluminum)
LF3-SH1	Shroud for LFX-SM* & LF3-30W & LF3-HL-30W, Reversible, Aluminum
LF3-SH2	Shroud for LFX-SM-MCTP & LFX-MD & LF3-50W & LF3-HL-50W, Reversible, Aluminum
LF3-SH1FG	Full-Glare Shroud for LF3-30W & LF3-HL-30W & LF4-12W & LF4-30W, Aluminum
LF3-SH2FG	Full-Glare Shroud for LF3-50W & LF3-HL-50W & LF4-50W, Aluminum
FL-SH1	Fits FLD2-15W, FLV12-6W
FL-SH2	Fits FLD2-28W, FLV12-12W & 24W
FL-SH3	Fits FLD2-42W, FLV12-32W
FL-SH4	Fits FLD2-50W

LFE-15W

LFE-30W

BUILDER SERIES COMPACT FLOOD LIGHT, INCLUDED 3CCT VERSIONS WITH 1/2" KNUCKLE **120V** BUILT-IN PC SWITCH

CATALOG NO.	DESCRIPTION			PCK QTY
LFE-15W-30K-KN	15W	1600LM	3000K	48
LFE-15W-40K-KN	15W	1600LM	4000K	48
LFE-15W-50K-KN	15W	1600LM	5000K	48
3CCT VERSION COMPACT FLOOD LIGHTS				
LFE-30W-MCT-KN	30W	3250LM	30K/40K/50K	24
3CCT VERSION COMPACT FLOOD LIGHTS WITH 1/2" KNUCKLE				
LFE-15W-MCT-KN-P	15W	1600LM	30K/40K/50K	48
LFE-30W-MCT-KN-P	30W	3250LM	30K/40K/50K	24
LFE-50W-MCT-KN-P	50W	5250LM	30K/40K/50K	16


LFE-15W-TR

LFE-30W-TR


LFE-50W-TR

BUILDER SERIES COMPACT FLOOD LIGHT, INCLUDED 3CCT VERSIONS WITH 1/2" KNUCKLE **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
LFE-15W-30K-TR	15W	1600LM	3000K	48
LFE-15W-40K-TR	15W	1600LM	4000K	48
LFE-15W-50K-TR	15W	1600LM	5000K	48
3CCT VERSION COMPACT FLOOD LIGHTS				
LFE-15W-MCT-TR	15W	1600LM	3000K/4000K/5000K	48
LFE-30W-MCT-TR	30W	3250LM	3000K/4000K/5000K	24
LFE-50W-MCT-TR	50W	5250LM	3000K/4000K/5000K	16
3CCT VERSION COMPACT FLOOD LIGHTS WITH 1/2" KNUCKLE				
LFE-15W-MCT-TR-P	15W	1600LM	3000K/4000K/5000K	48
LFE-30W-MCT-TR-P	30W	3250LM	3000K/4000K/5000K	24
LFE-50W-MCT-TR-P	50W	5250LM	3000K/4000K/5000K	16

LFE-80W-MCT-D
LFE-100W-MCT-D

Shown with 12in knuckle mounting option, fits 80w and larger

Shown with bottom bracket mounting option, fits 80w and larger

Shown with Slip fitter mounting option, fits 80w and larger

COMPACT FLOOD LIGHT 3CCT VERSIONS 120~277V MOUNTING OPTIONS SOLD SEPARATELY

CATALOG NO.	DESCRIPTION			PCK QTY
LFE-80W-MCT-D	80W	10500LM	3000K/4000K/5000K	1
LFE-100W-MCT-D	100W	13000LM	3000K/4000K/5000K	1
LFE-KN	LFE 1/2in knuckle mounting option, fits 80w and larger			
LFE-SF	LFE slip fitter mounting option, fits 80w and larger			
LFE-YK	LFE bottom bracket mounting option, fits 80w and larger			

FLDF-BR

FLDF-BK

FLAG-POLE 25° NARROW-BEAM FLOOD LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
FLDF-84W-30K-BR	84W	9000LM	3000K - Bronze	6
FLDF-84W-50K-BR	84W	9000LM	5000K - Bronze	6
FLDF-84W-30K-BK	84W	9000LM	3000K - Black	6
FLDF-84W-50K-BK	84W	9000LM	5000K - Black	6

FLDX-SM-15W-BRFS
Flat Shroud

Shown with optional FLDVX-FS
Flat Shroudmounting option, fits
80w and larger

FLDX-SM-15W-BK

FLDX ACC-WMA-30-BR

FLDX-MD-10-30W-BR
FLDX-LG-10-30W-MCTP-BR

FLDX-MD-10-30W-BK
FLDX-LG-10-30W-MCTP-BK

FLDX-LG-30-50W-MCTP-BR
FLDX-LG-10-30W-MCTP-BR

FLDX-LG-30-50W-MCTP-BK
FLDX-LG-10-30W-MCTP-BK

SPEC SERIES LED X-GEN BULLET FLOOD LIGHT WITH LONG SHROUD **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
SPEC SERIES LED X-GEN BULLET FLOOD LIGHTS WITH LONG SHROUDS				
FLDX-SM-15W-30K-BR	15W	1800LM	3000K - 60°, Bronze	12
FLDX-SM-15W-30K-BK	15W	1800LM	3000K - 60°, Black	12
FLDX-SM-15W-40K-BR	15W	1800LM	4000K - 60°, Bronze	12
FLDX-SM-15W-40K-BK	15W	1800LM	4000K - 60°, Black	12
FLDX-SM-15W-50K-BR	15W	1800LM	5000K - 60°, Bronze	12
FLDX-SM-15W-50K-BK	15W	1800LM	5000K - 60°, Black	12
MP **POWER ADJUSTABLE SPEC SERIES LED X-GEN BULLET FLOOD LIGHTS WITH LONG SHROUDS**				
FLDX-MD-10-30W-30K-BR	10W/20W/30W	120LM/W	3000K - 60°, Bronze	8
FLDX-MD-10-30W-30K-BK	10W/20W/30W	120LM/W	3000K - 60°, Black	8
FLDX-MD-10-30W-40K-BR	10W/20W/30W	120LM/W	4000K - 60°, Bronze	8
FLDX-MD-10-30W-40K-BK	10W/20W/30W	120LM/W	4000K - 60°, Black	8
FLDX-MD-10-30W-50K-BR	10W/20W/30W	120LM/W	5000K - 60°, Bronze	8
FLDX-MD-10-30W-50K-BK	10W/20W/30W	120LM/W	5000K - 60°, Black	8
MCTP **POWER & CCT ADJUSTABLE SPEC SERIES LED X-GEN BULLET FLOOD LIGHTS WITH LONG SHROUDS**				
FLDX-LG-10-30W-MCTP-BR	10W/20W/30W	120LM/W	3000K/4000K/5000K - 60°, Bronze	4
FLDX-LG-10-30W-MCTP-BK	10W/20W/30W	120LM/W	3000K/4000K/5000K - 60°, Black	4
FLDX-LG-30-50W-MCTP-BR	30W/40W/50W	120LM/W	3000K/4000K/5000K - 35°, Bronze	4
FLDX-LG-30-50W-MCTP-BK	30W/40W/50W	120LM/W	3000K/4000K/5000K - 35°, Black	4
FLDVX-FS-SM-BR	Flat Shroud For Sm Size Housing, Bronze			
FLDVX-FS-SM-BK	Flat Shroud For Sm Size Housing, Black			
FLDVX-FS-MD-BR	Flat Shroud For Md Size Housing, Bronze			
FLDVX-FS-MD-BK	Flat Shroud For Md Size Housing, Black			
FLDVX-FS-LG-BR	Flat Shroud For Lg Size Housing, Bronze			
FLDVX-FS-LG-BK	Flat Shroud For Lg Size Housing, Black			
FLDVX-SM-RL35	35-Degree Repl. Lens For Sm Size Housing			
FLDVX-MD-RL35	35-Degree Repl. Lens For Md Size Housing			
FLDVX-LG-RL35	35-Degree Repl. Lens For Lg Size Housing			
FLDVX-LG-RL60	60-Degree Repl. Lens For Lg Size Housing			

FLDX-MD-15W-RGBW-BT-BR

TC-RGBW-RC

SPEC SERIES RGBW BLUETOOTH WESTGATE APP BULLET 120-277V

CATALOG NO.	DESCRIPTION			PCK QTY
FLDX-MD-15W-RGBW-BT-BR	15W	720LM	RGBW - Bronze	4

FOR REMOTE CONTROL SEE PAGE 523

FLDXPRO-BR

FLDXPRO-BK

FLDXPRO-WH

SPEC SERIES POWER LED X-GEN BULLET FLOOD LIGHT WITH INTEGRATED PHOTOCELL 120-277V CCT & BEAM ANGLE- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
FLDXPRO-SM-5-15W-MCTPB-BR	5W/10W/15W	95LM/W	30K/40K/50K - Bronze	4
FLDXPRO-SM-5-15W-MCTPB-BK	5W/10W/15W	95LM/W	30K/40K/50K - Black	4
FLDXPRO-SM-5-15W-MCTPB-WH-P	5W/10W/15W	95LM/W	30K/40K/50K - White	4
FLDXPRO-MD-10-30W-MCTPB-BR	10W/20W/30W	95LM/W	30K/40K/50K - Bronze	4
FLDXPRO-MD-10-30W-MCTPB-BK	10W/20W/30W	95LM/W	30K/40K/50K - Black	4
FLDXPRO-MD-10-30W-MCTPB-WH-P	10W/20W/30W	95LM/W	30K/40K/50K - White	4

FLD4X-25W-MCTPB-D-BR

LED X-GEN BULLET FLOOD LIGHT, 0-10V DIMMING POWER, CCT & BEAM ANGLE ADJUSTABLE

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
FLD4X-25W-MCTPB-D-BR	15W/20W/25W	150LM/W	30K/40K/50K - Bronze	4
FLD4X-25W-MCTPB-D-BK	15W/20W/25W	150LM/W	30K/40K/50K - Black	4

FLD3-13W-MCT-D-KN

3RD GENERATION 3CCT FLOOD HEAD **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
FLD3-13W-MCT-D-KN	13W	1820LM	3000K/4000K/5000K	12
FLD3-25W-MCT-D-KN	25W	3500LM	3000K/4000K/5000K	12

FLD2-15W-D-KN

FLD2-28W-D-KN

FLD2-42W-D-KN

FLD2-KN

GARDEN AND FLAG BULLET LIGHT **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
FLD2-15W-30K-D-KN	15W	1900LM	3000K	12
FLD2-15W-50K-D-KN	15W	1900LM	5000K	12
FLD2-28W-30K-D-KN	28W	3500LM	3000K	8
FLD2-28W-50K-D-KN	28W	3500LM	5000K	8
FLD2-42W-30K-D-KN	42W	5200LM	3000K	6
FLD2-42W-50K-D-KN	42W	5200LM	5000K	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR SHROUDS SEE PAGE 50

WATTS	WIRES PULLED OUT	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-010WPO	0-10V Dim. Wires Pulled Out	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

WET LOCATIONS

FLVX-SM Bronze

FLVX-SM Black

FLVX-MD Bronze

FLVX-MD Black

FLVX-LG Bronze

FLVX-LG Black

12V SPEC SERIES LED X-GEN BULLET FLOOD LIGHT WITH LONG SHROUD

CATALOG NO.	DESCRIPTION			PCK QTY
12V SPEC SERIES LED X-GEN BULLET FLOOD LIGHTS WITH LONG SHROUDS				
FLVX-SM-6W-30K-BR	6W	700LM	3000K - 60°, Bronze	12
FLVX-SM-6W-30K-BK	6W	700LM	3000K - 60°, Black	12
FLVX-SM-6W-40K-BR	6W	700LM	4000K - 60°, Bronze	12
FLVX-SM-6W-40K-BK	6W	700LM	4000K - 60°, Black	12
FLVX-SM-12W-30K-BR	12W	1400LM	3000K - 60°, Bronze	12
FLVX-SM-12W-30K-BK	12W	1400LM	3000K - 60°, Black	12
FLVX-SM-12W-40K-BR	12W	1400LM	4000K - 60°, Bronze	12
FLVX-SM-12W-40K-BK	12W	1400LM	4000K - 60°, Black	12
FLVX-MD-24W-30K-BR	24W	2900LM	3000K - 60°, Bronze	8
FLVX-MD-24W-30K-BK	24W	2900LM	3000K - 60°, Black	8
FLVX-MD-24W-40K-BR	24W	2900LM	4000K - 60°, Bronze	8
FLVX-MD-24W-40K-BK	24W	2900LM	4000K - 60°, Black	8
12V SPEC SERIES LED X-GEN BULLET FLOOD LIGHTS WITH LONG SHROUDS-POWER & CCT ADJUSTABLE				
MCTP **FLVX-LG-30-50W-MCTP-BR**	30W/40W/50W	95LM/W	30K/40K/50K - 35°, Bronze	4
MCTP **FLVX-LG-30-50W-MCTP-BK**	30W/40W/50W	95LM/W	30K/40K/50K - 35°, Black	4
FLDVX-FS-SM-BR	Flat Shroud For Sm Size Housing, Bronze			
FLDVX-FS-SM-BK	Flat Shroud For Sm Size Housing, Black			
FLDVX-FS-MD-BR	Flat Shroud For Md Size Housing, Bronze			
FLDVX-FS-MD-BK	Flat Shroud For Md Size Housing, Black			
FLDVX-SM-RL35	35-Degree Repl. Lens For Sm Size Housing			
FLDVX-MD-RL35	35-Degree Repl. Lens For Md Size Housing			
FLDVX-LG-RL60	60-Degree Repl. Lens For LG Size Housing			

FLVXPRO-BR

FLVXPRO-BK

12V SPEC SERIES POWER LED X-GEN BULLET FLOOD LIGHT WITH INTEGRATED PHOTOCELL CCT & BEAM ANGLE- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
FLVXPRO-SM-6-12W-MCTPB-BR	3W/6W/12W	90LM/W	30K/40K/50K - Bronze	4
FLVXPRO-SM-6-12W-MCTPB-BK	3W/6W/12W	90LM/W	30K/40K/50K - Black	4
FLVXPRO-MD-10-30W-MCTPB-BR	10W/20W/30W	90LM/W	30K/40K/50K - Bronze	4
FLVXPRO-MD-10-30W-MCTPB-BK	10W/20W/30W	90LM/W	30K/40K/50K - Black	4

FLVX-MD-15W-RGBW-BT-BR

TC-RGBW-RC

12V SPEC SERIES RGBW BLUETOOTH WESTGATE APP BULLET

CATALOG NO.	DESCRIPTION			PCK QTY
FLVX-MD-15W-RGBW-BT-BR	15W	720LM	RGBW - Bronze	4

FOR REMOTE CONTROL SEE PAGE 523

WET LOCATIONS

GL-12V-12W-30K-BR

12V AC/DC LED GARDEN FLOOD LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
GL-12V-12W-30K-BR	12W	960LM	3000K - bronze, Spike Incl.	6
GL-12V-12W-40K-BR	12W	960LM	4000K - bronze, Spike Incl.	6
GL-12V-12W-50K-BR	12W	960LM	5000K - bronze, Spike Incl.	6
GL-12V-24W-30K-BR	24W	1920LM	3000K - bronze, Spike Incl.	6
GL-12V-24W-40K-BR	24W	1920LM	4000K - bronze, Spike Incl.	6
GL-12V-24W-50K-BR	24W	1920LM	5000K - bronze, Spike Incl.	6

c UL us LISTED DIMMING 0-10V WET LOCATIONS

GL-12W-30K-BR

LED GARDEN FLOOD LIGHT 120~277V

CATALOG NO.	DESCRIPTION			PCK QTY
GL-12W-30K-BR	12W	960LM	3000K - Bronze	6
GL-12W-40K-BR	12W	960LM	4000K - Bronze	6
GL-12W-50K-BR	12W	960LM	5000K - Bronze	6
GL-24W-30K-BR	24W	1920LM	3000K - Bronze	6
GL-24W-40K-BR	24W	1920LM	4000K - Bronze	6
GL-24W-50K-BR	24W	1920LM	5000K - Bronze	6

GL-MCTP-BR

GL-MCTP-BK

GL-MCTP-WH

MCTP-RC1

LED WHITE TUNABLE GARDEN FLOOD LIGHT, REMOTE SOLD SEPARATELY 120~277V

CATALOG NO.	DESCRIPTION			PCK QTY
GL-MCTP-BK	20W MAX.	1400LM MAX.	3000K~5700K - Black	6
GL-MCTP-BR	20W MAX.	1400LM MAX.	3000K~5700K - Bronze	6
GL-MCTP-WH	20W MAX.	1400LM MAX.	3000K~5700K - White	6
MCTP-RC1	Remote Control for Multi-Color Temp. & Power Outdoor Fixture (Required & One per projects)			

TC-GL15W RGBW

TC-RGBW-RC

BLUETOOTH WG APP COMPATIBLE RGBW FLOOD LIGHT, 40D LENS 12V

CATALOG NO.	DESCRIPTION			PCK QTY
TC-GL-12V-15W-RGBW-BT-BR	15W	405LM	RGBW - Bronze	6

FOR REMOTE CONTROL SEE PAGE 523

TC-FL-12V-36W-RGBW

BLUETOOTH WG APP COMPATIBLE RGBW FLOOD LIGHT, 60D LENS 12V

CATALOG NO.	DESCRIPTION			PCK QTY
TC-FL-12V-36W-RGBW-BT-BR	36W	824LM	RGBW - Bronze	4

FOR REMOTE CONTROL SEE PAGE 523

GARAGE & CANOPY LIGHTING

c UL us LISTED | DIMMING 0-10V | WET LOCATIONS | EM CAPABLE | SENSOR OPTION

CDX-35W-35K-BR

CDX-35W-35K-WH

SPEC SERIES LED ADJUSTABLE CANOPY/PARKING LIGHT 120-277V BRONZE & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
WHILE SUPPLIES LAST*	**SPEC SERIES LED ADJUSTABLE CANOPY/PARKING LIGHTS, 120-277V**			
CDX-35W-35K-BR	35W	4600LM	3500K - Bronze, 10.6" (L) x 10.6" (W) x 4-1/2" (H)	2
CDX-35W-35K-WH	35W	4600LM	3500K - White, 10.6" (L) x 10.6" (W) x 4-1/2" (H)	2
CDX-35W-40K-BR	35W	4600LM	4000K - Bronze, 10.6" (L) x 10.6" (W) x 4-1/2" (H)	2
CDX-35W-40K-WH	35W	4600LM	4000K - White, 10.6" (L) x 10.6" (W) x 4-1/2" (H)	2
CDX-35W-50K-BR	35W	4600LM	5000K - Bronze, 10.6" (L) x 10.6" (W) x 4-1/2" (H)	2
CDX-35W-50K-WH	35W	4600LM	5000K - White, 10.6" (L) x 10.6" (W) x 4-1/2" (H)	2
CDX-55W-35K-BR	55W	7250LM	3500K - Bronze, 10.6" (L) x 10.6" (W) x 4-1/2" (H)	2
CDX-55W-35K-WH	55W	7250LM	3500K - White, 10.6" (L) x 10.6" (W) x 4-1/2" (H)	2
CDX-55W-50K-BR	55W	7250LM	5000K - Bronze, 10.6" (L) x 10.6" (W) x 4-1/2" (H)	2
CDX-55W-50K-WH	55W	7250LM	5000K - White, 10.6" (L) x 10.6" (W) x 4-1/2" (H)	2
MCTP	**SPEC SERIES POWER & CCT- ADJUSTABLE LED ADJUSTABLE CANOPY/PARKING LIGHTS, 120-277V**			
CDX-35-55W-MCTP-BR	35W/45W/55W	120LM/W	30K/40K/50K - Bronze	
CDX-35-55W-MCTP-WH	35W/45W/55W	120LM/W	30K/40K/50K - White	

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
35W	OPT-EM-CDX-35	INTERNAL	OPT-PC-B	BUTTON
55W	OPT-EM-CDX-55	INTERNAL	**SENSOR**	DESCRIPTION
VANDAL RES.	DESCRIPTION		OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-TRS-T20	Tamper Resistant Screw		OPT-SEN-NLS-CDX	WG NETWORK SENSOR
	POWDER COATING		OPT-SEN-KEILTON-CDX	KEILTON NETWORK SENSOR
	OPT-CLR-95(BK/GR/SR/WH)		WEC-3RC	OPTIONAL REMOTE CONTROL

CDLX

POWER-ADJUSTABLE CANOPY LIGHT **120-277V** WET LOCATION, DARK BRONZE

CATALOG NO.	DESCRIPTION			PCK QTY
CDLX-SM-5-25W-30K	5W/10W/15W/25W	120LM/W	3000K - 8"X8"X3"	6
CDLX-SM-5-25W-40K	5W/10W/15W/25W	120LM/W	4000K - 8"X8"X3"	6
CDLX-SM-5-25W-50K	5W/10W/15W/25W	120LM/W	5000K - 8"X8"X3"	6
CDLX-MD-15-45W-30K	15W/25W/35W/45W	120LM/W	3000K - 10"X10"X3.63"	4
CDLX-MD-15-45W-40K	15W/25W/35W/45W	120LM/W	4000K - 10"X10"X3.63"	4
CDLX-MD-15-45W-50K	15W/25W/35W/45W	120LM/W	5000K - 10"X10"X3.63"	4
CDLX-LG-30-80W-30K	30W/40W/60W/80W	120LM/W	3000K - 14"X14"X4"	2
CDLX-LG-30-80W-40K	30W/40W/60W/80W	120LM/W	4000K - 14"X14"X4"	2
CDLX-LG-30-80W-50K	30W/40W/60W/80W	120LM/W	5000K - 14"X14"X4"	2

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

SIZE	EM OPTION	DESCRIPTION
SM	OPT-EM-CDLX-SM	INTERNAL
MD	OPT-EM-CDLX-MD	INTERNAL
LG	OPT-EM-CDLX-LG	INTERNAL

VANDAL RES.	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw

POWDER COATING
OPT-CLR-95(BK/GR/SR/WH)

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON
SENSOR	DESCRIPTION
OPT-SEN-2MD-35	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-CDXL	WG NETWORK SENSOR
OPT-SEN-KEILTON-CDXL	KEILTON NETWORK SENSOR
WEC-3RC	OPTIONAL REMOTE CONTROL

480V OPTIONS	DESCRIPTION
OPT-480V-CDLX-80	480V

CXER-30-50W

CXER-40-80W

CXES-30-50W

CXES-WH

CXES-30-60W

FIELD-INSTALLED SENSOR OPTIONS

CXER-30-50W-WH

CXER-40-80W-WH

CXES-40-80W

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

WEC-3PR-72-TLB-WH

WEC-3RC

BUILDER SERIES NEW CONCEPT GARAGE AND CEILING LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
SQUARE NEW CONCEPT GARAGE AND CEILING LIGHTS, POWER & CCT ADJUSTABLE, DAMP LOCATION				
CXES-10-30W-MCTP	10W/20W/30W	130LM/W	30K/40K/50K	4
CXES-30-60W-MCTP	30W/45W/60W	130LM/W	30K/40K/50K	2
CXES-40-80W-MCTP	40W/60W/80W	130LM/W	30K/40K/50K	2
CXES-10-30W-MCTP-WH	10W/20W/30W	130LM/W	30K/40K/50K	4
CXES-30-60W-MCTP-WH	30W/45W/60W	130LM/W	30K/40K/50K	2
CXES-40-80W-MCTP-WH	40W/60W/80W	130LM/W	30K/40K/50K	2
CXES-10-30W-MCTP-EM	10W/20W/30W	130LM/W	30K/40K/50K	4
CXES-30-60W-MCTP-EM	30W/45W/60W	130LM/W	30K/40K/50K	2
CXES-40-80W-MCTP-EM	40W/60W/80W	130LM/W	30K/40K/50K	2
ROUND NEW CONCEPT GARAGE AND CEILING LIGHTS, POWER & CCT ADJUSTABLE, DAMP LOCATION				
CXER-30-50W-MCTP-SR	30W/40W/50W	135LM/W	30K/40K/50K	4
CXER-40-80W-MCTP-SR	40W/60W/80W	135LM/W	30K/40K/50K	2
CXER-30-50W-MCTP-SR-WH	30W/40W/50W	135LM/W	30K/40K/50K	4
CXER-40-80W-MCTP-SR-WH	40W/60W/80W	135LM/W	30K/40K/50K	2
CXER-30-50W-MCTP-SR-EM	30W/40W/50W	135LM/W	30K/40K/50K	4
CXER-40-80W-MCTP-SR-EM	40W/60W/80W	135LM/W	30K/40K/50K	2
CXER-30-50W-MCTP-SR-EM-WH	30W/40W/50W	135LM/W	30K/40K/50K	4
CXER-40-80W-MCTP-SR-EM-WH	40W/60W/80W	135LM/W	30K/40K/50K	2

CGL Series

OPTIONAL FROSTED LENS FIELD REPLACE

LED GARAGE/CANOPY LIGHT 120-277V WET LOCATION

CATALOG NO.	DESCRIPTION			PCK QTY
CGL-40W-50K-D	40W	5200LM	5000K - 9" (L) x 9" (W) x 4-1/2" (H)	4
CGL-40W-40K-D	40W	5200LM	4000K - 9" (L) x 9" (W) x 4-1/2" (H)	4
CGL-55W-50K-D	55W	7100LM	5000K - 9" (L) x 9" (W) x 4-1/2" (H)	4
CGL-55W-40K-D	55W	7100LM	4000K - 9" (L) x 9" (W) x 4-1/2" (H)	4
CGL-75W-50K-D	75W	9700LM	5000K - 10" (L) x 10" (W) x 5" (H)	2
CGL-75W-40K-D	75W	9700LM	4000K - 10" (L) x 10" (W) x 5" (H)	2
CGL-100W-50K-D	100W	13000LM	5000K - 10" (L) x 10" (W) x 5" (H)	2
CGL-100W-40K-D	100W	13000LM	4000K - 10" (L) x 10" (W) x 5" (H)	2
CGL-FL1	Frosted Replacement Lens for CGL-40W & 55W			
CGL-FL2	Frosted Replacement Lens for CGL-75W & 100W			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
40W & 55W	OPT-EM-CGL-40-55	INTERNAL
75W & 100W	OPT-EM-CGL-75-100	INTERNAL

VANDAL RES.	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw

POWDER COATING
OPT-CLR-95(BK/GR/SR/WH)

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-CGL	WG NETWORK SENSOR
OPT-SEN-KEILTON-CGL	KEILTON NETWORK SENSOR
WEC-3RC	OPTIONAL REMOTE CONTROL

CXU Series

Up Light View

X-GEN GARAGE LIGHT WITH UPLIGHT SENSOR READY POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
CXU-18-60W-MCTP-SR	18W/30W/45W/60W	9900LM	30K/40K/50K - White	1
CXU-30-100W-MCTP-SR	30W/50W/75W/100W	16500LM	30K/40K/50K - White	1
CXU-18-60W-MCTP-SR-SIL	18W/30W/45W/60W	9900LM	30K/40K/50K - Silver	1
CXU-30-100W-MCTP-SR-SIL	30W/50W/75W/100W	16500LM	30K/40K/50K - Silver	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL	OPT-EM-CXU-60	External Box
	OPT-EM-CXU-100	External Box

VANDAL RES.	DESCRIPTION
N/A	N/A

SENSOR	DESCRIPTION
N/A	N/A

POWDER COATING
N/A

FIELD-INSTALLED SENSOR OPTIONS

WEC-3RC

WEC-3PR-72-TLB-WH

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

CAX-BR

ANGLED-BEAM GARAGE CANOPY, SENSOR READY CCT AND WATTAGE SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
CAX-20-45W-MCTP-SR	20W/30W/45W	140LM/W	30K/40K/50K	8
CAX-30-60W-MCTP-SR	30W/45W/60W	140LM/W	30K/40K/50K	8
CAX-40-75W-MCTP-SR	40W/60W/75W	140LM/W	30K/40K/50K	8
CAX-60-90W-MCTP-SR	60W/75W/90W	140LM/W	30K/40K/50K	8

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
45W & 60W	OPT-EM-CAX-40-60	INTERNAL	OPT-PC-B	BUTTON
75W & 90W	OPT-EM-CAX-75-90	INTERNAL		
VANDAL RES.	DESCRIPTION		SENSOR	DESCRIPTION
OPT-TRS-T20	Tamper Resistant Screw		FIELD-INSTALLED SENSOR OPTION SEE ABOVE	
POWDER COATING				
OPT-CLR-95(BK/GR/SR/WH)				

Shown with Stem-Mount

GPX Series

GPX-18-60W-MCTP-GCP-BR

GPX-18-60W-MCTP-GCP-SIL

GPX-18-60W-MCTP-GCP-WH

SPEC SERIES GARAGE LIGHT, CEILING OR STEM MOUNT 120~277V TYPE 3 LENS (TYPE 2 & TYPE 5 LENS ALSO AVAILABLE) POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GPX-18-60W-MCTP-GCP-BR	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-GCP-SIL	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-GCP-WH	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1

GAS STATION LIGHTS

GSX-SRFC-80-150W

SURFACE-MOUNT CANOPY LIGHT 120-277V POWER-ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GSX-SRFC-80-150W-50K	80W/100W/120W/150W	140LM/W	5000K	1

GSX-RECS-80-150W

RECESSED GAS STATION CANOPY LIGHT 120-277V POWER-ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GSX-RECS-80-150W-50K	80W/100W/120W/150W	140LM/W	5000K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-EM-GSX	MUST MOUNT ABOVE	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-3PDR-52	BI-LEVEL MICROWAVE
			WEC-3RC	REMOTE CONTROL

WET LOCATIONS

SL-10W-BZ-P

SL-10W-WH-P

SL-20W-BZ-P

SL-20W-WH-P

SL-30W-BZ-P

SL-30W-WH-P

LED SECURITY LIGHT WITH PIR SENSOR **120VAC** 180° SENSOR, 100° BEAM ANGLE (120° 28W) 80% DIM (OR OFF) WHEN NO MOTION DETECTED **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
SL-10W-MCT-BZ-P	10W	950LM	30K/40K/50K - Bronze	8
SL-10W-MCT-WH-P	10W	950LM	30K/40K/50K - White	8
SL-20W-50K-BZ-P	20W	1900LM	5000K - Bronze	8
SL-20W-30K-BZ-P	20W	1900LM	3000K - Bronze	8
SL-20W-MCT-BZ-P	20W	1900LM	3000K/4000K/5000K - Bronze	8
SL-20W-30K-WH-P	20W	1900LM	3000K - White	8
SL-20W-MCT-WH-P	20W	1900LM	3000K/4000K/5000K - White	8
SL-30W-30K-BZ-P	30W	2800LM	3000K - Bronze	8
SL-30W-MCT-BZ-P	30W	2800LM	3000K/4000K/5000K - Bronze	8
SL-30W-50K-WH-P	30W	2800LM	5000K - White	8
SL-30W-30K-WH-P	30W	2800LM	3000K - White	8
SL-30W-MCT-WH-P	30W	2800LM	3000K/4000K/5000K - White	8

***WHILE SUPPLIES LAST**

TRIAC DIMMABLE

WET LOCATIONS

SL-10W-BZ-D

SL-20W-BZ-D

SL-30W-BZ-D

SL-10W-WH-D

SL-20W-WH-D

SL-30W-WH-D

NO-SENSOR DIMMABLE LED FLOOD LIGHT 120V SEE BELOW FOR OPTIONAL MOTION SENSOR OR PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
SL-10W-50K-BZ-D	10W	950LM	5000K - Bronze	8
SL-10W-30K-BZ-D	10W	950LM	3000K - Bronze	8
MCT SL-10W-MCT-BZ-D	10W	950LM	30K/40K/50K - Bronze	8
SL-10W-50K-WH-D	10W	950LM	5000K - White	8
SL-10W-30K-WH-D	10W	950LM	3000K - White	8
MCT SL-10W-MCT-WH-D	10W	950LM	30K/40K/50K - White	8
SL-20W-50K-BZ-D	20W	1900LM	5000K - Bronze	8
SL-20W-30K-BZ-D	20W	1900LM	3000K - Bronze	8
MCT SL-20W-MCT-BZ-D	20W	1900LM	3000K/4000K/5000K - White	8
MCT SL-20W-MCT-WH-D	20W	1900LM	3000K/4000K/5000K - White	8
SL-30W-30K-BZ-D	30W	2800LM	3000K - Bronze	8
MCT SL-30W-MCT-BZ-D	30W	2800LM	3000K/4000K/5000K - Bronze	8
SL-30W-50K-WH-D	30W	2800LM	5000K - White	8
SL-30W-30K-WH-D	30W	2800LM	3000K - White	8
MCT SL-30W-MCT-WH-D	30W	2800LM	3000K/4000K/5000K - White	8

WHILE SUPPLIES LAST*

SL-20W-BZ

SL-28W-BZ-P

SL-28W-BZ-D

SL-40W-BZ-D

SL-20W-WH

SL-28W-WH-P

SL-28W-WH-D

SL-40W-WH-D

LED SQUARE HEAD SECURITY LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
NON-DIMMABLE LED SECURITY LIGHTS WITHOUT SENSOR, BASE COMPATIBLE WITH 4" ROUND W/P BOXES, 120V				
SL-20W-30K-BZ	20W	2000LM	3000K - Bronze	8
SL-20W-50K-BZ	20W	2000LM	5000K - Bronze	8
SL-20W-30K-WH	20W	2000LM	3000K - White	8
SL-20W-50K-WH	20W	2000LM	5000K - White	8
LED SECURITY LIGHTS WITH PIR SENSOR, 180° SENSOR 80%, DIM (OR OFF) WHEN NO MOTION DETECTED, 120-277V				
SL-28W-50K-WH-P	28W	3400LM	5000K - White	4
SL-28W-30K-WH-P	28W	3400LM	3000K - White	4
TRIAC DIMMABLE **DIMMABLE LED FLOOD LIGHTS WITH OPTIONAL MOTION SENSOR OR PHOTOCELL, 120V**				
SL-28W-50K-BZ-D	28W	3400LM	5000K - Bronze	4
SL-28W-30K-BZ-D	28W	3400LM	3000K - Bronze	4
MCT **SL-28W-MCT-BZ-D**	28W	3400LM	3000K/4000K/5000K - Bronze	4
SL-28W-50K-WH-D	28W	3400LM	5000K - White	4
MCT **SL-28W-MCT-WH-D**	28W	3400LM	3000K/4000K/5000K - White	4
SL-40W-50K-BZ-D	40W	4800LM	5000K - Bronze	4
SL-40W-30K-BZ-D	40W	4800LM	3000K - Bronze	4
MCT **SL-40W-MCT-BZ-D**	40W	4800LM	3000K/4000K/5000K - Bronze	4
MCT **SL-40W-MCT-WH-D**	40W	4800LM	3000K/4000K/5000K - White	4

FOR PHOTOCELL & SENSORS SEE PAGES 525

WHILE SUPPLIES LAST*

SLX-2H-BR-D

SLX-2H-BK-D

SLX-2H-WH-D

SLX-2H-BR-P

SLX-2H-BK-P

SLX-2H-WH-P

X-GEN ADVANCE SECURITY LIGHT 120V WITH AND WITHOUT MOTION SENSOR, POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
X-GEN ADVANCE SECURITY LIGHTS WITH PIR SENSOR				
SLX-2H-MCTP-BR-P	16W-25W	130LM/W	30K/40K/50K - Bronze	6
SLX-2H-MCTP-WH-P	16W-25W	130LM/W	30K/40K/50K - White	6
SLX-2H-MCTP-BK-P	16W-25W	130LM/W	30K/40K/50K - Black	6
TRIAC DIMMABLE **NO-SENSOR DIMMABLE X-GEN ADVANCE SECURITY LIGHTS**				
SLX-2H-MCTP-BR-D	16W-25W	130LM/W	30K/40K/50K - Bronze	6
SLX-2H-MCTP-WH-D	16W-25W	130LM/W	30K/40K/50K - White	6
SLX-2H-MCTP-BK-D	16W-25W	130LM/W	30K/40K/50K - Black	6

GET IT ON Google Play
Download on the App Store

SL-CAM-BR

SL-CAM-BK

SL-CAM-WH

SMART CAMERA ACCESSORY WITH 1/2” KNUCKLE

CATALOG NO.	DESCRIPTION
SL-CAM-WH	Security Camera Wg App Enabled White
SL-CAM-BK	Security Camera Wg App Enabled Black
SL-CAM-BR	Security Camera Wg App Enabled Bronze

SL-20W-BR-CAM

SL-20W-BK-CAM

SL-20W-WH-CAM

SL-30W-BR-CAM

SL-30W-BK-CAM

SL-30W-WH-CAM

3CCT SECURITY LIGHT WITH CAMERA, WG APP

CATALOG NO.	DESCRIPTION			PCK QTY
SL-20W-MCT-WH-CAM	20W	1900LM	30K/40K/50K - White	1
SL-20W-MCT-BK-CAM	20W	1900LM	30K/40K/50K - Black	1
SL-20W-MCT-BR-CAM	20W	1900LM	30K/40K/50K - Bronze	1
SL-30W-MCT-WH-CAM	30W	2800LM	30K/40K/50K - White	1
SL-30W-MCT-BK-CAM	30W	2800LM	30K/40K/50K - Black	1
SL-30W-MCT-BR-CAM	30W	2800LM	30K/40K/50K - Bronze	1
SL-CAM-WH	Security Camera Wg App Enabled White			
SL-CAM-BK	Security Camera Wg App Enabled Black			
SL-CAM-BR	Security Camera Wg App Enabled Bronze			

FLS-BR

FLS-WH

WEATHERPROOF LED ROUND FLOOD HEAD **120V** DARK BRONZE & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
FLS-10W-30K-BR	10W	950LM	3000K - bronze, 100°	12
FLS-10W-50K-BR	10W	950LM	5000K - bronze, 100°	12
FLS-10W-30K-WH	10W	950LM	3000K - White, 100°	12
FLS-10W-50K-WH	10W	950LM	5000K - White, 100°	12
FLS-10W-30K-BK	10W	950LM	3000K - Black, 100°	12
FLS-10W-50K-BK	10W	950LM	5000K - Black, 100°	12

FOR WEATHER-PROOF BOXES & COVERS SEE PAGE 554

FLH-10W-30K-BR

FLH-10W-30K-WH

WEATHERPROOF LED SQUARE FLOOD HEAD **120V** DARK BRONZE & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
FLH-10W-30K-BR	10W	1000LM	3000K - Bronze	12
FLH-10W-50K-BR	10W	1000LM	5000K - Bronze	12
FLH-10W-30K-WH	10W	1000LM	3000K - White	12
FLH-10W-50K-WH	10W	1000LM	5000K - White	12

OUTDOOR STEP LIGHTS

WET LOCATIONS

STP-10X10-BR



STP-10X10-BK

STP-10X10-GY

STP-10X10-WH

STP-10X3-BR

STP-10X3-BK



STP-10X3-GY



STP-10X3-WH

STP-8X3-BR

STP-8X3-BK

STP-8X3-GY

STP-8X3-WH

COMMERCIAL LARGE RECESSED WALL/STEP LIGHT **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
MCTP DIMMING 0-10V **STP-10X10-MCTP-BR**	10W/18W/25W	37LM/W	30K/40K/50K - Bronze	4
MCTP DIMMING 0-10V **STP-10X10-MCTP-BK**	10W/18W/25W	37LM/W	30K/40K/50K - Black	4
MCTP DIMMING 0-10V **STP-10X10-MCTP-GY**	10W/18W/25W	37LM/W	30K/40K/50K - Graphite RAL 7016	4
MCTP DIMMING 0-10V **STP-10X10-MCTP-WH**	10W/18W/25W	37LM/W	30K/40K/50K - White	4
MCT **STP-10X3-MCT-BR**	10W	47LM/W	30K/40K/50K - Bronze	6
MCT **STP-10X3-MCT-BK**	10W	47LM/W	30K/40K/50K - Black	6
MCT **STP-10X3-MCT-GY**	10W	47LM/W	30K/40K/50K - Graphite RAL 7016	6
MCT **STP-10X3-MCT-WH**	10W	47LM/W	30K/40K/50K - White	6
MCT DIMMING 0-10V **STP-8X3-MCTP-BR**	10W	31LM/W	30K/40K/50K - Bronze	18
MCT DIMMING 0-10V **STP-8X3-MCTP-BK**	10W	31LM/W	30K/40K/50K - Black	18
MCT DIMMING 0-10V **STP-8X3-MCTP-GY**	10W	31LM/W	30K/40K/50K - Graphite RAL 7016	18
MCT DIMMING 0-10V **STP-8X3-MCTP-WH**	10W	31LM/W	30K/40K/50K - White	18

CIGL-9-MCT

CIGL-20-MCT

CIGL-40-MCT

LINEAR ARCHITECTURAL INGROUND LIGHT, 3CCT

CATALOG NO.	DESCRIPTION		
CIGL-9-MCT	5W	420LM	30K/40K/50K
CIGL-20-MCT	10W	860LM	30K/40K/50K
CIGL-40-MCT	24W	2256LM	30K/40K/50K

IGLC-D8-30W-MCTP-30D-D

IGLC-D9-30W-MCTP-120D-D

IGLC-D11-50W-MCTP-15D-D

IGLC-D11-50W-MCTP-60D-D

STAINLESS STEEL COMMERCIAL INGROUND LIGHT

CATALOG NO.	DESCRIPTION			PKG. QTY.	PCK QTY
IGLC-D5-10W-MCT-24D	10W	85LM/W	30K/40K/50K - 5 Dia., 24° Beam Angle		
IGLC-D6-15W-MCT-24D-D	15W	85LM/W	30K/40K/50K - 6 Dia., 24° Beam Angle		
IGLC-D8-30W-MCTP-30D-D	12W/20W/30W	85LM/W	30K/40K/50K - 8 Dia., 30° Beam Angle		4
IGLC-D9-30W-MCTP-120D-D	12W/20W/30W	85LM/W	30K/40K/50K - 9 Dia., 120° Beam Angle		4
IGLC-D11-50W-MCTP-60D-D	22W/34W/50W	85LM/W	30K/40K/50K - 11 Dia., 60° Beam Angle		2
IGLC-D11-50W-MCTP-15D-D	22W/34W/50W	85LM/W	30K/40K/50K - 11 Dia., 15° Beam Angle		2

STREET LIGHTS

Shown with Wall Mounting Arm



ACC-AWM-GR

STL4 Series

Shown with Slip Fitter

Shown with Full Shroud

Shown with Half Shroud (Reversible)

LED STREET/ROADWAY LIGHT w/NEMA TWIST-LOCK PHOTOCELL SOCKET, (SHORTING CAP INCLUDED) FOR PHOTOCELL SEE PAGE 525

CATALOG NO.	DESCRIPTION			PCK QTY
STL4-15-50W-30K	15W/20W/30W/50W	145LM/W	3000K	1
STL4-15-50W-40K	15W/20W/30W/50W	145LM/W	4000K	1
STL4-15-50W-50K	15W/20W/30W/50W	145LM/W	5000K	1
STL4-30-100W-30K	30W/50W/80W/100W	145LM/W	3000K	1
STL4-30-100W-40K	30W/50W/80W/100W	145LM/W	4000K	1
STL4-30-100W-50K	30W/50W/80W/100W	145LM/W	5000K	1
STL4-50-150W-30K	50W/80W/100W/150W	140LM/W	3000K	1
STL4-50-150W-40K	50W/80W/100W/150W	145LM/W	4000K	1
STL4-50-150W-50K	50W/80W/100W/150W	140LM/W	5000K	1
STL4-80-200W-30K	80W/100W/150W/200W	140LM/W	3000K	1
STL4-80-200W-40K	80W/100W/150W/200W	145LM/W	4000K	1
STL4-80-200W-50K	80W/100W/150W/200W	140LM/W	5000K	1
STL4-30-100W-30K-480V	30W/50W/80W/100W	140LM/W	3000K	1
STL4-30-100W-40K-480V	30W/50W/80W/100W	145LM/W	4000K	1
STL4-30-100W-50K-480V	30W/50W/80W/100W	140LM/W	5000K	1
STL4-50-150W-30K-480V	50W/80W/100W/150W	140LM/W	3000K	1
STL4-50-150W-40K-480V	50W/80W/100W/150W	145LM/W	4000K	1
STL4-50-150W-50K-480V	50W/80W/100W/150W	140LM/W	5000K	1
STL4-80-200W-30K-480V	80W/100W/150W/200W	140LM/W	3000K	1
STL4-80-200W-40K-480V	80W/100W/150W/200W	145LM/W	4000K	1
STL4-80-200W-50K-480V	80W/100W/150W/200W	140LM/W	5000K	1
STL4-SF	STL4 Series Street Light Slip Fitter			
STL2-WMA	Wall Mounting Arm - 12-3/4" Length for 50W & above			
ACC-AWM-GR	Angled Corner Wall Mount Arm, 2-3/8In Dia, Grey			

SOLN-10W-WA
Wall & Pole Mounting Arm Included

SOLF-17W-50K

Application Example

SOLN Shown with SOLN-PMRS Round Pole Mounting Accessory

SOLN Shown with SOLN-PMRS Sqaure Pole Mounting Accessory

SOLN Shown with SOLN-WM Wall Mounting Arm

SOLN Shown with SOLN-SFA Slip Fitter Mounting Arm

POWERFUL HIGH-LUMEN SMART INTEGRATED SOLAR STREET AND FLOOD LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
SOLN-10W-50K-WA	10W	1500LM	5000K	1
SOLN-10W-30K-WA	10W	1500LM	3000K	1
SOLN-25W-50K	25W	3750LM	5000K	1
SOLN-25W-30K	25W	3750LM	3000K	1
SOLN-50W-50K	50W	10000LM	5000K	1
SOLN-50W-30K	50W	10000LM	3000K	1
SOLN-70W-50K	70W	14000LM	5000K	1
SOLN-70W-30K	70W	14000LM	3000K	1
SOLN-WM	SOLN Wall Mounting Accessory			
SOLN-SFA	SOLN Slip Fitter Mounting Accessory			
SOLN-PMRS	SOLN Round And Square Pole Mounting Accessory			
SOLF-RC	Remote Control for SOLN Series (One Per Project)			

Shown wth Pole-Top Mount (2" Poles), Sold Separately

Shown with Pole or Wall Mount Arm, Sold Separately

SOLA-SPLT-15W-50K



SOLA-RC

ROADWAY AND AREA SPLIT SOLAR LIGHT, WITH ADVANCED CONTROLLER REMOTE SOLAR PANEL INCLUDED WITH FIXTURE WALL & POLE MOUNTING OPTIONS AVAILABLE SOLD SEPARATELY

CATALOG NO.	DESCRIPTION			PCK QTY
SOLA-SPLT-15W-50K	15W	2250LM	5000K	1
SOLA-SPLT-30W-50K	30W	4500LM	5000K	1
SOLA-SPLT-PM	Pole Mounting Arm For Split Solar Lights			
SOLA-SPLT-WM	Wall Mounting Arm For Split Solar Lights			
SOLA-RC	Sola Solar Light Remote Control Unit - One Per Project			

SOLF Shown with Round Pole Mount



SOLF-17W-50K

SOLF-RC



SOLFSold Separately



SOLF Shown with Adjustable Slip FiltterSold Separately

SOLF Shown with Square Pole Mount

SOLF Shown with Wall Mount

LED SOLAR ROADWAY/FLOOD LIGHT, NO WIRING, INCLUDED INTELLIGENT CONTROLS

1 DAY CHARGE 3 DAY OPR., LIFEPO4 5YR. BATTERY

PROGRAMMABLE- DEFAULT SETTINGS, 15 SECOND AFTER THE ZONE IS CLEARED THE LIGHT GOES DOWN TO 40%

CATALOG NO.	DESCRIPTION			PCK QTY
SOLF-17W-50K	17W	1600LM	5000K	1
SOLF-36W-50K	36W	4000LM	5000K	1
SOLF-SFA	Adjustable Slip Filtter for Poles up to 2-3/4" O.D.			
SOLF-WM-17W	Wall Mount for SOLF-17W			
SOLF-WM-36W/54W	Wall Mount for SOLF-36W & 54W			
SOLF-PMR-17W	Round Pole Mount for SOLF-17W			
SOLF-PMR-36W/54W	Round Pole Mount for SOLF-36W & 54W			
SOLF-PMS-17W	Square Pole Mount for SOLF-17W			
SOLF-RC	Remote Control for SOLF Series			

WET LOCATIONS

SOLH-30W

SOLH-100W

SOLH-50W

SOLH-140W

SOLH-100W

COMPATIBLE WITH SOLN POLE/WALL MOUNTING ARMS

ADVANCED-TECH SOLAR STREET LIGHT 190LM/W AUTO COOL/HEAT **MADE TO ORDER**

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER
SOLH-30W-XXK-MM-CLR	Advanced-Tech Solar Street Light 30W 190LM/W Auto Cool/Heat	
SOLH-50W-XXK-MM-CLR	Advanced-Tech Solar Street Light 50W 190LM/W Auto Cool/Heat	
SOLH-100W-XXK-MM-CLR	Advanced-Tech Solar Street Light 100W 190LM/W Auto Cool/Heat	
SOLH-140W-XXK-MM-CLR	Advanced-Tech Solar Street Light 140W 190LM/W Auto Cool/Heat	
OPT-SOLH-30W-SC	Self-Cleaning Option Twice/Day For SOLH-30W	
OPT-SOLH-50W-SC	Self-Cleaning Option Twice/Day For SOLH-50W	
OPT-SOLH-100W-SC	Self-Cleaning Option Twice/Day For SOLH-100W	
OPT-SOLH-140W-SC	Self-Cleaning Option Twice/Day For SOLH-140W	
OPT-SOLH-30W-HYB120277V	Hybrid 120-277V Input Option Twice/Day For SOLH-30W	
OPT-SOLH-50W-HYB120277V	Hybrid 120-277V Input Option Twice/Day For SOLH-50W	
OPT-SOLH-100W-HYB120277V	Hybrid 120-277V Input Option Twice/Day For SOLH-100W	
OPT-SOLH-140W-HYB120277V	Hybrid 120-277V Input Option Twice/Day For SOLH-140W	
OPT-SOLH-30W-HYB277480V	Hybrid 277-480V Input Option Twice/Day For SOLH-30W	
OPT-SOLH-50W-HYB277480V	Hybrid 277-480V Input Option Twice/Day For SOLH-50W	
OPT-SOLH-100W-HYB277480V	Hybrid 277-480V Input Option Twice/Day For SOLH-100W	
OPT-SOLH-140W-HYB277480V	Hybrid 277-480V Input Option Twice/Day For SOLH-140W	

WET LOCATIONS

SOLA-5W-50K-WA

Shown Back Side

SOLA-RC

ROADWAY AND AREA SOLAR LIGHT, WITH ADVANCED CONTROLLER INTEGRATED SOLAR PANEL, 20" WALL/POLE MOUNT ARM INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
SOLA-5W-50K-WA	5W	750LM	5000K	1
SOLA-RC	Sola Solar Light Remote Control Unit - One Per Project			

WET LOCATIONS

SOLS- PRO

SOLS-PRO



SOLS-PRO with BRACKET

RC

PRO SOLAR SIGN LIGHT WITH UNIV MOUNTING AND RC

CATALOG NO.	DESCRIPTION			PCK QTY
SOLS-PRO-2FT-50K	5W	850LM	5000K - 2FT	1
SOLS-PRO-4FT-50K	10W	1700LM	5000K - 4FT	1

WET LOCATIONS



SOLS-1FT-MCT

SPEC SERIES

SPEC SERIES SOLAR SIGN AND BILLBOARD LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
SOLS-1FT-MCT	5W	500LM	3000K/6000K - 1FT	18

WET LOCATIONS

SOLW-TSP-MS-40K Installed

SOLW-TSP-MS-40K



SOLW-TSP-MS-40K Back View

SOLW-TSP-MS-40K Back Side

WallRay SOLAR LUMINAIRE PROG. REMOTE INCLUDED MOTION SENSOR

CATALOG NO.	DESCRIPTION		
SOLW-TSP-MS-40K	3W	380LM	4000K

WET LOCATIONS

SOLW-FSP-MS-40K Installed

SOLW-FSP-MS-40K



SOLW-FSP-MS-40K Back View



SOLW-FSP-MS-40K Back Side

LedgeRay SOLAR LUMINAIRE PROG. REMOTE INCLUDED MOTION SENSOR

CATALOG NO.	DESCRIPTION		
SOLW-FSP-MS-40K	3W	345LM	4000K

WET LOCATIONS

SOLW-BSP-MS-40K Installed

SOLW-BSP-MS-40K



SOLW-BSP-MS-40K Back View

SOLW-BSP-MS-40K Back Side

EdgeRay SOLAR LUMINAIRE PROG. REMOTE INCLUDED MOTION SENSOR

CATALOG NO.	DESCRIPTION		
SOLW-BSP-MS-40K	2W	385LM	4000K

DAB-SOL-A16-50W-MCT

DAB-SOL-B20-50W-MCT

DAB-SOL-B23-50W-MCT


DAB-BABack Side

DAB-SOL-PA3-2

DAB-SOL-PA4-1

DAB-SOL-A16-50W-MCT with 3inch light pole

DAB-SOL-B23-50W-MCT Double with 5inch light poleMCT

DAB-SOL-MOD-50WMCT

DAB-SOL-PA3-1

DAB-SOL-PA4-2

DAB-SOL-PA5-1

DAB-SOL-PA5-2

SOLAR DESIGNER AREA BELL LIGHT SYSTEM

CATALOG NO.	DESCRIPTION			PCK QTY
DAB-SOL-A16-50W-MCT	50W	160LM/W	30K/40K/50K - 16" Black	1
DAB-SOL-B20-50W-MCT	50W	160LM/W	30K/40K/50K - 20" Black	1
DAB-SOL-B23-50W-MCT	50W	160LM/W	30K/40K/50K - 23" Black	1
DAB-SOL-MOD-50W	Solar Power Engine And Panel, 50W Maximum Fixture Power, With 32In Mast			
DAB-BA	DAB Bell Arm For Mounting On Single Or Double Pole Adapters, Black			
DAB-SOL-PA3-1	3 Inches Pole-Top Adapter For 1 Solar Bell-Light Arm + Solar Engine Mast			
DAB-SOL-PA4-1	4 Inches Pole-Top Adapter For 1 Solar Bell-Light Arm + Solar Engine Mast			
DAB-SOL-PA5-1	5 Inches Pole-Top Adapter For 1 Solar Bell-Light Arm + Solar Engine Mast			
DAB-SOL-PA3-2	3 Inches Pole-Top Adapter For 2 Solar Bell-Light Arms + Solar Engine Mast			
DAB-SOL-PA4-2	4 Inches Pole-Top Adapter For 2 Solar Bell-Light Arms + Solar Engine Mast			
DAB-SOL-PA5-2	5 Inches Pole-Top Adapter For 2 Solar Bell-Light Arms + Solar Engine Mast			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL	OPT-EM-DAB	INTERNAL	OPT-LF3-PCK	BUTTON
	POWDER COATING		SENSOR	DESCRIPTION
	OPT-CLR-95(BK/GR/SR/WH)		FIELD-INSTALLED SENSOR OPTION SEE ABOVE	

GPX-SOLAR-A1

GPX-SOLAR-PWM

GPX-SOLAR-SF

GPX-SOLAR-A1

GPX-SOLAR-PWM

GPX-SOLAR-SF

SPEC SERIES SOLAR AREA/FLOOD LIGHT **120-277V** TYPE 5 LENS (TYPE 2 & TYPE 3 LENS ALSO AVAILABLE) MADE TO ORDER POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GPX-10W-SOLAR-A1	10W	1700LM	30K/40K/50K - Bronze	1
GPX-10W-SOLAR-PWM	10W	1700LM	30K/40K/50K - Bronze	1
GPX-10W-SOLAR-SF	10W	1700LM	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-CAT-BK	18W/30W/45W/60W	150LM/W	30K/40K/50K - Black	1
GPX-22-75W-MCTP-CAT-BK	22W/37W/56W/75W	150LM/W	40K/50K - Black	1
GPX-90-150W-MCTP-CAT-BK	90W/120W/150W	150LM/W	30K/40K/50K - Black	1
GPX-10W-SOLAR-A2	10W	1700LM	30K/40K/50K	1

BOL-G4-301-SOLAR + BOL-G4-SHAFT(2)

HEAD, SHAFT, ANCHOR BOLTS SET SOLD SEPARATELY

BOL-G4-SOLAR-RC

BOL-G4-ABK-R

SOLAR G4 MODULAR BOLLARD SYSTEM

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-G4-301-SOLAR-30K-BK	3W	130LM/W	3000K - Black Head	1
BOL-G4-301-SOLAR-40K-BK	3W	130LM/W	4000K - Black Head	1
BOL-G4-301-SOLAR-30K-BR	3W	130LM/W	3000K - Bronze Head	1
BOL-G4-301-SOLAR-40K-BR	3W	130LM/W	4000K - Bronze Head	1
BOL-G4-SHAFT-14-BK	G4 Bollard Shaft 14 Inch, Black			
BOL-G4-SHAFT-14-BR	G4 Bollard Shaft 14 Inch, Bronze			
BOL-G4-SHAFT-30-BK	G4 Bollard Shaft 30 Inch, Black			
BOL-G4-SHAFT-30-BR	G4 Bollard Shaft 30 Inch, Bronze			
BOL-G4-ABK-R	G4 Bollard Round Anchor Bolts & Mounting Plate			
BOL-G4-GSH-01-BK	G4 Bollard Round Anchor Bolts & Mounting Plate, Black			
BOL-G4-GSH-01-BR	G4 Bollard Round Anchor Bolts & Mounting Plate, Bronze			
BOL-G4-SOLAR-RC	Remote Control, Required 1 Per Projects			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

FOR OPT OPTION SEE PAGE 128

BOL-G5-ABK-R

BOL-G5 Series SOLAR + BOL-G4-SHAFT

HEAD, SHAFT, & ANCHOR BOLTS SET
SOLD SEPARATELY

SOLAR WESTGATE MODERN MODULAR BOLLARD SYSTEM G5

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-G5-SOLAR-MCT-BK	4W	600LM	30K/40K/50K - Black, Head	1
BOL-G5-SOLAR-MCT-BR	4W	600LM	30K/40K/50K - Bronze, Head	1
BOL-G5-SHAFT-14-BK	G5 Bollard Shaft 14 Inch, Black			
BOL-G5-SHAFT-14-BR	G5 Bollard Shaft 14 Inch, Bronze			
BOL-G5-SHAFT-33-BK	G5 Bollard Shaft 33 Inch, Black			
BOL-G5-SHAFT-33-BR	G5 Bollard Shaft 33 Inch, Bronze			
BOL-G5-ABK-R	G5 Bollard Round Anchor Bolts & Mounting Plate			
BOL-G5-GSH-01	G5 Bollard 180-Degree Glare Shield			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			



SOLR-WL1-30K-SEN-BK

SOLR-PL1-30K

SOLR-SL1-60K-SEN



SOLRW-30K

SOLR-WL2-MCT-SEN

SPEC SERIES SOLAR LIGHT COLLECTION

CATALOG NO.	DESCRIPTION		
SOLRW-30K	0.2W	50LM	3000K
SOLR-SL1-60K-SEN	0.5W+0.2W	100LM	6000K/3000K
SOLR-WL1-30K-SEN-BK	5W	500LM	3000K - Black
SOLR-WL2-MCT-SEN	8W	1000LM	3000K/6000K
SOLR-PL1-30K	3W	300LM	3000K

WET LOCATIONS

SOLB-BSP-MS-40K

SOLB-BSPD-MS-40K

SOLAR BOLLARD, REMOTE INCLUDED, MOTION SENSOR, GRAPHITE FINISH

CATALOG NO.	DESCRIPTION			PCK QTY
SOLB-BSP-MS-40K	2W	380LM	4000K	4
SOLB-BSPD-MS-40K	4W	730LM	4000K	4



STADIUM LIGHTING

SFX-G7

Slip Fitter Adapter for SFX Thailight

GENERATION 7 STADIUM LIGHT 120-277V OR 277-480V

CATALOG NO.	DESCRIPTION			PCK QTY
GENERATION 7 STADIUM LIGHTS, 120-277V				
SFX-G7-200-500W-45D-50K	200W/300W/400W/500W	150LM/W	5000K	1
SFX-G7-700-1000W-45D-50K	700W/800W/900W/1000W	150LM/W	5000K	1
GENERATION 7 STADIUM LIGHTS, 277-480V				
SFX-G7-200-500W-45D-50K-480V	200W/300W/400W/500W	150LM/W	5000K	1
SFX-G7-700-1000W-45D-50K-480V	700W/800W/900W/1000W	150LM/W	5000K	1
SFX-G7-1400-1700W-45D-50K-480V	1400W/1500W/1600W/1700W	150LM/W	5000K	1
SFX-G7-2100-2400W-45D-50K-480V	2100/2200/2300/2400W	140LM/W	5000K	1
SFX-G7-SF	Slip Fitter/Pole Adapter For SFX-G7			

SFX-G12

G12 ADJUSTABLE DISTRIBUTION ANGLE STADIUM LIGHT

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
SFX-G12AD-300-500W-50K	300W/400W/500W	155LM/W	5000K	1
SFX-G12AD-300-500W-50K-480V	300W/400W/500W	155LM/W	5000K	1
SFX-G12AD-400-600W-50K-480V	400W/500W/600W	155LM/W	5000K	1
SFX-G12AD-500-750W-50K-480V	500W/600W/750W	155LM/W	5000K	1

SFX-G10


SFX-G10-RGBW

SFX-G10-AIMDEV

Shown with Visor

Shown with Slip Fitter

Shown with Quick Clamp Adapter

PROFESSIONAL SPORTS LIGHT, SYNAPSE CONTROL (DALI D4i ZHAGA), 200-480V, 60°

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
SFX-G10-400-600W-60D-50K	400/500/600W	170LM/W	5000K	1
SFX-G10-400-800W-30D-50K	400/600/800W	170LM/W	5000K	1
SFX-G10-800-1200W-30D-50K	800/1000/1200	170LM/W	5000K	1
SFX-G10-600W-LENS-22D	SFX-G10 600W 22-Degree Replacement Lens			
SFX-G10-600W-LENS-30D	SFX-G10 600W 30-Degree Replacement Lens			
SFX-G10-600W-LENS-45D	SFX-G10 600W 45-Degree Replacement Lens			
SFX-G10-800W-LENS-45D	SFX-G10 800W 45-Degree Replacement Lens			
SFX-G10-800W-LENS-60D	SFX-G10 800W 60-Degree Replacement Lens			
SFX-G10-1200W-LENS-45D	SFX-G10 1200W 45-Degree Replacement Lens			
SFX-G10-1200W-LENS-60D	SFX-G10 1200W 60-Degree Replacement Lens			
SFX-G10-AIMDEV	SFX-G10 Aiming Device			

SPEC SERIES X GEN. RGB STADIUM LIGHT, DMX512 CONTROLLED

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
SFX-G10-600W-45D-RGB	600W	62LM/W	RGB - 45° Beam Angle	1
SFX-G10-800W-45D-RGB	800W	62LM/W	RGB - 45° Beam Angle	1
SFX-G10-1200W-45D-RGB	1200W	62LM/W	RGB - 45° Beam Angle	1
SFX-G10-SF	SFX-G10 Series Slip-Fitter Adapter			
SFX-G10-SF-BK	SFX-G10 Series Slip-Fitter Adapter Black			
SFX-G10-QC	SFX-G10 Series Quick Clamp Adapter For Flat Horizontal Bars			
SFX-G10-VISOR-600W	SFX-G10 Visor Accessory For 600W			
SFX-G10-VISOR-800W	SFX-G10 Visor Accessory For 800W			
SFX-G10-VISOR-1200W	SFX-G10 Visor Accessory For 1200W			
SFX-G10-SF-BK	SFX-G10 Series Slip-Fitter Adapter Black			

SFX-G11-800-120W-57K

SFX-G11-SH1

Shown with Optional Shroud

SFX-G10-AIMDEV

SQUARE PROFESSIONAL SPORTS LIGHT, SYNAPSE CONTROL (DALI D4i ZHAGA)
MADE TO ORDER - CALL FOR PRICING

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
SFX-G11-800-1200W-57K	800W/960W/1200W	140LM/W	5700K	1
SFX-G11-SH1	Shroud For One Module Of Symetric SFX-G11			

SIGN LIGHTS

c UL us LISTED

WET LOCATIONS

LOHB-2FT

LOHB-4FT

LOHB-4FT-WH

Flood Light Wall-Mounting Arm

LOHB-C Surface or Ceiling Mounting conversion Bracket with screw holes in base, (set of 2)

LOHB-H-2FT 2Ft. Surface Mounting conversion yoke, Steel (Also need LOHB-G)Thailight

LOHB-G

LED OUTDOOR SIGN LIGHT WITH 1/2" ADJUSTABLE KNUCKLE 120~277V

CATALOG NO.	DESCRIPTION			PCK QTY
LOHB-2FT-50W-30K	50W	6500LM	3000K	4
LOHB-2FT-50W-40K	50W	6600LM	4000K	4
LOHB-2FT-50W-50K	50W	6700LM	5000K	4
LOHB-4FT-120W-30K	120W	15300LM	3000K	1
LOHB-4FT-120W-40K	120W	15500LM	4000K	1
LOHB-4FT-120W-50K	120W	15600LM	5000K	1
LOHB-4FT-120W-30K-WH	120W	15300LM	3000K	1
LOHB-4FT-120W-40K-WH	120W	15500LM	4000K	1
LOHB-4FT-120W-50K-WH	120W	15600LM	5000K	1
LOHB-C	Surface/Ceiling Mounting conversion Bracket w/screw holes in base, (set of 2)			
LOHB-H-2FT	2Ft. Surface Mounting conversion yoke, Steel (Also need LOHB-G)			
LOHB-G	Side by side fixture coupling Also used with LOHB-G Surf. Mt. Bracket (set of 2)			

TSR-IP66-BK

TSR-IP66-WH

TSR Series

TUBULAR ROTATABLE IP66 SIGN LIGHT WITH MOUNT CANOPY

CATALOG NO.	DESCRIPTION			PCK QTY
TSR-IP66-80D-2FT-MCT5-D-WH	15W	1395LM	27K/30K/35K/40K/50K - 2FT, 80° Beam Angle, White	6
TSR-IP66-80D-3FT-MCT5-D-WH	20W	1860LM	27K/30K/35K/40K/50K - 3FT, 80° Beam Angle, White	6
TSR-IP66-80D-4FT-MCT5-D-WH	30W	2790LM	27K/30K/35K/40K/50K - 4FT, 80° Beam Angle, White	6
TSR-IP66-80D-6FT-MCT5-D-WH	40W	3720LM	27K/30K/35K/40K/50K - 6FT, 80° Beam Angle, White	6
TSR-IP66-80D-2FT-MCT5-D-BK	15W	1395LM	27K/30K/35K/40K/50K - 2FT, 80° Beam Angle, Black	6
TSR-IP66-80D-3FT-MCT5-D-BK	20W	1860LM	27K/30K/35K/40K/50K - 3FT, 80° Beam Angle, Black	6
TSR-IP66-80D-4FT-MCT5-D-BK	30W	2790LM	27K/30K/35K/40K/50K - 4FT, 80° Beam Angle, Black	6
TSR-IP66-80D-6FT-MCT5-D-BK	40W	3720LM	27K/30K/35K/40K/50K - 6FT, 80° Beam Angle, Black	6
TSR-IP66-133D-2FT-MCT5-D-WH	15W	1395LM	27K/30K/35K/40K/50K - 2FT, 133° Beam Angle, White	6
TSR-IP66-133D-3FT-MCT5-D-WH	20W	1860LM	27K/30K/35K/40K/50K - 3FT, 133° Beam Angle, White	6
TSR-IP66-133D-4FT-MCT5-D-WH	30W	2790LM	27K/30K/35K/40K/50K - 4FT, 133° Beam Angle, White	6
TSR-IP66-133D-6FT-MCT5-D-WH	40W	3720LM	27K/30K/35K/40K/50K - 6FT, 133° Beam Angle, White	6
TSR-IP66-133D-2FT-MCT5-D-BK	15W	1395LM	27K/30K/35K/40K/50K - 2FT, 133° Beam Angle, Black	6
TSR-IP66-133D-3FT-MCT5-D-BK	20W	1860LM	27K/30K/35K/40K/50K - 3FT, 133° Beam Angle, Black	6
TSR-IP66-133D-4FT-MCT5-D-BK	30W	2790LM	27K/30K/35K/40K/50K - 4FT, 133° Beam Angle, Black	6
TSR-IP66-133D-6FT-MCT5-D-BK	40W	3720LM	27K/30K/35K/40K/50K - 6FT, 133° Beam Angle, Black	6
TSR-IP66-ERK-WH	TSR Sign Light 12in Extension Rod Kit White, Set of 2			
TSR-IP66-ERK-BK	TSR Sign Light 12in Extension Rod Kit Black, Set of 2			
TSR-IP66-COUP-WH	TSR Sign Light Inline Coupling With Incl. Rod Kit White, Set of 2			
TSR-IP66-COUP-BK	TSR Sign Light Inline Coupling With Incl. Rod Kit Black, Set of 2			

CONSTRUCTION/TEMPORARY LIGHTING

WET LOCATIONS



CL-CONST-2WIRE

2WIRE ECONOMY CONSTRUCTION STRING LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
CL-CONST-50FT-50W-2WIRE	5X10W	6000LM	5000K - 50FT	1
CL-CONST-100FT-50W-2WIRE	10X10W	12000LM	5000K - 100FT	1
CL-CONST-50FT-50W-2WIRE	5X10W	6000LM	5000K - 50FT	1
CL-CONST-100FT-50W-2WIRE	10X10W	12000LM	5000K - 100FT	1
CL-CONST-40W-50K	40W	4800LM	5000K - 6FT CORD WITH 15A	1
CL-CONST-100W-50K	100W	12000LM	5000K - 6FT CORD WITH 15A	1
CL-CONST-E39-8FT	Lamp-Ready Construction Light E39 Mogul 150W Max 8Ft Cord Max 1200W Daisy Chai			
CL-CONST-LINEAR-IP65	90W	10800LM	5000K	
CL-CONST-UFO-IP65	130W	15600LM	5000K	
CL-CONST-LU-1FT-120V-PIGTAIL	5-15P 1Ft Straight Power Pigtail For Linear And Ufo Construction Lights			
CL-CONST-LU-1FT-277V-PIGTAIL	L7-15P 1Ft Twist-Lock Power Pigtail For Linear And Ufo Construction Lights			
CL-CONST-LU-25FT-EXTENSION-T	25Ft Extension Cord With Triple End For Linear And Ufo Construction Lights			

WET LOCATIONS

CL-CONST-E39-8FT

LAMP-READY CONSTRUCTION LIGHT E39 MOGUL - MAX 8FT CORD MAX 1200W DAISY CHAIN

CATALOG NO.	DESCRIPTION
CL-CONST-E39-8FT	Lamp-Ready Construction Light E39 Mogul 150W Max 8Ft Cord Max 1200W Daisy Chai

WET LOCATIONS



CL-CONST-LINEAR-IP65

CL-CONST-UFO-IP65

WET LOCATION LINKABLE TEMPORARY CONSTRUCTION LIGHTS IP65 HIGH-LUMEN & IMPACT RESISTANT

CATALOG NO.	DESCRIPTION		
CL-CONST-LINEAR-IP65	90W	10800LM	5000K
CL-CONST-UFO-IP65	130W	15600LM	5000K
CL-CONST-LU-1FT-120V-PIGTAIL	5-15P 1Ft Straight Power Pigtail For Linear And Ufo Construction Lights		
CL-CONST-LU-1FT-277V-PIGTAIL	L7-15P 1Ft Twist-Lock Power Pigtail For Linear And Ufo Construction Lights		
CL-CONST-LU-25FT-EXTENSION-T	25Ft Extension Cord With Triple End For Linear And Ufo Construction Lights		

CL-CONST-40W/100W-50K

LED CONSTRUCTION / TEMPORARY LIGHT WITH SOCKET FOR LINKING MULTIPLE UNITS

CATALOG NO.	DESCRIPTION			PCK QTY
CL-CONST-40W-50K	40W	4800LM	5000K - 6FT CORD WITH 15A	1
CL-CONST-100W-50K	100W	12000LM	5000K - 6FT CORD WITH 15A	1

WET LOCATIONS

WL-EZCG-10W-50K

WL-EZCG-SOLP

LED WORK LIGHT, HOOK & USB CABLE & ADAPTOR INCLUDED

CATALOG NO.	DESCRIPTION		
WL-EZCG-10W-50K	10W	300~600LM	5000K
WL-EZCG-SOLP	Solar panel 10 ft. cord & magnetic base		

WL-3IN1-10W

Retail Packaging - MOQ 1 Master Carton of 10

3IN1 LED WORK LIGHT (WORK LIGHT/SOS LIGHT/POWER BANK) USB CABLE INCLUDED

CATALOG NO.	DESCRIPTION		
WL-3IN1-10W	10W	400LM	6000K

ACCESSORIES



PSS3SVTZ
PSS4SVTZ
PSS5SVTZ

PRPT3
PRPT4
PRPT5
PRPT6

PRR32

PSR4

LF-AD-KNU

LF-AD-SF

PSS3R



PSS4C

POLE/ADAPTER ACCESSORIES, BRONZE FINISH

CATALOG NO.	DESCRIPTION
PSS3SVTZ	3" square pole vertical tenon, 3", bronze. Goes inside 3" pole to accept 2" slip fitter.
PSS4SVTZ	4" square pole vertical tenon, 4", bronze. Goes inside 4" pole to accept 2" slip fitter.
PSS5SVTZ	5" square pole vertical tenon, 5", bronze. Goes inside 5" pole to accept 2" slip fitter.
PRR32	3 in To 2 in Round Pole Reducer
GPEX-30-25-REDUCER	Universal Pole-Top Reducer From 3in To 2in Black
PRPT3	Tenon adaptor, 3" round pole, to standard tenon, bronze
PRPT4	Tenon adaptor, 4" round pole, to standard tenon, bronze
PRPT5	Tenon adaptor, 5" round pole, to standard tenon, bronze
PRPT6	Tenon adaptor, 6" round pole, to standard tenon, bronze
PSR4	Round to Square Adapter kit for 3", 4" and 5" round poles Separate gasket provided for each size pole.
LF-AD-SF	Slip onto pole top 2" Dim. fixture mounts directly on the side or top of the fixture
LF-AD-KNU	Fits over a standard tenon or bullhorn to adapt it to a 1/2" NPT threaded hub for knuckle fixtures
PSS4C	Pole cap polycarbonate
PSS3R	3" CenterBullhorn replacement cap
SFX-G10-SF-BK	SFX-G10 Series Slip-Fitter Adapter Black
SFX-G10-QCS	SFX-G10 Series Quick Clamp Adapter For Square Horizontal Bars

LFX-PASF



ACC-WM2

ACC-WM3

ACC-WM4


ACC-ACM

ACC-WMA

ACC-AWMA-BR

ACC-AWMA-BK

ACC-AWMA-GR

LF3-WMA

ACC-WPM20

WALL MOUNT ACCESSORIES

CATALOG NO.	DESCRIPTION
LF3-WMA	Wall mount plate bronze
LFX-PASF	Pole Adapter for Slip Fitter for LFX & LFX-XXL & LFXMAX & LFXPRO & LF4PRO Series, bronze
LFX-PASF-WH	Pole Adapter for Slip Fitter for LFX & LFX-XXL & LFXMAX & LFXPRO & LF4PRO Series, white
LFX-PASF-BK	Pole Adapter for Slip Fitter for LFX & LFX-XXL & LFXMAX & LFXPRO & LF4PRO Series, black
ACC-WM2	Wall mount bracket 90° curve bronze with 2" tenon to be used with Westgate slip fitter fixtures(-SF)
ACC-WM3	Wall mount bracket 90° bronze with 2" tenon to be used with Westgate slip fitter fixtures(-SF)
ACC-WM4	Wall mount bracket bronze with 2" tenon to be used with Westgate slip fitter fixtures (-SF)
ACC-ACM	Angled Wall Mount Arm, 2-3/8In Dia., Bronze
ACC-WMA-30-WH	Flood Light Wall-Mount- ing Arm 30", White
ACC-WMA-24-WH	Flood Light Wall-Mount- ing Arm 24", White
ACC-WMA-18-WH	Flood Light Wall-Mount- ing Arm 18", White
ACC-WMA-30-BR	Flood Light Wall-Mount- ing Arm 30", Bronze
ACC-WMA-24-BR	Flood Light Wall-Mount- ing Arm 24", Bronze
ACC-WMA-18-BR	Flood Light Wall-Mount- ing Arm 18", Bronze
ACC-WMA-30-BK	Flood Light Wall-Mount- ing Arm 30", Black
ACC-WMA-24-BK	Flood Light Wall-Mount- ing Arm 24", Black
ACC-WMA-18-BK	Flood Light Wall-Mount- ing Arm 18", Black
ACC-AWMA-BR	Architectural Wall Mount Arm For Post Top Lights, 2-3/8In Dia., Bronze
ACC-AWMA-BK	Architectural Wall Mount Arm For Post Top Lights, 2-3/8In Dia., Black
ACC-AWMA-GR	Architectural Wall Mount Arm For Post Top Lights, 2-3/8In Dia., Grey
ACC-WPM20	20In Wall And Pole Mounting Arm For Flood Lights With A Slip Fitter

PT2-180-R

PT2-180-S



PT3-180



PT3-120



PT4-090



PT4-180

BULLHORNS ACCESSORIES, BRONZE FINISH

CATALOG NO.	DESCRIPTION
PT2-180-R	Double in-line at 180°, 1'(H), 3' between centers
PT2-180-S	Square Pole Base Double in-line at 180°, 1'(H), 3' between centers, slips into 4" pole
PT3-120	Triple at 120°, 1' (H), 3'-5" between centers, slips on 2-3/8" tenon
PT3-180	Double in-line at 180°, 1'(H), 2'-7" between centers, slips on 2-3/8" pole
PT4-090	Quad at 90° 1'(H), 2'-10" between centers, slips on 2-3/8" tenon
PT4-180	Quad in-line at 180° 1(H), 2'-7", between centers, slips on 2-3/8" pole

PTA-190

PTA-290



PTA-2180

PTA-390

PTA-3120

PTA-490

BULLHORNS ACCESSORIES, BRONZE FINIS

CATALOG NO.	DESCRIPTION
PTA-190	90 degree round pole tenon adapter for 1 fixtures, slips into 2-3/8" pole
PTA-290	90 degree round pole tenon adapter for 2 fixture, slips into 2-3/8" pole
PTA-2180	180 degree round pole tenon adapter for 2 fixture,slips into 2-3/8" pole
PTA-390	90 degree round pole tenon adapter for 3 fixture,slips into 2-3/8" pole
PTA-3120	120 degree round pole tenon adapter for 3 fixture, slips into 2-3/8" pole
PTA-490	90 degree round pole tenon adapter for 4 fixture,slips into 2-3/8" pole

PSS4L1HTZ



PSS4T180HTZ



PSS4T90HTZ



PSS4TR90HTZ



PSS4Q90HTZ



PSS4Q90VTZ



PSS4TVTZ



PSS4TRVTZ

TENONS ACCESSORIES, BRONZE FINISH

CATALOG NO.	DESCRIPTION
PSS4L1HTZ	Square (single) horizontal tenon, bronze. goes inside 4" pole. No adaptor needed
PSS4T180HTZ	Square (twin) horizontal tenon,180°, bronze. goes inside 4" pole. No adaptor needed
PSS4TR90HTZ	Square (triple) horizontal tenon, 90°, bronze. goes inside 4" pole. No adaptor needed
PSS4T90HTZ	Square (twin) horizontal tenon,90°, bronze. goes inside 4" pole. No adaptor needed
PSS4Q90HTZ	Square (quad) horizontal tenon, 90°, bronze. Slips on 4" pole. (fits inside pole top)
PSS4Q90VTZ	4" 90° quad square vertical tenon. (fits inside pole top)
PSS4TVTZ	Twin square vertical tenon for 4" square pole. Two 2-3/8" vertical tenons. (fits inside pole top)
PSS4TRVTZ	Triple square vertical tenon for 4" square pole. Three 2-3/8" vertical tenons. (fits inside pole top)

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

TYPE	CATALOG NO.	POWDER COATING
WALL MOUNT/POLE/ADAPTER	LF3-WMA, ACC-WM2, ACC-WM3, ACC-WM4, PSS3SVTZ, PSS4SVTZ, PSS5SVTZ, PRPT3, PRPT4, PRPT5, PSR4, LF-AD-KNU, PSS4C	**OPT-CLR-35(BK/GR/SR/WH)**
BULLHORNS	PTA-190, PTA-290, PTA-2180, PTA-390, PTA-3120, PTA-490	**OPT-CLR-35(BK/GR/SR/WH)**
BULLHORNS	PT2-180-R,PT2-180-S,PT2-180, PT3-120, PT4-090, PT4-180	**OPT-CLR-60(BK/GR/SR/WH)**
TENONS	PSS4T180HTZ,PSS4T90HTZ, PSS4TR90HTZ, PSS4Q90HTZ	**OPT-CLR-40(BK/GR/SR/WH)**
TENONS	PSS4Q90VTZ, PSS4TVTZ, PSS4TRVTZ	**OPT-CLR-75(BK/GR/SR/WH)**

WPB-HM-ST


WPB-HM-DT

WPB-DB

WPB-SB

WPB-WA-SB-71

WPB-WA-SB-1013

WPB-WA-DB-710

WPB-WA-DB-101

WPB-WA-TB-710

WPB-WA-TB-1013

WPB-WA-QB-710

WPB-WA-QB-1013

WPB-FM-U

WPB-FM-H

WPB-FM-V


WPB-HM-DF

WPB-MA-2.5

WPB-MA-3

WPB-MA-4

WOOD POLES ACCESSORIES

CATALOG NO.	DESCRIPTION
WPB-HM-ST	Wood Pole Horizontal Single Tenon For Use With Slipfitter
WPB-HM-DT	Wood Pole Horizontal Double Tenon For Use With Slipfitter
WPB-DB	Wood Pole Single Bullhorn For Use With Slipfitter
WPB-SB	Wood Pole Double Bullhorn For Use With Slipfitter
WPB-WA-SB-710	7-10In Dia. Wood Pole Wraparound Bracket Single Bullhorn For Use With Slipfitter
WPB-WA-SB-1013	10-13In Dia. Wood Pole Wraparound Bracket Single Bullhorn For Use With Slipfitter
WPB-WA-DB-710	7-10In Dia. Wood Pole Wraparound Bracket Double Bullhorn For Use With Slipfitter
WPB-WA-DB-1013	10-13In Dia. Wood Pole Wraparound Bracket Double Bullhorn For Use With Slipfitter
WPB-WA-TB-710	7-10In Dia. Wood Pole Wraparound Bracket Triple Bullhorn For Use With Slipfitter
WPB-WA-TB-1013	10-13In Dia. Wood Pole Wraparound Bracket Triple Bullhorn For Use With Slipfitter
WPB-WA-QB-710	7-10In Dia. Wood Pole Wraparound Bracket Quad Bullhorn For Use With Slipfitter
WPB-WA-QB-1013	10-13In Dia. Wood Pole Wraparound Bracket Quad Bullhorn For Use With Slipfitter
WPB-FM-U	Wood Pole Universal Flood Mount
WPB-FM-H	Wood Pole Horizontal Flood Mount
WPB-FM-V	Wood Pole Vertical Flood Mount
WPB-HM-DF	Wood Pole Horizontal Mount Double Flood
WPB-MA-2.5	Wood Pole Mast Arm 2.5 Ft
WPB-MA-3	Wood Pole Mast Arm 3 Ft
WPB-MA-4	Wood Pole Mast Arm 4 Ft

PT-RB2

PT-RB3

POST-TOP ROSE BRANCHES WITH 1/2” INTERNAL THREAD FOR KNUCKLE-MT BULLET AND FLOOD

CATALOG NO.	DESCRIPTION
PT-RB2-BK	2 Post-Top Rose Branches With 1/2in Internal Thread For Knuckle-Mt Bullet And Flood Black
PT-RB2-BR	2 Post-Top Rose Branches With 1/2in Internal Thread For Knuckle-Mt Bullet And Flood Bronze
PT-RB3-BK	3 Post-Top Rose Branches With 1/2in Internal Thread For Knuckle-Mt Bullet And Flood Black
PT-RB3-BR	3 Post-Top Rose Branches With 1/2in Internal Thread For Knuckle-Mt Bullet And Flood Bronze

LF-THREAD

SPS-75

WRC-3-BRZ

HB-HOOK

OUTDOOR ACCESSORIES

CATALOG NO.	DESCRIPTION
LF-THREAD	1/2” hub adaptor for fixtures with trunnion bracket (on fixtures up to 50W)
WRC-3-BRZ	Weatherproof cover with three (3) 1/2” hubs
SPS-75	4” SQ. Swivel-type cover & 3/4” hub with 1/2” reducer
HB-HOOK	High Bay 2-1/2” heavy-duty Zinc Alloy hook with 1/2” steel locknut, set screw, cable bushing

SP10KV

10KV SURGE PROTECTION MODULE UL1449

CATALOG NO.	DESCRIPTION
SP10KV	SP10KV
SP10KV-480V	SP10KV-480V

ARCHITECTURAL OUTDOOR

TOL SERIES

TOL-A SERIES

LFXU SERIES

GPL SERIES

GPC SERIES

GPH SERIES

PML SERIES

DAB SERIES

GPX SERIES

GPX-CAT SERIES

GPX-PWM SERIES

GPE SERIES

GPA SERIES

POL SERIES


BOL-G8 SERIES

BOL-G7 SERIES

BOL-G5 SERIES

BOL-G4 SERIES

BOL-502 SERIES

BOL-700 SERIES

BOL-670 SERIES

BOL-608 SERIES

BOL-602 SERIES

BOL-505 SERIES

BOL-G2 SERIES

LCG SERIES

LCSB SERIES

LC800 SERIES

BPS SERIES

BOL-710 SERIES

BOL-800 SERIES

BOL-605 SERIES

WMS-POST SERIES

WSX SERIES

WSO SERIES

LRS-SWG SERIES

LRS-S SERIES

LRS-MC SERIES

TC-FL SERIES

WMC-UDL SERIES

DMX SERIES


SFX-G9 SERIES

DMX-CIGL SERIES

DMX-IGLC SERIES

WLF SERIES

GNB SERIES

GNBA SERIES

LRS-L SERIES

Search for the series name @WESTGATEMFG.COM

LRS-ML SERIES

LRS-M SERIES

LRS-P SERIES

LRS-H SERIES

LRS-E SERIES


LRS-J SERIES


LRS-O SERIES

WMQ5 SERIES

LMW SERIES



HNS SERIES

LVW SERIES

WMC SERIES

WMC4-CD SERIES

WMCL SERIES

WMCS SERIES

WMCSR SERIES

WMA SERIES

CRE SERIES

LDSC SERIES

LDS SERIES

LDS-RGBW SERIES

CREA SERIES

LRS-K SERIES

LRS-WS SERIES

LRS-R SERIES

LRS-S1 SERIES

LRS-SG SERIES

LDSS SERIES

LDSX SERIES

LRS-PV SERIES

LRS-A SERIES


LRS SERIES

LRS-SH SERIES

LDSL SERIES

LDSXL SERIES

LDSB SERIES

LRS-T SERIES

LRS-CR SERIES


LRS-Q SERIES

ERSH SERIES

LDSW SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

AREA & POST TOP



TOL-YOSEMITE | TOL SEQUOIA | TOL-KINGS | TOL-JOSHUA | TOL-REDWOOD

TREE OF LIGHT, A NATURAL DESIGNER LIGHT STRUCTURE FOR OPEN AREAS WESTGATE SIGNATURE

CATALOG NO.	DESCRIPTION			PCK QTY
TOL-YOSEMITE-BR	75W	125LM/W	30K/40K/50K - Bronze	1
TOL-SEQUOIA-BR	100W	125LM/W	30K/40K/50K - Bronze	1
TOL-KINGS-BR	150W	125LM/W	30K/40K/50K - Bronze	1
TOL-JOSHUA-BR	225W	125LM/W	30K/40K/50K - Bronze	1
TOL-REDWOOD-BR	275W	125LM/W	30K/40K/50K - Bronze	1
TOL-YOSEMITE-BK	75W	125LM/W	30K/40K/50K - Black	1
TOL-SEQUOIA-BK	100W	125LM/W	30K/40K/50K - Black	1
TOL-KINGS-BK	150W	125LM/W	30K/40K/50K - Black	1
TOL-JOSHUA-BK	225W	125LM/W	30K/40K/50K - Black	1
TOL-REDWOOD-BK	275W	125LM/W	30K/40K/50K - Black	1

WET LOCATIONS

TOL-A1-1L

TOL-A2-1L

TOL-A2-3L

TOL-A3-3L

TOL-A4-4L

TREE OF LIGHT POST TOP LIGHT BAR

CATALOG NO.	DESCRIPTION			PCK QTY
TOL-A1-1L-BR	25W	125LM/W	30K/40K/50K - Bronze	1
TOL-A2-1L-BR	25W	125LM/W	30K/40K/50K - Bronze	1
TOL-A2-3L-BR	75W	125LM/W	30K/40K/50K - Bronze	1
TOL-A3-3L-BR	75W	125LM/W	30K/40K/50K - Bronze	1
TOL-A4-4L-BR	100W	125LM/W	30K/40K/50K - Bronze	1
TOL-A1-1L-BK	25W	125LM/W	30K/40K/50K - Black	1
TOL-A2-1L-BK	25W	125LM/W	30K/40K/50K - Black	1
TOL-A2-3L-BK	75W	125LM/W	30K/40K/50K - Black	1
TOL-A3-3L-BK	75W	125LM/W	30K/40K/50K - Black	1
TOL-A4-4L-BK	100W	125LM/W	30K/40K/50K - Black	1

LFXU-90-150W Bronze

LFXU-25-75W Bronze

LFXU-90-150W-BK Black

LFXU-25-75W-BK Black

Shown with LFXU-UPG
POLE NOT INCLUDED



LFXU-25-75W-MCTP-PSR-BK
TWIN HEAD POLE NOT INCLUDED

SENSOR-READY PLUG & PLAY

WEC-3RC

WEC-3PR-78-AJ-WH
WEC-3PBT-78-AJ-WH

URBAN AREA AND ROADWAY LIGHT FOR 4" POLE, PHOTOCELL READY
WESTGATE SIGNATURE

CATALOG NO.	DESCRIPTION			PCK QTY
LFXU-25-75W-MCTP-PSR	25W/50W/75W	150LM/W	30K/40K/50K - Bronze	2
LFXU-25-75W-MCTP-PSR-BK	25W/50W/75W	150LM/W	30K/40K/50K - Black	2
LFXU-90-150W-MCTP-PSR	90W/100W/150W	150LM/W	30K/40K/50K - Bronze	2
LFXU-90-150W-MCTP-PSR-BK	90W/100W/150W	150LM/W	30K/40K/50K - Black	2
LFXU-LENS-TYPE2	LFXU Type 2 Replacement Lens			
LFXU-LENS-TYPE4	LFXU Type 4 Replacement Lens			
LFXU-UPG	Universal Pole Grabber Mounting For 4" Square And Round Poles			
LFXU-UPG-BK	Universal Pole Grabber Mounting For 4" Square And Round Poles, Black			
WEC-3PR-78-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level & RC (Optional RC WEC-3RC)			
WEC-3PBT-78-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level Bluetooth App Ready			

GPL-18-60W-MCTP

Shown with ACC-AWMA-BK
NOT INCLUDED

SPEC SERIES 17" MODERN LUCITE POST TOP, FITS ON 2 3/8" POLE POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GPL-18-60W-MCTP	18W/30W/45W/60W	140LM/W	30K/40K/50K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL	OPT-EM-GPL	INTERNAL

POWDER COATING
OPT-CLR-95(BK/GR/SR/WH)

PHOTOCELL	DESCRIPTION
OPT-LF3-PCK	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-GPL	WG NETWORK SENSOR
OPT-SEN-KEILTON-GPL	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

GPC-60-100W-MCTP

Shown With Frosted Lens

GPE-30-25-REDUCER

GPC-SH

Shown With OPT-GPC-APM

Shown With OPT-GPC-AWM

SPEC SERIES 24" X 14" SQ COACH POST TOP (FITS ON 3" OD PIPES/POLES)
POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GPC-60-100W-MCTP	60W/80W/100W	90LM/W	3000K/4000K/5000K - (Open Design)	1
GPC-SH	GPC House-Side Glare Shield			
GPE-30-25-REDUCER	Neck Reducer from 3" Inner Diameter to 2.5"			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	FROSTED GLASS	DESCRIPTION
ALL	OPT-GPC-GSF	4 SIDE
	OPT-GPC-GBF	BOTTOM ONLY

PC LENS	DESCRIPTION
OPT-GPC-PCLF	FROSTED
OPT-GPC-PCLC	CLEAR

WALL MOUNT
OPT-GPC-AWM

PHOTOCELL	DESCRIPTION
OPT-LF3-PCK	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-GPC	WG NETWORK SENSOR
OPT-SEN-KEILTON-GPC	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

PENDANT MOUNT
OPT-GPC-APM

PML-R14-MCT-DD-ORB

GPH-12-40W-MCTP-BK

GPH-12-40W-MCTP-GY

Shown with ACC-AWMA-GY

MODERN TOP-HAT POST-TOP AREA LIGHT WITH INDIRECT LIGHT SOURCE, CCT & WATTAGE SELECT FITS ON 2-3/8" POLES, SEE OPTION FOR 3" POLES BELOW

CATALOG NO.	DESCRIPTION			PCK QTY
GPH-12-40W-MCTP-BK	12W/20W/30W/40W	100LM/W	30K/40K/50K - 22" Dia X 20" H	1
GPH-12-40W-MCTP-BR	12W/20W/30W/40W	100LM/W	30K/40K/50K - 22" Dia X 20" H	1
GPH-12-40W-MCTP-GY	12W/20W/30W/40W	100LM/W	30K/40K/50K - 22" Dia X 20" H	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	3IN POLE ENTRY OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-GPH-3IN-BK	3IN POLE ENTRY Black	N/A	N/A
	OPT-GPH-3IN-BR	3IN POLE ENTRY Bronze	SENSOR	DESCRIPTION
	OPT-GPH-3IN-GY	3IN POLE ENTRY Gray	N/A	N/A
	POWDER COATING			
	N/A			

PML-BASE-R-ORB

ROUND LANTERN PIER MOUNT **120-277V** DUAL DIM, 14" W X 10" H

CATALOG NO.	DESCRIPTION			PCK QTY
PML-R14-MCT-DD-ORB	25W	2000LM	30K/40K/50K - Oil-Rubbed Bronze	1
PML-R14-MARBLE-LENS	Marbel-Pattern Resin Optional Replacement Lens For PML-R14			

PML-S-MCT-ORB

PML-M-MCT-ORB

PML-L-MCT-ORB

Shown with optional Honey Color Glass Lens (Field-installed)

PML-R-MCT-BR

PML-BASE-R-BK

PML-BASE-ORB

PML-V-MCT-ORB

PML-MCT-BK

PML-BASE-BK

SELECTABLE CCT PIER-MOUNT LIGHT **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
SELECTABLE CCT PIER-MOUNT LIGHTS, 120-277V				
PML-S-MCT-ORB	12W	345LM	30K/40K/50K	6
PML-M-MCT-ORB	15W	430LM	30K/40K/50K	4
PML-L-MCT-ORB	18W	460LM	30K/40K/50K	4
PML-S-HGLK	PML-S Honey Color Glass Replacement Lens Kit			
PML-M-HGLK	PML-M Honey Color Glass Replacement Lens Kit			
PML-L-HGLK	PML-L Honey Color Glass Replacement Lens Kit			
9" DIA. SELECTABLE CCT PIER-MOUNT LIGHTS, 120-277V				
PML-R-MCT-BR	12W	840LM	30K/40K/50K	4
PML-BASE-R-BK	Decorative Round Post And Pier Mounting Base, Black			
PML-BASE-R-ORB	Decorative Round Post And Pier Mounting Base, Oil-Rubbed Bronze			
8" ROUND SELECTABLE CCT PIER-MOUNT LIGHTS, 120V				
PML-V-MCT-ORB	12W	1500LM	30K/40K/50K	
SELECTABLE CCT PIER-MOUNT LIGHTS, 120V				
PML-MCT-BK	12W	1200LM	3000K/4000K/5000K	
PML-BASE-BK	Decorative Pier Mount Base For Post Top Lights - Black			

SENSOR-READY PLUG & PLAY

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

WEC-3PR-72-TLB-WH

WEC-3RC

DAB-A16

DAB-B20

DAB-B23

DAB-C25

DAB-BA

DAB-BA-CCK

Shown with DAB-WB-C
For Walls

DAB-PB-C
For Poles

Shown with DAB-PB-B
For Poles

Shown with DAB-WB-A
For Walls

Shown with 2 Fixtures 2 BA Arms A PA2-2 Pole Adapter
POLE NOT INCLUDED

Double DAB fixtures with DAB-PGB
installed on 4-inch light pole
POLE NOT INCLUDED

DAB-WB-D
For Walls

DAB-PB-D
For Poles

Shown with Shield

DAB-PA2-1
DAB-PA3-1
DAB-PA4-1

DAB-PA2-2
DAB-PA3-2
DAB-PA4-2

DESIGNER AREA BELL LIGHT SYSTEM (PHOTOCELL DISCONNECT SWITCH) SENSOR-READY

CATALOG NO.	DESCRIPTION			PCK QTY
DAB-A16-50-100W-MCTP-SR	50W/80W/100W	130LM/W	30K/40K/50K - 16" TYPE III, Black	1
DAB-B20-50-100W-MCTP-SR	50W/80W/100W	130LM/W	30K/40K/50K - 20" TYPE III, Black	1
DAB-B23-80-150W-MCTP-SR	80W/100W/150W	130LM/W	30K/40K/50K - 23" TYPE III, Black	1
DAB-C25-50-100W-MCTP-BK	50W/80W/100W	140LM/W	30K/40K/50K - 25" TYPE V, Black	1
DAB-C25-100-200W-MCTP-BK	100W/150W/200W	140LM/W	30K/40K/50K - 25" TYPE V, Black	1

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION
DAB-BA	DAB Bell Arm For Mounting On Single Or Double Pole Adapters, Black
DAB-BA-CCK	DAB Decorative Clip Kit For Two Dab-Ba Bell Arms, Two Clips
DAB-PB-B	DAB Decorative Straight Pole Bracket Model B, For Flat Or Round Poles, Black
DAB-PB-C	Dab Bent Decorative Pole-Mounting Bracket Model C, Black
DAB-PB-D	DAB Decorative Pole-Mounting Brackeet Model D, Black
DAB-WB-A	DAB Straight Wall Bracket Model A, Black
DAB-PA2-1	DAB 2 Inches Pole Adapter For 1 Bell Arm, Black
DAB-PA2-2	DAB 2 Inches Pole Adapter For 2 Bell Arms, Black
DAB-PA3-1	DAB 3 Inches Pole Adapter For 1 Bell Arm, Black
DAB-PA3-2	DAB 3 Inches Pole Adapter For 2 Bell Arms, Black
DAB-PA4-1	DAB 4 Inches Pole Adapter For 1 Bell Arm, Black
DAB-PA4-2	DAB 4 Inches Pole Adapter For 2 Bell Arms, Black
DAB-WB-C	DAB Bent Decorative Wall Bracket Model C, Black
DAB-WB-D	DAB Decorative Wall Bracket Model D, Black
DAB-PGB	Bell Fixture 24" Pole-Grabber Arm For 3" & 4" Round Poles
DAB-A16-SH	8" House Side Shield For DAB-A16
DAB-B20-SH	8" House Side Shield For DAB-B20
DAB-B23-SH	8" House Side Shield For DAB-B23
WEC-3MR-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Black, With Base (Optional Remote Control WEC-3RC)
WEC-3MBT-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base (Optional Remote Control WEC-3RC)
WEC-3PR-72-TLB-WH	600W Max, Zhaga 12-24VDC PIR Sensor, White, With Base (Optional Remote Control WEC-3RC)

GPX-A1 Single Arm for 2-3/8" Poles
POLE NOT INCLUDED

GPX-A2 Twin Arm for 2-3/8" Poles
POLE NOT INCLUDED

GPX DOUBLE ARM

GPX-BM Bell Mount for 2-3/8" Poles
POLE NOT INCLUDED

GPX-SF Slip fitter for 2-3/8" Poles
POLE NOT INCLUDED. TYPE 3 LENS

GPX-SF Slip fitter for 2-3/8" Poles
POLE NOT INCLUDED. TYPE 3 LENS

GPX-PWM Pole/Wall Mount
TYPE 3 LENS

GPX-CM
Ceiling Mount

GPX-PM75 Pipe Mount with 3/4"
Hub POLE NOT INCLUDED

GPX-PM75 Pipe Mount, Back View
POLE NOT INCLUDED

GPX-CM
Ceiling Mount, Back View

SPEC SERIES AREA/FLOOD LIGHT 120~277V, TYPE 5 LENS (TYPE 2 & TYPE 3 LENS ALSO AVAILABLE) MADE TO ORDER POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GPX-18-60W-MCTP-Q	18W/30W/45W/60W	150LM/W	30K/40K/50K	1
GPX-22-75W-MCTP-Q	22W/37W/56W/75W	150LM/W	40K/50K	1
GPX-90-150W-MCTP-Q	90W/120W/150W	150LM/W	30K/40K/50K	1
GPX-18-60W-MCTP-A1	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-A2	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-PWM	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-SF	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-BM	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-CM	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-PM75	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-22-75W-MCTP-A1	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1
GPX-22-75W-MCTP-A2	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1
GPX-22-75W-MCTP-PWM	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1
GPX-22-75W-MCTP-SF	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1
GPX-22-75W-MCTP-BM	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1
GPX-22-75W-MCTP-CM	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION			PCK QTY
GPX-22-75W-MCTP-PM75	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1
GPX-90-150W-MCTP-A1	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1
GPX-90-150W-MCTP-A2	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1
GPX-90-150W-MCTP-PWM	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1
GPX-90-150W-MCTP-SF	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1
GPX-90-150W-MCTP-BM	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1
GPX-90-150W-MCTP-CM	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1
GPX-90-150W-MCTP-PM75	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1

GPX-A1 Single Arm for 2-3/8" Poles
Black
POLE NOT INCLUDED

GPX-A2 Twin Arm for 2-3/8" Poles
Black
POLE NOT INCLUDED

GPX DOUBLE ARM
Black

GPX-BM Bell Mount for 2-3/8" Poles
Black
POLE NOT INCLUDED

GPX-PWM Pole/Wall Mount
Black
TYPE 3 LENS

GPX-PM75 Pipe Mount with 3/4" Hub
Black
POLE NOT INCLUDED

GPX-CM
Black
Ceiling Mount, Back View

GPX-SF Slip fitter for 2-3/8" Poles
Black
POLE NOT INCLUDED. TYPE 3 LENS

SPEC SERIES AREA/FLOOD LIGHT 120~277V, TYPE 5 LENS (TYPE 2 & TYPE 3 LENS ALSO AVAILABLE) MADE TO ORDER POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GPX-18-60W-MCTP-A1-BK	18W/30W/45W/60W	150LM/W	30K/40K/50K - Black	1
GPX-18-60W-MCTP-A2-BK	18W/30W/45W/60W	150LM/W	30K/40K/50K - Black	1
GPX-18-60W-MCTP-PWM-BK	18W/30W/45W/60W	150LM/W	30K/40K/50K - Black	1

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION			PCK QTY
GPX-18-60W-MCTP-SF-BK	18W/30W/45W/60W	150LM/W	30K/40K/50K - Black	1
GPX-18-60W-MCTP-BM-BK	18W/30W/45W/60W	150LM/W	30K/40K/50K - Black	1
GPX-18-60W-MCTP-CM-BK	18W/30W/45W/60W	150LM/W	30K/40K/50K - Black	1
GPX-18-60W-MCTP-PM75-BK	18W/30W/45W/60W	150LM/W	30K/40K/50K - Black	1
GPX-22-75W-MCTP-A1-BK	22W/37W/56W/75W	150LM/W	40K/50K - Black	1
GPX-22-75W-MCTP-A2-BK	22W/37W/56W/75W	150LM/W	40K/50K - Black	1
GPX-22-75W-MCTP-PWM-BK	22W/37W/56W/75W	150LM/W	40K/50K - Black	1
GPX-22-75W-MCTP-SF-BK	22W/37W/56W/75W	150LM/W	40K/50K - Black	1
GPX-22-75W-MCTP-BM-BK	22W/37W/56W/75W	150LM/W	40K/50K - Black	1
GPX-22-75W-MCTP-CM-BK	22W/37W/56W/75W	150LM/W	40K/50K - Black	1
GPX-22-75W-MCTP-PM75-BK	22W/37W/56W/75W	150LM/W	40K/50K - Black	1
GPX-90-150W-MCTP-A1-BK	90W/120W/150W	150LM/W	30K/40K/50K - Black	1
GPX-90-150W-MCTP-A2-BK	90W/120W/150W	150LM/W	30K/40K/50K - Black	1
GPX-90-150W-MCTP-PWM-BK	90W/120W/150W	150LM/W	30K/40K/50K - Black	1
GPX-90-150W-MCTP-SF-BK	90W/120W/150W	150LM/W	30K/40K/50K - Black	1
GPX-90-150W-MCTP-BM-BK	90W/120W/150W	150LM/W	30K/40K/50K - Black	1
GPX-90-150W-MCTP-CM-BK	90W/120W/150W	150LM/W	30K/40K/50K - Black	1
GPX-90-150W-MCTP-PM75-BK	90W/120W/150W	150LM/W	30K/40K/50K - Black	1
GPX-10W-SOLAR-A1-BK	10W	1700LM	30K/40K/50K - Black	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL	OPT-EM-GPX	INTERNAL	OPT-3MPC	ELECTRONIC
LENS OPTION		DESCRIPTION	SENSOR	DESCRIPTION
OPT-GPX-LENS-TYPE2S		TYPE 2S	OPT-SEN-3MR-3	BI-LEVEL MICROWAVE
OPT-GPX-LENS-TYPE3S		TYPE3S	OPT-SEN-NLS-GPX	WG NETWORK SENSOR
OPT-GPX-150W-LENS-TYPE3S		TYPE3S	OPT-SEN-KEILTON-GPX	KEILTON NETWORK SENSOR
OPT-GPX-LENS-FL		FROSTED GLASS LENS	WEC-8RC	REMOTE CONTROL
OPT-GPX-LENS-TYPE4		TYPE4		
POWDER COATING			480V OPTION	DESCRIPTION
OPT-CLR-95(BK/GR/SR/WH)			OPT-WP-480V	CHANGE VOLTAGE

GPX-CAT
Catenary Suspension Mount
SUSPENSION CABLE NOT INCLUDED

GPX-CAT-BK
Catenary Suspension Mount
SUSPENSION CABLE NOT INCLUDED

SCL-ASC-4MM-250FT
MOUNT ADAPTER

SCL-WRCL-DUPLEX

SCL-WRTH-14

SCL-TBJJ-14-4

SCL-WRCL-14

SCL-PEP-M8

SPEC SERIES AREA/FLOOD LIGHT POWER & CCT- ADJUSTABLE
120~277V, TYPE 3 LENS (TYPE 2 & TYPE 5 LENS ALSO AVAILABLE)

CATALOG NO.	DESCRIPTION			PCK QTY
GPX-18-60W-MCTP-CAT	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-22-75W-MCTP-CAT	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1
GPX-90-150W-MCTP-CAT	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-CAT-BK	18W/30W/45W/60W	150LM/W	30K/40K/50K - Black	1
GPX-22-75W-MCTP-CAT-BK	22W/37W/56W/75W	150LM/W	40K/50K - Black	1
GPX-90-150W-MCTP-CAT-BK	90W/120W/150W	150LM/W	30K/40K/50K - Black	1
SCL-WRCL-14	1/4In Galvanized Malleable Iron Wire Rope Clip			
SCL-TBJJ-14-4	1/4 X 4 Inch Jaw To Jaw Turnbuckle Galvanized Steel			
SCL-WRCL-DUPLEX	5/32In 4Mm Duplex 2-Post Wire Rope Clip Cable Clamp			
SCL-ASC-4MM-250FT	5/32In 4Mm Dia. Extra Duty Galvanized Aircraft Cable / Wire Rope 250Ft Roll			
SCL-WRTH-14	1/4In Galvanized Wire Rope Thimble			

WLF-24-40W-MCTP-BR-BA
Top-Of-Pole Mount Bell Arm Bronze

WLF-24-40W-MCTP-BK-BA
Top-Of-Pole Mount Bell Arm Black

12" DOME LIGHT WITH FLAT LENS 120-277V DUAL DIMMING, MADE TO ORDER

CATALOG NO.	DESCRIPTION		
WLF-24-40W-MCTP-BK-BA	24W/32W/40W	100LM/W	30K/40K/50K - Top-Of-Pole Mount Bell Arm
WLF-24-40W-MCTP-BR-BA	24W/32W/40W	100LM/W	30K/40K/50K - Top-Of-Pole Mount Bell Arm
DAB-BA-CCK	Decorative Clip Kit For Two Dab-Ba Bell Arms, Two Clips		
DAB-PA2-1	2 Inches Pole Adapter For 1 Bell Arm, Black		
DAB-PA2-2	2 Inches Pole Adapter For 2 Bell Arms, Black		
DAB-PA3-1	3 Inches Pole Adapter For 1 Bell Arm, Black		
DAB-PA3-2	3 Inches Pole Adapter For 2 Bell Arms, Black		
DAB-PA4-1	4 Inches Pole Adapter For 1 Bell Arm, Black		
DAB-PA4-2	4 Inches Pole Adapter For 2 Bell Arms, Black		

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL	OPT-EM-WLF	INTERNAL	OPT-PC-BUM	BUTTON
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-SEN-WLF	Be-LEVEL
			OPT-SEN-NLS-WLF	WG NETWORK SENSOR
			OPT-SEN-KEILTON-WLF	KEILTON NETWORK SENSOR

GPX-PWM Pole/Wall Mount

GPX-SF Slip fitter for 2-3/8" Poles

GPX-SF Slip fitter for 2-3/8" Poles

SPEC SERIES AREA/FLOOD LIGHT W/ PRE-INSTALLED MOUNTINGS 120~277V TYPE 3 LENS, MADE TO ORDER POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GPX-18-60W-MCTP-PWM	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-18-60W-MCTP-SF	18W/30W/45W/60W	150LM/W	30K/40K/50K - Bronze	1
GPX-22-75W-MCTP-PWM	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1
GPX-22-75W-MCTP-SF	22W/37W/56W/75W	150LM/W	40K/50K - Bronze	1
GPX-90-150W-MCTP-PWM	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1
GPX-90-150W-MCTP-SF	90W/120W/150W	150LM/W	30K/40K/50K - Bronze	1

FOR COLD-WEATHER EM OPTION SEE PAGE 527

GPE-60-100W-MCTP-BK

GPE-40-60W-MCTP
GPE-60-100W-MCTP

GPET-40-60W-MCTP
GPET-60-100W-MCTP
POLES IS NOT INCLUDED

GPE Folds For Shipment

GPE-30-25-REDUCER

GARDEN POST-TOP LIGHT, 120-277V POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION		
POWER & CCT- ADJUSTABLE GARDEN POST-TOP LIGHTS, 120-277V (FITS ON 3" OD PIPES/POLES)			
GPE-40-60W-MCTP	40W/50W/60W	130LM/W	30K/40K/50K - Bronze
GPE-60-100W-MCTP	60W/80W/100W	130LM/W	30K/40K/50K - Bronze
GPE-60-100W-MCTP-BK	60W/80W/100W	130LM/W	30K/40K/50K - Black
GPE-30-25-REDUCER	GPE Neck Reducer from 3" Inner Diameter to 2.5"		
POWER & CCT- ADJUSTABLE GARDEN POST-TOP LIGHTS, 120-277V, (FITS ON 2-3/8" OD PIPES/POLES) MADE TO ORDER			
GPET-40-60W-MCTP	40W/50W/60W	130LM/W	30K/40K/50K - Bronze
GPET-60-100W-MCTP	60W/80W/100W	130LM/W	30K/40K/50K - Bronze

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
GPE	OPT-EM-GPE	INTERNAL
GPET	OPT-EM-GPET	INTERNAL

POWDER COATING
OPT-CLR-95(BK/GR/SR/WH)

PHOTOCELL	DESCRIPTION
OPT-3MPC	ELECTRONIC

SENSOR	DESCRIPTION
OPT-SEN-3MR-3	BI-LEVEL MICROWAVE
OPT-SEN-NLS-GPE	WG NETWORK SENSOR
OPT-SEN-KEILTON-GPE	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

GPA-A37-80-150W-MCTP-BK

GPA-B32-80-150W-MCTP-BK

GPB-18-40-80W-MCTP-BK

GPA-A37-80-150W-MCTP-BK

GPA-A37 Shown With GPA-A37-DC-BK

GPA-A37 Shown With GPA-A37-DC-GD

GPA-B32 Shown With GPA-B32-DC-BK

GPA-B32 Shown With GPA-B32-DC-BK

Fixture Shown with Pole, POLE IS NOT INCLUDED

LED ACORN AREA LIGHT, FITS ON 3" OD PIPE/POLE WATTAGE & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
GPA-A37-80-150W-MCTP-BK	80W/100W/150W	135LM/W	30K/40K/50K - 37" H X 17" D	1
GPA-B32-80-150W-MCTP-BK	80W/100W/150W	135LM/W	30K/40K/50K - 32.5" H X 16" D	1
GPB-18-40-80W-MCTP-BK	40W/60W/80W	130LM/W	30K/40K/50K - Black	1
GPA-A37-DC-BK	GPA-A37 Decorative Cage Accessory Kit - Black			
GPA-A37-DC-GD	GPA-A37 Decorative Cage Accessory Kit - Black And Gold			
GPA-B32-DC-BK	GPA-B32 Decorative Cage Accessory Kit - Black			
GPA-B32-DC-GD	GPA-B32 Decorative Cage Accessory Kit - Black And Gold			
GPA-B32-RTC-GD	GPA-A37 And GPA-B32 Replacement Top Cap - Gold			
GPAB-WM-REDUCER-BK	GPA-A37 And GPA-B32 Reducer Sleeve For Installatoin On Wall And Mounting Arms.			

POL-D2-6FT-3PC-BR

POL-D2-6FT-3PC-BK

DECORATIVE 3-PIECE RESIDENTIAL POLE

CATALOG NO.	DESCRIPTION
POL-D2-6FT-3PC-BK	6FT Decorative Residential Pole 2in Top Black
POL-D2-6FT-3PC-BR	6FT Decorative Residential Pole 2in Top Bronze

3-PIECE POLE

POL-D1-ABK

POL-D1-BASECVR

DECORATIVE 3-PIECE LIGHT POLE

CATALOG NO.	DESCRIPTION
POL-D1-120-3PC-BK	120In Decorative Pole D1 Series, 3Pc, 2.36In Tenon, Black
POL-D1-120-3PC-BR	120In Decorative Pole D1 Series, 3Pc, 2.36In Tenon, Bronze
POL-D1-144-3PC-BK	144In Decorative Pole D1 Series, 3Pc, 2.36In Tenon, Black
POL-D1-144-3PC-BR	144In Decorative Pole D1 Series, 3Pc, 2.36In Tenon, Bronze
POL-D1-ABK	D1 Series Pole Anchor Bolt Kit 9/16 (M14)
POL-D1-BASECVR-BR	D1 Series Pole 2-Pc Cube Base Cover, Bronze
POL-D1-BASECVR-BK	D1 Series Pole 2-Pc Cube Base Cover, Black

PATHWAY & BOLLARD

BOL-100Q-BK

BOL-100Q-BK-WH

BOL-100Q-BR

BOL-100Q-BR-WH

BOL-200-BK-CH

BOL-200-BK-WH

BOL-200-BR-WH





ANCHOR BOLTS & MOUNTING PLATE SOLD SEPARATELY

G8 SQUARE 4-ZONE QUADRANT MODULAR BOLLARD SYSTEM POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-G8-100Q-MCTP-BK-WH	10W/18W/25W	80LM/W	30K/40K/50K - Head 4-Zone Quadrant, White Reflector, BK	1
BOL-G8-100Q-MCTP-BR-WH	10W/18W/25W	80LM/W	30K/40K/50K - Head 4-Zone Quadrant, White Reflector, BR	1
BOL-G8-100Q-MCTP-BK	10W/18W/25W	80LM/W	30K/40K/50K - Head 4-Zone Quadrant, Chrome Reflector, BK	1
BOL-G8-100Q-MCTP-BR	10W/18W/25W	80LM/W	30K/40K/50K - Head 4-Zone Quadrant, Chrome Reflector, BR	1
BOL-G8-200-MCTP-BK-WH	10W/18W/25W	80LM/W	30K/40K/50K - Head Square, White Reflector, BK	1
BOL-G8-200-MCTP-BR-WH	10W/18W/25W	80LM/W	30K/40K/50K - Head Square, White Reflector, BR	1
BOL-G8-200-MCTP-BK-CH	10W/18W/25W	80LM/W	30K/40K/50K - Head Square, Chrome Reflector, BK	1
BOL-G8-200-MCTP-BR-CH	10W/18W/25W	80LM/W	30K/40K/50K - Head Square, Chrome Reflector, BR	1
BOL-G8-SHAFT-10-BK	G8 Bollard 10in Shaft Black			

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION
BOL-G8-SHAFT-10-BR	G8 Bollard 10in Shaft Bronze
BOL-G8-SHAFT-20-BK	G8 Bollard 20in Shaft Black
BOL-G8-SHAFT-20-BR	G8 Bollard 20in Shaft Bronze
BOL-G8-SHAFT-26-BK	G8 Bollard 26in Shaft Black
BOL-G8-SHAFT-26-BR	G8 Bollard 26in Shaft Bronze
BOL-G8-SHAFT-34-BK	G8 Bollard 34in Shaft Black
BOL-G8-SHAFT-34-BR	G8 Bollard 34in Shaft Bronze
BOL-G8-ABK	G8 Bollard Anchor Bolt Kit
BOL-G8-200-REFL-CH	Bol-G8-200 Chrome Reflector Accessory
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)

BOL-G7-100D-MCTP

ANCHOR BOLTS & MOUNTING PLATE
SOLD SEPARATELY

G7 EXTERNAL-LOUVER MODULAR BOLLARD SYSTEM

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-G7-100D-MCTP-BK	10W/18W/25W	100LM/W	30K/40K/50K - Black, Head	1
BOL-G7-100D-MCTP-BR	10W/18W/25W	100LM/W	30K/40K/50K - Bronze, Head	1
BOL-G7-100D-MCTP-SIL	10W/18W/25W	100LM/W	30K/40K/50K - Silver, Head	1
BOL-G7-SHAFT-31-BK	BOL-G7 Shaft 31in, Black			
BOL-G7-SHAFT-31-BR	BOL-G7 Shaft 31in, Bronze Ral8019			
BOL-G7-SHAFT-31-SIL	BOL-G7 Shaft 31in, Silver Ral9006			
BOL-G7-SHAFT-19-BK	BOL-G7 Shaft 19in, Black			
BOL-G7-SHAFT-19-BR	BOL-G7 Shaft 19in, Bronze Ral8019			
BOL-G7-SHAFT-19-SIL	BOL-G7 Shaft 19in, Silver Ral9006			
BOL-G7-SHAFT-14-BK	BOL-G7 Shaft 14in, Black			
BOL-G7-SHAFT-14-BR	BOL-G7 Shaft 14in, Bronze Ral8014			
BOL-G7-SHAFT-14-SIL	BOL-G7 Shaft 14in, Silver Ral9006			
BOL-G7-SHAFT-9-BK	BOL-G7 Shaft 9in, Black			
BOL-G7-SHAFT-9-BR	BOL-G7 Shaft 9in, Bronze Ral8019			
BOL-G7-SHAFT-9-SIL	BOL-G7 Shaft 9in, Silver Ral9006			
BOL-G7-ABK	BOL-G7 Anchor Bolt Kit			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

FOR OPT OPTION SEE PAGE 128

BOL-G5-101 + BOL-G5-SHAFT

BOL-G5-401 + BOL-G5-SHAFT

BOL-G5-ABK-R
Anchor Bolts &
Mounting Plate

HEAD, SHAFT & ANCHOR BOLTS SET
SOLD SEPARATELY

ROUND WESTGATE MODERN MODULAR BOLLARD SYSTEM G5

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-G5-101-MCTP-BK	8W/13W/18W/25W	130LM/W	30K/40K/50K - Black, Head	1
BOL-G5-101-MCTP-BR	8W/13W/18W/25W	130LM/W	30K/40K/50K - Bronze, Head	1
BOL-G5-401-MCTP-BK	5W/8W/12W/15W	130LM/W	30K/40K/50K - Black, Head	1
BOL-G5-401-MCTP-BR	5W/8W/12W/15W	130LM/W	30K/40K/50K - Bronze, Head	1
BOL-G5-SHAFT-14-BK	G5 Bollard Shaft 14 Inch, Black			
BOL-G5-SHAFT-14-BR	G5 Bollard Shaft 14 Inch, Bronze			
BOL-G5-SHAFT-33-BK	G5 Bollard Shaft 33 Inch, Black			
BOL-G5-SHAFT-33-BR	G5 Bollard Shaft 33 Inch, Bronze			
BOL-G5-ABK-R	G5 Bollard Round Anchor Bolts & Mounting Plate			
BOL-G5-GSH-01	G5 Bollard 180-Degree Glare Shield			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

FOR OPT OPTION SEE PAGE 128

BOL-G5-SOLAR-MCT



BOL-G5-ABK-R
Anchor Bolts &
Mounting Plate

HEAD, SHAFT & ANCHOR BOLTS SET
SOLD SEPARATELY

SOLAR WESTGATE MODERN MODULAR BOLLARD SYSTEM G5

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-G5-SOLAR-MCT-BK	4W	600LM	30K/40K/50K - Black, Head	1
BOL-G5-SOLAR-MCT-BR	4W	600LM	30K/40K/50K - Bronze, Head	1
BOL-G5-SHAFT-14-BK	G5 Bollard Shaft 14 Inch, Black			
BOL-G5-SHAFT-14-BR	G5 Bollard Shaft 14 Inch, Bronze			
BOL-G5-SHAFT-33-BK	G5 Bollard Shaft 33 Inch, Black			
BOL-G5-SHAFT-33-BR	G5 Bollard Shaft 33 Inch, Bronze			
BOL-G5-ABK-R	G5 Bollard Round Anchor Bolts & Mounting Plate			
BOL-G5-GSH-01	G5 Bollard 180-Degree Glare Shield			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

FOR OPT OPTION SEE PAGE 128

BOL-G4-201 + BOL-G4-SHAFT

Shown with GFCI Shaft

BOL-G4-ABK-R
Anchor Bolts &
Mounting Plate

HEAD, SHAFT & ANCHOR BOLTS SET
SOLD SEPARATELY

G4 ROUND MODULAR BOLLARD SYSTEM

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-G4-201-MCTP-BK	7W/14W/22W	110LM/W	30K/40K/50K - Black, Head	1
BOL-G4-201-MCTP-BR	7W/14W/22W	110LM/W	30K/40K/50K - Bronze, Head	1
BOL-G4-SHAFT-14-BK	G5 Bollard Shaft 14 Inch, Black			
BOL-G4-SHAFT-14-BR	G5 Bollard Shaft 14 Inch, Bronze			
BOL-G4-SHAFT-30-BK	G5 Bollard Shaft 33 Inch, Black			
BOL-G4-SHAFT-30-BR	G5 Bollard Shaft 33 Inch, Bronze			
BOL-G4-SHAFT-23-GFCI-BK	G4 Bollard Shaft 23 Inch With GFCI Outlet Compartment, Black			
BOL-G4-SHAFT-23-GFCI-BR	G4 Bollard Shaft 23 Inch With GFCI Outlet Compartment, Bronze			
BOL-G4-SHAFT-30-GFCI-BK	G4 Bollard Shaft 30 Inch With GFCI Outlet Compartment, Black			
BOL-G4-SHAFT-30-GFCI-BR	G4 Bollard Shaft 30 Inch With GFCI Outlet Compartment, Bronze			
BOL-G4-ABK-R	G4 Bollard Round Anchor Bolts & Mounting Plate			
BOL-G4-GSH-01-BK	Glare Shield Accessory - Black			
BOL-G4-GSH-01-BR	Glare Shield Accessory - Bronze			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

FOR OPT OPTION SEE PAGE 128

BOL-G4-301-SOLAR + BOL-G4-SHAFT

HEAD, SHAFT & ANCHOR BOLTS SET
SOLD SEPARATELY

BOL-G4-SOLAR-RC
Remote Control

BOL-G4-ABK-R
Anchor Bolts &
Mounting Plate

SOLAR G4 MODULAR BOLLARD SYSTEM

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-G4-301-SOLAR-30K-BK	3W	130LM/W	3000K - Black Head	1
BOL-G4-301-SOLAR-40K-BK	3W	130LM/W	4000K - Black Head	1
BOL-G4-301-SOLAR-30K-BR	3W	130LM/W	3000K - Bronze Head	1
BOL-G4-301-SOLAR-40K-BR	3W	130LM/W	4000K - Bronze Head	1
BOL-G4-SHAFT-14-BK	G4 Bollard Shaft 14 Inch, Black			
BOL-G4-SHAFT-14-BR	G4 Bollard Shaft 14 Inch, Bronze			
BOL-G4-SHAFT-30-BK	G4 Bollard Shaft 30 Inch, Black			
BOL-G4-SHAFT-30-BR	G4 Bollard Shaft 30 Inch, Bronze			
BOL-G4-ABK-R	G4 Bollard Round Anchor Bolts & Mounting Plate			
BOL-G4-GSH-01-BK	G4 Bollard Round Anchor Bolts & Mounting Plate, Black			
BOL-G4-GSH-01-BR	G4 Bollard Round Anchor Bolts & Mounting Plate, Bronze			
BOL-G4-SOLAR-RC	Remote Control, Required 1 Per Projects			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

FOR OPT OPTION SEE PAGE 128

BOL-502-9-MCT 9"

BOL-502-32-MCT 32"

BOL-502-ABK
Anchor Bolts & Mounting Plate

RECTANGULAR PATH-LIGHT BOLLARD, 3CCT, 4-3/4" X 3-3/8"

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-502-9-MCT-BK	10W	100LM/W	30K/40K/50K - 9in Black	1
BOL-502-9-MCT-BR	10W	100LM/W	30K/40K/50K - 9in Bronze	1
BOL-502-32-MCT-BK	10W	100LM/W	30K/40K/50K - 32in Black	1
BOL-502-32-MCT-BR	10W	100LM/W	30K/40K/50K - 32in Bronze	1
BOL-502-ABK	BOL-502 Series Anchor Bolt Kit			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

FOR OPT OPTION SEE PAGE 128

BOL-700-BK

BOL-700-BR

BOL-700-SIL

BOL-700-ABK
Anchor Bolts & Mounting Plate

GLARE-FREE PATH BOLLARD POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-700-20-MCTP-BK	6W/12W	100LM/W	30K/40K/50K - 20" Black	1
BOL-700-20-MCTP-BR	6W/12W	100LM/W	30K/40K/50K - 20" Bronze	1
BOL-700-20-MCTP-SIL	6W/12W	100LM/W	30K/40K/50K - 20" Silver	1
BOL-700-37-MCTP-BK	10W/15W/20W	100LM/W	30K/40K/50K - 37" Black	1
BOL-700-37-MCTP-BR	10W/15W/20W	100LM/W	30K/40K/50K - 37" Bronze	1
BOL-700-37-MCTP-SIL	10W/15W/20W	100LM/W	30K/40K/50K - 37" Silver	1
BOL-700-ABK	BOL-700 Series Anchor Bolt Kit			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			



BOL-670-32-MCTP-BK



BOL-670-32-MCTP-BR

SQUARE REGRESSED ALL-LENS BOLLARD SELECTABLE POWER & CCT

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
BOL-670-32-MCTP-BR	14W/19W/24W	85LM/W	27K/30K/35K/40K/50K - Bronze	1
BOL-670-32-MCTP-BK	14W/19W/24W	85LM/W	27K/30K/35K/40K/50K - Black	1
BOL-670-LPE-12-BR	BOL-670 12.12in Light-Pole Base For Total Height Of 43.7in - Bronze			
BOL-670-LPE-12-BK	BOL-670 12.12in Light-Pole Base For Total Height Of 43.7in - Black			
BOL-670-LPE-22-BR	BOL-670 22in Light-Pole Base For Total Height Of 53.6in - Bronze			
BOL-670-LPE-22-BK	BOL-670 22in Light-Pole Base For Total Height Of 53.6in - Black			
BOL-670-LPE-39-BR	BOL-670 39.33in Light-Pole Base For Total Height Of 71in - Bronze			
BOL-670-LPE-39-BK	BOL-670 39.33in Light-Pole Base For Total Height Of 71in - Black			
BOL-ABK-S	BOL-670 Anchor Bolt Kit			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

BOL-608-26-S-MCTP

BOL-608-32-S-MCTP

BOL-608-ABK
Anchor Bolts & Mounting Plate

BOL-608RD-16-MCTP

BOL-608RD-41-MCTP

BOL-608R-ABK
Anchor Bolts & Mounting Plate

SQUARE OR ROUND BOLLARD OPEN DESIGN POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
SQUARE BOLLARD OPEN DESIGN, POWER AND CCT ADJUSTABL, 6-3/4" X 6-3/4"				
BOL-608-32-S-MCTP-BK	10W/18W/25W	100LM/W	30K/40K/50K - 32in Black	1
BOL-608-32-S-MCTP-BR	10W/18W/25W	100LM/W	30K/40K/50K - 32in Bronze	1
BOL-608-26-S-MCTP-BK	10W/18W/25W	100LM/W	30K/40K/50K - 26in Black	1
BOL-608-26-S-MCTP-BR	10W/18W/25W	100LM/W	30K/40K/50K - 26in Bronze	1
BOL-608-ABK	BOL-608-S Anchor Bolts And Mounting Plate			
ROUND BOLLARD OPEN DESIGN, POWER AND CCT ADJUSTABLE, 4-1/3"				
BOL-608RD-41-MCTP-BK	10W/18W/25W	100LM/W	30K/40K/50K - 41in Black	1
BOL-608RD-41-MCTP-BR	10W/18W/25W	100LM/W	30K/40K/50K - 41in Bronze	1
BOL-608RD-16-MCTP-BK	10W/18W/25W	100LM/W	30K/40K/50K - 16in Black	1
BOL-608RD-16-MCTP-BR	10W/18W/25W	100LM/W	30K/40K/50K - 16in Bronze	1
BOL-608R-ABK	BOL-608R Anchor Bolts And Mounting Plate			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

FOR OPT OPTION SEE PAGE 128

BOL-602-26-S-MCTP

BOL-602-40-S-MCTP

BOL-602-40-S-RGBW

BOL-602-ABK
Anchor Bolts & Mounting Plate

Remote Control

SQUARE BOLLARD LONG LENS POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
SQUARE BOLLARD LONG LENS, POWER AND CCT ADJUSTABLE				
BOL-602-40-S-MCTP-BK	10W/18W/25W	100LM/W	35K/40K/50K - 40in Black	1
BOL-602-40-S-MCTP-BR	10W/18W/25W	100LM/W	35K/40K/50K - 40in Bronze	1
BOL-602-26-S-MCTP-BK	10W/18W/25W	100LM/W	35K/40K/50K - 26in Black	1
BOL-602-26-S-MCTP-BR	10W/18W/25W	100LM/W	35K/40K/50K - 26in Bronze	1
WG SMART APP COMPATIBLE RGBW SQUARE BOLLARD LONG LENS, POWER AND CCT ADJUSTABLE				
BOL-602-40-S-RGBW-BK	34W		RGBW - 40in Black	
BOL-602-40-S-RGBW-BR	34W		RGBW - 40in Bronze	
BOL-602-ABK	BOL-602 Anchor Bolts And Mounting Plate			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

FOR REMOTE CONTROL SEE PAGE 523

BOL-505-26-MCT

BOL-505-40-MCT

BOL-505-ABK
Anchor Bolts & Mounting Plate

ROUND PATH-LIGHT BOLLARD, 4-3/4" DIAMETER

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-505-26-MCT-BK	15W	100LM/W	30K/40K/50K - 26in Black	1
BOL-505-26-MCT-BR	15W	100LM/W	30K/40K/50K - 26in Bronze	1
BOL-505-40-MCT-BK	15W	100LM/W	30K/40K/50K - 40in Black	1
BOL-505-40-MCT-BR	15W	100LM/W	30K/40K/50K - 40in Bronze	1
BOL-505-ABK	BOL-505 Series Anchor Bolt Kit			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	GFCI OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
ALL MODELS	OPT-BOL-GFCI	GFCI	OPT-TRS-T20	Tamper Resistant Screw
	POWDER COATING		LOCK OPTION	DESCRIPTION
	OPT-CLR-95(BK/GR/SR/WH)		OPT-BOL-LOCK	LOCK

BOL-G2-102F | BOL-G2-103D | BOL-G2-103F | BOL-G2-107D | BOL-G2-107F | BOL-G2-118 | BOL-G2-135 4-ZONE | BOL-G2-135 | BOL-G2-140

BOL-G2-103 | BOL-G2-103 | BOL-G2-102F

Anchor Bolts & Mounting Plate
SOLD SEPARATELY

ROUND WESTGATE MODULAR BOLLARD SYSTEM G2

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-G2-135-4Z-MCTP-BR	Head - 14W/19W/24W	100LM/W	30K/40K/50K - Bronze	1
BOL-G2-135-4Z-MCTP-BK	Head - 14W/19W/24W	100LM/W	30K/40K/50K - Black	1
BOL-G2-102F-MCTP-BK	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Black, Head	4
BOL-G2-102F-MCTP-BR	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Bronze, Head	4
BOL-G2-103F-MCTP-BK	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Black, Head	4
BOL-G2-103F-MCTP-BR	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Bronze, Head	4
BOL-G2-107F-MCTP-BK	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Black, Head	4
BOL-G2-107F-MCTP-BR	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Bronze, Head	4
BOL-G2-103D-MCTP-BK	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Black, Head	4
BOL-G2-103D-MCTP-BR	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Bronze, Head	4
BOL-G2-107D-MCTP-BK	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Black, Head	4
BOL-G2-107D-MCTP-BR	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Bronze, Head	4
BOL-G2-118-MCTP-BK	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Black, Head	4
BOL-G2-118-MCTP-BR	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Bronze, Head	4
BOL-G2-135-MCTP-BK	4-Zone Head - 14W/19W/24W	125LM/W	30K/40K/50K - Black, Head	4
BOL-G2-135-MCTP-BR	4-Zone Head - 14W/19W/24W	125LM/W	30K/40K/50K - Bronze, Head	4
BOL-G2-140-MCTP-BK	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Black, Head	4
BOL-G2-140-MCTP-BR	Head - 14W/19W/24W	125LM/W	30K/40K/50K - Bronze, Head	4
BOL-G2-SHAFT-31-BK	G2 Bollard Shaft 31 Inch, Black			
BOL-G2-SHAFT-31-BR	G2 Bollard Shaft 31 Inch, Bronze			
BOL-G2-SHAFT-19-BK	G2 Bollard Shaft 19 Inch, Black			
BOL-G2-SHAFT-19-BR	G2 Bollard Shaft 19 Inch, Bronze			
BOL-G2-SHAFT-14-BK	G2 Bollard Shaft 14 Inch, Black			
BOL-G2-SHAFT-14-BR	G2 Bollard Shaft 14 Inch, Bronze			
BOL-G2-SHAFT-9-BK	G2 Bollard Shaft 9 Inch, Black			
BOL-G2-SHAFT-9-BR	G2 Bollard Shaft 9 Inch, Bronze			
BOL-G2-ABK-R	G2 Bollard Round Replacement Anchor Bolts & Mounting Plate			
BOL-G2-102F-CR-WH	G2 Bollard Head 102F Replacement Cone Reflector, White			
BOL-G2-103-LAK-BK	G2 Bollard Louver Kit For Model 103, Black			
BOL-G2-103-LAK-BR	G2 Bollard Louver Kit For Model 103, Bronze			
BOL-R-ACC-FL	Field-installed replacement frosted lens			
BOL-G2-SH180-BR	180-Degree Glare Shield For BOL-G2-103 And 107 Bronze			
BOL-G2-SH180-BK	180-Degree Glare Shield For BOL-G2-103 And 107 Black			

BOL-42-R-L-C-MCTP-BK

BOL-42-S-C-C-MCTP-BK

Anchor Bolts & Mounting Plate Included

WHILE SUPPLIES LAST

ROUND AND SQUARE BOLLARD, 120-277VAC, 30K/40K/50K ADJUSTABLE POWER 14~24W & CCT
MADE TO ORDER

CATALOG NO.	DESCRIPTION	PCK QTY
BOL-42-S-C-C-MCTP-BK	Bollard 42In Square Flat Top Cone Clear Lens, Black,, 6" SQ	1
BOL-42-S-C-C-MCTP-BR	Bollard 42In Square Flat Top Cone Clear Lens, Bronz,, 6" SQ	1
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)	

BOL-RP-BR

11.5" UNIVERSAL BOLLARD RETROFIT PLATE KIT

CATALOG NO.	DESCRIPTION
BOL-RP-BR	11.5In Universal Bollard Retrofit Plate Kit Bronze
BOL-RP-BK	11.5In Universal Bollard Retrofit Plate Kit Black

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-EM-BOL	INTERNAL	OPT-PC-B	BUTTON
SHIELD OPTION		DESCRIPTION	SENSOR	DESCRIPTION
OPT-BOL-SH1		Shield	OPT-SEN-WMC	MICROWAVE BI-LEVEL
POWDER COATING			OPT-SEN-NLS-BOL	WG NETWORK SENSOR
OPT-CLR-95(BK/GR/SR/WH)			OPT-SEN-KEILTON-BOL	KEILTON NETWORK SENSOR

LCG6-10FT-48

LCG4-8FT-48

LCG6-4FT-24

LCG4-6FT-24

ARCHITECTURAL MODULAR LIGHT COLUMN

CATALOG NO.	DESCRIPTION			PCK QTY
LCG4-6FT-24-MCTP-BK	21W/28W/35W	110LM/W	30K/40K/50K - Black, 4.73in X 6FT	1
LCG4-8FT-48-MCTP-BK	45W/60W/75W	110LM/W	30K/40K/50K - Black, 4.73in X 8FT	1
LCG6-4FT-24-MCTP-BK	21W/28W/35W	110LM/W	30K/40K/50K - Black, 6.3in X 4FT	1
LCG6-10FT-48-MCTP-BK	45W/60W/75W	110LM/W	30K/40K/50K - Black, 6.3in X 10FT	1
LCG4-ABK	LCG4 Anchor Bolt Kit			
LCG6-ABK	LCG6 Anchor Bolt Kit For 4Ft And 5Ft			
LCG6H-ABK	LCG6 6Ft And Taller Anchor Bolt Kit			

LCSB-7FT-MCT-BR

LCSB-7FT-MCT-BK

DECORATIVE LIGHT COLUMN, ETL - WET - MCT, 5FT & 7FT

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER	
LCSB-5FT-MCT-BK	40W		30K/40K/50K - Black
LCSB-5FT-MCT-BR	40W		30K/40K/50K - Bronze
LCSB-7FT-MCT-BK	40W		30K/40K/50K - Black
LCSB-7FT-MCT-BR	40W		30K/40K/50K - Bronze
LCSB-ABK	LCSB Light Column Series Anchor Bolt Kit		



LC800-7FT-MCT

LIGHT COLUMN BOLLARD 7FT

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PKG. QTY.	PCK QTY
LC800-7FT-MCT-BK	30W	2165LM		30K/40K/50K - Black	1
LC800-7FT-MCT-BR	30W	2165LM		30K/40K/50K - Bronze	1
LC800-ABK	LC800 Light Column Series Anchor Bolt Kit				

BPS-BASE

Example Usages

LIGHTED COLUMN SYSTEM - 10FT MAX

CATALOG NO.	DESCRIPTION	PCK QTY
BPS-BASE-2FT	Bollard Pole System 2Ft Base	2
BPS-BASE-3FT	Bollard Pole System 3Ft Base	2
BPS-BASE-5FT	Bollard Pole System 5Ft Base	2
BPS-LH1	Bollard Pole System Single Lamp Holder Section 1Ft With 1/2" Hub	4
BPS-LH2	Bollard Pole System Double Lamp Holder Section 1Ft With 1/2" Hubs	4
BPS-EP-1FT	Bollard Pole System 1Ft Extension Pole	4
BPS-EP-2FT	Bollard Pole System 2Ft Extension Pole	4
BPS-LHT	Bollard Pole System Top Cap Lamp Holder With 1/2" Hub	50

BOL-710-16-MCTP

BOL-710-32-MCTP

BOL-710T-32-MCTP

ARCHITECTURAL REVERSE LIGHT BOLLARD SELECTABLE CCT & POWER

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-710-16-MCTP-BK	12W/16W/20W	100LM/W	30K/40K/50K - Black	1
BOL-710-16-MCTP-BR	12W/16W/20W	100LM/W	30K/40K/50K - Bronze	1
BOL-710-26-MCTP-BK	12W/16W/20W	100LM/W	30K/40K/50K - Black	1
BOL-710-26-MCTP-BR	12W/16W/20W	100LM/W	30K/40K/50K - Bronze	1
BOL-710-32-MCTP-BK	12W/16W/20W	100LM/W	30K/40K/50K - Black	1
BOL-710-32-MCTP-BR	12W/16W/20W	100LM/W	30K/40K/50K - Bronze	1
BOL-710T-32-MCTP-BK	12W/16W/20W	82LM/W	30K/40K/50K - Black	1
BOL-710T-32-MCTP-BR	12W/16W/20W	82LM/W	30K/40K/50K - Bronze	1
BOL-710-ABK	BOL-710 Anchor Bolt Kit			
BOL-710-SMB-BK	BOL-710 Surface-Mounting Base Bk			
BOL-710-SMB-BR	BOL-710 Surface-Mounting Base Br			
BOL-710-SMB-ABK	BOL-710 Anchor Bolt Kit For Surface-Mounting Base			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

Anchor Bolts & Mounting Plate Included

BOL-800-24-MCTP-BK

SYMMETRICAL PATH BOLLARD, 3CCT

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-800-24-MCTP-BK	10W/15W/20W	80LM/W	30K/40K/50K - 24" Black	1
BOL-800-24-MCTP-BR	10W/15W/20W	80LM/W	30K/40K/50K - 24" Bronze	1
BOL-800-24-MCTP-SIL	10W/15W/20W	80LM/W	30K/40K/50K - 24" Silver	1
BOL-800-42-MCTP-BK	10W/15W/20W	80LM/W	30K/40K/50K - 42" Black	1
BOL-800-42-MCTP-BR	10W/15W/20W	80LM/W	30K/40K/50K - 42" Bronze	1
BOL-800-42-MCTP-SIL	10W/15W/20W	80LM/W	30K/40K/50K - 42" Silver	1
BOL-800-ABK	BOL-800 Series Anchor Bolt Kit			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

BOL-605-ABK
Anchor Bolts & Mounting Plate

BOL-605-33-S-RP-MCT-BK

BOL-605-33-S-RP-MCT-BR

DECORATIVE SQUARE BOLLARDS WITH RAIN PATTERN, 3CCT

CATALOG NO.	DESCRIPTION			PCK QTY
BOL-605-33-S-RP-MCT-BK	25W	100LM/W	30K/40K/50K - 33" Black	1
BOL-605-33-S-RP-MCT-BR	25W	100LM/W	30K/40K/50K - 33" Bronze	1
BOL-605-ABK	BOL-605 Series Anchor Bolt Kit			
BOL-EBK4-M10	Set Of 4 Expansion Bolts 3/8 X 4 Inches (M10 X 100mm)			

WMS-POST1-18

WMS-POST1-36

POST FOR WMS, LMW, LWA-12W, LWAX-12W SERIES

CATALOG NO.	DESCRIPTION
WMS-POST1-18	18" One side optional Post, Bronze Finish
WMS-POST2-18	18" Two side optional Post, Bronze Finish
WMS-POST1-36	36" One side optional Post, Bronze Finish
WMS-POST2-36	36" Two side optional Post, Bronze Finish

BOLLARD CUSTOMIZATION

CATALOG NO.	POST SIZE		FIXTURES PER POLE		COLOR TEMP		FINISH	
	code	description	code	description	code	description	code	description
WMS-S	18	18 inch	1	1 Sided	30K	3000K	BR	Bronze
WMS-R	36	36 inch	2	2 Sided	40K	4000K	WH	White
LMW					50K	5000K		
LWA-12								

Mounting Options
Shown with LMW Series

Mounting Options
Shown with LWAX-12W Series

Mounting Options
Shown with WMS Series

DECORATIVE WALL PACKS

DIMMING 0-10V | TRIAC DIMMABLE | WET LOCATIONS | MCTP

WSX-20-40W-MCTP-HA
Horizontal Arm

WSX-20-40W-MCTP-HA
Shown with Optional White/ Alabaster Lenses
Standard is Frosted - See Options Below

WSX-20-40W-MCTP-SCH
45° Suspended Chain Canopy Cord

WSX-20-40W-MCTP-SRK-218
WSX-20-40W-MCTP-SRK-224

WSX-20-40W-MCTP-45DA
45° Arm

WSX-20-40W-MCTP-HLA
15" Long Horizontal Arm

WSX-20-40W-MCTP-HAD
Decorative Horizontal Arm

OPT-WSX-WG
Factory-Installed
Wire Guard Option

WSX-20-40W-MCTP-HAD
Decorative Horizontal Arm

SPEC SERIES X-GEN SEASIDE LIGHT 120-277V DIAMETER: 10-3/4", MADE TO ORDER

POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WSX-20-40W-MCTP-HA	20W/30W/40W	100LM/W	30K/40K/50K - Horizontal Arm	4
WSX-20-40W-MCTP-45DA	20W/30W/40W	100LM/W	30K/40K/50K - 45-Degree Arm	1
WSX-20-40W-MCTP-HAD	20W/30W/40W	100LM/W	30K/40K/50K - Decorative Horizontal Arm	1
WSX-20-40W-MCTP-HAD-AZ	20W/30W/40W	100LM/W	30K/40K/50K - Decorative Horizontal Arm	1
WSX-20-40W-MCTP-HLA	20W/30W/40W	100LM/W	30K/40K/50K - 15" Long Horizontal Arm	1
WSX-20-40W-MCTP-SCH	20W/30W/40W	100LM/W	30K/40K/50K - 45° Suspended Chain, Canopy, Cord	1
WSX-20-40W-MCTP-SRK-218	20W/30W/40W	100LM/W	30K/40K/50K - 18" or 36" Swivel Rod Kit	1
WSX-20-40W-MCTP-SRK-224	20W/30W/40W	100LM/W	30K/40K/50K - 24" or 48" Swivel Rod Kit	1
WSX-RL-WH	WSX Original White Lens Replacement (Default Lens)			
WSX-RL-FR	WSX Optional Frosted Lens			
WSX-RL-AB	WSX Optional Alabaster Lens			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	**OPT-EM-WSX**	BACK BOX	**OPT-PC-B**	BUTTON
WIREGUARD	DESCRIPTION		**SENSOR**	DESCRIPTION
OPT-WSX-WG	WIREGUARD		**OPT-SEN-WSX**	back box
	POWDER COATING		**OPT-SEN-NLS-WSX**	WG NETWORK SENSOR
	N/A		**OPT-SEN-KEILTON-WSX**	KEILTON NETWORK SENSOR

WSO-20-40W-MCTP-HA
Horizontal Arm

WSO-20-40W-MCTP-HAD
Decorative Horizontal Arm

WSO-20-40W-MCTP-HAD-AZ
Decorative Horizontal Arm Antique Brass

OCEANSIDE LIGHT **120-277V** POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION		
WSO-20-40W-MCTP-HA	20W/30W/40W	100LM/W	30K/40K/50K - Horizontal Arm
WSO-20-40W-MCTP-HAD	20W/30W/40W	100LM/W	30K/40K/50K - Decorative Horizontal Arm
WSO-20-40W-MCTP-HAD-AZ	20W/30W/40W	100LM/W	30K/40K/50K - Decorative Horizontal Arm

LRS-SWG-MCT5-ORB

LED SEASIDE OUTDOOR WALL LANTERN WITH WIREGUARD, **120V** 5CCT, 11" X 8.75" X 10.35"

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-SWG-MCT5-ORB	12W	1200LM	27K/30K/35K/40K/50K - Oil-Rubbed Bronze	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
LRS-L, LRS-S, LRS-SWG	**N/A**	N/A
LRS-PV	**OPT-EM-LRS-PV**	N/A

POWDER COATING
N/A

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL FOR LRS-PV, LRS-C, LRS-D
OPT-SEN-NLS-LRS	WG NETWORK SENSOR
OPT-SEN-KEILTON-LRS	KEILTON NETWORK SENSOR

LRS-S-MCT5-ORB

LED SEASIDE OUTDOOR WALL LANTERN, **120V** 5CCT, 10.5" X 8.7" X 8.7"

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-S-MCT5-ORB	12W	1200LM	27K/30K/35K/40K/50K - Oil-Rubbed Bronze	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LRS-L, LRS-S, LRS-SWG	**N/A**	N/A	**OPT-PC-B**	BUTTON
LRS-PV	**OPT-EM-LRS-PV**	N/A	**SENSOR**	DESCRIPTION
	POWDER COATING		**OPT-SEN-LDS**	INTERNAL MICROWAVE BI-LEVEL FOR LRS-PV, LRS-C, LRS-D
	N/A		**OPT-SEN-NLS-LRS**	WG NETWORK SENSOR
			OPT-SEN-KEILTON-LRS	KEILTON NETWORK SENSOR

LRS-MC-MCT5-P-BR

LRS-MC-MCT5-P-BK

LRS-MC-MCT5-P-BN

LRS-MC-MCT5-P-WH

MINI-CONE OUTDOOR WALL SCONCE WITH PHOTOCELL, 5" HEIGHT, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-MC-MCT5-P-BK	10W	700LM	27K/30K/35K/40K/50K - Black	10
LRS-MC-MCT5-P-WH	10W	700LM	27K/30K/35K/40K/50K - White	10
LRS-MC-MCT5-P-BN	10W	700LM	27K/30K/35K/40K/50K - Brushed nickel	10
LRS-MC-MCT5-P-BR	10W	700LM	27K/30K/35K/40K/50K - Bronze	10

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
ALL	**OPT-EM-LRS-MC**	EXTERNAL BACK BOX	**N/A**	N/A
	POWDER COATING		**SENSOR**	DESCRIPTION
	N/A		**N/A**	N/A

c UL us LISTED

WET LOCATIONS

AVAILABLE IN RGBW

TC-WW-36W-RGBW-BT-BK
TC-WW-72W-RGBW-BT-BK
4' Wall Wash

DMX-WW-SH2
Shield only

TC-FL-36W-RGBW-BT-BR
Round Flood Light

Remote Control

TC-FL-72W-RGBW-BT-BK
Round Flood Light

TC-FLS-96W-RGBW-BT-BK
Square Flood Light

DMX-FL-SH1
Shield only

DMX-FLS-SH1
Shield only

DMX-FLS-SHFG1
Shield only

WEC-2UGW-WIFI

WESTGATE SMART APP COMPATIBLE RGBW SERIES

CATALOG NO.	DESCRIPTION		
TC-FL-36W-RGBW-BT-BR	36W	824LM	RGBW - Bronze
TC-FL-72W-RGBW-BT-BK	72W		RGBW - Black Round Flood Light
TC-WW-36W-RGBW-BT-BK	36W		RGBW - Black Linear Light
TC-WW-72W-RGBW-BT-BK	72W		RGBW - Black Linear Light
TC-FLS-96W-RGBW-BT-BK	96W		RGBW - Black Square Flood Light
DMX-FL-SH1	Half Glare Shield for TC-FL-72W & DMX-FL-72W		
DMX-WW-SH2	Half Glare Shield for TC-WW-36W/72W & DMX-WW-36W		
DMX-FLS-SH1	Half Glare Shield for TC-FLS-96W & DMX-FLS-36W/72W/96W		
DMX-FLS-SHFG1	Full Glare Shield for TC-FL-96W & DMX-FL-36W/72W/96W		
WEC-2UGW-WIFI	Bluetooth to WiFi Gateway for full remote access and programming, also needed for scheduling		

WET LOCATIONS

AVAILABLE IN RGBW

GET IT ON Google Play

Download on the App Store

WMCS-UDL-RGBW-BK

WMC-UDL-RGBW-BK

WMCS-UDL-RGBW-WH

WMC-UDL-RGBW-WH

Remote Control

RGBW LED OUTDOOR CYLINDER LIGHT, IP65

CATALOG NO.	DESCRIPTION			PCK QTY
4" LED ROUND CYLINDER LIGHTS, 120V (UP/DOWN LIGH) H: 12"				
WMC-UDL-RGBW-BK	24W	1920LM	RGBW - Black	6
WMC-UDL-RGBW-WH	24W	1920LM	RGBW - White	6
4" LED SQUARE CYLINDER LIGHTS, 120V (UP/DOWN LIGHT) H: 10-1/4"				
WMCS-UDL-RGBW-BK	24W	1920LM	RGBW - Black	6
WMCS-UDL-RGBW-WH	24W	1920LM	RGBW - White	6

FOR REMOTE CONTROL SEE PAGE 523

DMX 512 COMPATIBLE RGBW SERIES

SPECIAL ORDER FOR PROJECTS - MINIMUM 3 MONTHS LEAD TIME

DMX CONTROLLER & CABLES NEEDED.

IN A DMX LIGHTING SETUP, LIGHTS NEED TO BE CONNECTED WITH CABLES. THE CABLES CAN BE "DAISY CHAINED" SO THAT EACH LIGHT CAN PLUG INTO THE ONE BEFORE IT INSTEAD OF ALL LIGHTS PLUGGING INTO THE DMX BOARD ITSELF.

DMX-FL-36W-RGBW-BT-BK
Round Flood Light

DMX-FL-72W-RGBW-BT-BK
Round Flood Light

DMX-FLS-96W-RGBW-BT-BK
DMX-FLS-192W-RGBW-BT-BK
Square Flood Light

DMX-FLS-SH1 Shield onlyBT-BR Round Flood LightWH

DMX-FLS-SHFG1
Shield only

DMX-WW-36W-RGBW-BT-BK
DMX-WW-72W-RGBW-BT-BK
Wall Wash

DMX-WW-SH2
Shield only

DMX-3PIN-EXT

DMX-FLS-SH2
Shield only

DMX 512 COMPATIBLE RGBW SERIES

CATALOG NO.	DESCRIPTION		PCK QTY
DMX-FL-36W-RGBW-BT-BK	36W	RGBW - Black Round Flood Light	
DMX-FL-72W-RGBW-BT-BK	72W	RGBW - Black Round Flood Light	
DMX-FLS-96W-RGBW-BT-BK	96W	RGBW - Black Square Flood Light	
DMX-FLS-192W-RGBW-BT-BK	192W	RGBW - Black Square Flood Light	
DMX-WW-36W-RGBW-BT-BK	36W	RGBW - Black Linear Light	
DMX-WW-72W-RGBW-BT-BK	72W	RGBW - Black Linear Light	
DMX-FL-SH1	Half Glare Shield for TC-FL-72W & DMX-FL-72W		
DMX-WW-SH2	Half Glare Shield for TC-WW-36W/72W & DMX-WW-36W		
DMX-FLS-SH1	Half Glare Shield for TC-FLS-96W & DMX-FLS-36W/72W/96W		
DMX-FLS-SHFG1	Full Glare Shield for TC-FL-96W & DMX-FL-36W/72W/96W		
DMX-3PIN-5FT-EXT	Dmx512 3-Pin Outdoor Extension Cord 5 Feet		
DMX-3PIN-10FT-EXT	Dmx512 3-Pin Outdoor Extension Cord 10 Feet		

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	GROUP OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
ALL	OPT-DMX-GROUP	Change fixture address to create light groups	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

SFX-G9-500W-45D-RGB. Shown with Optional Shroud

SPEC SERIES X GEN. RGB STADIUM LIGHT, DMX512 CONTROLLED - SPECIAL ORDER

CATALOG NO.	DESCRIPTION			PCK QTY
SFX-G9-500W-45D-RGB	500W		RGB	1
SFX-G9-800W-45D-RGB	800W		RGB	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	GROUP OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
ALL	OPT-DMX-GROUP	Change fixture address to create light groups	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

DMX-CIGL-9-RGBW

DMX-CIGL-20-RGBW

DMX-CIGL-40-RGBW

DMX 512 COMPATIBLE RGBW LINEAR ARCHITECTURAL INGROUND LIGHT

CATALOG NO.	DESCRIPTION		
DMX-CIGL-9-RGBW	11W	935LM	RGB+40K
DMX-CIGL-20-RGBW	22W	1870LM	RGB+40K
DMX-CIGL-40-RGBW	44W	3740LM	RGB+40K

IGLC-D5-10W-MCT-24D

IGLC-D9-30W-MCTP-120D-D

IGLC-D8-30W-MCTP-30D-D

IGLC-D11-50W-MCTP-60D-D

DMX 512 COMPATIBLE RGBW STAINLESS STEEL COMMERCIAL INGROUND LIGHT

CATALOG NO.	DESCRIPTION		
DMX-IGLC-D5-RGBW	12W	1020LM	RGB+40K
DMX-IGLC-D6-RGBW	18W	1530LM	RGB+40K
DMX-IGLC-D8-RGBW	24W	2040LM	RGB+40K
DMX-IGLC-D9-RGBW	42W	3570LM	RGB+40K
DMX-IGLC-D11-RGBW	54W	4590LM	RGB+40K

WLF-24-40W-MCTP-BR-HA

WLF-24-40W-MCTP-BK-HA

WLF-24-40W-MCTP-WH-HA

WLF-24-40W-MCTP-BK-SRK-218
WLF-24-40W-MCTP-BK-SRK-224

WLF-24-40W-MCTP-BK-SCH

WLF-24-40W-MCTP-BR-WB

WLF-24-40W-MCTP-BK-WB

WLF-24-40W-MCTP-WH-WB

12” DOME LIGHT WITH FLAT LENS 120-277V DUAL DIMMING, MADE TO ORDER

CATALOG NO.	DESCRIPTION			
WLF-24-40W-MCTP-WH-HA	24W/32W/40W	100LM/W	30K/40K/50K - 15" Horizontal Arm	1
WLF-24-40W-MCTP-BK-HA	24W/32W/40W	100LM/W	30K/40K/50K - 15" Horizontal Arm	1
WLF-24-40W-MCTP-BR-HA	24W/32W/40W	100LM/W	30K/40K/50K - 15" Horizontal Arm	1
WLF-24-40W-MCTP-WH-WB	24W/32W/40W	100LM/W	30K/40K/50K - 21" Wall-Mount Bell Arm	1
WLF-24-40W-MCTP-BK-WB	24W/32W/40W	100LM/W	30K/40K/50K - 21" Wall-Mount Bell Arm	1
WLF-24-40W-MCTP-BR-WB	24W/32W/40W	100LM/W	30K/40K/50K - 21" Wall-Mount Bell Arm	1
WLF-24-40W-MCTP-BK-SCH	24W/32W/40W	100LM/W	30K/40K/50K - 45" Suspended Chain, Canopy, Cord	1
WLF-24-40W-MCTP-BK-SRK-218	24W/32W/40W	100LM/W	30K/40K/50K - 18" or 36" Swivel Rod Kit	1
WLF-24-40W-MCTP-BK-SRK-224	24W/32W/40W	100LM/W	30K/40K/50K - 24" or 48" Swivel Rod Kit	1
WLF-24-40W-MCTP-BR-SRK-224	24W/32W/40W	100LM/W	30K/40K/50K - 24" or 48" Swivel Rod Kit	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL	OPT-EM-WLF	INTERNAL

POWDER COATING
N/A

PHOTOCELL	DESCRIPTION
OPT-PC-BUM	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-WLF	Be-LEVEL
OPT-SEN-NLS-WLF	WG NETWORK SENSOR
OPT-SEN-KEILTON-WLF	KEILTON NETWORK SENSOR

GNB-25W-MCT-BR-P

GNB-40W-MCT-BR-P

GNB-25W-MCT-WH-P

GNB-40W-MCT-WH-P

GNB-ARMKIT-ST18-BR

GNB-ARMKIT-ST18-BK

GNB-ARMKIT-ST18-WH

GNB-ARMKIT-HGN-BR

GNB-ARMKIT-HGN-BK

GNB-ARMKIT-HGN-WH

3CCT GOOSENECK BARN LIGHT WITH INTEGRATED PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
GNB-25W-MCT-BR-P	25W	3000LM	3000K/4000K/5000K - Bronze	2
GNB-25W-MCT-WH-P	25W	3000LM	3000K/4000K/5000K - White	2
GNB-25W-MCT-BK-P	25W	3000LM	3000K/4000K/5000K - Black	2
GNB-40W-MCT-BR-P	40W	4800LM	3000K/4000K/5000K - Bronze	2
GNB-40W-MCT-WH-P	40W	4800LM	3000K/4000K/5000K - White	2
GNB-40W-MCT-BK-P	40W	4800LM	3000K/4000K/5000K - Black	2
GNB-ARMKIT-ST18-BR	GNB Field-Installed 18" Straight Arm - Bronze			
GNB-ARMKIT-ST18-BK	GNB Field-Installed 18" Straight Arm - Black			
GNB-ARMKIT-ST18-WH	GNB Field-Installed 18" Straight Arm - White			
GNB-ARMKIT-HGN-BR	GNB Field-Installed Horizontal Gooseneck Arm - Bronze			
GNB-ARMKIT-HGN-BK	GNB Field-Installed Horizontal Gooseneck Arm - Black			
GNB-ARMKIT-HGN-WH	GNB Field-Installed Horizontal Gooseneck Arm - White			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-EM-GNB	BACK BOX	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	OPT-CLR-75(BK/GR/SR/WH)		N/A	N/A

GNBA-18-35W-MCTP-BK-P

GNBA-18-35W-MCTP-WH-P

GNBA-18-35W-MCTP-BR-P

GNBA-18-35W-MCTP-SIL-P

11" 3CCT ANGLED GOOSENECK BARN LIGHT WITH INTEGRATED PHOTOCELL

CATALOG NO.	DESCRIPTION			PCK QTY
GNBA-18-35W-MCTP-BK-P	18W/26W/35W	150LM/W	30K/40K/50K - Black	1
GNBA-18-35W-MCTP-WH-P	18W/26W/35W	150LM/W	30K/40K/50K - White	1
GNBA-18-35W-MCTP-BR-P	18W/26W/35W	150LM/W	30K/40K/50K - Bronze	1
GNBA-18-35W-MCTP-SIL-P	18W/26W/35W	150LM/W	30K/40K/50K - Silver	1

LRS-L-MCT5-BK

LED OUTDOOR LARGE WALL RESIDENTIAL LANTERN **120V**, 5CCT, 12.4” X 8.8” X 8.8”

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-L-MCT5-BK	12W	1200LM	27K/30K/35K/40K/50K - Black 12.4"X8.8"X8.8"	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
LRS-L, LRS-S, LRS-SWG	**N/A**	N/A
LRS-PV	**OPT-EM-LRS-PV**	N/A

POWDER COATING
N/A

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL FOR LRS-PV, LRS-C, LRS-D
OPT-SEN-NLS-LRS	WG NETWORK SENSOR
OPT-SEN-KEILTON-LRS	KEILTON NETWORK SENSOR

LRS-ML-MCT-P-BK

LRS-ML-SG-MCT-P-BK

8” MINI SQUARE LANTERN W/ PHOTOCELL - 3CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-ML-MCT-P-BK	12W	650LM	30K/40K/50K - 8" Black	6
LRS-ML-SG-MCT-P-BK	12W	650LM	30K/40K/50K - 8" Black, Seeded Glass	6

LRS-N1-MCT-P-ORB

LRS-M1-MCT-P-ORB

LRS-M2-MCT-P-ORB CRACK

Shown with Optional Bubble Glass

LRS-M2-MCT-P-ORB

Shown with Optional Crackled Glass

RESIDENTIAL LANTERN WITH PHOTOCELL CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
10" MODEL M RESIDENTIAL LANTERNS WITH PHOTOCELL, CCT SELECTABLE				
LRS-M1-MCT-P-ORB	12W	500LM	30K/40K/50K - With Frosted Lens & Ornament guard	6
LRS-M2-MCT-P-ORB	12W	500LM	30K/40K/50K - With Frosted Lens & Outer Clear Glass	6
LRS-M-RL-FG	Replacement Default Frosted Lens For LRS-M Series			
LRS-M-RL-BG	Replacement Bubble Glass Lens For LRS-M Series			
LRS-M-RL-CG	Replacement Crackled Glass Lens For LRS-M Series			
13" MODEL N RESIDENTIAL LANTERNS WITH PHOTOCELL, CCT SELECTABLE				
LRS-N1-MCT-P-ORB	20W	850LM	30K/40K/50K - With Frosted Lens & Outer Clear Glass	4
LRS-N-RL-FG	Replacement Default Frosted Lens For LRS-N Series			
LRS-N-RL-BG	Replacement Bubble Glass Lens For LRS-N Series			
LRS-N-RL-CG	Replacement Crackled Glass Lens For LRS-N Series			
8" ROUND MODEL V DIE-CAST MODERN WALL SCONCES WITH PHOTOCELL, CCT SELECTABLE				
LRS-V-MCT-P-ORB	12W	500LM	30K/40K/50K	

WEU-6-UDL-MCTP-BK-DD-P

WEU-6-UDL-MCTP-BR-DD-P

WEU-6-UDL-MCTP-WH-DD-P

WEU-10-UDL-MCTP-BK-DD-P

WEU-10-UDL-MCTP-BR-DD-P

WEU-10-UDL-MCTP-WH-DD-P

MODERN FLAT WALL PACK UP/DOWN SELECTABLE POWER & CCT, DUAL DIMMING

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
WEU-10-UDL-MCTP-BK-DD-P	14W/18W/24W	80LM/W	30K/40K/50K - Black	8
WEU-10-UDL-MCTP-BR-DD-P	14W/18W/24W	80LM/W	30K/40K/50K - Bronze	8
WEU-10-UDL-MCTP-WH-DD-P	14W/18W/24W	80LM/W	30K/40K/50K - White	8
WEU-6-UDL-MCTP-BK-DD-P	6W/10W/12W	80LM/W	30K/40K/50K - Black	8
WEU-6-UDL-MCTP-BR-DD-P	6W/10W/12W	80LM/W	30K/40K/50K - Bronze	8
WEU-6-UDL-MCTP-WH-DD-P	6W/10W/12W	80LM/W	30K/40K/50K - White	8


WFRA-X-UDL-MCTP-WH-DD-P

WFRA-X-UDL-MCTP-BK-DD-P

ORB WFRA-X-UDL-MCTP-BR-DD-P

6", 8", 12" FLAT WALL UP/DOWN LIGHT SELECTABLE POWER & 3CCT, DUAL DIMMING, 120/277V

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
WFRA-6-UDL-MCTP-WH-DD-P	10W/13W/17W	70LM/W	30K/40K/50K - White	8
WFRA-6-UDL-MCTP-BR-DD-P	10W/13W/17W	70LM/W	30K/40K/50K - Bronze	8
WFRA-6-UDL-MCTP-BK-DD-P	10W/13W/17W	70LM/W	30K/40K/50K - Black	8
WFRA-8-UDL-MCTP-WH-DD-P	12W/16W/20W	70LM/W	30K/40K/50K - White	8
WFRA-8-UDL-MCTP-BR-DD-P	12W/16W/20W	70LM/W	30K/40K/50K - Bronze	8
WFRA-8-UDL-MCTP-BK-DD-P	12W/16W/20W	70LM/W	30K/40K/50K - Black	8
WFRA-12-UDL-MCTP-WH-DD-P	15W/20W/25W	70LM/W	30K/40K/50K - White	4
WFRA-12-UDL-MCTP-BR-DD-P	15W/20W/25W	70LM/W	30K/40K/50K - Bronze	4
WFRA-12-UDL-MCTP-BK-DD-P	15W/20W/25W	70LM/W	30K/40K/50K - Black	4

LRS-P1-MCT-BR

LRS-P2-MCTP-BR

DIE-CAST HIGH PERFORMANCE SELECTABLE 3CCT WALL PACK, PC LENS

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-P1-MCT-BR	15W	975LM	30K/40K/50K - Bronze, 10"H	8
LRS-P2-MCTP-BR	20W/25W/30W	70LM/W	30K/40K/50K - Bronze, 15"H	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL	**OPT-LRS-EM**	BOX

POWDER COATING
N/A

VANDAL RES.	DESCRIPTION
N/A	N/A

SENSOR	DESCRIPTION
OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL
OPT-SEN-NLS-LRS	WG NETWORK SENSOR
OPT-SEN-KEILTON-LRS	KEILTON NETWORK SENSOR

LRS-G-MCT-C90-MGBR

LRS-G-MCT-C90-BK

LRS-G-MCT-C90-WH

LRS-H-MCT-C90-MGBR

LRS-H-MCT-C90-BK

LRS-H-MCT-C90-WH

LRS-H-RGBW-BK

Remote Control

ARCHITECTURAL OUTDOOR/INDOOR LED WALL LIGHTS **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
SQUARE MODEL G ARCHITECTURAL OUTDOOR/INDOOR LED WALL LIGHTS, 120V				
LRS-G-MCT-C90-BK	12W	650LM	3000K/4000K/5000K - Black	12
LRS-G-MCT-C90-WH	12W	650LM	3000K/4000K/5000K - White	12
LRS-G-MCT-C90-MGBR	12W	650LM	3000K/4000K/5000K - Marine Grade Bronze	12
SQUARE MODEL H ARCHITECTURAL OUTDOOR/INDOOR LED WALL LIGHTS, 120V				
LRS-H-MCT-C90-BK	12W	650LM	3000K/4000K/5000K - Black	12
LRS-H-MCT-C90-WH	12W	650LM	3000K/4000K/5000K - White	12
LRS-H-MCT-C90-MGBR	12W	650LM	3000K/4000K/5000K - Marine Grade Bronze	12
RGB WG APP OR REMOTE CONTROL 6" SQUARE MODEL H ARCHITECTURAL OUTDOOR/INDOOR LED WALL LIGHTS, 120V				
LRS-H-RGBW-BK	12W	650LM	5CCT AND RGB - Black	12

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LRS-E, LRS-F	**OPT-EM-LRS-R-BK**	BACK BOX	**OPT-PC-LRS-RBK**	EXTERNAL BOX
LRS-G, LRS-H, LRS-J, LRS-J1S	**OPT-EM-LRS-S-BK**	BACK BOX	**OPT-PC-LRS-RMGBR**	EXTERNAL BOX
LRS-E, LRS-F	**OPT-EM-LRS-R-WH**	BACK BOX	**OPT-PC-LRS-RWH**	EXTERNAL BOX
LRS-G, LRS-H	**OPT-EM-LRS-S-WH**	BACK BOX	**OPT-PC-LRS-SBK**	EXTERNAL BOX
LRS-E, LRS-F	**OPT-EM-LRS-R-MGBR**	BACK BOX	**OPT-PC-LRS-SMGBR**	EXTERNAL BOX
LRS-G, LRS-H	**OPT-EM-LRS-S-MGBR**	BACK BOX	**OPT-PC-LRS-SWH**	EXTERNAL BOX
LRS-J, LRS-J1S	**OPT-EM-LRS-S-BR**	BACK BOX		
LRS-JRS, LRS-JR1S	**OPT-EM-LRS-S-BN**	BACK BOX		
	POWDER COATING		**277V OPTION**	DESCRIPTION
	N/A		**OPT-277V-LRS-R**	EXTERNAL BOX
			OPT-277V-LRS-S	EXTERNAL BOX

LRS-E-MCT-C90-MGBR

LRS-E-MCT-C90-BK

LRS-E-MCT-C90-WH

LRS-F-RGBW-BK

Remote Control

LRS-F-MCT-C90-MGBR

LRS-F-MCT-C90-BK

LRS-F-MCT-C90-WH

ARCHITECTURAL OUTDOOR/INDOOR LED WALL LIGHT **120V OPTION**

CATALOG NO.	DESCRIPTION			PCK QTY
ROUND MODEL E ARCHITECTURAL OUTDOOR/INDOOR LED WALL LIGHTS, 120V				
LRS-E-MCT-C90-BK	12W	650LM	3000K/4000K/5000K - Black	12
LRS-E-MCT-C90-WH	12W	650LM	3000K/4000K/5000K - White	12
LRS-E-MCT-C90-MGBR	12W	650LM	3000K/4000K/5000K - Marine Grade Bronze	12
ROUND MODEL F ARCHITECTURAL OUTDOOR/INDOOR LED WALL LIGHTS, 120V				
LRS-F-MCT-C90-BK	12W	650LM	3000K/4000K/5000K - Black	12
LRS-F-MCT-C90-WH	12W	650LM	3000K/4000K/5000K - White	12
LRS-F-MCT-C90-MGBR	12W	650LM	3000K/4000K/5000K - Marine Grade Bronze	12
RGB WG APP OR REMOTE CONTROL 7" ROUND MODEL F ARCHITECTURAL OUTDOOR/INDOOR LED WALL LIGHTS, 120V				
LRS-F-RGBW-BK	12W	650LM	5CCT AND RGB - Black	12

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LRS-E, LRS-F	**OPT-EM-LRS-R-BK**	BACK BOX	**OPT-PC-LRS-RBK**	EXTERNAL BOX
LRS-G, LRS-H, LRS-J, LRS-J1S	**OPT-EM-LRS-S-BK**	BACK BOX	**OPT-PC-LRS-RMGBR**	EXTERNAL BOX
LRS-E, LRS-F	**OPT-EM-LRS-R-WH**	BACK BOX	**OPT-PC-LRS-RWH**	EXTERNAL BOX
LRS-G, LRS-H	**OPT-EM-LRS-S-WH**	BACK BOX	**OPT-PC-LRS-SBK**	EXTERNAL BOX
LRS-E, LRS-F	**OPT-EM-LRS-R-MGBR**	BACK BOX	**OPT-PC-LRS-SMGBR**	EXTERNAL BOX
LRS-G, LRS-H	**OPT-EM-LRS-S-MGBR**	BACK BOX	**OPT-PC-LRS-SWH**	EXTERNAL BOX
LRS-J, LRS-J1S	**OPT-EM-LRS-S-BR**	BACK BOX		
LRS-JRS, LRS-JR1S	**OPT-EM-LRS-S-BN**	BACK BOX		
POWDER COATING			**277V OPTION**	DESCRIPTION
N/A			**OPT-277V-LRS-R**	EXTERNAL BOX
			OPT-277V-LRS-S	EXTERNAL BOX

WET LOCATIONS
EM CAPABLE
MCT

LRS-J1S-MCT-C90-BK

LRS-J1S-MCT-C90-BN

LRS-J1S-MCT-C90-BR

LRS-J-MCT-C90-BK

LRS-J-MCT-C90-BN

LRS-J-MCT-C90-BR

LRS-JR1S-MCT-C90-BK

LRS-JRS-MCT-C90-BK

LRS-J1S-RGBWW-PB-BK

LRS-JS-RGBWW-PB-BK

CRI90 DECORATIVE OUTDOOR WALL LIGHT SOLID ACRYLIC SELECTABLE CCT

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
1-SIDE DECORATIVE OUTDOOR WALL LIGHT				
LRS-J1S-MCT-C90-BK	10W	700LM	3000K/4000K/5000K - Black	10
LRS-J1S-MCT-C90-BR	10W	700LM	3000K/4000K/5000K - Bronze	10
LRS-J1S-MCT-C90-BN	10W	700LM	3000K/4000K/5000K - Brushed-Nickel	10
2-SIDES DECORATIVE OUTDOOR WALL LIGHT				
LRS-J-MCT-C90-BK	20W	1400LM	3000K/4000K/5000K - Black	10
LRS-J-MCT-C90-BR	20W	1400LM	3000K/4000K/5000K - Bronze	10
LRS-J-MCT-C90-BN	20W	1400LM	3000K/4000K/5000K - Brushed-Nickel	10

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
MCT 1-SIDE				
LRS-JR1S-MCT-C90-BK	10W	700LM	30K/40K/50K -Black	10
LRS-JR1S-MCT-C90-BR	10W	700LM	30K/40K/50K -Bronze	10
LRS-JR1S-MCT-C90-BN	10W	700LM	30K/40K/50K - Brushed Nickel	10
MCT 2-SIDE				
LRS-JRS-MCT-C90-BK	20W	1400LM	30K/40K/50K -Black	10
LRS-JRS-MCT-C90-BR	20W	1400LM	30K/40K/50K -Bronze	10
LRS-JRS-MCT-C90-BN	20W	1400LM	30K/40K/50K - Brushed Nickel	10
RGBW PUSH BUTTON 1-SIDE				
LRS-JR1S-RGBWW-PB-BK	10W	700LM	RGBW -Black	10
LRS-JRS-RGBWW-PB-BK	20W	1400LM	RGBW -Black	10
RGBW PUSH BUTTON 2-SIDE				
LRS-J1S-RGBWW-PB-BK	10W	700LM	RGBW -Black	10
LRS-JS-RGBWW-PB-BK	20W	1400LM	RGBW -Black	10



LRS-O1-MCT-BR | LRS-O2-MCT-BR | LRS-O3-MCT-BR | Can Be Installed as Uplight

DIE-CAST MODERN WALL SCONCE, UP LIGHT OR DOWN LIGHT INSTALLATION, IP65 MODEL O

SELECTABLE 3CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-O1-MCT-BR	6W	420LM	30K/40K/50K - Bronze, 5" H	10
LRS-O2-MCT-BR	9W	630LM	30K/40K/50K - Bronze, 6" H	10
LRS-O3-MCT-BR	12W	840LM	30K/40K/50K - Bronze, 8" H	10



Up light -Bronze



Down light -White



Up-Down lights - Brushed Nickel

WMQ5-UDL-MCTP-BR-P

WMQ5-UDL-MCTP-BK-P

WMQ5-UDL-MCTP-WH-P

WMQ5-UDL-MCTP-BN-P

UP-DOWN SELECTABLE CUBE WALL LIGHT, 4.87"(L) X 4.87"(H) X 4.87"(W) POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WMQ5-UDL-MCTP-BK-P	6W/12W/15W/18W	104LM/W	30K/40K/50K - 30°, Bronze	6
WMQ5-UDL-MCTP-BR-P	6W/12W/15W/18W	104LM/W	30K/40K/50K - 30°, Brushed Nickel	6
WMQ5-UDL-MCTP-WH-P	6W/12W/15W/18W	104LM/W	30K/40K/50K - 30°, White	6
WMQ5-UDL-MCTP-BN-P	6W/12W/15W/18W	104LM/W	30K/40K/50K - 30°, Black	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL	OPT-EM-WMQ5-BK	BACK BOX
	OPT-EM-WMQ5-BR	BACK BOX
	OPT-EM-WMQ5-WH	BACK BOX
	OPT-EM-WMQ5-BN	BACK BOX

POWDER COATING
N/A

VANDAL RES.	DESCRIPTION
N/A	N/A

SENSOR	DESCRIPTION
N/A	N/A

c UL us LISTED | WET LOCATIONS | EM CAPABLE | SENSOR OPTION

LMW
Bronze

LMW-BK
Black

LMW-WH
White

Shown with EM

Shown with EM

Shown with Sensor

Shown with Sensor

LED MINI CUTOFF WALL PACK **120~277V** 5" X 5", DARK BRONZE & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
LMW-12W-30K	12W	1300LM	3000K - Bronze	12
LMW-12W-40K	12W	1300LM	4000K - Bronze	12
LMW-12W-50K	12W	1300LM	5000K - Bronze	12
LMW-12W-30K-WH	12W	1300LM	3000K - White	12
LMW-12W-40K-WH	12W	1300LM	4000K - White	12
LMW-12W-50K-WH	12W	1300LM	5000K - White	12
LMW-12W-30K-BK	12W	1320LM	3000K - Black	12
LMW-12W-40K-BK	12W	1320LM	4000K - Black	12
LMW-12W-50K-BK	12W	1320LM	5000K - Black	12

POWER & CTT - ADJUSTABLE LED MINI CUTOFF WALLPACK, 120~277V, 5" X 5"

LMW-10-24W-MCTP-P	10W/15W/24W	110LM/W	30K/40K/50K - Bronze	12
LMW-10-24W-MCTP-P-BK	10W/15W/24W	110LM/W	30K/40K/50K - White	12
LMW-10-24W-MCTP-P-WH	10W/15W/24W	110LM/W	30K/40K/50K - Black	12

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR BOLLARD SETTINGS SEE PAGE 133

WATTS	EM OPTION	DESCRIPTION
ALL	OPT-EM-LMW	EXTERNAL BACK BOX
	OPT-EM-LMW-WH	EXTERNAL BACK BOX

0-10V DIM OPTION	DESCRIPTION
OPT-010DIM	0-10V Dimming

POWDER COATING
N/A

PHOTOCELL	DESCRIPTION
OPT-PC-B1	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-LMW	PROGRAMMABLE MICROWAVE BI-LEVEL (ONLY 2" & 3")
OPT-SEN-NLS-LMW	WG NETWORK SENSOR
OPT-SEN-KEILTON-LMW	KEILTON NETWORK SENSOR
OPT-SEN-LMW-WH	PROGRAMMABLE MICROWAVE BI-LEVEL, WHITE (ONLY 2"&3")

HNS-58DL-CUSTOM

HNS-55PC-DD-CUSTOM-P

HNS-56UDL-CUSTOM
LIT UP

HNS-59NL-DT-CUSTOM

HOUSE NUMBER SIGNAGE **MADE TO ORDER** SPECIFY HOUSE No., CCT, FINISH

CATALOG NO.	DESCRIPTION
HNS-58DL-CUSTOM-XX	ADA House Number Signage 5in W x 8in H Downlight 120V 10W CR80 Custom CCT Digits Finish, Black
HNS-56UDL-CUSTOM	House Number Signage 10in W x 6in H Up/Downlight 120V 16W CR80 Custom CCT Digits Finish, Black, ORB or Custom Finish
HNS-59NL-DT-CUSTOM	ADA House Number Signage Num-Lit 4in W x 24in H 120V 16W TRIAC CR90 Custom CCT Digits Finish, Black, ORB or Custom Finish
HNS-55PC-DD-CUSTOM	Ada House Number Signage Full Lens 8in W x 10in H 120-277V Dual Dim Silk Screen No. Cust. CCT Digits Finish, Black, ORB or Custom Finish
HNS-BRAILLE	HNS Braille Numbers Option Added
HNS-PHOTOCELL	HNS Photocell Option Added

WET LOCATIONS MCT 3

LVW-100-MCT-ORB

LVW-110-MCT-ORB

LVW-110-UD-MCT-ORB

LVW-115-MCT-ORB

LVW-200-MCT-ORB

LVW-210-MCT-ORB

LVW-210-UD-MCT-ORB

LVW-215-MCT-ORB

LVW-250-MCT-ORB

LVW-300-MCT-ORB
LVW-300-MCT-WH


LVW-310-MCT-ORB
LVW-310-MCT-WH

12V SELECTABLE CCT LED MINI WALL SCONCE

CATALOG NO.	DESCRIPTION		
LVW-100-MCT-ORB	3W	200LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-110-MCT-ORB	3W	200LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-110-UD-MCT-ORB	6W	400LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-115-MCT-ORB	3W	200LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-200-MCT-ORB	3W	200LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-210-MCT-ORB	3W	200LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-210-UD-MCT-ORB	6W	400LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-215-MCT-ORB	3W	200LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-250-MCT-ORB	6W	400LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-300-MCT-ORB	6W	400LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-300-MCT-WH	6W	400LM	30K/40K/50K - White
LVW-310-MCT-ORB	6W	400LM	30K/40K/50K - Oil-Rubbed Bronze
LVW-310-MCT-WH	6W	400LM	30K/40K/50K - White

CYLINDER LIGHTS

TRIAC DIMMABLE · WET LOCATIONS · EM CAPABLE · SENSOR OPTION · MCT

WMC2-DL-BR

WMC2-DL-BK

WMC2-DL-WH

WMC2-DL-BN

WMC2-UDL-BR

WMC2-UDL-BK

WMC2-UDL-WH

WMC2-UDL-BN

WMC3-DL-BR

WMC3-DL-BK

WMC3-DL-WH

WMC3-DL-BN

WMC3-UDL-BR

WMC3-UDL-BK

WMC3-UDL-WH

WMC3-UDL-BN

2”/3” CCT-ADJUSTABLE LED OUTDOOR CYLINDER LIGHTS, IP65

CATALOG NO.	DESCRIPTION			PCK QTY
2” LED CYLINDER LIGHTS, 120V (DOWN LIGHT) H: 8”				
WMC2-DL-MCT-BR-DT	6W	400LM	3000K/4000K/5000K - 25°, Bronze	12
WMC2-DL-MCT-BN-DT	6W	400LM	3000K/4000K/5000K - 25°, Brushed Nickel	12
WMC2-DL-MCT-WH-DT	6W	400LM	3000K/4000K/5000K - 25°, White	12
WMC2-DL-MCT-BK-DT	6W	400LM	3000K/4000K/5000K - 25°, Black	12
WMC2-DL-MCT-AZ-DT	6W	400LM	3000K/4000K/5000K - 25°, Antique Bronze	12
2” LED CYLINDER LIGHTS, 120V (UP/DOWN LIGHT) H: 10”				
WMC2-UDL-MCT-BR-DT	12W	800LM	3000K/4000K/5000K - 25°, Bronze	12
WMC2-UDL-MCT-BN-DT	12W	800LM	3000K/4000K/5000K - 25°, Brushed Nickel	12
WMC2-UDL-MCT-WH-DT	12W	800LM	3000K/4000K/5000K - 25°, White	12
WMC2-UDL-MCT-BK-DT	12W	800LM	3000K/4000K/5000K - 25°, Black	12
WMC2-UDL-MCT-AZ-DT	12W	800LM	3000K/4000K/5000K - 25°, Antique Bronze	12

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION			PCK QTY
3" LED CYLINDER LIGHTS, 120V (DOWN LIGHT) H: 6"				
WMC3-DL-MCT-BR-DT	9W	650LM	3000K/4000K/5000K - 30°, Bronze	12
WMC3-DL-MCT-BN-DT	9W	650LM	3000K/4000K/5000K - 30°, Brushed Nickel	12
WMC3-DL-MCT-WH-DT	9W	650LM	3000K/4000K/5000K - 30°, White	12
WMC3-DL-MCT-BK-DT	9W	650LM	3000K/4000K/5000K - 30°, Black	12
WMC3-DL-MCT-AZ-DT	9W	650LM	3000K/4000K/5000K - 30°, Antique Bronze	12
3" LED CYLINDER LIGHTS, 120V (UP/DOWN LIGHT) H: 10"				
WMC3-UDL-MCT-BR-DT	18W	1300LM	3000K/4000K/5000K - 30°, Bronze	12
WMC3-UDL-MCT-BN-DT	18W	1300LM	3000K/4000K/5000K - 30°, Brushed Nickel	12
WMC3-UDL-MCT-WH-DT	18W	1300LM	3000K/4000K/5000K - 30°, White	12
WMC3-UDL-MCT-BK-DT	18W	1300LM	3000K/4000K/5000K - 30°, Black	12
WMC3-UDL-MCT-AZ-DT	18W	1300LM	3000K/4000K/5000K - 30°, Antique Bronze	12
ACRYLIC DROP LENS FOR WMC				
CWMC2-DL32	CMC2 And WMC2 32mm Acrylic Drop Lens			
CWMC3-DL32	CMC3 And WMC3 32mm Acrylic Drop Lens			

FOR OPT OPTION SEE PAGE 158

WMC-DL-BR

WMC-DL-BN

WMC-DL-WH

WMC-DL-BK

WMC-DL-AZ

WMC-UDL-BR

WMC-UDL-BN

WMC-UDL-WH

WMC-UDL-BK

WMC-UDL-AZ

4" LED OUTDOOR CYLINDER LIGHTS, IP65, 270V OPTION CCT-ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
4" LED CYLINDER LIGHTS, 120V (DOWN LIGHT) H: 8"				
WMC-DL-MCT-BR-DT	15W	1200LM	3000K/4000K/5000K - 40°, Bronze	6
WMC-DL-MCT-BN-DT	15W	1200LM	3000K/4000K/5000K - 40°, Brushed Nickel	6
WMC-DL-MCT-WH-DT	15W	1200LM	3000K/4000K/5000K - 40°, White	6
WMC-DL-MCT-BK-DT	15W	1200LM	3000K/4000K/5000K - 40°, Black	6
WMC-DL-MCT-AZ-DT	15W	1200LM	3000K/4000K/5000K - 40°, Antique Bronze	6
4" LED CYLINDER LIGHTS, 120V (UP/DOWN LIGHT) H: 12"				
WMC-UDL-MCT-BR-DT	30W	2400LM	3000K/4000K/5000K - 40°, Bronze	6
WMC-UDL-MCT-BN-DT	30W	2400LM	3000K/4000K/5000K - 40°, Brushed Nickel	6
WMC-UDL-MCT-WH-DT	30W	2400LM	3000K/4000K/5000K - 40°, White	6
WMC-UDL-MCT-BK-DT	30W	2400LM	3000K/4000K/5000K - 40°, Black	6
4" LED CYLINDER LIGHTS, 120-277V WITH PHOTOCELL (UP/DOWN LIGHT) H: 12"				
WMC4-UDL-MCTP-BR-DD-P	2x9W/2x12W /2x15W	80LM/W	30K/40K/50K - 45°, Bronze	6
WMC4-UDL-MCTP-BN-DD-P	2x9W/2x12W /2x15W	80LM/W	30K/40K/50K - 45°, Brushed Nickel	6
WMC4-UDL-MCTP-WH-DD-P	2x9W/2x12W /2x15W	80LM/W	30K/40K/50K - 45°, White	6
WMC4-UDL-MCTP-BK-DD-P	2x9W/2x12W /2x15W	80LM/W	30K/40K/50K - 45°, Black	6
WMC4-UDL-MCTP-AZ-DD-P	2x9W/2x12W /2x15W	2400LM	3000K/4000K/5000K - 45°, Antique Bronze	6

ACRYLIC DROP LENS FOR WMC

WMC4-DL32 WMC4 32mm Acrylic Drop Lens

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

SIZE	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
2" & 3"	OPT-EM-WMC-EXT-BR	EXTERNAL BACK BOX	OPT-PC-BUM	BUTTON
2" & 3"	OPT-EM-WMC-EXT-BN	EXTERNAL BACK BOX	**SENSOR**	DESCRIPTION
2" & 3"	OPT-EM-WMC-EXT-WH	EXTERNAL BACK BOX	OPT-SEN-WMC	ONLY FOR 4" & UP
2" & 3"	OPT-EM-WMC-EXT-BK	EXTERNAL BACK BOX	OPT-SEN-NLS-WMC	WG NETWORK SENSOR
4" & UP	OPT-EM-WMC	INTERNAL	OPT-SEN-KEILTON-WMC	KEILTON NETWORK SENSOR
			WEC-8RC	REMOTE CONTROL
	POWDER COATING		**277V OPTION**	DESCRIPTION
	N/A		OPT-277V	INTERNAL (ONLY FOR WMC DL UDL)

WMC4-UDL-CD-RGBW-BK

WMC4S-UDL-CD-RGBW-BK

4” UP/DOWN CYLINDER COMBINED DISTRIBUTION **120-277V** DUAL DIM

CATALOG NO.	DESCRIPTION			PCK QTY
WMC4-UDL-CD-MCT-BK-DD-P	12W	840LM	30K/40K/50K - Round Black	6
WMCS4-UDL-CD-MCT-BK-DD-P	12W	840LM	30K/40K/50K - Square Black	6

WMC4-UDL-CD-RGBW-BK

WMC4S-UDL-CD-RGBW-BK

TC-RGBW-RC

4” ROUND UP/DOWN CYLINDER COMBINED DISTRIBUTION **120-277V** DUAL DIM WG SMART APP OR REMOTE COMPATIBLE RGBW

CATALOG NO.	DESCRIPTION			PCK QTY
WMC4-UDL-CD-RGBW-BK	12W	840LM	RGBW - Round Black	6
WMC4S-UDL-CD-RGBW-BK	12W	840LM	RGBW - Square Black	6

WET LOCATIONS
EM CAPABLE
SENSOR OPTION

WMCL-DL-BR

WMCL-DL-BK

WMCL-DL-WH

WMCL-DL-BN

WMCL-DL-AZ

WMCL-UDL-BN

WMCL-UDL-WH

WMC6-24-UDL-BK

WMC6-24-UDL-BR

WMC6-24-UDL-WH

WMC6-24-UDL-BN

WMC8-UDL-BR

WMC8-UDL-BN

WMC8-UDL-BK

WMC8-UDL-WH

6” & 8” LED OUTDOOR CYLINDER LIGHTS, IP65 CCT-ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
MCT 6” LED CYLINDER LIGHTS, 120~277V (DOWN LIGHT) H: 8”				
WMCL-DL-MCT-BR	20W	1600LM	3000K/4000K/5000K - 45°, Bronze	4
WMCL-DL-MCT-BN	20W	1600LM	3000K/4000K/5000K - 45°, Brushed Nickel	4
WMCL-DL-MCT-WH	20W	1600LM	3000K/4000K/5000K - 45°, White	4
WMCL-DL-MCT-BK	20W	1600LM	3000K/4000K/5000K - 45°, Black	4
WMCL-DL-MCT-AZ	20W	1600LM	3000K/4000K/5000K - 45°, Antique Bronze	4
MCT 6” LED CYLINDER LIGHTS, 120~277V (UP/DOWN LIGHT) H: 18”				
WMCL-UDL-MCT-BN	40W	3200LM	3000K/4000K/5000K - 45°, Brushed Nickel	4
WMCL-UDL-MCT-WH	40W	3200LM	3000K/4000K/5000K - 45°, White	4

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION			PCK QTY
6" LED CYLINDER LIGHTS, 120~277V (UP/DOWN LIGHT SEPARATE CONTROLS) H: 24"				
WMC6-24-UDL-MCTP-DD-BK	2X18W/2X24W/2X30W	80LM/W	30K/40K/50K - Black	2
WMC6-24-UDL-MCTP-DD-BR	2X18W/2X24W/2X30W	80LM/W	30K/40K/50K - Bronze	2
WMC6-24-UDL-MCTP-DD-WH	2X18W/2X24W/2X30W	80LM/W	30K/40K/50K - White	2
WMC6-24-UDL-MCTP-DD-SIL	2X18W/2X24W/2X30W	80LM/W	30K/40K/50K - Silver	2
8" LED CYLINDER LIGHTS, 120-277V (DOWN LIGHT) H: 10.1"				
WMC8-DL-MCT-BR-D	40W	3200LM	3000K/4000K/5000K - 50°, Bronze	4
WMC8-DL-MCT-BN-D	40W	3200LM	3000K/4000K/5000K - 50°, Brushed Nickel	4
WMC8-DL-MCT-WH-D	40W	3200LM	3000K/4000K/5000K - 50°, White	4
WMC8-DL-MCT-BK-D	40W	3200LM	3000K/4000K/5000K - 50°, Black	4
8" LED CYLINDER LIGHTS, 120-277V (UP/DOWN LIGHT) H: 10.1"				
WMC8-UDL-MCT-BR-D	40W	3200LM	3000K/4000K/5000K - 50°, Bronze	4
WMC8-UDL-MCT-BN-D	40W	3200LM	3000K/4000K/5000K - 50°, Brushed Nickel	4
WMC8-UDL-MCT-WH-D	40W	3200LM	3000K/4000K/5000K - 50°, White	4
WMC8-UDL-MCT-BK-D	40W	3200LM	3000K/4000K/5000K - 50°, Black	4
CWMC6-DL32	CMC6 And WMC6 32mm Acrylic Drop Lens			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

SIZE	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
2" & 3"	OPT-EM-WMC-EXT-BR	EXTERNAL BACK BOX	OPT-PC-BUM	BUTTON
2" & 3"	OPT-EM-WMC-EXT-BN	EXTERNAL BACK BOX	SENSOR	DESCRIPTION
2" & 3"	OPT-EM-WMC-EXT-WH	EXTERNAL BACK BOX	OPT-SEN-WMC	ONLY FOR 4" & UP
2" & 3"	OPT-EM-WMC-EXT-BK	EXTERNAL BACK BOX	OPT-SEN-NLS-WMC	WG NETWORK SENSOR
4" & UP	OPT-EM-WMC	INTERNAL	OPT-SEN-KEILTON-WMC	KEILTON NETWORK SENSOR
			WEC-8RC	REMOTE CONTROL
	POWDER COATING		277V OPTION	DESCRIPTION
	N/A		OPT-277V	INTERNAL (ONLY FOR WMC DL UDL)



WMCSR-DL-BR WMCSR-DL-BK WMCSR-DL-WH WMCSR-DL-BN WMCSR-UD-BR WMCSR-UD-BK WMCSR-UD-WH WMCSR-UD-BN

4" LED ROUND-CORNER SQUARE OUTDOOR CYLINDER LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
WMCSR-UD-MCTP-D-BK	2 X 10W/15W/20W	100LM/W	30K/40K/50K - 11.8"H, Black	6
WMCSR-UD-MCTP-D-BR	2 X 10W/15W/20W	100LM/W	30K/40K/50K - 11.8"H, Bronze	6
WMCSR-UD-MCTP-D-SIL	2 X 10W/15W/20W	100LM/W	30K/40K/50K - 11.8"H, Silver	6
WMCSR-UD-MCTP-D-WH	2 X 10W/15W/20W	100LM/W	30K/40K/50K - 11.8"H, White	6
WMCSR-DL-MCTP-D-BK	10W/15W/20W	100LM/W	30K/40K/50K - 8.5"H, Black	6
WMCSR-DL-MCTP-D-BR	10W/15W/20W	100LM/W	30K/40K/50K - 8.5"H, Bronze	6
WMCSR-DL-MCTP-D-SIL	10W/15W/20W	100LM/W	30K/40K/50K - 8.5"H, Silver	6
WMCSR-DL-MCTP-D-WH	10W/15W/20W	100LM/W	30K/40K/50K - 8.5"H, White	6

TRIAC DIMMABLE | WET LOCATIONS | EM CAPABLE | SENSOR OPTION | MCT

WMCS-DL-BR

WMCS-DL-BN

WMCS-UDL-BR

WMCS-UDL-BN

4" EM CAPABLE LOCATION LED SQUARE OUTDOOR CYLINDER LIGHT, IP65 CCT-ADJUSTABLE
ALL MODELS ARE AVAILABLE IN BRONZE, BRUSHED NICKEL, BLACK, & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
4" LED SQUARE CYLINDER LIGHTS, 120V (DOWN LIGHT) H: 8"				
WMCS-DL-MCT-BR-DT	12W	960LM	3000K/4000K/5000K - 30°, Bronze	6
WMCS-DL-MCT-BN-DT	12W	960LM	3000K/4000K/5000K - 30°, Brushed Nickel	6
WMCS-DL-MCT-WH-DT	12W	960LM	3000K/4000K/5000K - 30°, White	6
WMCS-DL-MCT-BK-DT	12W	960LM	3000K/4000K/5000K - 30°, Black	6
4" LED SQUARE CYLINDER LIGHTS, 120V (UP/DOWN LIGHT) H: 10-1/4"				
WMCS-UDL-MCT-BR-DT	24W	1920LM	3000K/4000K/5000K - 30°, Bronze	6
WMCS-UDL-MCT-BN-DT	24W	1920LM	3000K/4000K/5000K - 30°, Brushed Nickel	6
WMCS-UDL-MCT-WH-DT	24W	1920LM	3000K/4000K/5000K - 30°, White	6
WMCS-UDL-MCT-BK-DT	24W	1920LM	3000K/4000K/5000K - 30°, Black	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

SIZE	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
4" & UP	OPT-EM-WMCS	INTERNAL	OPT-PC-B	BUTTON
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-SEN-WMC	ONLY FOR 4" & UP
			OPT-SEN-NLS-WMCS	WG NETWORK SENSOR
			OPT-SEN-KEILTON-WMCS	KEILTON NETWORK SENSOR
			WEC-8RC	REMOTE CONTROL

TRIAC DIMMABLE | DIMMING 0-10V | WET LOCATIONS | EM CAPABLE | SENSOR OPTION | MCT

WMCS5-DL-BR

WMCS5-DL-BN

WMCS5-UDL-BR

WMCS5-UDL-BN

5” EM CAPABLE LOCATION LED SQUARE OUTDOOR CYLINDER LIGHT, IP65 CCT-ADJUSTABLE
ALL MODELS ARE AVAILABLE IN BRONZE, BRUSHED NICKEL, BLACK, & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
5” LED SQUARE CYLINDER LIGHTS, 120-277V (DOWN LIGHT) H: 8”				
WMCS5-DL-MCT-BR-DD	20W	1600LM	30K/40K/50K - 30°, Bronze	6
WMCS5-DL-MCT-BN-DD	20W	1600LM	30K/40K/50K - 30°, Brushed Nickel	6
WMCS5-DL-MCT-WH-DD	20W	1600LM	30K/40K/50K - 30°, White	6
WMCS5-DL-MCT-BK-DD	20W	1600LM	30K/40K/50K - 30°, Black	6
5” LED SQUARE CYLINDER LIGHTS, 120-277V (UP/DOWN LIGHT) H: 12”				
WMCS5-UDL-MCT-BR-DD	40W	3200LM	30K/40K/50K - 30°, Bronze	6
WMCS5-UDL-MCT-BN-DD	40W	3200LM	30K/40K/50K - 30°, Brushed Nickel	6
WMCS5-UDL-MCT-WH-DD	40W	3200LM	30K/40K/50K - 30°, White	6
WMCS5-UDL-MCT-BK-DD	40W	3200LM	30K/40K/50K - 30°, Black	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

SIZE	EM OPTION	DESCRIPTION
4" & UP	OPT-EM-WMCS	INTERNAL

POWDER COATING
N/A

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-WMC	ONLY FOR 4" & UP
OPT-SEN-NLS-WMCS	WG NETWORK SENSOR
OPT-SEN-KEILTON-WMCS	KEILTON NETWORK SENSOR
WEC-8RC	REMOTE CONTROL

WMCS5-36-UDL-MCTP-DD-BK

WMCS5-36-UDL-MCTP-DD-WH

WMCS5-36-UDL-MCTP-DD-BR

WMCS5-36-UDL-MCTP-DD-BN

5” LED SQUARE OUTDOOR CYLINDER LIGHTS - 36”H

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
WMCS5-36-UDL-MCTP-DD-BK	30W/40W/50W	80LM/W		30K/40K/50K - Black	1
WMCS5-36-UDL-MCTP-DD-WH	30W/40W/50W	80LM/W		30K/40K/50K - White	1
WMCS5-36-UDL-MCTP-DD-BR	30W/40W/50W	80LM/W		30K/40K/50K - Bronze	1
WMCS5-36-UDL-MCTP-DD-SIL	30W/40W/50W	80LM/W		30K/40K/50K - Silver	1

WMCS6-24-UDL-MCTP-DD-BK

WMCS6-24-UDL-MCTP-DD-BR

WMCS6-24-UDL-MCTP-DD-BN

WMCS6-24-UDL-MCTP-DD-WH

WMCS6-36-UDL-MCTP-DD-BK

WMCS6-36-UDL-MCTP-DD-BR

WMCS6-36-UDL-MCTP-DD-BN

WMCS6-36-UDL-MCTP-DD-WH

6" EM CAPABLE LOCATION LED SQUARE OUTDOOR CYLINDER LIGHT, IP65 CCT-ADJUSTABLE
ALL MODELS ARE AVAILABLE IN BRONZE, BRUSHED NICKEL, BLACK, & WHITE, H:24" OR 36"

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
WMCS6-24-UDL-MCTP-DD-BK	30W/40W/50W		80LM/W	30K/40K/50K -Black	2
WMCS6-24-UDL-MCTP-DD-WH	30W/40W/50W		80LM/W	30K/40K/50K - White	2
WMCS6-24-UDL-MCTP-DD-BR	30W/40W/50W		80LM/W	30K/40K/50K - Bronze	2
WMCS6-24-UDL-MCTP-DD-SIL	30W/40W/50W		80LM/W	30K/40K/50K - Silver	2
WMCS6-36-UDL-MCTP-DD-BK	30W/40W/50W		80LM/W	30K/40K/50K -Black	2
WMCS6-36-UDL-MCTP-DD-WH	30W/40W/50W		80LM/W	30K/40K/50K - White	2
WMCS6-36-UDL-MCTP-DD-BR	30W/40W/50W		80LM/W	30K/40K/50K - Bronze	2
WMCS6-36-UDL-MCTP-DD-SIL	30W/40W/50W		80LM/W	30K/40K/50K - Silver	2

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

SIZE	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
4" & UP	OPT-EM-WMCS	INTERNAL	OPT-PC-B	BUTTON
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-SEN-WMC	ONLY FOR 4" & UP
			OPT-SEN-NLS-WMCS	WG NETWORK SENSOR
			OPT-SEN-KEILTON-WMCS	KEILTON NETWORK SENSOR
			WEC-8RC	REMOTE CONTROL



WMCS8-UDL-BK

8” EM CAPABLE LOCATION LED SQUARE OUTDOOR CYLINDER LIGHT, IP65 CCT-ADJUSTABLE ALL MODELS ARE AVAILABLE IN BRONZE, BRUSHED NICKEL, BLACK, & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
WMCS8-UDL-MCTD-BK-D	40W	80LM/W	30K/40K/50K - 30°, Bronze	1
WMCS8-UDL-MCTD-BR-D	40W	80LM/W	30K/40K/50K - 30°, Brushed Nickel	1
WMCS8-UDL-MCTD-WH-D	40W	80LM/W	30K/40K/50K - 30°, White	1
WMCS8-UDL-MCTD-SIL-D	40W	80LM/W	30K/40K/50K - 30°, Black	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

SIZE	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
4" & UP	OPT-EM-WMCS	INTERNAL	OPT-PC-B	BUTTON
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-SEN-WMC	ONLY FOR 4" & UP
			OPT-SEN-NLS-WMCS	WG NETWORK SENSOR
			OPT-SEN-KEILTON-WMCS	KEILTON NETWORK SENSOR
			WEC-8RC	REMOTE CONTROL

WMA-UDL-MCTP-BR-D

WMA-UDL-MCTP-BK-D

WMA-UDL-MCTP-WH-D

WMA-UDL-MCTP-SIL-D

7” ARCHITECTURAL COMMERCIAL DESIGNER OUTDOOR CYLINDER, UP/DOWN CONTROLS 14”H

CATALOG NO.	DESCRIPTION			PCK QTY
WMA-UDL-MCTP-BK-D	18W/30W/45W/60W	110LM/W	27K/30K/35K/40K/50K - Black	1
WMA-UDL-MCTP-BR-D	18W/30W/45W/60W	110LM/W	27K/30K/35K/40K/50K - Bronze	1
WMA-UDL-MCTP-WH-D	18W/30W/45W/60W	110LM/W	27K/30K/35K/40K/50K - White	1
WMA-UDL-MCTP-SIL-D	18W/30W/45W/60W	110LM/W	27K/30K/35K/40K/50K - Silver	1

WMC6-UDL-MCTP-BK-DD-P

WMC6-UDL-MCTP-BR-DD-P

WMC6-UDL-MCTP-BN-DD-P

WMC6-UDL-MCTP-WH-DD-P

WMC6-UDL-MCTP-AZ-DD-P

6” LED OUTDOOR CYLINDER LIGHTS, IP65 CCT-ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
WMC6-UDL-MCTP-BK-DD-P	2x12W/2x16W/2x20W	80LM/W	30K/40K/50K - 45°, Black	4
WMC6-UDL-MCTP-BR-DD-P	2x12W/2x16W/2x20W	80LM/W	30K/40K/50K - 45°, Bronze	4
WMC6-UDL-MCTP-BN-DD-P	2x12W/2x16W/2x20W	80LM/W	30K/40K/50K - 45°, Brushed Nickel	4
WMC6-UDL-MCTP-WH-DD-P	2x12W/2x16W/2x20W	80LM/W	30K/40K/50K - 45°, White	4
WMC6-UDL-MCTP-AZ-DD-P	2x12W/2x16W/2x20W	80LM/W	30K/40K/50K - 45°, Antique Bronze	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

SIZE	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
2” & 3”	**OPT-EM-WMC-EXT-BR**	EXTERNAL BACK BOX	**OPT-PC-BUM**	BUTTON
2” & 3”	**OPT-EM-WMC-EXT-BN**	EXTERNAL BACK BOX	**SENSOR**	DESCRIPTION
2” & 3”	**OPT-EM-WMC-EXT-WH**	EXTERNAL BACK BOX	**OPT-SEN-WMC**	ONLY FOR 4” & UP
2” & 3”	**OPT-EM-WMC-EXT-BK**	EXTERNAL BACK BOX	**OPT-SEN-NLS-WMC**	WG NETWORK SENSOR
4” & UP	**OPT-EM-WMC**	INTERNAL	**OPT-SEN-KEILTON-WMC**	KEILTON NETWORK SENSOR
			WEC-8RC	REMOTE CONTROL
	POWDER COATING		**277V OPTION**	DESCRIPTION
	N/A		**OPT-277V**	INTERNAL (ONLY FOR WMC DL UDL)

WALL SCONCES

01 Lunette | 02 Aperture | 03 Grasp | 04 Curve | 05 Pen



06 Still | 07 Passage | 08 Crush | 10 Burrow | 51Tunnel | 52 Grille

CREST BY WESTGATE LED WALL SCONCE, ALL MODELS PROVIDE UP/DOWN LIGHT

CATALOG NO.	DESCRIPTION		
CRES-51-30K-BR	15W	1300LM	3000K
CRES-51-30K-SIL	15W	1300LM	3000K
CRES-51-40K-BR	15W	1300LM	4000K
CRES-51-40K-SIL	15W	1300LM	4000K
CRES-51-50K-BR	15W	1300LM	5000K
CRES-51-50K-SIL	15W	1300LM	5000K
CRES-52-30K-BR	15W	1300LM	3000K
CRES-52-30K-SIL	15W	1300LM	3000K
CRES-52-40K-BR	15W	1300LM	4000K
CRES-52-40K-SIL	15W	1300LM	4000K
CRES-52-50K-BR	15W	1300LM	5000K
CRES-52-50K-SIL	15W	1300LM	5000K

CATALOG NO.	DESCRIPTION		
CRE-MP-01-30K-BR	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-01-30K-SIL	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-01-40K-BR	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-01-40K-SIL	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-01-50K-BR	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-01-50K-SIL	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-02-30K-BR	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-02-30K-SIL	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-02-40K-BR	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-02-40K-SIL	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-02-50K-BR	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-02-50K-SIL	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-03-30K-BR	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-03-30K-SIL	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-03-40K-BR	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-03-40K-SIL	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-03-50K-BR	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-03-50K-SIL	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-04-30K-BR	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-04-30K-SIL	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-04-40K-BR	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-04-40K-SIL	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-04-50K-BR	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-04-50K-SIL	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-05-30K-BR	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-05-30K-SIL	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-05-40K-BR	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-05-40K-SIL	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-05-50K-BR	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-05-50K-SIL	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-06-30K-BR	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-06-30K-SIL	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-06-40K-BR	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-06-40K-SIL	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-06-50K-BR	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-06-50K-SIL	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-07-30K-BR	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-07-30K-SIL	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-07-40K-BR	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-07-40K-SIL	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-07-50K-BR	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-07-50K-SIL	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-08-30K-BR	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-08-30K-SIL	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-08-40K-BR	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-08-40K-SIL	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-08-50K-BR	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-08-50K-SIL	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-10-30K-BR	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-10-30K-SIL	5W/10W/15W/20W	90LM/W	3000K
CRE-MP-10-40K-BR	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-10-40K-SIL	5W/10W/15W/20W	90LM/W	4000K
CRE-MP-10-50K-BR	5W/10W/15W/20W	90LM/W	5000K
CRE-MP-10-50K-SIL	5W/10W/15W/20W	90LM/W	5000K

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL	OPT-EM-CRE	INTERNAL	OPT-PC-B	120-277V
	(Not Compatibe With CRES)			
	POWDER COATING		SENSOR	
	OPT-CLR-85(BK/GR/SR/WH)		DEPENDS ON MODEL-CALL	

LDSC-18-MCTP-DD-BK

LDSC-18-MCTP-DD-ORB

LDSC-18-MCTP-DD-SIL

18” OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE **120-277V**, 9” WIDE

CATALOG NO.	DESCRIPTION			PCK QTY
LDSC-18-MCTP-DD-ORB	15W/20W/25W	80LM/W	30K/40K/50K - Oil-Rubbed Bronze	4
LDSC-18-MCTP-DD-SIL	15W/20W/25W	80LM/W	30K/40K/50K - Silver	4
LDSC-18-MCTP-DD-BK	15W/20W/25W	80LM/W	30K/40K/50K - Black	4

LDSC-24-MCTP-DD-BK

LDSC-24-MCTP-DD-ORB

LDSC-24-MCTP-DD-SIL

24” OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE **120-277V**, 9” WIDE

CATALOG NO.	DESCRIPTION			PCK QTY
LDSC-24-MCTP-DD-ORB	20W/25W/30W	80LM/W	30K/40K/50K - Oil-Rubbed Bronze	4
LDSC-24-MCTP-DD-SIL	20W/25W/30W	80LM/W	30K/40K/50K - Silver	4
LDSC-24-MCTP-DD-BK	20W/25W/30W	80LM/W	30K/40K/50K - Black	4

LDS-MCT5-DT-BK

LDS-MCT5-DT-ORB

LDS-MCT5-DT-SIL

10” OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE **120V**, 7” WIDE

CATALOG NO.	DESCRIPTION			PCK QTY
LDS-MCT5-DT-ORB	15W	980LM	27K/30K/35K/40K/50K - Oil-Rubbed Bronze	4
LDS-MCT5-DT-SIL	15W	980LM	27K/30K/35K/40K/50K - Silver	4
LDS-MCT5-DT-BK	15W	980LM	27K/30K/35K/40K/50K - Black	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LDS	OPT-EM-LDS		OPT-PC-B1	BUTTON
LDSX-S	OPT-EM-LDSX-S			
LDSX-L	OPT-EM-LDSX-L		SENSOR	DESCRIPTION
	277V OPTION	DESCRIPTION	OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL
	OPT-277V-LDS	EXTERNAL BOX	OPT-SEN-NLS-LDS	WG NETWORK SENSOR
	POWDER COATING		OPT-SEN-KEILTON-LDS	KEILTON NETWORK SENSOR
	N/A			

LDS-RGBW-BK

TC-RGBW-RC

7” OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE **120V**, 7” WIDE RGB WG APP OR REMOTE CONTROL

CATALOG NO.	DESCRIPTION			PCK QTY
LDS-RGBW-BK	15W	980LM	5CCT AND RGB - Black	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LDS	OPT-EM-LDS		OPT-PC-B1	BUTTON
LDSX-S	OPT-EM-LDSX-S			
LDSX-L	OPT-EM-LDSX-L		SENSOR	DESCRIPTION
	277V OPTION	DESCRIPTION	OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL
	OPT-277V-LDS	EXTERNAL BOX	OPT-SEN-NLS-LDS	WG NETWORK SENSOR
	POWDER COATING		OPT-SEN-KEILTON-LDS	KEILTON NETWORK SENSOR
	N/A			

LDS-MCT5-DT-PIR-BK

LDS-MCT5-DT-PIR-ORB

LDS-MCT5-DT-PIR-SIL

10” OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE WITH PIR SENSOR **120V**, 7” WIDE

CATALOG NO.	DESCRIPTION			PCK QTY
LDS-MCT5-DT-PIR-ORB	15W	980LM	27K/30K/35K/40K/50K - Oil-Rubbed Bronze	4
LDS-MCT5-DT-PIR-SIL	15W	980LM	27K/30K/35K/40K/50K - Silver	4
LDS-MCT5-DT-PIR-BK	15W	980LM	27K/30K/35K/40K/50K - Black	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
LDS	**OPT-EM-LDS**	
LDSX-S	**OPT-EM-LDSX-S**	
LDSX-L	**OPT-EM-LDSX-L**	

277V OPTION	DESCRIPTION
OPT-277V-LDS	EXTERNAL BOX

POWDER COATING
N/A

PHOTOCELL	DESCRIPTION
OPT-PC-B1	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL
OPT-SEN-NLS-LDS	WG NETWORK SENSOR
OPT-SEN-KEILTON-LDS	KEILTON NETWORK SENSOR

CREA-56-MCTP-BR

CREA-56-MCTP-WH

CREA-57-MCTP-BR

CREA-57-MCTP-WH

BEAM ADJUSTABLE

ADJUSTABLE BEAM ANGLE OUTDOOR/INDOOR DESIGNER WALL SCONCE **120-277V**

CATALOG NO.	DESCRIPTION		
CREA-56-MCTP-BR	14W/18W/24W	80LM/W	30K/40K/50K - Square, Bronze
CREA-57-MCTP-BR	14W/18W/24W	80LM/W	30K/40K/50K - Round, Bronze
CREA-56-MCTP-WH	14W/18W/24W	80LM/W	30K/40K/50K - Square, White
CREA-57-MCTP-WH	14W/18W/24W	80LM/W	30K/40K/50K - Round, White

LRS-K-24-MCT5-BR

24” DIE-CAST MODERN WALL SCONCE, MODEL K SELECTABLE 3CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-K-24-MCT5-BR	24W	700LM	27K/30K/35K/40K/50K - Bronze, 24" H	8

LRS-WS-12

LRS-WS-18

DIE-CAST OUTDOOR MODERN INDIRECT WALL SCONCE, MODEL WS SELECTABLE 3CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-WS-12-MCT5-BR	20W	1000LM	27K/30K/35K/40K/50K - Bronze, 12" H	10
LRS-WS-18-MCT5-BR	30W	1500LM	27K/30K/35K/40K/50K - Bronze, 18" H	10

LRS-R1-MCT5-DD-ORB

LRS-R2-MCT5-DD-ORB

DUAL-DIMMING MODERN RESIDENTIAL/COMMERCIAL WALL SCONCE

CATALOG NO.	DESCRIPTION			PCK QTY
LRS R MODERN RESIDENTIAL/COMMERCIAL WALL SCONCES				
LRS-R1-MCT5-DD-ORB	20W	1500LM	27K/30K/35K/40K/50K - 16"	
LRS-R2-MCT5-DD-ORB	25W	1875LM	27K/30K/35K/40K/50K - 24"	

LRS-S1-MCT5-DD-ORB

LRS-S2-MCT5-DD-ORB

DUAL-DIMMING MODERN RESIDENTIAL/COMMERCIAL WALL SCONCE

CATALOG NO.	DESCRIPTION			PCK QTY
LRS S MODERN RESIDENTIAL/COMMERCIAL WALL SCONCES				
LRS-S1-MCT5-DD-ORB	20W	1500LM	27K/30K/35K/40K/50K - 16"	
LRS-S2-MCT5-DD-ORB	25W	1875LM	27K/30K/35K/40K/50K - 24"	

LRS-SG2

LRS-SG3

LRS-SG1

LRS-SG4-MCT-BK

SEEDED GLASS WALL SCONCE, 120V - 3CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-SG1-MCT-ORB	12W	1200LM	30K/40K/50K - Oil-Rubbed Bronze, 6"X14", 120V	4
LRS-SG2-MCT-ORB	12W	1200LM	30K/40K/50K - Oil-Rubbed Bronze, 7"X18", 120V	4
LRS-SG3-MCT-ORB	12W	1200LM	30K/40K/50K - Oil-Rubbed Bronze, 6"X14", 120V	4
LRS-SG4-MCT-BK	12W	1200LM	30K/40K/50K - 11in Black	5
DIMMING 0-10V TRIAC DIMMABLE	**SEEDED GLASS WALL SCONCES, 120V - 3CCT DUAL DIMMING**			
LRS-SG1-MCT-DD-ORB	15W	1500LM	30K/40K/50K - Oil-Rubbed Bronze, 6"X14", 120V	4
LRS-SG2-MCT-DD-ORB	15W	1500LM	30K/40K/50K - Oil-Rubbed Bronze, 7"X18", 120V	4
LRS-SG3-MCT-DD-ORB	15W	1500LM	30K/40K/50K - Oil-Rubbed Bronze, 6"X14", 120V	4

LDSS-MCT5-ORB

OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE

CATALOG NO.	DESCRIPTION			PCK QTY
10" OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE, 120V (8.7" WIDE)				
LDSS-MCT5-ORB	12W	1200LM	27K/30K/35K/40K/50K - Oil-Rubbed Bronze	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	277V OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LDSW, LDSS	N/A	N/A	OPT-PC-B1	BUTTON
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL
			OPT-SEN-NLS-LDSW	WG NETWORK SENSOR
			OPT-SEN-KEILTON-LDSW	KEILTON NETWORK SENSOR

LDSX-S-12-16W-MCTP-ORB

LDSX-L-18-22W-MCTP-ORB

LDSX-L-18-22W-MCTP-ORB

OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE 120-277V

CATALOG NO.	DESCRIPTION		
FULL-LENS WALL SCONCE, POWER & CCT-ADJUSTABLE			
LDSX-S-12-16W-MCTP-ORB	12W/14W/16W	100LM/W	30K/40K/50K - 8" Oil-Rubbed Bronze
LDSX-L-18-22W-MCTP-ORB	18W/20W/22W	100LM/W	30K/40K/50K - 14" Oil-Rubbed Bronze

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LDS	OPT-EM-LDS		OPT-PC-B1	BUTTON
LDSX-S	OPT-EM-LDSX-S		SENSOR	DESCRIPTION
LDSX-L	OPT-EM-LDSX-L		OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL
			OPT-SEN-NLS-LDS	WG NETWORK SENSOR
			OPT-SEN-KEILTON-LDS	KEILTON NETWORK SENSOR
	POWDER COATING		277V OPTION	DESCRIPTION
	N/A		OPT-277V-LDS	EXTERNAL BOX

LRS-PV-MCT-DD



LRS-PV-RGBW

TC-RGBW-RC

LED RESIDENTIAL LANTERN WITH PHOTOCELL 120V

CATALOG NO.		DESCRIPTION	
12" OUTDOOR/INDOOR CEILING LIGHT, 120-277V			
LRS-PV-MCT-DD	25W	1920LM	30K/40K/50K - 12", Oil-Rubbed Bronze
RGB WG APP OR REMOTE CONTROL 13" OUTDOOR/INDOOR CEILING LIGHT, 120-277V			
LRS-PV-RGBW	25W	1920LM	5CCT AND RGB - 13", Oil-Rubbed Bronze

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
LRS-L, LRS-S, LRS-SWG	N/A	N/A
LRS-PV	OPT-EM-LRS-PV	N/A
	POWDER COATING	
	N/A	

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON
SENSOR	DESCRIPTION
OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL FOR LRS-PV, LRS-C, LRS-D
OPT-SEN-NLS-LRS	WG NETWORK SENSOR
OPT-SEN-KEILTON-LRS	KEILTON NETWORK SENSOR

LRS-A-MCT-PC

LRS-B-40K-PC
LRS-B-MCT-PC

LED RESIDENTIAL LANTERN WITH PHOTOCELL 120V

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-A-MCT-PC	12W	1150LM	3000K/4000K/5000K	6
LRS-B-40K-PC	6W	550LM	4000K	12
LRS-B-MCT-PC	6W	550LM	3000K/4000K/5000K	12

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
LRS-L, LRS-S, LRS-SWG	N/A	N/A
LRS-PV	OPT-EM-LRS-PV	N/A
	POWDER COATING	
	N/A	

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON
SENSOR	DESCRIPTION
OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL FOR LRS-PV, LRS-C, LRS-D
OPT-SEN-NLS-LRS	WG NETWORK SENSOR
OPT-SEN-KEILTON-LRS	KEILTON NETWORK SENSOR

LRS-C-MCT-D

LRS-D-30K-D
LRS-D-40K-D

LED DIMMABLE RESIDENTIAL LANTERN **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-C-MCT-D	12W	1100LM	3000K/4000K/5000K	6
LRS-D-30K-D	12W	1100LM	3000K	6
LRS-D-40K-D	12W	1100LM	4000K	6

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
LRS-L, LRS-S, LRS-SWG	**N/A**	N/A
LRS-PV	**OPT-EM-LRS-PV**	N/A

POWDER COATING
N/A

PHOTOCELL	DESCRIPTION
OPT-PC-B	BUTTON

SENSOR	DESCRIPTION
OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL FOR LRS-PV, LRS-C, LRS-D
OPT-SEN-NLS-LRS	WG NETWORK SENSOR
OPT-SEN-KEILTON-LRS	KEILTON NETWORK SENSOR

LRS-SH12

LRS-SH24

LRS-SH40

Shown with Honey Lens

SHOJI WINDOW WALL SCONCE, DUAL DIMMING **120-277V** POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-SH-12-MCTP-DT-ORB	9W/13W/17W	70LM/W	30K/40K/50K - Oil-rubbed bronze, 7"X12"	6
LRS-SH-12-MCTP-DD-ORB	9W/13W/17W	70LM/W	30K/40K/50K - Oil-rubbed bronze, 7"X12"	6
LRS-SH-24-MCTP-DD-ORB	18W/24W/30W	70LM/W	30K/40K/50K - Oil-rubbed bronze, 7"X24"	4
LRS-SH-40-MCTP-DD-ORB	40W/60W/80W	70LM/W	30K/40K/50K - Oil-rubbed bronze, 13"X40"	1
LRS-SH-12-HLK	Honey-Color Replacement Lens for LRS-SH-12			
LRS-SH-24-HLK	Honey-Color Replacement Lens for LRS-SH-24			

LDSL-MCT-D-BK

LDSL-MCT-D-BZ

LDSL-MCT-D-SIL

18" OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE **120-277V, 6" WIDE**

CATALOG NO.	DESCRIPTION			PCK QTY
LDSL-MCT-D-BZ	20W	1500LM	3000K/4000K/5000K - Bronze	6
LDSL-MCT-D-SIL	20W	1500LM	3000K/4000K/5000K - Silver	6
LDSL-MCT-D-BK	20W	1500LM	3000K/4000K/5000K - Black	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LDSL	OPT-EM-LDSL	INTERNAL	OPT-PC-B	BUTTON
LDSXL	OPT-EM-LDSXL	INTERNAL		
LDSXL	OPT-EM-LDSXL-277V	INTERNAL		
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

LDSXL-MCT-DD-BK

LDSXL-MCT-DD-ORB

LDSXL-MCT-DD-SIL

24" OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE **120-277V, 6" WIDE**

CATALOG NO.	DESCRIPTION			PCK QTY
LDSXL-MCT-DD-ORB	25W	1800LM	30K/40K/50K - Oil-Rubbed Bronze	4
LDSXL-MCT-DD-SIL	25W	1800LM	30K/40K/50K - Silver	4
LDSXL-MCT-DD-BK	25W	1800LM	30K/40K/50K - Black	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LDSL	OPT-EM-LDSL	INTERNAL	OPT-PC-B	BUTTON
LDSXL	OPT-EM-LDSXL	INTERNAL		
LDSXL	OPT-EM-LDSXL-277V	INTERNAL		
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

LDSXL-46-MCT-DD-BK

LDSXL-46-MCT-DD-ORB

LDSXL-46-MCT-DD-SIL

46” OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE 120-277V, 6” WIDE

CATALOG NO.	DESCRIPTION			PCK QTY
LDSXL-46-MCT-DD-ORB	50W	3600LM	30K/40K/50K - Oil-Rubbed Bronze	2
LDSXL-46-MCT-DD-SIL	50W	3600LM	30K/40K/50K - Silver	2
LDSXL-46-MCT-DD-BK	50W	3600LM	30K/40K/50K - Black	2

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LDSL	**OPT-EM-LDSL**	INTERNAL	**OPT-PC-B**	BUTTON
LDSXL	**OPT-EM-LDSXL**	INTERNAL		
LDSXL	**OPT-EM-LDSXL-277V**	INTERNAL		
	POWDER COATING		**SENSOR**	DESCRIPTION
	N/A		**N/A**	N/A



LDSB-40-MCTP-DD-ORB

LDSB-40-MCTP-DD-BK

LDSB-40-MCTP-DD-SIL

40” OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE 120-277V, 14” WIDE

CATALOG NO.	DESCRIPTION			PCK QTY
LDSB-40-MCTP-DD-BK	40W/60W/80W	80LM/W	30K/40K/50K - Black	1
LDSB-40-MCTP-DD-ORB	40W/60W/80W	80LM/W	30K/40K/50K - Oil-Rubbed Bronze	1
LDSB-40-MCTP-DD-SIL	40W/60W/80W	80LM/W	30K/40K/50K - Silver	1

LRS-T1-MCT5-DD-ORB

LRS-T2-MCT5-DD-ORB

DUAL-DIMMING MODERN RESIDENTIAL/COMMERCIAL WALL SCONCE

CATALOG NO.	DESCRIPTION		
LRS T MODERN RESIDENTIAL/COMMERCIAL WALL SCONCES			
LRS-T1-MCT5-DD-ORB	20W	1500LM	27K/30K/35K/40K/50K - 16"
LRS-T2-MCT5-DD-ORB	25W	1875LM	27K/30K/35K/40K/50K - 24"

LRS-TU-MCT5-DD-BR

LRS-TU-MCT5-DD-BK

LRS-TU-MCT5-DD-WH

LRS-TU-MCT5-DD-BN

Up-Down lights -Brushed Nicke

UP/DOWN TUNNEL WALL SCONCE RESIDENTIAL/COMMERCIAL DUAL DIMMING 12"H X 5.5"W X 2-1/8" D

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-TU-MCT5-DD-BK	2X12W	1920LM	27K/30K/35K/40K/50K - 30°, Bronze	6
LRS-TU-MCT5-DD-BN	2X12W	1920LM	27K/30K/35K/40K/50K - 30°, Brushed Nickel	6
LRS-TU-MCT5-DD-BR	2X12W	1920LM	27K/30K/35K/40K/50K - 30°, White	6
LRS-TU-MCT5-DD-WH	2X12W	1920LM	27K/30K/35K/40K/50K - 30°, Black	6

LRS-CR2-MCT-BR

8" DIE-CAST MODERN UP/DOWN WALL SCONCE, MODEL CR SELECTABLE 3CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-CR2-MCT-BR	2x6W	840LM	30K/40K/50K - Bronze, 8" H	8



LRS-Q-MCT5-BR

WALL CUBE WITH ADJUSTABLE BEAM ANGLE UP/DOWN LIGHT, OUTDOOR, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-Q-MCT5-BR	15W	800LM	27K/30K/35K/40K/50K - Bronze	10
LRS-Q-MCT5-BK	15W	800LM	27K/30K/35K/40K/50K - Black	10
LRS-Q-MCT5-WH	15W	800LM	27K/30K/35K/40K/50K - White	10

ERSH-25-BK

ERSH-185-BK

ERSH-25-BK

ERSH-PT185-BK

ERSH-18R-BK

ERSH-182-BK

ERSH-12C-BK

E26 GLASS WALL SCONCE INCLUDES LED T LAMP

CATALOG NO.	DESCRIPTION			PCK QTY
ERSH-1325-BK	6W	520LM	3000K - 13.25" Black	1
ERSH-185-BK	6W	520LM	3000K - 18.5" Black	1
ERSH-25-BK	6W	780LM	3000K - 25" Black	1
ERSH-PT185-BK	6W	520LM	3000K - 18.5" Black	1
ERSH-18R-BK	6W	700LM	3000K - Black	1
ERSH-18R2-BK	2X6W	2X700LM	3000K - Black	1
ERSH-12C-BK	2X4W	2X500LM	3000K - Black	1

LDSW-MCT5-ORB

LDSW-MCT5-SIL

OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE

CATALOG NO.	DESCRIPTION			PCK QTY
10" OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE, 120V (10" WIDE)				
LDSW-MCT5-ORB	12W	1200LM	27K/30K/35K/40K/50K - Oil-Rubbed Bronze	6
LDSW-MCT5-SIL	12W	1200LM	27K/30K/35K/40K/50K - Silver	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	277V OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
LDSW, LDSS	N/A	N/A	OPT-PC-B1	BUTTON
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-SEN-LDS	INTERNAL MICROWAVE BI-LEVEL
			OPT-SEN-NLS-LDSW	WG NETWORK SENSOR
			OPT-SEN-KEILTON-LDSW	KEILTON NETWORK SENSOR

COMMERCIAL INDOOR

LPS SERIES

LPNG SERIES

LPNP SERIES

LPNG-RGBW SERIES

TGL SERIES

SCXT SERIES

FEL SERIES

LPS SERIES


LPSB SERIES

SRL SERIES


LP-SLF SERIES

LTRE SERIES

LTRA SERIES

LTRG SERIES

LTRB SERIES

LTRD SERIES

LTRC SERIES

LTRI SERIES

LTRL SERIES

LTRM SERIES

LTRR SERIES

LTRW SERIES

LPCR SERIES

LTRAR SERIES

LRP-HL SERIES

LRT-HL SERIES

LSS SERIES

LSP SERIES

LSL SERIES

LSN SERIES

WA SERIES

SLR SERIES

LCL SERIES

CCL SERIES

LRSL SERIES

LRSL SERIES

WAS SERIES

WAE SERIES

WAEA SERIES

LPF SERIES

WASLR SERIES

SCLP SERIES

SCLP SERIES

SPL SERIES

SCLL SERIES

SCE SERIES

SCPL-UD SERIES

SCLP-UD SERIES

Search for the series name @WESTGATEMFG.COM

CRLX SERIES



CRL SERIES

CRLE SERIES

CRLE-FR SERIES

WPMX SERIESCRLEB

RSLC SERIES

CRLC SERIES

POB SERIES

GRIP & SUSPENSION SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

PANEL LIGHTS

LPS-2X2-20-40W-MCTP-D

LPS-1X4-20-40W-MCTP-D

LPS-2X4-30-50W-MCTP-D

INTERNAL-DRIVER LED SURFACE/RECESSED MOUNT PANEL, EDGELIT POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LPS-2X2-20-40W-MCTP-D	20W/33W/40W	100LM/W	30K/40K/50K	1
LPS-2X4-30-50W-MCTP-D	30W/40W/50W	100LM/W	30K/40K/50K	1
LPS-1X4-20-40W-MCTP-D	20W/33W/40W	100LM/W	30K/40K/50K	1

LPNG-1X4-MCTP4

LPNG-2X2-MCTP4

LPNG-2X4-MCTP4

LPNG-1X4-MCTP4-BK

LPNG-2X2-MCTP4-BK

LPNG-2X4-MCTP4-BK

LED BACKLIT PANEL LIGHT 100~277VAC MULTI COLOR TEMPERATURE & MULTI POWER

CATALOG NO.	DESCRIPTION			PCK QTY
MCTP LPNG-2X2-MCTP4	20/30/40W		30K/35K/40K/50K	4
LPNG-2X4-4KLM-50K-D*	40W	4200LM	5000K	4
LPNG-2X4-5KLM-35K-D*	50W	5140LM	3500K	4
MCTP LPNG-2X4-MCTP4	30/40/50W		30K/35K/40K/50K	4
LPNG-2X4-6KLM-50K-D	60W	6600LM	5000K	4
LPNG-2X4-6KLM-40K-D	60W	6600LM	4000K	4
LPNG-2X4-6KLM-35K-D	60W	6300LM	3500K	4
LPNG-2X4-7KLM-40K-D	60W	7920LM	4000K	4
LPNG-2X4-7KLM-35K-D	60W	7560LM	3500K	4
MCTP LPNG-2X4-8KLM-MCTP4	58W/68W/80W	100LM/W	30K/35K/40K/50K	4
MCTP LPNG-1X4-MCTP	20/30/40W		35K/40K/50K	4
MCTP LPNG-1X4-MCTP4	20/30/40W		30K/35K/40K/50K	4
MCTP LPNG-2X2-MCTP4-BK	20W/30W/40W		30K/35K/40K/50K	4
MCTP LPNG-2X4-MCTP4-BK	30W/40W/50W		30K/35K/40K/50K	4
MCTP LPNG-1X4-MCTP4-BK	20W/30W/40W		30K/35K/40K/50K	4

WHILE SUPPLIES LAST*

LPNP-1X4-MCTP4

LPNP-2X4-MCTP4

LPNP-2X2-MCTP4

SENSOR-READY PLUG & PLAY

WEC-2PR-28-AJ-WH
WEC-2BT-28-AJ-WH

WEC-3RC

PREMIUM FLAT PANEL 125 LM/W POWER AND WATTAGE SELECTABLE

CATALOG NO.	DESCRIPTION		PKG. QTY.	PCK QTY
PREMIUM FLAT PANELS, 125 LM/W, POWER AND WATTAGE SELECTABLE				
LPNP-2X2-4KLM-MCTP*	20W/30W/35W	125LM/W	35K/40K/50K	4
PREMIUM FLAT PANELS, 125 LM/W, POWER AND WATTAGE SELECTABLE				
LPNP-2X2-MCTP	19W/25W/32W	125LM/W	35K/40K/50K	4
LPNP-1X4-MCTP	19W/25W/32W	125LM/W	35K/40K/50K	4
LPNP-2X4-MCTP	24W/32W/40W	125LM/W	35K/40K/50K	4
PREMIUM FLAT PANELS, 125 LM/W, POWER AND WATTAGE SELECTABLE, SENSOR READY				
LPNP-2X2-MCTP-SR	19W/25W/32W	125LM/W	35K/40K/50K	4
LPNP-1X4-MCTP-SR	19W/25W/32W	125LM/W	35K/40K/50K	4
LPNP-2X4-MCTP-SR	24W/32W/40W	125LM/W	35K/40K/50K	4
PREMIUM FLAT PANELS, 125 LM/W, POWER AND WATTAGE SELECTABLE, EMERGENCY BACKUP				
LPNP-2X2-MCTP-EM	19W/25W/32W	125LM/W	35K/40K/50K	4
LPNP-1X4-MCTP-EM	19W/25W/32W	125LM/W	35K/40K/50K	4
LPNP-2X4-MCTP-EM	24W/32W/40W	125LM/W	35K/40K/50K	4
EM CAPABLE QUICK SHIP **WEC-2PR-28-AJ-WH**	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level & RC (Optional RC WEC-3RC)			
WEC-2BT-28-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level Bluetooth App Ready			

WHILE SUPPLIES LAST*



LPNG-1X4-RGBW

LPNG-2X2-RGBW

TC-RGBW-RC

RGBW LED PANEL LIGHT WESTGATE APP OR REMOTE CONTROL

CATALOG NO.	DESCRIPTION			PCK QTY
LPNG-2X2-RGBW	35W	4375LM	RGBW	4
LPNG-2X4-RGBW	40W	5000LM	RGBW	2
TC-RGBW-RC	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level & RC (Optional RC WEC-3RC)			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	FLEX WHIP	DESCRIPTION
ALL MODELS	OPT-EM-LPNG	EXTERNAL	OPT-FWH-63	6FT 3-Wire Whip
	PLUG IN CORD	DESCRIPTION	OPT-FWH-65	6FT 5-Wire Whip
	OPT-HBC-125TL-BK	8FT, 15A, 125V,BLACK	OPT-FWH-66	6FT 6-Wire Whip
	OPT-HBC-277TL-BK	8FT, 15A, 277V,BLACK	SENSOR	DESCRIPTION
	OPT-HBC-125SB-BK	10FT, 15A, 125V,18/3STR,BLCK	OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
	POWDER COATING		OPT-SEN-NLS-LPNG	WG NETWORK SENSOR
	OPT-CLR-LPNG		OPT-SEN-KEILTON-LPNG	KEILTON NETWORK SENSOR
			WEC-3RC	OPTIONAL RC

T-BAR MOUNTED LINEAR DROP LENS

T-BAR MOUNTED LINEAR FLAT LENS

With T-BAR clips, ready to install on the grid. Can also be suspended or surface mounted. Can be linked (with endcaps on, not seamless) coupling bracket included. With remote driver box, avail. 40W & 80W (sold separately) do not exceed max wattage of driver. Each fixture supplied with 6FT RJ11 cable, which plugs into the driver box. Driver box has 4 RJ11 Female sockets.
EXTERNAL DRIVER (ORDER SEPARATELY)

2 SCXT-L2FT INSTALLED ON T-BAR CEILING



SCXT SUSPENDED



SCXT INSTALLED ON T-BAR CEILING DRIVER MOUNTED ON TOP

SCXT-DRVK-RJ11

SCXT-BK INSTALLED ON T-BAR CEILING DRIVER MOUNTED ON TOP



SCXT-TGRID-DSP1



SCXT-SLT



SCXT-SLX

SCXT-SLC

SCXT-TB-DEEP

SCXT-TB-SLOTTED

SCXT-PK

SCXT-CMP-RJ11

SCXT-RJ11-COUPL

SCXT-TB916CK4

1" WIDE LINEAR SERIES FOR DIRECT T-GRID MOUNTING OR SUSPENSION POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION		
SCXT-2FT-10-20W-MCTP-D-DL	10W/15W/20W	110LM/W	30K/35K/40K
SCXT-4FT-20-40W-MCTP-D-DL	20W/30W/40W	110LM/W	30K/35K/40K
SCXT-8FT-40-80W-MCTP-D-DL	40W/60W/80W	110LM/W	30K/35K/40K
SCXT-L2FT-20-40W-MCTP-D-DL	20W/30W/40W	110LM/W	30K/35K/40K
SCXT-1FT-5-10W-MCTP-D-FL	5W/7.5W/10W	110LM/W	30K/35K/40K
SCXT-2FT-10-20W-MCTP-D-FL	10W/15W/20W	110LM/W	30K/35K/40K
SCXT-4FT-20-40W-MCTP-D-FL	20W/30W/40W	110LM/W	30K/35K/40K
SCXT-8FT-40-80W-MCTP-D-FL	40W/60W/80W	110LM/W	30K/35K/40K
SCXT-L1FT-10-20W-MCTP-D-FL	10W/15W/20W	110LM/W	30K/35K/40K
SCXT-L2FT-20-40W-MCTP-D-FL	20W/30W/40W	110LM/W	30K/35K/40K

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION		
SCXT-IC1FT-10-20W-MCTP-D-FL	10W/15W/20W	110LM/W	30K/35K/40K
SCXT-2FT-10-20W-MCTP-D-DL-BK	10W/15W/20W	110LM/W	30K/35K/40K - 2FT, Drop Lens, Can Adj. to 75% or 50%
SCXT-4FT-20-40W-MCTP-D-DL-BK	20W/30W/40W	110LM/W	30K/35K/40K - 4FT, Drop Lens, Can Adj. to 75% or 50%
SCXT-8FT-40-80W-MCTP-D-DL-BK	40W/60W/80W	110LM/W	30K/35K/40K - 8FT, Drop Lens, Can Adj. to 75% or 50%
SCXT-L2FT-20-40W-MCTP-D-DL-BK	20W/30W/40W	110LM/W	30K/35K/40K - 2FT. L-Shape, Drop Lens, Can Adj. to 75% or 50%
SCXT-2FT-10-20W-MCTP-D-FL-BK	10W/15W/20W	110LM/W	30K/35K/40K - 2FT, Flat Lens, Can Adj. to 75% or 50%
SCXT-4FT-20-40W-MCTP-D-FL-BK	20W/30W/40W	110LM/W	30K/35K/40K - 4TF, Flat Lens, Can Adj. to 75% or 50%
SCXT-8FT-40-80W-MCTP-D-FL-BK	40W/60W/80W	110LM/W	30K/35K/40K - 8FT, Flat Lens, Can Adj. to 75% or 50%
SCXT-L2FT-20-40W-MCTP-D-FL-BK	20W/30W/40W	110LM/W	30K/35K/40K - 2FT. L-Shape, Flat Lens, Can Adj. to 75% or 50%
OPT-SCXT-ULM-2FT-MCTP	2Ft Uplighitng Factory-Installed Adder Option - Directs 30% Of Power To Up		
OPT-SCXT-ULM-4FT-MCTP	4Ft Uplighitng Factory-Installed Adder Option - Directs 30% Of Power To Up		
OPT-SCXT-ULM-8FT-MCTP	8Ft Uplighitng Factory-Installed Adder Option - Directs 30% Of Power To Up		
SCXT-DRVK-RJ11-20W	SCXT Series 20W Driver Kit With Power & CCT Selection Switches		
SCXT-DRVK-RJ11-40W	SCXT Series 40W Driver Kit With Power & CCT Selection Switches		
SCXT-DRVK-RJ11-80W	SCXT Series 80W Driver Kit With Power & CCT Selection Switches		
SCXT-TGRID-DSP1	SCXT Series T-Grid Driver Support Platform For Up To 80W Driver Kit		
SCXT-TB916CK4	Set of 2 mounting clips for 9/16" T-bar ceilings, up to SCXT-4FT		
SCXT-TB916CK8	Set of 3 mounting clips for 9/16" T-bar ceilings, SCXT-6FT & above		
SCXT-CMP-RJ11-6FT	Comm. Multi-Purp. Extension Cable With RJ11 Ends - 6Ft		
SCXT-CMP-RJ11-8FT	Comm. Multi-Purp. Extension Cable With RJ11 Ends - 8Ft		
SCXT-CMP-RJ11-12FT	Comm. Multi-Purp. Extension Cable With RJ11 Ends - 12Ft		
SCXT-CMP-RJ11-24FT	Comm. Multi-Purp. Extension Cable With RJ11 Ends - 24Ft		
SCXT-RJ11-COUPL	RJ11 Coupling Female To Female		
SCXT-SLC	SCXT Swivel L Connector		
SCXT-SLC-BK	SCXT Swivel L Connector Black		
SCXT-SLT	SCXT-Swivel T Connector		
SCXT-SLT-BK	SCXT-Swivel T Connector Black		
SCXT-SLX	SCXT Swivel X Connector		
SCXT-SLX-BK	SCXT Swivel X Connector Black		
SCXT-PK	Pendant Kit For The Center Of Two SCXT Fixtures 7in Or 14in Drop Field-Installed		
SCXT-PK-BK	Pendant Kit For The Center Of Two SCXT Fixtures 7in Or 14in Drop Field-Installed Bk		
SCXT-TB-DEEP-CK4	SCXT Repl. Clip Kit For Deep Grids, For Up To 4Ft - Contains 2 Clips		
SCXT-TB-DEEP-CK8	SCXT Repl. Clip Kit For Deep Grids, For Up To 8Ft - Contains 3 Clips		
SCXT-TB-SLOTTED/BULLNOSE-CK4	SCXT Repl. Clip Kit For Slotted Or Bull-Nose Grids, For Up To 4Ft - Contains 2 Clips		
SCXT-TB-SLOTTED/BULLNOSE-CK8	SCXT Repl. Clip Kit For Slotted Or Bull-Nose Grids, For Up To 8Ft - Contains 3 Clips		

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
SCXT	OPT-EM-SCXT	EXTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	OPT-CLR-SCXT-2FT(BK/GR/SR/WH)		N/A	N/A
	OPT-CLR-SCXT-4FT(BK/GR/SR/WH)			
	OPT-CLR-SCXT-8FT(BK/GR/SR/WH)			
	OPT-CLR-SCXT-L2FT(BK/GR/SR/WH)			

SCXT-MIFK-8FT

SCXT FIELD-INSTALLED MUD-IN FLANGE-LESS RECESSED MOUNT KIT

CATALOG NO.	DESCRIPTION
SCXT-MIFK-2FT	SCXT-2FT Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCXT-MIFK-4FT	SCXT-4FT Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCXT-MIFK-8FT	SCXT-8FT Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCXT-MIFK-L1FT	SCXT-L1FT Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCXT-MIFK-L2FT	SCXT-L2FT Field-Installed Mud-In Flange-Less Recessed Mount Kit



SCXT-FMRK-8FT

SCXT FIELD-INSTALLED FLANGED RECESSED MOUNT DRYWALL KIT

CATALOG NO.	DESCRIPTION
SCXT-FMRK-2FT	SCXT-2FT Field-Installed Flanged Recessed Mount Drywall Kit
SCXT-FMRK-4FT	SCXT-4FT Field-Installed Flanged Recessed Mount Drywall Kit
SCXT-FMRK-8FT	SCXT-8FT Field-Installed Flanged Recessed Mount Drywall Kit
SCXT-FMRK-L1FT	SCXT-L1FT Field-Installed Flanged Recessed Mount Drywall Kit
SCXT-FMRK-L2FT	SCXT-L2FT Field-Installed Flanged Recessed Mount Drywall Kit

TGLK-1X4-MCTP

TGLK-2X2-MCTP

TGLK-2X4-MCTP

Ships disassembled for easy on-site handling

GEN 2 FRAME LIGHT KIT 4-PIECE VER. FOR EASY HANDLING, WATTAGE & CCT WITH GRID-MOUNT DRIVER BOX

CATALOG NO.	DESCRIPTION			PCK QTY
TGLK-1X4-MCTP	17W/26W/36W	110LM/W	35K/40K/50K	8
TGLK-2X2-MCTP	17W/26W/36W	110LM/W	35K/40K/50K	8
TGLK-2X4-MCTP	25W/35W/45W	110LM/W	35K/40K/50K	8

ELB-TBAR1

TGL-2X4-MCTP



TGL-2X2-MCTP

T-BAR GRID LIGHT (FRAME LIGHT) REMOTE DRIVER MCTP: MULTI COLOR TEMPERATURE & MULTI POWER

CATALOG NO.	DESCRIPTION		
TGL-2X2-MCTP	27W/35W/40W	150LM/W	3500K/4000K/5000K
TGL-2X4-MCTP	35W/45W/54W	150LM/W	3500K/4000K/5000K
ELB-TBAR1	T-BAR BRACKET FOR MOUNTING THE REMOTE DRIVER		

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	FLEX WHIP	DESCRIPTION
ALL MODELS	OPT-EM-TGL	EXTERNAL	OPT-FWH-63	6FT 3-Wire Whip
	POWDER COATING		OPT-FWH-65	6FT 5-Wire Whip
	N/A		OPT-FWH-66	6FT 6-Wire Whip
			SENSOR	DESCRIPTION
			N/A	N/A

TGL-2X4-RGB-RC-BT APPLICATION PHOTO

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW T-BAR GRID LIGHT (FRAME LIGHT) REMOTE DRIVER

CATALOG NO.	DESCRIPTION			PCK QTY
TGL-2X2-RGB-RC-BT	40W	100LM/W	RGB	5
TGL-2X4-RGB-RC-BT	60W	100LM/W	RGB	1

FOR REMOTE CONTROL SEE PAGE 521

FEL-1X4-MCT5

5CCT EDGE-LESS ARCHITECTURAL FLUSH MOUNT PANEL

CATALOG NO.	DESCRIPTION			PCK QTY
FEL-1X2-MCT5	30W	2100LM	27K/30K/35K/40K/50K	3
FEL-1X4-MCT5	60W	4200LM	27K/30K/35K/40K/50K	3

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
ALL	OPT-EM-FEL-1X2	INTERNAL	N/A	N/A
	OPT-EM-FEL-1X4	INTERNAL	SENSOR	DESCRIPTION
	POWDER COATING		N/A	N/A
	N/A			



INTERNAL-DRIVER LED SURFACE MOUNT PANEL 1X4 & LARGER CAN BE RECESS MOUNTED

CATALOG NO.	DESCRIPTION			PCK QTY
LPS-S4-50K-D	10W	700LM	5000K - 4" Square, 120VAC	20
LPS-S4-40K-D	10W	700LM	4000K - 4" Square, 120VAC	20
LPS-S4-30K-D	10W	700LM	3000K - 4" Square, 120VAC	20
LPS-S6-50K-D	12W	900LM	5000K - 6" Square, 120VAC	20
LPS-S6-40K-D	12W	900LM	4000K - 6" Square, 120VAC	20
LPS-S6-30K-D	12W	900LM	3000K - 6" Square, 120VAC	20
LPS-S8-50K-D	16W	1280LM	5000K - 8" Square, 120VAC	20
LPS-S8-40K-D	16W	1280LM	4000K - 8" Square, 120VAC	20
LPS-S8-30K-D	16W	1280LM	3000K - 8" Square, 120VAC	20
LPS-1X1-50K-D	18W	1700LM	5000K - 1' X 1', 120~277VAC	16
LPS-1X1-40K-D	18W	1700LM	4000K - 1' X 1', 120~277VAC	16
LPS-1X1-30K-D	18W	1700LM	3000K - 1' X 1', 120~277VAC	16
LPS-1X2-50K-D	25W	2500LM	5000K - 1' X 2', 120~277VAC	8
LPS-1X2-40K-D	25W	2500LM	4000K - 1' X 2', 120~277VAC	8
LPS-1X2-30K-D	25W	2500LM	3000K - 1' X 2', 120~277VAC	8
LPS-1X4-40K-D*	40W	4000LM	4000K - 1' X 4', 120~277VAC	1
LPS-2X2-30K-D	40W	4400LM	3000K - 2' X 2', 120~277VAC	1
LPS-2X4-50K-D*	50W	5500LM	5000K - 2' X 4', 120~277VAC	1
LPS-JBOX	Junction Box for 1 X 4, 2 X 2, 2 X 4 LPS T-Bar installation			

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	FLEX WHIP	DESCRIPTION	EM OPTION	DESCRIPTION
ALL MODELS	**OPT-FWH-63**	6FT 3-Wire Whip	**OPT-EM-LPS**	EXTERNAL
	OPT-FWH-65	6FT 5-Wire Whip	**SENSOR**	DESCRIPTION
	OPT-FWH-66	6FT 6-Wire Whip	**N/A**	N/A
	POWDER COATING			
	N/A			

LPSB-1X4-26-40W-MCTP5-D

LPSB-2X4-26-40W-MCTP5-D

LPSB-2X4-32-50W-MCTP5-D

LED SURFACE-MOUNT PANEL, BACKLIT POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LPSB-1X4-26-40W-MCTP5-D	26W/32W/40W	110LM/W	30K/35K/40K/50K/65K	1
LPSB-2X2-26-40W-MCTP5-D	26W/32W/40W	110LM/W	30K/35K/40K/50K/65K	1
LPSB-2X4-32-50W-MCTP5-D	32W/40W/50W	110LM/W	30K/35K/40K/50K/65K	1

SRL6-2FT-DWK

SRL6-4FT-DWK

SRL6-8FT-DWK



Shown with Drywall (Sheetrock) Kit

SLOT RECESSED COMMERCIAL LINEAR LIGHT, 4" OR 6" WIDE CCT & WATTAGE SELECT

CATALOG NO.	DESCRIPTION			PCK QTY
SRL4-2FT-MCTP	10W/15W/20W	110LM/W	30K/40K/50K - 2FT & 4" WIDE	
SRL4-4FT-MCTP	20W/30W/40W	110LM/W	30K/40K/50K - 4FT & 4" WIDE	
SRL4-8FT-MCTP	40W/60W/80W	110LM/W	30K/40K/50K - 8FT & 4" WIDE	
SRL6-2FT-MCTP	10W/15W/20W	110LM/W	35K/40K/50K - 2FT & 6" WIDE	6
SRL6-4FT-MCTP	20W/30W/40W	110LM/W	35K/40K/50K - 4FT & 6" WIDE	6
SRL6-8FT-MCTP	40W/60W/80W	110LM/W	35K/40K/50K - 8FT & 6" WIDE	6
SRL4-2FT-DWK	2Ft 4in Slot Recessed Linear Light Drywall Mounting Kit For SRL4-2FT			
SRL4-4FT-DWK	4Ft 4in Slot Recessed Linear Light Drywall Mounting Kit For SRL4-4FT			
SRL4-8FT-DWK	8Ft 4in Slot Recessed Linear Light Drywall Mounting Kit For SRL4-8FT			
SRL6-2FT-DWK	2Ft 6in Slot Recessed Linear Light Drywall Mounting Kit For SRL6-2FT			
SRL6-4FT-DWK	4Ft 6in Slot Recessed Linear Light Drywall Mounting Kit For SRL6-4FT			
SRL6-8FT-DWK	8Ft 6in Slot Recessed Linear Light Drywall Mounting Kit For SRL6-8FT			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

SIZE	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
2FT, 4FT	OPT-EM-SRL6	EXTERNAL	N/A	N/A
8FT	OPT-EM-SRL6-8FT	EXTERNAL	SENSOR	DESCRIPTION
	POWDER COATING		N/A	N/A
	N/A			

LP-SLF-2X4

LP-SLF-2X2

LP-SLF-1X4

SKY LIGHT RECESSED FRAME FOR PANEL LIGHT 2-3/4" DEEP **FIXTURE NOT INCLUDED**

CATALOG NO.	DESCRIPTION
LP-SLF-2X2	2X2 Sky Light Recessed Frame For Panel Lights 2-3/4 in Deep
LP-SLF-2X4	2X4 Sky Light Recessed Frame For Panel Lights 2-3/4 in Deep
LP-SLF-1X4	1X4 Sky Light Recessed Frame For Panel Lights 2-3/4 in Deep

LPNG-SRFC

LTRE-SMK

LPNG-RMK

LPNG-EMB

ELB-2048-EXTR

SCL-GSY10

ACCESSORIES FOR PANEL LIGHT

CATALOG NO.	DESCRIPTION
LPNG-SRFC-2X2	Surface mounting kit for 2X2 panel
LPNG-SRFC-2X4	Surface mounting kit for 2X4 panel
LPNG-SRFC-1X4	Surface mounting kit for 1X4 panel
LTRE-2X2-SMK	Designer Surface mounting kit for 2X2 panel
LTRE-2X4-SMK	DesignerSurface mounting kit for 2X4 panel
LTRE-1X4-SMK	Designer Surface mounting kit for 1X4 panel
LPNG-RMK-1X4	1x4' Recessed Mounting Flange Kit for installation in hard ceilings and surfaces
LPNG-RMK-2X2	2x2' Recessed Mounting Flange Kit for installation in hard ceilings and surfaces
LPNG-RMK-2X4	2x4' Recessed Mounting Flange Kit for installation in hard ceilings and surfaces
ELB-2048-EXTR	Field-installed emergency ballast; Input voltage: 100~277VAC, 50~60Hz; Input power: 4.8W (max); Output voltage: 12V~48VDC; Output power: 20W (max) Emergency operation: ≥90 mins.; Use w/ up to 60W LED fxtures; 20% lumens required by UL in power failure for FACTORY-INSTALLED OPTION see above.
LPNG-EMMB	Emergency Battery Mounting Bracket for 2x2 & 2x4 Panels-Allows backup unit installation on top of panel(Recommended for EM Installations on 2X2 & 2X4)
LPNG-EMMB-1X4	Emergency Battery Mounting Bracket for 1X4 Panels-Allows backup unit installation on top of panel

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL MODELS	OPT-EM-LTRE	MOUNTED ON TOP
	Ribbed LENS OPTION	DESCRIPTION
	OPT-2X2-RL	Ribbed LENS FOR 2X2
	OPT-2X4-RL	Ribbed LENS FOR 2X4
	POWDER COATING	
	N/A	

FLEX WHIP	DESCRIPTION
OPT-FWH-63	6FT 3-Wire Whip
OPT-FWH-65	6FT 5-Wire Whip
OPT-FWH-66	6FT 6-Wire Whip
SENSOR	DESCRIPTION
OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-LTRE	WG NETWORK SENSOR
OPT-SEN-KEILTON-LTRE	KEILTON NETWORK SENSOR
WEC-3RC	OPTIONAL RC



TROFFER LIGHTS

LTRE-G2-2X2-MCTP

LTRE-G2-2X4-MCTP

SENSOR-READY PLUG & PLAY

WEC-2PR-28-AJ-WH
WEC-2BT-28-AJ-WH

WEC-3RC

G2 PREMIUM CENTER-LENS TROFFER POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRE-G2-2X2-MCTP	15W/20W/25W/30W/40W	125LM/W	27K/30K/35K/40K/50K	4
G2 PREMIUM CENTER-LENS TROFFER POWER AND CCT ADJUSTABLE SENSOR READY				
LTRE-G2-2X2-MCTP-SR	15W/20W/25W/30W/40W	125LM/W	27K/30K/35K/40K/50K	4
LTRE-G2-2X4-MCTP-SR	23W/30W/35W/40W/50W	125LM/W	27K/30K/35K/40K/50K	4
WEC-2PR-28-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level & RC (Optional RC WEC-3RC)			
WEC-2BT-28-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level Bluetooth App Ready			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL MODELS	OPT-EM-LTRE	MOUNTED ON TOP

Ribbed LENS OPTION	DESCRIPTION
OPT-2X2-RL	Ribbed LENS FOR 2X2

POWDER COATING
N/A

FLEX WHIP	DESCRIPTION
OPT-FWH-63	6FT 3-Wire Whip
OPT-FWH-65	6FT 5-Wire Whip
OPT-FWH-66	6FT 6-Wire Whip

SENSOR	DESCRIPTION
OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-LTRE	WG NETWORK SENSOR
OPT-SEN-KEILTON-LTRE	KEILTON NETWORK SENSOR
WEC-3RC	OPTIONAL RC

LTRA-2X2-MCTP



LTRA-2X4-MCTP

LTRA-1X4-MCTP

APERTURE GRILLE TROFFER WATTAGE & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRA-1X4-MCTP	20W/25W/30W/40W	125LM/W	35K/40K/50K	1
LTRA-2X2-MCTP	20W/25W/30W/40W	125LM/W	35K/40K/50K	1
LTRA-2X4-MCTP	30W/40W/50W/60W	125LM/W	35K/40K/50K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	FLEX WHIP	DESCRIPTION
ALL MODELS	**OPT-EM-LTRA**	MOUNTED ON TOP	**OPT-FWH-63**	6FT 3-Wire Whip
SENSOR		DESCRIPTION	**OPT-FWH-65**	6FT 5-Wire Whip
OPT-SEN-2MDR-36		PROGRAMMABLE MICROWAVE BI-LEVEL	**OPT-FWH-66**	6FT 6-Wire Whip
OPT-SEN-NLS-LTRA		WG NETWORK SENSOR	**POWDER COATING**	
OPT-SEN-KEILTON-LTRA		KEILTON NETWORK SENSOR	**N/A**	
WEC-3RC		REMOTE CONTROL		

LTRG-1X4-MCTP

LTRG-2X2-MCTP

LTRG-2X4-MCTP

ARCHITECTURAL GRILLE TROFFER WATTAGE & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRG-2X2-MCTP	24W/28W/36W	120LM/W	35K/40K/50K	1
LTRG-1X4-MCTP	24W/28W/36W	120LM/W	35K/40K/50K	1
LTRG-2X4-MCTP	30W/40W/50W	120LM/W	35K/40K/50K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	FLEX WHIP	DESCRIPTION
ALL MODELS	**OPT-EM-LTRG**	MOUNTED ON TOP	**OPT-FWH-63**	6FT 3-Wire Whip
SENSOR		DESCRIPTION	**OPT-FWH-65**	6FT 5-Wire Whip
OPT-SEN-2MDR-36		PROGRAMMABLE MICROWAVE BI-LEVEL	**OPT-FWH-66**	6FT 6-Wire Whip
OPT-SEN-NLS-LTRG		WG NETWORK SENSOR	**POWDER COATING**	
OPT-SEN-KEILTON-LTRG		KEILTON NETWORK SENSOR	**N/A**	
WEC-3RC		REMOTE CONTROL		

LTRB-2X2-MCTP

LTRB-2X4-MCTP

SPEC SERIES ARCHITECTURAL TROFFER, BACK-LIT LED DESIGN
NO PARTIAL MUST BUY IN QTY OF FOUR POWER & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRB-2X2-MCTP	25W/30W/35W	110LM/W	35K/40K/50K	4
LTRB-2X4-MCTP	30W/40W/50W	110LM/W	35K/40K/50K	4
LTRB-1X4-MCTP	25W/30W/35W	110LM/W	35K/40K/50K	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER



LTRC-2X2-MCTP

PREMIUM CURVED INDIRECT TROFFER POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRC-2X2-MCTP	25W/30W/40W	125LM/W	35K/40K/50K	4
LTRC-2X4-MCTP	30W/40W/50W	125LM/W	35K/40K/50K	2

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL MODELS	**OPT-EM-LTRC**	MOUNTED ON TOP

SENSOR	DESCRIPTION
OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-LTRB	WG NETWORK SENSOR
OPT-SEN-KEILTON-LTRB	KEILTON NETWORK SENSOR
WEC-3RC	OPTIONAL RC

FLEX WHIP	DESCRIPTION
OPT-FWH-63	6FT 3-Wire Whip
OPT-FWH-65	6FT 5-Wire Whip
OPT-FWH-66	6FT 6-Wire Whip

POWDER COATING
N/A

LTRD-2X2-MCTP

LTRD-2X4-MCTP

SPEC SERIES LED DUAL LENS TROFFER LIGHT SELECTABLE COLOR TEMPERATURE & WATTAGE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRD-2X2-MCTP	25W/30W/35W	125LM/W	3500K/4000K/5000K	1
LTRD-2X4-MCTP	30W/40W/50W	125LM/W	3500K/4000K/5000K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL MODELS	**OPT-EM-LTRD**	MOUNTED ON TOP

SENSOR	DESCRIPTION
OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-LTRD	WG NETWORK SENSOR
OPT-SEN-KEILTON-LTRD	KEILTON NETWORK SENSOR
WEC-3RC	OPTIONAL RC

FLEX WHIP	DESCRIPTION
OPT-FWH-63	6FT 3-Wire Whip
OPT-FWH-65	6FT 5-Wire Whip
OPT-FWH-66	6FT 6-Wire Whip

POWDER COATING
N/A

LTRI-2X2-MCTP

LTRI-2X4-MCTP

SPEC SERIES INDIRECT MESH-BASKET TROFFER WATTAGE AND CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRI-2X2-MCTP	30W/40W/50W	110LM/W	30K/35K/40K/50K	1
LTRI-2X4-MCTP	50W/60W/72W	110LM/W	30K/35K/40K/50K	1

LTRL-2X2-MCTP4

LTRL-2X4-MCTP4

LTRL-2X2-SMK

ARCHITECTURAL ADVANCED BLADE DESIGN TROFFER WATTAGE & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRL-2X2-MCTP4	30W/40W/50W	115LM/W	30K/35K/40K/50K	1
LTRL-2X4-MCTP4	50W/60W/72W	115LM/W	30K/35K/40K/50K	1
LTRL-2X2-SMK	4.5" Deep 2X2 Surface Mounting Kit For LTRL And Other Deep Troffers			
LTRL-2X4-SMK	4.5" Deep 2X4 Surface Mounting Kit For LTRL And Other Deep Troffers			

LTRM-1X4-MCTP

LTRM-2X2-MCTP

LTRM-2X4-MCTP

ARCHITECTURAL SLOPED-LENS TROFFER POWER & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRM-2X2-MCTP	25W/30W/36W	125LM/W	35K/40K/50K	1
LTRM-2X4-MCTP	40W/45W/50W	125LM/W	35K/40K/50K	1
LTRM-1X4-MCTP	25W/30W/36W	125LM/W	35K/40K/50K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL MODELS	**OPT-EM-LTRM**	MOUNTED ON TOP

FLEX WHIP	DESCRIPTION
OPT-FWH-63	6FT 3-Wire Whip
OPT-FWH-65	6FT 5-Wire Whip
OPT-FWH-66	6FT 6-Wire Whip

POWDER COATING
N/A

SENSOR	DESCRIPTION
OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-LTRM	WG NETWORK SENSOR
OPT-SEN-KEILTON-LTRM	KEILTON NETWORK SENSOR
WEC-3RC	REMOTE CONTROL

LTRR-2X2-MCTP4

LTRR-2X2-SMK

ARCHITECTURAL RECESSED PANEL LIGHT WATTAGE & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRR-2X2-MCTP4	24W/35W/40W	110LM/W	30K/35K/40K/50K	1
LTRR-2X4-MCTP4	30W/40W/50W	110LM/W	30K/35K/40K/50K	1
LTRR-2X2-SMK	Deep 2X2 Surface-Mounting Kit For LTRR And Other Deep Troffers			
LTRR-2X4-SMK	Deep 2X4 Surface-Mounting Kit For LTRR And Other Deep Troffers			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	FLEX WHIP	DESCRIPTION
ALL MODELS	**OPT-EM-LTRR**	MOUNTED ON TOP	**OPT-FWH-63**	6FT 3-Wire Whip
SENSOR		DESCRIPTION	**OPT-FWH-65**	6FT 5-Wire Whip
OPT-SEN-2MDR-36		PROGRAMMABLE MICROWAVE BI-LEVEL	**OPT-FWH-66**	6FT 6-Wire Whip
OPT-SEN-NLS-LTRR		WG NETWORK SENSOR	**POWDER COATING**	
OPT-SEN-KEILTON-LTRR		KEILTON NETWORK SENSOR	**N/A**	
WEC-3RC		REMOTE CONTROL		

LTRW-2X2-MCTP4

LTRW-2X4-MCTP4

ARCHITECTURAL ADVANCED EDGE-LIT WING DESIGN TROFFER WATTAGE & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRW-2X2-MCTP4	24W/36W	115LM/W	30K/35K/40K/50K	1
LTRW-2X4-MCTP4	42W/50W	115LM/W	30K/35K/40K/50K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	FLEX WHIP	DESCRIPTION
ALL MODELS	**OPT-EM-LTRW**	MOUNTED ON TOP	**OPT-FWH-63**	6FT 3-Wire Whip
SENSOR		DESCRIPTION	**OPT-FWH-65**	6FT 5-Wire Whip
OPT-SEN-2MDR-36		PROGRAMMABLE MICROWAVE BI-LEVEL	**OPT-FWH-66**	6FT 6-Wire Whip
OPT-SEN-NLS-LTRW		WG NETWORK SENSOR	**POWDER COATING**	
OPT-SEN-KEILTON-LTRW		KEILTON NETWORK SENSOR	**N/A**	
WEC-3RC		REMOTE CONTROL		

LPCR-2X2-MCTP

LPCR-1X4-MCTP


LPCR-2X4-MCTP

PREMIUM IP65 CLEANROOM TROFFER POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LPCR-2X2-MCTP	25W/30W/40W	125LM/W	35K/40K/50K	2
LPCR-2X4-MCTP	30W/40W/50W	125LM/W	35K/40K/50K	1
LPCR-1X4-MCTP	25W/30W/40W	125LM/W	35K/40K/50K	2
LPCR-2X2-HL-MCTP	40W/48W/60W	125LM/W	30K/40K/50K	
LPCR-2X4-HL-MCTP	60W/80W/100W	125LM/W	30K/40K/50K	
LPCR-1X4-HL-MCTP	40W/48W/60W	125LM/W	30K/40K/50K	

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	FLEX WHIP	DESCRIPTION
ALL MODELS	**OPT-EM-LPCR**	MOUNTED ON TOP	**OPT-FWH-63**	6FT 3-Wire Whip
SENSOR		DESCRIPTION	**OPT-FWH-65**	6FT 5-Wire Whip
OPT-SEN-2MDR-36		PROGRAMMABLE MICROWAVE BI-LEVEL	**OPT-FWH-66**	6FT 6-Wire Whip
OPT-SEN-NLS-LPRC		WG NETWORK SENSOR	**POWDER COATING**	
OPT-SEN-KEILTON-LPRC		KEILTON NETWORK SENSOR	**N/A**	
WEC-3RC		OPTIONAL RC		

LRP-HL-2X2-MCTP

LRP-HL-2X4-MCTP

PREMIUM HIGH-LUMEN RETROFIT FLAT PANEL, NO PARTIAL MUST BUY IN PKG. QTY

CATALOG NO.	DESCRIPTION			PCK QTY
LRP-HL-2X2-MCTP	16W/20W/24W	125LM/W	35K/40K/50K	2
LRP-HL-2X4-MCTP	24W/30W/40W	125LM/W	35K/40K/50K	2

LTRAR-2X2-MCTP-SR

LTRAR-2X4-MCTP-SR

SENSOR-READY PLUG & PLAY

WEC-2PR-28-AJ-WH
WEC-2BT-28-AJ-WH

WEC-3RC

PASSIVE AIR RETURN CENTER LENS TROFFER, SENSOR-READY WATTAGE & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LTRAR-2X2-MCTP-SR	20W/25W/30W/35W	135LM/W	30K/35K/40K/50K	1
LTRAR-2X4-MCTP-SR	35W/40W/45W/50W	135LM/W	30K/35K/40K/50K	1
WEC-2PR-28-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level & RC (Optional RC WEC-3RC)			
WEC-2BT-28-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level Bluetooth App Ready			

SENSOR-READY PLUG & PLAY

WEC-2PR-28-AJ-WH
WEC-2BT-28-AJ-WH

WEC-3RC

LRP-HL-2X2-MCTP-SR

LRP-HL-2X4-MCTP-SR

LRT-HL-2X2-MCTP-SR

DLC PREMIUM HIGH-LUMEN RETROFIT PANEL/TROFFER, SENSOR-READY POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LED RETROFIT PANEL				
LRP-HL-2X4-MCTP-SR	20W/30W/40W	140LM/W	35K/40K/50K	
LRP-HL-2X2-MCTP-SR	20W/25W/30W	140LM/W	35K/40K/50K	
LRP-HL-1X4-MCTP-SR	20W/25W/30W	140LM/W	35K/40K/50K	
LED RETROFIT TROFFER				
LRT-HL-2X4-MCTP-SR	20W/30W/40W	140LM/W	35K/40K/50K	
LRT-HL-2X2-MCTP-SR	20W/25W/30W	140LM/W	35K/40K/50K	
LRT-HL-1X4-MCTP-SR	20W/25W/30W	140LM/W	35K/40K/50K	

LRT-HL-2X2-MCTP

WHILE SUPPLIES LAST

PREMIUM HIGH-LUMEN RETROFIT TROFFER, NO PARTIAL MUST BUY IN PKG. QTY POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LRT-HL-2X2-MCTP	15W/20W/25W	125LM/W	35K/40K/50K	2
LRT-HL-2X4-MCTP	30W/40W/50W	125LM/W	35K/40K/50K	2

LPNG-SRFC

LTRE-SMK

LPNG-RMK

LPNG-EMB

ELB-2048-EXTR

SCL-GSY10

ACCESSORIES FOR TROFFER LIGHT

CATALOG NO.	DESCRIPTION
LPNG-SRFC-2X2	Surface mounting kit for 2X2 panel
LPNG-SRFC-2X4	Surface mounting kit for 2X4 panel
LPNG-SRFC-1X4	Surface mounting kit for 1X4 panel
LTRE-2X2-SMK	Designer Surface mounting kit for 2X2 panel
LTRE-2X4-SMK	DesignerSurface mounting kit for 2X4 panel
LTRE-1X4-SMK	Designer Surface mounting kit for 1X4 panel
LPNG-RMK-1X4	1x4' Recessed Mounting Flange Kit for installation in hard ceilings and surfaces
LPNG-RMK-2X2	2x2' Recessed Mounting Flange Kit for installation in hard ceilings and surfaces
LPNG-RMK-2X4	2x4' Recessed Mounting Flange Kit for installation in hard ceilings and surfaces
ELB-2048-EXTR	Field-installed emergency ballast; Input voltage: 100~277VAC, 50~60Hz; Input power: 4.8W (max); Output voltage: 12V~48VDC; Output power: 20W (max) Emergency operation: ≥90 mins.; Use w/ up to 60W LED fxtures; 20% lumens required by UL in power failure for FACTORY-INSTALLED OPTION see above.
LPNG-EMMB	Emergency Battery Mounting Bracket for 2x2 & 2x4 Panels-Allows backup unit installation on top of panel(Recommended for EM Installations on 2X2 & 2X4)
LPNG-EMMB-1X4	Emergency Battery Mounting Bracket for 1X4 Panels-Allows backup unit installation on top of panel

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	FLEX WHIP	DESCRIPTION
ALL MODELS	OPT-EM-LTRE	MOUNTED ON TOP	OPT-FWH-63	6FT 3-Wire Whip
	Ribbed LENS OPTION	DESCRIPTION	OPT-FWH-65	6FT 5-Wire Whip
	OPT-2X2-RL	Ribbed LENS FOR 2X2	OPT-FWH-66	6FT 6-Wire Whip
	OPT-2X4-RL	Ribbed LENS FOR 2X4	SENSOR	DESCRIPTION
	POWDER COATING		OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
	N/A		OPT-SEN-NLS-LTRE	WG NETWORK SENSOR
			OPT-SEN-KEILTON-LTRE	KEILTON NETWORK SENSOR
			WEC-3RC	OPTIONAL RC



STRIP LIGHTS

EM CAPABLE

LSS-2FT-25W-MCTP

LSS-4FT-34W-MCTP

LSS-8FT-90W-MCTP

LSS-2FT-25W-MCTP-BK

LSS-4FT-46W-MCTP-BK

LSS-8FT-90W-MCTP-BK

LSS-CB2
LSS-CB2-BK

SCL-TBTC-WN

SCLCSYK-6FT

SCLGSY10

2FT/4FT/8FT SPEC SERIES HIGH-LUMEN LINEAR STRIP CCT & POWER ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
MCTP LSS-2FT-25W-MCTP	15W/17W/20W/25W	130LM/W	35K/40K/50K - White	6
MCTP LSS-4FT-34W-MCTP	24W/27W/30W/34W	130LM/W	35K/40K/50K - White	6
MCTP LSS-4FT-46W-MCTP	29W/34W/39W/46W	130LM/W	35K/40K/50K - White	6
MCTP LSS-8FT-90W-MCTP	85W/75W/65W/55W	130LM/W	35K/40K/50K - White	1
MCTP LSS-2FT-25W-MCTP-BK	15W/17W/20W/25W	130LM/W	35K/40K/50K - Black	6
MCTP LSS-4FT-46W-MCTP-BK	29W/34W/39W/46W	130LM/W	35K/40K/50K - Black	6
MCTP LSS-8FT-90W-MCTP-BK	85W/75W/65W/55W	130LM/W	35K/40K/50K - Black	1
LSS-CB2	Alignment Bracket for long runs			
LSS-CB2-BK	Alignment Bracket for long runs, Black Finish			
SCL-CSY1-6FT	Adj. 6Ft 1/16In, 1.5mm Single Suspen Sion 5In Canopy Set With Y Double Keyhole End Connectors, Non Power Side			
SCL-CSY1P-6FT	Adj. 6Ft 1/16In, 1.5mm Single Suspension 5In Canopy Set With Y Double Keyhole End ConnecTors, Power Side With Sjtw18/5 White Cord			
SCL-CSY1P-6FT-NC	Adj. 6Ft 1/16In, 1.5mm Single Suspension 5In Canopy Set With Y Double Keyhole End ConnecTor			
SCL-GSY10	Adjustable 10 Ft. 1/16", 1.5mm Sus Pension Kit With Y-Connector & Loop Grip & Hooks(2)			
SCL-GSY20	Adjustable 20 Ft. 1/16", 1.5mm Sus Pension Kit With Y-Connector & Loop Grip & Hooks(2)			
SCL-TBTC-WN	T-Bar Track Clip With Washer And Wing Nut			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PLUG IN CORD	DESCRIPTION
2FT & 3FT	OPT-EM-LSS-23	INTERNAL	OPT-HBC-125TL-WH	8FT, 15A, 125V,WHITE
4FT	OPT-EM-LSS-4	INTERNAL	OPT-HBC-277TL-WH	8FT, 15A, 277V,WHITE
8FT	OPT-EM-LSS-8	INTERNAL	OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT
	FLEX WHIP	DESCRIPTION	SENSOR	DESCRIPTION
	OPT-FWH-63	6FT 3-Wire Whip	OPT-SEN-2US	MICROWAVE
	OPT-FWH-65	6FT 5-Wire Whip	OPT-SEN-NLS-LSS	WG NETWORK SENSOR
	POWDER COATING		OPT-SEN-KEILTON-LSS	KEILTON NETWORK SENSOR
	N/A		WEC-3RC	(REMOTE NOT NEEDED)
			OPT-2P-58	OPTIONAL RC
				PIR SENSOR (Not remote capable)

LSP-4FT-40W-40K

LED SHOP LIGHT, **120V** WITH PLUG-IN CORD

CATALOG NO.	DESCRIPTION			PCK QTY
LSP-4FT-40W-40K	40W	4400LM	4000K	4

DLC LISTED · DIMMING 0-10V · EM CAPABLE · SENSOR OPTION

LSL-2FT-20W-35K-D

LSL-4FT-40W-35K-D



LSL-2FT-WG
LSL-4FT-WG

LSL-8FT-80W-40K-D-A

LSL-8FT-80W-40K-D-A
LSL-8FT-80W-50K-D-A
Split Version Req. 5 min Assembly

LSL-4FT-WK
Shown with Fixture

SCLCSYK-6FT

SCLGSY10

LSL-CB

SCL-TBTC-WN

WEC-3RC

2FT, 3FT, 4FT, 6FT, 8FT SPEC SERIES LED STRIP LIGHT, **120~277V**

(SAME FOOTPRINT AS STANDARD 4' 2L FLUOR. STRIPS) FOR SENSOR MODELS - SENSOR CAN BE DISCONNECTED

CATALOG NO.	DESCRIPTION			PCK QTY
LSL-2FT-20W-35K-D	20W	2100LM	3500K - 2FT	1
LSL-2FT-20W-40K-D	20W	2100LM	4000K - 2FT	1
LSL-2FT-20W-50K-D	20W	2100LM	5000K - 2FT	1
LSL-2FT-20W-MCT-D	20W	2270LM	35K/40K/50K - 2FT	1
LSL-3FT-30W-MCT-D	30W	3150LM	35K/40K/50K - 3FT	1

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION			PCK QTY
LSL-4FT-40W-35K-D	40W	4200LM	3500K - 4FT	1
LSL-4FT-40W-40K-D	40W	4200LM	4000K - 4FT	1
LSL-4FT-40W-50K-D	40W	4200LM	5000K - 4FT	1
MCT LSL-4FT-40W-MCT-D	40W	4200LM	35K/40K/50K - 4FT	1
MCT LSL-6FT-60W-MCT-D	60W	7300LM	35K/40K/50K - 6FT	1
LSL-8FT-80W-40K-D-A	80W	8400LM	4000K - 8FT, Split Version	1
LSL-8FT-80W-50K-D-A	80W	8400LM	5000K - 8FT, Split Version	1
LSL-8FT-80W-40K-D	80W	8400LM	4000K - 8FT	1
LSL-8FT-80W-50K-D	80W	8400LM	5000K - 8FT	1
MCT LSL-8FT-80W-MCT-D	80W	8400LM	35K/40K/50K - 8FT	1
LSL-8FT-84W-40K-D-HL	84W	11000LM	4000K - 8FT, High-Lumen	1
LSL-8FT-84W-50K-D-HL	84W	11000LM	5000K - 8FT, High-Lumen	1
MCT LSL-8FT-84W-MCT-D-HL	84W	11000LM	35K/40K/50K - 8FT, High-Lumen	1
MCT LSL-2FT-20W-MCT-D-SEN	20W	2100LM	35K/40K/50K - 2FT, With Sensor	1
MCT QUICK SHIP LSL-4FT-40W-MCT-D-SEN	40W	4200LM	35K/40K/50K - 4FT, With Sensor	1
MCT LSL-8FT-80W-MCT-D-SEN	80W	8400LM	35K/40K/50K - 8FT, With Sensor	1
MCT LSL-2FT-20W-MCT-D-EM-SEN	20W	2100LM	35K/40K/50K - 2FT, With Sensor & EM	1
MCT QUICK SHIP LSL-4FT-40W-MCT-D-EM-SEN	40W	4200LM	35K/40K/50K - 4FT, With Sensor & EM	1
MCT EM CAPABLE LSL-8FT-80W-MCT-D-EM-SEN	80W	8400LM	35K/40K/50K - 8FT, With Sensor & EM	1
LSL-2FT-WG	Wire Guard Kit For 2Ft. Strip Light			
LSL-4FT-WG	Wire Guard Kit For 4Ft. Strip Light			
LSL-4FT-WK	Shop Wings For 4Ft. Strip Light, Use 2 Kits For Lsl-8Ft			
SCL-TBTC-WN	T-Bar Track Clip With Washer And Wing Nut			
SCL-TBC-WN	T-Bar Clip With Suspension Hole On Top, Wing Nut And Washer Incl			
LSL-CB	Alignment Bracket for long runs			
SCL-CSY1-6FT	Adj. 6Ft 1/16In, 1.5mm Single Suspen Sion 5In Canopy Set With Y Double Keyhole End Connectors, Non Power Side			
SCL-CSY1P-6FT	Adj. 6Ft 1/16In, 1.5mm Single Suspension 5In Canopy Set With Y Double Keyhole End ConnecTors, Power Side With Sjtw18/5 White Cord			
SCL-CSY1P-6FT-NC	Adj. 6Ft 1/16In, 1.5mm Single Suspension 5In Canopy Set With Y Double Keyhole End ConnecTor			
SCL-GSY10	Adjustable 10 Ft. 1/16", 1.5mm Sus Pension Kit With Y-Connector & Loop Grip & Hooks(2)			
SCL-GSY20	Adjustable 20 Ft. 1/16", 1.5mm Sus Pension Kit With Y-Connector & Loop Grip & Hooks(2)			
WEC-3RC	Remote Control For Motion Sensors (For Sensor Fixtures)			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PLUG IN CORD	DESCRIPTION
2FT & 3FT	OPT-EM-LSL-23	INTERNAL	OPT-HBC-125TL-WH	8FT, 15A, 125V,WHITE
4FT	OPT-EM-LSL-4	INTERNAL	OPT-HBC-277TL-WH	8FT, 15A, 277V,WHITE
8FT	OPT-EM-LSL-8	INTERNAL	OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT
	FLEX WHIP	DESCRIPTION	SENSOR	DESCRIPTION
	OPT-FWH-63	6FT 3-Wire Whip	OPT-SEN-2US	MICROWAVE
	OPT-FWH-65	6FT 5-Wire Whip	OPT-SEN-NLS-LSL	WG NETWORK SENSOR
	POWDER COATING		OPT-SEN-KEILTON-LSL	KEILTON NETWORK SENSOR
	N/A		WEC-3RC	(REMOTE NOT NEEDED)
			OPT-2P-58	OPTIONAL RC
				PIR SENSOR (Not remote capable)

LSN-2FT-20W-MCT-D

LSN-4FT-32W-35K-D

LSN-8FT-64W-40K-D

LSN-8FT-80W-MCTP-D-SEN

WEC-3RC

SCLCSYK-6FT

SCLGSY10

SCL-TBTC-WN

LSN-2FT-WG
LSN-4FT-WG

LSN-CB

BUILDER SERIES NARROW STRIP, 120~277VAC

CATALOG NO.	DESCRIPTION			PCK QTY
NARROW STRIP, 120~277VAC				
MCT **LSN-2FT-20W-MCT-D**	20W	2600LM	3500K/4000K/5000K	8
LSN-4FT-32W-35K-D	32W	4160LM	3500K	8
LSN-4FT-32W-40K-D	32W	4160LM	4000K	8
LSN-4FT-32W-50K-D	32W	4160LM	5000K	8
LSN-4FT-40W-35K-D	40W	5200LM	3500K	8

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION			PCK QTY
LSN-4FT-40W-40K-D	40W	5200LM	4000K	8
LSN-4FT-40W-50K-D	40W	5200LM	5000K	8
MCTP LSN-4FT-40W-MCTP-D	25W/30W40W	130LM/W	3500K/4000K/5000K	8
MCTP LSN-4FT-40W-MCTP5-D	25W/30W/40W	130LM/W	30K/35K/40K/50K/60K	8
LSN-8FT-64W-40K-D	64W	8320LM	4000K	4
LSN-8FT-64W-50K-D	64W	8320LM	5000K	4
MCTP LSN-8FT-50W-MCTP-D	30W/40W/50W	130LM/W	3500K/4000K/5000K	4
MCTP LSN-8FT-80W-MCTP-D	50W/64W/80W	130LM/W	3500K/4000K/5000K	4
MCTP LSN-8FT-80W-MCTP5-D	50W/64W/80W	130LM/W	30K/35K/40K/50K/60K	5
MCTP **NARROW STRIP WITH SENSOR (SENSOR CAN BE DISCONNECTED), 120~277VAC**				
LSN-2FT-20W-MCT-D-SEN	20W	2600LM	3500K/4000K/5000K	8
QUICK SHIP LSN-4FT-40W-MCTP-D-SEN	25W/30W40W	130LM/W	3500K/4000K/5000K	8
QUICK SHIP LSN-8FT-80W-MCTP-D-SEN	50W/64W/80W	130LM/W	3500K/4000K/5000K	4
MCTP EM CAPABLE **NARROW STRIP WITH SENSOR (SENSOR CAN BE DISCONNECTED) & EMERGENCY BACKUP , 120~277VAC**				
QUICK SHIP LSN-2FT-20 W-MCT-D-EM-SEN	20W	2600LM	3500K/4000K/5000K	8
QUICK SHIP LSN-4FT-40W-MCTP-D-EM-SEN	25W/30W40W	130LM/W	3500K/4000K/5000K	8
EM CAPABLE LSN-8FT-80W-MCTP-D-EM-SEN	50W/64W/80W	130LM/W	3000K/4000K/5000K	4
LSN-CB	Alignment Bracket for long runs			
LSN-2FT-WG	Wire Guard Kit For 2ft LSN Strip Light			
LSN-4FT-WG	Wire Guard Kit For 4ft OR Set of 2 For 8 ft LSN Strip Light			
SCL-TBTC-WN	T-Bar Track Clip With Washer And Wing Nut			
WEC-3RC	Remote Control For Motion Sensors (For Sensor Fixtures)			
SCL-CSY1-6FT	Adj. 6Ft 1/16In, 1.5mm Single Suspen Sion 5In Canopy Set With Y Double Keyhole End Connectors, Non Power Side			
SCL-CSY1P-6FT	Adj. 6Ft 1/16In, 1.5mm Single Suspension 5In Canopy Set With Y Double Keyhole End ConnecTors, Power Side With Sjtw18/5 White Cord			
SCL-CSY1P-6FT-NC	Adj. 6Ft 1/16In, 1.5mm Single Suspension 5In Canopy Set With Y Double Keyhole End ConnecTor			
SCL-GSY10	Adjustable 10 Ft. 1/16", 1.5mm Sus Pension Kit With Y-Connector & Loop Grip & Hooks(2)			
SCL-GSY20	Adjustable 20 Ft. 1/16", 1.5mm Sus Pension Kit With Y-Connector & Loop Grip & Hooks(2)			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PLUG IN CORD	DESCRIPTION
2FT & 3FT	OPT-EM-LSN-23	INTERNAL	OPT-HBC-125TL-WH	8FT, 15A, 125V,WHITE
4FT	OPT-EM-LSN-4	INTERNAL	OPT-HBC-277TL-WH	8FT, 15A, 277V,WHITE
8FT	OPT-EM-LSN-8	INTERNAL	OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT
	FLEX WHIP	DESCRIPTION	SENSOR	DESCRIPTION
	OPT-FWH-63	6FT 3-Wire Whip	OPT-SEN-2US	MICROWAVE
	OPT-FWH-65	6FT 5-Wire Whip	OPT-SEN-NLS-LSN	WG NETWORK SENSOR
	POWDER COATING		OPT-SEN-KEILTON-LSN	KEILTON NETWORK SENSOR
	N/A		WEC-3RC	(REMOTE NOT NEEDED)
			OPT-2P-58	OPTIONAL RC
				PIR SENSOR (Not remote capable)

WA-2FT-10-20W-MCTP

WA-4FT-20-40W-MCTP

SPEC SERIES LED ARCHITECTURAL WRAP-AROUND LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
SPEC SERIES LED ARCHITECTURAL WRAP-AROUND LIGHT				
WA-2FT-25W-35K-D*	25W	2750LM	3500K - 2FTx8.2"	5
WA-2FT-25W-50K-D*	25W	2750LM	5000K - 2FTx8.2"	5
MCT **WA-2FT-25W-MCT-D***	25W	2800LM	35K/40K/50K - 2FTx8.2"	5
MCTP **SPEC SERIES POWER & CCT ADJUSTABLE LED ARCHITECTURAL WRAP-AROUND LIGHT**				
WA-2FT-10-20W-MCTP	10W/15W/20W	110LM/W	35K/40K/50K - 4FTx8.2"	
WA-4FT-20-40W-MCTP	20W/30W/40W	110LM/W	35K/40K/50K - 4FTx8.2"	5

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-EM-WA	INTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-2P-58	PIR SENSOR (Not remote capable)
			OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
			OPT-SEN-NLS-WA	WG NETWORK SENSOR
			OPT-SEN-KEILTON-WA	KEILTON NETWORK SENSOR
			WEC-3RC	REMOTE CONTROL

SLR-4FT-40W-50K-D

LED 4FT. 2-LAMP STRIP RETROFIT KIT

CATALOG NO.	DESCRIPTION			PCK QTY
SLR-4FT-40W-50K-D	40W	4400LM	5000K - 4FT.	12

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-EM-SLR	INTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
			OPT-SEN-NLS-SLR	WG NETWORK SENSOR
			OPT-SEN-KEILTON-SLR	KEILTON NETWORK SENSOR
			WEC-3RC	REMOTE CONTROL

LCL-2FT-20W-MCTP

LCL-4FT-40W-MCTP



2FT & 4FT LINEAR CORNER CORRIDOR POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LCL-2FT-20W-MCTP	10W/15W/20W	115LM/W	3500K/4000K/5000K	6
LCL-4FT-40W-MCTP	20W/30W/40W	115LM/W	3500K/4000K/5000K	6

POWER & CCT ADJUSTABLE LINEAR CORNER CORRIDOR WITH BI-LVL SENSOR & EMERGENCY BACKUP

LCL-2FT-20W-MCTP-EM-SEN	10W/15W/20W	115LM/W	35K/40K/50K	6
LCL-4FT-40W-MCTP-EM-SEN	20W/30W/40W	115LM/W	35K/40K/50K	6

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL MODELS	**OPT-EM-LCL**	INTERNAL
POWDER COATING		
N/A		

PLUG IN CORD	DESCRIPTION
OPT-HBC-125TL-WH	8FT, 15A, 125V,WHITE
OPT-HBC-277TL-WH	8FT, 15A, 277V,WHITE
OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT
SENSOR	DESCRIPTION
OPT-SEN-2US	MICROWAVE
OPT-SEN-NLS-LCL	WG NETWORK SENSOR
OPT-SEN-KEILTON-LCL	KEILTON NETWORK SENSOR
WEC-3RC	(REMOTE NOT NEEDED)
OPT-2P-58	OPTIONAL RC

CCL-2FT-MCT5-DD

CCL-2FT-MCT5-DD-BK

CCL-4FT-MCT5-DD

CCL-4FT-MCT5-DD-BK

MODERN SURFACE CEILING LIGHT, DUAL DIM, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
CCL-2FT-MCT5-DD	18W/24W/30W	100LM/W	27K/30K/35K/40K/50K - 2FT	1
CCL-2FT-MCT5-DD-BK	18W/24W/30W	100LM/W	27K/30K/35K/40K/50K - 2FT, Black	1
CCL-4FT-MCT5-DD	36W/48W/60W	100LM/W	27K/30K/35K/40K/50K - 4FT	1
CCL-4FT-MCT5-DD-BK	36W/48W/60W	100LM/W	27K/30K/35K/40K/50K - 4FT, Black	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL	**OPT-EM-CCL**	External Box
POWDER COATING		
N/A		

PHOTOCELL	DESCRIPTION
N/A	N/A
SENSOR	DESCRIPTION
N/A	N/A

LRSL-4FT

LRSL-8FT

LRSL SERIES WITH CLEAR OR FROSTED LED T8 LAMPS, NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
LRSL-4FT-2L-6PK-40K-C	18W	2200LM	4000K - per lamp, 4FT, 2 LAMPS (Inc)	6
LRSL-8FT-T4L-6PK-40K-C	18W	2200LM	4000K - per lamp, 8FT, 4 LAMPS (Inc)	6
LRSL-4FT-2L-6PK-50K-C	18W	2200LM	5000K - per lamp, 4FT, 2 LAMPS (Inc)	6
LRSL-8FT-T4L-6PK-50K-C	18W	2200LM	5000K - per lamp, 8FT, 4 LAMPS (Inc)	6
LRSL-4FT-2L-6PK-40K-F	18W	2200LM	4000K - per lamp, 4FT, 2 LAMPS (Inc)	6
LRSL-8FT-T4L-6PK-40K-F	18W	2200LM	4000K - per lamp, 8FT, 4 LAMPS (Inc)	6
LRSL-4FT-2L-6PK-50K-F	18W	2200LM	5000K - per lamp, 4FT, 2 LAMPS (Inc)	6
LRSL-8FT-T4L-6PK-50K-F	18W	2200LM	5000K - per lamp, 8FT, 4 LAMPS (Inc)	6

LRSL-4FT-2L-6PK

LRSL-8FT-T4L-6PK

4FT & 8FT LED-READY STRIP LIGHT, DIRECT AC INPUT **120-277V** FOR TYPE B (AC) T8 (CAN ALSO BE USED AS 4FT 1L OR 8FT 2L) WITHOUT LAMP NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION
LRSL-4FT-2L-6PK	4FT, 2 LAMPS (Not Included)
LRSL-8FT-T4L-6PK	8FT, 4 LAMPS (Not Included)



WRAP AROUND LIGHTS

EM CAPABLE



WAS-4FT-MCTP

LED STANDARD WRAP-AROUND FIXTURE, 120~277V FOR FACTORY-INSTALLED OPTIONS SEE PAGE 218

CATALOG NO.	DESCRIPTION			PCK QTY
WAS-4FT-42W-35K-D	42W	4400LM	3500K - 4FT	1
WAS-4FT-42W-50K-D	42W	4400LM	5000K - 4FT	1
WAS-4FT-MCTP	22W/30W/38W	130LM/W	30K/40K/50K - 4FT	1

EM CAPABLE

SENSOR OPTION

WAE-2FT

WAE-4FT

WAE-8FT

BUILDER SERIES

2FT/4FT/8FT BUILDER SERIES LED ECONOMY WRAP-AROUND FIXTURES, 5.4" WIDE MCTP*: MULTI COLOR TEMPERATURE & MULTI POWER

CATALOG NO.	DESCRIPTION			PCK QTY
LED ECONOMY WRAP-AROUND FIXTURES, 0-10V DIMMING				
WAE-4FT-30K-D	40W	3200LM	3000K	6
WAE-4FT-40K-D	40W	3200LM	4000K	6
WAE-4FT-50K-D	40W	3200LM	5000K	6
CCT ADJUSTABLE LED ECONOMY WRAP-AROUND FIXTURES, 0-10V & TRIAC DIMMING				
WAE-2FT-MCT-DD	20W	1600LM	3000K/4000K/5000K	6
WAE-4FT-MCT-DD	40W	3200LM	3000K/4000K/5000K	6
CCT5 ADJUSTABLE LED ECONOMY WRAP-AROUND FIXTURES, 0-10V				
WAE-4FT-40W-MCT5-D	40W		27K/30K/35K/40K/50K	6
POWER & CCT ADJUSTABLE LED ECONOMY WRAP-AROUND FIXTURE				
WAE-4FT-40-65W-MCTP-DD	40W/50W/65W	120LM/W	30K/40K/50K	6
WAE-8FT-MCTP-DD	48W/64W/80W	70LM/W	27K/30K/35K/40K/50K	1
POWER & CCT ADJUSTABLE LED ECONOMY WRAP-AROUND FIXTURE WITH REMOTE CONTROL				
WAE-4FT-MCTP	40W Max.		2700K-5000K	6
CCT ADJUSTABLE LED ECONOMY WRAP-AROUND FIXTURES WITH SENSOR (SENSOR CAN BE DISCON.), 0-10V & TRIAC DIMMING				
WAE-2FT-MCT-DD-SEN	20W		3000K/4000K/5000K	
WAE-4FT-MCT-DD-SEN	40W		3000K/4000K/5000K	
QUICK SHIP WAE-8FT-MCTP-DD-SEN	48W/64W/80W	70LM/W	27K/30K/35K/40K/50K	1
WEC-3RC	Remote Control For Motion Sensors (For Sensor Fixtures)			
CCT ADJUSTABLE LED ECONOMY WRAP-AROUND FIXTURES WITH SENSOR (SENSOR CAN BE DISCONNECTED) & EMERGENCY BACKUP, 0-10V & TRIAC DIMMING				
WAE-2FT-MCT-DD-EM-SEN	20W		3000K/4000K/5000K	
QUICK SHIP WAE-4FT-MCT-DD-EM-SEN	40W		3000K/4000K/5000K	
EM CAPABLE WAE-8FT-MCTP-DD-EM-SEN	48W/64W/80W	70LM/W	27K/30K/35K/40K/50K	1
WEC-3RC	Remote Control For Motion Sensors (For Sensor Fixtures)			
CCT ADJUSTABLE LED ECONOMY WRAP-AROUND FIXTURES, TRIAC DIMMING				
WAE-2FT-MCT-DT*	20W	1600LM	3000K/4000K/5000K	6

WHILE SUPPLIES LAST*

WAEW-4FT-30-50W-MCTP-D

4FT BUILDER SERIES LED ECONOMY WIDE (10") WRAP-AROUND FIXTURE

CATALOG NO.	DESCRIPTION			PCK QTY
WAEW-4FT-30-50W-MCTP-D	30W/40W/50W	120LM/W	30K/40K/50K	4
QUICK SHIP WAEW-4FT-30-50W-MCTP-D-SEN	30W/40W/50W	120LM/W	30K/40K/50K	4
EM CAPABLE WAEW-4FT-30-50W-MCTP-D-EM-SEN	30W/40W/50W	120LM/W	30K/40K/50K	4

LPF-2FT-MCT-DD

LINEAR PUFF FIXTURE, DUAL DIMMING TRIAC & 0-10V SELECTABLE POWER & CCT

CATALOG NO.	DESCRIPTION		
LPF-2FT-MCT-DD	25W	2250LM	30K/40K/50K - 2FT
LPF-4FT-MCT-DD	40W	3600LM	30K/40K/50K - 4FT

WASLR-4FT-2L-NL

LED-READY 4FT 2-LAMP WRAP - LAMP NOT ICLUDED

CATALOG NO.	DESCRIPTION
WASLR-4FT-2L-NL	Led-Ready 4Ft 2-Lamp Wrap - No Lamps

COMMERCIAL LINEAR LIGHTS

cULus LISTED · DIMMING 0-10V · EM CAPABLE · SENSOR OPTION

SCLT-4FT
White



SCLP-4FT-BK
Black

SCLT-4FT-BK
Black

SCLP-4FT
White



SCLP-CB

LED PARABOLIC SUSPENDED DOWN LIGHT, 120~277V ALUMINUM FINISH

CATALOG NO.	DESCRIPTION			PCK QTY
MCT SCLP-4FT-40W-MCT-D	40W	4600LM	35K/40K/50K - White	2
MCTP SCLP-4FT-50W-MCTP-D	35W/40W/50W	115LM/W	35K/40K/50K - White	2
MCTP SCLP-4FT-50W-MCTP-D-BK	35W/40W/50W	115LM/W	35K/40K/50K - Black	2
SCLT-4FT-40W-50K-D	40W	4600LM	5000K - White	2
SCLT-4FT-40W-MCT-D	40W	4600LM	35K/40K/50K - White	2
MCT SCLT-4FT-50W-MCTP-D	30W/40W/50W	115LM/W	35K/40K/50K - White	2
MCTP SCLT-4FT-50W-MCTP-D-BK	30W/40W/50W	115LM/W	35K/40K/50K - Black	2
MCTP SCLP-CB	COUPLING BRACKET			

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	UP LIGHT	DESCRIPTION
ALL MODELS	OPT-EM-AC2EXT	EXTERNAL	OPT-SCLP-ULK	UP LIGHT 20W, MCT
	POWDER COATING		SURFACE MOUNT	DESCRIPTION
	N/A		OPT-SCLP-SURF	SURFACE-MOUNT

SCLP-UD-4FT-60W-MCT-D

SCLP-UD-CB

LED PARABOLIC SUSPENDED PERH. BASKET & LOUVER UP/DOWN LIGHT, 120~277V
SUSPENSION KIT & CABLE NOT INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
SCLP-UD-4FT-60W-MCT-D	40W/20W	4400LM/2100LM	3500K/4000K/5000K	1
SCLP-UD-CB	COUPLING BRACKET			

SPL-4FT-40W-MCT-D

4FT LED SUSPENDED UP/DOWN CLEAR PANEL LIGHT, 120~277V SUSPENSION & CORD NOT INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
SPL-4FT-40W-50K-D*	40W	2100LM/2100LM	5000K	2
SPL-4FT-40W-40K-D*	40W	2100LM/2100LM	4000K	2
SPL-4FT-40W-MCT-D	40W	2100LM/2100LM	3500K/4000K/5000K	2

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-EM-SPL	EXTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

SCLL-UD-4FT-60W-35K-D

SCLL-CB

LED LINEAR SUSPENDED PERFORATED BASKET LIGHT (UP/DOWN) SUSPENSION KIT & CABLE NOT INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
SCLL-UD-4FT-60W-50K-D	40W/20W OR 60W	4400LM/2100LM	5000K	1
SCLL-UD-4FT-60W-40K-D	40W/20W OR 60W	4400LM/2100LM	4000K	1
SCLL-UD-4FT-60W-35K-D	40W/20W OR 60W	4400LM/2100LM	3500K	1
SCLL-UD-4FT-60W-MCT-D	40W/20W OR 60W	4400LM/2100LM	35K/40K/50K	1
SCLL-CB	COUPLING BRACKET			


SCE-8FT-70W-MCTP-D-BK

SCE-8FT-70W-MCTP-D


SCE-8FT-70W-MCTP-D-SIL

SCE-XB
X CONNECTOR

SCE-SB-SIL
SEAMLESS CONNECTOR FOR ALL FINISHES

SCE-LB
L CONNECTOR

SCE-TB
T CONNECTOR

SCE-WM-KIT-SIL
WALL-MOUNT KIT FOR ALL FINISHES

BUILDER SERIES LINEAR LIGHT POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
SCE-4FT-40W-MCTP-D	30W/35W/40W	110LM/W	3500K/4000K/5000K - White	8
SCE-4FT-40W-MCTP-D-BK	30W/35W/40W	110LM/W	3500K/4000K/5000K - Black	8
SCE-4FT-40W-MCTP-D-SIL	30W/35W/40W	110LM/W	3500K/4000K/5000K - Silver	8
SCE-6FT-50W-MCTP-D	40W/45W/50W	110LM/W	3500K/4000K/5000K - White	6
SCE-6FT-50W-MCTP-D-BK	40W/45W/50W	110LM/W	3500K/4000K/5000K - Black	6
SCE-6FT-50W-MCTP-D-SIL	40W/45W/50W	110LM/W	3500K/4000K/5000K - Silver	6
SCE-8FT-70W-MCTP-D	50W/60W/72W	110LM/W	35K/40K/50K - White	4
SCE-8FT-70W-MCTP-D-BK	50W/60W/72W	110LM/W	35K/40K/50K - Black	4
SCE-8FT-70W-MCTP-D-SIL	50W/60W/72W	110LM/W	35K/40K/50K - Silver	4
SCE-ULM-4FT-MCTP-D	4Ft SCE Series Uplight Module 35/40/50K Transfers 30% Power To Top			
SCE-ULM-6FT-MCTP-D	6Ft SCE Series Uplight Module 35/40/50K Transfers 30% Power To Top			
SCE-ULM-8FT-MCTP-D	8Ft SCE Series Uplight Module 35/40/50K Transfers 30% Power To Top			
SCE-TB	SCE Series T Linking Bracket			
SCE-LB	SCE Series L Linking Bracket			
SCE-XB	SCE Series X Linking Bracket			
SCE-TB-BK	SCE Series T Linking Bracket, Black			
SCE-LB-BK	SCE Series L Linking Bracket, Black			
SCE-XB-BK	SCE Series X Linking Bracket, Black			
SCE-SB-SIL	SCE Series Straight Linking Bracket -Seamless Connection For All Finishes			
SCE-TB-SIL	SCE Series T Linking Bracket, Silver			
SCE-LB-SIL	SCE Series L Linking Bracket, Silver			
SCE-XB-SIL	SCE Series X Linking Bracket, Silver			
SCE-WM-KIT-SIL	Wall-Mount Brkt, Field-Installed, Use 2 For 4Ft And 6Ft, 3 For 8Ft, Silver			
SCE-FLEXLENS-25FT	SCE Flexible Lens Roll Of 25Ft			
SCE-FLEXLENS-100FT	SCE Flexible Lens Roll Of 100Ft			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

FOR SUSPENSION KIT SEE PAGES 231-235

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-EM-SCE	INTERNAL	N/A	N/A
	OPT-EM-SCE-8FT	INTERNAL	SENSOR	DESCRIPTION
	POWDER COATING		N/A	N/A
	N/A			

SCPL-UD-4FT-60W-50K-D

SCLP-UD-CB

4FT LED SUSPENDED 2/3 PERFORATED BASKETLIGHT (UP/DOWN) SUSPENSION KIT & CABLE NOT INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
SCPL-UD-4FT-60W-50K-D	40W/20W OR 60W	4400LM/2100LM	5000K	1
SCPL-UD-4FT-60W-40K-D	40W/20W OR 60W	4400LM/2100LM	4000K	1
SCPL-UD-4FT-60W-35K-D	40W/20W OR 60W	4400LM/2100LM	3500K	1
SCPL-UD-4FT-60W-MCT-D	60W	4400LM/2100LM	35K/40K/50K	1
SCLP-UD-CB	COUPLING BRACKET			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
All	OPT-EM-SL1INT	INTERNAL

SENSOR	DESCRIPTION
OPT-SEN-2US	MICROWAVE
OPT-SEN-NLS-SCP	WG NETWORK SENSOR
OPT-SEN-KEILTON-SCP	KEILTON NETWORK SENSOR
WEC-3RC	REMOTE CONTROL

UP/DOWN LIGHT	DESCRIPTION
OPT-SCL-LMT-35K	UP/DOWN LIGHT MODULE
OPT-SCL-LMT-40K	
OPT-SCL-LMT-50K	

POWDER COATING
OPT-CLR-100 (BK/GR/SR/WH)

SCPP-UD-4FT-60W-50K-D

SCPP-DEC

4FT LED SUSPENDED 2/3 LOUVER & PERFORATED CENTER BASKET LIGHT (UP/DOWN) SUSPENSION KIT & CABLE NOT INCLUDED, COUPLING CLIPS INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
SCPP-UD-4FT-60W-50K-D	40W/20W OR 60W	4400LM/2100LM	5000K	1
SCPP-UD-4FT-60W-40K-D	40W/20W OR 60W	4400LM/2100LM	4000K	1
SCPP-UD-4FT-60W-35K-D	40W/20W OR 60W	4400LM/2100LM	3500K	1
SCPP-DEC	DECORATIVE END CAP FOR SCPP			

COMMERCIAL RECESSED LIGHTS

CRLX-18W

CRLX-27W

CRLX-40W

CRLX-80W

Back View ENGINE + TRIM

SPEC SERIES COMMERCIAL RECESS LIGHT POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION		
MCTP CRLX4-14-27W-MCTP	14W/20W/27W	80LM/W	30K/35K/40K - 4"
MCTP CRLX6-18-40W-MCTP	18W/27W/40W	85LM/W	30K/35K/40K - 6"
MP CRLX6-50-80W-MP-30K	50W/65W/80W	85LM/W	3000K - 6"
MP CRLX6-50-80W-MP-40K	50W/65W/80W	85LM/W	4000K - 6"
MP CRLX6-50-80W-MP-50K	50W/65W/80W	85LM/W	5000K - 6"
MCTP CRLX8-18-40W-MCTP	18W/27W/40W	85LM/W	30K/35K/40K - 8"
MP CRLX8-50-80W-MP-30K	50W/65W/80W	85LM/W	3000K - 8"
MP CRLX8-50-80W-MP-40K	50W/65W/80W	85LM/W	4000K - 8"
MP CRLX8-50-80W-MP-50K	50W/65W/80W	85LM/W	5000K - 8"
MCTP CRLX10-18-40W-MCTP	18W/27W/40W	85LM/W	30K/35K/40K - 10"
MP CRLX10-50-80W-MP-30K	50W/65W/80W	85LM/W	3000K - 10"
MP CRLX10-50-80W-MP-40K	50W/65W/80W	85LM/W	4000K - 10"
MP CRLX10-50-80W-MP-50K	50W/65W/80W	85LM/W	5000K - 10"



CRL-HSG

CRL-BH

LED COMMERCIAL RECESSED LIGHT HOUSINGS

CATALOG NO.	DESCRIPTION
CRL-HSG-4	Commercial Recessed Light Housings, 4"
CRL-HSG-6	Commercial Recessed Light Housings, 6"
CRL-HSG-8	Commercial Recessed Light Housings, 8"
CRL-HSG-10	Commercial Recessed Light Housings, 10"
CRL-BH	Bar Hanger For Commercial Recessed Housings

c UL us LISTED · ENERGY STAR · DIMMING 0-10V · DAMP LOCATIONS · EM CAPABLE

Shown with Housing (Not Included, See Below)

WHILE SUPPLIES LAST

LED COMMERCIAL RECESSED LIGHT, 120~277V

CATALOG NO.	DESCRIPTION		
CRL4-27W-30K	27W	1800LM	3000K
CRL4-27W-40K	27W	1900LM	4000K
CRL4-27W-50K	27W	1950LM	5000K
CRL6-18W-30K	18W	1639LM	3000K
CRL6-18W-50K	18W	1639LM	5000K
CRL6-27W-30K	27W	2387LM	3000K
CRL6-40W-30K	40W	3447LM	3000K
CRL6-40W-50K	40W	3447LM	5000K
CRL6-54W-30K	54W	4500LM	3000K
CRL6-54W-40K	54W	4500LM	4000K
CRL6-54W-50K	54W	4500LM	5000K
CRL8-18W-30K	18W	1639LM	3000K
CRL8-18W-50K	18W	1639LM	5000K
CRL8-27W-30K	27W	2387LM	3000K
CRL8-40W-30K	40W	3447LM	3000K
CRL8-40W-50K	40W	3447LM	5000K
CRL8-54W-30K	54W	4500LM	3000K
CRL8-54W-40K	54W	4500LM	4000K
CRL8-54W-50K	54W	4500LM	5000K
CRL10-18W-30K	18W	1639LM	3000K
CRL10-18W-50K	18W	1639LM	5000K
CRL10-27W-30K	27W	2387LM	3000K
CRL10-40W-30K	40W	3447LM	3000K
CRL10-40W-50K	40W	3447LM	5000K
CRL10-54W-30K	54W	4500LM	3000K
CRL10-54W-40K	54W	4500LM	4000K
CRL10-54W-50K	54W	4500LM	5000K

CRLE

CRLE-TRM-BK

CRLE-TRM-BN

CRLE-TRM-BR


CRLE-RI

CRLE-TBAR

BUILDER SERIES COMMERCIAL RECESS LIGHT POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
CRLE4-5-12W-MCTP-WH	5W/7W/12W	100LM/W	30K/35K/40K - 4"	8
CRLE6-7-18W-MCTP-WH	7W/10W/18W	100LM/W	30K/35K/40K - 6"	8
CRLE6-HO-25-40W-MCTP-WH	25W/30W/40W	100LM/W	30K/35K/40K - 6", High-Output	8
CRLE8-10-22W-MCTP-WH	10W/15W/22W	100LM/W	30K/35K/40K - 8"	8
CRLE8-HO-34-52W-MCTP-WH	34W/42W/52W	100LM/W	30K/35K/40K - 8", High-Output	8
CRLE10-20-32W-MCTP-WH	20W/25W/32W	100LM/W	30K/35K/40K - 10"	4
CRLE10-HO-26-40W-MCTP-WH	26W/32W/40W	100LM/W	30K/35K/40K - 10", High-Output	4
CRLE-RI-TBAR-UNV	Snap-In Comm. Recessed Light Universal TBAR Plate			
CRLE-RI-UNV	Snap-In Comm. Recessed Light Universal Rough-In Plate			
CRLE4-TRM-BK	4" Snap-In Comm. Recessed Light 4In Black Trim + Ring Set			
CRLE4-TRM-BN	4" Snap-In Comm. Recessed Light 4In Brushed Nickel Trim + Ring Set			
CRLE6-TRM-BK	6" Snap-In Comm. Recessed Light 6In Black Trim + Ring Set			
CRLE6-TRM-BN	6" Snap-In Comm. Recessed Light 6In Brushed Nickel Trim + Ring Set			
CRLE8-TRM-BK	8" Snap-In Comm. Recessed Light 8In Black Trim + Ring Set			
CRLE8-TRM-BN	8" Snap-In Comm. Recessed Light 8In Brushed Nickel Trim + Ring Set			
CRLE10-TRM-BK	10" Snap-In Comm. Recessed Light 10In Black Trim + Ring Set			
CRLE10-TRM-BN	10" Snap-In Comm. Recessed Light 10In Brushed Nickel Trim + Ring Set			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-EM-CRLE	EXTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

CRLE4-BF-7-12W-MCTP-FR

CRLE6-BF-10-18W-MCTP-FR

CRLE8-BF-15-25W-MCTP-FR

FIRE-RATED DEEP BAFFLE COMMERCIAL RECESSED LIGHT POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
CRLE4-BF-7-12W-MCTP-FR	7W/9W/12W	130LM/W	27K/30K/35K/40K/50K	18
CRLE6-BF-10-18W-MCTP-FR	10W/14W/18W	130LM/W	27K/30K/35K/40K/50K	12
CRLE8-BF-15-25W-MCTP-FR	15W/20W/25W	130LM/W	27K/30K/35K/40K/50K	12

CRLB4-7-15W-MCTP5-WH

CRLB6-10-18W-MCTP5-WH

CRLB8-18-30W-MCTP5-WH

CRLB10-22-38W-MCTP5-WH

BUILDER SERIES COMMERCIAL RECESSED LIGHT WITH REMOTE DRIVER 5CCT CRI90 0-10V ADJUSTABLE POWER

CATALOG NO.	DESCRIPTION			PCK QTY
CRLB4-7-15W-MCTP5-WH	7W/11W/15W	86LM/W	27K/30K/35K/40K/50K - 4" White	16
CRLB6-10-18W-MCTP5-WH	10W/15W/18W	86LM/W	27K/30K/35K/40K/50K - 6" White	12
CRLB8-18-30W-MCTP5-WH	18W/24W/30W	86LM/W	27K/30K/35K/40K/50K - 8" White	8
CRLB10-22-38W-MCTP5-WH	22W/30W/38W	86LM/W	27K/30K/35K/40K/50K - 10" White	8

RSLC6-BF

LED COMMERCIAL SLIM CANLESS RECESSED REGRESSED BAFFLE LIGHT **120-277V** 0~10V DIM

CATALOG NO.	DESCRIPTION			PCK QTY
RSLC6-BF-30K	15W	1200LM	3000K - 6"	12
RSLC6-BF-40K	15W	1200LM	4000K - 6"	12
RSLC8-BF-30K	18W	1440LM	3000K - 8"	12
RSLC6-BF-MCT5	15W	1200LM	27K/30K/35K/40K/50K - 6"	20
RSLC8-BF-MCT5	18W	1440LM	27K/30K/35K/40K/50K - 8"	22
RSL-BF-EXT-6FT	RSL-BF 6FT. DC extension cord			
RSL-BF-EXT-10FT	RSL-BF 10FT. DC extension cord			
RSL-BF-EXT-20FT	RSL-BF 20FT. DC extension cord			

CRLC-468-RIBH-JB



CRLCS-46-RIBH-JB

MOUNTING PLATE WITH BRACKETS AND J-BOX

CATALOG NO.	DESCRIPTION
CRLC-468-RIBH-JB	CRLC Series Mounting Plate With Brackets And J-Box 4/6/8 in
CRLCS-46-RIBH-JB	CRLC Square Mounting Plate With Brackets And J-Box 4/6 in

CRLC-EGN-40W-MCTP-D

ROUND & OPEN RECESSED LIGHT

SQUARE & OPEN RECESSED LIGHT

ROUND & WALL WASH RECESSED LIGHT

SQUARE & WALL WASH RECESSED LIGHT

CRLC-TRM-4 Round


CRLC-TRM-4 Round Wall Wash

CRLC-TRM-4 Square


CRLC-TRM-4 Square Wall Wash

4” LED COMMERCIAL RECESSED LIGHT (CLIP-ON/SNAP-IN) WITH OR WITHOUT HOUSING

CATALOG NO.	DESCRIPTION		
LIGHT ENGINE ONLY			
CRLC-EGN-20W-MCTP-D	10W/15W/20W	80LM/W	30K/35K/40K
CRLC-EGN-40W-MCTP-D	27W/34W/40W	80LM/W	30K/35K/40K
4” 20W & 40W			
CRLC4-20W-MCTP-D	10W/15W/20W	80LM/W	30K/35K/40K
CRLC4-20W-MCTP-A-D	10W/15W/20W	80LM/W	30K/35K/40K
CRLC4-20W-MCTP-D-WH	10W/15W/20W	80LM/W	30K/35K/40K
CRLC4-20W-MCTP-A-D-WH	10W/15W/20W	80LM/W	30K/35K/40K
CRLC4-20W-MCTP-D-RG	10W/15W/20W	80LM/W	30K/35K/40K
CRLC4-20W-MCTP-S-D	10W/15W/20W	80LM/W	30K/35K/40K
CRLC4-20W-MCTP-SA-D	10W/15W/20W	80LM/W	30K/35K/40K
CRLC4-20W-MCTP-S-D-WH	10W/15W/20W	80LM/W	30K/35K/40K
CRLC4-20W-MCTP-SA-D-WH	10W/15W/20W	80LM/W	30K/35K/40K
CRLC4-40W-MCTP-D	27W/34W/40W	80LM/W	30K/35K/40K
CRLC4-40W-MCTP-A-D	27W/34W/40W	80LM/W	30K/35K/40K
CRLC4-40W-MCTP-D-WH	27W/34W/40W	80LM/W	30K/35K/40K
CRLC4-40W-MCTP-A-D-WH	27W/34W/40W	80LM/W	30K/35K/40K
CRLC4-40W-MCTP-D-RG	27W/34W/40W	80LM/W	30K/35K/40K
CRLC4-40W-MCTP-S-D	27W/34W/40W	80LM/W	30K/35K/40K
CRLC4-40W-MCTP-SA-D	27W/34W/40W	80LM/W	30K/35K/40K
CRLC4-40W-MCTP-S-D-WH	27W/34W/40W	80LM/W	30K/35K/40K
CRLC4-40W-MCTP-SA-D-WH	27W/34W/40W	80LM/W	30K/35K/40K
LIGHT ENGINE ONLY			
CRLC-EGN-60W-MCTP-D	40W/50W/60W	80LM/W	30K/35K/40K
4” 60W MAX			
CRLC4-60W-MCTP-D	40W/50W/60W	80LM/W	30K/35K/40K
CRLC4-60W-MCTP-D-WH	40W/50W/60W	80LM/W	30K/35K/40K
CRLC4-60W-MCTP-D-RG	40W/50W/60W	80LM/W	30K/35K/40K
CRLC4-60W-MCTP-S-D	40W/50W/60W	80LM/W	30K/35K/40K
CRLC4-60W-MCTP-S-D-WH	40W/50W/60W	80LM/W	30K/35K/40K

4” TRIMS ONLY

CATALOG NO.	DESCRIPTION
CRLC-TRM-4	4" Trim For CRLC Series, Haze Finish
CRLC-TRM-4A	CRLC Series 4in Round Wall Wash Trim - Haze
CRLC-TRM-4-WH	4" Trim For CRLC Series, Haze Finish, White
CRLC-TRM-4A-WH	CRLC Series 4in Round Wall Wash Trim - White
CRLC-TRM-4-RG	CRLC Series 4in Round Down Light Trim - Rose Gold
CRLC-TRM-4S	CRLC Series 4in Square Down Light Trim - Haze
CRLC-TRM-4SA	CRLC Series 4in Square Wall Wash Trim - Haze
CRLC-TRM-4S-WH	CRLC Series 4in Square Down Light Trim - White
CRLC-TRM-4SA-WH	CRLC Series 4in Square Wall Wash Trim - White

CRLC-EGN-60W-MCTP-D

CRLC-TRM-6S
Square Trim
Open Haze Finish & White Ring



CRLC-TRM-6SA
Square Trim
Wall White Haze Finish & White Ring

CRLC-TRM-6
Round Trim
Open Haze Finish & White Ring

CRLC-TRM-6-WH
Round Trim
Open White finish & White ring

CRLC-TRM-6-RG
Round Trim
Open Rose Gold & White Ring

CRLC-TRM-6A
Round Trim
Wall Wash Haze Finish & White Ring

6” LED COMMERCIAL RECESSED LIGHT (CLIP-ON/SNAP-IN) WITH OR WITHOUT HOUSING

CATALOG NO.	DESCRIPTION			PCK QTY
LIGHT ENGINE ONLY				
CRLC-EGN-20W-MCTP-D	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC-EGN-40W-MCTP-D	27W/34W/40W	80LM/W	30K/35K/40K	
6” 20W & 40W				
CRLC6-20W-MCTP-D	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC6-20W-MCTP-A-D	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC6-20W-MCTP-D-WH	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC6-20W-MCTP-A-D-WH	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC6-20W-MCTP-D-RG	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC6-20W-MCTP-S-D	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC6-20W-MCTP-SA-D	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC6-20W-MCTP-S-D-WH	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC6-20W-MCTP-SA-D-WH	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC6-40W-MCTP-D	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC6-40W-MCTP-A-D	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC6-40W-MCTP-D-WH	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC6-40W-MCTP-A-D-WH	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC6-40W-MCTP-D-RG	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC6-40W-MCTP-S-D	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC6-40W-MCTP-SA-D	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC6-40W-MCTP-S-D-WH	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC6-40W-MCTP-SA-D-WH	27W/34W/40W	80LM/W	30K/35K/40K	
LIGHT ENGINE ONLY				
CRLC-EGN-60W-MCTP-D	40W/50W/60W	80LM/W	30K/35K/40K	
6” 60W MAX				
CRLC6-60W-MCTP-D	40W/50W/60W	80LM/W	30K/35K/40K	
CRLC6-60W-MCTP-D-WH	40W/50W/60W	80LM/W	30K/35K/40K	
CRLC6-60W-MCTP-D-RG	40W/50W/60W	80LM/W	30K/35K/40K	
CRLC6-60W-MCTP-S-D	40W/50W/60W	80LM/W	30K/35K/40K	
CRLC6-60W-MCTP-S-D-WH	40W/50W/60W	80LM/W	30K/35K/40K	

6” TRIMS ONLY

CATALOG NO.	DESCRIPTION	PCK QTY
CRLC-TRM-6	6" Trim For CRLC Series, Haze Finish	
CRLC-TRM-6A	CRLC Series 6in Round Wall Wash Trim - Haze	
CRLC-TRM-6-WH	6" Trim For CRLC Series, Haze Finish, White	
CRLC-TRM-6A-WH	CRLC Series 6in Round Wall Wash Trim - White	
CRLC-TRM-6-RG	CRLC Series 6in Round Down Light Trim - Rose Gold	
CRLC-TRM-6S	CRLC Series 6in Square Down Light Trim - Haze	
CRLC-TRM-6SA	CRLC Series 6in Square Wall Wash Trim - Haze	
CRLC-TRM-6S-WH	CRLC Series 6in Square Down Light Trim - White	
CRLC-TRM-6SA-WH	CRLC Series 6in Square Wall Wash Trim - White	

CRLC-EGN-60W-MCTP-D

CRLC-TRM-6S
Square Trim
Open Haze Finish & White Ring



CRLC-TRM-6SA
Square Trim
Wall White Haze Finish & White Ring

CRLC-TRM-6
Round Trim
Open Haze Finish & White Ring

CRLC-TRM-6-WH
Round Trim
Open White finish & White ring

CRLC-TRM-6-RG
Round Trim
Open Rose Gold & White Ring

CRLC-TRM-6A
Round Trim
Wall Wash Haze Finish & White Ring

8”/10”LED COMMERCIAL RECESSED LIGHT (CLIP-ON/SNAP-IN) WITH OR WITHOUT HOUSING

CATALOG NO.	DESCRIPTION			PCK QTY
LIGHT ENGINE ONLY				
CRLC-EGN-20W-MCTP-D	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC-EGN-40W-MCTP-D	27W/34W/40W	80LM/W	30K/35K/40K	
8” 20W MAX				
CRLC8-20W-MCTP-D	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC8-20W-MCTP-D-WH	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC8-20W-MCTP-D-RG	10W/15W/20W	80LM/W	30K/35K/40K	
10” 20W MAX				
CRLC10-20W-MCTP-D	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC10-20W-MCTP-D-WH	10W/15W/20W	80LM/W	30K/35K/40K	
CRLC10-20W-MCTP-D-RG	10W/15W/20W	80LM/W	30K/35K/40K	
8” 40W MAX				
CRLC8-40W-MCTP-D	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC8-40W-MCTP-D-WH	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC8-40W-MCTP-D-RG	27W/34W/40W	80LM/W	30K/35K/40K	
10” 40W MAX				
CRLC10-40W-MCTP-D	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC10-40W-MCTP-D-WH	27W/34W/40W	80LM/W	30K/35K/40K	
CRLC10-40W-MCTP-D-RG	27W/34W/40W	80LM/W	30K/35K/40K	
LIGHT ENGINE ONLY				
CRLC-EGN-60W-MCTP-D	40W/50W/60W	80LM/W	30K/35K/40K	
8” 60W MAX				
CRLC8-60W-MCTP-D	40W/50W/60W	80LM/W	30K/35K/40K	
CRLC8-60W-MCTP-D-WH	40W/50W/60W	80LM/W	30K/35K/40K	
CRLC8-60W-MCTP-D-RG	40W/50W/60W	80LM/W	30K/35K/40K	
10” 60W MAX				
CRLC10-60W-MCTP-D	40W/50W/60W	80LM/W	30K/35K/40K	
CRLC10-60W-MCTP-D-WH	40W/50W/60W	80LM/W	30K/35K/40K	
CRLC10-60W-MCTP-D-RG	40W/50W/60W	80LM/W	30K/35K/40K	

8”/10” TRIMS ONLY

CATALOG NO.	DESCRIPTION	PCK QTY
8” TRIMS		
CRLC-TRM-8	8" Trim For CRLC Series, Haze Finish	
CRLC-TRM-8-WH	8" Trim For CRLC Series, White Finish	
CRLC-TRM-8-RG	CRLC Series 8in Round Down Light Trim - Rose Gold	
10” TRIMS		
CRLC-TRM-10	CRLC Series 10in Round Down Light Trim - Haze	
CRLC-TRM-10-WH	CRLC Series 10in Round Down Light Trim - White	
CRLC-TRM-10-RG	CRLC Series 10in Round Down Light Trim - Rose Gold	

COMMERCIAL SPECIALTY

POB-F-3FT-40W

POB-UD-3FT-45W-40K-D
POB-UD-4FT-60W-40K-D



POB-HB-3FT-56W

POB-VB-3FT-56W

PATIENT OVERBED HEALTHCARE LIGHT WITH PULL CHAIN AND INDICATOR LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
POB-UD-3FT-45W-40K-D	15W UP 35W DOWN	5175LM	4000K - 3FT	4
POB-UD-4FT-60W-40K-D	20W UP 40W DOWN	6900LM	4000K - 4FT	4
POB-F-3FT-40W	20W UP 20W DOWN	2800LM	27K/30K/40K - 3FT	4
POB-HB-3FT-56W	20W UP 36W DOWN	2800LM	27K/30K/40K - 3FT	4
POB-VB-3FT-56W	20W UP 36W DOWN	2800LM	27K/30K/40K - 3FT	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
All	OPT-EM-SL1INT	INTERNAL

SENSOR	DESCRIPTION
OPT-SEN-2US	MICROWAVE
OPT-SEN-NLS-SCP	WG NETWORK SENSOR
OPT-SEN-KEILTON-SCP	KEILTON NETWORK SENSOR
WEC-3RC	REMOTE CONTROL

UP/DOWN LIGHT	DESCRIPTION
OPT-SCL-LMT-35K	UP/DOWN LIGHT MODULE
OPT-SCL-LMT-40K	
OPT-SCL-LMT-50K	

POWDER COATING
OPT-CLR-100 (BK/GR/SR/WH)

SCL-CSK-6FT
SCL-CSK-12FT
SCL-CSK-20FT

SCL-CSK-6FT-BK
SCL-CSK-12FT-BK
SCL-CSK-20FT-BK

SCL-CSMK-6FT
SCL-CSMK-12FT
SCL-CSMK-20FT

SCL-CSMK-6FT-BK
SCL-CSMK-12FT-BK
SCL-CSMK-20FT-BK

SCL-CSKC-6FT
SCL-CSKC-12FT
SCL-CSKC-20FT

SCL-CSKC-6FT-BK
SCL-CSKC-12FT-BK
SCL-CSKC-20FT-BK

SCL-CS1-6FT
SCL-CS1-12FT
SCL-CS1-20FT

SCL-CS1-6FT-BK
SCL-CS1-12FT-BK
SCL-CS1-20FT-BK

SCL-CS1P-6FT
SCL-CS1P-12FT
SCL-CS1P-20FT

SCL-CS1P-6FT-BK
SCL-CS1P-12FT-BK
SCL-CS1P-20FT-BK

SCL-CS1P-6FT-NC
SCL-CS1P-12FT-NC
SCL-CS1P-20FT-NC

SCL-CS1P-6FT-NC-BK
SCL-CS1P-12FT-NC-BK
SCL-CS1P-20FT-NC-BK

GRIP & SUSPENSION ACCESSORIES

COMPATIBLE SERIES: SCX (SINGLE KEYHOLE)/ LSL, LSS ("Y" END & HOOK OR "Y" END & TOGGLE)/SCLP, SCPL-UD, SCLL, SCPP, SCX6 ("Y" END & KEYHOLE) & 2FT, 3FT, 4FT FIXTURES NEED 2 SUSPENSION & CABLES (2 ON ENDS)/ 6FT & 8FT FIXTURES NEED 3 SUSPENSION & CABLES (1 IN CENTER, 2 ON ENDS)

CATALOG NO.	DESCRIPTION
SCL-4CS10	ADJ. 10FT 1/16in QUAD CABLE SUSP. CANOPY KIT, KEYHOLE CONNECTORS (NO CORD INCL.)
SCL-CSK-6FT	ADJ. 6FT 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES WITH KEYHOLE END CONNECTORS
SCL-CSK-12FT	ADJ. 12FT 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES WITH KEYHOLE END CONNECTORS
SCL-CSK-20FT	ADJ. 20ft 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES WITH KEYHOLE END CONNECTORS
SCL-CSK-6FT-BK	ADJ. 6FT 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES WITH KEYHOLE END CONNECTORS, BLACK
SCL-CSK-12FT-BK	ADJ. 12FT 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES WITH KEYHOLE END CONNECTORS, BLACK
SCL-CSK-20FT-BK	ADJ. 20ft 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES WITH KEYHOLE END CONNECTORS BLACK
SCL-CSMK-6FT	ADJ. 6FT 1/16in SUSPENSION CANOPY COMPLETE KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS
SCL-CSMK-12FT	ADJ. 12FT 1/16in SUSPENSION CANOPY COMPLETE KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS
SCL-CSMK-20FT	ADJ. 20ft 1/16in SUSPENSION CANOPY COMPLETE KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS
SCL-CSMK-6FT-BK	ADJ. 6FT 1/16in SUSPENSION CANOPY COMPLETE KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS BLACK
SCL-CSMK-12FT-BK	ADJ. 12FT 1/16in SUSPENSION CANOPY COMPLETE KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS BLACK
SCL-CSMK-20FT-BK	ADJ. 20ft 1/16in SUSPENSION CANOPY COMPLETE KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS BLACK
SCL-CSKC-6FT	ADJ. 6FT 1/16in SUSPENSION CANOPY COMPLETE KIT WITH DECOR NON-POWER CEILING ATTACHMENT - KEYHOLE ENDS
SCL-CSKC-12FT	ADJ. 12FT 1/16in SUSPENSION CANOPY COMPLETE KIT WITH DECOR NON-POWER CEILING ATTACHMENT - KEYHOLE ENDS
SCL-CSKC-20FT	ADJ. 20FT 1/16in SUSPENSION CANOPY COMPLETE KIT WITH DECOR NON-POWER CEILING ATTACHMENT - KEYHOLE ENDS
SCL-CSKC-6FT-BK	ADJ. 6FT 1/16in SUSPENSION CANOPY COMPLETE KIT WITH DECOR NON-POWER CEILING ATTACHMENT - KEYHOLE ENDS BLACK
SCL-CSKC-12FT-BK	ADJ. 12FT 1/16in SUSPENSION CANOPY COMPLETE KIT WITH DECOR NON-POWER CEILING ATTACHMENT - KEYHOLE ENDS BLACK
SCL-CSKC-20FT-BK	ADJ. 20FT 1/16in SUSPENSION CANOPY COMPLETE KIT WITH DECOR NON-POWER CEILING ATTACHMENT - KEYHOLE ENDS BLACK
SCL-CS1-6FT	ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE
SCL-CS1-12FT	ADJ. 12FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE
SCL-CS1-20FT	ADJ. 20FT 1/16in SINGLE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE
SCL-CS1-6FT-BK	BLACK ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE
SCL-CS1-12FT-BK	BLACK ADJ. 12FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE
SCL-CS1-20FT-BK	ADJ. 20FT 1/16in SINGLE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE, BLACK
SCL-CS1P-6FT	ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE WITH SJTW18/5 WHITE CORD
SCL-CS1P-12FT	ADJ. 12FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE WITH CORD
SCL-CS1P-20FT	ADJ. 20FT 1/16in SINGLE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE WITH SJTW18/5 WHITE CORD
SCL-CS1P-6FT-BK	BLACK ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE WITH SJTW18/5 BLACK CORD
SCL-CS1P-12FT-BK	BLACK ADJ. 12FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR WITH CORD
SCL-CS1P-20FT-BK	ADJ. 20FT 1/16in SINGLE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE WITH SJTW18/5 WHITE CORD, BLACK
SCL-CS1P-6FT-NC	ADJ. 6FT 1/16in,1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE WITHOUT CORD
SCL-CS1P-12FT-NC	ADJ. 12FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE WITHOUT CORD
SCL-CS1P-20FT-NC	ADJ. 20FT 1/16in SINGLE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITHOUT CORD
SCL-CS1P-6FT-NC-BK	BLACK ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE WITHOUT CORD
SCL-CS1P-12FT-NC-BK	BLACK ADJ. 12FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR WITHOUT CORD
SCL-CS1P-20FT-NC-BK	ADJ. 20FT 1/16in SINGLE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITHOUT CORD, BLACK
OPT-SCL-XLENGTH	LABOR CHARGE FOR CUSTOM CABLE LENGTH, SPECIFY DESIRED LENGTH IN PO. MUST PURCHASE SUFFICIENT ROLLS OF AIRCRAFT CABLE & POWER CORD SEE PAGE 173

SCL-CSQMK-6FT
SCL-CSQMK-12FT
SCL-CSQMK-20FT

SCL-CSQMK-6FT-BK
SCL-CSQMK-12FT-BK
SCL-CSQMK-20FT-BK

SCL-CSQ1-6FT
SCL-CSQ1-12FT
SCL-CSQ1-20FT

SCL-CSQ1-6FT-BK
SCL-CSQ1-12FT-BK
SCL-CSQ1-20FT-BK

SCL-CSQ1P-6FT
SCL-CSQ1P-12FT
SCL-CSQ1P-20FT

SCL-CSQ1P-6FT-BK
SCL-CSQ1P-12FT-BK
SCL-CSQ1P-20FT-BK

SCL-CSQ1P-6FT-NC
SCL-CSQ1P-6FT-NC
SCL-CSQ1P-6FT-NC

SCL-CSQ1P-6FT-NC-BK
SCL-CSQ1P-6FT-NC-BK
SCL-CSQ1P-6FT-NC-BK

SCL-CCK-6FT
SCL-CCK-12FT
SCL-CCK-20FT

SCL-CCK-6FT-BK
SCL-CCK-12FT-BK
SCL-CCK-20FT-BK

SCL-CS1M-6FT
SCL-CS1M-12FT
SCL-CS1M-20FT

SCL-CS1M-6FT-BK
SCL-CS1M-12FT-BK
SCL-CS1M-20FT-BK

SCL-CS1MP-6FT
SCL-CS1MP-12FT
SCL-CS1MP-20FT

SCL-CS1MP-6FT-BK
SCL-CS1MP-12FT-BK
SCL-CS1MP-20FT-BK

GRIP & SUSPENSION ACCESSORIES

COMPATIBLE SERIES: SCX (SINGLE KEYHOLE)/ LSL, LSS ("Y" END & HOOK OR "Y" END & TOGGLE)/SCLP, SCPL-UD, SCLL, SCPP, SCX6 ("Y" END & KEYHOLE) & 2FT, 3FT, 4FT FIXTURES NEED 2 SUSPENSION & CABLES (2 ON ENDS)/ 6FT & 8FT FIXTURES NEED 3 SUSPENSION & CABLES (1 IN CENTER, 2 ON ENDS)

CATALOG NO.	DESCRIPTION
SCL-CSQMK-6FT	ADJ. 6FT 1/16in SUSPENSION CANOPY COMPLETE SQ KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS
SCL-CSQMK-12FT	ADJ. 12FT 1/16in SUSPENSION CANOPY COMPLETE SQ KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS
SCL-CSQMK-20FT	ADJ. 20FT 1/16in SUSPENSION CANOPY COMPLETE SQ KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS
SCL-CSQMK-6FT-BK	ADJ. 6FT 1/16in SUSPENSION CANOPY COMPLETE SQ KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS, BLACK
SCL-CSQMK-12FT-BK	ADJ. 12FT 1/16in SUSPENSION CANOPY COMPLETE SQ KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS BLACK
SCL-CSQMK-20FT-BK	ADJ. 20FT 1/16in SUSPENSION CANOPY COMPLETE SQ KIT WITH MINI NON-POWR CANOPY KEYHOLE END CONNECTORS BLACK
SCL-CSQ1-6FT	ADJ. 6FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE
SCL-CSQ1-12FT	ADJ. 12FT 1/16in,1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE
SCL-CSQ1-20FT	ADJ. 20FT 1/16in SINGLE SQUARE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE
SCL-CSQ1-6FT-BK	ADJ. 6FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE, BLACK
SCL-CSQ1-12FT-BK	ADJ. 12FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE, BLACK
SCL-CSQ1-20FT-BK	ADJ. 20FT 1/16in SINGLE SQUARE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE, BLACK
SCL-CSQ1P-6FT	ADJ. 6FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITH CORD
SCL-CSQ1P-12FT	ADJ. 12FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITH CORD
SCL-CSQ1P-20FT	ADJ. 20FT 1/16in SINGLE SQUARE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, KIT
SCL-CSQ1P-6FT-BK	ADJ. 6FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITH CORD, BLACK
SCL-CSQ1P-12FT-BK	ADJ. 12FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITH CORD, BLACK
SCL-CSQ1P-20FT-BK	ADJ. 20FT 1/16in SINGLE SQUARE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, KIT, BLACK
SCL-CSQ1P-6FT-NC	ADJ. 6FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITHOUT CORD
SCL-CSQ1P-12FT-NC	ADJ. 12FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITHOUT CORD
SCL-CSQ1P-20FT-NC	ADJ. 20FT 1/16in SINGLE SQUARE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITHOUT CORD
SCL-CSQ1P-6FT-NC-BK	ADJ. 6FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITHOUT CORD, BLACK
SCL-CSQ1P-12FT-NC-BK	ADJ. 12FT 1/16in, 1.5mm SINGLE SQUARE SUSPENSION 5in CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITHOUT CORD, BLACK
SCL-CSQ1P-20FT-NC-BK	ADJ. 20FT 1/16in SINGLE SQUARE SUSPENSION CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE, WITHOUT CORD, BLACK
SCL-CCK-6FT	ADJ. 6FT 1/16in SUSPENSION WIRE WITH DECOR CEILING ATTACHMENT - KEYHOLE END
SCL-CCK-12FT	ADJ. 12FT 1/16in SUSPENSION WIRE WITH DECOR CEILING ATTACHMENT - KEYHOLE END
SCL-CCK-20FT	ADJ. 20FT 1/16in SUSPENSION WIRE WITH DECOR CEILING ATTACHMENT - KEYHOLE END
SCL-CCK-6FT-BK	ADJ. 6FT 1/16in SUSPENSION WIRE WITH DECOR CEILING ATTACHMENT - KEYHOLE END BLACK
SCL-CCK-12FT-BK	ADJ. 12FT 1/16in SUSPENSION WIRE WITH DECOR CEILING ATTACHMENT - KEYHOLE END BLACK
SCL-CCK-20FT-BK	ADJ. 20FT 1/16in SUSPENSION WIRE WITH DECOR CEILING ATTACHMENT - KEYHOLE END BLACK
SCL-CS1M-6FT	ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 2in MINI CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE
SCL-CS1MP-6FT-BK	ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 2in MINI CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE WITH SJTW18/5 WHITE CORD, BLACK
SCL-CS1MP-6FT	ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 2in MINI CANOPY SET WITH KEYHOLE END CONNECTOR, POWER SIDE WITH SJTW18/5 WHITE CORD
SCL-CS1M-6FT-BK	ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 2in MINI CANOPY SET WITH KEYHOLE END CONNECTOR, NON-POWER SIDE, BLACK

SCL-CSYK-6FT
SCL-CSYK-12FT
SCL-CSYK-20FT

SCL-CSYK-6FT-BK
SCL-CSYK-12FT-BK
SCL-CSYK-20FT-BK

SCL-CSY1-6FT
SCL-CSY1-12FT

SCL-CSY1P-6FT
SCL-CSY1P-12FT

SCL-CSY1P-6FT-NC

SCL-3CS10

CMC-SRK-218-5C-WH
CMC-SRK-224-5C-WH

CMC-SRK-218-5C-BK
CMC-SRK-224-5C-BK

CMC-SRK-218-5C-BR
CMC-SRK-224-5C-BR

SCL-GTY10
SCL-GTY20
SCL-GTY210
SCL-GTY220

SCL-GSY10
SCL-GSY20

SCL-GSY110
SCL-GSY120

SCL-GS10
SCL-GS20

SCL-GS210
SCL-GS220

SCL-CSR-12FT

SCL-CSR-12FT-BK

SCL-WRCL-14

SCL-TBJJ-14-4

SCL-WRCL-DUPLEX

SCL-PEP-M8

SCL-ASC-4MM-250FT

SCL-WRTH-14

GRIP & SUSPENSION ACCESSORIES

COMPATIBLE SERIES: SCX (SINGLE KEYHOLE)/ LSL, LSS ("Y" END & HOOK OR "Y" END & TOGGLE)/SCLP, SCPL-UD, SCLL, SCPP, SCX6 ("Y" END & KEYHOLE) & 2FT, 3FT, 4FT FIXTURES NEED 2 SUSPENSION & CABLES (2 ON ENDS)/ 6FT & 8FT FIXTURES NEED 3 SUSPENSION & CABLES (1 IN CENTER, 2 ON ENDS)

CATALOG NO.	DESCRIPTION
SCL-CSYK-6FT	ADJ. 6FT 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES - KEYHOLE Y END CONNECTORS
SCL-CSYK-12FT	ADJ. 12FT 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES - KEYHOLE Y END CONNECTORS
SCL-CSYK-20FT	ADJ. 20FT 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES - KEYHOLE Y END CONNECTORS
SCL-CSYK-12FT-BK	ADJ. 12FT 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES - KEYHOLE Y END CONNECTORS BLACK
SCL-CSYK-6FT-BK	ADJ. 6FT 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES - KEYHOLE Y END CONNECTORS BLACK
SCL-CSYK-20FT-BK	ADJ. 20FT 1/16in SUSPENSION CANOPY COMPLETE KIT FOR BOTH SIDES - KEYHOLE Y END CONNECTORS BLACK
SCL-CSY1-6FT	ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH Y DOUBLE KEYHOLE END CONNECTORS, NON-POWER SIDE
SCL-CSY1P-6FT	ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH Y DOUBLE KEYHOLE END CONNECTORS, POWER SIDE WITH SJTW18/5 WHITE CORD
SCL-CSY1P-6FT-NC	ADJ. 6FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH Y DOUBLE KEYHOLE END CONNECTORS
SCL-CSY1-12FT	ADJ. 12FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH Y DOUBLE KEYHOLE END CONNECTORS, NON-POWER SIDE
SCL-CSY1P-12FT	ADJ. 12FT 1/16in, 1.5mm SINGLE SUSPENSION 5in CANOPY SET WITH Y DOUBLE KEYHOLE END CONNECTORS, POWER SIDE WITH SJTW18/5 WHITE CORD
SCL-3CS10	ADJ. 10FT 1/16in, 1.5mm TRIPLE-CABLE SUSPENSION 5in CANOPY KIT WITH KEYHOLE END & CONNECTORS, CABLE BUSHING, 9" DIA., NO CORD INCL.
SCL-GTY10	ADJUSTABLE 1/16" 10 FT., 1.5mm SUSPENSION KIT WITH LOOP GRIPPER & TOGGLE ENDS(2)
SCL-GTY20	ADJUSTABLE 1/16" 20 FT., 1.5mm SUSPENSION KIT WITH LOOP GRIPPER & TOGGLE ENDS(2)
SCL-GTY210	HEAVY-DUTY ADJUSTABLE 5/64" 10 FT., 2mm SUSPENSION KIT WITH LOOP GRIPPER & TOGGLE ENDS(2)
SCL-GTY220	HEAVY-DUTY ADJUSTABLE 5/64" 20 FT., 2mm SUSPENSION KIT WITH LOOP GRIPPER & TOGGLE ENDS(2)
SCL-GSY10	ADJUSTABLE 10 FT. 1/16", 1.5mm SUSPENSION KIT WITH Y-CONNECTOR & LOOP GRIP & HOOKS(2)
SCL-GSY20	ADJUSTABLE 20 FT. 1/16", 1.5mm SUSPENSION KIT WITH Y-CONNECTOR & LOOP GRIP & HOOKS(2)
SCL-GSY110	ADJ. 10FT 1/16IN, 1.5mm SINGLE SUSPENSION CABLE WITH Y HOOK ENDS, LOOP GRIPPER ON TOP (ORDER 3 FOR 8FT.)(1)
SCL-GSY120	ADJ. 20FT 1/16IN, 1.5mm SINGLE SUSPENSION CABLE WITH Y HOOK ENDS, LOOP GRIPPER ON TOP (ORDER 3 FOR 8FT.)(1)
SCL-GS10	ADJ. 10FT 1/16IN, 1.5mm DOUBLE SUSPENSION CABLE WITH SINGLE KEYHOLE CONN., LOOP GRIPPER ON TOP(2)
SCL-GS20	ADJ. 20FT 1/16IN, 1.5mm DOUBLE SUSPENSION CABLE WITH SINGLE KEYHOLE CONN., LOOP GRIPPER ON TOP(2)
SCL-GS210	HEAVY-DUTY ADJUSTABLE 5/64" 10 FT., 2mm SUSPENSION KIT WITH LOOP GRIPPER & HOOK(1)
SCL-GS220	HEAVY-DUTY ADJUSTABLE 5/64" 20 FT., 2mm SUSPENSION KIT WITH LOOP GRIPPER & HOOK(1)
CMC-SRK-218-5C-WH	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, White
CMC-SRK-218-5C-BK	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, Black
CMC-SRK-218-5C-BR	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, Bronze
CMC-SRK-224-5C-WH	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, White
CMC-SRK-224-5C-BK	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, Black
CMC-SRK-224-5C-BR	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, Bronze
SCL-CSR-12FT	Adj. 12Ft Rectangular Canopy With Two Aircraft Cables For Linear Fixtures Up To 6Ft Long
SCL-CSR-12FT-BK	Adj. 12Ft Rectangular Canopy With Two Aircraft Cables For Linear Fixtures Up To 6Ft Long, Black
SCL-WRCL-14	1/4in GALVANIZED MALLEABLE IRON WIRE ROPE CLIP
SCL-TBJJ-14-4	1/4 X 4 INCH JAW TO JAW TURNBUCKLE GALVANIZED STEEL
SCL-WRCL-DUPLEX	5/32in 4mm DUPLEX 2-POST WIRE ROPE CLIP CABLE CLAMP
SCL-PEP-M8	PAD EYE PLATE STAPLE HOOK, SIZE M8, 2in X 1.5in STAINLESS
SCL-ASC-4MM-250FT	5/32in 4mm DIA. EXTRA DUTY GALVANIZED AIRCRAFT CABLE / WIRE ROPE 250FT ROLL
SCL-WRTH-14	1/4in GALVANIZED WIRE ROPE THIMBLE

SCL-6FT-SJTW18/5
SCL-6FT-SJTW18/6

SCL-6FT-SJTW18/5-BK
SCL-6FT-SJTW18/6-BK

SCL-12FT-SJTW18/5
SCL-12FT-SJTW18/6

SCL-12FT-SJTW18/5-BK
SCL-12FT-SJTW18/6-BK

SCL-100FT-SJTW18/5
SCL-100FT-SJTW18/6

SCL-100FT-SJTW18/5-BK
SCL-100FT-SJTW18/6-BK

SCL-6FT-AWM18/5-CLR
SCL-12FT-AWM18/5-CLR
SCL-100FT-AWM18/5-CLR
SCL-100FT-AWM18/6-CLR

SCL-ASC-50FT
SCL-ASC-100FT
SCL-ASC-500FT
SCL-ASC-1000FT

FWH-6FT-16/3
FWH-6FT-16/5
FWH-6FT-16/6

SCL-LCB-BK

SCL-LCB

SCL-CMDCK-2PK

SCL-CMSCK-2PK

GRIP & SUSPENSION ACCESSORIES

COMPATIBLE SERIES: SCX (SINGLE KEYHOLE)/ LSL, LSS ("Y" END & HOOK OR "Y" END & TOGGLE)/SCLP, SCPL-UD, SCLL, SCPP, SCX6 ("Y" END & KEYHOLE) & 2FT, 3FT, 4FT FIXTURES NEED 2 SUSPENSION & CABLES (2 ON ENDS)/ 6FT & 8FT FIXTURES NEED 3 SUSPENSION & CABLES (1 IN CENTER, 2 ON ENDS)

CATALOG NO.	DESCRIPTION
SCL-6FT-SJTW18/5	WHITE 6 FT. CORD, SJTW 18 AWG 5-CONDUCT (WH/BK/GN/PU/GY)
SCL-6FT-SJTW18/6	WHITE 6 FT. CORD, SJTW 18 AWG 6-CONDUCT (WH/BK/GN/PU/GY + RED FOR EMERGENCY))
SCL-6FT-SJTW18/5-BK	BLACK 12 FT. CORD, SJTW 18 AWG 5-CONDUCT (WH/BK/GN/PU/GY)
SCL-6FT-SJTW18/6-BK	BLACK 12 FT. CORD, SJTW 18 AWG 6-CONDUCT (WH/BK/GN/PU/GY + RED FOR EMERGENCY)
SCL-12FT-SJTW18/5	WHITE 12 FT. CORD, SJTW 18 AWG 5-CONDUCT (WH/BK/GN/PU/GY)
SCL-12FT-SJTW18/6	WHITE 12 FT. CORD, SJTW 18 AWG 6-CONDUCT (WH/BK/GN/PU/GY + RED FOR EMERGENCY)
SCL-12FT-SJTW18/5-BK	BLACK 12 FT. CORD, SJTW 18 AWG 5-CONDUCT (WH/BK/GN/PU/GY)
SCL-12FT-SJTW18/6-BK	BLACK 12 FT. CORD, SJTW 18 AWG 6-CONDUCT (WH/BK/GN/PU/GY + RED FOR EMERGENCY)
SCL-100FT-SJTW18/5	WHITE 100 FT. CORD, SJTW 18 AWG 5-CONDUCT (WH/BK/GN/PU/GY)
SCL-100FT-SJTW18/6	WHITE 100 FT. CORD, SJTW 18 AWG 6-CONDUCT (WH/BK/GN/PU/GY + RED FOR EMERGENCY)
SCL-100FT-SJTW18/5-BK	BLACK 100 FT. CORD, SJTW 18 AWG 5-CONDUCT (WH/BK/GN/PU/GY)
SCL-100FT-SJTW18/6-BK	BLACK 100 FT. CORD, SJTW 18 AWG 6-CONDUCT (WH/BK/GN/PU/GY + RED FOR EMERGENCY)
SCL-6FT-AWM18/5-CLR	6FT CORD, SJTW 18 AWM 5-CONDUCTOR, CLEAR
SCL-12FT-AWM18/5-CLR	12FT CORD, SJTW 18 AWM 5-CONDUCTOR, CLEAR
SCL-100FT-AWM18/5-CLR	100FT CORD, SJTW 18 AWM 5-CONDUCTOR, CLEAR
SCL-100FT-AWM18/6-CLR	100FT CORD, AWM 18 AWG 6-CONDUCTOR, CLEAR
SCL-ASC-50FT	1/16" 50 FT. STEEL AIRCRAFT SUSPENSION CABLE
SCL-ASC-100FT	1/16IN 100FT ROLL STEEL AIRCRAFT SUSPENSION CABLE
SCL-ASC-500FT	1/16" 500 FT. STEEL AIRCRAFT SUSPENSION CABLE
SCL-ASC-1000FT	1/16IN 1000FT ROLL STEEL AIRCRAFT SUSPENSION CABLE
FWH-6FT-16/3	6FT 16AWG 3-WIRE FLEX FIXTURE WHIP, STR. & 90D 1/2" CONN.
FWH-6FT-16/5	6FT 16AWG 5-WIRE FLEX FIXTURE WHIP, STR. & 90D 1/2" CONN.
FWH-6FT-16/6	6FT 16AWG 6-WIRE FLEX FIXTURE WHIP, STR. & 90D 1/2" CONN.
SCL-LCB-BK	LOCKING 3/8": DIA. CABLE BUSHING FOR CANOPY SETS, BLACK
SCL-LCB	LOCKING 3/8": DIA. CABLE BUSHING FOR CANOPY SETS
SCL-CMDCK-2PK	2-PACK REPLACEMENT DECOR CEILING ATTACHMENT FOR 1/16in CABLE WITH CRIMP SLEEVES
SCL-CMSCK-2PK	2-PACK REPLACEMENT DECOR SLOPE CEILING ATTACHMENT FOR 1/16in CABLE WITH CRIMP SLEEVES

FML-SK6

LFCF-SK10-BR

LFCF-SK10-BN

SCL-4CS10

SCL-ABCH

SCL-ABC

SCL-ABCH-BK

SCL-ABC-BK

SCL-ABCQ2K

SCL-ABCQ2K-BK

SCL-ABC2K

SCL-ABC2K-BK

SCL-CTB

SCL-ACSE

SCL-ALG

SCL-AH

SCL-TG1420

SCL-AYC

SCL-AKHC

SCL-CMC

SCL-TGS1420

SCL-TBC-WN

SCL-TBTC-WN

SCL-AUC

SCL-YCK

SCL-ABCQ

SCL-ABCQH

GRIP & SUSPENSION ACCESSORIES

COMPATIBLE SERIES: SCX (SINGLE KEYHOLE)/ LSL, LSS ("Y" END & HOOK OR "Y" END & TOGGLE)/SCLP, SCPL-UD, SCLL, SCPP, SCX6 ("Y" END & KEYHOLE) & 2FT, 3FT, 4FT FIXTURES NEED 2 SUSPENSION & CABLES (2 ON ENDS)/ 6FT & 8FT FIXTURES NEED 3 SUSPENSION & CABLES (1 IN CENTER, 2 ON ENDS)

CATALOG NO.	DESCRIPTION
FML-SK6	6FT ADJUSTABLE SUSPENSION KIT, 2-WIRE CLEAR CABLE INCL.
LFCF-SK10-BR	10FT 4-LINE CANOPY SUSPENSION KIT FOR DECORATIVE LIGHTS, 2-WIRE CLEAR CABLE INCL., BRONZE
LFCF-SK10-BN	10FT 4-LINE CANOPY SUSPENSION KIT FOR DECORATIVE LIGHTS, 2-WIRE CLEAR CABLE INCL., BRUSHED NICKEL
SCL-4CS10	ADJ. 10FT 1/16in QUAD CABLE SUSP. CANOPY KIT, KEYHOLE CONNECTORS (NO CORD INCL.)
SCL-ABCQ2K	2in SQUARE NON-POWERFEED SIDE MINI CANOPY CONVERSION KIT
SCL-ABCQ2K-BK	2in SQUARE NON-POWERFEED SIDE MINI CANOPY CONVERSION KIT - BLACK
SCL-ABC2K	2IN NON-POWERFEED SIDE MINI CANOPY CONVERSION KIT
SCL-ABC2K-BK	2IN NON-POWERFEED SIDE MINI CANOPY CONVERSION KIT - BLACK
SCL-ABCH	5IN AUXILIARY BLANK CANOPY WITH CORD GRIP
SCL-ABC	5IN AUXILIARY BLANK CANOPY FOR SUSPENSION CABLES
SCL-ABCH-BK	5IN AUXILIARY BLANK CANOPY WITH CORD GRIP - BLACK
SCL-ABC-BK	5IN AUXILIARY BLANK CANOPY FOR SUSPENSION CABLES - BLACK
SCL-ABCQ	AUXILIARY SQUARE BLANK CANOPY FOR SUSPENSION CABLES
SCL-ABCQH	AUXILIARY SQUARE BLANK CANOPY FOR SUSPENSION CABLES WITH CABLE HOLE AND CORD GRIP
SCL-ACSE	AIRCRAFT CABLE STOPPER END
SCL-AH	HEAVY-DUTY AUXILIARY HOOK FOR UP TO 1/16" AIRCRAFT CABLES
SCL-TG1420	AUXILIARY TOP GRIPPER SIDE EXIT WITH 1/4-20 THREAD FOR 1/16IN AIRCRAFT CABLE
SCL-AYC	AUXILIARY Y CONNECTOR FOR AIRCRAFT SUSPENSION CABLE, 1/16"
SCL-AKHC	AUXILIARY KEYHOLE CONNECTOR FOR AIRCRAFT SUSPENSION CABLE, 1/16"
SCL-CTB	CANOPY SET TOP BRACKET FOR MOUNTING ON JUNCTION BOX OR CEILING- 1/4-20
SCL-TBC-WN	T-BAR CLIP WITH SUSPENSION HOLE ON TOP, WING NUT AND WASHER INCL.
SCL-TBTC-WN	T-BAR TRACK CLIP WITH WASHER AND WING NUT
SCL-AUC	AUXILIARY UNIVERSAL SURFACE CONNECTOR FOR 1/6 IN AIRCRAFT SUSPENSION CABLE
SCL-CMC	AUXILIARY CEILING-MOUNT CONNECTOR FOR 1/16in AIRCRAFT SUSPENSION CABLES
SCL-YCK	ADJ. 1/16in Y CONVERSION SUSPENSION CABLE WITH TOGGLE ENDS
SCL-TGS1420	ADJ. SWIVEL TOP GRIP REPLACEMENT CONNECTOR TO ADAPT SCL-CS SERIES TO SLOPE CEILINGS
SCL-ALG	AUXILIARY LOOP GRIP FOR AIRCRAFT SUSPENSION CABLE, 1/16"

ARCHITECTURAL INDOOR

SFL SERIES

ST360 SERIES

SCSSL SERIES

CWS SERIES

SRC SERIES

SRPL SERIES

SCXCR SERIES

SCR SERIES

SCRR SERIES

SCRH SERIES

SCRH-RGBW SERIES

DPL SERIES

DSP SERIES

SCX-2X2 SERIES

SCXC SERIES

SCXA SERIES

SCXA2 SERIES

SCX-RGBW SERIES

SCX SERIES

SCX-REG SERIES

SCX-LUV SERIES

SCX-LUV-WH SERIES

SCX-DIAM-WH SERIES

SCX-DIAM-GD SERIES

LRP-HL SERIES

SCX-DP SERIES

SCX-IDL SERIES

SCX-L SERIES

SCX-Y SERIES

SCX-IND SERIES

WA SERIES

SCX-DLP SERIES

SCX-BK-LUV SERIES

SCX-BK-IND SERIES

SCX4 SERIES

SCX4-LUV SERIES

WAS SERIES

SCX2 SERIES

SCXR SERIES

SCX4-IP66 SERIES

SCSSL SERIES

SCP SERIES

SCLP SERIES

HEX SERIES


HEX-RGB SERIES

CMC1 SERIES

CMC2 SERIES

CMC2-ADJ SERIES

Search for the series name @WESTGATEMFG.COM

CMC4 SERIES

CMC3 SERIES

CMC4-ADJ SERIES

CMC5-MILAN SERIES

CMC2-2TONE SERIES

CMC3-2TONE SERIES

CMC4-2TONE SERIES

CMC6 SERIES

CMCS8 SERIES

CMC8S SERIES

CMC9 SERIES

CMC12 SERIES

CMC4-RGBW SERIES

CMCSR SERIES

CMCW SERIES

TRPK SERIES

TRE SERIES

TRD SERIES

TRD SERIES

TRS SERIES

TRP SERIES

TRM SERIES

TRL SERIES

TRL SERIES


TRK SERIES

TR1 SERIES

WCPL SERIES


WPLC SERIES

POB SERIES

FDLH SERIES


LSC SERIES

LMIR SERIES

LVL SERIES

LVF SERIES

LVB SERIES

LVC SERIES


LVD SERIES

LVO SERIES

LVE SERIES

LVA SERIES

LVG SERIES

LVJ SERIES

LVP SERIES

VLA SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

PENDANTS

SFL-4FT-60W-MCTP-BK

SFL-4FT-60W-MCTP

SFL-4FT-60W-MCTP-GD

LED SUSPENDED FRAME FIXTURE, 120~277V POWER & CCT-ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
SFL-4FT-60W-MCTP	40W/50W/60W	7000LM	30K/35K/40K - White	4
SFL-4FT-60W-MCTP-BK	40W/50W/60W	7000LM	30K/35K/40K - Black	4
SFL-4FT-60W-MCTP-GD	40W/50W/60W	7000LM	30K/35K/40K - Gold	4



Can be Installed Vertically

ST360-4FT-MCTP-DD

ST360-8FT-MCTP-DD

SUSPENDED 360° COMMERCIAL TUBE LIGHT WATTAGE & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
ST360-2FT-MCTP-DD	17W/19W/21W/23W	80LM/W	30K/35K/40K	1
ST360-3FT-MCTP-DD	25W/27W/29W/31W	80LM/W	30K/35K/40K	1
ST360-4FT-MCTP-DD	33W/35W/37W/39W	80LM/W	30K/35K/40K	1
ST360-6FT-MCTP-DD	50W/54W/58W/62W	80LM/W	30K/35K/40K	1
ST360-8FT-MCTP-DD	66W/70W/74W/78W	80LM/W	30K/35K/40K	1


SCSL-UD-BK


SCSL-UD-AP-BK


SCSL-UD


SCSL-UD-AP

SCSL
PC Lens shown with Round Endcap


SCSL-AP
Optic Lens Version


SCSL-CEC

SCSL-WM-BK


SCSL-WM

ARCHITECTURAL 0.7" (18MM) SLIM UP&DOWN /W SEPARATE CONTROLS LINEAR LIGHT

POWER & CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
ARCHITECTURAL 0.7" SLIM UP&DOWN /W SEPARATE CONTROLS LINEAR LIGHT, PC LENS - POWER & CCT SELECTABLE				
SCSL-UD-4FT-MCTP	20W/23W/26W/29W	90LM/W	27K/30K/35K/40K/50K - 4FT White	6
SCSL-UD-4FT-MCTP-BK	20W/23W/26W/29W	90LM/W	27K/30K/35K/40K/50K - 4FT Black	6
SCSL-UD-6FT-MCTP	30W/34W/37W/40W	90LM/W	27K/30K/35K/40K/50K - 6FT White	4
SCSL-UD-6FT-MCTP-BK	30W/34W/37W/40W	90LM/W	27K/30K/35K/40K/50K - 6FT Black	4
SCSL-UD-8FT-MCTP	40W/46W/52W/60W	90LM/W	27K/30K/35K/40K/50K - 8FT White	4
SCSL-UD-8FT-MCTP-BK	40W/46W/52W/60W	90LM/W	27K/30K/35K/40K/50K - 8FT Black	4
ARCHITECTURAL 0.7" SLIM UP&DOWN /W SEPARATE CONTROLS LINEAR LIGHT, 36° APERTURE OPTICS - POWER & CCT SELECTABLE				
SCSL-UD-AP-4FT-MCTP	20W/23W/26W/29W	90LM/W	27K/30K/35K/40K/50K - 4FT White	6
SCSL-UD-AP-4FT-MCTP-BK	20W/23W/26W/29W	90LM/W	27K/30K/35K/40K/50K - 4FT Black	6
SCSL-UD-AP-6FT-MCTP	30W/34W/37W/40W	90LM/W	27K/30K/35K/40K/50K - 6FT White	4
SCSL-UD-AP-6FT-MCTP-BK	30W/34W/37W/40W	90LM/W	27K/30K/35K/40K/50K - 6FT Black	4
SCSL-UD-AP-8FT-MCTP	40W/46W/52W/60W	90LM/W	27K/30K/35K/40K/50K - 8FT White	4
SCSL-UD-AP-8FT-MCTP-BK	40W/46W/52W/60W	90LM/W	27K/30K/35K/40K/50K - 8FT Black	4
ARCHITECTURAL 0.7" SLIM UP&DOWN /W SEPARATE CONTROLS WALL SCONCE, 36° APERTURE OPTICS - CCT SELECTABLE				
SCSL-WM-UD-AP-12-MCT	7W	630LM	27K/30K/35K/40K/50K - 7W	6
SCSL-WM-UD-AP-12-MCT-BK	7W	630LM	27K/30K/35K/40K/50K - 7W	6
SCSL-WM-UD-AP-18-MCT	15W	1350LM	27K/30K/35K/40K/50K - 15W	6
SCSL-WM-UD-AP-18-MCT-BK	15W	1350LM	27K/30K/35K/40K/50K - 15W	6
SCSL-WM-UD-AP-24-MCT	20W	1800LM	27K/30K/35K/40K/50K - 20W	6
SCSL-WM-UD-AP-24-MCT-BK	20W	1800LM	27K/30K/35K/40K/50K - 20W	6
SCSL-REC	SCSL Rounded End Cap, White			
SCSL-REC-BK	SCSL Rounded End Cap, Black			
SCSL-CEC	SCSL Coupling End Cap, White			
SCSL-CEC-BK	SCSL Coupling End Cap, Black			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
ALL	OPT-EM-SCSL-WH	IN CANOPY	N/A	N/A
	OPT-EM-SCSL-BK	IN CANOPY	480V OPTION	DESCRIPTION
	POWDER COATING		N/A	N/A
	N/A			



CWS-48-MCTP-DWA
Comes with Suspension Cables

CWS-12-MCTP CWS-18-MCTP CWS-48-MCTP
Show with DWA Accessories

COMMERCIAL AND WAITING-ROOM INDOOR WALL SCONCE AND SUSPENDED LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
CWS-12-MCTP	10W/15W/20W	85LM/W	30K/35K/40K	1
CWS-18-MCTP	10W/15W/20W	85LM/W	30K/35K/40K	1
CWS-48-MCTP	20W/30W/40W	85LM/W	30K/35K/40K	1

SRC-D24UD-MCTP-BK

SRC-D24UD-MCTP



SRC-D48UD-MCTP-BK

SRC-D48UD-MCTP

HIGH-OUTPUT ROUND LINEAR CHANDELIER, UP/DOWN LIGHT WITH SEPARATE CONTROLS, 1-7/8"W CHANNEL POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
SRC-D24UD-MCTP-BK	0W/40W/80W	65LM/W	30K/35K/40K - Black	1
SRC-D24UD-MCTP	0W/40W/80W	65LM/W	30K/35K/40K - White	1
SRC-D36UD-MCTP-BK	0W/80W/120W	65LM/W	30K/35K/40K - Black	1
SRC-D36UD-MCTP	0W/80W/120W	65LM/W	30K/35K/40K - White	1
SRC-D48UD-MCTP-BK	0W/120W/160W	65LM/W	30K/35K/40K - Black	1
SRC-D48UD-MCTP	0W/120W/160W	65LM/W	30K/35K/40K - White	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
ALL	OPT-EM-SRC	INTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

SRPL-40W-MCT-D

LED SUSPENDED UP/DOWN CLEAR ROUND PANEL LIGHT, 22" DIAMETER, 6FT HEIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
SRPL-40W-35K-D*	40W	2100LM/2100LM	3500K	1
SRPL-40W-50K-D*	40W	2100LM/2100LM	5000K	1
SRPL-40W-MCT-D	40W	2100LM/2100LM	3500K/4000K/5000K	1

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL MODELS	OPT-EM-SRPL	INTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
			OPT-SEN-NLS-SRPL	WG NETWORK SENSOR
			OPT-SEN-KEILTON-SRPL	KEILTON NETWORK SENSOR
			WEC-3RC	REMOTE CONTROL

MCTP



SCXCF-D24UD-MCTP4



SCXCF-D24UD-MCTP4-BK

FULL CIRCLE 10FT CHANDELIER, UP & DOWN RATIO ADJUSTABLE WITH CANOPY & CABLE

CATALOG NO.	DESCRIPTION		
SCXCF-D24UD-MCTP4	20W/30W/40W	100LM/W	30K/35K/40K/50K - 24" White
SCXCF-D24UD-MCTP4-BK	20W/30W/40W	100LM/W	30K/35K/40K/50K - 24" Black
SCXCF-D36UD-MCTP4	60W/70W/80W	100LM/W	30K/35K/40K/50K - 36" White
SCXCF-D36UD-MCTP4-BK	60W/70W/80W	100LM/W	30K/35K/40K/50K - 36" Black
SCXCF-D48UD-MCTP4	80W/90W/100W	100LM/W	30K/35K/40K/50K - 48" White
SCXCF-D48UD-MCTP4-BK	80W/90W/100W	100LM/W	30K/35K/40K/50K - 48" Black

SCR-24D-MCTP-SMB

SCR-24D-MCTP-D

LED ARCHITECTURAL ROUND SUSPENDED DOWN LIGHT, (WITH UP LIGHT OPTION, SEE FACTORY-INSTALLED OPTIONS BELOW)

CATALOG NO.	DESCRIPTION			PCK QTY
SCR-16D-MCTP5-D	10W/15W/20W/25W/30W	100LM/W	27K/30K/35K/40K/50K	1
SCR-18D-MCTP5-D	15W/20W/25W/30W/35W	100LM/W	27K/30K/35K/40K/50K	1
SCR-24D-MCTP5-D	30W/35W/40W/45W/50W	100LM/W	27K/30K/35K/40K/50K	1
SCR-36D-MCTP5-D	40W/60W/80W/100W/120W	100LM/W	27K/30K/35K/40K/50K	1
SCR-48D-MCTP5-D	120W/140W/160W/180W/200W	100LM/W	27K/30K/35K/40K/50K	1
SCR-24D-40K-D	50W	5197LM	4000K - 24" Dia	1
SCR-24D-MCTP-D*	30W/40W/50W	60LM/W	3000K/3500K/4000K - 24" Dia	1
SCR-32D-MCTP-D	40W/60W/80W	110LM/W	30K/35K/40K - 32" Dia	1
SCR-48D-MCTP-D	60W/80W/100W	110LM/W	30K/35K/40K - 48" Dia	1
SCR-24D-MCTP-SMB	Surface Mounting Bracket For SCR-24D-MCTP-D			
SCR-32D-MCTP-SMB	Surface Mounting Bracket For SCR-32D-MCTP-D			
SCR-48D-MCTP-SMB	Surface Mounting Bracket For SCR-48D-MCTP-D			
SCR-1618D-ULK	Uplight Kit For 16in & 18in SCR Fixtures			
SCR-24D-ULK	Uplight Kit For 24in SCR Fixtures			
SCR-3648D-ULK	Uplight Kit For 36in & 48in SCR Fixtures			

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	UPLIGHT OPTION	DESCRIPTION
ALL MODELS	OPT-SCR-ULK	120V Installation Only
	POWDER COATING	
	N/A	

EM OPTION	DESCRIPTION
OPT-EM-SCR	EXTERNAL
SENSOR	DESCRIPTION
OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-SCR	WG NETWORK SENSOR
OPT-SEN-KEILTON-SCR	KEILTON NETWORK SENSOR
WEC-3RC	REMOTE CONTROL

SCRR-24D-MCTP5-D

SCRR-24D-ULK

SCRR-3648D-RODKIT

REGRESSED ARCHITECTURAL PANEL LIGHT W/ 10FT SUS. CABLE **120-277V** SELECTABLE CCT/POWER

CATALOG NO.	DESCRIPTION			PCK QTY
SCRR-16D-MCTP5-D	10W/15W/20W/25W/30W	130LM/W	27K/30K/35K/40K/50K	1
SCRR-18D-MCTP5-D	15W/20W/25W/30W/35W	130LM/W	27K/30K/35K/40K/50K	1
SCRR-24D-MCTP5-D	30W/35W/40W/45W/50W	130LM/W	27K/30K/35K/40K/50K	1
SCRR-36D-MCTP5-D	40W/60W/80W/100W/120W	130LM/W	27K/30K/35K/40K/50K	1
SCRR-48D-MCTP5-D	120W/140W/160W/180W	130LM/W	27K/30K/35K/40K/50K	1
SCRR-1618D-ULK	Uplight Kit For 16in & 18in SCRR Fixtures			
SCRR-24D-ULK	Uplight Kit For 24in SCRR Fixtures			
SCRR-3648D-ULK	Uplight Kit For 36in & 48in SCRR Fixtures			
SCRR-1824D-RODKIT	Rod Kit For 18in & 24in SCRR Fixtures			
SCRR-3648D-RODKIT	Rod Kit For 36in & 48in SCRR Fixtures			

SCRH-UD-BK

SCRH-UD-WH

SCRH-WS-WH

SCRH-WS-WH


SCRH-UD-14-BK

SCRH-UD-14-WH


SCRH-UD-16-BK

SCRH-UD-16-WH

HOLLOW CIRCLE PENDANT OR WALL SCONCE WITH UPLIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
SCRH-UD-14-MCT5-DD-WH	20W	1000LM	27K/30K/35K/40K/50K - White	
SCRH-UD-14-MCT5-DD-BK	20W	1000LM	27K/30K/35K/40K/50K - Black	
SCRH-UD-16-MCT5-DD-WH	25W	1200LM	27K/30K/35K/40K/50K - White	
SCRH-UD-16-MCT5-DD-BK	25W	1200LM	27K/30K/35K/40K/50K - Black	

18" HOLLOW CIRCLE PENDANT WITH UPLIGHT

SCRH-UD-18-MCT5-DD-WH	30W	50LM/W	27K/30K/35K/40K/50K - White	1
SCRH-UD-18-MCT5-DD-BK	30W	50LM/W	27K/30K/35K/40K/50K - Black	1
SCRH-UD-24-MCT5-DD-WH	40W	50LM/W	27K/30K/35K/40K/50K - White	1
SCRH-UD-24-MCT5-DD-BK	40W	50LM/W	27K/30K/35K/40K/50K - Black	1
SCRH-UD-36-MCT5-DD-WH	80W	50LM/W	27K/30K/35K/40K/50K - White	1
SCRH-UD-36-MCT5-DD-BK	80W	50LM/W	27K/30K/35K/40K/50K - Black	1

8" HOLLOW CIRCLE WALL SCONCE WITH UPLIGHT - 120V

SCRH-WS-WH	10W	500LM	27K/30K/35K/40K/50K - White	10
SCRH-WS-BK	10W	500LM	27K/30K/35K/40K/50K - Black	10



SCXCF-RGBWW-BT



SCXCF-RGBWW-BT

FULL CIRCLE 10FT CHANDELIER UP & DOWN RATIO ADJUSTABLE WITH CANOPY & CABLE

CATALOG NO.	DESCRIPTION			PCK QTY
SCXCF-D24UD-RGBWW-BT	40W	4000LM	RGBW - Bronze	1
SCXCF-D24UD-RGBWW-BT-BK	40W	4000LM	RGBW - Black	1
SCXCF-D36UD-RGBWW-BT	80W	8000LM	RGBW - Bronze	1
SCXCF-D36UD-RGBWW-BT-BK	80W	8000LM	RGBW - Black	1
SCXCF-D48UD-RGBWW-BT	100W	10000LM	RGBW - Bronze	1
SCXCF-D48UD-RGBWW-BT-BK	100W	10000LM	RGBW - Black	1

CMC-OWCC-BK

CMC-OWCC-WH

5" OLD-WORK RECESSED CEILING CANOPY WITH JUNCTION BOX

CATALOG NO.	DESCRIPTION
CMC-OWCC-WH	5In Old-Work Recessed Ceiling Canopy With Junction Box For CMC Cylinders, White (Except CMC9)
CMC-OWCC-BK	5In Old-Work Recessed Ceiling Canopy With Junction Box For CMC Cylinders, Black (Except CMC9)

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
1", 2" 3"	**N/A**	N/A
1", 2" 3"	**N/A**	N/A
4" & 6"	**OPT-EM-CMC46**	INTERNAL
9" white	**OPT-EM-CMC9-WH**	Extension Cylinder - White
9" black	**OPT-EM-CMC9-BK**	Extension Cylinder - Black

POWDER COATING
N/A

TRACK PENDANT CONVERSION	DESCRIPTION
OPT-CMC-TRACK-H-WH	3.3FT TRACK PENDANT CONVERSION, H-TYPE
OPT-CMC-TRACK-H-BK	

SENSOR	DESCRIPTION
N/A	N/A

SCL-CSR-12FT

SCL-CSR-12FT-BK

GRIP & SUSPENSION ACCESSORIES

CATALOG NO.	DESCRIPTION
SCL-CSR-12FT	Adj. 12Ft Rectangular Canopy With Two Aircraft Cables For Linear Fixtures Up To 6Ft Long
SCL-CSR-12FT-BK	Adj. 12Ft Rectangular Canopy With Two Aircraft Cables For Linear Fixtures Up To 6Ft Long, Black

DECORATIVE BULBS & SOCKETS

DPL-01-18K
Free Form 7.5" Diameter

DPL-02-18K
Tear Drop 7" Diameter

DPL-04-18K
Round Form 3.2" Diameter

DPL-05-18K
Round Form 5.2" Diameter

DPL-06-18K
Round Dimple 8" Diameter

DPL-07M-18K
Round Metal Mesh 8" Diameter

DPL-03-18K
Long Form 2.4X10"

DPL-08-20K

DECORATIVE PENDANT LAMP, E26 BASE **120V**

CATALOG NO.	DESCRIPTION		
DPL-01-18K	4W	160LM	1800K - Free Form 7.5in Dia
DPL-02-18K	4W	160LM	1800K - Tear Drop 7in Dia
DPL-03-18K	4W	160LM	1800K - Long Form 2.4X10in
DPL-04-18K	4W	160LM	1800K - Round Form 3.2in Dia
DPL-05-18K	4W	160LM	1800K - Round Form 5.2in Dia
DPL-06-18K	4W	160LM	1800K - Round Dimple 8in Dia
DPL-07M-18K	4W	160LM	1800K - Round Metal Mesh 8in Dia
DPL-08-20K	4W	220LM	2000K

DSP-039-6FT-BK

DSP-039-6FT-RG

DSP-066-6FT-AB

DSP-066-6FT-BK

DSP-066-6FT-BR

DSP-066-6FT-GB

DSP-722-6FT-GB

DSP-722-6FT-RG

DSP-761-6FT-AB

DSP-761-6FT-AC

DSP-974-6FT-AB

DECORATIVE SOCKET PENDANT 6FT CORD - E26 MEDIUM BASE

CATALOG NO.	DESCRIPTION
DSP-066-6FT-BK	Decorative Socket Pendant 066 6Ft Blk Cord - Black
DSP-066-6FT-AB	Decorative Socket Pendant 066 6Ft Blk Cord - Antique Brass
DSP-066-6FT-BR	Decorative Socket Pendant 066 6Ft Blk Cord - Brass
DSP-066-6FT-GB	Decorative Socket Pendant 066 6Ft Blk Cord - Gun Black
DSP-761-6FT-AC	Decorative Socket Pendant 761 6Ft Blk Cord - Antique Copper
DSP-761-6FT-AB	Decorative Socket Pendant 761 6Ft Blk Cord - Antique Brass
DSP-722-6FT-RG	Decorative Socket Pendant 761 6Ft Blk Cord - Rose Gold
DSP-722-6FT-GB	Decorative Socket Pendant 761 6Ft Blk Cord - Gun Black
DSP-974-6FT-AB	Decorative Socket Pendant 974 6Ft Blk Cord - Antique Brass
DSP-039-6FT-RG	Decorative Socket Pendant 039 6Ft Blk Cord - Rose Gold
DSP-039-6FT-BK	Decorative Socket Pendant 039 6Ft Blk Cord - Black
DSP-CORD-FAB-BK	Replacement Fabric Cord For DSP Decorative Sockets - Black



LINEAR & ACCENT LIGHTS



SHOWN WITH SUSPENSION KIT



SHOWN WITH RECESSED MOUNTING FLANGES

SCL-4CS10

2.75” SCX 2X2 & 2X4 LINEAR LIGHT

CATALOG NO.	DESCRIPTION		
SCX-2X2-40-80W-MCTP	40W/60W/80W	110LM/W	30K/35K/40K/50K
SCX-2X4-60-120W-MCTP	60W/90W/120W	110LM/W	30K/35K/40K/50K
SCL-4CS10	ADJ. 10FT 1/16in QUAD CABLE SUSP. CANOPY KIT, KEYHOLE CONNECTORS (NO CORD INCL.)		

SCXC-Q

1 QUARTER CIRCLE SHOWN WITH SUSPENSION KITS

CREATED WITH 4 QUARTER CIRCLES

CREATED WITH 4 QUARTER CIRCLES SHOWN WITH SUSPENSION KIT

SCL-3CS10

SCX QUARTER OF CIRCLE 4CCT

CATALOG NO.	DESCRIPTION			PCK QTY
SCXC-Q24-10W-MCT4	10W	1100LM	30K/35K/40K/50K - 24”	4
SCXC-Q36-20W-MCT4	20W	2200LM	30K/35K/40K/50K - 36”	4
SCXC-Q48-25W-MCT4	25W	2750LM	30K/35K/40K/50K - 48”	2
SCL-3CS10	ADJ. 10FT 1/16in TRIPLE-CABLE SUSPENSION CANOPY KIT WITH KEYHOLE END CONNECTORS (NO CORD INCL.)			



SCXA-4FT-40W-MCTP-BB
UGR25 50D FULL OPTIC



SCXA-4FT-40W-MCTP-WW
UGR25 50D FULL OPTIC

SCXA-4FT-40W-MCTP-CD-BB
UGR25 50D COMBINED DISTRIBUTION OPTIC + PC LENS

SCXA-4FT-40W-MCTP-CD-WW
UGR25 50D COMBINED DISTRIBUTION OPTIC + PC LENS

ARCHITECTURAL 2-3/4" OPTIC & COMBINED-DISTRIBUTION LINEAR WITH MULTIPLE APERTURE OPTIONS

CATALOG NO.	DESCRIPTION			PCK QTY
SCXA-2FT-20W-MCTP-CD-BB	10W/15W/20W	100LM/W	30K/35K/40K - 7.5" Optic Ends	1
SCXA-2FT-20W-MCTP-CD-WW	10W/15W/20W	100LM/W	30K/35K/40K - 7.5" Optic Ends	1
SCXA-4FT-40W-MCTP-CD-BB	20W/30W/40W	100LM/W	30K/35K/40K - 7.5" Optic Ends	6
SCXA-4FT-40W-MCTP-CD-WW	20W/30W/40W	100LM/W	30K/35K/40K - 7.5" Optic Ends	6
SCXA-6FT-60W-MCTP-CD-BB	40W/50W/60W	100LM/W	30K/35K/40K - 15" Optic Ends	4
SCXA-6FT-60W-MCTP-CD-WW	40W/50W/60W	100LM/W	30K/35K/40K - 15" Optic Ends	4
SCXA-8FT-80W-MCTP-CD-BB	60W/70W/80W	100LM/W	30K/35K/40K - 23" Optic Ends	4
SCXA-8FT-80W-MCTP-CD-WW	60W/70W/80W	100LM/W	30K/35K/40K - 23" Optic Ends	4
SCXA-2FT-20W-MCTP-BB	10W/15W/20W	100LM/W	30K/35K/40K	1
SCXA-2FT-20W-MCTP-WW	10W/15W/20W	100LM/W	30K/35K/40K	1
SCXA-4FT-40W-MCTP-BB	20W/30W/40W	100LM/W	30K/35K/40K	6
SCXA-4FT-40W-MCTP-WW	20W/30W/40W	100LM/W	30K/35K/40K	6
SCXA-6FT-60W-MCTP-BB	40W/50W/60W	100LM/W	30K/35K/40K	4
SCXA-6FT-60W-MCTP-WW	40W/50W/60W	100LM/W	30K/35K/40K	4
SCXA-8FT-80W-MCTP-BB	60W/70W/80W	100LM/W	30K/35K/40K	4
SCXA-8FT-80W-MCTP-WW	60W/70W/80W	100LM/W	30K/35K/40K	4
SCXA-BCP-2FT-BK	2Ft (Also 4Ft) Blank Cover-Plate Accessory To Replace Center Pc Lens, Black			
SCXA-BCP-2FT-WH	2Ft (Also 4Ft) Blank Cover-Plate Accessory To Replace Center Pc Lens, White			
SCXA-BCP-4FT-BK	4Ft (Also 6Ft 8Ft) Blank Cover-Plate Accessory To Replace Center Pc Lens, Black			
SCXA-BCP-4FT-WH	4Ft (Also 6Ft 8Ft) Blank Cover-Plate Accessory To Replace Center Pc Lens, White			
SCXA-OLS-40D-BK	Replacement Optic Lens 40D 6In Long, Black			
SCXA-OLS-40D-WH	Replacement Optic Lens 40D 6In Long, White			
SCX-TRACK-H-BK	Scx Track Light Socket End Extension H-Type, Black			
SCX-TRACK-H-WH	Scx Track Light Socket End Extension H-Type, White			
SCXA-OLS-60D-BK	Replacement Standard Optic Lens 60D 6In Long, Black			
SCXA-OLS-60D-WH	Replacement Standard Optic Lens 60D 6In Long, White			



SCXA2-4FT-40W-MCTP-BB
UGR25 50D FULL OPTIC



SCXA2-4FT-40W-MCTP-WW
UGR25 50D FULL OPTIC



SCX2-TRACK-H

SCXA2-4FT-40W-MCTP-CD-BB
UGR25 50D COMBINED DISTRIBUTION OPTIC + PC LENS

SCXA2-4FT-40W-MCTP-CD-WW
UGR25 50D COMBINED DISTRIBUTION OPTIC + PC LENS

ARCHITECTURAL 2" OPTIC & COMBINED-DISTRIBUTION LINEAR WITH MULTIPLE APERTURE OPTIONS

CATALOG NO.	DESCRIPTION			PCK QTY
SCXA2-2FT-20W-MCTP-CD-BB	10W/15W/20W	100LM/W	30K/35K/40K - 7.5" Optic Ends	1
SCXA2-2FT-20W-MCTP-CD-WW	10W/15W/20W	100LM/W	30K/35K/40K - 7.5" Optic Ends	1
SCXA2-4FT-40W-MCTP-CD-BB	20W/30W/40W	100LM/W	30K/35K/40K - 7.5" Optic Ends	6
SCXA2-4FT-40W-MCTP-CD-WW	20W/30W/40W	100LM/W	30K/35K/40K - 7.5" Optic Ends	6
SCXA2-6FT-60W-MCTP-CD-BB	40W/50W/60W	100LM/W	30K/35K/40K - 15" Optic Ends	4
SCXA2-6FT-60W-MCTP-CD-WW	40W/50W/60W	100LM/W	30K/35K/40K - 15" Optic Ends	4
SCXA2-8FT-80W-MCTP-CD-BB	60W/70W/80W	100LM/W	30K/35K/40K - 23" Optic Ends	4
SCXA2-8FT-80W-MCTP-CD-WW	60W/70W/80W	100LM/W	30K/35K/40K - 23" Optic Ends	4
SCXA2-2FT-20W-MCTP-BB	10W/15W/20W	100LM/W	30K/35K/40K	1
SCXA2-2FT-20W-MCTP-WW	10W/15W/20W	100LM/W	30K/35K/40K	1
SCXA2-4FT-40W-MCTP-BB	20W/30W/40W	100LM/W	30K/35K/40K	6
SCXA2-4FT-40W-MCTP-WW	20W/30W/40W	100LM/W	30K/35K/40K	6
SCXA2-6FT-60W-MCTP-BB	40W/50W/60W	100LM/W	30K/35K/40K	4
SCXA2-6FT-60W-MCTP-WW	40W/50W/60W	100LM/W	30K/35K/40K	4
SCXA2-8FT-80W-MCTP-BB	60W/70W/80W	100LM/W	30K/35K/40K	4
SCXA2-8FT-80W-MCTP-WW	60W/70W/80W	100LM/W	30K/35K/40K	4
SCX2-TRACK-H-BK	Track Light Socket End Extension H-Type Black			
SCX2-TRACK-H-WH	Track Light Socket End Extension H-Type White			
SCXA2-BCP-4FT-BK	Blank Cover For 4Ft to Replace PC Lens, Black			
SCXA2-BCP-6FT-BK	Blank Cover For 6Ft to Replace PC Lens, Black			
SCXA2-BCP-8FT-BK	Blank Cover For 8Ft to Replace PC Lens, Black			
SCXA2-BCP-4FT-WH	Blank Cover For 4Ft to Replace PC Lens, White			
SCXA2-BCP-6FT-WH	Blank Cover For 6Ft to Replace PC Lens, White			
SCXA2-BCP-8FT-WH	Blank Cover For 8Ft to Replace PC Lens, White			
SCXA2-OLS-50D-BK	Replacement Standard Optic Lens 50D 8in Long, Black			
SCXA2-OLS-50D-WH	Replacement Standard Optic Lens 50D 8in Long, White			

UGR OPTIC LENS

CATALOG NO.	DESCRIPTION
OPT-SCXA2-4FT-WH-50D	UGR Less Than 10, 50D Optic, White
OPT-SCXA2-4FT-WH-70D	UGR Less Than 10, 70D Optic, White
OPT-SCXA2-4FT-BK-50D	UGR Less Than 10, 50D Optic, Black
OPT-SCXA2-4FT-BK-70D	UGR Less Than 10, 70D Optic, Black
OPT-SCXA2-6FT-WH-50D	UGR Less Than 10, 50D Optic, White
OPT-SCXA2-6FT-WH-70D	UGR Less Than 10, 70D Optic, White
OPT-SCXA2-6FT-BK-50D	UGR Less Than 10, 50D Optic, Black
OPT-SCXA2-6FT-BK-70D	UGR Less Than 10, 70D Optic, Black
OPT-SCXA2-8FT-WH-50D	UGR Less Than 10, 50D Optic, White
OPT-SCXA2-8FT-WH-70D	UGR Less Than 10, 70D Optic, White
OPT-SCXA2-8FT-BK-50D	UGR Less Than 10, 50D Optic, Black
OPT-SCXA2-8FT-BK-70D	UGR Less Than 10, 70D Optic, Black

SCX-6FT-RGBWW-BT

TC-RGBW-RC


SCX-L White


SCX-T White

SCX-X White


SCX-IC White


SCX-C120 White

SCX-Y White


SCX-C60 White

SCX-OC White


SCX-6" White


SCX-9" White

WG SMART APP & REMOTE CONTROLLED COMPATIBLE SCX LINEAR LIGHT RGB OR 4CCT UPLIGHT OPTION

CATALOG NO.	DESCRIPTION			PCK QTY
SCX-1FT-RGBWW-BT	10W	110LM/W	RGB	6
SCX-2FT-RGBWW-BT	20W	110LM/W	RGB	6
SCX-3FT-RGBWW-BT	30W	110LM/W	RGB	6
SCX-4FT-RGBWW-BT	40W	110LM/W	RGB	6
SCX-6FT-RGBWW-BT	60W	110LM/W	RGB	4
SCX-8FT-RGBWW-BT	80W	110LM/W	RGB	4
SCX-L-RGBWW	SCX 2.75 in Linear L Section RGBW 2700K-5000K + RGB			
SCX-T-RGBWW	SCX 2.75 in Linear T Section RGBW 2700K-5000K + RGB			
SCX-X-RGBWW	SCX 2.75 in Linear X Section RGBW 2700K-5000K + RGB			
SCX-IC-RGBWW	SCX 2.75 in Linear Inside Corner RGBW 2700K-5000K + RGB			
SCX-C120-RGBWW	SCX 2.75 in Linear 120D Section RGBW 2700K-5000K + RGB			
SCX-Y-RGBWW	SCX 2.75 in Linear Y Section RGBW 2700K-5000K + RGB			
SCX-C60-RGBWW	SCX Mct4 60-Degree Corner 30/35/40/50K			
SCX-OC-RGBWW	SCX 2.75 in Linear Outside Corner RGBW 2700K-5000K + RGB			
SCX-6IN-RGBWW	SCX 2.75 in Linear 6In Section RGBW 2700K-5000K + RGB			
SCX-9IN-RGBWW	SCX 2.75 in Linear 9In Section RGBW 2700K-5000K + RGB			
OPT-SCX-ULM-2FT-RGB	SCX 2Ft Rgb Uplight Option			
OPT-SCX-ULM-3FT-RGB	SCX 3Ft Rgb Uplight Option			
OPT-SCX-ULM-4FT-RGB	SCX 4Ft Rgb Uplight Option			
OPT-SCX-ULM-6FT-RGB	SCX 6Ft Rgb Uplight Option			
OPT-SCX-ULM-8FT-RGB	SCX 8Ft Rgb Uplight Option			

To Install our 4CCT uplight option, see page 252. With this option, Uplight will be disabled when switched to RGB mode.

FOR REMOTE CONTROL SEE PAGE 523


SCX Flat Lens (Linkable)

SCX Regressed Lens

SCX Chrome Louver Lens

SCX White Louver Lens (Linkable)

SCX White Diamond Louver


SCX Gold Diamond Louver

SCX-6IN-MCT4

SCX-9IN-MCT4

SCX-L-MCT4

SCX-T-MCT4

SCX-X-MCT4

SCX-IC-MCT4

SCX-OC-MCT4

SCX-Y-MCT4


SCX-C120-MCT4

SCX-C60-MCT4


SCX-RC-MCT4

SCX 2-3/4" SUPERIOR ARCHITECTURAL SEAMLESS LINKABLE LINEAR LIGHTING SYSTEM

CATALOG NO.	DESCRIPTION		
SCX 2-3/4" (Linkable)			
SCX-1FT-10W-MCT4-D	10W	1100LM	30K/35K/40K/50K
SCX-2FT-20W-MCT4-D	20W	2200LM	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D	30W	3300LM	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D	40W	4400LM	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D	60W	6600LM	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D	80W	8800LM	30K/35K/40K/50K
REGRESSED 2-3/4" MADE TO ORDER			
SCX-1FT-10W-MCT4-D-REG	10W	1100LM	30K/35K/40K/50K
SCX-2FT-20W-MCT4-D-REG	20W	2200LM	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-REG	30W	3300LM	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-REG	40W	4400LM	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-REG	60W	6600LM	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-REG	80W	8800LM	30K/35K/40K/50K
CHROME LOUVER 2-3/4" (Linkable) MADE TO ORDER			
SCX-1FT-10W-MCT4-D-LUV	10W	1100LM	30K/35K/40K/50K
SCX-2FT-20W-MCT4-D-LUV	20W	2200LM	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-LUV	30W	3300LM	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-LUV	40W	4400LM	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-LUV	60W	6600LM	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-LUV	80W	8800LM	30K/35K/40K/50K
WHITE LOUVER 2-3/4" (Linkable) MADE TO ORDER			
SCX-1FT-10W-MCT4-D-LUV-WH	10W	1100LM	30K/35K/40K/50K
SCX-2FT-20W-MCT4-D-LUV-WH	20W	2200LM	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-LUV-WH	30W	3300LM	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-LUV-WH	40W	4400LM	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-LUV-WH	60W	6600LM	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-LUV-WH	80W	8800LM	30K/35K/40K/50K
WHITE DIAMOND LOUVER 2-3/4" MADE TO ORDER			
SCX-1FT-10W-MCT4-D-DIAM	10W	110LM/W	30K/35K/40K/50K
SCX-2FT-20W-MCT4-D-DIAM	20W	110LM/W	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-DIAM	30W	110LM/W	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-DIAM	40W	110LM/W	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-DIAM	60W	110LM/W	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-DIAM	80W	110LM/W	30K/35K/40K/50K
GOLD DIAMOND LOUVER 2-3/4" MADE TO ORDER			
SCX-1FT-10W-MCT4-D-DIAM-GD	10W	110LM/W	30K/35K/40K/50K
SCX-2FT-20W-MCT4-D-DIAM-GD	20W	110LM/W	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-DIAM-GD	30W	110LM/W	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-DIAM-GD	40W	110LM/W	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-DIAM-GD	60W	110LM/W	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-DIAM-GD	80W	110LM/W	30K/35K/40K/50K


SCX Drop Lens


SCX PMMA Drop Lens

SCX Indirect Lens Downlight

SCX-L (Linkable)


SCX-Y2FT (Linkable)


SCX Indirect Uplight

SCX 2-3/4" SUPERIOR ARCHITECTURAL SEAMLESS LINKABLE LINEAR LIGHTING SYSTEM

CATALOG NO.	DESCRIPTION		
DROP LENS 2-3/4" MADE TO ORDER			
SCX-1FT-10W-MCT4-D-DL	10W	1100LM	30K/35K/40K/50K
SCX-2FT-20W-MCT4-D-DL	20W	2200LM	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-DL	30W	3300LM	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-DL	40W	4400LM	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-DL	60W	6600LM	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-DL	80W	8800LM	30K/35K/40K/50K
SOLID PMMA LENS 2-3/4"			
SCX-2FT-20W-MCT4-DLP	20W	2200LM	30K/35K/40K/50K
SCX-4FT-40W-MCT4-DLP	40W	4400LM	30K/35K/40K/50K
INDIRECT 2-3/4" MADE TO ORDER			
SCX-2FT-20W-MCT4-D-IND	20W	2200LM	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-IND	30W	3300LM	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-IND	40W	4400LM	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-IND	60W	6600LM	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-IND	80W	8800LM	30K/35K/40K/50K
IDL 2-3/4" MADE TO ORDER			
SCX-2FT-20W-MCT4-D-IDL	20W	2200LM	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-IDL	30W	3300LM	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-IDL	40W	4400LM	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-IDL	60W	6600LM	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-IDL	80W	8800LM	30K/35K/40K/50K
SCX1F & 2F L FIXTURE			
SCX-L1FT-20W-MCT4	20W	2200LM	30K/35K/40K/50K
SCX-L2FT-40W-MCT4	40W	4400LM	30K/35K/40K/50K
SCX 2F Y FIXTURE			
SCX-Y2FT-60W-MCT4-D	60W	6600LM	30K/35K/40K/50K
SCL-3CS10	ADJ. 10FT 1/16in TRIPLE-CABLE SUSPENSION CANOPY KIT WITH KEYHOLE END CONNECTORS (NO CORD INCL.)		
MODULES FOR SCX SERIES			
SCX-6IN-MCT4	SCX 2.75In Linear 6In Section 30K/35K/40K/50K		
SCX-9IN-MCT4	SCX 2.75In Linear 9In Section 30K/35K/40K/50K		
SCX-L-MCT4	SCX 2.75In Linear L Section 30K/35K/40K/50K		
SCX-T-MCT4	SCX 2.75In Linear T Section 30K/35K/40K/50K		
SCX-X-MCT4	SCX 2.75In Linear X Section 30K/35K/40K/50K		
SCX-IC-MCT4	SCX 2.75In Linear Inside Corner 30K/35K/40K/50K		
SCX-Y-MCT4	SCX 2.75In Linear Y Section 30K/35K/40K/50K		
SCX-C120-MCT4	SCX 2.75In Linear 120D Section 30K/35K/40K/50K		
SCX-C60-MCT4	SCX 60-Degree Corner 30/35/40/50K		
SCX-RC-MCT4	SCX Round Corner Module 30/35/40/50K		
SCX-OC-MCT4	SCX 2.75in Linear Outside Corner Section 30K/35K/40K/50K		

UPLIGHT FOR SCX 2-3/4" SERIES AND THEIR VARIANTS

CATALOG NO.	DESCRIPTION		
OPT-SCX-ULM-2FT-8W-MCT4	8W	880LM	30K/35K/40K/50K
OPT-SCX-ULM-3FT-12W-MCT4	12W	1320LM	30K/35K/40K/50K
OPT-SCX-ULM-4FT-16W-MCT4	16W	1760LM	30K/35K/40K/50K
OPT-SCX-ULM-6FT-24W-MCT4	24W	2640LM	30K/35K/40K/50K
OPT-SCX-ULM-8FT-32W-MCT4	32W	3520LM	30K/35K/40K/50K
OPT-SCX-ULM-L2FT-16W-MCT4	16W	1760LM	30K/35K/40K/50K
OPT-SCX-ULM-Y2FT-24W-MCT4	24W	2640LM	30K/35K/40K/50K

SCX Indirect Uplight Black

SCX-BK Flat Lens (Linkable)

SCX-BK Drop Lens

SCX-BK Chrome Louver Lens (Linkable)

SCX-6IN-MCT4-BK

SCX-9IN-MCT4-BK


SCX-L-MCT4-BK

SCX-T-MCT4-BK

SCX-X-MCT4-BK

SCX-IC-MCT4-BK

SCX-Y-MCT4-BK


SCX-C120-MCT4-BK

SCX-C60-MCT4-BK

SCX-RC-MCT4-BK

SCX 2-3/4" SUPERIOR ARCHITECTURAL SEAMLESS LINKABLE LINEAR LIGHTING SYSTEM - BLACK FOR THE UPLIGHT OPTION SEE PAGE 252

CATALOG NO.	DESCRIPTION		
SCX 2-3/4" (Linkable)			
SCX-1FT-10W-MCT4-D-BK	10W	110LM/W	30K/35K/40K/50K
SCX-2FT-20W-MCT4-D-BK	20W	110LM/W	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-BK	30W	110LM/W	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-BK	40W	110LM/W	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-BK	60W	110LM/W	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-BK	80W	110LM/W	30K/35K/40K/50K
LOUVER 2-3/4" (Linkable) MADE TO ORDER			
SCX-2FT-20W-MCT4-D-LUV-BK	20W	2200LM	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-LUV-BK	30W	3300LM	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-LUV-BK	40W	4400LM	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-LUV-BK	60W	6600LM	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-LUV-BK	80W	8800LM	30K/35K/40K/50K
DROP LENS 2-3/4" MADE TO ORDER			
SCX-2FT-20W-MCT4-D-DL-BK	20W	2200LM	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-DL-BK	30W	3300LM	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-DL-BK	40W	4400LM	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-DL-BK	60W	6600LM	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-DL-BK	80W	8800LM	30K/35K/40K/50K
INDIRECT 2-3/4" MADE TO ORDER			
SCX-2FT-20W-MCT4-D-IND-BK	20W	110LM/W	30K/35K/40K/50K
SCX-3FT-30W-MCT4-D-IND-BK	30W	110LM/W	30K/35K/40K/50K
SCX-4FT-40W-MCT4-D-IND-BK	40W	110LM/W	30K/35K/40K/50K
SCX-6FT-60W-MCT4-D-IND-BK	60W	110LM/W	30K/35K/40K/50K
SCX-8FT-80W-MCT4-D-IND-BK	80W	110LM/W	30K/35K/40K/50K

MODULES FOR SCX 2-3/4" SERIES - BLACK

CATALOG NO.	DESCRIPTION
SCX-6IN-MCT4-BK	SCX 2.75In Linear 6In Section 30K/35K/40K/50K, Black
SCX-9IN-MCT4-BK	SCX 2.75In Linear 9In Section 30K/35K/40K/50K, Black
SCX-L-MCT4-BK	SCX 2.75In Linear L Section 30K/35K/40K/50K, Black
SCX-T-MCT4-BK	SCX 2.75In Linear T Section 30K/35K/40K/50K, Black
SCX-X-MCT4-BK	SCX 2.75In Linear X Section 30K/35K/40K/50K, Black
SCX-IC-MCT4-BK	SCX 2.75In Linear Inside Corner 30K/35K/40K/50K
SCX-Y-MCT4-BK	SCX 2.75In Linear Y Section 30K/35K/40K/50K, Black
SCX-C120-MCT4-BK	SCX 2.75In Linear 120D Section 30K/35K/40K/50K, Black
SCX-C60-MCT4-BK	SCX 60-Degree Corner 30/35/40/50K, Black
SCX-RC-MCT4-BK	SCX Round Corner Module 30/35/40/50K Black


SCX1.5 (Linkable)


SCX1.5-BK (Linkable)


SCX1.5-L1FT (Linkable)


SCX1.5-L2FT (Linkable)


SCX1.5-L1FT-BK (Linkable)


SCX1.5-L2FT-BK (Linkable)

SCX 1.5" SUPERIOR ARCHITECTURAL SEAMLESS LINKABLE LINEAR LIGHTING SYSTEM

CATALOG NO.	DESCRIPTION		
SCX 1.5 (Linkable)			
SCX1.5-2FT-UD-MCTP5-D	8W/11W/13W/15W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-3FT-UD-MCTP5-D	12W/17W/20W/23W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-4FT-UD-MCTP5-D	16W/22W/26W/30W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-6FT-UD-MCTP5-D	24W/34W/40W/45W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-8FT-UD-MCTP5-D	32W/44W/52W/60W	110LM/W	27K/30K/35K/40K/50K
SCX 1.5 Black (Linkable)			
SCX1.5-2FT-UD-MCTP5-D-BK	8W/11W/13W/15W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-3FT-UD-MCTP5-D-BK	12W/17W/20W/23W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-4FT-UD-MCTP5-D-BK	16W/22W/26W/30W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-6FT-UD-MCTP5-D-BK	24W/34W/40W/45W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-8FT-UD-MCTP5-D-BK	32W/44W/52W/60W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-L			
SCX1.5-L1FT-UD-MCTP5	8W/11W/13W/15W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-L2FT-UD-MCTP5	16W/22W/26W/30W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-L Black			
SCX1.5-L1FT-UD-MCTP5-BK	8W/11W/13W/15W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-L2FT-UD-MCTP5-BK	16W/22W/26W/30W	110LM/W	27K/30K/35K/40K/50K
SCX1.5-CONKIT	Scx1.5 Connection Buckle		
MODULES FOR SCX 1.5" SERIES			
SCX1.5-1FT-UD-MCT5	1Ft 1.5in Linear Light Internal Driver 5CCT 7.5W Up/Down		
SCX1.5-6IN-UD-MCT5	SCX1.5 6In Module 5CCT		
SCX1.5-9IN-UD-MCT5	SCX1.5 9In Module 5CCT		
SCX1.5-L-UD-MCT5	SCX1.5 L Corner Module 5CCT		
SCX1.5-T-UD-MCT5	SCX1.5 T Corner Module 5CCT		
SCX1.5-X-UD-MCT5	SCX1.5 X Corner Module 5CCT		
SCX1.5-IC-UD-MCT5	SCX1.5 Inside Corner Module 5CCT		
SCX1.5-OC-UD-MCT5	SCX1.5 Outside Corner Module 5CCT		
SCX1.5-Y-UD-MCT5	SCX1.5 Y Corner Module 5CCT		
SCX1.5-C120-UD-MCT5	SCX1.5 120D Corner Module 5CCT		
SCX1.5-C60-UD-MCT5	SCX1.5 60D Corner Module 5CCT		
SCX1.5-1FT-UD-MCT5-BK	1Ft 1.5in Linear Light Internal Driver 5CCT 7.5W Up/Down, Black		
SCX1.5-6IN-UD-MCT5-BK	SCX1.5 6In Module 5CCT Black		
SCX1.5-9IN-UD-MCT5-BK	SCX1.5 9In Module 5CCT Black		
SCX1.5-L-UD-MCT5-BK	SCX1.5 L Corner Module 5CCT Black		
SCX1.5-T-UD-MCT5-BK	SCX1.5 T Corner Module 5CCT Black		
SCX1.5-X-UD-MCT5-BK	SCX1.5 X Corner Module 5CCT Black		
SCX1.5-IC-UD-MCT5-BK	SCX1.5 Inside Corner Module 5CCT Black		
SCX1.5-OC-UD-MCT5-BK	SCX1.5 Outside Corner Module 5CCT Black		
SCX1.5-Y-UD-MCT5-BK	SCX1.5 Y Corner Module 5CCT Black		
SCX1.5-C120-UD-MCT5-BK	SCX1.5 120D Corner Module 5CCT Black		
SCX1.5-C60-UD-MCT5-BK	SCX1.5 60D Corner Module 5CCT Black		


SCX4 White Louver Lens (Linkable)

SCX4 Indirect Lens Downlight

SCX4 Wall Wash View


SCX4 Flat Lens (Linkable)


SCX4 Wall Wash Lens


SCX4-L-MCT4


SCX4-T-MCT4


SCX4-X-MCT4

SCX4-IC-MCT4

SCX 4" SUPERIOR ARCHITECTURAL SEAMLESS LINKABLE LINEAR LIGHTING SYSTEM

CATALOG NO.	DESCRIPTION		
SCX4 4" (Linkable)			
SCX4-1FT-10W-MCT4-D	10W	1100LM	30K/35K/40K/50K
SCX4-2FT-20W-MCT4-D	20W	2200LM	30K/35K/40K/50K
SCX4-3FT-30W-MCT4-D	30W	3300LM	30K/35K/40K/50K
SCX4-4FT-40W-MCT4-D	40W	4400LM	30K/35K/40K/50K
SCX4-6FT-60W-MCT4-D	60W	6600LM	30K/35K/40K/50K
SCX4-8FT-80W-MCT4-D	80W	8800LM	30K/35K/40K/50K
WHITE LOUVER 4" (Linkable)			
SCX4-1FT-10W-MCT4-D-LUV-WH	10W	1100LM	30K/35K/40K/50K
SCX4-2FT-20W-MCT4-D-LUV-WH	20W	2200LM	30K/35K/40K/50K
SCX4-3FT-30W-MCT4-D-LUV-WH	30W	3300LM	30K/35K/40K/50K
SCX4-4FT-40W-MCT4-D-LUV-WH	40W	4400LM	30K/35K/40K/50K
SCX4-6FT-60W-MCT4-D-LUV-WH	60W	6600LM	30K/35K/40K/50K
SCX4-8FT-80W-MCT4-D-LUV-WH	80W	8800LM	30K/35K/40K/50K
IDL 4"			
SCX4-2FT-20W-MCT-D-IDL	20W	2200LM	30K/35K/40K/50K
SCX4-3FT-30W-MCT-D-IDL	30W	3300LM	30K/35K/40K/50K
SCX4-4FT-40W-MCT-D-IDL	40W	4400LM	30K/35K/40K/50K
SCX4-6FT-60W-MCT-D-IDL	60W	6600LM	30K/35K/40K/50K
SCX4-8FT-80W-MCT-D-IDL	80W	8800LM	30K/35K/40K/50K
WALLWASH 4"			
SCX4-2FT-20W-MCT4-WSH	20W	2200LM	
SCX4-3FT-30W-MCT4-WSH	30W	3300LM	30K/35K/40K/50K
SCX4-4FT-40W-MCT4-WSH	40W	4400LM	30K/35K/40K/50K
SCX4-L-MCT4	SCX 4In Linear L Section 30K/35K/40K/50K		
SCX4-T-MCT4	SCX 4In Linear T Section 30K/35K/40K/50K		
SCX4-X-MCT4	SCX 4In Linear X Section 30K/35K/40K/50K		
SCX4-IC-MCT4	SCX 4In Linear Inside Corner Section 30K/35K/40K/50K		

UPLIGHT FOR SCX4 SERIES AND THEIR VARIANTS

CATALOG NO.	DESCRIPTION		
OPT-SCX-ULM-2FT-8W-MCT4	8W	880LM	30K/35K/40K/50K
OPT-SCX-ULM-3FT-12W-MCT4	12W	1320LM	30K/35K/40K/50K
OPT-SCX-ULM-4FT-16W-MCT4	16W	1760LM	30K/35K/40K/50K
OPT-SCX-ULM-6FT-24W-MCT4	24W	2640LM	30K/35K/40K/50K
OPT-SCX-ULM-8FT-32W-MCT4	32W	3520LM	30K/35K/40K/50K



SCX2 2" (Linkable)



SCX2 Track Light (Linkable)



SCX2-L-MCT4

SCX2-T-MCT4

SCX2-X-MCT4

SCX2-IC-MCT4

SCX2-DC-MCT4



SCX2-C60-MCT4

SCX 2" SUPERIOR ARCHITECTURAL SEAMLESS LINKABLE LINEAR LIGHTING SYSTEM

CATALOG NO.	DESCRIPTION		
SCX2 2" (Linkable)			
SCX2-1FT-10W-MCT4-D	10W	1100LM	30K/35K/40K/50K
SCX2-2FT-20W-MCT4-D	20W	2200LM	30K/35K/40K/50K
SCX2-3FT-30W-MCT4-D	30W	3300LM	30K/35K/40K/50K
SCX2-4FT-40W-MCT4-D	40W	4400LM	30K/35K/40K/50K
SCX2-6FT-60W-MCT4-D	60W	6600LM	30K/35K/40K/50K
SCX2-8FT-80W-MCT4-D	80W	8800LM	30K/35K/40K/50K
SCX2 TRACK LIGHT (Linkable)			
SCX2-1FT-10W-MCT4-D-TR	10W	1100LM	30K/35K/40K/50K
SCX2-2FT-20W-MCT4-D-TR	20W	2200LM	30K/35K/40K/50K
SCX2-3FT-30W-MCT4-D-TR	30W	3300LM	30K/35K/40K/50K
SCX2-4FT-40W-MCT4-D-TR	40W	4400LM	30K/35K/40K/50K
SCX2-6FT-60W-MCT4-D-TR	60W	6600LM	30K/35K/40K/50K
SCX2-8FT-80W-MCT4-D-TR	80W	8800LM	30K/35K/40K/50K

UPLIGHT FOR SCX2 SERIES AND THEIR VARIANTS

CATALOG NO.	DESCRIPTION		
OPT-SCX-ULM-2FT-8W-MCT4	8W	880LM	30K/35K/40K/50K
OPT-SCX-ULM-3FT-12W-MCT4	12W	1320LM	30K/35K/40K/50K
OPT-SCX-ULM-4FT-16W-MCT4	16W	1760LM	30K/35K/40K/50K
OPT-SCX-ULM-6FT-24W-MCT4	24W	2640LM	30K/35K/40K/50K
OPT-SCX-ULM-8FT-32W-MCT4	32W	3520LM	30K/35K/40K/50K

MODULES FOR SCX2 SERIES

CATALOG NO.	DESCRIPTION
SCX2-L-MCT4	SCX 2In Linear L Section 30K/35K/40K/50K
SCX2-T-MCT4	SCX 2In Linear T Section 30K/35K/40K/50K
SCX2-X-MCT4	SCX 2In Linear X Section 30K/35K/40K/50K
SCX2-IC-MCT4	SCX 2In Linear Inside Corner Section 30K/35K/40K/50K
SCX2-OC-MCT4	SCX 2In Linear Outside Corner Section 30K/35K/40K/50K
SCX2-C60-MCT4	SCX2 Mct4 60-Degree Corner 30/35/40/50K



SCX6 6" (Linkable)



LOUVER 6" (Linkable)



SCX6-L-MCTP

SCX6-T-MCTP

SCX6-X-MCTP

SCX6-IC-MCTP

SCX 6" SUPERIOR ARCHITECTURAL SEAMLESS LINKABLE LINEAR LIGHTING SYSTEM

CATALOG NO.	DESCRIPTION		
SCX6 6" (Linkable)			
SCX6-2FT-20-30W-MCTP	20W/25W/30W	110LM/W	30K/35K/40K/50K
SCX6-3FT-30-45W-MCTP	20W/25W/30W	110LM/W	30K/35K/40K/50K
SCX6-4FT-40-60W-MCTP	20W/25W/30W	110LM/W	30K/35K/40K/50K
SCX6-6FT-60-90W-MCTP	20W/25W/30W	110LM/W	30K/35K/40K/50K
SCX6-8FT-80-120W-MCTP	20W/25W/30W	110LM/W	30K/35K/40K/50K
LOUVER 6" (Linkable)			
SCX6-2FT-20-30W-MCTP-LUV-WH	20W/25W/30W	110LM/W	30K/35K/40K/50K
SCX6-3FT-30-45W-MCTP-LUV-WH	20W/25W/30W	110LM/W	30K/35K/40K/50K
SCX6-4FT-40-60W-MCTP-LUV-WH	20W/25W/30W	110LM/W	30K/35K/40K/50K
SCX6-6FT-60-90W-MCTP-LUV-WH	20W/25W/30W	110LM/W	30K/35K/40K/50K
SCX6-8FT-80-120W-MCTP-LUV-WH	20W/25W/30W	110LM/W	30K/35K/40K/50K

UPLIGHT FOR SCX6 SERIES AND THEIR VARIANTS

CATALOG NO.	DESCRIPTION		
OPT-SCX6-ULM-2FT-8W-MCT4	8W	880LM	30K/35K/40K/50K
OPT-SCX6-ULM-3FT-12W-MCT4	12W	1320LM	30K/35K/40K/50K
OPT-SCX6-ULM-4FT-16W-MCT4	16W	1760LM	30K/35K/40K/50K
OPT-SCX6-ULM-6FT-24W-MCT4	24W	2640LM	30K/35K/40K/50K
OPT-SCX6-ULM-8FT-32W-MCT4	32W	3520LM	30K/35K/40K/50K

MODULES FOR SCX6 SERIES

CATALOG NO.	DESCRIPTION
SCX6-L-MCTP	SCX6 L Corner MCTP
SCX6-T-MCTP	SCX6 T Module MCTP
SCX6-X-MCTP	SCX6 X Module MCTP
SCX6-IC-MCTP	SCX6 Inside Corner Module MCTP

SCXR (Linkable)



SCXR LOUVER (Linkable)



SCXR-BK (Linkable)

SCXR-LNL

SCXR SUPERIOR ARCHITECTURAL SEAMLESS LINKABLE LINEAR LIGHTING SYSTEM

CATALOG NO.	DESCRIPTION		
SCXR (Linkable)			
SCXR-2FT-20W-MCT4-D	20W	1900LM	30K/35K/40K/50K
SCXR-2FT-20W-MCT4-D	20W	1900LM	30K/35K/40K/50K
SCXR-4FT-40W-MCT4-D	40W	4400LM	30K/35K/40K/50K
SCXR-8FT-80W-MCT4-D	80W	8800LM	30K/35K/40K/50K
SCXR LOUVER (Linkable)			
SCXR-2FT-20W-MCT4-D-LUV	20W	1900LM	30K/35K/40K/50K
SCXR-2FT-20W-MCT4-D-LUV	20W	1900LM	30K/35K/40K/50K
SCXR-4FT-40W-MCT4-D-LUV	40W	4400LM	30K/35K/40K/50K
SCXR-8FT-80W-MCT4-D-LUV	80W	8800LM	30K/35K/40K/50K
SCXR -BK(Linkable)			
SCXR-2FT-20W-MCT4-D-BK	20W	1900LM	30K/35K/40K/50K
SCXR-4FT-40W-MCT4-D-BK	40W	3800LM	30K/35K/40K/50K
SCXR-8FT-80W-MCT4-D-BK	80W	7600LM	30K/35K/40K/50K

UPLIGHT FOR SCXR SERIES

CATALOG NO.	DESCRIPTION		
OPT-SCX-ULM-4FT-16W-MCT4	16W	1760LM	30K/35K/40K/50K
OPT-SCX-ULM-8FT-32W-MCT4	32W	3520LM	30K/35K/40K/50K

SCXR CORNERS & ACCESSORIES

CATALOG NO.	DESCRIPTION
SCXR-LNL	Round SCXR 3.5In Dia. L Corner - Not Lighted
SCXR-LK-1FT-GRILL	SCXR 1Ft Section PC Louver Kit Without Lens
SCXR-LK-1FT-LENSONROLL	SCXR 1Ft Film On Roll Of 853Ft, Must Use With SCXR-LK

SCX1.5-FMRK-4FT (with SCX1.5-4FT-UD-MCTP5-D)

SCX1.5-FMRK-4FT

SCX1.5 FIELD-INSTALLED FLANGED RECESSED MOUNT DRYWALL KIT

CATALOG NO.	DESCRIPTION
SCX1.5-FMRK-1FT	SCX1.5-1Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX1.5-FMRK-2FT	SCX1.5-2Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX1.5-FMRK-3FT	SCX1.5-3Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX1.5-FMRK-4FT	SCX1.5-4Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX1.5-FMRK-6FT	SCX1.5-6Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX1.5-FMRK-8FT	SCX1.5-8Ft Field-Installed Flanged Recessed Mount Drywall Kit

NOT FOR T-BAR CEILINGS, ORDER THE FACTORY INSTALLED OPTION OPT-SCX-TBAR, SEE PAGE 268

SCX1.5-MIFK-4FT (with SCX1.5-4FT-UD-MCTP5-D)

SCX1.5-MIFK-4FT

SCX1.5 FIELD-INSTALLED MUD-IN FLANGE-LESS RECESSED MOUNT KIT

CATALOG NO.	DESCRIPTION
SCX1.5-MIFK-1FT	2-4In SCX1.5-1Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCX1.5-MIFK-2FT	2-4In SCX1.5-2Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCX1.5-MIFK-3FT	2-4In SCX1.5-3Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCX1.5-MIFK-4FT	2-4In SCX1.5-4Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCX1.5-MIFK-6FT	2-4In SCX1.5-6Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCX1.5-MIFK-8FT	2-4In SCX1.5-8Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit



SCX-MIFK-6FT



SCX-MIFK

2”- 4” SCX FIELD-INSTALLED MUD-IN FLANGE-LESS RECESSED MOUNT KIT

CATALOG NO.	DESCRIPTION
SCX-MIFK-1FT	2-4In SCX-1Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCX-MIFK-2FT	2-4In SCX-2Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCX-MIFK-3FT	2-4In SCX-3Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCX-MIFK-4FT	2-4In SCX-4Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCX-MIFK-6FT	2-4In SCX-6Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit
SCX-MIFK-8FT	2-4In SCX-8Ft Field-Installed Mud-In Flange-Less Recessed Mount Kit

SCX-FMRK-6FT

SCX-FMRK

SCX & SCX2 & SCX4 FIELD-INSTALLED FLANGED RECESSED MOUNT DRYWALL KIT

CATALOG NO.	DESCRIPTION
SCX-FMRK-1FT	SCX-1Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX-FMRK-2FT	SCX-2Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX-FMRK-3FT	SCX-3Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX-FMRK-4FT	SCX-4Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX-FMRK-6FT	SCX-6Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX-FMRK-8FT	SCX-8Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX2-FMRK-1FT	SCX2-1Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX2-FMRK-2FT	SCX2-2Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX2-FMRK-3FT	SCX2-3Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX2-FMRK-4FT	SCX2-4Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX2-FMRK-6FT	SCX2-6Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX2-FMRK-8FT	SCX2-8Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX4-FMRK-1FT	SCX4-1Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX4-FMRK-2FT	SCX4-2Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX4-FMRK-3FT	SCX4-3Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX4-FMRK-4FT	SCX4-4Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX4-FMRK-6FT	SCX4-6Ft Field-Installed Flanged Recessed Mount Drywall Kit
SCX4-FMRK-8FT	SCX4-8Ft Field-Installed Flanged Recessed Mount Drywall Kit

OPT-SCX-WMA

WALL MOUNTING WITH 5” ARMS (ADD-ON OPTION, DOES NOT INCLUDE FIXTURE)

CATALOG NO.	DESCRIPTION
OPT-SCX-WMA-1FT	1FT
OPT-SCX-WMA-2FT	2FT
OPT-SCX-WMA-3FT	3FT
OPT-SCX-WMA-4FT	4FT
OPT-SCX-WMA-6FT	6FT
OPT-SCX-WMA-8FT	8FT

ADD THIS OPTION TO THE FIXTURE AND WALL MOUNTING ARMS WITH WALL CANOPY WILL BE INSTALLED ON BACK OF FIXTURE. THE LENGTH OF EACH ARM IS 5”. CONNECTION CABLES WILL ENTER THE FIXTURE THROUGH ONE OF THE ARMS. ON YOUR PURCHASE ORDER SPECIFY THE POSTION OF YOUR WIRE ENTRY FROM THE WALL AND THE ARM WILL BE INSTALLED ON THE BACK ACCORDINGLY.



OPT-SCX-WM

WALL MOUNTING (ADD-ON OPTION, DOES NOT INCLUDE FIXTURE)

CATALOG NO.	DESCRIPTION
OPT-SCX-WM-1FT	1FT
OPT-SCX-WM-2FT	2FT
OPT-SCX-WM-3FT	3FT
OPT-SCX-WM-4FT	4FT
OPT-SCX-WM-6FT	6FT
OPT-SCX-WM-8FT	8FT
OPT-SCXR-WM-4FT	4FT
OPT-SCXR-WM-8FT	8FT

ADD THIS OPTION TO THE FIXTURE AND WALL MOUNTING BRACKETS WILL BE INSTALLED ON BACK OF FIXTURE. CONNECTION CABLES WILL ENTER THE FIXTURE THROUGH ONE OF THESE WALL-MOUNTING BRACKETS. ON YOUR PURCHASE ORDER SPECIFY THE POSTION OF YOUR WIRE ENTRY FROM THE WALL AND THE BRACKETS WILL BE INSTALLED ON THE BACK ACCORDINGLY.



SCX Surface Mount

SURFACE MOUNTING

YOU DO NOT NEED TO ORDER ANY ACCESSORIES
SCREW AND ANCHOR KIT PROVIDED WITH EACH FIXTURE CAN BE USED TO FASTEN THE FIXTURE DIRECTLY TO THE HARD SURFACE THROUGH THE HOLES ON TOP OF THE FIXTURE.

NOT APPLICABLE TO INDIRECT SERIES

SCX FLEXLENS

SCX CONTINUOUS FLEXIBLE LENS 25FT OR 100FT

CATALOG NO.	DESCRIPTION
SCX-FLEXLENS-25FT	25FT
SCX-FLEXLENS-100FT	100FT
SCX2-FLEXLENS-25FT	25FT
SCX2-FLEXLENS-100FT	100FT
SCX4-FLEXLENS-25FT	25FT
SCX4-FLEXLENS-100FT	100FT

SCL-RS

SUSPENSION ROD KITS

CATALOG NO.	DESCRIPTION	PCK QTY
SCL-RS-12	12 INCH	Set of 2
SCL-RS-18	18 INCH	Set of 2
SCL-RS-24	24 INCH	Set of 2
SCL-RS-36	36 INCH	Set of 2
SCL-RS-48	48 INCH	Set of 2

NOT APPLICABLE TO INDIRECT, SCXR SERIES



SCX ACOUSTIC BLUE



SCX ACOUSTIC GRAY

SCX INSTALLED ACOUSTIC OPTIONS - 9MM THICKNESS

CATALOG NO.	DESCRIPTION
OPT-SCX-AK-2FT-9MM-HY2204	2FT Dark Gray
OPT-SCX-AK-4FT-9MM-HY2204	4FT Dark Gray
OPT-SCX-AK-6FT-9MM-HY2204	6FT Dark Gray
OPT-SCX-AK-8FT-9MM-HY2204	8FT Dark Gray
OPT-SCX-AK-2FT-9MM-HY2210	2FT Dark Blue
OPT-SCX-AK-4FT-9MM-HY2210	4FT Dark Blue
OPT-SCX-AK-6FT-9MM-HY2210	6FT Dark Blue
OPT-SCX-AK-8FT-9MM-HY2210	8FT Dark Blue
OPT-SCX4-AK-2FT-9MM-HY2204	2FT Dark Gray
OPT-SCX4-AK-4FT-9MM-HY2204	4FT Dark Gray
OPT-SCX4-AK-6FT-9MM-HY2204	6FT Dark Gray
OPT-SCX4-AK-8FT-9MM-HY2204	8FT Dark Gray
OPT-SCX4-AK-2FT-9MM-HY2210	2FT Dark Blue
OPT-SCX4-AK-4FT-9MM-HY2210	4FT Dark Blue
OPT-SCX4-AK-6FT-9MM-HY2210	6FT Dark Blue
OPT-SCX4-AK-8FT-9MM-HY2210	8FT Dark Blue

SCX-WK01

SCX2-WK02

WOOD TRIMS

CATALOG NO.	DESCRIPTION
OPT-SCX2-WK02-2FT-MAPLE	2FT -MAPLE FINISH
OPT-SCX2-WK02-4FT-MAPLE	4FT -MAPLE FINISH
OPT-SCX2-WK02-6FT-MAPLE	6FT -MAPLE FINISH
OPT-SCX2-WK02-8FT-MAPLE	8FT -MAPLE FINISH
OPT-SCX2-WK02-2FT-WALNUT	2FT -WALNUT FINISH
OPT-SCX2-WK02-4FT-WALNUT	4FT -WALNUT FINISH
OPT-SCX2-WK02-6FT-WALNUT	6FT -WALNUT FINISH
OPT-SCX2-WK02-8FT-WALNUT	8FT -WALNUT FINISH
OPT-SCX2-WK02-2FT-FREOAK	2FT -FRENCH OAK FINISH
OPT-SCX2-WK02-4FT-FREOAK	4FT -FRENCH OAK FINISH
OPT-SCX2-WK02-6FT-FREOAK	6FT -FRENCH OAK FINISH
OPT-SCX2-WK02-8FT-FREOAK	8FT -FRENCH OAK FINISH
OPT-SCX2-WK02-2FT-EBONY	2FT -EBONY FINISH
OPT-SCX2-WK02-4FT-EBONY	4FT -EBONY FINISH
OPT-SCX2-WK02-6FT-EBONY	6FT -EBONY FINISH
OPT-SCX2-WK02-8FT-EBONY	8FT -EBONY FINISH
OPT-SCX-WK01-2FT-MAPLE	2FT -MAPLE FINISH
OPT-SCX-WK01-4FT-MAPLE	4FT -MAPLE FINISH
OPT-SCX-WK01-6FT-MAPLE	6FT -MAPLE FINISH
OPT-SCX-WK01-8FT-MAPLE	8FT -MAPLE FINISH
OPT-SCX-WK01-2FT-WALNUT	2FT -WALNUT FINISH
OPT-SCX-WK01-4FT-WALNUT	4FT -WALNUT FINISH
OPT-SCX-WK01-6FT-WALNUT	6FT -WALNUT FINISH
OPT-SCX-WK01-8FT-WALNUT	8FT -WALNUT FINISH
OPT-SCX-WK01-2FT-FREOAK	2FT -FRENCH OAK FINISH
OPT-SCX-WK01-4FT-FREOAK	4FT -FRENCH OAK FINISH
OPT-SCX-WK01-6FT-FREOAK	6FT -FRENCH OAK FINISH
OPT-SCX-WK01-8FT-FREOAK	8FT -FRENCH OAK FINISH
OPT-SCX-WK01-2FT-EBONY	2FT -EBONY FINISH
OPT-SCX-WK01-4FT-EBONY	4FT -EBONY FINISH
OPT-SCX-WK01-6FT-EBONY	6FT -EBONY FINISH
OPT-SCX-WK01-8FT-EBONY	8FT -EBONY FINISH



COLOR OF YOUR CHOICE

CATALOG NO.	DESCRIPTION
OPT-CLR-SCX-1FT(BK/GR/SR/WH)	
OPT-CLR-SCX-2FT(BK/GR/SR/WH)	
OPT-CLR-SCX-3FT(BK/GR/SR/WH)	
OPT-CLR-SCX-4FT(BK/GR/SR/WH)	
OPT-CLR-SCX-6FT(BK/GR/SR/WH)	
OPT-CLR-SCX-8FT(BK/GR/SR/WH)	
OPT-CLR-SCX-FMR(BK/GR/SR/WH)	
OPT-CLR-SCX-RODSET(BK/GR/SR/WH)	
OPT-CLR-SCX-CORNERS(BK/GR/SR/WH)	
OPT-CLR-SCL-RS(BK/GR/SR/WH)	

ADD THIS OPTION TO THE FIXTURE AND SPECIFY YOUR DESIRED COLOR ON YOUR PURCHASE ORDER OR PROVIDE A SWATCH TO MATCH. FOR PAINTED FLANGED FIXTURES OR OPTIONAL ROD MOUNTING SET PLEASE ALSO ADD THE RELEVANT OPTION BELOW FOR EACH FIXTURE.

BLUE OR GREEN OR PURPLE ACCENT UPLIGHT

CATALOG NO.	DESCRIPTION
OPT-SCX-ULM-BU	Blue
OPT-SCX-ULM-GR	Green
OPT-SCX-ULM-PU	Purple

ADD THIS OPTION TO THE UPLIGHT OPTION TO GET BLUE OR GREEN ACCENT UPLIGHT. (UPLIGHT OPTION MUST BE INCLUDED)

REDUCED WATTAGE/LUMENS (SPECIFY)

CATALOG NO.	DESCRIPTION
OPT-SCX-WTD-2FT	Wattage-Tunable Driver 2FT 10/15/20W
OPT-SCX-WTD-3FT	Wattage-Tunable Driver 3FT 15/22.5/30W
OPT-SCX-WTD-4FT	Wattage-Tunable Driver 4FT 20/30/40W
OPT-SCX-WTD-6FT	Wattage-Tunable Driver 6FT 30/45/60W
OPT-SCX-WTD-8FT	Wattage-Tunable Driver 8FT 40/60/80W

COMPATIBLE WITH SCX, SCX2 & SCX4 SERIES

WALL MOUNTING WITH 5 INCH ARMS (ADD-ON OPTION, DOES NOT INCLUDE FIXTURE)

CATALOG NO.	DESCRIPTION
OPT-SCX-WMA-1FT	1FT
OPT-SCX-WMA-2FT	2FT
OPT-SCX-WMA-3FT	3FT
OPT-SCX-WMA-4FT	4FT
OPT-SCX-WMA-6FT	6FT
OPT-SCX-WMA-8FT	8FT

ADD THIS OPTION TO THE FIXTURE AND WALL MOUNTING ARMS WITH WALL CANOPY WILL BE INSTALLED ON BACK OF FIXTURE. THE LENGTH OF EACH ARM IS 5". CONNECTION CABLES WILL ENTER THE FIXTURE THROUGH ONE OF THE ARMS. ON YOUR PURCHASE ORDER SPECIFY THE POSTION OF YOUR WIRE ENTRY FROM THE WALL AND THE ARM WILL BE INSTALLED ON THE BACK ACCORDINGLY.

DEDICATED WIRING FOR UPLIGHT CONTROL

CATALOG NO.	DESCRIPTION
OPT-SCX-ULC-2FT-MCT4	2FT
OPT-SCX-ULC-3FT-MCT4	3FT
OPT-SCX-ULC-4FT-MCT4	4FT
OPT-SCX-ULC-6FT-MCT4	6FT
OPT-SCX-ULC-8FT-MCT4	8FT



RECESSED MOUNT WITH VISIBLE FLANGES & SLIP-THROUGH BRACKET (ADD-ON OPTION, DOES NOT INCLUDE FIXTURE)

CATALOG NO.	DESCRIPTION
OPT-SCX-FMR-1FT	1FT
OPT-SCX-FMR-2FT	2FT
OPT-SCX-FMR-3FT	3FT
OPT-SCX-FMR-4FT	4FT
OPT-SCX-FMR-6FT	6FT
OPT-SCX-FMR-8FT	8FT
OPT-SCX-FMR-L	L
OPT-SCX-FMR-T	T
OPT-SCX-FMR-X	X
OPT-SCX-FMR-Y	Y
OPT-SCX-FMR-IC	INSIDE CORNER
OPT-SCX2-FMR-1FT	1FT
OPT-SCX2-FMR-2FT	2FT
OPT-SCX2-FMR-3FT	3FT
OPT-SCX2-FMR-4FT	4FT
OPT-SCX2-FMR-6FT	6FT
OPT-SCX2-FMR-8FT	8FT
OPT-SCX2-FMR-L	L
OPT-SCX2-FMR-T	T
OPT-SCX2-FMR-X	X
OPT-SCX2-FMR-Y	Y
OPT-SCX2-FMR-IC	INSIDE CORNER
OPT-SCX4-FMR-1FT	1FT
OPT-SCX4-FMR-2FT	2FT
OPT-SCX4-FMR-3FT	3FT
OPT-SCX4-FMR-4FT	4FT
OPT-SCX4-FMR-6FT	6FT
OPT-SCX4-FMR-8FT	8FT
OPT-SCX4-FMR-L	L
OPT-SCX4-FMR-T	T
OPT-SCX4-FMR-X	X
OPT-SCX4-FMR-Y	Y
OPT-SCX4-FMR-IC	INSIDE CORNER
OPT-SCX6-FMR-1FT	1FT
OPT-SCX6-FMR-2FT	2FT
OPT-SCX6-FMR-3FT	3FT
OPT-SCX6-FMR-4FT	4FT
OPT-SCX6-FMR-6FT	6FT
OPT-SCX6-FMR-8FT	8FT
OPT-SCX6-FMR-L	L
OPT-SCX6-FMR-T	T
OPT-SCX6-FMR-X	X
OPT-SCX6-FMR-Y	Y
OPT-SCX6-FMR-IC	INSIDE CORNER
OPT-SCX-FMR-2X2	2X2
OPT-SCX-FMR-2X4	2X4

ADD THIS OPTION TO THE FIXTURE AND THE FIXTURE WILL BE EQUIPED WITH A 1/2" WIDE FLANGE ON FOUR SIDES. ADVANCED DESIGN TOGGLE STYLE BRACKETS WILL ALSO BE PROVIDED, TO ADJUST AND HOLD THE FIXTURE AGAINST DRYWALL OR OTHER HARD CEILING FROM THE TOP.
WHEN LINKING TO ANOTHER FIXTURE OR CORNER MODULE, CALL US OR SEND A COPY OF YOUR PLAN ALONG WITH YOUR PO AND FLANGES WILL BE REMOVED ON THOSE ENDS THAT NEED TO MAKE A SEAMLESS CONNECTIONS.

NOT APPLICABLE TO INDIRECT, SCXR SERIES



FLANGELESS RECESS MOUNT IN DRYWALL (MUD-IN) FOR SPACKLING (ADD-ON OPTION, DOES NOT INCLUDE FIXTURE)

CATALOG NO.	DESCRIPTION
OPT-SCX-MIF-1FT	1FT
OPT-SCX-MIF-2FT	2FT
OPT-SCX-MIF-3FT	3FT
OPT-SCX-MIF-4FT	4FT
OPT-SCX-MIF-6FT	6FT
OPT-SCX-MIF-8FT	8FT
OPT-SCX-MIF-2X2	2X2
OPT-SCX-MIF-2X4	2X4
OPT-SCX-MIF-L	L
OPT-SCX-MIF-T	T
OPT-SCX-MIF-X	X
OPT-SCX-MIF-Y	Y
OPT-SCX-MIF-IC	INSIDE CORNER

ORDER THIS OPTION AND THE FIXTURE WILL BE EQUIPED WITH MUD-IN BRACKETS ON ALL FOUR SIDES, MOUNTED AT 1/16" FROM THE LENS SURFACE (SPECIFY IF OTHER SPACING IS NEEDED). WHEN LINKING TO ANOTHER FIXTURE OR CORNER FIXTURE MODULE CALL US OR SEND A COPY OF YOUR PLAN ALONG WITH YOUR PO AND FLANGES WILL BE REMOVED ON THOSE ENDS THAT NEED TO MAKE A SEAMLESS CONNECTION

NOT APPLICABLE TO INDIRECT, SCXR SERIES



SCX RECESSED FLANGELESS WOOD INSTALL

FLANGELESS RECESSED INSTALLATION IN WOOD CEILING

YOU DO NOT NEED TO ORDER ANY ACCESSORIES
MAKE RECESSED PREPARATIONS BY INSTALLING A HORIZONTAL PLANK OF WOOD ON TOP OF THE WOOD CEILING AT RECESSED HEIGHT OF 3-3/8". SCREW AND ANCHOR KIT PROVIDED WITH EACH FIXTURE CAN BE USED TO FASTEN THE TOP OF THE FIXTURE TO THE WOOD PLANK THROUGH THE HOLES ON TOP OF THE FIXTURE. YOU CAN ALSO INSTALL VERTICAL WOOD BOARDS ON TOP OF THE CEILING AT THE EDGE OF THE OPENING AND OPEN THE FIXTURE AND PUT SCREWS THROUGH THE SIDES OF THE FIXTURE HOUSING TO FASTEN IT TO THE WOOD BOARDS.

NOT APPLICABLE TO INDIRECT, SCXR SERIES

SCX TRIAC DIMMING

CATALOG NO.	DESCRIPTION
OPT-SCX-1FT-TRIAC	SCX, SCX2, SCX4 1FT TRIAC DIMMING
OPT-SCX-2FT-TRIAC	SCX, SCX2, SCX4 2FT TRIAC DIMMING
OPT-SCX-3FT-TRIAC	SCX, SCX2, SCX4 3FT TRIAC DIMMING
OPT-SCX-4FT-TRIAC	SCX, SCX2, SCX4 4FT TRIAC DIMMING
OPT-SCX-6FT-TRIAC	SCX, SCX2, SCX4 6FT TRIAC DIMMING
OPT-SCX-8FT-TRIAC	SCX, SCX2, SCX4 8FT TRIAC DIMMING



T-BAR INSTALLATION (ADD-ON OPTION, DOES NOT INCLUDE FIXTURE)

CATALOG NO.	DESCRIPTION
OPT-SCX-TBAR-1FT	1FT
OPT-SCX-TBAR-2FT	2FT
OPT-SCX-TBAR-4FT	4FT
OPT-SCX-TBAR-6FT	6FT
OPT-SCX-TBAR-8FT	8FT
OPT-SCX4-TBAR-1FT	1FT
OPT-SCX4-TBAR-2FT	2FT
OPT-SCX4-TBAR-4FT	4FT
OPT-SCX4-TBAR-6FT	6FT
OPT-SCX4-TBAR-8FT	8FT
OPT-SCX-TBAR-2X2	2X2
OPT-SCX-TBAR-2X4	2X4
OPT-FWH-63	6FT 3-WIRE FLEX WHIP
OPT-FWH-65	6FT 5-WIRE FLEX WHIP
OPT-FWH-66	6FT 6-WIRE FLEX WHIP
SCL-GS10	ADJ. 10FT 1/16in DOUBLE SUSPENSION CABLE WITH SINGLE KEYHOLE CONN., LOOP GRIPPER ON TOP
SCL-GS20	ADJ. 20FT 1/16in DOUBLE SUSPENSION CABLE WITH SINGLE KEYHOLE CONN., LOOP GRIPPER ON TOP
SCL-GSY110	ADJ. 10FT 1/16IN SINGLE SUSPENSION CABLE WITH Y HOOK ENDS, LOOP GRIPPER ON TOP
SCL-GSY120	ADJ. 20FT 1/16IN SINGLE SUSPENSION CABLE WITH Y HOOK ENDS, LOOP GRIPPER ON TOP

ADD THIS OPTION TO THE FIXTURE AND 1/2" WIDE FLANGES WILL BE INSTALLED ON THE TWO LONG SIDES OF THE FIXTURE. THE TWO ENDS OF THE FIXTURE WILL FALL ONTO THE T-BAR GRIDS AND WILL BE SUPPORTED THIS WAY. THE T-BAR TILES ON THE TWO SIDES OF THE FIXTURE MUST BE CUT TO ALLOW FOR THE WIDTH OF THE FIXTURE. THE TILES WILL FALL ONTO AND BE SUPPORTED BY THE FLANGES ON BOTH SIZES OF THE FIXTURE. IF YOU PLAN TO SUPPORT THE FIXTURE BY THE GRIDS ON THREE SIDES AND TILE ON ONE SIDE, CALL US OR SPECIFY ON YOUR PO AND FLANGE WILL BE INSTALLED ONLY ON ONE SIDE OF THE FIXTURE. TO PROVIDE SAFETY AND SUPPORT FROM THE BEAMS ABOVE THE T-BAR CEILING ORDER 10FT OR 20FT AIRCRAFT SUSPENSION KITS BELOW.

NOT APPLICABLE TO INDIRECT, SCXR SERIES

WALL GRAZER ASSEMBLY KIT FOR SCX SCX2 SCX4

CATALOG NO.	DESCRIPTION
OPT-SCX-WGRZR-1FT	1FT Wall Grazer Kit
OPT-SCX-WGRZR-2FT	2FT Wall Grazer Kit
OPT-SCX-WGRZR-3FT	3FT Wall Grazer Kit
OPT-SCX-WGRZR-4FT	4FT Wall Grazer Kit
OPT-SCX-WGRZR-6FT	6FT Wall Grazer Kit
OPT-SCX-WGRZR-8FT	8FT Wall Grazer Kit

EM-SCX

EMERGENCY BATTERY BACKUP

CATALOG NO.	DESCRIPTION
OPT-EM-SCX	1FT, 2FT, 3FT, 4FT, 6FT
OPT-EM-SCX-8FT	8FT
OPT-EM-SCX2	1FT, 2FT, 3FT, 4FT, 6FT
OPT-EM-SCX2-8FT	8FT
OPT-EM-SCX4	1FT, 2FT, 3FT, 4FT, 6FT
OPT-EM-SCX4-8FT	8FT
OPT-EM-SCX6	2FT, 3FT, 4FT, 6FT
OPT-EM-SCX6-8FT	8FT
OPT-EM-SCX-2X2-2X4	2X2, 2X4

ADD THIS OPTION FOR 90-MINUTE BATTERY BACKUP INSTALLATION. IF ORDERING A SERIES OF THIS FIXTURE TO LINK, CALL US OR SPECIFY ON YOUR PURCHASE ORDER, ON WHICH FIXTURES TO INSTALL THE BACKUP AND WHERE YOU WOULD LIKE THE TEST BUTTONS.



OPT-SEN

MICROWAVE BI-LEVEL MOTION SENSORS

CATALOG NO.	DESCRIPTION
OPT-SEN-SCX-3MRLV-5	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-SCXR	PROGRAMMABLE MICROWAVE BI-LEVEL FOR SCXR
WEC-8RC	OPTIONAL REMOTE CONTROL FOR SENSOR
OPT-SEN-2US-DAYLIGHT INTERNAL FOR ALL MODELS	MICROWAVE BI-LEVEL DIMMING (REMOTE NOT NEEDED) DAYLIGHT SENSOR
OPT-SEN-SCX2	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-SCX4	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-SCX6	PROGRAMMABLE MICROWAVE BI-LEVEL
SCX-UVC-12W	SCX ANTIVIRUS UVC SECTION 12W 280nM UV LIGHT WITH REVERSE-LOGIC SENSOR

THIS OPTION INSTALLS AN ADVANCED MOTION SENSOR THAT WILL TURN THE LIGHTS ON WHEN THE AREA IS OCCUPIED. WHEN THE AREA IS CLEARED, AFTER A PRESET HOLD TIME OF 5 SECONDS OR MORE, THE LIGHTS ARE DIMMED TO A STANDBY LEVEL OF 30% OR MORE. IF STILL NO MOTION IS DETECTED, AFTER THE STANDBY PERIOD THE LIGHTS ARE TURNED OFF. ALL SETTINGS ARE PROGRAMMABLE WITH A REMOTE CONTROL.

SCX CUSTOM DESIGN QUOTES - CALL





SCX4-IP66-SUR-8FT-40-80W-MCTP
SURFACE MOUNTED



SCX4-IP66-SUR-8FT-80-160W-MCTP

SCX4-IP66-SURF
SIDE CONNECTOR



SCX4-IP66-SUS-8FT-80-160W-MCTP
WALL MOUNTED, Rod Kit Sold Separately

SCX4-IP66-SUS-8FT-80-160W-MCTP
SUSPENDED, Rod Kit Sold Separately

SCX4-IP66-SCBK

SCX4-IP66-ACPT-6FT
SCX4-IP66-ACPT-10FT

SCX4-IP66-JUMP

LINEAR LIGHT, 120~277V, IP66 WET LOCATION POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION		
SCX4-IP66-SUR-4FT-40-80W-MCTP	40W/60W/80W	105LM/W	35K/40K/50K - Surface Mounted
SCX4-IP66-SUR-8FT-80-160W-MCTP	80W/120W/160W	105LM/W	35K/40K/50K - Surface Mounted
SCX4-IP66-SUS-4FT-40-80W-MCTP	40W/60W/80W	105LM/W	35K/40K/50K - Suspended
SCX4-IP66-SUS-8FT-80-160W-MCTP	80W/120W/160W	105LM/W	35K/40K/50K - Suspended
SCX4-IP66-ACPT-6FT	SCX4-IP66 6Ft Ac Pigtail With Female Wet Loc. Connector		
SCX4-IP66-ACPT-10FT	SCX4-IP66 10Ft Ac Pigtail With Female Wet Loc. Connector		
SCX4-IP66-JUMP-6IN	SCX4-IP66 6In Ac Jump Cable With Male And Female Wet Loc. Connector		
SCX4-IP66-JUMP-12IN	SCX4-IP66 12In Ac Jump Cable With Male And Female Wet Loc. Connector		
SCX4-IP66-JUMP-2FT-WH	SCX4-IP66 2FT Ac Jump Cable With Male And Female Wet Loc. Connector		
SCX4-IP66-JUMP-4FT-WH	SCX4-IP66 4FT Ac Jump Cable With Male And Female Wet Loc. Connector		
SCX4-IP66-JUMP-6FT-WH	SCX4-IP66 6FT Ac Jump Cable With Male And Female Wet Loc. Connector		
SCX4-IP66-JUMP-8FT-WH	SCX4-IP66 8FT Ac Jump Cable With Male And Female Wet Loc. Connector		
SCX4-IP66-CB	SCX4-IP66 Coupling Bracket		
SCX4-IP66-RODKIT-18IN	SCX4-IP66 18In Suspension Rod Kit		
SCX4-IP66-RODKIT-24IN	SCX4-IP66 24In Suspension Rod Kit		
SCX4-IP66-SCBK	SCX4-IP66 Bracket Set For Suspension With Aircraft Cable		

FOR SUSPENSION KIT SEE PAGES 231

SCSSL PC Lens shown with Round Endcap



SCSSL-AP Optic Lens Version



SCSSL-AP Optic Lens Version

SCSSL PC Lens shown with Round Endcap

SCSSL-BK PC Lens shown with Round Endcap



SCSSL-AP-BK Optic Lens Version



SCSSL-CEC

SCSSL-CECBK

SCSSL-REC

SCSSL-REC-BK

ARCHITECTURAL 0.4" SLIM UP&DOWN /W SEPARATE CONTROLS LINEAR LIGHT, DUAL DIMMING

POWER & CCT SELECTABLE

CATALOG NO.	DESCRIPTION		
ARCHITECTURAL 0.4" SLIM UP&DOWN /W SEPARATE CONTROLS LINEAR LIGHT, PC LENS - POWER & CCT SELECTABLE			
SCSSL-UD-4FT-MCTP	10W/15W/20W	70LM/W	27K/30K/35K/40K/50K - 4FT White
SCSSL-UD-4FT-MCTP-BK	10W/15W/20W	70LM/W	27K/30K/35K/40K/50K - 4FT Black
SCSSL-UD-6FT-MCTP	15W/23W/30W	70LM/W	27K/30K/35K/40K/50K - 6FT White
SCSSL-UD-6FT-MCTP-BK	15W/23W/30W	70LM/W	27K/30K/35K/40K/50K - 6FT Black
SCSSL-UD-8FT-MCTP	20W/30W/40W	70LM/W	27K/30K/35K/40K/50K - 8FT White
SCSSL-UD-8FT-MCTP-BK	20W/30W/40W	70LM/W	27K/30K/35K/40K/50K - 8FT Black
ARCHITECTURAL 0.4" SLIM UP&DOWN /W SEPARATE CONTROLS LINEAR LIGHT, APERTURE OPTICS - POWER & CCT SELECTABLE			
SCSSL-UD-AP-4FT-MCTP	10W/15W/20W	80LM/W	27K/30K/35K/40K/50K - 4FT White
SCSSL-UD-AP-4FT-MCTP-BK	10W/15W/20W	80LM/W	27K/30K/35K/40K/50K - 4FT Black
SCSSL-UD-AP-6FT-MCTP	15W/23W/30W	80LM/W	27K/30K/35K/40K/50K - 6FT White
SCSSL-UD-AP-6FT-MCTP-BK	15W/23W/30W	80LM/W	27K/30K/35K/40K/50K - 6FT Black
SCSSL-UD-AP-8FT-MCTP	20W/30W/40W	80LM/W	27K/30K/35K/40K/50K - 8FT White
SCSSL-UD-AP-8FT-MCTP-BK	20W/30W/40W	80LM/W	27K/30K/35K/40K/50K - 8FT Black
SCSSL-REC	SCSSL Rounded End Cap		
SCSSL-REC-BK	SCSSL Rounded End Cap Black		
SCSSL-CEC	SCSSL Coupling End Cap		
SCSSL-CEC-BK	SCSSL Coupling End Cap Black		

SCP-8FT-40-60W-MCTP
DIRECT LIGHT



SCP-8FT-40-60W-MCTP-BK
DIRECT LIGHT

SCP-8FT-40-60W-MCTP
INDIRECT LIGHT



SCP-8FT-40-60W-MCTP-BK
INDIRECT LIGHT

EURO-DESIGN DIE-CAST SUSPENDED LINEAR LIGHT, DIRECT OR INDIRECT - REVERSIBLE

POWER & CCT SELECTABLE

CATALOG NO.	DESCRIPTION		PKG. QTY.	PCK QTY
SCP-4FT-20-30W-MCTP	20W/25W/30W	80LM/W	3000K/3500K/4000K - White	12
SCP-8FT-40-60W-MCTP	40W/50W/60W	80LM/W	3000K/3500K/4000K - White	12
SCP-4FT-20-30W-MCTP-BK	20W/25W/30W	80LM/W	3000K/3500K/4000K - Black	12
SCP-8FT-40-60W-MCTP-BK	40W/50W/60W	80LM/W	3000K/3500K/4000K - Black	12

FOR FACTORY-INSTALLED OPTIONS SEE BELOW SCPL PAGE XXX

SDTL-6FT-25-50W-MCTP



SDTL-6FT-25-50W-MCTP-BK

LINEAR TUBE DECORATIVE SUSP. LIGHT POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION		
SDTL-4FT-20-30W-MCTP	20W/25W/30W	105LM/W	30K/35K/40K - White
SDTL-6FT-25-50W-MCTP	25W/40W/50W	105LM/W	30K/35K/40K - White
SDTL-8FT-40-60W-MCTP	40W/50W/60W	105LM/W	30K/35K/40K - White
SDTL-4FT-20-30W-MCTP-BK	20W/25W/30W	105LM/W	30K/35K/40K - Black
SDTL-6FT-25-50W-MCTP-BK	25W/40W/50W	105LM/W	30K/35K/40K - Black
SDTL-8FT-40-60W-MCTP-BK	40W/50W/60W	105LM/W	30K/35K/40K - Black



HEX-96X190-RGB-RC-BT

TC-RGBW-RC

HEX CAR SHOP DECORATIVE LIGHT KIT WITH FRAME 96” X 190” WESTGATE APP OR REMOTE CONTROL

CATALOG NO.	DESCRIPTION			PCK QTY
HEX-96X190-RGB-RC-BT	534W	130LM/W	RGB	1

FOR REMOTE CONTROL SEE PAGE 521



HEX-96X190-534W-65K-UNIV

HEX CAR SHOP DECORATIVE LIGHT KIT WITH FRAME 96” X 190”

CATALOG NO.	DESCRIPTION			PCK QTY
HEX-96X190-534W-65K-UNIV	534W	130LM/W	6500K	1
HEX-96X190-534W-30K-UNIV	534W	130LM/W	3000K	1

INDOOR CYLINDER LIGHTS

TRIAC DIMMABLE | DAMP LOCATIONS | EM CAPABLE | MCT

CMC1L-MCT-BK + CMC1-TRM-AG

CMC1L-MCT-BK

CMC1XL-MCT-WH

CMC1 Round Fixture Not Included

CMC1L-MCT-BK + CMC1-TRM-BN

CMCS1XL-MCT-BK+ CMC-CS-8FT-BK

CMCS1XL-MCT-WH+ CMC-SRK-218-5C-WH

CMCS1XL-MCT-BK

CMCS1XL-MCT-WH

CMCS1-MCT-BK+ CMC-CS-8FT-BK

CMCS1-MCT-WH+ CMC-SRK-218-5C-WH

1.6" ARCHITECTURAL CEILING CYLINDER WITH INTERNAL DRIVERS INCL. CLEAR & FORSTED LENSES

CATALOG NO.	DESCRIPTION			PCK QTY
CMC1L-MCT-WH	10W	700LM	30K/40K/50K - 12" H	8
CMC1L-MCT-BK	10W	700LM	30K/40K/50K - 12" H, 60°	8
CMC1XL-MCT-WH	10W	700LM	30K/40K/50K - 18" H	8
CMC1XL-MCT-BK	10W	700LM	30K/40K/50K - 18" H, 60°	8
CMCS1XL-MCT-DT-WH	9W	630LM	30K/40K/50K - 18" H SQUARE, 40°	8
CMCS1XL-MCT-DT-BK	9W	630LM	30K/40K/50K - 18" H SQUARE, 40°	8
CMC1-TRM-BN	1in Cylinder Trim, Brushed Nickel			
CMC1-TRM-AG	1in Cylinder Trim, Anodized Gold			
CMC1-DL15	CMC1 15mm Acrylic Drop Lens			
SUSPENSION ACCESSORIES FOR CMC SERIES				
CMC-CS-8FT-WH	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, White			
CMC-CS-8FT-BK	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, Black			
CMC-SRK-218-5C-WH	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, White			
CMC-SRK-218-5C-BK	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, Black			
CMC-SRK-224-5C-WH	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, White			
CMC-SRK-224-5C-BK	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, Black			
CMC-SRK-340-5C-WH	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, White			
CMC-SRK-340-5C-BK	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, Black			

DAMP LOCATIONS
EM CAPABLE

CMC2XL-MCT-DD-WH+
CMC-CS-8FT-WH+
CMC2-PS12-WG

CMC2-MCT-DT-BK+
CMC-CS-8FT-BK+
CMC2-PS12-BG

CMC2L-MCT-DT-WH+
CMC-CS-8FT-WH+
CMC2-DCR-WG

CMC2-MCT-DT-BK

CMC2-MCT-DT-BK+
CMC2-TRM-AG

CMC2-MCT-DT-WH+
CMC2-TRM-BN

CMC2-MCT-DT-BK+
CMC2-TRMWM-AG

CMC2-MCT-DT-BK+
CMC-CS-8FT-BK

CMC2XL-MCT-DD-BK+
CMC-CS-8FT-BK

CMC2L-BK+
DL32+Cord

CMC2XL-MCT-DD-BK+
CMC2-DS-BG +
CMC-CS-8FT-BK

CMCS2L-MCT-BK

CMCS2XXL-MCT-WH

CMCS2L-MCT-BK+
CMC-CS-8FT-BK

2" ARCHITECTURAL CEILING CYLINDER WITH INTERNAL DRIVERS

CATALOG NO.	DESCRIPTION			PCK QTY
CMC2-MCT-DT-WH	6W	450LM	30K/40K/50K - 9"H,120V, 30°	6
CMC2-MCT-DT-BK	6W	450LM	30K/40K/50K - 9"H, 120V, 30°	6
CMC2L-MCT-DT-WH	6W	450LM	30K/40K/50K - 12"H, 120V, 30°	6
CMC2L-MCT-DT-BK	6W	450LM	30K/40K/50K - 12"H, 120V, 30°	6
CMC2XL-MCT-DD-BK	20W	1500LM	30K/40K/50K - 18"H, 120-277V, 30°	6
CMC2XL-MCT-DD-WH	20W	1500LM	30K/40K/50K - 18"H, 120-277V, 30°	6
CMCS2L-MCT-DT-WH	6W	450LM	30K/40K/50K - 12"H SQUARE, 40°	12
CMCS2L-MCT-DT-BK	6W	450LM	30K/40K/50K - 12"H SQUARE, 40°	12
CMCS2XL-MCT-DT-WH	20W	1500LM	30K/40K/50K - 18"H SQUARE, 40°	8
CMCS2XL-MCT-DT-BK	20W	1500LM	30K/40K/50K - 18"H SQUARE, 40°	8
CMCS2XXL-MCT-DT-WH	20W	1500LM	30K/40K/50K - 24"H SQUARE, 40°	6
CMCS2XXL-MCT-DT-BK	20W	1500LM	30K/40K/50K - 24"H SQUARE, 40°	6
CMC2-TRM-AG	2in Cylinder Trim, Anodized Gold			
CMC2-TRM-BN	2in Cylinder Trim, Brushed Nickel			
CMC2-TRMWM-AG	Decorative Wide-Mouth Replacement Lens Cap for CMC2, Anodized Gold			
CMC2-TRMWM-BN	Decorative Wide-Mouth Replacement Lens Cap for CMC2, Brushed Nickel			
CMC2-HCDK-BK	2in Cylinder Honeycomb Diffuser Kit, Black			

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION
CMC2-HCDK-AG	2in Cylinder Honeycomb Diffuser Kit, Anodized Gold
CMC2-DS-BG	Decorative Shield Reflector Replacement For Lens Cap Of CMC2, Black Gold
CMC2-DS-WG	Decorative Shield Reflector Replacement For Lens Cap Of CMC2, White Gold
CMC2-DCR-BG	Decorative Cone Reflector Kit for CMC2, Black Gold
CMC2-DCR-WG	Decorative Cone Reflector Kit for CMC2, White Gold
CMC2-PS12-WG-KIT	CMC2 12in Pan Shade, White/Gold
CMC2-PS12-BG-KIT	CMC2 12in Pan Shade, Black/Gold
CMC2-PS14-WG-KIT	CMC2 14in Pan Shade, White/Gold
CMC2-PS14-BG-KIT	CMC2 14in Pan Shade, Black/Gold
CMC2-MLA-BK	Decorative Middle Light Accessory Fits All CMC2, Black
CMC2-MLA-WH	Decorative Middle Light Accessory Fits All CMC2, White
CWMC2-DL32	CMC2 And WMC2 32Mm Acrylic Drop Lens
CMC-CS-8FT-WH	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, White
CMC-CS-8FT-BK	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, Black
CMC-SRK-218-5C-WH	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, White
CMC-SRK-218-5C-BK	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, Black
CMC-SRK-224-5C-WH	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, White
CMC-SRK-224-5C-BK	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, Black
CMC-SRK-340-5C-WH	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, White
CMC-SRK-340-5C-BK	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, Black

TRIAC DIMMABLE · DAMP LOCATIONS · EM CAPABLE · MCT

CMC2L-ADJ-MCT-DT

CMC2L-ADJ-MCT-DT ANGLED

2” TILT HEAD INDOOR CYLINDER CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
CMC2L-ADJ-MCT-DT-BK	6W	400LM	30K/40K/50K - Black, 30°	6
CMC2L-ADJ-MCT-DT-WH	6W	400LM	30K/40K/50K - White, 30°	6

CMC4-MCTP-DD-BK

CMC4-MCTP-DD-BK +
CMC-CS8FT-BK

CMC4-MCTP-DD-WH+
CMC4-TRM-BN

CMC4-MCTP-DD-BK+
CMC4-TRM-AG

CMC4-MCTP-DD-BK+
CMC4-TRM-AG+
CMC4-HCDK-AG

CMCS4S-MCTP-DD-BK

CMCS4-MCTP-DD-BK

CMC-JBCK-BK

CMC-JBCK-WH

CMC4-HCDK-BK

CMC4-HCDK-WH

Shown with Up Light Kit

CMC4-MCTP-DD-BK+
CMC-CS-8FT-BK

CMC4-MCTP-DD-BK+
CMC4-WPCK-WH+
CMC-SRK-224-5C-WH

CMC4HL-MCTP-DD-BK+
CMC4-PCR-KIT

CMC4-MCTP-DD-BK+
CMC4-DS14-BS-KIT

CMC4HL-MCTP-DD-WH+
CMC4-FS14-WG-KIT

CMCS4-MCTP-DD-BK+
CMC-CS-8FT-BK

CMCS4S-MCTP-DD-WH+
CMC-SRK-224-5C-WH

4” ARCHITECTURAL CEILING CYLINDER

CATALOG NO.	DESCRIPTION			PCK QTY
4” ROUND ARCHITECTURAL CEILING CYLINDERS				
CMC4-MCTP-DD-WH	9W/12W/15W	75LM/W	30K/40K/50K - 9.6"H, 45°	6
CMC4-MCTP-DD-BK	9W/12W/15W	75LM/W	30K/40K/50K - 9.6"H, 45°	6
CMC4HL-MCTP-DD-WH	24W/32W/40W	80LM/W	30K/40K/50K - 10"H HIGH-LUMEN, 45°	6
CMC4HL-MCTP-DD-BK	24W/32W/40W	80LM/W	30K/40K/50K - 10"H HIGH-LUMEN, 45°	6
CMC4S-MCTP-DD-WH	9W/12W/15W	76LM/W	30K/40K/50K - 5"H, 45°	12
CMC4S-MCTP-DD-BK	9W/12W/15W	76LM/W	30K/40K/50K - 5"H, 45°	12
4” SQUARE ARCHITECTURAL CEILING CYLINDERS				
CMCS4-MCTP-DD-WH	21W/28W/35W	80LM/W	30K/40K/50K - 10"H, 30°	6
CMCS4-MCTP-DD-BK	21W/28W/35W	80LM/W	30K/40K/50K - 10"H, 30°	6
CMCS4S-MCTP-DD-WH	9W/12W/15W	76LM/W	30K/40K/50K - 5"H, 30°	12
CMCS4S-MCTP-DD-BK	9W/12W/15W	76LM/W	30K/40K/50K - 5"H, 30°	12
CMC46-ULK	5W	400LM	30K/40K/50K, 45°	

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION
CMC-JBCK-WH	Cylinder And Pendant Lighting J-Box Cover Canopy For Up To 4 Pipe Entries, Wh
CMC-JBCK-BK	Cylinder And Pendant Lighting J-Box Cover Canopy For Up To 4 Pipe Entries, Bk
CMC4-TRM-AG	4in Cylinder Trim, Anodized Gold
CMC4-TRM-BN	4in Cylinder Trim, Brushed Nickel
CMC4-HCDK-BK	4in Cylinder Honeycomb Diffuser Kit, Black
CMC4-HCDK-AG	4in Cylinder Honeycomb Diffuser Kit, Anodized Gold
CMC4-FS14-WG-KIT	CMC4 14in Flat Shade, White/Gold
CMC4-FS14-BG-KIT	CMC4 14in Flat Shade, Black/Gold
CMC4-FS14-WS-KIT	CMC4 14in Flat Shade, White/Silver
CMC4-FS14-BS-KIT	CMC4 14in Flat Shade, Black/Silver
CMC4-DS14-WG-KIT	CMC4 14in Dome Shade, White/Gold
CMC4-DS14-BG-KIT	CMC4 14in Dome Shade, Black/Gold
CMC4-DS14-WS-KIT	CMC4 14in Dome Shade, White/Silver
CMC4-DS14-BS-KIT	CMC4 14in Dome Shade, Black/Silver
CMC4-PCR-KIT	12in Dia. Prismatic Pc Highbay Reflector Kit For CMC4
CMC4-WPCK-WH	CMC4 Weatherproof Conversion Kit For Cord Or Down-Rod, White
CMC4-WPCK-BK	CMC4 Weatherproof Conversion Kit For Cord Or Down-Rod, Black
CMCS4-WPCK-WH	CMCS4 Weatherproof Conversion Kit For Cord Or Down-Rod, White
CMCS4-WPCK-BK	CMCS4 Weatherproof Conversion Kit For Cord Or Down-Rod, Black
CMC4-SNA-BK	Snoot Accessory For CMC4 Round Reduces Beam Angle To 25D, Black
CMC4-SNA-WH	Snoot Accessory For CMC4 Round Reduces Beam Angle To 25D, White
CMC4-SH9-BK	9in Wide Shade For CMC4 And CMC4S, Black
CMC4-SH9-WH	9in Wide Shade For CMC4 And CMC4S, White
CMC4-DL32	WMC 4in 32Mm Acrylic Drop Lens
CMC-CS-8FT-WH	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, White
CMC-CS-8FT-BK	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, Black
CMC-SRK-218-5C-WH	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, White
CMC-SRK-218-5C-BK	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, Black
CMC-SRK-224-5C-WH	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, White
CMC-SRK-224-5C-BK	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, Black
CMC-SRK-340-5C-WH	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, White
CMC-SRK-340-5C-BK	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, Black

CMCS4-ADJ-MCTP-DD-BK

CMCS4-ADJ-MCTP-DD-WH

4” SQUARE ADJUSTABLE-HEAD COMMERCIAL CYLINDER, H: 9.5”

CATALOG NO.	DESCRIPTION			PCK QTY
CMCS4-ADJ-MCTP-DD-BK	12W/16W/20W	80LM/W	30K/40K/50K - Black, 45°	6
CMCS4-ADJ-MCTP-DD-WH	12W/16W/20W	80LM/W	30K/40K/50K - White, 45°	6

CMC3-MCTP-DD-BK+
CMC3-HCDK-AG

CMC3-MCTP-DD-WH+
CMC3-HCDK-BK

CMC3-MCTP-DD-BK+
CMC3-TRM-AG

CMC3-MCTP-DD-WH+
CMC3-TRM-BN

CMC3-BK+DL32+Cord

CMC3S-MCT-D-BK

SHOWN WITH DROP LENS

3" ARCHITECTURAL CEILING CYLINDER INCL. CLEAR & FROSTED LENSES

CATALOG NO.	DESCRIPTION			PCK QTY
CMC3-MCTP-DD-WH	5W/7W/9W	75LM/W	30K/40K/50K - 3"D X 9.7"H, 120~277V, 30°	6
CMC3-MCTP-DD-BK	5W/7W/9W	75LM/W	30K/40K/50K - 3"D X 9.7"H, 120~277V, 30°	6
CMC3S-MCT-D-WH	9W	700LM	30K/40K/50K - 3"D X 5.12"H, 120~277V, 30°	12
CMC3S-MCT-D-BK	9W	700LM	30K/40K/50K - 3"D X 5.12"H, 120~277V, 30°	12
CMC3-TRM-AG	3in Cylinder Trim, Anodized Gold			
CMC3-TRM-BN	3in Cylinder Trim, Brushed Nickel			
CMC3-HCDK-BK	3in Cylinder Honeycomb Diffuser Kit, Black			
CMC3-HCDK-AG	3in Cylinder Honeycomb Diffuser Kit, Anodized Gold			
CWMC3-DL32	CMC3 And WMC3 32Mm Acrylic Drop Lens			

SUSPENSION ACCESSORIES FOR CMC SERIES. FOR 12FT & 20 FT SUSPENSION CABLE & CANOPY SET SEE PAGE 283

CMC-CS-8FT-WH	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, White
CMC-CS-8FT-BK	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, Black
CMC-SRK-218-5C-WH	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, White
CMC-SRK-218-5C-BK	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, Black
CMC-SRK-224-5C-WH	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, White
CMC-SRK-224-5C-BK	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, Black
CMC-SRK-340-5C-WH	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, White
CMC-SRK-340-5C-BK	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, Black



CMC4-ADJ-MCTP-DD-WH



CMC4-GIM-MCTP-DD-BK

4” INDOOR CYLINDER POWER & CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
TILT HEAD 4” INDOOR CYLINDER, POWER & CCT- ADJUSTABLE				
CMC4-ADJ-MCTP-DD-BK	12W/16W/20W	80LM/W	30K/40K/50K - Black, 45°	6
CMC4-ADJ-MCTP-DD-WH	12W/16W/20W	80LM/W	30K/40K/50K - White, 45°	6
GIMBAL HEAD 4” INDOOR CYLINDER, POWER & CCT- ADJUSTABLE				
CMC4-GIM-MCTP-DD-BK	12W/16W/20W	80LM/W	30K/40K/50K - Black, 45°	6
CMC4-GIM-MCTP-DD-WH	12W/16W/20W	80LM/W	30K/40K/50K - White, 45°	6

CMC5-MILAN1-MCTP-DD-GD
Gold and Black

CMC5-MILAN1-MCTP-DD-BN
Brushed Nickel and Black

CMC5-MILAN2-MCTP-DD-GD
Black and Gold

CMC5-MILAN2-MCTP-DD-BN
Black and Brushed Nickel

MILAN SERIES 5” CEILING CYLINDER

CATALOG NO.	DESCRIPTION			PCK QTY
CMC5-MILAN1-MCTP-DD-GD	12W/16W/20W	80LM/W	30K/40K/50K - Gold/Black, 25°	4
CMC5-MILAN1-MCTP-DD-BN	12W/16W/20W	80LM/W	30K/40K/50K - Brush Nickel/Black, 25°	4
CMC5-MILAN2-MCTP-DD-GD	12W/16W/20W	80LM/W	30K/40K/50K - Gold/Black, 45°	4
CMC5-MILAN2-MCTP-DD-BN	12W/16W/20W	80LM/W	30K/40K/50K - Brush Nickel/Black, 45°	

3" 2-TONE ARCHITECTURAL CEILING CYLINDERS

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
CMC3-2TONE-MCTP-DD-WHBN	9W/12W/15W	80LM/W	30K/40K/50K - White/Brushed Nickel, 30°	6
CMC3-2TONE-MCTP-DD-WHGD	9W/12W/15W	80LM/W	30K/40K/50K - White/Gold, 30°	6
CMC3-2TONE-MCTP-DD-BKBN	9W/12W/15W	80LM/W	30K/40K/50K - Black/Brushed Nickel, 30°	6
CMC3-2TONE-MCTP-DD-BKGD	9W/12W/15W	80LM/W	30K/40K/50K - Black/Gold, 30°	6

4" 2-TONE ARCHITECTURAL CEILING CYLINDERS

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
CMC4-2TONE-MCTP-DD-WHBN	15W/20W/25W	80LM/W	30K/40K/50K - White/Brushed Nickel, 45°	6
CMC4-2TONE-MCTP-DD-WHGD	15W/20W/25W	80LM/W	30K/40K/50K - White/Gold, 45°	6
CMC4-2TONE-MCTP-DD-BKBN	15W/20W/25W	80LM/W	30K/40K/50K - Black/Brushed Nickel, 45°	6
CMC4-2TONE-MCTP-DD-BKGD	15W/20W/25W	80LM/W	30K/40K/50K - Black/Gold, 45°	6

6” 2-TONE ARCHITECTURAL CEILING CYLINDERS

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
CMC6-2TONE-MCTP-DD-WHBN	18W/24W/30W	80LM/W	30K/40K/50K - White/Brushed Nickel, 25°	4
CMC6-2TONE-MCTP-DD-WHGD	18W/24W/30W	80LM/W	30K/40K/50K - White/Gold, 25°	4
CMC6-2TONE-MCTP-DD-BKBN	18W/24W/30W	80LM/W	30K/40K/50K - Black/Brushed Nickel, 25°	4
CMC6-2TONE-MCTP-DD-BKGD	18W/24W/30W	80LM/W	30K/40K/50K - Black/Gold, 25°	4

THIN SUSPENSION CABLE & CANOPY SET FOR CMC SERIES, XFT, 5-WIRE, WHITE/BLACK

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER
CMC-CS-8FT-TW-WH	Suspension Thinwall Cable & Canopy Set For CMC Series, 8FT, 5-Wire, White	
CMC-CS-8FT-TW-BK	Suspension Thinwall Cable & Canopy Set For CMC Series, 8FT, 5-Wire, Black	
CMC-CS-12FT-TW-WH	Suspension Thinwall Cable & Canopy Set For CMC Series, 12FT, 5-Wire, White	
CMC-CS-12FT-TW-BK	Suspension Thinwall Cable & Canopy Set For CMC Series, 12FT, 5-Wire, Black	
CMC-CS-20FT-TW-WH	Suspension Thinwall Cable & Canopy Set For CMC Series, 20FT, 5-Wire, White	
CMC-CS-20FT-TW-BK	Suspension Thinwall Cable & Canopy Set For CMC Series, 20FT, 5-Wire, Black	

CMC6-MCTP-DD

Shown with Drop Lens

CMC6S-MCTP-DD

CMC6HL-MCTP-DD

CMC6XHL-MCTP-DD

Shown with Up Light Kit

CMC6-WPCK

CMC-JBCK-BK

CMC-JBCK-WH

6” ARCHITECTURAL CEILING CYLINDER INCL. CLEAR & FROSTED LENSES

CATALOG NO.	DESCRIPTION			PCK QTY
6” ROUND ARCHITECTURAL CEILING CYLINDERS				
CMC6-MCTP-DD-WH	21W/28W/35W	75LM/W	30K/40K/50K - 8.74"H, 120~277V, 25°	6
CMC6-MCTP-DD-BK	21W/28W/35W	75LM/W	30K/40K/50K - 8.74"H, 120~277V, 25°	6
CMC6S-MCTP-DD-WH	18W/24W/30W	80LM/W	30K/40K/50K - 6.75"H, 25°	
CMC6S-MCTP-DD-BK	18W/24W/30W	80LM/W	30K/40K/50K - 6.75"H, 25°	
CMC6HL-MCTP-DD-BK	27W/36W/45W	80LM/W	30K/40K/50K - 12"H, 25°	6
CMC6HL-MCTP-DD-WH	27W/36W/45W	80LM/W	30K/40K/50K - 12"H, 25°	6
CMC6XHL-MCTP-DD-BK	36W/48W/60W	80LM/W	30K/40K/50K - 15.5"H, 25°	6
CMC6XHL-MCTP-DD-WH	36W/48W/60W	80LM/W	30K/40K/50K - 15.5"H, 25°	
CMC46-ULK	5W	400LM	30K/40K/50K, 45°	
CMC-JBCK-WH	Cylinder And Pendant Lighting J-Box Cover Canopy For Up To 4 Pipe Enteries, Wh			
CMC-JBCK-BK	Cylinder And Pendant Lighting J-Box Cover Canopy For Up To 4 Pipe Enteries, Bk			
CMC6-TRM-AG	6in Cylinder Trim, Anodized Gold			
CMC6-TRM-BN	6in Cylinder Trim, Brushed Nickel			
CMC6-WPCK-WH	CMC6 Weatherproof Conversion Kit For Cord Or Down-Rod, White			
CMC6-WPCK-BK	CMC6 Weatherproof Conversion Kit For Cord Or Down-Rod, Black			
CMC6-HCDK-AG	6in Cylinder Honeycomb Diffuser Kit, Anodized Gold			
CMC6-HCDK-BK	6in Cylinder Honeycomb Diffuser Kit, Black			
CWMC6-DL32	CMC6 And WMC6 32Mm Acrylic Drop Lens			
SUSPENSION ACCESSORIES FOR CMC SERIES. FOR 12FT & 20 FT SUSPENSION CABLE & CANOPY SET SEE PAGE 283				
CMC-CS-8FT-WH	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, White			
CMC-CS-8FT-BK	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, Black			
CMC-SRK-218-5C-WH	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, White			
CMC-SRK-218-5C-BK	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, Black			
CMC-SRK-224-5C-WH	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, White			
CMC-SRK-224-5C-BK	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, Black			
CMC-SRK-340-5C-WH	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, White			
CMC-SRK-340-5C-BK	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, Black			



CMCS8-MCT-D-BK

8” SQUARE INDOOR CYLINDER CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION		
CMCS8-MCT-D-BK	40W	80LM/W	30K/40K/50K - Black
CMCS8-MCT-D-WH	40W	80LM/W	30K/40K/50K - White

CMC8S-MCTP-DD-BK

8” ROUND INDOOR CYLINDER CCT- ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
CMC8S-MCTP-DD-BK	30W/40W/50W	80LM/W	30K/40K/50K - 5.5"H, Black, 25°	4
CMC8S-MCTP-DD-WH	30W/40W/50W	80LM/W	30K/40K/50K - 5.5"H, White, 25°	4
CMC8S-REFL-BK	CMC8S Replacement Lens Black			
CMC8S-REFL-WH	CMC8S Replacement Lens White			
CMC8S-REFL-SIL	CMC8S Replacement Lens Silver			

CMC9-MCTP-D-BK

CMC9-MCTP-D-WH

Shown with Extention Cylinder Black

Shown with Extention Cylinder White

CMC-CS

Shown with CMC9-WBK-BK

Shown with CMC9-WBK-WH

9" ARCHITECTURAL CEILING CYLINDER INCLUDED CLEAR & FROSTED LENSES

CATALOG NO.	DESCRIPTION			PCK QTY
CMC9-MCTP-D-BK	60W/70W/80W	80LM/W	30K/40K/50K - 10"H, 120~277V, 70°	1
CMC9-MCTP-D-WH	60W/70W/80W	80LM/W	30K/40K/50K - 10"H, 120~277V, 70°	1
CMC9-EC-BK	Decorative Extension Cylinder Black, Adds 5"H			
CMC9-EC-WH	Decorative Extension Cylinder White, Adds 5"H			
CMC9-HCDK-BK	9in Cylinder Honeycomb Diffuser Kit, Black			
CMC9-REFL-BK	Inside-Black Reflector			
CMC9-REFL-WH	Inside-White Reflector			
CMC9-WBK-BK	CMC9 Wall Bracket Kit And Conversion Top To IP65, Black			
CMC9-WBK-WH	CMC9 Wall Bracket Kit And Conversion Top To IP65, White			
CMC9-WPCK-BK	CMC9-Weatherproof Conversion Kit For Cord Or Down-Rod, Black			
CMC9-WPCK-WH	CMC9-Weatherproof Conversion Kit For Cord Or Down-Rod, White			

SUSPENSION ACCESSORIES FOR CMC SERIES. FOR 12FT & 20 FT SUSPENSION CABLE & CANOPY SET SEE PAGE 290

CMC-CS-8FT-WH	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, White
CMC-CS-8FT-BK	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, Black
CMC-SRK-218-5C-WH	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, White
CMC-SRK-218-5C-BK	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, Black
CMC-SRK-224-5C-WH	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, White
CMC-SRK-224-5C-BK	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, Black
CMC-SRK-340-5C-WH	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, White
CMC-SRK-340-5C-BK	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, Black

CMC12-BK 14"H

CMC12-WH 14"H

CMC12-SIL 14"H

CMC12L-BK 20"H

CMC12L-WH 20"H

CMC12L-SIL 20"H

12" COMMERCIAL CEILING CYLINDER

CATALOG NO.	DESCRIPTION			PCK QTY
CMC12-MCTP-D-BK	60W/80W/100W	125LM/W	30K/40K/50K - 14"H, Black, 75°	1
CMC12-MCTP-D-WH	60W/80W/100W	125LM/W	30K/40K/50K - 14"H, White, 75°	1
CMC12-MCTP-D-SIL	60W/80W/100W	125LM/W	30K/40K/50K - 14"H, Sliver, 75°	1
CMC12L-MCTP-D-BK	60W/80W/100W	125LM/W	30K/40K/50K - 20"H, Black, 75°	1
CMC12L-MCTP-D-WH	60W/80W/100W	125LM/W	30K/40K/50K - 20"H, White, 75°	1
CMC12L-MCTP-D-SIL	60W/80W/100W	125LM/W	30K/40K/50K - 20"H, Sliver, 75°	1
CMC12-REFL-WH	Cmc12 Replacement Reflector - White			
CMC12-REFL-SIL	Cmc12 Replacement Reflector - Silver			
CMC12-REFL-GD	Cmc12 Replacement Reflector - Matte Gold			
CMC12-SRK-218-5C-BK	1/2In Universal Downrod Kit With 5 Wires 2X18 H36In Bk			
CMC12-SRK-218-5C-WH	1/2In Universal Downrod Kit With 5 Wires 2X18 H36In Wh			
CMC12-SRK-218-5C-BR	1/2In Universal Downrod Kit With 5 Wires 2X18 H36In Bronze			
CMC12-SRK-218-5C-SIL	1/2In Universal Downrod Kit With 5 Wires 2X18 H36In Silver			
CMC12-SRK-224-5C-BK	1/2In Universal Downrod Kit With 5 Wires 2X24 H48In Bk			
CMC12-SRK-224-5C-WH	1/2In Universal Downrod Kit With 5 Wires 2X24 H48In Wh			
CMC12-SRK-224-5C-BR	1/2In Universal Downrod Kit With 5 Wires 2X24 H48In Bronze			
CMC12-SRK-224-5C-SIL	1/2In Universal Downrod Kit With 5 Wires 2X24 H48In Silver			
CMC12-SRK-340-5C-BK	1/2In Universal Downrod Kit With 5 Wires 3X40 H120In Bk			
CMC12-SRK-340-5C-WH	1/2In Universal Downrod Kit With 5 Wires 3X40 H120In Wh			
CMC12-SRK-340-5C-BR	1/2In Universal Downrod Kit With 5 Wires 3X40 H120In Bronze			
CMC12-SRK-340-5C-SIL	1/2In Universal Downrod Kit With 5 Wires 3X40 H120In Silver			

CMC6-MCTP-DD-BK-RGBW

TC-RGBW-RC

CMC6-MCTP-DD-WH-RGBW

CMC RGBW CYLINDER LIGHT, PENDANT OR SURFACE MOUNT, APP CONTROLLED

CATALOG NO.	DESCRIPTION			PCK QTY
CMC2L-RGBW-BK	6W	300LM	27K-50K + RGB - Black	6
CMC2L-RGBW-WH	6W	300LM	27K-50K + RGB - White	6
CMC3-RGBW-BK	9W	550LM	27K-50K + RGB - Black	6
CMC3-RGBW-WH	9W	550LM	27K-50K + RGB - White	6
CMC4-RGBW-BK	15W	900LM	27K-50K + RGB - Black, 45°	6
CMC4-RGBW-WH	15W	900LM	27K-50K + RGB - White, 45°	6
CMC6-RGBW-BK	20W	1200LM	27K-50K + RGB - Black, 25°	8
CMC6-RGBW-WH	20W	1200LM	27K-50K + RGB - White, 25°	8

CMCSR9S-MCTP-DD-BK

CMCSR9S-MCTP-DD-WH

CMCSR7S-MCTP-DD-BK

CMCSR7S-MCTP-DD-WH

CMCSR3S-MCTP-DD-BK

CMCSR3S-MCTP-DD-WH

CMCSR6-MCTP-DD-BK

CMCSR6-MCTP-DD-WH

CMCSR4S-MCTP-DD-BK

CMCSR4S-MCTP-DD-WH

CMCSR4-MCTP-DD-BK

CMCSR4-MCTP-DD-WH

EU-DESIGN SQUARE ROUNDED-CORNER COMMERCIAL CYLINDER

CATALOG NO.	DESCRIPTION			PCK QTY
3" SQUARE ROUNDED-CORNER COMMERCIAL CYLINDERS				
CMCSR3S-MCTP-DD-BK	9W/12W/15W	80LM/W	30K/40K/50K - 3"D X 4"H, Black, 35°	8
CMCSR3S-MCTP-DD-WH	9W/12W/15W	80LM/W	30K/40K/50K - 3"D X 4"H, White, 35°	8
4" SQUARE ROUNDED-CORNER COMMERCIAL CYLINDERS, 10" LONG				
CMCSR4-MCTP-DD-BK	12W/16W/20W	80LM/W	30K/40K/50K - 4"D X 10"H, Black, 45°	6
CMCSR4-MCTP-DD-WH	12W/16W/20W	80LM/W	30K/40K/50K - 4"D X 10"H, White, 45°	6
4" SQUARE ROUNDED-CORNER COMMERCIAL CYLINDERS				
CMCSR4S-MCTP-DD-BK	12W/16W/20W	80LM/W	30K/40K/50K - 4"D X 5"H, Black, 45°	8
CMCSR4S-MCTP-DD-WH	12W/16W/20W	80LM/W	30K/40K/50K - 4"D X 5"H, White, 45°	8
6" SQUARE ROUNDED-CORNER COMMERCIAL CYLINDERS				
CMCSR6-MCTP-DD-BK	24W/32W/40W	70LM/W	30K/40K/50K - 6"D X 6"H, Black, 50°	6
CMCSR6-MCTP-DD-WH	24W/32W/40W	70LM/W	30K/40K/50K - 6"D X 6"H, White, 50°	6
7" SQUARE ROUNDED-CORNER COMMERCIAL CYLINDERS				
CMCSR7S-MCTP-DD-WH	30W/40W/50W	80LM/W	30K/40K/50K - 7"D X 7"H, Black, 50°	8
CMCSR7S-MCTP-DD-BK	30W/40W/50W	80LM/W	30K/40K/50K - 7"D X 7"H, White, 50°	8
9" SQUARE ROUNDED-CORNER COMMERCIAL CYLINDERS				
CMCSR9S-MCTP-DD-WH	42W/56W/70W	80LM/W	30K/40K/50K - 9"D X 9"H, Black, 50°	8
CMCSR9S-MCTP-DD-BK	42W/56W/70W	80LM/W	30K/40K/50K - 9"D X 9"H, White, 50°	8

CMC1 Round Fixture not Included

CMC1 Square Fixture not Included

CMC1 Square Fixture not Included

CMC1 Square Fixture not Included

CMC1 Square Fixture not Included

CMC2 Round Fixture not Included

CMC2 Square Fixture not Included

CMC3 Round Fixture not Included

CMC4 Round Fixture not Included

CMC4 Round Fixture not Included

CMC4 Square Fixture not Included

CMC4 Square Fixture not Included

CMC6 Round Fixture not Included

CMC6 Round Fixture not Included

CMC9 Round Fixture not Included

CMC9 Round Fixture not Included

SUSPENSION ACCESSORIES FOR CMC SERIES

CATALOG NO.	DESCRIPTION
CMC-CS-8FT-WH	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, White
CMC-CS-8FT-BK	Suspension Cable & Canopy Set For CMC Series, 8Ft, 5-Wire, Black
CMC-CS-12FT-WH	Suspension Cable & Canopy Set For CMC Series, 12Ft, 5-Wire, White
CMC-CS-12FT-BK	Suspension Cable & Canopy Set For CMC Series, 12Ft, 5-Wire, Black
CMC-CS-20FT-WH	Suspension Cable & Canopy Set For CMC Series, 20Ft, 5-Wire, White
CMC-CS-20FT-BK	Suspension Cable & Canopy Set For CMC Series, 20Ft, 5-Wire, Black
CMC-SRK-218-5C-WH	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, White
CMC-SRK-218-5C-BK	Universal Swivel W/ Rod Kit, 18 Or 36 Inches, 5-Wire, Black
CMC-SRK-224-5C-WH	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, White
CMC-SRK-224-5C-BK	Universal Swivel W/ Rod Kit, 24 Or 48 Inches, 5-Wire, Black
CMC-SRK-340-5C-WH	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, White
CMC-SRK-340-5C-BK	Universal Swivel W/ Rod Kit, 40 Or 80 Or 120 Inches, 5-Wire, Black

CMCW3-COB

CMCW5-COB

CMCW6-COB

CMCW8-COB

CMCW10-COB

IP65 SPEC CYLINDER COB WITH OPTIC LENS, 36° BEAM ANGLE

CATALOG NO.	DESCRIPTION			PCK QTY
CMCW3-COB-10W-MCT-36D-DT-WH	10W	900LM	30K/35K/40K - 3.5" D X 4.2" H, White, 120V	18
CMCW3-COB-10W-MCT-36D-DT-BK	10W	900LM	30K/35K/40K - 3.5" D X 4.2" H, Black, 120V	18
CMCW5-COB-25W-MCT-36D-DT-WH	25W	2250LM	30K/35K/40K - 5" D X 4.5" H, White, 120V	12
CMCW5-COB-25W-MCT-36D-DT-BK	25W	2250LM	30K/35K/40K - 5" D X 4.5" H, Black, 120V	12
CMCW6-COB-30W-MCT-36D-DT-WH	30W	2500LM	30K/35K/40K - 6.3" D X 4.3" H, White, 120V	6
CMCW6-COB-30W-MCT-36D-DT-BK	30W	2500LM	30K/35K/40K - 6.3" D X 4.3" H, Black, 120V	6
CMCW8-COB-35W-MCT-36D-D-WH	35W	3100LM	30K/35K/40K - 8.4" D X 4.7" H, White, 120-277V	6
CMCW8-COB-35W-MCT-36D-D-BK	35W	3100LM	30K/35K/40K - 8.4" D X 4.7" H, Black, 120-277V	6
CMCW10-COB-40W-MCT-36D-D-WH	40W	3850LM	30K/35K/40K - 9.8" D X 5" H, White, 120-277V	4
CMCW10-COB-40W-MCT-36D-D-BK	40W	3850LM	30K/35K/40K - 9.8" D X 5" H, Black, 120-277V	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	OPTIC LENS OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
ALL	OPT-CMCW3-COB-24D	24° OPTIC CMCW3	N/A	N/A
	OPT-CMCW3-COB-60D	60° OPTIC CMCW3	480V OPTION	DESCRIPTION
	OPT-CMCW6-COB-24D	24° OPTIC CMCW6	N/A	N/A
	OPT-CMCW6-COB-60D	60° OPTIC CMCW6	POWDER COATING	
	OPT-CMCW10-COB-24D	24° OPTIC CMCW10	N/A	
	OPT-CMCW10-COB-60D	60° OPTIC CMCW10		

CMCW3-SMD

CMCW5-SMD

CMCW6-SMD

CMCW8-SMD

CMCW10-SMD

IP65 SPEC CYLINDER SMD WITH PC LENS, 75° BEAM ANGLE

CATALOG NO.	DESCRIPTION				PCK QTY
TRIAC DIMMABLE	**CMCW3-SMD-10W-MCT-75D-DT-WH**	10W	850LM	30K/35K/40K - 3.5" D X 4.2" H, White, 120V	18
TRIAC DIMMABLE	**CMCW3-SMD-10W-MCT-75D-DT-BK**	10W	850LM	30K/35K/40K - 3.5" D X 4.2" H, Black, 120V	18
TRIAC DIMMABLE	**CMCW5-SMD-25W-MCT-75D-DT-BK**	25W	2300LM	30K/35K/40K - 5" D X 4.5" H, White, 120V	12
TRIAC DIMMABLE	**CMCW5-SMD-25W-MCT-75D-DT-WH**	25W	2300LM	30K/35K/40K - 5" D X 4.5" H, Black, 120V	12
TRIAC DIMMABLE	**CMCW6-SMD-30W-MCT-75D-DT-BK**	30W	2800LM	30K/35K/40K - 6.3" D X 4.3" H, White, 120V	6
TRIAC DIMMABLE	**CMCW6-SMD-30W-MCT-75D-DT-WH**	30W	2800LM	30K/35K/40K - 6.3" D X 4.3" H, Black, 120V	6
DIMMING 0-10V	**CMCW8-SMD-35W-MCT-75D-D-BK**	35W	3650LM	30K/35K/40K - 8.4" D X 4.7" H, White, 120-277V	6
DIMMING 0-10V	**CMCW8-SMD-35W-MCT-75D-D-WH**	35W	3650LM	30K/35K/40K - 8.4" D X 4.7" H, Black, 120-277V	6
DIMMING 0-10V	**CMCW10-SMD-40W-MCT-75D-D-BK**	40W	4350LM	30K/35K/40K - 9.8" D X 5" H, White, 120-277V	4
DIMMING 0-10V	**CMCW10-SMD-40W-MCT-75D-D-WH**	40W	4350LM	30K/35K/40K - 9.8" D X 5" H, Black, 120-277V	4

TRACK LIGHTS

DAMP LOCATIONS

TRPK-4L-GU10-30K-BN

TRPK-3L-GU10-30K-BN

TRPK-6L-GU10-30K-BN

TRACK PACK W/ LED GU10 LAMP

CATALOG NO.	DESCRIPTION			PCK QTY
TRPK-3L-GU10-30K-BN	3X6.5W	3x500LM	3000K - Brush Nickel	6
TRPK-4L-GU10-30K-BN	4X6.5W	4x500LM	3000K - Brush Nickel	6
TRPK-6L-GU10-30K-BN	6X6.5W	5x500LM	3000K - Brush Nickel	6

TRE-5-15W-MCTP-36D-BK

TRE-15-25W-MCTP-36D-BK

TRE-25-35W-MCTP-36D-BK

Shown with TRE26-BK Black

TRE-5-15W-MCTP-36D-WH

TRE-15-25W-MCTP-36D-WH

TRE-25-35W-MCTP-36D-WH

Shown with TRE26-WH White

BUILDER SERIES TRACK HEAD WITH EXT. DRIVERS, 120V POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
TRE-5-15W-MCTP-36D-BK	5W/10W/15W	84LM/W	30K/35K/40K - Black	20
TRE-5-15W-MCTP-36D-WH	5W/10W/15W	84LM/W	30K/35K/40K - White	20
TRE-15-25W-MCTP-36D-BK	15W/20W/25W	84LM/W	30K/35K/40K - Black	12
TRE-15-25W-MCTP-36D-WH	15W/20W/25W	84LM/W	30K/35K/40K - White	12
TRE-25-35W-MCTP-36D-BK	25W/30W/35W	84LM/W	30K/35K/40K - Black	10
TRE-25-35W-MCTP-36D-WH	25W/30W/35W	84LM/W	30K/35K/40K - White	10
TRE26-BK	3.5In Modern Par-Lamp Track Head 120V 3-Wire, Black			
TRE26-WH	3.5In Modern Par-Lamp Track Head 120V 3-Wire, White			

TRD-BK

Fixture Shown with Antiglare Honeycomb Louver

TRD-WH

Fixture Shown with Antiglare Honeycomb Louver

SPEC SERIES DIE-CAST ZOOMABLE TRACK HEAD WATTAGE & CCT & BEAM ANGLE SELECT

CATALOG NO.	DESCRIPTION			PCK QTY
TRD-20W-MCTB-BK	20W	1700LM	27K/30K/35K/40K/50K - Black	16
TRD-20W-MCTB-WH	20W	1700LM	27K/30K/35K/40K/50K - White	16
TRD-30W-MCTB-BK	30W	2700LM	27K/30K/35K/40K/50K - Black	12
TRD-30W-MCTB-WH	30W	2700LM	27K/30K/35K/40K/50K - White	12
TRD-20W-MCTB-HCL-BK	Antiglare Honeycomb Louver For Zoomable TRD-20W-MCTB Black			
TRD-20W-MCTB-HCL-WH	Antiglare Honeycomb Louver For Zoomable TRD-20W-MCTB White			
TRD-30W-MCTB-HCL-BK	Antiglare Honeycomb Louver For Zoomable TRD-30W-MCTB Black			
TRD-30W-MCTB-HCL-WH	Antiglare Honeycomb Louver For Zoomable TRD-30W-MCTB White			
TRD-20W-MCTB-BD-BK	Barn Door For Zoomable TRD-20W-MCTB Black			
TRD-20W-MCTB-BD-WH	Barn Door For Zoomable TRD-20W-MCTB White			
TRD-30W-MCTB-BD-BK	Barn Door For Zoomable TRD-30W-MCTB Black			
TRD-30W-MCTB-BD-WH	Barn Door For Zoomable TRD-30W-MCTB White			

TRD-8W-MCT5-36D-BK

TRD-12W-MCT5-36D-BK
TRD-15W-MCT5-36D-BK

TRD-20W-MCT5-36D-BK

TRD-30W-MCT5-36D-BK

SPEC SERIES DIE-CAST TRACK HEAD 5CCT, **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TRD-8W-MCT5-36D-BK	8W	720LM	27K/30K/35K/40K/50K - Black	40
TRD-8W-MCT5-36D-WH	8W	720LM	27K/30K/35K/40K/50K - White	40
TRD-12W-MCT5-36D-BK	12W	1080LM	27K/30K/35K/40K/50K - Black	24
TRD-12W-MCT5-36D-WH	12W	1080LM	27K/30K/35K/40K/50K - White	24
TRD-15W-MCT5-36D-BK	15W	1350LM	27K/30K/35K/40K/50K - Black	24
TRD-15W-MCT5-36D-WH	15W	1350LM	27K/30K/35K/40K/50K - White	24
TRD-20W-MCT5-36D-BK	20W	1800LM	27K/30K/35K/40K/50K - Black	16
TRD-20W-MCT5-36D-WH	20W	1800LM	27K/30K/35K/40K/50K - White	16
TRD-30W-MCT5-36D-BK	30W	2700LM	27K/30K/35K/40K/50K - Black	16
TRD-30W-MCT5-36D-WH	30W	2700LM	27K/30K/35K/40K/50K - White	16
TRD-8W-LENS-15D	TRD 8W Replacement Lens 15-Degree			
TRD-8W-LENS-25D	TRD 8W Replacement Lens 25-Degree			
TRD-8W-LENS-55D	TRD 8W Replacement Lens 55-Degree			
TRD-12W-LENS-15D	TRD 12W & 15W Replacement Lens 15-Degree			
TRD-12W-LENS-25D	TRD 12W & 15 Replacement Lens 25-Degree			
TRD-12W-LENS-55D	TRD 12W & 15 Replacement Lens 55-Degree			
TRD-20W-LENS-15D	TRD 20W Replacement Lens 15-Degree			
TRD-20W-LENS-25D	TRD 20W Replacement Lens 25-Degree			
TRD-20W-LENS-60D	TRD 20W Replacement Lens 60-Degree			
TRD-30W-LENS-12D	TRD 30W Replacement Lens 12-Degree			
TRD-30W-LENS-24D	TRD 30W Replacement Lens 24-Degree			
TRD-30W-LENS-60D	TRD 30W Replacement Lens 60-Degree			

TRS-10-20W-BK

TRS-10-20W-WH

TRS-20-30W-BK

TRS-20-30W-WH

STANDARD TRACK HEAD SERIES, WATTAGE & CCT SELECT, H-TYPE TO J-TYPE CONV. KIT AVAILABLE, 120V

CATALOG NO.	DESCRIPTION			PCK QTY
STANDARD TRACK HEAD SERIES, WATTAGE & CCT SELECT, BEAM ANGLE: 36°				
TRS-10-20W-MCTP-36D-WH	10W/15W/20W	90LM/W	27K/30K/35K/40K/50K - White	20
TRS-10-20W-MCTP-36D-BK	10W/15W/20W	90LM/W	27K/30K/35K/40K/50K - Black	20
TRS-20-30W-MCTP-36D-WH	20W/25W/30W	90LM/W	27K/30K/35K/40K/50K - White	20
TRS-20-30W-MCTP-36D-BK	20W/25W/30W	90LM/W	27K/30K/35K/40K/50K - Black	20
STANDARD TRACK HEAD SERIES, WATTAGE & CCT & BEAM ANGLE SELECT (BEAM ANGLE: 20°-50°)				
TRS-10-20W-MCTPB-36D-WH	10W/15W/20W	90LM/W	27K/30K/35K/40K/50K - White, Zoomable	20
TRS-10-20W-MCTPB-36D-BK	10W/15W/20W	90LM/W	27K/30K/35K/40K/50K - Black, Zoomable	20
TRS-20-30W-MCTPB-36D-WH	20W/25W/30W	90LM/W	27K/30K/35K/40K/50K - White, Zoomable	20
TRS-20-30W-MCTPB-36D-BK	20W/25W/30W	90LM/W	27K/30K/35K/40K/50K - Black, Zoomable	20
TRS-H-J-WH	H-Type To J-Type Connector Head Converter for TRS Series, White			
TRS-H-J-BK	H-Type To J-Type Connector Head Converter for TRS Series, Black			

TRP-8-15W-MCTP-20D-BK

TRP-8-15W-MCTP-20D-WH

TRACK PUCK LIGHT 120V, 20° BEAM ANGLE POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
TRP-8-15W-MCTP-20D-WH	8W/12W/15W	90LM/W	27K/30K/35K/40K/50K - White	20
TRP-8-15W-MCTP-20D-BK	8W/12W/15W	90LM/W	27K/30K/35K/40K/50K - Black	20

TRK39-48-MCT5-D-BK

TRK39-48-MCT5-D-WH

3X9W 48" TRACK KIT, 5CCT, 36° BEAM ANGLE, **120V**, DIMMABLE

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
TRK39-48-MCT5-D-BK	3X9W	3X810LM	27K/30K/35K/40K/50K - Black	9
TRK39-48-MCT5-D-WH	3X9W	3X810LM	27K/30K/35K/40K/50K -White	9

TRM-100-4W-27K-36D-BK

1" MICRO TRACK HEAD, **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TRM-100-4W-27K-36D-BK	4W	300LM	2700K - Black	50
TRM-100-4W-27K-36D-WH	4W	300LM	2700K - White	50
TRM-100-4W-30K-36D-BK	4W	300LM	3000K - Black	50
TRM-100-4W-30K-36D-WH	4W	300LM	3000K - White	50
TRM-125-6W-27K-36D-BK	6W	400LM	2700K - Black	50
TRM-125-6W-27K-36D-WH	6W	400LM	2700K - White	50
TRM-125-6W-30K-36D-BK	6W	400LM	3000K - Black	50
TRM-125-6W-30K-36D-WH	6W	400LM	3000K - White	50

SFX-G12

SFX-G12

SFX-G12

SFX-G12

SFX-G12

SFX-G12

ADJ. LINEAR TRACK LIGHT CCT ADJUSTABLE, **120V**, 110° BEAM ANGLE

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
TRL-16-18W-MCT-WH	18W	1440LM	30K/40K/50K - White	20
TRL-16-18W-MCT-BK	18W	1440LM	30K/40K/50K - Black	20
TRL-28-30W-MCT-WH	30W	2400LM	30K/40K/50K - White	12
TRL-28-30W-MCT-BK	30W	2400LM	30K/40K/50K - Black	12
TRL-39-50W-MCT-WH	50W	4000LM	30K/40K/50K - White	12
TRL-39-50W-MCT-BK	50W	4000LM	30K/40K/50K - Black	12

SFX-G12

SFX-G12


SFX-G12

SFX-G12

SFX-G12

SFX-G12

ADJ. LINEAR TRACK LIGHT CCT ADJUSTABLE, **120V** - 45° BEAM ANGLE

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
TRLO-16-18W-MCT-WH	18W	1440LM	30K/40K/50K - White	20
TRLO-16-18W-MCT-BK	18W	1440LM	30K/40K/50K - Black	20
TRLO-28-30W-MCT-WH	30W	2400LM	30K/40K/50K - White	12
TRLO-28-30W-MCT-BK	30W	2400LM	30K/40K/50K - Black	12
TRLO-39-50W-MCT-WH	50W	4000LM	30K/40K/50K - White	12
TRLO-39-50W-MCT-BK	50W	4000LM	30K/40K/50K - Black	12

c UL us LISTED

TR1-R-10W-WH-50K

TR1-S-10W-WH-50K

WHILE SUPPLIES LAST

LED TRACK LIGHT, **120V** (FIT HALO® AND COMPATIBLE TRACKS AND ACCESSORIES)

CATALOG NO.	DESCRIPTION		
TR1-R-10W-WH-50K	10W	702LM	5000K - 25° LED ADJ. CYLINDER
TR1-S-10W-WH-30K	10W	681LM	3000K - 25° LED ADJ. SQUARE
TR1-S-10W-WH-40K	10W	706LM	4000K - 25° LED ADJ. SQUARE
TR1-S-10W-WH-50K	10W	732LM	5000K - 25° LED ADJ. SQUARE

3-WIRE TRACKS

TR-LE

TR-MC

TR-SC

TR-LE-CL10A-WH

TR-LE-CL10A-BK

TR-LC

TR-TC

TR-XC

TR-FC

TR-JBEF

TR-MONC

TR-FLEXC

TR-CCON


TR-EC

TR-EXTCON

TRACK ACCESSORIES

CATALOG NO.	DESCRIPTION
TR-2FT-BK	2Ft 3-Wire Track, Black
TR-2FT-WH	2Ft 3-Wire Track, White
TR-4FT-BK	4Ft 3-Wire Track, Black
TR-4FT-WH	4Ft 3-Wire Track, White
TR-6FT-BK	6Ft 3-Wire Track, Black
TR-6FT-WH	6Ft 3-Wire Track, White
TR-8FT-BK	8Ft 3-Wire Track, Black
TR-8FT-WH	8Ft 3-Wire Track, White
TR-LE-BK	3-Wire Track Live End, Black with Top Access 1/2" KO
TR-LE-WH	3-Wire Track Live End, White with Top Access 1/2" KO
TR-MC-BK	3-Wire Track Mini Connector, Black
TR-MC-WH	3-Wire Track Mini Connector, White
TR-SC-BK	3-Wire Track Straight Connector, Black
TR-SC-WH	3-Wire Track Straight Connector, White
TR-LC-BK	3-Wire Track L Connector, Black
TR-LC-WH	3-Wire Track L Connector, White
TR-TC-BK	3-Wire Track T Connector, Black
TR-TC-WH	3-Wire Track T Connector, White
TR-XC-BK	3-Wire Track X Connector, Black
TR-XC-WH	3-Wire Track X Connector, White
TR-FLEXC-BK	3-Wire Track Flex Connector, Black
TR-FLEXC-WH	3-Wire Track Flex Connector, White
TR-FC-BK	3-Wire Track Floating Canopy, Black
TR-FC-WH	3-Wire Track Floating Canopy, White
TR-MONC-BK	3-Wire Track Mono Canopy, Black
TR-MONC-WH	3-Wire Track Mono Canopy, White
TR-JBEF-BK	3-Wire Track J-Box End Feed Kit, Black
TR-JBEF-WH	3-Wire Track J-Box End Feed Kit, White
TR-CCON-BK	3-Wire Track Conduit Connector, Black
TR-CCON-WH	3-Wire Track Conduit Connector, White
TR-EC-BK	3-Wire Track End Cap, Black
TR-EC-WH	3-Wire Track End Cap, White
TR-EXTCON-BK	3-Wire Track To Track Extension Connector, Black
TR-EXTCON-WH	3-Wire Track To Track Extension Connector, White
TR-PENDKIT-BK	3-Wire Track 3Ft Pendant Wiring Kit, Black
TR-PENDKIT-WH	3-Wire Track 3Ft Pendant Wiring Kit, White
TR-LE-CL10A-BK	Track Live End With 10A Current Limiter Black
TR-LE-CL10A-WH	Track Live End With 10A Current Limiter White



WCLP-UD-4FT-50W-MCT-D

LED LOUVER WALL LIGHTS (UP/DOWN)

CATALOG NO.	DESCRIPTION		
WCLP-UD-2FT-25W-MCT-D	25W	2750LM	3500K/4000K/5000K
WCLP-UD-4FT-50W-MCT-D	50W	5500LM	3500K/4000K/5000K

WCPL-UD-4FT-50W-MCT-D

LED PERFORATED WALL LIGHTS (UP/DOWN)

CATALOG NO.	DESCRIPTION		
WCPL-UD-2FT-25W-MCT-D	25W	2750LM	3500K/4000K/5000K
WCPL-UD-4FT-50W-MCT-D	50W	5500LM	3500K/4000K/5000K

WCF-UD-EFT-36W-MCTP-DD-WH



WCF-UD-EFT-36W-MCTP-DD-BK

3FT FLAT WALL LIGHT, SEPARATE UP AND DOWN CONTROLS - DUAL DIMMING

CATALOG NO.	DESCRIPTION			PCK QTY
WCF-UD-EFT-36W-MCTP-DD-BK	36W	2800LM	27K/30K/40K - Black	1
WCF-UD-EFT-36W-MCTP-DD-WH	36W	2800LM	27K/30K/40K - White	1

FDLH-12-MCT5

HALF CIRCLE INDOOR WALL SCONCE, 5CCT

CATALOG NO.	DESCRIPTION		
FDLH-12-MCT5	12W	960LM	27K/30K/35K/40K/50K

LSC-10-MCTP-BN

LSC-15-MCTP-BN

LSC-18-MCTP-BN

MODERN INDOOR WALL SCONCE POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION		
LSC-10-MCTP-BN	9W/12W/15W	80LM/W	30K/40K/50K - Brushed Nickel
LSC-15-MCTP-BN	12W/18W/20W	80LM/W	30K/40K/50K - Brushed Nickel
LSC-18-MCTP-BN	15W/20W/25W	80LM/W	30K/40K/50K - Brushed Nickel

LMIR-18R-24D-MCT-DF
LMIR-18R-32D-MCT-DF
LMIR-18R-40D-MCT-DF

LMIR-MC18-2432-MCT-DF

LMIR-18-2028-MCT-DF
LMIR-18-2436-MCT-DF
LMIR-18-2840-MCT-DF

LMIR-36-2028-MCT-DF
LMIR-36-2436-MCT-DF
LMIR-36-4836-MCT-DF

SPEC SERIES LED MIRRORS AND CABINET, DIMMING, WITH DEFOGGER FEATURE (ALL SPECIAL SIZES & FEATURES AVAIL. BY SPECIAL ORDER) ADJUSTABLE COLOR TEMPERATURE

CATALOG NO.	DESCRIPTION	
SQUARE LED MIRRORS		
LMIR-18-2028-MCT-DF	35W	3000K/4500K/6500K - 20"W X 28"H
LMIR-18-2436-MCT-DF	44W	3000K/4500K/6500K - 24"W X 36"H
LMIR-18-2840-MCT-DF	48W	3000K/4500K/6500K - 28"W X 40"H
LMIR-36-2028-MCT-DF	31W	3000K/4500K/6500K - 20"W X 28"H
LMIR-36-2436-MCT-DF	39W	3000K/4500K/6500K - 24"W X 36"H
LMIR-36-4836-MCT-DF	50W	3000K/4500K/6500K - 48"W X 36"H
SQUARE LED MEDICINE CABINET MIRROR		
LMIR-MC18-2432-MCT-DF	35W	2700K-6500K - 24"W X 32"H
ROUND LED MIRRORS		
LMIR-18R-24D-MCT-DF	30W	30K/45K/65K - 24"
LMIR-18R-32D-MCT-DF	48W	30K/45K/65K - 32"
LMIR-18R-40D-MCT-DF	68W	30K/45K/65K - 40"

LVL-2FT-MCT-DD

2FT LED VANITY LIGHT, 120-277VAC

CATALOG NO.	DESCRIPTION			PCK QTY
LVL-2FT-MCT-DD	20W	2200LM	30K/40K/50K	3
LVL-2FT-17W-30K*	17W	1900LM	3000K	3
LVL-2FT-17W-40K*	17W	1900LM	4000K	3

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	ROCKER SWITCH OPTION	DESCRIPTION
ALL MODELS	OPT-EM-LVL	INTERNAL	OPT-VL-RS-BK	BOX
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
			OPT-SEN-NLS-LVL	WG NETWORK SENSOR
			OPT-SEN-KEILTON-LVL	KEILTON NETWORK SENSOR
			WEC-3RC	REMOTE CONTROL

LVF-36-MCT5-BN

LVF-18-MCT5-BN

LVF-48-MCT5-BN

LVF-24-MCT5-BN

LVF-WS-MCT5-BN

Fixture Shown with OPT-VL-RS-BK Factory-Installed Switch Option

BULDER SERIES VANITY LIGHTS WITH SLIDE-TO-CENTER WALL CANOPY

CATALOG NO.	DESCRIPTION		
LVF-18-MCT5-BN	12W	1020LM	27K/30K/35K/40K/50K - 18" Brushed Nickel
LVF-24-MCT5-BN	16W	1360LM	27K/30K/35K/40K/50K - 24" Brushed Nickel
LVF-30-MCT5-BN	20W	1600LM	27K/30K/35K/40K/50K - 30" Brushed Nickel
LVF-36-MCT5-BN	24W	2000LM	27K/30K/35K/40K/50K - 36" Brushed Nickel
LVF-48-MCT5-BN	32W	2700LM	27K/30K/35K/40K/50K - 48" Brushed Nickel
LVF-WS-MCT5-BN	16W	1360LM	27K/30K/35K/40K/50K - 14" Brushed Nickel

LVB-12-MCT-PC

LVB-18-MCT-PC

LVB-36-MCT-PC

LVB-24-MCT-PC

LVB-48-MCT-PC

MODEL LVB LED SEMI-FLUSH VANITY LIGHT, 3CCT, PC LENS, **120V**

CATALOG NO.	DESCRIPTION		
LVB-12-MCT-BN	8W	560LM	30K/40K/50K - Brushed-Nickel, 12"
LVB-12-MCT-PC	8W	560LM	30K/40K/50K - Polished-Chrome, 12"
LVB-18-MCT-BN	12W	840LM	30K/40K/50K - Brushed-Nickel, 18"
LVB-18-MCT-PC	12W	840LM	30K/40K/50K - Polished-Chrome, 18"
LVB-24-MCT-BN	16W	1440LM	30K/40K/50K - Brushed-Nickel, 24"
LVB-24-MCT-PC	16W	1440LM	30K/40K/50K - Polished-Chrome, 24"
LVB-36-MCT-BN	24W	1680LM	30K/40K/50K - Brushed-Nickel, 36"
LVB-36-MCT-PC	24W	1680LM	30K/40K/50K - Polished-Chrome, 36"
LVB-48-MCT-BN	32W	2240LM	30K/40K/50K - Brushed-Nickel, 48"
LVB-48-MCT-PC	32W	2240LM	30K/40K/50K - Polished-Chrome, 48"



LVC-24-MCT5-BN



LVC-36-MCT5-BN

MODEL LVC ARCHITECTURAL LED MULTI COLOR-TEMP. VANITY LIGHT W/ CUBE PC LENS, **120V**

CATALOG NO.	DESCRIPTION		
LVC-24-MCT5-BN	16W	1120LM	27K/30K/35K/40K/50K - Brushed Nickel 24"
LVC-36-MCT5-BN	24W	1680LM	27K/30K/35K/40K/50K - Brushed Nickel 36"

LVD-24-MCT5-BN

LVD-48-MCT5-BN

LVD-WS-MCT5-BN

MODEL LVD ARCHITECTURAL LED MULTI COLOR-TEMP. VANITY LIGHT WITH TUBE PC, **120V**

CATALOG NO.	DESCRIPTION		
LVD-24-MCT5-BN	16W	1300LM	27K/30K/35K/40K/50K - Brushed Nickel 24"
LVD-36-MCT5-BN	24W	2000LM	27K/30K/35K/40K/50K - Brushed Nickel 36"
LVD-48-MCT5-BN	32W	2700LM	27K/30K/35K/40K/50K - Brushed Nickel 48"
LVD-WS-MCT5-BN	16W	1360LM	27K/30K/35K/40K/50K - Brushed Nickel 14"

LVO-18-MCT5-BK

LVO-18-MCT5-BN



OVAL-BACK 360° MODERN VANITY LIGHT

CATALOG NO.	DESCRIPTION		
LVO-18-MCT5-BN	18W	1260LM	27K/30K/35K/40K/50K - Brushed Nickel 18"
LVO-18-MCT5-BK	18W	900LM	27K/30K/35K/40K/50K - Black 18"
LVO-24-MCT5-BN	24W	1680LM	27K/30K/35K/40K/50K - Brushed Nickel 24"
LVO-24-MCT5-BK	24W	1200LM	27K/30K/35K/40K/50K - Black 24"
LVO-36-MCT5-BN	36W	2520LM	27K/30K/35K/40K/50K - Brushed Nickel 36"
LVO-36-MCT5-BK	36W	1800LM	27K/30K/35K/40K/50K - Black 36"

LVE-36-MCT-BN

LVE-24-MCT-BN

MODEL LVE MULTI COLOR-TEMPERATURE VANITY LIGHT (3CCT), WITH PC LENS AND METAL RINGS, **120V, 277V OPTION**

CATALOG NO.	DESCRIPTION		
LVE-24-MCT-BN	17W	1760LM	3000K/3500K/4000K - Brushed Nickel 24"
LVE-36-MCT-BN	25W	2560LM	3000K/3500K/4000K - Brushed Nickel 36"
LVE-48-MCT-BN	34W	3500LM	3000K/3500K/4000K - Brushed Nickel 48"

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	277V OPTION	DESCRIPTION	ROCKER SWITCH OPTION	DESCRIPTION
ALL	OPT-277V	INTERNAL	OPT-VL-RS-BK	BOX
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

LVA-36-MCT5-BN

LVA-24-MCT5-BN

MODEL LVA ARCHITECTURAL LED DUAL GLASS MULTI COLOR-TEMP. VANITY LIGHT, **120V**

CATALOG NO.	DESCRIPTION		
LVA-24-MCT5-BN	20W	1400LM	27K/30K/35K/40K/50K - Brushed Nickel 24"
LVA-36-MCT5-BN	30W	2100LM	27K/30K/35K/40K/50K - Brushed Nickel 36"



LVG-24-MCT5-BN

LVG-36-MCT5-BN

MODEL LVG ARCHITECTURAL LED MULTI COLOR-TEMPERATURE VANITY LIGHT WITH SQUARE PC LENS **120V**

CATALOG NO.	DESCRIPTION		
LVG-24-MCT5-BN	18W	1300LM	27K/30K/35K/40K/50K - Brushed Nickel 24"
LVG-36-MCT5-BN	30W	2000LM	27K/30K/35K/40K/50K - Brushed Nickel 36"

LVJ-24-MCT5-BK

LVJ-18-MCT5-BK

LVJ-24-MCT5-BN

LVJ-18-MCT5-BN

SPEC SERIES WIDE PMMA LENS VANITY LIGHT, 5CCT

CATALOG NO.	DESCRIPTION		
LVJ-18-MCT5-BK	18W	1260LM	27K/30K/35K/40K/50K - Black 18"
LVJ-18-MCT5-BN	18W	1260LM	27K/30K/35K/40K/50K - Brushed Nickel 18"
LVJ-24-MCT5-BK	24W	1680LM	27K/30K/35K/40K/50K - Black 24"
LVJ-24-MCT5-BN	24W	1680LM	27K/30K/35K/40K/50K - Brushed Nickel 24"
LVJ-36-MCT5-BK	36W	2520LM	27K/30K/35K/40K/50K - Black 36"
LVJ-36-MCT5-BN	36W	2520LM	27K/30K/35K/40K/50K - Brushed Nickel 36"

LVP-24-MCT5-BK

LVP-24-MCT5-BN

PMMA LENS VANITY LIGHT, 5CCT **120V**

CATALOG NO.	DESCRIPTION		
LVP-18-MCT5-BK	20W	1400LM	27K/30K/35K/40K/50K - Black 18"
LVP-18-MCT5-BN	20W	1400LM	27K/30K/35K/40K/50K - Brushed Nickel 18"
LVP-24-MCT5-BK	25W	1800LM	27K/30K/35K/40K/50K - Black 24"
LVP-24-MCT5-BN	25W	1800LM	27K/30K/35K/40K/50K - Brushed Nickel 24"
LVP-36-MCT5-BK	30W	3000LM	27K/30K/35K/40K/50K - Black 36"
LVP-36-MCT5-BN	30W	3000LM	27K/30K/35K/40K/50K - Brushed Nickel 36"

LVS-36-BB



LVS-36-BK

LVS-36-BN

LVS-WS-21

SPEC SERIES SLIM ROTATABLE VANITY LIGHTS AND SONCES, **120V**

CATALOG NO.	DESCRIPTION		
LVS-24-MCT5-BN	20W	1400LM	27K/30K/35K/40K/50K - 24" Brushed Nickel
LVS-24-MCT5-BK	20W	1400LM	27K/30K/35K/40K/50K - 24" Black
LVS-24-MCT5-BB	20W	1400LM	27K/30K/35K/40K/50K - 24" Brushed Brass
LVS-36-MCT5-BN	30W	2100LM	27K/30K/35K/40K/50K - 36" Brushed Nickel
LVS-36-MCT5-BK	30W	2100LM	27K/30K/35K/40K/50K - 36" Black
LVS-36-MCT5-BB	30W	2100LM	27K/30K/35K/40K/50K - 36" Brushed Brass
LVS-48-MCT5-BN	40W	2800LM	27K/30K/35K/40K/50K - 48" Brushed Nickel
LVS-48-MCT5-BK	40W	2800LM	27K/30K/35K/40K/50K - 48" Black
LVS-48-MCT5-BB	40W	2800LM	27K/30K/35K/40K/50K - 48" Brushed Brass
LVS-WS-21-MCT5-BN	14W	980LM	27K/30K/35K/40K/50K - 21" Brushed Nickel
LVS-WS-21-MCT5-BK	14W	980LM	27K/30K/35K/40K/50K - 21" Black
LVS-WS-21-MCT5-BB	14W	980LM	27K/30K/35K/40K/50K - 21" Brushed Brass

DAMP LOCATIONS

VLM-E26-1L-BK

VLM-E26-2L-BK

VLM-E26-3L-BK

VLM-E26-4L-BK

E26 LAMP-READY VANITY LIGHT

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER
VLM-E26-1L-BK	Medium Base M Series Vanity Light 1-Lamp Black	
VLM-E26-2L-BK	Medium Base M Series Vanity Light 2-Lamp Black	
VLM-E26-3L-BK	Medium Base M Series Vanity Light 3-Lamp Black	
VLM-E26-4L-BK	Medium Base M Series Vanity Light 4-Lamp Black	
VLM-E26-1L-BN	Medium Base M Series Vanity Light 1-Lamp Bn	
VLM-E26-2L-BN	Medium Base M Series Vanity Light 2-Lamp Bn	
VLM-E26-3L-BN	Medium Base M Series Vanity Light 3-Lamp Bn	
VLM-E26-4L-BN	Medium Base M Series Vanity Light 4-Lamp Bn	

DAMP LOCATIONS

VLA-E26-2L-BK

VLA-E26-3L-BK

VLA-E26-4L-BK

E26 LAMP-READY VANITY LIGHT

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER
VLA-E26-2L-BK	Medium Base A Series Vanity Light 2-Lamp Black	
VLA-E26-3L-BK	Medium Base A Series Vanity Light 3-Lamp Black	
VLA-E26-4L-BK	Medium Base A Series Vanity Light 4-Lamp Black	
VLA-E26-2L-BN	Medium Base A Series Vanity Light 2-Lamp Bn	
VLA-E26-3L-BN	Medium Base A Series Vanity Light 3-Lamp Bn	
VLA-E26-4L-BN	Medium Base A Series Vanity Light 4-Lamp Bn	

INDUSTRIAL LIGHTING

UHXMAX SERIES

UHX-SR SERIES

UHXE SERIES

UHXF SERIES

UHL SERIES

LHB2 SERIES

RLB SERIES


RMS SERIES

SLRP SERIES

SLR SERIES

LLB SERIES

LLHC SERIES

LHCMAX SERIES

LHCX SERIES

LLHB-RGBWW SERIES

LLHB4 SERIES

LLHB SERIES

LLHBF SERIES

LIH SERIES

UHT SERIES

LVTT SERIES

LTPV SERIES

LVTE SERIES

VTA SERIES

VTA-RGBWW SERIES

VTU SERIES

LVTF SERIES

LLVT SERIES

LLVT SERIES

LRLVT SERIES

EXPF SERIES

EXPR SERIES

EXPL SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

UFO HIGH BAY

UHXMAX-WH

UHXMAX-BK

SENSOR-READY
PLUG & PLAY

WEC-3PR-78-AJ-WH
WEC-3PBT-78-AJ-WH

WEC-3RC



UHXMAX-ALR

UHXMAX-PCR

UHXMAX-SMB

UHXMAX-WG

UHXMAX-PCC

MAX-FEATURE UFO, SENSOR-READY POWER & CCT & DIGITAL BEAM ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
UHXMAX-70-150W-MCTPB-SR	70W/110W/150W	140LM/W	35K/40K/50K - Black	1
UHXMAX-70-150W-MCTPB-SR-WH	70W/110W/150W	140LM/W	35K/40K/50K - White	1
UHXMAX-120-200W-MCTPB-SR	120W/160W/200W	140LM/W	35K/40K/50K - Black	1
UHXMAX-120-200W-MCTPB-SR-WH	120W/160W/200W	140LM/W	35K/40K/50K - White	1
UHXMAX-180-240W-MCTPB-SR	180W/200W/240W	140LM/W	35K/40K/50K - Black	1
UHXMAX-180-240W-MCTPB-SR-WH	180W/200W/240W	140LM/W	35K/40K/50K - White	1
UHXMAX-200-300W-MCTP-SR	200W/240W/300W	140LM/W	35K/40K/50K - Black, 90° Fixed Beam	1
UHXMAX-SMB-A	UHXMAX 70-150W & 200-300W Surface-Mounting Bracket Black			
UHXMAX-SMB-A-WH	UHXMAX 70-150W & 200-300W Surface-Mounting Bracket White			
UHXMAX-SMB-B	UHXMAX 120-200W &180-240W Surface-Mounting Bracket Black			
UHXMAX-SMB-B-WH	UHXMAX 120-200W &180-240W Surface-Mounting Bracket White			
UHXMAX-PCR-A-90D	UHXMAX 70-150W 90D Pc Reflector			
UHXMAX-PCC-A	UHXMAX 70-150W Reflector Bottom Pc Cover			
UHXMAX-PCR-B-90D	UHXMAX 120-200W &180-240W 90D Pc Reflector			
UHXMAX-PCC-B	UHXMAX 120-200W &180-240W Reflector Bottom Pc Cover			
UHXMAX-ALR-A-90D	UHXMAX 70-150W 90D Aluminum Reflector			
UHXMAX-ALR-B-90D	UHXMAX 120-200W &180-240W 90D Aluminum Reflector			
UHXMAX-WG-A	UHXMAX 70-150W Wireguard			
UHXMAX-WG-B	UHXMAX 120-200W &180-240W Wireguard			
WEC-3PR-78-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level & RC (Optional RC WEC-3RC)			
WEC-3PBT-78-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level Bluetooth App Ready			

UHX-SR-BK

UHX-SR-WH

SENSOR-READY
PLUG & PLAY

WEC-3PR-72-TLB-WH

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

WEC-3RC

SPEC SERIES UFO HIGH BAY, SENSOR-READY

CATALOG NO.	DESCRIPTION			PCK QTY
UHX-150W-MP-40K-SR	50W/80W/100W/150W	140LM/W	4000K - Black	1
UHX-150W-MP-50K-SR	50W/80W/100W/150W	140LM/W	5000K - Black	1
UHX-G2-150W-MP-40K-SR	80W/100W/150W	180LM/W	4000K - Black	1
UHX-G2-150W-MP-50K-SR	80W/100W/150W	180LM/W	5000K - Black	1
UHX-230W-MP-40K-SR	100W/150W/200W/230W	140LM/W	4000K - Black	1
UHX-230W-MP-50K-SR	100W/150W/200W/230W	140LM/W	5000K - Black	1
UHX-G2-240W-MP-40K-SR	150W/200W/240W	175LM/W	4000K - Black	1
UHX-G2-240W-MP-50K-SR	150W/200W/240W	175LM/W	5000K - Black	1
UHX-300W-MP-50K-SR	150W/200W/230W/300W	140LM/W	5000K - Black	1
UHX-G2-320W-MP-50K-SR	200W/240W/320W	165LM/W	5000K - Black	1
UHX-G2-400W-MP-50K-SR	300W/350W/400W	165LM/W	5000K - Black	1
UHX-150W-MCTP-SR	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K - Black	1
UHX-150W-MCTP-WH-SR	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K - White	1
UHX-G2-150W-MCTPB-SR	80W/100W/150W	180LM/W	30K/40K/50K - Black	1
UHX-G2-150W-MCTPB-WH-SR	80W/100W/150W	180LM/W	30K/40K/50K - White	1
UHX-230W-MCTP-SR	100W/150W/200W/230W	130LM/W	30K/40K/50K/57K - Black	1
UHX-230W-MCTP-WH-SR	100W/150W/200W/230W	130LM/W	30K/40K/50K/57K - White	1
UHX-G2-240W-MCTPB-SR	150W/200W/240W	175LM/W	30K/40K/50K - Black	1
UHX-G2-240W-MCTPB-WH-SR	150W/200W/240W	175LM/W	30K/40K/50K - White	1
UHX-G2-320W-MCTPB-SR	200W/240W/320W	165LM/W	30K/40K/50K - Black	1
UHX-G2-320W-MCTPB-WH-SR	200W/240W/320W	165LM/W	30K/40K/50K - White	1
WEC-3MR-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Black, With Base (Optional Remote Control WEC-3RC)			
WEC-3MBT-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base (Optional Remote Control WEC-3RC)			
WEC-3PR-72-TLB-WH	600W Max, Zhaga 12-24VDC PIR Sensor, White, With Base (Optional Remote Control WEC-3RC)			

FOR FACTORY-INSTALLED OPTIONS AND ACCESSORIES SEE PAGE 317

UHX-MCTP-480V

UHX-MCTP-WH-480V

WHILE SUPPLIES LAST

SPEC SERIES NEW GENERATION - UFO HIGH BAY **480V** MADE TO ORDER

CATALOG NO.	DESCRIPTION			PCK QTY
UHX-230W-MP-50K-480V	100W/150W/200W/230W	160LM/W	5000K - Black	1
UHX-300W-MP-50K-480V	150W/200W/240W/300W	160LM/W	5000K - Black	1
UHX-150W-MCTP-WH-480V	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K - White	1
UHX-230W-MCTP-WH-480V	100W/150W/200W/230W	125LM/W	30K/40K/50K/57K - White	1

FOR FACTORY-INSTALLED OPTIONS AND ACCESSORIES SEE PAGE 317

UHX-BK

UHX-WH



UHX-ALR
UHX-ALRW

UHX-PCR

UHX-PCDC

UHX-FL

UHX-PCC

HB-EB-50
HB-EB-75

UHX-RING

UHX-SMB

UHX-SA-5075

UHX-WG

UHX-G2-REFL-AR

UHX-SC

SCL-GS210
SCL-GS220

SPEC SERIES NEW GENERATION - UFO HIGH BAY **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
UHX-150W-MP-40K*	50W/80W/100W/150W	140LM/W	4000K - Black	1
UHX-230W-MP-50K*	100W/150W/200W/230W	140LM/W	5000K - Black	1
UHX-150W-MCTP-WH*	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K - White	1
UHX-230W-MCTP-WH*	100W/150W/200W/230W	125LM/W	30K/40K/50K/57K - White	1
HB-RING	Highbay top ring adapter, 1/2in			
HB-EB-50/75	UFO top threaded hub expansion bushing from 1/2" to 3/4"			
UHX-SMB	Surface Mounting Yoke Bracket For 100W To 300W			
UHX-WG-A	Wire Guard, Fits On Fixtures 150W (MP & MCTP) & 230W (MP Only) & All G2-150W			
UHX-WG-B	Wire Guard, Fits On Fixtures 230W (MCTP Only) & 300W MP & All G2-240W			
UHX-ALR-A	60° Alum. Reflector For 150W (MP & MCTP) & 230W (MP Only)			
UHX-ALR-B	60° Alum. Reflector For 230W (MCTP Only) & 300W MP			

WHILE SUPPLIES LAST*

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION
UHX-G2-ALR-A	60° Alum. Reflector For G2-150W
UHX-G2-ALR-B	60° Alum. Reflector For G2-240W
UHX-ALRW-A	90° Alum. Reflector For 150W (MP & MCTP) & 230W (MP Only)
UHX-ALRW-B	90° Alum. Reflector For 230W (MCTP Only) & 300W MP
UHX-G2-ALRW-A	90° Alum. Reflector For G2-150W
UHX-G2-ALRW-B	Prismatic PC Reflector For G2-240W
UHX-PCR-A	Prismatic PC Reflector For 150W (MP & MCTP) & 230W (MP Only)
UHX-PCR-B	Prismatic PC Reflector For 230W (MCTP Only) & 300W MP
UHX-G2-PCR-A	Prismatic PC Reflector For G2-150W
UHX-G2-PCR-B	Prismatic PC Reflector For G2-240W
UHX-G2-PCR-C	Prismatic PC Reflector For G2-320W & 400W (NOT MCTPB)
UHX-G2-150W-REFL-AR	UHX-G2 150W Reflector Adapter For UHX-PCR-B
UHX-G2-240W-REFL-AR	UHX-G2 240W Reflector Adapter For UHX-PCR-B
UHX-PCDC	PC Drop Lens Cover For PC Reflectors (Not for Alum. Reflectors), Fits All Sizes
UHX-PCC	PC Bottom Cover For PC Reflectors (Not for Alum. Reflectors), Fits All Sizes
UHX-SC	Safety Cable
SCL-GS210	Heavy-Duty Adjustable 5/64" 10 Ft. Suspension Kit With Loop Gripper & Hook(1)
SCL-GS220	Heavy-Duty Adjustable 5/64" 20 Ft. Suspension Kit With Loop Gripper & Hook(1)
UHX-FL-A	Replacement Frosted PC Lens For UHX-150W-MP only
UHX-FL-B	Replacement Frosted PC Lens For UHX-150W-MCTP & UHX-230W-MP only
UHX-FL-C	Replacement Frosted PC Lens For 230W-MCTP & 300W
UHX-CL-A	Replacement Clear Lens For Up To 150W
UHX-CL-B	Replacement Clear Lens For 230W-MP (NOT FOR 230W-MCTP)
UHX-CL-C	Replacement Clear Lens For 230W-MCTP & 300W
UHX-SA-5075	1/2in Stem-mounting adapter with cable passage with 3/4in bushing

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL	OPT-EM-UHX	ON TOP

WIRE CABLE OPTION	DESCRIPTION
OPT-HBC-5WR-20FT-BK	5-WIRE CABLE

SENSOR	DESCRIPTION
OPT-SEN-UHX	MICROWAVE
OPT-SEN-NLS-UHX	WG NETWORK SENSOR
OPT-SEN-KEILTON-UHX	KEILTON NETWORK SENSOR

PLUG IN CORD	DESCRIPTION
OPT-HBC-125TL-BK	8FT, 15A, 125V,16/3TL,BLK
OPT-HBC-125TL-WH	8FT, 15A, 125V,16/3TL,WHT
OPT-HBC-277TL-BK	8FT, 15A, 277V,16/3TL,BLK
OPT-HBC-277TL-WH	8FT, 15A, 277V,16/3TL,WHT
OPT-HBC-125SB-BK	10FT, 15A, 125V,18/3STR,BLK
OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT

POWDER COATING
N/A

UHXE-80-150W-MCTP4-SR
UHXE-165-220W-MCTP4-SR

UHXE-165-220W-MCTP4-SR-WH

SHOWN WITH
UHXE-RPMB

HB-RING

UHX-SA-5075

SENSOR-READY
PLUG & PLAY

WEC-3RC

WEC-3PR-72-TLB-WH

HB-EB-50
HB-EB-75

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

SHOWN WITH
UHXE-RPMB

SHOWN WITH
UHXE-PCR-A-90D
UHXE-PCR-B-90D

SHOWN WITH
UHXE-PCR-A-60D
UHXE-PCR-B-60D

UHXE-PCC-A
UHXE-PCC-B

UHX-SC

BUILDER SERIES UFO HIGH BAY, SENSOR-READY 120-277V POWER AND CCT - ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
UHXE-80-150W-MCTP4-SR*	80W/110W/150W	140LM/W	30K/35K/40K/50K - Black	1
UHXE-165-220W-MCTP4-SR*	165W/190W/220W	140LM/W	30K/35K/40K/50K - Black	1
UHXE-165-220W-MCTP4-SR-WH*	165W/190W/220W	140LM/W	30K/35K/40K/50K - White	1
UHXE-SMB*	UHXE Surface Mounting U Bracket, Black			
UHXE-RPMB*	UHXE 1-FT Rigid Pipe Stand with Canopy for Hard Surface (not Swivel)			
UHXE-PCR-A-90D*	UHXE-80-150W 90-Degree PC Reflector			
UHXE-PCR-A-60D*	UHXE-80-150W 60-Degree PC Reflector			
UHXE-PCR-B-90D*	UHXE-165-220W 90-Degree PC Reflector			
UHXE-PCR-B-60D*	UHXE-165-220W 60-Degree PC Reflector			
UHXE-PCC-A*	UHXE-80-150W Bottom Cover For Pc Reflector, Fits Both 60D 90D			
UHXE-PCC-B*	UHXE-165-220W Bottom Cover For Pc Reflector, Fits Both 60D 90D			
HB-RING*	Highbay top ring adapter, 1/2in			
HB-EB-50/75*	UFO top threaded hub expansion bushing from 1/2" to 3/4"			
UHX-SC*	Safety Cable			
UHX-SA-5075*	1/2in Stem-mounting adapter with cable passage with 3/4in bushing			
WEC-3MR-72-TLB-BK*	600W Max, Zhaga 12-24VDC Microwave Sensor, Black, With Base (Optional Remote Control WEC-3RC)			
WEC-3MBT-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base (Optional Remote Control WEC-3RC)			
WEC-3PR-72-TLB-WH	600W Max, Zhaga 12-24VDC PIR Sensor, White, With Base (Optional Remote Control WEC-3RC)			

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL 120-277V	OPT-EM-UHXE	ON TOP
POWDER COATING		
N/A		
SENSOR		DESCRIPTION
SENSOR READY SEE ABOVE TABLE		

PLUG IN CORD	DESCRIPTION
OPT-HBC-125TL-BK	8FT, 15A, 125V,16/3TL,BLK
OPT-HBC-125TL-WH	8FT, 15A, 125V,16/3TL,WHT
OPT-HBC-277TL-BK	8FT, 15A, 277V,16/3TL,BLK
OPT-HBC-277TL-WH	8FT, 15A, 277V,16/3TL,WHT
OPT-HBC-125SB-BK	10FT, 15A, 125V,18/3STR,BLK
OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT

SENSOR-READY PLUG & PLAY
SEE PAGES 92-93

UHXF-100-150W-MCTP-SR

UHXF-150-240W-MCTP-SR

WeC-3RC

WEC-3PR-72-TLB-WH

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

IP69 UFO HIGH BAY FOR FOOD AND CHEMICAL FACILITIES SENSOR-READY

CATALOG NO.	DESCRIPTION			PCK QTY
UHXF-100-150W-MCTP-SR	100W/120W/150W	145LM/W	30K/40K/50K	1
UHXF-150-240W-MCTP-SR	150W/200W/240W	145LM/W	30K/40K/50K	1

UHL-100W-50K
UHL-150W-50K

ECONOMY HIGH BAY LAMP & SOCKET, ADJUSTABLE ANGLE (UFO ALTERNATIVE)

CATALOG NO.	DESCRIPTION			PCK QTY
UHL-100W-50K	100W	12000LM	5000K - Black	18
UHL-150W-50K	150W	18000LM	5000K - Black	8
ELB-23120-HH-AC-FLEX	20W MAX, 175VDC, LI-ION 4000MAH BATTERY			

LHB2-50W-50K

LHB2-50W-50K-WH

WHILE SUPPLIES LAST

HIGH LUMEN LED MINI HIGH BAY 120-277VAC PC REFLECTOR INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
LHB2-50W-50K-WH	50W	6750LM	5000K - 8-1/4" Dia X 5-1/2"(H), White	1
LHB2-50W-40K-WH	50W	6750LM	4000K - 8-1/4" Dia X 5-1/2"(H), White	1
LHB2-50W-30K-WH	50W	6750LM	3000K - 8-1/4" Dia X 5-1/2"(H), White	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL 120-277V	OPT-EM-LHB2	ULHB-HBMK
	POWDER COATING	
	N/A	

SENSOR	DESCRIPTION
OPT-SEN-ULHB	ULHB-SK
OPT-SEN-NLS-LHB2	WG NETWORK SENSOR
OPT-SEN-KEILTON-LHB2	KEILTON NETWORK SENSOR

PLUG IN CORD	DESCRIPTION
OPT-HBC-125TL-BK	8FT, 15A, 125V,16/3TL,BLK
OPT-HBC-125TL-WH	8FT, 15A, 125V,16/3TL,WHT
OPT-HBC-277TL-BK	8FT, 15A, 277V,16/3TL,BLK
OPT-HBC-277TL-WH	8FT, 15A, 277V,16/3TL,WHT
OPT-HBC-125SB-BK	10FT, 15A, 125V,18/3STR,BLK
OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT

RLB-80-120W-MCTP-BK

RLB-80-120W-MCTP-WH

LED ROUND LOW BAY 120-277VAC PC REFLECTOR INCLUDED

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
RLB-80-120W-MCTP-BK	80W/100W/120W	140LM/W	30K/40K/50K - Black	1
RLB-80-120W-MCTP-WH	80W/100W/120W	140LM/W	30K/40K/50K - White	1

RETROFIT STRIP

RMS-MCTP

MAGNETIC RETROFIT STRIP KIT WITH EXTENSION DRIVER POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
RMS-2FT-25W-MCTP	15W/20W/25W	140LM/W	27K/30K/35K/40K/50K - 2FT X 2	10
RMS-3FT-35W-MCTP	20W/28W/35W	140LM/W	27K/30K/35K/40K/50K - 3FT X 2	10
RMS-4FT-35W-MCTP	20W/28W/35W	140LM/W	27K/30K/35K/40K/50K - 4FT X 2	10
RMS-4FT3-40W-MCTP	20W/30W/40W	140LM/W	27K/30K/35K/40K/50K - 4FT X 3	10
RMS-4FT-46W-MCTP	30W/38W/46W	140LM/W	27K/30K/35K/40K/50K - 4FT X 2	10
RMS-4FT4-46W-MCTP	30W/38W/46W	140LM/W	27K/30K/35K/40K/50K - 4FT X 4	10
RMS-2FT-LENS	2FT X 2 Frosted Lens Kit For 2FT RMS Magnetic Retrofit Kit			
RMS-3FT-LENS	3FT X 2 Frosted Lens Kit For 3FT RMS Magnetic Retrofit Kit			
RMS-4FT-LENS	4FT X 2 Frosted Lens Kit For 4FT RMS Magnetic Retrofit Kit			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
ALL	OPT-EM-RMS	EXTERNAL BACK BOX	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

SLRP-4FT-20-40W-MCTP
SLRP-8FT-40-80W-MCTP

PREMIUM STRIP-LIGHT LED RETROFIT KIT WITH LENS

CATALOG NO.	DESCRIPTION			PCK QTY
SLRP-4FT-20-40W-MCTP	20W/30W/40W	127LM/W	35K/40K/50K	4
SLRP-8FT-40-80W-MCTP	40W/60W/80W	127LM/W	35K/40K/50K	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

EM CAPABLE

SLR-4FT-40W-50K-D

LED 4FT 2-LAMP STRIP RETROFIT KIT

CATALOG NO.	DESCRIPTION			PCK QTY
SLR-4FT-40W-50K-D	40W	4400LM	5000K - 4FT.	12

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL MODELS	**OPT-EM-SLR**	INTERNAL

POWDER COATING
N/A

PHOTOCELL	DESCRIPTION
N/A	N/A

SENSOR	DESCRIPTION
OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
OPT-SEN-NLS-SLR	WG NETWORK SENSOR
OPT-SEN-KEILTON-SLR	KEILTON NETWORK SENSOR
WEC-3RC	REMOTE CONTROL

LINEAR HIGH BAY

LLB-4FT-40W-MCTP-D

SHOWN WITH REFLECTOR

LLB-8FT-40W-MCTP-D

4FT LINEAR LOW BAY SELECTABLE CCT & POWER

CATALOG NO.	DESCRIPTION			PCK QTY
LLB-4FT-40W-MCTP-D	20W/30W/40W	150LM/W	35K/40K/50K	4
LLB-4FT-60W-MCTP-D	40W/50W/60W	150LM/W	35K/40K/50K	4
LLB-4FT-60W-MCTP-D-SEN	40W/50W/60W	150LM/W	35K/40K/50K	4
LLB-4FT-60W-MCTP-D-EM	40W/50W/60W	150LM/W	35K/40K/50K	4
LLB-4FT-80W-MCTP-D	60W/70W/80W	150LM/W	35K/40K/50K	4
LLB-4FT-REFL	LLB-4FT Reflector			

8FT LINEAR LOW BAY SELECTABLE CCT & POWER

CATALOG NO.	DESCRIPTION			PCK QTY
LLB-8FT-80W-MCTP-D	60W/70W/80W	150LM/W	35K/40K/50K	1
LLB-8FT-80W-MCTP-D-SEN	60W/70W/80W	150LM/W	35K/40K/50K	1
LLB-8FT-80W-MCTP-D-EM	60W/70W/80W	150LM/W	35K/40K/50K	1
LLB-8FT-120W-MCTP-D	80W/100W/120W	150LM/W	35K/40K/50K	1
LLB-8FT-160W-MCTP-D	120W/140W/160W	150LM/W	35K/40K/50K	1
LLB-8FT-REFL	LLB-8FT Reflector			

LLHC-80-150W-MCTP

ADJUSTABLE LENS



WIREGUARD

SENSOR-READY PLUG & PLAY
(ONE SENSOR PER FIXTURE)

WEC-3RC

WEC-3PR-72-TLB-WH

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

BUILDER SERIES COMPACT LINEAR HIGH BAY POWER & CCT - ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LLHC-80-150W-MCTP	80W/110W/150W	150LM/W	30K/35K/40K/50K - 10"(H) X 14 2/3"(W) X 1 8/9"(D)	1
LLHC-80-150W-MCTP-SR	80W/110W/150W	150LM/W	30K/35K/40K/50K	1
LLHC-165-220W-MCTP-SR	165W/190W/220W	150LM/W	30K/35K/40K/50K	1
LLHC-220-340W-MCTP-SR	220W/280W/340W	140LM/W	40K/50K	1
LLHC-340-430W-MCTP-SR	340W/390W/430W	140LM/W	40K/50K	1
LLHC-WG1	LLHC Wireguard for 150W			
LLHC-WG2	LLHC Wireguard for 220W			
WEC-3MR-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Black, With Base (Optional Remote Control WEC-3RC)			
WEC-3MBT-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base (Optional Remote Control WEC-3RC)			
WEC-3PR-72-TLB-WH	600W Max, Zhaga 12-24VDC PIR Sensor, White, With Base (Optional Remote Control WEC-3RC)			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PLUG IN CORD	DESCRIPTION
ALL	OPT-EM-LLHC	EXTERNAL	OPT-HBC-125TL-WH	8FT, 15A, 125V,WHITE
	POWDER COATING		OPT-HBC-277TL-WH	8FT, 15A, 277V,WHITE
	N/A		OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT
			480 OPTION	DESCRIPTION
			OPT-LLHC-480V	480V

LHCMAX-MCTPB-SR-BK

SENSOR-READY PLUG & PLAY
(ONE SENSOR PER FIXTURE)

WEC-3RC

WEC-3PR-72-TLB-WH

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

X-GENERATION DIGITAL BEAM ANGLE LINEAR HIGH BAY, SENSOR-READY POWER & CCT & BEAM ANGLE SELECTABLE

CATALOG NO.	DESCRIPTION		
LHCMAX-60-105W-MCTPB-SR-BK	60W/85W/105W	140LM/W	35K/40K/50K
LHCMAX-105-160W-MCTPB-SR-BK	105W/130W/160W	140LM/W	35K/40K/50K
LHCMAX-165-240W-MCTPB-SR-BK	165W/215W/240W	140LM/W	35K/40K/50K
LHCMAX-255-320W-MCTPB-SR-BK	255W/295W/320W	140LM/W	35K/40K/50K
WEC-3MR-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Black, With Base (Optional Remote Control WEC-3RC)		
WEC-3MBT-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base (Optional Remote Control WEC-3RC)		
WEC-3PR-72-TLB-WH	600W Max, Zhaga 12-24VDC PIR Sensor, White, With Base (Optional Remote Control WEC-3RC)		

SENSOR-READY
PLUG & PLAY

WEC-3RC

WEC-3PR-72-TLB-WH

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

LLHB4-MCTP
LLHB4-MP
(200W TO 500W)

LHCX LENS CHANGE



SHOWN WITH LIFEGUARD &
SURFACE-MOUNTING KIT

X-GENERATION COMPACT LINEAR HIGH BAY, SENSOR READY

CATALOG NO.	DESCRIPTION		
MCTP	**X-GENERATION COMPACT LINEAR HIGH BAY, SENSOR READY, POWER &CCT & BEAM ANGLE SELECTABLE**		
LHCX-80-155W-MCTPB-D-SR	80W/105W/155W	140LM/W	35K/40K/50K
LHCX-200-300W-MCTPB-D-SR	200W/240W/300W	140LM/W	35K/40K/50K
MCTP	**LINEAR HIGH BAY, SENSOR READY, POWER & CCT SELECTABLE, 90D X 90D LENS** LENS ACCESSORIES ARE NOT COMPATIBLE		
LHCX-110-150W-MCTP-SR	110W/130W/150W	140LM/W	35K/40K/50K - 14.17" X 11.00" X 1.77"
LHCX-165-215W-MCTP-SR	165W/180W/215W	140LM/W	35K/40K/50K - 1811" X 11.81" X 1.77"
LHCX-255-320W-MCTP-SR	255W/290W/320W	140LM/W	35K/40K/50K - 23.03" X 11.81" X 1.77"
MP	**LINEAR HIGH BAY, SENSOR READY, POWER SELECTABLE, 90D X 90D LENS** LENS ACCESSORIES ARE NOT COMPATIBLE		
LHCX-350-480W-MP-50K-D-SR	350W/400W/480W	160LM/W	5000K
LHCX-350-480W-MP-40K-D-SR	350W/400W/480W	160LM/W	4000K
LHCX-400-640W-MP-50K-D-SR	400W/500W/640W	160LM/W	5000K
LHCX-400-640W-MP-40K-D-SR	400W/500W/640W	160LM/W	4000K
LHCX-SMK	Surface-mounting Kit		
LHCX-WG1	Wireguard For 150W Max Model		

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION
LHCX-WG2	Wireguard For 215W Max Model
LHCX-WG3	Wireguard For 320W Max Model
LHCX-PM75	LHCX Pendant Mounting Accessory, 3/4in Hole On Top And Two 1/2in KO
LHCX-LENS-150W-45X90	LHCX 110-150W Size Special Narrow-Aisle Lens Kit 45Dx90D
LHCX-LENS-215W-45X90	LHCX 165-215W Size Special Narrow-Aisle Lens Kit 45Dx90D
LHCX-LENS-320W-45X90	LHCX 255-320W Size Special Narrow-Aisle Lens Kit 45Dx90D
LHCX-LENS-150W-110X110	LHCX 110-150W Size Special Wide-Angle Lens Kit 110Dx110D
LHCX-LENS-215W-110X110	LHCX 165-215W Size Special Wide-Angle Lens Kit 110Dx110D
LHCX-LENS-320W-110X110	LHCX 255-320W Size Special Wide-Angle Lens Kit 110Dx110D
LHCX-LENS-150W-65X65	LHCX 110-150W Size Special Medium-Angle Lens Kit 65Dx65D
LHCX-LENS-215W-65X65	LHCX 165-215W Size Special Medium-Angle Lens Kit 65Dx65D
LHCX-LENS-320W-65X65	LHCX 255-320W Size Special Medium-Angle Lens Kit 65Dx65D
WEC-3MR-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Black, With Base (Optional Remote Control WEC-3RC)
WEC-3MBT-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base (Optional Remote Control WEC-3RC)
WEC-3PR-72-TLB-WH	600W Max, Zhaga 12-24VDC PIR Sensor, White, With Base (Optional Remote Control WEC-3RC)

LHCX-RODKIT-A	Rod Kit With Canopy For LHCX Up To 215W
LHCX-RODKIT-B	Rodkit With Canopy For LHCX For 200W And Larger
LHCX-SMK-480V	LHCX Surface Mounting Kit For LHCX-480V

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
ALL	OPT-EM-LHCX-150	EM	N/A	N/A
	OPT-EM-LHCX-215	EM	480V OPTION	DESCRIPTION
	OPT-EM-LHCX-320	EM	OPT-LHCX-480V	480V

LLHB-120W-RGBWW-D-BT

RGBW + 3CCT LED LINEAR HIGH BAY, FIXTURE HANGERS INCL., SUSPENSION CABLE NOT INCL.

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
LLHB-120W-RGBWW-D-BT	120W	120LM/W		RGBW	1
LLHB-200W-RGBWW-D-BT	200W	120LM/W		RGBW	1
LLHB-RGBWW-RC	120W RGB And 3CCT Linear High Bay 120-277V 0-10V Smart App & RC				
LLHB-RGBWW-SMK	200W RGB And 3CCT Linear High Bay 120-277V 0-10V Smart App & RC				
LLHB-RGBW-PMB	Remote Control For LLHB-RGBWW				

LLHB4-MCTP
LLHB4-MP
(200W TO 500W)

LLHB4-50W
LLHB4-MP
(100W TO 150W)

LLHB4-MCTP-BK

LLHB4-100W-WG
LLHB4-150W-WG

OPT-LLHB4-SMK



LLHB4-RODKIT

SENSOR-READY
PLUG & PLAY

WEC-3RC

WEC-3PR-78-AJ-WH
WEC-3PBT-78-AJ-WH

SPEC SERIES 4TH GENERATION OF LINEAR HIGH BAY, SENSOR READY 120-277V/480V

CATALOG NO.	DESCRIPTION			PCK QTY
4TH GENERATION OF LINEAR HIGH BAYS 120-277V SENSOR READY				
LLHB4-50W-40K-D-SR	50W	125LM/W	4000K	1
LLHB4-50W-50K-D-SR	50W	125LM/W	5000K	1
MP POWER ADJUSTABLE 4TH GENERATION OF LINEAR HIGH BAYS 120-277V SENSOR READY				
LLHB4-100W-MP-40K-D-SR	50W/80W/100W	125LM/W	4000K	1
LLHB4-100W-MP-50K-D-SR	50W/80W/100W	125LM/W	5000K	1
LLHB4-150W-MP-40K-D-SR	80W/110W/150W	125LM/W	4000K	1
LLHB4-150W-MP-50K-D-SR	80W/110W/150W	125LM/W	5000K	1
LLHB4-200W-MP-40K-D-SR	100W/150W/200W	125LM/W	4000K	1
LLHB4-200W-MP-50K-D-SR	100W/150W/200W	125LM/W	5000K	1
LLHB4-300W-MP-40K-D-SR	150W/225W/300W	125LM/W	4000K	1
LLHB4-300W-MP-50K-D-SR	150W/225W/300W	125LM/W	5000K	1
LLHB4-410W-MP-50K-D-SR	200W/300W/410W	125LM/W	5000K	1
LLHB4-500W-MP-50K-D-SR	250W/400W/500W	125LM/W	5000K	1
MCTP POWER & CCT ADJUSTABLE 4TH GENERATION OF LINEAR HIGH BAYS 120-277V SENSOR READY				
LLHB4-80-150W-MCTP-SR	80W/110W/150W	125LM/W	35K/40K/50K	1
LLHB4-80-150W-MCTP-SR-BK	80W/110W/150W	125LM/W	35K/40K/50K	1
4TH GENERATION OF LINEAR HIGH BAYS 480V SENSOR READY				
LLHB4-50W-40K-D-SR-480V	50W	125LM/W	4000K	1
LLHB4-50W-50K-D-SR-480V	50W	125LM/W	5000K	1
MP POWER ADJUSTABLE 4TH GENERATION OF LINEAR HIGH BAYS 480V SENSOR READY				
LLHB4-100W-MP-40K-D-SR-480V	50W/80W/100W	125LM/W	4000K	1
LLHB4-100W-MP-50K-D-SR-480V	50W/80W/100W	125LM/W	5000K	1
LLHB4-150W-MP-40K-D-SR-480V	80W/110W/150W	125LM/W	4000K	1
LLHB4-150W-MP-50K-D-SR-480V	80W/110W/150W	125LM/W	5000K	1
LLHB4-200W-MP-40K-D-SR-480V	100W/150W/200W	125LM/W	4000K	1
LLHB4-200W-MP-50K-D-SR-480V	100W/150W/200W	125LM/W	5000K	1
LLHB4-300W-MP-40K-D-SR-480V	150W/225W/300W	125LM/W	4000K	1
LLHB4-300W-MP-50K-D-SR-480V	150W/225W/300W	125LM/W	5000K	1
LLHB4-410W-MP-50K-D-SR-480V	200W/300W/410W	125LM/W	5000K	1
LLHB4-500W-MP-50K-D-SR-480V	250W/400W/500W	125LM/W	5000K	1
MCTP POWER & CCT ADJUSTABLE 4TH GENERATION OF LINEAR HIGH BAYS 480V SENSOR READY				
LLHB4-80-150W-MCTP-SR-480V	80W/110W/150W	125LM/W	35K/40K/50K	1
LLHB4-80-150W-MCTP-SR-BK-480V	80W/110W/150W	125LM/W	35K/40K/50K	1
LLHB4-100W-WG	Wire Guard for 100W			
LLHB4-150W-WG	Wire Guard for 150W			
LLHB4-RODKIT	Rod kit 3-1/4" Dia X 40" H and 1/2" Thread			

FOR FACTORY-INSTALLED OPTIONS AND ACCESSORIES SEE PAGE 331

EM CAPABLE

LLHB4-MCTP
LLHB4-MP
(200W TO 500W)



LLHB4-MP
(100W TO 150W)

LLHB4-100W-WG
LLHB4-150W-WG



LLHB4-RODKIT

OPT-LLHB4-SMK

WHILE SUPPLIES LAST

SPEC SERIES 4TH GENERATION OF LINEAR HIGH BAY 120-277V/480V

CATALOG NO.	DESCRIPTION			PCK QTY
MCTP	**POWER & CCT ADJUSTABLE 4TH GENERATION OF LINEAR HIGH BAYS 120-277V**			
LLHB4-80-150W-MCTP	80W/110W/150W	125LM/W	35K/40K/50K	1
MP	**POWER ADJUSTABLE 4TH GENERATION OF LINEAR HIGH BAYS 120-277V**			
LLHB4-100W-MP-40K-D	50W/80W/100W	125LM/W	4000K - 2FT. X 13.77	1
LLHB4-100W-MP-50K-D	50W/80W/100W	125LM/W	5000K - 2FT. X 13.77	1
LLHB4-150W-MP-40K-D	80W/110W/150W	125LM/W	4000K - 2FT. X 17.75	1
LLHB4-150W-MP-50K-D	80W/110W/150W	125LM/W	5000K - 2FT. X 17.75	1
LLHB4-300W-MP-40K-D	150W/225W/300W	125LM/W	4000K - 4FT. X 17.75	1
LLHB4-300W-MP-50K-D	150W/225W/300W	125LM/W	5000K - 4FT. X 17.75	1
LLHB4-410W-MP-50K-D	200W/300W/410W	125LM/W	5000K - 4FT. X 23.20	1
MCTP	**POWER & CCT ADJUSTABLE 4TH GENERATION OF LINEAR HIGH BAYS 480V 7 DAYS LEAD TIME**			
LLHB4-80-150W-MCTP-480V	80W/110W/150W	125LM/W	35K/40K/50K	1
MP	**POWER ADJUSTABLE 4TH GENERATION OF LINEAR HIGH BAYS 480V 7 DAYS LEAD TIME**			
LLHB4-100W-MP-40K-D-480V	50W/80W/100W	125LM/W	4000K - 2FT. X 13.77	1
LLHB4-100W-MP-50K-D-480V	50W/80W/100W	125LM/W	5000K - 2FT. X 13.77	1
LLHB4-150W-MP-40K-D-480V	80W/110W/150W	125LM/W	4000K - 2FT. X 17.75	1
LLHB4-150W-MP-50K-D-480V	80W/110W/150W	125LM/W	5000K - 2FT. X 17.75	1
LLHB4-300W-MP-40K-D-480V	150W/225W/300W	125LM/W	4000K - 4FT. X 17.75	1
LLHB4-300W-MP-50K-D-480V	150W/225W/300W	125LM/W	5000K - 4FT. X 17.75	1
LLHB4-410W-MP-50K-D-480V	200W/300W/410W	125LM/W	5000K - 4FT. X 23.20	1
LLHB4-100W-WG	Wire Guard for 100W			
LLHB4-150W-WG	Wire Guard for 150W			
LLHB4-RODKIT	Rod kit 3-1/4" Dia X 40" H and 1/2" Thread			

*PER INDUSTRY STANDARDS, LUMENS ARE REPORTED WITHOUT FROSTED LENS (REMOVABLE)

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
50W TO 150W	OPT-EM-LLHB4-50-150	EXTERNAL
200W TO 500W	OPT-EM-LLHB4-200-500	INTERNAL

SURGE PROTECTOR	DESCRIPTION
OPT-SP-10KV	120-277V
OPT-SP-10KV-480V	480V

SURF. OPTION
OPT-LLHB4-SMK

FLEX WHIP
OPT-FWH-63
OPT-FWH-65
OPT-FWH-66

UP LIGHT	DESCRIPTION
OPT-LLHB-ULM-2FT-20W	150W & ABOVE
OPT-LLHB-ULM-2FT-40W	150W & ABOVE
OPT-LLHB-ULM-4FT-40W	500W & ABOVE
OPT-LLHB-ULM-4FT-60W	500W & ABOVE

SENSOR	DESCRIPTION
OPT-SEN-LLHB4	MICROWAVE BI-LEVEL SENSOR
OPT-SEN-NLS-LLHB4	WG NETWORK SENSOR
OPT-SEN-KEILTON-LLHB4	KEILTON NETWORK SENSOR

PLUG IN CORD	DESCRIPTION
OPT-HBC-125TL-WH	8FT, 15A, 125V,WHITE
OPT-HBC-277TL-WH	8FT, 15A, 277V,WHITE
OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT

Sensor-Ready
Plug & Play

LLHB-MP-D-SR
LLHB-MP-D-SR-480V

LED LINEAR HIGH BAY, SENSOR-READY FIXTURE HANGERS INCLUDED, SUSPENSION CABLE NOT INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
4-FOOT LED LINEAR HIGH BAY 120-277V SENSOR-READY				
LLHB-60-120W-MP-40K-D-SR	60W/90W/120W	135LM/W	4000K	1
LLHB-60-120W-MP-50K-D-SR	60W/90W/120W	135LM/W	5000K	1
LLHB-90-180W-MP-40K-D-SR	90W/135W/180W	135LM/W	4000K	1
LLHB-90-180W-MP-50K-D-SR	90W/135W/180W	135LM/W	5000K	1
LLHB-120-240W-MP-40K-D-SR	120W/180W/240W	135LM/W	4000K	1
LLHB-120-240W-MP-50K-D-SR	120W/180W/240W	135LM/W	5000K	1
4-FOOT LED LINEAR HIGH BAY 480V SENSOR-READY				
LLHB-60-120W-MP-40K-D-SR-480V	60W/90W/120W	135LM/W	4000K	1
LLHB-60-120W-MP-50K-D-SR-480V	60W/90W/120W	135LM/W	5000K	1
LLHB-90-180W-MP-40K-D-SR-480V	90W/135W/180W	135LM/W	4000K	1
LLHB-90-180W-MP-50K-D-SR-480V	90W/135W/180W	135LM/W	5000K	1
LLHB-120-240W-MP-40K-D-SR-480V	120W/180W/240W	135LM/W	4000K	1
LLHB-120-240W-MP-50K-D-SR-480V	120W/180W/240W	135LM/W	5000K	1

LLHB4-D
LLHB4-D-480V

LED LINEAR HIGH BAY FIXTURE HANGERS INCLUDED, SUSPENSION CABLE NOT INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
LED LINEAR HIGH BAY 120-277V				
LLHB-120W-40K-D	100W	15500LM	4000K - Frosted lens, 4FTx11-1/4"	1
LLHB-180W-40K-D	150W	23250LM	4000K - Frosted lens, 4FTx15-7/8"	1
LLHB-240W-MP-50K-D	240W Max.	150LM/W	5000K - Frosted lens, 4FTx20-1/2"	1
LLHB-240W-MP-40K-D	240W Max.	150LM/W	4000K - Frosted lens, 4FTx20-1/2"	1
LED LINEAR HIGH BAY 480V 7 DAYS LEAD TIME				
LLHB-120W-50K-D-480V	100W	15500LM	5000K - Frosted lens, 4FTx11-1/4"	1
LLHB-120W-40K-D-480V	100W	15500LM	4000K - Frosted lens, 4FTx11-1/4"	1
LLHB-180W-50K-D-480V	150W	23250LM	5000K - Frosted lens, 4FTx15-7/8"	1
LLHB-180W-40K-D-480V	150W	23250LM	4000K - Frosted lens, 4FTx15-7/8"	1

*PER INDUSTRY STANDARDS, LUMENS ARE REPORTED WITHOUT FROSTED LENS (REMOVABLE)

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
ALL MODELS	OPT-EM-LLHB	MOUNTED ON TOP
	FLEX WHIP	DESCRIPTION
	OPT-FWH-63	6FT 3-Wire Whip
	OPT-FWH-65	6FT 5-Wire Whip
	OPT-FWH-66	6FT 6-Wire Whip
	POWDER COATING	
	OPT-CLR-95(BK/GR/SR/WH)	
	SURF. OPTION	
	OPT-LLHB-SMK	
	SURGE PROTECTOR	
	OPT-SP-10KV	

CLEAR LENS	DESCRIPTION
OPT-LLHB-CL-120/180	120W & 180W
OPT-LLHB-CL-240	240W
UP LIGHT	DESCRIPTION
OPT-LLHB-ULM-4FT-40W	500W & ABOVE
OPT-LLHB-ULM-4FT-60W	500W & ABOVE
PLUG IN CORD	DESCRIPTION
OPT-HBC-125TL-WH	8FT, 15A, 125V,WHITE
OPT-HBC-277TL-WH	8FT, 15A, 277V,WHITE
OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT
SENSOR	DESCRIPTION
OPT-2P-58	PIR SENSOR (Not remote capable)
OPT-SEN-3MR-4-WH	SENSOR
OPT-SEN-NLS-LLHB	WG NETWORK SENSOR
OPT-SEN-KEILTON-LLHB	KEILTON NETWORK SENSOR
WEC-8RC	OPTIONAL REMOTE

LLHB4-50W-40K-D

WHILE SUPPLIES LAST

SPEC SERIES 4TH GENERATION OF LINEAR HIGH BAYS 120-277V

CATALOG NO.	DESCRIPTION			PCK QTY
LLHB4-50W-40K-D	50W	7750LM	4000K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	UP LIGHT	DESCRIPTION
50W TO 150W	OPT-EM-LLHB4-50-150	EXTERNAL	OPT-LLHB-ULM-2FT-20W	150W & ABOVE
200W TO 500W	OPT-EM-LLHB4-200-500	INTERNAL	OPT-LLHB-ULM-2FT-40W	150W & ABOVE
	SURGE PROTECTOR	DESCRIPTION	OPT-LLHB-ULM-4FT-40W	500W & ABOVE
	OPT-SP-10KV	120-277V	OPT-LLHB-ULM-4FT-60W	500W & ABOVE
	OPT-SP-10KV-480V	480V		
	SURF. OPTION		SENSOR	DESCRIPTION
	OPT-LLHB4-SMK		OPT-SEN-LLHB4	MICROWAVE BI-LEVEL SENSOR
	FLEX WHIP		OPT-SEN-NLS-LLHB4	WG NETWORK SENSOR
	OPT-FWH-63		OPT-SEN-KEILTON-LLHB4	KEILTON NETWORK SENSOR
	OPT-FWH-65		PLUG IN CORD	DESCRIPTION
	OPT-FWH-66		OPT-HBC-125TL-WH	8FT, 15A, 125V,WHITE

ELB-2048-EXTR

H-SCREW

CH-1010
CH-1212

SCL-GSY10
SCL-GSY20

LED LINEAR HIGH BAY ACCESSORIES

CATALOG NO.	DESCRIPTION
ELB-2048-EXTR	Field-installed emergency driver, Input voltage: 100~277AC, Output voltage: 12V~48VDC, Output power: 20W (Max), Emergency operation: ≥90 mins., Recharge: 24 Hrs.
CH-1212	Steel jack chain, 100ft., 12GA, (Meets weight requirements for Linear High Bays)
CH-1010	Steel jack chain, 100ft., 10GA
SCL-GSY10	Adjustable 10 Ft. 1/16", 1.5mm SusPension Kit With Y-Connector & Loop Grip & Hooks(2)
SCL-GSY20	Adjustable 20 Ft. 1/16", 1.5mm SusPension Kit With Y-Connector & Loop Grip & Hooks(2)
H-SCREW	Steel flat hanger screw with single hole, 1/4" x 3"

SENSOR-READY PLUG & PLAY
(ONE SENSOR PER FIXTURE)

WEC-3RC

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

WEC-3PR-72-TLB-WH

LLHBF-80-160W
LLHBF-120-200W

LLHBF-60-105W
LLHBF-105-150W
LLHBF-130-200W
LLHBF-255-300W

LED LINEAR HIGH BAY ACCESSORIES

CATALOG NO.	DESCRIPTION			PCK QTY
LLHBF-60-105W-MCTP-SR	60W/85W/105W	150LM/W	40K/45K/50K	1
LLHBF-80-160W-MCTP-SR	80W/120W/160W	150LM/W	40K/45K/50K	1
LLHBF-105-150W-MCTP-SR	105W/130W/150W	150LM/W	40K/45K/50K	1
LLHBF-120-200W-MCTP-SR	120W/160W/200W	150LM/W	40K/45K/50K	1
LLHBF-130-200W-MCTP-SR	130W/165W/200W	150LM/W	40K/45K/50K	1
LLHBF-255-300W-MCTP-SR	255W/280W/300W	150LM/W	40K/45K/50K	1
WEC-3MR-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Black, With Base (Optional Remote Control WEC-3RC)			
WEC-3MBT-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base (Optional Remote Control WEC-3RC)			
WEC-3PR-72-TLB-WH	600W Max, Zhaga 12-24VDC PIR Sensor, White, With Base (Optional Remote Control WEC-3RC)			

Shown with LIH-SUSKIT

Shown with LIH-SMA

Shown with LIH-YK

Shown with LIH-SH1

NATATORIUM INDIRECT HIGH BAY, ADJUSTABLE LENSES

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
LIH-1S-300W-50K-43D	300W	46070LM	5000K	1
LIH-2S-600W-50K-43D	600W	81930LM	5000K	1
LIH-SUSKIT	LIH Series Suspension Chain Kit			
LIH-YK	LIH Series Yoke-Mounting Kit			
LIH-SMA	LIH Series 3/4in Stem-Mounting Adapter			
LIH-SH1	LIH Series Short Glare Shield			

UHT-200W-50K-480V

Shown with UHT-PAIR-KIT

HIGH-TEMP IP66 HIGH BAY, 158°F 480V, MADE TO ORDER

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER	
UHT-200W-50K-480V	200W	32000LM	5000K
UHT-PAIR-KIT	Twin Paring Kit With Jbox To Attach Two UHT Fixtures		

VAPOR LIGHTS

LVTT-2FT-15-30W-MCTP-SR

LVTT-4FT-30-60W-MCTP-SR

LVTT-8FT-60-120W-MCTP-SR

TUBE VAPOR TIGHT - SELECTABLE POWER & CCT - SENSOR-READY

CATALOG NO.	DESCRIPTION		
LVTT-2FT-15-30W-MCTP-SR	15W/20W/25W/30W	130LM/W	35K/40K/50K
LVTT-4FT-30-60W-MCTP-SR	30W/40W/50W/60W	130LM/W	35K/40K/50K
LVTT-8FT-60-120W-MCTP-SR	60W/80W/100W/120W	130LM/W	35K/40K/50K
LVTT-JUMP-6FT	LVTT Jumper Cable With Connectors On Both Ends 6FT		
LVTT-JUMP-12FT	LVTT Jumper Cable With Connectors On Both Ends 12FT		
LVTT-PTAIL-6FT	LVTT Pigtail Power Cable With Connector On One End 6FT		
LVTT-PTAIL-12FT	LVTT Pigtail Power Cable With Connector On One End 12FT		
LVTT-SMK	LVTT Surface-Mounting Kit With Two Brackets		

LTPV-MCTP-D



LTPV-SLC

LTPV-EC-SR

LTVP-SLC-SR

SENSOR-READY PLUG & PLAY
(ONE SENSOR PER FIXTURE)

WEC-3RC

WEC-3PR-72-TLB-WH

WEC-3MR-72-TLB-BK
WEC-3MBT-72-TLB-BK

BUILDER SERIES MODULAR LINEAR VAPOR LIGHT, QUICK CONNECT, TRI-PROOF: WATER, DUST & IMPACT RESISTANCE

CATALOG NO.	DESCRIPTION			PCK QTY
LTPV-2FT-18W-MCTP-D	10W/15W/18W	130LM/W	30K/40K/50K	9
LTPV-4FT-36W-MCTP-D	20W/28W/36W	130LM/W	30K/40K/50K	9
LTPV-8FT-70W-MCTP-D	55W/60W/70W	140LM/W	30K/40K/50K	9
LTPV-SLC	LTPV Seamless Coupling Channel With Connection Cable			10
LTPV-SLC-SR	LTPV Seamless Coupling Channel Sensor-Ready			10
LTPV-EC-SR	LTPV Sensor-Ready Endcap			10
WEC-3MR-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Black, With Base (Optional Remote Control WEC-3RC)			
WEC-3MBT-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base (Optional Remote Control WEC-3RC)			
WEC-3PR-72-TLB-WH	600W Max, Zhaga 12-24VDC PIR Sensor, White, With Base (Optional Remote Control WEC-3RC)			

LVTE-8FT

LLVT-8FT

LVTE-2FT

LVTE-4FT



LVTE-4FT-JBOX-MB

LVTE-4FT-JBOX-MB-IP65



LVTE-4FT-45D-MBK

LVTE-4FT-TP-MBK

LVTE-4FT-100-135W-MCTP

LVTE-4FT-PVMBK

NEMA 4X BUILDER SERIES LINEAR VAPOR-TIGHT FIXTURES CCT & WATTAGE SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
LVTE-2FT-15-25W-MCTP	15W/17W/20W/25W	140LM/W	35K/40K/50K - 4.25"	4
LVTE-4FT-20-35W-MCTP	20W/28W/35W	140LM/W	35K/40K/50K - 4.25"	4
LVTE-4FT-30-46W-MCTP	30W/38W/46W	140LM/W	35K/40K/50K - 4.25"	4
LVTE-4FT-30-60W-MCTP	30W/45W/60W	140LM/W	35K/40K/50K - 4.25"	4
LVTE-8FT-45-65W-MCTP	45W/55W/65W	140LM/W	35K/40K/50K - 4.25"	1
LVTE-8FT-65-110W-MCTP	65W/75W/90W/110W	140LM/W	35K/40K/50K - 4.25"	1
LVTE-4FT-100-135W-MCTP	100W/120W/135W	150LM/W	35K/40K/50K	1
LVTE-4FT-150-200W-MCTP	150W/175W/200W	150LM/W	35K/40K/50K	1
LVTE-4FT-200-245W-MCTP	200W/230W/245W	150LM/W	35K/40K/50K	1
BUILDER SERIES LINEAR VAPOR-TIGHT FIXTURES WITH SENSOR & EMERGENCY BACKUP CCT & WATTAGE SELECTABLE				
LVTE-2FT-15-25W-MCTP-EM-SEN	15W/17W/20W/25W	140LM/W	35K/40K/50K	4
LVTE-4FT-20-35W-MCTP-EM-SEN	20W/28W/35W	140LM/W	35K/40K/50K	4
LVTE-4FT-30-46W-MCTP-EM-SEN	30W/38W/46W	140LM/W	35K/40K/50K	4
LVTE-4FT-30-60W-MCTP-EM-SEN	30W/45W/60W	140LM/W	35K/40K/50K	4
LVTE-8FT-45-65W-MCTP-EM-SEN	45W/55W/65W	140LM/W	35K/40K/50K	1
LVTE-8FT-65-110W-MCTP-EM-SEN	65W/75W/90W/110W	140LM/W	35K/40K/50K	1
LVTE-4FT-100-135W-MCTP-EM-SEN	100W/120W/135W	150LM/W	35K/40K/50K	1
LVTE-4FT-150-200W-MCTP-EM-SEN	150W/175W/200W	150LM/W	35K/40K/50K	1
LVTE-4FT-200-245W-MCTP-EM-SEN	200W/230W/245W	150LM/W	35K/40K/50K	1
LVTE ACCESSORIES				
LVTE-4FT-45D-MBK	LVTE Corner Mounting Bracket Kit - Set Of Two - Use 2 Sets For 8Ft			
LVTE-4FT-JBOX-MB	LVTE Mounting Bracket For Junction Box Connection - Use 2 For 8Ft			
LVTE-4FT-JBOX-MB-IP65	LVTE Waterproof Mounting Bracket For Junction Box - Use 2 For 8Ft			
LVTE-4FT-TP-MBK	LVTE Tamper-Proof Mounting Bracket Kit - Set Of Two - Use 2 Sets For 8Ft			
LVTE-4FT-PVMBK	LVTE Adjustable Pivot Mounting Bracket Kit - Set Of Two - Use 2 Sets For 8Ft			
4.75" WIDE LED LINEAR VAPOR LIGHT				
LLVT-8FT-65W-50K-D	65W	8450LM	5000K	1
LLVT-8FT-100W-40K-D	100W	13000LM	4000K	1

VTA-15-30W-MCTP



ADJUSTABLE ANGLE

HIGH-OUTPUT DUAL-SELECTABLE VAPOR-TIGHT WITH ADJUSTABLE ANGLE

CATALOG NO.	DESCRIPTION		
VTA-15-30W-MCTP	15W/20W/30W	110LM/W	30K/40K/50K



VTA-12-20W-RGBWW-P

RGBW SWITCH SELECT VAPOR-TIGHT WITH ADJUSTABLE ANGLE W/ PHOTOCELL

CATALOG NO.	DESCRIPTION		
VTA-12-20W-RGBWW-P	12W/16W/20W	100LM/W	RGBW



VTU-12W
VTU-20W

LED UNIVERSAL VAPOR LIGHTS **120-277V**, IP65 NEMA 3R ALL MOUNTING OPTIONS IN ONE BOX

CATALOG NO.	DESCRIPTION		
VTU-12W-30K	12W	840LM	3000K
VTU-12W-50K	12W	900LM	5000K
VTU-20W-30K	20W	1685LM	3000K
VTU-20W-50K	20W	1785LM	5000K

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
ALL	OPT-EM-VTU	INTERNAL	OPT-PC-B	BUTTON
	POWDER COATING		SENSOR	DESCRIPTION
	OPT-CLR-85(BK/GR/SR/WH)		OPT-SEN-3MRLV-5	PROGRAMMABLE MICROWAVE BI-LEVEL
			OPT-SEN-NLS-VTU	WG NETWORK SENSOR
			OPT-SEN-KEILTON-VTU	KEILTON NETWORK SENSOR
			WEC-8RC	REMOTE CONTROL

LVTF-4FT-30-60W-MCTP

4FT FIBERGLASS VAPOR TIGHT, IP67 NSF, DLC FOR STAIRWAY PASSAGEWAY

CATALOG NO.	DESCRIPTION		
LVTF-4FT-30-60W-MCTP	30W/45W/60W	140LM/W	35K/40K/50K

LLVT-2FT-25W-MCTP-D

LLVT-4FT-40W-MCTP-D
LLVT-4FT-75W-MCTP-D

LED TRADITIONAL LINEAR VAPOR LIGHT **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
6-1/4" WIDE POLYCARBONATE LED LINEAR VAPOR LIGHT				
LLVT-2FT-25W-MCTP-D	15W/20W/25W	130LM/W	35K/40K/50K	6
LLVT-2FT-RL	2FT REPLACEMENT LENS			
6-3/4" WIDE POLYCARBONATE LED LINEAR VAPOR LIGHT				
LLVT-4FT-40W-MCTP-D	20W/30W/40W	130LM/W	35K/40K/50K	6
LLVT-4FT-75W-MCTP-D	40W/60W/75W	130LM/W	35K/40K/50K	6

LLVT-4FT-100W-MCTP-D
LLVT-4FT-150W-MCTP-D
LLVT-4FT-200W-MCTP-D

LED LINEAR VAPOR LIGHT **100-150W**

CATALOG NO.	DESCRIPTION			PCK QTY
LLVT-4FT-100W-MCTP-D	50W/80W/100W	130LM/W	35K/40K/50K - 52" X 14.5"	1
LLVT-4FT-150W-MCTP-D	80/110/150W	130LM/W	35K/40K/50K - 52" X 14.5"	1
LLVT-4FT-200W-MCTP-D	100W/150W/200W	130LM/W	35K/40K/50K - 52" X 14.5"	1
LLVT-4FT-RL2T	OPTIONAL REPLACEMENT FROSTED LENS FOR LLVT			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DES	PLUG IN CORD	DESCRIPTION
25W to 46W	OPT-EM-LLVT-25-46	INTERNAL	OPT-HBC-125TL-WH	8FT, 15A, 125V,WHITE
65W to 155W	OPT-EM-LLVT-65-155	INTERNAL	OPT-HBC-277TL-WH	8FT, 15A, 277V,WHITE
	SURGE PROTECTOR	DES	OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT
	OPT-SP-10KV	120-277V	SENSOR	DESCRIPTION
	OPT-SP-10KV-480V	480V	OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
	POWDER COATING		OPT-SEN-NLS-LLVT	WG NETWORK SENSOR
	N/A		OPT-SEN-KEILTON-LLVT	KEILTON NETWORK SENSOR
	N/A		WEC-3RC	OPTIONAL RC

LLVT-4FT-100W-MCT-D-480V
LLVT-4FT-150W-MCT-D-480V

LLVT-4FT-40W-MCT-D-480V

LLVT-8FT-65W-50K-D-480V
LLVT-8FT-100W-40K-D-480V

LED LINEAR VAPOR LIGHT **480V** MADE TO ORDER

CATALOG NO.	DESCRIPTION			PCK QTY
6-3/4" WIDE POLYCARBONATE LED LINEAR VAPOR LIGHT 480V				
LLVT-4FT-40W-MCT-D-480V	40W	5000LM	35K/40K/50K	6
14-1/2" WIDE POLYCARBONATE LED LINEAR VAPOR LIGHT 480V				
LLVT-4FT-100W-MCT-D-480V	100W	13500LM	35K/40K/50K	1
LLVT-4FT-150W-MCT-D-480V	150W	20250LM	35K/40K/50K	1
3" WIDE LED LINEAR VAPOR LIGHT 480V				
LLVT-8FT-65W-50K-D-480V	65W	8450LM	5000K	1
LLVT-8FT-100W-40K-D-480V	100W	13000LM	4000K	1

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DES	PLUG IN CORD	DESCRIPTION
25W to 46W	OPT-EM-LLVT-25-46	INTERNAL	OPT-HBC-125TL-WH	8FT, 15A, 125V,WHITE
65W to 155W	OPT-EM-LLVT-65-155	INTERNAL	OPT-HBC-277TL-WH	8FT, 15A, 277V,WHITE
	SURGE PROTECTOR	DES	OPT-HBC-125SB-WH	10FT, 15A, 125V,18/3STR,WHT
	OPT-SP-10KV	120-277V	SENSOR	DESCRIPTION
	OPT-SP-10KV-480V	480V	OPT-SEN-2MDR-36	PROGRAMMABLE MICROWAVE BI-LEVEL
	POWDER COATING		OPT-SEN-NLS-LLVT	WG NETWORK SENSOR
	N/A		OPT-SEN-KEILTON-LLVT	KEILTON NETWORK SENSOR
	N/A		WEC-3RC	OPTIONAL RC

LRLVT-8FT-4L

LAMP-READY LINEAR VAPOR LIGHT

CATALOG NO.	DESCRIPTION
LRLVT-4FT-2L	Lamp-Ready 4Ft 2-Lamp Linear Vapor Tight 4In Wide
LRLVT-4FT-4L	Lamp-Ready 4Ft 4-Lamp Linear Vapor Tight 10In Wide
LRLVT-8FT-4L	Lamp-Ready 8Ft 4-Lamp Linear Vapor Tight 7In Wide

EXPF-30W-50K

HAZARDOUS LOCATION FLOOD/HIGH BAY LIGHT **120-277V** CLASS 1, DIV. 2

CATALOG NO.	DESCRIPTION		
EXPF-30W-50K	30W	4200LM	5000K
EXPF-60W-50K	60W	8400LM	5000K
EXPF-100W-50K	100W	14000LM	5000K
EXPF-180W-60K	180W	20700LM	6000K
EXPF-240W-50K	240W	21000LM	5000K
LF-AD-SF-GY	Slips Onto Pole Top 2" Dim. Fixture Mounts Directly On The Side Or Top Of This Device		

Shown with Dome Glass & Done Wireguard

Shown with Flat Wireguard

Shown with U Shape Lens & Wireguard

EXPR

ROUND HAZARDOUS LOCATION FLOOD/HIGH BAY LIGHT **120-277V/480V** CLASS 1, DIV. 2

CATALOG NO.	DESCRIPTION		
EXPR-30W-50K	30W	146 LM/W	5000K
EXPR-60W-50K	60W	143 LM/W	5000K
EXPR-100W-50K	100W	153 LM/W	5000K
EXPR-150W-50K	150W	155 LM/W	5000K
EXPR-30-60W-WGF	Flat Wire Guard For EXPR 30W To 60W		
EXPR-100-150W-WGF	Flat Wire Guard For EXPR 100W To 150W		
EXPR-30-60W-LD	Dome Lens For EXPR 30W To 60W		
EXPR-100-150W-LD	Dome Lens For EXPR 100W To 150W		
EXPR-30-60W-WGD	Dome Wire Guard For EXPR 30W To 60W		
EXPR-100-150W-WGD	Dome Wire Guard For EXPR 100W To 150W		
EXPR-30-60W-LU	U- shape Jelly-Jar Lens For EXPR 30W To 60W		
EXPR-30-60W-WGU	U- shape Jelly-Jar Wire Guard For EXPR 30W To 60W		
EXPR-150W-50K-480V	150W	150 LM/W	5000K

EXPL

LINEAR HAZARDOUS LOCATION FLOOD/HIGH BAY LIGHT **120-277V/480V** CLASS 1, DIV. 2

CATALOG NO.	DESCRIPTION		
EXPL-40W-50K	40W	135 LM/W	5000K
EXPL-80W-50K	80W	135 LM/W	5000K
EXPL-120W-50K	120W	130 LM/W	5000K
EXPL-80W-50K-480V	80W	135 LM/W	5000K

EXP-HA03-050-U-50-000-CG-S

EXP-HA04-100-U-50-012-CG-B

EXP-HA05-150-U-50-019-CG-S-DM

EXP-HA06-080-U-50-000-DP-P-DM

EXP-HA10-075-U-50-000-CG-V-AP

EXP-HA09-2740_T

HAZARDOUS LOCATION - FLOOD LIGHT, HIGHBAY, LOWBAY, LINEAR LIGHTS

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
EXP-HA03-050-U-50-000-CG-T	50W	7000LM	5000K	
EXP-HA03-070-U-50-000-CG-T	70W	9800LM	5000K	
EXP-HA03-050-U-40-000-CG-T	50W	7000LM	4000K	
EXP-HA03-070-U-40-000-CG-T	70W	9800LM	4000K	
EXP-HA04-075-U-50-012-CG-B-DM	75W	4500LM	5000K	
EXP-HA04-100-U-50-012-CG-B-DM	100W	15000LM	5000K	
EXP-HA04-150-U-50-012-CG-B	150W	22500LM	5000K	
EXP-HA04-150-V-50-012-CG-B	150W	22500LM	5000K	
EXP-HA04-240-U-50-000-CG-B	240W	36000LM	5000K	
EXP-HA04-240-U-50-012-CG-B	240W	36000LM	5000K	
EXP-HA04-240-V-50-012-CG-B	240W	36000LM	5000K	
EXP-HA10-075-U-50-000-CG-M-AP	30W/53W/75W	10500LM	5000K	
EXP-HA05-075-U-50-016-CG-T-DM	75W	10500LM	5000K	
EXP-HA05-100-U-50-000-CG-T-DM	100W	14000LM	5000K	
EXP-HA05-100-U-50-016-CG-T-DM	100W	14000LM	5000K	
EXP-HA05-100-V-50-016-CG-T	100W	14000LM	5000K	
EXP-HA05-150-U-50-000-CG-T-DM	150W	21000LM	5000K	
EXP-HA05-150-U-50-019-CG-T-DM	150W	21000LM	5000K	
EXP-HA05-150-U-40-019-CG-T-DM	150W	21000LM	4000K	
EXP-HA05-150-U-50-019-CG-T-ED	150W	21000LM	5000K	
EXP-HA05-150-V-50-019-CG-T	150W	21000LM	5000K	
EXP-HA05-150-V-50-019-CG-T-DM	150W	21000LM	5000K	
EXP-HA05-200-U-50-019-CG-T-DM	200W	28000LM	5000K	
EXP-HA05-240-U-50-019-CG-T-DM	240W	33600LM	5000K	
EXP-HA05-240-U-50-019-CG-T-ED	240W	33600LM	4000K	
EXP-HA05-240-V-50-019-CG-T	240W	33600LM	5000K	
EXP-HA05-240-V-50-019-CG-T-DM	240W	33600LM	5000K	
EXP-HA06-030-U-50-000-DP-P-DM	30W	4500LM	5000K	
EXP-HA06-050-U-50-000-DP-P-DM	50W	7500LM	5000K	
EXP-HA06-050-U-50-000-DP-P-ED	50W	7500LM	5000K	
EXP-HA06-080-U-50-000-DP-P-DM	80W	12000LM	5000K	
EXP-HA06-100-U-50-000-DP-P-DM	100W	15000LM	5000K	
EXP-HA06-100-U-50-000-DP-P-ED	100W	15000LM	5000K	
EXP-HA09-2740/T	5*1.5mm²(5*16Awg); Up To 300V Upper & Bottom Thread Size: 1-1/2" Npt			
EXP-BC-HA09-02	Tubular Rail Mount Bracket, 2Pcs/Set			
EXP-BC-HA09-01	Angular Rail Mount Bracket, 2Pcs/Set			
EXP-BC-HA09-03	Inclined Rail Mount Bracket, 2Pcs/Set			
EXP-BC-HA09-04	Wall Mount Bracket, 2Pcs/Set			
EXP-AD-HA09-01	Protective Cover			
EXP-BC-HA03-02	Compatible With C1D1 HA03 Lowbay Light			
EXP-BC-HA03-03	Compatible With C1D1 HA03 Lowbay Light			
EXP-BC-HA03-04	Compatible With C1D1 HA03 Lowbay Light			
EXP-BC-HA04-03	Compatible With C1D2 HA04 Flood Light			
EXP-BC-HA05-03	Compatible With C1D2 HA05 Highbay Light			
EXP-BC-HA05-04	Compatible With C1D2 HA05 Highbay Light			
EXP-BC-HA05-05	Compatible With C1D2 HA05 Highbay Light			
EXP-BC-HA05-06	Compatible With C1D2 HA05 Highbay Light			
EXP-MK-HA10-02	Compatible With C1D2 HA10 Highbay Light			
EXP-MK-HA10-06	Compatible With C1D2 HA10 Highbay Light			
EXP-MK-HA10-07	Compatible With C1D2 HA10 Highbay Light			
EXP-MK-HA10-09	Compatible With C1D2 HA10 Highbay Light			
EXP-DLK-HA10-09	Compatible With C1D2 HA10 Highbay Light			

DOCK LIGHTS

WET LOCATIONS

LDL-R-36W-57K-A40
LDL-R-30W-60K-A40

LDL-R-63W-57K-A40
LDL-R-60W-60K-A40

LDL-R-E26-A40

LDL-S-63W-57K-B40R
LDL-S-50W-60K-B40R

LOADING DOCK LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
LDL-R-36W-57K-A40	36W	3960LM	5700K	2
LDL-R-30W-60K-A40	30W	3300LM	6000K	2
LDL-R-63W-57K-A40	63W	6930LM	5700K	2
LDL-R-60W-60K-A40	60W	6600LM	6000K	2
LDL-S-63W-57K-B40R	63W	6930LM	5700K	2
LDL-S-50W-60K-B40R	50W	7000LM	6000K	2
LDL-R-E26-A40	Loading Dock For Par Lamps With 1Ft Wp Connector And 40In Bracket			

RESIDENTIAL

RDPS SERIES


RDDF SERIES

RDPF SERIES

RDL SERIES

RDFM SERIES

SDL SERIES

TC-RDPS SERIES

RDJ SERIES


HL HOUSING


ICF HOUSING


FR-HL HOUSING

RSL SERIES

SSLRB SERIES

RSL-G2 SERIES

RSL-REG-FR SERIES

RSL-FR SERIES

RSL-GIM-FR SERIES

RSL-JB SERIES

RSL-ADJ SERIES

RSL-GIM SERIES

RSL-APD SERIES

RDL-BF SERIES

RDLS-ADJ SERIES

RDL1S SERIES

RDL4S-SB SERIES

RDLTS SERIES

SDLTS SERIES

LDLS SERIES

LRD SERIES

RDTL SERIES

DLSU SERIES

DLST SERIES


DLSE SERIES

DLSE-RGB SERIES

DLSN SERIES

DLSF SERIES

DLS SERIES

FMD SERIES

FDL SERIES

FDLO SERIES

FODL SERIES

FSL SERIES

FCRB SERIES

FCR SERIES


FCS SERIES

FMHT SERIES

FMLU SERIES

FEL SERIES

Search for the series name @WESTGATEMFG.COM

FMLS SERIES

FMLT SERIES

FMLE SERIES

FML-UGR SERIES

TC-FML SERIES

FML-TRM SERIES


ELB-09120-AC-JB

FMLB SERIES

FMLB-WP SERIES

FMLB-REG SERIES

FMLB-FMF SERIES

FMLB-CMC SERIES

FMLB-CS SERIES

LCFF SERIES

FCD SERIES

LCEU SERIES

LCFCSERIES

LCFN SERIES

LCFA SERIES

LCFPM SERIES

LCFS SERIES

LCFQ SERIES

LCFT SERIES

LCFW SERIES

LCFK SERIES

LCFI SERIES

LCFL SERIES

LDAP SERIES

LCFD SERIES

LCFP SERIES

LCFR SERIES

LCFB SERIES

LCFH SERIES

LCFE-E26 SERIES

LCFE SERIES

LCFG SERIES

LCFG-E26 SERIES

DSP SERIES

DPL SERIES

BRL SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM



TRIMS & HOUSINGS

RDPS2-MCT5

2” ROUND COMPOSITE RECESSED TRIM, SMOOTH

CATALOG NO.	DESCRIPTION		
RDPS2-MCT5	7W	600LM	27K/30K/35K/40K/50K

RDPS2-ADJ-MCT5

2” ADJUSTABLE ROUND COMPOSITE RECESSED TRIM

CATALOG NO.	DESCRIPTION		
RDPS2-ADJ-MCT5	7W	600LM	27K/30K/35K/40K/50K



RDDF6-MCT5-PIR

6” ECO SHALLOW PC DOB RECESS TRIM, 5CCT WITH PIR MOTION SENSOR

CATALOG NO.	DESCRIPTION		
RDDF6-MCT5-PIR	10W	1000LM	27K/30K/40K/50K/60K - 6” BAFFLE

RDDF4-MCT5

RDDF6-MCT5

4", 6" BUILDER SERIES ECO SHALLOW PC DOB RECESS TRIM 5CCT SELECTABLE

CATALOG NO.	DESCRIPTION		
RDDF4-MCT5	6.5W	650LM	27K/30K/40K/50K/60K - 4" BAFFLE
RDDF6-MCT5	10W	1000LM	27K/30K/40K/50K/60K - 6" BAFFLE
RDDS4-MCT5	6.5W	650LM	27K/30K/40K/50K/60K - 4" SMOOTH
RDDS6-MCT5	10W	1000LM	27K/30K/40K/50K/60K - 6" SMOOTH

RDPF4-MCT5

RDPS6-MCT5

WHILE SUPPLIES LAST

4", 6" BUILDER PLUS ENVIRONMENTAL SERIES LED RECESSED LIGHT TRIM COMPOSITE SERIES 5CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
RDPF4-MCT5	10W	800LM	27K/30K/35K/40K/50K - 4" BAFFLE	12
RDPF6-MCT5	13W	1040LM	27K/30K/35K/40K/50K - 6" BAFFLE	8
RDPS4-MCT5	10W	800LM	27K/30K/35K/40K/50K - 4" SMOOTH	12
RDPS6-MCT5	13W	1040LM	27K/30K/35K/40K/50K - 6" SMOOTH	8

RDPF4-MCTP

RDPF6-MCTP

WHILE SUPPLIES LAST

4”, 6” BUILDER PLUS ENVIRONMENTAL SERIES PC, LED RECESSED LIGHT TRIM, COMPOSITE SERIES 5CCT+3 POWER-LEVEL SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
RDPF4-MCTP	8W/10W/13W	80LM/W	27K/30K/35K/40K/50K - 4" BAFFLE	12
RDPF6-MCTP	10W/13W/17W	80LM/W	27K/30K/35K/40K/50K - 6" BAFFLE	8

RDPF4-ADJ-MCT5
RDPF6-ADJ-MCT5

4”, 6” BUILDER PLUS ENVIRONMENTAL SERIES PC ADJUSTABLE-HEAD LED RECESSED LIGHT TRIM 5CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
RDPF4-ADJ-MCT5	10W	800LM	27K/30K/35K/40K/50K - 4”	12
RDPF6-ADJ-MCT5	11W	880LM	27K/30K/35K/40K/50K - 6”	8

RDL-ADJ

RDL3


RDL6-ORB

RDL4-ORB


RDL6-ST-ORB

RDL4-ST-ORB

RDL6-BF

RDL-WP

RDL4-BF

RDL6-ST

RD46-ST

3", 4", 5/6" SPEC SERIES LED RECESSED TRIM SERIE 5CCT SELECTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
SMOOTH METAL LED RECESSED TRIM SERIES 4" & 5/6" SELECTABLE 5CCT [JA8]				
WET LOCATIONS **RDL4-ST-MCT5**	10W	700LM	27K/30K/35K/40K/50K - 4"	24
WET LOCATIONS **RDL4-ST-MCT5-ORB**	10W	700LM	27K/30K/35K/40K/50K - 4"	24
WET LOCATIONS **RDL4-ST-MCT5-BK**	10W	700LM	27K/30K/35K/40K/50K - 4"	24
RDL6-ST-MCT5	15W	1275LM	27K/30K/35K/40K/50K - 5/6"	16
RDL6-ST-MCT5-ORB	15W	1275LM	27K/30K/35K/40K/50K - 5/6"	16
RDL6-ST-MCT5-BK	15W	1275LM	27K/30K/35K/40K/50K - 5/6"	16
BAFFLE METAL LED RECESSED TRIM SERIES 4" & 5/6" SELECTABLE 5CCT [JA8]				
RDL4-BF-MCT5	10W	700LM	27K/30K/35K/40K/50K - 4"	24
RDL4-BF-MCT5-ORB	10W	700LM	27K/30K/35K/40K/50K - 4"	24
RDL4-BF-MCT5-BK	10W	700LM	27K/30K/35K/40K/50K - 4"	24
RDL6-BF-MCT5	15W	1275LM	27K/30K/35K/40K/50K - 5/6"	16
RDL6-BF-MCT5-ORB	15W	1275LM	27K/30K/35K/40K/50K - 5/6"	16
RDL6-BF-MCT5-BK	15W	1275LM	27K/30K/35K/40K/50K - 5/6"	16
SPEC PLUS & WESTGATE SIGNATURE LED RECESSED TRIM SERIES 3", 4", 5/6" SELECTABLE 5CCT [JA8]				
RDL3-MCT5-WP*	7W	560LM	27K/30K/35K/40K/50K - 3"	20
RDL4-MCT5-WP*	8W	650LM	27K/30K/35K/40K/50K - 4"	20
RDL6-MCT5-WP*	14W	1140LM	27K/30K/35K/40K/50K - 5/6"	20
WESTGATE SIGNATURE ADJUSTABLE BAFFLE METAL LED RECESSED TRIM SERIES 4" & 5/6" SELECTABLE 5CCT [JA8]				
RDL4-ADJ-MCT5	8W	650LM	27K/30K/35K/40K/50K - 4"	12
RDL6-ADJ-MCT5	11W	900LM	27K/30K/35K/40K/50K - 5/6"	8

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
UP TO 19W	OPT-EM-RDL	EXTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

RDMF4-MCT5

RDMF4-MCT5-BK

RDMF4-MCT5-ORB

RDMF6-MCT5



RDMF6-MCT5-BK



RDMF6-MCT5-ORB

4”, 6” WESTGATE SIGNATURE DEEP BAFFLE RETROFIT METAL LED RECESSED TRIM

POWER AND CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
RDMF4-MCT5	6W/7W/9.5W	550LM/650W/800LM	27K/30K/35K/40K/50K - White	10
RDMF4-MCT5-BK	6W/7W/9.5W	550LM/650W/800LM	27K/30K/35K/40K/50K - Black	10
RDMF4-MCT5-ORB	6W/7W/9.5W	550LM/650W/800LM	27K/30K/35K/40K/50K - Oil-rubbed bronze	10
RDMF6-MCT5	8W/10W/13W	750LM/900W/1100LM	27K/30K/35K/40K/50K - White	10
RDMF6-MCT5-BK	8W/10W/13W	750LM/900W/1100LM	27K/30K/35K/40K/50K - Black	10
RDMF6-MCT5-ORB	8W/10W/13W	750LM/900W/1100LM	27K/30K/35K/40K/50K - Oil-rubbed bronze	10

RDL4-BF-TRMB-BK



RDL4-BF-TRMB-BN



RDL4-BF-TRMB-ORB



RDL4-BF-TRMB-GD

RDL4-BF-TRMB-WH



RDL6-BF-TRMB-BK



RDL6-BF-TRMB-BN

RDL6-BF-TRMB-ORB

RDL6-BF-TRMB-GD

RDL6-BF-TRMB-WH

4", 6" LED BAFFLE AND SMOOTH RECESSED TRIM, CLIP-ON RDL-BF & RDL-ST

CATALOG NO.	DESCRIPTION
RDL4-BF-TRMB-BK	RDL4-BF series color trim, baffle, black finish
RDL4-BF-TRMB-BN	RDL4-BF series color trim, baffle, brushed nickel finish
RDL4-BF-TRMB-ORB	RDL4-BF series color trim, baffle, oil-rubbed bronze finish
RDL4-BF-TRMB-GD	RDL4-BF series color trim, baffle, Specular Gold
RDL6-BF-TRMB-BK	RDL6-BF series color trim, baffle, black finish
RDL6-BF-TRMB-BN	RDL6-BF series color trim, baffle, brushed nickel
RDL6-BF-TRMB-ORB	RDL6-BF series color trim, baffle, oil-rubbed bronze finish
RDL6-BF-TRMB-GD	RDL6-BF series color trim, baffle, Specular Gold
RDL4-BF-TRMS-BK	RDL4-BF series color trim, smooth, black finish
RDL4-BF-TRMS-BN	RDL4-BF series color trim, smooth, brushed nickel
RDL4-BF-TRMS-WH	RDL4-BF series color trim, smooth, white finish
RDL4-BF-TRMS-ORB	RDL4-BF series color trim, smooth, oil-rubbed bronze finish
RDL4-BF-TRMS-GD	RDL4-BF series color trim, smooth, Specular Gold
RDL6-BF-TRMS-BK	RDL6-BF series color trim, smooth, black finish
RDL6-BF-TRMS-BN	RDL6-BF series color trim, smooth, brushed nickel
RDL6-BF-TRMS-WH	RDL6-BF series color trim, smooth, white finish
RDL6-BF-TRMS-ORB	RDL6-BF series color trim, smooth, oil-rubbed bronze finish
RDL6-BF-TRMS-GD	RDL6-BF series color trim, smooth, Specular Gold

TRIAC DIMMABLE

SDPS2-MCT5

SDL4

SDL4-BF

SDL6-BF

2", 4", 5/6" LED SQUARE TRIM

CATALOG NO.	DESCRIPTION			PCK QTY
2" SQUARE COMPOSITE RECESSED TRIM, SMOOTH				
SDPS2-MCT5	7W	600LM	27K/30K/35K/40K/50K - 2"	50
SMOOTH LED SQUARE TRIMS 4", 5/6"				
SDL4-MCT5	10W	650LM	27K/30K/35K/40K/50K - 4"	24
SDL6-MCT5	15W	1155LM	27K/30K/35K/40K/50K - 5/6"	16
BAFFLE LED SQUARE TRIMS 4", 5/6"				
SDL4-BF-27K*	10W	600LM	2700K - 4"	24
SDL4-BF-30K*	10W	650LM	3000K - 4"	24
SDL4-BF-50K*	10W	700LM	5000K - 4"	24
SDL4-BF-MCT5	10W	700LM	27K/30K/35K/40K/50K - 4"	24
SDL6-BF-27K	16.5W	1073LM	2700K - 5/6"	16
SDL6-BF-30K	16.5W	1100LM	3000K - 5/6"	16
SDL6-BF-41K	16.5W	1150LM	4100K - 5/6"	16
SDL6-BF-50K	16.5W	1200LM	5000K - 5/6"	16
SDL6-BF-MCT5	15W	1155LM	27K/30K/35K/40K/50K - 5/6"	16

WHILE SUPPLIES LAST*

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
UP TO 19W	OPT-EM-SDL	EXTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A



TC-RDPS4-10W-RGBW-WIFI

TC-RGBW-RC

4”, 6” WG SMART APP COMPATIBLE RGBW SMOOTH RECESSED LIGHT TRIM - ROUND **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-RDPS4-10W-RGBW-WIFI	10W	650LM	RGBW - E26 Base	12
TC-RDPS6-13W-RGBW-WIFI	13W	850LM	RGBW - E26 Base	8

RDL4-BF-MCT5-12V

RDL4-ST-MCT5-12V

4” **12V** LOW-VOLTAGE LED REPLACEMENT TRIMS FOR MR16 HOUSINGS

CATALOG NO.	DESCRIPTION			PCK QTY
RDL4-BF-MCT5-12V	11W	77LM	27K/30K/35K/40K/50K - 4"	24
RDL4-ST-MCT5-12V	11W	77LM	27K/30K/35K/40K/50K - 4"	24

RDJ4-MCT5

RDJ4-TRM-BK

4” J-BOX DIRECT-MOUNT RECESSED LIGHT, FITS 3-O AND 4-O OCTAGON BOXES

CATALOG NO.	DESCRIPTION			PCK QTY
RDJ4-MCT5	10W	700LM	27K/30K/35K/40K/50K - 4"	20
RDJ4-TRM-BK	4 inch magnetic trim for RDJ4 , Black			

RDL3

RDL4

RDL6

RDL6-ADJ

RDL4-ADJ

RDL4-BF

RDL4-ADJ

WHILE SUPPLIES LAST

3", 4", 5/6" SPEC PLUS SERIES SINGLE CCT LED TRIMS E26 included in the box (JA8-E-2016 COMPLIANT)

CATALOG NO.	DESCRIPTION			PCK QTY
RDL3-27K-WP	9W	540LM	2700K - 3"	20
RDL3-41K-WP	9W	540LM	4100K - 3"	20
RDL3-50K-WP	9W	540LM	5000K - 3"	20
RDL4-27K-WP	12W	650LM	2700K - 4"	12
RDL4-30K-WP	12W	700LM	3000K - 4"	12
RDL4-35K-WP	12W	725LM	3500K - 4"	12
RDL4-65K-WP	12W	850LM	6500K - 4"	12
RDL6-30K-WP	19W	1250LM	3000K - 5/6"	8
RDL6-41K-WP	19W	1300LM	4100K - 5/6"	8
RDL6-50K-WP	19W	1350LM	5000K - 5/6"	8
RDL6-65K-WP	19W	1400LM	6500K - 5/6"	8
RDL4-BF-27K	10W	650LM	2700K - 4"	24
RDL4-BF-30K-ORB	10W	680LM	3000K - 4" Oil-Rubbed Bronze	24
RDL4-BF-35K	10W	720LM	3500K - 4"	24
RDL4-BF-41K	10W	746LM	4100K - 4"	24
RDL4-BF-50K	10W	761LM	5000K - 4"	24
RDL6-BF-35K	18W	1280LM	3500K - 5/6"	16
RDL4-ADJ-27K	10W	650LM	2700K - 4"	12
RDL4-ADJ-30K	10W	650LM	3000K - 4"	12
RDL4-ADJ-41K	10W	650LM	4100K - 4"	12
RDL4-ADJ-50K	10W	650LM	5000K - 4"	12
RDL6-ADJ-50K	13W	900LM	5000K - 5/6"	8

HL2R-ICAT

HL2DW-ICAT

HL3R-ICAT

HL3-ICAT

HL4R-ICAT

HL4DW-ICAT

HL4-ICAT

HL4RS-ICAT


HL4S-ICAT

HL6R-ICAT


HL6-ICAT

HL6RS-ICAT

HL6S-ICAT

LED RECESSED HOUSING

CATALOG NO.	DESCRIPTION
HL2R-ICAT	2In Led (TP24) Remodel Recessed Housing ICAT UL
HL2DW-ICAT	2In Led (TP24) Double-Wall Recessed Housing ICAT UL
HL3R-ICAT	3In Led (TP24) Remodel Recessed Housing ICAT UL
HL3-ICAT	3In Led (TP24) Recessed Housing ICAT UL
HL4R-ICAT	4In Led (TP24) Remodel Recessed Housing ICAT UL
HL4DW-ICAT	4In Led (TP24) Double-Wall Recessed Housing ICAT UL
HL4-ICAT	4In Led (TP24) Recessed Housing ICAT UL
HL4RS-ICAT	4In Led (TP24) Shallow Remodel Recessed Housing ICAT UL
HL4S-ICAT	4In Led (TP24) Shallow Recessed Housing ICAT UL
HL6R-ICAT	6In Led (TP24) Remodel Recessed Housing ICAT UL
HL6-ICAT	6In Led (TP24) Recessed Housing ICAT UL
HL6RS-ICAT	6In Led (TP24) Shallow Remodel Recessed Housing ICAT UL
HL6S-ICAT	6In Led (TP24) Shallow Recessed Housing ICAT UL


ICF4SJBB


ICF4SJBP


ICFAL-4

ICFAL-6

FIRE-RATED AIRTIGHT LED RECESSED LIGHT HOUSING NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION	PCK QTY
ICF4SJBB	4" Fire-Rated Junction Box With Bar Hangers For Surface Mount Down Lights	24
ICF4SJBP	4" Fire-Rated Junction Box Housing For Led Surface Mount Down Lights & J-Box Recessed Lights	6
ICFAL-4	4" Fire-Rated Ic New Construction Led Recessed Housing	4
ICFAL-6	6" Fire-Rated Ic New Construction Led Recessed Housing	4


FR-HL4-AT

FR-HL6-AT

FIRE-RATED RECESSED HOUSING GEN. 2, IC & AT, CONFROM TO UL263 & UL1598

CATALOG NO.	DESCRIPTION	PCK QTY
FR-HL4-AT	4in 2hr Fire-Rated Recessed Housing New Const.	4
FR-HL6-AT	6in 2hr Fire-Rated Recessed Housing New Const.	4



RECESSED LIGHTS & TRIMS

RSL4-G2-MCT5

4", 6" RSL G2 SECOND GENERATION SLIM CANLESS WAFER LIGHT, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
RSL4-G2-MCT5	10W	700LM	27K/30K/35K/40K/50K - 4" White	20
RSL4-G2-MCT5-BK	10W	700LM	27K/30K/35K/40K/50K - 4" Black	20
RSL4-G2-MCT5-ORB	10W	700LM	27K/30K/35K/40K/50K - 4"Oil-Rubbed Bronze	20
RSL6-G2-MCT5	12W	1000LM	27K/30K/35K/40K/50K - 6" White	20
RSL6-G2-MCT5-BK	12W	1000LM	27K/30K/35K/40K/50K - 6" Black	20
RSL6-G2-MCT5-ORB	12W	1000LM	27K/30K/35K/40K/50K - 6" Oil-Rubbed Bronze	20



RSL4-D2W

TC-RSL4-RGBWW

4", 6" ROUND CANLESS SLIM LIGHT 120V

CATALOG NO.	DESCRIPTION			PCK QTY
CANLESS SLIM LIGHTS, DIM-TO-WARM				
RSL4-D2W	11W	700LM	DIM TO WARM 22-40K	12
RSL6-D2W	12W	900LM	DIM TO WARM 22-40K	12
WG SMART APP OR REMOTE COMPATIBLE RGBWW SLIM CANLESS RECESSED LIGHTS				
TC-RSL4-RGBWW	9W	630LM	RGBWW	24
TC-RSL6-RGBWW	12W	840LM	RGBWW	24

RSL3



RSL4

RSL10

RSL6



RSL6

RSLC6

3", 4", 6", 8" & 12" LED ULTRA SLIM CANLESS RECESSED LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
LED 5CCT ULTRA SLIM ROUND RECESSED LIGHTS, 120V				
RSL3-MCT5	6W	400LM	27K/30K/35K/40K/50K - 3"	24
RSL3-MCT5-BN	6W	400LM	27K/30K/35K/40K/50K - 3"	24
RSL3-MCT5-ORB	6W	400LM	27K/30K/35K/40K/50K - 3"	24
RSL4-MCT5	9W	630LM	27K/30K/35K/40K/50K - 4"	24
RSL4-MCT5-ORB	9W	630LM	27K/30K/35K/40K/50K - 4"	24
RSL6-MCT5	15W	1125LM	27K/30K/35K/40K/50K - 6"	24
RSL6-MCT5-ORB	15W	1125LM	27K/30K/35K/40K/50K - 6"	24
RSL8-MCT5	18W	1350LM	27K/30K/35K/40K/50K - 8"	24
RSL10-MCT5	20W	1500LM	27K/30K/35K/40K/50K - 10"	24
RSL12-MCT5	24W	1800LM	27K/30K/35K/40K/50K - 12"	24
LED 5CCT BAFFLE ULTRA SLIM ROUND RECESSED LIGHTS, 120V				
RSL4-BF-MCT5	9W	650LM	27K/30K/35K/40K/50K - 4"	12
RSL6-BF-MCT5	15W	1200LM	27K/30K/35K/40K/50K - 6"	12
RSL-BF-EXT-6FT-MCT5	6 FT Extension Cord for RSL-BF			
RSL-BF-EXT-10FT-MCT5	10 FT Extension Cord for RSL-BF			
RSL-BF-EXT-20FT-MCT5	20 FT Extension Cord for RSL-BF			
WET LOCATION LED 5CCT SLIM CANLESS ROUND RECESSED LIGHTS, 120V				
RSL3-MCT5-WP	6W	400LM	27K/30K/35K/40K/50K - 3"	24
RSL4-MCT5-WP	9W	630LM	27K/30K/35K/40K/50K - 4"	24
RSL6-MCT5-WP	15W	1125LM	27K/30K/35K/40K/50K - 6"	24
RSL8-MCT5-WP	18W	1350LM	27K/30K/35K/40K/50K - 8"	24
RSL10-MCT5-WP	20W	1500LM	27K/30K/35K/40K/50K - 10"	24
RSL12-MCT5-WP	24W	1800LM	27K/30K/35K/40K/50K - 12"	24
LED COMMERCIAL SLIM CANLESS ROUND RECESSED REGRESSED BAFFLE LIGHTS 120-277V, 0~10V DIMMING				
RSLC6-BF-30K	15W	1200LM	3000K - 6"	18
RSLC6-BF-40K	15W	1200LM	4000K - 6"	19
RSLC6-BF-MCT5	15W	1200LM	27K/30K/35K/40K/50K - 6"	20
RSLC8-BF-30K	18W	1440LM	3000K - 8"	21
RSLC8-BF-MCT5	18W	1440LM	27K/30K/35K/40K/50K - 8"	22
RSL-BF-EXT-6FT	RSL-BF 6FT. DC extension cord			23
RSL-BF-EXT-10FT	RSL-BF 10FT. DC extension cord			24
RSL-BF-EXT-20FT	RSL-BF 20FT. DC extension cord			25
LED 5CCT ULTRA SLIM SQAURE RECESSED LIGHTS, 120V				
SSL4-MCT5	9W	630LM	27K/30K/35K/40K/50K - 4"	24
SSL6-MCT5	15W	1125LM	27K/30K/35K/40K/50K - 6"	24
SSL8-MCT5	18W	1350LM	27K/30K/35K/40K/50K - 8"	24
SSL12-MCT5	24W	1800LM	27K/30K/35K/40K/50K - 12"	24
RSL-EXT-10FT-MCT	10 Ft. Extension Cable for use with all MCT Slim Lights			

RSL4-TRM

SSL4-TRM

RSL6-TRM


SSL6-TRM

LED ULTRA SLIM RECESSED TRIMS (CLIP ON RSL & SSL SLIM LIGHTS)

CATALOG NO.	DESCRIPTION
RSL4-TRM-BK	4" Black Clip-on Trim
RSL4-TRM-ORB	4" Oil-rubbed Bronze Clip-on Trim
RSL4-TRM-CU	4" Copper Clip-on Trim
RSL4-TRM-BZ	4" Bronze Clip-on Trim
RSL4-TRM-BN	4" Brushed Nickel Clip-on Trim
RSL4-TRM-CH	4" Chrome Clip-on Trim
SSL4-TRM-BK	4" Black Clip-on Trim
SSL4-TRM-ORB	4" Oil-rubbed Bronze Clip-on Trim
SSL4-TRM-CU	4" Copper Clip-on Trim
SSL4-TRM-BZ	4" Bronze Clip-on Trim
SSL4-TRM-BN	4" Brushed Nickel Clip-on Trim
SSL4-TRM-CH	4" Chrome Clip-on Trim
RSL6-TRM-BK	6" Black Clip-on Trim
RSL6-TRM-ORB	6" Oil-rubbed Bronze Clip-on Trim
RSL6-TRM-CU	6" Copper Clip-on Trim
RSL6-TRM-BZ	6" Bronze Clip-on Trim
RSL6-TRM-BN	6" Brushed Nickel Clip-on Trim
RSL6-TRM-CH	6" Chrome Clip-on Trim
SSL6-TRM-BK	6" Black Clip-on Trim
SSL6-TRM-ORB	6" Oil-rubbed Bronze Clip-on Trim
SSL6-TRM-CU	6" Copper Clip-on Trim
SSL6-TRM-BZ	6" Bronze Clip-on Trim
SSL6-TRM-BN	6" Brushed Nickel Clip-on Trim
SSL6-TRM-CH	6" Chrome Clip-on Trim

SSLRB6-MCT5

SSLRB6-TRM-BK

SSLRB6-TRM-BN

SSLRB6-TRM-ORB

LED 5CCT ADJUSTABLE ULTRA SLIM ROUND-BACK CANLESS RECESSED LIGHTS

CATALOG NO.	DESCRIPTION			PCK QTY
SSLRB4-MCT5	9W	630LM	27K/30K/35K/40K/50K - 4"	24
SSLRB6-MCT5	15W	1125LM	27K/30K/35K/40K/50K - 6"	24
SSLRB4-TRM-BK	4 inch square trim for SSLRB4, black			
SSLRB4-TRM-BN	4 inch square trim for SSLRB4, brushed nickel			
SSLRB4-TRM-ORB	4 inch square trim for SSLRB4, oil-rubbed bronze			
SSLRB6-TRM-BK	6 inch square trim for SSLRB6, black			
SSLRB6-TRM-BN	6 inch square trim for SSLRB6, brushed nickel			
SSLRB6-TRM-ORB	6 inch square trim for SSLRB6, oil-rubbed bronze			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
UP TO 19W	OPT-EM-RSL	EXTERNAL	N/A	N/A
	POWDER COATING		SENSOR	DESCRIPTION
	N/A		N/A	N/A

RSL-RI


RSL-RIBH


RSL4-RIBH

RSL6-RIBH


RSL-568-RIBH

RSL-81012-RIBH

RSL-346-RI


XXX


XXX


XXX

XXX


XXX


SSL-RI


SSL-346-R


SSL-81012-RI


SSL-346-RI-13


SSL-81012-RI-13


SSL-568-RIBH


SSL-81012-RIBH

RSL-EXT-10FT

RSL-GR

RSL-VB

LED ULTRA SLIM RECESSED LIGHT ACCESSORIES

CATALOG NO.	DESCRIPTION
RSL2-RI	2" Round Rough-in Plate, 26" Long
RSL3-RI	3" Round Rough-in Plate, 26" Long
RSL3-RIBH	New Construction Recessed LT Mounting Plate 3" Hole With Hanger Bars
RSL4-RI	4" Round Rough-in Plate, 26" Long
RSL4-RI-13	4" Round Rough-in Plate, 13" Long
RSL4-RIL-13	13" Long Recessed Lt Mounting Plate 4" Hole With 1/2In Lip
RSL4-RIBH	New Construction Recessed LT Mounting Plate 4" Hole With Hanger Bars
RSL6-RI	6" Round Rough-in Plate, 26" Long
RSL6-RI-13	6" Round Rough-in Plate, 13" Long
RSL6-RIL-13	13" Long Recessed Lt Mounting Plate 6" Hole With 1/2In Lip
RSL6-RIBH	New Construction Recessed LT Mounting Plate 6" Hole With Hanger Bars
RSL-346-RI	3", 4", 6" Round Rough-in Plate, 26" Long
RSL-346-RI-13	3", 4", 6 Round Rough-in Plate, 13" Long
RSL-346-RIBH	3", 4", 6" (Adjustable) Round Galvanized plate with Bar Hangers
RSL-568-RIBH	5", 6", 8" (Adjustable) Round Galvanized plate with Bar Hangers
RSL8-RI	8" Round Rough-in Plate, 26" Long
RSL12-RI	12" Round Rough-in Plate, 26" Long
RSL-81012-RI	8", 10", 12" Round Rough-in Plate, 26" Long
RSL-81012-RI-13	8", 10", 12" Round Rough-in Plate, 13" Long
RSL-81012-RIBH	8", 10", 12" (Adjustable) Round Galvanized plate with Bar Hangers
SSL4-RI	4" Square Rough-in Plate, 26" Long
SSL6-RI	6" Square Rough-in Plate, 26" Long
SSL-346-RI	3", 4", 6" Square Rough-in Plate, 26" Long
SSL-346-RI-13	3", 4", 6 Square Rough-in Plate, 13" Long
SSL-346-RIBH	3", 4", 6" (Adjustable) Square Galvanized plate with Bar Hangers
SSL-568-RIBH	5", 6", 8" (Adjustable) Square Galvanized plate with Bar Hangers
SSL12-RI	12" Square Rough-in Plate, 26" Long
SSL-81012-RI	8", 10", 12" Square Rough-in Plate, 26" Long
SSL-81012-RI-13	8", 10", 12" Square Rough-in Plate, 13" Long
SSL-81012-RIBH	8", 10", 12" (Adjustable) Square Galvanized plate with Bar Hangers
RSL-EXT-10FT	10 Ft Extension Cord For Slim Recessed Lights
RSL4-GR	Goof ring for 4in lights with butterfly wings
RSL6-GR	Goof ring for 6in lights with butterfly wings
RSL8-GR	Goof ring for 8in lights with butterfly wings
RSL10-GR	Goof ring for 10in lights with butterfly wings
RSL12-GR	Goof ring for 12in lights with butterfly wings
RSL4-VB	4" Vapor Barrier For Slim Recessed Lights
RSL6-VB	6" Vapor Barrier For Slim Recessed Lights



RSL3-G2-MCT5-FR

3”, 4”, 6” ROUND FIRE-RATED EDGE-LIT SLIM RECESS LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
RSL3-G2-MCT5-FR	6W	600LM	27K/30K/35K/40K/50K - 3”	24
RSL4-G2-MCT5-FR	9W	900LM	27K/30K/35K/40K/50K - 4”	24
RSL6-G2-MCT5-FR	12W	1200LM	27K/30K/35K/40K/50K - 6”	24



SSL4-G2-MCT5-FR

4”, 6” SQUARE FIRE-RATED EDGE-LIT SLIM RECESS LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
SSL4-G2-MCT5-FR	9W	900LM	27K/30K/35K/40K/50K - 4”	24
SSL6-G2-MCT5-FR	12W	1200LM	27K/30K/35K/40K/50K - 6”	24

RSL4-REG-MCT5-FR

4”, 6” ROUND FIRE-RATED EDGE-LIT SLIM REGRESSED RECESS LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
RSL4-REG-MCT5-FR	9W	900LM	27K/30K/35K/40K/50K - 4”	24
RSL6-REG-MCT5-FR	14W	1400LM	27K/30K/35K/40K/50K - 6”	18



SSL6-REG-MCT5-FR

4”, 6” SQUARE FIRE-RATED EDGE-LIT SLIM REGRESSED RECESS LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
SSL4-REG-MCT5-FR	9W	900LM	27K/30K/35K/40K/50K - 4"	24
SSL6-REG-MCT5-FR	14W	1400LM	27K/30K/35K/40K/50K - 6"	18

4”, 6” FIRE-RATED (2 HR) SLIM WAFER CANLESS RECESSED LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
RSL4-MCT5-FR	9W	630LM	27K/30K/35K/40K/50K - 4"	24
SSL4-MCT5-FR	9W	630LM	27K/30K/35K/40K/50K - 4"	24
RSL6-MCT5-FR	12W	840LM	27K/30K/35K/40K/50K - 6"	24
SSL6-MCT5-FR	12W	840LM	27K/30K/35K/40K/50K - 6"	24

RSL6-ADJ-MCT5-FR

4”, 6” ADJUSTABLE FIRE-RATED SLIM CANLESS RECESSED LIGHT, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
RSL4-ADJ-MCT5-FR	9W	630LM	27K/30K/35K/40K/50K - 4"	24
RSL6-ADJ-MCT5-FR	12W	840LM	27K/30K/35K/40K/50K - 6"	12



RSL4-GIM-MCT5-FR

4", 6" ROUND GIMBAL FIRE-RATED EDGE-LIT SLIM RECESS LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
RSL4-GIM-MCT5-FR	9W	900LM	27K/30K/35K/40K/50K - 4"	24
RSL6-GIM-MCT5-FR	12W	1200LM	27K/30K/35K/40K/50K - 6"	18

RSL4-JB-MCT5

4", 6" SLIM SNAP-IN CANLESS RECESSED LIGHT WITH J-BOX, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
RSL4-JB-MCT5	10W	650LM	27K/30K/35K/40K/50K - 4"	24
RSL6-JB-MCT5	12W	1000LM	27K/30K/35K/40K/50K - 6"	24

RSL4-ADJ-G2-MCT5

4", 6" ROUND ADJUSTABLE CANLESS LIGHT, **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
NEW GENERATION OF ADJUSTABLE ANGLE CANLESS LIGHT				
RSL4-ADJ-G2-MCT5	9W	630LM	27K/30K/35K/40K/50K - 4"	24
RSL6-ADJ-G2-MCT5	12W	840LM	27K/30K/35K/40K/50K - 6"	24
LED 5CCT ADJUSTABLE ULTRA SLIM CANLESS RECESSED LIGHTS				
RSL4-ADJ-MCT5	9W	700LM	27K/30K/35K/40K/50K - 4"	24
WET LOCATION ADJUSTABLE LED 5CCT SLIM CANLESS RECESSED LIGHTS				
RSL4-ADJ-MCT5-WP	9W	630LM	27K/30K/35K/40K/50K - 4"	24
RSL6-ADJ-MCT5-WP	15W	1125LM	27K/30K/35K/40K/50K - 6"	24

RSL4-GIM-MCT5

4” LED GIMBAL (EYEBALL) ROUND CANLESS RECESSED SNAP-IN LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
RSL4-GIM-MCT5	10W	800LM	27K/30K/35K/40K/50K - 4"	24

RSL4-APD-MCT5

4” LED 5CCT ADJUSTABLE PULL-DOWN ULTRA SLIM CANLESS RECESSED LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
RSL4-APD-MCT5	10W	700LM	27K/30K/35K/40K/50K - 4"	12

RDL4S-BF-MCT5-BK

RDL4S-BF-MCT5-WH

RDL6S-BF-MCT5-BK

RDL6S-BF-MCT5-WH

4”, 6” CANLESS DEEP BAFFLE RECESSED LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
RDL4S-BF-MCT5-WH	12W	1050LM	27K/30K/35K/40K/50K - 4" White	20
RDL4S-BF-MCT5-BK	12W	1050LM	27K/30K/35K/40K/50K - 4" Black	20
RDL4S-BF-MCT5-ORB	12W	1050LM	27K/30K/35K/40K/50K - 4" Oil-rubbed bronze	20
RDL6S-BF-MCT5-WH	14W	1200LM	27K/30K/35K/40K/50K - 6" White	20
RDL6S-BF-MCT5-BK	14W	1200LM	27K/30K/35K/40K/50K - 6" Black	20
RDL6S-BF-MCT5-ORB	14W	1200LM	27K/30K/35K/40K/50K - 6" Oil-rubbed bronze	20

RDL4S-BF-D2W-WH

RDL6S-BF-D2W-WH

4", 6" CANLESS DEEP RECESS LIGHT, DIM TO WARM

CATALOG NO.	DESCRIPTION		
RDL4S-BF-D2W-WH	12W	1050LM	DIM TO WARM 22-40K
RDL6S-BF-D2W-WH	14W	1200LM	DIM TO WARM 22-40K

RDL1S-ADJ

RDLD3S-ADJ

SDLD3S-ADJ

RDL3S-ADJ-WH

RDL3S-ADJ-BK

SDL3S-ADJ-WH

SDL3S-ADJ-BK

1", 3", 4" ADJUSTABLE CANLESS LIGHT, BLACK & WHITE

CATALOG NO.	DESCRIPTION			PCK QTY
1" & 3" ADJUSTABLE (EYEBALL) ROUND ARCHITECTURAL CANLESS LIGHT 5CCT				
RDL1S-ADJ-MCT5	6W	350LM	27K/30K/35K/40K/50K - 1" White	24
RDL3S-ADJ-MCT5-WH	7W	700LM	27K/30K/35K/40K/50K - 3" White	20
3" & 4" ROUND REGRESSED CANLESS GIMBAL				
RDLD3S-ADJ-MCT5-WH	9W	800LM	27K/30K/35K/40K/50K - 3" White	30
RDLD4S-ADJ-MCT5-WH	15W	1100LM	27K/30K/35K/40K/50K - 4" White	20
RDLD3S-ADJ-MCT5-BK	9W	800LM	27K/30K/35K/40K/50K - 3" Black	30
RDLD4S-ADJ-MCT5-BK	15W	1100LM	27K/30K/35K/40K/50K - 4" Black	20
3" & 4" SQUARE REGRESSED CANLESS GIMBAL				
SDLD3S-ADJ-MCT5-WH	9W	800LM	27K/30K/35K/40K/50K - 3" White	30
SDLD4S-ADJ-MCT5-WH	15W	1100LM	27K/30K/35K/40K/50K - 4" White	20
SDLD3S-ADJ-MCT5-BK	9W	800LM	27K/30K/35K/40K/50K - 3" Black	30
SDLD4S-ADJ-MCT5-BK	15W	1100LM	27K/30K/35K/40K/50K - 4" Black	20
3" LED ADJUSTABLE (EYEBALL) CANLESS RECESSED LIGHTS (JA8-E-2016 COMPLIANT) (ROUND & SQUARE)				
RDL3S-ADJ-40K-WH	8W	600LM	4000K - 3" White	18
SDL3S-ADJ-27K-WH	8W	600LM	2700K - 3" White	18
SDL3S-ADJ-30K-WH	8W	600LM	3000K - 3" White	18
SDL3S-ADJ-40K-WH	8W	600LM	4000K - 3" White	18
SDL3S-ADJ-50K-WH	8W	600LM	5000K - 3" White	18
RSL-346-RIBH	3", 4", 6" (Adjustable) Galvanized plate with Bar Hangers			



RDL1S-ST



SDL1S-ST

RSL-1-RIBH

HIGH-OUTPUT LOW-GLARE CANLESS RECESSED LIGHTS, ROUND & SQUARE

CATALOG NO.	DESCRIPTION		
RDL1S-ST-MCT5-BK	8W	600LM	27K/30K/35K/40K/50K - Black
RDL1S-ST-MCT5-WH	8W	600LM	27K/30K/35K/40K/50K - White
SDL1S-ST-MCT5-BK	8W	600LM	27K/30K/35K/40K/50K - Black
SDL1S-ST-MCT5-WH	8W	600LM	27K/30K/35K/40K/50K - White
RSL-1-RIBH	1in (Adjustable) Galvanized Mounting Plate with Bar Hangers		

RDL2S-SB-WH
RDL4S-SB-WH
RDL6S-SB-WH

RDL2S-SB-BK
RDL4S-SB-BK
RDL6S-SB-BK

SDL2S-SB-WH
SDL4S-SB-WH
SDL6S-SB-WH

SDL2S-SB-BK
SDL4S-SB-BK
SDL6S-SB-BK

2", 4", 6" HIGH-LUMEN DIE-CAST LED SNAP-IN CANLESS RECESSED LIGHT, BLACK & WHITE SMOOTH AND BAFFLE TRIMS INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
2" & 4" HIGH-LUMEN DIE-CAST LED SNAP-IN CANLESS RECESSED LIGHTS				
RDL2S-SB-MCT5-BK*	9W	600LM	27K/30K/35K/40K/50K - 2" Round, Black	20
RDL4S-SB-MCT5-WH*	15W	1350LM	27K/30K/35K/40K/50K - 4" Round, White	20
RDL4S-SB-MCT5-BK*	15W	1350LM	27K/30K/35K/40K/50K - 4" Round, Black	20
SDL2S-SB-MCT5-BK*	9W	600LM	27K/30K/35K/40K/50K - 2" Square, Black	20
SDL4S-SB-MCT5-WH*	15W	1350LM	27K/30K/35K/40K/50K - 4" Square, White	20
SDL4S-SB-MCT5-BK*	15W	1350LM	27K/30K/35K/40K/50K - 4" Square, Black	20
6" ANTI-GLARE COMMERCIAL/RESIDENTIAL CANLESS RECESSED LIGHTS, DUAL DIM				
RDL6S-SB-MCTP5-DD-WH	15W/20W/25W	85LM/W	27K/30K/35K/40K/50K	20
RDL6S-SB-MCTP5-DD-BK	15W/20W/25W	85LM/W	27K/30K/35K/40K/50K	20

WHILE SUPPLIES LAST*

RDL2S



SDL2S

2” LED CANLESS RECESSED LIGHT BAFFLE, JA8-E-2016 COMPLIANT

CATALOG NO.	DESCRIPTION			PCK QTY
RDL2S-BF-40K-WH*	8W	600LM	4000K - Round	18
RDL2S-BF-50K-WH*	8W	600LM	5000K - Round	18
MCT RDL2S-BF-MCT-WH	8W	600LM	3000K/4000K/5000K - Round	18
SDL2S-BF-27K-WH*	8W	600LM	2700K - Square	18
SDL2S-BF-40K-WH*	8W	600LM	4000K - Square	18
SDL2S-BF-50K-WH*	8W	600LM	5000K - Square	18
MCT SDL2S-BF-MCT-WH	8W	600LM	3000K/4000K/5000K - Square	18
RSL-346-RIBH	3”, 4”, 6” (Adjustable) Galvanized plate with Bar Hangers			
RDL2S-TRIM-ST-WH	Smooth Reflector Trim For RDL2S-BF, White			
SDL2S-TRIM-ST-WH	Smooth Reflector Trim For SDL2S-BF, White			

WHILE SUPPLIES LAST*



1”, 2”, 3”, 4” ROUND HOTEL SPEC CANLESS THIN-TRIM RECESS LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
MCT RDLT1S-ST-MCT5-WH	7W	550LM	27K/30K/35K/40K/50K - 1” White	40
MCT RDLT2S-ST-MCT5-WH	12W	900LM	27K/30K/35K/40K/50K - 2” White	20
MCTP RDLT3S-ST-MCTP5-WH	12W/15W/18W	82LM/W	27K/30K/35K/40K/50K - 3” White	20
MCTP RDLT4S-ST-MCTP5-WH	12W/15W/18W	82LM/W	27K/30K/35K/40K/50K - 4” White	20
MCT RDLT1S-ST-MCT5-BK	7W	550LM	27K/30K/35K/40K/50K - 1” Black	40
MCT RDLT2S-ST-MCT5-BK	12W	900LM	27K/30K/35K/40K/50K - 2” Black	20
MCTP RDLT3S-ST-MCTP5-BK	12W/15W/18W	82LM/W	27K/30K/35K/40K/50K - 3” Black	20
MCTP RDLT4S-ST-MCTP5-BK	12W/15W/18W	82LM/W	27K/30K/35K/40K/50K - 4” Black	20



1", 2", 3", 4" SQUARE HOTEL SPEC CANLESS THIN-TRIM RECESS LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
SDLT1S-ST-MCT5-WH	7W	550LM	27K/30K/35K/40K/50K - 1" White	40
SDLT2S-ST-MCT5-WH	12W	900LM	27K/30K/35K/40K/50K - 2" White	20
SDLT3S-ST-MCTP5-WH	12W/15W/18W	82LM/W	27K/30K/35K/40K/50K - 3" White	20
SDLT4S-ST-MCTP5-WH	12W/15W/18W	82LM/W	27K/30K/35K/40K/50K - 4" White	20
SDLT1S-ST-MCT5-BK	7W	550LM	27K/30K/35K/40K/50K - 1" Black	40
SDLT2S-ST-MCT5-BK	12W	900LM	27K/30K/35K/40K/50K - 2" Black	20
SDLT3S-ST-MCTP5-BK	12W/15W/18W	82LM/W	27K/30K/35K/40K/50K - 3" Black	20
SDLT4S-ST-MCTP5-BK	12W/15W/18W	82LM/W	27K/30K/35K/40K/50K - 4" Black	20

LDLS-6-MCT5


LDLS-12-MCT5


LDLS-6-RI

MINI LINEAR OPTIC-LIGHT FIXTURES, SNAP IN 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LDLS-6-MCT5	11W	600LM	27K/30K/35K/40K/50K	20
LDLS-12-MCT5	18W	1200LM	27K/30K/35K/40K/50K	20
LDLS-6-12-RI	26in Mounting Plate For LDSL6 And LDLS12 Snap-In Linear Lights			

ELB-0895

LED EMERGENCY DRIVER FOR ALL RECESSED TRIM

CATALOG NO.	DESCRIPTION
ELB-0895	Field-installed emergency ballast for all LED recessed trims; Input voltage: 100~277VAC, 50~60Hz; Output: 8W Maximum for 90 minutes

LRD-TL-10W-MCT5-4R-BK

LRD-TL-10W-MCT5-4R-C

LRD-TL-10W-MCT5-4R-HZ


LRD-TL-10W-MCT5-4R-MG

LRD-TL-10W-MCT5-4R-WH


LRD-TL-10W-MCT5-4S-BK

LRD-TL-10W-MCT5-4S-C

LRD-TL-10W-MCT5-4S-HZ


LRD-TL-10W-MCT5-4S-MG

LRD-TL-10W-MCT5-4S-WH

LRD-TL-10W-MCT5-4SM1-WH

LRD-TL-20W-MCT5-4SM2-WH

LRD-TL-30W-MCT5-4SM3-WH

4" LED ARCHITECTURAL TRIMLESS RECESSED LIGHT

CATALOG NO.	DESCRIPTION		
4" ROUND			
LRD-TL-10W-MCT5-4R-BK	10W	700LM	27K/30K/35K/40K/50K - Black
LRD-TL-10W-MCT5-4R-C	10W	700LM	27K/30K/35K/40K/50K - Clear
LRD-TL-10W-MCT5-4R-HZ	10W	700LM	27K/30K/35K/40K/50K - Haze
LRD-TL-10W-MCT5-4R-MG	10W	700LM	27K/30K/35K/40K/50K - Matte Gold
LRD-TL-10W-MCT5-4R-WH	10W	700LM	27K/30K/35K/40K/50K - White
4" SQUARE			
LRD-TL-10W-MCT5-4S-BK	10W	700LM	27K/30K/35K/40K/50K - Black
LRD-TL-10W-MCT5-4S-C	10W	700LM	27K/30K/35K/40K/50K - Clear
LRD-TL-10W-MCT5-4S-HZ	10W	700LM	27K/30K/35K/40K/50K - Haze
LRD-TL-10W-MCT5-4S-MG	10W	700LM	27K/30K/35K/40K/50K - Matte Gold
LRD-TL-10W-MCT5-4S-WH	10W	700LM	27K/30K/35K/40K/50K - White
4" REGRESSED SQUARE			
LRD-TL-10W-MCT5-4RM-WH	10W	70LM/W	27K/30K/35K/40K/50K - White
LRD-TL-10W-MCT5-4SM1-WH	10W	70LM/W	27K/30K/35K/40K/50K - White
LRD-TL-20W-MCT5-4SM2-WH	20W	1400LM	27K/30K/35K/40K/50K - White
LRD-TL-30W-MCT5-4SM3-WH	30W	2100LM	27K/30K/35K/40K/50K - White
LRD-TL-10W-MCT5-4RM-BK	10W	70LM/W	27K/30K/35K/40K/50K - Black
LRD-TL-10W-MCT5-4SM1-BK	10W	70LM/W	27K/30K/35K/40K/50K - Black
LRD-TL-20W-MCT5-4SM2-BK	20W	1400LM	27K/30K/35K/40K/50K - Black
LRD-TL-30W-MCT5-4SM3-BK	30W	2100LM	27K/30K/35K/40K/50K - Black

LRD-3WTR-ABK LRD-3WTR-BK LRD-3WTR-C LRD-3WTR-HZ LRD-3WTR-MG LRD-3WTR-WH


LRD-4WTR-BK LRD-4WTR-ABK LRD-4WTR-C LRD-4WTR-MG LRD-4WTR-HZ LRD-4WTR-WH

LRD-3WTRPH-BK LRD-3WTRPH-WH LRD-3WTRSL-BK LRD-3WTRSL-WH LRD-3WTRSL-BK LRD-3WTRSL-WH LRD-3WTRPH-BK LRD-3WTRPH-WH

2,” 4” LED ARCHITECTURAL WINGED RECESSED LIGHT

CATALOG NO.	DESCRIPTION		
2” OPEN TRIM			
LRD-10W-MCT5-3WTR-ABK	10W	700LM	27K/30K/35K/40K/50K - Black on Black
LRD-10W-MCT5-3WTR-BK	10W	700LM	27K/30K/35K/40K/50K - Black
LRD-10W-MCT5-3WTR-C	10W	700LM	27K/30K/35K/40K/50K - Clear
LRD-10W-MCT5-3WTR-HZ	10W	700LM	27K/30K/35K/40K/50K - Haze
LRD-10W-MCT5-3WTR-MG	10W	700LM	27K/30K/35K/40K/50K - Matte Gold
LRD-10W-MCT5-3WTR-WH	10W	700LM	27K/30K/35K/40K/50K - White
2” PIN HOLE TRIM			
LRD-10W-MCT5-3WTRPH-BK	10W	700LM	27K/30K/35K/40K/50K - Black
LRD-10W-MCT5-3WTRPH-WH	10W	700LM	27K/30K/35K/40K/50K - White
2” SLOT TRIM			
LRD-10W-MCT5-3WTRSL-BK	10W	700LM	27K/30K/35K/40K/50K - Black
LRD-10W-MCT5-3WTRSL-WH	10W	700LM	27K/30K/35K/40K/50K - White
4” OPEN TRIM			
LRD-10W-MCT5-4WTR-ABK	10W	700LM	27K/30K/35K/40K/50K - Black on Black
LRD-10W-MCT5-4WTR-BK	10W	700LM	27K/30K/35K/40K/50K - Black
LRD-10W-MCT5-4WTR-C	10W	700LM	27K/30K/35K/40K/50K - Clear
LRD-10W-MCT5-4WTR-HZ	10W	700LM	27K/30K/35K/40K/50K - Haze
LRD-10W-MCT5-4WTR-MG	10W	700LM	27K/30K/35K/40K/50K - Matte Gold
LRD-10W-MCT5-4WTR-WH	10W	700LM	27K/30K/35K/40K/50K - White
4” PIN HOLE TRIM			
LRD-10W-MCT5-4WTRPH-BK	10W	700LM	27K/30K/35K/40K/50K - Black
LRD-10W-MCT5-4WTRPH-WH	10W	700LM	27K/30K/35K/40K/50K - White
4” SLOT TRIM			
LRD-10W-MCT5-4WTRSL-BK	10W	700LM	27K/30K/35K/40K/50K - Black
LRD-10W-MCT5-4WTRSL-WH	10W	700LM	27K/30K/35K/40K/50K - White

LED ARCHITECTURAL MULTIPLE-TRIM RECESSED LIGHT

CATALOG NO.	DESCRIPTION		
LRD-10W-MCT5-WTM1-WH	10W	700LM	27K/30K/35K/40K/50K - White
LRD-10W-MCT5-WTM2-WH	20W	1400LM	27K/30K/35K/40K/50K - White
LRD-10W-MCT5-WTM3-WH	30W	2100LM	27K/30K/35K/40K/50K - White

LRD ACCESSORIES

CATALOG NO.	DESCRIPTION
LRD-FGL	Frosted Glass Lens For LRD Series

RDS2TL-BK

RDS3TL-BK

RD4TL-BK

RD2TL-BK

RD3TL-BK

RDS4TL-BK

RDS4TL

RDS2TL

RD4TL

RD2TL

RD3TL

ROUND CANLESS & TRIMLESS RECESSED LIGHTS - CRI90

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
RD2TL-MCT5	9W	600LM	27K/30K/35K/40K/50K		12
RD2TL-HL-MCT5	14W	950LM	27K/30K/35K/40K/50K		12
RD3TL-MCT5	15W	1000LM	27K/30K/35K/40K/50K		12
RD4TL-MCT5	20W	1600LM	27K/30K/35K/40K/50K		6
RDS2TL-MCT5	9W	600LM	27K/30K/35K/40K/50K		12
RDS3TL-MCT5	15W	1000LM	27K/30K/35K/40K/50K		12
RDS4TL-MCT5	20W	1600LM	27K/30K/35K/40K/50K		6
RD2TL-MCT5-BK	9W	600LM	27K/30K/35K/40K/50K - Black		12
RD2TL-HL-MCT5-BK	14W	950LM	27K/30K/35K/40K/50K - Black		12
RD3TL-MCT5-BK	15W	1000LM	27K/30K/35K/40K/50K - Black		12
RD4TL-MCT5-BK	20W	1600LM	27K/30K/35K/40K/50K - Black		6
RDS2TL-MCT5-BK	9W	600LM	27K/30K/35K/40K/50K - Black		12
RDS3TL-MCT5-BK	15W	1000LM	27K/30K/35K/40K/50K - Black		12
RDS4TL-MCT5-BK	20W	1600LM	27K/30K/35K/40K/50K - Black		6
RDG2TL-MCT5	6W	400LM	27K/30K/35K/40K/50K		12
RDG3TL-MCT5	9W	730LM	27K/30K/35K/40K/50K		12
RDG4TL-MCT5	15W	1250LM	27K/30K/35K/40K/50K		6
RDSG2TL-MCT5	6W	400LM	27K/30K/35K/40K/50K		12
RDSG3TL-MCT5	9W	730LM	27K/30K/35K/40K/50K		12
RDSG4TL-MCT5	15W	1250LM	27K/30K/35K/40K/50K		6
RDG2TL-MCT5-BK	6W	400LM	27K/30K/35K/40K/50K - Black		12
RDG3TL-MCT5-BK	9W	730LM	27K/30K/35K/40K/50K - Black		12
RDG4TL-MCT5-BK	15W	1250LM	27K/30K/35K/40K/50K - Black		6
RDSG2TL-MCT5-BK	6W	400LM	27K/30K/35K/40K/50K - Black		12
RDSG3TL-MCT5-BK	9W	730LM	27K/30K/35K/40K/50K - Black		12
RDSG4TL-MCT5-BK	15W	1250LM	27K/30K/35K/40K/50K - Black		6

EDGE-LIT & DISK LIGHTS

DLU6-MCT5



DLU6-MCT5-BK

6" ECO METAL DISK LIGHT - 120V

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
DLU6-MCT5	12W	850LM	27K/30K/35K/40K/50K	30
DLU6-MCT5-BK	12W	850LM	27K/30K/35K/40K/50K - Black	30



DLSU6-MCT5

6" ECO METAL DISK LIGHT 120V

CATALOG NO.	DESCRIPTION			PCK QTY
DLSU6-MCT5	14.8W	1000LM	3000K - 6"	20

DLST6-MCT5

6" ECONOMY EASY-INSTALL DISK - POLYCARBONATE HOUSING

CATALOG NO.	DESCRIPTION			PCK QTY
DLST6-MCT5	10W	1000LM	27K/30K/40K/50K/60K - 6"	10

DLST6-MCT5-IP65

6” ECONOMY EASY-INSTALL DISK, IP65 - POLYCARBONATE HOUSING

CATALOG NO.	DESCRIPTION			PCK QTY
DLST6-MCT5-IP65	10W	1000LM	27K/30K/40K/50K/60K - 6"	10

DLST6-MCT5-PIR

6” ECONOMY EASY-INSTALL DISK WITH PIR MOTION SENSOR PC HOUSING

CATALOG NO.	DESCRIPTION			PCK QTY
DLST6-MCT5-PIR	10W	1000LM	27K/30K/40K/50K/60K - 6"	10

DLSE6-MCT5

DLSE6-MCT5-BR

DLSE6-MCT5-BN

4”, 6” BUILDER SERIES LED 5CCT DISK LIGHT ECONOMY DISC LIGHT JA8-E-2019 COMPLIANT

CATALOG NO.	DESCRIPTION			PCK QTY
DLSE4-MCT5	10W	630LM	27K/30K/35K/40K/50K - 4" White	30
DLSE4-MCT5-BR	10W	630LM	27K/30K/35K/40K/50K - 4" Bronze	30
DLSE6-MCT5	15W	1000LM	27K/30K/35K/40K/50K - 6" White	24
DLSE6-MCT5-BR	15W	1000LM	27K/30K/35K/40K/50K - 6" Bronze	24
DLSE6-MCT5-BN	15W	1000LM	27K/30K/35K/40K/50K - 6" Brushed Nickel	24

DLSE4-MCT5-PIR

4”, 6” BUILDER SERIES LED ECONOMY DISK LIGHT WITH PIR MOTION SENSOR

CATALOG NO.	DESCRIPTION			PCK QTY
DLSE4-MCT5-PIR	10W	630LM	27K/30K/35K/40K/50K - 4"	30
DLSE6-MCT5-PIR	15W	1000LM	27K/30K/35K/40K/50K - 6"	24



DLSE6-RGBW

TC-RGBW-RC

6" WG SMART APP COMPATIBLE RGBW BUILDER SERIES LED ECONOMY DISK LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
DLSE6-RGBW	15W	1000LM	27K/30K/35K/40K/50K - 6"	24

WHILE SUPPLIES LAST

4", 6" BUILDER SERIES LED MULTI-CCT ECONOMY DISC LIGHT JA8-E-2019 COMPLIANT

CATALOG NO.	DESCRIPTION			PCK QTY
DLSE4-MCT	9W	540LM	3000K/4000K/5000K - 4" White	20
DLSE6-40K	15W	900LM	4000K - 6" White	20
DLSE6-50K	15W	900LM	5000K - 6" White	20
DLSE6-MCT-BN	15W	1000LM	3000K/4000K/5000K - 6" Brushed Nickel	20

DLSN

WHILE SUPPLIES LAST

4", 6" LED DISC LIGHT **120V** J-BOX MOUNTING (JA8-E-2016 COMPLIANT)

CATALOG NO.	DESCRIPTION			PCK QTY
DLSN4-50K	10W	600LM	5000K - 4"	20
DLSN6-27K	15W	1000LM	2700K - 6"	20
DLSN6-30K	15W	1000LM	3000K - 6"	20
DLSN6-50K	15W	1000LM	5000K - 6"	20

DLSF4-MCT5

DLSF6-MCT5

4”, 6” ARCHITECTURAL FLAT EDGE-LIT SURFACE DISK LIGHT, 5CCT

CATALOG NO.	DESCRIPTION		
DLSF4-MCT5	12W	1080LM	27K/30K/35K/40K/50K - 4”
DLSF6-MCT5	14W	1350LM	27K/30K/35K/40K/50K - 6”

4”, 6” 8”, 10”, 12” SPEC SERIES 3CCT HIGH-PERFORMANCE DISC LIGHT 120V

DIE CAST ALUMINUM, ALL MOUNTING OPTIONS INCL.

CATALOG NO.	DESCRIPTION			PCK QTY
DLS4-MCT	9W	540LM	3000K/4000K/5000K - 4”	20
DLS6-MCT	15W	900LM	3000K/4000K/5000K - 6”	20
DLS6-MCT-BN	15W	900LM	3000K/4000K/5000K - 6” Brushed Nickel	20
DLS6-MCT-BR	15W	900LM	3000K/4000K/5000K - 6” Bronze	20
DLS8-MCT	20W	1200LM	3000K/4000K/5000K - 8”	10
DLS10-MCT	25W	1500LM	3000K/4000K/5000K - 10”	10
DLS12-MCT	30W	1800LM	3000K/4000K/5000K - 12”	5

WHILE SUPPLIES LAST

SPEC SERIES HIGH-PERFORMANCE DISC LIGHT 120V DIE CAST ALUMINUM, MOUNTING OPTIONS INCL.

CATALOG NO.	DESCRIPTION			PCK QTY
DLS4-27K	9W	550~600LM	2700K - 4”	20
DLS4-30K	9W	550~600LM	3000K - 4”	20
DLS4-41K	9W	550~600LM	4100K - 4”	20
DLS4-50K	9W	550~600LM	5000K - 4”	20
DLS6-30K	15W	950~1000LM	3000K - 6”	20
DLS6-41K	15W	950~1000LM	4100K - 6”	20
DLS6-30K-BR	15W	950~1000LM	3000K - 6” Bronze	20
DLS6-30K-BN	15W	950~1000LM	3000K - 6” Brushed Nickel	20

DLS6-MCT-277V

DLS12-MCT-277V

6”, 12” SPECS SERIES HIGH-PERFORMANCE DIE-CAST DISK LIGHT **277V**

CATALOG NO.	DESCRIPTION			PCK QTY
DLS6-MCT-277V	15W	900LM	3000K/4000K/5000K - 6"	20
DLS12-MCT-277V	30W	1800LM	3000K/4000K/5000K - 12"	5

4”, 6”, 8”, 10”, 12” SPECS SERIES HIGH-PERFORMANCE DIE-CAST DISK LIGHTS WITH PIR

CATALOG NO.	DESCRIPTION			PCK QTY
DLS4-MCT-PIR	9W	540LM	3000K/4000K/5000K - 4"	20
DLS6-MCT-PIR	15W	900LM	3000K/4000K/5000K - 6"	20
DLS8-MCT-PIR	20W	1200LM	3000K/4000K/5000K - 8"	10
DLS10-MCT-PIR	25W	1500LM	3000K/4000K/5000K - 10"	10
DLS12-MCT-PIR	30W	1800LM	3000K/4000K/5000K - 12"	5

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
DLS6, DLSE6, DLSN6	**OPT-EM-DLS6**	MOUNT IN EXTENDED BASE
DLS8	**OPT-EM-DLS8**	MOUNT IN EXTENDED BASE
DLS10	**OPT-EM-DLS10**	MOUNT IN EXTENDED BASE
DLS12	**OPT-EM-DLS12**	MOUNT IN EXTENDED BASE
DLS6-277V	**OPT-EM-DLS6-277V**	MOUNT IN EXTENDED BASE
DLS12-277V	**OPT-EM-DLS12-277V**	MOUNT IN EXTENDED BASE

POWDER COATING
N/A

PHOTOCELL	DESCRIPTION
OPT-PC-DLS6	Photocell
OPT-PC-DLS8	Photocell
OPT-PC-DLS10	Photocell
OPT-PC-DLS12	Photocell
OPT-PC-DLS6-277V	Photocell
OPT-PC-DLS12-277V	Photocell

277V OPTION	DESCRIPTION
OPT-277V-DLS6	277V
OPT-277V-DLS8	277V
OPT-277V-DLS10	277V
OPT-277V-DLS12	277V

FLUSH MOUNT LIGHTS

FMD-11--MCT5-BN

FMD-11--MCT5-ORB

FMD-11--MCT5-WH

LED 5CCT DOME FLUSH MOUNT

CATALOG NO.	DESCRIPTION			PCK QTY
FMD-11-MCT5-BN	20W	1500LM	27K/30K/35K/40K/50K - 11" Brushed Nickel	8
FMD-11-MCT5-ORB	20W	1500LM	27K/30K/35K/40K/50K - 11" Oil-Rubbed Bronze	8
FMD-11-MCT5-WH	20W	1500LM	27K/30K/35K/40K/50K - 11" White	8
FMD-13-MCT5-BN	24W	1800LM	27K/30K/35K/40K/50K - 13" Brushed Nickel	8
FMD-13-MCT5-ORB	24W	1800LM	27K/30K/35K/40K/50K - 13" Oil-Rubbed Bronze	8
FMD-13-MCT5-WH	24W	1800LM	27K/30K/35K/40K/50K - 13" White	8

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
FMD-11	**OPT-EM-FMD11**	EXTERNAL BOX
FMD-11	**OPT-EM-FMD11-BN**	EXTERNAL BOX
FMD-11	**OPT-EM-FMD11-ORB**	EXTERNAL BOX
FMD-13	**OPT-EM-FMD13**	EXTERNAL BOX
FMD-13	**OPT-EM-FMD13-BN**	EXTERNAL BOX
FMD-13	**OPT-EM-FMD13-ORB**	EXTERNAL BOX

POWDER COATING
N/A

PHOTOCELL	DESCRIPTION
N/A	N/A

SENSOR	DESCRIPTION
OPT-SEN-2US	MICROWAVE
OPT-SEN-NLS-FMD	WG NETWORK SENSOR
OPT-SEN-KEILTON-FMD	KEILTON NETWORK SENSOR
OPT-SEN-2USRC	OPTIONAL RC

FDL

FDL-BK

FDL Shown with EM

FDL-BK Shown with FDL-SFK-BK

FDLS

LED 5CCT DOUBLE RING FLUSH MOUNT 120V

CATALOG NO.	DESCRIPTION			PCK QTY
FDL-10-MCT5	12W	900LM	27K/30K/35K/40K/50K - 10" D X 3-1/4" H	8
FDL-12-MCT5	16W	1200LM	27K/30K/35K/40K/50K - 12" D X 3-1/4" H	8
FDLS-12-MCT5	20W	1500LM	27K/30K/35K/40K/50K - 12" D X 2-1/8" H	8
FDL-12-MCT5-BK	16W	1200LM	27K/30K/35K/40K/50K - 12" D X 3-1/4" H Black	8
FDLS-14-MCT5	24W	1800LM	27K/30K/35K/40K/50K - 14" D X 2-1/8" H	8
FDL-14-MCT5-BK	20W	1500LM	27K/30K/35K/40K/50K - 14" D X 3-1/4" H Black	8
FDL-16-MCT5	24W	1800LM	27K/30K/35K/40K/50K - 16" D X 3-1/4" H	8
FDL-18-MCT	30W	2200LM	3000K/4000K/5000K - 18" D X 3-1/4" H	5
FDL-SFK	Semi-Flush Accessory Kit For Fdl Flush-Mount Series			
FDL-SFK-BK	Semi-Flush Accessory Kit For Fdl Flush-Mount Series, Bk			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
FDL-10	**OPT-EM-FDL-10**	MOUNT IN EXTENDED BASE
FDL-12	**OPT-EM-FDL-12**	MOUNT IN EXTENDED BASE
FDL-14	**OPT-EM-FDL-14**	MOUNT IN EXTENDED BASE
FDL-16	**OPT-EM-FDL-16**	MOUNT IN EXTENDED BASE
FDL-18	**OPT-EM-FDL-18**	INTERNAL

SENSOR	DESCRIPTION
OPT-SEN-2US	MICROWAVE
OPT-SEN-NLS-FDL	WG NETWORK SENSOR
OPT-SEN-KEILTON-FDL	KEILTON NETWORK SENSOR
WEC-3RC	REMOTE CONTROL

PHOTOCELL	DESCRIPTION
OPT-PC-FM	BUTTON WITH AUXILIARY BASE

277V OPTION	DESCRIPTION
OPT-277V-FDL-10	EXTERNAL BOX
OPT-277V-FDL-12	EXTERNAL BOX
OPT-277V-FDL-14	EXTERNAL BOX
OPT-277V-FDL-16	EXTERNAL BOX
OPT-277V-FDL-18	INTERNAL

POWDER COATING
N/A

FDLO-32-MCT5-Bk

FDLO-32-MCT5-BN

32" OVAL CEILING DOUBLE-RING FLUSH MOUNT

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
FDLO-32-MCT5-BN	48W	3000LM	27K/30K/35K/40K/50K - Brushed Nickel	1
FDLO-32-MCT5-BK	48W	3000LM	27K/30K/35K/40K/50K - Black	1

FODL-12HL-MCTP5-DD

FODL-SK6

HIGH-LUMENS DUAL-LENS OUTDOOR CEILING LIGHT, DUAL DIMMING SELECTABLE POWER & CC

CATALOG NO.	DESCRIPTION			PCK QTY
FODL-12HL-MCTP5-DD	15W/20W/25W	120LM/W	27K/30K/35K/40K/50K	6
FODL-16HL-MCTP5-DD	20W/25W/30W	120LM/W	27K/30K/35K/40K/50K	4
FODL-SK6	FOLD 6FT Suspension Pendant Kit			

TRIAC DIMMABLE · EM CAPABLE · SENSOR OPTION · MCT 5

FSL-11-MCT5

FSL-11-MCT5-GD

LED 5CCT SINGLE RING FLUSH MOUNT

CATALOG NO.	DESCRIPTION			PCK QTY
FSL-11-MCT5	16W	1200LM	27K/30K/35K/40K/50K - 11"	8
FSL-11-MCT5-GD	16W	1200LM	27K/30K/35K/40K/50K - 11" Gold	8
FSL-13-MCT5	20W	1500LM	27K/30K/35K/40K/50K - 13"	8
FSL-13-MCT5-GD	20W	1500LM	27K/30K/35K/40K/50K - 13" Gold	8
FSL-15-MCT5	24W	1800LM	27K/30K/35K/40K/50K - 15"	8
FSL-15-MCT5-GD	24W	1800LM	27K/30K/35K/40K/50K - 15" Gold	8

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
FSL-11	**OPT-EM-FSL-11**	MOUNT IN EXTENDED BASE
FSL-13	**OPT-EM-FSL-13**	MOUNT IN EXTENDED BASE
FSL-15	**OPT-EM-FSL-15**	MOUNT IN EXTENDED BASE

SENSOR	DESCRIPTION
OPT-SEN-2US	MICROWAVE BI-LEVEL DIMMING
OPT-SEN-NLS-FSL	WG NETWORK SENSOR
OPT-SEN-KEILTON-FSL	KEILTON NETWORK SENSOR
WEC-3RC	REMOTE CONTROL

PHOTOCELL	DESCRIPTION
OPT-PC-FM	BUTTON WITH AUXILIARY BASE

277V OPTION	DESCRIPTION
OPT-277V-FSL-11	EXTERNAL BOX
OPT-277V-FSL-13	EXTERNAL BOX
OPT-277V-FSL-15	EXTERNAL BOX

POWDER COATING
N/A

TRIAC DIMMABLE · DAMP LOCATIONS · EM CAPABLE

FCRB-11HL-MCT5

LED 5CCT CLOUD FIXTURES 120V

CATALOG NO.	DESCRIPTION			PCK QTY
FCRB-11HL-MCT5	20W	1500LM	27K/30K/35K/40K/50K - 11" DIA	8
FCRB-14-MCT5	20W	1500LM	27K/30K/35K/40K/50K - 14" DIA	8
FCRB-16-MCT5	20W	1500LM	27K/30K/35K/40K/50K - 16" DIA	8

FCR-11-MCT5

LED 5CCT CLOUD FIXTURES 120V

CATALOG NO.	DESCRIPTION			PCK QTY
FCR-11-MCT5	16W	1200LM	27K/30K/35K/40K/50K - 11" DIA	8
FCR-14-MCT5	24W	1800LM	27K/30K/35K/40K/50K - 14" DIA	8

FCS-11HL-MCT5

LED 5CCT CLOUD FIXTURES 120V

CATALOG NO.	DESCRIPTION			PCK QTY
FCS-11HL-MCT5	20W	1500LM	27K/30K/35K/40K/50K - 11" DIA	8
FCS-13-MCT5	20W	1800LM	27K/30K/35K/40K/50K - 13" DIA	8

FCS-11-12W-40K

SHOWN WITH EM

SHOWN WITH EM

LED CLOUD FIXTURES 120V

CATALOG NO.	DESCRIPTION			PCK QTY
FCS-11-12W-40K	15W	1100LM	4000K - 11" DIA	2

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION
FCR-11	OPT-EM-FCR11	INTERNAL
FCR-14	OPT-EM-FCR14	INTERNAL
FCS11, FCS11HL	OPT-EM-FCS11	INTERNAL
FCS14	OPT-EM-FCS14	INTERNAL
FCS13	OPT-EM-FCS13	INTERNAL

SENSOR	DESCRIPTION
OPT-SEN-2US	MICROWAVE
OPT-SEN-NLS-FCS	WG NETWORK SENSOR
OPT-SEN-KEILTON-FCS	KEILTON NETWORK SENSOR
OPT-SEN-2USRC	OPTIONAL RC

PHOTOCELL	DESCRIPTION
OPT-PC-FM	BUTTON WITH AUXILIARY BASE

277V OPTION	DESCRIPTION
OPT-277V-FCR-11	EXTERNAL BOX
OPT-277V-FCS-11	EXTERNAL BOX
OPT-277V-FCS-11HL	EXTERNAL BOX
OPT-277V-FCS-13	EXTERNAL BOX

POWDER COATING
N/A

FMHT-WH

FMHT-BK

FMHR-WH

FMHR-BK

FLUSH MOUNT FIXTURES 120V

CATALOG NO.	DESCRIPTION			PCK QTY
FREE FORM FLUSH MOUNT FIXTURES - 120V				
FMHT-16-MCT5-WH	20W	1400LM	27K/30K/35K/40K/50K - 16" White	1
FMHT-16-MCT5-BK	20W	1400LM	27K/30K/35K/40K/50K - 16" Black	1
FMHT-20-MCT5-WH	30W	2100LM	27K/30K/35K/40K/50K - 20" White	1
FMHT-20-MCT5-BK	30W	2100LM	27K/30K/35K/40K/50K - 20"Black	1
FMHT-24-MCT5-WH	40W	2800LM	27K/30K/35K/40K/50K - 24" White	1
FMHT-24-MCT5-BK	40W	2800LM	27K/30K/35K/40K/50K - 24" Black	1
ROUND FLUSH MOUNT FIXTURES - 120V				
FMHR-15-MCT5-WH	20W	1400LM	27K/30K/35K/40K/50K - 15" White	1
FMHR-15-MCT5-BK	20W	1400LM	27K/30K/35K/40K/50K - 15" Black	1
FMHR-19-MCT5-WH	30W	2100LM	27K/30K/35K/40K/50K - 19" White	1
FMHR-19-MCT5-BK	30W	2100LM	27K/30K/35K/40K/50K - 19" Black	1
FMHR-23-MCT5-WH	30W	2100LM	27K/30K/35K/40K/50K - 23" White	1
FMHR-23-MCT5-BK	30W	2100LM	27K/30K/35K/40K/50K - 23" Black	1



FMLU-R12-MCT5-BK



FMLU-R12-MCT5-WH

12" FLUSH-MOUNT LIGHT WITH UPLIGHT, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
FMLU-R12-MCT5-BK	25W	1600LM	27K/30K/35K/40K/50K - 12" Black	6
FMLU-R12-MCT5-WH	25W	1600LM	27K/30K/35K/40K/50K - 12" White	6

FEL

FEL-SEN

FEL-TRM-BK

FEL-TRM-BN

FEL-TRM-GD

5CCT EDGE-LESS ARCHITECTURAL FLUSH MOUNT

CATALOG NO.	DESCRIPTION			PCK QTY
5CCT EDGE-LESS ARCHITECTURAL FLUSH MOUNT				
FEL-R6-MCT5	10W	700LM	27K/30K/35K/40K/50K - 6"	20
FEL-R8-MCT5	15W	1050LM	27K/30K/35K/40K/50K - 8"	10
FEL-R10-MCT5	20W	1400LM	27K/30K/35K/40K/50K - 10"	10
FEL-R12-MCT5	25W	1750LM	27K/30K/35K/40K/50K - 12"	5
FEL-R14-MCT5	30W	2100LM	27K/30K/35K/40K/50K - 14"	5
5CCT EDGE-LESS ARCHITECTURAL FLUSH MOUNT WITH PRE-INSTALLED MOTION SENSOR				
FEL-R6-MCT5-SEN	10W	700LM	27K/30K/35K/40K/50K - 6"	20
FEL-R8-MCT5-SEN	15W	1050LM	27K/30K/35K/40K/50K - 8"	10
FEL-R10-MCT5-SEN	20W	1400LM	27K/30K/35K/40K/50K - 10"	10
FEL-R12-MCT5-SEN	25W	1750LM	27K/30K/35K/40K/50K - 12"	5
FEL-R14-MCT5-SEN	30W	2100LM	27K/30K/35K/40K/50K - 14"	5
TRIM ACCESSORIES				
FEL-R6-TRM-BK	FEL-R6 Decorative Trim Black			
FEL-R6-TRM-BN	FEL-R6 Decorative Trim Brushed Nickel			
FEL-R6-TRM-GD	FEL-R6 Decorative Trim Gold			
FEL-R8-TRM-BK	FEL-R8 Decorative Trim Black			
FEL-R8-TRM-BN	FEL-R8 Decorative Trim Brushed Nickel			
FEL-R8-TRM-GD	FEL-R8 Decorative Trim Gold			
FEL-R10-TRM-BK	FEL-R1 Decorative Trim Black			
FEL-R10-TRM-BN	FEL-R10 Decorative Trim Brushed Nickel			
FEL-R10-TRM-GD	FEL-R10 Decorative Trim Gold			
FEL-R12-TRM-BK	FEL-R12 Decorative Trim Black			
FEL-R12-TRM-BN	FEL-R12 Decorative Trim Brushed Nickel			
FEL-R12-TRM-GD	FEL-R12 Decorative Trim Gold			
FEL-R14-TRM-BK	FEL-R14 Decorative Trim Black			
FEL-R14-TRM-BN	FEL-R14 Decorative Trim Brushed Nickel			
FEL-R14-TRM-GD	FEL-R14 Decorative Trim Gold			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	VANDAL RES.	DESCRIPTION
FEL-R6	**OPT-EM-FEL-R6**	MOUNT IN EXTENDED BASE	**N/A**	N/A
FEL-R8	**OPT-EM-FEL-R8**	MOUNT IN EXTENDED BASE	**SENSOR**	DESCRIPTION
FEL-R10	**OPT-EM-FEL-R10**	MOUNT IN EXTENDED BASE	**N/A**	N/A
FEL-R12	**OPT-EM-FEL-R12**	MOUNT IN EXTENDED BASE	**POWDER COATING**	
FEL-R14	**OPT-EM-FEL-R14**	MOUNT IN EXTENDED BASE	**N/A**	

EM CAPABLE

CONTRACTOR-FRIENDLY SNAP-IN FLUSH MOUNT SERIES, 5CCT E26 VER. INCL. RECESS ACCESSORIES

CATALOG NO.	DESCRIPTION			PCK QTY
CONTRACTOR-FRIENDLY SNAP-IN FLUSH MOUNT SERIES, 5CCT, 120V				
FMLS-R5-MCT5-DT	11W	680LM	27K/30K/35K/40K/50K - 5"	12
FMLS-R7-MCT5-DT	14W	900LM	27K/30K/35K/40K/50K - 7"	12
FMLS-R9-MCT5-DT	20W	1300LM	27K/30K/35K/40K/50K - 9"	8
FMLS-R11-MCT5-DT	25W	1650LM	27K/30K/35K/40K/50K - 11"	8
DUAL-DIMMING CONTRACTOR-FRIENDLY SNAP-IN FLUSH MOUNT SERIES, 5CCT AVAIL. WITH SLIM, 120-277V				
FMLS-R5-MCT5-DD	11W	680LM	27K/30K/35K/40K/50K - 5"	12
FMLS-R7-MCT5-DD	14W	1000LM	27K/30K/35K/40K/50K - 7"	12
FMLS-R9-MCT5-DD	20W	1600LM	27K/30K/35K/40K/50K - 9"	8
FMLS-R11-MCT5-DD	25W	2000LM	27K/30K/35K/40K/50K - 11"	8
FMLS-R7-MCT5-DD-EM	14W	1000LM	27K/30K/35K/40K/50K - 7"	8
FMLS-R9-MCT5-DD-EM	20W	1600LM	27K/30K/35K/40K/50K - 9"	8



TRIMS FOR FMLS SERIES

CATALOG NO.	DESCRIPTION
FMLS-R5-TRIM-BK	FMLS-R5 Accessory Trim, Black
FMLS-R7-TRIM-BK	FMLS-R7 Accessory Trim, Black
FMLS-R9-TRIM-BK	FMLS-R9 Accessory Trim, Black
FMLS-R11-TRIM-BK	FMLS-R11 Accessory Trim, Black
FMLS-R7-TRIM-BK-EM	FMLS-R7 Accessory Trim, Black, EM VERSION
FMLS-R9-TRIM-BK-EM	FMLS-R9 Accessory Trim, Black, EM VERSION
FMLS-R5-TRIM-BN	FMLS-R5 Accessory Trim, Brushed Nickel
FMLS-R7-TRIM-BN	FMLS-R7 Accessory Trim, Brushed Nickel
FMLS-R9-TRIM-BN	FMLS-R9 Accessory Trim, Brushed Nickel
FMLS-R11-TRIM-BN	FMLS-R11 Accessory Trim, Brushed Nickel
FMLS-R7-TRIM-BN-EM	FMLS-R7 Accessory Trim, Brushed Nickel, EM VERSION
FMLS-R9-TRIM-BN-EM	FMLS-R9 Accessory Trim, Brushed Nickel, EM VERSION

FMLT-R7-MCT5

ULTRA-ECONOMY QUICK-INSTALL FLUSH-MOUNT LIGHT **120V** 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
FMLT-R5-MCT5	10W	740LM	27K/30K/35K/40K/50K - 5"	20
FMLT-R7-MCT5	15W	1260LM	27K/30K/35K/40K/50K - 7"	20
FMLT-R9-MCT5	18W	1440LM	27K/30K/35K/40K/50K - 9"	10
FMLT-R12-MCT5	24W	2150LM	27K/30K/35K/40K/50K - 12"	5

FMLE-R9-MCT5-E26

WHILE SUPPLIES LAST

BUILDER COMPOSITE SERIES DECORATIVE FLUSH MOUNT FIXTURE **120V**

5CCT E26 VER. INCL. (EXCEPT R12) RECESS ACCESSORIES

CATALOG NO.	DESCRIPTION			PCK QTY
FMLE-R5-MCT5-E26	9W	650LM	27K/30K/35K/40K/50K - 5"	20
FMLE-R9-MCT5-E26	17W	1300LM	27K/30K/35K/40K/50K - 9"	10
FMLE-R12-MCT5	21W	1500LM	27K/30K/35K/40K/50K - 12"	5

FML-R18-MCT5-URG-010V

COMMERCIAL FLUSH MOUNT SERIES UGR<19 LOW-GLARE, 0-10V DIMMABLE, **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
FML-R6-MCT5-UGR-010V	11W	660LM	27K/30K/35K/40K/50K - 6"	20
FML-R8-MCT5-UGR-010V	14W	980LM	27K/30K/35K/40K/50K - 8"	10
FML-R10-MCT5-UGR-010V	17W	1020LM	27K/30K/35K/40K/50K - 10"	10
FML-R12-MCT5-UGR-010V	22W	1540LM	27K/30K/35K/40K/50K - 12"	10
FML-R14-MCT5-UGR-010V	26W	1560LM	27K/30K/35K/40K/50K - 14"	5
FML-R16-MCT5-UGR-010V	30W	2100LM	27K/30K/35K/40K/50K - 16"	5
FML-R18-MCT5-UGR-010V	35W	2450LM	27K/30K/35K/40K/50K - 18"	3
FML-R20-MCT5-UGR-010V	40W	2800LM	27K/30K/35K/40K/50K - 20"	3
FML-R22-MCT5-UGR-010V	45W	3150LM	27K/30K/35K/40K/50K - 22"	3
FML-R24-MCT5-UGR-010V	50W	3500LM	27K/30K/35K/40K/50K - 24"	3

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
FML-R6	**OPT-EM-FML-R6**	MOUNT IN EXTENDED BASE	**OPT-PC-FML8**	BUTTON
FML-R8	**OPT-EM-FML-R8**	MOUNT IN EXTENDED BASE	**OPT-PC-FML10**	BUTTON
FML-R10	**OPT-EM-FML-R10**	MOUNT IN EXTENDED BASE	**277V OPTION**	DESCRIPTION
FML-R12	**OPT-EM-FML-R12**	MOUNT IN EXTENDED BASE	**OPT-277V-FML-R8**	EXTERNAL BOX
FML-R14	**OPT-EM-FML-R14**	MOUNT IN EXTENDED BASE	**OPT-277V-FML-R10**	EXTERNAL BOX
FML-R16	**OPT-EM-FML-R16**	EXTERNAL EM PACKAGE	**SENSOR**	DESCRIPTION
FML-R18	**OPT-EM-FML-R18**	EXTERNAL EM PACKAGE	**N/A**	N/A
FML-R20	**OPT-EM-FML-R20**	EXTERNAL EM PACKAGE	**POWDER COATING**	
FML-R22	**OPT-EM-FML-R22**	EXTERNAL EM PACKAGE	**N/A**	

FML-R14-MCT5-URG

FLUSH MOUNT SERIES, UGR<19 LOW-GLARE

CATALOG NO.	DESCRIPTION			PCK QTY
FML-R6-MCT5-UGR	11W	700LM	27K/30K/35K/40K/50K - 6"	20
FML-R8-MCT5-UGR	14W	980LM	27K/30K/35K/40K/50K - 8"	10
FML-R10-MCT5-UGR	17W	1190LM	27K/30K/35K/40K/50K - 10"	10
FML-R12-MCT5-UGR	22W	1540LM	27K/30K/35K/40K/50K - 12"	10
FML-R14-MCT5-UGR	26W	1820LM	27K/30K/35K/40K/50K - 14"	5
FML-R16-MCT5-UGR	30W	2100LM	27K/30K/35K/40K/50K - 16"	5
FML-R18-MCT5-UGR	35W	2450LM	27K/30K/35K/40K/50K - 18"	3
FML-R20-MCT5-UGR	40W	2800LM	27K/30K/35K/40K/50K - 20"	3
FML-R22-MCT5-UGR	45W	3150LM	27K/30K/35K/40K/50K - 22"	3
FML-R24-MCT5-UGR	50W	3500LM	27K/30K/35K/40K/50K - 24"	3

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
FML-R6	**OPT-EM-FML-R6**	MOUNT IN EXTENDED BASE	**OPT-PC-FML8**	BUTTON
FML-R8	**OPT-EM-FML-R8**	MOUNT IN EXTENDED BASE	**OPT-PC-FML10**	BUTTON
FML-R10	**OPT-EM-FML-R10**	MOUNT IN EXTENDED BASE	**277V OPTION**	DESCRIPTION
FML-R12	**OPT-EM-FML-R12**	MOUNT IN EXTENDED BASE	**OPT-277V-FML-R8**	EXTERNAL BOX
FML-R14	**OPT-EM-FML-R14**	MOUNT IN EXTENDED BASE	**OPT-277V-FML-R10**	EXTERNAL BOX
FML-R16	**OPT-EM-FML-R16**	EXTERNAL EM PACKAGE	**SENSOR**	DESCRIPTION
FML-R18	**OPT-EM-FML-R18**	EXTERNAL EM PACKAGE	**N/A**	N/A
FML-R20	**OPT-EM-FML-R20**	EXTERNAL EM PACKAGE	**POWDER COATING**	
FML-R22	**OPT-EM-FML-R22**	EXTERNAL EM PACKAGE	**N/A**	

TC-FML-12-22W-RGBW-WIFI

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW FLUSH MOUNT FIXTURE **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-FML-8-14W-RGBW-WIFI	14W	980LM	RGBW	20
TC-FML-10-17W-RGBW-WIFI	17W	1190LM	RGBW	20
TC-FML-12-22W-RGBW-WIFI	22W	1540LM	RGBW	20
TC-FML-14-26W-RGBW-WIFI	26W	1820LM	RGBW	20

FML-R8-MCT

SHOWN WITH EM BASE

SHOWN WITH FML-SKG

SHOWN WITH FML-RK-712

SPEC SERIES ARCHITECTURAL DIE-CAST FLUSH MOUNT FIXTURE **120V**, 3CCT

CATALOG NO.	DESCRIPTION			PCK QTY
FML-R6-MCT	11W	660LM	30K/40K/50K - 6"	20
FML-R8-MCT	14W	840LM	30K/40K/50K - 8"	10
FML-R10-MCT	17W	1020LM	30K/40K/50K - 10"	10
FML-R18-MCT	30W	2100LM	30K/40K/50K - 18"	5
FML-ULK-MCT	15W	850LM	30K/40K/50K	
FML-RK-712	7" OR 12" ROD KIT FOR FML FOR 18" & 22" FML SERIES			
FML-SK6	6FT ADJUSTABLE SUSPENSION KIT FOR 18" & 22" FML SERIES			

FML-R6-11W-50K

FML-S6-11W-50K

WHILE SUPPLIES LAST

ARCHITECTURAL FLUSH MOUNT SURFACE FIXTURE **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
FML-R6-11W-50K	11W	550LM	5000K - 6" DIAMETER	20
FML-R8-14W-50K	14W	750LM	5000K - 8" DIAMETER	10
FML-S6-11W-50K	11W	550LM	5000K - 6" X 6"	20
FML-S8-14W-30K	14W	750LM	3000K - 8" X 8"	20
FML-S10-17W-30K	17W	950LM	3000K - 10" X 10"	20

FML-R6-TRM-BK

FML-R6-TRM-BN

FML-R6-TRM-BR

FML COLOR TRIM (CLIP ON)

CATALOG NO.	DESCRIPTION
FML-R6-TRM-BK	6" ROUND TRIM FOR FML-R6 SERIES, BLACK FINISH
FML-R6-TRM-BN	6" ROUND TRIM FOR FML-R6 SERIES, BRUSHED NICKEL FINISH
FML-R6-TRM-BR	6" ROUND TRIM FOR FML-R6 SERIES, BRONZE FINISH
FML-R8-TRM-BK	8" ROUND TRIM FOR FML-R6 SERIES, BLACK FINISH
FML-R8-TRM-BN	8" ROUND TRIM FOR FML-R6 SERIES, BRUSHED NICKEL FINISH
FML-R8-TRM-BR	8" ROUND TRIM FOR FML-R6 SERIES, BRONZE FINISH
FML-R10-TRM-BK	10" ROUND TRIM FOR FML-R6 SERIES, BLACK FINISH
FML-R10-TRM-BN	10" ROUND TRIM FOR FML-R6 SERIES, BRUSHED NICKEL FINISH
FML-R10-TRM-BR	10" ROUND TRIM FOR FML-R6 SERIES, BRONZE FINISH

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	PHOTOCELL	DESCRIPTION
FML-R6	**OPT-EM-FML-R6**	MOUNT IN EXTENDED BASE	**OPT-PC-FML8**	BUTTON
FML-R8	**OPT-EM-FML-R8**	MOUNT IN EXTENDED BASE	**OPT-PC-FML10**	BUTTON
FML-R10	**OPT-EM-FML-R10**	MOUNT IN EXTENDED BASE	**277V OPTION**	DESCRIPTION
FML-R12	**OPT-EM-FML-R12**	MOUNT IN EXTENDED BASE	**OPT-277V-FML-R8**	EXTERNAL BOX
FML-R14	**OPT-EM-FML-R14**	MOUNT IN EXTENDED BASE	**OPT-277V-FML-R10**	EXTERNAL BOX
FML-R16	**OPT-EM-FML-R16**	EXTERNAL EM PACKAGE	**SENSOR**	DESCRIPTION
FML-R18	**OPT-EM-FML-R18**	EXTERNAL EM PACKAGE	**N/A**	N/A
FML-R20	**OPT-EM-FML-R20**	EXTERNAL EM PACKAGE	**POWDER COATING**	
FML-R22	**OPT-EM-FML-R22**	EXTERNAL EM PACKAGE	**N/A**	


ELB-09120-AC-JB

EM BACKUP, 4" SQARE J-BOX WITH FLAT BRACKET

CATALOG NO.	DESCRIPTION
ELB-09120-AC-JB	4in SQARE J-BOX WITH FLAT BRACKET FOR CEILING L IGHTS WITH 9W AC-CONNECT

FMLB

FMLB-SEN

FMLB-TRM-ALAB-BK

FMLB-TRM-ALAB-GD

FMLB-TRM-ALAB-BN

FMLB-TRM-BN

FMLB-TRM-BK

BUILDER SERIES FLUSH MOUNT FIXTURE - 5CCT - 120V

CATALOG NO.	DESCRIPTION			PCK QTY
FMLB-R5-MCT5	8W	560LM	27K/30K/35K/40K/50K - 5"	
FMLB-R7-MCT5	12W	900LM	27K/30K/35K/40K/50K - 7"	
FMLB-R9-MCT5	18W	1440LM	27K/30K/35K/40K/50K - 9"	20
FMLB-R12-MCT5	24W	2000LM	27K/30K/35K/40K/50K - 12"	
FMLB-R15-MCT5	36W	3050LM	27K/30K/35K/40K/50K - 15"	
BUILDER SERIES FLUSH MOUNT FIXTURES WITH SENSOR				
FMLB-R7-MCT5-SEN	12W	900LM	27K/30K/35K/40K/50K - 7"	
QUICK SHIP **FMLB-R9-MCT5-SEN**	18W	1440LM	27K/30K/35K/40K/50K - 9"	20
FMLB-R12-MCT5-SEN	24W	2000LM	27K/30K/35K/40K/50K - 12"	
FMLB-R15-MCT5-SEN	36W	3050LM	27K/30K/35K/40K/50K - 15"	
FMLB-SEN-RC	Remote Control For FMLB Sensor Series			
COLOR TRIM ACCESSORIES				
FMLB-R5-TRM-BN	FMLB-R5 Color Trim - Brushed Nickel			
FMLB-R5-TRM-BK	FMLB-R5 Color Trim - Black			
FMLB-R7-TRM-BN	FMLB-R7 Color Trim - Brushed Nickel			
FMLB-R7-TRM-BK	FMLB-R7 Color Trim - Black			
FMLB-R9-TRM-BN	FMLB-R9 Color Trim - Brushed Nickel			
FMLB-R9-TRM-BK	FMLB-R9 Color Trim - Black			
FMLB-R12-TRM-BN	FMLB-R12 Color Trim - Brushed Nickel			
FMLB-R12-TRM-BK	FMLB-R12 Color Trim - Black			
FMLB-R15-TRM-BN	FMLB-R12 Color Trim - Brushed Nickel			
FMLB-R15-TRM-BK	FMLB-R12 Color Trim - Black			
ALABASTER STONE LENSES WITH METAL TRIMS				
FMLB-R7-TRM-ALAB-BK	FMLB-R7 Real Alabaster Lens With Trim - Black			
FMLB-R7-TRM-ALAB-GD	FMLB-R7 Real Alabaster Lens With Trim - Gold			
FMLB-R7-TRM-ALAB-BN	FMLB-R7 Real Alabaster Lens With Trim - Brushed Nickel			
FMLB-R9-TRM-ALAB-BK	FMLB-R9 Real Alabaster Lens With Trim - Black			
FMLB-R9-TRM-ALAB-GD	FMLB-R9 Real Alabaster Lens With Trim - Gold			
FMLB-R9-TRM-ALAB-BN	FMLB-R9 Real Alabaster Lens With Trim - Brushed Nickel			
FMLB-R12-TRM-ALAB-BK	FMLB-R12 Real Alabaster Lens With Trim - Black			
FMLB-R12-TRM-ALAB-GD	FMLB-R12 Real Alabaster Lens With Trim - Gold			
FMLB-R12-TRM-ALAB-BN	FMLB-R12 Real Alabaster Lens With Trim - Brushed Nickel			

FMLB-WP-R7-MCT5-DD | FMLB-WP-R9-MCT5-DD | FMLB-WP-R12-MCT5-DD | FMLB-WP-R15-MCT5-DD

FMLB-WP-R9-TRM-BH1-BK | FMLB-WP-R9-TRM-BH1-BR | FMLB-WP-R9-TRM-BH1-GD

WET LOCATION BUILDER SERIES FLUSH MOUNT FIXTURES - 5CCT - 120-277V

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	PCK QTY
FMLB-WP-R7-MCT5-DD	12W	1200LM	27K/30K/35K/40K/50K	20
FMLB-WP-R9-MCT5-DD	18W	1890LM	27K/30K/35K/40K/50K	20
FMLB-WP-R12-MCT5-DD	24W	2760LM	27K/30K/35K/40K/50K	10
FMLB-WP-R15-MCT5-DD	36W	4320LM	27K/30K/35K/40K/50K	10
FMLB-WP-R9-TRM-BH1-BK	9in Bulk-Head Trim For Fmlb-Wp-R9 Wet Loc Surface-Mt - Black			
FMLB-WP-R9-TRM-BH1-BR	9in Bulk-Head Trim For Fmlb-Wp-R9 Wet Loc Surface-Mt - Bronze Ral 8019			
FMLB-WP-R9-TRM-BH1-GD	9in Bulk-Head Trim For Fmlb-Wp-R9 Wet Loc Surface-Mt - Gold			

FMLB-R5-MCT5-REG-BK | FMLB-R5-MCT5-REG-WH

REGRESSED CEILING LIGHT BUILT WITH FMLB FIXTURES INCLUDED, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
FMLB-R5-MCT5-REG-WH	8W	560LM	27K/30K/35K/40K/50K - White	1
FMLB-R5-MCT5-REG-BK	8W	560LM	27K/30K/35K/40K/50K - Black	1
FMLB-R7-MCT5-REG-WH	12W	900LM	27K/30K/35K/40K/50K - White	1
FMLB-R7-MCT5-REG-BK	12W	900LM	27K/30K/35K/40K/50K - Black	1
FMLB-R9-MCT5-REG-WH	18W	1440LM	27K/30K/35K/40K/50K - White	1
FMLB-R9-MCT5-REG-BK	18W	1440LM	27K/30K/35K/40K/50K - Black	1
FMLB-R12-MCT5-REG-WH	24W	2000LM	27K/30K/35K/40K/50K - White	1
FMLB-R12-MCT5-REG-BK	24W	2000LM	27K/30K/35K/40K/50K - Black	1
FMLB-R15-MCT5-REG-WH	36W	3050LM	27K/30K/35K/40K/50K - White	1
FMLB-R15-MCT5-REG-BK	36W	3050LM	27K/30K/35K/40K/50K - Black	1



FMLB-R9-MCT5-FMF12-BG



FMLB-R9-MCT5-FMF12-WG

CEILING LIGHT BUILT WITH FMLB FIXTURES INCLUDED, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
FMLB-R9-MCT5-FMF12-WG	18W	1440LM	27K/30K/35K/40K/50K - 9" White/Gold	1
FMLB-R9-MCT5-FMF12-BG	18W	1440LM	27K/30K/35K/40K/50K - 9" Black/Gold	1
FMLB-R12-MCT5-FMF15-WG	24W	2000LM	27K/30K/35K/40K/50K - 12" White/Gold	1
FMLB-R12-MCT5-FMF15-BG	24W	2000LM	27K/30K/35K/40K/50K - 12" Black/Gold	1

TRIAC DIMMABLE

MCT 5

FMLB-CMC5S

White Black

FMLB-CMC7S

White Black

FMLB-CMC7

White Black

FMLB-CMC9FL

White Black

White/Gold Black/Gold

White/Gold Black/Gold

White/Gold Black/Gold

CYLINDER BUILT WITH FMLB FIXTURES INCLUDED, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
FMLB-R5-MCT5-CMC5S-WH	8W	560LM	27K/30K/35K/40K/50K - White	1
FMLB-R5-MCT5-CMC5S-BK	8W	560LM	27K/30K/35K/40K/50K - Black	1
FMLB-R5-MCT5-CMC5S-WG	8W	560LM	27K/30K/35K/40K/50K - White/Gold	1
FMLB-R5-MCT5-CMC5S-BG	8W	560LM	27K/30K/35K/40K/50K - Black/Gold	1
FMLB-R7-MCT5-CMC7S-WH	12W	900LM	27K/30K/35K/40K/50K - White	1
FMLB-R7-MCT5-CMC7S-BK	12W	900LM	27K/30K/35K/40K/50K - Black	1
FMLB-R7-MCT5-CMC7S-WG	12W	900LM	27K/30K/35K/40K/50K - White/Gold	1
FMLB-R7-MCT5-CMC7S-BG	12W	900LM	27K/30K/35K/40K/50K - Black/Gold	1
FMLB-R7-MCT5-CMC7-WH	12W	900LM	27K/30K/35K/40K/50K - White	1
FMLB-R7-MCT5-CMC7-BK	12W	900LM	27K/30K/35K/40K/50K - Black	1
FMLB-R7-MCT5-CMC7-WG	12W	900LM	27K/30K/35K/40K/50K - White/Gold	1
FMLB-R7-MCT5-CMC7-BG	12W	900LM	27K/30K/35K/40K/50K - Black/Gold	1
FMLB-R9-MCT5-CMC9FL-WH	18W	1440LM	27K/30K/35K/40K/50K - White	1
FMLB-R9-MCT5-CMC9FL-BK	18W	1440LM	27K/30K/35K/40K/50K - Black	1

FMLB SERIES ACCESSORIES

CATALOG NO.	DESCRIPTION
FMLB-CS-10FT-WH	FMLB 10FT Suspension Cord And Canopy Accessory - White
FMLB-CS-10FT-BK	FMLB 10FT Suspension Cord And Canopy Accessory - Black
FMLB-CSC-10FT-WH	FMLB Canopy And Cord Pendant Cylinder Accessory 10FT White
FMLB-CSC-10FT-BK	FMLB Canopy And Cord Pendant Cylinder Accessory 10FT Black
FMLB-SRK-412-3W-WH	FMLB Downrod Kit Pendant Cylinder Accessory 4X1FT 3-Wire White
FMLB-SRK-412-3W-BK	FMLB Downrod Kit Pendant Cylinder Accessory 4X1FT 3-Wire Black

SURFACE MOUNT LIGHTS

LCFF

SHOWN WITH ROD & CANOPY

SHOWN WITH SUSPENSION KIT & CANOPY



LCFF-WS

LED 5CCT INTEGRATED LED FABRIC DRUM

CATALOG NO.	DESCRIPTION			PCK QTY
LCFF-15-MCT5-BR	25W	1400LM	27K/30K/35K/40K/50K - 15" Bronze	2
LCFF-18-MCT5-BR	35W	1800LM	27K/30K/35K/40K/50K - 18" Bronze	2
LCFF-22-MCT5-BR	45W	2100LM	27K/30K/35K/40K/50K - 22" Bronze	2
LCFF-15-MCT5-BN	25W	1400LM	27K/30K/35K/40K/50K - 15" Brushed Nickel	2
LCFF-18-MCT5-BN	35W	1800LM	27K/30K/35K/40K/50K - 18" Brushed Nickel	2
LCFF-22-MCT5-BN	45W	2100LM	27K/30K/35K/40K/50K - 22" Brushed Nickel	2

INTEGRATED LED MODERN WALL SCONCE

LCFF-WS-WH	10W	500LM	27K/30K/35K/40K/50K - White	5
LCFF-WS-BR	10W	500LM	27K/30K/35K/40K/50K - Bronze	5
LCFF-WS-BN	10W	500LM	27K/30K/35K/40K/50K - Brushed Nickel	5

LCF-ROD-5-BR	5In Suspension Rod For Ceiling Fixture Swivel Canopy, Bronze
LCF-ROD-12-BR	12In Suspension Rod For Ceiling Fixture Swivel Canopy, Bronze
LCF-ROD-24-BR	24In Suspension Rod For Ceiling Fixture Swivel Canopy, Bronze
LCF-ROD-36-BR	36In Suspension Rod For Ceiling Fixture Swivel Canopy, Bronze
LCF-ROD-48-BR	48In Suspension Rod For Ceiling Fixture Swivel Canopy, Bronze
LCF-ROD-5-BN	5In Suspension Rod For Ceiling Fixture Swivel Canopy, Brushed Nickel
LCF-ROD-12-BN	12In Suspension Rod For Ceiling Fixture Swivel Canopy, Brushed Nickel
LCF-ROD-24-BN	24In Suspension Rod For Ceiling Fixture Swivel Canopy, Brushed Nickel
LCF-ROD-36-BN	36In Suspension Rod For Ceiling Fixture Swivel Canopy, Brushed Nickel
LCF-ROD-48-BN	48In Suspension Rod For Ceiling Fixture Swivel Canopy, Brushed Nickel
LCF-CANOPY-S-BR	Swivel Ceiling Canopy For Ceiling Fixtures, Bronze
LCF-CANOPY-S-BN	Swivel Ceiling Canopy For Ceiling Fixtures, Brushed Nickel
LFCF-SK10-BR	10Ft 4Line Canopy Suspension Kit For Decorative Lights, Bronze
LFCF-SK10-BN	10Ft 4Line Canopy Suspension Kit For Decorative Lights, Brushed Nickel
FML-ULK-MCT	15W, 850Lm, 30K/40K/50K Up Light Kit

FCD-13-MCT-BG

MODERN 3CCT FLUSH MOUNT DRUM

CATALOG NO.	DESCRIPTION			PCK QTY
FCD-13-MCT-BG	25W	2350LM	3000K/4000K/5000K - 13" Black/Gold	5
FCD-16-MCT-BG	30W	2800LM	3000K/4000K/5000K - 16" Black/Gold	5

LCEU-8-30K-WH | LCEU-8-30K-BK | LCEU-8-30K-CU | LCEU-12-30K-WH | LCEU-12-30K-BK | LCEU-12-30K-CU

EU PENDANT WITH INDIRECT LIGHT SOURCE

CATALOG NO.	DESCRIPTION			PCK QTY
LCEU-8-30K-WH	8W	395LM	3000K - 8" White With Copper Reflector	2
LCEU-8-30K-BK	8W	220LM	3000K - 8" Black With Copper Reflector	2
LCEU-8-30K-CU	8W	650LM	3000K - 8" Copper With White Reflector	2
LCEU-12-30K-WH	12W	815LM	3000K - 12" White With Copper Reflector	8
LCEU-12-30K-BK	12W	540LM	3000K - 12" Black With Copper Reflector	8
LCEU-12-30K-CU	12W	1400LM	3000K - 12" Copper With White Reflector	8

LCFC-MCT5-BK

LCFC-MCT5-WH

SHOWN WITH MODIFICATION ACCESSORY

5CCT INTEGRATED LED MODERN CONE PENDANT LIGHT, 12" DAI.- 5FT ADJ. CORD

CATALOG NO.	DESCRIPTION			PCK QTY
LCFC-MCT5-BK	25W	1300LM	27K/30K/35K/40K/50K - Black	2
LCFC-MCT5-WH	25W	1300LM	27K/30K/35K/40K/50K - White	2
LCFC-BF-ACC-GD	LCFC Pendant Modification Accessory, Electroplated Gold			
LCFC-BF-ACC-BN	LCFC Pendant Modification Accessory, Brushed Nickel			

LCFN-MCT5-BK

LCFN-MCT5-WH

NORDIC DESIGN PENDANT WITH LEATHER STRAP, INTEGRATED 5CCT LED - 10FT ADJ. CORD

CATALOG NO.	DESCRIPTION			PCK QTY
LCFN-MCT5-WH	25W	1400LM	27K/30K/35K/40K/50K - White	2
LCFN-MCT5-BK	25W	1400LM	27K/30K/35K/40K/50K - Black	2

LCFA-MCT5-BK

LCFA-MCT5-BK

SHOWN WITH
WIREGUARD BLACK

SHOWN WITH
WIREGUARD WHITE

12” INTEGRATED LED VINTAGE PENDANT LIGHT, 5CCT- 5FT ADJ. CORD

CATALOG NO.	DESCRIPTION			PCK QTY
LCFA-MCT5-BK	25W	1300LM	27K/30K/35K/40K/50K - Black (Copper Inside)	2
LCFA-MCT5-WH	25W	1300LM	27K/30K/35K/40K/50K - White Gloss (Copper Inside)	2
LCFA-WG-BK	LCFA Wire Guard, Black			
LCFA-WG-WH	LCFA Wire Guard, White			


LCFPM-MCT5-BK

LCFPM-MCT5-WH

5” MINI PAN PENDANT W/ 4.FT CORD, **120V** - 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LCFPM-MCT5-BK	10W	700LM	27K/30K/35K/40K/50K - Black	1
LCFPM-MCT5-WH	10W	700LM	27K/30K/35K/40K/50K - White	1

LCFS-MCT-BK
LCFS-MCT-WH

LCFQ-MCT-BK
All Black

LCFQ-MCT-BK
Shown with Brushed Nickel

LCFQ-MCT-BK
Shown with
Anodized Gold

LCFQ-MCT-WH
All White

LCFQ-MCT-WH
Shown with Brushed Nickel

LCFQ-MCT-WH
Shown with
Anodized Gold

LCFT-BK
Black

LCFT-WH
White

LCFT-BN
Brushed Nickel

Shown with
Acrylic Drop Lens

LCFW-MCTP-BK
Black

LCFW-MCTP-WH
White

LCFK-MCTP-BK
Black

LCFK-MCTP-WH
White

COMMERCIAL/RESIDENTIAL POWER & CCT-ADJUSTABLE CONE PENDANT

CATALOG NO.	DESCRIPTION			PCK QTY
M3T 3CCT CONE PENDANT WITH 5FT ADJ. DOWNROD, 7" DIAMETER				
LCFS-MCT-BK	6W/9W/12W	600LM Max.	30K/40K/50K - Black	4
LCFS-MCT-WH	6W/9W/12W	600LM Max.	30K/40K/50K - White	4
M3T 3CCT CONE PENDANT WITH 6FT ADJ. CORD, 6"DIAMETER				
LCFQ-MCT-BK	6W/9W/12W	600LM Max.	30K/40K/50K - Black	12
LCFQ-MCT-WH	6W/9W/12W	600LM Max.	30K/40K/50K - White	12
CMC2-TRMWM-AG	Replacement Trim Accessory, Anodized Gold			
CMC2-TRMWM-BN	Replacement Trim Accessory, Brushed Nickel			
MCTP POWER & CCT ADJUSTABLE TAPERED PENDANT WITH 6FT ADJ. CORD, 2"DIAMETER				
LCFT-MCTP-BK	3W/6W/9W	720LM Max.	30K/40K/50K - Black	8
LCFT-MCTP-WH	3W/6W/9W	720LM Max.	30K/40K/50K - White	8
LCFT-MCTP-BN	3W/6W/9W	720LM Max.	30K/40K/50K - Brushed Nickel	8
LCFT-DL25	LCFT 2in 25mm Acrylic Drop Lens			
MCTP WINE BOTTLE PENDANT, COMMERCIAL/RESIDENTIAL 10FT ADJ. CORD				
LCFW-MCTP-BK	6W/9W/12W	960LM Max.	30K/40K/50K - Black	4
LCFW-MCTP-WH	6W/9W/12W	960LM Max.	30K/40K/50K - White	4
MCTP COCONUT PENDANT, COMMERCIAL/RESIDENTIAL WITH 6FT ADJ. CORD, 6"DIAMETER				
LCFK-MCTP-BK	6W/9W/12W	960LM Max.	30K/40K/50K - Black	4
LCFK-MCTP-WH	6W/9W/12W	960LM Max.	30K/40K/50K - White	4

LCFI-WS-WH



LCFI-MCT5-WH

11" DECORATIVE 2-LEVEL PENDANT - 5FT ADJ. CORD

CATALOG NO.	DESCRIPTION			PCK QTY
LCFI-MCT5-WH	12W	600LM	27K/30K/35K/40K/50K - White	4
LCFI-MCT5-BK	12W	600LM	27K/30K/35K/40K/50K - Black	4
INTEGRATED LED MODERN WALL SCONCE				
LCFI-WS-WH	10W	500LM	27K/30K/35K/40K/50K - White	5
LCFI-WS-BK	10W	500LM	27K/30K/35K/40K/50K - Black	5

LCFL-MCT5-BG

LCFL-MCT5-WH

LCFL-WS-BG

12" MODERN DESIGNER LED PENDANT - 5FT ADJ. CORD

CATALOG NO.	DESCRIPTION			PCK QTY
LCFL-MCT5-WH	10W	500LM	27K/30K/35K/40K/50K - White	4
LCFL-MCT5-BG	10W	500LM	27K/30K/35K/40K/50K - Black/Gold	4
INTEGRATED LED MODERN WALL SCONCE				
LCFL-WS-WH	10W	500LM	27K/30K/35K/40K/50K - White	5
LCFL-WS-BG	10W	500LM	27K/30K/35K/40K/50K - Black/Gold	5

LDAP-10-MCT5

MODERN 3CCT FLUSH MOUNT DRUM

CATALOG NO.	DESCRIPTION			PCK QTY
LDAP-10-MCT5	12W	700LM	27K/30K/35K/40K/50K - BLACK, 10" Dia.	4
LDAP-14-MCT5	18W	900LM	27K/30K/35K/40K/50K - BLACK, 14" Dia.	4

LCFD-MCT-BK

LCFD-MCT-WH

LCFD-MCT-WS

LCFD-MCT-BG

LCFD-20-MCT-BG

LCFD-20-MCT-WS

LCFD-WS-BK

5CCT INTEGRATED LED MODERN DOME PENDANT LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
12" INTEGRATED LED MODERN DOME PENDANT LIGHTS, 5CCT				
LCFD-MCT5-BK	25W	1300LM	27K/30K/35K/40K/50K - 12"X62" Black	2
LCFD-MCT5-WH	25W	1300LM	27K/30K/35K/40K/50K - 12"X62" White	2
LCFD-MCT5-WS	25W	1300LM	27K/30K/35K/40K/50K - 12"X62" White/Silver	2
LCFD-MCT5-BG	25W	1300LM	27K/30K/35K/40K/50K - 12"X62" Black/Gold	2
20" INTEGRATED LED MODERN DOME PENDANT LIGHTS				
LCFD-20-MCT5-WS	40W	2250LM	27K/30K/35K/40K/50K - 20"X62" White/Silver	2
LCFD-20-MCT5-BG	40W	2250LM	27K/30K/35K/40K/50K - 20"X62" Black/Gold	2
INTEGRATED LED MODERN WALL SCONCE				
LCFD-WS-BK	10W	500LM	27K/30K/35K/40K/50K - Black	5
LCFD-WS-WH	10W	500LM	27K/30K/35K/40K/50K - White	5

LCFP-MCT5-BG

LCFP-MCT5-WH

LCFP-WS-BK

LCFP-WS-BK

LED PAN PENDANT, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
20" INTEGRATED LED PAN PENDANT WITH 6FT ADJ. ROD DOWN, 5CCT				
LCFP-MCT5-WG	40W	2800LM	27K/30K/35K/40K/50K - White/Gold	1
LCFP-MCT5-BG	40W	2800LM	27K/30K/35K/40K/50K - Black/Gold	1
5" PAN DESIGN WALL SCONCE, 5CCT				
LCFP-WS-WH	10W	700LM	27K/30K/35K/40K/50K - White	5
LCFP-WS-BK	10W	700LM	27K/30K/35K/40K/50K - Black	5

LCFR-MCT5-WG

LCFR-MCT5-BG

12" LARGE INTEGRATED LED DOME PENDANT WITH 6FT CORD, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LCFR-MCT5-WG	24W	820LM	27K/30K/35K/40K/50K - White/Gold	2
LCFR-MCT5-BG	24W	820LM	27K/30K/35K/40K/50K - Black/Gold	2

LCFB

5CCT INTEGRATED LED PENDANT LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
LCFB-1L-MCT5	12W	810LM	27K/30K/35K/40K/50K - Single	4
LCFB-3LR-MCT5	36W	2430LM	27K/30K/35K/40K/50K - Triple w/ Square Canopy	2
LCFB-3LS-MCT5	36W	2430LM	27K/30K/35K/40K/50K - Triple w/ Straight Bar	1

LCFH

5CCT INTEGRATED LED HOLOGRAM PENDANT LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
LCFH-1L-MCT5	12W	810LM	27K/30K/35K/40K/50K - Single	4
LCFH-3LR-MCT5	36W	2430LM	27K/30K/35K/40K/50K - Triple w/ Square Canopy	2
LCFH-3LS-MCT5	36W	2430LM	27K/30K/35K/40K/50K - Triple w/ Straight Bar	1

LCFE-E26-V1L-BK

LCFE-E26-V1L-BN

LCFE-E26-P1L-BK

LCFE-E26-P1L-BN

LCFE-E26-V2L-BK

LCFE-E26-V2L-BN

LCFE-E26-P5L-BK

LCFE-E26-P5L-BN

LCFE-E26-V3L-BK

LCFE-E26-V3L-BN

LCFE SERIES E26 LAMP-READY CHANDELIER

CATALOG NO.	DESCRIPTION
LCFE-E26-V1L-BK	LCFE Series Lamp-Ready 1-Lamp Wall Sconce Black
LCFE-E26-V1L-BN	LCFE Series Lamp-Ready 1-Lamp Wall Sconce Brushed Nickel
LCFE-E26-V2L-BK	LCFE Series Lamp-Ready 2-Lamp Wall Sconce Black
LCFE-E26-V2L-BN	LCFE Series Lamp-Ready 2-Lamp Wall Sconce Brushed Nickel
LCFE-E26-V3L-BK	LCFE Series Lamp-Ready 3-Lamp Wall Sconce Black
LCFE-E26-V3L-BN	LCFE Series Lamp-Ready 3-Lamp Wall Sconce Brushed Nickel
LCFE-E26-P1L-BK	LCFE Series Lamp-Ready 1-Lamp Pendant 54In Adj. Downrod Black
LCFE-E26-P1L-BN	LCFE Series Lamp-Ready 1-Lamp Pendant 54In Adj. Downrod Brushed Nickel
LCFE-E26-P5L-BK	LCFE Series Lamp-Ready 5-Lamp Chandelier 8Ft Height Adjustable Black
LCFE-E26-P5L-BN	LCFE Series Lamp-Ready 5-Lamp Chandelier 8Ft Height Adjustable Brushed Nickel

LCFE-MCT5-BK

LCFE-MCT5-BN

4" LED GLASS LENS PENDANT WITH 6FT ADJ. ROD, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LCFE-MCT5-BN	12W	720LM	27K/30K/35K/40K/50K - Brushed Nickel	4
LCFE-MCT5-BK	12W	720LM	27K/30K/35K/40K/50K - Black	4

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	EM OPTION	DESCRIPTION	277V OPTION	DESCRIPTION
LCFF, LCFN, LDAP, LCFD	**OPT-EM-LCFX-WH**	INTERNAL White	**OPT-277V-LCFX-WH**	277V
LCFC, LCFP, LCFR, LCFB	**OPT-EM-LCFX-BK**	INTERNAL Black	**OPT-277V-LCFX-BK**	277V
LCFS, LCFQ, LCFA, LCFH	**OPT-EM-LCFX-BN**	INTERNAL Brushed Nickel	**OPT-277V-LCFX-BN**	277V
LCFS, LCFQ, LCFA, LCFE				

WIRE CABLE	DESCRIPTION	POWDER COATING
OPT-HBC-3WR-6FT-WH	12FT Cable (not for LCFE)	**N/A**
OPT-HBC-3WR-6FT-BK	12FT Cable (not for LCFE)	

LCFG-8-MCT5-FR-BK

LCFG-8-MCT5-FR-GD

FROSTED GLASS ARCHITECTURAL GLOBE PENDANT - MULTI-CCT

CATALOG NO.	DESCRIPTION			PCK QTY
LCFG-8-MCT5-FR-GD	12W	1000LM	27K/30K/35K/40K/50K - 8" Gold	2
LCFG-12-MCT5-FR-GD	20W	1600LM	27K/30K/35K/40K/50K - 12" Gold	2
LCFG-8-MCT5-FR-BK	12W	1000LM	27K/30K/35K/40K/50K - 8" Black	2
LCFG-12-MCT5-FR-BK	20W	1600LM	27K/30K/35K/40K/50K - 12" Black	2

LCFG-SG-BK

LCFG-SG-GD

LCFG-FR-BK

LCFG-FR-GD

LAMP-READY ARCHITECTURAL GLOBE PENDANT, E26 BASE

CATALOG NO.	DESCRIPTION
SEEDED GLASS E26 LAMP-READY ARCHITECTURAL GLOBE PENDANT	
LCFG-8-E26-SG-GD	8In Seeded Glass E26 Architectural Globe Pendant 67In - Gold
LCFG-12-E26-SG-GD	12In Seeded Glass E26 Architectural Globe Pendant 67In - Gold
LCFG-8-E26-SG-BK	8In Seeded Glass E26 Architectural Globe Pendant 67In - Black
LCFG-12-E26-SG-BK	12In Seeded Glass E26 Architectural Globe Pendant 67In - Black
FROSTED GLASS E26 LAMP-READY ARCHITECTURAL GLOBE PENDANT	
LCFG-8-E26-FR-GD	8In Frosted Glass E26 Architectural Globe Pendant 67In - Gold
LCFG-12-E26-FR-GD	12In Frosted Glass E26 Architectural Globe Pendant 67In - Gold
LCFG-8-E26-FR-BK	8In Frosted Glass E26 Architectural Globe Pendant 67In - Black
LCFG-12-E26-FR-BK	12In Frosted Glass E26 Architectural Globe Pendant 67In - Black

DSW-066GS-GB

DSW-066GS-CU

DSW-066GS-BN

8" DECORATIVE VINTAGE WALL SOCKET

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER
DSW-066GS-GB	Vintage 8in Decorative Wall Socket For Deco Lamps - Gun Black	
DSW-066GS-CU	Vintage 8in Decorative Wall Socket For Deco Lamps - Ant. Copper	
DSW-066GS-BN	Vintage 8in Decorative Wall Socket For Deco Lamps - Brushed Nickel	

DSP-039-6FT-BK

DSP-039-6FT-RG

DSP-066-6FT-AB

DSP-066-6FT-BK

DSP-066-6FT-BR

DSP-066-6FT-GB

DSP-722-6FT-GB

DSP-722-6FT-RG

DSP-761-6FT-AB

DSP-761-6FT-AC

DSP-974-6FT-AB

DECORATIVE SOCKET PENDANT 6FT CORD - E26 MEDIUM BASE

CATALOG NO.	DESCRIPTION
DSP-066-6FT-BK	Decorative Socket Pendant 066 6Ft Blk Cord - Black
DSP-066-6FT-AB	Decorative Socket Pendant 066 6Ft Blk Cord - Antique Brass
DSP-066-6FT-BR	Decorative Socket Pendant 066 6Ft Blk Cord - Brass
DSP-066-6FT-GB	Decorative Socket Pendant 066 6Ft Blk Cord - Gun Black
DSP-761-6FT-AC	Decorative Socket Pendant 761 6Ft Blk Cord - Antique Copper
DSP-761-6FT-AB	Decorative Socket Pendant 761 6Ft Blk Cord - Antique Brass
DSP-722-6FT-RG	Decorative Socket Pendant 761 6Ft Blk Cord - Rose Gold
DSP-722-6FT-GB	Decorative Socket Pendant 761 6Ft Blk Cord - Gun Black
DSP-974-6FT-AB	Decorative Socket Pendant 974 6Ft Blk Cord - Antique Brass
DSP-039-6FT-RG	Decorative Socket Pendant 039 6Ft Blk Cord - Rose Gold
DSP-039-6FT-BK	Decorative Socket Pendant 039 6Ft Blk Cord - Black
DSP-CORD-FAB-BK	Replacement Fabric Cord For DSP Decorative Sockets - Black

DPL-01-18K
Free Form 7.5" Diameter

DPL-02-18K
Tear Drop 7" Diameter

DPL-04-18K
Round Form 3.2" Diameter

DPL-05-18K
Round Form 5.2" Diameter

DPL-06-18K
Round Dimple 8" Diameter

DPL-07M-18K
Round Metal Mesh 8" Diameter

DPL-03-18K
Long Form 2.4X10"

DPL-08-20K

DECORATIVE PENDANT LAMP, E26 BASE **120V**

CATALOG NO.	DESCRIPTION		
DPL-01-18K	4W	160LM	1800K - Free Form 7.5in Dia
DPL-02-18K	4W	160LM	1800K - Tear Drop 7in Dia
DPL-03-18K	4W	160LM	1800K - Long Form 2.4X10in
DPL-04-18K	4W	160LM	1800K - Round Form 3.2in Dia
DPL-05-18K	4W	160LM	1800K - Round Form 5.2in Dia
DPL-06-18K	4W	160LM	1800K - Round Dimple 8in Dia
DPL-07M-18K	4W	160LM	1800K - Round Metal Mesh 8in Dia
DPL-08-20K	4W	220LM	2000K

BRL-SHL-BK

BRL-SHL-WH

BRL-SHR-BK

BRL-SHR-WH

BRL-RH-BK

BRL-RH-BN

BRL-RH-WH

BRL-RV-BK

BRL-RV-BN

BRL-RV-WH

BRL-SV-BK

BRL-SV-WH

BEDSIDE READING LAMPS WITH BACKLIGHT, WIRELESS CHARGING, & USB OPTIONS

CATALOG NO.	DESCRIPTION			PCK QTY
BRL-RH-WH	3W	120LM	3000K - Horizontal Recessed, White	20
BRL-RH-BK	3W	120LM	3000K - Horizontal Recessed, Black	20
BRL-RH-BN	3W	120LM	3000K - Horizontal Recessed, Brushed Nickel	20
BRL-RV-WH	3W	120LM	3000K - Vertical Recessed, White	20
BRL-RV-BK	3W	120LM	3000K - Vertical Recessed, Black	20
BRL-RV-BN	3W	120LM	3000K - Vertical Recessed, Brushed Nickel	20
BRL-SHR-WCH-WH	10W	500LM	3000K - Horiz. Surf. Backlit + USB & W/L CHG., Right Side, White	5
BRL-SHR-WCH-BK	10W	500LM	3000K - Horiz. Surf. Backlit + USB & W/L CHG., Right Side, Black	5
BRL-SHL-WCH-WH	10W	500LM	3000K - Horiz. Surf. Backlit + USB & W/L CHG., Left Side, White	5
BRL-SHL-WCH-BK	10W	500LM	3000K - Horiz. Surf. Backlit + USB & W/L CHG., Left Side, Black	5
BRL-SV-WH	10W	500LM	3000K - Vert. Surf. Backlit + USB, White	5
BRL-SV-BK	10W	500LM	3000K - Vert. Surf. Backlit + USB, Black	5

CEILING FANS

WFL-DC-120 SERIES

WF-DC-352 SERIES

WF-DC-352-MCT5 SERIES

WF-318WP SERIES

WFL-DC-336WP SERIES

WF-215-3B SERIES

WF-DC-216 SERIES

WFL-103-PC SERIES

WFL-116-WS SERIES

WFL-418 SERIES

WF-DR SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

ENERGY STAR FANS

WFL-DC-120-RC-5B-42-MCT5-BK-BK
With Remote Control Black and Black Blades

WFL-DC-120-RC-5B-42-MCT5-WH-WH
With Remote Control Black and Black Blades

WFL-DC-120-RC-5B-42-MCT5-BN-OK
With Remote Control Brush Nickel and Light Oak Blades

WFL-DC-121-RC-5B-52-MCT5-BK-BK
With Remote Control Black and Black Blades

WFL-DC-122-RC-3B-46-MCT5-BK-RW
With Remote Control Black and Rosewood Blades

WFL-DC-123-RC-3B-56-MCT5-BN-NW
With Remote Control Black and Natural Wood Blades

WFL-DC-124-RC-3B-52-MCT5-BK-BK
With Remote Control Black and Black Blades

WFL-DC-124-RC-3B-52-MCT5-BN-NW
With Remote Control Brush Nickel and Natural Wood Blades

WFL-DC-124-RC-3B-52-MCT5-WH-WH
With Remote Control White and White Blades

WFL-DC-125-RC-3B-52-MCT5-AZ-BK
With Remote Control Antique Brass and Black Blades

WFL-DC-125-RC-3B-52-MCT5-BN-BK
With Remote Control Brush Nickel and Black Blades

WFL-DC-125-RC-3B-52-MCT5-GD-BK
With Remote Control Gold and Black Blades

DC CEILING FAN AND LIGHT WITH REMOTE, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
WFL-DC-120-RC-5B-42-MCT5-BK-BK	18W	109LM/W	30K/35K/40K/50K/65K - Black and Black blades	1
WFL-DC-120-RC-5B-42-MCT5-WH-WH	18W	109LM/W	30K/35K/40K/50K/65K - White and White blades	1
WFL-DC-120-RC-5B-42-MCT5-BN-OK	18W	109LM/W	30K/35K/40K/50K/65K - Brush Nickel and Light Oak blades	1
WFL-DC-121-RC-5B-52-MCT5-BK-BK	18W	109LM/W	30K/35K/40K/50K/65K - Black and Black blades	1
WFL-DC-122-RC-3B-46-MCT5-BK-RW	22W	100LM/W	30K/35K/40K/50K/65K - Black and Rosewood blades	1
WFL-DC-123-RC-3B-56-MCT5-BN-NW	22W	103LM/W	30K/35K/40K/50K/65K - Black and Natural Wood blades	1
WFL-DC-124-RC-3B-52-MCT5-BK-BK	22W	103LM/W	30K/35K/40K/50K/65K - Black and Black blades	1
WFL-DC-124-RC-3B-52-MCT5-BN-NW	22W	103LM/W	30K/35K/40K/50K/65K - Brush Nickel and Natural Wood blades	1
WFL-DC-124-RC-3B-52-MCT5-WH-WH	22W	103LM/W	30K/35K/40K/50K/65K - White and White blades	1
WFL-DC-125-RC-3B-52-MCT5-AZ-BK	18W	108LM/W	30K/35K/40K/50K/65K - Antique Brass and Black blades	1
WFL-DC-125-RC-3B-52-MCT5-BN-BK	18W	108LM/W	30K/35K/40K/50K/65K - Brush Nickel and Black blades	1
WFL-DC-125-RC-3B-52-MCT5-GD-BK	18W	108LM/W	30K/35K/40K/50K/65K - Gold and Black blades	1

REPLACEMENT REMOTE CONTROL AVAILABLE TO PURCHASE

WF-DC-352-RC-3B-52-BK

WF-DC-352-RC-3B-52-BRWA

WF-DC-352-RC-3B-52-BZ

52” 3-BLADE DC CEILING FAN WITH REMOTE CONTROL

CATALOG NO.	DESCRIPTION
WF-DC-352-RC-3B-52-BZ	52in Outdoor Damp Loc 3-Blade DC Fan Remote Bronze
WF-DC-352-RC-3B-52-BK	52in Outdoor Damp Loc 3-Blade DC Fan Remote Black
WF-DC-352-RC-3B-52-BRWA	52in Outdoor Damp Loc 3-Blade DC Fan Remote Brown

REPLACEMENT REMOTE CONTROL AVAILABLE TO PURCHASE

WFL-DC-352-RC-3B-52-MCT5-BK

WFL-DC-352-RC-3B-52-MCT5-BRWA

WFL-DC-352-RC-3B-52-MCT5-BZ

52” 3-BLADE DC CEILING FAN & LIGHT WITH REMOTE CONTROL 5CCT

CATALOG NO.	DESCRIPTION
WF-DC-352-RC-3B-52-BRWA	52in Outdoor Damp Loc 3-Blade DC Fan Remote Brown
WFL-DC-352-RC-3B-52-MCT5-BZ	52in Outdoor Damp Loc 3-Blade DC Fan & 18W & 5CCT Light Remote Bronze
WFL-DC-352-RC-3B-52-MCT5-BK	52in Outdoor Damp Loc 3-Blade DC Fan & 18W & 5CCT Light Remote Black

REPLACEMENT REMOTE CONTROL AVAILABLE TO PURCHASE

WET LOCATION FANS

WF-318WP-RC-3B-52-BR-WA
With Remote Control Bronze And Walnut Blades

52” 3-BLADE OUTDOOR CEILING FAN REMOTE CONTROL

CATALOG NO.	DESCRIPTION	PCK QTY
WF-318WP-RC-3B-52-BR-WA	52” 3-Blade Outdoor Ceiling Fan Remote Control, Bronze And Walnut Blades	1

REPLACEMENT REMOTE CONTROL AVAILABLE TO PURCHASE

WFL-DC-336WP-RC-5B-54-MCT-BKBR
With Remote Control Black and Brown

WFL-DC-336WP-RC-5B-54-MCT-BKWA
With Remote Control Black and Walnut

54” 5-BLADE OUTDOOR WESTGATE CEILING FAN AND LIGHT WITH REMOTE, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
WFL-DC-336WP-RC-5B-54-MCT-BKWA	22W		27K/30K/35K/40K/50K - Black/Brown	1
WFL-DC-336WP-RC-5B-54-MCT-BKBR	22W		27K/30K/35K/40K/50K - Black/Walnut	1

REPLACEMENT REMOTE CONTROL AVAILABLE TO PURCHASE

INDUSTRIAL FANS

WF-215-3B-56-BK
With Wall Switch Black

WF-215-3B-56-WH
With Wall Switch White

56” INDUSTRIAL 3-BLADE CEILING FAN WITH WALL SWITCH MATTE

CATALOG NO.	DESCRIPTION	PCK QTY
WF-215-3B-56-BK	56In Industrial 3-Blade Ceiling Fan With Wall Switch Matte Black	1
WF-215-3B-56-WH	56In Industrial 3-Blade Ceiling Fan With Wall Switch Matte White	1

REPLACEMENT WALL SWITCH AVAILABLE TO PURCHASE

ENERGY STAR

WF-DC-216-RC-6B-60-BK WF-DC-216-RC-6B-72-BK
With Remote Control Black

WF-DC-216-RC-6B-60-BN WF-DC-216-RC-6B-72-BN
With Remote Control Brush Nickel

WF-DC-216-RC-6B-60-WH WF-DC-216-RC-6B-72-WH
With Remote Control White

WESTGATE DC 6-BLADE CEILING FAN WITH REMOTE

CATALOG NO.	DESCRIPTION	PCK QTY
WF-DC-216-RC-6B-60-BK	60” DC 6-Blade Fan With Remote Black	1
WF-DC-216-RC-6B-60-BN	60” DC 6-Blade Fan With Remote Brush Nickel	1
WF-DC-216-RC-6B-60-WH	60” DC 6-Blade Fan With Remote White	1
WF-DC-216-RC-6B-72-BK	72” DC 6-Blade Fan With Remote Black	1
WF-DC-216-RC-6B-72-BN	72” DC 6-Blade Fan With Remote Brush Nickel	1
WF-DC-216-RC-6B-72-WH	72” DC 6-Blade Fan With Remote White	1

REPLACEMENT REMOTE CONTROL AVAILABLE TO PURCHASE

INDOOR CEILING FANS

WFL-103-PC-5B-52-BN-RWSO
With Pull Chain Brush Nickel and Reversible Rosewood Silver Oak

WFL-103-PC-5B-52-WH-WH
With Pull Chain White and White Blades

WFL-105-PC-5B-52-SN-RWSO
With Pull Chain Satin Nickel and Reversible Rosewood and Silver Oak

WFL-105-PC-5B-52-WH-WH
With Pull Chain White and White Blades

WFL-107-PC-5B-52-BN-RWSO
With Pull Chain Brush Nickel and Reversible Rosewood and Silver Oak

WFL-107-PC-5B-52-WH-WH
With Pull Chain White and White Blades

WFL-112-PC-3B-52-MCT-BK-BK
With Pull Chain Black and Black Blades

WFL-112-PC-3B-52-MCT-BN-RWS
With Pull Chain Brush Nickel and Reversible Rosewood and Silver Blades

WFL-112-PC-3B-52-MCT-WH-WH
With Pull Chain White and White Blades

WFL-113-PC-5B-52-MCT-BN-RWBK
With Pull Chain Brush Nicke and Reversible Black and Rosewood Blades

WFL-113-PC-5B-52-MCT-WH-WH
With Pull Chain White and White Blades

WFL-114-PC-3B-52-BN-WNS
With Pull Chain Brush Nickel and Reversible Walnut and Silver Blades

WFL-115-PC-3B-52-MCT-WH-WH
With Pull Chain White and White Blades

WFL-115-PC-3B-52-MCT-BK-BK
With Pull Chain Black and Black Blades

WFL-115-PC-3B-52-MCT-BN-RWS
With Pull Chain Brush Nickel and Reversible Rosewood and Silver Blades

WFL-119-PC-4B-48-BN-BK
With Pull Chain Brush Nickel and Black Blades

WESTGATE CEILING FANS

CATALOG NO.	DESCRIPTION			PCK QTY
WFL-103-PC-5B-52-BN-RWSO	7W*3	600LM*3	3000K - Brush Nickel and Reversible Rosewood/Silver oak	1
WFL-103-PC-5B-52-WH-WH	7W*3	600LM*3	3000K - White and White blades	1
WFL-105-PC-5B-52-SN-RWSO	7W*3	600LM*3	3000K - Satin Nickel and Reversible Rosewood /Silver oak	1
WFL-105-PC-5B-52-WH-WH	7W*3	600LM*3	3000K - White and White blades	1
WFL-107-PC-5B-52-BN-RWSO	9W*2	800LM*2	3000K - Brush Nickel and Reversible Rosewood/Silver oak	1
WFL-107-PC-5B-52-WH-WH	9W*2	800LM*2	3000K - White and White blades	1
WFL-112-PC-3B-52-MCT-BK-BK	20W	1750LM	30K/40K/50K - Black and Black blades	1
WFL-112-PC-3B-52-MCT-BN-RWS	20W	1750LM	30K/40K/50K - Brush Nickel and Reversible Rosewood/Silver blades	1
WFL-112-PC-3B-52-MCT-WH-WH	20W	1750LM	30K/40K/50K - White and White blades	1

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION			PCK QTY
WFL-113-PC-5B-52-MCT-BN-RWBK	20W	1750LM	30K/40K/50K - Brush Nickel and Reversible Black/ Rosewood blades	1
WFL-113-PC-5B-52-MCT-WH-WH	20W	1750LM	30K/40K/50K - White and White blades	1
WFL-114-PC-3B-52-BN-WNS	1X19W	89LM/W	3000K - Brush Nickel and Reversible Walnut/Silver blades	1
WFL-115-PC-3B-52-MCT-BK-BK	20W	1750LM	30K/40K/50K - Black and Black blades	1
WFL-115-PC-3B-52-MCT-BN-RWS	20W	1750LM	30K/40K/50K - Brush Nickel and Reversible Rosewood/ Silver blades	1
WFL-115-PC-3B-52-MCT-WH-WH	20W	1750LM	30K/40K/50K - White and White blades	1
WFL-119-PC-4B-48-BN-BK	3X19W	89LM/W	3000K - Brush Nickel and Black blades	1

WFL-116-WS-3B-52-30K-WH-WH
With Wall Switch White and White Blades

WFL-116-WS-3B-52-30K-BK-BK
With Wall Switch Black and Black Blades

WFL-116-WS-3B-52-30K-BN-RWS
With Wall Switch Brush Nickel and Reversible Rosewood and Silver Blades

WFL-118-WS-4B-52-30K-WH-WH
With Wall Switch White and White Blades

WFL-118-WS-4B-52-30K-BK-BK
With Wall Switch Black and Black Blades

WFL-118-WS-4B-52-30K-BN-S
With Wall Switch Brush Nickel and Silver Blades

WFL-512-WS-3B-36-30K-BK-BK
With Wall Switch Black and Black Blades

WFL-512-WS-3B-36-30K-BN-BK
With Wall Switch Brush Nickel and Black Blades

WFL-512-WS-3B-36-30K-GD-BK
With Wall Switch Gold and Black Blades

WFL-512-WS-3B-36-30K-WH-WH
With Wall Switch White and White Blades

WFL-117DL-WS-4B-52-30K-BK-BK
With Wall Switch Black and Black Blades

WESTGATE CEILING FAN AND LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
WFL-116-WS-3B-52-30K-WH-WH	19W	1600LM	3000K - White and White blades	1
WFL-116-WS-3B-52-30K-BK-BK	19W	1600LM	3000K - Black and Black blades	1
WFL-116-WS-3B-52-30K-BN-RWS	19W	1600LM	3000K - Brush Nickel and Reversible Rosewood/Silver blades	1
WFL-118-WS-4B-52-30K-WH-WH	19W	1600LM	3000K - White and White blades	1
WFL-118-WS-4B-52-30K-BK-BK	19W	1600LM	3000K - Black and Black blades	1
WFL-118-WS-4B-52-30K-BN-S	19W	1600LM	3000K - Brush Nickel/Silver Blades	1
WFL-512-WS-3B-36-30K-BK-BK	18W	1700LM	3000K - Black and Black blades	1
WFL-512-WS-3B-36-30K-BN-BK	18W	1700LM	3000K - Brush Nickel and Black blades	1
WFL-512-WS-3B-36-30K-GD-BK	18W	1700LM	3000K - Gold and Black blades	1
WFL-512-WS-3B-36-30K-WH-WH	18W	1700LM	3000K - White and White blades	1
WFL-117DL-WS-4B-52-30K-BK-BK	19W	1600LM	3000K - Black and Black blades	1

REPLACEMENT WALL SWITCH AVAILABLE TO PURCHASE

WFL-418-RC-3B-52-MCT5-BK
With Remote Control Black

WFL-418-RC-3B-52-MCT5-WH
With Remote Control White

52” CONTEMPORARY 3-BLADE CEILING FAN AND LIGHT WITH REMOTE, 5CCT

CATALOG NO.	DESCRIPTION			PCK QTY
WFL-418-RC-3B-52-MCT5-BK	18W	2160LM	30K/35K/40K/50K/65K - Black	1
WFL-418-RC-3B-52-MCT5-WH	18W	2160LM	30K/35K/40K/50K/65K - White	1

REPLACEMENT REMOTE CONTROL AVAILABLE TO PURCHASE



WF DRAWING

DOWNROD

CEILING FAN EXTENSION DOWNROD

CATALOG NO.	DESCRIPTION
WF-DR-12-BN	Ceiling Fan Extension Downrod 12in, Brush Nickel
WF-DR-18-BN	Ceiling Fan Extension Downrod 18in, Brush Nickel
WF-DR-24-BN	Ceiling Fan Extension Downrod 24in, Brush Nickel
WF-DR-36-BN	Ceiling Fan Extension Downrod 36in, Brush Nickel
WF-DR-48-BN	Ceiling Fan Extension Downrod 48in, Brush Nickel
WF-DR-60-BN	Ceiling Fan Extension Downrod 60in, Brush Nickel
WF-DR-12-BK	Ceiling Fan Extension Downrod 12in, Black
WF-DR-18-BK	Ceiling Fan Extension Downrod 18in, Black
WF-DR-24-BK	Ceiling Fan Extension Downrod 24in, Black
WF-DR-36-BK	Ceiling Fan Extension Downrod 36in, Black
WF-DR-48-BK	Ceiling Fan Extension Downrod 48in, Black
WF-DR-60-BK	Ceiling Fan Extension Downrod 60in, Black
WF-DR-12-WH	Ceiling Fan Extension Downrod 12in, White
WF-DR-18-WH	Ceiling Fan Extension Downrod 18in, White
WF-DR-24-WH	Ceiling Fan Extension Downrod 24in, White
WF-DR-36-WH	Ceiling Fan Extension Downrod 36in, White
WF-DR-48-WH	Ceiling Fan Extension Downrod 48in, White
WF-DR-60-WH	Ceiling Fan Extension Downrod 60in, White
WF-DR-72-BN	Ceiling Fan Extension Downrod 72in Brush Nickel
WF-DR-72-BK	Ceiling Fan Extension Downrod 72in Black
WF-DR-72-WH	Ceiling Fan Extension Downrod 72in White

LAMPS

CL-XHL SERIES


CL-HL SERIES

CL-EHL SERIES

CL-FLT SERIES

CL-FLTW SERIES

ED-MCTP SERIES

ED SERIES

HBL SERIES

HPL SERIES


T8-EXZ SERIES


T8-EXZ-PRO SERIES

T8-EZX-GS SERIES

T8-EZX-TB SERIES

T8-EM SERIES

T8-EZ6-U2F SERIES

T8-U2F-EZ3 SERIES

T8-EZ6-GS SERIES


T8-TYPB SERIES


T8-DIM SERIES


T8-HL-DIM SERIES


T8-HL=ELV SERIES


T8-HL-SPLIT SERIES


T8-HL SERIES


T12-EZX SERIES

T5-EZ26-GS SERIES

T5-TYPB SERIES

T-RFG SERIES


T8HO-R17D SERIES


T10 SERIES

LPL SERIES

STG SERIES


STG-RGB SERIES

STG-LANT- RGBIC SERIES

A19 SERIES

A19-8PK SERIES

Search for the series name @WESTGATEMFG.COM

A19-FLA SERIES

TC-A19-RGBW SERIES

MR16 SERIES

M16-RGB SERIES

MR11 SERIES

BR30 SERIES

PAR SERIES

PAR36 SERIES

PAR-RGBW SERIES

GZ SERIES

GZ-G9 SERIES

G10 SERIES

E12-FLA SERIES

TC-E12 SERIES

ST19-FLA SERIES

ST64-DECO SERIES

DPL SERIES

DSP SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

CORN LAMPS

CL-XHL-12-27W | CL-XHL-18-36W | CL-XHL-27-45W, CL-XHL-36-54W, CL-XHL-45-63W | CL-XHL-54-80W, CL-XHL-63-100W, CL-XHL-80-120W | CL-XHL-100-150W | CL-XHL-120-200W, CL-XHL-200-300W

DLC HIGH-LUMEN LED CORN LAMPS **100-277V AC**

CATALOG NO.	DESCRIPTION			PCK QTY
CL-XHL-12-27W-MCTP-E39	12W/18W/27W	145LM/W	30K/40K/50K - E39	24
CL-XHL-18-36W-MCTP-E39	18W/27W/36W	145LM/W	30K/40K/50K - E39	12
CL-XHL-27-45W-MCTP-E39	27W/36W/45W	145LM/W	30K/40K/50K - E39	12
CL-XHL-36-54W-MCTP-E39	36W/45W/54W	145LM/W	30K/40K/50K - E39	12
CL-XHL-45-63W-MCTP-E39	45W/54W/63W	145LM/W	30K/40K/50K - E39	12
CL-XHL-54-80W-MCTP-E39	54W/63W/80W	145LM/W	30K/40K/50K - E39	6
CL-XHL-63-100W-MCTP-E39	63W/80W/100W	145LM/W	30K/40K/50K - E39	6
CL-XHL-80-120W-MCTP-E39	80W/100W/120W	145LM/W	30K/40K/50K - E39	6
CL-XHL-100-150W-MCTP-E39	100W/120W/150W	145LM/W	30K/40K/50K - E39	6
CL-XHL-120-200W-MCTP-E39	120W/150W/200W	145LM/W	30K/40K/50K - E39	6
CL-XHL-200-300W-MCTP-E39	200W/240W/300W	145LM/W	30K/40K/50K - E39	6

CL-HL

ENLARGER

REDUCER

WHILE SUPPLIES LAST

HIGH-LUMEN LED CORN LAMP WITH UP LIGHT **100-277V AC**

CATALOG NO.	DESCRIPTION			PCK QTY
CL-HL-27W-30K-E26	27W	3510LM	3000K - E26, H: 7.13" X D: 3.74"	12
CL-HL-45W-30K-E39	45W	5850LM	3000K - E39, H: 10.20" X D: 3.74"	12
CL-HL-75W-30K-E39	75W	9750LM	3000K - E39, H: 12.17" X D: 3.74"	12
CL-HL-100W-30K-E39	100W	13000LM	3000K - E39, H: 9.88" X D: 5.75"	6
E26-ENLARGER	ENLARGES E26 (MED.), BASE TO BE USED IN E39 (MOGUL) SOCKET			6
E39-REDUCER	REDUCES E39 (MOGUL), BASE TO BE USED IN E26 (MED.) SOCKET			6

CL-EHL-12-27W-MCTP-E26
CL-EHL-36-54W-MCTP-E39
CL-EHL-80-120W-MCTP-E39

CL-EHL
(12W TO 27W)

CL-EHL
(36W TO 54W)

CL-EHL
(75W TO 120W)

INTERNAL DRIVER CL-HL
(200W TO 300W)

EXTERNAL DRIVER
CL-HL-200W-EXTR
CL-HL-200W-480W

POWER & CCT SWITCHES

ENLARGER

REDUCER

HIGH-LUMEN LED CORN LAMP **100-277V AC**

CATALOG NO.	DESCRIPTION			PCK QTY
MCTP	**POWER & CCT ADJUSTABLE HIGH-LUMEN LED CORN LAMP 100-277V AC**			
CL-EHL-12-27W-MCTP-E26	27MAX	150LM/W	30K/40K/50K - E26 H: 6.69" X D: 2.36"	24
CL-EHL-36-54W-MCTP-E39	54MAX	150LM/W	30K/40K/50K - E39 H: 9.84" X D: 3.34"	12
CL-EHL-80-120W-MCTP-E39	120MAX	150LM/W	30K/40K/50K - E39 H: 11.14" X D: 5.11"	6
CL-EHL-80-120W-MCTP-EX39	80W/100W/120W	135LM/W	30K/40K/50K - E39 H: 11.14" X D: 5.11"	6

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

HIGH-LUMEN LED CORN LAMP 100-277V AC DLC EXCEPT E26

CATALOG NO.				PCK QTY
CL-EHL-12W-30K-E26	12W	1500LM	3000K - H: 4.90" X D: 2.36" 30~50MH	24
CL-EHL-12W-50K-E26	12W	1860LM	5000K - H: 4.90" X D: 2.36" 30~50MH	24
CL-EHL-18W-30K-E26	18W	2250LM	3000K - H: 5.70" X D: 2.36" 50~60MH	24
CL-EHL-18W-50K-E26	18W	2610LM	5000K - H: 5.70" X D: 2.36" 50~60MH	24
CL-EHL-27W-30K-E26	27W	3375LM	3000K - H: 6.69" X D: 2.36" 50~70MH	24
CL-EHL-27W-50K-E26	27W	4185LM	5000K - H: 6.69" X D: 2.36" 50~70MH	24
CL-EHL-36W-30K-E26	36W	4500LM	3000K - H: 7.55" X D: 3.34" 50~100MH	12
CL-EHL-36W-50K-E26	36W	5580LM	5000K - H: 7.55" X D: 3.34" 50~100MH	12
CL-EHL-36W-30K-E39	36W	4500LM	3000K - H: 8.30" X D: 3.34" 50~100MH	12
CL-EHL-36W-50K-E39	36W	5580LM	5000K - H: 8.30" X D: 3.34" 50~100MH	12
CL-EHL-45W-30K-E39	45W	5625LM	3000K - H: 9.84" X D: 3.34" 70~100MH	12
CL-EHL-45W-50K-E39	45W	6975LM	5000K - H: 9.84" X D: 3.34" 70~100MH	12
CL-EHL-54W-30K-E39	54W	6750LM	3000K - H: 9.84" X D: 3.34" 70~125MH	12
CL-EHL-54W-50K-E39	54W	8370LM	5000K - H: 9.84" X D: 3.34" 70~125MH	12
CL-EHL-75W-30K-E39	75W	9375LM	3000K - H: 9.84" X D: 5.11" 70~125MH	6
CL-EHL-75W-50K-E39	75W	11625LM	5000K - H: 9.84" X D: 5.11" 70~125MH	6
CL-EHL-100W-30K-E39	100W	12500LM	3000K - H: 10.31" X D: 5.11" 70~175MH	6
CL-EHL-100W-50K-E39	100W	15500LM	5000K - H: 10.31" X D: 5.11" 70~175MH	6
CL-EHL-120W-30K-E39	120W	15600LM	3000K - H: 11.14" X D: 5.11" 200~400MH	6
CL-EHL-120W-50K-E39	120W	17400LM	5000K - H: 11.14" X D: 5.11" 200~400MH	6
CL-HL-200W-50K-E39	200W	28000LM	5000K - H: 14.25" X D: 5.75" 600MH	6
CL-HL-240W-50K-E39	240W	34800LM	5000K - H: 13.15" X D: 5.50" 800W HID	6
CL-HL-300W-50K-E39	300W	43500LM	5000K - H: 13.15" X D: 5.50" 800W HID	6
CL-HL-200W-50K-E39-EXTR	200W	28000LM	5000K - H: 14.25" X D: 5.75" 600MH	4
CL-HL-200W-50K-E39-480V	200W	28000LM	5000K - H: 14.25" X D: 5.75" 600MH	4
CL-EHL-75W-30K-EX39	75W	135LM/W	3000K - H: 9.84" X D: 5.11" 70~125MH	6
CL-EHL-75W-50K-EX39	75W	135LM/W	5000K - H: 9.84" X D: 5.11" 70~125MH	6
CL-EHL-100W-30K-EX39	100W	135LM/W	3000K - H: 10.31" X D: 5.11" 70~175MH	6
CL-EHL-100W-50K-EX39	100W	135LM/W	5000K - H: 10.31" X D: 5.11" 70~175MH	6
CL-EHL-120W-30K-EX39	120W	135LM/W	3000K - H: 11.14" X D: 5.11" 200~400MH	6
CL-EHL-120W-50K-EX39	120W	135LM/W	5000K - H: 11.14" X D: 5.11" 200~400MH	6
E26-ENLARGER	ENLARGES E26 (MED.), BASE TO BE USED IN E39 (MOGUL) SOCKET			6
E39-REDUCER	REDUCES E39 (MOGUL), BASE TO BE USED IN E26 (MED.) SOCKET			6

NOTE: FOR 125W OR BELOW: IF USED IN ENCLOSED FIXTURE, CHECK SPEC SHEET FOR MINIMUM SPACE REQUIRED
FOR 200W OR ABOVE: DO NOT USE THE LAMPS IN ENCLOSED FIXTURES
THE DIMENSION OF THE EXTERNAL DRIVER FOR 200-EXTR & 480V LAMPS IS 9.5"X2.5"X1.5"

CL-FLT-54-75W-50K-E39
CL-FLT-75-115W-50K-E39

LED 180 DEGREE FLAT HID RETROFIT LAMP POWER & CCT ADJUSTABLE

CATALOG NO.				PCK QTY
CL-FLT-54-75W-50K-E39	54W/63W/75W	150LM/W	5000K - 11.7"(L) x 5.5"(W) x 3.4"(H)	8
CL-FLT-75-115W-50K-E39	75W/97W/115W	150LM/W	5000K - 11.7"(L) x 5.5"(W) x 3.4"(H)	8

CL-FLT-36-54W-50K-E39

CL-FLTW-54-75W-50K-E39

LED 180 DEGREE FLAT HID RETROFIT LAMP

CATALOG NO.	DESCRIPTION			PCK QTY
CL-FLT-36-54W-50K-E39	36W/45W/54W	150LM/W	5000K - Flat	6
CL-FLTW-54-75W-50K-E39	54W/63W/75W	150LM/W	5000K - Adjustable	6
CL-FLTW-75-110W-50K-E39	75W/97W/110W	150LM/W	5000K - Adjustable	6

ED28-17-25W-MCTP-C-EX39

ED37-30-45W-MCTP-C-EX39

HID-STYLE FILAMENT LAMP, SELECTABLE POWER & CCT, 120-277V, GLASS LENS

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
ED28-17-25W-MCTP-C-EX39	17W/20.5W/25W	180LM/W	30K/40K/50K	10
ED37-30-45W-MCTP-C-EX39	30W/38W/45W	180LM/W	30K/40K/50K	10

ED LAMPS

HID-STYLE FILAMENT LAMP 120-277V GLASS LENS

CATALOG NO.	DESCRIPTION			PCK QTY
ED23-20W-40K-C-E26	20W	3500LM	4000K - E26 Medium Base	10
ED23-20W-50K-C-E26	20W	3500LM	5000K - E26 Medium Base	10
ED23-20W-40K-C-EX39	20W	3500LM	4000K - E39 Mogul Base	10
ED23-20W-50K-C-EX39	20W	3500LM	5000K - E39 Mogul Base	10
ED28-40W-40K-C-EX39	40W	7200LM	4000K - E39 Mogul Base	10
ED28-40W-50K-C-EX39	40W	7200LM	5000K - E39 Mogul Base	10
ED37-55W-40K-C-EX39	55W	10010LM	4000K - E39 Mogul Base	10
ED37-55W-50K-C-EX39	55W	10010LM	5000K - E39 Mogul Base	10

HBL-80-120W-MCT-E39
HBL-120-160W-MCT-E39

HIGH-PERFORMANCE HIGH BAY LAMP POWER & CCT ADJUSTABLE

CATALOG NO.	DESCRIPTION			PCK QTY
HBL-80-120W-MCT-E39	80W/100W/120W	150LM/W	30K/40K/50K - E39 Mogul Base	4
HBL-120-160W-MCT-E39	120W/140W/160W	150LM/W	30K/40K/50K - E39 Mogul Base	4

HPL-E26

HPL-HB-50K-E39

HPL-HB-R

LED HIGH POWER LAMPS 120-277V

CATALOG NO.	DESCRIPTION			PCK QTY
HPL-20W-30K-E26	20W	2500LM	3000K - E26 Medium Base	20
HPL-20W-50K-E26	20W	2500LM	5000K - E26 Medium Base	20
HPL-24W-30K-E26*	24W	3000LM	3000K - E26 Medium Base	20
HPL-32W-30K-E26	32W	4000LM	3000K - E26 Medium Base	20
HPL-34W-30K-E26	34W	4250LM	3000K - E26 Medium Base	12
HPL-34W-50K-E26	34W	4250LM	5000K - E26 Medium Base	12
HPL-HB-60W-50K-E39*	60W	6480LM	5000K - E39 Mogul Base	4
HPL-HB-75W-50K-E39*	75W	8100LM	5000K - E39 Mogul Base	4
HPL-HB-100W-50K-E39*	100W	12500LM	5000K - E39 Mogul Base	4
HPL-HB-R1	Optional PC Reflector for HPL-HB-60W			12
HPL-HB-R2	Optional PC Reflector for HPL-HB-75W			8
HPL-HB-R3	Optional PC Reflector for HPL-HB-120W & HPL-HB-140W			8

WHILE SUPPLIES LAST*



T8 LAMPS

T8-EZX-4FT-12-18W-MCTP-F
T8-EZX-4FT-12-18W-MCTP-C

X-GEN WATTAGE & CCT ADJ. LED T8 GLASS LAMPS - TYPE A+B (A/C OR BALLAST) - NO POWER SELECT WITH BALLAST, DIMMABLE NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-EZX-4FT-12-18W-MCTP-F	12W/15W/18W	130LM/W	27K/30K/35K/40K/50K - FROSTED	12 & 36
T8-EZX-4FT-12-18W-MCTP-C	12W/15W/18W	130LM/W	27K/30K/35K/40K/50K - CLEAR	12 & 36

T8-EZX-PRO-F
T8-EZX-PRO-C

X-GEN LED T8 PC+ALUM. SHATTER-PROOF LAMPS, TYPE A+B FOR A/C OR BALLAST

NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-EZX-PRO-2FT-10W-40K-C	10W	1300LM	4000K - Clear, G13, Type A & B	25
T8-EZX-PRO-2FT-10W-40K-F	10W	1300LM	4000K - Frosted, G13, Type A & B	25
T8-EZX-PRO-2FT-10W-50K-C	10W	1300LM	5000K - Clear, G13, Type A & B	25
T8-EZX-PRO-2FT-10W-50K-F	10W	1300LM	5000K - Frosted, G13, Type A & B	25
T8-EZX-PRO-4FT-12W-40K-F	12W	1560LM	4000K - Frosted, G13, Type A & B	25
T8-EZX-PRO-4FT-12W-50K-F	12W	1560LM	5000K - Frosted, G13, Type A & B	25
T8-EZX-PRO-4FT-18W-40K-C	18W	2340LM	4000K - Clear, G13, Type A & B	25
T8-EZX-PRO-4FT-18W-40K-F	18W	2340LM	4000K - Frosted, G13, Type A & B	25
T8-EZX-PRO-4FT-18W-50K-C	18W	2340LM	5000K - Clear, G13, Type A & B	25
T8-EZX-PRO-4FT-18W-50K-F	18W	2340LM	5000K - Frosted, G13, Type A & B	25

T8-EZX-MCT-GS-2FT-8W-C
T8-EZX-MCT-GS-2FT-8W-F

X-GEN 3CCT LED T8 GLASS LAMPS
3 COLOR-TEMPERATURES IN ONE LAMP TYPE A+B (A/C OR BALLAST) NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-EZX-MCT-GS-2FT-8W-C	8W	1216LM	35K/40K/50K - Clear, G13, Type A & B	12
T8-EZX-MCT-GS-3FT-12W-C	12W	1500LM	35K/40K/50K - Clear, G13, Type A & B	12
T8-EZX-MCT-GS-3FT-12W-F	12W	1500LM	35K/40K/50K - Frosted, G13, Type A & B	12
T8-EZX-MCT-GS-4FT-15W-F	15W	1875LM	35K/40K/50K - Frosted, G13, Type A & B	12

T8-EZX-TB-4FT-12-18W-50K-F
T8-EZX-TB-4FT-12-18W-50K-C

X-GEN SELECTABLE-POWER LED T8 GLASS LAMPS,
TYPE B FOR DIRECT A/C (BALLAST OVERRIDE) NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-EZX-TB-4FT-12-18W-50K-F	12W/15W/18W	120LM/W	5000K - Frosted, G13, Type B	12
T8-EZX-TB-4FT-12-18W-50K-C	12W/15W/18W	120LM/W	5000K - Clear, G13, Type B	12
T8-EZX-TB-4FT-12-18W-40K-F	12W/15W/18W	120LM/W	4000K - Frosted, G13, Type B	12
T8-EZX-TB-4FT-12-18W-40K-C	12W/15W/18W	120LM/W	4000K - Clear, G13, Type B	12

T8-EM-4FT-12-15W-MCTP-F

EMERGENCY (90-MIN) T8 LAMP **120-277V** - TYPE B FOR DIRECT A/C (BALLAST OVERRIDE)

CATALOG NO.	DESCRIPTION			PCK QTY
T8-EM-4FT-12-15W-MCTP-F	12W/15W/18W	108LM/W	35K/40K/50K - FROSTED	12

T8-EZ6-U2F-15W-41K-C
T8-EZ6-U2F-15W-41K-F

U-SHAPED T8 EZ6 LED GLASS LAMPS NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-EZ6-U2F-15W-41K-C	15W	2100LM	4100K - Ballast Compatible Or 100~277 Ac	10
T8-EZ6-U2F-15W-41K-F	15W	2000LM	4100K - Ballast Compatible Or 100~277 Ac	10
T8-EZ6-U2F-15W-50K-C	15W	2100LM	5000K - Ballast Compatible Or 100~277 Ac	10
T8-EZ6-U2F-15W-50K-F	15W	2000LM	5000K - Ballast Compatible Or 100~277 Ac	10

T8-U2F-EZ3-15W-41K-C
T8-U2F-EZ3-15W-50K-C

U-SHAPED T8 LED PLASTIC/ALUMINUM LAMPS NO PARTIAL/MUST SHIP CASE QTY

WORKS 3 WAYS: 1) WITH EXISTING ELECTRONIC BALLAST 2) A/C DIRECT ONE END 3) A/C DIRECT 2 ENDS

CATALOG NO.	DESCRIPTION			PCK QTY
T8-U2F-EZ3-15W-41K-C	15W	1450LM	4100K - BALLAST COMPATIBLE OR 100~277 AC	10
T8-U2F-EZ3-15W-50K-C	15W	1500LM	5000K - BALLAST COMPATIBLE OR 100~277 AC	10

T8-U2F-EZ3

T8-EZ6-GS-2FT

T8-EZ6-GS-3FT

T8-EZ6-GS-4FT

NEW GEN. - TYPE A + B (DOUBLE UL) 2FT. 3FT. & 4FT. LED T8-EZ6 GLASS LAMPS, 180°(CLEAR) & 240° (FROSTED) Beam Angle, ELECTRONIC BALLASTS (TYPE A), ALSO WORK WITH A/C DIRECT **120~277V** ONE END OR BOTH ENDS (TYPE B) NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-EZ6-GS-2FT-10W-30K-C	10W	1250LM	3000K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-2FT-10W-30K-F	10W	1200LM	3000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-2FT-10W-35K-C	10W	1250LM	3500K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-2FT-10W-35K-F	10W	1200LM	3500K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-2FT-10W-40K-C	10W	1250LM	4000K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-2FT-10W-40K-F	10W	1200LM	4000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-2FT-10W-50K-C	10W	1250LM	5000K - Clear, G13, Type A & B	12 & 36

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION			PCK QTY
T8-EZ6-GS-2FT-10W-50K-F	10W	1200LM	5000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-3FT-12W-40K-C	12W	1600LM	4000K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-3FT-12W-40K-F	12W	1560LM	4000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-3FT-12W-50K-C	12W	1600LM	5000K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-3FT-12W-50K-F	12W	1560LM	5000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-15W-30K-C	15W	1875LM	3000K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-15W-30K-F	15W	1800LM	3000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-15W-35K-C	15W	1875LM	3500K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-15W-35K-F	15W	1800LM	3500K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-15W-40K-C	15W	1875LM	4000K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-15W-40K-F	15W	1800LM	4000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-15W-50K-C	15W	1875LM	5000K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-15W-50K-F	15W	1800LM	5000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-18W-30K-C	18W	2250LM	3000K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-18W-30K-F	18W	2160LM	3000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-18W-35K-C	18W	2250LM	3500K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-18W-35K-F	18W	2160LM	3500K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-18W-40K-C	18W	2250LM	4000K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-18W-40K-F	18W	2160LM	4000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-18W-50K-C	18W	2250LM	5000K - Clear, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-18W-50K-F	18W	2160LM	5000K - Frosted, G13, Type A & B	12 & 36
T8-EZ6-GS-4FT-18W-65K-C	18W	2250LM	6500K - Clear	12 & 36
T8-EZ6-GS-4FT-18W-65K-F	18W	2250LM	6500K - Frosted	12 & 36

c UL us LISTED

T8-4FT-TYPB-17W-40K-F
T8-4FT-TYPB-17W-40K-C

4FT, T8 GLASS LAMP WORKS WITH A/C DIRECT **120-277V** ONE END OR BOTH ENDS (TYPE B)

NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-4FT-TYPB-17W-40K-F	17W	2200LM	4000K - FROSTED	25
T8-4FT-TYPB-17W-40K-C	17W	2200LM	4000K - CLEAR	25
T8-4FT-TYPB-17W-50K-F	17W	2200LM	5000K - FROSTED	25
T8-4FT-TYPB-17W-50K-C	17W	2200LM	5000K - CLEAR	25
T8-4FT-TYPB-14W-40K-F	14W	1800LM	4000K - FROSTED	25
T8-4FT-TYPB-10.5WHL-40K-F	10.5W	1700LM	4000K - FROSTED	12 & 36
T8-4FT-TYPB-10.5WHL-40K-C	10.5W	1700LM	4000K - CLEAR	12 & 36

WHILE SUPPLIES LAST

T8-4FT-DIM-18W-35K-C
T8-4FT-DIM-18W-50K-F

4FT. T8 LED GLASS LAMPS DIMMABLE DIRECT A/C (one end N+L) NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-4FT-DIM-18W-35K-C	18W	1900LM	3500K - 90~140VAC, CLEAR	12 & 36
T8-4FT-DIM-18W-50K-F	18W	2150LM	5000K - 90~140VAC, FROSTED	12 & 36

T8-HL-4FT-DIM-18W-40K-C
T8-HL-4FT-DIM-18W-40K-F

NEW GEN HIGH LUMEN 4FT. LED T8 GLASS LAMPS DIMMABLE DIRECT A/C (ONE END N+L)
NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-HL-4FT-DIM-18W-40K-C	18W	2250LM	4000K - Clear	12 & 36
T8-HL-4FT-DIM-18W-40K-F	18W	2160LM	4000K - Frosted	12 & 36
T8-HL-4FT-DIM-18W-50K-C	18W	2250LM	5000K - Clear	12 & 36
T8-HL-4FT-DIM-18W-50K-F	18W	2160LM	5000K - Frosted	12 & 36

T8-HL-4FT-ELV-18W-50K-F

4FT. LED T8 GLASS LAMPS ELV DIMMABLE (TYPE A), ALSO WORK WITH A/C DIRECT **120~277V** ONE END OR BOTH ENDS (TYPE B)

CATALOG NO.	DESCRIPTION			PCK QTY
T8-HL-4FT-ELV-18W-50K-F	18W	2250LM	5000K - Frosted	12 & 36

T8-HL-8FT-SPLIT-42W-40K-C
T8-HL-8FT-SPLIT-42W-40K-F

8FT. SPLIT VERSION LED T8 LAMPS, TYPE B NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-HL-8FT-SPLIT-42W-40K-C	42W	6000LM	4000K - Clear	18
T8-HL-8FT-SPLIT-42W-40K-F	42W	5500LM	4000K - Frosted	18
T8-HL-8FT-SPLIT-42W-50K-C	42W	6000LM	5000K - Clear	18
T8-HL-8FT-SPLIT-42W-50K-F	42W	5500LM	5000K - Frosted	18
T8-R17D-CONV	17D Conversion kit			

T8-HL-8FT-40W-40K-C
T8-HL-8FT-40W-40K-F

8FT. LED T8 LAMPS, TYPE B DIRECT A/C **120-277V** (TWO ENDS) NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8-HL-8FT-40W-40K-C	40W	4600LM	4000K - Clear	20
T8-HL-8FT-40W-40K-F	40W	4400LM	4000K - Frosted	20
T8-HL-8FT-40W-50K-C	40W	4600LM	5000K - Clear	20
T8-HL-8FT-40W-50K-F	40W	4400LM	5000K - Frosted	20

T12-EZX-MCT-GS-4FT-16W-F

T12 X-GEN SELECTABLE-CCT LED LAMPS, TYPE A+B FOR A/C OR BALLAST
NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T12-EZX-MCT-GS-4FT-16W-F	16W	2000LM	30K/40K/50K/65K - Frosted, G13, Type B	20

T5-EZ6-GS-4FT-24W-40K-F
T5-EZ6-GS-4FT-24W-50K-F

4FT. LED T5 GLASS LAMPS, TYPE A+B, WORK WITH DIRECT A/C OR BALLAST

CATALOG NO.	DESCRIPTION			PCK QTY
T5-EZ6-GS-4FT-24W-40K-F	24W	3000LM	4000K - Frosted	12 & 36
T5-EZ6-GS-4FT-24W-50K-F	24W	3000LM	5000K - Frosted	12 & 36

T5-TYPB-25W-40K-F

WHILE SUPPLIES LAST

4FT. LED T5 GLASS LAMPS NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T5-TYPB-25W-40K-F	25W	3200LM	4000K - Frosted	40

T-RFG-5FT-22W-50K-C
T-RFG-6FT-30W-50K-C

5FT. & 6FT. LED REFRIGERATOR LAMPS

CATALOG NO.	DESCRIPTION			PCK QTY
T-RFG-5FT-22W-50K-C	22W	3100LM	5000K - Clear	25
T-RFG-6FT-30W-50K-C	30W	4200LM	5000K - Clear	25

T8HO-R17D-65K-360D

LED SIGN TUBE 360°, R17D ENDS, SINGLE/DOUBLE ENDED NO PARTIAL/MUST SHIP CASE QTY

CATALOG NO.	DESCRIPTION			PCK QTY
T8HO-R17D-4FT-65K-360D	21W	125LM/W	6500K	25
T8HO-R17D-5FT-65K-360D	26W	125LM/W	6500K	25
T8HO-R17D-6FT-65K-360D	31W	125LM/W	6500K	25
T8HO-R17D-7FT-65K-360D	37W	125LM/W	6500K	25
T8HO-R17D-8FT-65K-360D	42W	125LM/W	6500K	25



T10-12-6W-27K
T10-9-4W-27K

LED T10 FILAMENT LAMP **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
T10-12-6W-27K	6W	780LM	2700K	50
T10-12-6W-30K	6W	780LM	3000K	50
T10-12-6W-40K	6W	780LM	4000K	50
T10-9-4W-27K	4W	520LM	2700K	50
T10-9-4W-30K	4W	520LM	3000K	50
T10-9-4W-40K	4W	520LM	4000K	50

ELB-23120-HH-AC-FLEX

LED EMERGENCY DRIVER FOR ALL T8 LAMPS

CATALOG NO.	DESCRIPTION
ELB-23120-HH-AC-FLEX	120VAC 23W BACKUP FOR T8 LAMPS

LPL-G24-AB-11W
LPL-GX23-AB-8W

LED TYPE A+B PL LAMPS

CATALOG NO.	DESCRIPTION			PCK QTY
LPL-G24-AB-11W	11W	1300LM	4000K	1
LPL-GX23-AB-8W	8W	800LM	4000K	1

STG-2412-27K

STG-2412-27K-WH

12 LED LAMPS /24FT. STG

CATALOG NO.	DESCRIPTION			PCK QTY
STG-2412-27K	1W per bulb	75LM per S14 bulb	2700K - Black	12
STG-2412-27K-WH	1W per bulb	75LM per S14 bulb	2700K - White	12

STG-5315-RGB-BT

TC-RGBW-RC

53FT 15-BULB ST14 RGB STRING LIGHT

CATALOG NO.	DESCRIPTION
STG-5315-RGB-BT	53Ft 15-Bulb ST14 Rgb String Light 1M Appart With 11 Fairy Lights In Between Bluetooth

STG-2415-LANT-RGBIC-BT

TC-RGBW-RC

LANTERN DESIGN STRING LIGHT RGB BLUETOOTH APP CONTROLLED

CATALOG NO.	DESCRIPTION
STG-2415-LANT-RGBIC-BT	24Ft 15-Lamp Lantern Design String Light Rgb Bluetooth App Controlled
STG-4830-LANT-RGBIC-BT	48Ft 30-Lamp Lantern Design String Light Rgb Bluetooth App Controlled

A19-9W-MCT5-D

A19 LED LAMPS

CATALOG NO.	DESCRIPTION			PCK QTY
A19-9W-MCT5-D	9W	800LM	27K/30K/35K/40K/50K	1

A19-8PK-9W-30K-D

A19 LED LAMPS (Medium Base) 240° 15K Hours

CATALOG NO.	DESCRIPTION			PCK QTY
A19-8PK-9W-30K-D	9W	700LM	3000K - 8-PACK	64
A19-8PK-9W-40K-D	9W	810LM	4000K - 8-PACK	64
A19-8PK-9W-50K-D	9W	810LM	5000K - 8-PACK	64
A19-40PK-9W-30K-D	9W	700LM	3000K - 40-PACK	40
A19-40PK-9W-40K-D	9W	810LM	4000K - 40-PACK	40
A19-40PK-9W-50K-D	9W	810LM	5000K - 40-PACK	40

A19-FLA-7W-27K-D

LED FILAMENT A19 BULB **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
A19-FLA-7W-27K-D	7W	800LM	2700K - Clear	100
A19-FLA-7W-30K-D	7W	800LM	3000K - Clear	100
A19-FLA-7W-40K-D	7W	800LM	4000K - Clear	100

TC-A19-9W-RGBW-WIFI

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW A19 LAMP **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-A19-9W-RGBW-WIFI	9W	800LM	RGBW - E26 Base	50

MR16-400L-27K-D

MR16-500L-C90-30K-D

MR16 LED LAMPS, **12V** AC/DC GU5.3 BASE 36° 6° *Dimmable with magnetic ballast only

CATALOG NO.	DESCRIPTION			PCK QTY
MR16-400L-27K-D	5W	380LM	2700K - 80CRI	200
MR16-400L-30K-D	5W	380LM	3000K - 80CRI	200
MR16-400L-41K-D	5W	390LM	4100K - 80CRI	200
MR16-400L-50K-D	5W	400LM	5000K - 80CRI	200
MR16-500L-C90-30K-D	7W	500LM	3000K - 90CRI	100
MR16-500L-C90-40K-D	7W	560LM	4000K - 90CRI	100
MR16-500L-C90-50K-D	7W	560LM	5000K - 90CRI	100

MR16-5W-RGB

LED T10 FILAMENT LAMP **120V**

CATALOG NO.	DESCRIPTION		
MR16-5W-RGB	5W	280LM	RGB - 12V 30° REMOTE CONTROL

MR11-250L-27K

MR11 LED LAMPS, **12V** AC/DC GU5.3 BASE 36°

CATALOG NO.	DESCRIPTION		
MR11-250L-27K	3W	250LM	2700K
MR11-250L-30K	3W	250LM	3000K

BR30-9W-MCT5-D

BR30 LED LAMPS

CATALOG NO.	DESCRIPTION			PCK QTY
BR30-9W-MCT5-D	9W	800LM	27K/30K/35K/40K/50K	1

PAR30-9W-MCT5-D-WP

PAR30S-9W-MCT5-D-WP

PAR38-12W-MCT5-D-WP

PAR30, PAR30S, PAR38 LED LAMPS, 5CCT, WEATHERPROOF

CATALOG NO.	DESCRIPTION			PCK QTY
PAR30-9W-MCT5-D-WP	9W	800LM	27K/30K/35K/40K/50K	24
PAR30S-9W-MCT5-D-WP	9W	800LM	27K/30K/35K/40K/50K	24
PAR38-12W-MCT5-D-WP	12W	1200LM	27K/30K/35K/40K/50K	1

PAR36-12W-30K

PAR36 **12V** AC/DC G53 Terminal Base, IP65, WET LOCATION

CATALOG NO.	DESCRIPTION			PCK QTY
PAR36-12W-30K	12W	1000LM	3000K	20
PAR36-12W-40K	12W	1000LM	4000K	20
PAR36-12W-50K	12W	1000LM	5000K	20

TC-PAR20-4.5W-RGBW-WIFI

TC-PAR30-11W-RGBW-WIFI

TC-PAR38-10W-RGBW-WIFI

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW PAR20/PAR30/PAR38 **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-PAR20-4.5W-RGBW-WIFI	4.5W	400LM	RGBW - E26 Base	50
TC-PAR30-11W-RGBW-WIFI	11W	850LM	RGBW - E26 Base	50
TC-PAR38-10W-RGBW-WIFI	10W	1050LM	RGBW - E26 Base	50

GZ-JC-39L-27K

GZ-JC-13L-32K

GZ-JC-WP-3W-32K

BA15

GZ-G4-9L-32K

GZ-JC-60L-TFL

GZ-JC-300L

12-VOLT LED REPLACEMENT LAMPS

CATALOG NO.	DESCRIPTION			PCK QTY
GZ-JC-39L-27K	3W	250LM	2700K - 12VAC/DC	1000
DAMP LOCATIONS **GZ-JC-39L-30K**	3W	250LM	3000K - 12VAC/DC	1000
GZ-JC-18L-27K	3W	250LM	2700K - 12VAC/DC	1000
WET LOCATIONS **GZ-JC-WP-3W-32K**	3W	180LM	3200K - 12VAC/DC	1000
GZ-S8-32K-G2	2.2W	230LM	3200K - 12V	500
GZ-G4-9L-32K	2W	120LM	3200K - 12V	1000
GZ-JC-60L-TFL	3W	60LM	TURTLE FRIENDLY CCT	1000
WET LOCATIONS **GZ-JC-300L-27K**	3W	300LM	2700K - 360° Beam Angle	1000
WET LOCATIONS **GZ-JC-300L-30K**	3W	300LM	3000K - 360° Beam Angle	1000

GZ-G9-3W-32K
GZ-G9-3W-55K

LED REPLACEMENT LAMPS **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
GZ-G9-3W-32K	3W	240LM	3200K - G9	500
GZ-G9-3W-55K	3W	250LM	5500K - G9	500

G10-600L-30K-D

HIGH POWER GU10 120V

CATALOG NO.	DESCRIPTION			PCK QTY
G10-600L-30K-D	7.5W	500LM	3000K - SMD CRI80 30° ANGLE	60
G10-600L-50K-D	7.5W	600LM	5000K - SMD CRI80 30° ANGLE	60

E12-FLA-4W-30K-D
E12-FLA-4W-30K-D-F-BT

LED FILAMENT CANDELABRA **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
E12-FLA-4W-30K-D	4W	500LM	3000K - CLEAR TORPEDO	48
E12-FLA-4W-30K-D-F-BT	4W	500LM	3000K - FROSTED BENT TIP	48
E12-FLA-5W-27K-D	4W	400LM	2700K - CLEAR TORPEDO	48
E12-FLA-5W-40K-D	4W	400LM	4000K - CLEAR TORPEDO	48
E12-FLA-5W-27K-D-F-BT	4W	300LM	2700K - FROSTED BENT TIP	48
E12-FLA-5W-40K-D-F-BT	4W	300LM	4000K - FROSTED BENT TIP	48

TC-E12-4.5W-RGBW-WIFI

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW CANDELABRA **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-E12-4.5W-RGBW-WIFI	4.5W	325LM	RGBW - E12 Base	50

ST19-FLA-5W-27K-D-CL
ST19-FLA-5W-22K-D-AM

LED FILAMENT ST19 BULB **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
ST19-FLA-5W-27K-D-CL	5W	430LM	2700K	24
ST19-FLA-5W-30K-D-CL	5W	650LM	3000K	24
ST19-FLA-5W-40K-D-CL	5W	650LM	4000K	24
ST19-FLA-5W-22K-D-AM	5W	380LM	2200K (Amber Glass, LED Component 2700K)	24

ST64-DECO-4W

LED DECO FILAMENT ST64 BULB, **120V** E26 BASE

CATALOG NO.	DESCRIPTION			PCK QTY
ST64-DECO-4W-27K-D-AMB	4W	140LM	2700K - AMBER GLASS	50
ST64-DECO-4W-27K-D-CL	4W	140LM	2700K - CLEAR	50
ST64-DECO-4W-30K-D-CL	4W	140LM	3000K - CLEAR	50

DECORATIVE BULBS & SOCKETS

DPL-01-18K
Free Form 7.5" Diameter

DPL-02-18K
Tear Drop 7" Diameter

DPL-04-18K
Round Form 3.2" Diameter

DPL-05-18K
Round Form 5.2" Diameter

DPL-06-18K
Round Dimple 8" Diameter

DPL-07M-18K
Round Metal Mesh 8" Diameter

DPL-03-18K
Long Form 2.4X10"

DPL-08-20K

DECORATIVE PENDANT LAMP, E26 BASE **120V**

CATALOG NO.	DESCRIPTION		
DPL-01-18K	4W	160LM	1800K - Free Form 7.5in Dia
DPL-02-18K	4W	160LM	1800K - Tear Drop 7in Dia
DPL-03-18K	4W	160LM	1800K - Long Form 2.4X10in
DPL-04-18K	4W	160LM	1800K - Round Form 3.2in Dia
DPL-05-18K	4W	160LM	1800K - Round Form 5.2in Dia
DPL-06-18K	4W	160LM	1800K - Round Dimple 8in Dia
DPL-07M-18K	4W	160LM	1800K - Round Metal Mesh 8in Dia
DPL-08-20K	4W	220LM	2000K

DSP-039-6FT-BK

DSP-039-6FT-RG

DSP-066-6FT-AB

DSP-066-6FT-BK

DSP-066-6FT-BR

DSP-066-6FT-GB

DSP-722-6FT-GB

DSP-722-6FT-RG

DSP-761-6FT-AB

DSP-761-6FT-AC

DSP-974-6FT-AB

DECORATIVE SOCKET PENDANT 6FT CORD – E26 MEDIUM BASE

CATALOG NO.	DESCRIPTION
DSP-066-6FT-BK	Decorative Socket Pendant 066 6Ft Blk Cord - Black
DSP-066-6FT-AB	Decorative Socket Pendant 066 6Ft Blk Cord - Antique Brass
DSP-066-6FT-BR	Decorative Socket Pendant 066 6Ft Blk Cord - Brass
DSP-066-6FT-GB	Decorative Socket Pendant 066 6Ft Blk Cord - Gun Black
DSP-761-6FT-AC	Decorative Socket Pendant 761 6Ft Blk Cord - Antique Copper
DSP-761-6FT-AB	Decorative Socket Pendant 761 6Ft Blk Cord - Antique Brass
DSP-722-6FT-RG	Decorative Socket Pendant 761 6Ft Blk Cord - Rose Gold
DSP-722-6FT-GB	Decorative Socket Pendant 761 6Ft Blk Cord - Gun Black
DSP-974-6FT-AB	Decorative Socket Pendant 974 6Ft Blk Cord - Antique Brass
DSP-039-6FT-RG	Decorative Socket Pendant 039 6Ft Blk Cord - Rose Gold
DSP-039-6FT-BK	Decorative Socket Pendant 039 6Ft Blk Cord - Black
DSP-CORD-FAB-BK	Replacement Fabric Cord For DSP Decorative Sockets - Black

UNDER CABINET

UCE SERIES


UCA SERIES

UCR SERIES


UCA-RGBW SERIES

1.1


PSA SERIES

LED undercabinet 12V angled shot


UC-24V SERIES

UCM SERIES

B0003099


UC-ADJ SERIES

B0003094

PL12-PIR SERIES

PL12-RGBW SERIES

PL12R-30K-WH

PL12S SERIES

PL120-ADJ-30K-BN1


PL12 SERIES

TC-PL12 SERIES

PL12-ADJ SERIES

PL12-PIDR-12_24-BK

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

UNDER CABINET LIGHTS

UCE-9-WHT

UCE-12-WHT

UCE-18-WHT

UCE-21-WHT

UCE-24-WHT

UCE-32-WHT

UCE-40-WHT

BUILDER SERIES 5CCT HARD-WIRE UNDER CABINET LIGHT OPTIONAL CORD

CATALOG NO.	DESCRIPTION			PCK QTY
UCE-9-WHT	3W	180LM	27K/30K/35K/40K/50K - White	10
UCE-12-WHT	5W	300LM	27K/30K/35K/40K/50K - White	10
UCE-18-WHT	8W	480LM	27K/30K/35K/40K/50K - White	10
UCE-21-WHT	10W	600LM	27K/30K/35K/40K/50K - White	10
UCE-24-WHT	12W	720LM	27K/30K/35K/40K/50K - White	10
UCE-32-WHT	16W	960LM	27K/30K/35K/40K/50K - White	10
UCE-40-WHT	20W	1200LM	27K/30K/35K/40K/50K - White	10
UCA-LC8-WHT	8in Linking Cord For UCA And UCE Series, White			
UCA-PC-6FT-WHT	6Ft Power Cord Cord For UCA And UCE Series, White			

UCA-12-WHT

UCA-24-WHT

UCA-33-WHT

UCA-DISPLAY

UCA-12-BRZ

UCA-24-BRZ

UCA-33-BRZ

ADJUSTABLE ANGLE MULTI COLOR-TEMPERATURE UNDER CABINET LIGHT **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
UCA-8-WHT	3W	150LM	2700K/3000K/4000K - White	10
UCA-12-WHT	5W	275LM	2700K/3000K/4000K - White	10
UCA-16-WHT	6.5W	390LM	2700K/3000K/4000K - White	10
UCA-21-WHT	8W	450LM	2700K/3000K/4000K - White	10
UCA-24-WHT	12W	650LM	2700K/3000K/4000K - White	10
UCA-33-WHT	16W	900LM	2700K/3000K/4000K - White	10
UCA-42-WHT	20W	1100LM	2700K/3000K/4000K - White	10
UCA-LC12-WHT	12" Linking Cable for White UCA Series - White color			
UCA-LC8-WHT	8in Linking Cord For Uce And UCE Series, White			
UCA-PC-6FT-WHT	6Ft Power Cord Cord For Uce And UCE Series, White			
UCA-8-BRZ	3W	150LM	2700K/3000K/4000K - Bronze	10
UCA-12-BRZ	5W	275LM	2700K/3000K/4000K - Bronze	10
UCA-16-BRZ	6.5W	390LM	2700K/3000K/4000K - Bronze	10
UCA-21-BRZ	8W	450LM	2700K/3000K/4000K - Bronze	10
UCA-24-BRZ	12W	650LM	2700K/3000K/4000K - Bronze	10
UCA-33-BRZ	16W	900LM	2700K/3000K/4000K - Bronze	10
UCA-42-BRZ	20W	1100LM	2700K/3000K/4000K - Bronze	10
UCA-LC12-BLK	12" Linking Cable for Bronze UCA Series - Black color (Matches the color of included cables)			
UCA-LC8-BLK	8in Linking Cord For UCA And UCE Series, Black			
UCA-PC-6FT-BLK	6Ft Power Cord Cord For UCA And UCE Series, Black			
UCA-DISPLAY	Display Board for UCA Series			

MULTI COLOR-TEMPERATURE LIGHT ACCESSORIES INCLUDED

6.' Power Cord
8" Interconnect Cable
End-to-End Coupling
Mounting Screws

On/Off Switch with
100% /50% Dimming.
Color Temp. selection
Switch: 2700K/ 3000K/ 4000k

3/8" KOs
Cable Connector Included

UCLB-120V-32-MCT-D

UCLB-120V-ENDCAP

UCLB-120V-JB

UCLB-120V-POWCORD-10FT

UCLB-120V-SWIVEL-L

UCLB-120V-JUMP6-18-24



UCLB-120V-DCON

120V UNDERCAB LIGHT BAR, CRI90 SELECTABLE CCT

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER		PCK QTY
UCLB-120V-12-MCT-D	4.5W	382LM	30K/40K/50K		80
UCLB-120V-16-MCT-D	6W	510LM	30K/40K/50K		80
UCLB-120V-24-MCT-D	9W	765LM	30K/40K/50K		60
UCLB-120V-32-MCT-D	12W	1020LM	30K/40K/50K		50
UCLB-120V-DCON	UCLB End-To-End Direct Connector Without A Gap				
UCLB-120V-JUMP6	UCLB Jumper Cable 6in				
UCLB-120V-JUMP18	UCLB Jumper Cable 18in				
UCLB-120V-JUMP24	UCLB Jumper Cable 24in				
UCLB-120V-SWIVEL-L	UCLB Lighted Swivel L 3W 3CCT CR90 Triac Dim				
UCLB-120V-POWCORD-10FT	UCLB 10-Foot Power Cord With Switch				
UCLB-120V-ENDCAP	UCLB Replacement Endcap				
UCLB-120V-JB	UCLB Junction Box Without Switch				

UCR-12-WHT

UCR-18-WHT

UCR-24-WHT

UCR-32-WHT

UCR-40-WHT

UCR-12-BK

UCR-18-BK

UCR-24-BK

UCR-32-BK

UCR-40-BK

UNDER CABINET SERIES WITH RECEPTACLES AND USB PORTS

CATALOG NO.			DESCRIPTION	PCK QTY
UCR-12-WHT	5W	300LM	27K/30K/35K/40K/50K - White, 1 Outlet	10
UCR-18-WHT	8W	480LM	27K/30K/35K/40K/50K - White, 1 outlet, 1 USB port, and 1 USB-C port	10
UCR-24-WHT	12W	720LM	27K/30K/35K/40K/50K - White, 3 outlets, 2 USB ports, 2 USB-C ports	10
UCR-32-WHT	16W	960LM	27K/30K/35K/40K/50K - White, 4 outlets, 2 USB ports, 2 USB-C ports	10
UCR-40-WHT	20W	1200LM	27K/30K/35K/40K/50K - White, 4 outlets, 2 USB ports, 2 USB-C ports	10
UCR-12-BK	5W	300LM	27K/30K/35K/40K/50K - Black, 1 Outlet	10
UCR-18-BK	8W	480LM	27K/30K/35K/40K/50K - Black, 1 outlet, 1 USB port, and 1 USB-C port	10
UCR-24-BK	12W	720LM	27K/30K/35K/40K/50K - Black, 3 outlets, 2 USB ports, 2 USB-C ports	10
UCR-32-BK	16W	960LM	27K/30K/35K/40K/50K - Black, 4 outlets, 2 USB ports, 2 USB-C ports	10
UCR-40-BK	20W	1200LM	27K/30K/35K/40K/50K - Black, 4 outlets, 2 USB ports, 2 USB-C ports	10



UCA-RGBW-BR

UCA-RGBW-WHT

RGBW 9 MODES & 3CCT UNDER CABINET LIGHT PUSH-BUTTON COLOR CONTROL

CATALOG NO.	DESCRIPTION			PCK QTY
UCA-RGBW-PB-12-BR	5W	275LM	30K/40K/50K + RGB - Bronze	10
UCA-RGBW-PB-12-WH	5W	275LM	30K/40K/50K + RGB - White	10
UCA-RGBW-PB-18-BR	8W	440LM	30K/40K/50K + RGB - Bronze	10
UCA-RGBW-PB-18-WH	8W	440LM	30K/40K/50K + RGB - White	10
UCA-RGBW-PB-24-BR	12W	660LM	30K/40K/50K + RGB - Bronze	10
UCA-RGBW-PB-24-WH	12W	660LM	30K/40K/50K + RGB - White	10
UCA-RGBW-PB-32-BR	16W	880LM	30K/40K/50K + RGB - Bronze	10
UCA-RGBW-PB-32-WH	16W	880LM	30K/40K/50K + RGB - White	10
UCA-RGBW-PB-40-BR	20W	1100LM	30K/40K/50K + RGB - Bronze	10
UCA-RGBW-PB-40-WH	20W	1100LM	30K/40K/50K + RGB - White	10

PSAL-WH

PSAL-BR

PSAL-BN

ANGLED POWER STRIP & UNDER CABINET LIGHT W/ POWER RECEPTACLE

CATALOG NO.	DESCRIPTION			PCK QTY
PSAL-13-1R-MCT5-WH	N/A	420LM	27K/30K/35K/40K/50K - 13" White	12
PSAL-13-1R-MCT5-BR	N/A	420LM	27K/30K/35K/40K/50K - 13" Bronze	12
PSAL-13-1R-MCT5-BN	N/A	420LM	27K/30K/35K/40K/50K - 13" Brushed Nickel	12
PSAL-18-2R-MCT5-WH	N/A	600LM	27K/30K/35K/40K/50K - 18" White	12
PSAL-18-2R-MCT5-BR	N/A	600LM	27K/30K/35K/40K/50K - 18" Bronze	12
PSAL-18-2R-MCT5-BN	N/A	600LM	27K/30K/35K/40K/50K - 18" Brushed Nickel	12
PSAL-24-3R-MCT5-WH	N/A	790LM	27K/30K/35K/40K/50K - 24" White	6
PSAL-24-3R-MCT5-BR	N/A	790LM	27K/30K/35K/40K/50K - 24" Bronze	6
PSAL-24-3R-MCT5-BN	N/A	790LM	27K/30K/35K/40K/50K - 24" Brushed Nickel	6
PSAL-30-3R-MCT5-WH	N/A	900LM	27K/30K/35K/40K/50K - 30" White	6
PSAL-30-3R-MCT5-BR	N/A	900LM	27K/30K/35K/40K/50K - 30" Bronze	6
PSAL-30-3R-MCT5-BN	N/A	900LM	27K/30K/35K/40K/50K - 30" Brushed Nickel	6
PSAL-36-4R-MCT5-WH	N/A	1050LM	27K/30K/35K/40K/50K - 36" White	6
PSAL-36-4R-MCT5-BR	N/A	1050LM	27K/30K/35K/40K/50K - 36" Bronze	6
PSAL-36-4R-MCT5-BN	N/A	1050LM	27K/30K/35K/40K/50K - 36" Brushed Nickel	6
PSAL-42-4R-MCT5-WH	N/A	1275LM	27K/30K/35K/40K/50K - 42" White	6
PSAL-42-4R-MCT5-BR	N/A	1275LM	27K/30K/35K/40K/50K - 42" Bronze	6
PSAL-42-4R-MCT5-BN	N/A	1275LM	27K/30K/35K/40K/50K - 42" Brushed Nickel	6



PSAL-RGBWW-BN

PSAL-RGBWW-BR



PSAL-RGBWW-WH

RGB + CCT ANGLED POWER STRIP & UNDERCABINET LIGHT W/ POWER RECEPTACLE

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	
PSAL-13-1R-1U-RGBWW-WH	6W	420LM	RGBW - White	
PSAL-18-2R-1U-RGBWW-WH	8W	600LM	RGBW - White	
PSAL-24-3R-2U-RGBWW-WH	10.5W	790LM	RGBW - White	
PSAL-30-3R-2U-RGBWW-WH	12W	900LM	RGBW - White	
PSAL-36-4R-2U-RGBWW-WH	14W	1050LM	RGBW - White	
PSAL-42-4R-2U-RGBWW-WH	17W	1275LM	RGBW - White	

PSA-WH

PSA-BR

PSA-BN

ANGLED POWER STRIP W/ POWER & USB RECEPTACLES

CATALOG NO.	DESCRIPTION
PSA-12-2R-1U-WH	12In Angled 2-Receptacle 1 Usb 20A Power Strip White
PSA-12-2R-1U-BR	12In Angled 2-Receptacle 1 Usb 20A Power Strip Bronze
PSA-12-2R-1U-BN	12In Angled 2-Receptacle 1 Usb 20A Power Strip Brushed Nickel
PSA-18-2R-1U-WH	18In Angled 2-Receptacle 1 Usb 20A Power Strip White
PSA-18-2R-1U-BR	18In Angled 2-Receptacle 1 Usb 20A Power Strip Bronze
PSA-18-2R-1U-BN	18In Angled 2-Receptacle 1 Usb 20A Power Strip Brushed Nickel
PSA-24-3R-2U-WH	24In Angled 3-Receptacle 2 Usb 20A Power Strip White
PSA-24-3R-2U-BR	24In Angled 3-Receptacle 2 Usb 20A Power Strip Bronze
PSA-24-3R-2U-BN	24In Angled 3-Receptacle 2 Usb 20A Power Strip Brushed Nickel
PSA-30-3R-2U-WH	30In Angled 3-Receptacle 2 Usb 20A Power Strip White
PSA-30-3R-2U-BR	30In Angled 3-Receptacle 2 Usb 20A Power Strip Bronze
PSA-30-3R-2U-BN	30In Angled 3-Receptacle 2 Usb 20A Power Strip Brushed Nickel
PSA-36-4R-2U-WH	36In Angled 4-Receptacle 2 Usb 20A Power Strip White
PSA-36-4R-2U-BR	36In Angled 4-Receptacle 2 Usb 20A Power Strip Bronze
PSA-36-4R-2U-BN	36In Angled 4-Receptacle 2 Usb 20A Power Strip Brushed Nickel
PSA-42-4R-2U-WH	42In Angled 4-Receptacle 2 Usb 20A Power Strip White
PSA-42-4R-2U-BR	42In Angled 4-Receptacle 2 Usb 20A Power Strip Bronze
PSA-42-4R-2U-BN	42In Angled 4-Receptacle 2 Usb 20A Power Strip Brushed Nickel

UCW-12V



UCW-24V

UC-DISPLAY

LED LINEAR UNDER CABINET LIGHT USE EXTERNAL DRIVERS

CATALOG NO.	DESCRIPTION			PCK QTY
UCW6WW	2W	140LM	3000K - 6"	30
UCW6W	2W	168LM	6000K - 6"	30
UCW12WW	3W	250LM	3000K - 12"	30
UCW12W	3W	280LM	6000K - 12"	30
UCW20WW	5W	420LM	3000K - 20"	30
UCW20W	5W	462LM	6000K - 20"	30
UCW32WW	8W	590LM	3000K - 32"	30
UCW32W	8W	640LM	6000K - 32"	30
UCW40WW	11W	820LM	3000K - 40"	30
UCW40W	11W	880LM	6000K - 40"	30
UC6WW	2W	140LM	3000K - 6"	30
UC6W	2W	168LM	6000K - 6"	30
UC12WW	3W	250LM	3000K - 12"	30
UC12W	3W	280LM	6000K - 12"	30
UC20WW	5W	420LM	3000K - 20"	30
UC40WW	11W	820LM	3000K - 40"	30
UC40W	11W	880LM	6000K - 40"	30
UC-DISPLAY	Display Board for UC Series			

POWER SUPPLY

PLUG-IN DRIVERS 12V/24V NON-DIMMING

CATALOG NO.	DESCRIPTION
UC12PS6W	6W, 12V, POWER SUPPLY WITH CABLE
UCPS6W	6W, 24V, POWER SUPPLY W/ CABLE
UCPS12W	12W, 24V, POWER SUPPLY W/ 1.5 POWER CABLE
UCPS24W	24W, 24V, 1A, POWER SUPPLY W/ 1.5 POWER CABLE
UCPS48W	48W, 24V, 1A, POWER SUPPLY W/ 1.5 POWER CABLE

TRANSFORMERS

MAGNETIC DIMMABLE DRIVERS 12V/24V USE MAGNETIC LOW-VOLTAGE DIMMERS

NOT DIMMABLE WITH RGB PRODUCTS (USE THE DIMMING FEATURE OF YOUR RGB CONTROLLER)

CATALOG NO.	DESCRIPTION
UCM-20L-12DC	DIMMABLE, 20W, 12V, 5" X 2-1/8" X 2"
UCM-40L-12DC	DIMMABLE, 40W, 12V, 5" X 2-1/8" X 2"
UCM-50L-12DC	DIMMABLE, 50W, 12V, 5" X 2-1/8" X 2"
UCM-100L-12DC	DIMMABLE, 100W, 12V, 5" X 4-1/8" X 2"
UCM-150L-12DC	DIMMABLE, 150W, 12V, 5" X 4-1/8" X 4"
UCM-300L-12DC	DIMMABLE, 300W, 12V, 5" X 4-1/8" X 4"
UCM-20L-24DC	DIMMABLE, 20W, 24V, 5" X 2-1/8" X 2"
UCM-40L-24DC	DIMMABLE, 40W, 24V, 5" X 2-1/8" X 2"
UCM-50L-24DC	DIMMABLE, 50W, 24V, 5" X 2-1/8" X 2"
UCM-60L-24DC	DIMMABLE, 60W, 24V, 5" X 2-1/8" X 2"
UCM-96L-24DC	DIMMABLE, 96W, 24V, 5" X 4-1/8" X 2"
UCM-150L-24DC	DIMMABLE, 150W, 24V, 5" X 4-1/8" X 4"
UCM-300L-24DC	DIMMABLE, 300W, 24V, 5" X 4-1/8" X 4"

*NOT DIMMABLE WITH RGB PRODUCTS. USE THE DIMMING FEATURE OF YOUR RGB CONTROLLER

ACCESSORIES

UNDER CABINET LIGHTING PARTS & ACCESSORIES

CATALOG NO.	DESCRIPTION
UCDIMMER	LED UNDER CABINET LIGHTS DIMMER
UCDIMMER-TOUCH	LINEAR UNDER CABINET TOUCH DIMMER TO CONNECT TO FIXTURES END, BLACK
UCDIMMER-TOUCH-WH	LINEAR UNDER CABINET TOUCH DIMMER TO CONNECT TO FIXTURES END, WHITE
UCJUNCTION-W	HARD WIRE POWER FEED IN / OUT, WHITE
UCSENS-PIR-1	PIR SENSOR, AUTO ON/OFF WHEN MOVEMENT, MAX 72W, 4" (10CM) RANGE, 120D, -20°C TO 40°C INDOORS

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION
UCSENS-PIR	PIR SENSOR, AUTO ON/OFF WHEN MOVEMENT, MAX 72W, 4" (10CM) RANGE, 120D, -20°C TO 40°C INDOORS
UCCONCABLE	3.25 FT. CONNECTOR CABLE, BLACK
UCCONCABLE-WH	3.25 FT. CONNECTOR CABLE, WHITE
UCCONCABLE-10	10 FT. UNDER CABINET LIGHT CONNECTOR CABLE, BOTH SIDE MALE, BLACK
UCCONCABLE-10-WH	10 FT. UNDER CABINET LIGHT CONNECTOR CABLE, BOTH SIDE MALE, WHITE
UCCOP-3F	3 FT. UNDER CABINET LIGHT COUPLING, BOTH SIDE FEMALE, BLACK
UCCOP-3F-WH	3 FT. UNDER CABINET LIGHT COUPLING, BOTH SIDE FEMALE, WHITE
UCPOWERC-10F	10 FT. UNDER CABINET LIGHT POWER CONNECTOR, 1 SIDE MALE, 1 SIDE FEMALE, BLACK
UCPOWERC-10F-WH	10 FT. UNDER CABINET LIGHT POWER CONNECTOR, 1 SIDE MALE, 1 SIDE FEMALE, WHITE
UCRE04	4 OUTPUT EASY RECEPTACLE
UCRE08	8 OUTPUT EASY RECEPTACLE
UCAC01	CORNER CONNECTOR, BLACK
UCAC01-WH	CORNER CONNECTOR, WHITE
UCPLASCONN-WH	PLASTIC CONNECTOR, WHITE
UCMAGNET+3M	2 PCS OF MAGNET AND 2 PCS OF 3M TAPE FOR LED UNDER CABINET LIGHTS

c UL us LISTED

UC-ADJ

LED ADJUSTABLE UNDER CABINET **24V**

CATALOG NO.	DESCRIPTION			PCK QTY
UC-ADJ-12W	5W	400LM	6000K - 11.81"	30
UC-ADJ-20WW	8W	600LM	3000K - 19.68"	30
UC-ADJ-20W	8W	640LM	6000K - 19.68"	30
UC-ADJ-40WW	16W	1200LM	3000K - 39.37"	30
UC-ADJ-40W	16W	1280LM	6000K - 39.37"	30
UC-ADJ-PIR	PIR SENSOR FOR U/C ADJUSTABLE SERIES			
UC-ADJ-DMR	TOUCH DIMMER WITH MEMORY FOR U/C ADJUSTABLE SERIES			

T5 & ACCESSORIES

LED LINKABLE STRIP WITH INTERNAL DRIVER 120VAC DIRECT DIMMABLE

SURFACE MOUNTING BRACKETS & SCREWS INCLUDED

CATALOG NO.	DESCRIPTION			PCK QTY
T5-12IN-5W-30K-D	5W	575LM	3000K - 1FT.	24
T5-12IN-5W-40K-D	5W	575LM	4000K - 1FT.	24
T5-12IN-5W-50K-D	5W	625LM	5000K - 1FT.	24
T5-22IN-9W-30K-D	9W	1035LM	3000K - 2FT.	24
T5-22IN-9W-40K-D	9W	1035LM	4000K - 2FT.	24
T5-22IN-9W-50K-D	9W	1125LM	5000K - 2FT.	24
T5-47IN-16W-30K-D	16W	1840LM	3000K - 4FT.	24
T5-47IN-16W-50K-D	16W	2000LM	5000K - 4FT.	24
T5-6FT-PC	6 FT. Plug-in Power Cord			
T5-6FT-PCS	6 FT. Plug-in Power Cord with Switch			
T5-8IN-JUMP	8" Linking Cable			
T5-6FT-PT	6' AC Input Wire (PIGTAIL)			
T5-COUPLER	Coupler (1 Included)			
T5-MAGSET	Clip-on Secure Magnet Set			

PL12-MCT5

12V PUCK 5CCT WITH PIR SENSOR

CATALOG NO.	DESCRIPTION		
PL12-MCT5-PIR-WH	5W	300LM	27K/30K/35K/40K/50K - White
PL12-MCT5-PIR-BN	5W	300LM	27K/30K/35K/40K/50K - Brushed-Nickel

TC-PL12-RGBW

Remote Control

WG SMART APP COMPATIBLE RGBW PUCK LIGHT ROUND

CATALOG NO.	DESCRIPTION		
TC-PL12-RGBW	4W	250LM	RGB
TC-PL12-RGBW-SPLITTER4	RGB Puck Light 4-Port Splitter With 6in Cable		
TC-PL12-RGBW-CONTROLLER	RGBW In-Line Smart Controller App Compatible		

ROUND ADJUSTABLE PUCK LIGHT

3-PACK ROUND ADJUSTABLE PUCK LIGHT

LED ADJUSTABLE PUCK LIGHT 120V 6FT POWER CORD WITH IN-LINE SWITCH

CATALOG NO.	DESCRIPTION		
3" ROUND ADJUSTABLE PUCK LIGHT			
PL120ADJ-30K-WH	4.5W	250LM	3000K - White
PL120ADJ-40K-WH	4.5W	250LM	4000K - White
PL120ADJ-50K-WH	4.5W	250LM	5000K - White
PL120ADJ-30K-BK	4.5W	250LM	3000K - Black
PL120ADJ-40K-BK	4.5W	250LM	4000K - Black
PL120ADJ-50K-BK	4.5W	250LM	5000K - Black
PL120ADJ-30K-BN	4.5W	250LM	3000K - Brushed-Nickel
PL120ADJ-40K-BN	4.5W	250LM	4000K - Brushed-Nickel
PL120ADJ-50K-BN	4.5W	250LM	5000K - Brushed-Nickel
3-PACK 3" ROUND ADJUSTABLE PUCK LIGHT			
PL120ADJ-3KIT-30K-WH	4.5W	250LM	3000K - White
PL120ADJ-3KIT-40K-WH	4.5W	250LM	4000K - White
PL120ADJ-3KIT-50K-WH	4.5W	250LM	5000K - White
PL120ADJ-3KIT-30K-BK	4.5W	250LM	3000K - Black
PL120ADJ-3KIT-40K-BK	4.5W	250LM	4000K - Black
PL120ADJ-3KIT-50K-BK	4.5W	250LM	5000K - Black
PL120ADJ-3KIT-30K-BN	4.5W	250LM	3000K - Brushed-Nickel
PL120ADJ-3KIT-40K-BN	4.5W	250LM	4000K - Brushed-Nickel
PL120ADJ-3KIT-50K-BN	4.5W	250LM	5000K - Brushed-Nickel

ROUND & SQUARE SLIM PUCK LIGHT

PL12R & PL12S SERIES COLOR TRIMS

ROUND SLIM PUCK LIGHT

3-PACK ROUND SLIM PUCK LIGHT

PL12 SERIES COLOR TRIM

ROUND ADJUSTABLE PUCK LIGHT - DRIVER NOT INCL

LED PUCK LIGHT ACCESSORIES

LED PUCK LIGHT 3.3 FT CORD WITH MALE SOCKET, MOUNTING HARDWARE, SCREWLESS TRIM

CATALOG NO.	DESCRIPTION		
4" ROUND & SQUARE SLIM PUCK LIGHT 12V			
PL12R-30K-WH	3.5W	230LM	3000K - White
PL12R-40K-WH	3.5W	230LM	4000K - White
PL12R-50K-WH	3.5W	230LM	5000K - White
PL12S-30K-WH	3.5W	230LM	3000K - White
PL12S-40K-WH	3.5W	230LM	4000K - White
PL12S-50K-WH	3.5W	230LM	5000K - White
PL12R & PL12S SERIES COLOR TRIMS			
PL12R-TRM-BK	PL12R series replacement color trim-Black		
PL12R-TRM-BN	PL12R series replacement color trim-Brushed-Nickel		
PL12R-TRM-BR	PL12R series replacement color trim-Bronze		
PL12S-TRM-BK	PL12S series replacement color trim-Black		
PL12S-TRM-BN	PL12S series replacement color trim-Brushed-Nickel		
PL12S-TRM-BR	PL12S series replacement color trim-Bronze		
3" ROUND SLIM PUCK LIGHT - 1/8IN H (1/16IN WHEN RECESSED) 12V			
PL12-30K-WH	2W	120LM	3000K - White
PL12-40K-WH	2W	120LM	4000K - White
PL12-50K-WH	2W	120LM	5000K - White
PL12-30K-BK	2W	120LM	3000K - Black
PL12-40K-BK	2W	120LM	4000K - Black
PL12-50K-BK	2W	120LM	5000K - Black
PL12-30K-BN	2W	120LM	3000K - Brushed-Nickel
PL12-40K-BN	2W	120LM	4000K - Brushed-Nickel
PL12-50K-BN	2W	120LM	5000K - Brushed-Nickel

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION		
3" ROUND SLIM PUCK LIGHT - 5CCT ADJUSTABLE - 5/8IN H (1/16IN WHEN RECESSED) 12V			
PL12-MCT5-WH	4W	250LM	27K/30K/35K/40K/50K - White
PL12-MCT5-BK	4W	250LM	27K/30K/35K/40K/50K - Black
PL12-MCT5-BN	4W	250LM	27K/30K/35K/40K/50K - Brushed-Nickel
3-PACK 3" ROUND SLIM PUCK LIGHT - 1/8IN H (1/16IN WHEN RECESSED) 12V			
PL12-3KIT-30K-WH	2W	120LM	3000K - White
PL12-3KIT-40K-WH	2W	120LM	4000K - White
PL12-3KIT-50K-WH	2W	120LM	5000K - White
PL12-3KIT-30K-BK	2W	120LM	3000K - Black
PL12-3KIT-40K-BK	2W	120LM	4000K - Black
PL12-3KIT-50K-BK	2W	120LM	5000K - Black
PL12-3KIT-30K-BN	2W	120LM	3000K - Brushed-Nickel
PL12-3KIT-40K-BN	2W	120LM	4000K - Brushed-Nickel
PL12-3KIT-50K-BN	2W	120LM	5000K - Brushed-Nickel
PL12 SERIES COLOR TRIMS			
PL12-TRM-BK	PL12 series replacement color trim-Black		
PL12-TRM-BN	PL12 series replacement color trim-Brushed-Nickel		
PL12-TRM-BR	PL12 series replacement color trim-Bronze		
3" ROUND ADJUSTABLE PUCK LIGHT - DRIVER NOT INCLUDED 12V			
PL12ADJ-30K-WH	4.5W	250LM	3000K - White
PL12ADJ-40K-WH	4.5W	250LM	4000K - White
PL12ADJ-50K-WH	4.5W	250LM	5000K - White
PL12ADJ-30K-BK	4.5W	250LM	3000K - Black
PL12ADJ-40K-BK	4.5W	250LM	4000K - Black
PL12ADJ-50K-BK	4.5W	250LM	5000K - Black
PL12ADJ-30K-BN	4.5W	250LM	3000K - Brushed-Nickel
PL12ADJ-40K-BN	4.5W	250LM	4000K - Brushed-Nickel
PL12ADJ-50K-BN	4.5W	250LM	5000K - Brushed-Nickel
LED PUCK LIGHT ACCESSORIES			
PL12-SPLIT3-WH	3-Hole mini splitter with female socket & 40" cord, white		
PL12-SPLIT3-BK	3-Hole mini splitter with female socket & 40" cord, Black		
PL12-SPLIT6-WH	6-Hole mini splitter with female socket & 40" cord, white		
PL12-SPLIT6-BK	6-Hole mini splitter with female socket & 40" cord, Black		
PL12-SPLIT10-WH	10-Hole mini splitter with female socket & 40" cord, white		
PL12-SPLIT10-BK	10-Hole mini splitter with female socket & 40" cord, Black		
PL12-PF-WH	6" Power feed cord, White		
PL12-PF-BK	6" Power feed cord, Black		
PL12-PIDR-12W-WH	12W Plug-in driver with switch, white		
PL12-PIDR-12W-BK	12W Plug-in driver with switch, Black		
PL12-PIDR-24W-WH	24W Plug-in driver with switch, white		
PL12-PIDR-24W-BK	24W Plug-in driver with switch, Black		
PL12-ILDMR-WH	In-Line dimming control, White		
PL12-ILDMR-BK	In-Line dimming control, Black		
PL12-HWDR-25W-D	25W Hardwired Dimmable driver with switch, 120V		

PL12-DISPLAY

LED PUCK LIGHTS DISPLAY BOARD

CATALOG NO.	DESCRIPTION
PL12-DISPLAY	Display board with Brochures for PL12 Series

RIBBON LIGHTING

ULR-IN-SO SERIES

ULR-IN-HO SERIES

ULR-IN-HO-BK Black Ribbon light

ULR-IN-XHO SERIES

YHO RIBBON PIC

ULR-COB SERIES

ULR-IN-16FT-HO-COBB-WT


ULR-OT-49F-HO ULR-OT-16F-HO1

ULR-IN-XHO SERIES

RGBW CONTROLLER SERIES


ULR-OT-49F-HO ULR-OT-16F-HO1


ULR-OT-49F-HO ULR-OT-16F-HO1

ULR-COB SERIES

ULS SERIES

ULR-IN-PIDR2

ULR-IN-HWDR-150W

ELECTRONIC DRIVER SERIES


LEDDR-24V-WP

CHANEL & LENS SERIES


ULR-CH-SURF-SHALLOW

ULR-2WRE

ULR-COB-WT SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

ULR-IN-16FT-SO

ULR-IN-98FT-SO

INDOOR TANDEM COUPLINGS

INDOOR POWER FEED CABLES

24V INDOOR LED RIBBON LIGHT - STANDARD OUTPUT

CATALOG NO.	DESCRIPTION		
STANDARD OUTPUT LED RIBBON—INDOOR 16.4FT ROLLS, MAX RUN 49FT			
ULR-IN-16F-SO-27K	1.5W/FT	100LM/FT	2700K - 8mm Width 16.4FT Reel Length
ULR-IN-16F-SO-30K	1.5W/FT	100LM/FT	3000K - 8mm Width 16.4FT Reel Length
ULR-IN-16F-SO-35K	1.5W/FT	100LM/W	3500K - 8mm Width 16.4FT Reel Length
ULR-IN-16F-SO-40K	1.5W/FT	100LM/FT	4000K - 8mm Width 16.4FT Reel Length
ULR-IN-16F-SO-50K	1.5W/FT	100LM/FT	5000K - 8mm Width 16.4FT Reel Length
STANDARD OUTPUT LED RIBBON—INDOOR 98.4FT ROLLS, MAX RUN 49FT			
ULR-IN-98F-SO-27K	1.5W/FT	100LM/FT	2700K - 8mm Width 98.4FT Reel Length
ULR-IN-98F-SO-30K	1.5W/FT	100LM/FT	3000K - 8mm Width 98.4FT Reel Length
ULR-IN-98F-SO-35K	1.5W/FT	100LM/W	3500K - 8mm Width 98.4FT Reel Length
ULR-IN-98F-SO-40K	1.5W/FT	100LM/FT	4000K - 8mm Width 98.4FT Reel Length
ULR-IN-98F-SO-50K	1.5W/FT	100LM/FT	5000K - 8mm Width 98.4FT Reel Length
INDOOR TANDEM COUPLINGS			
ULR-IN-SO-COUP-6I-WR	Coupling to connect 2 standard output ribbons, 6”		
ULR-IN-SO-COUP-3F-WR	Coupling to connect 2 standard output ribbons, 3ft		
ULR-IN-SO-COUP-NO-WR	Coupling to connect 2 standard output ribbons, no wire		
INDOOR POWER FEED CABLES			
ULR-IN-SO-CONN-6I-WR	1 side ribbon connector, 1 side female socket to driver, 6”		
ULR-IN-SO-CONN-3F-WR	1 side ribbon connector, 1 side female socket to driver, 3ft		
ULR-IN-SO-CONN-3F-PT	1 side ribbon connector, 1 side open end, 3ft		
ULR-IN-SO-CONN-10F-PT	1 side ribbon connector, 1 side open end, 10ft		

ULR-IN-16FT-HO

ULR-IN-HO

ULR-IN-98FT-HO

INDOOR TANDEM COUPLINGS

INDOOR POWER FEED CABLES

24V INDOOR LED RIBBON LIGHT - HIGH OUTPUT

CATALOG NO.	DESCRIPTION		
HIGH OUTPUT LED RIBBON—INDOOR 16.4FT ROLLS MAX RUN 20FT			
ULR-IN-16F-HO-27K	4.4W/FT	310LM/FT	2700K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-30K	4.4W/FT	310LM/FT	3000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-35K	4.4W/FT	310LM/FT	3500K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-40K	4.4W/FT	330LM/FT	4000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-50K	4.4W/FT	350LM/FT	5000K - 10mm Width 16.4FT Reel Length
HIGH OUTPUT LED BLACK RIBBON—INDOOR 16.4FT ROLLS MAX RUN 20FT			
ULR-IN-16F-HO-27K-BK	4.4W/FT	310LM/FT	2700K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-30K-BK	4.4W/FT	310LM/FT	3000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-35K-BK	4.4W/FT	310LM/FT	3500K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-40K-BK	4.4W/FT	330LM/FT	4000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-50K-BK	4.4W/FT	350LM/FT	5000K - 10mm Width 16.4FT Reel Length
HIGH OUTPUT LED RIBBON—INDOOR 98.4FT ROLLS MAX RUN 20FT			
ULR-IN-98F-HO-27K	4.4W/FT	310LM/FT	2700K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-HO-30K	4.4W/FT	310LM/FT	3000K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-HO-35K	4.4W/FT	310LM/FT	3500K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-HO-40K	4.4W/FT	330LM/FT	4000K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-HO-50K	4.4W/FT	350LM/FT	5000K - 10mm Width 98.4FT Reel Length
INDOOR TANDEM COUPLINGS			
ULR-IN-HO-COUP-6I-WR	Coupling to connect 2 high & Extra output ribbons, 6"		
ULR-IN-HO-COUP-3F-WR	Coupling to connect 2 high & Extra output ribbons, 3ft		
ULR-IN-HO-COUP-NO-WR	Coupling to connect 2 high & Extra output ribbons, no wire		
INDOOR POWER FEED CABLES			
ULR-IN-HO-CONN-6I-WR	1 side ribbon connector, 1 side female socket to driver, 6"		
ULR-IN-HO-CONN-3F-WR	1 side ribbon connector, 1 side female socket to driver, 3ft		
ULR-IN-HO-CONN-3F-PT	1 side ribbon connector, 1 side open end, 3ft		
ULR-IN-HO-CONN-10F-PT	1 side ribbon connector, 1 side open end, 10ft		

ULR-IN-16F-XHO

ULR-IN-98F-XHO

ULR-IN-16F-XHO

INDOOR TANDEM COUPLINGS

INDOOR POWER FEED CABLES

24V INDOOR LED RIBBON LIGHT - EXTRA HIGH OUTPUT XHO MODEL MUST BE INSTALLED IN ALUMINUM CHANNEL FOR BETTER HEAT DISSIPATION

CATALOG NO.	DESCRIPTION		
EXTRA HIGH OUTPUT LED RIBBON—INDOOR 16.4FT ROLLS MAX RUN 11FT			
ULR-IN-16F-XHO-27K	8.8W/FT	620LM/FT	2700K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-XHO-30K	8.8W/FT	620LM/FT	3000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-XHO-35K	8.8W/FT	620LM/FT	3500K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-XHO-40K	8.8W/FT	680LM/FT	4000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-XHO-50K	8.8W/FT	700LM/FT	5000K - 10mm Width 16.4FT Reel Length
EXTRA HIGH OUTPUT LED RIBBON—INDOOR 98.4FT ROLLS MAX RUN 11FT			
ULR-IN-98F-XHO-27K	8.8W/FT	620LM/FT	2700K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-XHO-30K	8.8W/FT	620LM/FT	3000K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-XHO-35K	8.8W/FT	620LM/FT	3500K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-XHO-40K	8.8W/FT	680LM/FT	4000K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-XHO-50K	8.8W/FT	700LM/FT	5000K - 10mm Width 98.4FT Reel Length
ULTRA HIGH OUTPUT LED RIBBON—INDOOR 16.4FT ROLLS MAX RUN 14FT			
ULR-IN-16F-YHO-27K	6.7W/FT	820LM/FT	2700K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-YHO-30K	6.7W/FT	820LM/FT	3000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-YHO-35K	6.7W/FT	820LM/FT	3500K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-YHO-40K	6.7W/FT	880LM/FT	4000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-YHO-50K	6.7W/FT	900LM/FT	5000K - 10mm Width 16.4FT Reel Length
INDOOR TANDEM COUPLINGS			
ULR-IN-HO-COUP-6I-WR	Coupling to connect 2 high & Extra output ribbons, 6"		
ULR-IN-HO-COUP-3F-WR	Coupling to connect 2 high & Extra output ribbons, 3ft		
ULR-IN-HO-COUP-NO-WR	Coupling to connect 2 high & Extra output ribbons, no wire		
INDOOR POWER FEED CABLES			
ULR-IN-HO-CONN-6I-WR	1 side ribbon connector, 1 side female socket to driver, 6"		
ULR-IN-HO-CONN-3F-WR	1 side ribbon connector, 1 side female socket to driver, 3ft		
ULR-IN-HO-CONN-3F-PT	1 side ribbon connector, 1 side open end, 3ft		
ULR-IN-HO-CONN-10F-PT	1 side ribbon connector, 1 side open end, 10ft		

ULR-IN-16FT-HO-COBB

ULR-IN-98FT-HO-COBB

INDOOR TANDEM COUPLINGS

INDOOR POWER FEED CABLES

24V INDOOR COB RIBBON LIGHT - HIGH OUTPUT

CATALOG NO.	DESCRIPTION		
HIGH OUTPUT COB RIBBON—INDOOR 16.4FT ROLLS MAX RUN 20FT			
ULR-IN-16F-HO-COB-27K	3W/FT	290LM/FT	2700K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-COB-30K	3W/FT	304LM/FT	3000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-COB-35K	3W/FT	304LM/FT	3500K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-COB-40K	3W/FT	337LM/FT	4000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-COB-50K	3W/FT	340LM/FT	5000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-HO-COB-65K	3W/FT	340LM/FT	6500K - 10mm Width 16.4FT Reel Length
HIGH OUTPUT COB RIBBON—INDOOR 98.4FT ROLLS MAX RUN 20FT			
ULR-IN-98F-HO-COB-27K	3W/FT	290LM/FT	2700K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-HO-COB-30K	3W/FT	304LM/FT	3000K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-HO-COB-35K	3W/FT	304LM/FT	3500K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-HO-COB-40K	3W/FT	337LM/FT	4000K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-HO-COB-50K	3W/FT	340LM/FT	5000K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-HO-COB-65K	3W/FT	340LM/FT	6500K - 10mm Width 98.4FT Reel Length
INDOOR TANDEM COUPLINGS			
ULR-IN-HO-COB-COUP-6I-WR	Coupling to connect 2 COB ribbons, 6"		
ULR-IN-HO-COB-COUP-3F-WR	Coupling to connect 2 COB ribbons, 3ft		
ULR-IN-HO-COB-COUP-NO-WR	Coupling to connect 2 COB ribbons, no wire		
INDOOR POWER FEED CABLES			
ULR-IN-HO-COB-CONN-6I-WR	1 side ribbon connector, 1 side female socket to driver, 6"		
ULR-IN-HO-COB-CONN-3F-WR	1 side ribbon connector, 1 side female socket to driver, 3ft		
ULR-IN-HO-COB-CONN-3F-PT	1 side ribbon connector, 1 side open end, 3ft		
ULR-IN-HO-COB-CONN-10F-PT	1 side ribbon connector, 1 side open end, 10ft		

ULR-IN-16FT-HO-COBB-WT

ULR-M2-M3-3A

ULR-LTECH-E2

ULR-T86-JB

24V INDOOR WHITE-TUNING COB RIBBON LIGHT
WHITE-TUNING WITH CONTROLLER - HIGH OUTPUT INSTALL WITH ELECTRONIC DRIVERS ONLY

CATALOG NO.	DESCRIPTION		
ULR-IN-16F-HO-COB-WT	3W/FT	340LM/FT	White Tuning - 10mm Width 16.4FT Reel Length
ULR-M2-M3-3A	White-Tuning Ribbon Light Controller With Remote		
ULR-LTECH-E2	White-Tuning Ribbon Light Wall-Mount Controller		
ULR-T86-JB	86X86mm PVC Junction Box For Wall-Mount Controllers		

ULR-IN-16FT-HO

INDOOR TANDEM COUPLINGS

INDOOR POWER FEED CABLES

24V IP54 DAMP LOCATION LED RIBBON LIGHT - HIGH OUTPUT

CATALOG NO.	DESCRIPTION		
HIGH OUTPUT LED RIBBON— DAMP LOCATION 16.4FT ROLLS MAX RUN 20FT			
ULR-IP54-16F-HO-27K	4.4W/FT	310LM/FT	2700K - 10mm Width 16.4FT Reel Length
ULR-IP54-16F-HO-30K	4.4W/FT	310LM/FT	3000K - 10mm Width 16.4FT Reel Length
ULR-IP54-16F-HO-35K	4.4W/FT	310LM/FT	3500K - 10mm Width 16.4FT Reel Length
ULR-IP54-16F-HO-40K	4.4W/FT	330LM/FT	4000K - 10mm Width 16.4FT Reel Length
ULR-IP54-16F-HO-50K	4.4W/FT	350LM/FT	5000K - 10mm Width 16.4FT Reel Length
INDOOR TANDEM COUPLINGS			
ULR-IP54-HO-COUP-6I-WR	Coupling to connect 2 high & Extra output ribbons, 6”		
ULR-IP54-HO-COUP-3F-WR	Coupling to connect 2 high & Extra output ribbons, 3ft		
ULR-IP54-HO-COUP-NO-WR	Coupling to connect 2 high & Extra output ribbons, no wire		
INDOOR POWER FEED CABLES			
ULR-IP54-HO-CONN-6I-WR	1 side ribbon connector, 1 side female socket to driver, 6”		
ULR-IP54-HO-CONN-3F-WR	1 side ribbon connector, 1 side female socket to driver, 3ft		
ULR-IP54-HO-CONN-3F-PT	1 side ribbon connector, 1 side open end, 3ft		
ULR-IP54-HO-CONN-10F-PT	1 side ribbon connector, 1 side open end, 10ft		

ULR-IN-16FT-HO

INDOOR TANDEM COUPLINGS

INDOOR POWER FEED CABLES

24V LED RGBW RIBBON LIGHT MAX RUN 16.4FT INDOOR & OUTDOOR VERSIONS

INSTALL WITH ELECTRONIC DRIVERS ONLY

CATALOG NO.	DESCRIPTION		
ULR-IN-16F-HO-RGBW	5.8W/FT	225LM/FT	RGB - 20FT Max 12mm Width 16.4FT Reel Length IP20
ULR-OT-16F-HO-RGBW	5.8W/FT	225LM/FT	RGB - 20FT Max 12mm Width 16.4FT Reel Length IP67
RGBW-WIFI-CONTROLLER	RGBW lighting controller with integrated WI-FI and app, RC incl.		
ULR-IN-HO-RGBW-COUP-6I-WR	Coupling to connect 2 RGBW ribbons, 6”		
ULR-IN-HO-RGBW-COUP-3F-WR	Coupling to connect 2 RGBW ribbons, 3ft.		
ULR-IN-HO-RGBW-COUP-NO-WR	Coupling to connect 2 RGBW ribbons, no wire		
ULR-IN-HO-RGBW-CONN-6I-WR	1 side ribbon connector, 1 side open end, 6”		
ULR-IN-HO-RGBW-CONN-3F-WR	1 side ribbon connector, 1 side open end, 3ft		
ULR-OT-HO-RGBW-CONN-3F-WR	3ft RGBW 5C wire both side’s open with 1 rubber jacket		

ULR-M4-M4-3A

RGBW-WIFI-CONTROLLER

ULR-LTECH-E5S

ULR-T86-JB

RGBW CONTROLLERS REQUIRES 24V ELECTRONIC DRIVER

CATALOG NO.	DESCRIPTION
ULR-M4-M4-3A	RGBW Controller (Remote incl.), 288W Max, 12-24 VDC
RGBW-WIFI-CONTROLLER	RGBW lighting controller with integrated WI-FI and app, RC incl.
ULR-LTECH-E5S	RGBW-Tuning Ribbon Light Wall-Mount Controller
ULR-T86-JB	86X86mm PVC Junction Box For Wall-Mount Controllers

c UL us LISTED

WET LOCATIONS

ULR-OT-16FT-HO

ULR-OT-98FT-HO

INDOOR TANDEM COUPLINGS

INDOOR POWER FEED CABLES

24V IP67 OUTDOOR LED RIBBON LIGHT - HIGH OUTPUT

CATALOG NO.	DESCRIPTION		
HIGH OUTPUT LED RIBBON—OUTDOOR 16.4FT ROLLS MAX RUN 20FT			
ULR-OT-16F-HO-27K	4.4W/FT	310LM/FT	2700K - 10mm Width 16.4FT Reel Length
ULR-OT-16F-HO-30K	4.4W/FT	310LM/FT	3000K - 10mm Width 16.4FT Reel Length
ULR-OT-16F-HO-35K	4.4W/FT	310LM/FT	3500K - 10mm Width 16.4FT Reel Length
ULR-OT-16F-HO-40K	4.4W/FT	330LM/FT	4000K - 10mm Width 16.4FT Reel Length
ULR-OT-16F-HO-50K	4.4W/FT	350LM/FT	5000K - 10mm Width 16.4FT Reel Length
HIGH OUTPUT LED RIBBON—OUTDOOR 49FT ROLLS MAX RUN 20FT			
ULR-OT-49F-HO-27K	4.4W/FT	350LM/FT	2700K - 10mm Width 49FT Reel Length
ULR-OT-49F-HO-30K	4.4W/FT	310LM/FT	3000K - 10mm Width 49FT Reel Length
ULR-OT-49F-HO-35K	4.4W/FT	310LM/FT	3500K - 10mm Width 49FT Reel Length
ULR-OT-49F-HO-40K	4.4W/FT	330LM/FT	4000K - 10mm Width 49FT Reel Length
ULR-OT-49F-HO-50K	4.4W/FT	350LM/FT	5000K - 10mm Width 49FT Reel Length
OUTDOOR TANDEM COUPLINGS			
ULR-OT-HO-COUP-6I-WR	Coupling to connect 2 high & Extra output ribbons, 6”		
ULR-OT-HO-COUP-3F-WR	Coupling to connect 2 high & Extra output ribbons, 3ft		
ULR-OT-HO-COUP-NO-WR	Coupling to connect 2 high & Extra output ribbons, no wire		
OUTDOOR POWER FEED CABLES			
ULR-OT-HO-CONN-6I-WR	1 side ribbon connector, 1 side female socket to driver, 6”		
ULR-OT-HO-CONN-3F-WR	1 side ribbon connector, 1 side female socket to driver, 3ft		
ULR-OT-HO-CONN-3F-PT	1 side ribbon connector, 1 side open end, 3ft		
ULR-OT-HO-CONN-10F-PT	1 side ribbon connector, 1 side open end, 10ft		

ULR-OT-16FT-HO

ULR-OT-98FT-HO

INDOOR TANDEM COUPLINGS

INDOOR POWER FEED CABLES

24V IP67 OUTDOOR LED RIBBON LIGHT - EXTRA HIGH OUTPUT

CATALOG NO.	DESCRIPTION			
EXTRA HIGH OUTPUT LED RIBBON—OUTDOOR 16.4FT ROLLS MAX RUN 16.4FT				
ULR-OT-16F-XHO-27K	5.8W/FT	440LM/FT	2700K - 10mm Width	16.4FT Reel Length
ULR-OT-16F-XHO-30K	5.8W/FT	440LM/FT	3000K - 10mm Width	16.4FT Reel Length
ULR-OT-16F-XHO-35K	5.8W/FT	440LM/FT	3500K - 10mm Width	16.4FT Reel Length
ULR-OT-16F-XHO-40K	5.8W/FT	450LM/FT	4000K - 10mm Width	16.4FT Reel Length
ULR-OT-16F-XHO-50K	5.8W/FT	450LM/FT	5000K - 10mm Width	16.4FT Reel Length
EXTRA HIGH OUTPUT LED RIBBON—OUTDOOR 49FT ROLLS MAX RUN 16.4FT				
ULR-OT-49F-XHO-27K	5.8W/FT	450LM/FT	2700K - 10mm Width	49FT Reel Length
ULR-OT-49F-XHO-30K	5.8W/FT	440LM/FT	3000K - 10mm Width	49FT Reel Length
ULR-OT-49F-XHO-35K	5.8W/FT	440LM/FT	3500K - 10mm Width	49FT Reel Length
ULR-OT-49F-XHO-40K	5.8W/FT	450LM/FT	4000K - 10mm Width	49FT Reel Length
ULR-OT-49F-XHO-50K	5.8W/FT	450LM/FT	5000K - 10mm Width	49FT Reel Length
OUTDOOR TANDEM COUPLINGS				
ULR-OT-HO-COUP-6I-WR	Coupling to connect 2 high & Extra output ribbons, 6”			
ULR-OT-HO-COUP-3F-WR	Coupling to connect 2 high & Extra output ribbons, 3ft			
ULR-OT-HO-COUP-NO-WR	Coupling to connect 2 high & Extra output ribbons, no wire			
OUTDOOR POWER FEED CABLES				
ULR-OT-HO-CONN-6I-WR	1 side ribbon connector, 1 side female socket to driver, 6”			
ULR-OT-HO-CONN-3F-WR	1 side ribbon connector, 1 side female socket to driver, 3ft			
ULR-OT-HO-CONN-3F-PT	1 side ribbon connector, 1 side open end, 3ft			
ULR-OT-HO-CONN-10F-PT	1 side ribbon connector, 1 side open end, 10ft			

INDOOR TANDEM COUPLINGS

INDOOR POWER FEED CABLES

ULR-OT-16FT-HO-COBB

ULR-OT-98FT-HO-COBB

24V OUTDOOR COB RIBBON LIGHT - HIGH OUTPUT

CATALOG NO.	DESCRIPTION		
HIGH OUTPUT COB RIBBON—OUTDOOR 16.4FT ROLLS MAX RUN 20FT			
ULR-OT-16F-HO-COB-27K	3W/FT	290LM/FT	2700K - 10mm Width 16.4FT Reel Length
ULR-OT-16F-HO-COB-30K	3W/FT	304LM/FT	3000K - 10mm Width 16.4FT Reel Length
ULR-OT-16F-HO-COB-35K	3W/FT	304LM/FT	3500K - 10mm Width 16.4FT Reel Length
ULR-OT-16F-HO-COB-40K	3W/FT	337LM/FT	4000K - 10mm Width 16.4FT Reel Length
ULR-OT-16F-HO-COB-50K	3W/FT	340LM/FT	5000K - 10mm Width 16.4FT Reel Length
ULR-OT-16F-HO-COB-65K	3W/FT	340LM/FT	6500K - 10mm Width 16.4FT Reel Length
HIGH OUTPUT COB RIBBON—OUTDOOR 98.4FT ROLLS MAX RUN 20FT			
ULR-OT-98F-HO-COB-27K	3W/FT	290LM/FT	2700K - 10mm Width 98.4FT Reel Length
ULR-OT-98F-HO-COB-30K	3W/FT	304LM/FT	3000K - 10mm Width 98.4FT Reel Length
ULR-OT-98F-HO-COB-35K	3W/FT	304LM/FT	3500K - 10mm Width 98.4FT Reel Length
ULR-OT-98F-HO-COB-40K	3W/FT	337LM/FT	4000K - 10mm Width 98.4FT Reel Length
ULR-OT-98F-HO-COB-50K	3W/FT	340LM/FT	5000K - 10mm Width 98.4FT Reel Length
ULR-OT-98F-HO-COB-65K	3W/FT	340LM/FT	6500K - 10mm Width 98.4FT Reel Length
INDOOR TANDEM COUPLINGS			
ULR-OT-HO-COB-COUP-6I-WR	6In Ribbon-To-Ribbon Coupling For COB IP65 Creates IP20 Ends		
ULR-OT-HO-COB-COUP-3F-WR	3Ft Ribbon-To-Ribbon Coupling For COB IP65 Creates IP20 Ends		
INDOOR POWER FEED CABLES			
ULR-OT-HO-COB-CONN-3F-PT	3Ft Ribbon Pigtail Snap Connector To Female End For COB IP65 Creates IP20 End		
ULR-OT-HO-COB-CONN-10F-PT	10Ft Ribbon Pigtail Snap Connector To Female End For COB IP65 Creates IP20 End		
ULR-OT-HO-COB-CONN-6I-WR	6In Ribbon Pigtail Snap Connector To Stripped End For COB IP65 Creates IP20 End		
ULR-OT-HO-COB-CONN-3F-WR	3Ft Ribbon Pigtail Snap Connector To Stripped End For COB IP65 Creates IP20 End		
ULR-OT-HO-COB-CONN-6I-WR-IP65	COB Ribbon Wet Loc IP65 Cap With Pigtail For Solder And Silicone Bag Of 5, Creates IP65 End		
ULR-OT-HO-COB-UCLIP-5PC	COB Ribbon Wet Loc IP65 Mounting Clips And Screws Bag Of 5		
ULR-OT-HO-COB-ENDC-5PC	COB Ribbon Wet Loc IP65 Closed End Cap Bag Of 5, Use With Silicone For IP65 Results		



ULS

24V LED FLEXIBLE SHEET 24CMX48CM

CATALOG NO.	DESCRIPTION		PCK QTY
ULS-2448-35W-30K	35W	3000K	1
ULS-2448-35W-40K	35W	4000K	1
ULS-2448-35W-50K	35W	5000K	1
ULS-2448-70W-WT	35W	WT: White Tuning	1

ULR-IN-PIDR

LED INDOOR ELECTRONIC RIBBON LIGHT PLUG-IN DRIVERS FOR DIMMABLE DRIVERS SEE PAGE 468

CATALOG NO.	DESCRIPTION
ULR-IN-PIDR-48W	48W MAX, 2A, 100~240V INPUT, 15A Plug & Male 24V Connector
ULR-IN-PIDR-72W	72W MAX, 3A, 100~240V INPUT Plug & Male 24V Connector

ULR-IN-HWDR

LED INDOOR ELECTRONIC RIBBON LIGHT HARDWIRE DRIVERS, NON-DIMMABLE

CATALOG NO.	DESCRIPTION
ULR-IN-HWDR-75W	75W MAX, 3.2A, 85~264V INPUT, 15A, 24V
ULR-IN-HWDR-100W	100W MAX, 4.5A, 85~264V INPUT, 15A, 24V
ULR-IN-HWDR-150W	150W MAX, 6.5A, 85~132V INPUT, 15A, 24V
ULR-IN-HWDR-200W	200W MAX, 8.8A, 90~132V INPUT, 15A, 24V
ULR-IN-HWDR-350W	350W MAX, 14.6A, 90~132V INPUT, 15A, 24V
ULR-IN-HWDR-450W	450W MAX, 18.8A, 90~132V INPUT, 15A, 24V
ULR-IN-HWDR-600W	600W MAX, 25A, 90~132V INPUT, 15A, 24V

DIMMING 0-10V

TRIAC DIMMABLE

ELECTRONIC DRIVER

5-IN-1 DIMMABLE ELECTRONIC LED DRIVER WITH JUNCTION BOX **120-277V**

CATALOG NO.	DESCRIPTION
LEDDR-24V-60W-UNIV	5-In-1 Dimmable Electronic Led Driver With Junction Box, 120-277V To 24V 60W
LEDDR-24V-96W-UNIV	5-In-1 Dimmable Electronic Led Driver With Junction Box, 120-277V To 24V 96W
LEDDR-24V-120W-UNIV	5-In-1 Dimmable Electronic Led Driver With Junction Box, 120-277V To 24V 120W
LEDDR-24V-150W-UNIV	5-In-1 Dimmable Electronic Led Driver With Junction Box, 120-277V To 24V 150W
LEDDR-24V-192W-UNIV	5-In-1 Dimmable Electronic Led Driver With Junction Box, 120-277V To 24V 192W
LEDDR-24V-288W-UNIV	5-In-1 Dimmable Electronic Led Driver With Junction Box, 120-277V To 24V 288W
LEDDR-24V-384W-UNIV	5-In-1 Dimmable Electronic Led Driver With Junction Box, 120-277V To 24V 384W

WET LOCATIONS



LEDDR-24V-WP

24V LED OUTDOOR ELECTRONIC NON-DIMMABLE DRIVER **120V** INPUT FOR MAG. DIMMABLE DRIVERS SEE ABOVE

CATALOG NO.	DESCRIPTION	
LEDDR-24V-WP-200W	200W	120V INPUT

ULR-CH





ULR-CH-SURF-DEEP



SURFACE MOUNT CHANNELS & LENSES

CATALOG NO.	DESCRIPTION
ULR-CH-SURF-SHALLOW	12X6 mm Surface mount channel, 4ft.
ULR-CH-SURF-DEEP	12X12 mm Surface mount channel, 4ft.
ULR-LENS-SURF-F	Frosted Lens for 12X6 mm & 12X12 mm Channels
ULR-LENS-SURF-C	Clear Lens for 12X6 mm & 12X12 mm Channels
ULR-CH-SURF-SHALLOW-CAP	End Cap for 12X6 mm Channels
ULR-CH-SURF-DEEP-CAP	End Cap for 12X12 mm Channels
ULR-CH-SURF-16X14	16X14 mm Surface mount channel, 4ft.
ULR-LENS-SURF-16X14-F	Frosted Lens for 16X14 mm Channels
ULR-LENS-SURF-16X14-C	Clear Lens for 16X14 mm Channels
ULR-LENS-SURF-16X14-CAP	End Cap for 16X14 mm Channels

ULR-CH-MUD-13X15



ULR-CH-MUD-37X15



MUD-IN RECESSED MOUNT CHANNELS & LENSES

CATALOG NO.	DESCRIPTION
ULR-CH-MUD-13X15	13X15 mm Mud-InRecessed mount channel, 4ft.
ULR-LENS-MUD-13X15-F	Frosted Lens for 13X15 mm Channels
ULR-LENS-MUD-13X15-C	Clear Lens for 13X15 mm Channels
ULR-CH-MUD-13X15-CAP	End Cap for 13X15 mm Channels
ULR-CH-MUD-37X15	37X15 mm Mud-In Recessed mount channel (Can fit 2 Ribbons), 4ft.
ULR-LENS-MUD-37X15-F	Frosted Lens for 37X15 mm Channels
ULR-LENS-MUD-37X15-C	Clear Lens for 37X15 mm Channels
ULR-LENS-MUD-37X15-CAP	End Cap for 37X15 mm Channels

ULR-CH-45D

45 DEGREE CHANNEL & LENSES

CATALOG NO.	DESCRIPTION
ULR-CH-45D	12X18 mm 45° Channel, 4ft.
ULR-LENS-45D-F	Frosted Lens for 45° Channels
ULR-CH-45D-CAP	End Cap for 45° Channels





ULR-CH-REC



ULR-CH-REC-SHALLOW



ULR-CH-SURF-16X14

RECESSED MOUNT CHANNELS & LENSES

CATALOG NO.	DESCRIPTION
ULR-CH-REC-SHALLOW	20X10 mm Recessed mount channel, 4ft.
ULR-CH-REC-DEEP	20X20 mm Recessed mount channel(Can fit 2 Ribbons), 4ft.
ULR-LENS-REC-F	Frosted Lens for 20X10 mm & 20X20 mm Chennels
ULR-LENS-REC-C	Clear Lens for 20X10 mm & 20X20 mm Chennels
ULR-CH-REC-SHALLOW-CAP	End Cap for 20X10 mm Channels
ULR-CH-REC-DEEP-CAP	End Cap for 20X20 mm Channels
ULR-CH-REC-12X7	12X7 mm Recessed mount channel, 4ft.
ULR-LENS-REC-12X7-F	Frosted Lens for 12X7 mm Channels
ULR-LENS-REC-12X7-C	Clear Lens for 12X7 mm Channels
ULR-CH-REC-12X7-CAP	End Cap for 12X7 mm Channels
ULR-CH-REC-12X12	12X12 mm Recessed mount channel, 4ft.
ULR-LENS-REC-12X12-F	Frosted Lens for 12X12 mm Channels
ULR-LENS-REC-12X12-C	Clear Lens for 12X12 mm Channels
ULR-CH-REC-12X12-CAP	End Cap for 12X12 mm Channels



ACCESSORIES

ACCESSORIES

CATALOG NO.	DESCRIPTION
ULR-OUT-ENDC-5PC	End cap for IP67 ribbons, Pack of 5
ULR-OUT-UCLIP-10PC	Mounting Clip, Pack of 10
ULR-OUT-SGLUE	Silicone glue for sealing compound
ULR-2HSTRP	2-hole rubber strap, Pack of 10

ULR-DCJ

EXTENSION CORDS FOR SECONDARY-SIDE OF DRIVERS

CATALOG NO.	DESCRIPTION
ULR-DCJ-2ML-1FT	DC Jumper cable, Both sides male, 1ft.
ULR-DCJ-2ML-3FT	DC Jumper cable, Both sides male, 3ft.
ULR-DCJ-2ML-10FT	DC Jumper cable, Both sides male, 10ft.
ULR-DCJ-1M1F-1FT	DC Jumper cable, one side male one side female, 1ft.
ULR-DCJ-1M1F-3FT	DC Jumper cable, one side male one side female, 3ft.
ULR-DCJ-1M1F-10FT	DC Jumper cable, one side male one side female, 10ft.
ULR-DCJ-2FM-1FT	DC Jumper cable, Both sides female, 1ft.
ULR-DCJ-2FM-3FT	DC Jumper cable, Both sides female, 3ft.
ULR-DCJ-2FM-10FT	DC Jumper cable, Both sides female, 10ft.
ULR-DCJ-1S1F-3FT	DC Jumper cable, one side female one side striped, 3ft
ULR-DCJ-1S1F-10FT	DC Jumper cable, one side female one side striped, 10ft
ULR-DCJ-1S1M-3FT	DC Jumper cable, one side male one side striped, 3ft
ULR-DCJ-1S1M-10FT	DC Jumper cable, one side male one side striped, 10ft

ULR-2WRE

ACCESSORIES

CATALOG NO.	DESCRIPTION
ULR-2WRE-50FT-18	50' Roll of 18/2 AWG wire
ULR-2WRE-100FT-18	100' Roll of 18/2 AWG wire
ULR-2WRE-50FT-22	50' Roll of 22/2 AWG wire
ULR-2WRE-100FT-22	100' Roll of 22/2 AWG wire
ULR-5WRE-50FT-22	50' Roll of 22/5 AWG wire
ULR-5WRE-100FT-22	100' Roll of 22/5 AWG wire

CUSTOM LENGTHS/ORDER BY FOOT

WE CUT & SOLDER EACH SECTION WITH YOUR DESIRED SIZES

PROVIDE THE LIGHTING PLAN/ WIRING DIAGRAM - ENSURE TO ORDER PIGTAILS/CONNECTORS

24V INDOOR LED RIBBON LIGHT - STANDARD OUTPUT IP20

CATALOG NO.	DESCRIPTION		
ULR-IN-1FT-SO-27K	1.5W/FT	100LM/FT	2700K - 8mm Width
ULR-IN-1FT-SO-30K	1.5W/FT	100LM/FT	3000K - 8mm Width
ULR-IN-1FT-SO-40K	1.5W/FT	100LM/FT	4000K - 8mm Width
ULR-IN-1FT-SO-50K	1.5W/FT	100LM/FT	5000K - 8mm Width

24V INDOOR LED RIBBON LIGHT - HIGH OUTPUT IP20

CATALOG NO.	DESCRIPTION		
HIGH OUTPUT LED RIBBON—INDOOR			
ULR-IN-1FT-HO-27K	4.4W/FT	310LM/FT	2700K - 10mm Width
ULR-IN-1FT-HO-30K	4.4W/FT	310LM/FT	3000K - 10mm Width
ULR-IN-1FT-HO-40K	4.4W/FT	330LM/FT	4000K - 10mm Width
ULR-IN-1FT-HO-50K	4.4W/FT	350LM/FT	5000K - 10mm Width
HIGH OUTPUT LED BLACK RIBBON—INDOOR			
ULR-IN-1FT-HO-27K-BK	4.4W/FT	310LM/FT	2700K - 10mm Width
ULR-IN-1FT-HO-30K-BK	4.4W/FT	310LM/FT	3000K - 10mm Width
ULR-IN-1FT-HO-40K-BK	4.4W/FT	330LM/FT	4000K - 10mm Width
ULR-IN-1FT-HO-50K-BK	4.4W/FT	350LM/FT	5000K - 10mm Width

24V INDOOR LED RIBBON LIGHT - EXTRA HIGH OUTPUT IP20

CATALOG NO.	DESCRIPTION		
EXTRA HIGH OUTPUT LED RIBBON—INDOOR			
ULR-IN-1FT-XHO-27K	8.8W/FT	620LM/FT	2700K - 10mm Width
ULR-IN-1FT-XHO-30K	8.8W/FT	620LM/FT	3000K - 10mm Width
ULR-IN-1FT-XHO-40K	8.8W/FT	680LM/FT	4000K - 10mm Width
ULR-IN-1FT-XHO-50K	8.8W/FT	700LM/FT	5000K - 10mm Width
ULTRA HIGH OUTPUT LED RIBBON—INDOOR			
ULR-IN-1FT-YHO-27K	6.7W/FT	820LM/FT	2700K - 10mm Width
ULR-IN-1FT-YHO-30K	6.7W/FT	820LM/FT	3000K - 10mm Width
ULR-IN-1FT-YHO-40K	6.7W/FT	880LM/FT	4000K - 10mm Width
ULR-IN-1FT-YHO-50K	6.7W/FT	900LM/FT	5000K - 10mm Width

24V INDOOR COB RIBBON LIGHT - HIGH OUTPUT IP20

CATALOG NO.	DESCRIPTION		
EXTRA HIGH OUTPUT COB RIBBON—INDOOR			
ULR-IN-1FT-HO-COB-27K	3W/FT	290LM/FT	2700K - 10mm Width
ULR-IN-1FT-HO-COB-30K	3W/FT	304LM/FT	3000K - 10mm Width
ULR-IN-1FT-HO-COB-40K	3W/FT	337LM/FT	4000K - 10mm Width
ULR-IN-1FT-HO-COB-50K	3W/FT	340LM/FT	5000K - 10mm Width
ULR-IN-1FT-HO-COB-65K	3W/FT	340LM/FT	6500K - 10mm Width

24V INDOOR WHITE-TUNING COB RIBBON LIGHT

WHITE-TUNING WITH CONTROLLER -HIGH OUTPUT INSTALL WITH ELECTRONIC DRIVERS ONLY

CATALOG NO.	DESCRIPTION		
ULR-IN-1FT-HO-COB-WT	3W/FT	340LM/FT	White Tuning
OPT-CONECT-WTUNE-CTRL	Connect Ribbon With White Tunning Controller and Driver		

24V IP54 DAMP LOCATION LED RIBBON LIGHT - HIGH OUTPUT IP54

CATALOG NO.	DESCRIPTION		
HIGH OUTPUT LED RIBBON— DAMP LOCATION			
ULR-IP54-1FT-HO-27K	4.4W/FT	310LM/FT	2700K - 10mm Width
ULR-IP54-1FT-HO-30K	4.4W/FT	310LM/FT	3000K - 10mm Width
ULR-IP54-1FT-HO-40K	4.4W/FT	330LM/FT	4000K - 10mm Width
ULR-IP54-1FT-HO-50K	4.4W/FT	350LM/FT	5000K - 10mm Width

24V LED RGBW RIBBON LIGHT

CATALOG NO.	DESCRIPTION		
ULR-IN-1FT-HO-RGBW	5.8W/FT	225LM/FT	RGB - 10mm Width IP20
ULR-OT-1FT-HO-RGBW	5.8W/FT	225LM/FT	RGB - 10mm Width IP67
OPT-CONECT-RGBW-CTRL	Connect RGBW With Controller and Driver		

24V IP67 OUTDOOR LED RIBBON LIGHT - HIGH OUTPUT IP67

CATALOG NO.	DESCRIPTION		
HIGH OUTPUT LED RIBBON—OUTDOOR			
ULR-OT-1FT-HO-27K	4.4W/FT	310LM/FT	2700K - 10mm Width
ULR-OT-1FT-HO-30K	4.4W/FT	310LM/FT	3000K - 10mm Width
ULR-OT-1FT-HO-40K	4.4W/FT	330LM/FT	4000K - 10mm Width
ULR-OT-1FT-HO-50K	4.4W/FT	350LM/FT	5000K - 10mm Width

24V IP67 OUTDOOR LED RIBBON LIGHT - EXTRA HIGH OUTPUT IP67

CATALOG NO.	DESCRIPTION		
EXTRA HIGH OUTPUT LED RIBBON—OUTDOOR			
ULR-OT-1FT-XHO-27K	5.8W/FT	440LM/FT	2700K - 10mm Width
ULR-OT-1FT-XHO-30K	5.8W/FT	440LM/FT	3000K - 10mm Width
ULR-OT-1FT-XHO-40K	5.8W/FT	450LM/FT	4000K - 10mm Width
ULR-OT-1FT-XHO-50K	5.8W/FT	450LM/FT	5000K - 10mm Width

FACTORY-INSTALLED OPTIONS FOR ULR 1FT

CATALOG NO.	DESCRIPTION
OPT-PT-2HW-6I	Solder 6" 2 Wire Pigtail To Ribbon
OPT-PT-2HW-36I	Solder 36" 2 Wire Pigtail To Ribbon
OPT-PT-2HW-120I	Solder 120" 2 Wire Pigtail To Ribbon
OPT-PT-2HW-240I	Solder 240" 2 Wire Pigtail To Ribbon
OPTF-PTF-2W-6I	Solder 6" 2 Wire Pigtail To Ribbon With Female DC
OPTF-PTF-2W-36I	Solder 36" 2 Wire Pigtail To Ribbon With Female DC
OPTF-PTF-2W-120I	Solder 120" 2 Wire Pigtail To Ribbon With Female DC
OPTF-PTF-2W-240I	Solder 240" 2 Wire Pigtail To Ribbon With Female DC
OPT-PT-5HW-6I	Solder 6" 5 Wire Pigtail To Ribbon
OPT-PT-5HW-36I	Solder 36" 5 Wire RGBW Pigtail To Ribbon
OPT-PT-5HW-120I	Solder 120" 5 Wire RGBW Pigtail To Ribbon
OPT-PT-5HW-240I	Solder 240" 5 Wire RGBW Pigtail To Ribbon
OPT-COUP-2HW	Couple Two Ribbons No Wire
OPT-COUP-2HW-XXI	Couple Two Ribbons W. Speficified Lenght 2 Wire
OPT-COUP-2HW-6I	Couple Two Ribbons W. 6" 2 Wire
OPT-COUP-2HW-36I	Couple Two Ribbons W. 36" 2 Wire
OPT-COUP-2HW-120I	Couple Two Ribbons W. 120" 2 Wire
OPT-COUP-2HW-240I	Couple Two Ribbons W. 240" 2 Wire
OPT-COUP-5HW-XXI	Couple Two Ribbons W. Speficified Lenght 5 Wire
OPT-COUP-5HW-6I	Couple Two RGBW Ribbons W. 6" 5 Wire
OPT-COUP-5HW-36I	Couple Two RGBW Ribbons W. 36" 5 Wire
OPT-COUP-5HW-120I	Couple Two RGBW Ribbons W. 120" 5 Wire
OPT-COUP-5HW-240I	Couple Two RGBW Ribbons W. 240" 5 Wire

LANDSCAPE

AD-018 SERIES

AD120 SERIES

LFLD SERIES

LF4-12V SERIES


LD-CR SERIES

LD-CR SERIES

LD-AN SERIES

LD-110 SERIES

AD-003 SERIES

LD-006 SERIES

LFLV SERIES

LD-009 SERIES

GL SERIES

FLV12 SERIES

LD-176 SERIES

LD-174 SERIES

LD-009 SERIES

AD-131 SERIES

AD-003 SERIES

LFLD2 SERIES


SOLR SERIES

SOLRW SERIES

SOL-PL SERIES


SOLR-WL2 SERIES

LD-192 SERIES

AD-003-WH SERIES

LD-180 SERIES

LF12 SERIES

AD-102 SERIES

AA-18L SERIES

LA-002 SERIES

LA-111-CR SERIES

LA-AN SERIES

LA-CR SERIES

LAL-12V-118 SERIES

LAL-12V-117 SERIES

LAL SERIES

LAL-136 SERIES

AA SERIES

LA-112 SERIES

LAL-145 SERIES

AA-19L SERIES

AA-19L-ORB SERIES

AA-23L SERIES

AA-46L SERIES

WMC2 SERIES

LVW-215 SERIES

LVW-110 SERIES

Search for the series name @WESTGATEMFG.COM

AMERICA'S MOST **DEPENDABLE** LIGHTING

LVW-210-UD SERIES

LVW-210 SERIES

LVW-250 SERIES


LVW-300 SERIES

LVW-310 SERIES

AS-158 SERIES


LS-158 SERIES

LS-185 SERIES

LS-155SERIES

LS-175 SERIES

LS-160 SERIES

LS-172 SERIES

SLSM-LH SERIES

SLM SERIES

HSL SERIES


SL3-F SERIES

SLE-A SERIES


SLE-EL SERIES


SLT-A SERIES

SLT-B SERIES

SLT-S SERIES

UW SERIES

IGL SERIES

IGLA SERIES

WL-140 SERIES

LD-001 SERIES

WLL SERIES

WL-137 SERIES

WL-181 SERIES

WL-FGBZ SERIES

TR-ZC SERIES

TR-2Z SERIES

TR-DT SERIES

TR-MT SERIES

MR16 SERIES

WE167 SERIES

A-41 SERIES

BC SERIES

LA-BZ SERIES


GZ SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

DIRECTIONAL LIGHTS

AD-018-BK

AD-018-AZ

AD-018-ORB

AD-018-WH

12V 7W LED NEW GENERATION ALUMINUM SPOT LIGHT

ALUMINUM, BLACK & METALLIC OIL-RUBBED BRONZE & BRASS SIMULATION FINISHES

CATALOG NO.	DESCRIPTION		
AD-018-MCT-BK	7W	600LM	30K/40K/50K
AD-018-MCT-ORB	7W	600LM	30K/40K/50K
AD-018-MCT-AZ	7W	600LM	30K/40K/50K
AD-018-MCT-WH	7W	700LM	30K/40K/50K
AD-018-RGBW-PB-ORB	7W	600LM	RGBW PUSH BUTTON
AD-018-RGBWW-BT-ORB	7W	600LM	RGBW APP CONTROL

AD120-017

AD120-018

120V GARDEN BULLET WITHOUT/WITH SHROUD

CATALOG NO.	DESCRIPTION			PCK QTY
AD120-017-MCT-ORB	8W	700LM	30K/40K/50K	
AD120-017-MCT-BK	8W	700LM	30K/40K/50K	
AD120-017-MCT-WH	8W	700LM	30K/40K/50K	
AD120-018-MCT-ORB	8W	700LM	30K/40K/50K	
AD120-018-MCT-BK	8W	700LM	30K/40K/50K	

LFLD-5W-30K-BZ

LFLD-5W-30K-BZB

LD-180-BZ

LFLD2-6W-30K-BZ

LFLD3-8W-30K-BZ

12V LED DIRECTIONAL LIGHT SOLID BRASS

CATALOG NO.	DESCRIPTION		
LFLD-5W-30K-BZB	5W	400LM	3000K
LFLD-5W-30K-BZ	5W	400LM	3000K
LD-180-BZ	6W	300LM	3000K
LFLD2-6W-30K-BZ	6W	280LM	3000K
LFLD3-8W-30K-BZ	8W	430LM	3000K

LF12-6W

LF12-G2

12V AC/DC LED GARDEN LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
LF12-6W-27K-KN	6W	400LM	2700K	
LF12-6W-30K-KN	6W	400LM	3000K	
LF12-6W-40K-KN	6W	450LM	4000K	
LF12-6W-50K-KN	6W	450LM	5000K	
LF12-6W-RGBW-KN	6W	450LM	RGB + 3000K	

2ND GEN. 12V AC/DC LED GARDEN LIGHT

LF12-G2-7W-MCT5-BK	7W	500-550LM	27K/30K/35K/40K/50K
LF12-G2-7W-MCT5-ORB	7W	500-550LM	27K/30K/35K/40K/50K

LF4-12V-6W LF4-12V-12W

LF4-12V-24W LF4-12V-30W

LF4-12V-50W

SHROUD on page XX

12V INTEGRATED LED WALL WASH LIGHT

CATALOG NO.	DESCRIPTION		
LF4-12V-6W-30K	6W	440LM	3000K
LF4-12V-6W-50K	6W	500LM	5000K
LF4-12V-12W-30K	12W	1080LM	3000K
LF4-12V-12W-50K	12W	1260LM	5000K
LF4-12V-24W-30K	24W	2155LM	3000K
LF4-12V-24W-50K	24W	2500LM	5000K
LF4-12V-30W-30K	30W	2700LM	3000K
LF4-12V-30W-50K	30W	3150LM	5000K
LF4-12V-50W-30K	50W	4500LM	3000K
LF4-12V-50W-50K	50W	5250LM	5000K

LD-098-CR

LD-176-CR

LD-009-BZ

LD-009-BZB

LD-176-BZ

LD-176-BZB

12V LED DIRECTIONAL LIGHT SOLID COPPER & SOLID BRASS

CATALOG NO.	DESCRIPTION		
LD-098-CR	5W	400LM	3000K
LD-176-CR	5W	400LM	3000K
LD-009-BZ	5W	400LM	3000K
LD-009-BZB	5W	400LM	3000K
LD-176-BZ	5W	400LM	3000K
LD-176-BZB	5W	400LM	3000K

LD-006-BZB

LD-103-BZB

LD-103-AN

LD-099-BZ

LD-099-BZB

LD-174-BZ

LD-110-BZ

12V LED DIRECTIONAL LIGHT

CATALOG NO.	DESCRIPTION		
LD-006-BZ	5W	400LM	3000K
LD-006-BZB	5W	400LM	3000K
LD-103-BZ	5W	400LM	3000K
LD-103-BZB	5W	400LM	3000K
LD-103-AN	5W	400LM	3000K
LD-099-BZ	5W	400LM	3000K
LD-099-BZB	5W	400LM	3000K
LD-174-BZ	5W	400LM	3000K
LD-110-BZ	5W	400LM	3000K

AD-102-BK

AD-003-BK

AD-003-SIL

AD-131-BR

12V LED DIRECTIONAL LIGHT ALUMINUM

CATALOG NO.	DESCRIPTION		
AD-102-BK	5W	400LM	3000K
AD-102-BR	5W	400LM	3000K
AD-003-BK	5W	400LM	3000K
AD-003-BR	5W	400LM	3000K
AD-003-SIL	5W	400LM	3000K
AD-131-BR	5W	400LM	3000K

LD-192-BZ Brass

LD-192-BZB Brass

AD-192-BK Aluminum

LD-192-FBK Fiber Glass

12V LED DIRECTIONAL LIGHT

CATALOG NO.	DESCRIPTION		
LD-192-BZ	5W	400LM	3000K
LD-192-BZB	5W	400LM	3000K
LD-192-FBK	5W	400LM	3000K
AD-192-BK	5W	400LM	3000K
AD-192-BR	5W	400LM	3000K

WHILE SUPPLIES LAST

LFLV-7W

LFLV-12W

12V INTEGRATED LED LANDSCAPE UPLIGHT

CATALOG NO.	DESCRIPTION		
LFLV-7W-27K	7W	500LM	2700K
LFLV-7W-40K	7W	550LM	4000K

WET LOCATIONS



SOLR-PL1-30K

SOLR-SL1-60K-SEN



SOLRW-30K



SOLR-WL2-MCT-SEN

SOLR-WL1-30K-SEN-BK

SPEC SERIES SOLAR LIGHT COLLECTION

CATALOG NO.	DESCRIPTION		
SOLRW-30K	0.2W	50LM	3000K
SOLR-SL1-60K-SEN	0.5W+0.2W	100LM	6000K/3000K
SOLR-WL1-30K-SEN-BK	5W	500LM	3000K
SOLR-WL2-MCT-SEN	8W	1000LM	3000K/6000K
SOLR-PL1-30K	3W	300LM	3000K

GL-12V-BR

12V AC/DC LED GARDEN FLOOD LIGHT

CATALOG NO.	DESCRIPTION		
GL-12V-12W-30K-BR	12W	960LM	3000K
GL-12V-12W-40K-BR	12W	960LM	4000K
GL-12V-12W-50K-BR	12W	960LM	5000K
GL-12V-24W-30K-BR	24W	1920LM	3000K
GL-12V-24W-40K-BR	24W	1920LM	4000K
GL-12V-24W-50K-BR	24W	1920LM	5000K

FLV12-6W

FLV12-12W FLV12-24W

FLV12-32W

SHROUD

12V INTEGRATED LED LANDSCAPE FLOOD LIGHT

CATALOG NO.	DESCRIPTION		
FLV12-6W-30K	6W	500LM	3000K
FLV12-6W-50K	6W	550LM	5000K
FLV12-12W-30K	12W	1200LM	3000K
FLV12-12W-50K	12W	1300LM	5000K
FLV12-24W-30K	24W	2200LM	3000K
FLV12-24W-50K	24W	2500LM	5000K
FLV12-32W-30K	32W	3200LM	3000K
FLV12-32W-50K	32W	3500LM	5000K

PATH & AREA LIGHTS

LA-112-BZ-23IN

LA-115-BZ-23IN

LA-117-BZ-23IN

LA-116-BZ-23IN

LA-120-BZ-23IN

23" 12V LED AREA LIGHT SOLID BRASS

CATALOG NO.	DESCRIPTION		
LA-112-BZ	3W	200LM	3000K
LA-115-BZ	3W	200LM	3000K
LA-117-BZ	3W	200LM	3000K
LA-116-BZ	3W	200LM	3000K
LA-120-BZ	3W	200LM	3000K

LA-118-BZ-23IN

LA-111-BZ-23IN

LA-008-BZ-20IN

LA-010-BZ-23IN

LA-002-BZ-23.5IN

12V LED AREA LIGHT SOLID BRASS

CATALOG NO.	DESCRIPTION		
LA-118-BZ	3W	200LM	3000K
LA-111-BZ	3W	200LM	3000K
LA-008-BZ	3W	200LM	3000K
LA-010-BZ	3W	200LM	3000K
LA-002-BZ	3W	200LM	3000K

LA-112-BZ-12IN

LA-115-BZ-12IN

LA-117-BZ-12IN

LA-116-BZ-12IN

LA-118-BZ-12IN

LA-111-BZ-12IN

LA-111-CR-12IN

LA-117-CR-12IN

LA-116-CR-12IN

12" 12V LED AREA LIGHT SOLID BRASS

CATALOG NO.	DESCRIPTION		
LA-112-BZ-12IN	3W	200LM	3000K
LA-115-BZ-12IN	3W	200LM	3000K
LA-117-BZ-12IN	3W	200LM	3000K
LA-116-BZ-12IN	3W	200LM	3000K
LA-118-BZ-12IN	3W	200LM	3000K
LA-111-BZ-12IN	3W	200LM	3000K
LA-111-CR-12IN	3W	200LM	3000K
LA-116-CR-12IN	3W	200LM	3000K
LA-117-CR-12IN	3W	200LM	3000K

LA-112-AN-23IN

LA-117-AN-23IN

LA-116-AN-23IN

LA-111-AN-23IN

23" 12V AGED NICKEL COLLECTION CAST BRASS, AGED NICKEL FINISH

CATALOG NO.	DESCRIPTION		
LA-112-AN	3W	200LM	3000K
LA-117-AN	3W	200LM	3000K
LA-116-AN	3W	200LM	3000K
LA-111-AN	3W	200LM	3000K

LA-111-CR-23IN

LA-117-CR-23IN

LA-116-CR-23IN

23" 12V LED AREA LIGHT SOLID COPPER

CATALOG NO.	DESCRIPTION		
LA-111-CR	3W	200LM	3000K
LA-116-CR	3W	200LM	3000K
LA-117-CR	3W	200LM	3000K

LA-010-CR-20IN

LA-118-CR-18IN

LA-112-CR-12IN

12V LED AREA LIGHT SOLID COPPER

CATALOG NO.	DESCRIPTION		
LA-010-CR	3W	200LM	3000K
LA-112-CR	3W	200LM	3000K
LA-118-CR	3W	200LM	3000K

WET LOCATIONS

HUT Model LAL-12V-117

HAMMERHEAD Model LAL-12V-118

OPERA Model LAL-12V-120

AFAR Model Adjustable LAL-12V-122

EUCLID Model LAL-12V-124-15

EUCLID Model LAL-12V-124-31

LEAN Model LAL-12V-127

SURVEIL Model LAL-12V-128

BELL Model LAL-12V-130

12V LED AREA LIGHT - GROUND OR SURFACE MOUNT POWDER-COATED BRONZE OR BLACK

CUSTOM DESIGN ALUMINUM SPIKE & SURFACE MOUNTING BASE INCLUDED

CATALOG NO.	DESCRIPTION		
LAL-12V-117-31-30K-BR	10W	720LM	3000K
LAL-12V-117-31-30K-BK	10W	720LM	3000K
LAL-12V-118-31-30K-BR	10W	720LM	3000K
LAL-12V-118-31-30K-BK	10W	720LM	3000K
LAL-12V-120-23-30K-BR	10W	720LM	3000K
LAL-12V-120-23-30K-BK	10W	720LM	3000K
LAL-12V-122-31-30K-BR	10W	720LM	3000K
LAL-12V-122-31-30K-BK	10W	720LM	3000K
LAL-12V-124-15-30K-BR	10W	720LM	3000K
LAL-12V-124-15-30K-BK	10W	720LM	3000K
LAL-12V-124-31-30K-BR	10W	720LM	3000K
LAL-12V-124-31-30K-BK	10W	720LM	3000K
LAL-12V-127-23-30K-BR	10W	720LM	3000K
LAL-12V-127-23-30K-BK	10W	720LM	3000K
LAL-12V-128-31-30K-BR	10W	720LM	3000K
LAL-12V-128-31-30K-BK	10W	720LM	3000K
LAL-12V-130-31-30K-BR	10W	720LM	3000K
LAL-12V-130-31-30K-BK	10W	720LM	3000K

LAL-145-MCT5-ORB

LAL-145-MCT5-BK

LAL-136-MCT-ORB
LAL-136-RGBWW-BT-ORB

LAL-136-MCT-BK
LAL-136-RGBWW-BT-BK

LAL-131-30K-ORB

LAL-131-30K-BK

LAL-126-SIL-23IN

23" 12V LED PATH LIGHT POWDER-COATED BRONZE OR BLACK OR SILVER

CATALOG NO.	DESCRIPTION		
LAL-145-MCT5-ORB	3W	200LM	27K/30K/35K/40K/50K
LAL-145-MCT5-BK	3W	200LM	27K/30K/35K/40K/50K
LAL-136-MCT-ORB	5W	300LM	30K/40K/50K
LAL-136-MCT-BK	5W	300LM	30K/40K/50K
LAL-136-RGBWW-BT-ORB	5W	200LM	RGBW
LAL-136-RGBWW-BT-BK	5W	200LM	RGBW
LAL-136-RGBWW-PB-ORB	5W	200LM	RGBWW
LAL-131-30K-ORB	5W	200LM	3000K
LAL-131-30K-BK	5W	200LM	3000K
LAL-126-SIL	3W	200LM	3000K

AA-146-BK-13IN AA-146-BR-13IN

12V LED PAGODA LIGHT BLACK OR BRONZE

CATALOG NO.	DESCRIPTION		
AA-146-BK	3W	200LM	3000K
AA-146-BR	3W	200LM	3000K

AA SERIES NEW GENERATION OF PATH LIGHT

AA-18L-ORB
AA-STEM-22-MCT-ORB
AA-STEM-15-MCT-ORB
AA-STEM-22-RGBW-PB-ORB
AA-STEM-15-RGBW-PB-ORB
AA-STEM-22-RGBWW-BT-ORB
AA-STEM-15-RGBWW-BT-OR

AA-18L-BK
AA-STEM-22-MCT-BK
AA-STEM-15-MCT-BK
AA-STEM-22-RGBW-PB-BK
AA-STEM-15-RGBW-PB-BK
AA-STEM-22-RGBWW-BT-BK
AA-STEM-15-RGBWW-BT-BK

AA-18L-AZ
AA-STEM-22-MCT-AZ
AA-STEM-15-MCT-AZ
AA-STEM-22-RGBW-PB-AZ
AA-STEM-15-RGBW-PB-AZ
AA-STEM-22-RGBWW-BT-AZ
AA-STEM-15-RGBWW-BT-AZ

AA-19L-ORB
AA-STEM-22-MCT-ORB
AA-STEM-15-MCT-ORB
AA-STEM-22-RGBW-PB-ORB
AA-STEM-15-RGBW-PB-ORB
AA-STEM-22-RGBWW-BT-ORB
AA-STEM-15-RGBWW-BT-ORB

AA-19L-BK
AA-STEM-22-MCT-BK
AA-STEM-15-MCT-BK
AA-STEM-22-RGBW-PB-BK
AA-STEM-15-RGBW-PB-BK
AA-STEM-22-RGBWW-BT-BK
AA-STEM-15-RGBWW-BT-BK

AA-19L-AZ
AA-STEM-22-MCT-AZ
AA-STEM-15-MCT-AZ
AA-STEM-22-RGBW-PB-AZ
AA-STEM-15-RGBW-PB-AZ
AA-STEM-22-RGBWW-BT-AZ
AA-STEM-15-RGBWW-BT-AZ

AA-20L-ORB
AA-STEM-22-MCT-ORB
AA-STEM-15-MCT-ORB
AA-STEM-22-RGBW-PB-ORB
AA-STEM-15-RGBW-PB-ORB
AA-STEM-22-RGBWW-BT-ORB
AA-STEM-15-RGBWW-BT-ORB

AA-20L-BK
AA-STEM-22-MCT-BK
AA-STEM-15-MCT-BK
AA-STEM-22-RGBW-PB-BK
AA-STEM-15-RGBW-PB-BK
AA-STEM-22-RGBWW-BT-BK
AA-STEM-15-RGBWW-BT-BK

AA-20L-AZ
AA-STEM-22-MCT-AZ
AA-STEM-15-MCT-AZ
AA-STEM-22-RGBW-PB-AZ
AA-STEM-15-RGBW-PB-AZ
AA-STEM-22-RGBWW-BT-AZ
AA-STEM-15-RGBWW-BT-AZ

AA-21L-ORB
AA-STEM-22-MCT-ORB
AA-STEM-15-MCT-ORB
AA-STEM-22-RGBW-PB-ORB
AA-STEM-15-RGBW-PB-ORB
AA-STEM-22-RGBWW-BT-ORB
AA-STEM-15-RGBWW-BT-ORB

AA-21L-BK
AA-STEM-22-MCT-BK
AA-STEM-15-MCT-BK
AA-STEM-22-RGBW-PB-BK
AA-STEM-15-RGBW-PB-BK
AA-STEM-22-RGBWW-BT-BK
AA-STEM-15-RGBWW-BT-BK

AA-21L-AZ
AA-STEM-22-MCT-AZ
AA-STEM-15-MCT-AZ
AA-STEM-22-RGBW-PB-AZ
AA-STEM-15-RGBW-PB-AZ
AA-STEM-22-RGBWW-BT-AZ
AA-STEM-15-RGBWW-BT-AZ

AA-22L-ORB
AA-STEM-22-MCT-ORB
AA-STEM-15-MCT-ORB
AA-STEM-22-RGBW-PB-ORB
AA-STEM-15-RGBW-PB-ORB
AA-STEM-22-RGBWW-BT-ORB
AA-STEM-15-RGBWW-BT-ORB

AA-22L-BK
AA-STEM-22-MCT-BK
AA-STEM-15-MCT-BK
AA-STEM-22-RGBW-PB-BK
AA-STEM-15-RGBW-PB-BK
AA-STEM-22-RGBWW-BT-BK
AA-STEM-15-RGBWW-BT-BK

AA-22L-AZ
AA-STEM-22-MCT-AZ
AA-STEM-15-MCT-AZ
AA-STEM-22-RGBW-PB-AZ
AA-STEM-15-RGBW-PB-AZ
AA-STEM-22-RGBWW-BT-AZ
AA-STEM-15-RGBWW-BT-AZ

AA-23L-ORB
AA-STEM-22-MCT-ORB
AA-STEM-15-MCT-ORB
AA-STEM-22-RGBW-PB-ORB
AA-STEM-15-RGBW-PB-ORB
AA-STEM-22-RGBWW-BT-ORB
AA-STEM-15-RGBWW-BT-ORB

AA-23L-BK
AA-STEM-22-MCT-BK
AA-STEM-15-MCT-BK
AA-STEM-22-RGBW-PB-BK
AA-STEM-15-RGBW-PB-BK
AA-STEM-22-RGBWW-BT-BK
AA-STEM-15-RGBWW-BT-BK

AA-23L-AZ
AA-STEM-22-MCT-AZ
AA-STEM-15-MCT-AZ
AA-STEM-22-RGBW-PB-AZ
AA-STEM-15-RGBW-PB-AZ
AA-STEM-22-RGBWW-BT-AZ
AA-STEM-15-RGBWW-BT-AZ

AA-24L-ORB
AA-STEM-22-MCT-ORB
AA-STEM-15-MCT-ORB
AA-STEM-22-RGBW-PB-ORB
AA-STEM-15-RGBW-PB-ORB
AA-STEM-22-RGBWW-BT-ORB
AA-STEM-15-RGBWW-BT-ORB

AA-24L-BK
AA-STEM-22-MCT-BK
AA-STEM-15-MCT-BK
AA-STEM-22-RGBW-PB-BK
AA-STEM-15-RGBW-PB-BK
AA-STEM-22-RGBWW-BT-BK
AA-STEM-15-RGBWW-BT-BK

AA-24L-AZ
AA-STEM-22-MCT-AZ
AA-STEM-15-MCT-AZ
AA-STEM-22-RGBW-PB-AZ
AA-STEM-15-RGBW-PB-AZ
AA-STEM-22-RGBWW-BT-AZ
AA-STEM-15-RGBWW-BT-AZ

AA-46L-ORB
AA-STEM-22-MCT-ORB
AA-STEM-15-MCT-ORB
AA-STEM-22-RGBW-PB-ORB
AA-STEM-15-RGBW-PB-ORB
AA-STEM-22-RGBWW-BT-ORB
AA-STEM-15-RGBWW-BT-ORB

AA-46L-BK
AA-STEM-22-MCT-BK
AA-STEM-15-MCT-BK
AA-STEM-22-RGBW-PB-BK
AA-STEM-15-RGBW-PB-BK
AA-STEM-22-RGBWW-BT-BK
AA-STEM-15-RGBWW-BT-BK

TC-RGBW-RC

LED PATH LIGHT

CATALOG NO.	DESCRIPTION		
3CCT LED PATH LIGHTS			
AA-STEM-22-MCT-ORB	5W	200LM	30K/40K/50K
AA-STEM-22-MCT-BK	5W	200LM	30K/40K/50K
AA-STEM-22-MCT-AZ	5W	200LM	30K/40K/50K
AA-STEM-15-MCT-ORB	5W	200LM	30K/40K/50K
AA-STEM-15-MCT-BK	5W	200LM	30K/40K/50K
AA-STEM-15-MCT-AZ	5W	200LM	30K/40K/50K
PUSH BUTTON RGBW LED PATH LIGHTS			
AA-STEM-22-RGBW-PB-ORB	5W	200LM	RGBW
AA-STEM-22-RGBW-PB-BK	5W	200LM	RGBW
AA-STEM-22-RGBW-PB-AZ	5W	200LM	RGBW
AA-STEM-15-RGBW-PB-ORB	5W	200LM	RGBW
AA-STEM-15-RGBW-PB-BK	5W	200LM	RGBW
AA-STEM-15-RGBW-PB-AZ	5W	200LM	RGBW
RGBWW BLUETOOTH WG APP LED PATH LIGHTS			
AA-STEM-22-RGBWW-BT-ORB	5W	200LM	RGBW
AA-STEM-22-RGBWW-BT-BK	5W	200LM	RGBW
AA-STEM-22-RGBWW-BT-AZ	5W	200LM	RGBW
AA-STEM-15-RGBWW-BT-ORB	5W	200LM	RGBW
AA-STEM-15-RGBWW-BT-BK	5W	200LM	RGBW
AA-STEM-15-RGBWW-BT-AZ	5W	200LM	RGBW

ALUMINUM PATH LIGHT CAP

CATALOG NO.	DESCRIPTION
AA-18L-ORB	Model 18 Aluminum Path Light Cap, Oil-Rubbed Bronze
AA-18L-BK	Model 18 Aluminum Path Light Cap, Black
AA-18L-AZ	Model 18 Aluminum Path Light Cap, Antique Brass
AA-19L-ORB	Model 19 Aluminum Path Light Cap, Oil-Rubbed Bronze
AA-19L-BK	Model 19 Aluminum Path Light Cap, Black
AA-19L-AZ	Model 19 Aluminum Path Light Cap, Antique Brass
AA-20L-ORB	Model 20 Aluminum Path Light Cap, Oil-Rubbed Bronze
AA-20L-BK	Model 20 Aluminum Path Light Cap, Black
AA-20L-AZ	Model 20 Aluminum Path Light Cap, Antique Brass
AA-21L-ORB	Model 21 Aluminum Path Light Cap, Oil-Rubbed Bronze
AA-21L-BK	Model 21 Aluminum Path Light Cap, Black
AA-21L-AZ	Model 21 Aluminum Path Light Cap, Antique Brass
AA-22L-ORB	Model 22 Aluminum Path Light Cap, Oil-Rubbed Bronze
AA-22L-BK	Model 22 Aluminum Path Light Cap, Black
AA-22L-AZ	Model 22 Aluminum Path Light Cap, Antique Brass
AA-23L-ORB	Model 23 Aluminum Path Light Cap, Oil-Rubbed Bronze
AA-23L-BK	Model 23 Aluminum Path Light Cap, Black
AA-23L-AZ	Model 23 Aluminum Path Light Cap, Antique Brass
AA-24L-ORB	Model 24 Aluminum Path Light Cap, Oil-Rubbed Bronze
AA-24L-BK	Model 24 Aluminum Path Light Cap, Black
AA-24L-AZ	Model 24 Aluminum Path Light Cap, Antique Brass
AA-46L-MCT5-ORB	Model 46 Aluminum Path Light Cap, Oil-Rubbed Bronze
AA-46L-MCT5-BK	Model 46 Aluminum Path Light Cap, Black

NEW GENERATION OF INTEGRATED LED PATH LIGHTS, ALUM. ALLOY
SELECTABLE COLOR TEMPERATURE OR PUSH-BUTTON RGBWW WITH SCENES, APP-CONTROLLED RGBWW
IN 3 FINISHES, SIMULATED DARK BRASS, BLACK, METALLIC OIL-RUBBED BRONZE
2 DIFFERENT HEIGHTS: 15" OR 22"
STEMS AND CAPS SOLD SEPARATELY

WMC1-12V-DL

WMC2-12V-DL

WMC1-12V-UDL

WMC2-12V-UDL

12V LED WALL CYLINDER

CATALOG NO.	DESCRIPTION		
12V 1.6" LED WALL CYLINDERS 25°			
WMC1-12V-DL-MCT-ORB	3W	300LM	30K/40K/50K
WMC1-12V-DL-MCT-BN	3W	300LM	30K/40K/50K
WMC1-12V-DL-MCT-BK	3W	300LM	30K/40K/50K
WMC1-12V-UDL-MCT-ORB	2X3W	600LM	30K/40K/50K
WMC1-12V-UDL-MCT-BN	2X3W	600LM	30K/40K/50K
WMC1-12V-UDL-MCT-BK	2X3W	600LM	30K/40K/50K
12V 2" LED WALL CYLINDERS 25°			
WMC2-12V-DL-MCT-ORB	5W	500LM	30K/40K/50K
WMC2-12V-DL-MCT-BN	5W	500LM	30K/40K/50K
WMC2-12V-DL-MCT-BK	5W	500LM	30K/40K/50K
WMC2-12V-UDL-MCT-ORB	10W	1000LM	30K/40K/50K
WMC2-12V-UDL-MCT-BN	10W	1000LM	30K/40K/50K
WMC2-12V-UDL-MCT-BK	10W	1000LM	30K/40K/50K

WET LOCATIONS

LVW-100-MCT-ORB
5.25IN D x 2.66IN H

LVW-110-MCT-ORB
3.12IN W x 3.40IN H x 3.71IN D

LVW-110-UD-MCT-ORB
3.71IN W x 4.12IN H x 5.20IN D

LVW-115-MCT-ORB
5.25IN D x 3.75IN H

LVW-200-MCT-ORB
5.20IN SQ x 2.66IN H

LVW-210-MCT-ORB
3.75IN W x 4.12IN H x 3.41IN D

LVW-210-UD-MCT-ORB
3.75IN W x 4.12IN H x 5.20IN D

LVW-215-MCT-ORB
5.25IN SQ x 4.33IN H

LVW-250-MCT-ORB
5.75IN W x 5.75IN H x 2.25IN D

LVW-300-MCT-ORB
LVW-300-MCT-WH
7IN W x 5IN H x 2.25IN D

LVW-310-MCT-ORB
LVW-310-MCT-WH
7.50IN W x 4.20IN H x 2IN D

12V SELECTABLE CCT LED MINI WALL SCONCE

CATALOG NO.	DESCRIPTION		
LVW-100-MCT-ORB	3W	200LM	30K/40K/50K
LVW-110-MCT-ORB	3W	200LM	30K/40K/50K
LVW-110-UD-MCT-ORB	6W	400LM	30K/40K/50K
LVW-115-MCT-ORB	3W	200LM	30K/40K/50K
LVW-200-MCT-ORB	3W	200LM	30K/40K/50K
LVW-210-MCT-ORB	3W	200LM	30K/40K/50K
LVW-210-UD-MCT-ORB	6W	400LM	30K/40K/50K
LVW-215-MCT-ORB	3W	200LM	30K/40K/50K
LVW-250-MCT-ORB	6W	400LM	30K/40K/50K
LVW-300-MCT-ORB	6W	400LM	30K/40K/50K
LVW-300-MCT-WH	6W	400LM	30K/40K/50K
LVW-310-MCT-ORB	6W	400LM	30K/40K/50K
LVW-310-MCT-WH	6W	400LM	30K/40K/50K

AS-158-BR-4IN

4” STEP LIGHT WITH LED LAMP ALUMINUM

CATALOG NO.	DESCRIPTION		
AS-158-BR	3W	200LM	3000K
AS-158-BK	3W	200LM	3000K
AS-158-MCT-ORB	2.5W	80LM	30K/40K/50K

LS-185-BZ-3IN

LS-158-BZ-4IN

LS-159-BZ-4IN

LS-175-ORB-LEDI

STEP LIGHT WITH LED LAMP

CATALOG NO.	DESCRIPTION		
LS-185-BZ	3W	200LM	3000K
LS-158-BZ	3W	200LM	3000K
LS-158-SS	3W	200LM	3000K
LS-159-BZ	3W	200LM	3000K
LS-175-ORB-LEDI	3W	200LM	27K/30K/35K/40K/50K

LS-124-BZ

LS-161-BZ

LS-155-BZ

LS-160-BZ LS-160-AN

LED STEP LIGHT WITH INTEGRATED SMD LED MODULE

CATALOG NO.	DESCRIPTION		
LS-124-AN	3W	200LM	3000K
LS-161-BZ	3W	200LM	3000K
LS-160-BZ	3W	200LM	3000K
LS-160-AN	3W	200LM	3000K
LS-155-BZ	3W	200LM	3000K

SLSM-LH-MCT5-ORB Surface Mount NO HOUSING

SLSM-LH-MCT5-WH Surface Mount NO HOUSING

LS-172-BZ-LEDI Surface Mount NO HOUSING

SURFACE-MOUNT HORIZONTAL LOUVER STEP LIGHT

CATALOG NO.	DESCRIPTION		
SLSM-LH-MCT5-ORB	4W	30LM	27K/30K/35K/40K/50K
SLSM-LH-MCT5-WH	4W	30LM	27K/30K/35K/40K/50K
LS-172-BZ-LEDI	3W	200LM	3000K

SLM-R1-BK

SLM-R1-WH

SLM-S1-BK

SLM-S1-WH

MINI STEP LIGHT 12V

CATALOG NO.	DESCRIPTION		
SLM-R1-12V-30K-BK	2W	160LM	3000K
SLM-R1-12V-30K-WH	2W	160LM	3000K
SLM-S1-12V-30K-BK	2W	160LM	3000K
SLM-S1-12V-30K-WH	2W	160LM	3000K

HSL-7-MCT HSL-7-RGBCW



HSL-12-MCT HSL-12-RGBCW

LED HARDSCAPE LIGHT WITH FRONT TRIM 8FT CABLE BRONZE

CATALOG NO.	DESCRIPTION		
HSL-7-MCT	5W	200LM	30K/40K/50K
HSL-12-MCT	7W	280LM	30K/40K/50K
HSL-7-RGBCW	5W	200LM	RGBCW
HSL-12-RGBCW	7W	280LM	RGBCW

SLE-A-120V-MCT-WH
SLE-A-12V-MCT-WH

SLE-A-120V-MCT-ORB
SLE-A-12V-MCT-ORB
SLE-A-120V-RGBWW-PB-ORB

SLE-A-120V-MCT-BN
SLE-A-12V-MCT-BN

SLE-A-120V-MCT-PIR-WH
SLE-A-12V-MCT-PIR-WH

SLE-A-120V-MCT-PIR-ORB
SLE-A-12V-MCT-PIR-ORB

SLE-F-120V-MCT-WH
SLE-F-12V-MCT-WH

SLE-F-120V-MCT-ORB
SLE-F-12V-MCT-ORB

SLE-F-120V-MCT-BN
SLE-F-12V-MCT-BN

SLE-LH-120V-MCT-WH
SLE-LH-12V-MCT-WH

SLE-LH-120V-MCT-ORB
SLE-LH-12V-MCT-ORB

SLE-LH-120V-MCT-BN
SLE-LH-12V-MCT-BN

SLE-EL-120V-MCT5-WH
SLE-EL-12V-MCT5-WH

SLE-EL-120V-MCT5-ORB
SLE-EL-12V-MCT5-ORB

SELECTABLE CCT LED INTEGRATED STEP LIGHT

CATALOG NO.	DESCRIPTION		
MODEL A - 120V SELECTABLE CCT LED INTEGRATED STEP LIGHTS			
SLE-A-120V-MCT-WH	3.5W	100LM	30K/40K/50K
SLE-A-120V-MCT-ORB	3.5W	50LM	30K/40K/50K
SLE-A-120V-RGBWW-PB-ORB	3.5W	50LM	RGBWW
SLE-A-120V-MCT-BN	3.5W	50LM	30K/40K/50K
MODEL A - 120V SELECTABLE CCT LED INTEGRATED STEP LIGHTS WITH PIR MOTION SENSOR & PHOTOCELL			
SLE-A-120V-MCT-PIR-WH	3W	150LM	30K/40K/50K
SLE-A-120V-MCT-PIR-ORB	3W	75LM	30K/40K/50K
MODEL LH - 120V SELECTABLE CCT LED INTEGRATED STEP LIGHTS			
SLE-LH-120V-MCT-WH	5W	150LM	30K/40K/50K
SLE-LH-120V-MCT-ORB	5W	75LM	30K/40K/50K
SLE-LH-120V-MCT-BN	5W	75LM	30K/40K/50K
MODEL F - 120V SELECTABLE CCT LED INTEGRATED STEP LIGHTS			
SLE-F-120V-MCT-WH	3.5W	200LM	30K/40K/50K
SLE-F-120V-MCT-ORB	3.5W	100LM	30K/40K/50K
SLE-F-120V-MCT-BN	3.5W	75LM	30K/40K/50K
MODEL EL - 120V SELECTABLE CCT LED INTEGRATED STEP LIGHTS			
SLE-EL-120V-MCT5-WH	3W	90LM	27K/30K/35K/40K/50K
SLE-EL-120V-MCT5-ORB	3W	50LM	27K/30K/35K/40K/50K
MODEL A - 12V SELECTABLE CCT LED INTEGRATED STEP LIGHTS			
SLE-A-12V-MCT-WH	3.5W	100LM	30K/40K/50K
SLE-A-12V-MCT-ORB	3.5W	50LM	30K/40K/50K
SLE-A-12V-RGBWW-PB-ORB	3.5W	50LM	RGBWW
SLE-A-12V-MCT-BN	3.5W	50LM	30K/40K/50K
MODEL A - 12V SELECTABLE CCT LED INTEGRATED STEP LIGHTS WITH PIR MOTION SENSOR & PHOTOCELL			
SLE-A-12V-MCT-PIR-WH	3W	150LM	30K/40K/50K
SLE-A-12V-MCT-PIR-ORB	3W	75LM	30K/40K/50K
MODEL LH - 12V SELECTABLE CCT LED INTEGRATED STEP LIGHTS			
SLE-LH-12V-MCT-WH	5W	150LM	30K/40K/50K
SLE-LH-12V-MCT-ORB	5W	75LM	30K/40K/50K
SLE-LH-12V-MCT-BN	5W	75LM	30K/40K/50K
MODEL F - 12V SELECTABLE CCT LED INTEGRATED STEP LIGHTS			
SLE-F-12V-MCT-WH	3.5W	200LM	30K/40K/50K
SLE-F-12V-MCT-ORB	3.5W	100LM	30K/40K/50K
SLE-F-12V-MCT-BN	3.5W	75LM	30K/40K/50K
MODEL EL - 12V SELECTABLE CCT LED INTEGRATED STEP LIGHTS			
SLE-EL-12V-MCT5-WH	3W	90LM	27K/30K/35K/40K/50K
SLE-EL-12V-MCT5-ORB	3W	50LM	27K/30K/35K/40K/50K



Fits in Single Gang Switch Boxes (NOT INCLUDED)



SLEA

12V/120V STEP LIGHT ENGINE POLYCARBONATE

CATALOG NO.	DESCRIPTION		
SLEA-12V-27K	2W	86LM	2700K
SLEA-12V-30K	2W	86LM	3000K
SLEA-12V-40K	2W	86LM	4000K
SLEA-12V-50K	2W	86LM	5000K
SLEA-120V-27K	2W	86LM	2700K
SLEA-120V-30K	2W	86LM	3000K
SLEA-120V-40K	2W	86LM	4000K
SLEA-120V-50K	2W	86LM	5000K

SLT-A-WH

SLT-A-BN

SLT-A-AZ

SLT-A-ORB

FACE PLATE FOR SLEA PRECISION-CAST ALUMINUM, ORDER SEPARATELY

CATALOG NO.	DESCRIPTION
SLT-A-WH	Trim For Step Egn, Recessed, White
SLT-A-BN	Trim For Step Egn, Recessed, Brushed Nickel
SLT-A-AZ	Trim For Step Egn, Recessed, Antique Bronze
SLT-A-ORB	Trim For Step Egn, Recessed, Oil-Rubbed Bronze

SLEB

12V/120V STEP LIGHT ENGINE POLYCARBONATE

CATALOG NO.	DESCRIPTION		
SLEB-12V-27K	2W	86LM	2700K
SLEB-12V-30K	2W	86LM	3000K
SLEB-12V-40K	2W	86LM	4000K
SLEB-12V-50K	2W	86LM	5000K
SLEB-120V-27K	2W	86LM	2700K
SLEB-120V-30K	2W	86LM	3000K
SLEB-120V-40K	2W	86LM	4000K
SLEB-120V-50K	2W	86LM	5000K

SLT-B-WH

SLT-B-BN

SLT-B-AZ

SLT-B-ORB

FACE PLATE FOR SLEB PRECISION-CAST ALUMINUM, ORDER SEPARATELY

CATALOG NO.	DESCRIPTION
SLT-B-WH	Vertical Recessed Trim, White
SLT-B-BN	Vertical Recessed Trim , Brushed Nickel
SLT-B-AZ	Vertical Recessed Trim, Antique Bronze Finished
SLT-B-ORB	Vertical Recessed Trim , Oil-Rubbed Bronze

SLE

12V/120V STEP LIGHT ENGINE POLYCARBONATE

CATALOG NO.	DESCRIPTION		
SLE-12V-27K	2W	100LM	2700K
SLE-12V-30K	2W	100LM	3000K
SLE-12V-40K	2W	100LM	4000K
SLE-12V-50K	2W	118LM	5000K
SLE-120V-27K	2W	90LM	2700K
SLE-120V-30K	2W	90LM	3000K
SLE-120V-40K	2W	90LM	4000K
SLE-120V-50K	2W	104LM	5000K

Clear PVC Gasket Set Included with Light Engine for J-Box or Weatherproof Box Mounting

CLEAR PVC GASKET SET INCLUDED WITH LIGHT ENGINE FOR J-BOX OR WEATHERPROOF BOX MOUNTING



SLT-LH-ORB



SLT-LH-BN

SLT-LH-WH

SLT-LH-AZ

SLT-F-ORB



SLT-F-BN

SLT-F-WH

SLT-F-AZ

SLT-S-ORB

SLT-S-BN

SLT-S-WH

SLT-S-AZ

SLT-LV-ORB

SLT-LV-BN

SLT-LV-WH

SLT-LV-AZ

FACE PLATE FOR SLE PRECISION-CAST ALUMINUM, ORDER SEPARATELY

CATALOG NO.	DESCRIPTION
SLT-LH-ORB	Trim For Step Egn, Louver Horizontal Slots, Oil-Rubbed Bronze
SLT-LH-BN	Trim For Step Egn, Louver Horizontal Slots, Brush Nickle
SLT-LH-WH	Trim For Step Egn, Louver Horizontal Slots, White
SLT-LH-AZ	Trim For Step Egn, Flat, White
SLT-F-ORB	Trim For Step Egn, Flat, Oil-Rubbed Bronze
SLT-F-BN	Trim For Step Egn, Flat, Brush Nickle
SLT-F-WH	Trim For Step Egn, Flat, White
SLT-F-AZ	Trim For Step Egn, Flat, Antique Bronze
SLT-S-ORB	Trim For Step Egn, Scoop, Oil-Rubbed Bronze
SLT-S-BN	Trim For Step Egn, Scoop, Brush Nickle
SLT-S-WH	Trim For Step Egn, Scoop, White
SLT-S-AZ	Trim For Step Egn, Scoop, Antique Bronze
SLT-LV-ORB	Trim For Step Egn, Louver Vertical Slots, Oil-Rubbed Bronze
SLT-LV-BN	Trim For Step Egn, Louver Vertical Slots, Brush Nickle
SLT-LV-WH	Trim For Step Egn, Louver Vertical Slots, White
SLT-LV-AZ	Trim For Step Egn, Louver Vertical Slots, Antique Bronze

UW-125-SS

UW-125-BS

UW-126-BZ

LED UNDERWATER LIGHT 30FT CABLE, INCL. 5W 30K MR16

CATALOG NO.	DESCRIPTION		
UW-125-SS	5W	400LM	3000K
UW-125-BS	5W	400LM	3000K
UW-126-BZ	5W	400LM	3000K

WL-140-FBK FIBER GLASS For PAR36 No Lamp

LD-001-BZ CAST BRASS For PAR36 No Lamp

PAR36 LAMP NOT INCLUDED

CATALOG NO.	DESCRIPTION
WL-140-FBK	Fiber Glass, Black
LD-001-BZ	Die-cast Brass, Antique Bronze Finish

IGLA-3W-30K-BN

IGLA-7W-30K-BN

12V ALUMINUM INTEGRATED LED INGROUND LIGHT PVC SLEEVES, BRUSHED NICKEL FINISH

CATALOG NO.	DESCRIPTION		
IGLA-3W-30K-BN	3W	320LM	3000K
IGLA-7W-30K-BN	7W	720LM	3000K

IGL-1W

IGL-3W

IGL-7W

IGL-1W-TWLN

RGBW-WIFI-CONTROLLER

12V INTEGRATED LED (IN GROUND) LIGHT

CATALOG NO.	DESCRIPTION		
IGL-1W-30K	1W	100LM	3000K
IGL-1W-40K	1W	100LM	4000K
IGL-1W-TWLN	1W in ground light lock nut for thin wall		
IGL-3W-30K	3W	290LM	3000K
IGL-3W-40K	3W	290LM	4000K
IGL-3W-RGBW	3W	290LM	RGB+3000K
IGL-7W-30K	7W	620LM	3000K
IGL-7W-40K	7W	620LM	4000K
IGL-10W-RGBW	10W	620LM	RGB+3000K
RGBW-WIFI-CONTROLLER	RGBW lighting controller with integrated WI-FI and app, RC incl.		

IGL-1W-TRM-AL-RBK

IGL-1W-TRM-AL-RWH

IGL-1W-TRM-AL-RAZ

IGL-1W-TRM-AL-RBN

IGL-1W-TRM-AL-RLBN

IGL-1W-TRM-AL-SCP

IGL-1W-TRM-AL-SCP-AZ

IGL-1W-TRM-SS-1WY

IGL-1W-TRM-SS-2WY

IGL-1W-TRM-SS-SQR

IGL-1W-TRM-SS-SQSQ

OPTIONAL TRIM FOR 1W IN-GROUND FIXTURE

CATALOG NO.	DESCRIPTION
IGL-1W-TRM-AL-RBK	1.8" DIAMETER
IGL-1W-TRM-AL-RWH	1.8" DIAMETER
IGL-1W-TRM-AL-RBN	1.8" DIAMETER
IGL-1W-TRM-AL-RLBN	2.75" DIAMETER
IGL-1W-TRM-AL-SCP	1.8" DIAMETER
IGL-1W-TRM-SS-1WY	1.8" DIAMETER
IGL-1W-TRM-SS-2WY	1.8" DIAMETER
IGL-1W-TRM-SS-SQR	1.8" DIAMETER
IGL-1W-TRM-SS-SQSQ	1.8" DIAMETER
IGL-1W-TRM-AL-RAZ	1.8" DIAMETER
IGL-1W-TRM-AL-SCP-AZ	1.8" DIAMETER

IGL-3W-TRM-SS-R

IGL-3W-TRM-AL-RBN

IGL-3W-TRM-AL-AZ

IGL-3W-TRM-SS-SCP

IGL-3W-TRM-SS-SCP-AZ

IGL-3W-TRM-SS-1WY

IGL-3W-TRM-SS-2WY

IGL-3W-TRM-SS-SQR

IGL-3W-TRM-SS-SQSQ

OPTIONAL TRIM FOR 3W IN-GROUND FIXTURE

CATALOG NO.	DESCRIPTION
IGL-3W-TRM-SS-1WY	
IGL-3W-TRM-SS-2WY	
IGL-3W-TRM-SS-SQR	
IGL-3W-TRM-SS-SQSQ	
IGL-3W-TRM-SS-R	
IGL-3W-TRM-AL-RBN	
IGL-3W-TRM-SS-SCP	
IGL-3W-TRM-SS-SCP-AZ	
IGL-3W-TRM-AL-AZ	

WL-105-1-BK

WL-181-BR WL-181-BK

WL-181-BZ

WL-157-FGBZ

WHILE SUPPLIES LAST

12V WELL LIGHT WITH SLEEVE & LED LAMP INCL. 5W 30K

CATALOG NO.	DESCRIPTION		
WL-105-1-BK	5W	400LM	3000K
WL-181-BK	5W	400LM	3000K
WL-181-BZ	5W	400LM	3000K
WL-181-BR	5W	400LM	3000K
WL-157-FGBZ	5W	400LM	3000K

WL-701-FGBZ

WL-705-FGBZ

WL-707-FGBZ

WL-708-FGBZ

12V SOLID BRASS WELL LIGHT WITH DIRECTIONAL LAMP BRACKET INCL. 5W 30K 400LM

CATALOG NO.	DESCRIPTION		
WL-701-FGBZ	5W	400LM	3000K
WL-705-FGBZ	5W	400LM	3000K
WL-707-FGBZ	5W	400LM	3000K
WL-708-FGBZ	5W	400LM	3000K

WLL-105-30K-BK
WLL-105-RGBWW-BT-ORB

WLL-106-30K-BK

WLL-152-30K-BK
WLL-152-30K-ORB

WLL-157-30K-BK
WLL-157-RGBWW-BT-ORB

WLL-159-30K-BK

WLL-181-30K-BK
WLL-181-RGBWW-BT-ORB

INTEGRATED ALUMINUM LED WELL/PATH LIGHT PVC SLEEVE, 4INCH DIAMETER

CATALOG NO.	DESCRIPTION		
WLL-105-30K-BK	6W	580LM	3000K
WLL-105-RGBWW-BT-ORB	6W	580LM	RGBW
WLL-106-30K-BK	6W	500LM	3000K
WLL-152-30K-BK	6W	200LM	3000K
WLL-152-30K-ORB	6W	200LM	3000K
WLL-157-30K-BK	6W	500LM	3000K
WLL-157-RGBWW-BT-ORB	6W	180LM	RGBW
WLL-159-30K-BK	6W	400LM	3000K
WLL-181-30K-BK	6W	580LM	3000K
WLL-181-RGBWW-BT-ORB	6W	420LM	RGBW

WL-137-BK

WL-137-BZ Solid Brass

WL-138-BK

WL-138-BZ Solid Brass

WL-138-SS

12V WELL LIGHT WITH SLEEVE & LED LAMP INCL. 5W 30K

CATALOG NO.	DESCRIPTION		
WL-137-BK	5W	400LM	3000K
WL-137-BZ	5W	400LM	3000K
WL-138-BK	5W	400LM	3000K
WL-138-BZ	5W	400LM	3000K
WL-138-SS	5W	400LM	3000K

TR-300W-MT-SS-WIFI

TR-ZC-WIFI

WIFI WG APP MULTI-TAP 12V/13V/14V/15V AC LANDSCAPE TRANSFORMER

CATALOG NO.	DESCRIPTION
TR-300W-MT-SS-WIFI	300W
TR-ZC-WIFI	Wifi Controller

TR-100W-2Z-TPC-SS

TR-100W-2Z-TPC-BK

12V AC MULTI-ZONE TRANSFORMER, PROGRAMMABLE, ON AT DUSK OFF AFTER 2/4/6/8HRS

CATALOG NO.	DESCRIPTION	
TR-100W-2Z-TPC-SS	100W	2-Zone
TR-200W-2Z-TPC-SS	200W	2-Zone
TR-300W-3Z-TPC-SS	300W	3-Zone
TR-100W-2Z-TPC-BK	100W	2-Zone
TR-200W-2Z-TPC-BK	200W	2-Zone
TR-300W-3Z-TPC-BK	300W	3-Zone

TR-40W-DT-TPC-SS TR-75W-DT-TPC-SS

TR-100W-DT-TPC-SS TR-200W-DT-TPC-SS

DUAL-TAP 12V/15V AC LANDSCAPE TRANSFORMER WITH TIMER & PHOTOCELL SLIDE DOOR

STAINLESS STEEL

CATALOG NO.	DESCRIPTION
TR-40W-DT-TPC-SS	40W
TR-75W-DT-TPC-SS	75W
TR-100W-DT-TPC-SS	100W
TR-200W-DT-TPC-SS	200W

TR-150W-MT-SS

TR-300W-MT-SS

TR-600W-MT-SS TR-900W-MT-SS

MULTI-TAP 12V/13V/14V/15V AC LANDSCAPE PROFESSIONAL SERIES, STAINLESS STEEL

TRANSFORMER MULTI-TAP, TIMER & PHOTOCELL READY (NOT INCLUDED) HINGE DOOR

CATALOG NO.	DESCRIPTION
TR-75W-MT-T-SS	75W
TR-150W-MT-SS	150W
TR-300W-MT-SS	300W
TR-600W-MT-SS	600W
TR-900W-MT-SS	900W

TR-MTMR

TR-DTMR

TR-PC

MULTI-TAP LANDSCAPE TRANSFORMER PLUG-IN OPTION

CATALOG NO.	DESCRIPTION
TR-MTMR	MECHANICAL TIMER
TR-DTMR	DIGITAL TIMER
TR-PC	PHOTOCELL

LVT-60

LVT-100

DRY LOCATION AC TRANSFORMER 12V

CATALOG NO.	DESCRIPTION
LVT-60	60W
LVT-100	100W

MR16-400L-D

MR16-500L-D

MR16-5W-RGB

MR16

CATALOG NO.	DESCRIPTION		
MR16-400L-27K-D	5W	380LM	2700K
MR16-400L-30K-D	5W	380LM	3000K
MR16-400L-41K-D	5W	390LM	4100K
MR16-400L-50K-D	5W	400LM	5000K
MR16-500L-C90-30K-D	7W	500LM	3000K
MR16-500L-C90-40K-D	7W	560LM	4000K
MR16-500L-C90-50K-D	7W	560LM	5000K

WE167-CAP



WE167-CAP-BZ

WE167 with brass hub

WE167-25 with brass hub

PVC POST WITH BRASS HUB

CATALOG NO.	DESCRIPTION
WE167	3" 18-1/2" PVC mounting post with brass hub
WE167-25	3" 25" PVC mounting post with brass hub
WE167-CAP	Cap only for WE167
WE167-CAP-BZ	Brass with bronze finish Cap only for WE167

TL-118-MCT

MODERN LED TREE LIGHT

CATALOG NO.	DESCRIPTION		
TL-118-MCT-ORB	4.5W	300LM	30K/40K/50K
TL-118-MCT-AZ	4.5W	300LM	30K/40K/50K



LSP-TREERING-24D-6L

A-41-S

A-GM-50

LG-SMB-BZ

A-STAB Shown With Fixture

TREE LIGHTING ACCESSORIES

CATALOG NO.	DESCRIPTION
LSP-TREERING-24D-6L	24in Palm Tree Lighting Ring For 6 Lights
A-41-S	Tree mounting base
A-GM-50	Gutter Surface Mounting Bracket With 1/2In Hub, Orb
A-STAB	Inground Stabilizer Plate With Male And Female 1/2" Hubs
LG-SMB-BZ	12V brass landscape tree or surface bracket, antique bronze finish

BC

BUNGEE CORD

CATALOG NO.	DESCRIPTION
BC-10	10" Bungee cords with hooks
BC-15	15" Bungee cords with hooks
BC-18	18" Bungee cords with hooks
BC-21	21" Bungee cords with hooks
BC-32	32" Bungee cords with hooks

LA-T-BZ

LA-90-BZ

LA-FMS21-BZ

Sample Installation with LD-006-BZ (NOT INCLUDED)



Sample Installation with LD-006-BZ (NOT INCLUDED)

PATH LIGHTING ACCESSORIES

CATALOG NO.	DESCRIPTION
LA-T-BZ	Fixture mounting "T" Attachment
LA-90-BZ	Fixture mounting 90° elbow Attachment
LA-FMS21-BZ	21" Solid brass fixture mounting stem Antique bronze finish

WET LOCATIONS

PAR36-IP65

PAR36-IP65

CATALOG NO.	DESCRIPTION		
PAR36-12W-30K	12W	1000LM	3000K
PAR36-12W-40K	12W	1000LM	4000K
PAR36-12W-50K	12W	1000LM	5000K

GZ-JC-39L

GZ-JC-18L-27K

GZ-JC-WP-3W-32K

GZ-S8-32K-G2

GZ-JC-60L-TFL

GZ-JC-300L-27K
GZ-JC-300L-30K

12V AC/DC REPLACEMENT LAMP

CATALOG NO.	DESCRIPTION		
GZ-JC-39L-27K	3W	250LM	2700K
GZ-JC-39L-30K	3W	250LM	3000K
GZ-JC-18L-27K	3W	250LM	2700K
GZ-JC-WP-3W-32K	3W	180LM	3200K
GZ-S8-32K-G2	2.2W	230LM	3200K
GZ-G4-9L-32K	2W	120LM	3200K
GZ-JC-60L-TFL	3W	60LM	TURTLE FRIENDLY CCT
GZ-JC-300L-27K	3W	300LM	2700K
GZ-JC-300L-30K	3W	300LM	3000K

B-41-AN

B-41

BRASS BASE

CATALOG NO.	DESCRIPTION
B-41	1/2" NPT hub,Solid Brass, Antique Bronze finish
B-41-AN	1/2" NPT hub,Solid Brass, Aged Nickel finish

A-41-BK

A-41-BR

A-51-BK

ALUMINUM BASE

CATALOG NO.	DESCRIPTION
A-41-BR	1/2" NPT hub,Cast aluminum, Bronze Powder coat finish
A-41-BK	1/2" NPT hub,Cast aluminum, Black Powder coat finish
A-51-BK	1/2In Modern Surface Mounting Base, Alum., Black
A-51-ORB	1/2In Modern Surface Mounting Base, Alum., Orb

LSWN1

LSWN2

LSWN2-100

SILICON-FILLED WIRE NUT

CATALOG NO.	DESCRIPTION
LSWN1	Bag of 24, Waterproof wire connectors, for up to two 14-2 + one 16-2 cables
LSWN2	Box of 24, Waterproof wire connectors, for up to three 12-2 cables
LSWN2-100	Jar of 100, Waterproof wire connectors, for up to three 12-2 cables

WL-SLEEVE

SPIKE-BG

SPIKE-10

SPIKE

CATALOG NO.	DESCRIPTION
WL-SLEEVE	PVC sleeve Kit for 4" well lights
SPIKE-BG	8.5" PVC spike
SPIKE-10	10" PVC spike

LA-STEM-REPL-LED

LA-STEM-RL

LA-STEM-KNOB

AREA LIGHTING REPLACEMENT PART

CATALOG NO.	DESCRIPTION
LA-STEM-RL	Replacement Glass Lens for Path Light stem
LA-STEM-KNOB	Replacement Knob
LA-STEM-REPL-LED	3000K Replacement LED Tower for path lights Also fits Pagoda Lights
LA-STEM-REPL-LED-27K	2700K Replacement LED Tower for path lights Also fits Pagoda Lights
LA-STEM-REPL-LED-40K	4000K Replacement LED Tower for path lights Also fits Pagoda Lights
LA-STEM-REPL-LED-50K	5000K Replacement LED Tower for path lights Also fits Pagoda Lights

AA-1-RG

PAGODA LIGHT REPLACEMENT GLASS

CATALOG NO.	DESCRIPTION
AA-145-RG	Replacement Glass for 2-Tier pagodas
AA-146-RG	Replacement Glass for 3-Tier pagodas
AA-147-RG	Replacement Glass for 4-Tier pagodas

WE-CONN

LSFLC-20

12V SNAP CONNECTOR

CATALOG NO.	DESCRIPTION
WE-CONN	black color
LSFLC-20	20 Fast-Lock In-Line Landscape Connectors

LOV ROLL

LOW-VOLTAGE CABLE MUST ORDER IN MULTIPLES OF 500FT

CATALOG NO.	DESCRIPTION
LOV-14	#14 AWG (41 Strands)
LOV-12	#12 AWG (65 Strands)
LOV-10	#10 AWG (104 Strands)
LOV-8	#8 AWG (168 Strands)

LOV ROLL

LOW-VOLTAGE CABLE MUST ORDER IN MULTIPLES OF 100FT

CATALOG NO.	DESCRIPTION
LOV-14-100FT	#14 AWG (41 Strands)
LOV-12-100FT	#12 AWG (65 Strands)
LOV-10-100FT	#10 AWG (104 Strands)
LOV-8-100FT	#8 AWG (168 Strands)

LS-REPL-LED

STEP LIGHTING REPLACEMENT LED MODULE

CATALOG NO.	DESCRIPTION
LS-REPL-LED	3000K Replacement LED Module
LS-REPL-LED-27K	2700K Replacement LED Module

BOLLARD CUSTOMIZATION

CATALOG NO.	POST SIZE		FIXTURES PER POLE		COLOR TEMP		FINISH	
	code	description	code	description	code	description	code	description
WMS-S	18	18 inch	1	1 Sided	30K	3000K	BR	Bronze
WMS-R	36	36 inch	2	2 Sided	40K	4000K	WH	White
LMW					50K	5000K		
LWA-12								

Mounting Options Shown with LMW Series

Mounting Options Shown with LWA-12W Series

Mounting Options Shown with WMS Series

LANDSCAPE-DISPLAY

LANDSCAPE-DISPLAY2-UBK

LANDSCAPE-DISPLAY2-UBR

LANDSCAPE DISPLAY

CATALOG NO.	DESCRIPTION
LANDSCAPE-DISPLAY	Display for Landscape
LANDSCAPE-DISPLAY2-UBK	Display for Landscape
LANDSCAPE-DISPLAY2-UBR	Display for Landscape

SMART & RGBW

TC-GL SERIES

TC-FL SERIES

FLDX SERIES

FLVX SERIES

WMCS SERIES

CMC4 SERIES


SFX SERIES

LRS-PV SERIES


LRS-H SERIES

LRS-F SERIES

LDS SERIES

TC-RDPS SERIES

TC-RSL SERIES

TC-FML SERIES


TC-DLSE


STG-5315 SERIES

STG-LANT SERIES

TC-PAR SERIES

TC-E12 SERIES

TC-A19 SERIES

TC-G25 SERIES

TC-PL12 SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

TC-GL15W RGBW

TC-RGBW-RC

BLUETOOTH WG APP COMPATIBLE RGBW FLOOD LIGHT, 40° LENS 12V

CATALOG NO.	DESCRIPTION			PCK QTY
TC-GL-12V-15W-RGBW-BT-BR	15W	405LM	RGBW	6

TC-FL-12V-36W-RGBW

TC-RGBW-RC

BLUETOOTH WG APP COMPATIBLE RGBW FLOOD LIGHT, 60° LENS 12V

CATALOG NO.	DESCRIPTION			PCK QTY
TC-FL-12V-36W-RGBW-BT-BR	36W	824LM	RGBW	4

TC-FL-36W-RGBW-BT-BR

TC-RGBW-RC

BLUETOOTH WG APP COMPATIBLE RGBW FLOOD LIGHT, 60° LENS 120-277V

CATALOG NO.	DESCRIPTION			PCK QTY
TC-FL-36W-RGBW-BT-BR	36W	824LM	RGBW	4

FLDX-MD-15W-RGBW-BT-BR

TC-RGBW-RC

SPEC SERIES RGBW BLUETOOTH WESTGATE APP BULLET **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
FLDX-MD-15W-RGBW-BT-BR	15W	720LM	RGBW	4

FLVX-MD-15W-RGBW-BT-BR

TC-RGBW-RC

SPEC SERIES RGBW BLUETOOTH WESTGATE APP BULLET **12V**

CATALOG NO.	DESCRIPTION			PCK QTY
FLVX-MD-15W-RGBW-BT-BR	15W	720LM	RGBW	4

WMCS-UDL-RGBW-BK

WMC-UDL-RGBW-BK

WMCS-UDL-RGBW-WH

WMC-UDL-RGBW-WH

TC-RGBW-RC

RGBW LED OUTDOOR CYLINDER LIGHTS IP65

CATALOG NO.	DESCRIPTION			PCK QTY
4" LED ROUND CYLINDER LIGHTS, 120V (UP/DOWN LIGH) H: 12"				
WMC-UDL-RGBW-BK	24W	1920LM	RGBW	6
WMC-UDL-RGBW-WH	24W	1920LM	RGBW	6
4" LED SQUARE CYLINDER LIGHTS, 120V (UP/DOWN LIGHT) H: 10-1/4"				
WMCS-UDL-RGBW-BK	24W	1920LM	RGBW	6
WMCS-UDL-RGBW-WH	24W	1920LM	RGBW	6

CMC6-MCTP-DD-BK-RGBW

CMC6-MCTP-DD-WH-RGBW

TC-RGBW-RC

CMC RGBW CYLINDER LIGHT, PENDANT OR SURFACE MOUNT, APP CONTROLLED

CATALOG NO.	DESCRIPTION			PCK QTY
CMC2L-RGBW-BK	6W	300LM	27K-50K + RGB	6
CMC2L-RGBW-WH	6W	300LM	27K-50K + RGB	6
CMC3-RGBW-BK	9W	550LM	27K-50K + RGB	6
CMC3-RGBW-WH	9W	550LM	27K-50K + RGB	6
CMC4-RGBW-BK	15W	900LM	27K-50K + RGB	6
CMC4-RGBW-WH	15W	900LM	27K-50K + RGB	6
CMC6-RGBW-BK	20W	1200LM	27K-50K + RGB	8
CMC6-RGBW-WH	20W	1200LM	27K-50K + RGB	8

SFX-G9-RGB

SPEC SERIES X GEN. RGB STADIUM LIGHTS, DMX512 CONTROLLED **SPECIAL ORDER**

CATALOG NO.	DESCRIPTION		PCK QTY
SFX-G9-500W-45D-RGB	500W	RGB	1
SFX-G9-800W-45D-RGB	800W	RGB	1

LRS-PV-RGBW

TC-RGBW-RC

RGB WG APP OR RC 13" OUTDOOR/INDOOR CEILING LIGHT **120-277V**

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-PV-RGBW	25W	1920LM	5CCT AND RGB	4

LRS-H-RGBW-BK

TC-RGBW-RC

RGB WG APP OR RC 6”
SQUARE MODEL H ARCHITECTURAL OUTDOOR/INDOOR LED WALL LIGHT **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-H-RGBW-BK	12W	650LM	5CCT AND RGB	12

LRS-F-RGBW-BK

TC-RGBW-RC

RGB WG APP OR RC 7”
ROUND MODEL F ARCHITECTURAL OUTDOOR/INDOOR LED WALL LIGHT **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
LRS-F-RGBW-BK	12W	650LM	5CCT AND RGB	12

LDS-RGBW-BK

TC-RGBW-RC

RGB WG APP OR RC OUTDOOR/INDOOR LED DECORATIVE WALL SCONCE **120V** 7” WIDE

CATALOG NO.	DESCRIPTION			PCK QTY
LDS-RGBW-BK	15W	980LM	5CCT AND RGB	4



TC-RDPS-RGBW-WIFI

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW SMOOTH RECESSED LIGHT TRIM - ROUND **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-RDPS4-10W-RGBW-WIFI	10W	650LM	RGBW	12
TC-RDPS6-13W-RGBW-WIFI	13W	850LM	RGBW	8

TC-RSL-RGBWW

TC-RGBW-RC

WG SMART APP OR REMOTE COMPATIBLE RGBWW ULTRA SLIM CANLESS RECESSED LIGHT ROUND **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-RSL4-RGBWW	9W	630LM	RGBWW	24
TC-RSL6-RGBWW	12W	840LM	RGBWW	24

TC-FML-RGBW-WIFI

TC-RGBW-RCI

WG SMART APP COMPATIBLE RGBW FLUSH MOUNT FIXTURE **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-FML-8-14W-RGBW-WIFI	14W	980LM	RGBW	20
TC-FML-10-17W-RGBW-WIFI	17W	1190LM	RGBW	20
TC-FML-12-22W-RGBW-WIFI	22W	1540LM	RGBW	20
TC-FML-14-26W-RGBW-WIFI	26W	1820LM	RGBW	20



DLSE6-RGBW

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW BUILDER SERIES LED ECONOMY DISK LIGHT

CATALOG NO.	DESCRIPTION			PCK QTY
DLSE6-RGBW	15W	1000LM	27K/30K/35K/40K/50K	24

STG-5315

TC-RGBW-RC

53FT 15-BULB ST14 RGB STRING LIGHT

CATALOG NO.	DESCRIPTION	PCK QTY
STG-5315-RGB-BT	53Ft 15-Bulb ST14 Rgb String Light 1M Appart With 11 Fairy Lights In Between Bluetooth	

STG-LANT-RGBW

TC-RGBW-RC

LANTERN DESIGN STRING LIGHT RGB BLUETOOTH APP CONTROLLED

CATALOG NO.	DESCRIPTION
STG-2415-LANT-RGBIC-BT	24Ft 15-Lamp Lantern Design String Light Rgb Bluetooth App Controlled
STG-4830-LANT-RGBIC-BT	48Ft 30-Lamp Lantern Design String Light Rgb Bluetooth App Controlled

TC-RGBW-RC

TC-PAR20-4.5W-RGBW-WIFI

TC-PAR30-11W-RGBW-WIFI

TC-PAR38-10W-RGBW-WIFI

WG SMART APP COMPATIBLE RGBW PAR20/PAR30/PAR38 **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-PAR20-4.5W-RGBW-WIFI	4.5W	400LM	RGBW	50
TC-PAR30-11W-RGBW-WIFI	11W	850LM	RGBW	50
TC-PAR38-10W-RGBW-WIFI	10W	1050LM	RGBW	50

TC-G25-5W-RGBW-WIFI

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW G25 LAMP **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-G25-5W-RGBW-WIFI	5W	450LM	RGBW	50

TC-E12-4.5W-RGBW-WIFI

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW CANDELABRA **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-E12-4.5W-RGBW-WIFI	4.5W	325LM	RGBW	50

TC-A19-9W-RGBW-WIFI

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW A19 LAMP **120V**

CATALOG NO.	DESCRIPTION			PCK QTY
TC-A19-9W-RGBW-WIFI	9W	800LM	RGBW	50

TC-PL12-RGBW

TC-RGBW-RC

WG SMART APP COMPATIBLE RGBW PUCK LIGHT ROUND

CATALOG NO.	DESCRIPTION		
TC-PL12-RGBW	4W	250LM	RGB
TC-PL12-RGBW-SPLITTER4	RGB Puck Light 4-Port Splitter With 6in Cable		
TC-PL12-RGBW-CONTROLLER	RGBW In-Line Smart Controller App Compatible		

CONTROL SOLUTIONS

KEILTON AUTANI CONTROLS

KEILTON BASIC CONTROLS

HOMEWELL GEBC CONTROLS

LLHB SERIES

WEC SERIES

REMOTE CONTROLS

WEC-MOD SERIES

WEC-SW SERIES

PC SERIES

ELB SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

KEA-EFS106-AUX.C1

KEA-IFS108-AUX.B1

KEA-IFS108.B1

KEA-EFS106-AUX-W.D1

KEA-IFS105SE.B1

KEA-FA102.C2

KEA-MWS105E.B1

KEA-WP1018A.A0

KEA-CS107D.B1

KEA-PPA102S.C2

KEILTON+AUTANI SMART MOTION SENSOR LIGHTING CONTROL SYSTEM

CATALOG NO.	DESCRIPTION
KEA-EFS106-AUX.C1	High Bay Sensor, 0-10V Bi-level PIR M, 12V, IP40, 40ft, 3.5mm AUX, Smart Bluetooth
KEA-IFS108-AUX.B1	Low Bay Fixture Sensor, PIR, 12V DC up to 20ft, 2.5mm AUX, Smart Bluetooth
KEA-IFS108.B1	Low Bay Fixture Sensor, PIR, 12V DC up to 20ft, PH2.0-4pin, Smart Bluetooth
KEA-EFS106-AUX-W.D1	High Bay Sensor, 0-10V Bi-level PIR M, 12V, IP66, 40ft, 3.5mm AUX, Smart Bluetooth
KEA-IFS105SE.B1	Low Bay Fixture Sensor, PIR, 12V DC up to 20ft, Integrated Wiring, Smart Bluetooth
KEA-DC30	PH2.0-4A cable sensor cable for KEA-IFS108, the other end fly leads, 12"
KEA-FA102.C2	Integrated 12V BT Fixture Adapter, 0-10V, 12V DC, 200ft Transmission, Smart Bluetooth
KEA-MWS105E.B1	Integrated 12V Eco Microwave Sensor, 12V DC up to 20ft, Smart Bluetooth
KEA-FC30	Power cable for KEA-FA102, 12"
KEA-CC30	Connecting cable for KEA-FA102, 12"
KEA-WP1018A.A0	Wall Switch, 8-Key AAA Battery-Powered, 100ft Transmission, Smart Bluetooth
KEA-PPA102S.C2	Line Voltage 6A BT Fixture Controller, 0-10V, 120-277VAC, 200mA, 200ft Transmission, Smart Bluetooth
KEA-CS107D.B1	Ceiling Occupancy Sensor, 0-10V, 120-277VAC up to 20ft, 200mA, 200ft Transmission, Smart Bluetooth

KEB-EFS07-AUX

KEB-IFS06R

KEB-IFS06R-AUX

KEB-RM51

KEB-IFS05SE

KEB-EFS01RE

KKEB-EFS07-Z10-W

KEB-EFS07-AUX-W

KEILTON BASIC MOTION SENSOR LIGHTING CONTROL SYSTEM

CATALOG NO.	DESCRIPTION
KEB-IFS06R-AUX	Low Bay Fixture Sensor, PIR, 12V DC up to 20ft, 2.5mm AUX, Remote Control Option
KEB-IFS06R	Low Bay Fixture Sensor, PIR, 12V DC up to 20ft, PH2.0-4pin, Remote Control Option
KEB-EFS07-AUX	High Bay Sensor, 0-10V Bi-level PIR M, 12V, IP40, 40ft, 3.5mm AUX, Remote Control Option
KEB-EFS07-AUX-W	Outdoor High Bay Sensor, 0-10V Bi-level PIR, 12V, IP66, 40ft, 3.5mm AUX, Remote Control Option
KEB-EFS07-Z10-W	High Bay Sensor, 0-10V Bi-level PIR, 12V, IP40, 40ft, Z10 Zhaga, Remote Control Option
KEB-EFS01RE	High Bay External Sensor, 0-10V Bi-level PIR, 120-277V AC, 40ft, 10A relay, IP40, Remote Control Option
KEB-IFS05SE	Low Bay Internal Fixture Sensor, 0-10V Bi-level, 12V, IP66, 40ft,
KEB-RM51	Optional IR Remote Controller for Basic Sensor Series

GEBC-620-CON-BLE

GEBC-620-CON-BLE-GE



GEBC-623-CON-BLE-GE

GEBC-810-B-M6-BLE-GE

GEBC-810-B-M7-BLE-GE

GEBC-ANT-1P-4T-BLE-GE

GEBC-GT-001-GE

GEBCM6-BLE-GE

HOMEWELL GEBC CONTROLS

ON-BLE-GE-TX

GEBC-ANT-6-4T-H-BLE-GE

GEBC-BR-WS205-GE

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER
GEBC-620-CON-BLE-GE	12-24VDC Internal 0-10V Diimming & CCT Controller BT Gebc Or WG NLS Apps Or Compatible Wall Switches	
GEBC-623-CON-BLE-GE	12-24VDC Internal 0-10V Diimming Controller BT Gebc Or WG NLS Apps Or Compatible Wall Switches	
GEBC-810-B-M6-BLE-GE	12-24VDC 20ft NLC Microwave Sensor W/ Daylight Harv. Ip20 BT Gebc Or WG NLS Apps	
GEBC-810-B-M7-BLE-GE	12-24VDC 20ft NLC Microwave Sensor W/ Daylight Harv. IP65 BT Gebc Or WG NLS Apps	
GEBC-ANT-11-4T-BLE-GE-BR	12-24VDC 40ft NLC Microwave Sensor W/ Daylight Harv. IP65 BT Gebc & NLS Apps - Bronze	
GEBC-ANT-15P	12-24VDC 12ft Troffer & Panel Oval Sensor With Daylight Harv.3Rc Compatible	
GEBC-ANT-15P-BLE-GE	12-24VDC 12ft NLC Troffer & Panel Oval Sensor With Daylight Harv BT Gebc & NLS Apps	
GEBC-ANT-1P-4T-BLE-GE	12-24VDC 15ft NLC PIR Troffer & Panel Sensor With Daylight Harv. 2.5mm Audio Jack BT Gebc Or WG NLS Apps	
GEBC-ANT-1P-4T-BLE-GE-NFC	12-24VDC 15ft NLC PIR Troffer & Panel Sensor With Daylight Harv. 2.5mm Audio Jack BT Gebc Or WG NLS Apps Nfc Commissioning	
GEBC-ANT-5-4T-BLE-GE	12-24VDC 50ft NLC Microwave Sensor With Daylight Harv. IP65 3.5mm Audio Jack BT Gebc Or WG NLS Apps	
GEBC-ANT-5-4T-CON-BLE-GE	12-24VDC 100ft NLC Microwave Sensor IP65 3.5Mm Audio Jack BT Gebc Or WG NLS Apps	
GEBC-ANT-5-4T-CON-BLE-GE-TX	12-24VDC 500ft NLC Node-To-Node Range Extender IP65 3.5Mm Audio Jack BT Gebc Or WG NLS Apps	
GEBC-ANT-5-ZT-BLE-GE-BK	12-24VDC 40ft NLC Microwave Sensor W/ Daylight Harv. IP65 Zhaga Base BT Gebc & NLS Apps - Bk	
GEBC-ANT-6-4T-H-BLE-GE	12-24VDC 50ft NLC PIR Sensor With Daylight Harv. IP65 3.5Mm Audio Jack BT Gebc Or WG NLS Apps	
GEBC-ANT-7-BLE-GE	12-24VDC 20ft NLC Strip-Light Microwave Sensor W/ Daylight Harv. BT Gebc Or WG NLS Apps	
GEBC-ANT-703P-C-BLE-GE-BK	12-24VDC 50ft PIR Side-Mt NLC Sensor With Daylight Harv. IP65 3.5Mm Audio Jack Control Gebc & NLS Apps - Black	
GEBC-ANT-703P-C-BLE-GE-WH	12-24VDC 50ft PIR Side-Mt NLC Sensor With Daylight Harv. IP65 3.5Mm Audio Jack Control Gebc & NLS Apps	
GEBC-BC-USDM101-6-GE	120/277V 0-10V Diimming & CCT Wall Switch BT Gebc Or WG NLS Apps Or Compatible With Gebc-620	
GEBC-BR-WS205-GE	Battery-Op 0-10V Diimming & CCT Wall Switch BT Gebc Or WG NLS Apps Or Compatible With Gebc-620	
GEBC-BRI-PP08-RY-GE	120/277V Power Pack To Relay 0-10V Signals To Fixtures With Total 20A Capacity	
GEBC-BRI-USDM101-5-GE	120/277V 0-10V Diimming Wall Switch BT Gebc Or WG NLS Apps Or Compatible With Gebc-620	
GEBC-BRI-WS206-GE	Battery-Op 0-10V Diimming Wall Switch BT Gebc Or WG NLS Apps Or Compatible With Gebc-623	
GEBC-GT-001-GE	5V Usb Gateway For Wifi Connection And Remote Programming Of Gebc NLS Sensors	

LLHB-SENB

LLHB-SMB

SL-HPIR-BZ
SL-HPIR-WH

SL-PIR-BZ
SL-PIR-WH

WEC-2CPDR-3

WEC-2ADP

WEC-2P-44

WEC-2MD-33

WEC-2MDRH-35

WEC-2MDR-27

WEC-2MDR-33

WEC-2MDBTH-36

WEC-2DLH-22

WEC-2MRHB2

WEC-2P-58

WEC-2PR-28-AJ-WH

WEC-3MDR-42

WEC-3PDR-52

WEC-3MR-48

WEC-3MR-45

WEC-3MR-3-BR
WEC-3MR-3-WH

WEC-3MR-4-BR
WEC-3MR-4-WH

WEC-3PDR-58-BR
WEC-3PDR-58-WH

WEC-3MRLV-5-BR
WEC-3MRLV-5-CLR

WEC-3MRLV-5-GY
WEC-3MRLV-5-WH

WEC-3MR-72-TLB-BK

WEC-3MRLV-6

WEC-3MRLV-6-GY

WEC-3MRLV-6-BR

YM183-W

YM2108-W

YM2108-T-W

WEC-3PR-60

WEC-3PDR-48-480V

WEC-3PR-78-AJ-WH

WEC-ON50-BR
WEC-ON50-WH

MOTION SENSOR FOR OUTDOOR SEE COMPATIBLE SENSOR LIST IN DESCRIPTION

CATALOG NO.	DESCRIPTION
LLHB-SENB	Galvanized Steel Sensor Mounting Bracket
LLHB-SMB	Motion Sensor Mounting Box For Linear High Bay Fixtures
SL-HPIR-BZ	Bronze 240°, 350W Max Load
SL-HPIR-WH	White 240°, 350W Max Load
SL-PIR-BZ	Bronze 180°, 350W Max Load
SL-PIR-WH	White 180°, 350W Max Load
WEC-2ADP	Ac To Dc Adapter Module For Ant-4

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION
WEC-2CPDR-3	600W Max, 0-10V PIR 120-277V Ceiling Sensor Dip & Rc (Optional Remote Control WEC-3RC)
WEC-2DLH-22	600W Max, 0-10V Daylight Harvesting Module, White
WEC-2MD-33	600W Max, 0-10V Mw 120-277V Low-Ceiling Sensor Dip
WEC-2MDRH-35	120-277 Vac Microwave Sensor, Bi-Level, Daylight Havest, Dip And Rc
WEC-2MDR-27	12-24Vdc Internal Microwave Sensor For Strip Lights (Optional Remote Control WEC-3RC)
WEC-2MDR-33	600W Max, Microwave Sensor For Linear Strip Lights With Dip (Optional Remote Control WEC-2RC-33)
WEC-2MD-TRIAC	Triac Bi-Level Microwave Sensor 120V, Clear
WEC-2MRHB2	600W Max, 0-10V Microwave Highbays Sensor Kit (Optional Remote Control WEC-7RC)
WEC-2P-44	600W Max, 0-10V PIR 6-24Vdc Troffer Sensor Dip
WEC-2P-58	600W Max, On/Off PIR 120-277V Highbay Sensor
WEC-2PR-28-AJ-SOCKET	12-24Vdc 1-Pin 2.5Mm Socket For Audio-Jack Panel And Troffer Sensor
WEC-2PR-28-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level & RC (Optional RC WEC-3RC)
WEC-3MDR-42	600W Max, 0-10V Mw 120-277V Sensor Dip & Rc (Optional Remote Control WEC-3RC)
WEC-3MR-3-BR	600W Max, Microwave IP67 Sensor, 1/2" Thread, Bronze (Optional Remote Control WEC-8RC)
WEC-3MR-3-WH	600W Max, Microwave IP67 Sensor, 1/2" Thread, White (Optional Remote Control WEC-8RC)
WEC-3MR-45	600W Max, 0-10V Mw 120-277V IP66 Highbay Sensor & Rc (Optional Remote Control WEC-3RC)
WEC-3MR-4-BR	600W Max, 90-Degree IP67 Microwave Sensor, Bronze (Optional Remote Control WEC-8RC)
WEC-3MR-4-WH	600W Max, 90-Degree IP67 Microwave Sensor, White (Optional Remote Control WEC-8RC)
WEC-3MR-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Rc Ready, Black, With Base (Optional Remote Control WEC-3RC)
WEC-3MRLV-5-BR	600W Max, 0-10V Microwave, 120-277V - Bronze (Optional Remote Control WEC-8RC)
WEC-3MRLV-5-CLR	600W Max, 0-10V Microwave, 120-277V - Clear (Optional Remote Control WEC-8RC)
WEC-3MRLV-5-GY	600W Max, 0-10V Microwave, 120-277V - Gray (Optional Remote Control WEC-8RC)
WEC-3MRLV-5-WH	600W Max, 0-10V Microwave, 120-277V - White (Optional Remote Control WEC-8RC)
WEC-3MRLV-6	IP65 120-277 Vac Split Microwave Sensor, Bi-Level, Dip And Rc (Optional RC WEC-3RC)
WEC-3MRLV-6-BR	IP65 120-277 Vac Split Microwave Sensor, Bi-Level, Dip And Rc, Bronze (Optional RC WEC-3RC)
WEC-3MRLV-6-GY	IP65 120-277 Vac Split Microwave Sensor, Bi-Level, Dip And Rc, Gray (Optional RC WEC-3RC)
WEC-3PDR-48-480V	120V-480V Pir Ip65 Bi-Level Motion Sensor, Remote Capable (Optional Remote Control WEC-3RC)
WEC-3PDR-52	600W Max, 0-10V PIR 120-277V Sensor Dip & Rc (Optional Remote Control WEC-3RC)
WEC-3PDR-58-BR	600W Max, 0-10V PIR IP65 120-277V Sensor Dip And Rc , Bronze (Optional Remote Control WEC-3RC)
WEC-3PDR-58-WH	600W Max, 0-10V PIR IP65 120-277V Sensor Dip And Rc , Bronze (Optional Remote Control WEC-3RC)
WEC-3PR-60	600W Max, 0-10V PIR 120-277V Ip66 Knuckle Sensor Dip & Rc (Optional Remote Control WEC-3RC)
WEC-3PR-72-TLB-WH	600W Max, Zhaga 12-24VDC PIR Sensor, Rc Ready, White, With Base (Optional Remote Control WEC-3RC)
WEC-3PR-78-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level & RC (Optional RC WEC-3RC)
WEC-AJ-SA	12-24Vdc Swivel Arm For 3.5Mm Plug-In 1-Pin Audio-Jack Sensors
WEC-AJ-SOCKET	12-24Vdc 1-Pin Audio Jack Sensor Receptacle Socket 1/2In Npt
WEC-ON50-BR	Sensor Mounting Offset Nipple, 1/2 Inch Size , Bronze
WEC-ON50-WH	Sensor Mounting Offset Nipple, 1/2 Inch Size , White
YM183-W	Occupancy Pir Sensor, 180°, 30Ft (720Ft), 120V 800/1200W Max, Single Pole, Neutral Req.
YM2108-T-W	Vacancy & Occupancy Pir Sensor, 180°, 25Ft (600Ft), 120V 600/1000W Max, 3-Way, Neutral Req.
YM2108-W	Vacancy & Occupancy Pir Sensor, 180°, 30Ft (720Ft), 120V 800/1200W Max, Single Pole, Neutral Req.
WEC-3MBT-72-TLB-BK-3PIN	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base (Optional Remote Control WEC-3RC)
WEC-3PR-72-TLB-WH-3PIN	600W Max, Zhaga 12-24VDC PIR Sensor, White, With Base (Optional Remote Control WEC-3RC)

WEC-2BT-28-AJ-WH

WEC-3PBT-78-AJ-WH

WEC-3MDBTH-36

WEC-2MDBTH-36

WEC-3MBT-72-TLB-BK
WEC-3MBT-72-WH

WEC-3PBT-72-WH

WEC-2UGW-WIFI

BLUETOOTH APP READY - MOTION SENSOR FOR OUTDOOR

CATALOG NO.	DESCRIPTION
WEC-2BT-28-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level Bluetooth App Ready
WEC-3PBT-78-AJ-WH	PIR Sensor 1-Pin Audio Jack Contact 600W 40Ft 120-277V 0-10V Bi-Level Bluetooth App Ready
WEC-3MDBTH-36	Split Microwave Sensor For Outdoor Bluetooth Mesh, , Bluetooth App Ready
WEC-2MDBTH-36	Split Microwave Sensor For Indoor Bluetooth Mesh, , Bluetooth App Ready
WEC-3MBT-72-TLB-BK	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base
WEC-3MBT-72-WH	Microwave Sensor Zhaga Base Bluetooth Mesh, Bluetooth App Ready
WEC-3PBT-72-WH	Pir Sensor Zhaga Base Bluetooth Mesh, , Bluetooth App Ready
WEC-2UGW-WIFI	Industrial Gateway With Multi-Signal Input - Wifi Output
WEC-3MBT-72-TLB-BK-3PIN	600W Max, Zhaga 12-24VDC Microwave Sensor, Bluetooth App Ready, Black, With Base (Optional Remote Control WEC-3RC)
WEC-3PR-72-TLB-WH-3PIN	600W Max, Zhaga 12-24VDC PIR Sensor, White, With Base (Optional Remote Control WEC-3RC)

TC-RGBW-RC

WEC-2RC

WEC-3RC

WEC-8RC

WEC-2RC-33

REMOTE CONTROL FOR MOTION SENSORS FOR COMPATIBILITY, SEE PREVIOUS PAGE

CATALOG NO.	DESCRIPTION
WEC-8RC	Remote Control For WEC-3MR-4 & WEC-3MR-3
WEC-2RC	Remote Control For WEC-2MD-36, Silver
WEC-3RC	Remote Control For Motion Sensors
WEC-2RC-33	Remote Control For WEC-2MDR-33 Motion Sensor
TC-RGBW-RC	Westgate App Compatible Remote Control



WEC-MOD-010V-BT
WEC-MOD-010V-WIFI
WEC-MOD-TR-WIFI

WESTGATE SMART LIGHTING CONTROL MODULE - 1/2IN KNUCKLE

CATALOG NO.	DESCRIPTION
WEC-MOD-010V-BT	WG Smart Lighting Control Module 1000W 0-10V Bluetooth IP65
WEC-MOD-010V-WIFI	WG Smart Lighting Control Module 1000W 0-10V Wifi IP65
WEC-MOD-TR-WIFI	WG Smart Lighting Control Module 300W Triac Wifi IP65
WEC-MOD-WIFI-RC	WG Smart Remote Control Compatible With Wifi Lighting Modules

*The WEC-MOD installed on a 0~10V or Triac fixture to control the luminaries via WIFI, BT or a remote control.

WEC-SW-PB1-010V-BT
WEC-SW-PB1-TR-WIFI

WESTGATE SMART LIGHTING CONTROL SWITCHES SWITCHES WORK AS STAND ALONE OR WITH WESTGATE APP

CATALOG NO.	DESCRIPTION
WEC-SW-PB1-010V-BT	WEC-SW-PB1-010V-BT
WEC-SW-PB1-TR-WIFI	WEC-SW-PB1-TR-WIFI

*This stand-alone "wall dimmer" functions similarly to traditional wall switches by directly wiring to fixture.

WESTGATE CONTROLS

PC-1
PC-1H

PC-1S

SL-PC

PC-2S

PC-B
PC-BU

PC-BP

PC-TLSC

WEC-3MPCN

PC-BUM

PC-TLSOC-3PIN

PC-TLSOC-7PIN

PC-TWIST
PC-TWIST-480V

LF3-PCK
LF3-PCK-480V

WEC-3MPC-GY

PHOTOCONTROLS FOR OUTDOOR

CATALOG NO.	DESCRIPTION
PC-1	120V Stem Mount 1800W Photocell
PC-1H	277V Stem Mount 1800W Photocell
PC-1S	Photocell Swivel Arm 120V , 1000W
PC-2S	Swivel Photocell , 120Vac , 1800W
PC-B	Button Photocell , 120Vac , 500W
PC-BU	Button Photocell, 120-277Vac , 500W
PC-BP	Photocell With 1-Gange Stainless Steel Plate And Gasket , 120Vac , 500W
PC-BUM	Mini Button Photocell, 120-277Vac , 500W
PC-TLSC	Twist Lock Shorting Cap For Photocell Socket
PC-TLSOC-3PIN	3-Pin Socket Twist Lock For Smart Control Systems
PC-TLSOC-7PIN	7-Pin Socket Twist Lock For Smart Control Systems
PC-TWIST	Twist Lock Photocell 1000W Tungeston 120-277V AC
PC-TWIST-480V	Twist Lock Photocell 1000W Tungeston 480V AC
LF3-PCK	Twist-Lock Photocell Kit, 120-277V
LF3-PCK-480V	Twist-Lock Photocell Kit, 480V
SL-PC	Micro Button Photocell, 120/277V, 40W
WEC-3MPC-GY	Microwave IP67 Photocell With 1/2" Thread, Gray
WEC-3MPCN	Ultra-Violet Photocell, 120-277V 1/2in NPT Size
PC-TW-PSE-0-10V	Infrared Photocell Works With 0-10V Drivers

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

TYPE	CATALOG NO.	DESCRIPTION
OUTDOOR FIXTURES	**OPT-SP-10KV**	Factory Installled, 10KV surge protector

ELB-0848

ELB-1048-HH

ELB-1248

ELB-1548-HH

ELB-18150-B

ELB-2048
ELB-20150

ELB-0460-FM

ELB-2048-EXTR

ELB-08170-EXTR

ELB-08120-AC
ELB-09120-AC
ELB-12120-AC
ELB-15120-AC


ELB-09120-AC-JB

ELB-3048-FLEX
ELB-30150-FLEX

ELB-2048-IP65
ELB-20150-IP65

ELB-20175-AC-FLEX
ELB-23120-HH-AC-FLEX

ELB-0895

ELB-40170-AC-FLEX

ELB-60170-AC-FLEX

ELB-CW-18W-MW
ELB-CW-27W-MW

ELB-CW-27W-MV-IP66

ELB-15300-HH-B

ELB-0856-CP-SD-HH-B
ELB-1556-CP-SD-HH-B
ELB-2056-CP-SD-HH-B

EMERGENCY BATTERY BACKUPS

CATALOG NO.	DESCRIPTION			
ELB-0848	25-48V DC	8W MAX	Li-ion 2500mAh	8W SPLIT
ELB-1048-HH	25-48V DC	10W MAX	LifeP04 3000mAh	10W SPLIT HEAT TOLERANT
ELB-1248	25-48V DC	12W MAX	Li-ion 2500mAh	12W SPLIT
ELB-1548-HH	25-48V DC	15W MAX	LifeP04 3000mAh	15W SPLIT HEAT TOLERANT
ELB-2048	25-48V DC	20W MAX	Li-ion 4000mAh	20W SPLIT

TABLE CONTINUES ON THE NEXT PAGE

CONTINUED FROM PREVIOUS PAGE

CATALOG NO.	DESCRIPTION			
ELB-0460-FM	10-60V DC	4W MAX	Li-ion 2500mAh	4W INTEGRATED
ELB-2048-EXTR	25-48V DC	20W MAX	Ni-MH 4000mAh	20W INTEGRATED
ELB-3048-FLEX	25-48V DC	30W MAX	Li-ion 4000mAh	30W INTEGRATED
ELB-0895	95V DC MAX	8W MAX	Ni-MH 2600mAh	8W INTEGRATED HIGH DC VOLTAGE
ELB-30150-FLEX	50-150V DC	30W MAX	Li-ion 4000mAh	30W INTEGRATED HIGH DC VOLTAGE
ELB-2048-IP65	25-48V DC	20W MAX	Li-ion 4000mAh	20W INTEGRATED IP65
ELB-20150-IP65	50-150V DC	20W MAX	Li-ion 4000mAh	20W INTEGRATED HIGH DC VOLTAGE IP65
ELB-20150	50-150V DC	20W MAX	Li-ion 4000mAh	20W INTEGRATED HIGH DC VOLTAGE
ELB-08170-EXTR	170VDC	8W MAX	Li-ion	WITH FLEX
ELB-08120-AC	120V AC	8W MAX	Li-ion	8W & AC VOLTAGE
ELB-09120-AC	120V AC	9W MAX	Li-ion	9W & AC VOLTAGE
ELB-09120-AC-JB	4in SQARE J-BOX WITH FLAT BRACKET FOR CEILING LIGHTS WITH 9W AC-CONNECT			
ELB-12120-AC	120V AC	12W MAX	Li-ion	12W & AC VOLTAGE
ELB-15120-AC	120V AC	15W MAX	Li-ion	15W & AC VOLTAGE
ELB-20175-AC-FLEX	175VDC	20W MAX	Li-ion 4000mAh	20W INTEGRATED
ELB-40170-AC-FLEX	170VDC	40W MAX		DIRECT AC-CONNECT
ELB-60170-AC-FLEX	170VDC	60W MAX		DIRECT AC-CONNECT
ELB-18150-B	50-150VDC	18W MAX	Li-ion	18W SPLIT
ELB-CW-18W-MW	COLD-WEATHER LED EMERGENCY BACKUP 18W MULTI-VOLTAGE INTERNAL			
ELB-CW-27W-MW	COLD-WEATHER LED EMERGENCY BACKUP 27W MULTI-VOLTAGE INTERNAL			
ELB-CW-27W-MW-IP66	COLD-WEATHER LED EMERGENCY BACKUP 27W MULTI-VOLTAGE INTERNAL, IP66			
ELB-15300-HH-B	60-300VDC 15W CONSTANT-POWER INTERNAL BACKUP 100-347V INPUT SELF-TEST			
ELB-23120-HH-AC-FLEX	120VAC 23W BACKUP FOR T8 LAMPS AND DOB DOWNLIGHTS			
ELB-0856-CP-SD-HH-B	100-347VAC 25-56VDC 8W LiFePO4 CONSTANT POWER SELF-DIAG. 2PC BOXED EM			
ELB-1556-CP-SD-HH-B	100-347VAC 25-56VDC 15W LiFePO4 CONSTANT POWER SELF-DIAG. 2PC BOXED EM			
ELB-2056-CP-SD-HH-B	100-347VAC 25-56VDC 20W LiFePO4 CONSTANT POWER SELF-DIAG. 2PC BOXED EM			

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

CATALOG NO.	DESCRIPTION
OPT-EM-CW2EXT	COLD-WEATHER EXTERNAL EMERGENCY POWER SUPPLY 27W FACTORY OPTION
OPT-EM-CW2INT	COLD-WEATHER INTERNAL EMERGENCY POWER SUPPLY 27W FACTORY OPTION
OPT-EM-CW1INT	COLD-WEATHER INTERNAL EMERGENCY POWER SUPPLY 18W FACTORY OPTION

EXIT & EMERGENCY

XTSL SERIES

XT-RW

XTU-RG SERIES

XD-TH SERIES

XD-SDT SERIES

XT-ELRMA SERIES

XTN-EL1RGCA SERIES

XE SERIES

XT-WP SERIES

XT-WP SERIES

XT-N4X SERIES

CHI-XTU SERIES

NYC-XT SERIES

XTU-CLR SERIES

XTSL-CL-RW SERIES

XTU-CL-SDT SERIES

XTU-CL-RG-EM SERIES

XT-CL-RW-EM SERIES

XIT-STRIP SERIES

XT-C-ADJ SERIES

LLXT SERIES

XT-CLWP SERIES

XTCL-N4X SERIES

CWLEZ SERIES

XTN-ELR-CL-EM SERIES

EL-MT SERIES

EL-M5 SERIES

EL-M5-HO SERIES

EL-M2 SERIES

EL-M1 SERIES

EL-1 SERIES

EL-1L SERIES


EL-1L-RC SERIES

EL-1D SERIES

EL-2A SERIES

Search for the series name @WESTGATEMFG.COM

EL-HO SERIES

EL-EHO SERIES

EL-WP SERIES



EL-RH SERIES

EL-RH-WP SERIES



EL-DRH SERIES

LEDTBE SERIES

TFX SERIES

LESW-EM SERIES

DBEL SERIES

DELW SERIES

MELW-ACEM SERIES

RH-N4X SERIES

ELN4X SERIES

SHIELD GUARDS

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

XTSL-RW

XTSL-GW

BUILDER SERIES SUPER SLIM LED EXIT SIGN 120-277V 12”W X 7-1/2”H X 1”D

CATALOG NO.	DESCRIPTION			
XTSL-RW	Universal Single/Double	RED	White	1.2V Ni-MH
XTSL-GW	Universal Single/Double	GREEN	White	1.2V Ni-MH

XT-RW-EM

LED EXIT SIGN EXIT SIGN 120-277V 12”W X 7-1/2”H X 1-1/2”D

CATALOG NO.	DESCRIPTION			
XT-RW-EM	Universal Single/Double	RED	White	NiCd
XT-GW-EM	Universal Single/Double	GREEN	White	NiCd

XTU-EM

XTU-EM-BK

UNIVERSAL 2-CIRCUIT SELECTABLE RED/GREEN EXIT SIGN SINGLE, REMOTE CAPABLE SELF-DIAGNOSTIC-TEST

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	
XTU-RG-2C-UNIV	3W	Universal Single/Double	Red/Green	NI-MH
XTU-RG-2C-UNIV-BK	3W	Universal Single/Double	Red/Green	NI-MH
XTU-RG-EM-RC	3W	Red/Green	Remote Capability	NI-MH
XTU-RG-EM-SDT	3W	Red/Green	Self Diagnostics Test	NI-MH

XTU-EM

XTU-EM-BK

2-IN-1 COLOR- SELECTABLE UNIVERSAL EXIT SIGN 120-277V 15-1/2"W X 12-1/2"H X 9"D

DEFAULT IS RED, FLIP SWITCH INSIDE AND CHANGE PROVIDED GREEN FILM[S] FOR GREEN

CATALOG NO.	DESCRIPTION				
XTU-RG-EM-BK	Universal Single/Double	RED/GREEN	Black	1.2V Ni-MH	
XTU-RG-EM	Universal Single/Double	RED/GREEN	White	1.2V Ni-MH	
XTU-RG-2C-120V	Universal Single/Double	RED/GREEN	White	N/A	Two Circuits
XTU-RG-2C-277V	Universal Single/Double	RED/GREEN	White	N/A	Two Circuits
XTU-RG-BK-2C-120V	Universal Single/Double	RED/GREEN	Black	N/A	Two Circuits
XTU-RG-BK-2C-277V	Universal Single/Double	RED/GREEN	Black	N/A	Two Circuits

XD-TH

SPEC SERIES THIN DIECAST LED EXIT SIGN 120-277V 11-13/16"W X 7-3/4"H X 7/8"D

CATALOG NO.	DESCRIPTION			
XD-TH-1GAAEM	Single Face	Green	Aluminum	NiCd
XD-TH-1GBBEM	Single Face	Green	Black	NiCd
XD-TH-1GWWEM	Single Face	Green	White	NiCd
XD-TH-1RAAEM	Single Face	Red	Aluminum	NiCd
XD-TH-1RBBEM	Single Face	Red	Black	NiCd
XD-TH-1RWWEM	Single Face	Red	White	NiCd
XD-TH-2GAAEM	Double Face	Green	Aluminum	NiCd
XD-TH-2GBBEM	Double Face	Green	Black	NiCd
XD-TH-2GWWEM	Double Face	Green	White	NiCd
XD-TH-2RAAEM	Double Face	Red	Aluminum	NiCd
XD-TH-2RBBEM	Double Face	Red	Black	NiCd
XD-TH-2RWWEM	Double Face	Red	White	NiCd

XD-1RG-A-EM-SDT

SELF-DIAGNOSTIC-TEST, SELECTABLE RED/GREEN DIE-CAST EXIT SIGN 120-277V

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	
XD-1RG-A-EM-SDT	1.2W	Red/Green	Self Diagnostics Test	LiFePO4
XD-2RG-A-EM-SDT	1.2W	Red/Green	Self Diagnostics Test	LiFePO4

XT-EL

XT-EL1RCA

XT-ELRMA

BUILDER SERIES EDGELIT LED EXIT SIGN WITH ALUMINUM HOUSING SINGLE FACE WITH OPTIONAL DOUBLE FACE, OPT. RECESS-MT. ACCESSORY.

CATALOG NO.	DESCRIPTION				
XT-EL1RCA-EM	Single Face	Red	Clear	NiCd	Aluminum
XT-EL1GCA-EM	Single Face	Green	Clear	NiCd	Aluminum
XT-EL2RM-CP	Field-Installed Double-Face Mirror Panel only to Convert Single Face to Double Face- Red				
XT-EL2GM-CP	Field-Installed Double-Face Mirror Panel only to Convert Single Face to Double Face- Green				
XT-ELRMA	Field-Installed Recessed Mounting Conversion Kit, Order together with Exit Sign above				
XT-EL1RCA-EM-WH	Single Face	Red	Clear	NiCd	White
XT-EL1GCA-EM-WH	Single Face	Green	Clear	NiCd	White
XT-EL2RM-WH-CP	Field-Installed Double-Face Mirror Panel only to Convert Single Face to Double Face- Red White				
XT-EL2GM-WH-CP	Field-Installed Double-Face Mirror Panel only to Convert Single Face to Double Face- Green White				
XT-ELRMA-WH	Field-Installed Recessed Mounting Conversion Kit, Order together with Exit Sign above White				

*XT-ELRMA RECESSED CONVERSION KIT (FIXTURE NOT INCL.)



XTN-EL1RGCA-EM

XTN-ELR-CL-1R-EM

XTN-ELR-CL-1G-EM

XTN-ELRMA

EDGELIT SELECTABLE RED/GREEN EXIT SIGN 120-277V

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER	
XTN-EL1RGCA-EM	4W	Single Face	Red/Green
XTN-EL2RGM-CP	4W	Double Face	Red/Green
XTN-ELRMA	4.6W	360LM	Red
XTN-ELR-CL-1R-EM	4.6W	360LM	Red
XTN-ELR-CL-1G-EM	4.6W	360LM	Green

XE-1RCA-EM

XE-1GCA-EM

SPEC SERIES EDGELIT LED EXIT SIGN 120-277V 13"W X 11-1/8"H X 1-3/4"D

CATALOG NO.	DESCRIPTION				
XE-1RCA-EM	Single Face	Red	Clear	Aluminum	NiCd
XE-1RCW-EM	Single Face	Red	Clear	White	NiCd
XE-2RMW-EM	Double Face	Red	Mirror	White	NiCd
XE-2RMA-EM	Double Face	Red	Mirror	Aluminum	NiCd
XE-1GCA-EM	Single Face	Green	Clear	Aluminum	NiCd
XE-1GCW-EM	Single Face	Green	Clear	White	NiCd
XE-2GMW-EM	Double Face	Green	Mirror	White	NiCd
XE-2GMA-EM	Double Face	Green	Mirror	Aluminum	NiCd
XE-2C-120V	Optional Dual circuits, 120V				
XE-2C-277V	Optional Dual circuits, 277V				
XE-SDT	Optional Self Diagnostics Test				

XT-WP-RG-EM

XT-WP-GG-EM

WET LOCATION LED EXIT SIGN, UNIVERSAL

CATALOG NO.	DESCRIPTION			
XT-WP-RG-EM	Universal Single/Double	Red	Gray	NiCd
XT-WP-GG-EM	Universal Single/Double	Green	Gray	NiCd

XT-WP-EM

SPEC SERIES WET LOCATION LED EXIT SIGN 120-277V

(TWO-CIRCUITS OPTION AVAILABLE) 12-1/2"W X 9-1/4"H X 4-3/8"D

CATALOG NO.	DESCRIPTION			
XT-WP-1RG-EM	Single Face	Red	Gray	NiCd
XT-WP-2RG-EM	Double Face	Red	Gray	NiCd
XT-WP-2GG-EM	Double Face	Green	Gray	NiCd
XT-WP-1RB-EM	Single Face	Red	Black	NiCd
XT-WP-1GB-EM	Single Face	Green	Black	NiCd
XT-WP-2RB-EM	Double Face	Red	Black	NiCd
XT-WP-2GB-EM	Double Face	Green	Black	NiCd
XT-WP-SDT	Optional Self Diagnostics Test			
XT-WP-2C-120V	Optional Dual circuits, 120V			
XT-WP-2C-277V	Optional Dual circuits, 277V			

XTN4X

SPEC SERIES NEMA 4X LED EXIT SIGN 120-277V 14-3/4"W X 10"H X 6"D

CATALOG NO.	DESCRIPTION				
XTN4X-1GB	3.8W	Single Face	Green	Black	-
XTN4X-1GW	3.8W	Single Face	Green	White	-
XTN4X-1RB	3.2W	Single Face	Red	Black	-
XTN4X-1RW	3.2W	Single Face	Red	White	-
XTN4X-2GB	3.8W	Double Face	Green	Black	-
XTN4X-2GW	3.8W	Double Face	Green	White	-
XTN4X-2RB	3.2W	Double Face	Red	Black	-
XTN4X-2RW	3.2W	Double Face	Red	White	-
XTN4X-1GBEM	3.8W	Single Face	Green	Black	NiCd
XTN4X-1GWEM	3.8W	Single Face	Green	White	NiCd
XTN4X-1RBEM	3.2W	Single Face	Red	Black	NiCd
XTN4X-1RWEM	3.2W	Single Face	Red	White	NiCd
XTN4X-2GBEM	3.8W	Double Face	Green	Black	NiCd
XTN4X-2GWEM	3.8W	Double Face	Green	White	NiCd
XTN4X-2RBEM	3.2W	Double Face	Red	Black	NiCd
XTN4X-2RWEM	3.2W	Double Face	Red	White	NiCd

NYC-XT-EL2RCA-EM

NYC-XT-ELCL-1R-EM

NYC-XTR-EL1RCA-EM

NYC-XTR-ELCL-1R-EM

NYC-XT-2BE-1RW-EM

NYC-XT-3BE-1RW-EM

NYC-LED2BE

NYC-LED3BE

NEW YORK APPROVED EXIT & EMERGENCY LIGHT

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	
EXIT SIGNS				
NYC-XT-RW-EM	4W	Red	White	LiFePO4
NYC-XT-EL1RCA-EM	Single Face	Red	White	LiFePO4
NYC-XT-EL2RCA-EM	Double Face	Red	White	LiFePO4
NYC-XTR-EL1RCA-EM	Single Face	Red	White	LiFePO4
NYC-XT-2BE-1RW-EM	2 Head	Red	White	LiFePO4
NYC-XT-3BE-1RW-EM	3 Head	Red	White	LiFePO4
COMBO EXIT & EMERGENCY				
NYC-XTR-ELCL-1R-EM	3.5W	Red	White	LiFePO4
NYC-XT-ELCL-1R-EM	3.5W	Red	White	LiFePO4
EMERGENCY LIGHTS				
NYC-LED2BE	2 Head 4W	800LM	White	LiFePO4
NYC-LED3BE	3 Head 4.5W	1200LM	White	LiFePO4

CHI-XT-EL1RCA-EM

CHI-XTU-EL1RCA-EM

CHI-XT-2BE-1RW-EM

CHI-LED2BE

CHI-LED3BE

CHICAGO APPROVED EXIT & EMERGENCY LIGHT

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	
EXIT SIGNS				
CHI-XT-RW-EM	4W	Red	White	LiFePO4
CHI-XT-EL1RCA-EM	4W	Single Face	Red	LiFePO4
CHI-XT-EL2RCA-EM	4W	Double Face	Red	LiFePO4
CHI-XTU-EL1RCA-EM	4W	Single Face	Red	LiFePO4
CHI-XTU-EL2RCA-EM	4W	Double Face	Red	LiFePO4
COMBO EXIT & EMERGENCY				
CHI-XT-2BE-1RW-EM	2 Head 6.5W	Red	White	LiFePO4
EMERGENCY LIGHTS				
CHI-LED2BE	2 Head 4W	800LM	White	LiFePO4
CHI-LED3BE	3 Head 4.5W	1200LM	White	LiFePO4
ACCESSORIES				
CHI-XT-2RF-LR	Left and Right Arrow	Red	White	LiFePO4
CHI-XT-2RF-L	Left Arrow	Red	White	LiFePO4
CHI-XT-2RF-R	Right Arrow	Red	White	LiFePO4
CHI-XT-2RF-STAIRS	No Arrow	Red	White	LiFePO4
CHI-XT-2RF-STAIRS-R	Right Arrow	Red	White	LiFePO4
CHI-XT-2RF-STAIRS-L	Left Arrow	Red	White	LiFePO4
CHI-XT-2RF-STAIRS-LR	Left and Right Arrow	Red	White	LiFePO4
CHI-XT-EL-RP1-LR	Single Face	Left and Right Arrow	Red	LiFePO4
CHI-XT-EL-RP1-L	Single Face	Left Arrow	Red	LiFePO4
CHI-XT-EL-RP1-R	Single Face	Right Arrow	Red	LiFePO4
CHI-XT-EL-RP1-STAIRS	Single Face	No Arrow	Red	LiFePO4
CHI-XT-EL-RP1-STAIRS-R	Single Face	Right Arrow	Red	LiFePO4
CHI-XT-EL-RP1-STAIRS-L	Single Face	Left Arrow	Red	LiFePO4
CHI-XT-EL-RP1-STAIRS-LR	Single Face	Left and Right Arrow	Red	LiFePO4
CHI-XT-EL-RP2-LR	Double Face	Left and Right Arrow	Red	LiFePO4
CHI-XT-EL-RP2-L	Double Face	Left Arrow	Red	LiFePO4
CHI-XT-EL-RP2-R	Double Face	Right Arrow	Red	LiFePO4
CHI-XT-EL-RP2-STAIRS	Double Face	No Arrow	Red	LiFePO4
CHI-XT-EL-RP2-STAIRS-R	Double Face	Right Arrow	Red	LiFePO4
CHI-XT-EL-RP2-STAIRS-L	Double Face	Left Arrow	Red	LiFePO4
CHI-XT-EL-RP2-STAIRS-LR	Double Face	Left and Right Arrow	Red	LiFePO4



XTU-RG-2C-UNIV

UNIVERSAL SINGLE/DOUBLE ROUND-HEAD COMBO

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	
XTU-CLR-RG-EM	2.8W	160LM	Red/Green	White
XTU-CLR-RG-EM-SDT	2.8W	160LM	Red/Green	Self Diagnostics Test

XTSL-CL-RW

BUILDER SERIES SUPER SLIM LED EXIT SIGN WITH ADJUSTABLE LED HEAD **120-277V**

12”W X 7-3/5”H X 1”D

CATALOG NO.	DESCRIPTION			
XTSL-CL-RW	Universal Single/Double	RED	White	3.6 Ni-MH
XTSL-CL-GW	Universal Single/Double	GREEN	White	3.6 Ni-MH

XTU-CL-RG-EM-SDT

XTU-CL-RG-EM-SDT-BK

UNIVERSAL COMBO UNIT, SINGLE/DOUBLE, RED/GREEN W/ SELF-DIAGNOSTIC-TEST

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		
XTU-CL-RG-EM-SDT	4.6W	Red/Green	White	Ni-cad
XTU-CL-RG-EM-SDT-BK	4.6W	Red/Green	Black	Ni-cad

XTU-CL-RG-EM

XTU-CL-RG-EM-BK

2-IN-1 COLOR-SELEC UNIVERSAL COMBO UNIT 120-277V 15-1/2"W X 12-1/2"H X 9"D

DEFAULT IS RED, FLIP SWITCH INSIDE AND CHANGE PROVIDED GREEN FILM[S] FOR GREEN

CATALOG NO.	DESCRIPTION				
XTU-CL-RG-EM-BK	Universal Single/Double	RED/GREEN	Black	1.2V Ni-MH	
XTU-CL-RG-EM	Universal Single/Double	RED/GREEN	White	1.2V Ni-MH	
XTU-CL-RG-EM-RC	Universal Single/Double	RED/GREEN	White	1.2V Ni-MH	Remote Capable
XTU-CL-RG-EM-RC-BK	Universal Single/Double	RED/GREEN	Black	1.2V Ni-MH	Remote Capable

XT-CL-RW-EM

COMBINATION LED EXIT SIGN & LED EMERGENCY 120-277V 21"W X 9"H X 4-7/16"D

CATALOG NO.	DESCRIPTION			
XT-CL-RW-EM	Universal Single/Double	Red	White	NiCd
XT-CL-GW-EM	Universal Single/Double	Green	White	NiCd

XIT-STRIP-W

XIT-STRIP-B

LED STRIP COMBINATION EXIT/EMERGENCY LIGHT, SINGLE OR DOUBLE FACE

CATALOG NO.	DESCRIPTION			
XIT-STRIP-2R-W	Double Face	Red	White	NiCd
XIT-STRIP-2G-W	Double Face	Green	White	NiCd
XIT-STRIP-2R-B	Double Face	Red	Black	NiCd
XIT-STRIP-2G-B	Double Face	Green	Black	NiCd

XT-C-ADJ

SPEC SERIES COMBO DIE-CAST ALUMINUM LED EXIT SIGN ADJUSTABLE HEAD

120-277V 12-1/2"W X 11-3/4"H X 2-3/8"D

CATALOG NO.	DESCRIPTION			
XT-C-ADJ-3RBBEM	Universal Single/Double	Red	Black	NiCd
XT-C-ADJ-3RAAEM	Universal Single/Double	Red	Aluminum	NiCd
XT-C-ADJ-3RWWEM	Universal Single/Double	Red	White	NiCd
XT-C-ADJ-3GBBEM	Universal Single/Double	Green	Black	NiCd
XT-C-ADJ-3GAAEM	Universal Single/Double	Green	Aluminum	NiCd
XT-C-ADJ-3GWWEM	Universal Single/Double	Green	White	NiCd
XT-C-ADJ-RC	Optional Remote Capability			

LLXT-RW

LLXT-GB

LOW LEVEL LED EXIT & EMERGENCY COMBO

CATALOG NO.	DESCRIPTION			
LLXT-RW	Universal Single	RED	Frost White	NiCd
LLXT-GW	Universal Single	GREEN	Frost White	NiCd
LLXT-RB	Universal Single	RED	Black	NiCd
LLXT-GB	Universal Single	GREEN	Black	NiCd

XT-CLWP-RG-EM

XT-CLWP-GG-EM

WET LOCATION COMBO LED EXIT & EMERGENCY SIGN, UNIVERSAL

CATALOG NO.	DESCRIPTION			
XT-CLWP-RG-EM	Universal Single/Double	Red	White	NiCd
XT-CLWP-GG-EM	Universal Single/Double	Green	White	NiCd

XTCLN4X

SPEC SERIES NEMA 4X COMBINATION LED EXIT SIGN & LED EMERGENCY 120-277V NEMA 4X RATED

CATALOG NO.							DESCRIPTION
XTCLN4X	6	6V	12W	12W	W	WHITE	6V, 15W, SINGLE FACE
	12	12V	15W	15W	B	BLACK	6V, 28W, SINGLE FACE
			28W	28W	G	GRAY	12V, 15W, SINGLE FACE
							12V, 28W, SINGLE FACE
							6V, 12W, DOUBLE FACE
							12V, 12W, DOUBLE FACE

CWLEZXTEU

SPEC SERIES WET LOCATION COMBINATION LED EXIT SIGN & LED EMERGENCY 3.6W 120-277V 13-11/16"W X 12-3/8"H X 4-1/16"D

CATALOG NO.	DESCRIPTION			
CWLEZXTE1GW	Single Face	Green	White	
CWLEZXTE1GG	Single Face	Green	Gray	
CWLEZXTE1RW	Single Face	Red	White	
CWLEZXTE1RG	Single Face	Red	Gray	
CWLEZXTE1GB	Single Face	Green	Black	
CWLEZXTE1RB	Single Face	Red	Black	
CWLEZXTE2GB	Double Face	Green	Black	
CWLEZXTE2RB	Double Face	Red	Black	
CWLEZXTE2GW	Double Face	Green	White	
CWLEZXTE2GG	Double Face	Green	Gray	
CWLEZXTE2RW	Double Face	Red	White	
CWLEZXTE2RG	Double Face	Red	Gray	
CWLEZ-SDT	Optional Self Diagnostics Test			
CWLEZ-RC	Optional Remote Capability			
CWLEZ-CW	Optional Cold Weather			

XTN-EL-CL-1R-EM

XTN-ELR-CL-1G-EM

EDGELIT SURFACE-MOUNT COMBO EXIT & EMERGENCY LIGHT 120-277V

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER		
XTN-EL-CL-1R-EM	2.8W Max	Single Face	Red	NI-MH
XTN-EL-CL-1G-EM	2.8W Max	Single Face	Green	NI-MH

EL-MT

MODERN MINI BUG-EYE EMERGENCY LIGHT **120-277V** 7" X 7"

CATALOG NO.	DESCRIPTION				
EL-MT	1.5W(2)	150LM	White	Wall	3.6V NiCd
EL-MT-HO	1.5W(2)	250LM	White	Wall	3.6V NiCd

EL-M5

EL-M5-BK

MODERN MINI EMERGENCY LIGHT **120-277V** 7"H X 14"W

CATALOG NO.	DESCRIPTION				
EL-M5	1W(2)	150LM	White	Wall	3.6V NiCd
EL-M5-BK	1W(2)	150LM	Black	Wall	3.6V NiCd

EL-M5-HO-WP

WET LOCATION MODERN MINI EMERGENCY LIGHT **120-277V** 7"H X 14"W

CATALOG NO.	DESCRIPTION				
EL-M5-HO-WP	1.5W(2)	200LM	White	Wall	3.6V NiCd

EL-M2

EL-M2-BK

LED 2-HEAD MINI EMERGENCY LIGHT 120-277V 4"H X 8-1/2"W X 1-3/4"D

CATALOG NO.	DESCRIPTION				
EL-M2	1W(2)	200LM	White	Wall	3.6V NiCd
EL-M2-BK	1W(2)	200LM	Black	Wall	3.6V NiCd

EL-M1

EL-M1-BK

LED 2-HEAD MINI EMERGENCY LIGHT 120-277V 4-1/4"H X 9-1/4"W X 1 3/5"D

CATALOG NO.	DESCRIPTION					
EL-M1	1W(2)	200LM	White	Wall	3.6V Ni-MH	200LM
EL-M1-BK	1W(2)	200LM	Black	Wall	3.6V Ni-MH	200LM

EL-1

BUILDER SERIES LED EMERGENCY LIGHT 120-277V 13.7"W X 4.3"H X 3.5"D

CATALOG NO.	DESCRIPTION			
EL-1	1W per Head	White	Wall & Ceiling	NiCd

EL-1L



EL-1L-BK

SPEC SERIES LARGE LED EMERGENCY LIGHT WITH HIGHER OUTPUT 120-277V

15-1/2"W X 5"H X 4-3/4"D

CATALOG NO.	DESCRIPTION			
EL-1L	1.2W per Head	White	Wall & Ceiling	NiCd
EL-1L-BK	1.2W per Head	Black	Wall & Ceiling	NiCd

EL-1L-RC

SPEC SERIES LARGE LED EMERGENCY LIGHT WITH REMOTE CAPABLE & HIGHER OUTPUT 120-277V

15-1/2"W X 5"H X 4-3/4"D

CATALOG NO.	DESCRIPTION				
EL-1L-RC	1.2W per Head	White	Wall & Ceiling	NiCd	Remote Capable

EL-1D

LED 2-HEAD DESIGNER EMERGENCY LIGHT 120-277V

4-1/3"H X 13-1/2"W X 3-1/2"D

CATALOG NO.	DESCRIPTION			
EL-1D	2.4W(2)	White	Wall	3.6V NiCd

EL-2A

BUILDER SERIES LED EMERGENCY LIGHT 120-277V 4-5/8"H X 9-1/2"W X 2-1/4"D

CATALOG NO.	DESCRIPTION			
EL-2A	1.2W per head	White	Wall & Ceiling	3.6V 1Ah NI-CAD

EL-HO

SPEC SERIES LED 2-HEAD HIGH-OUTPUT EMERGENCY LIGHT 120-277V 5"H X 12-1/2"W X 2-4/5"D

CATALOG NO.	DESCRIPTION			
EL-HO	3W(2)	White	Lead Acid	650LM

EL-EHO

LED 2-HEAD EXTRA HIGH-OUTPUT EMERGENCY LIGHT 120-277V 5"H X 12-1/2"W X 2-4/5"D

CATALOG NO.	DESCRIPTION			
EL-EHO	10W per Head	White	Lead Acid	1250LM

EL-WP

WET LOCATION LED 2-HEAD EMERGENCY LIGHT 120-277V 4-1/5"H X 12-1/4"W X 5-1/4'D

CATALOG NO.	DESCRIPTION				
EL-WP	6W(2)	White	Wall & Ceiling	6V Ni-MH	400LM



EL-RECESS-6L-XHO

SQUARE & ROUND
TRIMS INCLUDED

EL-SURF-6L-XHO

EL-4HB-XHO

EL-OW-1L-XHO

LIFEPO4 EXTRA HIGH-OUTPUT EMERGENCY LIGHTS - SURFACE, RECESSED & WALL MOUNTED

CATALOG NO.	DESCRIPTION			
EL-4HB-XHO	4X1.5W	800LM	4-HEAD WALL-MOUNT	LiFePO4 Battery
EL-RECESS-6L-XHO	7W	1200LM	RECESSED CEILING-MOUNT	LiFePO4 Battery
EL-SURF-6L-XHO	7W	1200LM	SURFACE CEILING-MOUNT	LiFePO4 Battery
EL-OW-1L-XHO	6W	700LM	CEILING-MOUNT	LiFePO4 Battery

COMMERCIAL 4-HOUR EMERGENCY WP 9/18W 3CCT PHOTOCELL 120-277V SELF-DIAGNOSTIC

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	
EW4HR-MCT-SDT-BK	9W/18W	88LM/W	30K/40K/50K	4
EW4HR-MCT-SDT-BR	9W/18W	88LM/W	30K/40K/50K	4
EW4HR-MCT-SDT-WH	9W/18W	88LM/W	30K/40K/50K	4

EL-DRH-MCT-BK



EL-DRH-MCT-BR

DECORATIVE EMERGENCY REMOTE HEAD

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER	
EL-DRH-MCT-BK	3W	300LM	Black
EL-DRH-MCT-BR	3W	300LM	Bronze

LEDTBE-2-WP

LEDTBE-2-WP-BK

WET LOCATION BUG-EYE 2-HEAD EMERGENCY LIGHT

CATALOG NO.	DESCRIPTION	ARRIVES THIS SEASON CHECK & PRE-ORDER	
LEDTBE-2-WP	3.5W	660LM	White
LEDTBE-2-WP-BK	3.5W	660LM	Black

LEDTFX

WET LOCATION LED EMERGENCY LIGHT WITH REMOTE CAPABILITY 120-277V

6"H X 12-1/2"W X 8-1/2"D

CATALOG NO.	DESCRIPTION			
LEDTFX-2	1.875W per Head	Gray	Wall	NiCd
LEDTFX-2-B	1.875W per Head	Black	Wall	NiCd

LESW-15-30W-MCTP-P-EM

LESW-15-30W-MCTP-P-WH-EM

SELECTABLE 15-30W, 30K/40K/50K, 120-277V BUILDER SERIES ECONOMY OUTDOOR EMERGENCY WALL PACK WITH PHOTOCELL MADE TO ORDER

CATALOG NO.	DESCRIPTION			
LESW-15-30W-MCTP-P-EM	15W/20W/30W	135LM/W	3000K/4000K/5000K	Bronze
LESW-15-30W-MCTP-P-WH-EM	15W/20W/30W	135LM/W	3000K/4000K/5000K	White

DBEL

SPEC SERIES DECORATIVE OUTDOOR LED AC/EMERGENCY UNIT 120-277V

3-5/8"H X 10-1/2"W X 6-3/5"D

CATALOG NO.	DESCRIPTION			
DBEL-ACEM-WH-SDT	12W	White	NiCd	With Photocell
DBEL-ACEM-BK-SDT	12W	Black	NiCd	With Photocell
DBEL-ACEM-BR-SDT	12W	Dark Bronze	NiCd	With Photocell
DBEL-ACEM-N-SDT	12W	Nickel	NiCd	With Photocell
DBEL-ACEM-WH-SDT-CW	12W	White	NiCd	With Cold Weather & Photocell
DBEL-ACEM-BK-SDT-CW	12W	Black	NiCd	With Cold Weather & Photocell
DBEL-ACEM-BR-SDT-CW	12W	Dark Bronze	NiCd	With Cold Weather & Photocell
DBEL-ACEM-N-SDT-CW	12W	Nickel	NiCd	With Cold Weather & Photocell

DELW-15W-MCT-BK

DELW-15W-MCT-WH

DELW-15W-MCT-BR

BUILDER SERIES DECORATIVE OUTDOOR LED AC/EMERGENCY UNIT 120-277V

3-5/8"H X 10-1/2"W X 6-3/5"D

CATALOG NO.	DESCRIPTION			
DELW-15W-MCT-BK	15W	Black	NiCd	With Photocell
DELW-15W-MCT-BR	15W	Dark Bronze	NiCd	With Photocell
DELW-15W-MCT-WH	15W	White	NiCd	With Photocell

MELW-ACEM-40K-SDT-BK

MELW-ACEM-40K-SDT-BR

MELW-ACEM-40K-SDT-WH

SPECIFICATION EMERGENCY WALL PACK W/ PHOTOCELL & SELF-DIAGNOSTIC-TEST, 4000K

CATALOG NO.	DESCRIPTION		ARRIVES THIS SEASON CHECK & PRE-ORDER	
MELW-ACEM-40K-SDT-BK	18W	1500LM	Self Diagnostics Test	Black
MELW-ACEM-40K-SDT-WH	18W	1500LM	Self Diagnostics Test	White
MELW-ACEM-40K-SDT-BR	18W	1500LM	Self Diagnostics Test	Bronze

RHN4X

SPEC SERIES NEMA 4X OUTDOOR LED REMOTE HEAD 120-277V 4-7/8"H X 9-5/8"W X 5-1/2"D

CATALOG NO.	DESCRIPTION			
RHN4X-1W	3.3W per Head	6V/12VDC	White	Single Square Head
RHN4X-1B	3.3W per Head	6V/12VDC	Black	Double Square Head
RHN4X-2W	3.3W per Head	6V/12VDC	White	Single Square Head
RHN4X-2B	3.3W per Head	6V/12VDC	Black	Double Square Head

ELN4X

SPEC SERIES NEMA 4X LED EMERGENCY LIGHT 120-277V

CATALOG NO.	DESCRIPTION			
ELN4X-12-15W-B	15W	12V	Black	NiCd
ELN4X-12-15W-W	15W	12V	White	NiCd
ELN4X-12-36W-B	36W	12V	Black	NiCd
ELN4X-12-36W-W	36W	12V	White	NiCd
ELN4X-12-54W-B	54W	12V	Black	NiCd
ELN4X-12-54W-W	54W	12V	White	NiCd
ELN4X-6-15W-B	15W	6V	Black	NiCd
ELN4X-6-15W-W	15W	6V	White	NiCd
ELN4X-6-36W-B	36W	6V	Black	NiCd
ELN4X-6-36W-W	36W	6V	White	NiCd
ELN4X-6-54W-B	54W	6V	Black	NiCd
ELN4X-6-54W-W	54W	6V	White	NiCd

EL-RH

INDOOR SQUARE LED REMOTE HEAD 120-277V

CATALOG NO.	DESCRIPTION				
EL-RH1	1W per Head	3.6V/6V/9.9V/12 DC	White	Single	6-3/8"(H) x 4-1/4"(W) x 4-1/4"(D)
EL-RH2	1W per Head	3.6V/6V/9.9V/12 DC	White	Double	6-3/4"(H) x 4-1/4"(W) x 10-3/8"(D)

EL-RH-WP

WET LOCATION OUTDOOR SQUARE LED REMOTE HEAD 120-277V

CATALOG NO.	DESCRIPTION				
EL-RH1-WP	1W per Head	3.6V/6V/9.9V/12 DC	White	Single	6-3/8"(H) x 4-1/4"(W) x 4-1/4"(D)
EL-RH2-WP	1W per Head	3.6V/6V/9.9V/12 DC	White	Double	6-3/4"(H) x 4-1/4"(W) x 10-3/8"(D)

PCS-1

BG-1



BGR-1

WG-1

WG-3

POLYCARBONATE VANDAL/ENVIRONMENTAL SHIELD GUARD

CATALOG NO.	DESCRIPTION
PCS-1	For use with most standard Exit signs
BG-1	For use with most standard Exit signs
BGR-1	For use with most standard Emergency lights
WG-1	Wire Guard, 13-3/4 X 15-1/4 X 6"
WG-3	Wire Guard, 13-3/4 X 30-1/4 X 6"

ELECTRICAL

W1B SERIES


W1C SERIES

W1D SERIES


W2B SERIES


W2C SERIES

WC2 SERIES

W2D SERIES


W2X SERIES


W3 SERIES

W3D SERIES


WRB SERIES

WRC SERIES

WRE SERIES


WXB SERIES

WXF SERIES

WXR SERIES

LB SERIES


LL SERIES


LR SERIES


C SERIES

T SERIES

SLB SERIES

CG SERIES

LH150 SERIES

PL SERIES

M507CW SERIES

MS50 SERIES

GPA SERIES

GPS SERIES

EX143 SERIES

MVP98 SERIES

MVP99 SERIES

MVP94 SERIES

MVP99-360 SERIES

CH, FH & H-SCREW SERIES

Search for the series name @WESTGATEMFG.COM

YM SERIES

USB2 SERIES

EVC SERIES

MyWestgate delivers real-time stock, product data, and total control in one powerful platform!

Search for the series name @WESTGATEMFG.COM

W1B50-3

W1B50-4

W1B50-5

W1B50-5X

ONE-GANG BOXES 2" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
W1B50-3	1/2" Trade Size, 3 Outlet Holes, 18.3 Cu. In.	20
W1B50-3-WH	1/2" Trade Size, 3 Outlet Holes, 18.3 Cu. In., White	20
W1B50-3-BRZ	1/2" Trade Size, 3 Outlet Holes, 18.3 Cu. In., Bronze	20
W1B75-3	3/4" Trade Size, 3 Outlet Holes, 18.3 Cu. In.	20
W1B75-3-WH	3/4" Trade Size, 3 Outlet Holes, 18.3 Cu. In., White	20
W1B75-3-BRZ	3/4" Trade Size, 3 Outlet Holes, 18.3 Cu. In., Bronze	20
W1B100-3	1" Trade Size, 3 Outlet Holes, 18.3 Cu. In.	20
W1B50-4	1/2" Trade Size, 4 Outlet Holes, 18.3 Cu. In.	20
W1B50-4-WH	1/2" Trade Size, 4 Outlet Holes, 18.3 Cu. In., White	20
W1B50-4-BRZ	1/2" Trade Size, 4 Outlet Holes, 18.3 Cu. In.,Bronze	20
W1B75-4	3/4" Trade Size, 4 Outlet Holes, 18.3 Cu. In.	20
W1B75-4-WH	3/4" Trade Size, 4 Outlet Holes, 18.3 Cu. In., White	20
W1B75-4-BRZ	3/4" Trade Size, 4 Outlet Holes, 18.3 Cu. In., Bronze	20
W1B50-5	1/2" Trade Size, 5 Outlet Holes, 18.3 Cu. In.	20
W1B50-5-WH	1/2" Trade Size, 5 Outlet Holes, 18.3 Cu. In., White	20
W1B50-5-BRZ	1/2" Trade Size, 5 Outlet Holes, 18.3 Cu. In.,Bronze	20
W1B75-5	3/4" Trade Size, 5 Outlet Holes, 18.3 Cu. In.	20
W1B75-5-WH	3/4" Trade Size, 5 Outlet Holes, 18.3 Cu. In., White	20
W1B75-5-BRZ	3/4" Trade Size, 5 Outlet Holes, 18.3 Cu. In. Bronze	20
W1B50-5X	1/2" Trade Size, 5 Outlet Holes, 18.3 Cu. In.	20
W1B75-5X	3/4" Trade Size, 5 Outlet Holes, 18.3 Cu. In.	20

W1BC

W1BC-G

W1C-DV

W1C-GV

W1C-P020

W1C-P030

W1C-P040

W1C-SV

W1C-SW

ONE-GANG DEVICE COVERS

CATALOG NO.	DESCRIPTION	PCK QTY
W1BC	Blank Cover	50
W1BC-WH	Blank Cover, White	50
W1BC-BRZ	Blank Cover, Bronze	50
W1BC-G	Heavy Duty Galvanized Blank Cover - Gray	50
W1C-DV	Duplex, Vertical	25
W1C-DV-WH	Duplex, Vertical, White	25
W1C-DV-BRZ	Duplex, Vertical, Bronze	25
W1C-GV	Gfci, Vertical	25
W1C-GV-WH	Gfci, Vertical – White	25
W1C-GV-BRZ	Gfci, Vertical – Bronze	25
W1C-PO20	20A Receptacle, 1.60" Diameter	25
W1C-PO30	30A Receptacle, 1.75" Diameter	25
W1C-PO40	40-50A Receptacle, 2.30" Diameter	25
W1C-SV	Single Receptacle, Vertical	25
W1C-SV-WH	Single Receptacle, Vertical, White	25
W1C-SV-BRZ	Single Receptacle, Vertical, Bronze	25
W1C-SW	1 Lever, Vertical, Switch Not Included	25
W1C-SW-WH	1 Lever, Vertical, Switch Not Included	25
W1C-SW-BRZ	1 Lever, Vertical, Switch Not Included	25

W1C-TS

W1C-DH

W1C-GH

W1CL-GV

W1CL-SV

W1CL-DV

ONE-GANG DEVICE COVERS

CATALOG NO.	DESCRIPTION	PCK QTY
W1C-TS	Toggle Switch, Vertical	25
W1C-TS-WH	Toggle Switch, Vertical, White	25
W1C-TS-BRZ	Toggle Switch, Vertical, Bronze	25
W1C-DH	Duplex, Horizontal	25
W1C-GH	Gfci, Horizontal	25
W1C-GH-WH	Gfci, Horizontal – White	25
W1C-GH-BRZ	Gfci, Horizontal – Bronze	25
W1CL-DV	Lockable 1 Gang W/P Cover 1 Si	25
W1CL-GV	Lockable 1 Gang W/P Device Cov	25
W1CL-SV	Lockable 1 Gang W/P Cover 1 Si	25
W1C-SH	Single Receptacle Horizontal	25

W1DB50-3

W1DB50-4

W1DB50-5X

ONE-GANG BOXES 2-5/8" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
W1DB50-3	1/2" Trade Size, 3 Outlet Holes, 23.8 Cu. In.	12
W1DB75-3	3/4" Trade Size, 3 Outlet Holes, 23.8 Cu. In.	12
W1DB100-3	1" Trade Size, 3 Outlet Holes, 23.8 Cu. In.	12
W1DB50-4	1/2" Trade Size, 4 Outlet Holes, 23.8 Cu. In.	12
W1DB75-4	3/4" Trade Size, 4 Outlet Holes, 23.8 Cu. In.	12
W1DB50-5X	1/2" Trade Size, 5 Outlet Holes, 23.8 Cu. In.	12
W1DB75-5X	3/4" Trade Size, 5 Outlet Holes, 23.8 Cu. In.	12
W1DB100-5X	1" Trade Size, 5 Outlet Holes, 23.8 Cu. In	12

W2B50-3

W2B50-4

W2B50-5X

W2B50-6X

W2B50-7

W2B50-7X

TWO-GANG STANDARD BOXES 2" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
W2B50-3	1/2" Trade Size, 3 Outlet Holes, 30.5 Cu. In.	12
W2B75-3	3/4" Trade Size, 3 Outlet Holes, 30.5 Cu. In.	12
W2B100-3	1" Trade Size, 3 Outlet Holes, 30.5 Cu. In.	12
W2B50-4	1/2" Trade Size, 4 Outlet Holes, 30.5 Cu. In.	12
W2B75-4	3/4" Trade Size, 4 Outlet Holes, 30.5 Cu. In.	12
W2B100-4	1" Trade Size, 4 Outlet Holes, 30.5 Cu. In.	12
W2B50-5	1/2" Trade Size, 5 Outlet Holes, 30.5 Cu. In.	12
W2B75-5	3/4" Trade Size, 5 Outlet Holes, 30.5 Cu. In.	12
W2B50-5X	1/2" Trade Size, 5 Outlet Holes, 30.5 Cu. In.	12
W2B75-5X	3/4" Trade Size, 5 Outlet Holes, 30.5 Cu. In.	12
W2B100-5X	1" Trade Size, 4 Outlet Holes, 30.5 Cu. In.	12
W2B50-6X	1/2" Trade Size, 6 Outlet Holes, 30.5 Cu. In.	12
W2B75-6X	3/4" Trade Size, 6 Outlet Holes, 30.5 Cu. In.	12
W2B50-7	1/2" Trade Size, 7 Outlet Holes, 30.5 Cu. In.	12
W2B75-7	3/4" Trade Size, 7 Outlet Holes, 30.5 Cu. In.	12
W2B50-7X	1/2" Trade Size, 7 Outlet Holes, 30.5 Cu. In.	12
W2B75-7X	3/4" Trade Size, 7 Outlet Holes, 30.5 Cu. In.	12
W2B50-9	1/2" Trade Size, 9 Outlet Holes, 30.5 Cu. In.	12
W2B75-9	3/4" Trade Size, 9 Outlet Holes, 30.5 Cu. In	12

W2BC

W2BC-G

W2C-2D



W2C-2G

W2C-2S

W2C-GD

W2C-GS

W2C-SD

W2C-SW

W2CL-P050

W2CL-P060

W2C-DH

TWO-GANG DEVICE COVERS

CATALOG NO.	DESCRIPTION	PCK QTY
W2BC	2 Gang Weatherproof Blank Cove	25
W2BC-WH	2 Gang Weatherproof Blank Cove, White	25
W2BC-BRZ	2 Gang Weatherproof Blank Cove, Bronze	25
W2C-2D	2 Duplex Receptacles	12
W2BC-G	Heavy Duty Galvanized Blank Cover	25
W2C-2G	2 Gfci Receptacles	12
W2C-2S	2 Single Receptacles 1.406" Diameter	12
W2C-GD	1 Gfci & 1 Duplex Receptacle	12
W2C-GS	1 Gfci & 1 Single Receptacle	12
W2C-SD	1 Duplex & 1 Single Receptacle 1.41" Diameter	12
W2C-SW	2 Levers + 2-15A Single Pole Switches -Not Included	12
W2CL-PO50	40-50A Receptacle, 2.125" Diameter, Lockable	12
W2CL-PO60	60A Receptacle, 2.468" Diameter, Lockable	12
W2C-DH	Over-Sized Duplex, Horizontal	12

SERVICE ENTRANCE CAPS

CATALOG NO.	DESCRIPTION	PCK QTY
WC2-50	Service Entrance Caps, Die-Cas	15
WC2-75	Service Entrance Caps, Die-Cas	10
WC2-100	Service Entrance Caps, Die-Cas	7
WC2-125	Service Entrance Caps, Die-Cas	5
WC2-150	Service Entrance Caps, Die-Cas	4
WC2-200	Service Entrance Caps, Die-Cas	4
WC2-250	Service Entrance Caps, Die-Cas	1
WC2-300	Service Entrance Caps, Die-Cas	1
WC2-350	Service Entrance Caps, Die-Cas	1
WC2-400	Service Entrance Caps, Die-Cas	1

W2DB50-5

W2DB50-7X

TWO-GANG DEEP BOXES 2-5/8" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
W2DB50-5	1/2" Trade Size, 5 Outlet Holes, 40.3 Cu. In.	9
W2DB75-5	3/4" Trade Size, 5 Outlet Holes, 40.3 Cu. In.	9
W2DB100-5	1" Trade Size, 5 Outlet Holes, 40.3 Cu. In.	9
W2DB50-7X	1/2" Trade Size, 7 Outlet Holes, 40.3 Cu. In.	9
W2DB75-7X	3/4" Trade Size, 7 Outlet Holes, 40.3 Cu. In.	9
W2DB100-7X	1" Trade Size, 7 Outlet Holes, 40.3 Cu. In.	9

TWO-GANG EXTENSION BOXES 1-9/16" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
W2XB50-6	1/2" Trade Size, 6 Outlet Holes, 15.0 Cu. In.	9
W2XB75-6	3/4" Trade Size, 6 Outlet Holes, 15.0 Cu. In.	9
W2XB50-8	1/2" Trade Size, 8 Outlet Holes, 15.0 Cu. In.	9
W2XB75-8	3/4" Trade Size, 8 Outlet Holes, 15.0 Cu. In.	9

W3BC

W3C-3S

W3C-3D



W3C-3G

THREE-GANG DEVICE COVER

CATALOG NO.	DESCRIPTION	PCK QTY
W3BC	Blank Cover	7
W3C-3D	3 Duplex Receptacles	7
W3C-3G	3 Gfci Receptacles	7
W3C-3S	3 Single 1.41" Diameter Receptacles	7

W3DB50-7

THREE-GANG DEEP BOXES 2-5/8" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
W3DB50-7	1/2" Trade Size, 7 Outlet Holes, 54.0 Cu. In.	10
W3DB75-7	3/4" Trade Size, 7 Outlet Holes, 54.0 Cu. In.	10
W3DB100-7	1" Trade Size, 7 Outlet Holes, 54.0 Cu. In	10

WRB50-5

ROUND EXTENSION BOXES 4" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
WRB50-5	1/2" Trade Size, 5 Outlet Holes, 15.8 Cu. In.	16
WRB50-5-WH	1/2" Trade Size, 5 Outlet Holes, 15.8 Cu. In., White	16
WRB50-5-BRZ	1/2" Trade Size, 5 Outlet Holes, 15.8 Cu. In., Bronze	16
WRB50-5-BK	1/2" Trade Size, 5 Outlet Holes, 15.8 Cu. In., Black	16
WRB75-5	3/4" Trade Size, 5 Outlet Holes, 54.0 Cu. In	16

WRC-1

WRC-2

WRC-3

W4RBC

ROUND COVERS 4" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
WRC-1	1/2" Trade Size, 1 Outlet Holes	25
WRC-1-WH	1/2" Trade Size, 1 Outlet Holes, White	25
WRC-1-BRZ	1/2" Trade Size, 1 Outlet Holes, Bronze	25
WRC-1-BK	1/2" Trade Size, 1 Outlet Holes, Black	25
WRC-2	1/2" Trade Size, 2 Outlet Holes	25
WRC-2-WH	1/2" Trade Size, 2 Outlet Holes, White	25
WRC-2-BRZ	1/2" Trade Size, 2 Outlet Holes, Bronze	25
WRC-2-BK	1/2" Trade Size, 2 Outlet Holes, Black	25
WRC-3	1/2" Trade Size, 3 Outlet Holes	25
WRC-3-WH	1/2" Trade Size, 3 Outlet Holes,White	25
WRC-3-BRZ	1/2" Trade Size, 3 Outlet Holes, Bronze	25
WRC-3-BK	1/2" Trade Size, 3 Outlet Holes, Black	25
W4RBC	4" Round Blank Cover With Gasket	50

ONE-GANG RECTANGULAR COVERS

CATALOG NO.	DESCRIPTION	PCK QTY
WRE-1	1/2" Trade Size, 1 Outlet Holes	25
WRE-1-WHT	1/2" Trade Size, 1 Outlet Holes,White	25
WRE-1-BRZ	1/2" Trade Size, 1 Outlet Holes, Bronze	25
WRE-2	1/2" Trade Size, 2 Outlet Holes	25
WRE-2-WHT	1/2" Trade Size, 2 Outlet Holes, White	25
WRE-2-BRZ	1/2" Trade Size, 2 Outlet Holes, Bronze	25
WRE-3	1/2" Trade Size, 3 Outlet Holes	25
WRE-3-WH	1/2" Trade Size, 3 Outlet Holes, White	25
WRE-3-BRZ	1/2" Trade Size, 3 Outlet Holes, Bronze	25

WXB50-4



WXB50-6

ONE-GANG EXTENSION BOXES 1-3/8" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
WXB50-4	1/2" Trade Size, 4 Outlet Holes, 9.5 Cu. In.	12
WXB75-4	3/4" Trade Size, 4 Outlet Holes, 9.5 Cu. In.	12
WXB50-6	1/2" Trade Size, 6 Outlet Holes, 9.5 Cu. In	12
WXB75-6	3/4" Trade Size, 6 Outlet Holes, 9.5 Cu. In.	12

WXF50-4

WXF50-6

ONE-GANG FLANGED EXTENSION BOXES 1-9/16" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
WXF50-2	1/2" Trade Size, 2 Outlet Holes, 13.5 Cu. In.	10
WXF75-2	3/4" Trade Size, 2 Outlet Holes, 13.5 Cu. In.	10
WXF50-4	1/2" Trade Size, 4 Outlet Holes, 13.5 Cu. In.	10
WXF75-4	3/4" Trade Size, 4 Outlet Holes, 13.5 Cu. In.	10
WXF50-6	1/2" Trade Size, 6 Outlet Holes, 13.5 Cu. In.	10
WXF75-6	3/4" Trade Size, 6 Outlet Holes, 13.5 Cu. In	10

WXR-1

WXR-2

WXR50-4

WRC-GASKET

ONE-GANG FLANGED EXTENSION RING 1" DEEP

CATALOG NO.	DESCRIPTION	PCK QTY
WXR-1	1 Gang W/P Extension Ring	24
WXR-2	2 Gang W/P Extension Ring	12
WXR50-4	4" Round W/P Ext. Box 4 1/2" H	16
WXR75-4	4" Round W/P Ext. Box 4 3/4" H	16
WRC-GASKET	Universal 1-Gang Foam Gasket	25

THREADED CONDUIT BODIES LB SERIES

CATALOG NO.	DESCRIPTION				PCK QTY
LB-50CG	1/2"	4-5/16"	1-5/16"	2-1 1/32"	10
LB-75CG	3/4"	5-3/32"	1-9/16"	2-5/8"	10
LB-100CG	1"	5-29/32"	1-13/16"	3"	5
LB-125CG	1-1/4"	7-13/16"	2-1/2"	3-3/4"	2
LB-150CG	1-1/2"	7-13/16"	2-1/2"	3-3/4"	2
LB-200CG	2"	10-1/16"	3-3/16"	4-3/4"	1
LB-250CG	2-1/2"	12-13/16" 12-	4-1/2"	5-9/16"	1
LB-300CG	3"	13/16"	4-1/2"	6-5/32""	1
LB-400CG	4"	15-5/8"	5-9/16"	7-9/16"	1

THREADED CONDUIT BODIES LL SERIES

CATALOG NO.	DESCRIPTION				PCK QTY
LL-50CG	1/2"	4-5/16"	2-1/32"	1-5/8"	10
LL-75CG	3/4"	5-3/32"	2-5/16"	1-7/8"	10
LL-100CG	1"	5-29/32"	2-11/16"	2-1/8"	5
LL-125CG	1-1/4"	7-13/16"	3-1/2"	2-3/4"	2
LL-150CG	1-1/2"	7-13/16"	3-1/2"	2-3/4"	2
LL-200CG	2"	10-1/16"	4-9/32"	3-5/8"	1
LL-250CG	2-1/2"	12-13/16" 12-	5-7/8"	4-1/4"	1
LL-300CG	3"	13/16"	5-7/8"	4-3/4"	1
LL-400CG	4"	15-5/8"	7-21/32"	5-7/8"	1



THREADED CONDUIT BODIES LR SERIES

CATALOG NO.	DESCRIPTION				PCK QTY
LR-50CG	1/2"	4-5/16"	2-1/32"	1-5/8"	10
LR-75CG	3/4"	5-3/32"	2-5/16"	1-7/8"	10
LR-100CG	1"	5-29/32"	2-11/16"	2-1/8"	5
LR-125CG	1-1/4"	7-13/16"	3-1/2"	2-3/4"	2
LR-150CG	1-1/2"	7-13/16"	3-1/2"	2-3/4"	2
LR-200CG	2"	10-1/16"	4-9/32"	3-5/8"	1
LR-250CG	2-1/2"	12-13/16" 12-	5-7/8"	4-1/4"	1
LR-300CG	3"	13/16"	5-7/8"	4-3/4"	1
LR-400CG	4"	15-5/8"	7-21/32"	5-7/8"	1

THREADED CONDUIT BODIES C SERIES

CATALOG NO.	DESCRIPTION				PCK QTY
C-50CG	1/2"	4-11/16"	1-5/16"	1-5/8"	10
C-75CG	3/4"	5-1/2"	1-9/16"	1-7/8"	10
C-100CG	1"	6-7/16"	1-13/16"	2-1/8"	5
C-125CG	1-1/4"	8-3/8"	2-1/2"	2-3/4"	2
C-150CG	1-1/2"	8-3/8"	2-1/2"	2-3/4"	2
C-200CG	2"	10-9/16"	3-3/16"	3-5/8"	1
C-250CG	2-1/2"	13-1/2"	4-1/2"	4-1/4"	1
C-300CG	3"	13-1/2"	4-1/2"	4-3/4"	1
C-400CG	4"	16-5/16"	5-9/16"	5-7/8"	1

THREADED CONDUIT BODIES T SERIES

CATALOG NO.	DESCRIPTION				PCK QTY
T-50CG	1/2"	4-11/16"	2-1/32"	1-5/8"	10
T-75CG	3/4"	5-1/2"	2-5/16"	1-7/8"	10
T-100CG	1"	6-7/16"	2-11/16"	2-1/8"	5
T-125CG	1-1/4"	8-3/8"	3-1/2"	2-3/4"	2
T-150CG	1-1/2"	8-3/8"	3-1/2"	2-3/4"	2
T-200CG	2"	10-9/16"	4-9/32"	3-5/8"	1
T-250CG	2-1/2"	13-1/2"	5-7/8"	4-1/4"	1
T-300CG	3"	13-1/2"	5-7/8"	4-3/4"	1
T-350CG	3-1/2"	16-5/16"	7-21/32"	5-7/8"	1
T-400CG	4"	16-5/16"	7-21/32"	5-7/8"	1

THREADED CONDUIT BODIES SLB SERIES

CATALOG NO.	DESCRIPTION				PCK QTY
SLB-50	1/2"	3-9/32"	1-3/8"	1-5/8"	20
SLB-75	3/4"	3-19/32"	1-9/16"	1-27/32"	20
SLB-100	1"	4-5/16"	1-31/32"	2-1/8"	10

COVERS & GASKETS FOR THREADED CONDUIT BODIES

CATALOG NO.	DESCRIPTION				PCK QTY
CG-50	1/2"	3-7/8"	1-5/16"	-	
CG-75	3/4"	4-11/16"	1-9/16"	-	50
CG-100	1	5-3/8"	1-3/4"	-	50
CG-125/150	1-1/4" &	7-5/16"	2-1/2"	-	25
CG-200	1-1/2"	9-1/2"	3-1/8"	-	10
CG-250/300	2"	12-1/16"	4-7/16"	-	10
CG-350/400	2-1/2"	15-1/16"	5/9/2016"	-	5

LH150-1

LAMP HOLDERS

CATALOG NO.	DESCRIPTION	PCK QTY
LH150-1	Standard Weatherproof Lamp Holder	20
LH150-1-WH	Standard Weatherproof Lamp Holder, Bronze	12
LH150-GASKET	Silicon Gasket For Lh150	20

PL-50

LAMP HOLDERS

CATALOG NO.	DESCRIPTION	PCK QTY
PL-50	Close-Up Plug 1/2" - 50 Per Ba	500 per bag
PL-50-BRZ	Close-Up Plug 1/2" - 50 Per Ba, Bronze	500 per bag
PL-50-WH	Close-Up Plug 1/2" - 50 Per Ba, White	500 per bag
PL-75	Close-Up Plug 3/4" - 50 Per Ba	500 per bag
PL-100	Close-Up Plug 1" - 50 Per Bag	200 per bag

M507CW-UL

PORCELAIN LAMP HOLDERS

CATALOG NO.	DESCRIPTION	PCK QTY
M507CW-UL	E26, Porcelain Lampholder With Pull Chain, 2 Terminal Screws, 660W/250V Rating, White	48

MS507C-UL

PLASTIC LAMP HOLDERS

CATALOG NO.	DESCRIPTION	PCK QTY
MS507C-UL	E26, Bakelite Keyless Lampholder With 2 Terminal Screws, 660W/250V Rating, White	108
MS507CW-UL	E26, Bakelite Lampholder With Pull Chain, 2 Terminal Screws, 660W/250V Rating, White	108

GPA3-2

ANGLE PLUG, GENERAL PURPOSE CORDS 125V-13A GRAY

CATALOG NO.	DESCRIPTION	PCK QTY
GPA3-2	Spt-2 16Awg/ 3 Conductor, Angle Plug, Nema 5-15P, 125V, Gray, 3Ft	100
GPA6-2	Spt-2 16Awg/ 3 Conductor, Angle Plug, Nema 5-15P, 125V, Gray, 6Ft	100
GPA8-2	Spt-2 16Awg/ 3 Conductor, Angle Plug, Nema 5-15P, 125V, Gray, 8Ft	100

GPS3-2

STRAIGHT PLUG, GENERAL PURPOSE CORDS 125V-13A GRAY

CATALOG NO.	DESCRIPTION	PCK QTY
GPS3-2	Spt-2 16Awg/ 3 Conductor, Straight Plug, Nema 5-15P, 125V, Gray, 3Ft	100
GPS6-2	Spt-2 16Awg/ 3 Conductor, Straight Plug, Nema 5-15P, 125V, Gray, 6Ft	100
GPS8-2	Spt-2 16Awg/ 3 Conductor, Straight Plug, Nema 5-15P, 125V, Gray, 8Ft	100



EX143-50

STRAIGHT PLUG WITH VINYL INSULATION

CATALOG NO.	DESCRIPTION	PCK QTY
EX143-50	Replacement Cords For Range Or Dryer	

MVP98

DIRECTIONAL ARMORED GROUND CLAMP WITH STEEL SCREWS

CATALOG NO.	DESCRIPTION	PCK QTY
MVP98	Trade Size 1/2"- 1" Wire Size 4-6-8	100

MVP99

FEED-THROUGH ARMORED GROUND CLAMP WITH STEEL SCREWS

CATALOG NO.	DESCRIPTION	PCK QTY
MVP99	Trade Size 1/2"- 1" Wire Size 4-6-8,	100

MVP94

FEED-THROUGH ARMORED GROUND CLAMP WITH STEEL SCREWS

CATALOG NO.	DESCRIPTION	PCK QTY
MVP94-50	1/2" Feed-Through Armored Ground Clamp	100
MVP94-75	3/4" Feed-Through Armored Ground Clamp	100



MVP99-360-1C

MVP99-360-2C

FEED-THROUGH ARMORED GROUND CLAMP WITH CABLE ADAPTOR

CATALOG NO.	DESCRIPTION	PCK QTY
MVP99-360-1C	Trade Size 1/2"- 1" Wire Size 4-6-8, Master 80 With 1 Armored Cable Adaptor	80
MVP99-360-2C	Trade Size 1/2"- 1" Wire Size 4-6-8, Master 80 With 2 Armored Cable Adaptor	80

CH-1212

FH-E

H-SCREW

FH-S

STEEL JACK CHAIN & FIXTURE HANGER

CATALOG NO.	DESCRIPTION
CH-1212	Steel Jack Chain, 100Ft., 12Ga, (Meets Weight Requirements For Linear High Bays)
CH-1010	Steel Jack Chain, 100Ft., 10Ga
FH-S	Side Mount Steel Fixture Hangers, 10Ga
FH-E	End Mount Steel Fixture Hangers, 10Ga
H-SCREW	Steel Flat Hanger Screw With Single Hole, 1/4" X 3"

YM183-W

YM2108-T-W

YM2108-W

OCCUPANCY/VACANCY SENSORS

CATALOG NO.	DESCRIPTION
YM183-W	Occupancy Pir Sensor, 180°, 30Ft (720Ft), 120V 800/1200W Max, Single Pole, Neutral Req.
YM2108-W	Vacancy & Occupancy Pir Sensor, 180°, 30Ft (720Ft), 120V 800/1200W Max, Single Pole, Neutral Req.
YM2108-T-W	Vacancy & Occupancy Pir Sensor, 180°, 25Ft (600Ft), 120V 600/1000W Max, 3-Way, Neutral Req.

USB2-15TR

USB2-20TR

2 VERTICAL USB PORT 5V DC

CATALOG NO.	DESCRIPTION
USB2-15TR-WH	15A Receptacle W/2 Usb Ports
USB2-20TR-WH	20A Receptacle W/2 Usb Ports

EVC-A-48A-MP-BT

EVC-PEDESTAL-4.5FT

EVC-C-40A-AC-9.6KW-J1772
EVC-C-48A-AC-11.5KW-J1772

SAE-J1772
Connector

EVC-FM-48A-AC-11.5KWX2-J177

EV CHARGER, AC POWER 120-240V, SAE J1772 CONNECTOR

CATALOG NO.	DESCRIPTION
EVC-A-48A-MP-BT	Level 2 48A, 11.5KW, Selectable Power, Westgate App Enabled
EVC-A-40A-AC-9.6KW-J1772	Level 2, 40A, 9.6KW, Wall Mount
EVC-A-48A-AC-11.5KW-J1772	Level 2, 48A, 11.5KW, Wall Mount
EVC-C-40A-AC-9.6KW-J1772	Level 2, 40A, 9.6KW, Wall Mount
EVC-C-48A-AC-11.5KW-J1772	Level 2, 48A, 11.5KW, Wall Mount
EVC-FM-48A-AC-11.5KWX2-J1772	Level 2, 48AX2, 11.5KWX2, WiFi+LAN+4G POS integ. (CC payments)
EVC-PEDESTAL-4.5FT	4.5FT Pedestal Accessory

FACTORY-INSTALLED OPTIONS, ENTER DESIRED OPTION CODE(S) AS LINE ITEMS ON YOUR PURCHASE ORDER UNDER THE PRODUCT CATALOG NUMBER

WATTS	APP OPTION	DESCRIPTION	4G OPTION	DESCRIPTION
ALL	**OPT-EVC-APP**	Single-User Smart Bluetooth App-Enabled	**OPT-EVC-FM-4G**	Integrated 4G, Built-in cellular for remote access
	POWDER COATING		**POS OPTION**	DESCRIPTION
	N/A		**OPT-EVC-FM-POS**	Integrated POS, Built-in payment system for easy, secure transactions on-site

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LWAX-SM

LWAX-LG

LWAX-MD

LWAX-SM-WH

POWER & CCT-ADJUSTABLE CUTOFF WALL PACK, 120-277V TYPE 2 LENS

CATALOG NO.	DESCRIPTION		
LWAX-SM-12W-50K	12W	1500LM	5000K
LWAX-MD-30W-30K	30W	3900LM	3000K
LWAX-MD-30W-50K	30W	3900LM	5000K
LWAX-SM-12W-30K-WH	12W	1500LM	3000K

LED ADJUSTABLE CUTOFF WALL PACK, 120-277V

CATALOG NO.	DESCRIPTION		
LWA-120NW	120W	13700LM	4000K
LWA-20WW	20W	2000LM	3000K

LED CUTOFF WALL PACK, 120-277V

CATALOG NO.	DESCRIPTION		
LWP-22CW	22W	2000LM	5000K
LWP-80CW	80W	7900LM	5000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LW360-25W-30K-WH

LW360-60W-30K LW360-80W-30K

LED ROTATABLE WALL PACKS, 120-277V

CATALOG NO.	DESCRIPTION		
LW360-25W-MCT-G2	25W	3250LM	30K/40K/50K - Bronze
LW360-60W-40K	60W	8100LM	4000K
LW360-60W-30K	60W	8100LM	3000K
LW360-80W-30K	80W	10800LM	3000K
LW360-80W-40K	80W	10800LM	4000K
LW360-25W-30K-WH	25W	3375LM	3000K

LED NON-CUTOFF WALL PACKS, 120-277V

CATALOG NO.	DESCRIPTION		
WML-HL-100W-30K	100W	14800LM	3000K
WML-HL-30W-30K	30W	4200LM	3000K
WML-HL-50W-50K	50W	7100LM	5000K
WML-HL-60W-30K	60W	8700LM	3000K
WML-HL-80W-30K	80W	11600LM	3000K
WML-HL-80W-50K	80W	11600LM	5000K

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST



SHIELD FOR WML 30W

CATALOG NO.	DESCRIPTION
WML-SH1	Shield For WML 30W

LED NON-CUTOFF WALL PACKS WITH DIRECTIONAL OPTIC LENS

CATALOG NO.	DESCRIPTION		
WML2-28W-50K-HL-SM-D	28W	3500LM	5000K
WML2-50W-30K-HL	48W	6000LM	3000K
WML2-50W-30K-SM	50W	5500LM	3000K
WML2-120W-30K-HL-LG	120W	15000LM	3000K

LED SMALL NON-CUTOFF WALL PACK WITH PHOTOCELL, 120V

CATALOG NO.	DESCRIPTION		
LESW-12W-30K-P	12W	1225LM	3000K

LED SMALL (11") WALL PACK WITH PHOTOCELL 120-277V TYPE 2 LENS

CATALOG NO.	DESCRIPTION		
LSWX-20W-30K-PC	20W	2450LM	3000K - Bronze

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LFX-XXL DARK BRONZE

LFX-LG

LFX-XL

SPEC SERIES POWER-ADJUSTABLE AREA LIGHT, TYPE 3 LENS

CATALOG NO.	DESCRIPTION		
LFX-LG-50-150W-30K	50W/80W/100W/150W	140LM/W	3000K
LFX-LG-50-150W-40K	50W/80W/100W/150W	140LM/W	4000K
LFX-XL-150-300W-30K	150W/200W/240W/300W	145LM/W	3000K
LFX-XL-150-300W-40K	150W/200W/240W/300W	145LM/W	4000K
LFX-XXL-300-600W-50K	300W/400W/500W/600W	140LM/W	5000K
LFX-XXL-300-600W-50K-480V	300W/400W/500W/600W	140LM/W	5000K

SPEC SERIES POWER & CCT ADJUSTABLE ARCHITECTURAL ROUND-BACK FLOOD LIGHT, 120-277V

CATALOG NO.	DESCRIPTION		
LF4PRO-50-150W-MCTP	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K

LED FLOOD LIGHTS LF3 SERIES WITH KNUCKLE, 120~277V (NOT DIMMABLE)

CATALOG NO.	DESCRIPTION		
LF-55WW-KN	55W	4500LM	3000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LF2 ARCHITECTURAL FLOOD LIGHTS, 120-277V

CATALOG NO.	DESCRIPTION		
LF2-10CW-TR	10W	942LM	5000K
LF2-10WW-TR	10W	900LM	3000K
LF2-80WW-TR	80W	6282LM	3000K

12V LED GARDEN LIGHT

CATALOG NO.	DESCRIPTION		
LF12-6NW	6W	450LM	4000K
LF12-20WW	20W	1330LM	3000K
LF12-30CW	30W	2000LM	5000K
LF12-50WW	50W	3330LM	3000K
LF12-6W-RGBW-KN	6W	450LM	RGB + 3000K - KNUCKLE

LED FLOOD LIGHTS LF3 SERIES w/ SLIP FITTER, 120~277V

CATALOG NO.	DESCRIPTION		
LF3-80WW-SF	80W	9600LM	3000K
LF3-300WW-SF	300W	30800LM	3000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED FLOOD LIGHTS LF3 SERIES WITH U BRACKET, 120~277V (NOT DIMMABLE)

CATALOG NO.	DESCRIPTION		
LF3-WH-30WW-TR	30W	3600LM	3000K
LF3-30WW-TR	30W	3600LM	3000K
LF3-30NW-TR	30W	3600LM	4000K
LF3-50NW-TR	50W	6100LM	4000K
LF3-100WW-TR	100W	10000LM	3000K

LED FLOOD LIGHTS LF3 SERIES WITH YOKE, 120~277V

CATALOG NO.	DESCRIPTION		
LF3-150WW -YK	150W	20680LM	3000K
LF3-300CW-YK	300W	39000LM	5000K



LED FLOOD LIGHTS LF3 SERIES, 120~277V

CATALOG NO.	DESCRIPTION		
LF3-HL-80W-40K-D	80W	10400LM	4000K
LF3-HL-100W-30K	100W	13000LM	3000K
LF3-HL-150W-30K	150W	19700LM	3000K
LF3-HL-300W-40K	300W	39000LM	4000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST



LED FLOOD LIGHTS LF3 SERIES, 480V

CATALOG NO.	DESCRIPTION		
LF3-HL-100W-40K-480V	100W	13200LM	4000K
LF3-HL-100W-50K-480V	100W	13200LM	5000K
LF3-HL-150W-40K-480V	150W	20680LM	4000K
LF3-HL-230W-40K-480V	230W	31000LM	4000K

LED FLOOD LIGHTS LF3 SERIES, 120~277V

CATALOG NO.	DESCRIPTION		
LF3-HL-80W-40K-TR	80W	10700LM	4000K
LF3-HL-100W-30K-TR	100W	13000LM	3000K
LF3-HL-300W-50K-TR	300W	39000LM	5000K

ACCESSORIES FOR LF3 HL CSERIES

CATALOG NO.	DESCRIPTION
LF3-EXTARM	STRAIGHT EXTENSTION ARM FOR SHOE BOX APPLICATION, WITH K/O TO INSTALL PC OR SENSOR (LF3-80~300)
LF3-HL-ASA	ADJUSTABLE STRAIGHT ARM FOR LF3-HL SERIES
LF3-HL-EXT	STRAIGHT EXTENSTION ARM FOR SHOE BOX APPLICATION
LF3-HL-PMR2	ROUND POLE MOUNT FOR LF3-HL-300W
LF3-HL-PMS1	SQUARE POLE MOUNT FOR LF3-HL-80W/100W/150W
LF3-HL-RSF	ROUND SLIP FITTER FOR LF3-HL SERIES
LF3-HL-SF	ADJUSTABLE SLIP FITTER FOR POLE MOUNT
LF3-HL-FSF	
LF3-HL-PK2	
LF3-HL-RA	
LF3-HL-TR-230/300W	U BRACKET FOR LF3-HL-230W&300W

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

LF3-HL-TR-80/100/150W	U BRACKET FOR LF3-HL-80W,100W, AND 150W.
LF3-HL-YK-100W/150W/230W	ADJUSTABLE U SHAPE YOKE MOUNT FOR LF3-HL-100W/150W/230W
LF3-HL-YK-300W	ADJUSTABLE U SHAPE YOKE MOUNT FOR LF3-HL-300W
LF3-HL-TYPEII-150W/230W/300W	TYPE 2 LENS FOR LF3-HL SERIES LF3-HL 150W/230W/300W (ORDER 2)
LF3-HL-TYPEIII-100W	TYPE 3 LENS FOR LF3-HL SERIES 100W (ORDER 2)
LF3-HL-TYPEIII-150W/230W/300W	TYPE 3 LENS FOR LF3-HL SERIES LF3-HL 150W/230W/300W (ORDER 2)
LF3-HL-TYPEIV-100W	TYPE 4 LENS FOR LF3-HL SERIES 100W (ORDER 2)
LF3-HL-TYPEIV-150W/230W/300W	TYPE 4 LENS FOR LF3-HL SERIES LF3-HL 150W/230W/300W (ORDER 2)

LF3 ACCESSORIES

CATALOG NO.	DESCRIPTION
LF3-SH4FG	FULL-GLARE SHROUD FOR LF3-HL-230W
LF3-SH5	SHROUD FOR LF3-220W/300W
LF3-EXTARM	STRAIGHT EXTENSTION ARM FOR SHOE BOX APPLICATION, WITH K/O TO INSTALL PC OR SENSOR (LF3-80~300)
LF3-STR	STREET LIGHT ARM 6" LONG WITH 20" WIRE AND STRAIN RELIEF CONNECTOR (LF3-80~300)
LF3-TR	TRUNNION BRACKET FOR LF3 SERIES
LF3-SF	ADJUSTABLE SLIP FITTER FOR POLE MOUNT 2"~2-1/2", WITH K/O TO INSTALL PC OR SENSOR (LF3-80~300)
LF3-PK	
LF3-WMA	WALL MOUNTING PLATE FOR LF3 AN
LF3-WG3	WIRE GUARD FOR LF3-HL-80W/100W
LF3-WG4	WIRE GUARD FOR LF3-HL-230W
LF3-WG5	WIRE GUARD FOR LF3-HL-300W
LF3-YOK	ADJUSTABLE U SHAPE YOKE MOUNT 5"L X 4"H WITH 20" WIRE & STRAIN RELIEF CON. (LF3-80~300)
LF3-TYPEIII-150W/300W	TYPE 3 LENS FOR LF3 SERIES - FITS 150W & 300W FIXTURES - ONE LENS PANEL
LF3-TYPEIII-80W/100W/220W	TYPE 3 LENS FOR LF3 SERIES - FITS 80W & 100W & 220W FIXTURES - ONE LENS PANEL
LF3-TYPEIV-150W/300W	TYPE 4 LENS FOR LF3 SERIES - FITS 150W & 300W FIXTURES - ONE LENS PANEL
LF3-TYPEIV-80W/100W/220W	TYPE 4 LENS FOR LF3 SERIES - FITS 80W & 100W & 220W FIXTURES - ONE LENS PANEL

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

COMPACT FLOOD LIGHTS

CATALOG NO.	DESCRIPTION		
LFE-80W-MCT-D	80W	10500LM	3000K/4000K/5000K
LFE-100W-MCT-D	100W	13000LM	3000K/4000K/5000K
LFE-15W-MCT-TR	15W	1600LM	3000K/4000K/5000K
LFE-30W-MCT-TR	30W	3250LM	3000K/4000K/5000K
LFE-50W-MCT-TR	50W	5250LM	3000K/4000K/5000K
LF4-12CW-KN	12W	1300LM	5000K
LF4-30WW-TR	30W	3100LM	3000K
LF4-100CW-TR	100W	11200LM	5000K
LF4-12WW-TR	12W	1240LM	3000K

SHROUD FOR LF4 SERIES

CATALOG NO.	DESCRIPTION
LF4-SH4	Shroud For Lf4 Series (Bronze) Fits Lf4-80W & 100W (Cast Aluminum)
LF4-SH5	Shroud For Lf4 Series (Bronze) Fits Lf4-150W (Cast Aluminum)

ECONOMY FLOOD/AREA LIGHT SERIES TYPE 3 LENSES

CATALOG NO.	DESCRIPTION		
LFCO-80W-40K	80W	10800LM	4000K
LFCO-80W-50K	80W	10800LM	5000K
LFCO-TR1	"U" Bracket For 80W 100W 150W		
LFCO-TR2	"U" Bracket For 300W		
LFCO-SA			
LFCO-SF			

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED BULLET FLOOD LIGHTS w/ 1/2" KNUCKLE (1st Gen.)

CATALOG NO.	DESCRIPTION		
FLD-12WW-WH	12W	800LM	3000K
FLD-12CW-GRN	12W	800LM	5000K
FLD-30WW	30W	2450LM	3500K
FLD-30CW-WH	30W	2500LM	5000K
FLD-30WW-WH	30W	2450LM	3000K
FLD-30CW-GRN	30W	2500LM	5000K
FLD-30WW-GRN	30W	2450LM	3000K

SHROUD FITS FLD2-50W

CATALOG NO.	DESCRIPTION
FL-SH4	POLYCARBONATE SHROUD (BRONZE) FITS FLD2-50W

12V INTEGRATED LED LANDSCAPE UPLIGHTS

CATALOG NO.	DESCRIPTION		
LFLV-7W-27K	7W	500LM	2700K
LFLV-7W-40K	7W	550LM	4000K

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

LED GARDEN POST LIGHT, 100-277V

CATALOG NO.	DESCRIPTION		
LGP-100W-30K	100W	12000LM	3000K
LGP-A2	Auxiliary Second Arm		
LGP-EXTARM	External Arm for LGP		

HAZARDOUS LOCATION CLASS 1 DIV. 2 FLOOD LIGHT

CATALOG NO.	DESCRIPTION		
EXPF-180W-60K	180W	20700LM	6000K

SL-20W-BZ-P
Dark Bronze

SL-20W-WH-P
White

SL-30W-BZ-P
Dark Bronze

SL-30W-WH-P
White

PHOTOCELL SECURITY LIGHTS

CATALOG NO.	DESCRIPTION		
SL-20W-30K-BZ-P	20W	1900LM	3000K - Bronze
SL-20W-30K-WH-P	20W	1900LM	3000K - White
SL-20W-50K-BZ-P	20W	1900LM	5000K - Bronze
SL-30W-30K-BZ-P	30W	2800LM	3000K - Bronze
SL-30W-30K-WH-P	30W	2800LM	3000K - White
SL-30W-50K-WH-P	30W	2800LM	5000K - White

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

SL-28W-BZ-D
Bronze

SL-28W-WH-D
Bronze/White

SL-40W-BZ-D
Bronze

DIMMABLE SECURITY LIGHTS

CATALOG NO.	DESCRIPTION		
SL-28W-30K-BZ-D	28W	3400LM	3000K - Bronze
SL-28W-50K-WH-D	28W	3400LM	5000K - White
SL-40W-30K-BZ-D	40W	4800LM	3000K - Bronze
SL-40W-50K-BZ-D	40W	4800LM	5000K - Bronze

SL-10W-BZ-D
Dark Bronze

SL-10W-WH-D
White

SL-20W-BZ-D
Dark Bronze

SL-20W-WH-D
White

SL-30W-BZ-D
Dark Bronze

SL-30W-WH-D
White

DIMMABLE SECURITY LIGHTS

CATALOG NO.	DESCRIPTION		
SL-10W-30K-BZ-D	10W	950LM	3000K - Bronze
SL-10W-30K-WH-D	10W	950LM	3000K - White
SL-10W-50K-BZ-D	10W	950LM	5000K - Bronze
SL-10W-50K-WH-D	10W	950LM	5000K - White
SL-20W-30K-BZ-D	20W	1900LM	3000K - Bronze
SL-20W-50K-BZ-D	20W	1900LM	5000K - Bronze
SL-30W-30K-BZ-D	30W	2800LM	3000K - Bronze
SL-30W-30K-WH-D	30W	2800LM	3000K - White
SL-30W-50K-WH-D	30W	2800LM	5000K - White

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

SECURITY LIGHTS

CATALOG NO.	DESCRIPTION		
SL-20W-30K-BZ	20W	2000LM	3000K - Bronze
SL-20W-30K-WH	20W	2000LM	3000K - White
SL-20W-50K-BZ	20W	2000LM	5000K - Bronze

PHOTOCELL SECURITY LIGHTS

CATALOG NO.	DESCRIPTION		
SL-20W-50K-WH	20W	2000LM	5000K - White
SL-28W-30K-WH-P	28W	3400LM	3000K - White
SL-28W-50K-WH-P	28W	3400LM	5000K - White





LOHB ACCESSORIES

CATALOG NO.	DESCRIPTION
LOHB-A	LOHB 3.3 FT SUSPENSION CABLE (SET OF 2)
LOHB-E	LOHB "T" MOUNTING BRACKET STAINLESS STEEL
LOHB-F	LOHB " X " MOUNTING BRACKET STAINLESS STEEL
LOHB-K	1/2" NPT THREADED-KNUCKLE ADAPTOR (SET OF 2)
LOHB-SH-2FT	SHROUD FOR LOHB-2FT
LOHB-SH-4FT	SHROUD FOR LOHB-4FT

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED RESIDENTIAL LANTERNS

CATALOG NO.	DESCRIPTION		
LRS-B-40K-PC	6W	550LM	4000K
LRS-C-30K-D	12W	1100LM	3000K
LRS-C-40K-D	12W	1100LM	4000K
LRS-D-30K-D	12W	1100LM	3000K
LRS-D-40K-D	12W	1100LM	4000K

CRES ENGINES & TRIMS

CATALOG NO.	DESCRIPTION		
CRES-EGN-30K-BR	15W	1300LM	3000K
CRES-EGN-30K-SIL	15W	1300LM	3000K
CRES-EGN-40K-BR	15W	1300LM	4000K
CRES-EGN-40K-SIL	15W	1300LM	4000K
CRES-EGN-50K-SIL	15W	1300LM	5000K
CRES-51-SIL	Trim for CRES-51, Sliver		

CREST ENGINES

CATALOG NO.	DESCRIPTION		
CRE-EGN-30K-BR	10W(2.5WX4)	900LM	3000K
CRE-EGN-30K-SIL	10W(2.5WX4)	900LM	3000K
CRE-EGN-40K-BR	10W(2.5WX4)	900LM	4000K
CRE-EGN-HL20-30K-SIL	20W(5WX4)	1800LM	3000K
CRE-EGN-HL20-50K-SIL	20W(5WX4)	1800LM	5000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

4" CYLINDER LIGHTS, 120V, IP65

CATALOG NO.	DESCRIPTION		
WMC-DL-15W-50K-BN	15W	1144LM	5000K

LED DECORATIVE WALL SCONCE

CATALOG NO.	DESCRIPTION		
LDS-12W-30K-D	12W	1200LM	3000K

LED STREET/ROADWAY LIGHTS w/NEMA TWIST-LOCK PHOTOCELL SOCKET, (SHORTING CAP INCL.)

CATALOG NO.	DESCRIPTION		
STL3-50W-50K	50W	6750LM	5000K
STL2-80W-30K	80W	10800LM	3000K

SPEC SERIES LED ADJUSTABLE CANOPY/PARKING LIGHTS, 120-277V

CATALOG NO.	DESCRIPTION		
CDX-35W-35K-BR	35W	4600LM	3500K - Bronze
CDX-35W-35K-WH	35W	4600LM	3500K - White
CDX-35W-40K-BR	35W	4600LM	4000K - Bronze
CDX-35W-40K-WH	35W	4600LM	4000K - White
CDX-35W-50K-BR	35W	4600LM	5000K - Bronze
CDX-35W-50K-WH	35W	4600LM	5000K - White
CDX-55W-35K-BR	55W	7250LM	3500K - Bronze
CDX-55W-35K-WH	55W	7250LM	3500K - White
CDX-55W-50K-BR	55W	7250LM	5000K - Bronze
CDX-55W-50K-WH	55W	7250LM	5000K - White

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

LED CANOPY/GARAGE WITH ULTRASONIC MULTI-LEVEL MOTION SENSOR

CATALOG NO.	DESCRIPTION		
CDL2-45CW-M	45W	2880LM	5000K

VAPOR LIGHTS, 120-277V, IP65 NEMA 3R

CATALOG NO.	DESCRIPTION		
VT-CM-12W-50K	12W	861LM	5000K

BOL-42-R-L-C-MCTP-BK
Black

BOL-42-S-C-C-MCTP-BK
Black

ROUND AND SQUARE BOLLARD, 120-277VAC, (ADJUSTABLE POWER 14~24W & CCT 30K/40K/50K)

CATALOG NO.	DESCRIPTION		
BOL-42-S-C-C-MCTP-BK	12~22W	130LM/W	30K/40K/50K
BOL-42-S-C-C-MCTP-BR	12~22W	130LM/W	30K/40K/50K
BOL-R-ACC-FL	BOLLARD ROUND FROSTED LENS ACCESSORY		

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

MOTION SENSOR

CATALOG NO.	DESCRIPTION
WEC-2MD-35	0-10V MW 120-277V SENSOR DIP, WHITE
WEC-2MDR-33	MICROWAVE SENSOR FOR LINEAR STRIP LIGHTS WITH DIP, REMOTE CAPABLE
WEC-2MDR-36	0-10V MW 120-277V SENSOR + SENSOR HEAD DIP & RC, WHITE
WEC-2MDRH-36	120-277 VAC SPLIT MICROWAVE SENSOR, BI-LEVEL, DAYLIGHT HAVEST, DIP AND RC
WEC-2TS	0-10V TEMPERATURE SENSOR FIXTURE CONTROLLER
WEC-2P-44	0-10V PIR 6-24VDC TROFFER SENSOR DIP
WEC-3MDR-42	0-10V MW 120-277V SENSOR DIP & RC
WEC-3MR-4-BR	90-DEGREE IP67 MICROWAVE SENSOR, REMOTE CAPABLE, BRONZE
WEC-3MR-4-WH	90-DEGREE IP67 MICROWAVE SENSOR, REMOTE CAPABLE, WHITE
WEC-3MRLV-5-GY	0-10V MW LOW-VOLTAGE DIMMER WITH REMOTE DRIVER 120-277V REMOTE CAPABLE - GRAY
WEC-3MRLV-5-WH	0-10V MW LOW-VOLTAGE DIMMER WITH REMOTE DRIVER 120-277V REMOTE CAPABLE - WHITE
WEC-3PDR-52	0-10V PIR 120-277V SENSOR DIP & RC
WEC-3PDR-52CAP-BR	REPLACEMENT CAP WITH LENS FOR BRI823 BRONZE TO MATCH COLOR OF LIGHTS
WEC-ON50-WH	SENSOR MOUNTING OFFSET NIPPLE, 1/2 INCH SIZE , WHITE

LED WORK LIGHT S-HOOK, USB CABLE & ADAPTOR INCL.

CATALOG NO.	DESCRIPTION		
WL-EZCG-10W-50K	10W	300~600LM	5000K
WL-EZCG-SOLP	Solar panel 10 ft. cord & magnetic base		

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

Retail Packaging - MOQ 1 Master Carton of 10

3IN1 LED WORK LIGHT(WORK LIGHT/SOS LIGHT/POWER BANK) USB CABLE INCL.

CATALOG NO.	DESCRIPTION		
WL-3IN1-10W	10W	400LM	6000K



WESTGATE SMART LIGHTING CONTROL MODULES - 1/2" KNUCKLE

CATALOG NO.	DESCRIPTION
WEC-MOD-010V-BT	WG Smart Lighting Control Module 1000W 0-10V Bluetooth IP65
WEC-MOD-010V-WIFI	WG Smart Lighting Control Module 1000W 0-10V Wifi IP65
WEC-MOD-TR-WIFI	WG Smart Lighting Control Module 300W Triac Wifi IP65

WESTGATE SMART LIGHTING CONTROL SWITCHES SWITCHES WORK AS STAND ALONE OR WITH WESTGATE APP.

CATALOG NO.	DESCRIPTION
WEC-SW-PB1-010V-BT	WG Smart Push Button Wall Switch 1000W 0-10V Bluetooth + Wall Plate
WEC-SW-PB1-TR-WIFI	WG Smart Push Button Wall Switch 300W Triac Wifi + Wall Plate

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

UHXE-80-150W-MCTP4-SR
UHXE-165-220W-MCTP4-SR
Black

UHXE-165-220W-MCTP4-SR-WH
Bronze

SHOWN WITH
UHXE-SMB

SHOWN WITH
UHXE-RPMB

SHOWN WITH
UHXE-PCR-A-90D
UHXE-PCR-B-90D

SHOWN WITH
UHXE-PCR-A-60D
UHXE-PCR-B-60D

UHXE-PCC-A
UHXE-PCC-B

BUILDER SERIES POWER AND CCT- ADJUSTABLE UFO HIGHBAY, 120-277V (SENSOR-READY)

CATALOG NO.	DESCRIPTION		
UHXE-80-150W-MCTP4-SR	80W/110W/150W	140LM/W	30K/35K/40K/50K - Black
UHXE-165-220W-MCTP4-SR	165W/190W/220W	140LM/W	30K/35K/40K/50K - Black
UHXE-165-220W-MCTP4-SR-WH	165W/190W/220W	140LM/W	30K/35K/40K/50K
UHXE-SMB	UHXE Surface Mounting U Bracket, Black		
UHXE-RPMB	UHXE 1-FT Rigid Pipe Stand with Canopy for Hard Surface (not Swivel)		
UHXE-PCR-A-90D	UHXE-80-150W 90-Degree PC Reflector		
UHXE-PCR-A-60D	UHXE-80-150W 60-Degree PC Reflector		
UHXE-PCR-B-90D	UHXE-165-220W 90-Degree PC Reflector		
UHXE-PCR-B-60D	UHXE-165-220W 60-Degree PC Reflector		
UHXE-PCC-A	UHXE-80-150W Bottom Cover For Pc Reflector, Fits Both 60D 90D		
UHXE-PCC-B	UHXE-165-220W Bottom Cover For Pc Reflector, Fits Both 60D 90D		

SPEC SERIES NEW GENERATION - UFO HIGHBAY, 120-277V

CATALOG NO.	DESCRIPTION		
UHX-150W-MP-40K	50W/80W/100W/150W	140LM/W	4000K - Black
UHX-230W-MP-50K	100W/150W/200W/230W	140LM/W	5000K - Black
UHX-150W-MCTP-WH	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K - White

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

UHX-230W-MCTP-WH	100W/150W/200W/230W	125LM/W	30K/40K/50K/57K - White
UHX-230W-MP-50K-480V	100W/150W/200W/230W	160LM/W	5000K - Black
UHX-300W-MP-50K-480V	150W/200W/240W/300W	160LM/W	5000K - Black
UHX-150W-MCTP-WH-480V	50W/80W/100W/150W	125LM/W	30K/40K/50K/57K - White
UHX-230W-MCTP-WH-480V	100W/150W/200W/230W	125LM/W	30K/40K/50K/57K - White



LED HIGH-LUMEN UFO HIGH BAY, 110° BEAM ANGLE- HOOK WITH 3/4" THREAD

CATALOG NO.	DESCRIPTION		
ULHB-150W-50K	150W	19500LM	5000K
ULHB-240W-40K	240W	31200LM	4000K
ULHB-100W-50K-480V	100W	13000LM	5000K
ULHB-90KIT-100/150	90 Degree Reflector and Glass Kit for 100W & 150W (Conversion from default 110° beam angle)		
ULHB-90KIT-200/240	90 Degree Reflector and Glass Kit for 200W & 240W (Conversion from default 110° beam angle)		
ULHB-ALR-100/150	Aluminum Reflector for 100W & 150W		
ULHB-ALR-200/240	Aluminum Reflector for 200W & 240W		
ULHB-FL-200/240	FROSTED LENS FOR ULHB 200-240W		
ULHB-FL-50/100/150	FROSTED LENS FOR ULHB 50-150W		
ULHB-PCC-200/240	Polycarbonate Cover for 200W & 240W (for ULHB-PCR-200/240 only) - Increases heat captured in the reflector. Not recomended when not necessary.		
ULHB-PCR-100/150	Polycarbonate Reflector for 100W & 150W		
ULHB-PCR-200/240	Polycarbonate Reflector for 200W & 240W		
ULHB-SC-100/150	Safety Cable for 100W & 150W		
ULHB-SC-200/240	Safety Cable for 200W & 240W		
ULHB-SC-300	Safety Cable for 300W		
ULHB-SK	Ultrasonic Bi-Level (Dimming) Motion Sensor Kit for 120~277V UFO High Bays		
ULHB-SK-480V	Ultrasonic Bi-Level (Dimming) Motion Sensor Kit for 480V UFO High Bays		
ULHB-SMB-100/150	Surface Mount Bracket for 100W & 150W		
ULHB-SMB-200/240	Surface Mount Bracket for 200W & 240W		
ULHB-WG-100/150	Wire Guard for 100W & 150W		
ULHB-WG-200/240	Wire Guard for 200W & 240W		
ULHB-WG-300	Wire Guard for 300W		

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED FOOD SERVICE & LABORATORY HIGH BAY

CATALOG NO.	DESCRIPTION		
UFHB-150W-50K	150W	20250LM	5000K

LED SATURN ARCHITECTURAL HIGH BAY

CATALOG NO.	DESCRIPTION		
USHB-150W-40K	150W	19500LM	4000K
USHB-240W-40K	240W	31200LM	4000K

UFO HIGHBAY

CATALOG NO.	DESCRIPTION		
LHB2-50W-30K-WH	50W	6750LM	3000K
LHB2-50W-40K-WH	50W	6750LM	4000K
LHB2-50W-50K-WH	50W	6750LM	5000K

IP69 2-FOOT LINEAR HIGH BAYFOR FOOD AND CHEMICAL FACILITIES, SENSOR READY

CATALOG NO.	DESCRIPTION		
LLHBF-120-200W-MCTP-SR	120W/160W/200W	150LM/W	40K/45K/50K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED LINEAR HIGH BAY

CATALOG NO.	DESCRIPTION		
LLHB2-100W-40K-D	100W	14000LM	4000K
LLHB2-150W-40K-D	150W	21600LM	4000K
LLHB2-220W-40K-D	220W	30800LM	4000K

LED LINEAR VAPOR LIGHT

CATALOG NO.	DESCRIPTION		
LLVT-8FT-100W-40K-D	100W	13000LM	4000K

SPEC SERIES 4TH GENERATION OF LINEAR HIGH BAYS

CATALOG NO.	DESCRIPTION
LLHB-CL-120/180	CLEAR LENS FOR LLHB 120W & 180W
LLHB-OC-REMOTE	INDOOR HIGHBAY OCCUPANCY SENSOR WITH BI-LEVEL DIMMING - NEEDS LLHB-OC-REMOTE TO CHANGE SETTINGS

SPEC SERIES 4TH GENERATION OF LINEAR HIGH BAYS, 480V

CATALOG NO.	DESCRIPTION		
LLHB4-200W-50K-D	200W	31000LM	5000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

4 Ft

LLHB4-MCTP
LLHB4-MP (200W TO 500W)
White

2 Ft

LLHB4-MP (100W TO 150W)
White

OPT-LLHB4-SMK

LLHB4-100W-WG
LLHB4-150W-WG



LLHB4-RODKIT

SPEC SERIES 4TH GENERATION OF LINEAR HIGH BAYS

CATALOG NO.	DESCRIPTION		
LLHB4-80-150W-MCTP	80W/110W/150W	125LM/W	35K/40K/50K
LLHB4-100W-MP-40K-D	50W/80W/100W	125LM/W	4000K - 2FT. X 13.77
LLHB4-100W-MP-50K-D	50W/80W/100W	125LM/W	5000K - 2FT. X 13.77
LLHB4-150W-MP-40K-D	80W/110W/150W	125LM/W	4000K - 2FT. X 17.75
LLHB4-150W-MP-50K-D	80W/110W/150W	125LM/W	5000K - 2FT. X 17.75
LLHB4-300W-MP-40K-D	150W/225W/300W	125LM/W	4000K - 4FT. X 17.75
LLHB4-300W-MP-50K-D	150W/225W/300W	125LM/W	5000K - 4FT. X 17.75
LLHB4-410W-MP-50K-D	200W/300W/410W	125LM/W	5000K - 4FT. X 23.20
LLHB4-80-150W-MCTP-480V	80W/110W/150W	125LM/W	35K/40K/50K
LLHB4-100W-MP-40K-D-480V	50W/80W/100W	125LM/W	4000K - 2FT. X 13.77
LLHB4-100W-MP-50K-D-480V	50W/80W/100W	125LM/W	5000K - 2FT. X 13.77
LLHB4-150W-MP-40K-D-480V	80W/110W/150W	125LM/W	4000K - 2FT. X 17.75
LLHB4-150W-MP-50K-D-480V	80W/110W/150W	125LM/W	5000K - 2FT. X 17.75
LLHB4-300W-MP-40K-D-480V	150W/225W/300W	125LM/W	4000K - 4FT. X 17.75
LLHB4-300W-MP-50K-D-480V	150W/225W/300W	125LM/W	5000K - 4FT. X 17.75
LLHB4-410W-MP-50K-D-480V	200W/300W/410W	125LM/W	5000K - 4FT. X 23.20
LLHB4-50W-40K-D	50W	7750LM	4000K
LLHB4-150W-WG	LLHB4 Linear Highbay 150W Wireguard - White		
LLHB4-SMB	LLHB4 Linear Highbay Surface Mounting Bracket Set		

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED LINEAR HIGH BAY

CATALOG NO.	DESCRIPTION		
LLHB-90W-40K-D	90W	14400LM	4000K
LLHB-180W-40K-D	150W	23250LM	4000K - Frosted lens, 4FTx15-7/8"

CORN LAMPS, 100~277V AC

CATALOG NO.	DESCRIPTION		
CL-36W-30K-E26	35W	4456LM	3000K
CL-36W-30K-E39	36W	4456LM	3000K
CL-36W-50K-E39	36W	4788LM	5000K

LED 180 DEGREE FLAT HID RETROFIT LAMP

CATALOG NO.	DESCRIPTION		
CL-FLT-36-54W-50K-E39	36W/45W/54W	150LM/W	5000K - Flat
CL-FLT-54-75W-50K-E39	54W/63W/75W	150LM/W	5000K
CL-FLT-75-115W-50K-E39	75W/97W/115W	150LM/W	5000K
CL-FLTW-54-75W-50K-E39	54W/63W/75W	150LM/W	5000K - Adjustable
CL-FLTW-75-110W-50K-E39	75W/97W/110W	150LM/W	5000K - Adjustable

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

HIGH-LUMEN LED CORN LAMP WITH UP LIGHT,100~277V AC

CATALOG NO.	DESCRIPTION		
CL-HL-14W-30K-E26	14W	1820LM	3000K
CL-HL-27W-30K-E26	27W	3510LM	3000K
CL-HL-36W-30K-E26	36W	4680LM	3000K
CL-HL-36W-30K-E39	36W	4680LM	3000K
CL-HL-45W-30K-E39	45W	5850LM	3000K
CL-HL-75W-30K-E39	75W	9750LM	3000K
CL-HL-100W-30K-E39	100W	13000LM	3000K

LED CONSTRUCTION STRING LIGHT

CATALOG NO.	DESCRIPTION		
CL-CONST-75W-50K	75W	12500LM	5000K

LED HIGH POWER LAMPS, 120~277V

CATALOG NO.	DESCRIPTION		
HPL-HB-60W-50K-E39	60W	6480LM	5000K - E39 Mogul Base
HPL-HB-75W-50K-E39	75W	8100LM	5000K - E39 Mogul Base
HPL-HB-100W-50K-E39	100W	12500LM	5000K - E39 Mogul Base
HPL-HB-R1	Optional PC Reflector for HPL-HB-60W		
HPL-HB-R2	Optional PC Reflector for HPL-HB-75W & 100W		
HPL-HB-R3	Optional PC Reflector for HPL-HB-120W & HPL-HB-140W		

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED 180 DEGREE FLAT HID RETROFIT LAMP

CATALOG NO.	DESCRIPTION		
CL-FLT-75W-50K-E39	75W	9000LM	5000K
CL-FLT-115W-50K-E39	115W	13570LM	5000K

PREMIUM HIGH-OUTPUT LED PANELS, 125LM/W

CATALOG NO.	DESCRIPTION		
LP-2X4-50W-40K-D-HL	50W	6260LM	4000K
LP-2X4-50W-50K-D-HL	50W	6260LM	5000K

LED PANEL LIGHTS

CATALOG NO.	DESCRIPTION		
LP-1X4-40W-27K-DS	40W	3600LM	2700K
LP-2X4-60W-27K-DS	60W	5400LM	2700K
LP-2X4-60W-35K-DS	60W	6300LM	3500K
LP-2X4-72W-27K-DS	72W	6480LM	2700K
LP-2X4-72W-35K-DS	72W	7560LM	3500K

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

LED PANEL 2X4

CATALOG NO.	DESCRIPTION		
LP-2X4-72W-27K-D	72W	7200LM	2700K

ADJUSTABLE AIRCRAFT CABLE SUSPENSION KIT

CATALOG NO.	DESCRIPTION
LP-SSPC-1X4	Adjustable Aircraft Cable Suspension Kit For 1X4 Panel
LP-SSPC-2X2	Adjustable Aircraft Cable Suspension Kit For 2X2 Panel
LP-SSPC-2X4	Adjustable Aircraft Cable Suspension Kit For 2X4 Panel

RECESSED MOUNTING FLANGE KIT FOR 2X2 PANELS

CATALOG NO.	DESCRIPTION
LP-RMK-2X2	Recessed Mounting Flange Kit For 2X2 Panels

LED BACKLIT PANEL LIGHT, 100~277VAC

CATALOG NO.	DESCRIPTION		
LPNG-2X2-4KLM-50K-D	40W	4400LM	5000K
LPNG-2X4-4KLM-50K-D	40W	4200LM	5000K
LPNG-2X4-5KLM-35K-D	50W	5140LM	3500K
LPNG-2X4-5KLM-50K-D	50W	5250LM	5000K
LPNG-2X4-6KLM-35K-D	60W	6300LM	3500K
LPNG-2X4-6KLM-40K-D	60W	6600LM	4000K
LPNG-2X4-6KLM-50K-D	60W	6600LM	5000K
LPNG-2X4-7KLM-35K-D	60W	7560LM	3500K
LPNG-1X4-4KLM-27K-D	40W	3800LM	2700K
LPNG-1X4-4KLM-50K-D	40W	4400LM	5000K
LPNG-1X4-MCTP	20/30/40W		35K/40K/50K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

SINGLE CCT T-BAR GRID LIGHTS

CATALOG NO.	DESCRIPTION		
TGL-2X4-30K	60W	6000LM	3000K
TGL-2X4-40K	60W	6000LM	4000K

INTERNAL-DRIVER LED SURFACE MOUNT PANELS, (1X4 & LARGER CAN BE RECESS MOUNTED)

CATALOG NO.	DESCRIPTION		
LPS-1X4-40K-D	40W	4000LM	4000K - 1' X 4', 120~277VAC
LPS-2X2-30K-D	40W	4400LM	3000K - 2' X 2', 120~277VAC
LPS-2X4-50K-D	50W	5500LM	5000K - 2' X 4', 120~277VAC

DURABLE (PC BODY) TROFFER LIGHTS, 140LM/W

CATALOG NO.	DESCRIPTION		
LTRP-2X2-35W-50K-D	35W	4900LM	5000K
LTRP-2X4-50W-50K-D	50W	6850LM	5000K

SPEC SERIES LED SELECTABLE COLOR TEMP. & WATTAGE TROFFERS, AC 100~277V

CATALOG NO.	DESCRIPTION		
LTRE-2X2-MCTP	26W, 32W, 40W	125LM/W	3500K, 4000K, 5000K
LTRE-2X4-MCTP	32W, 40W, 50W	125LM/W	3500K, 4000K, 5000K
LTRE-1X4-MCTP	26W, 32W, 40W	125LM/W	3500K, 4000K, 5000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

BUILDER SERIES POWER & CCT- ADJUSTABLE STACK TROFFER REQUIRES 1 MINUTE ASSEMBLY

CATALOG NO.	DESCRIPTION		
LTRS-1X4-MCTP	25W/35W/36W/40W	125LM/W	3500K/4000K/5000K

LED DIRECT-INDIRECT (METAL HOUSING+PC LENS) TROFFERS

CATALOG NO.	DESCRIPTION		
LTR-2X4-50W-40K-D	50W	5590LM	4000K
LTR-2X4-50W-50K-D	50W	5702LM	5000K

HIGH LUMEN LED RETROFIT BASKET TROFFER

CATALOG NO.	DESCRIPTION		
LRT-HL-2X2-40W-40K-D	40W	5200LM	4000K
LRT-HL-2X4-50W-40K-D	50W	6500LM	4000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

SCX LINEAR SERIES

CATALOG NO.	DESCRIPTION		
SCX-2FT-20W-30K-D	20W	2240LM	3000K
SCX-2FT-20W-35K-D	20W	2300LM	3500K
SCX-2FT-20W-40K-D	20W	2360LM	4000K
SCX-2FT-20W-50K-D	20W	2420LM	5000K
SCX-3FT-30W-30K-D	30W	3360LM	3000K
SCX-ULM-8FT-32W-50K	UPLIGHT FOR SCX		
SCX-IC-30K	SCX SERIES INSIDE CORNER SECTION 30K		
SCX-IC-35K	SCX SERIES INSIDE CORNER SECTION 35K		
SCX-IC-40K	SCX SERIES INSIDE CORNER SECTION 40K		
SCX-IC-50K	SCX SERIES INSIDE CORNER SECTION 50K		
SCX-T-35K	SCX SERIES T SECTION 35K		
SCX-T-40K	SCX SERIES T SECTION 40K		
SCX-T-50K	SCX SERIES T SECTION 50K		

LED SUSPENDED UP/DOWN CLEAR ROUND PANEL LIGHT, 22" DIA., 6FT HEIGHT

CATALOG NO.	DESCRIPTION		
SRPL-40W-35K-D	40W	2100LM/2100LM	3500K
SRPL-40W-50K-D	40W	2100LM/2100LM	5000K

LED ARCHITECTURAL ROUND SUSPENDED DOWN LIGHT, 24" DIA, 6FT HEIGHT

CATALOG NO.	DESCRIPTION		
SCR-24D-40K-D	50W	5197LM	4000K - 24" Dia

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED SUSPENDED UP/DOWN CLEAR PANEL LIGHT, 120~277V (SUSPENSION & CORD NOT INCL.)

CATALOG NO.	DESCRIPTION			
SPL-4FT-40W-40K-D	40W	2100LM/2100LM	4000K
SPL-4FT-40W-50K-D	40W	2100LM/2100LM	5000K

4FT 2in MICRO OPTIC LINEAR LIGHT

CATALOG NO.	DESCRIPTION		
SCO-4FT-40W-MCT-WB	40W	3760LM	3500K/4000K/5000K

ARCHITECTURAL PARABOLIC SUSPENDED LIGHT - 4FT

CATALOG NO.	DESCRIPTION		
SCLP-4FT-40W-MCT-D	40W	4600LM	35K/40K/50K - White

LED SUSPENDED 2/3 PERFORATED BASKETLIGHT (UP/DOWN)

CATALOG NO.	DESCRIPTION		
SCPL-UD-4FT-60W-35K-D	40W/20W OR 60W	4400LM/2100LM	3500K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED PARABOLIC SUSPENDED LIGHT

CATALOG NO.	DESCRIPTION		
SCLT-4FT-40W-50K-D	40W	4600LM	5000K - White
SCLT-4FT-40W-MCT-D	40W	4600LM	35K/40K/50K - White

SPEC SERIES LED STRIP LIGHT, 120~277V

CATALOG NO.	DESCRIPTION		
LSL-8FT-64W-35K-D	64W	7000LM	3500K

SUSPENSION KIT

CATALOG NO.	DESCRIPTION
SCL-CSY	ADJ. 6FT 1/16in DOUBLE SUSPENSION KIT WITH Y DOUBLE KEY HOLE CONNECTORS, CANOPIES, T-BAR CLIPS, ACCESSORIES
SCL-CS	

ARCHITECTURAL SUSPENDED COMMERCIAL LIGHT

CATALOG NO.	DESCRIPTION		
SCL-2FT-25W-50K-D	25W	2750LM	5000K
SCL-2FT-25W-40K-D	25W	2750LM	4000K
SCL-2FT-25W-35K-D	25W	2750LM	3500K
SCL-4FT-40W-35K-D	40W	4400LM	3500K
SCL-4FT-UD-40W-50K-D	15W/25W	1650LM/2750LM	5000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST



LED LINEAR SUSPENDED PERFORATED BASKET LIGHT (UP/DOWN)

CATALOG NO.	DESCRIPTION		
SCLL-UD-4FT-60W-50K-D	40W/20W OR 60W	4400LM/2100LM	5000K
SCLL-UD-4FT-60W-40K-D	40W/20W OR 60W	4400LM/2100LM	4000K
SCLL-UD-4FT-60W-35K-D	40W/20W OR 60W	4400LM/2100LM	3500K

LED STANDARD WRAP-AROUND FIXTURE, 120~277V

CATALOG NO.	DESCRIPTION		
WAS-4FT-42W-35K-D	42W	4400LM	3500K - 4FT
WAS-4FT-42W-50K-D	42W	4400LM	5000K - 4FT

SPEC SERIES LED ARCHITECTURAL WRAP-AROUND LIGHT

CATALOG NO.	DESCRIPTION		
WA-2FT-25W-35K-D	25W	2750LM	3500K - 2FTx8.2"
WA-2FT-25W-40K-D	25W	2750LM	4000K
WA-2FT-25W-50K-D	25W	2750LM	5000K - 2FTx8.2"
WA-2FT-25W-MCT-D	25W	2800LM	35K/40K/50K - 2FTx8.2"



BUILDER SERIES LED ECONOMY WRAP-AROUND FIXTURES

CATALOG NO.	DESCRIPTION		
WAE-2FT-MCT-DT	20W	1600LM	3000K/4000K/5000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED ARCHITECTURAL STRIP LIGHT, 120~277V

CATALOG NO.	DESCRIPTION		
CSL-4FT-40W-50K-D	40W	4600LM	5000K
CSL-4FT-40W-35K-D	40W	4600LM	3500K
CSL-4FT-25W-50K-OC	25W	3000LM	5000K
CSL-4FT-25W-40K-OC	25W	3000LM,	4000K



U-SHAPED T8 LED PLASTIC/ALUMINUM LAMPS

CATALOG NO.	DESCRIPTION		
T8-U2F-EZ3-15W-41K-C	15W	1450LM	4100K
T8-U2F-EZ3-15W-50K-C	15W	1500LM	5000K

4FT. LED T5 GLASS LAMPS

CATALOG NO.	DESCRIPTION		
T5-TYPB-25W-40K-F	25W	3200LM	4000K - Frosted
T5-TYPB-25W-50K-F	25W	3200LM	5000K

X-GEN 3CCT LED T8 GLASS LAMPS 3 COLOR-TEMPERATURES IN ONE LAMP TYPE A+B (A/C OR BALLAST)

CATALOG NO.	DESCRIPTION		
T8-EZX-MCT-GS-2FT-8W-C	8W	1216LM	35K/40K/50K - Clear, G13, Type A & B
T8-EZX-MCT-GS-3FT-12W-C	12W	1500LM	35K/40K/50K - Clear, G13, Type A & B

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED T8 2FT , PLASTIC ALUMINUM TUBE

CATALOG NO.	DESCRIPTION		
T8-EZ6-AHL-2FT-15W-40K-F	15W	1650LM	4000K
T8-EZ6-AHL-2FT-15W-40K-C	15W	1725LM	4000K
T8-EZ6-AHL-4FT-18W-30K-F	18W	1980LM	3000K
T8-EZ6-AHL-4FT-18W-40K-F	18W	1980LM	4000K
T8-EZ6-AHL-4FT-18W-50K-F	18W	1980LM	5000K

4FT. T8-EZ4 LED LAMPS 110° Beam Angle Clear, 200° Frosted ELECTRONIC BALLASTS (TYPE A)

CATALOG NO.	DESCRIPTION		
T8-EZ4-18W-40K-C	18W	2200LM	4000K

X-GEN SELECTABLE-POWER LED T8 GLASS LAMPS, TYPE B FOR DIRECT A/C (BALLAST OVERRIDE)

CATALOG NO.	DESCRIPTION		
T8-EZX-TB-4FT-12-18W-50K-F	12W/15W/18W	120LM/W	5000K - Frosted, G13, Type B
T8-EZX-TB-4FT-12-18W-50K-C	12W/15W/18W	120LM/W	5000K - Clear, G13, Type B
T8-EZX-TB-4FT-12-18W-40K-F	12W/15W/18W	120LM/W	4000K - Frosted, G13, Type B
T8-EZX-TB-4FT-12-18W-40K-C	12W/15W/18W	120LM/W	4000K - Clear, G13, Type B

U-SHAPED T8 EZ6 LED GLASS LAMPS

CATALOG NO.	DESCRIPTION		
T8-EZ6-U2F-15W-41K-C	15W	2100LM	4100K
T8-EZ6-U2F-15W-50K-C	15W	2100LM	5000K
T8-EZ6-U2F-15W-50K-F	15W	2000LM	5000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

4FT. T8 GLASS LAMPS WORKS WITH A/C DIRECT (120-2777) ONE END OR BOTH ENDS (TYPE B)

CATALOG NO.	DESCRIPTION		
T8-4FT-TYPB-2E-18W-40K-C	18W	2200LM	4000K
T8-4FT-TYPB-2E-18W-40K-F	18W	2200LM	4000K

4FT. T8 LED GLASS LAMPS DIMMABLE DIRECT A/C (one end N+L)

CATALOG NO.	DESCRIPTION		
T8-4FT-DIM-18W-35K-C	18W	1900LM	3500K - 90~140VAC, CLEAR
T8-4FT-DIM-18W-50K-C	18W	2150LM	5000K
T8-4FT-DIM-18W-50K-F	18W	2150LM	5000K - 90~140VAC, FROSTED

CRL ENGINES

CATALOG NO.	DESCRIPTION		
CRL-EGN-18W-30K	18W	1639LM	3000K
CRL-EGN-18W-50K	18W	1639LM	5000K
CRL-EGN-27W-30K	27W	2387LM	3000K
CRL-EGN-40W-30K	40W	3447LM	3000K
CRL-EGN-40W-50K	40W	3447LM	5000K
CRL-EGN-54W-30K	54W	4500LM	3000K
CRL-EGN-54W-40K	54W	4500LM	4000K
CRL-EGN-54W-50K	54W	4500LM	5000K

CRLC ENGINES

CATALOG NO.	DESCRIPTION		
CRLC-EGN-15W-30K-D	15W	1200LM	3000K
CRLC-EGN-15W-50K-D	15W	1275LM	5000K
CRLC-EGN-20W-50K-D	20W	1720LM	5000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED VANITY LIGHT, 120~277VAC

CATALOG NO.	DESCRIPTION		
LVL-2FT-17W-30K	17W	1900LM	3000K
LVL-2FT-17W-40K	17W	1900LM	4000K

LED TRACK LIGHTS, 120V

CATALOG NO.	DESCRIPTION		
TR1-R-10W-WH-50K	10W	702LM	5000K - 25° LED ADJ. CYLINDER
TR1-S-10W-BK-30K	10W	681LM	3000K - 25° LED ADJ. CYLINDER
TR1-S-10W-BK-40K	10W	706LM	4000K - 25° LED ADJ. CYLINDER
TR1-S-10W-WH-30K	10W	681LM	3000K - 25° LED ADJ. SQUARE
TR1-S-10W-WH-40K	10W	706LM	4000K - 25° LED ADJ. SQUARE
TR1-S-10W-WH-50K	10W	732LM	5000K - 25° LED ADJ. SQUARE
TR1-REFL-13D	Replacement Reflector For Tr1 Series Track Lights 13"		

BUILDER PLUS ENVIRONMENTAL SERIES PC 5CCT+3 POWER-LEVEL SELECTABLE LED RECESSED LIGHT TRIM- COMPOSITE SERIES

CATALOG NO.	DESCRIPTION		
RDPF4-MCTP	8W/10W/13W	80LM/W	27K/30K/35K/40K/50K
RDPF6-MCTP	10W/13W/17W	80LM/W	27K/30K/35K/40K/50K

BUILDER PLUS ENVIRONMENTAL SERIES PC 5CCT SELECTABLE LED RECESSED LIGHT TRIM- COMPOSITE SERIES

CATALOG NO.	DESCRIPTION		
RDPF4-MCT5	10W	800LM	27K/30K/35K/40K/50K
RDPF6-MCT5	13W	1040LM	27K/30K/35K/40K/50K
RDPS4-MCT5	10W	800LM	27K/30K/35K/40K/50K
RDPS6-MCT5	13W	1040LM	27K/30K/35K/40K/50K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

SPEC PLUS & WESTGATE SIGNATURE LED RECESSED TRIM SERIES 3", 4", 5/6" SELECTABLE 5CCT [JA8]

CATALOG NO.	DESCRIPTION		
RDL3-MCT5-WP	7W	560LM	27K/30K/35K/40K/50K - 3"
RDL4-MCT5-WP	8W	650LM	27K/30K/35K/40K/50K - 4"
RDL6-MCT5-WP	14W	1140LM	27K/30K/35K/40K/50K - 6"

SINGLE CCT LED TRIMS 3", 4", 5/6" E26 included in the box (JA8-E-2016 COMPLIANT)

CATALOG NO.	DESCRIPTION		
RDL3-27K-WP	9W	540LM	2700K - 3"
RDL3-41K-WP	9W	540LM	4100K - 3"
RDL3-50K-WP	9W	540LM	5000K - 3"
RDL4-27K-WP	12W	650LM	2700K - 4"
RDL4-35K-WP	12W	725LM	3500K - 4"
RDL4-65K-WP	12W	850LM	6500K - 4"
RDL6-65K-WP	19W	1400LM	6500K - 5/6"
RDL4-BF-27K	10W	650LM	2700K - 4"
RDL4-BF-35K	10W	720LM	3500K - 4"
RDL4-BF-41K	10W	746LM	4100K - 4"
RDL4-BF-50K	10W	761LM	5000K - 4"
RDL6-BF-35K	18W	1280LM	3500K - 5/6"
RDL4-ADJ-27K	10W	650LM	2700K - 4"
RDL4-ADJ-30K	10W	650LM	3000K - 4"
RDL4-ADJ-41K	10W	650LM	4100K - 4"
RDL4-ADJ-50K	10W	650LM	5000K - 4"
RDL6-ADJ-50K	13W	900LM	5000K - 5/6"

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

4" LED SQUARE TRIMS

CATALOG NO.	DESCRIPTION		
SDL4-BF-27K	10W	600LM	2700K - 4"
SDL4-BF-30K	10W	650LM	3000K - 4"
SDL4-BF-50K	10W	700LM	5000K - 4"
SDL6-BF-27K	16.5W	1073LM	2700K - 5/6"
SDL6-BF-30K	16.5W	1100LM	3000K - 5/6"
SDL6-BF-41K	16.5W	1150LM	4100K - 5/6"
SDL6-BF-50K	16.5W	1200LM	5000K - 5/6"

SINGLE CCT LED ULTRA SLIM RECESSED LIGHTS, 120V

CATALOG NO.	DESCRIPTION		
SSL4-27K	9W	630LM	2700K
SSL6-27K	15W	1125LM	2700K
SSL6-30K	15W	1125LM	3000K
SSL6-40K	15W	1125LM	4000K
SSL6-50K	15W	1125LM	5000K



AIRTIGHT LED RECESSED LIGHT HOUSING

CATALOG NO.	DESCRIPTION
ICFAL-4	4" Fire-Rated IC New Construction Led Recessed Housing
ICFAL-6	6" Fire-Rated IC New Construction Led Recessed Housing

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST



SINGLE CCT LED ULTRA SLIM RECESSED LIGHTS, 120V

CATALOG NO.	DESCRIPTION		
RSL3-27K	6W	400LM	2700K
RSL3-30K-ORB	6W	400LM	3000K
RSL3-40K	6W	400LM	4000K
RSL3-50K	6W	420LM	5000K
RSL4-30K-BN	9W	630LM	3000K
RSL4-30K-ORB	9W	630LM	3000K
RSL4-40K	9W	650LM	4000K
RSL4-50K	9W	650LM	5000K
RSL6-27K	15W	1125LM	2700K
RSL6-30K-BN	15W	1125LM	3000K
RSL6-40K	15W	1125LM	4000K
RSL8-40K	18W	1300LM	4000K
RSL8-MCT	18W	1300LM	3000K/4000K/5000K

LED COMMERCIAL SLIM CANLESS RECESSED REGRESSED BAFFLE LIGHTS 120-277V, 0~10V DIMMING

CATALOG NO.	DESCRIPTION		
RSLC6-BF-30K	15W	1200LM	3000K - 6"
RSLC8-BF-30K	18W	1440LM	3000K - 8"

4" SINGLE CCT LED ADJUSTABLE PULL-DOWN ULTRA SLIM RECESSED LIGHTS

CATALOG NO.	DESCRIPTION		
RSL4-APD-50K	12W	700LM	5000K

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

4" SINGLE CCT LED ADJUSTABLE PULL-DOWN ULTRA SLIM RECESSED LIGHTS

CATALOG NO.	DESCRIPTION		
RSL4-ADJ-27K	9W	700LM	2700K
RSL4-ADJ-40K	9W	700LM	4000K
RSL4-ADJ-50K	9W	700LM	5000K
RSL6-ADJ-30K	12W	900LM	3000K

2" LED RECESSED LIGHTS (Baffle)(JA8-E-2016 COMPLIANT)

CATALOG NO.	DESCRIPTION		
RDL2S-BF-27K-WH	8W	600LM	2700K
RDL2S-BF-40K-WH	8W	600LM	4000K - Round
RDL2S-BF-50K-WH	8W	600LM	5000K - Round

2" LED RECESSED LIGHTS (Baffle)(JA8-E-2016 COMPLIANT)

CATALOG NO.	DESCRIPTION		
SDL2S-BF-27K-WH	8W	600LM	2700K - Square
SDL2S-BF-40K-WH	8W	600LM	4000K - Square
SDL2S-BF-50K-WH	8W	600LM	5000K - Square

3" LED ADJUSTABLE (EYEBALL) RECESSED LIGHTS (JA8-E-2016 COMPLIANT)

CATALOG NO.	DESCRIPTION		
SDL3S-ADJ-27K-WH	8W	600LM	2700K - 3" White
SDL3S-ADJ-30K-WH	8W	600LM	3000K - 3" White
SDL3S-ADJ-40K-WH	8W	600LM	4000K - 3" White

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

DUSK-TO-DAWN AREA LIGHT, 120-277V

CATALOG NO.	DESCRIPTION		
LRD-EGN-10W-35K-D	10W	700LM	3500K
LRD-EGN-10W-40K-D	10W	700LM	4000K
LRD-EGN-10W-50K-D	10W	700LM	5000K

LED 5CCT CLOUD FIXTURE WITH PRE-INSTALLED SENSOR, 120V

CATALOG NO.	DESCRIPTION		
FCRB-16-MCT5-SEN	20W	1400LM	27K/30K/35K/40K/50K

12V LED DIRECTIONAL LIGHTS - ALUMINUM

CATALOG NO.	DESCRIPTION		
FCS-11-12W-40K	15W	1100LM	4000K - 11" DIA

BUILDER COMPOSITE SERIES DECORATIVE FLUSH MOUNT FIXTURES 120V 5CCT E26 VER. INCL. (EXCEPT R12) RECESS ACCESSORIES

CATALOG NO.	DESCRIPTION		
FMLE-R5-MCT5-E26	9W	650LM	27K/30K/35K/40K/50K - 5"
FMLE-R9-MCT5-E26	17W	1300LM	27K/30K/35K/40K/50K - 9"
FMLE-R12-MCT5	21W	1500LM	27K/30K/35K/40K/50K - 12"

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

SPEC SERIES ARCHITECTURAL DIE-CAST FLUSH MOUNT FIXTURES, 120V, 3CCT

CATALOG NO.	DESCRIPTION		
FML-R6-MCT	11W	660LM	30K/40K/50K - 6"
FML-R8-MCT	14W	840LM	30K/40K/50K - 8"
FML-R10-MCT	17W	1020LM	30K/40K/50K - 10"
FML-R14-MCT	26W	1560LM	30K/40K/50K
FML-R18-MCT	30W	2100LM	30K/40K/50K - 18"

ARCHITECTURAL FLUSH MOUNT SURFACE FIXTURES, 120V

CATALOG NO.	DESCRIPTION		
FML-R6-11W-50K	11W	550LM	5000K
FML-R8-14W-30K	14W	750LM	3000K
FML-R8-14W-50K	14W	750LM	5000K
FML-R10-17W-30K	17W	950LM	3000K
FML-S6-11W-50K	11W	550LM	5000K
FML-S8-14W-30K	14W	750LM	3000K
FML-S10-17W-30K	17W	950LM	3000K

LED DRUM FIXTURES, 120V

CATALOG NO.	DESCRIPTION		
FDL-14-20W-30K	20W	1500LM	3000K
FDL-16-25W-30K	25W	1800LM	3000K
FDL-16-MCT5	24W	1800LM	27K/30K/35K/40K/50K
FDL-18-30W-30K	30W	2250LM	3000K

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

BUILDER SERIES 6" LED ECONOMY DISC LIGHT, 120V

CATALOG NO.	DESCRIPTION		
DLSE6-50K	15W	900LM	5000K - 6" White
DLSE6-MCT-BN	15W	1000LM	3000K/4000K/5000K

LED DISC LIGHT 4" & 6" 120V (J-BOX MOUNTING)(JA8-E-2016 COMPLIANT)

CATALOG NO.	DESCRIPTION		
DLSN4-27K	10W	600LM	2700K
DLSN4-50K	10W	600LM	5000K - 4"
DLSN6-27K	15W	1000LM	2700K - 6"
DLSN6-41K	15W	1000LM	4100K
DLSN6-50K	15W	1000LM	5000K - 6"
DLSN6-30K-BN	15W	1000LM	3000K

SPEC SERIES HIGH-PERFORMANCE DISC LIGHTS, 120V DIE CAST ALUMINUM, ALL MOUNTING OPTIONS INCL.

CATALOG NO.	DESCRIPTION		
DLS4-27K	9W	550~600LM	2700K - 4"
DLS4-30K	9W	550~600LM	3000K - 4"
DLS4-41K	9W	550~600LM	4100K - 4"
DLS4-50K	9W	550~600LM	5000K - 4"
DLS6-30K	15W	950~1000LM	3000K - 6"
DLS6-41K	15W	950~1000LM	4100K - 6"
DLS6-30K-BN	15W	950~1000LM	3000K - 6" Brushed Nickel

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

G4 BASE LAMPS

CATALOG NO.	DESCRIPTION		
GZ-JC-39L-27K	3W	250LM	2700K - 12VAC/DC
GZ-JC-39L-30K	3W	250LM	3000K - 12VAC/DC

LED PL LAMPS

CATALOG NO.	DESCRIPTION		
LPL-EB-14W-H-L-40K	12W	1200LM	4000K
LPL-EB-9W-H-40K	9W	800LM	4000K - Horizontal 90°

PAR LAMPS

CATALOG NO.	DESCRIPTION		
PAR30-LN-10W-50K-D	10W	900LM	5000K
PAR38-18W-30K-D	18W	1620LM	3000K

A19 LAMP, CRI 90

CATALOG NO.	DESCRIPTION		
A19-C90-8PK-800L-50K-D	9.5W	800LM	5000K

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

24-VOLT INDOOR LED RIBBON LIGHTS - EXTRA HIGH OUTPUT

CATALOG NO.	DESCRIPTION		
ULR-IN-16F-XHO-27K	8.8W/FT	620LM/FT	2700K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-XHO-30K	8.8W/FT	620LM/FT	3000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-XHO-35K	8.8W/FT	620LM/FT	3500K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-XHO-40K	8.8W/FT	680LM/FT	4000K - 10mm Width 16.4FT Reel Length
ULR-IN-16F-XHO-50K	8.8W/FT	700LM/FT	5000K - 10mm Width 16.4FT Reel Length
ULR-IN-98F-XHO-27K	8.8W/FT	620LM/FT	2700K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-XHO-30K	8.8W/FT	620LM/FT	3000K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-XHO-35K	8.8W/FT	620LM/FT	3500K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-XHO-40K	8.8W/FT	680LM/FT	4000K - 10mm Width 98.4FT Reel Length
ULR-IN-98F-XHO-50K	8.8W/FT	700LM/FT	5000K - 10mm Width 98.4FT Reel Length

LED T5 RETROFIT LAMPS WITH INTERNAL DRIVER

CATALOG NO.	DESCRIPTION		
T5-22IN-9W-40K	9W	1035LM	4000K
T5-22IN-9W-50K	9W	1125LM	5000K
T5-47IN-16W-50K	16W	2000LM	5000K
T5-6FT-PC	6 FT. Plug-in Power Cord		
T5-6FT-PCS	7 FT. Plug-in Power Cord		
T5-8IN-JUMP	8" Linking Cable		
T5-6FT-PT	6' AC Input Wire (PIGTAIL)		
T5-COUPLER	Coupler (1 Included)		
T5-MAGSET	Clip-on Secure Magnet Set		

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

LED PUCK LIGHTS, 120V INTERNAL DRIVERS Surface/Recess

CATALOG NO.	DESCRIPTION		
PL12ADJ-30K-BK	4.5W	250LM	3000K - Black
PL12ADJ-40K-BK	4.5W	250LM	4000K - Black
PL12ADJ-50K-BK	4.5W	250LM	5000K - Black

DIRECTIONAL LIGHT, 12V, SOLID BRASS

CATALOG NO.	DESCRIPTION		
LD-184-BZ	5W	400LM	3000K

STEP LIGHT, 12V

CATALOG NO.	DESCRIPTION		
AS-159-BK	3W	200LM	3000K
AS-159-BR	3W	200LM	3000K

STEP LIGHT, 12V

CATALOG NO.	DESCRIPTION		
LS-159-BZ	3W	200LM	3000K - Bronze

WELL LIGHTS WITH SLEEVE & LED LAMPS

CATALOG NO.	DESCRIPTION		
WL-105-1-BK	5W	400LM	3000K - Black
WL-170-BK	5W	400LM	3000K
WL-181-BK	5W	400LM	3000K - Black
WL-181-BR	5W	400LM	3000K - Bronze
WL-181-BZ	5W	400LM	3000K - Antique Bronze

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

PLUG-IN DRIVERS (Non-Dimming)

CATALOG NO.	DESCRIPTION
UC12PS6W	6W, 12V, POWER SUPPLY WITH CABLE
UCPS6W	6W, 24V, POWER SUPPLY W/ CABLE
UCPS12W	12W, 24V, POWER SUPPLY W/ 1.5 POWER CABLE
UCPS24W	24W, 24V, 1A, POWER SUPPLY W/ 1.5 POWER CABLE
UCPS48W	48W, 24V, 1A, POWER SUPPLY W/ 1.5 POWER CABLE



LED LINEAR UNDERCABINET LIGHTS (Use External Drivers)

CATALOG NO.	DESCRIPTION		
UCW6WW	2W	140LM	3000K - 6"
UCW6W	2W	168LM	6000K - 6"
UCW12WW	3W	250LM	3000K - 12"
UCW12W	3W	280LM	6000K - 12"
UCW20WW	5W	420LM	3000K - 20"
UCW20W	5W	462LM	6000K - 20"
UCW32WW	8W	590LM	3000K - 32"
UCW32W	8W	640LM	6000K - 32"
UCW40WW	11W	820LM	3000K - 40"
UCW40W	11W	880LM	6000K - 40"
UC6WW	2W	140LM	3000K - 6"
UC6W	2W	168LM	6000K - 6"
UC12WW	3W	250LM	3000K - 12"
UC12W	3W	280LM	6000K - 12"
UC20WW	5W	420LM	3000K - 20"
UC40WW	11W	820LM	3000K - 40"
UC40W	11W	880LM	6000K - 40"

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED ADJUSTABLE UNDERCABINET, 24V

CATALOG NO.	DESCRIPTION		
UC-ADJ-12W	5W	400LM	6000K - 11.81"
UC-ADJ-20WW	8W	600LM	3000K - 19.68"
UC-ADJ-20W	8W	640LM	6000K - 19.68"
UC-ADJ-40WW	16W	1200LM	3000K - 39.37"
UC-ADJ-40W	16W	1280LM	6000K - 39.37"
UC-ADJ-PIR	PIR SENSOR FOR U/C ADJUSTABLE SERIES		
UC-ADJ-DMR	TOUCH DIMMER WITH MEMORY FOR U/C ADJUSTABLE SERIES		

UNDER CABINET LIGHTING PARTS & ACCESSORIES

CATALOG NO.	DESCRIPTION
UCDIMMER	LED UNDER CABINET LIGHTS DIMMER
UCDIMMER-TOUCH	LINEAR UNDER CABINET TOUCH DIMMER TO CONNECT TO FIXTURES END, BLACK
UCDIMMER-TOUCH-WH	LINEAR UNDER CABINET TOUCH DIMMER TO CONNECT TO FIXTURES END, WHITE
UCJUNCTION-W	HARD WIRE POWER FEED IN / OUT, WHITE
UCSENS-PIR-1	PIR SENSOR, AUTO ON/OFF WHEN MOVEMENT, MAX 72W, 4" (10CM) RANGE, 120D, -20°C TO 40°C INDOORS
UCSENS-PIR	PIR SENSOR, AUTO ON/OFF WHEN MOVEMENT, MAX 72W, 4" (10CM) RANGE, 120D, -20°C TO 40°C INDOORS
UCCONCABLE	3.25 FT. CONNECTOR CABLE, BLACK
UCCONCABLE-WH	3.25 FT. CONNECTOR CABLE, WHITE
UCCONCABLE-10	10 FT. UNDER CABINET LIGHT CONNECTOR CABLE, BOTH SIDE MALE, BLACK
UCCONCABLE-10-WH	10 FT. UNDER CABINET LIGHT CONNECTOR CABLE, BOTH SIDE MALE, WHITE
UCCOP-3F	3 FT. UNDER CABINET LIGHT COUPLING, BOTH SIDE FEMALE, BLACK
UCCOP-3F-WH	3 FT. UNDER CABINET LIGHT COUPLING, BOTH SIDE FEMALE, WHITE
UCPOWERC-10F	10 FT. UNDER CABINET LIGHT POWER CONNECTOR, 1 SIDE MALE, 1 SIDE FEMALE, BLACK
UCPOWERC-10F-WH	10 FT. UNDER CABINET LIGHT POWER CONNECTOR, 1 SIDE MALE, 1 SIDE FEMALE, WHITE
UCRE04	4 OUTPUT EASY RECEPTACLE
UCRE08	8 OUTPUT EASY RECEPTACLE
UCAC01	CORNER CONNECTOR, BLACK
UCAC01-WH	CORNER CONNECTOR, WHITE
UCPLASCONN-WH	PLASTIC CONNECTOR, WHITE

FINAL PRODUCTION DEALS

WHILE SUPPLIES LAST

LED EMERGENCY DRIVER

CATALOG NO.	DESCRIPTION
ELB-2548-EXTR	LED EMERGENCY DRIVER FOR LED PRODUCTS WITH EXTERNAL DRIVER, UL RECOGNIZED 120-277 INPUT 25W 90

LED EMERGENCY DRIVER

CATALOG NO.	DESCRIPTION			
RHLED2-MV	1W per Head	3.6V/6V/9.9V/12 DC	Grey	Double
RHLED2-WP-MV	1W per Head	3.6V/6V/9.9V/12 DC	Grey	Double

COMBINATION LED EXIT SIGN & LED EMERGENCY, 120~277V, 21"(W) x 9"(H) x 4-7/16"(D)

CATALOG NO.	DESCRIPTION			
XT-CL-RB-EM	Universal Single/Double	Red	Black	NiCd

LED EXIT SIGN WITH REMOTE CAPABILITY, 120~277V

CATALOG NO.	DESCRIPTION			
XT-RCRW-EM	Universal Single/Double	RED	White	Lead Acid
XT-RCGW-EM	Universal Single/Double	GREEN	White	Lead Acid

EMERGENCY BATTERY BACKUPS

CATALOG NO.	DESCRIPTION
ELB-08120-AC	SPLIT 120VAC 8W Li-Ion EMERGENCY LED BACKUP FOR DOB FIXTURES
ELB-0860-FLEX	30-60VDC 8W Li-Ion LED EMERGENCY BACKUP WITH FLEX FOR BACKLIT PANELS
ELB-18150-B	SPLIT 50-150VDC 18W Li-Ion EMERGENCY LED BACKUP FOR LED T8 & T5 LAMPS AND RECESSED TRIMS, UL CEC

FINAL PRODUCTION DEALS
WHILE SUPPLIES LAST

SENSOR, IP66

CATALOG NO.	DESCRIPTION
MSO-IP66-KN	OUTDOOR BI-LEVEL PROGRAMMABLE MOTIONS SENSOR WITH 1/2" KNUCKLE

EXTENSION CORD

CATALOG NO.	DESCRIPTION
EX143-25	SJTW 14Awg/3C, 25 Ft, 13A, 125V, Outside Extension Cord, 10 Pcs/Ctn
EX163-50	SJTW 14Awg/3C, 50 Ft, 13A, 125V, Outside Extension Cord, 8 Pcs/Ctn
EXL143-50	SJTW 14Awg/3C, 50 Ft, 15A, 125V, Blue Outdoor Extension Cord, Lighted Plug, 6 Pcs/Ctn
EXL123-50	SJTW 3C/12Awg, 50 Ft, 15A, 125V, Blue Outdoor Extension Cord, Lighted Plug, 4 Pcs/Ctn

STRAIGHT ANGLE PLUG WITH THICK VINYL INSULATION

CATALOG NO.	DESCRIPTION
DRY5	Heavy-Duty Strain Relief Protects Cord Resulting In Longer Cord Life

VACANCY SENSOR AUTO/MANUAL-ON 120V W. LED INDC.

CATALOG NO.	DESCRIPTION
YM2105-W	Vacancy Sensor Auto/Manual-On 120V W. Led Indc.(No Neutral Required)

OCCUPANCY/VACANCY SENSORS

CATALOG NO.	DESCRIPTION
YM183-W	Occupancy PIR Sensor, 180°, 30FT (720FT), 120V 800/1200W max, Single Pole, Neutral Req.

NEED ADDITIONAL SERVICES?

REVIEW THE BELOW LIST OF FLAT RATE SERVICES OFFERED BY WESTGATE

Add a part number from the below lists to your PO to request additional services.

Optional Add-Ons:

PART #	SERVICE DESCRIPTION	2026 Terms
/SR-EXTW-3YR	3 years Additional Warranty	Request A Quote
/SR-STRG-14D	Additional 14days Storage*	Request A Quote
/SR-STRG-30D	Additional 30days Storage*	Request A Quote
/SR-EXPED-LTL	Expedited Pallet Delivery**	Request A Quote
/SR-SIGN-PKG	Signature Required For FedEx/UPS Delivery	Request A Quote

*** Westgate offers up to 14 days of free storage hold for your orders.**
**** Free freight is the standard speed is at Westgate's discretion.**

Mandatory Charges:

PART #	SERVICE DESCRIPTION	2026 Terms
/SR-RESI-D	Residential Pallet Delivery fee*	Request A Quote
/SR-LIFT-G	Lift Gate fee	Request A Quote
/SR-REDELIVERY	Truck Re-delivery Fee	Request A Quote
/SR-WAIT-T	Wait Fee At The Delivery Location	Request A Quote

*** The additional fee applies even if when the standard shipping is Prepaid by Westgate.**
Westgate will send a new invoice referencing the original purchase order number when the additional freight charges occur after the initial invoice.

Westgate will send a new invoice referencing the original purchase order number when the additional freight charges occur after the initial invoice.

Download the Latest Catalogue

@WESTGATEMFG

Lighting the Backbone of America.

WWW.WESTGATEMFG.COM

ASK YOUR AUTHORIZED WESTGATE DISTRIBUTOR

$1