

# Yamamoto

JAPANESE PRECISION MEETS AMERICAN MUSCLE

# 275

PROUDLY BASED IN BLOOMINGTON, IL, **USA**, YAMAMOTO NORTH AMERICA REPRESENTS THE WORLD'S BEST SOFT-MOUNT INDUSTRIAL LAUNDRY EQUIPMENT.

BACKED BY AN EXTENSIVE SUPPORT NETWORK, JAPANESE ENGINEERING, AND A **5 YEAR WARRANTY**, OUR EQUIPMENT IS BUILT TO EXCEED **50,000 CYCLES!**

## KEY FEATURES:

- **2 WAY 14 DEGREE TILT**
- **ONE OF A KIND, SELF-SERVICEABLE & PNEUMATIC DRAIN VALVE**
- **PNEUMATIC SOFTMOUNT SUSPENSION**
- **TRIPLE SEAL AUTOMATIC BEARING LUBRICATOR**
- **OVERSIZED 2-PIECE BRASS PNEUMATIC FILL VALVES**
- **EASY WATER RECLAMATION CONVERSION**
- **100 PROGRAM TOUCHSCREEN CONTROL**
- **UP TO 8 CHEMICAL INJECTION PORTS**



A TRUSTED CHOICE BY PROFESSIONALS IN HOSPITALITY, HEALTHCARE, ATHLETIC, & INDUSTRIAL LAUNDRIES.

FOR **+75 YEARS**



## WITH YOU FOREVER

YAMAMOTO NORTH AMERICA LLC PO BOX 3264 BLOOMINGTON, IL 61701  
WWW.YAMAMOTO-NA.COM - 866.204.0519 - INFO@YAMAMOTO-NA.COM

Model No.		WUN275	
Capacity (Best Practices)		125kg	275bs
Drum	Diameter	φ1320mm	Φ52.0"
	Depth	860mm	33.9"
	L / Cubic Feet	1177L	41.6ft <sup>3</sup>
Machine Size (Packing Size)	Height	2549mm(2550mm)	100.4"(100.4")
	Width	2109mm(2280mm)	83.0"(89.8")
	Depth	2601mm(2760mm)	102.4"(108.7")
Weight of empty machine		5900kg	13008lbs
Crated Weight		6000kg	13228lbs
Drum Speed	Washing Speed	20~40rpm	
	Extraction Speed	100~640 rpm	
G - Force	High Speed	303G	
Dynamic Loading	Frequency	10.7Hz	
	Dynamic floor weight	3000kg/m <sup>2</sup>	614.7lbs/ft <sup>2</sup>
Loading Door	Door Height	1417mm	55.8"
	Door Opening	φ800mm	φ31.5"
Power	Electrical phase, Voltage, Frequency	3-phase, AC200~240V, 60Hz	
	Full load current	65A	
Minimum Supply-Circuit Conductor Ampacity		80A	
Maximum rating of Supply Circuit Overcurrent Protective Device		80A	
Motor Size		25HP(18.5KW)	
Cold water Supply	Connection Port	2NPT	
	Water Supply Pressure	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Hot water Supply	Connection Port	2NPT	
	Water Supply Pressure	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Detergent Box Water	Connection Port	1/2NPT	
	Water Supply Pressure	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Water Drain	Connection Port	4NPT	
Compressed-Air	Connection Port	3/8"O.D.	
	Pressure	0.7-1.0MPa , 101.5-43.5psi , 7-10bar	
Steam	Supply Port	1NPT	
	Pressure	0.5-0.7MPa, 72.5-101.5psi , 5-7bar	
Usage environment	Temperature Of Surrounding	5-45°C	41-113°F
	Humidity	30-85%	

