

Yamamoto

JAPANESE PRECISION MEETS AMERICAN MUSCLE

1000

PROUDLY BASED IN BLOOMINGTON, IL,
USA, YAMAMOTO NORTH AMERICA
REPRESENTS THE WORLD'S BEST
SOFT-MOUNT INDUSTRIAL LAUNDRY
EQUIPMENT.

BACKED BY AN EXTENSIVE SUPPORT
NETWORK, JAPANESE ENGINEERING, AND A
5 YEAR WARRANTY, OUR EQUIPMENT IS
BUILT TO EXCEED **50,000** CYCLES!

KEY FEATURES:

- ONE OF A KIND, SELF-SERVICEABLE DRAIN VALVE
- DUAL SOFTMOUNT SUSPENSION
- TRIPLE SEAL AUTOMATIC BEARING LUBRICATOR
- OVERSIZED 2-PIECE BRASS FILL VALVES
- POST & PIN DOOR LOCK ASSEMBLY
- 100 PROGRAM TOUCHSCREEN CONTROL
- UP TO 8 CHEMICAL INJECTION PORTS



A TRUSTED CHOICE BY
PROFESSIONALS IN HOSPITALITY,
HEALTHCARE, ATHLETIC, &
INDUSTRIAL LAUNDRIES.

FOR **+75** YEARS

WITH YOU FOREVER

YAMAMOTO NORTH AMERICA LLC PO BOX 3264 BLOOMINGTON, IL 61701
WWW.YAMAMOTO-NA.COM - 866.204.0519 - INFO@YAMAMOTO-NA.COM

Model No.		WUN100	
Capacity (Best Practices)		46 kg	100.0 lbs
Drum	Diameter	φ965 mm	φ37.9"
	Depth	592 mm	23.3"
	L/ Cubic Feet	432 L	15.2 cu.ft
	Pound capacity	100 lbs	
Machine Size (Packing Size)	Height	1825mm (2000)	71.9" (78.8)
	Width	1250mm (1450)	49.1" (57.1)
	Depth	1505mm (1700)	59.2" (67)
Weight of empty machine		1340 kg	2955 lbs
Crated Weight		1400 kg	3090 lbs
Drum Speed	Washing Speed	20~50rpm	
	Extraction Speed	100~750rpm	
G - Force	High Speed	303 G	
Dynamic Loading	Frequency	12.5 Hz	
	Dynamic floor weight	2000kg/m ²	409.6lb/ft ²
Loading Door	Door Height	980 mm , 38.6"	
	Door Opening	φ475 mm , φ18.7"	
Power	Electrical phase, Voltage, Frequency	3-phase, AC208~230V, 60Hz	
	Maximum Amperage	25A	
Minimum Ampacity	Supply-Circuit Conductor	40A	
Maximum Rating of Supply Circuit Overcurrent Protective Device		40A	
Motor Size		10HP (7.5KW)	
Cold Water Supply	Connection Port	1·1/2NPT	
	Water Supply Pressure	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Hot Water Supply	Connection Port	1·1/2NPT	
	Water Supply Pressure	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Detergent Cup Water	Connection Port	1/2NPT	
	Water Supply Pressure	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Water Drain	Connection Port	3NPT	
Steam	Supply Port	3/4NPT	
	Drain Port	3/8NPT	
	Pressure	0.4-0.6MPa , 58-87psi , 4-6bar	
Heating System		Hot Water Supply& Steam	
Usage environment	Temperature Of Surrounding	5-45°C , 41-113°F	
	Humidity	30-85%	
	Altitude	The machine should be installed in the altitude which is lower than in 3280 ft.	

