

# Yamamoto

JAPANESE PRECISION MEETS AMERICAN MUSCLE

# 70

PROUDLY BASED IN BLOOMINGTON, IL,  
**USA**, YAMAMOTO NORTH AMERICA  
REPRESENTS THE WORLD'S BEST  
SOFT-MOUNT INDUSTRIAL LAUNDRY  
EQUIPMENT.

BACKED BY AN EXTENSIVE SUPPORT  
NETWORK, JAPANESE ENGINEERING, AND A  
5 YEAR WARRANTY, OUR EQUIPMENT IS  
BUILT TO EXCEED **50,000** CYCLES!

## KEY FEATURES:

- ONE OF A KIND, SELF-SERVICEABLE DRAIN VALVE
- DUAL SOFTMOUNT SUSPENSION
- TRIPLE SEAL AUTOMATIC BEARING LUBRICATOR
- OVERSIZED 2-PIECE BRASS FILL VALVES
- POST & PIN DOOR LOCK ASSEMBLY
- 100 PROGRAM TOUCHSCREEN CONTROL
- UP TO 8 CHEMICAL INJECTION PORTS



A TRUSTED CHOICE BY  
PROFESSIONALS IN HOSPITALITY,  
HEALTHCARE, ATHLETIC, &  
INDUSTRIAL LAUNDRIES.

FOR **+75** YEARS

## WITH YOU FOREVER

YAMAMOTO NORTH AMERICA LLC PO BOX 3264 BLOOMINGTON, IL 61701  
WWW.YAMAMOTO-NA.COM - 866.204.0519 - INFO@YAMAMOTO-NA.COM

Model No.		WUN70	
Capacity		31.8kg	70lbs
Drum	Diameter	890mm	35.0"
	Depth	461mm	18.1"
	L/Cubic Feet	286 L	10.1cu. Ft
Machine Size (Packing Size)	Height	1715mm (1900)	67.5" (74.9)
	Width	1150mm (1300)	45.3" (51.2)
	Depth	1295mm (1500)	51.0" (59.1)
Weight of empty machine		850kg	1875lbs
Crated Weight		905kg	2000lbs
Drum Speed	Washing Speed	20-50rpm	
	Extraction Speed	100-800rpm	
G - Force	High Speed	318G	
Dynamic Loading	Frequency	13.3 Hz	
	Dynamic Floor Weight	1700kg/m2	348.2lb/ft2
Loading Door	Door Height	915mm	36"
	Door Opening	475mm	18.7"
Power	Electrical Phase, Voltage, Frequency	Three-phase, AC208-230V, 60Hz / *2Three - Phase or Single-phase, AC208-230V,60Hz	
	Maximum Amperage	20A / *2 22A	
Minimum Supply-Circuit Conductor Ampacity		30A	
Maximum Rating of Supply Circuit Overcurrent Protective Device		30A	
Motor Size		7.SHP (5.Skw)	
Cold Water Supply	Connection Port	1 NPT	
	Water Supply Pressure	0.1-0.3MPa, 14.5-43.5psi, 1-3bar	
Hot Water Supply	Connection Port	1 NPT	
	Water Supply Pressure	0.1-0.3MPa, 14.5-43.5psi, 1-3bar	
Detergent Cup Water	Connection Port	½ NPT	
	Water Supply Pressure	0.1-0.3MPa, 14.5-43.5psi, 1-3bar	
Water Drain	Connection Port	2 • 1/2NPT	
Steam	Supply Port	1/2NPT	
	Drain Port	3/8NPT	
	Pressure	0.4-0.6MPa,58-87psi, 4-6bar	
Heating System		Hot Water Supply & Steam	
Usage Environment	Temperature of Surrounding	5-45•c, 41-113°F	
	Humidity	30-85%	
	Altitude	The machine should be installed in the altitude which is lower than in 3280 ft.	

