

Yamamoto

JAPANESE PRECISION MEETS AMERICAN MUSCLE

55

PROUDLY BASED IN BLOOMINGTON, IL,
USA, YAMAMOTO NORTH AMERICA
REPRESENTS THE WORLD'S BEST
SOFT-MOUNT INDUSTRIAL LAUNDRY
EQUIPMENT.

BACKED BY AN EXTENSIVE SUPPORT
NETWORK, JAPANESE ENGINEERING, AND A
5 YEAR WARRANTY, OUR EQUIPMENT IS
BUILT TO EXCEED **50,000** CYCLES!

KEY FEATURES:

- ONE OF A KIND, SELF-SERVICEABLE DRAIN VALVE
- DUAL SOFTMOUNT SUSPENSION
- TRIPLE SEAL AUTOMATIC BEARING LUBRICATOR
- OVERSIZED 2-PIECE BRASS FILL VALVES
- POST & PIN DOOR LOCK ASSEMBLY
- 100 PROGRAM TOUCHSCREEN CONTROL
- UP TO 8 CHEMICAL INJECTION PORTS



A TRUSTED CHOICE BY
PROFESSIONALS IN HOSPITALITY,
HEALTHCARE, ATHLETIC, &
INDUSTRIAL LAUNDRIES.

FOR **+75** YEARS

WITH YOU FOREVER

YAMAMOTO NORTH AMERICA LLC PO BOX 3264 BLOOMINGTON, IL 61701
WWW.YAMAMOTO-NA.COM - 866.204.0519 - INFO@YAMAMOTO-NA.COM

Model No.		WUN55	
Capacity (Best Practices)		25kg	55.0 lbs
Drum	Diameter	φ762 mm	φ30.0"
	Depth	486 mm	19.1"
	L/ Cubic Feet	221 L	7.8 cu.ft
	Pound capacity	55 lbs	
Machine Size (Packing Size)	Height	1565mm (1750)	61.6" (68.9)
	Width	1016mm (1200)	40.0" (47.3)
	Depth	1235mm (1400)	48.7" (55.2)
Weight of empty machine		660 kg	1455 lbs
Crated Weight		705 kg	1555 lbs
Drum Speed	Washing Speed	20~50rpm	
	Extraction Speed	100~880rpm	
G - Force	High Speed	330 G	
Dynamic Loading	Frequency	14.7 Hz	
	Dynamic floor weight	1500kg/m ²	307.2lb/ft ²
Loading Door	Door Height	835 mm	32.9"
	Door Opening	φ405 mm	φ15.9"
Power	Electrical phase, Voltage, Frequency	3-phase, AC208~230V, 60Hz	
	Maximum Amperage	14A	
Minimum Supply-Circuit Conductor Ampacity		20A	
Maximum Rating of Supply Circuit Overcurrent Protective Device		20A	
Motor Size		5 HP (3.7kw)	
Cold Water Supply	Connection Port	1NPT	
	Water Supply Pressure	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Hot Water Supply	Connection Port	1NPT	
	Water Supply Pressure	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Detergent Cup Water	Connection Port	1/2NPT	
	Water Supply Pressure	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Water Drain	Connection Port	2·1/2NPT	
Steam	Supply Port	1/2NPT	
	Drain Port	3/8NPT	
	Pressure	0.4-0.6MPa , 58-87psi , 4-6bar	
Heating System		Hot Water Supply& Steam	
Usage environment	Temperature Surrounding Of	5-45°C , 41-113°F	
	Humidity	30-85%	
	Altitude	The machine should be installed in the altitude which is lower than in 3280 ft.	

