

Yamamoto

JAPANESE PRECISION MEETS AMERICAN MUSCLE

30

PROUDLY BASED IN BLOOMINGTON, IL,
USA, YAMAMOTO NORTH AMERICA
REPRESENTS THE WORLD'S BEST
SOFT-MOUNT INDUSTRIAL LAUNDRY
EQUIPMENT.

BACKED BY AN EXTENSIVE SUPPORT
NETWORK, JAPANESE ENGINEERING, AND A
5 YEAR WARRANTY, OUR EQUIPMENT IS
BUILT TO EXCEED **50,000** CYCLES!

KEY FEATURES:

- ONE OF A KIND, SELF-SERVICEABLE DRAIN VALVE
- DUAL SOFTMOUNT SUSPENSION
- TRIPLE SEAL AUTOMATIC BEARING LUBRICATOR
- OVERSIZED 2-PIECE BRASS FILL VALVES
- POST & PIN DOOR LOCK ASSEMBLY
- 100 PROGRAM TOUCHSCREEN CONTROL
- UP TO 8 CHEMICAL INJECTION PORTS



A TRUSTED CHOICE BY
PROFESSIONALS IN HOSPITALITY,
HEALTHCARE, ATHLETIC, &
INDUSTRIAL LAUNDRIES.

FOR **+75** YEARS

WITH YOU FOREVER

YAMAMOTO NORTH AMERICA LLC PO BOX 3264 BLOOMINGTON, IL 61701
WWW.YAMAMOTO-NA.COM - 866.204.0519 - INFO@YAMAMOTO-NA.COM

Model No.		WUN30 (3-phase/※Single-phase)	
Capacity (Best Practices)		10kg	30.0 lbs
Drum	Diameter	Φ660 mm	Φ25.9"
	Depth	375 mm	Φ14.7"
	L/ Cubic Feet	128 L	4.5 cu.ft
	Pound capacity	30 lbs	
Machine Size (Packing Size)	Height	1550mm (1750)	61.1" (68.9)
	Width	870mm (1070)	34.3" (42.2)
	Depth	1070mm (1270)	42.2" (50.1)
Weight of empty machine		500 kg	1103 lbs
Crated Weight		600 kg	1323 lbs
Drum Speed	Washing Speed	20~50rpm	
	Extraction Speed	100~800rpm / ※100-750rpm	
G - Force	High Speed	236 G / ※207 G	
Dynamic Loading	Frequency	15.8 Hz	
	Dynamic floor weight	1400kg/m ²	328lb/ft ²
Loading Door	Door Height	835 mm	32.9"
	Door Opening	φ405 mm	φ15.9"
Power	Electrical phase, Voltage, Frequency	3-phase /※Single-phase , AC208~230V, 60Hz	
	Maximum Amperage	9A	
Minimum Supply-Circuit Conductor Ampacity		15A	
Maximum Rating of Supply Circuit Overcurrent Protective Device		15A	
Motor Size		3 HP (2.2kw)	
Cold Water Supply	Connection Port	3/4NPT	
	Water Pressure Supply	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Hot Water Supply	Connection Port	3/4NPT	
	Water Pressure Supply	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Detergent Cup Water	Connection Port	1/2NPT	
	Water Pressure Supply	0.1-0.3MPa , 14.5-43.5psi , 1-3bar	
Water Drain	Connection Port	2·1/2NPT	
Steam	Supply Port	1/2NPT	
	Drain Port	3/8NPT	
	Pressure	0.4-0.6MPa , 58-87psi , 4-6bar	
Heating System		Hot Water Supply& Steam	
Usage environment	Temperature of Surrounding	5-45°C , 41-113°F	
	Humidity	30-85%	
	Altitude	The machine should be installed in the altitude which is lower than in 3280 ft.	

※WUN104 single-phase

