

# Rustic Gray




## Porcelain Pavers

Our Rustic Gray porcelain paver reflects a beautiful ashen finish with soft undertones to satisfy traditional and classic tastes. Weathered wood finishes replicate the appearance of natural reclaimed wood but without the disadvantages of fading, twisting, warping, decay, and poor fire resistance inherent in wood.

Tile Tech® hardscape systems provide architects and design professionals with a complete solution to transform any roof deck, walkway, driveway, courtyard, or patio into beautiful, useful spaces. Embracing USGBC LEED standards, our paving products boast a composition that includes 35% pre-consumer recycled materials. With no traces of Volatile Organic Compounds (VOC) and a Solar Reflectance Index (SRI) of  $\geq 32$ , porcelain pavers emerge as an eco-friendly choice that goes beyond conventional paving solutions.



VISIT OUR 3D MODEL LIBRARY FOR INSTALLATION TIPS!




# Specifications

## Available Sizes (Rectified)




23-1/2" x 23-1/2"  
597 x 597 mm



23-1/2" x 47-1/2"  
597 x 1207 mm

## Color and Shade Variation



**V3**  
Moderate variation

## LEED Opportunities

- Recycled Content:  
MR Credit 4.1 and 4.2 (2 LEED pts.)
- Regional Materials (500 mi)  
EQ Credit 4.2 (1 LEED pt.)
- Low Emmitting Materials  
EQ Credit 4.2 (1 LEED pt.)
- Innovation in Design  
ID Credit 1.1 - 1.4 (1-4 LEED pts.)
- Heat Island Effect (Non-roof)  
SS Credit 7.1 (1 LEED pt.)

## Shipping Details

- Packaging (24" x 24")  
72 pcs. | 279 Sq.Ft. | 2,700 lbs./pallet
- Packaging (24" x 48")  
32 pcs. | 256 Sq.Ft. | 2,350 lbs./pallet



Thickness:	3/4" 19 mm	
Weight:	9 lbs./Sq.Ft.	
Water Absorption:	Max. 0.05%	ISO10543-3
Static Load (Center)	≥1,840 lbf.	ASTM N/A, EN 12825
Bending Strength	3,300 lbs.	ASTM C-648, ISO 10545-4
Distribution Load	2,500 lbs.	ASTM N/A, EN 12825
Slip Resistant	R11	DIN51130
COF (Wet, Dry)	>0.60	ASTM C-1028-7, ISO N/A
Abrasion Resistant	Yes (Class 5)	ASTM C-1027, ISO 10545-6
Stain Resistant	Yes (Class 5)	ASTM C-1378, ISO 10545-14
Frost Resistant	Yes	ASTM C-1026, ISO 10545-12
Chemical Resistance	Yes	ASTM C-650, ISO 10545-13
Solar Reflectance (SRI)	50	
Rectified	Yes	

Full test reports and specification details available on our website.

