

The **Revillusion**® Family of Electric Fireplaces



Experience Better Living.

Firebox
Series



Revillusion®

Mesmerizing Flames. Revolutionary Design.

Available
in 24, 30, 36
& 42 inch
widths



Revellusion®



Key Benefits



Timeless Aesthetic

The ageless appeal of the fireplace creates an authentic, ever-lasting impression.



Design with Style

Tailor your fireplace to your desired look and feel by selecting between a more traditional or modern aesthetic.



Complete Perspective

Enjoy a full-depth view of the fireplace with the ability to see clearly through the flames.



Revillusion® Flame Effect

Patented Dimplex flame effect producing ultra-realistic flames that mimic natural fire.



Powerful Heating

Powerful fan-forced heater provides on-demand heat up to 1,000 sq. ft.



Authentic Realogs®

Handcrafted from real wood, these logs feature inner LED lights that emit a lifelike, pulsating glow, simulating burning logs.



Reflective Flame Panel

The translucent acrylic panel allows you to enjoy the look of flames appearing from within the logs.

Herringbone Backer



24" (RBF24DLX)



30" (500002388)



36" (500002400)




36" Portrait (500002398)



42" (500002410)

Accessory:



Trim Kit (Available in 24" or 30" only)



Mood-maker Remote

Customize the light color and intensity for a fireplace that reflects your personality.

Available
in 24, 30, 36
& 42 inch
widths



Revellusion®





Key Benefits



Timeless Aesthetic

The ageless appeal of the fireplace creates an authentic, ever-lasting impression.



Design with Style

Tailor your fireplace to your desired look and feel by selecting between a more traditional or modern aesthetic.



Complete Perspective

Enjoy a full-depth view of the fireplace with the ability to see clearly through the flames.



Revillusion® Flame Effect

Patented Dimplex flame effect producing ultra-realistic flames that mimic natural fire.



Powerful Heating

Powerful fan-forced heater provides on-demand heat up to 1,000 sq. ft.



Authentic Realogs®

Handcrafted from real wood, these logs feature inner LED lights that emit a lifelike, pulsating glow, simulating burning logs.



Reflective Flame Panel

The translucent acrylic panel allows you to enjoy the look of flames appearing from within the logs.



Mood-maker Remote

Customize the light color and intensity for a fireplace that reflects your personality.

Weathered Concrete Backer



24" (RBF24DLXWC)



30" (500002389)



36" (500002401)




36" Portrait (500002399)




42" (500002411)

Accessory:



Trim Kit (Available in 24" or 30" only)

Available
in 20 &
25 inch
widths



Revillusion® Log Sets



Key Benefits



Artful Design

Realistic flames, and quality crafted logs come together to create an illusion of a true burning fire.



Complete Perspective

Enjoy a full-depth view to the back of the hearth with the ability to see clearly through the flames.



Instant Coziness

Simply plug-in and savor the gentle dance of flames and the snug warmth it brings.



Revillusion® Flame Effect

Patented Dimplex flame effect producing ultra-realistic flames that mimic natural fire.



Authentic Realogs®

Handcrafted from real wood, these logs feature inner LED lights that emit a lifelike, pulsating glow, simulating burning logs.



Reflective Flame Panel

The translucent acrylic panel allows you to see to the back of the existing hearth space and see the flames appear from within the logs.



Simple Plug-in

No installation required; simply plug into any standard household outlet anywhere you'd like.



RLG20 (shown with Ash Mat accessory)



RLG25



Easy Control

Use the included remote or hidden touch controls to easily operate your fireplace.

Revillusion Fireplace Comparison

Series	Revillusion® Deluxe	Revillusion®				Revillusion® Log Set	
Size	24"	30"	36"	36"P	42"	20"	25"
Ember Bed	Realogs®	Realogs®				Realogs®	Realogs® with Ash Mat
Flame Color Settings	Adjust flame base color from red and orange						Adjust the flame base color to red or orange
Flame Effect	Revillusion® Flame					Revillusion® Flame	
Flame Technology	Optiflame®	Optiflame®	Optiflame®	Optiflame®	Optiflame®	Optiflame®	Optiflame®
Flame Speed	•						
Flame Only	•	•	•	•	•	•	•
Installation	Built-In					Log Set	
Interior Surround	Herringbone or Weathered Concrete Interior						
Light Settings	Mood Lighting Brightness and Flicker Ambient Light Sensor					Brightness & Flicker 360° Light	
Heat Operation	ComfortSaver®	Powerful Supplemental Heat - Option to use 240V supply for up to 9200 BTU				Supplemental heating	
Heating Range	Up to 1,000 sq. ft.	Up to 1,000 sq. ft.				Up to 1,000 sq. ft.	
Heater Element	Ceramic	Steel Sheathed				Ceramic	
Heat Disable	Onboard controls or hardware disconnect						
Heat Only	•	•	•	•	•	•	•
Built-in Thermostat	•	•	•	•	•		
Wiring Type	Hardwire (Optional 120V Plug Kit Included)					Plug-in	
Volts	120	120 208 240				120	120
Watts	1500	1375 1975 2575				1500	1500
BTU	5118	4400 6745 8794				5118	5118
Display	•	•	•	•	•		
Remote Control	Mood-maker Remote Hidden-Touch Controls					Membrane Remote	
Timer	•	•	•	•	•		
Optional Accessories	Trim Kit	Trim Kit				Ash Mat	
Remote Control	•	•	•	•	•	•	•
Warranty Include parts/service	2-year limited	2-year limited	2-year limited	2-year limited	2-year limited	1-year limited	2-year limited
Dimensions (WxHxD)	25-1/4 × 22-7/8 × 12-1/8 in 64.0 × 58.1 × 30.7 cm	31-1/8 × 26-5/8 × 12-1/8 in 79.2 × 67.4 × 30.7 cm	37-1/8 × 26-5/8 × 12-1/8 in 94.4 × 67.4 × 30.7 cm	37-1/8 × 31 × 12-1/8 in 94.4 × 78.8 × 30.7 cm	43-1/4 × 31 × 12-1/8 in 109.8 × 78.8 × 30.7 cm	23-3/4 × 19 × 12-1/2 in 60.3 × 48.2 × 31.7 cm	25-5/8 × 19 × 13 in 65.0 × 48.2 × 32.9 cm



Experience Better Living.

Scan for more information on dimensions, accessories, technical details.

To view full series visit: dimplex.com

1-800-668-6663

