

CHEMICAL & STAIN RESISTANCE

ACIDS	5 MINUTES	24 HOURS
Acetic Acid - 5%	0	0
Acetic Acid - 28%	0	0
Citric Acid - 10%	0	0
Hydrochloric Acid - 5%	0	0
Hydrochloric Acid - 10%	0	0
Sodium Hydroxide - 5%	0	0
Sodium Hydroxide - 10%	0	0
Sulfuric Acid - 5%	0	0
Sulfuric Acid - 10%	0	0

BASES / ALKALIS	5 MINUTES	24 HOURS
Ammonia - 5%	0	0
Ammonium Hydroxide - 10%	0	0
Ammonium Hydroxide - 30%	0	0
Sodium Carbonate - 10%	0	0

ALCOHOLS	5 MINUTES	24 HOURS
Ethyl (Denatured) Alcohol - 30%	0	0
Ethyl (Denatured) Alcohol - 70%	0	0
Ethyl (Denatured) Alcohol - 90%	0	0
Hand Sanitizer (Alcohol Based)	0	0
Rubbing Alcohol (70% Isopropyl)	0	0

AROMATICS	5 MINUTES	24 HOURS
Crude Oil	0	0
Fuel Oil #1	0	0
Kerosene	0	0
Mineral Oil	0	0
Mineral Spirits (White Spirit)	0	0
Turpentine	0	0
Unleaded Gasoline (Regular Grade)	0	0

HEALTHCARE	5 MINUTES	24 HOURS
Aniline Blue	0	0
Betadine Skin Cleanser	3C	3C
Betadine Solution - 10%	3C	3C
Blood	0	0
Disclosing Solution (to show plaque on teeth)	3C	3C
Formaldehyde - 37%	0	0
Hematoxylin	3C	3C
Iodine Gram Stain	3C	3C
Iodine Tincture	3C	3C
Methylene Blue	3C	3C
Potassium Permanganate - 1.5%	0	0
Silver Nitrate - 5%	0	0
Tincture of Benzoin	0	0
Urea Solution	0	0
Wright's Blood Stain	0	0

CLEANERS / DISINFECTANTS	5 MINUTES	24 HOURS
A456 II Germicide	0	0
Acetone	0	0
Bleach - 5.25%	0	0
Bleach - 10%	0	0
Disinfectant - 5% Phenol	0	0
Ecoshine Stainless Steel Polish	0	0
Lemon Eze Cream Cleanser	0	0
Lime-A-Way	0	0
QC 31 Neutral Cleaner	0	0
QC 52 Glass Cleaner	0	0
QC 53 General Purpose Cleaner	0	0

OTHER STAINING AGENTS	5 MINUTES	24 HOURS
Ball Point Pen	0	0
Bicarbonate	0	0
Coffee (Hot)	0	0
Cola Soda	0	0
Hair Dye	0	0
Olive Oil	0	0
Permanent Marker	0	0
Printer Toner	0	0
Red Kool Aid	0	0
Red Wine	0	0
Shoe Polish - Paste Brown	0	0
Tar	0	0
Yellow Mustard	0	0

RATINGS KEY
 0 - No Change
 1 - Slight Change
 2 - Moderate Change
 3 - Severe Change
 D: Surface Dulling
 A: Surface Attack
 C: Color Change