

Architects/Roof Consultants

HICKMAN

EDGE SYSTEMS

PRE-ENGINEERED EDGE METAL SOLUTIONS

www.HickmanEdgeSystems.com | 828-676-1700

Bringing your vision to life.



PROTECTING THE INTEGRITY OF YOUR DESIGN AND ROOF

In any building project, the roof edge is a vital part of the structure that cannot be overlooked. It is the frontline of defense and key component to protecting the building from structural damage in any inclement weather. But you also want to make sure that it matches the aesthetics of your overall design. There are a variety of questions you want to ask yourself when you are selecting the roof edge system.

Will it look the way you want?

Will it fit within your timetable?

Will there be a warranty?

Will it comply with building requirements?

Will it look clean and consistent?

By choosing Hickman—the largest roof edge metal manufacturer in North America—**your answer can be a yes to all of these vital questions.**

Visit hickmanedgesystems.com for a full list of available products.

**THE INDUSTRY'S LARGEST
PORTFOLIO OF TESTED
ROOFING AND BUILDING
ENVELOPE SOLUTIONS.**

**Custom Engineered for Aesthetics
and Functionality**

**Backed by some of the Strongest
Warranties in the Industry**

ANSI/SPRI/FM 4435/ES-1 Tested

FM Approved for Wind Uplift Protection

**FASCIA | COPING
WOOD NAILER ALTERNATIVES
WATER CONTROL | ACCESSORIES**

TERMINEDGE FASCIA PRODUCTS





Hickman's TerminEdge fascia products combine custom engineering and superior performance with an attractive appearance.






The patented design of our extruded aluminum anchor bar on TerminEdge EX, XT, HG, and Canted Fascia, securely terminates the membrane—providing protection superior to any other shop-fabricated roof edge.

Simplify your projects with the high quality, economical prices, and quick-to-ship convenience you will get with our TerminEdge and TerminEdge One fascia products.




TERMINEDGE FASCIA ADVANTAGES

- Includes manufacturer's wind warranty
- ANSI/SPRI/FM 4435/ES-1 tested
- FM approved for wind uplift protection
- Miami-Dade County approved to comply with the "High Velocity Hurricane Zone of the Florida Building Code"
- Reusable/recyclable materials
- Multiple colors, materials, and sizes available

PRODUCT LINE	 EX	 EX MB	 XT	 XT MB	 HG	 HG MB
VERSIONS	• Single-Ply • Single-Ply With Butyl Strip	Built-up or Modified	Single-Ply	Built-up or Modified	• Single-Ply • Single-Ply With Butyl Strip	Built-up or Modified
COVER MATERIALS	24 ga., 22 ga., .040"	24 ga., 22 ga., .040"	22 ga., .050", .063"	22 ga., .050", .063"	24 ga., 22 ga., .040", .050", .063"	24 ga., 22 ga., .040", .050", .063"
WIND WARRANTY	Lifetime, 215 MPH	Lifetime, 215 MPH	Lifetime, 215 MPH	Lifetime, 215 MPH	Lifetime, 215 MPH	Lifetime, 215 MPH
ANSI/SPRI/FM 4435/ES-1	X	X	X	X	X	X
FM APPROVED	X	X	X	X	X	X
MIAMI-DADE COUNTY	X	X	X	X	X	X

PRODUCT LINE	 CANTED EX WD	 CANTED EX	 CANTED XT WD	 CANTED XT	 DRIP EDGE EX
VERSIONS	Galvanized Waterdam	Existing Beveled Wood Nailers	Galvanized Waterdam	Existing Beveled Wood Nailers	• Flat Flange • Pitched Flange
COVER MATERIALS	24 ga., 22 ga., .040", .050", .063"	24 ga., 22 ga., .040", .050", .063"	22 ga., .050", .063"	22 ga., .050", .063"	24 ga., 22 ga., .040"
WIND WARRANTY	Lifetime, 215 MPH	Lifetime, 215 MPH	Lifetime, 215 MPH	Lifetime, 215 MPH	Lifetime, 215 MPH
ANSI/SPRI/FM 4435/ES-1	X		X		X
FM APPROVED	X		X		X
MIAMI-DADE COUNTY	X		X		X

TERMINEDGE & TERMINEDGE ONE FASCIA PRODUCTS




PRODUCT LINE					
	TERMINEDGE	TERMINEDGE ONE	TERMINEDGE ONE MB	TERMINEDGE ONE EXTENDED	TERMINEDGE ONE EXTENDED MB
VERSIONS	Single-Ply	Single-Ply	Built-up or Modified	Single-Ply	Built-up or Modified
COVER MATERIALS	24 ga., 22 ga. .040", .050"	24 ga., 22 ga. .040", .050", .063"	24 ga., 22 ga. .040", .050", .063"	22 ga. .050", .063"	22 ga. .050", .063"
WIND WARRANTY	20 Year, 120 MPH	20 Year, 120 MPH	20 Year, 120 MPH	20 Year, 120 MPH	20 Year, 120 MPH
ANSI/SPRI/FM 4435/ES-1	X	X*	X*	X	X
FM APPROVED	X	X*	X*	X	X
MIAMI-DADE COUNTY	X	X*	X*	X	X




*Tested in 24 ga. 22 ga, and .040" Only



OTHER FASCIA PRODUCTS

Versatile & Economical in a Range of Designs, Colors, & Finishes

PRODUCT LINE	 ECONOSNAP	 ECONOCRIMP	 SAFEGUARD NP
VERSIONS	Single-Ply, Snap-on	Single-Ply, Crimp-on	Built-up or Modified
COVER MATERIALS	24 ga., 22 ga. .040", .050", .063"	24 ga., 22 ga. .040", .050", .063"	24 ga. 22 ga. .040", .050", .063"
WIND WARRANTY	20 Year, 120 MPH	20 Year, 120 MPH	20 Year, 120 MPH
ANSI/SPRI/FM 4435/ES-1	X	X	X
FM APPROVED	X	X	X
MIAMI-DADE COUNTY	X	X	X

PRODUCT LINE	 DRIP EDGE	 PVC/TPO DRIP EDGE	 SKIRTED PVC/TPO DRIP EDGE	 MBED-B	 GRAVEL STOP
VERSIONS	Kynar	PVC or TPO Coated	PVC or TPO Coated with Factory Applied- Flashing	Built-up or Modified	Kynar
COVER MATERIALS	24 ga., 22 ga. .040", .050", .063"	24 ga. with PVC or TPO Coating	24 ga. with PVC or TPO Coating	24 ga., 22 ga. .040", .050", .063"	24 ga., 22 ga. .040", .050", .063"
WIND WARRANTY	10 Year, 90 MPH	10 Year, 90 MPH	10 Year, 90 MPH	10 Year, 90 MPH	10 Year, 90 MPH
ANSI/SPRI/FM 4435/ES-1	X	X	X	X	X
FM APPROVED	X	X	X	X	X
MIAMI-DADE COUNTY	X	X	X	X	X







CREATIVE DESIGN SERIES

Design-Friendly Roof Edges That Inspire


Developed for the needs of design professionals, our Creative Design Series roof edges allow you to choose from unique designs that are perfect for any commercial building. The Creative Design Series fascia products will inspire your imagination and complement your vision.

CDS FASCIA ADVANTAGES

- 20 Year, 120 MPH Wind Warranty
- Versions: Bullnose, Cornice, Shadow Line
(Available in Single-Ply and Built-up or Modified)
- Available in a variety of materials and over 30 colors.

PRODUCT LINE	 BULLNOSE	 BULLNOSE MB	 CORNICE	 CORNICE MB	 SHADOWLINE	 SHADOWLINE MB
VERSIONS	Single-Ply	Built-up or Modified	Single-Ply	Built-up or Modified	Single-Ply	Built-up or Modified
COVER MATERIALS	24 ga., .040"	24 ga., .040"	22 ga. .050", .063"	22 ga. .050", .063"	22 ga. .050", .063"	22 ga. .050", .063"
WIND WARRANTY	20 Year, 120 MPH	20 Year, 120 MPH	20 Year, 120 MPH	20 Year, 120 MPH	20 Year, 120 MPH	20 Year, 120 MPH
ANSI/SPRI/FM 4435/ES-1	X	X				

ELIMINAILER-T & EDGEBOX RI




Premier Envelope Protection

Hickman's wood nailer alternative products make using a wood nailer obsolete. The roof perimeter and corners serve as the first line of defense against severe winds, rain, hail, storms, tornados, hurricanes, and much more. If the edge fails, the entire roof system is in jeopardy.

Replacing old wood nailers at the building perimeter with Eliminailer-T or EdgeBox RI significantly reduces the risk of failure and helps protect the entire roof system from costly damages and blow off.


WOOD NAILER ALTERNATIVE ADVANTAGES

- Lifetime, 215 MPH Wind Warranty
- Made with heavy gauge materials that will not warp, crack, split, rot, or deform
- Continuous insulation to the roof edge
- Non-combustible, made with recyclable and reusable materials

PRODUCT LINE	 ELIMINAILER-T	 ELIMINAILER-T FOR METAL RETROFITS	 EDGEBOX RI
VERSIONS	• 1.5" x 2.5" • 1.5" x 5.5" • 3" x 2.5" • 3" x 5.5" • 5.2" x 4" • 5.2" x 5.5"	• 1.5" x 5.5" • 3" x 5.5" (Pitched or Non-Pitched)	• 3.5" Min/16" Max (Width) • 1.25" Min/16" Max (Height)
MATERIALS	Heavy Gauge Aluminum	Heavy Gauge Aluminum	20 ga. Galv. Steel (Spines required when over 6")
WIND WARRANTY	Lifetime, 215 MPH	Lifetime, 215 MPH	Lifetime, 215 MPH
ANSI/SPRI/FM 4435/ES-1	X	X	X*
FM APPROVED	X	X	X*
MIAMI-DADE COUNTY	X	X	X*

* Tested up to 4.5" (Height) and 5.5" (Width)

PERMASNAP COPING









Proven Protection and a Perfect Fit

Continuing a tradition of innovative, rigorously tested roof edge systems, PermaSnap coping products are the perfect complement to your building's natural aesthetics. A variety of options, including standard and custom colors as well as anodized finishes, accommodate multiple roof conditions. It's exactly what you need for your building: the right design, the right quality, the right color and finish.


PERMASNAP ADVANTAGES

- Includes manufacturer's wind warranty
- ANSI/SPRI/FM 4435/ES-1 Tested
- FM and Miami-Dade County Approved
- Factory fabricated, welded, or quicklock miters create a clean appearance
- No exposed fasteners with snap-on design

PRODUCT LINE							
	PERMASNAP PREMIER PLUS	PERMASNAP PLUS	PERMASNAP PREMIER	PERMASNAP	PERMASNAP CANTILEVER	DOUBLE SLOPE	PERMASNAP CONTINUOUS CLEAT
VERSIONS	• Tapered • Flat • Existing Slope	• Tapered • Flat • Existing Slope	• Tapered • Flat • Existing Slope	• Tapered • Flat • Existing Slope	• Single • Double	• Tapered • Existing Slope	• Tapered • Flat • Existing Slope
WIND WARRANTY	Lifetime, 215 MPH	20-Year, 120 MPH	20-Year, 120 MPH	20-Year, 120 MPH	20-Year, 120 MPH	20-Year, 120 MPH	20-Year, 120 MPH
COVER MATERIALS	24 ga., 22 ga. .040", .050", .063"	24 ga., 22 ga. .040", .050", .063"	24 ga., 22 ga. .040", .050", .063"	24 ga., 22 ga. .040", .050", .063"	24 ga., 22 ga. .040", .050", .063"	24 ga., 22 ga. .040", .050", .063"	24 ga., 22 ga. .040", .050", .063"
DESIGN ELEMENTS	16 ga. Clip Flush Face Snap-on	16 ga. Clip Inside Flush; Outside Drip Snap-on	20 ga. Clip Drip Profile Snap-on	20 ga. Clip Inside Flush; Outside Drip Snap-on	16 ga. Clip/ 20 ga. Riser Flush Face Snap-on	20 ga. Clip Flush or Drip Snap-on	20 ga. Cleat (Inside and Outside) Crimp-on
TESTED MAX WALL WIDTH	24" (.040"/24 ga.) 32" (.050"/.063"/22 ga.)	24"	16"	16"	24"*	N/A	24"
ANSI/SPRI/FM 4435/ES-1	X	X	X	X	X*		X
FM APPROVED	X		X		X*		X
MIAMI-DADE COUNTY	X		X		X*		X

* Single Cantilever Version Only

ROOFER'S EDGE COPING




Great Quality at a Price That Fits Your Budget

Roofer's Edge Coping is a great alternative to shop-fabricated coping – economically priced, yet made to exacting standards.

ROOFER'S EDGE ADVANTAGES

- 10 Year, 90 MPH Wind Warranty
- Versions: Tapered, Flat, Existing Slope
- Cover Materials: 24 ga., or 22 ga. Steel and .040", .050", or .063" Aluminum
- ANSI/SPRI/FM 4435/ES-1 tested

CREATIVE DESIGN SERIES









Design-Friendly Options to Match Your Building

Developed for the needs of design professionals, the Creative Design Series is perfect for any commercial building. These unique products inspire the imagination and complement your vision for high-profile building projects.

CDS COPING ADVANTAGES

- 20 Year, 120 MPH Wind Warranty
- Versions: Box Face, Bullnose, Cornice, Leak-Tite, Shadowline, Stone-Look
- Available in a variety of materials and colors to match your unique design

PRODUCT						
VERSIONS	BOX FACE	BULLNOSE	SHADOWLINE	CORNICE	LEAK-TITE	STONE-LOOK
SIZES	Outside Face: 4.5" - 12" Inside Face: 2.25" - 6" Wall Size: 5" - 24"	Outside Face: 4.5" - 12" Inside Face: 2.25" - 6" Wall Size: 4" - 24"	Outside Face: 7.75" - 12" Inside Face: 6.5" - 10" Wall Size*: 7.25" - 24"	Outside Face: 7" - 12" Inside Face: 2.25" - 6" Wall Size: 5" - 24"	Outside Face: 3" - 12" Inside Face: 2.25" - 4" Wall Size**: 3.5" - 39.875"	Outside Face: 3.5" - 12" Inside Face: 2.25" - 6" Wall Size***: 5" - 32"
COVER MATERIALS	24 ga., 22 ga. Steel .040", .050", .063" Aluminum	22 ga. Steel .050", .063" Aluminum	22 ga. Steel .050", .063" Aluminum	22 ga. Steel .050", .063" Aluminum	24 ga., 22 ga. Steel .040", .050", .063" Aluminum	22 ga. Steel .050", .063" Aluminum

*ANSI/SPRI/FM 4435/ES-1 Tested Up to 16" Wall

**ANSI/SPRI/FM 4435/ES-1 Tested and FM/Miami-Dade Approved Up to 16" Wall

***ANSI/SPRI/FM 4435/ES-1 Tested and FM/Miami-Dade Approved Up to 32" Wall

WATER CONTROL







Superior Roof Drainage with an Attractive Appearance

Unique design, superior roof drainage, and attractive appearance make Wind Resistant gutters and downspouts stand out from the crowd. Wind Resistant and Wind Resistant XL Gutters are specifically engineered and tested to meet the requirements of the ANSI/SPRI GT-1 Standard for Gutter Systems Used with Low-Slope Roofs. The design incorporates heavy-gauge aluminum internal gutter brackets for strength and support to ensure the system stays secured to prevent wind uplift—no external brackets or wind straps needed.

WATER CONTROL ADVANTAGES

- Includes manufacturer's wind warranty
- ANSI/SPRI/GT-1 tested to comply with International Building Code (Wind Resistant & XL Gutters ONLY)
- Pre-punched fastening holes ensure correct fastener placement and spacing
- Prefabricated miters, fasteners, and accessories ensure proper fit and eliminates field fabrication

PRODUCT LINE					
	WIND RESISTANT GUTTERS	WIND RESISTANT XL GUTTERS	OTHER GUTTERS	INDUSTRIAL DOWNSPOUTS	OTHER DOWNSPOUTS
VERSIONS	• Offset • Chamfer • Box	• Box	• Half Round • K-Style	• Box • Open Face	• Round • Corrugated
SIZES	Bottom Width & Front Height: 5.25", 5.75", 6.25", 6.75", 7.25", 7.75" Back Height: 1" More Than Front Height	Bottom Width & Front Height: 8", 10", 12", 14" Back Height: 1" More Than Front Height	Half Round: 5", 6", 7", 8", 9", 10" (Diameter) K-Style: 6", 7", 8" (Width)	Width: Min. 3" Max. 10" Depth: Min. 3" Max. 10"	Round: 3", 4", 5", 6", 8" (Diameter) Corrugated: 3" x 4" and 4" x 5"
MATERIALS	24 ga., 22 ga. .040", .050", .063"	22 ga. .050", .063"	24 ga., 22 ga. .032", .040", .050"	24 ga., 22 ga. .040", .050", .063"	24 ga., 22 ga. .032", .040", .050"
WARRANTY	30 Year, 160 MPH	30 Year, 160 MPH	10 Year, 90 MPH	5-Year Workmanship	5-Year Workmanship
ANSI/SPRI GT-1 TESTED	X	X		N/A	N/A
FM APPROVED	X	X		N/A	N/A
MIAMI-DADE APPROVED	X			N/A	N/A






OTHER WATER CONTROL PRODUCTS:


- Scuppers and Conductor Heads
- Flow-Thru Drain Bar
- Eco-Edge Drain Bar
- Eco-Edge Inspection Chamber

ACCESSORIES


High-Quality Products to Complete Your Roofing Projects

Designed to provide long-lasting performance, Hickman's accessories supply the flexibility to fit any project. Easy to install, our accessories are effective as a complement to our other product lines or as a stand-alone application. Each product comes with a 5-year workmanship warranty and offers the performance and consistency you and your customers rely on.

PRODUCT LINE	 PERMASPAN EXPANSION JOINTS	 REGLETS	 T-BAR
VERSIONS	• Roof to Wall • Roof to Roof • Roof to Wall (3-Axis) • Roof to Roof (3-Axis)	1 piece • In-Wall Surface Mount • Surface Mount 2 pieces • In-Wall Drive-Lock • Drive-Lock • Thru-Wall	• T-Bar Fascia • Extruded • Formed • Paver
PRODUCT LINE	 DRAIN BAR	 WATER DRAINAGE	 OTHER
VERSIONS	• Flow-Thru • Eco-Edge	• Thru-Wall Scupper • Conductor Heads • Thru-Wall Scuppers w/ Conductor Head • Eco-Edge Inspection Chamber	• Ledge Cap (shown) • Soffit Cleat • Lightning Rod Brackets • Extender • Extender with Offset

EXPRESS COLORS*

Bone White



Stone White



Almond



Sandstone



Sierra Tan



Medium Bronze



Dark Bronze



Clear Anodized



Cityscape



Slate Gray

STANDARD COLORS

Granite



Burnished Slate



Classic Bronze



Midnight Bronze



Mansard Brown



Musket Gray



Charcoal



Graphite



Black ▲



Iron Ore



Inkwell

Onyx
(Matte Black) ▲

Terra Cotta



Colonial Red



Cardinal Red



Pacific Blue



Interstate Blue



Hemlock Green




Forest Green



Patina Green ▲

PREMIUM COLORS

Award Blue




Anodic Clear



Silversmith



Silver



Champagne



Weathered Zinc



Copper Penny

* = Also in Mill Finish

▲ = Must Specify Supplier

Our colors are deep, rich and true. Made of Valspar's Fluorpon® High Performance Hylar 5000®/Kynar 500® finish, they offer the ultimate in resistance against fading and weathering. Custom colors also available.

THE INDUSTRY'S BEST WARRANTIES

Guaranteeing the Safety of Our Customers, Friends, & Family

Because every Hickman product is carefully designed, fabricated, and tested, we stand by our quality with industry leading wind and performance warranties. Hickman warranties are for replacement or repair of any portion of the system that has failed due to a defect in Hickman supplied materials. Covers the roof edge for the number of years listed on the roof on which it was originally installed.

PRODUCT LINE	LIFETIME, 215 MPH	30 YEAR, 160 MPH	20 YEAR, 120 MPH	10 YEAR, 90 MPH	KYNAR 500® PAINT	5 YEAR WORKMANSHIP
ACCESSORIES					X	X
CREATIVE DESIGN FASCIA AND COPING			X		X	X
DRIP EDGE FASCIA (Kynar or PVC/TPO Coated)				X	X	X
ECONOSNAP and ECONOCRIMP FASCIA			X		X	X
ELIMINAILER-T AND EDGEBOX RI	X					X
GRAVEL STOP FASCIA				X	X	X
HALF ROUND AND K-STYLE GUTTER				X	X	X
MBED-B FASCIA				X	X	X
PERMASNAP COPING (All Except PermaSnap Premier Plus)			X		X	X
PERMASNAP PREMIER PLUS COPING	X				X	X
PERMASPAN EXPANSION JOINTS			X		X	X
ROOFER'S EDGE COPING				X	X	X
SAFEGUARD NP FASCIA			X		X	X
TERMINEDGE EX, XT, HG (Fascia and Drip Edge)	X				X	X
TERMINEDGE AND TERMINEDGE ONE FASCIA			X		X	X
WIND RESISTANT & WIND RESISTANT XL GUTTER		X			X	X

*All products listed above include a Kynar® Paint Warranty. Custom post-coated Kynar 500® colors are available with an included 10 year Kynar 500® finish warranty or a 20 year Kynar 500® finish warranty is available upon request.

Cutting edge design made easy.



HICKMAN

EDGE SYSTEMS

Hickman Edge Systems
4 Commerce Way
Arden, NC 28704

www.hickmanedgesystems.com
info@hickmanedgesystems.com
826-676-1700

