



ROMA-X SPECIFICATIONS

HOSPITALITY DIVISION
eurotech
LUXURY SHOWER DOORS

FEATURES

- 304 stainless steel
- (4) 2-9/16" dual sided rollers
- Up to 3/8" out of plumb adjustability
- 4 configurations
- Dual water diverter sets (aluminum and polycarbonate)
- 12" ladder style back-to-back handle
- Door grippers incorporated into wall brackets
- EuroSafe Glass Film (safety film) included on both panels
- Standard clear tempered glass with optional ultra-clear (low iron) tempered glass or rain tempered glass
- 5/16 (8mm) or 3/8 (10mm) glass options
- Option for Enduroshield treatment to reduce cleaning time up to 90%



FINISHES



Polished Stainless



Matte Black




Brushed Stainless





Satin Brass


HANDLE & TOWEL BAR OPTIONS




24 inch Ladder Style Towel Bar




18 inch Flat Style Handle




18 inch Ladder Style Handle



8 inch Ladder Style Handle





24 inch Rounded Towel Bar





CONFIGURATIONS

exterior or interior door capability







**FOOTPRINT USING
 ALUMINUM WATER GUARD**



**FOOTPRINT USING
 POLYCARBONATE L-SEAL**



PARTS LIST

- 1) wall bracket
- 2) standoff
- 3) roller
- 4) track
- 5) door panel
- 6) F-seal
- 7) fixed panel
- 8) V-seal
- 9) handle
- 10) aluminum u-channel
- 11) 1/4" shims
- 12) bottom guide
- 13) safety bumper
- 14) aluminum water guard
- 15) L-seal

