



# Specification Guide

## Division 8



Visit our website





**Cavity  
Sliders™**

# About Us

Cavity Sliders USA Inc is the premier manufacturer of sliding door hardware. With strict attention to detail from design through to production, Cavity Sliders offers a product line that is high quality, reliable, and operates smoothly.

From humble beginnings in New Zealand as a family business, Cavity Sliders has grown to become a world leader in the supply of sliding door hardware. With distributors located throughout North America, Australia, and New Zealand, Cavity Sliders is committed to upholding the quality level of its existing product line. Emphasis is also placed on developing new products to meet the changing trends of the modern market.



Circa 1986



Circa 1992



Circa 1996



Circa 2005

# About our Products

## Product Range

---

**At CS Cavity Sliders, we're best known for our high-quality pocket door systems.** But we don't stop there — we're your go-to experts for all things interior and sliding, offering complete solutions to elevate your space.

Our product lineup includes precision-engineered pocket door systems, versatile track systems, innovative handles, and advanced automatic units — all crafted to meet the highest standards of quality and innovation.

## CaviSlider

---

The CS Cavity Slider® and CS Cavity Slider® Ultimate are kitset pocket frames suitable for residential and commercial projects. CS Cavity Sliders are constructed from aluminum extrusions, making them structurally robust. The kitset is quick and easy to assemble, and the extrusions can be cut down to suit your door size.

## CaviLock

---

The CaviLock range is a comprehensive selection of hardware tailored for pocket and sliding doors. Whether you need high-quality commercial ADA-compliant locks for restrooms or residential privacy locks, CaviLock has the perfect handle to meet your project's needs.

## CaviTrack

---

CS Track Systems feature durable aluminum extrusions engineered for smooth and reliable performance in a variety of interior sliding applications. Built to last, these track systems work seamlessly with our carriages and components, ensuring easy specification and optimal performance. Whether for barn sliding, multi-profile, bypass, or pocket doors, our CaviTrack range provides a dependable solution designed to meet diverse needs with precision and quality.

## AutoCav

---

The CS AutoCav is a fully automated pocket door system suitable for commercial and residential use. It is customized on a per job basis in line with the client's project requirements.



## ● CaviSlider

|                                         |    |
|-----------------------------------------|----|
| CS Cavity Slider® Pocket Frame          | 8  |
| CS Cavity Slider® Ultimate Pocket Frame | 8  |
| CS Jamb Kit™                            | 12 |

## ● CaviTrack

|                                         |    |
|-----------------------------------------|----|
| CaviTrack - Quick Reference             | 17 |
| CS TopMountTrack - Single               | 22 |
| CS TopMountTrack - Double/Triple        | 24 |
| CS FH-CeilingMountTrack - Single        | 26 |
| CS FH-CeilingMountTrack - Double/Triple | 28 |
| CS WallMountTrack                       | 30 |
| CS SideMountTrack                       | 32 |
| CS BarnDoorTrack                        | 34 |
| CS HeavyDutyTrack                       | 36 |
| CS Frameless Glass Clamp                | 38 |
| Door Collection System                  | 40 |
| Floor Channel & Bearing Guide System    | 41 |
| Carriage Packs                          | 42 |

## ● CaviLock

|                             |    |
|-----------------------------|----|
| Handle & Lock Product Range | 46 |
| CL400 Magnetic              | 48 |
| CS BarnDoorStrike           | 58 |
| CL200 Range                 | 60 |
| CL100 Lever                 | 62 |
| CL100 FlushTurn             | 64 |
| Halliday + Baillie Handles  | 66 |

## ● ADA Compliant Hardware

|                                 |    |
|---------------------------------|----|
| ADA Handle & Lock Product Range | 74 |
| Specifying ADA Handles          | 75 |
| CL400 ADA Magnetic              | 76 |
| CS BarnDoorStrike               | 78 |
| CL100 ADA LaviLock              | 80 |
| CL100 ADA Lever                 | 82 |
| CL100 ADA Indicator Lock        | 84 |

## ● AutoCav

|                                 |    |
|---------------------------------|----|
| CS AutoCav®                     | 88 |
| CS AutoCav® Pro                 | 90 |
| AutoCav® Access Control Options | 92 |

## ● Product Codes

|                                      |     |
|--------------------------------------|-----|
| CS Cavity Slider Pocket Frame        | 94  |
| CS Track Systems                     | 96  |
| CS Barn Track Systems                | 98  |
| Carriage Packs                       | 99  |
| Track Kits                           | 101 |
| Collection Packs                     | 103 |
| Floor Channel & Bearing Guide System | 103 |
| Components                           | 104 |
| CL400 Magnetic                       | 106 |
| CL400 ADA Magnetic                   | 109 |
| CS BarnDoorStrike                    | 110 |
| CL200 Range                          | 111 |
| CL100                                | 112 |
| Halliday + Baillie Handles           | 114 |


## ● Displays & Jigs

|                               |     |
|-------------------------------|-----|
| Cavity Sliders Sample Options | 116 |
| CL400 Magnetic Cutout Jigs    | 118 |
| Jig Router Bits               | 119 |
| Door Groove Cutter            | 119 |

|                            |     |
|----------------------------|-----|
| Frequently Asked Questions | 120 |
| Warranty Conditions        | 122 |
| Copyright Conditions       | 124 |
| Notes                      | 125 |

# CaviSlider

Pocket Frame Systems



# CS Cavity Slider® Pocket Door Frame

**The CS Cavity Slider® is a practical solution for those areas where there is not enough space for a swinging door.**


In addition to its space-saving attributes in restrooms, hallways, and laundries, it can be used with confidence for architectural feature openings around your project.

Compatible with SofStop® soft open / soft close.

## Features

---

- Structurally robust due to its construction from aluminum extrusions
- Easy to assemble and install
- Available for 2x4 and 2x6 framing
- Can be cut down to size on site
- Suitable for residential and commercial projects (meets Type 1 construction code without any combustible materials)



# CS Cavity Slider® Features with CS Jamb Kit™



**Smooth running carriages**  
with encased ball bearings.  
Up to 500 lb (240 kg) capacity

**SofStop Soft Close/Soft Open**  
also available



**Corner joining brackets** ensure precise right angled assembly



**T-joining brackets** for easy assembly of slats to split jambs & back stud

**Strong aluminum frame** complies with Type 1 Construction

**Head jambs designed for serviceability**

**Split Jambs and slats** use hollow core technology for superior rigidity


**Horizontal slats** for added strength

**3/4" jamb thickness**

**Bottom plate assembly**


Patent Pending

**Adjustable T-Guide**



**Pre-drilled closing jamb** for seamless attachment to track profile

**Can be easily cut down on site** for custom door sizes



**Pre-grooved for Trim Clips** for quick & easy installation

**Door Thickness**

1-3/8" to 1-3/4"  
2x4 Stud

1-3/8" to 2-1/4"  
2x6 Stud



**2x4**



**2x6**

**Extruded aluminum track** incorporated into head unit

Compatible with 4" and 6" stud sizes

**Stain-grade poplar** prepared and ready for paint



Cycle tested  
1 million openings



ADA Compliant



Available with  
SofStop®



Single or  
Bi-Parting units



Maximum door  
weight

Learn More




# CS Cavity Slider® Pocket Door Frame

## Features

- Accommodates 1-3/8" to 1-3/4" doors (35 to 44.5 mm)
- Up to 4'0" x 8'0" door size (1220 x 2438 mm) and can be cut down on site
- Designed for 2x4 Stud Size

## Product Specifications


### Elevation



# CS Cavity Slider® Ultimate Pocket Door Frame


- The gold standard of pocket frames. It is the largest and most robust manufactured pocket frame on the market
- Accommodates 1-3/8" to 2-1/4" doors (35 to 57 mm)
- Up to 5'0" x 10'0" door size (1524 x 3048 mm) and can be cut down on site
- Designed for 2x6 Stud Size

### Elevation



## Technical Specifications

### Plan




## Standard CS Track Features

- Heavy duty one-piece extruded aluminum track.
- Minimal clearance means the carriages/wheels cannot jump off the track or jam.
- Large diameter wheels with precision ground bearings make for smooth running.
- Radiused track reduces friction and allows dust to be pushed into the gutters so the door always slides smoothly.
- M8 body made from cast stainless steel for strength and reliability. 4-wheel carriages are standard on all doors over 200lb.
- CarriSnap™ quick release system allows the door to be removed easily from the track; no need to unscrew anything and lose door height adjustment.

## Rough Opening

DH - Door Height    DW - Door Width

| Dimension             | Inches        |
|-----------------------|---------------|
| RO Height             | DH + 4-1/4"   |
| RO Width   Single     | (DW x 2) + 2" |
| RO Width   Bi-Parting | (DW x 4) + 2" |



## How to Order

### 1. Choose Framing and Door Size

Frames can be cut down on site to maximize size for each model:

| Framing                   | CS SKU     | Max Door Size |                |
|---------------------------|------------|---------------|----------------|
|                           |            | Inches        | Millimeter     |
| 4" Framing<br>(2x4 Stud)* | CSS4K3068  | 3'0" x 6'8"   | 914 x 2032 mm  |
|                           | CSS4K3080  | 3'0" x 8'0"   | 914 x 2438 mm  |
|                           | CSS4K4080  | 4'0" x 8'0"   | 1219 x 2438 mm |
| 6" Framing<br>(2x6 Stud)  | CSU6K2680  | 2'6" x 8'0"   | 762 x 2438 mm  |
|                           | CSU6K3080  | 3'0" x 8'0"   | 914 x 2438 mm  |
|                           | CSU6K4080  | 4'0" x 8'0"   | 1219 x 2438 mm |
|                           | CSU6K3090  | 3'0" x 9'0"   | 914 x 2743 mm  |
|                           | CSU6K4090  | 4'0" x 9'0"   | 1219 x 2743 mm |
|                           | CSU6K30100 | 3'0" x 10'0"  | 914 x 3048 mm  |
|                           | CSU6K40100 | 4'0" x 10'0"  | 1219 x 3048 mm |
|                           | CSU6K50100 | 5'0" x 10'0"  | 1524 x 3048 mm |

\* More sizes available through distribution. Reach out for more information

### 2. Choose a Carriage Pack (one per door)

Includes: Carriages, mounting plates, T-Guide, fixing screws, and adjusting wrench

| Standard            | M6 (200 lb / 90 kg)  |              |
|---------------------|----------------------|--------------|
|                     | M8 (500 lb / 240 kg) |              |
|                     | Minimum Door Width   |              |
| CS SofStop          | No Stop              | 1 Stop       |
| 0 - 200 lb (90 kg)  | 23" (584 mm)         | 26" (660 mm) |
| CS SofStop HD       | No Stop              | 1 Stop       |
| 0 - 350 lb (160 kg) | 26" (660 mm)         | 29" (737 mm) |

### 3. For 2x4 and 2x6 Stud Frames up to 8', choose your CS Jamb Kit

Includes: Head jambs, split jambs, closing jamb, and fixing screws

| Framing                   | Door Size   | Jamb Size | Door Thickness | Product SKU        |
|---------------------------|-------------|-----------|----------------|--------------------|
| 4" Framing<br>(2x4 Stud)* | 3'0" x 8'0" | 4-9/16"   | 1-3/8"         | JK4SW3080-138-4916 |
|                           |             |           | 1-3/4"         | JK4SW3080-134-4916 |
|                           |             | 4-7/8"    | 1-3/8"         | JK4SW3080-138-478  |
|                           |             |           | 1-3/4"         | JK4SW3080-134-478  |
|                           | 4'0" x 8'0" | 4-9/16"   | 1-3/4"         | JK4SW4080-134-4916 |
|                           |             | 4-7/8"    | 1-3/4"         | JK4SW4080-134-478  |
| 6" Framing<br>(2x6 Stud)  | 3'0" x 8'0" | 6-9/16"   | 1-3/8"         | JK6UW3080-138-6916 |
|                           |             |           | 1-3/4"         | JK6UW3080-134-6916 |
|                           |             | 6-7/8"    | 1-3/8"         | JK6UW3080-138-678  |
|                           |             |           | 1-3/4"         | JK6UW3080-134-678  |
|                           | 4'0" x 8'0" | 6-9/16"   | 1-3/4"         | JK6UW4080-134-6916 |
|                           |             | 6-7/8"    | 1-3/4"         | JK6UW4080-134-678  |

# CS Jamb Kit™

CS Cavity Slider® Pocket Door Jamb Kit  
For 2x4 and 2x6 Framing

## Features

- Pre-drilled holes for easy installation
- Easy to cut to size
- Grooved for CS Trim Clips
- No prep work needed
- Stain-grade poplar construction – ready for paint
- 3/4" jamb thickness

## The CS Jamb Kit includes:

### Head Jambs x2


Includes two (2) head jambs pre-grooved to accept CS Cavity Sliders trim clips for accessibility to track.

### Split Jambs x2

Includes two (2) split jambs pre-grooved to accept CS Cavity Sliders trim clips to encase wall cavity.

### Closing Jamb

Includes one (1) closing jamb to complete the door frame with a secure and polished fit.



CS Jamb Kit™ packaging



CS Ultimate Jamb Kit™ packaging



**The CS Jamb Kit simplifies pocket door finishing with a ready-to-install solution.**


Made from stain-grade poplar, it features pre-drilled holes and a grooved design ready for CS Trim Clips. With no prep work required, the CS Jamb Kit streamlines installation, saving you valuable time.





# CaviTrack

Sliding Door Track Systems



# CaviTrack Features

## Our products come with a number of unique features:

- Heavy duty one-piece extruded aluminum track.
- Pre-machined mounting holes.
- Radiused track reduces friction and allows dust to be pushed into the gutters so the door always slides smoothly.
- M8 body made from cast stainless steel for strength and reliability. 4-wheel carriages are standard on all doors over 200 lb.
- Fascia is removable for future servicing requirements (Available for TopMountTrack, WallMountTrack, and SideMountTrack).

## SofStop® Features & Options


- Single or Twin action (soft open/soft close) options available.
- High quality soft close mechanism has been independently tested to 100,000 cycles.
- The soft close mechanism is hidden from sight, yet remains fully serviceable.

|                            |                           |               |                |
|----------------------------|---------------------------|---------------|----------------|
| <b>Standard</b>            | M6 (200 lb/90 kg)         |               |                |
|                            | M8 (500 lb/240 kg)        |               |                |
| <b>CS SofStop</b>          | <b>Minimum Door Width</b> |               |                |
|                            | <b>No Stop</b>            | <b>1 Stop</b> | <b>2 Stops</b> |
| <b>0 - 200 lb (90 kg)</b>  | 23" (584 mm)              | 26" (660 mm)  | 28" (711 mm)   |
| <b>CS SofStop HD</b>       | <b>No Stop</b>            | <b>1 Stop</b> | <b>2 Stops</b> |
| <b>0 - 350 lb (160 kg)</b> | 26" (660 mm)              | 29" (737 mm)  | 31" (787 mm)   |







## How to Order

### Refer to Carriage Packs page for more information







- 1. Choose track configuration (single, double, or triple)**
- 2. Specify track length**  
Available in 6', 8', 12', and 24' pre-cut lengths or can be cut down to specified length on request.
- 3. Specify door weight and width (see options)**
- 4. Choose a carriage pack (one per door)**
  - M6 (200 lb)
  - M8 (500 lb)
  - SofStop
  - CS Door Collection System (for telescoping doors)  
Includes M6 or M8 carriage pack plus door collection system for 2 door or 3 door setup
- 5. Fascia and End Caps (optional) - Specify finish**  
Available for TopMountTrack, WallMountTrack, and SideMountTrack







# Quick Reference





| Description                                                                                                           | Image                                                                                | Dimensions                                                                            |
|-----------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| CS TopMountTrack - Single<br>Clear or Black Anodized<br>(Available in custom lengths up to 24 ft)                     |    |    |
| Clip on fascia for CS TopMountTrack - Single<br>Clear or Bronze Anodized<br>(Available in custom lengths up to 24 ft) |     |    |
| CS TopMountTrack - Double - 1-3/8" door thickness<br>(Available in custom lengths up to 24 ft)                        |    |   |
| CS TopMountTrack - Double - 1-3/4" door thickness<br>(Available in custom lengths up to 24 ft)                        |  |  |
| CS TopMountTrack - Triple - 1-3/8" door thickness<br>(Available in custom lengths up to 24 ft)                        |  |  |
| CS TopMountTrack - Triple - 1-3/4" door thickness<br>(Available in custom lengths up to 24 ft)                        |  |  |

# Quick Reference

| Description                                                                                            | Image                                                                                | Dimensions                                                                            |
|--------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| CS FH-CeilingMountTrack - Single<br>(Available in custom lengths up to 24 ft)                          |    |    |
| CS FH-CeilingMountTrack - Double<br>1-3/8" door thickness<br>(Available in custom lengths up to 24 ft) |    |    |
| CS FH-CeilingMountTrack - Double<br>1-3/4" door thickness<br>(Available in custom lengths up to 24 ft) |  |   |
| CS FH-CeilingMountTrack - Triple<br>1-3/8" door thickness<br>(Available in custom lengths up to 24 ft) |  |  |
| CS FH-CeilingMountTrack - Triple<br>1-3/4" door thickness<br>(Available in custom lengths up to 24 ft) |  |  |

| Description                                                                                                                                                  | Image                                                                               | Dimensions                                                                            |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| <p>CS WallMountTrack</p> <p>1-3/8" &amp; 1-3/4" door thickness</p> <p>For thicker doors, please inquire</p> <p>(Available in custom lengths up to 24 ft)</p> |    |    |
| <p>Clip on fascia for CS WallMountTrack</p> <p>Clear or Bronze Anodized</p> <p>(Available in custom lengths up to 24 ft)</p>                                 |   |    |
| <p>CS SideMountTrack</p> <p>1-3/8" &amp; 1-3/4" door thickness</p> <p>For thicker doors, please inquire</p> <p>(Available in custom lengths up to 24 ft)</p> |   |   |
| <p>Clip on fascia for CS SideMountTrack</p> <p>Clear or Bronze Anodized</p> <p>(Available in custom lengths up to 24 ft)</p>                                 |  |  |

# Quick Reference


| Description                                                                                         | Image                                                                                | Dimensions                                                                            |
|-----------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| CS Barn Door Track<br>(Available in set lengths up to 19 ft)                                        |     |   |
| CS Barn Door Hangers & Stops Pack                                                                   |     |                                                                                       |
| SofStop 264 lb Single Pack for CS Barn Door Track<br>Two (2) required for soft open and soft close. |   |                                                                                       |
| CS HeavyDutyTrack<br>(Available in custom lengths up to 28 ft)                                      |  |  |
| CS Frameless Glass Clamp<br>3/8" glass thickness                                                    |   |  |
| CS Frameless Glass Clamp<br>1/2" glass thickness                                                    |                                                                                      |                                                                                       |

# Standard Components


## Carriages

- Large diameter wheels with precision ground bearings ensure smooth running and longevity.
- Self-centering hanger bolt ensures the door hangs plumb.
- High performance nylon tires.
- Both M6 and M8 carriages are made to fit any of our standard track profiles.
- Hanger bolts allow for 1/2" vertical height adjustment using the wrench provided.


**M6 Carriage**  
(up to 200 lb per pair)



**M8 Carriage**  
(up to 500 lb per pair)




**M10 Carriage**  
(up to 1100 lb per pair)




## Mounting Plates

- CarriSnap™ quick release system allows the door to be installed or removed easily from the carriage without altering door height adjustment.
- Plastic stop on the mounting plate hits on the track stop in the track (not the carriage body like other products on the market).


**M6/M8 Mounting Plate**




**M6/M8 Mounting Plate with Stop**




**Track Stop**



**Adjusting Wrench**




**Standard T-Guide**  
1" (25 mm)





## Carriage Adjustment

**Minimum Clearance**




**Maximum Clearance**



Use adjusting wrench supplied to adjust door clearance

# CS TopMountTrack - Single

## Technical Specifications




## Features

- Suitable for incorporating into pocket frame assemblies for a smooth running high end system.
- 304 stainless steel components available for corrosive environments.
- Track can be configured to suit bi-parting.
- Clip-on fascia available. Standard finishes: Clear or Bronze Anodized. Inquire about custom colors.

|                        |                                                                |
|------------------------|----------------------------------------------------------------|
| <b>Track Finish</b>    | Clear anodized, Black anodized                                 |
| <b>Fascia Finish</b>   | Clear or bronze anodized                                       |
| <b>Door Thickness</b>  | No fascia: No limit<br>With fascia: 1-3/8" - 1-3/4" (35-45 mm) |
| <b>Max Door Weight</b> | Standard: 500 lb (240 kg)<br>SofStop: 350 lb (160 kg)          |
| <b>Carriage Pack</b>   | M6/M8/SofStop                                                  |

## Suggested Assembly Detail



Available as a Track Kit.  
See page 101.



**CS TopMountTrack Systems** are a series of smooth-running, low-profile sliding door tracks designed for seamless integration into site-built pocket door frames, bypass wardrobes, telescoping room dividers, and more.


Compatible with SofStop® soft open / soft close.




# CS TopMountTrack - Double/Triple

## Technical Specifications


**Double Track - 1-3/8" doors**




**Triple Track - 1-3/8" doors**




All TopMountTracks are available with fascia



**Double Track - 1-3/4" doors**



**Triple Track - 1-3/4" doors**



## Features


- Suitable for incorporating into pocket frame assemblies for a smooth running high end system.
- 304 stainless steel components available for corrosive environments.
- Track can be configured to suit bi-parting set-up.

| Track                             | Double                         | Triple                         |
|-----------------------------------|--------------------------------|--------------------------------|
| <b>Track Finish</b>               | Mill-Finish                    | Mill-Finish                    |
| <b>Fascia Finish</b>              | Clear or Bronze Anodized       | Clear or Bronze Anodized       |
| <b>Recommended Door Thickness</b> | 1-3/8" or 1-3/4" (35 or 45 mm) | 1-3/8" or 1-3/4" (35 or 45 mm) |
| <b>Max Weight per Door</b>        | 500 lb (240 kg)                | 500 lb (240 kg)                |
| <b>Carriage Pack</b>              | M6 or M8                       | M6 or M8                       |

\*For thicker doors, please contact us for suitable options

## Suggested Assembly Detail

### CS Door Collection System



## Door Collection System

Where multiple doors are required to slide in conjunction with one another, the CS Door Collection System ensures a smooth running telescopic system. The doors are connected so that there is no need for floor tracks or guides through the opening.

Available as a Track Kit.  
See page 101.



**CS TopMountTrack Systems are a series of smooth-running, low-profile sliding door tracks designed for seamless integration into site-built pocket door frames, bypass wardrobes, telescoping room dividers, and more.**


For telescoping doors, this multiple-track system pairs with the CS Collection System for a seamless and elegant look.

Compatible with SofStop® soft open / soft close.



# CS FH-CeilingMountTrack - Single

## Technical Specifications




## Features

- Suitable for large room dividers or surface sliding applications.\*
- Track can be configured to suit bi-parting door set-up.
- 304 stainless steel components available for corrosive environments.
- Track may be painted on site to match ceiling color.

\*Not suitable for use in a pre-fabricated pocket frame. You will need to build a wall either side of the track when using in a pocket application.

|                        |                                                       |
|------------------------|-------------------------------------------------------|
| <b>Track Finish</b>    | Clear anodized                                        |
| <b>Door Thickness</b>  | No limit                                              |
| <b>Max Door Weight</b> | Standard: 500 lb (240 kg)<br>SofStop: 350 lb (160 kg) |
| <b>Carriage Pack</b>   | M6/M8/SofStop                                         |

## Suggested Assembly Detail




Available as a Track Kit.  
See page 102.



**The CS FH-CeilingMountTrack is supplied with full-length fins that enable the ceiling lining to be fixed flush with the underside of the track.**

This ensures the continuation of the ceiling-line through where the door slides. The track can also be painted on site to match the ceiling color.


Compatible with SofStop® soft open / soft close.




# CS FH-CeilingMountTrack - Double/Triple

## Technical Specifications


### Double Track - 1-3/8" doors




### Double Track - 1-3/4" doors



### Triple Track - 1-3/8" doors



### Triple Track - 1-3/4" doors



## Features

- Suitable for large room dividers or surface sliding applications.\*
- Track can be configured to suit bi-parting door set-up.
- 304 stainless steel components available for corrosive environments.
- Track may be painted on site to match ceiling color.


\*Not suitable for use in a pre-fabricated pocket frame. You will need to build a wall either side of the track when using in a pocket application.

| Track                      | Double                         | Triple                         |
|----------------------------|--------------------------------|--------------------------------|
| Finish                     | Mill-Finish                    | Mill-Finish                    |
| Recommended Door Thickness | 1-3/8" or 1-3/4" (35 or 45 mm) | 1-3/8" or 1-3/4" (35 or 45 mm) |
| Max Weight per Door        | 500 lb (240 kg)                | 500 lb (240 kg)                |
| Carriage Pack              | M6 or M8                       | M6 or M8                       |

\*For thicker doors, please contact us for suitable options

## Suggested Assembly Detail

### CS Door Collection System



## Door Collection System

Where multiple doors are required to slide in conjunction with one another, the CS Door Collection System ensures a smooth running telescopic system. The doors are connected so that there is no need for floor tracks or guides through the opening.

**The CS FH-CeilingMountTrack for multi-track systems features full-length fins, allowing ceiling linings to be installed seamlessly flush with the underside of the track.**

This ensures the continuation of the ceiling-line through where the door slides. The track can also be painted on site to match the ceiling color.


For telescoping doors, this multiple-track system pairs with the CS Collection System for a seamless and elegant look.

Compatible with SofStop® soft open / soft close.



# CS WallMountTrack

## Technical Specifications




## Features

- 304 stainless steel components available for corrosive environments.
- Track can be configured to suit bi-parting doors.

|                        |                                                       |
|------------------------|-------------------------------------------------------|
| <b>Fascia Finish</b>   | Clear or Bronze Anodized                              |
| <b>Door Thickness</b>  | 1-3/8" to 1-3/4" (35-45 mm)                           |
| <b>Max Door Weight</b> | Standard: 500 lb (240 kg)<br>SofStop: 350 lb (160 kg) |
| <b>Carriage Pack</b>   | M6/M8/SofStop                                         |

## Suggested Assembly Detail



\*For doors thicker than 1-3/4", please contact us for installation information

**The CS WallMountTrack is suitable for surface sliding applications where there is enough strength in the wall to side mount a track system above an opening.**

Installation is quick and easy as the track is supplied with pre-machined fixing slots.


Compatible with SofStop® soft open / soft close.



# CS SideMountTrack

## Contemporary Barn Door Track

### Technical Specifications




### Features

- Available only as a single-track setup; double or triple-track versions are not available.
- 304 stainless steel components available for corrosive environments.
- Track can be configured to suit bi-parting doors.

|                        |                                                       |
|------------------------|-------------------------------------------------------|
| <b>Fascia Finish</b>   | Clear or Bronze Anodized                              |
| <b>Door Thickness</b>  | 1-3/8" to 1-3/4" (35-45 mm)                           |
| <b>Max Door Weight</b> | Standard: 500 lb (240 kg)<br>SofStop: 350 lb (160 kg) |
| <b>Carriage Pack</b>   | M6/M8/SofStop                                         |

### Suggested Assembly Detail



\*For doors thicker than 1-3/4", please contact us for installation information

Available as a Track Kit.  
See page 102.



**The CS SideMountTrack is an ideal surface sliding solution where vertical fixing space is limited.**


This system is side fixed through the track profile. It is popular when the top of the door opening is close to the ceiling and there isn't structural support for fixture above the track.

Compatible with SofStop® soft open / soft close.



# CS BarnDoorTrack


## Technical Specifications



## Features

- Track is high-quality, heavy duty extruded aluminum.
- No exposed fasteners gives a clean look.
- Ultra smooth running acetal wheels.
- Track is adjustable off the wall for baseboards and casing clearance.

## Suggested Assembly Detail




|                                      |                  |
|--------------------------------------|------------------|
| <b>Track Finish</b>                  | Black anodized   |
| <b>Maximum Weight (per track)</b>    | 650 lb (300 kg)  |
| <b>Maximum Weight (per door)</b>     | 400 lb* (180 kg) |
| <b>Maximum Door Weight (SofStop)</b> | 264 lb (120 kg)  |
| <b>Minimum Door Thickness</b>        | 1-1/4" (32 mm)   |

\*Doors over 400 lb require extra hangers or a customized solution

## Width Options

Two width options are available with the CS BarnDoorTrack



## How to Specify

1. Determine Door Width
2. Specify track length  
Available in 6, 7, 8, 9, 10, 12, 13, 14, 15, 16, 17, 18 and 19 ft pre-cut lengths
3. Determine overall thickness (door + gap + moulding) and choose a bracket
  - a. Narrow option: 1-5/8" to 2-3/8" (40 - 61 mm)
  - b. Wide option: 2-3/8" to 3-1/8" (62 - 80 mm)
4. Select Hanger Pack (one pack per door)  
(Includes carriages, mounting plates, T-Guide, screws, and an adjusting wrench)
  - a. Standard operation  
Standard CS Barn Door Hangers & Stops Pack
  - b. SofStop  
Two SofStop Single Packs

**The CS BarnDoorTrack is suitable for surface sliding applications where there is enough strength in the wall to side mount a track above an opening.**


It is designed to offer adjustability of the door out from the wall. This allows for clearance with baseboards and casings without an unsightly head spacer.

Compatible with SofStop® soft open / soft close.



# CS HeavyDutyTrack

## Technical Specifications




## Features

- High-quality, ultra heavy-duty extruded aluminum track designed to take oversized or heavy doors up to 1100 lb.
- Pre-machined mounting holes.
- Includes our M10 Carriage Packs made from cast stainless steel and extra-large diameter nylon wheels with precision ground bearings for strength, reliability, and smoothness.

|                           |                  |
|---------------------------|------------------|
| <b>Track Finish</b>       | Clear anodized   |
| <b>Max Door Weight</b>    | 1100 lb (500 kg) |
| <b>Min Door Thickness</b> | 1-9/16" (40 mm)  |
| <b>Carriage Pack</b>      | M10 only         |

## Suggested Assembly Detail



## How to Order

1. Specify track length  
Available in lengths up to 28 ft
2. Choose an M10 carriage pack (one pack per door)  
Includes carriages, mounting plates, T-Guide, screws, and an adjusting wrench, installation instructions and stops if required

\*Not currently available with SofStop

**The CS HeavyDutyTrack is an ultra heavy duty extruded track system designed to accommodate oversized or heavy doors up to a maximum of 1100 lb (500 kg).**


This track is suitable for a wide range of commercial, industrial and residential applications such as large feature doors (as pictured) or large factory doors.

The track is supplied in a clear (natural) anodized finish making it suitable for interior or exterior use.



# CS Frameless Glass Clamp

## Technical Specifications



## Features

- Compatible with all of the standard CS tracks (ordered separately).
- Frameless glass clamp suitable for sliding glass doors up to 500lb.
- Removable end cap.

|                            |                              |
|----------------------------|------------------------------|
| <b>Clamp Finish</b>        | Clear anodized               |
| <b>Glass Thickness</b>     | 3/8" (10 mm) or 1/2" (12 mm) |
| <b>Maximum Door Weight</b> | 500 lb (240 kg)              |
| <b>Carriage Pack</b>       | M8 only                      |


## How to Order

The CS Frameless Glass clamp system is compatible with all of the standard CS tracks (ordered separately).

1. Specify clamp length  
Available in 2, 3, 4, 5 and 6 ft pre-cut lengths
2. Choose number of M8 (500 lb) carriage packs (one pack per door)  
Includes carriages, mounting plates, fixing screws, adjusting wrench and installation instructions
3. Specify Frameless Glass U-Guide  
One per door – suits 3/8" and 1/2" glass

## Suggested Assembly Detail

(CS TopMountTrack - Single shown)



\*Assuming 1/2" middle carriage height adjustment and 1/2" floor clearance

**The CS Frameless Glass clamp system is designed to take sliding glass doors of 3/8" or 1/2" thickness.**

The clamp is compatible with all of the standard CS track systems. Use this system for a distinctive, smooth running, reliable frameless sliding glass door system.




The doors are connected so that there is no need for floor tracks or guides through the opening.

## Features

- Pack includes: pick-up extrusion, guides and fixing screws to allow one door to pick up the next.
- Available for double or triple door set-ups - simply choose your number of doors and carriage type (M6 or M8).
- Pickup extrusion comes standard as 7' 6" length. Can be cut to required door height.
- You will also need to choose double or triple FH-CeilingMountTrack or CS TopMountTrack of the required length.
- Suitable for 1-3/8" to 1-3/4" thick doors. For thicker doors, please inquire about suitable options.


## Technical Specifications

## Plan - Pick Up Extrusions



## CS Door Collection System

Elevation



## How to Order

1. Choose number of doors (double door or triple door kit)
2. Choose a collection pack  
Includes carriages, mounting plates, adjusting wrench, extrusions, guides and fixing screws to allow one door to pick up the next

### Pickup Pack



## Pickup Pack



## Pickup Pack




## Pickup Pack




You will also require CS FH-CeilingMountTrack (double or triple) or CS TopMountTrack (double or triple)

# Floor Channel & Bearing Guide System


**Floor channel, aluminum bronze anodized with PVC insert**




**Bottom guide, ball bearing roller (stainless steel) for surface mount floor channel**




**Bottom guide, ball bearing roller (stainless steel) for door bottom channel**




**Bottom guide, ball bearing roller (stainless steel) for recessed floor channel**



**Ball bearing single roller, stainless steel**




**Ball bearing double roller, stainless steel**




# Carriage Packs

## M6 (200 lb)


DKM0601 - M6 Single Door with no stop



DKM0611 - M6 Single Door with 1 stop




DKM0621 - M6 Single Door with 2 stops




## M8 (500 lb)


DKM0801 - M8 Single Door with no stop



DKM0811 - M8 Single Door with 1 stop




DKM0821 - M8 Single Door with 2 stops



## M10 (1100 lb)


DKM1000 - M10 Single Door with no stop



DKM1010 - M10 Single Door with 1 stop



DKM1020 - M10 Single Door with 2 stops




## CS SofStop Single Action


DKS0501 - (0 - 200 lb) no stops



DKS0511 - (0 - 200 lb) 1 stop




DKS0521 - (0 - 200 lb) 2 stops




## CS SofStop Double Action


DKS0701 - (0 - 200 lb) no stops



DKS0711 - (0 - 200 lb) 1 stop




DKS0721 - (0 - 200 lb) 2 stops




## CS SofStop HD Double Action


DKS0801 - (200-350 lb) no stops



DKS0811 - (200-350 lb) 1 stop




DKS0821 - (200-350 lb) 2 stops



## CS Barn Door Hanger Pack

TSBS001 - CS Barn Door Hangers & Stops Pack



TSBS100 - SofStop (264 lb) Single Pack for Barn Door Track



# Door Collection Systems

## M6 (200 lb)

DKO6201 - 2 Door M6 (200 lb) 1-3/8" Collection Pack  
DKO6221 - 2 Door M6 (200 lb) 1-3/4" Collection Pack



## M8 (500 lb)


DKO8201 - 2 Door M8 (500 lb) 1-3/8" Collection Pack  
DKO8221 - 2 Door M8 (500 lb) 1-3/4" Collection Pack



DKO6301 - 3 Door M6 (200 lb) 1-3/8" Collection Pack  
DKO6321 - 3 Door M6 (200 lb) 1-3/4" Collection Pack



DKO8301 - 3 Door M8 (500 lb) 1-3/8" Collection Pack  
DKO8321 - 3 Door M8 (500 lb) 1-3/4" Collection Pack






# Handle & Lock Product Range



## CL400® Magnetic

A range of high quality passage, privacy and locking handles suitable for single or double pocket doors. Page 50.



## CS BarnDoorStrike

Enables the CL400 Magnetic range of sliding door hardware to be compatible for barn door applications. Page 58.



## CL200 Range

A range of high quality passage and privacy handles suitable for pocket doors. Page 60.



## CL100 Lever

Commercial grade lever handle. Page 62.



## CL100 FlushTurn

A circular flush turn specifically designed for sliding doors. Page 64.



## Halliday + Baillie Handles


Flush handles and stylish edge pulls to suit wood or aluminum doors. Page 66.

For ADA compliant handles, see page 72.

# CL400<sup>®</sup> Magnetic Technical Detail


## Door Cutout

The CL400<sup>®</sup> requires a simple door cutout. Complete instructions and templates are supplied with every handle.



## Face Plate

Two different face plate widths are available, to suit doors 1-3/8" and 1-3/4" thick.



## Features

- Architectural styling with a wide range of configurations and finish options available
- No on site alteration of handle is required
- Reliable, high quality components
- Suitable for pocket or barn slider style doors\*
- Step by step installation instructions with detailed diagrams and templates are included
- Can be used to upgrade existing hardware by retrofitting over smaller box cutout
- Positive grip for heavy doors
- Simple cutout ensures quick fitting
- Front edge incorporates a finger hole to retrieve door from the pocket
- Moving parts sit flush until the door closes to minimize wear
- Patented magnetic catch and plunger action<sup>†</sup> produces a positive hold close without the need to activate the snib
- Hidden fixing screws - only three small screws showing on the face plate
- Available with a choice of face plate widths to suit doors 1-3/8" and 1-3/4" thick

\* Not suitable where high security is a requirement


<sup>†</sup> US Patent No. 10036185

# CL400<sup>®</sup> Magnetic Technical Detail


## Striker

Depending on the configuration of the handle, the striker supplied is designed to either sit flush with the face of the closing jamb or recessed into the closing jamb. Striker cutout template and instructions are supplied with your handle and cover installation into a flush or recessed closing jamb.

### Flush Striker - Passage and Privacy Handles



### Recessed Striker - Key Locking Handles



# CL100 Technical Detail


## CL100 Mortise Lock Features

The CL100 Mortise Lock is a versatile mortise that has many different internal and external hardware options.

- Suitable for pocket doors and surface sliding doors
- Easy to operate
- Corrosion-resistant
- For use with wood or aluminum doors

## Key Locking

CL100 Mortise Locks with key locking function are supplied with a Euro Profile cylinder housing a Schlage C Keyway.




# CL200 Range

## Technical Detail


### Specifications

Two face plate widths are available. Handles can be adjusted to suit doors from 1-3/8" to 1-1/2" or 1-5/8" to 1-3/4" thick.


**Front Plate**



**Side Handle**




**Striker**




# CL400<sup>®</sup> Magnetic Passage

## Technical Specifications


### Front Plate



### Side Handle



### Flush Striker



## Features

- Door slides flush back into the pocket
- Patented Magnetic Technology
- Positive Grip For Heavy Doors
- Suitable for pocket or barn door style sliding doors

|                       |                             |
|-----------------------|-----------------------------|
| <b>Door Thickness</b> | 1-3/8" to 1-3/4" (34-46 mm) |
|-----------------------|-----------------------------|

|                            |                       |
|----------------------------|-----------------------|
| <b>Suitable Door Types</b> | Wood, Aluminum, Steel |
|----------------------------|-----------------------|

|                |                                 |
|----------------|---------------------------------|
| <b>Options</b> | Magnetic Latching, Non-Latching |
|----------------|---------------------------------|

## Finish Options



Bright Chrome



Satin Chrome



Oil Rubbed Bronze



Satin Nickel



Matte Black

**The CL400® is a stylish architectural option for passage handles.**

Designed to complement the privacy and locking range, this handle features a positive hold close action to ensure the door doesn't bounce off the closing jamb.


\* Not suitable where high security is a requirement




# CL400<sup>®</sup> Magnetic Privacy

## Technical Specifications


### Front Plate



### Side Handle



### Flush Striker



## Features

- Door slides flush back into the pocket
- Patented Magnetic Technology
- Positive Grip For Heavy Doors
- Suitable for pocket or barn door style sliding doors

**Door Thickness** 1-3/8" to 1-3/4" (34-46 mm)

**Suitable Door Types** Wood, Aluminum, Steel

**Options** Snib/Emergency

## Finish Options



Bright Chrome



Satin Chrome



Oil Rubbed Bronze



Satin Nickel



Matte Black

**The CL400® Privacy option matches the other configurations in the range.**


The magnetic latching feature ensures the door doesn't roll open - even if the snib is not engaged.




# CL400<sup>®</sup> Magnetic Key Locking

## Technical Specifications


**Front Plate**



**Side Handle**



**Recessed Striker**



## Features

- Security
- Door slides flush back into the pocket
- Patented Magnetic Technology
- Positive Grip For Heavy Doors
- Suitable for pocket or barn door style sliding doors

**Door Thickness** 1-3/8" to 1-3/4" (34-46 mm)

**Suitable Door Types** Wood, Aluminum, Steel

**Options** Key/Snib, Key/Key

## Finish Options



Bright Chrome



Satin Chrome



Oil Rubbed Bronze



Satin Nickel



Matte Black

**The CL400® Key Locking option is suitable for residential or light commercial use in internal situations where medium security is required.**

It incorporates a single or double Euro Profile cylinder with Schlage C Keyway. All Key Locking handles come with a raised shroud as standard for increased security.\*


\* Not suitable where high security is a requirement




# CL400<sup>®</sup> Magnetic Bi-Parting

## Technical Specifications


Passage - Non-Latching




Passage - Latching



Privacy




Key Locking






Matching Handle Set

Passage / Privacy



Key Locking



## Features

- Patented Magnetic Technology
- Positive Grip For Heavy Doors
- Suitable for pocket or barn door style sliding doors
- Durability and Reliability

|                            |                                   |
|----------------------------|-----------------------------------|
| <b>Door Thickness</b>      | 1-3/8" to 1-3/4" (34-46 mm)       |
| <b>Suitable Door Types</b> | Wood, Aluminum, Steel             |
| <b>Options</b>             | Passage, Privacy, and Key Locking |

## Finish Options



Bright Chrome



Satin Chrome



Oil Rubbed Bronze



Satin Nickel



Matte Black

**The CL400® Bi-Parting set is suitable for use where two doors meet in the middle. Passage, Privacy, and Key Locking configurations are available.**

The positive hold close action brings the doors together smoothly and holds them together until ready to open.

Note: Privacy and Key Locking configurations are not suitable as a high security option when used in a Bi-Parting door setup.





# CS BarnDoorStrike

## Technical Specifications

A hidden bracket is supplied as standard.

A right angle bracket can be ordered where additional fixing strength is required, e.g heavy commercial use.



## Features

- Suitable for doors  $1\frac{3}{8}$ " or  $1\frac{3}{4}$ " thick
- ADA compliant with the use of the CL400 ADA handle
- Easy to install
- Available in a range of finishes
- Suitable for use with CL400 Passage, Privacy, and Key Locking handles

## Finish Options



Bright Chrome



Satin Chrome




Oil Rubbed Bronze



Satin Nickel



Matte Black



Paint Primed White

**The CS BarnDoorStrike pairs with the CL400® Magnetic and CL400® ADA Magnetic sliding door hardware, making them compatible with barn door applications.**


This barn door strike is available for use with CL400® Magnetic Passage, Privacy, and Key Locking configurations and CL400® ADA Passage and Privacy handles.




# CL200 Range

## Technical Specifications


### Front Plate



### Side Handle



### Striker



## Features

- Passage, Privacy, and Bi-Parting options are available in a range of finishes
- Suitable for use on wood or aluminum doors
- Integrated snib button allows more space in the side pull
- Handles are not handed
- Large finger pull has more depth for greater purchase
- Simple installation with easy to follow instructions


## Configurations

### Passage

(Non-latching)

Passage handles are suitable for situations where locking or latching is not required.


These handles do not have a striker or magnet.



### Privacy

Snib/Emergency

Privacy handles have a discreet triangular shaped snib button on one side and Emergency Release on the other side. They are suitable for sliding doors where latching is required.




### Bi-Parting Mate

(To latch with Privacy)

The Bi-Parting mate includes a striker on the face plate to enable it to latch with a privacy handle.

For Bi-Parting passage doors, order two single passage handles.



## Finish Options



Bright Chrome



Satin Chrome



Oil Rubbed Bronze



Satin Nickel



Matte Black

**The CaviLock® CL200 is a durable range of sliding door hardware suitable for residential, commercial, and hospitality applications.**

Privacy handles incorporate a patented latching system\*, ensuring a smooth locking action. This handle is not handed.


Two face plate widths are available. Handles can be adjusted to suit doors from 1-3/8" to 1-1/2" or 1-5/8" to 1-3/4" thick.

\*Patent pending



# CL100 Lever

## Technical Specifications



## Features

- Ultra-durable and corrosion-resistant construction
- Key locking may be added to any CL100 Range Handle with the addition of a Euro Profile cylinder with American Schlage C Keyway
- Suitable for pocket or surface sliding doors

## Configurations

Cylinders are not handed

|                   |                      |  |
|-------------------|----------------------|--|
| <b>CL100A7002</b> | Lever - Key/Key      |  |
| <b>CL100A7010</b> | Lever - Key/Turn     |  |
| <b>CL100A7004</b> | Lever - Key One Side |  |
| <b>CL100A7014</b> | Lever - Turn/Emerg   |  |
| <b>CL100B5002</b> | Lever Only           |  |

## Construction

|                                |                         |
|--------------------------------|-------------------------|
| <b>Case</b>                    | Die cast Zinc           |
| <b>Internal Parts</b>          | Bronze/Brass            |
| <b>Screws, springs etc</b>     | Stainless Steel         |
| <b>Faceplate &amp; striker</b> | Brushed Stainless Steel |

## Finish Options




Stainless Steel

Looking for the ADA compliant version of this handle? See page 82.

**The CaviLock® CL100 Lever is the most common commercial side handle fitted to the CL100 Mortise Lock.**


It is robust and strong and has a commercial look that matches other commercial handles and locks in most applications.

The vertical lever grip enables a positive pull action on even the heaviest doors.




# CL100 FlushTurn


## Technical Specifications




**Top View**



**Striker**



**Escutcheon**



## Features

- Ultra-durable and corrosion-resistant construction
- Key locking may be added to any CL100 Range Handle with the addition of a Euro Profile cylinder with American Schlage C Keyway
- Suitable for pocket or surface sliding doors

## Configurations

Cylinders are not handed

|                   |                          |                                                                                                                                                                         |
|-------------------|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>CL100A1004</b> | FlushTurn - Key/Key      |   |
| <b>CL100A1006</b> | FlushTurn - Key One Side |                                                                                     |
| <b>CL100A9004</b> | FlushTurn Only           |                                                                                                                                                                         |

## Construction

|                                |                         |
|--------------------------------|-------------------------|
| <b>Case</b>                    | Die cast Zinc           |
| <b>Internal Parts</b>          | Bronze/Brass            |
| <b>Screws, springs etc</b>     | Stainless Steel         |
| <b>Faceplate &amp; striker</b> | Brushed Stainless Steel |

## Finish Options



Stainless Steel

**The CL100 FlushTurn, crafted from high-quality brass, perfectly complements other circular hardware for hinged doors and is specifically designed for pocket doors.**

Its shallow fitting depth and positive turn action make it a popular choice for both latching and non-latching applications. Paired with the CL100 Mortise Lock and Euro Profile Cylinder, it offers an attractive and secure medium security option.








# Halliday + Baillie

## HB660 7" Flush Pull

### Technical Specifications



### Features

- Minimalistic and sleek design provides a contemporary look
- Ample depth for effective grip
- Suitable for a wide range of sliding and pocket applications
- Suited for door thickness  $1\frac{3}{8}"$  and greater
- Can be installed in combination with HB680 Pocket Door Edge Pull as Halliday + Baillie 620 Flush Pull Passage Set

### Finish Options



Bright Chrome



Satin Chrome

Oil Rubbed  
Bronze

Satin Nickel



Matte Black



Satin Brass

Also available as a set with HB680 Pocket Door Edge Pull.  
See page 114 for details.

**Halliday + Baillie Flush Pulls are suitable for both residential and commercial applications.**


Compatible with wooden and aluminum doors.



# Halliday + Baillie

## HB680 Pocket Door Edge Pull

### Technical Specifications



### Features

- Edge pull is easy to grasp with one or two fingers
- Slim-line mortise blends well with minimalistic overall look
- Can be installed in combination with HB660 7" Flush Pull as Halliday + Baillie 620 Flush Pull Passage Set

### Finish Options



Bright Chrome



Satin Chrome

Oil Rubbed  
Bronze

Satin Nickel



Matte Black




Satin Brass

Also available as a set with HB660 7" Flush Pull.  
See page 114 for details.


**The Halliday + Baillie Edge Pull allows for easy operation of sliding doors.**

Designed for passage functions, the spring-loaded edge pull sits flush inside the mortise and allows extraction with the push of a button.





# ADA Compliant Hardware



# ADA Handle & Lock Product Range



### CL400® ADA Magnetic

A range of high quality passage and privacy hardware with offset pull handle. Suitable for single or double pocket doors. Page 76.



### CS BarnDoorStrike

Enables the CL400 Magnetic range of sliding door hardware to be compatible for barn door applications. Page 78.



### CL100 ADA LaviLock

Commercial grade disabled rest room access lock with privacy indication. Page 80.



### CL100 ADA Lever

Commercial grade privacy or key lock with lever handle. Page 82.



### CL100 ADA Indicator Lock


Commercial grade disabled access lock with privacy indication. Page 84.

# Specifying ADA Handles

Whether you are specifying, supplying, or installing openings for public or commercial use it is important to be aware of the requirements of these openings, to ensure they comply with the Americans with Disabilities Act.

## What are the primary requirements for an ADA Opening?

- Clear Walkthrough Width**  
 ADA openings must provide a minimum 32-inch clear walkthrough to ensure wheelchair accessibility.
- Sliding Door Protrusion**  
 For sliding doors, ensure a minimum 4-inch protrusion into the doorway to allow full accessibility of all hardware.
- Door Handle Height**  
 Door handle operable parts must be positioned 34-inches minimum and 48-inches maximum above the finish floor or ground, per ADA Standards for Accessible Design.
- Hardware Requirements**  
 ADA-compliant hardware, such as pulls or levers, must protrude from the door and be operable without requiring tight pinching, grasping, or twisting of the wrist.
- Operating Force**  
 The operating force needed to open or close a door (including unlatching) must not exceed 5 pounds of force (lbf).




## CaviLock ADA Compliant Hardware

**CaviLock offers innovative sliding door hardware designed to meet ADA (Americans with Disabilities Act) compliance standards.** Combining functionality, durability, and style, these solutions provide effortless access for individuals with varying levels of mobility.


### CL400 ADA Magnetic Handle

- Features the patented magnetic mechanism of the award-winning CL400 Magnetic Handle
- Seamlessly complements the CL400 Magnetic range
- Engineered for effortless operation with a closed fist or flat palm, ensuring full accessibility



### CL100 ADA Handle


- Configurable with a large LaviLock faceplate for full ADA compliance
- Features clear visual cues and a large, easy-to-grasp lever handle
- Specifically engineered for commercial restroom applications



# CL400<sup>®</sup> ADA Magnetic




## Technical Specifications



## Features

- Compliant with ADA Standards for Accessible Design
- Easy to use - no tight pinching or twisting of the wrist
- Striker sits flush with closing jamb
- Matches other hardware in the CL400 range

## Configurations



## Finish Options



Bright Chrome



Satin Chrome



Oil Rubbed Bronze



Satin Nickel

**Door Thickness** 1-3/8" to 1-3/4" (34-46 mm)

**Suitable Door Types** Wood, Aluminum, Steel

**Options** Snib One Side, Snib/Emergency

**The CL400® ADA Magnetic Handle matches the look and functionality of the existing CL400® Magnetic range of pocket door hardware, with added ADA functionality.**

Utilizing the patented magnetic mechanism of the CL400 Magnetic, this addition to the range provides flexibility for building owners. The CL400 ADA uses the same door cutout and striker and is able to be retrofitted over existing CL400 flush handles for the requirements of ADA tenants.

The CL400 ADA is compatible with egress applications.





# CS BarnDoorStrike



## Technical Specifications

A hidden bracket is supplied as standard.

A right angle bracket can be ordered where additional fixing strength is required, e.g heavy commercial use.



## Features

- Suitable for doors  $1\frac{3}{8}"$  or  $1\frac{3}{4}"$  thick
- ADA compliant with the use of the CL400 ADA handle
- Easy to install
- Available in a range of finishes
- Suitable for use with CL400 Passage, Privacy, and Key Locking handles

## Finish Options



Bright Chrome



Satin Chrome




Oil Rubbed Bronze



Satin Nickel



Matte Black



Paint Primed White

**The CS BarnDoorStrike pairs with the CL400® Magnetic and CL400® ADA Magnetic sliding door hardware, making them compatible with barn door applications.**


This barn door strike is available for use with CL400® Magnetic Passage, Privacy, and Key Locking configurations and CL400® ADA Passage and Privacy handles.



# CL100 ADA LaviLock



## Technical Specifications



## Features

- Compliant with ADA Standards for Accessible Design
- Easy to use - no tight pinching or twisting of the wrist
- Matches other hardware in the CL100 range
- Egress Free - Even when in locked position the handle on the inside remains unlocked

## Technical Information

|                            |                                                       |
|----------------------------|-------------------------------------------------------|
| <b>Min. Door Thickness</b> | 1-3/8" (34 mm)                                        |
| <b>Suitable Door Types</b> | Wood, Aluminum, Steel                                 |
| <b>Options</b>             | ADA LaviLock - Left Hand<br>ADA LaviLock - Right Hand |

## Finish Options



Stainless Steel

**The CL100 ADA LaviLock is a sliding door lockset meticulously crafted to prioritize accessibility, ease of operation, and lasting performance.**

Specifically engineered for commercial restrooms, this innovative lockset redefines convenience for users with disabilities. With its sleek design and robust construction, the CL100 ADA LaviLock ensures effortless access and unmatched durability, meeting the demands of high-traffic environments.




# CL100 ADA Lever




## Technical Specifications


Front



Side



Striker



## Features

- Compliant with ADA Standards for Accessible Design
- Easy to use - no tight pinching or twisting of the wrist
- Matches other hardware in the CL100 range
- The CL100 ADA Lever includes a Euro Profile cylinder with American Schlage C Keyway, specified as either KA (Keyed Alike) or KD (Keyed to Differ). It is most suitable for 1-3/4" thick doors

## Technical Information

|                            |                                                    |
|----------------------------|----------------------------------------------------|
| <b>Min. Door Thickness</b> | 1-3/8" (34 mm)<br>Back Set: 2-3/64" (56 mm)        |
| <b>Suitable Door Types</b> | Wood, Aluminum, Steel                              |
| <b>Options</b>             | ADA Lever - Turn/Key<br>ADA Lever - Turn/Emergency |

## Finish Options



Stainless Steel

**The CL100 ADA Lever is a disabled access lever handle designed with ease of use and longevity of service in mind. Brass and stainless steel working components ensure reliability.**

The privacy turn has been designed in accordance with ADA Accessibility Guidelines for Buildings and Facilities and is easily operable without pinching, grasping or twisting of the wrist. The vertical lever grip enables a positive pull action on even the heaviest doors.




# CL100 ADA Indicator Lock




## Technical Specifications


Front



Side



Striker



## Features

- Compliant with ADA Standards for Accessible Design
- Easy to use - no tight pinching or twisting of the wrist
- Matches other hardware in the CL100 range
- Egress Free - Even when in locked position the handle on the inside remains unlocked

## Technical Information

**Min. Door Thickness** 1-3/8" (34 mm)

**Door Protrusion** 4" (100 mm)

**Backset** 2-3/16" (56 mm)

**Options** ADA Indicator Lock - Left Hand  
ADA Indicator Lock - Right Hand

## Finish Options



Stainless Steel

**The CL100 ADA Indicator Lock is a disabled access lockset designed with ease of use and longevity of service in mind.**


Brass and stainless steel working components ensure reliability. The Indicator Lock is self-latching and utilizes 'fail safe' single action egress functionality and is supplied as a complete set including CL100 Mortise Lock Case, Lever Handles, Stainless Steel Indication Plates and Slide Locking Buttons including Emergency Release.






# AutoCav

Automatic Units





## Features

### Smooth, controlled operation

- Precision automation with adjustable speeds for a consistent, quiet experience.

### Built-in safety

- Safety beams and continuous force feedback protect users during operation.

### Operates during power outages

- Integrated battery backup allows continued operation when power is lost.

### Factory tested

- Pre-wired and tested in the factory before delivery for faster, simpler installation.


### Flexible control options

- Compatible with a wide range of sensors and switches.

- Single doors up to 264 lb (120 kg).
- Bi-Parting doors up to 132 lb (60 kg) per door.
- Choose how you want the door to open and close and which switches, sensors and buttons you require.
- WC options available.
- Tested to 1 million cycles – suitable for low, medium and high traffic environments.

## Rough Opening

| Dimension             | Inches                           |
|-----------------------|----------------------------------|
| RO Height             | Door height + 9-7/8" (251mm)     |
| RO Width - Single     | (Door width x2) + 1-3/16" (30mm) |
| RO Width - Bi-Parting | (Door width x4) + 7/16" (10mm)   |



## Options

Incorporate any of the architectural detail options below with the AutoCav<sup>®</sup> cavity slider to create a specific look or to provide a unique solution to your design requirements.

## Configurations



Single




Bi-Parting


**High-performance automated cavity sliding door systems for residential and commercial projects.**

The CS AutoCav® range brings smooth, automated operation to cavity sliding doors, designed to meet your project's automation requirements. The CS AutoCav is for both residential and commercial applications, and delivers reliable, hands-free access where it matters most.

From ensembles and wardrobes to accessible bathrooms and commercial environments, AutoCav can be specified to meet your exact sliding door needs.



# AutoCav<sup>®</sup> Pro



## Features

### Smooth, controlled operation

- Precision automation with adjustable speeds for a consistent, quiet experience.

### Built-in safety

- Safety beams and continuous force feedback protect users during operation.

### Operates during power outages

- Integrated battery backup allows continued operation when power is lost.

### Factory tested

- Pre-wired and tested in the factory before delivery for faster, simpler installation.


### Flexible control options

- Compatible with a wide range of sensors and switches.

- Single doors up to 264 lb (120 kg).
- Bi-Parting doors up to 132 lb (60 kg) per door.
- Choose how you want the door to open and close and which switches, sensors and buttons you require.
- WC options available.
- Tested to 1 million cycles – suitable for low, medium and high traffic environments.

## Rough Opening

| Dimension             | Inches                           |
|-----------------------|----------------------------------|
| RO Height             | Door height + 10-1/4" (260mm)    |
| RO Width - Single     | (Door width x2) + 1-3/16" (30mm) |
| RO Width - Bi-Parting | (Door width x4) + 7/16" (10mm)   |



## Options

Incorporate any of the architectural detail options below with the AutoCav<sup>®</sup> cavity slider to create a specific look or to provide a unique solution to your design requirements.

## Configurations



Single



Bi-Parting

**Our CS AutoCav® Pro is our most advanced fully automated cavity slider system - designed for a range of applications, from commercial and architectural environments to healthcare facilities.**

Built with high-quality components, CS AutoCav Pro guarantees reliability and durability. Easy access to the track via access points in the head unit simplify servicing, ensuring a dependable, long-lasting system.



## AutoCav® Access Control Options

AutoCav can be configured to suit how the space is used. Doors can be set to open, close, hold open, or operate while locked — depending on the selected configuration.

### Wall-Mounted Controls


- Push Buttons
- PDL Switches



### Hands-Free Access

- Handwave sensors
- Overhead motion sensors



| Standard Configurations                                                            | Includes                                      |                                                 |
|------------------------------------------------------------------------------------|-----------------------------------------------|-------------------------------------------------|
|    | Handwave Sensor Pack (Stainless Steel Finish) | Handwave (Open cycle)                           |
|                                                                                    |                                               | Handwave (Open cycle while locked)              |
|                                                                                    | Optional extras                               | Key switch (Lock and hold open)                 |
|                                                                                    |                                               | Handwave (Hold Open/ Hold Close)                |
|   | Handwave Sensor Pack (White Finish)           | Handwave (Open cycle)                           |
|                                                                                    |                                               | Handwave (Open cycle while locked)              |
|                                                                                    | Optional extras                               | Key switch (Lock and hold open). S/Steel Finish |
|                                                                                    |                                               | Handwave (Hold Open/ Hold Close)                |
|  | PDL Switch Pack                               | Spring return PDL (Open cycle)                  |
|                                                                                    |                                               | Double PDL switch (Open cycle and hold open)    |
|                                                                                    | Optional extras                               | Key switch (Lock and hold open)                 |
|                                                                                    |                                               | Drywire (for external access control)           |
|  | Push Button Pack                              | Push button (Open cycle)                        |
|                                                                                    |                                               | Push button (Open while locked)                 |
|                                                                                    | Optional extras                               | Key switch (Lock and hold open)                 |
|                                                                                    |                                               | Push button (Hold Open/ Hold Close)             |
|  | Overhead Sensor Pack                          | Overhead Sensor (Open cycle)                    |
|                                                                                    |                                               | Overhead Sensor (Open while locked)             |
|                                                                                    | Optional extras                               | Key switch (Lock and hold open)                 |
|                                                                                    |                                               | Drywire (for external access control)           |

## Upgrade to AutoCav Pro

If you require any of the following please get in touch as you will need a CS AutoCav Pro:


- Piezo Button (LED Indicator)
- Partial Door Open Mode
- Custom Speed
- Side Mount configuration
- Open cycle time longer than 10 seconds
- Door weight over 264 lb (120 kg)

## Service & Support

All AutoCav systems are designed for long-term reliability.

- Recommended servicing every ~5000 uses
- Suitable for low, moderate, and high-use environments
- Backed by CS support and expertise
- 5-year warranty (12 months on electrical components).

# Product Codes



## CS Cavity Slider Pocket Frame






Select Frame, Carriage Pack, and Jamb Kit

| Item                                                                             | Description                                          | Model                | Code       | Price (\$) |
|----------------------------------------------------------------------------------|------------------------------------------------------|----------------------|------------|------------|
|  | CS Cavity Slider®<br>Pocket Door Frame only          | 3068 (3'0" x 6'8")   | CSS4K3068  | 875        |
|                                                                                  |                                                      | 3080 (3'0" x 8'0")   | CSS4K3080  | 955        |
|                                                                                  |                                                      | 4080 (4'0" x 8'0")   | CSS4K4080  | 1070       |
|  | CS Cavity Slider® Ultimate<br>Pocket Door Frame only | 2680 (2'6" x 8'0")   | CSU6K2680  | 1185       |
|                                                                                  |                                                      | 2880 (2'8" x 8'0")   | CSU6K2880  | 1185       |
|                                                                                  |                                                      | 3080 (3'0" x 8'0")   | CSU6K3080  | 1185       |
|                                                                                  |                                                      | 4080 (4'0" x 8'0")   | CSU6K4080  | 1295       |
|                                                                                  |                                                      | 3090 (3'0" x 9'0")   | CSU6K3090  | 1365       |
|                                                                                  |                                                      | 4090 (4'0" x 9'0")   | CSU6K4090  | 1480       |
|                                                                                  |                                                      | 30100 (3'0" x 10'0") | CSU6K30100 | 1555       |
|                                                                                  |                                                      | 40100 (4'0" x 10'0") | CSU6K40100 | 1665       |
|                                                                                  |                                                      | 50100 (5'0" x 10'0") | CSU6K50100 | 1850       |

| Item                                                                               | Description                                                          | Jamb Size | Door Thickness | Code               | Price (\$) |
|------------------------------------------------------------------------------------|----------------------------------------------------------------------|-----------|----------------|--------------------|------------|
|  | CS Cavity Slider®<br>Pocket Door Jamb Kit<br>3'0" x 8'0"             | 4-9/16"   | 1-3/8"         | JK4SW3080-138-4916 | 400        |
|                                                                                    |                                                                      |           | 1-3/4"         | JK4SW3080-134-4916 | 400        |
|                                                                                    |                                                                      | 4-7/8"    | 1-3/8"         | JK4SW3080-138-478  | 400        |
|                                                                                    |                                                                      |           | 1-3/4"         | JK4SW3080-134-478  | 400        |
|  | CS Cavity Slider®<br>Pocket Door Jamb Kit<br>4'0" x 8'0"             | 4-9/16"   | 1-3/4"         | JK4SW4080-134-4916 | 420        |
|                                                                                    |                                                                      |           | 1-3/4"         | JK4SW4080-134-478  | 420        |
|                                                                                    | CS Cavity Slider®<br>Ultimate Pocket Door<br>Jamb Kit<br>3'0" x 8'0" | 6-9/16"   | 1-3/8"         | JK6UW3080-138-6916 | 500        |
|                                                                                    |                                                                      |           | 1-3/4"         | JK6UW3080-134-6916 | 500        |
|                                                                                    |                                                                      | 6-7/8"    | 1-3/8"         | JK6UW3080-138-678  | 500        |
|                                                                                    |                                                                      |           | 1-3/4"         | JK6UW3080-134-678  | 500        |
|  | CS Cavity Slider®<br>Ultimate Pocket Door<br>Jamb Kit<br>4'0" x 8'0" | 6-9/16"   | 1-3/4"         | JK6UW4080-134-6916 | 520        |
|                                                                                    |                                                                      | 6-7/8"    | 1-3/4"         | JK6UW4080-134-678  | 520        |

# CS Cavity Slider Pocket Frame

Select Frame, Carriage Pack, and Jamb Kit

| Item                                                                                | Description                                         | Code    | Price (\$) |
|-------------------------------------------------------------------------------------|-----------------------------------------------------|---------|------------|
|    | M6 (200 lb) with no track stops                     | DKM0601 | 175        |
|    | M6 (200 lb) with 1 track stop                       | DKM0611 | 210        |
|    | M8 (500 lb) with no track stops                     | DKM0801 | 365        |
|    | M8 (500 lb) with 1 track stop                       | DKM0811 | 390        |
|    | SofStop Single Action (0-200 lb) with no stops      | DKS0501 | 470        |
|    | SofStop Single Action (0-200 lb) with 1 stop        | DKS0511 | 495        |
|    | SofStop Double Action (0-200 lb) with no stops      | DKS0701 | 665        |
|   | SofStop Double Action (0-200 lb) with 1 stop        | DKS0711 | 685        |
|  | SofStop HD Double Action (200-350 lb) with no stops | DKS0801 | 705        |
|  | SofStop HD Double Action (200-350 lb) with 1 stop   | DKS0811 | 735        |

All SofStop Carriage Packs include 2x M8 carriages



## CS Track Systems

Tracks are available in popular pre-cut lengths or can be cut to custom lengths between 6 and 24 ft (to the nearest foot). A per foot rate applies to custom lengths, which includes cutting fee.

| Item                                                                                | Description                                                                        | Length          | Code          | Price (\$) |
|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-----------------|---------------|------------|
|    | CS TopMountTrack - Single<br>Clear Anodized                                        | 6 ft            | CT6-NA        | 225        |
|                                                                                     |                                                                                    | 8 ft            | CT8-NA        | 310        |
|                                                                                     |                                                                                    | 12 ft           | CT12-NA       | 455        |
|                                                                                     |                                                                                    | 24 ft           | CT24-NA       | 915        |
|                                                                                     |                                                                                    | Custom          | CTNSS-NA      | 43/ft      |
|    | CS TopMountTrack - Single<br>Black Anodized                                        | 6 ft            | CT6-BA        | 275        |
|                                                                                     |                                                                                    | 8 ft            | CT8-BA        | 365        |
|                                                                                     |                                                                                    | 12 ft           | CT12-BA       | 540        |
|                                                                                     |                                                                                    | Custom          | CTNSS-BA      | 54/ft      |
|    | CS TopMountTrack - Single Fascia<br>Clear Anodized<br>Suits 1-3/8" or 1-3/4" door  | 6 ft            | FNA-6         | 65         |
|                                                                                     |                                                                                    | 8 ft            | FNA-8         | 80         |
|                                                                                     |                                                                                    | 12 ft           | FNA-12        | 125        |
|                                                                                     |                                                                                    | 24 ft           | FNA-24        | 245        |
|                                                                                     |                                                                                    | Custom          | FNA-NSS       | 13/ft      |
|    | CS TopMountTrack - Single Fascia<br>Bronze Anodized<br>Suits 1-3/8" or 1-3/4" door | 6 ft            | FBA-6         | 60         |
|                                                                                     |                                                                                    | 8 ft            | FBA-8         | 80         |
|                                                                                     |                                                                                    | 12 ft           | FBA-12        | 120        |
|                                                                                     |                                                                                    | 24 ft           | FBA-24        | 245        |
|                                                                                     |                                                                                    | Custom          | FBA-NSS       | 13/ft      |
|  | CS TopMountTrack - Single End Cap (x1) - Fascia One Side                           | Clear Anodized  | ZK00427       | 29         |
|                                                                                     | CS TopMountTrack - Single End Cap (x1) - Fascia One Side                           | Bronze Anodized | ZK00430       | 29         |
|  | CS TopMountTrack - Single End Cap (x1) - Fascia Both Sides                         | Clear Anodized  | ZK00428       | 29         |
|                                                                                     | CS TopMountTrack - Single End Cap (x1) - Fascia Both Sides                         | Bronze Anodized | ZK00429       | 29         |
|  | CS TopMountTrack - Double<br>1-3/8" door thickness                                 | 6 ft            | TSTM2-138-6   | 295        |
|                                                                                     |                                                                                    | 8 ft            | TSTM2-138-8   | 380        |
|                                                                                     |                                                                                    | 12 ft           | TSTM2-138-12  | 595        |
|                                                                                     |                                                                                    | 24 ft           | TSTM2-138-24  | 1185       |
|                                                                                     |                                                                                    | Custom          | TSTM2-138-NSS | 54/ft      |
|  | CS TopMountTrack - Double<br>1-3/4" door thickness                                 | 6 ft            | TSTM2-134-6   | 320        |
|                                                                                     |                                                                                    | 8 ft            | TSTM2-134-8   | 420        |
|                                                                                     |                                                                                    | 12 ft           | TSTM2-134-12  | 645        |
|                                                                                     |                                                                                    | 24 ft           | TSTM2-134-24  | 1285       |
|                                                                                     |                                                                                    | Custom          | TSTM2-134-NSS | 59/ft      |
|   | CS TopMountTrack - Triple<br>1-3/8" door thickness                                 | 6 ft            | TSTM3-138-6   | 420        |
|                                                                                     |                                                                                    | 8 ft            | TSTM3-138-8   | 550        |
|                                                                                     |                                                                                    | 12 ft           | TSTM3-138-12  | 835        |
|                                                                                     |                                                                                    | 24 ft           | TSTM3-138-24  | 1680       |
|                                                                                     |                                                                                    | Custom          | TSTM3-138-NSS | 76         |
|   | CS TopMountTrack - Triple<br>1-3/4" door thickness                                 | 6 ft            | TSTM3-134-6   | 455        |
|                                                                                     |                                                                                    | 8 ft            | TSTM3-134-8   | 605        |
|                                                                                     |                                                                                    | 12 ft           | TSTM3-134-12  | 915        |
|                                                                                     |                                                                                    | 24 ft           | TSTM3-134-24  | 1830       |
|                                                                                     |                                                                                    | Custom          | TSTM3-134-NSS | 81/ft      |

# CS Track Systems

Tracks are available in popular pre-cut lengths or can be cut to custom lengths between 6 and 24ft (to the nearest foot). A per foot rate applies to custom lengths, which includes cutting fee.

| Item                                                                                | Description                                               | Length                                       | Code            | Price (\$) |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------|----------------------------------------------|-----------------|------------|
|    | CS FH-CeilingMountTrack - Single                          | 6 ft                                         | TSFH1-6         | 290        |
|                                                                                     |                                                           | 8 ft                                         | TSFH1-8         | 375        |
|                                                                                     |                                                           | 12 ft                                        | TSFH1-12        | 580        |
|                                                                                     |                                                           | 24 ft                                        | TSFH1-24        | 1170       |
|                                                                                     |                                                           | Custom                                       | TSFH1-NSS       | 54/ft      |
|    | CS FH-CeilingMountTrack - Double<br>1-3/8" door thickness | 6 ft                                         | TSFH2-138-6     | 350        |
|                                                                                     |                                                           | 8 ft                                         | TSFH2-138-8     | 465        |
|                                                                                     |                                                           | 12 ft                                        | TSFH2-138-12    | 700        |
|                                                                                     |                                                           | 24 ft                                        | TSFH2-138-24    | 1410       |
|                                                                                     |                                                           | Custom                                       | TSFH2-138-NSS   | 65/ft      |
|    | CS FH-CeilingMountTrack - Double<br>1-3/4" door thickness | 6 ft                                         | TSFH2-134-6     | 385        |
|                                                                                     |                                                           | 8 ft                                         | TSFH2-134-8     | 500        |
|                                                                                     |                                                           | 12 ft                                        | TSFH2-134-12    | 780        |
|                                                                                     |                                                           | 24 ft                                        | TSFH2-134-24    | 1555       |
|                                                                                     |                                                           | Custom                                       | TSFH2-134-NSS   | 70/ft      |
|   | CS FH-CeilingMountTrack - Triple<br>1-3/8" door thickness | 6 ft                                         | TSFH3-138-6     | 465        |
|                                                                                     |                                                           | 8 ft                                         | TSFH3-138-8     | 610        |
|                                                                                     |                                                           | 12 ft                                        | TSFH3-138-12    | 935        |
|                                                                                     |                                                           | 24 ft                                        | TSFH3-138-24    | 1880       |
|                                                                                     |                                                           | Custom                                       | TSFH3-138-NSS   | 86/ft      |
|  | CS FH-CeilingMountTrack - Triple<br>1-3/4" door thickness | 6 ft                                         | TSFH3-134-6     | 530        |
|                                                                                     |                                                           | 8 ft                                         | TSFH3-134-8     | 700        |
|                                                                                     |                                                           | 12 ft                                        | TSFH3-134-12    | 1060       |
|                                                                                     |                                                           | 24 ft                                        | TSFH3-134-24    | 2120       |
|                                                                                     |                                                           | Custom                                       | TSFH3-134-NSS   | 97/ft      |
|  | CS HeavyDutyTrack - Single                                | Custom                                       | TSHDT1NA0NSS    | 162/ft     |
|  | CS Frameless Glass Clamp<br>3/8" glass thickness          | 2 ft                                         | FGCTM1NA0020-38 | 900        |
|                                                                                     |                                                           | 3 ft                                         | FGCTM1NA0030-38 | 990        |
|                                                                                     |                                                           | 4 ft                                         | FGCTM1NA0040-38 | 1070       |
|                                                                                     |                                                           | 5 ft                                         | FGCTM1NA0050-38 | 1160       |
|                                                                                     |                                                           | 6 ft                                         | FGCTM1NA0060-38 | 1240       |
|                                                                                     | CS Frameless Glass Clamp<br>1/2" glass thickness          | 2 ft                                         | FGCTM1NA0020-12 | 900        |
|                                                                                     |                                                           | 3 ft                                         | FGCTM1NA0030-12 | 990        |
|                                                                                     |                                                           | 4 ft                                         | FGCTM1NA0040-12 | 1070       |
|                                                                                     |                                                           | 5 ft                                         | FGCTM1NA0050-12 | 1160       |
|                                                                                     |                                                           | 6 ft                                         | FGCTM1NA0060-12 | 1240       |
|                                                                                     |                                                           | Cut down charge for CS Frameless Glass Clamp |                 | 50         |
|  | CS Frameless Glass U-Guide<br>Suits 3/8" & 1/2" glass     |                                              | FGUG            | 90         |





## CS Barn Track Systems

| Item                                                                                | Description                                                                                                                           | Length | Code         | Price (\$) |
|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|--------|--------------|------------|
|    | CS WallMountTrack Kit<br>(including fascia and end caps)<br><br>Suits 1-3/8" to 1-3/4" door thickness<br><br>Natural (Clear) Anodized | 6 ft   | TSWMNA-6     | 415        |
|                                                                                     |                                                                                                                                       | 8 ft   | TSWMNA-8     | 540        |
|                                                                                     |                                                                                                                                       | 12 ft  | TSWMNA-12    | 820        |
|                                                                                     |                                                                                                                                       | 24 ft  | TSWMNA-24    | 1650       |
|                                                                                     |                                                                                                                                       | Custom | TSWMNA-NSS   | 75/ft      |
|    | CS WallMountTrack Kit<br>(including fascia and end caps)<br><br>Suits 1-3/8" to 1-3/4" door thickness<br><br>Bronze Anodized          | 6 ft   | TSWMBA-6     | 415        |
|                                                                                     |                                                                                                                                       | 8 ft   | TSWMBA-8     | 540        |
|                                                                                     |                                                                                                                                       | 12 ft  | TSWMBA-12    | 820        |
|                                                                                     |                                                                                                                                       | 24 ft  | TSWMBA-24    | 1650       |
|                                                                                     |                                                                                                                                       | Custom | TSWMBA-NSS   | 75/ft      |
|    | CS WallMountTrack<br>(Carriage Section only)                                                                                          | Custom | ZA00244      | 60/ft      |
|    | CS SideMountTrack Kit<br>(including fascia and end caps)<br><br>Suits 1-3/8" to 1-3/4" door thickness<br><br>Natural (Clear) Anodized | 6 ft   | TSCTSMNA-6   | 350        |
|                                                                                     |                                                                                                                                       | 8 ft   | TSCTSMNA-8   | 455        |
|                                                                                     |                                                                                                                                       | 12 ft  | TSCTSMNA-12  | 705        |
|                                                                                     |                                                                                                                                       | 24 ft  | TSCTSMNA-24  | 1410       |
|                                                                                     |                                                                                                                                       | Custom | TSCTSMNA-NSS | 65/ft      |
|   | CS SideMountTrack Kit<br>(including fascia and end caps)<br><br>Suits 1-3/8" to 1-3/4" door thickness<br><br>Bronze Anodized          | 6 ft   | TSCTSMBA-6   | 350        |
|                                                                                     |                                                                                                                                       | 8 ft   | TSCTSMBA-8   | 455        |
|                                                                                     |                                                                                                                                       | 12 ft  | TSCTSMBA-12  | 705        |
|                                                                                     |                                                                                                                                       | 24 ft  | TSCTSMBA-24  | 1410       |
|                                                                                     |                                                                                                                                       | Custom | TSCTSMBA-NSS | 65/ft      |
|  | CS SideMountTrack<br>(Carriage Section only)                                                                                          | Custom | ZA00351      | 43/ft      |
|  | Barn Door Track Pack<br>(Includes track, fixing bracket and screw pack)<br><br>Narrow                                                 | 6 ft   | TSBS1830N    | 945        |
|                                                                                     |                                                                                                                                       | 7 ft   | TSBS2135N    | 1020       |
|                                                                                     |                                                                                                                                       | 8 ft   | TSBS2440N    | 1080       |
|                                                                                     |                                                                                                                                       | 9 ft   | TSBS2745N    | 1155       |
|                                                                                     |                                                                                                                                       | 10 ft  | TSBS3050N    | 1220       |
|                                                                                     |                                                                                                                                       | 12 ft  | TSBS3660N    | 1625       |
|  | Barn Door Track Pack<br>(Includes track, fixing bracket and screw pack)<br><br>Wide                                                   | 6 ft   | TSBS1830W    | 945        |
|                                                                                     |                                                                                                                                       | 7 ft   | TSBS2135W    | 1015       |
|                                                                                     |                                                                                                                                       | 8 ft   | TSBS2440W    | 1080       |
|                                                                                     |                                                                                                                                       | 9 ft   | TSBS2745W    | 1155       |
|                                                                                     |                                                                                                                                       | 10 ft  | TSBS3050W    | 1220       |
|                                                                                     |                                                                                                                                       | 12 ft  | TSBS3660W    | 1625       |
|                                                                                     |                                                                                                                                       | 13 ft  | TSBS3962W    | 1900       |
|                                                                                     |                                                                                                                                       | 14 ft  | TSBS4267W    | 2170       |
|                                                                                     |                                                                                                                                       | 15 ft  | TSBS4572W    | 2440       |
|                                                                                     |                                                                                                                                       | 16 ft  | TSBS4877W    | 2715       |
|                                                                                     |                                                                                                                                       | 17 ft  | TSBS5182W    | 2985       |
|                                                                                     |                                                                                                                                       | 18 ft  | TSBS5486W    | 3260       |
|                                                                                     |                                                                                                                                       | 19 ft  | TSBS5791W    | 3530       |

# Carriage Packs

Suitable for use with:

- CS Cavity Slider®
- CS TopMountTrack - Single/Double/Triple
- CS FH-CeilingMountTrack - Single/Double/Triple
- CS WallMountTrack

| Item                                                                                | Description                     | Code    | Price per pack (\$) |
|-------------------------------------------------------------------------------------|---------------------------------|---------|---------------------|
|    | M6 (200 lb) with no track stops | DKM0601 | 175                 |
|    | M6 (200 lb) with 1 track stop   | DKM0611 | 210                 |
|     | M6 (200 lb) with 2 track stops  | DKM0621 | 235                 |
|    | M8 (500 lb) with no track stops | DKM0801 | 365                 |
|  | M8 (500 lb) with 1 track stop   | DKM0811 | 390                 |
|   | M8 (500 lb) with 2 track stops  | DKM0821 | 415                 |

Suitable for use with:

- CS Barn Door Track



| Item                                                                                | Description                                      | Code    | Price (\$) |
|-------------------------------------------------------------------------------------|--------------------------------------------------|---------|------------|
|  | CS Barn Door Hangers & Stops Pack                | TSBS001 | 595        |
|   | SofStop (264 lb) Single Pack for Barn Door Track | TSBS100 | 255        |

For double soft close and soft open, two (2) Barn Door Track SofStop Packs are required. The Minimum Door Width for the use of SofStop is 24".

## Carriage Packs

Suitable for use with:

- CS Cavity Slider®
- CS TopMountTrack - Single
- CS FH-CeilingMountTrack
- CS WallMountTrack


| Item                                                                               | Description                                         | Code    | Price per pack (\$) |
|------------------------------------------------------------------------------------|-----------------------------------------------------|---------|---------------------|
|   | SofStop Single Action (0-200 lb) with no stops      | DKS0501 | 470                 |
|   | SofStop Single Action (0-200 lb) with 1 stop        | DKS0511 | 495                 |
|   | SofStop Single Action (0-200 lb) with 2 stops       | DKS0521 | 515                 |
|   | SofStop Double Action (0-200 lb) with no stops      | DKS0701 | 665                 |
|   | SofStop Double Action (0-200 lb) with 1 stop        | DKS0711 | 685                 |
|   | SofStop Double Action (0-200 lb) with 2 stops       | DKS0721 | 705                 |
|  | SofStop HD Double Action (200-350 lb) with no stops | DKS0801 | 705                 |
|  | SofStop HD Double Action (200-350 lb) with 1 stop   | DKS0811 | 735                 |
|  | SofStop HD Double Action (200-350 lb) with 2 stops  | DKS0821 | 755                 |

All SofStop Carriage Packs include 2x M8 carriages

## Carriage Packs

Suitable for use with:

- CS HeavyDutyTrack

| Item                                                                                | Description                       | Code    | Price per pack (\$) |
|-------------------------------------------------------------------------------------|-----------------------------------|---------|---------------------|
|  | M10 (1100 lb) with no track stops | DKM1000 | 970                 |
|   | M10 (1100 lb) with 1 track stop   | DKM1010 | 1430                |
|  | M10 (1100 lb) with 2 track stops  | DKM1020 | 1890                |

# Track Kits

Track Combo Kits include the track and carriage pack required for your selected sliding door application.

## CS TopMountTrack - Single

| Item                                                                             | Description                                                             | Carriage     | Code      | Price (\$) |
|----------------------------------------------------------------------------------|-------------------------------------------------------------------------|--------------|-----------|------------|
|  | 6' TopMountTrack - Single Track Kit<br>Includes Track and Carriage Pack | 200 lb (M6)  | KCT6-M611 | 435        |
|                                                                                  |                                                                         | Twin SofStop | KCT6-S711 | 910        |
|                                                                                  | 8' TopMountTrack - Single Track Kit<br>Includes Track and Carriage Pack | 200 lb (M6)  | KCT8-M611 | 520        |
|                                                                                  |                                                                         | Twin SofStop | KCT8-S711 | 995        |

## CS TopMountTrack - Double (Bypass)

| Item                                                                                                                 | Description                                                                                    | Door Width                                                                                                          | Color   | Carriage     | Code            | Price (\$)      |      |
|----------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|---------|--------------|-----------------|-----------------|------|
| <br>1-3/8" Door<br>Natural Fascia   | 6' TopMountTrack - Double<br>Track Kit<br><br>Includes Track, Fascia, and<br>2x Carriage Packs | 1-3/8"                                                                                                              | Natural | 200 lb (M6)  | KTM2N6-M621-138 | 830             |      |
|                                                                                                                      |                                                                                                |                                                                                                                     |         | Twin SofStop | KTM2N6-S701-138 | 1690            |      |
|                                                                                                                      |                                                                                                |                                                                                                                     | Bronze  | 200 lb (M6)  | KTM2B6-M621-138 | 825             |      |
|                                                                                                                      |                                                                                                |                                                                                                                     |         | Twin SofStop | KTM2B6-S701-138 | 1685            |      |
| <br>1-3/8" Door<br>Bronze Fascia  |                                                                                                | 1-3/4"                                                                                                              | Natural | 200 lb (M6)  | KTM2N6-M621-134 | 855             |      |
|                                                                                                                      |                                                                                                |                                                                                                                     |         | Twin SofStop | KTM2N6-S701-134 | 1715            |      |
|                                                                                                                      |                                                                                                |                                                                                                                     | Bronze  | 200 lb (M6)  | KTM2B6-M621-134 | 850             |      |
|                                                                                                                      |                                                                                                |                                                                                                                     |         | Twin SofStop | KTM2B6-S701-134 | 1710            |      |
| <br>1-3/4" Door<br>Natural Fascia | 8' TopMountTrack - Double<br>Track Kit<br><br>Includes Track, Fascia, and<br>2x Carriage Packs | 1-3/8"                                                                                                              | Natural | 200 lb (M6)  | KTM2N8-M621-138 | 930             |      |
|                                                                                                                      |                                                                                                |                                                                                                                     |         | Twin SofStop | KTM2N8-S701-138 | 1790            |      |
|                                                                                                                      |                                                                                                |                                                                                                                     | Bronze  | 200 lb (M6)  | KTM2B8-M621-138 | 930             |      |
|                                                                                                                      |                                                                                                |                                                                                                                     |         | Twin SofStop | KTM2B8-S701-138 | 1790            |      |
|                                                                                                                      |                                                                                                | <br>1-3/4" Door<br>Bronze Fascia | 1-3/4"  | Natural      | 200 lb (M6)     | KTM2N8-M621-134 | 970  |
|                                                                                                                      |                                                                                                |                                                                                                                     |         |              | Twin SofStop    | KTM2N8-S701-134 | 1830 |
|                                                                                                                      |                                                                                                |                                                                                                                     |         | Bronze       | 200 lb (M6)     | KTM2B8-M621-134 | 970  |
|                                                                                                                      |                                                                                                |                                                                                                                     |         |              | Twin SofStop    | KTM2B8-S701-134 | 1830 |



Track Kit packaging

## Track Kits

Track Combo Kits include the track and carriage pack required for your selected sliding door application.

### CS FH-CeilingMountTrack

| Item                                                                             | Description                                                           | Carriage     | Code      | Price (\$) |
|----------------------------------------------------------------------------------|-----------------------------------------------------------------------|--------------|-----------|------------|
|  | 6' FH-CeilingMountTrack Combo Kit<br>Includes Track and Carriage Pack | 200 lb (M6)  | KFH6-M621 | 525        |
|                                                                                  |                                                                       | Twin SofStop | KFH6-S721 | 995        |
|                                                                                  | 8' FH-CeilingMountTrack Combo Kit<br>Includes Track and Carriage Pack | 200 lb (M6)  | KFH8-M621 | 610        |
|                                                                                  |                                                                       | Twin SofStop | KFH8-S721 | 1080       |

### CS SideMountTrack (Contemporary Barn Door Track)

| Item                                                                                                     | Description                                                              | Color   | Carriage     | Code       | Price (\$) |
|----------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|---------|--------------|------------|------------|
| <br>Natural<br>Anodized | 6' SideMountTrack Combo Kit<br>Includes Track, Fascia, and Carriage Pack | Natural | 200 lb (M6)  | KSMN6-M621 | 585        |
|                                                                                                          |                                                                          |         | Twin SofStop | KSMN6-S721 | 1055       |
|                                                                                                          |                                                                          | Bronze  | 200 lb (M6)  | KSMB6-M621 | 585        |
|                                                                                                          |                                                                          |         | Twin SofStop | KSMB6-S721 | 1055       |
| <br>Bronze<br>Anodized | 8' SideMountTrack Combo Kit<br>Includes Track, Fascia, and Carriage Pack | Natural | 200 lb (M6)  | KSMN8-M621 | 690        |
|                                                                                                          |                                                                          |         | Twin SofStop | KSMN8-S721 | 1160       |
|                                                                                                          |                                                                          | Bronze  | 200 lb (M6)  | KSMB8-M621 | 690        |
|                                                                                                          |                                                                          |         | Twin SofStop | KSMB8-S721 | 1160       |




Track Kit packaging


# Collection Packs

Suitable for use with:

- CS TopMountTrack - Double/Triple
- CS FH-CeilingMountTrack - Double/Triple

| Item                                                                               | Description                              | Code    | Price per pack (\$) |
|------------------------------------------------------------------------------------|------------------------------------------|---------|---------------------|
|   | 2 Door M6 (200 lb) 13/8" Collection Pack | DKO6201 | 735                 |
|                                                                                    | 2 Door M6 (200 lb) 13/4" Collection Pack | DKO6221 | 735                 |
|   | 3 Door M6 (200 lb) 13/8" Collection Pack | DKO6301 | 1135                |
|                                                                                    | 3 Door M6 (200 lb) 13/4" Collection Pack | DKO6321 | 1135                |
|   | 2 Door M8 (500 lb) 13/8" Collection Pack | DKO8201 | 1190                |
|                                                                                    | 2 Door M8 (500 lb) 13/4" Collection Pack | DKO8221 | 1190                |
|  | 3 Door M8 (500 lb) 13/8" Collection Pack | DKO8301 | 1850                |
|                                                                                    | 3 Door M8 (500 lb) 13/4" Collection Pack | DKO8321 | 1850                |

# Floor Channel & Bearing Guide System

| Item                                                                                | Description                                            | Length | Code    | Price (\$) |
|-------------------------------------------------------------------------------------|--------------------------------------------------------|--------|---------|------------|
|  | Single Stainless Steel Ball Bearing Roller Guide       |        | ZK00384 | 62         |
|  | Double Stainless Steel Ball Bearing Roller Guide       |        | ZK00385 | 99         |
|  | Aluminum bronze anodized floor channel with PVC insert | 6 ft   | ZK00386 | 125        |
|                                                                                     |                                                        | 8 ft   | ZK00387 | 153        |
|                                                                                     |                                                        | 12 ft  | ZK00388 | 226        |
|                                                                                     |                                                        | 24 ft  | ZK00389 | 450        |

## Components

| Item                                                                                | Description (Parts sold individually)                                                                                            | Code    | Price Each (\$) |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|---------|-----------------|
|    | M6 Carriage (200 lb per pair)                                                                                                    | ZK00396 | 62              |
|    | M8 Carriage (500 lb per pair)                                                                                                    | ZK00344 | 161             |
|    | M6/M8 Mounting Plate                                                                                                             | ZK00095 | 26              |
|    | M6/M8 Mounting Plate with Stop                                                                                                   | ZK00096 | 36              |
|    | Track Stop                                                                                                                       | ZK00377 | 31              |
|    | M6/M8 Adjusting Wrench                                                                                                           | ZM00008 | 8               |
|    | Extra Long M6 Hanger Pin (2-3/8" or 60 mm)                                                                                       | ZK00135 | 10              |
|    | Extra Long M8 Hanger Pin (2-3/8" or 60 mm)                                                                                       | ZK00138 | 23              |
|   | Joining Pin (For use with the Cavity Slider Pocket Frame, TopMountTrack Double/Triple, HeavyDutyTrack, and FH-CeilingMountTrack) | ZK00305 | 1               |
|  | Joining Pin (For use with TopMountTrack - Single, CS WallMountTrack, and CS SideMountTrack)                                      | ZK00439 | 1               |
|  | Extra Tall 2" (50 mm) T-Guide Kit                                                                                                | ZK00067 | 18              |
|  | Black Plastic T-Guide 1" (25 mm) Kit                                                                                             | ZK00069 | 15              |
|  | T-Guide Base (CS Cavity Slider Pocket Frame)                                                                                     | ZK00322 | 9               |
|  | Door Guide T 1-3/16" (30 mm)<br>(CS Cavity Slider Pocket Frame)                                                                  | ZK00328 | 2               |
|  | Door Guide T 2" (50 mm)<br>(CS Cavity Slider Pocket Frame)                                                                       | ZK00331 | 4               |
|  | SofStop Activator                                                                                                                | ZK00327 | 9               |
|  | SofStop Dual Action Mechanism - 0-200 lb                                                                                         | ZK00505 | 285             |
|   | SofStop HD Dual Action Mechanism - 200-350 lb                                                                                    | ZK00506 | 365             |

# Slat Kits

| Item                                                                             | Description                                                   | Code       | Price (\$) |
|----------------------------------------------------------------------------------|---------------------------------------------------------------|------------|------------|
|  | Slat Kit 3068<br>(Includes 2 slats, screws and slat joiners)  | CSSK3000   | 78         |
|                                                                                  | Slat Kit 3080<br>(Includes 2 slats, screws and slat joiners)  | CSSK3000HD | 78         |
|                                                                                  | Slat Kit 4080<br>(Includes 2 slats, screws and slat joiners)  | CSSK4000   | 95         |
|                                                                                  | Slat Kit 50100<br>(Includes 2 slats, screws and slat joiners) | CSSK5000   | 117        |

# Additional Components

## M10 (1100lb) Components

| Item                                                                                | Description (Parts sold individually) | Code    | Price (\$) |
|-------------------------------------------------------------------------------------|---------------------------------------|---------|------------|
|    | M10 Carriage (1100 lb per pair)       | ZK00128 | 265        |
|    | M10 Mounting Plate                    | ZK00129 | 240        |
|   | M10 Mounting Plate with Stop          | ZK00130 | 515        |
|  | M10 Track Stop Aluminum               | ZK00308 | 250        |
|  | M10 Adjusting Wrench                  | ZM00009 | 34         |

# Stainless Steel Components



## M8 (500lb) Components

| Item                                                                                | Description                                    | Code    | Price Each (\$) |
|-------------------------------------------------------------------------------------|------------------------------------------------|---------|-----------------|
|  | M8 Carriage Stainless Steel ( 500 lb per pair) | ZK00381 | 210             |
|  | M8 Mounting Plate - Stainless Steel            | ZK00112 | 90              |
|  | M8 Mounting Plate with Stop - Stainless Steel  | ZK00113 | 170             |
|  | M8 Track Stop Aluminum                         | ZK00377 | 31              |



## M10 (1100lb) Components

| Item                                                                                | Description                                          | Code    | Price Each (\$) |
|-------------------------------------------------------------------------------------|------------------------------------------------------|---------|-----------------|
|  | M10 Carriage Stainless Steel (1100 lb per pair)      | ZK00145 | 685             |
|  | M10 Mounting Plate - Stainless Steel                 | ZK00147 | 285             |
|  | M10 Mounting Plate with Track Stop - Stainless Steel | ZK00148 | 570             |

## CL400 Magnetic Passage

| Function                           |                                                                                   | Finish        | Door Thickness |       |            |       |
|------------------------------------|-----------------------------------------------------------------------------------|---------------|----------------|-------|------------|-------|
|                                    |                                                                                   |               | 1-3/8"         | Price | 1-3/4"     | Price |
| Blank/Blank<br>(Non-Latching)      |  | Bright Chrome | CL400A0025     | 392   | CL400A0026 | 392   |
|                                    |                                                                                   | Satin Chrome  | CL400A0125     | 345   | CL400A0126 | 345   |
|                                    |                                                                                   | ORB           | CL400A0225     | 441   | CL400A0226 | 441   |
|                                    |                                                                                   | Satin Nickel  | CL400A0325     | 345   | CL400A0326 | 345   |
|                                    |                                                                                   | Matte Black   | CL400A0425     | 446   | CL400A0426 | 446   |
| Blank/Blank<br>(Magnetic Latching) |  | Bright Chrome | CL400A0028     | 539   | CL400A0029 | 539   |
|                                    |                                                                                   | Satin Chrome  | CL400A0128     | 474   | CL400A0129 | 474   |
|                                    |                                                                                   | ORB           | CL400A0228     | 589   | CL400A0229 | 589   |
|                                    |                                                                                   | Satin Nickel  | CL400A0328     | 474   | CL400A0329 | 474   |
|                                    |                                                                                   | Matte Black   | CL400A0428     | 589   | CL400A0429 | 589   |




## CL400 Magnetic Privacy

| Function         |                                                                                     | Finish        | Door Thickness |       |            |       |
|------------------|-------------------------------------------------------------------------------------|---------------|----------------|-------|------------|-------|
|                  |                                                                                     |               | 1-3/8"         | Price | 1-3/4"     | Price |
| LH Emerg/Snib RH |  | Bright Chrome | CL400B0028     | 605   | CL400B0033 | 605   |
|                  |                                                                                     | Satin Chrome  | CL400B0128     | 532   | CL400B0133 | 532   |
|                  |                                                                                     | ORB           | CL400B0228     | 658   | CL400B0233 | 658   |
|                  |                                                                                     | Satin Nickel  | CL400B0328     | 532   | CL400B0333 | 532   |
|                  |                                                                                     | Matte Black   | CL400B0428     | 658   | CL400B0433 | 658   |
| LH Snib/Emerg RH |  | Bright Chrome | CL400B0029     | 605   | CL400B0034 | 605   |
|                  |                                                                                     | Satin Chrome  | CL400B0129     | 532   | CL400B0134 | 532   |
|                  |                                                                                     | ORB           | CL400B0229     | 658   | CL400B0234 | 658   |
|                  |                                                                                     | Satin Nickel  | CL400B0329     | 532   | CL400B0334 | 532   |
|                  |                                                                                     | Matte Black   | CL400B0429     | 658   | CL400B0434 | 658   |

Pricing covers popular SKUs. For other finishes, door thicknesses or configurations, inquire for pricing and availability.

Refer to handling/selection procedure on page 121.






## CL400 Magnetic Key Locking (Handed)

| Function       |                                                                                    | Finish        | Door Thickness |       |            |       |
|----------------|------------------------------------------------------------------------------------|---------------|----------------|-------|------------|-------|
|                |                                                                                    |               | 1-3/8"         | Price | 1-3/4"     | Price |
| LH Snib/Key RH |   | Bright Chrome | CL400C0027     | 647   | CL400C0037 | 647   |
|                |                                                                                    | Satin Chrome  | CL400C0127     | 569   | CL400C0137 | 569   |
|                |                                                                                    | ORB           | CL400C0227     | 706   | CL400C0237 | 706   |
|                |                                                                                    | Satin Nickel  | CL400C0327     | 569   | CL400C0337 | 569   |
|                |                                                                                    | Matte Black   | CL400C0427     | 706   | CL400C0437 | 706   |
| LH Key/Snib RH |   | Bright Chrome | CL400C0028     | 647   | CL400C0038 | 647   |
|                |                                                                                    | Satin Chrome  | CL400C0128     | 569   | CL400C0138 | 569   |
|                |                                                                                    | ORB           | CL400C0228     | 706   | CL400C0238 | 706   |
|                |                                                                                    | Satin Nickel  | CL400C0328     | 569   | CL400C0338 | 569   |
|                |                                                                                    | Matte Black   | CL400C0428     | 706   | CL400C0438 | 706   |
| Key/Key        |  | Bright Chrome | CL400C0029     | 647   | CL400C0039 | 647   |
|                |                                                                                    | Satin Chrome  | CL400C0129     | 569   | CL400C0139 | 569   |
|                |                                                                                    | ORB           | CL400C0229     | 706   | CL400C0239 | 706   |
|                |                                                                                    | Satin Nickel  | CL400C0329     | 569   | CL400C0339 | 569   |
|                |                                                                                    | Matte Black   | CL400C0429     | 706   | CL400C0439 | 706   |

Pricing covers popular SKUs. For other finishes, door thicknesses or configurations, inquire for pricing and availability.

Refer to handing/selection procedure on page 121.



## CL400 Magnetic Bi-Parting

| Function                                                                                                                     | Finish        | Door Thickness |       |            |       |
|------------------------------------------------------------------------------------------------------------------------------|---------------|----------------|-------|------------|-------|
|                                                                                                                              |               | 1-3/8"         | Price | 1-3/4"     | Price |
| Passage<br>(Non Magnetic,<br>non-latching)  | Bright Chrome | CL400D0025     | 757   | CL400D0026 | 757   |
|                                                                                                                              | Satin Chrome  | CL400D0125     | 748   | CL400D0126 | 748   |
|                                                                                                                              | ORB           | CL400D0225     | 862   | CL400D0226 | 862   |
|                                                                                                                              | Satin Nickel  | CL400D0325     | 790   | CL400D0326 | 790   |
|                                                                                                                              | Matte Black   | CL400D0425     | 862   | CL400D0426 | 862   |
| Passage<br>(Magnetic latching)              | Bright Chrome | CL400D0028     | 894   | CL400D0029 | 894   |
|                                                                                                                              | Satin Chrome  | CL400D0128     | 787   | CL400D0129 | 787   |
|                                                                                                                              | ORB           | CL400D0228     | 972   | CL400D0229 | 972   |
|                                                                                                                              | Satin Nickel  | CL400D0328     | 787   | CL400D0329 | 787   |
|                                                                                                                              | Matte Black   | CL400D0428     | 972   | CL400D0429 | 972   |
| Privacy<br>Emerg/Snib                       | Bright Chrome | CL400D0038     | 894   | CL400D0043 | 894   |
|                                                                                                                              | Satin Chrome  | CL400D0138     | 787   | CL400D0143 | 787   |
|                                                                                                                              | ORB           | CL400D0238     | 972   | CL400D0243 | 972   |
|                                                                                                                              | Satin Nickel  | CL400D0338     | 787   | CL400D0343 | 787   |
|                                                                                                                              | Matte Black   | CL400D0438     | 972   | CL400D0443 | 972   |
| Snib/Key                                   | Bright Chrome | CL400D0052     | 960   | CL400D0062 | 960   |
|                                                                                                                              | Satin Chrome  | CL400D0152     | 845   | CL400D0162 | 845   |
|                                                                                                                              | ORB           | CL400D0252     | 1091  | CL400D0262 | 1091  |
|                                                                                                                              | Satin Nickel  | CL400D0352     | 845   | CL400D0362 | 845   |
|                                                                                                                              | Matte Black   | CL400D0452     | 1091  | CL400D0462 | 1091  |
| Key/Key                                   | Bright Chrome | CL400D0055     | 960   | CL400D0065 | 960   |
|                                                                                                                              | Satin Chrome  | CL400D0155     | 845   | CL400D0165 | 845   |
|                                                                                                                              | ORB           | CL400D0255     | 1090  | CL400D0265 | 1090  |
|                                                                                                                              | Satin Nickel  | CL400D0355     | 845   | CL400D0365 | 845   |
|                                                                                                                              | Matte Black   | CL400D0455     | 1090  | CL400D0465 | 1090  |



Pricing covers popular SKUs. For other finishes, door thicknesses or configurations, inquire for pricing and availability.

Refer to handing/selection procedure on page 121.



## CL400 ADA Magnetic Passage

| Function                                      |                                                                                   | Finish        | Door Thickness |       |            |       |
|-----------------------------------------------|-----------------------------------------------------------------------------------|---------------|----------------|-------|------------|-------|
|                                               |                                                                                   |               | 1-3/8"         | Price | 1-3/4"     | Price |
| Blank/Blank<br>(Non-latching)<br>Non-magnetic |  | Bright Chrome | CL406A0025     | 594   | CL406A0026 | 594   |
|                                               |                                                                                   | Satin Chrome  | CL406A0125     | 572   | CL406A0126 | 572   |
|                                               |                                                                                   | ORB           | CL406A0225     | 616   | CL406A0226 | 616   |
|                                               |                                                                                   | Satin Nickel  | CL406A0325     | 572   | CL406A0326 | 572   |
| Blank/Blank<br>(Magnetic latching)            |  | Bright Chrome | CL406A0028     | 688   | CL406A0029 | 688   |
|                                               |                                                                                   | Satin Chrome  | CL406A0128     | 655   | CL406A0129 | 655   |
|                                               |                                                                                   | ORB           | CL406A0228     | 715   | CL406A0229 | 715   |
|                                               |                                                                                   | Satin Nickel  | CL406A0328     | 655   | CL406A0329 | 655   |

## CL400 ADA Magnetic Privacy (Handed)

| Function         |                                                                                     | Finish        | Door Thickness |       |            |       |
|------------------|-------------------------------------------------------------------------------------|---------------|----------------|-------|------------|-------|
|                  |                                                                                     |               | 1-3/8"         | Price | 1-3/4"     | Price |
| LH Emerg/Snib RH |   | Bright Chrome | CL406B0028     | 848   | CL406B0033 | 848   |
|                  |                                                                                     | Satin Chrome  | CL406B0128     | 810   | CL406B0133 | 810   |
|                  |                                                                                     | ORB           | CL406B0228     | 910   | CL406B0233 | 910   |
|                  |                                                                                     | Satin Nickel  | CL406B0328     | 810   | CL406B0333 | 810   |
| LH Snib/Emerg RH |  | Bright Chrome | CL406B0029     | 848   | CL406B0034 | 848   |
|                  |                                                                                     | Satin Chrome  | CL406B0129     | 810   | CL406B0134 | 810   |
|                  |                                                                                     | ORB           | CL406B0229     | 910   | CL406B0234 | 910   |
|                  |                                                                                     | Satin Nickel  | CL406B0329     | 810   | CL406B0334 | 810   |

## CL400 ADA Magnetic Bi-Parting


| Function                       |                                                                                     | Finish        | Door Thickness |       |            |       |
|--------------------------------|-------------------------------------------------------------------------------------|---------------|----------------|-------|------------|-------|
|                                |                                                                                     |               | 1-3/8"         | Price | 1-3/4"     | Price |
| Passage<br>(Magnetic latching) |  | Bright Chrome | CL406D0028     | 1144  | CL406D0029 | 1144  |
|                                |                                                                                     | Satin Chrome  | CL406D0128     | 1089  | CL406D0129 | 1089  |
|                                |                                                                                     | ORB           | CL406D0228     | 1179  | CL406D0229 | 1179  |
|                                |                                                                                     | Satin Nickel  | CL406D0328     | 1089  | CL406D0329 | 1089  |
| Privacy<br>Emergency/Snib      |  | Bright Chrome | CL406D0038     | 1354  | CL406D0043 | 1354  |
|                                |                                                                                     | Satin Chrome  | CL406D0138     | 1212  | CL406D0143 | 1212  |
|                                |                                                                                     | ORB           | CL406D0238     | 1324  | CL406D0243 | 1324  |
|                                |                                                                                     | Satin Nickel  | CL406D0338     | 1212  | CL406D0343 | 1212  |

Pricing covers popular SKUs. For other finishes, door thicknesses or configurations, inquire for pricing and availability.

Refer to handing/selection procedure on page 121.


## CS BarnDoorStrike

| Description         | Finish             | Code        | Price (\$) |
|---------------------|--------------------|-------------|------------|
| CS BarnDoorStrike   | Bright Chrome      | CL400SA0025 | 275        |
|                     | Satin Chrome       | CL400SA0125 | 275        |
|                     | ORB                | CL400SA0225 | 275        |
|                     | Satin Nickel       | CL400SA0325 | 275        |
|                     | Matte Black        | CL400SA0425 | 275        |
|                     | Paint Primed White | CL400SA0725 | 275        |
| Right Angle Bracket | Bright Chrome      | CL400BA0025 | 55         |
|                     | Satin Chrome       | CL400BA0125 | 55         |
|                     | ORB                | CL400BA0225 | 55         |
|                     | Satin Nickel       | CL400BA0325 | 55         |
|                     | Matte Black        | CL400BA0425 | 55         |
|                     | Paint Primed White | CL400BA0725 | 55         |




## CL200 Range Passage

| Function    | Finish        | Door Thickness |       |            |       |
|-------------|---------------|----------------|-------|------------|-------|
|             |               | 1-3/8"         | Price | 1-3/4"     | Price |
| Blank/Blank | Bright Chrome | CL205A0000     | 285   | CL205A0015 | 285   |
|             | Satin Chrome  | CL205A0001     | 221   | CL205A0016 | 221   |
|             | ORB           | CL205A0002     | 285   | CL205A0017 | 285   |
|             | Satin Nickel  | CL205A0003     | 221   | CL205A0018 | 221   |
|             | Matte Black   | CL205A0006     | 285   | CL205A0021 | 285   |



## CL200 Range Privacy (Not Handed)

| Function       | Finish        | Door Thickness |       |            |       |
|----------------|---------------|----------------|-------|------------|-------|
|                |               | 1-3/8"         | Price | 1-3/4"     | Price |
| Snib/Emergency | Bright Chrome | CL205D0000     | 322   | CL205D0030 | 322   |
|                | Satin Chrome  | CL205D0003     | 253   | CL205D0033 | 253   |
|                | ORB           | CL205D0006     | 322   | CL205D0036 | 322   |
|                | Satin Nickel  | CL205D0009     | 253   | CL205D0039 | 253   |
|                | Matte Black   | CL205D0018     | 322   | CL205D0048 | 322   |




Pricing covers popular SKUs. For other finishes, door thicknesses or configurations, inquire for pricing and availability.

Refer to handing/selection procedure on page 121.




# CL200 Bi-Parting Mate (to latch with Privacy)

Bi-Parting handles are ordered as two separate items. Choose a privacy handle then add a Bi-Parting mate with striker. For Bi-Parting Passage handles, order 2x single passage handles.

| Function                                                     | Finish        | Door Thickness |       |            |       |
|--------------------------------------------------------------|---------------|----------------|-------|------------|-------|
|                                                              |               | 1-3/8"         | Price | 1-3/4"     | Price |
| Bi-Parting Mate<br>Blank/Blank<br>(with latching face plate) | Bright Chrome | CL205C0000     | 297   | CL205C0015 | 297   |
|                                                              | Satin Chrome  | CL205C0001     | 228   | CL205C0016 | 228   |
|                                                              | ORB           | CL205C0002     | 297   | CL205C0017 | 297   |
|                                                              | Satin Nickel  | CL205C0003     | 228   | CL205C0018 | 228   |
|                                                              | Matte Black   | CL205C0006     | 297   | CL205C0021 | 297   |








# CL100 FlushTurn



| Function                     | Finish                                                                                              | Code       | Price |
|------------------------------|-----------------------------------------------------------------------------------------------------|------------|-------|
| Key/Key<br>(not handed)      |  Stainless Steel   | CL100A1070 | 580   |
| Key One Side<br>(not handed) |  Stainless Steel  | CL100A1006 | 580   |
| FlushTurn Only               |  Stainless Steel | CL100A9004 | 521   |

Pricing covers popular SKUs. For other finishes, door thicknesses or configurations, inquire for pricing and availability. Refer to handing/selection procedure on page 121.

## CL100 Lever

| Function                       |                                                                                    | Finish          | Code       | Price |
|--------------------------------|------------------------------------------------------------------------------------|-----------------|------------|-------|
| Key/Key<br>(not handed)        |   | Stainless Steel | CL100A7054 | 642   |
| Key/Turn<br>(not handed)       |   | Stainless Steel | CL100A7058 | 642   |
| Key One Side<br>(not handed)   |   | Stainless Steel | CL100A7056 | 642   |
| Turn/Emergency<br>(not handed) |   | Stainless Steel | CL100A7014 | 642   |
| Lever Only                     |  | Stainless Steel | CL100B5002 | 546   |



## CL100 ADA Lever

| Function                      |                                                                                     | Finish          | Code       | Price |
|-------------------------------|-------------------------------------------------------------------------------------|-----------------|------------|-------|
| Turn / Key (not handed)       |  | Stainless Steel | CL100A7018 | 735   |
| Turn / Emergency (not handed) |  | Stainless Steel | CL100A7020 | 735   |



Pricing covers popular SKUs. For other finishes, door thicknesses or configurations, inquire for pricing and availability.

Refer to handing/selection procedure on page 121.

# CL100 ADA LaviLock

| Function   |                                                                                   | Finish          | Code       | Price |
|------------|-----------------------------------------------------------------------------------|-----------------|------------|-------|
| Left Hand  |  | Stainless Steel | CL100B3010 | 659   |
| Right Hand |  | Stainless Steel | CL100B3008 | 659   |

# CL100 ADA Indicator Lock


| Function   |                                                                                   | Finish          | Code       | Price |
|------------|-----------------------------------------------------------------------------------|-----------------|------------|-------|
| Left Hand  |  | Stainless Steel | CL100B3016 | 691   |
| Right Hand |  | Stainless Steel | CL100B3015 | 691   |

Pricing covers popular SKUs. For other finishes, door thicknesses or configurations, inquire for pricing and availability.  
Refer to handing/selection procedure on page 121.


## Halliday + Baillie 660 7" Flush Pull

| Function                          |                                                                                   | Finish        | Code       | Price |
|-----------------------------------|-----------------------------------------------------------------------------------|---------------|------------|-------|
| Halliday + Baillie 660 Flush Pull |  | Satin Nickel  | CL800A4320 | 170   |
|                                   |                                                                                   | Matte Black   | CL800A4321 | 170   |
|                                   |                                                                                   | ORB           | CL800A4322 | 190   |
|                                   |                                                                                   | Bright Chrome | CL800A4323 | 190   |
|                                   |                                                                                   | Satin Brass   | CL800A4324 | 190   |
|                                   |                                                                                   | Satin Chrome  | CL800A4325 | 170   |


## Halliday + Baillie 680 Pocket Door Edge Pull

| Function                                     |                                                                                   | Finish        | Code       | Price |
|----------------------------------------------|-----------------------------------------------------------------------------------|---------------|------------|-------|
| Halliday + Baillie 680 Pocket Door Edge Pull |  | Satin Nickel  | CL800A4330 | 230   |
|                                              |                                                                                   | Matte Black   | CL800A4331 | 230   |
|                                              |                                                                                   | ORB           | CL800A4332 | 260   |
|                                              |                                                                                   | Bright Chrome | CL800A4333 | 260   |
|                                              |                                                                                   | Satin Brass   | CL800A4334 | 260   |
|                                              |                                                                                   | Satin Chrome  | CL800A4335 | 230   |

## Halliday + Baillie 620 Flush Pull Passage Set

| Function                                                                                                                         |                                                                                     | Finish        | Code       | Price |
|----------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------|------------|-------|
| Halliday + Baillie 620 Flush Pull Passage Set<br><br>Includes:<br><br>2 x HB660 7" Flush Pull<br>1 x HB680 Pocket Door Edge Pull |  | Satin Nickel  | CL800A4340 | 555   |
|                                                                                                                                  |                                                                                     | Matte Black   | CL800A4341 | 555   |
|                                                                                                                                  |                                                                                     | ORB           | CL800A4342 | 615   |
|                                                                                                                                  |                                                                                     | Bright Chrome | CL800A4343 | 615   |
|                                                                                                                                  |                                                                                     | Satin Brass   | CL800A4344 | 615   |
|                                                                                                                                  |                                                                                     | Satin Chrome  | CL800A4345 | 555   |

# Displays and Jigs



# Cavity Sliders Sample Options



## CL400 ADA Magnetic + CL400 Magnetic + CL200 Counter Top Display

### CLDISPLAY101

#### Features:

- Mobile mechanical display
- CL400 ADA Privacy + CL400 Privacy + CL200 Privacy function

|                   |           |
|-------------------|-----------|
| <b>Dimensions</b> | 18" x 12" |
| <b>Net Price</b>  | \$300     |



## CL400 Magnetic + CL200 Counter Top Display

### CLDISPLAY102

#### Features:

- Mobile mechanical display
- CL400 Privacy + CL200 Privacy function

|                   |           |
|-------------------|-----------|
| <b>Dimensions</b> | 18" x 12" |
| <b>Net Price</b>  | \$200     |



## CS Cavity Slider™ Pocket Frame


### CSSKDISPLAY

#### Features:

- Full aluminum structure
- Finishing jambs on one side
- Supplied with M6/M8 carriage and mounting plate
- 2x4 Frame model version

|                   |           |
|-------------------|-----------|
| <b>Dimensions</b> | 2' x 2'6" |
| <b>Net Price</b>  | \$70      |

# Cavity Sliders Sample Options



## CL100 ADA Lever Counter Top Display

### CLDISPLAY03

Features:

- Mobile mechanical display
- ADA Turn / Key

|                   |          |
|-------------------|----------|
| <b>Dimensions</b> | 5" x 14" |
| <b>Net Price</b>  | \$100    |



## Presentation Kit

### ZG00384

Kit Contents:

- Specification Guide
- Mini Pocket Frame

Standard Components:

- M6 Carriage (200 lb per pair)
- M8 Carriage (500 lb per pair)
- Mount Plate
- Mount Plate with Stop
- Track Stop
- Wrench

Track Samples:

- TopMountTrack - Double 1-3/8"
- FH-CeilingMountTrack
- TopMountTrack - Single
- SideMountTrack with Fascia

|                   |                    |
|-------------------|--------------------|
| <b>Dimensions</b> | 16.5" x 14.5" x 6" |
| <b>Net Price</b>  | \$120              |



## 4x4 CS Cavity Slider™ Showroom Display


### CSSKDISPLAY01

Features:

- Mechanical Cavity Slider Display
- Standard pocket frame, 2x4 stud size
- 25" x 42" x 1-3/4" display door with CL400 Magnetic Privacy Lock, Satin Nickel finish
- Dual action soft close function

|                   |              |
|-------------------|--------------|
| <b>Dimensions</b> | 4' x 4' x 2' |
| <b>Net Price</b>  | \$700        |

# CL400<sup>®</sup> Magnetic Cutout Jigs



## CL400 Magnetic Handle Cutout Jig

### CL400T0000

This jig is made from quality materials that will last a lifetime. It allows for accurate and consistent cutting of the handle recess for the CL400 Magnetic.

#### Contents:

- Handle Cutout Jig
- 1/2" Guide Bush
- Wavy Washer
- Universal Nut
- 1/2" Solid Carbide Spiral Cutter
- 1/2" Alignment Pin
- Instructions

#### List Price

\$460



## CL400 Magnetic Striker Cutout Jig

### CL400T0003

This jig is made from quality materials that will last a lifetime. It allows for quick, accurate mounting of the CL400 Striker in any wooden closing jamb.

#### Contents:

- Main Striker Jig
- Striker Jig Insert
- Screws
- 1/4" Alignment Pin
- 1/4" Solid Carbide Spiral Cutter
- 1/4" Guide Bush
- Universal Nut
- Wavy Washer
- Instructions

#### List Price

\$335

# Carbide Spiral Cutters



## 1/2" Solid Carbide Spiral Cutter for Handle Cutout Jig

CL400TA015

Up-cut two flute Solide Carbide spiral cutter, 1/2" shank x 1/2" cut diameter x 2" cut length to be used with Handle Cutout Jig. This solid carbide spiral cutter has been chosen to do the best job possible and is recommended.

|                   |          |
|-------------------|----------|
| <b>List Price</b> | \$125/ea |
|-------------------|----------|



## 1/4" Solid Carbide Spiral Cutter for Striker Cutout Jig

CL400TA029

Up-cut two flute Solide Carbide spiral cutter, 1/4" shank x 1/4" cut diameter x 1-1/4" cut length to be used with Striker Cutout Jig. This solid carbide spiral cutter has been chosen to do the best job possible and is recommended.

|                   |         |
|-------------------|---------|
| <b>List Price</b> | \$75/ea |
|-------------------|---------|

# Door Groove Cutter



ZM00010


The router cutter that we use on our own doors is now available for your use. This cutter is custom made to cut a groove slot that suits the CS range of T-Guides.

Features:

- Custom made to suit the CS range of T-Guides
- Cut accurate grooves - quickly and easily

**Note:** Groove cut dimensions should be checked regularly to make sure cut is to spec. If not, cutters will need to be retipped.

|                   |       |
|-------------------|-------|
| <b>List Price</b> | \$135 |
|-------------------|-------|




# Frequently Asked Questions

## What is a “Track Stop”?

A Track Stop is needed when no physical stops are present, i.e., your door does not come to rest at a closing jamb or wall stud.

Example:

A pair of bi-parting doors or a barn door track.



## How do I choose the right carriage pack for my project?

Each project is unique. Here are a few examples to help determine the type of carriage pack needed for your project.

| Project                                                                                                                                             | Carriage Pack Selection                                                   |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------|
| Single pocket door being installed with the CS Cavity Slider Pocket Frame<br>Door Weight: 150 lb<br>Door Width: 30"<br>SofStop (Soft Close)         | Track Stops Needed: 0<br>1x SofStop Carriage Pack,<br>No Stops            |
| A bi-parting pair of pocket frames installed with the CS Cavity Slider Pocket Frame<br>Door Weight: 300 lb<br>Door Width: 36"<br>Standard Carriages | Track Stops Needed: 2 (One for each frame)<br>2x M8 Carriage Pack, 1 Stop |
| A barn door mounted to the wall using the CS CaviTrack SideMount<br>Door Weight: 160 lb<br>Door Width: 40"<br>Twin SofStop (Soft Close/Soft Open)   | Track Stops Needed: 2<br>1x Twin SofStop Carriage Pack,<br>2 Stops        |

## What is a “CS SofStop”?

A CS SofStop mechanism is designed to slow down the door. It must be paired with a physical stop to ensure the mechanism does not break.

To use the CS SofStop in your project, your door must meet minimum door width requirements. Please review the table to confirm that your door is compatible.

### SofStop Minimum Door Widths

| CS SofStop          | No Stop      | 1 Stop       | 2 Stops      |
|---------------------|--------------|--------------|--------------|
| 0 - 200 lb (90 kg)  | 23" (584 mm) | 26" (660 mm) | 28" (711 mm) |
| CS SofStop HD       | No Stop      | 1 Stop       | 2 Stops      |
| 0 - 350 lb (160 kg) | 26" (660 mm) | 29" (737 mm) | 31" (787 mm) |


## How do I choose the handing of my pocket door hardware?

Each project is unique. Here are a few examples to help determine the type of carriage pack needed for your project.

- 1. Stand with your back against the door's closing jamb
- 2. Look directly into the door's pocket
- 3. Determine which side you'd like your snib (Privacy Function) or key on.

Example:

The homeowner would like to add a lock to this bathroom. Upon positioning themselves and looking into the pocket, the homeowner's RIGHT hand is inside the bathroom. Therefore, the door's handing would be: **Right Hand (RH) Snib/Left Hand (LH) Emergency**



### CL400 Magnetic Selection Procedure

To order, ensure you have the following information ready:

| Function                                        | Finish                                     | Door Thickness                                             |
|-------------------------------------------------|--------------------------------------------|------------------------------------------------------------|
| <input type="checkbox"/> Single Door            | <input type="checkbox"/> Bright Chrome     | <input type="checkbox"/> 1-3/8" to 1-9/16"<br>(34 - 40 mm) |
| <input type="checkbox"/> Bi-Parting Door        | <input type="checkbox"/> Satin Chrome      | <input type="checkbox"/> 1-5/8" to 1-3/4"<br>(40 - 46 mm)  |
| <input type="checkbox"/> Passage (Non Latching) | <input type="checkbox"/> Oil Rubbed Bronze | <input type="checkbox"/> 1-13/16" to 2"<br>(46 - 52 mm)    |
| <input type="checkbox"/> Passage (Mag Latching) | <input type="checkbox"/> Satin Nickel      | <input type="checkbox"/> 2" to 2-1/4"<br>(52 - 57 mm)      |
| <input type="checkbox"/> Privacy Locking        | <input type="checkbox"/> Matte Black       |                                                            |
| <input type="checkbox"/> Key Locking            |                                            |                                                            |

| Function  | LH                       | RH                       |
|-----------|--------------------------|--------------------------|
| Blank     | <input type="checkbox"/> | <input type="checkbox"/> |
| Snib      | <input type="checkbox"/> | <input type="checkbox"/> |
| Key       | <input type="checkbox"/> | <input type="checkbox"/> |
| Emergency | <input type="checkbox"/> | <input type="checkbox"/> |

## How to choose my CL200 Range handle?

- 1. Select the functionality and snib type.
- 2. Select the finish.
- 3. Select the door thickness.

Example:

If you require a CL200 Privacy Snib/Emergency in Oil Rubbed Bronze for a door thickness of 1-3/8", the code will be CL205D0006 (refer to product codes on page 111)

### Bi-Parting (Double Doors):

Passage with striker + Privacy



CL205D0009 + CL205C0003

For Bi-Parting Passage handles, order 2x single passage handles.

# Warranty Conditions



## Cavity Sliders USA Incorporated

### Valued Customer,

On behalf of the whole CS team, we would like to thank you for purchasing our products. Since our establishment in 1986, we have strived to reach levels of optimal performance in both manufacturing and customer service. Cavity Sliders USA Inc. is dedicated to providing products that meet the needs of our customers. We constantly monitor the marketplace and are innovators in our field. New products are under constant development, so that as your needs change, we are right there with you.

We trust you are enjoying the many benefits of our products. Should you have any inquiries or comments, please feel confident in calling one of our friendly customer services staff.

Regards,

Laurie McCowan  
President, Cavity Sliders USA Inc.

The warranties herein form part of the TERMS OF TRADE FOR GOODS AND SERVICES and the general conditions of Warranty are also contained in that contract.

The Company's maximum liability hereunder is limited to the purchase price of the Goods. In no event shall the Company be liable for any consequential, indirect, incidental or special and/or punitive damages of any nature arising from the sale or use of the Goods, whether based on contract, warranty, tort, strict liability, patent infringement, or otherwise, even if advised of the possibility of such damages.

### Note:

- This warranty only applies to the original user of the Goods. This warranty is not transferable.
- This warranty is limited to the repair or replacement of faulty parts only. The costs of removal and reinstallation of Goods and/or shipping and freight are excluded.
- This warranty excludes normal wear and tear or Goods used in extremely high use situations where the manufacturer has not been consulted regarding the suitability of the Goods.
- The warranty on Goods supplied by the Company but not manufactured by the Company shall be the warranty of the original manufacturer.
- Finish Warranty - finishes susceptible to early deterioration or oxidation (often referred to as living finishes, e.g. Oil Rubbed Bronze) are excluded from this warranty.

### 1. Goods supplied but not manufactured by the Company

The warranty on Goods supplied by the Company but not manufactured by the Company shall be the warranty of the original manufacturer.

### 2. Goods manufactured by the Company:

**TEN (10) YEARS WARRANTY\*** on the following categories of Goods supplied by the Company:

- CaviSlider - Pocket frames manufactured by Cavity Sliders
- CaviTrack

**FIVE (5) YEARS WARRANTY\*** on the following categories of Goods supplied by the Company:

- CL100 MorticeLock
- CL200 Range
- CL400<sup>#</sup> Magnetic

**TWO (2) YEARS WARRANTY\*** on the following categories of Goods supplied by the Company:

- Automatic Units<sup>#</sup>

\* Excludes normal wear and tear including but not limited to replaceable parts and powder coated / pre-finished surfaces.

# Electronic components carry a 12 month warranty.

# Warranty Conditions



## Cavity Sliders USA Incorporated

### Instructions of Care

In order to maintain the warranty, the Customer is recommended to follow Instructions of Care and to inform any third party purchaser of the same information.

| Instructions of Care                                                | Common misuse is:                                                                                                            |
|---------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Only use the correct Operating Manuals                              | Attempting to use or repair the Goods without proper knowledge                                                               |
| Operate within the rated capacity                                   | Not checking the manufacturer's recommended ratings                                                                          |
| Do not place heavy loads on the Goods                               | Incorrect packing and shipment of the Goods causing damage to the exterior                                                   |
| Do not expose to impact, excessive movement or continual relocation | Not realising that the Goods contain sensitive parts or may damage easily                                                    |
| Do not expose to excessive vibration or heat                        | Not realising that the parts are sensitive to excessive vibration and heat                                                   |
| Do not expose the Goods to water or excessive moisture              | Not realising that timber may be a component and that excessive moisture damages sensitive parts and may discolor the finish |

### Making a claim for damaged or defective Goods or defective Services

The Company will provide a form for any claims for damaged or defective Goods or Services but will not accept any claim by the Customer for any reasons where the Customer may be prejudiced by the defect or failure of the Goods or Services. This warranty is limited to the repair or replacement of faulty parts only. The Company will not accept any claim by the Customer for any and all costs incurred including economic loss, consequential loss or any other form of loss whatsoever. This warranty will not apply where:

- Goods or Services have not been paid in full and according to the terms of payment.
- The defect or failure is due to or resulting from damage, poor installation, misuse or use contrary to the printed instructions of the Company for maintenance or care when in the possession of the Customer.
- The defect or failure is due to persons not technically competent to use the Goods.
- The defect or failure is due to the Goods not being used for the purpose for which they were specified.
- The defect or failure is caused by the Customer or a third party on behalf of the Customer attempting integration or interfacing of the Goods with other Goods.
- The Customer or any third party altering the Goods in any way different to the condition in which they were supplied or installed.
- The defect or failure is due to environmental conditions of the Customer's site causing deterioration.
- The defect is due to the Customer or its agent attempting modification or repair of the Goods.
- The failure is caused by use in situations where the Manufacturer's specified capacity is exceeded.

### How to claim

For all inquiries, please contact the Customer Services Department of your nearest Cavity Sliders USA Inc. branch (details below) and request a claim form. The serial number (starting with SA-----) can be found on your invoice. All repairs, possible charges or replacements are at the sole discretion of Cavity Sliders USA Inc.

We welcome your feedback about product improvements or service. Please email [sales@cavitysliders.com](mailto:sales@cavitysliders.com)

# Copyright Conditions

|                                                    |             |                                  |
|----------------------------------------------------|-------------|----------------------------------|
| <b>CS Cavity Slider®</b>                           |             | 61213 - 04.2023                  |
| <b>CS CaviTrack™</b>                               | (O.D. 2019) | Patent pending, 61350 - 02.2021  |
| <b>CS FH-CeilingMountTrack™</b>                    | (O.D. 2008) | Patent pending, 60883 - 04.2022  |
| <b>CS WallMountTrack™</b>                          | (O.D. 2008) | Patent pending, 60882 - 07.2019  |
| <b>CS CaviTrack™</b>                               | (O.D. 2020) | Patent pending, 61387 - 04.2020  |
| <b>CS BarnDoorTrack™</b>                           | (O.D. 2008) | Patent pending, 61207 - 07.2019  |
| <b>CS TopMountTrack™</b>                           | (O.D. 2008) | Patent pending, 61208 - 02.2021  |
| <b>CS Floor Channel &amp; Bearing Guide System</b> | (O.D. 1986) | Patent pending, 61303 - 03.2019  |
| <b>CS HeavyDutyTrack™</b>                          | (O.D. 2013) | Patent pending, 611532 - 07.2019 |
| <b>CS Frameless Glass™</b>                         | (O.D. 1998) | Patent pending, 61173 - 12.2019  |
| <b>CaviLock® CL400 Magnetic</b>                    | (O.D. 2013) | US Patent No. 10036185 - 05.2022 |
| <b>CaviLock® BarnDoorStrike</b>                    | (O.D. 2018) | 61316 - 12.2018                  |
| <b>CaviLock® CL200</b>                             | (O.D. 2017) | Patent pending, 61278 - 03.2019  |
| <b>CaviLock® CL100 Lever™</b>                      | (O.D. 1995) | 60287 - 03.2017                  |
| <b>CaviLock® CL100 FlushTurn™</b>                  | (O.D. 1995) | 60884 - 09.2022                  |
| <b>CaviLock® Timber EdgePull™</b>                  | (O.D. 2005) | 60141/2 - 03.2017                |
| <b>CaviLock® CL400 Magnetic</b>                    | (O.D. 2017) | 61225 - 05.2022                  |
| <b>CaviLock® CL100 LaviLock™</b>                   | (O.D. 1995) | 60242 - 11.2017                  |
| <b>CaviLock® CL100 IndicatorLock™</b>              | (O.D. 1995) | 61248 - 11.2017                  |
| <b>CaviLock® CL100 ADA Lever</b>                   | (O.D. 2014) | 61008 - 11.2017                  |
| <b>CS AutoCav™ Commercial</b>                      | (O.D. 1986) | 61083 - 01.2021                  |
| <b>CS AutoCav™ Residential</b>                     | (O.D. 1986) | 61367 - 01.2022                  |

© All copyright and other property in this document is reserved by Cavity Sliders USA Inc. Details and specifications are subject to change without notice.

Whilst all care is taken to ensure the accuracy of all information, no responsibility will be accepted for any errors or omissions.

Drawings and pictures are not to scale. All dimensions in inches and millimeters. Colors shown may not accurately represent product.

Timber lock blocks shown do not depict actual doors.

CaviLock® is a Registered Trademark.

© 2026

[illegible]

Product Pricing







## Contact us

---

-  2662 E Del Amo Blvd  
Carson, CA 90221
-  (888) 466 0030
-  (310) 769 5824
-  [sales@cavitysliders.com](mailto:sales@cavitysliders.com)

## Connect with us

---

-  [/CavitySlidersUSA](#)
-  [@cavitysliders](#)
-  [/cavitysliders](#)
-  [/company/cavitysliders](#)

**CavitySliders.com**