

MADE IN ITALY. MADE TO EXCEL.

MARVEL

— MERAVIGLIA

Interactive version



 **atlas concorde**

September 2023

Diamond decor designed by
Zaha Hadid Architects

MARBLE LOOK

PORCELAIN TILES
GRES PORCELLANATO
Grès cérame
Feinsteinzeug
Gres porcelánico
Керамический гранит



Atlas Concorde is one of the leading global brands in the production of ceramic tiles and large slabs for design and architecture. With over 50 years of history, two production plants, and numerous showroom in the capitals of international design, Atlas Concorde offers integrated and sustainable ceramic systems for floors, walls, outdoor spaces, worktops, bathroom furnishings, facades and special projects. Design your world with Atlas Concorde.

Atlas Concorde è uno dei principali brand mondiali nella produzione di superfici e grandi lastre ceramiche per il design e l'architettura. Con oltre cinquant'anni di storia, due stabilimenti produttivi, numerose showroom nelle capitali della progettazione internazionale, offriamo sistemi ceramici integrati e sostenibili per pavimenti, rivestimenti, outdoor, piani di lavoro, arredo bagno, facciate e progetti speciali. Design your world with Atlas Concorde.

atlasconcorde.com

MARVEL
MERAVIGLIA



Index

- ⇄ Inspiration
- ⇄ Diamond decor designed by Zaha Hadid Architects
- ⇄ Image gallery
- ⇄ Surface range & Technical specifications

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO



Infinite present.



INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY




SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





Calacatta Meraviglia



Calacatta Bernini



Silver Majestic



Grigio Elegante



Black Origin

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY




SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





Polished



Hammered

Sensitech

✂ 9 mm **Matte**

✂ 20 mm **Outdoor**

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





Diamond decor designed by
Zaha Hadid Architects

© Copyright Zaha Hadid Limited 2023 manufactured by Ceramiche Atlas Concorde under license from Zaha Hadid Limited.

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO



Zaha Hadid Architects



DIAMOND DECOR CONCEPT

“ZHA contaminates a classic mosaic with a disrupting element. A foreign body into a crystalline structure which gives an unsuspected dynamism”.

Paolo Zilli
ASSOCIATE DIRECTOR
Zaha Hadid Architects

ZHA is a British architectural firm founded in 1980 by Zaha Hadid, a naturalized British-born Iraqi architect and designer, the leading and foremost exponent of deconstructivism. | ZHA è lo studio di architettura britannico fondato nel 1980 da Zaha Hadid, architetta e designer irachena naturalizzata britannica, capofila e massima esponente del decostruttivismo.



© Copyright Zaha Hadid Limited 2023 manufactured by Ceramiche Atlas Concorde under license from Zaha Hadid Limited.

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





© Copyright Zaha Hadid Limited 2023 manufactured by Ceramiche Atlas Concorde under license from Zaha Hadid Limited



© Copyright Zaha Hadid Limited 2023 manufactured by Ceramiche Atlas Concorde under license from Zaha Hadid Limited

Optimism for the future, the continuous pursuit of excellence, and a strong international presence are the common values that gave rise to the partnership between Zaha Hadid Architects and Atlas Concorde. | Ottimismo per il futuro, continua ricerca di eccellenza e forte presenza internazionale sono i valori comuni che hanno dato vita alla collaborazione tra Zaha Hadid Architects e Atlas Concorde.

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO



Image Gallery

↔ Living Room & Dining
Calacatta Meraviglia | Silver Majestic



↔ Private Bathroom
Calacatta Meraviglia



↔ Penthouse
Grigio Elegante | Calacatta Bernini



↔ Hotel Bathroom
Grigio Elegante | Black Origin



↔ Villa
Calacatta Bernini



↔ Boutique
Calacatta Meraviglia | Black Origin



↔ Hotel Lobby & Bar
Silver Majestic | Black Origin



↔ Corporate Building
Calacatta Meraviglia | Silver Majestic



↔ Museum Hall
Calacatta Bernini



INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Calacatta Meraviglia
Polished
120x240 cm | 47¹/₄"x94¹/₂"

WALL
Marvel Meraviglia Calacatta Meraviglia
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia Silver Majestic
Polished
120x278 cm | 47¹/₄"x109¹/₂"

SIDE TABLE | Contatto
Atlas Concorde Habitat
Calacatta Meraviglia
Silk
ø 70 cm | 27¹/₂"

COUNTERTOP
Atlas Plan
Calacatta Meraviglia
Polished
162x324 cm | 63³/₄"x127¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





Calacatta Meraviglia

Polished

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING

PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO



INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO



^
SIDE TABLE | **Contatto**
Atlas Concorde Habitat
Calacatta Meraviglia
Silk
ø 70 cm | 27 1/2"

>
SIDE TABLE | **Contatto**
Atlas Concorde Habitat
Nero Marquina
Polished
ø 70 cm | 27 1/2"

FLOOR
Marvel Meraviglia
Calacatta Meraviglia
Polished
120x240 cm | 47 1/4"x94 1/2"

WALL
Marvel Meraviglia
Calacatta Meraviglia
Polished
120x278 cm | 47 1/4"x109 1/2"





FLOOR
Marvel Meraviglia Calacatta Meraviglia
Polished
120x240 cm | 47¹/₄"x94¹/₂"

FLOOR - OUTDOOR
Marvel Meraviglia Calacatta Meraviglia Hammered
Outdoor Sensitech ✕ 20mm
60x120 cm | 23⁵/₈"x47¹/₄"

WALL
Marvel Meraviglia Silver Majestic
Polished
120x278 cm | 47¹/₄"x109¹/₂"

COUNTERTOP
Atlas Plan
Calacatta Meraviglia
Polished
162x324 cm | 63³/₄"x127¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia
Calacatta Meraviglia Hammered
Outdoor Sensitech ∇ 20mm
60x120 cm | 23 $\frac{3}{8}$ "x47 $\frac{1}{4}$ "

COFFEE TABLE | **Brooklyn 25**
Atlas Concorde Habitat
Fior di Bosco
Silk
90x60 cm | 35 $\frac{3}{8}$ "x23 $\frac{5}{8}$ "

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING

PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Calacatta Meraviglia
Velvet
120x120 cm | 47¹/₄"x47¹/₄"

WALL
Marvel Meraviglia Calacatta Meraviglia
Velvet
60x120 cm | 23⁵/₈"x47¹/₄"

Marvel Meraviglia Calacatta Meraviglia
Diamond Polished
46,6x284,6 cm | 18³/₈"x112"

Marvel Meraviglia Calacatta Meraviglia
Hexagon Polished
40,3x46,6 cm | 15⁷/₈"x18³/₈"

SIDE TABLE | Contatto
Atlas Concorde Habitat
Black Lava
Leathered
ø 45 cm | 17³/₄"

SINKS
Freestanding
Atlas Concorde Habitat
Calacatta Meraviglia
Velvet
65x50x85 cm | 25⁵/₈"x19⁵/₈"x33¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM

PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO



FLOOR
Marvel Meraviglia Calacatta Meraviglia
Velvet
120x120 cm | 47¹/₄"x47¹/₄"

WALL
Marvel Meraviglia Calacatta Meraviglia
Velvet
60x120 cm | 23⁵/₈"x47¹/₄"

Marvel Meraviglia Calacatta Meraviglia
Diamond Polished
46,6x284,6 cm | 18³/₈"x112"

Marvel Meraviglia Calacatta Meraviglia
Hexagon Polished
40,3x46,6 cm | 15⁷/₈"x18³/₈"

SIDE TABLE | **Contatto**
Atlas Concorde Habitat
Black Lava
Leathered
ø 45 cm | 17³/₄"

SINKS
Freestanding
Atlas Concorde Habitat
Calacatta Meraviglia
Velvet
65x50x85 cm | 25⁵/₈"x19²/₈"x33¹/₂"



<

FLOOR
Marvel Meraviglia
Calacatta Meraviglia
Velvet
120x120 cm | 47¹/₄"x47¹/₄"

WALL
Marvel Meraviglia
Calacatta Meraviglia
Velvet
60x120 cm | 23⁵/₈"x47¹/₄"

Marvel Meraviglia
Calacatta Meraviglia
Diamond Polished
46,6x284,6 cm | 18³/₈"x112"

^

WALL
Marvel Meraviglia
Calacatta Meraviglia
Velvet
60x120 cm | 23⁵/₈"x47¹/₄"

Marvel Meraviglia
Calacatta Meraviglia
Hexagon Polished
40,3x46,6 cm | 15⁷/₈"x18³/₈"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





WALL
Marvel Meraviglia Calacatta Meraviglia
Diamond Polished
46,6x284,6 cm | 18⁷/₈"x112"

Diamond decor designed by
Zaha Hadid Architects

© Copyright Zaha Hadid Limited 2023 manufactured by Ceramiche Atlas Concorde under license from Zaha Hadid Limited

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Grigio Elegante
Velvet
120x120 cm | 47 1/4" x 47 1/4"

WALL
Marvel Meraviglia Calacatta Bernini
Polished
120x278 cm | 47 1/4" x 109 1/2"

Marvel Meraviglia Grigio Elegante
Polished
120x278 cm | 47 1/4" x 109 1/2"

Boost Balance White
Matte
120x278 cm | 47 1/4" x 109 1/2"

SIDE TABLE | Contatto
Atlas Concorde Habitat
Nero Marquina
Polished
ø 70 cm | 27 1/2"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE

HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Grigio Elegante
Velvet
120x120 cm | 47¹/₄"x47¹/₄"

WALL
Marvel Meraviglia Calacatta Bernini
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Boost Balance White
Matte
120x278 cm | 47¹/₄"x109¹/₂"

SIDE TABLE | **Contatto**
Atlas Concorde Habitat
Nero Marquina
Polished
ø 70 cm | 27¹/₂"

COUNTERTOP
Atlas Plan
Calacatta Bernini
Polished
162x324 cm | 63³/₄"x127¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE

HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia
Grigio Elegante
Velvet
120x120 cm | 47¹/₄"x47¹/₄"

WALL
Marvel Meraviglia
Grigio Elegante
Polished
120x278 cm | 47¹/₄"x109¹/₂"



FLOOR
Marvel Meraviglia
Grigio Elegante
Velvet
120x120 cm | 47¹/₄"x47¹/₄"

SIDE TABLE | **Contatto**
Atlas Concorde Habitat
Nero Marquina
Polished
ø 70 cm | 27¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE

HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR	WALL	COUNTERTOP	DINING TABLE Brooklyn 75
Marvel Meraviglia	Marvel Meraviglia	Atlas Plan	Atlas Concorde Habitat
Grigio Elegante	Calacatta Bernini	Calacatta Bernini	Nero Marquina
Velvet	Polished	Polished	Polished
120x120 cm 47 1/4"x47 1/4"	120x278 cm 47 1/4"x109 1/2"	162x324 cm 63 3/4"x127 1/2"	100x240 cm 39 3/8"x94 1/2"



INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Grigio Elegante
Polished
120x120 cm | 47¹/₄"x47¹/₄"

Marvel Meraviglia Grigio Elegante
Matte Sensitech
60x120 cm | 23⁵/₈"x47¹/₄"

WALL
Marvel Meraviglia Grigio Elegante
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia Black Origin
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia Grigio Elegante
Grid Velvet
59,5x118,2 cm | 23³/₈"x46¹/₂"

SIDE TABLE | Contatto
Atlas Concorde Habitat
Calacatta Meraviglia
Silk
ø 45 cm | 17³/₄"

SINKS
Freestanding
Atlas Concorde Habitat
Grigio Elegante
Polished
65x50x85 cm | 25⁵/₈"x19⁵/₈"x33¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia
Grigio Elegante
Polished
120x120 cm | 47⁷/₈"x47⁷/₈"

Marvel Meraviglia
Grigio Elegante
Matte Sensitech
60x120 cm | 23³/₈"x47⁷/₈"

WALL
Marvel Meraviglia
Grigio Elegante
Polished
120x278 cm | 47⁷/₈"x109¹/₂"

Marvel Meraviglia
Black Origin
Polished
120x278 cm | 47⁷/₈"x109¹/₂"

Marvel Meraviglia
Grigio Elegante
Grid Velvet
59,5x118,2 cm | 23³/₈"x46¹/₂"

SIDE TABLE | **Contatto**
Atlas Concorde Habitat
Calacatta Meraviglia
Silk
ø 45 cm | 17³/₄"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Grigio Elegante
Polished
120x120 cm | 47¹/₄"x47¹/₄"

WALL
Marvel Meraviglia Grigio Elegante
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia Black Origin
Polished
120x278 cm | 47¹/₄"x109¹/₂"

SINKS
Freestanding
Atlas Concorde Habitat
Grigio Elegante
Polished
65x50x85 cm | 25⁵/₈"x19⁵/₈"x33¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Calacatta Bernini Hammered
Outdoor Sensitech $\times$ 20mm
60x120 cm | 23 $\frac{3}{4}$ "x47 $\frac{1}{4}$ "

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





Calacatta Bernini

Hammered

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Calacatta Bernini
Polished
120x240 cm | 47¹/₄"x94¹/₂"

FLOOR - OUTDOOR
Marvel Meraviglia Calacatta Bernini Hammered
Outdoor Sensitech $\nless 20$ mm
60x120 cm | 23³/₈"x47¹/₄"

WALL
Marvel Meraviglia Black Origin
Polished
120x278 cm | 47¹/₄"x109¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Calacatta Bernini
Polished
120x240 cm | 47¹/₄"x94¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Calacatta Bernini Hammered
Outdoor Sensitech ∇ 20mm
60x120 cm | 23 $\frac{5}{8}$ "x47 $\frac{1}{4}$ "

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR

Marvel Meraviglia
Calacatta Bernini Hammered
Outdoor Sensitech ∇ 20mm
60x120 cm | 23 $\frac{3}{8}$ "x47 $\frac{1}{4}$ "

Marvel Meraviglia
Calacatta Bernini Hammered
Round Sensitech ∇ 20mm
33x120 cm | 13"x47 $\frac{1}{4}$ "

Marvel Meraviglia
Calacatta Bernini Hammered
Elemento L Sensitech ∇ 20mm
33x120 cm | 13"x47 $\frac{1}{4}$ "

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Calacatta Meraviglia
Polished
120x240 cm | 47¹/₄"x94¹/₂"

Marvel Meraviglia Black Origin
Polished
120x240 cm | 47¹/₄"x94¹/₂"

WALL
Marvel Meraviglia Calacatta Meraviglia
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia Black Origin
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia Black Origin
Diamond Polished
46.6x284.6 cm | 18³/₈"x112"

DESK
Atlas Plan
Calacatta Meraviglia
Polished
162x324 cm | 63³/₄"x127¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





^		
FLOOR	WALL	
Marvel Meraviglia	Marvel Meraviglia	Marvel Meraviglia
Calacatta Meraviglia	Calacatta Meraviglia	Black Origin
Polished	Polished	Polished
120x240 cm 47 1/4"x94 1/2"	120x278 cm 47 1/4"x109 1/2"	120x278 cm 47 1/4"x109 1/2"
<		
FLOOR	WALL	FURNITURE
Marvel Meraviglia	Marvel Meraviglia	Calacatta Meraviglia
Calacatta Meraviglia	Black Origin	
Polished	Diamond Polished	Polished
120x240 cm 47 1/4"x94 1/2"	46,6x284,6 cm 18 3/8"x112"	120x278 cm 47 1/4"x109 1/2"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO



FLOOR
Marvel Meraviglia
Calacatta Meraviglia
Polished
120x240 cm | 47¹/₄"x94¹/₂"

WALL
Marvel Meraviglia
Black Origin
Polished
120x278 cm | 47¹/₄"x109¹/₂"



FLOOR
Marvel Meraviglia
Black Origin
Polished
120x240 cm | 47¹/₄"x94¹/₂"



FLOOR
Marvel Meraviglia Silver Majestic
Polished
120x240 cm | 47¹/₄"x94¹/₂"

WALL
Marvel Meraviglia Silver Majestic
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia Black Origin
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia Silver Majestic
Diamond Polished
46,6x284,6 cm | 18³/₈"x112"

DESK
Black Origin
Polished
120x278 cm | 47¹/₄"x109¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia
Silver Majestic
Polished
120x240 cm | 47¹/₄"x94¹/₂"

WALL
Marvel Meraviglia
Silver Majestic
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia
Black Origin
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia
Silver Majestic
Diamond Polished
46,6x284,6 cm | 18³/₈"x112"

DESK
Black Origin
Polished
120x278 cm | 47¹/₄"x109¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





^
FLOOR
Marvel Meraviglia
Silver Majestic
Polished
120x240 cm | 47¹/₄"x94¹/₂"

>
FLOOR
Marvel Meraviglia
Silver Majestic
Diamond Polished
46,6x284,6 cm | 18³/₈"x112"



INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia
Silver Majestic
Polished
120x240 cm | 47 1/4"x94 1/2"

WALL
Marvel Meraviglia
Silver Majestic
Polished
120x278 cm | 47 1/4"x109 1/2"

BAR COUNTER
Black Origin
Polished
120x278 cm | 47 1/4"x109 1/2"



INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Calacatta Meraviglia
Polished
120x240 cm | 47 1/4" x 94 1/2"

WALL
Marvel Meraviglia Calacatta Meraviglia
Polished
120x278 cm | 47 1/4" x 109 1/2"

Marvel Meraviglia Silver Majestic
Polished
120x278 cm | 47 1/4" x 109 1/2"

DESK
Calacatta Meraviglia
Polished
120x278 cm | 47 1/4" x 109 1/2"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Calacatta Meraviglia
Polished
120x240 cm | 47¹/₄"x94¹/₂"

WALL
Marvel Meraviglia Calacatta Meraviglia
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Marvel Meraviglia Silver Majestic
Polished
120x278 cm | 47¹/₄"x109¹/₂"

DESK
Calacatta Meraviglia
Polished
120x278 cm | 47¹/₄"x109¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO



FLOOR

Marvel Meraviglia
Calacatta Meraviglia
Polished
120x240 cm | 47¹/₄"x94¹/₂"

Marvel Meraviglia
Silver Majestic
Polished
120x278 cm | 47¹/₄"x109¹/₂"

DESK

Calacatta Meraviglia
Polished
120x278 cm | 47¹/₄"x109¹/₂"



FLOOR
Marvel Meraviglia
Calacatta Meraviglia
Polished
120x240 cm | 47¹/₄"x94¹/₂"

WALL
Marvel Meraviglia
Silver Majestic
Polished
120x278 cm | 47¹/₄"x109¹/₂"

DINING TABLE | **Brooklyn 75**
Atlas Concorde Habitat
Boost Smoke
Hammered
180x100 cm | 70⁷/₈"x39³/₈"



INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia Calacatta Bernini
Polished
120x240 cm | 47¹/₄"x94¹/₂"

WALL
Marvel Meraviglia Calacatta Bernini
Polished
120x278 cm | 47¹/₄"x109¹/₂"

Boost Balance Ash
Matte
120x278 cm | 47¹/₄"x109¹/₂"

DESK
Calacatta Bernini
Polished
120x278 cm | 47¹/₄"x109¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





Calacatta Bernini

Polished

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





<

FLOOR
Marvel Meraviglia
Calacatta Bernini
Polished
120x240 cm | 47¹/₄"x94¹/₂"

WALL
Marvel Meraviglia
Calacatta Bernini
Polished
120x278 cm | 47¹/₄"x109¹/₂"

DESK
Calacatta Bernini
Polished
120x278 cm | 47¹/₄"x109¹/₂"

^

FLOOR
Marvel Meraviglia
Calacatta Bernini
Polished
120x240 cm | 47¹/₄"x94¹/₂"

WALL
Marvel Meraviglia
Calacatta Bernini
Grid Velvet
59,5x118,2 cm | 23³/₈"x46¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





FLOOR
Marvel Meraviglia
Calacatta Bernini
Polished
120x240 cm | 47 1/4"x94 1/2"

WALL
Marvel Meraviglia
Calacatta Bernini
Polished
120x278 cm | 47 1/4"x109 1/2"



INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



LIVING ROOM & DINING
PRIVATE BATHROOM
PENTHOUSE
HOTEL BATHROOM
VILLA
BOUTIQUE
HOTEL LOBBY & BAR
CORPORATE BUILDING
MUSEUM HALL

SURFACE
RANGE &
TECHNICAL
SPECS



ENJOY
THE VIDEO





Surface range & Technical specifications

- ◇ PORCELAIN TILES: A SAFE CHOICE
- ◇ MARVEL MERAVIGLIA RANGE
- ◇ SENSITECH TECHNOLOGY
- ◇ MARVEL WORLD
- ◇ TECHNICAL SPECIFICATIONS

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



SAFE CHOICE
COLLECTION RANGE
DIAMOND DECOR
DESIGNED BY
ZAHA HADID ARCHITECTS
SENSITECH TECHNOLOGY
MARVEL WORLD
TECHNICAL SPECIFICATIONS
& CERTIFICATIONS

ENJOY
THE VIDEO





Porcelain tiles: a safe choice.

VERSATILE
Versatile

HYGIENIC
Igienico

SAFE
Sicuro

FIREPROOF
Resistente al fuoco

LONG LASTING
Dura a lungo

**EASY TO CLEAN
AND DISINFECT**
Facile da pulire e sanificare

ECO-FRIENDLY
Rispetta l'ambiente

RESISTANT
Resistente

RECYCLABLE
Riciclabile

ZERO PVC
Zero PVC

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS




SAFE CHOICE
COLLECTION RANGE
DIAMOND DECOR
DESIGNED BY
ZAHA HADID ARCHITECTS
SENSETECH TECHNOLOGY
MARVEL WORLD
TECHNICAL SPECIFICATIONS
& CERTIFICATIONS

ENJOY
THE VIDEO



Porcelain tiles

PORCELAIN TILES- Gres Porcellanato - Grès cérame - Feinsteinzeug - Gres porcelánico - Керамический гранит
RECTIFIED MONOCALIBER - Rettificato monocalibro - Rectifié mono-calibre - Geschliffen einkalbrig - Rectificado monocalibre - Ретифицированный в одном калибре







Floor & Wall

Furniture

160x320* cm - 63 ³ / ₄ "x126"	± 6 mm	Polished ■ Matte ●	Polished ■			
120x278 cm - 47 ¹ / ₄ "x109 ¹ / ₂ "	± 6 mm	Polished ●	Polished ●	Polished ●	Polished ●	Polished ●
120x240 cm - 47 ¹ / ₄ "x94 ¹ / ₂ "	± 9 mm	Polished	Polished	Polished	Polished	Polished
120x120 cm - 47 ¹ / ₄ "x47 ¹ / ₄ "	± 9 mm	Polished Velvet	Polished Velvet	Polished Velvet	Polished Velvet	Polished
75x150 cm - 29 ¹ / ₂ "x59"	± 9 mm	Polished	Polished	Polished	Polished	Polished
75x75 cm - 29 ¹ / ₂ "x29 ¹ / ₂ "	± 9 mm	Polished	Polished	Polished	Polished	Polished
60x120 cm - 23 ⁵ / ₈ "x47 ¹ / ₄ "	± 6 mm	Polished	Polished			Polished
60x120 cm - 23 ⁵ / ₈ "x47 ¹ / ₄ "	± 9 mm	Polished Velvet Matte Sensitech Hammered Matte Sensitech	Polished Velvet Matte Sensitech Hammered Matte Sensitech	Polished Velvet Matte Sensitech	Polished Velvet Matte Sensitech Hammered Matte Sensitech	Polished Matte Sensitech
60x60 cm - 23 ⁵ / ₈ "x23 ⁵ / ₈ "	± 9 mm	Polished Matte Sensitech	Polished Matte Sensitech	Polished Matte Sensitech	Polished Matte Sensitech	Polished Matte Sensitech
30x60 cm - 11 ³ / ₄ "x23 ⁵ / ₈ "	± 9 mm	Polished Matte Sensitech	Polished Matte Sensitech	Polished Matte Sensitech	Polished Matte Sensitech	Polished Matte Sensitech



Outdoor

60x120 cm - 23 ⁵ / ₈ "x47 ¹ / ₄ "	± 20 mm	Hammered Outdoor Sensitech	Hammered Outdoor Sensitech		Hammered Outdoor Sensitech	
---	---------	---	---	--	---	--





Countertops

Furniture

162x324* cm - 63 ³ / ₄ "x127 ¹ / ₂ "	± 12 mm	Polished ■ Silk ■	Polished ■ Silk ■			
159x324* cm - 62 ⁵ / ₈ "x127 ¹ / ₂ "	± 20 mm		Polished Matte			

* Atlas Plan

■ Also available in bookmatch

● Also available kit endless

Sensitech

pag.125

Sensitech, the porcelain tile surface made using a production method patented in Italy that combines superior slip-resistance with an unprecedented tactile softness, guaranteeing ease of cleaning and maintenance.
Sensitech, la superficie in gres porcellanato realizzata con metodo produttivo brevettato in Italia, che associa elevate prestazioni di resistenza allo scivolamento ad un'inedita morbidezza tattile, garantendo facilità di pulizia e manutenzione.

Velvetech

Velvetech, the new porcelain tile surface developed by Atlas Concorde with patent pending in Italy.
Velvetech, la nuova superficie in gres porcellanato sviluppata da Atlas Concorde con brevetto depositato in Italia.

Note on Polished and Velvet surface finish / Nota sulla finitura Velvet e Lappata

The Polished and Velvet finishes are suitable for residential or low-traffic commercial floors, where no anti-slip performance is required. If the product is in direct contact with the outdoors, moisture and dirt absorption devices must be used to prevent scratching. The glossy Polished finish offers a surprisingly bright, mirrored surface with slight irregularities typical of natural marbles. The surface's shine and great ease of cleaning are the result of in-depth studies and technical research aimed at ensuring its durability over time. The Velvet surface replicates the effect of semi-Polished marble. It has a velvety touch and silky highlights. The natural character of the surface is highlighted by areas of different opacity perceptible in oblique or reflected light. Le finiture Lappata e Velvet sono indicate per pavimenti residenziali o commerciali poco sollecitati, laddove non siano richieste prestazioni antiscivolo. Se il prodotto è a diretto contatto con l'esterno, prevedere dei dispositivi di assorbimento dell'umidità e dello sporco per prevenire la formazione di graffi. La finitura Lappata lucida offre una superficie sorprendentemente brillante e specchiante, con lievi irregolarità tipiche dei marmi naturali. La lucentezza e l'elevata facilità di pulizia della superficie sono frutto di studi approfonditi e accurate ricerche tecniche volte a garantire la persistenza nel tempo. La superficie Velvet replica l'effetto di un marmo levigato. Si distingue per la mano vellutata e per i riflessi semi-opachi. La naturalezza della superficie è evidenziata da zone di diversa opacità percettibili in luce radente o riflessa.

Destination of use

 Velvet Velvetech 9 mm	 Polished ± 6/9 mm Matte ± 6 mm	 Matte Sensitech ± 9 mm Hammered Matte Sensitech ± 9 mm Hammered Outdoor Sensitech ± 20 mm	 R9 A Matte ± 6 mm R10 B Matte Sensitech ± 9 mm R10 B Hammered Matte Sensitech ± 9 mm R11 C Hammered Outdoor Sensitech ± 20 mm	Color-shading V3 Moderate Variation All colors
---	---	---	---	---

CALACATTA MERA VIGLIA

CALACATTA BERNINI

SILVER MAJESTIC

GRIGIO ELEGANTE

BLACK ORIGIN

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



SAFE CHOICE
COLLECTION RANGE
DIAMOND DECOR
DESIGNED BY
ZAHA HADID ARCHITECTS
SENSITECH TECHNOLOGY
MARVEL WORLD
TECHNICAL SPECIFICATIONS
& CERTIFICATIONS

ENJOY
THE VIDEO



Matte

Sensitech

The matte finish combines beauty and performance. Sensitech technology ensures slip resistance, ease of cleaning, and an original touch. | La finitura opaca coniuga estetica e performance. La tecnologia Sensitech offre resistenza allo scivolamento, facilità di pulizia e un'inedita gradevolezza al tatto.



Polished

Glossy, reflective finish that underscores the brightness of the background and the irregularities typical of Polished natural marble. | Finitura lucida e riflettente che esalta la luminosità del fondo e le irregolarità tipiche del marmo naturale lucidato.



Velvet

Velvetech

The Velvet surface replicates the effect of semi-Polished marble. It has a velvety touch and semi-opaque highlights. The natural character of the surface is highlighted by areas of different opacity perceptible in oblique or reflected light. | La superficie Velvet replica l'effetto di un marmo levigato. Si distingue per la mano vellutata e per i riflessi semi-opachi. La naturalezza della superficie è evidenziata da zone di diversa opacità percettibili in luce radente o riflessa.



Hammered

Sensitech

- ✂ 9 mm Matte
- ✂ 20 mm Outdoor

The Hammered surface reproduces the natural character of split marble as if just cut out of the quarry. | La superficie Hammered riproduce la naturalezza del marmo «a spacco» come appena uscito dalla cava.



INDEX	≡
INSPIRATION	>
DIAMOND DECOR DESIGNED BY ZAHA HADID ARCHITECTS	>
IMAGE GALLERY	>
SURFACE RANGE & TECHNICAL SPECS	>
SAFE CHOICE COLLECTION RANGE DIAMOND DECOR DESIGNED BY ZAHA HADID ARCHITECTS SENSITECH TECHNOLOGY MARVEL WORLD TECHNICAL SPECIFICATIONS & CERTIFICATIONS	
ENJOY THE VIDEO	▶

Porcelain tiles




Marvel Meraviglia Calacatta Meraviglia ⁽¹⁾ ⁽²⁾
120x278 cm - 47 1/4"x109 1/2" **Kit Endless** also available. *



Marvel Meraviglia Calacatta Bernini ⁽¹⁾ ⁽²⁾
120x278 cm - 47 1/4"x109 1/2" **Kit Endless** also available. *



Marvel Meraviglia Silver Majestic ⁽¹⁾ ⁽²⁾
120x278 cm - 47 1/4"x109 1/2" **Kit Endless** also available. *



Marvel Meraviglia Grigio Elegante ⁽¹⁾ ⁽²⁾
120x278 cm - 47 1/4"x109 1/2" **Kit Endless** also available. *



Marvel Meraviglia Black Origin ⁽¹⁾ ⁽²⁾
120x278 cm - 47 1/4"x109 1/2" **Kit Endless** also available. *



* **The Endless Kits guarantee the presence of the exact sequence of graphics inside the packaging.** - I Kit Endless garantiscono la presenza dell'esatta sequenza delle grafiche all'interno dell'imballo. - Les Kit Endless garantissent la présence de la séquence exacte des graphismes à l'intérieur de l'emballage. - Kit Endless garantiert die exakten grafischen Sequenzen in der Packung. - Комплекты Kit Endless обеспечивают наличие точной последовательности рисунков внутри упаковки.

⁽¹⁾ **The various graphics of the product are distributed randomly in the boxes, without the possibility of choosing between the available patterns.** - All'interno delle casse, le varie grafiche del prodotto sono distribuite in modo casuale, senza possibilità di scelta tra i pattern disponibili. - À l'intérieur delle caisses, les différents graphismes du produit sont distribués en mode aléatoire, sans possibilité de choix entre les motifs disponibles. - Die Kisten enthalten die verschiedenen Grafiken des Artikels nach dem Zufallsprinzip, ohne dass Sie zwischen den einzelnen Motiven wählen können. - En el interior de las cajas, los distintos gráficos de los productos se distribuyen de forma aleatoria, sin que se pueda elegir el patrón disponible. - Рисунки распределены в ящиках в случайном порядке, без возможности выбора из доступных рисунков.

⁽²⁾ **Minor misalignments in the continuity of the veins between different graphics is normal for this type of product.** - Eventuali piccoli disallineamenti nella continuità delle venature tra grafiche diverse sono una caratteristica intrinseca di questa tipologia di prodotto. - Les éventuels petits désalignements de la continuité des veinures entre différents graphismes sont une caractéristique intrinsèque de cette typologie de produit. - Eventuelle kleine Versätze im Verlauf der Aderungen zwischen unterschiedlichen Grafiken sind charakteristisch für dieses Produkt. - Cualquier pequeño desalineado en la continuidad de las vetas entre diferentes gráficos es una característica intrínseca de este tipo de productos. - Возможные небольшие смещения рисунка прожилок на стыке плит являются характеристикой данного вида изделий.

Diamond

Decor designed by **Zaha Hadid Architects**

© Copyright Zaha Hadid Limited 2023
manufactured by Ceramiche Atlas Concorde under license from Zaha Hadid Limited.

mod A

mod B

mod C

mod D

mod B rotated 180°

mod A rotated 180°

Marvel Meraviglia
Calacatta Meraviglia Diamond Polished
46,6x284,6 cm - 18³/₈"x112"

Calacatta Meraviglia + Black Origin

Marvel Meraviglia
Black Origin Diamond Polished
46,6x284,6 cm - 18³/₈"x112"

Black Origin + Calacatta Meraviglia

Marvel Meraviglia
Silver Majestic Diamond Polished
46,6x284,6 cm - 18³/₈"x112"

Silver Majestic + Black Origin

A

a

B

b

mod A

50,5 cm - 19⁷/₈"

46,6 cm - 18³/₈"

44,8 cm - 17⁷/₈"

40,3 cm - 15⁷/₈"

A

a

B

b

mod B

50,5 cm - 19⁷/₈"

46,6 cm - 18³/₈"

58,3 cm - 23"

51,9 cm - 20⁷/₈"

A

a

B

b

mod C

52,9 cm - 20⁷/₈"

46,6 cm - 18³/₈"

54,2 cm - 21¹/₈"

49,8 cm - 19⁷/₈"

A

a

B

b

mod D

52,9 cm - 20⁷/₈"

46,6 cm - 18³/₈"

54,2 cm - 21¹/₈"

49,3 cm - 19⁷/₈"

118

119

INDEX

INSPIRATION

DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS


IMAGE
GALLERY

SURFACE
RANGE &
TECHNICAL
SPECS


SAFE CHOICE
COLLECTION RANGE
DIAMOND DECOR
DESIGNED BY
ZAHA HADID ARCHITECTS
SENSITECH TECHNOLOGY
MARVEL WORLD
TECHNICAL SPECIFICATIONS
& CERTIFICATIONS

ENJOY
THE VIDEO


Porcelain Tiles Decors




Marvel Meraviglia Calacatta Meraviglia Hexagon ⁽¹⁾ Polished
40,3x46,6 cm - 15⁷/₈"x18³/₈"




Marvel Meraviglia Calacatta Bernini Hexagon ⁽¹⁾ Polished
40,3x46,6 cm - 15⁷/₈"x18³/₈"




Marvel Meraviglia Silver Majestic Hexagon ⁽¹⁾ Polished
40,3x46,6 cm - 15⁷/₈"x18³/₈"




A 50,5 cm - 19⁷/₈"
a 46,6 cm - 18³/₈"
B 44,8 cm - 17⁷/₈"
b 40,3 cm - 15⁷/₈"



Marvel Meraviglia Grigio Elegante Hexagon ⁽¹⁾ Polished
40,3x46,6 cm - 15⁷/₈"x18³/₈"



Marvel Meraviglia Black Origin Hexagon ⁽¹⁾ Polished
40,3x46,6 cm - 15⁷/₈"x18³/₈"




Marvel Meraviglia Calacatta Meraviglia Mosaico Matte [Sensitech](#)
30x30 cm - 11³/₄"x11³/₄"



Marvel Meraviglia Calacatta Bernini Mosaico Matte [Sensitech](#)
30x30 cm - 11³/₄"x11³/₄"




Marvel Meraviglia Silver Majestic Mosaico Matte [Sensitech](#)
30x30 cm - 11³/₄"x11³/₄"



35x35 cm
1³/₈"x1³/₈"



Marvel Meraviglia Grigio Elegante Mosaico Matte [Sensitech](#)
30x30 cm - 11³/₄"x11³/₄"



Marvel Meraviglia Black Origin Mosaico Matte [Sensitech](#)
30x30 cm - 11³/₄"x11³/₄"

⁽¹⁾ Marvel Meraviglia Hexagon recalls the hexagonal Module A of Diamond designed by ZHA, which can be combined with to clad larger surfaces. Or use it on its own to give rooms a prestigious touch. Marvel Meraviglia Hexagon riprende il modulo esagonale A di Diamond designed by ZHA, a cui si può abbinare per ricoprire superfici più estese. Oppure utilizzare da solo per conferire agli ambienti un tocco di pregio. Marvel Meraviglia Hexagon reprend le module hexagonal A de Diamond designed by ZHA, auquel elle peut être associée pour recouvrir de plus grandes superficies. Elle peut aussi être utilisée seule pour conférer une touche d'élégance aux espaces.- Marvel Meraviglia Hexagon greift das Sechskantmodul A von Diamond designed by ZHA auf und kann mit diesem kombiniert werden, um ausgedehntere Flächen zu verkleiden. Es kann auch allein verwendet werden, um dem Ambiente besonderes Prestige zu verleihen.- Marvel Meraviglia Hexagon toma el módulo hexagonal A de Diamond diseñado por ZHA, con el cual se puede combinar para cubrir superficies más grandes. O bien, se puede utilizar solo para dar un toque de prestigio a los ambientes.- Marvel Meraviglia Hexagon перенимает шестигранный модуль A у декора Diamond от ZHA и может сочетаться с последним для облицовки более крупных поверхностей. Также может использоваться отдельно для придания интерьерам ноты изысканности.



INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



SAFE CHOICE
COLLECTION RANGE
DIAMOND DECOR
DESIGNED BY
ZAHA HADID ARCHITECTS
SENSITECH TECHNOLOGY
MARVEL WORLD
TECHNICAL SPECIFICATIONS
& CERTIFICATIONS

ENJOY
THE VIDEO



Porcelain Tiles Decors




Marvel Meraviglia Calacatta Meraviglia
Grid Velvet
59,5x118,2 cm - 23³/₈"x46¹/₂"



Marvel Meraviglia Calacatta Bernini
Grid Velvet
59,5x118,2 cm - 23³/₈"x46¹/₂"



Marvel Meraviglia Grigio Elegante
Grid Velvet
59,5x118,2 cm - 23³/₈"x46¹/₂"



Marvel Meraviglia Silver Majestic
Grid Velvet
59,5x118,2 cm - 23³/₈"x46¹/₂"

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS




SAFE CHOICE
COLLECTION RANGE
DIAMOND DECOR
DESIGNED BY
ZAHA HADID ARCHITECTS
SENSITECH TECHNOLOGY
MARVEL WORLD
TECHNICAL SPECIFICATIONS
& CERTIFICATIONS

ENJOY
THE VIDEO



Trim tiles

Indoor trim tiles



Outdoor trim tiles ± 20 mm



Outdoor Porcelain tiles ± 20 mm

For further details on the 20mm thick products, related trim pieces and installation systems - in particular for recommendations and precautions during installation- please refer to the Outdoor Design section on the Atlas Concorde website or to the Outdoor Design catalogue. Per dettagli sul prodotto e sui relativi pezzi speciali in 20mm di spessore, per i sistemi di posa e, in particolare, per raccomandazioni, accorgimenti e precauzioni in fase di posa e progettazione, si raccomanda di prendere visione del catalogo Outdoor Design e della sezione Outdoor Design del sito Atlas Concorde. - Pour plus de renseignements sur le produit, les pièces spéciales de 20mm d'épaisseur et sur les systèmes de pose, ainsi que pour tous conseils et recommandations et précautions d'emploi pendant la pose ou en phase de conception, nous vous recommandons de lire le catalogue Outdoor Design et de consulter la section Outdoor Design sur le site d'Atlas Concorde. - Bitte beachten Sie die detaillierten Informationen zum Produkt und zu den zugehörigen Formteilen in 20mm Stärke, zu den Verlegesystemen sowie vor allem die Empfehlungen, Tipps und bei der Planung und Verlegung zu beachtenden Vorsichtsmaßnahmen, die im Katalog Outdoor Design sowie im Bereich Outdoor Design der Atlas Concorde-Website aufgeführt sind. - Para mayor información sobre el producto y sus relativas piezas especiales de 20mm de grosor, para los sistemas de colocación, y en particular, para las recomendaciones, cautelas y precauciones en la fase de colocación y diseño, se recomienda consultar el catálogo Outdoor Design y la sección Outdoor Design del sitio Atlas Concorde. - Подробнее о плитках и о специальных элементах толщиной 20мм, о системах монтажа, о мерах предосторожности при проектировании и укладке можно узнать в каталоге Outdoor Design и в разделе Outdoor Design на сайте Atlas Concorde.


Windowsill / Threshold

Davanzale / Soglia

Reinforcement: expanded continuous panel
Rinforzo: pannello continuo espanso

Thermal conductivity of the insulation
Conducibilità termica dell'isolante 0,0323

Insulating and waterproof system
Sistema coibentante e impermeabile



Sensitech

SAFE. SOFT. SMART.

INDOOR & OUTDOOR
CONTINUITY

SOFT TO
THE TOUCH

EXTREMELY
SAFE

HYGIENIC AND EASY TO
CLEAN

LONG-LASTING
QUALITIES

Traditional anti-slip surface

The innovative Sensitech Surface

Sensitech is the high-tech surface for indoor and outdoor settings created by Atlas Concorde Laboratories. The surface combines high slip resistance performance with tactile softness. With Sensitech, the meaning of surface evolves and takes on a reassuring, pleasant and practical touch, making architectural spaces more comfortable and appealing. | Sensitech è la superficie ad alto coefficiente tecnologico per gli ambienti interni ed esterni realizzata dai Laboratori Atlas Concorde. La superficie coniuga elevate prestazioni di resistenza allo scivolamento ad una maggiore morbidezza tattile. Con Sensitech il significato di superficie si evolve e assume un tocco rassicurante, piacevole e pratico, rendendo gli spazi architettonici sempre più confortevoli e appaganti.

discover more

INDEX

INSPIRATION

DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS

IMAGE
GALLERY

SURFACE
RANGE &
TECHNICAL
SPECS

SAFE CHOICE
COLLECTION RANGE
DIAMOND DECOR
DESIGNED BY
ZAHA HADID ARCHITECTS
SENSITECH TECHNOLOGY
MARVEL WORLD
TECHNICAL SPECIFICATIONS
& CERTIFICATIONS

ENJOY
THE VIDEO

125

MARVEL
MERAVIGLIA

MARVEL
ONYX

MARVEL
X

MARVEL
GALA

MARVEL
TRAVERTINE

MARVEL
SHINE

MARVEL
DREAM

MARVEL
EDGE

MARVEL
STONE

MARVEL
GEMS

MARVEL
PRO

MARVEL



DOWNLOAD
MARVEL WORLD
CATALOG

MARVELWORLD

A world of emotions

Marvel World encompasses all the marble-look surfaces of Atlas Concorde in a single tool capable of offering ample creative potential: a complete stylistic project for inspiration, color range, and availability of formats and decors.

Marvel World racchiude tutte le superfici effetto marmo di Atlas Concorde in un unico strumento in grado di offrire ampie potenzialità creative: un progetto stilistico completo per ispirazione, ampiezza cromatica e disponibilità di formati e decori.

126

Note

For information and details relating to codes, packaging and weight it is recommended to refer to the latest pricelist. - Per le informazioni e i dati relativi a codici, imballaggi e pesi occorre sempre consultare l'ultimo listino aggiornato e in vigore. - Pour toutes informations et renseignements concernant les codes, les emballages et les poids, il y a toujours lieu de consulter le dernier tarif en vigueur et mis à jour. - Für Informationen und Daten die den Code, die Verpackung und das Gewicht betreffen bitte die aktuellste Preisliste zugrunde legen. - Para acceder a la información y a los datos relativos a códigos, embalajes y pesos hay que consultar siempre la última lista de precios actualizada y vigente. - Для информации о кодах, упаковках и весе обращайтесь к последнему действующему прайс-листу.

Colors and optical features of the materials illustrated in this catalogue are to be regarded as mere indications. - I colori e le caratteristiche estetiche dei materiali illustrati nel presente catalogo sono da ritenersi puramente indicativi. - Les coloris et les caractéristiques esthétiques des références illustrées dans le catalogue sont donnés à titre purement indicatif. - Die Farben und die ästhetischen Eigenschaften der in diesem Katalog abgebildeten Produkte sind als reine Richtwerte zu betrachten. - Los colores y las características estéticas de los materiales ilustrados en el presente catálogo deben ser considerados como puramente indicativos. - Цвета и эстетические характеристики описанных в настоящем каталоге материалов являются только ориентировочными.

Atlas Concorde reserves the right to modify any product without notice and will not be liable for any direct or indirect damage resulting from such modifications. - Atlas Concorde si riserva di modificare i prodotti senza preavviso, declinando ogni responsabilità su eventuali danni diretti o indiretti derivanti da eventuali modifiche. - Atlas Concorde se réserve le droit de modifier ses produits sans préavis et décline toute responsabilité concernant les éventuels dommages directs ou indirects qui pourraient dériver de ces modifications. - Atlas Concorde behält sich das Recht vor jederzeit und ohne vorherige Ankündigung, die Produkte zu verändern, und lehnt jede Haftung bei direkten oder indirekten Schäden ab, die von diesen Veränderungen herrühren. - Atlas Concorde se reserva el derecho de modificar los productos sin previo aviso, rechaza cualquier responsabilidad sobre eventuales daños directos o indirectos derivados de eventuales modificaciones. - Atlas Concorde оставляет за собой право изменять характеристики изделий без предварительного уведомления, отклоняя при этом любую ответственность за прямые или косвенные убытки, возникшие в результате изменений.

127

THANKS TO

Axolight

axolight.it

mdf italia

mdfitalia.com

esperia®

esperialuci.com

nube

nubeitalia.com

CANTORI

cantori.it

**Lumen
center.**

lumencenteritalia.com

PAOLO CASTELLI

paolocastelli.com

Gallotti&Radice

galottiradice.it

CEPPI

THE ITALIAN TOUCH

ceppisrl.com

INDEX

INSPIRATION

DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS

IMAGE
GALLERY

SURFACE
RANGE &
TECHNICAL
SPECS

SAFE CHOICE
COLLECTION RANGE
DIAMOND DECOR
DESIGNED BY
ZAHA HADID ARCHITECTS
SENSITECH TECHNOLOGY
MARVEL WORLD
TECHNICAL SPECIFICATIONS
& CERTIFICATIONS

ENJOY
THE VIDEO



Porcelain tiles - Rectified monocaliber

Gres porcellanato - Rettificato monocalibro

Compliant with standards EN 14411 annex G group B1a
Compliant with standards ISO 13006 annex G group B1a
Conforme alla norma EN 14411 Appendice G gruppo B1a
Conforme alla norma ISO 13006 Appendice G gruppo B1a

160x320 cm - 36 ³ / ₈ "x126"	± 6 mm	75x150 cm - 29 ¹ / ₂ "x59"	± 9 mm
120x278 cm - 47 ¹ / ₄ "x109 ¹ / ₂ "	± 6 mm	75x75 cm - 29 ¹ / ₂ "x29 ¹ / ₂ "	± 9 mm
120x240 cm - 47 ¹ / ₄ "x94 ¹ / ₂ "	± 9 mm	60x60 cm - 23 ³ / ₈ "x23 ³ / ₈ "	± 9 mm
120x120 cm - 47 ¹ / ₄ "x47 ¹ / ₄ "	± 9 mm	30x60 cm - 11 ³ / ₄ "x23 ³ / ₈ "	± 9 mm
60x120 cm - 23 ³ / ₈ "x47 ¹ / ₄ "	± 6 mm		
60x120 cm - 23 ³ / ₈ "x47 ¹ / ₄ "	± 9 mm	60x120 cm - 23 ³ / ₈ "x47 ¹ / ₄ "	± 20 mm

Technical features Caratteristiche tecniche	Test Method Metodo di prova	Requirements for nominal size N / Requisiti per dimensione nominale N			Porcelain tiles			
		7 cm ≤ N < 15 cm	N ≥ 15 cm		Polished ± 6 mm	Polished Velvet ± 9 mm	Matte Sensitech ± 9 mm	Outdoor Sensitech ± 20 mm
 Length and width Lunghezza e larghezza Thickness Spessore Straightness of sides Rettilinearità degli spigoli Rectangularity (Measurement only on short edges when L/l ≥ 3) Ortogonalità (Misurazione da condurre solo sui lati corti quando L/l ≥ 3)	ISO 10545-2	(mm)	(%)	(mm)	Suitable for Conforme	Suitable for Conforme	Suitable for Conforme	Suitable for Conforme
		± 0,9 (*) Non-rect. ± 0,4 (*) Rect.	± 0,6 (*) Non-rect. ± 0,3 (*) Rect.	± 2,0 (*) Non-rect. ± 1,0 (*) Rect.				
		± 0,5 (**)	± 5 (**)	± 0,5 (**)				
		± 0,8 (****) Non-rect. ± 0,4 (****) Rect.	± 0,5 (****) Non-rect. ± 0,3 (****) Rect.	± 1,5 (****) Non-rect. ± 0,8 (****) Rect.				
 Surface flatness Planarità	ISO 10545-2	c.c. ± 0,8 Non-rect. c.c. ± 0,6 Rect.	c.c. ± 0,5 Non-rect. c.c. ± 0,4 Rect.	c.c. ± 2,0 Non-rect. c.c. ± 1,8 Rect.	Suitable for Conforme	Suitable for Conforme	Suitable for Conforme	Suitable for Conforme
		e.c. ± 0,8 Non-rect. e.c. ± 0,6 Rect.	e.c. ± 0,5 Non-rect. e.c. ± 0,4 Rect.	e.c. ± 2,0 Non-rect. e.c. ± 1,8 Rect.				
		w. ± 0,8 Non-rect. w. ± 0,6 Rect.	w. ± 0,5 Non-rect. w. ± 0,4 Rect.	w. ± 2,0 Non-rect. w. ± 1,8 Rect.				
 Water absorption (in% by mass) Massa d'acqua assorbita (come % della massa)	ISO 10545-3	E_v ≤ 0,5% Individual Maximum 0,6% E _v ≤ 0,5% Valore massimo singolo 0,6%			≤ 0,1 %	≤ 0,1 %	≤ 0,1 %	≤ 0,1 %
	ASTM C373	Requirement ANSI A137.1 Water absorption max ≤ 0,5%			≤ 0,5 %	≤ 0,5 %	≤ 0,5 %	≤ 0,5 %
 Breaking strength Sforzo di rottura	ISO 10545-4	S ≥ 700N (for thickness < 7,5 mm - per spessore < 7,5 mm) S ≥ 1300N (for thickness ≥ 7,5 mm - per spessore ≥ 7,5 mm)			S ≥ 1000 N	S ≥ 1500 N	S ≥ 1500 N	S ≥ 10000 N
		R ≥ 35 N/mm ²			R ≥ 40 N/mm ²	R ≥ 40 N/mm ²	R ≥ 40 N/mm ²	R ≥ 45 N/mm ²
 Modulus of rupture Resistenza alla flessione	EN 1339 Annex F	-			-	-	-	≥ U4 60x120
		-			-	-	-	≥ U4 60x120
 Bending strength and breaking load Resistenza a flessione e al carico di rottura (4)/(5)	ISO 10545-5	Declared value Valore dichiarato			≥ 0,55	≥ 0,55	≥ 0,55	≥ 0,55
		-			-	-	-	≥ U4 60x120
 Impact resistance, as coefficient of restitution Resistenza all'impatto, espresso come coefficiente di restituzione	ISO 10545-6	-			-	-	-	≥ U4 60x120
		-			-	-	-	≥ U4 60x120
 Resistance to deep abrasion of unglazed tiles (removed volume) Resistenza all'abrasione profonda delle piastrelle non smaltate (volume materiale asportato)	ISO 10545-8	-			-	-	-	≥ U4 60x120
		-			-	-	-	≥ U4 60x120
 Coefficient of thermal linear expansion Coefficiente di dilatazione termica lineare	ISO 10545-9	Declared value Valore dichiarato			≤ 7MK ⁻¹	≤ 7MK ⁻¹	≤ 7MK ⁻¹	≤ 7MK ⁻¹
		-			-	-	-	≥ U4 60x120
 Thermal shock resistance Resistenza agli sbalzi termici	ISO 10545-10	Pass according to EN ISO 10545-1 Test superato in accordo con ISO 10545-1			Resistant Resiste	Resistant Resiste	Resistant Resiste	Resistant Resiste
		-			-	-	-	≥ U4 60x120
 Moisture expansion (in mm/m) Dilatazione all'umidità (in mm/m)	ISO 10545-12	Declared value Valore dichiarato			≤ 0,01% (0,1mm/m)	≤ 0,01% (0,1mm/m)	≤ 0,01% (0,1mm/m)	≤ 0,01% (0,1mm/m)
		-			-	-	-	≥ U4 60x120
 Frost resistance Resistenza al gelo	EN 12004-2	Declared value Valore dichiarato			≥ 1,0 N/mm ² (Class C2 - EN 12004)	≥ 1,0 N/mm ² (Class C2 - EN 12004)	≥ 1,0 N/mm ² (Class C2 - EN 12004)	≥ 1,0 N/mm ² (Class C2 - EN 12004)
		-			-	-	-	≥ U4 60x120
 Bond strength / adhesion for Cementitious Adhesives Adesione mediante trazione su adesivi cementizi	-	Class A1 or A1_f Classe A1 oppure A1 _f			A1 - A1 _f	A1 - A1 _f	A1 - A1 _f	A1 - A1 _f
		-			-	-	-	≥ U4 60x120
 Reaction to fire Reazione al fuoco	ISO 10545-13	Minimum Class B Classe minima B			A	A	A	A
		-			-	-	-	≥ U4 60x120
 Resistance to low concentrations of acids and alkalis Resistenza a basse concentrazioni di acidi e alcali	ISO 10545-14	Declared Class Classe dichiarata			LA	LA	LA	LA
		-			-	-	HA	HA
 Resistance to high concentrations of acids and alkalis Resistenza ad alte concentrazioni di acidi e alcali	ISO 10545-14	Declared Class Classe dichiarata			5	Polished 5 Velvet	5	5
		-			-	-	-	≥ U4 60x120
 Resistance to staining, for unglazed tiles Resistenza alle macchie per piastrelle non smaltate	DIN EN 16165 ANNEX B (EX DIN 51130)	Declared value Valore dichiarato			N.C.	N.C.	R10	R11
		-			-	-	-	≥ U4 60x120
 Barefoot Ramp Test Metodo della rampa a piedi nudi	DIN EN 16165 ANNEX A (EX DIN 51037)	Declared value Valore dichiarato			0	0	A+B	A+B+C
		-			-	-	-	≥ U4 60x120
 Pendulum Friction Test Metodo del Pendolo	BS EN 16165 ANNEX C (EX BS 7976)	PTV ≥ 36 classifies the surface as 'low slip risk'			≥ 36 Dry ≤ 24 Wet	≥ 36 Dry ≤ 24 Wet	≥ 36 Dry ≥ 36 Wet	≥ 36 Dry ≥ 36 Wet
		-			-	-	-	≥ U4 60x120
 Coefficient of friction (COF) Coefficiente di attrito	AS 4586	Declared Classification of the new pedestrian surface materials according to the Pendulum Test			-	-	Class P3	Class P4
		-			-	-	-	≥ U4 60x120
 Dynamic coefficient of friction (DCOF) Coefficiente di attrito dinamico	UNE EN 16165 ANNEX C (EX UNE 41901 EX 2017)	Declared value Valore dichiarato			-	-	Class C2	Class C3
		-			-	-	-	≥ U4 60x120
 Coefficient of friction (COF) Coefficiente di attrito	B.C.R.A Rep. CEC/81	D.M. 236/89 del 14/06/89 μ > 0,40 per elemento sconvolgente su pavimentazione asciutta μ > 0,40 per elemento sconvolgente gomma dura su pavimentazione bagnata			> 0,40 Asciutto < 0,40 Bagnato	> 0,40 Asciutto < 0,40 Bagnato	> 0,40 Asciutto < 0,40 Bagnato	> 0,40 Asciutto < 0,40 Bagnato
		-			-	-	-	≥ U4 60x120
 Dynamic coefficient of friction (DCOF) Coefficiente di attrito dinamico	ANSI A 326,3	-			dry DCOF ≥ 0,42	Polished dry DCOF ≥ 0,42 Velvet et DCOF ≥ 0,42	wet DCOF ≥ 0,50	wet DCOF ≥ 0,55
		-			-	-	-	≥ U4 60x120

^(*) The permissible deviation, in % or mm, of the average size for each tile (2 or 4 sides) from work size (WS). Deviazione ammissibile, in % oppure mm, della dimensione media di ogni piastrella (2 oppure 4 lati) dalla dimensione di fabbricazione (WS).

^(**) The permissible deviation, in % or mm, of the average thickness for each tile from the work size thickness (WS). Deviazione ammissibile, in % oppure mm, dello spessore medio di ogni piastrella dallo spessore riportato nella dimensione di fabbricazione (WS).

^(***) The maximum permissible deviation from straightness, in % or mm, related to the corresponding work sizes (WS). Deviazione massima ammissibile di rettilineità, in % oppure mm, in rapporto alle dimensioni di fabbricazione (WS) corrispondenti.

^(****) The maximum permissible deviation from rectangularity, in % or mm, related to the corresponding work sizes (WS). Deviazione massima ammissibile di ortogonalità, in % oppure mm, in rapporto alle dimensioni di fabbricazione (WS) corrispondenti.

^(v) The maximum permissible deviation from centre curvature, in % or mm, related to diagonal calculated from the work sizes (WS). Deviazione massima ammissibile della curvatura del centro, in % oppure mm, in rapporto alla diagonale calcolata secondo le dimensioni di fabbricazione (WS).

^(vi) The maximum permissible deviation from edge curvature, in % or mm, related to the corresponding work sizes (WS). Deviazione massima ammissibile della curvatura dello spigolo, in % oppure mm, in rapporto alle dimensioni di fabbricazione (WS) corrispondenti.

^(vii) The maximum permissible deviation from warpage, in % or mm, related to diagonal calculated from the work sizes (WS). Deviazione massima ammissibile dello sverglamento, in % oppure mm, in rapporto alla diagonale calcolata secondo le dimensioni di fabbricazione (WS).

^(viii) Determination of slip resistance of pedestrian surfaces; it does not cover sports surfaces and road surfaces for vehicles (skid resistance). Determinazione della resistenza allo sconvolgimento delle superfici pedonabili, non si applica alle pavimentazioni sportive ed alle pavimentazioni stradali veicolari.

^(ix) Anti-slip performance is guaranteed at the time of delivery of the product. Le prestazioni anti-slip vengono garantite al momento della consegna del prodotto.

^(x) For further details, please refer to outdoor design general catalogue. Per maggiori informazioni riferirsi al catalogo generale Outdoor Design.

^(xi) Only for products with 20 mm thickness. Solo per prodotti a 20mm di spessore.

^(xii) PTV ≥ 36 Wet on demand / su richiesta (xiii) P3 on demand / su richiesta (xiv) C2 on demand / su richiesta

Ethical identity



For Atlas Concorde, being Made in Italy is not just a prestigious certification of style, design, and production excellence, but an identity that involves all aspects of its business. For this reason, we identify with the values expressed by Confindustria Ceramica's ethical code, which guarantee absolute compliance with labor regulations, and with the marks Made in Italy and Ceramics of Italy, which certify the quality of authentic Italian style.

Per Atlas Concorde, Made in Italy non è solo un prestigioso attestato di stile, design ed eccellenza produttiva, ma un modo di essere che coinvolge tutti gli aspetti della propria attività. Per questo ci riconosciamo nei valori espressi dal codice etico di Confindustria Ceramica, che garantiscono il rispetto assoluto delle normative sul lavoro, e nei marchi Made in Italy e Ceramics of Italy, che certificano la qualità dell'autentico stile italiano.

Certifications

Company certifications



Product certifications



Product declarations



Certifications for export to international markets*



Shipments can be made in accordance with national requirements anywhere in the world, even in markets with complex customs procedures such as Egypt, Morocco and Kurdistan, thanks to our active cooperation with accredited certification bodies in each country. - Possibilità di spedizioni conformi alle prescrizioni nazionali ovunque nel mondo, anche in mercati con procedure doganali complesse come Egitto, Marocco, Kurdistan, grazie alla collaborazione sempre attiva con gli enti di certificazione accreditati

* In ciascun paese. - Dank unserer aktiven Zusammenarbeit mit den akkreditierten Zertifizierungsstellen in den einzelnen Ländern können die Sendungen in Übereinstimmung mit den nationalen Anforderungen überall auf der Welt versandt werden, selbst auf Märkten mit komplexen Zollverfahren wie Ägypten, Marokko und Kurdistan. - Possibilité d'expéditions conformes aux prescriptions nationales partout dans le monde, même sur les marchés dont les procédures douanières sont complexes comme l'Égypte, le Maroc ou le Kurdistan, grâce à la collaboration toujours active avec les organismes de certification homologués dans chaque pays. - Se pueden realizar envíos según la normativa nacional a cualquier parte del mundo, incluso a mercados con procedimientos aduaneros complejos como Egipto, Marruecos o Kurdistan, gracias a la cooperación permanente con los organismos de certificación acreditados en cada país. - Компания имеет возможность осуществлять поставки в любую точку мира в соответствии с национальными требованиями, даже на рынках со сложными таможенными процедурами, таких как Египет, Марокко, Курдистан, благодаря неизменно активному сотрудничеству с аккредитованными органами сертификации в каждой стране.

^(*) Classificazione UPEC aggiornata al - Classement UPEC mis à jour au: 2023

^(*) Si consiglia la consultazione della pagina - On vous conseille de vous connecter à: <https://database.cstb.fr/holderdetails?UId=ETB-2094&AppRef=QB32>

^(*) Per ulteriori informazioni scrivere a - Pour tous renseignements complémentaires merci d'ecrire à: france@atlasconcorde.it

^(*) Tutti i prodotti Atlas Concorde in gres porcellanato e in monocottura in pasta bianca possono essere utilizzati per progetti edili che seguono le linee guida del GREEN BUILDING COUNCIL e possono contribuire all'ottenimento del rating LEED V4 degli edifici. All Atlas Concorde porcelain tiles and white-body single-fired products can be used for building projects that follow the guidelines of the GREEN BUILDING COUNCIL and can contribute to the achievement of the LEED V4 rating for buildings.

INDEX



INSPIRATION



DIAMOND DECOR
DESIGNED BY
ZAHA HADID
ARCHITECTS



IMAGE
GALLERY



SURFACE
RANGE &
TECHNICAL
SPECS



SAFE CHOICE
COLLECTION RANGE
DIAMOND DECOR
DESIGNED BY
ZAHA HADID ARCHITECTS
SENSITECH TECHNOLOGY
MARVEL WORLD
TECHNICAL SPECIFICATIONS
& CERTIFICATIONS

ENJOY
THE VIDEO





Ceramiche Atlas Concorde S.p.A.
Via Canaletto 141
41042 Spezzano di Fiorano (MO) – Italia

Atlas Concorde USA, Inc.
117 Seaboard Lane – Suite F170
Franklin, TN 37067 – USA

Atlas Concorde Russia
Business centre “Meliora Place”
Prospekt Mira 6
129090 Moscow – Russia

Atlas Concorde Middle East, Fz-Llc
Building 8 – Suite 106
D3 Dubai Design District
United Arab Emirates

atlasconcorde.com

Copyright 2023 by Ceramiche Atlas Concorde S.p.A
(41042 Spezzano di Fiorano (MO) – Italia)
September 2023