

**PRODUCT
NOVELTIES**

 intra lighting

INDEX

We care.

For people and for the planet.

KEY AREAS WE WILL FOCUS ON

01**PRODUCTS**

Circular and human-friendly products

- Products supporting people's well-being
- Responsible use of materials
- Material and data transparency
- Energy-efficient products
- Repairability, prolonging products life
- Design for disassembly
- High recyclability

02**SOLUTIONS**

Healthy living and improved well-being with light

- Human-centric lighting solutions
- Supporting health, positive feelings and motivation
- All-in-one acoustics solutions
- Smart use of artificial and natural light
- Connection with different LMS systems

03**COMPANY**

Sustainable and ethical company

- Becoming a net zero company
- High ethical standards
- Environmental-friendly production
- Responsible supplier choice
- A caring employer
- Care for local community

We have always been ahead of time. We lived and acted sustainably before sustainability became synonymous with responsible behaviour towards the environment and people. Concern about what kind of world we will leave to our children has always been present in everything we do. We were not guided by regulations; we were guided by conscience and consciousness.

Our initiatives

100%

2.000+

1.000hl

green energy*

trees planted

rainwater harvesting
for watering green areas

We contributed for the purchase of 2023 seedlings for Kras, we will donate 1500 hours of our work in a renovation action and will support the project long-term.



We support culture, sports, health and social initiatives in our local community.



We have our own solar power plant and heat pump. Renewable energy source for electricity: 29% in 2022 | 72% in 2023 | 100% by 2024.



We breath new life in old degraded buildings. We reuse a lot of the construction materials from the demolition work.



We are surrounded by green areas. We planted 60 fruit and leaf trees of local varieties and more than 1000 plants.

Present globally connected locally

Our company, established in 1989, is a global provider of smart lighting solutions. We are present worldwide but always closely connected to the local environment. As one of the most important players in the lighting market, we strive to contribute to the world's well-being. We work closely with architects, lighting designers, engineers and interior designers around the globe to co-create engaging lighting solutions and foremost vibrant spaces.

Headquarters

Slovenia, Šempeter pri Gorici


Offices

Croatia - Zagreb
Italy - Milan
Netherlands - Leerdam
Serbia - Belgrade
Slovenia - Ljubljana
UAE - Dubai
USA - New York

Production plants

Slovenia, Šempeter pri Gorici
Croatia, Čazma
Serbia, Donji Milanovac
USA, Pennsylvania, Trevose (coming soon)

Presence



400+

employees

68

countries

34+

years of experience

37,6

mio EUR turnover in 2022



Made in Europe

State of the art production

With a new production process, we have reduced energy consumption, raw materials, natural resources and waste. We introduced an automated vertical storage system, a modern powder coating system and an automated guided vehicle for flexible internal logistics.



Solar panels generate enough energy to run the factory and HQ autonomously.



Safe and comfortable working environment



Modern powder coating system with low water and energy consumption, pre-treatment tunnel with passivation (corrosion protection), and automated powder application with a recovery system.

7 24 ISO
year warranty thousand m² certified productions

Quality in every detail

Our products are thoughtfully designed, manufactured and tested in order to ensure reliable operation throughout their life span, strongly limit the environmental impact and co-create pleasant living conditions. Quality is one of our highest priorities and a way of life.



Automated guided vehicle for flexible internal logistics



Automated vertical storage system



Robotic Welding Systems




Turn-mill center with collaborative robot



All the products are 100% tested in our own lab, one of the biggest in Europe.



Just a click away

Visit our website to comprehend the portfolio quickly, discover the novelties, and find the product you are looking for. There are different ways to find inspiration for your projects. The user experience is simple, fast and intuitive. Make a click!



Find the product in less than a minute!

There are many ways to find a product. Search visually by family or models. Or technically by filters, defining a specific feature or installation type. There is also a Quick ship filter available.



Intra Configurator

Intra Configurator is an easy, fast and accurate tool, with simple feature selection. Its role is to prevent all the mistakes that could be done while planning. Every product also gets its own technical card and all the necessary documentation downloads.

Intra Constructor PRO

Work smarter. Be faster.

There has never been an easier way to design your next lighting system. Intra Constructor PRO enables quick, simple and precise selection of lighting modules that can be personalized to fit best in your interior design. Every design is unique and no piece is forgotten




100%
accurate
∅
forgotten parts



Interactive product presentations

Get all the product presentations in only one download. Browse through them offline, quickly and easily, the complete portfolio, new products included, is presented.




Architecture and design platforms

We are, where you are. Get inspired, create mood boards and explore our products and projects.



Our lighting guides

Equip yourself with precious knowLEDge about lighting in different project types and its impact on people's well-being. Our lighting guides are available in interactive PDF, so they'll support your work also offline.



Bim

A game changer for the construction industry.

BIM offers an intelligent 3D process to efficiently plan, design and construct throughout the building life cycle, to support and manage your projects easily. A wide range of our products is available in 3D BIM at BIM object library.

Our products are available in the following formats:





Pixy

Authentically magnetic

Move your table. Pixy will follow

Se sposti il tavolo, Pixy lo segue

Premaknite svojo mizo. Pixy vam bo sLEDila

Pixy is never fixed. It is always flexible. Which makes it the perfect choice for restaurants and bars where moving tables is a daily routine. With a small carbon rod and a magnet, you can instantly move and redirect the light without using the ladder. We think that Pixy is nicer when grouped. Combine composition over and over again.

Pixy non si fissa. È sempre flessibile. È la soluzione perfetta per ristoranti e bar dove tutti i giorni si devono spostare i tavoli. Non serve la scala, in un attimo puoi spostare e orientare la luce con una tige in carbonio e un magnete. Per noi Pixy dà il massimo quando è in gruppo. Si può comporre e ricombinare a piacere.

Pixy ni nikoli fiksna. Je povsem fleksibilna in kot taka odlična izbira za restavracije in bare, kjer je premikanje miz vsakodnevna rutina. Z majhno karbonsko palico in magnetom lahko svetlobo v trenutku premaknete in preusmerite brez uporabe lestve. Menimo, da je Pixy lepša v kompoziciji, ki jo lahko kar naprej spremojate.





15

Bar B / Visualization: Render Atelier



Private residence / Visualization: Render Atelier
Private residence / Interior design: Notio / Visualization: Duaviz




16



Vinarija Tarpoš, Aranđelovac, Srbija / Architecture: AteljeAL, Beograd / Photography: Miloš Martinović

Private residence, Croatia / Interior design: Notio / Visualization: Vividforge

Private residence / Interior design: Notio / Visualization: Vividforge



MAIN FEATURES



Step-less orientation

The magnet allows step-less orientation. This gives you freedom when moving and redirecting the light to the desired position. It comes very useful in situations where moving furniture is a daily routine.




Aesthetic solution for concrete ceilings

The driver is integrated into the ceiling cup, so it is appropriate for installing it when you can't have a remote driver. Thanks to the magnets, Pixy can be simply adjusted to the desired direction.


Combine your favourite composition

With cluster installation you can combine up to seven spots. Cables can become part of the design and remote power-in position will no longer be a problem.







One bar, 3 or 5 spots

Why having many single ceiling cups when you can have only one aesthetic bar with integrated driver? 3 or 5 spots can be flexibly rotated and dimmed.





	S Suspended	C/W Ceiling / Wall	C/W D Ceiling / Wall with integrated driver	C/W-BAR 3 Ceiling / Wall with integrated driver	C/W-BAR 5 Ceiling / Wall with integrated driver
Beam angle	30°, 50°	30°, 50°	30°, 50°	30°, 50°	30°, 50°
Orientation	± 95° / 360°	± 58° / 360°	± 58° / 360°	± 58° / 360°	± 58° / 360°
Luminaire luminous flux	690 - 1550 lm	690 - 1550 lm	690 - 1550 lm	3x 690 - 1550 lm	5x 690 - 1550 lm
LED colour	927, 930, 935, 940	927, 930, 935, 940	927, 930, 935, 940	927, 930, 935, 940	927, 930, 935, 940
Driver	Casambi, DALI, FO	Casambi, DALI, FO	Casambi, DALI, FO	Casambi, DALI, FO	Casambi, DALI, FO
Driver position	Ceiling cup / Remote	Remote	Ceiling cup	Ceiling bar	Ceiling bar
Dimensions	SH (mm): 500 - 2000				




Standard: Special colours:



Light source: High-power COB LED, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C. **Optic:** Highly efficient with uniform distribution, metalized polycarbonate with lacquer finish. **Body:** Steel-sheet, powder coated. **Ceiling cup:** Ceiling cup with or without driver or ceiling bar with integrated driver must be ordered separately. **Control gear:** Constant current driver (order separately). In the Pixy C Bar integrated highly-efficient driver with fixed output (FO) or dimmable (DALI-TD, Casambi). **Power supply:** 250 - 450mA / 230V 50Hz.

Sorgente: COB LED High-power, CRI>90, MacAdam≤2, 50.000h L90 B10 a 35°C. **Ottica:** Ottica ad alta efficienza con distribuzione uniforme, policarbonato metallizzato tramite laccatura. **Corpo:** Lamiera d'acciaio, verniciatura a polvere. **Rosone:** Rosone con o senza alimentatore da ordinare separatamente o sistema C BAR con alimentatore integrato da ordinare separatamente. **Alimentazione:** Alimentatore a corrente costante (ordinare separatamente). Nella Pixy C Bar è compreso alimentatore ON-OFF (FO) o dimmerabile (DALI-TD, Casambi). **Alimentatore:** 250 - 450mA / 230V 50Hz.

Svetlobni vir: Visoko učinkovit COB LED modul, CRI>90, barvno odstopanje MacAdam≤2, 50.000 h L90 B10 na 35 °C. **Optika:** Visoko učinkovit metaliziran in lakiran polikarbonat z enakomerno porazdelitvijo svetlobnega snopa (srednji, široki svetlobni snop). **Ohišje:** Pločevina, prašno barvana. **Stropna rozeta:** Stropno razeto ali nosilec z ali brez LED konverterja je treba naročiti ločeno. **Napajalnik:** LED konverter s konstantnim tokom je treba naročiti ločeno. Stropna konzola je opremljena z LED konverterjem s konstantnim tokom (FO) ali regulacijskim izhodom (DALI-TD, Casambi). **Napajanje:** 250 - 450 mA / 230 V 50 Hz.



Black Hole

Extreme phenomenon

Its perfection absorbs you

This is a story of how the light found the way out of the black hole to enlighten your space. Black hole is a perfect luminaire for all your galaxies – home, office, hospitality. Because of its size and distinct look it has absolutely no chance to stay invisible.

It is multifunctional. It offers different possibilities of illumination. The acoustic surface reduces noise and improves speech audibility. With its integrated Bluetooth loudspeaker, you can listen to your favourite music, and its sophisticated design brings a touch of luxury to your space. Last but not least, the atmosphere it creates might help you find the way out whenever you feel stuck in a black hole.

La perfezione ti cattura

Black hole narra di come la luce trova la strada per uscire da un buco nero e illumina i tuoi spazi. È la soluzione perfetta per le galassie della tua vita: casa, ufficio, alberghi. Non rischia davvero di passare inosservata, sia per le dimensioni che per il design esclusivo.

È multifunzionale, dispone di diverse modalità di illuminazione. La superficie acustica abbatte il rumore e migliora l'intelligibilità del parlato. La tua musica viene diffusa dall'altoparlante bluetooth integrato e i tuoi spazi vengono resi sontuosi dal sofisticato design. Ma, soprattutto, l'atmosfera che si crea ti aiuta a trovare la tua personale via d'uscita ogni volta che ti senti bloccato in un buco nero.

Njena popolnost vas posrka

To je zgodba o tem, kako je svetloba našla pot iz črne luknje in razsvetlila vaš prostor. Črna luknja je popolna svetilka za vse vaše galaksije – dom, pisarno, gostinstvo. Zaradi svoje velikosti in izražitega videza jo je nemogoče prezreti.

Je večnamenska. Ponuja različne možnosti osvetlitve. Akustična površina zmanjšuje hrup in izboljšuje slišnost govora. Preko vgrajenega zvočnika s tehnologijo Bluetooth lahko poslušate svojo najljubšo glasbo, njena elegantna oblika pa v vaš prostor vselej vnese pridih razkošja. Nenazadnje, vzdušje, ki ga ustvarja, vam lahko pomaga najti izhod, ko se počutite, kot da ste obtičali v črni luknji.





Private residence / Visualization: Viscato
Private residence, Paris / Visualization: Duaviz



MAIN FEATURES




A touch of luxury

Black Hole is different from other luminaires even at a glance, always adding a touch of luxury to the space. Its soft round form is ageless.

Noise reduction

The noise level in a space has an impact on the well-being. The big acoustic surface of Black Hole reduces the noise pollution in the space and improves the acoustics.





Dome-shaped black interior

It creates the essence of Black Hole, where you lose the sense of the product deepness. Direct / indirect illumination can be switched or dimmed separately, making this luminaire a perfect fit for your changing needs.

Bluetooth Sound System

With the use of wireless BlueTooth technology, you can connect smartphones, computers, or tablets and enjoy your favourite music with a built-in speakers system.

FEATURES:

Output power: 4x30W | Peak power: 4x50W | Dynamic frequency response range: 100 Hz - 15000 Hz +/- 3 dB, 80 Hz - 20000 Hz +/- 5 dB | Bluetooth version: 5.1



Black Hole

Technical Overview




FAMILY MEMBER



TECH. SPECS


LUMINAIRE LUMINOUS FLUX	LIGHT DISTRIBUTION	LED COLOUR	DRIVER
4400 - 4800 lm	Direct 50% / Indirect 50%	927, 930, 940	Casambi, DALI, TD
MATERIAL	SOUND ABSORBING SURFACE	SUSPENSION HEIGHT	
Perforated eco leather	1 m ²	1500, 3000, 5000 mm	

MATERIALS



Light source: High-flux LED strip, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C. **Optic:** Satin opal polycarbonate diffuser (SOP). **Body:** Aluminium dome, powder coated, with faux leather upholstery. **Ceiling cup:** For suspended versions, the ceiling cup and suspension set must be ordered separately. Find out more on the technical pages or online product configurator. **Control gear:** Integrated highly-efficient driver with fixed output (FO-DS) or dimmable (DALI-DS, TD, Casambi) - separate switching. **Power supply:** 230V 50Hz.

Sorgente: Strip LED High-flux, CRI>90, MacAdam≤2, 50.000h L90 B10 a 35°C. **Optica:** Diffusore in policarbonato opale satinato (SOP). **Corpo:** Cupola in alluminio, verniciata a polvere, con rivestimento in ecopelle. **Rosone:** Per le versioni a sospensione, il rosone e il kit di sospensione deve essere ordinato separatamente. Maggiori informazioni nelle pagine relative alle caratteristiche tecniche o sul configuratore del prodotto on line. **Alimentazione:** Alimentatore integrato on/off ad alta efficienza (FO-DS) o dimmerabile (DALI-DS, TD, Casambi) - accensione separata. **Alimentatore:** 230V 50Hz. **Svetlobni vir:** Visoko svetilen LED trak, CRI>90, barvno odstopanje MacAdam≤2, 50.000 h L90 B10 na 35 °C. **Optika:** Satiniran opalni polikarbonatni difuzor (SOP). **Ohišje:** Aluminijasta kupola, prašno barvana. Obod iz umetnega usnja. **Stropna rozeta:** Za viseče verzije se rozete in vešala naročajo posebej. Več na straneh s tehnično vsebino ali v spletnem konfiguratorju. **Napajnik:** Integriran visoko učinkoviti LED konverter s konstantnim tokom (FO-DS) ali regulacijskim izhodom (DALI-DS, TD, Casambi) - ločeno prižiganje. **Napajanje:** 230 V 50 Hz.



Futon

Circles of light

Acoustic. Mirror. O.
Three versions of thin elegance.

Futon comes in three versions. All different all unique all multipurpose. Futon Acoustic is perfect when you want to combine unique ambient lighting, functionality of acoustics and trendy colours. Futon O, a shining ring, makes your walls shine in a different way, while Futon Mirror is a mirror and a lamp all-in-one. Alone or in a creative composition, Futon gives its best.

Acoustic. Mirror. O. Tre versioni diverse della stessa sottile eleganza.

Futon è disponibile in tre versioni. Tutte diverse, tutte uniche, tutte multiuso. Futon Acoustic è perfetto quando si desidera combinare un'illuminazione unica degli ambienti, le funzionalità dell'acustica e i colori di tendenza. Futon O è un anello scintillante che fa risplendere le tue pareti in modo diverso, mentre Futon Mirror è sia uno specchio che una lampada. Da solo o in una composizione creativa, Futon offre sempre il meglio di sé.

Acoustic. Mirror. O. Tri različice prefinjene elegancije.

Futon je na voljo v treh različicah. Vse drugačne, vse edinstvene, vse večnamenske. Futon Acoustic je prava izbira, ko želite kombinirati ambientalno svetlobo s funkcionalnostjo akustičnega absorberja in modnimi barvami. Futon O je sijoč obroč, s katerim bo vaša stena zasijala na različne načine. Futon Mirror pa je svetilka in ogledalo v enem. Futon vedno dobro izpade. Najsibo samostojno najsibo v domiselnih kombinacijah.





33

Daste Bistrò, Bergamo, Italy / Architecture: Okam Studio and Daniele Fazio Studio / Photography: Luca Argenton



Mesner Bistrò, Hafling, Italy / Architecture:Interior Team

34



Brandnamic, Bressanone, Italy / Photography: Brandnamic
Private residence / Interior design: Notio / Visualization: Duaviz



37

Private residence / Visualization: Studio Spacer



Private residence, Slovenia / Interior design & visualization: Studio Spacer

Private residence / Visualization: Studio Spacer



38



MAIN FEATURES





Rich in light effect

The hidden light source illuminates the sound absorbing acoustic panel from the inner edge. Subsiding evenly, it creates a rich glow effect on the fabric.

Maximum acoustic comfort

Futon enables effective soundproofing and sound absorbing in all areas with higher frequencies.



Make it double for a double effect

There will be no acoustic trouble if you choose Futon double. One suspension, but double acoustic fibre or opal diffuser, double light source (on both sides) and most of all double effect.



A mirror? A lamp? Both!

Futon Mirror is a mirror and a lamp all-in-one. The lateral light will illuminate your face and clothes in the best way without any shadows or colour deviations.



No steam on the mirror surface

This version of Futon is ideal for bathrooms, especially those with inadequate ventilation. A special mirror demister warms up the mirror at 30-35°C, a perfect temperature to prevent the mirror surface from the condensation of steam.



Futon


Technical Overview



S
Suspended



C/W
Ceiling / Wall



	Acoustic	SD Acoustic	SD Acoustic	O	Mirror Round	Mirror Oval	Mirror Rectangular
Luminaire luminous flux	510 - 1450 lm	1000 - 1400 lm	1000 - 1400 lm	1010 - 2215 lm	1650 - 2650 lm	2700 - 2950 lm	2550 - 3900 lm
Optic	SOP	SOP	SOP	SOP	SOP	SOP	SOP
LED colour	927, 930, 940	927, 930, 940	927, 930, 940	927, 930, 935, 940	927, 930, 940	927, 930, 940	927, 930, 940
Driver	Casambi, DALI, FO	Casambi, DALI, FO	Casambi, DALI, FO	Casambi, DALI, FO	Casambi, DALI, FO	Casambi, DALI, FO	Casambi, DALI, FO
Driver position	Remote	Ceiling cup / Remote	Ceiling cup / Remote	Ceiling cup / Remote	Remote	Remote	Remote
Material	RecycLED ISOPEL acoustic panel	RecycLED ISOPEL acoustic panel	SOP (Satin opal diffuser)	-	Mirror	Mirror	Mirror
IP Protection	IP40	IP40	IP40	IP40	IP44	IP44	IP44
Sound absorbing surface	0,6 / 2,4 m ² (S), 0,3 / 1,2 m ² (C/W)	0,6	-	-	-	-	-
Colour	B D J	B D J	B D J	B D J	B D H F Y	B D H F Y	B D H F Y
Textile colour	Grey, Blue, Green	Grey, Blue, Green	-	-	-	-	-

Dimensions	D (mm): 611, 1216 SH (mm): 1500, 3000, 5000	D (mm): 611 SH Rod (mm): 500 - 2000 SH Suspension set (mm): 1500, 3000, 5000	D (mm): 611 SH Rod (mm): 500 - 2000 SH Suspension set (mm): 1500, 3000, 5000	D (mm): 611, 1216 SH Suspension set (mm): 1500, 3000, 5000	D (mm): 611, 900	H (mm): 906, 1506




Light source: High-flux LED strip, CRI>90, MacAdam<2, 50000h L90 B10 at 35°C.
Optic: Satin opal polycarbonate diffuser (SOP). **Body:** Extruded aluminium profile, powder coated with acoustic panel or satin opal diffuser or mirror plate. **Ceiling cup:** Ceiling cup with or without driver must be ordered separately. **Control gear:** Constant voltage driver - order separately. **Power supply:** 24V DC.

Sorgente: Strip LED High-flux, CRI>90, MacAdam<2, 50.000h L90 B10 a 35°C.
Ottica: Diffusore in policarbonato opale satinato (SOP). **Corpo:** Profilo in alluminio estruso, verniciatura a polvere con pannello acustico o schermo opale satinato o specchio. **Rosone:** Rosone con o senza alimentatore da ordinare separatamente. **Alimentazione:** Alimentatore a tensione costante - ordinare separatamente. **Alimentatore:** 24V DC.



Svetlobni vir: Visoko svetilen LED trak, CRI>90, barvno odstopanje MacAdam<2, 50.000 h L90 B10 na 35 °C. **Optika:** Satiniran opalni polikarbonatni difuzor (SOP). **Ohišje:** Ekstrudiran profil iz aluminija, prašno barvan s centralno ploščo iz akustičnega materiala, satiniranega opalnega difuzorja ali z zrcalom. **Stropna rozeta:** Stropno rozeto z ali brez LED konverterja je treba naročiti ločeno. **Napajalnik:** LED konverter s konstantno napetostjo - ločeno naročanje. **Napajanje:** 24 V DC.



Lysabel

A saber of light

Finally, you can have the lightsaber you always wanted


Finalmente potrai avere la spada laser che hai sempre desiderato

Končno si lahko priskrbite svetlobni meč, ki ste si ga vedno želeli

Lysabel will always bring a touch of sophistication to your space, whether vertical, horizontal, inclined, single or grouped in different creative compositions. It is a slender homogeneously lit tube without shadows. Its look is clean, minimalist and refined, with every last detail carefully crafted. Looks fragile, but it's not. Its force is versatile – for the power of light and of appearance.

Lysabel riesce a donare un tocco di raffinatezza agli ambienti, sia in posizione verticale che orizzontale o inclinata, da sola o in gruppo, per dare origine a diverse composizioni che sprizzano creatività. Si tratta di un tubo sottile illuminato in maniera uniforme, senza ombre. Le sue linee sono pulite, minimaliste ed eleganti: ogni suo minimo dettaglio nasce da un'attenta lavorazione. Può sembrare fragile, ma non lo è. La sua forza consiste nella versatilità: una fusione tra potere ed estetica della luce.

Lysabel bo v vaš prostor vedno prinesla kanček prefinjenosti, naj bo v navpični, vodoravni, nagnjeni postavitvi, samostojna ali v različnih kreativnih kompozicijah. Je vitka homogeno osvetljena cev brez senc. Njen videz je čist, minimalističen in prefinjen ter vključuje skrbno oblikovane detajle. IzgLEDa krhka, vendar ni. Zaradi svetlobe in videza je njena moč vsestranska.






45

Hotel lobby, Dubai, UAE / Visualization: Render Atelier



Fabiani Business Hotel, Vienna, Austria / Architecture: AKSL arhitekti / Visualization: Studio Spacer

46



**One product,
different looks**


The different inclination of single tubes totally changes the product's appearance. Set it the way you like it, and change it over time. It will be like having a new luminaire.





Lysabel



Technical Overview



MAIN FEATURES


Always slim in different lengths

Lysabel is available in different sizes. Combine them and create elegant compositions.



It is also beautiful in horizontally

It can be wholly horizontal or a little inclined with a simple suspension ring. The ring also functions as an aesthetic accessory.




Light source: High-flux LED strip, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C. **Optic:** Satin opal polycarbonate diffuser (SOP). **Body:** Aluminium, powder or PVD coated. **Ceiling cup:** Ceiling cup with or without driver must be ordered separately. **Control gear:** Constant voltage driver - order separately. **Power supply:** 24V DC.

Sorgente: Strip LED High-flux, CRI>90, MacAdam≤2, 50.000h L70 B10 a 35°C. **Ottica:** Diffusore in policarbonato opale satinato (SOP). **Corpo:** Alluminio, verniciato a polvere o PVD. **Rosone:** Rosone con o senza alimentatore da ordinare separatamente. **Alimentazione:** Alimentatore a tensione costante - ordinare separatamente. **Alimentatore:** 24V DC.

Svetlobni vir: Visoko svetilen LED trak, CRI>90, barvno odstopanje MacAdam≤2, 50.000 h L90 B10 na 35 °C. **Optika:** Satiniran opalni polikarbonatni difuzor (SOP). **Ohišje:** Aluminij, prašno ali PVD barvano. **Stropna rozeta:** Stropno rozeto z ali brez LED konverterja je potrebno naročiti ločeno. **Napajalnik:** LED konverter s konstantno napetostjo - ločeno naročanje. **Napajanje:** 24 V DC.





Issa

Miss impact

Big open spaces deserve to be arranged with style

Issa is an opal tube that shines along the entire length. One diameter and a variety of sizes allow lots of creativity in compositions.

It brings a general illumination to big open spaces, staircases and halls, with a touch of elegance. Due to its smooth milky surface and important size it stands out like a decorative element also when off.

Stile e design per i grandi open space


Issa è un tubo opalino che si illumina in tutta la sua lunghezza. Massima creatività delle composizioni, grazie all'unico diametro e all'ampia varietà di lunghezze.


Per l'illuminazione completa di grandi open space, scale e hall. Grazie alla superficie liscia bianco latte e alle dimensioni importanti, costituisce un elemento decorativo che si distingue anche a luce spenta.

Veliki odprtih prostorov si zaslužijo, da jih uredimo s slogom

Issa je opalna cev, ki sije po celotni dolžini. Enoten premer in različne velikosti omogočajo veliko ustvarjalnosti pri kompozicijah.

Primerena je za splošno osvetlitev velikih odprtih prostorov, stopnišč in hodnikov s pridihom eleganc. Zaradi gladke mlečne površine in velikosti izstopa kot dekorativni element, tudi ko ni prižgana.





53

Private office, USA / Visualization: Studio Spacer



54

**MAIN FEATURES****It can be inclined on purpose**

Adjust the suspension height the way you prefer Issa to be suspended. In line, completely vertically or a little inclined.

The maximal inclination angle is 60°.

**Vertically or horizontally**

Or both. Mix and match different products the way you want.



Issa

Technical Overview



Different lengths

Issa is available in different sizes. The combination of them creates a composition which adds an artistic touch to the ambience.



With or without a spot

It depends on the intensity of light you want to achieve whether to choose a spot or not. Do you prefer Issa to shine vividly or to glow softly?




Play with colours

Milky or tunable white is always a good choice. But sometimes, the RGB option gives an added value when creating a playful and dynamic atmosphere.



S H Suspended horizontal	S V Suspended vertical	S VS Suspended vertical with spot
Luminaire luminous flux	760 - 4900 lm 1460 lm/m	760 - 5900 lm 1460 lm/m
Optic	SOP	SOP
LED colour	927, 930, 935, 940	927, 930, 935, 940
Dynamic illumination	RGB, Tunable white 2700-6500K	RGB, Tunable white 2700-6500K
Driver	Casambi, DALI, FO	Casambi, DALI, FO
Driver position	Ceiling cup, remote	Ceiling cup, remote
Spot information		
Luminaire luminous flux	-	-
Beam angle	-	-
LED colour	-	-



Light source: High-flux LED strip, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C.; High-power COB LED, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C.; RGB LED strip optional. **Optic:** Satin opal polycarbonate diffuser (SOP) **Body:** Polycarbonate. **Ceiling cup:** Ceiling cup with or without driver must be ordered separately. **Control gear:** Driver must be ordered separately. **Power supply:** 24V DC/125mA.

Sorgente: Strip LED High-flux, CRI>90, MacAdam≤2, 50.000h L90 B10 a 35°C.; COB LED High-power, CRI>90, MacAdam≤2, 50.000h L90 B10 a 35°C.; strip LED RGB opzionale. **Ottica:** Diffusore in policarbonato opale satinato (SOP) **Corpo:** Policarbonato. **Rosone:** Rosone con o senza alimentatore da ordinare separatamente. **Alimentazione:** Alimentatore da ordinare separatamente. **Alimentatore:** 24V DC/125mA.

Svetlobni vir: Visoko svetilen LED trak, CRI>90, barvno odstopanje MacAdam≤2, 50.000 h L90 B10 na 35 °C.; Visoko učinkovit COB LED modul, CRI>90, barvno odstopanje MacAdam≤2, 50.000 h L90 B10 na 35 °C.; RGB LED trak opcijsko. **Optika:** Satiniran opalni polikarbonatni difuzor (SOP) **Ohišje:** Polikarbonat. **Stropna rozeta:** Stropno rozeto z ali brez LED konverterja je treba naročiti ločeno. **Napajalnik:** LED konverter je treba naročiti ločeno. **Napajanje:** 24 V DC/125 mA.



Gramm

The lightest light

Feather lightness in the space

Leggera come piuma nello spazio

Peresna lahkoostnost v prostoru

Gramm is elegant and focused, meant to enlighten only what is needed. It is round-shaped, and its main feature is the possibility of rotation which allows a lot of flexibility. When you want a pleasant indirect light, you simply rotate it up with one move.


A name, a guarantee. Gramm will always bring a feeling of feather lightness to the space. Because Gramm is light, period.

Gramm è elegante e funzionale, per illuminare solo laddove è necessario. La caratteristica distintiva, definita dalla forma rotonda, è la sua possibilità di rotazione. Per ottenere una luce indiretta e più gradevole, basta ruotarla verso l'alto con un solo gesto, e poi nuovamente verso il basso.

Un nome, una garanzia. Gramm porterà sempre nello spazio una sensazione di leggerezza, come una piuma. Perché Gramm è leggerezza, e questo basta.

Gramm je elegantna svetilka, ki usmerjeno osvetljuje le, kar je potrebno. Je okrogle oblike, njena glavna prednost pa je možnost vrtenja, ki omogoča veliko prilagodljivosti. Ko želite prijetno indirektno svetlubo, jo preprosto zavrtite z enim gibom navzgor.

Gramm. Ime, ki pove vse. V prostor bo ta svetilka vedno prinesla občutek peresne lahkoosti. Ker je preprosto lahka.





Private residence, Italy / Visualisation: Render Atelier
Q Electronics / Visualisation: Render Atelier



Soft ambient light



This slim luminaire brings elegance and softness with both its looks and light. The optic offers a pleasant illumination with low glare, perfect for all situations when you don't need a classic office lighting.



Just rotate it for indirect light

You rotate it up with one move when you want a pleasant indirect light. This is its great advantage.

	S LGO Suspended low glare linear grid optic	S SOP Suspended satin opal diffuser	S DUO Suspended double
Luminaire luminous flux	210 lm/m	681 lm/m	122 - 1228 lm
Optic	LGO	SOP	SOP, LGO
LED colour	927, 930, 940	927, 930, 940	927, 930, 935, 940
Driver	Casambi, DALI, FO	Casambi, DALI, FO	Casambi, DALI, FO
Driver position	Ceiling cup, remote	Ceiling cup, remote	Ceiling cup, remote
Colour			
Dimensions	L (mm): 560 - 1660 SH (mm): 500 - 2000	L (mm): 560 - 1660 SH (mm): 500 - 2000	L (mm): 560 - 1660 SH (mm): 1000 - 2000



Light source: High-flux LED strip, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C. **Optic:** Satin opal polycarbonate diffuser (SOP). Low glare linear grid optic (LGO). **Body:** Extruded aluminium profile, powder coated. **Ceiling cup:** Ceiling cup with or without driver must be ordered separately. **Control gear:** Constant voltage driver - order separately. **Power supply:** 24V DC.

Sorgente: Strip LED High-flux, CRI>90, MacAdam≤2, 50.000h L90 B10 a 35 °C. **Ottica:** Diffusore in policarbonato opale satinato (SOP). Ottica con griglia lineare a basso abbagliamento (LGO). **Corpo:** Profilo in alluminio estruso, verniciatura a polvere. **Rosone:** Rosone con o senza alimentatore da ordinare separatamente. **Alimentazione:** Alimentatore a tensione costante - ordinare separatamente. **Alimentatore:** 24V DC.

Svetlobni vir: Visoko svetilen LED trak, CRI>90, barvno odstopanje MacAdam≤2, 50.000 h L90 B10 na 35 °C. **Optika:** Satiniran opalni polikarbonatni difuzor (SOP). Linearna optična rešetka z omejenim bleščanjem (LGO). **Ohišje:** Ekstrudiran profil iz aluminija, prašno barvan. **Stropna rozeta:** Stropno rozeto z ali brez LED konverterja je potreben naročiti ločeno. **Napajalnik:** LED konverter s konstantno napetostjo - ločeno naročanje. **Napajanje:** 24 V DC.





Rylo Pro

Office first

Your best office buddy

Whether it is suspended, recessed or floor, Rylo Pro is mostly intended for offices – for single ones, open spaces and conference rooms, offering illumination with no glare, high visual comfort and wellbeing.

The floor version of Rylo Pro is really practical: no installation needed, just plug-in and start. It is easy to move from one workstation to another.

Il tuo collega migliore


Rylo Pro è pensato essenzialmente per l'ufficio: per spazi singoli, open space e sale conferenze. Può essere collocato in sospensione, incassato o a pavimento, per diffondere sempre una luce non abbagliante, per il massimo benessere e comfort visivo.

Nella versione da terra, Rylo Pro è una soluzione praticissima, che non richiede installazione. Si inserisce la spina e ci si mette al lavoro. Si trasferisce facilmente da una postazione di lavoro ad un'altra.

Vaš najboljši pisarniški kolega

Ne gLEDete na to, ali je viseča, vgradna ali talna, je svetilka Rylo Pro večinoma namenjena pisarnam – individualnim, skupnim in konferenčnim sobam. Ponuja osvetljenost brez bleščanja, visoko vizualno udobje in dobro počutje.

Talna različica Rylo Pro je resnično praktična: montaža ni potrebna, samo vključite jo in prižgete. Premikanje z ene delovne postaje na drugo je preprosto.






67

Private office / Visualisation: Studio Spacer



68



Private office, Germany / Visualisation: Studio Spacer



69

Private office, Ljubljana, Slovenia / Visualisation: Studio Spacer



Private office / Visualisation: Studio Spacer


70

UGR
<19**MAIN FEATURES****Wide family range**

The family range is wide – from single modules to linear systems, and also T forms for double desks.


**No glare,
light comfort**

Inappropriate lighting causes headaches and eye trouble. Create a healthier working environment with lighting which affects our well-being, mood and concentration. With indirect illumination you can create a softer light environment.

UGR
<16

Advanced sensor - wireless presence and daylight sensor communicate with other luminaires in order to keep all indirect on when presence of people are detected by single luminaire.

IQ sensor - the luminaire switch on automatically due to presence and dim to desired light level depending on daylight.



Rylo Pro

Technical Overview



 Single*
// Line

 Single*
// Line

 Single*
// Line

 Single*
// Line





RI	RV	C/S	SDI
Recessed trimm-less	Recessed visible trim	Ceiling / Suspended	Suspended direct-indirect

Glare control (UGR class)	UGR<19	UGR<19	UGR<19	UGR<19	UGR<19	UGR<16	UGR<16
Luminaire luminous flux	34 - 167 lm/spot	1700 lm + 3600 lm for LED colour 930	3400 lm + 7200 lm for LED colour 930				
Number of spots	8+8, 16+16	8+8, 16+16	8+8, 16+16	8+8, 16+16	8+8, 16+16	32	32+32
Light distribution	Direct	Direct	Direct	Direct / Indirect	Direct, Direct / Indirect	Direct / Indirect	Direct / Indirect
Optics	50°, Asymmetric	50°	50°				
LED colour	927, 930, 935, 940	927, 930, 935, 940	927, 930, 935, 940	927, 930, 935, 940	927, 930, 935, 940	927, 930, 935, 940	927, 930, 935, 940
Driver	Casambi, DALI, FO, IQ sensor	Casambi, FO, IQ sensor, TD	Casambi, FO, IQ sensor, TD				
Driver position	Integrated	Integrated	Integrated	Integrated	Ceiling cup	Integrated	Integrated

Colour	 	 	See the colour options below	See the colour options below	 	
--------	---	---	------------------------------	------------------------------	---	---

Dimensions	L (mm): 1682 - 3082	L (mm): 1682 - 3082	L (mm): 1682 - 3082	L (mm): 1962 - 3082 SH (mm): 1500, 3000, 5000	L (mm): 1125 - 2805 SH (mm): 1500, 3000, 5000		
------------	---------------------	---------------------	---------------------	--	--	--	--



For C/S, SDI, S/SDI versions, the optical funnel and blind module colour are always black (except with the white version). *Single module is possible by adding end caps to the Line module.



Standard: Special colours:

Light source: High-flux PCB LED modules, mid-power SMD LED, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C. / High-power LED, CRI>90, MacAdam≤2, 50.000h L80 B10 at 35°C. **Optic:** Low glare spot optical system with UGR<19. Satin opal polycarbonate diffuser (SOP) for indirect light. **Body:** Extruded aluminium profile, powder coated. **Control gear:** Integrated highly-efficient driver with fixed output (FO) or dimmable (DALI-TD, Casambi). Optional separate switching for direct / indirect versions. **Power supply:** 230V 50Hz.

Sorgente: Moduli PCB LED High-flux, SMD LED mid-power, CRI>90, MacAdam≤2, 50.000h L90 B10 a 35 °C. / High-power COB LED, CRI>90, MacAdam≤2, 50.000h L80 B10 a 35 °C. **Ottica:** Sistema ottico spot a basso abbagliamento con UGR<19. Schermo opale satinato in policarbonato (SOP) per luce indiretta.. **Corpo:** Profilo in alluminio estruso, verniciatura a polvere. **Alimentazione:** Alimentatore ad alta efficienza on/off (FO) o dimmerabile (DALI-TD, Casambi) integrato . Accensione separata opzionale per la versione luce diretta / indiretta. **Alimentatore:** 230V 50Hz.

Svetlobni vir: High-flux PCB LED moduli, z SMD LED, CRI>90, MacAdam≤2, 50.000 h L90 B10 na 35 °C. / Visoko učinkovit COB LED modul, CRI>90, barvno odstopanje MacAdam≤2, 50.000 h L80 B10 na 35 °C. **Optika:** Reflektorski optični sistem z omejenim bleščanjem UGR<19. Opalni polikarbonatni difuzor (SOP) za indirektno osvetlitev. **Ohišje:** Ekstrudiran profil iz aluminija, prašno barvan. **Napajalnik:** Integriran visoko učinkoviti LED konverter s konstantnim tokom (FO) ali regulacijskim izhodom (DALI-TD, Casambi). Opcionalno ločeno prižiganje direktno / indirektno komponente. **Napajanje:** 230 V 50 Hz.



Lynar

It's your move

Sweet home for light modules

Lynar is an elegant, endless modular profile that offers maximum flexibility.

The choice of modules is wide and the installation is tool-free, simple, fast and safe. Combine them the way you want and change or move at anytime.

It covers a wide range of use - from office, galleries, retail, hospitality to private residences.

L'accoglienza chiede modularità di luce

Lynar è un profilo modulare elegante e infinito che offre soluzioni di massima flessibilità.

L'ampia scelta dei moduli è accompagnata da modalità di installazione rapide e sicure, di una facilità che non richiede utensili. I moduli sono liberamente combinabili e possono sempre essere cambiati o riposizionati.



Ampia la gamma delle applicazioni: dagli uffici alle gallerie d'arte, dai negozi alle strutture ricettive ma anche alle abitazioni.


Varno zavetje svetilnih modulov

Lynar je eleganten, neskončen modularni profil, ki nudi maksimalno fleksibilnost.

Izbira modulov je bogata, montaža pa je možna brez orodja, je enostavna, hitra in varna. Kombinirajte jih tako, kot želite, in jih kadarkoli spremenite ali premaknite.

Zajema širok nabor uporabe – od pisarne, galerij, trgovin, gostinstva do zasebnih bivališč.







Hotel Feel Good / Architecture: AKSL arhitekti / Visualisation: Studio Spacer
Private office / Visualisation: Studio Spacer



Private residence / Visualisation: Render Atelier
Private residence / Visualisation: Studio Spacer






Quick installation

The installation of modules is simple, fast and safe. The products are fixed with a mechanical coupling that ensures a reliable and lifelong grip.



Light line

Choose Kalis inset for general illumination. It can turn out very well in a composition as an interesting graphic element.




Keep on moving

Get the maximum flexibility of adjusting the light in the space. Not just the first time, but anytime. Repositioning the modules has never been easier.


Internal or external power supply

Depending on the desired visual effect and profile installation type, the power supply can be positioned inside the profile, externally in the ceiling cup or remotely.





	RI Recessed trim-less	RV Recessed visible trim	C/S Ceiling / Suspended	SDI Suspended Direct / Indirect
Indirect luminaire luminous flux/m	-	-	-	990 lm/m (DALI)
LED colour	-	-	-	827, 830, 835, 840, 930, 940
Electrical connection	48Vdc (not included, order separately)			
Colour	D	2	1 2 3 6 9 +	1 2 3 6 9 +



* The inner part of the profile is always black



Linear extruded aluminium profile system with integrated 48V track. Indirect light option with SOP diffuser. Wide range of light insets (linear, spot, pendant). Power supply can be mounted remotely (PSE) or inside the profile (PSI).

Sistema lineare in alluminio estruso con binario 48V integrato. Disponibile con luce indiretta con schermo SOP. Ampia gamma di lampade installabili (lineari, spot, pendenti). Il trasformatore può essere installato remoto (PSE) o all'interno del profilo (PSI).

Linijski sistem iz ekstrudiranega aluminijskega profila z vgrajeno 48 V tračnico. Možnost indirektno osvetlitve z opalnim difuzorjem vzdolž sistema. Širok nabor svetlobnih elementov (linearni, reflektorski, viseči). Napajalni modul je lahko montiran v sam profil (PSI) ali pa izven njega (PSE).

Spot insets



Atos LYN

Luminaire luminous flux: Up to 2x 458 - 555 lm
Beam angle: 26 mm (18°, 25°), 32 mm (20°, 30°, 50°), 45 mm (30°, 59°, 28-46°)
LED colour: 827, 830, 840, 927, 930, 935, 940
Spots: 1x / 2x
Driver: DALI
Diameter: 26, 32, 45 mm



Eye LYN

Luminaire luminous flux: Up to 1400 lm
Beam angle: 10°, 22°, 26°, 30°, 45°, 46°, 22 - 45°
LED colour: 927, 930, 935, 940
Driver: DALI
Diameter: 60 mm

Pendant insets



Biba LYN

Luminaire luminous flux: Up to 936 lm
Beam angle: 42°, 62°
LED colour: 830, 840, 927, 930, 935, 940
Driver: DALI
Diameter: 75 mm



Pipes 45 S LYN

Luminaire luminous flux: Up to 1300 lm
Beam angle: 42°, 62°
LED colour: 830, 840, 927, 930, 935, 940
Driver: DALI
Diameter: 45 mm



Pixy LYN

Luminaire luminous flux: Up to 3100 lm
Beam angle: 30°, 50°
LED colour: 830, 840, 927, 930, 935, 940
Driver: DALI
Diameter: 75 mm



Zoe LYN

Luminaire luminous flux: Up to 1481 lm, 12W
LED colour: 830, 840, 927, 930, 935, 940
Driver: DALI

Linear insets



Kalis 36 LYN

Luminaire luminous flux: Up to 1600lm
Module length: 285 mm - 1405 mm
Optic: SOP, DPR
LED colour: 827, 830, 835, 840, 930, 940
Driver: DALI



Rylo LYN WW

Luminaire luminous flux: 995 - 1094 lm
Module length: 105 - 285 mm (4x, 8x, 12x spot)
LED colour: 927, 930, 940
Driver: DALI



Vertical and horizontal corner

90° (both) and 135° (horizontal)
Integrated PWR connection module
Dimension: 50x50 mm

Power supply



PSE - power supply external

PWR supply position: Integrated in the ceiling cup
PWR supply type: 48V constant voltage driver



PSI - power supply internal

PWR supply position: Integrated in the profile inset
PWR supply type: 48V constant voltage driver



LiY

Maximally minimal

Pure light effect

LiY is perfect for elegant spaces where you just can't have an ordinary spot. Its main advantage is the appearance of pure light without any source glare. It is minimalist. Imagine, the opening on the bottom of the funnel is only 8 mm wide. Then, it depends on the housing colour whether you want the whole luminaire to stand out or to completely blend in.

LiY can perform as a single spot, in a pair, or in a row of three, four or more. It can be fixed or flexible, allowing to change the beam angle and orientation, always having visual attention on the object.

La purezza della luce

LiY è la soluzione perfetta per quegli spazi eleganti in cui non ci si può accontentare di un'illuminazione comune. Il suo vantaggio principale risiede nel suo aspetto di luce pura, senza alcun tipo di abbagliamento. La sua forza è nel minimalismo: l'apertura nella parte inferiore del corpo lampada ha un'ampiezza di soli 8 mm. A seconda dello stile dell'ambiente si può decidere se fare risaltare l'intera lampada o se fonderla completamente con l'ambiente.

LiY si presta come punto luce singolo oppure può essere utilizzata in coppia o anche in una fila di tre, quattro o più punti luce. Può rimanere in posizione fissa o mobile, permettendo di modificare l'angolo e l'orientamento del fascio, concentrando sempre l'attenzione sull'oggetto.


Čisti svetlobni učinek

LiY je kot nalač za elegantne prostore, v katerih navadnega reflektorja preprosto ne morete imeti. Njegova glavna prednost je čista svetloba brez bleščanja svetlobnega vira. Je minimalistična. Predstavljajte si, da je odprtina na dnu lijaka široka le 8 mm. Od barve ohišja je odvisno, ali želite, da celotna svetilka izstopa ali se popolnoma neopazno zlije s stropom.

LiY lahko prostor osvetljuje samostojno, v paru ali v vrsti treh, štirih ali več reflektorjev. Lahko je fiksna ali fleksibilna, kar omogoča spreminjanje kota in usmerjenosti žarka ter ohranja vizualno pozornost na predmetu.



The product has a custom colour.



89

Lake villa, Italy / Visualisation: Studio Spacer



Private residence / Visualisation: Studio Spacer

90



MAIN FEATURES




Double rotation and clean looks

With a simple gesture you can change both, the direction and the inclination angle of the light. In a row of spotlights, you can set each spot individually. And then change it when needed.

Trim-less installation

For a precise and clean trim-less installation of two or three spots in a row, you can use the installation kit. In this case the "only light" effect is even greater.







OPTICS

LFO - A guarantee of maximum visual comfort

Due to special design of Bartenbach LFO optic, all you can see is pure light. The light source is hidden deep inside the optics offering high visual comfort.

**No double ring**

With the Bartenbach LFO optic the light circle is well-defined and homogeneous. At the limits the light intensity is still high.


**RI**
Recessed trim-less**RV**
Recessed visible trim**F**
Fixed

Beam angle	LFO 33°, 50°
Orientation	-
Luminaire luminous flux*	up to 190 lm / spot
LED colour	927, 930, 935, 940
Driver	Casambi, DALI, FO
Driver position	Remote
IP protection**	IP44
Funnel colour	2 H F Y
Frame colour	2

A
Adjustable

Beam angle	LFO 33°, 50°
Orientation	25° / 360°
Luminaire luminous flux*	up to 190 lm / spot
LED colour	927, 930, 935, 940
Driver	Casambi, DALI, FO
Driver position	Remote
IP protection**	IP44
Funnel colour	1 2 H F Y
Frame colour	1 2

Dimensions



* The data refer to one spot. Multiply the number with the number of spots. ** IP value from the exposed side.



GRO




Light source: High-power LED, CRI>90, MacAdam≤2,5, 50.000h L80 B10 at 35°C. **Optic:** Acrylic glare-free LFO lens. **Body:** Polycarbonate. Optional with metallized coating. **Control gear:** Constant current driver - order separately. **Power supply:** 500 - 800 mA.

Sorgente: High-power COB LED, CRI>90, MacAdam≤2,5, 50.000h L80 B10 at 35°C. **Ottica:** Lente acrilica glare-free LFO. **Coppo:** Policarbonato. Opzionale con rivestimento metallizzato. **Alimentazione:** Alimentatore a corrente costante - ordinare separatamente. **Alimentatore:** 500 - 800 mA.

Svetlobni vir: Visoko učinkovit COB LED modul, CRI>90, barvno odstopanje MacAdam≤2,5, 50.000h L80 B10 na 35°C. **Optika:** Akrilna LFO leča brez bleščanja. **Ohišje:** Polikarbonat. Opcijsko z metallizirano prevleko. **Napajalnik:** LED konverter s konstantnim tokom - ločeno naročanje. **Napajanje:** 500 - 800 mA.





Conic

An iconic spot

No need to putty at all

When you want a spot on a higher level, choose Conic. It's distinguished by prestigious finishes, wide range of colours and clean looks.

Most of all, Conic stands out for its innovative, easy and clean installation in a finished plaster ceilings, with tools of standard sizes and no puttying.

Non rimarrai di stucco

Se vuoi un faretto spot di livello superiore, c'è Conic. Ha finiture di pregio, una vasta gamma di colori e un aspetto semplice.

Ma soprattutto prevede una soluzione di installazione innovativa, semplice e pulita, per controsoffitti in gesso con l'utilizzo di strumenti standard senza dover stuccare.

Pozabite na kitanje

Ko želite reflektor višjega ranga, izberite Conic. Odlikujejo ga prestižni premazi, široka paleta barv in čist videz.

Predvsem pa Conic izstopa po svoji inovativni, enostavni in čisti vgradnji v mavčne strope z orodjem standardnih velikosti in brez izravnave površin s kitanjem.






Prestigious look with trendy colours

The interior of the funnel can be gold, bronze or onyx coated which gives a luminaire prestigious look. Gold & bronze are on trend, but at the same time timeless chic finishes, perfect to match all kinds of interiors.

IP44


It's the perfect solution for high moisture environments like bathrooms. It offers pleasant and functional light as well as IP44 protection.





Conic

Technical Overview



RI kit for installation
without puttying

REVOLUTIONARY TRIM-LESS INSTALLATION



Make a hole with a standard
80 mm hole saw



Paint the ceiling, no puttying
needed




Twist and level the RI kit with
the ceiling




Click in the spot and the funnel

ADJUSTABLE (A)



FIXED (F)



RI

Recessed trim-less

Beam angle

20°, 30°, 55°

Orientation

25° / 360° (A)

Luminaire luminous flux

540 - 970 lm

LED colour

927, 930, 935, 940

Dynamic light

Dim to warm (D2W)**

Driver

Casambi, DALI, FO

Driver position

Remote

IP protection*

IP44

RI kit / Frame colour

Inner colour

RV

Recessed visible trim

20°, 30°, 55°

25° / 360° (A)

540 - 970 lm

927, 930, 935, 940





Dim to warm (D2W)**

Casambi, DALI, FO

Remote

IP44

Dimensions



*IP value from the exposed side. **Dim to warm is possible on 55°beam angle.



≥ 85 %



D2W



GR0



CASAMBI



Light source: High-power COB LED, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C. **Optic:** Highly efficient with uniform distribution, metallized polycarbonate with lacquer finish. **Body:** Polycarbonate. Optional with metallized coating. **Control gear:** Constant current driver - order separately. **Power supply:** 150 - 900 mA.

Sorgente: High-power COB LED, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C. **Ottica:** Ottica ad alta efficienza con distribuzione uniforme, policarbonato metallizzato tramite laccatura. **Corpo:** Policarbonato. Optional con rivestimento metallizzato. **Alimentazione:** Alimentatore a corrente costante - ordinare separatamente. **Alimentatore:** 150 - 900 mA.

Svetlobni vir: Visoko učinkovit COB LED modul, CRI>90, barvno odstopanje MacAdam≤2, 50.000 h L90 B10 na 35 °C. **Optika:** Visoko učinkovit metaliziran in lakiran polikarbonat z enakomerno porazdelitvijo svetlobnega snopa. **Ohišje:** Polikarbonat. Opcijsko z metalizirano prevleko. **Napajalnik:** LED konverter s konstantnim tokom - ločeno naročanje. **Napajanje:** 150 - 900 mA.



7
YEAR
WARRANTY



CE



E22



Rylo

Extraordinary light comfort

If you don't want to see where the light comes from, this is the solution

Rylo is not a common downlight. With its special optics it provides high visual comfort and generates circular light emission.

It doesn't show off. The light source is hidden and all you can see is pure light with absolutely no glare. It is universal, perfect for all spaces and projects.

Se non vuoi vedere da dove proviene la luce, questa è la soluzione

Rylo non è un normale faretto a luce diffusa. Le speciali soluzioni ottiche generano un'emissione luminosa spot per un elevato comfort visivo.


Non vuole certo mettersi in mostra. La fonte luminosa rimane nascosta e quello che si vede è pura luce senza abbagliamento. Perfetto per tutti gli spazi e progetti.

Če ne želite videti, od kod prihaja svetloba, je to rešitev

Rylo ni običajen reflektor. S svojo posebno optiko zagotavlja veliko vizualno udobje in ustvarja krožno oddajanje svetlobe.

Se ne izpostavlja. Vir svetlobe je skrit in vse, kar lahko vidite, je čista svetloba popolnoma brez bleščanja. Je univerzalen, primeren za vse prostore in projekte.





B&W law office, Ljubljana, Slovenia / Interior design: AKSL arhitekti / Visualisation: Studio Spacer
103
Private residence, Italy / Visualisation: Render Atelier

Private club, Dubai, UAE / Visualisation: Render Atelier



MAIN FEATURES



Wallwasher Rylo RV WW

Homogenous wall illumination with specific Bartenbach MDB-W wallwash optics.





Great light comfort

Create a healthier environment with lighting which importantly affects our well-being and mood. Rylo provides low glare and offers high light comfort.

Rylo

Technical Overview



MULTISPOT	MULTISPOT	WALLWASHER
Beam angle	22°, 30°, 50°, Asymmetric	22°, 30°, 50°, Asymmetric
Luminaire luminous flux	up to 200 lm/spot	up to 160 lm/spot
Glare control	<19	<19
LED colour	927, 930, 935, 940	927, 930, 935, 940
Driver	Casambi, DALI, FO	Casambi, DALI, FO
Driver position	Remote	Remote / Integrated*
Colour	1 2	1 2

* The driver is integrated only in the Rylo C 10x version.



Light source: High-flux PCB LED modules, mid-power SMD LED, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C. / High-power LED, CRI>90, MacAdam≤2,5, 50.000h L80 B10 at 35°C. **Optic:** Low glare spot optical system with UGR<19, wallwasher. **Body:** Extruded aluminium profile, powder coated. **Control gear:** Constant current driver - order separately. **Power supply:** 250-800mA.

Sorgente: Moduli PCB LED High-flux, SMD LED mid-power, CRI>90, MacAdam≤2, 50.000h L90 B10 a 35°C. / High-power COB LED, CRI>90, MacAdam≤2,5, 50.000h L80 B10 a 35°C. **Ottica:** Sistema ottico spot a basso abbagliamento con UGR<19, wallwasher. **Corpo:** Profilo in alluminio estruso, verniciatura a polvere. **Alimentazione:** Alimentatore a corrente costante - ordinare separatamente. **Alimentatore:** 250-800mA. **Svetlobni vir:** High-flux PCB LED moduli, z SMD LED, CRI>90, MacAdam≤2, 50.000 h L90 B10 na 35 °C. / Visoko učinkovit COB LED modul, CRI>90, barvno odstopanje MacAdam≤2,5, 50.000 h L80 B10 na 35 °C. **Optika:** Reflektorski optični sistem z omejenim bleščanjem UGR<19, wallwasher. **Ohije:** Ekstrudiran profil iz aluminija, prašno barvan. **Napajalnik:** LED konverter s konstantnim tokom - ločeno naročanje. **Napajanje:** 250-800mA.



Eye

Good looking all around

Don't roll your eyes, roll your Eye

Eye, un occhio sul tuo mondo

Ne zavijajte z očmi, zavrtite Eye

There are really a lot of spots out there, but Eye is not just »one more spot«. Come closer. All the details are carefully thought out. Its clean elegant look with the possibility of a 360-degree orientation makes it a perfect luminaire for hospitality, retail and private residences.

Esistono tantissimi faretti spot sul mercato, ma Eye non è come gli altri. Guarda bene. Vedrai che ogni dettaglio è stato studiato con attenzione. Il design pulito ed elegante, orientabile a 360 gradi ne fa una lampada ideale per strutture ricettive, negozi, abitazioni. Usa Eye dove preferisci; grazie all'elevata classe di protezione IP, potrai adottare lo stesso stile sia per gli interni che per gli esterni.

Obstaja res veliko točkovnih svetil, vendar Eye ni zgolj eno izmed njih. Približajte se. Vsi detajli so skrbno premišljeni. Zaradi čistega elegantnega videza z možnostjo 360-stopinske orientacije je popolna svetilka za gostinstvo, maloprodajo in zasebna bivališča.





109

B&W law office, Ljubljana, Slovenia / Interior design: AKSL arhitekti / Visualisation: Studio Spacer



Feel Good Hotel, Valencia, Spain / Interior design: AKSL arhitekti / Visualisation: Studio Spacer

110



Eye

Technical Overview



[Watch video](#)

MAIN FEATURES



Innovative swivel system

Eye is unique for the way it can be rotated in all directions, while the swivel mechanism remains invisible. Three types of optics allow a wide range of use.


Nothing is left to chance

All the details of this product communicate elegance, precision and perfection. Even when seen from the backside. In the track version the driver (FO, DALI or Casambi) is integrated in a track adapter.



C 60	C 80	T 60	T 80
Ceiling	Ceiling	Track	Track

Beam angle	Reflector	34°, 45°	30°, 65°	34°, 45°	30°, 65°
Luminaire luminous flux	up to 1400 lm*	up to 2800 lm	up to 1400 lm	up to 2800 lm	up to 2800 lm
LED colour	927, 930, 935, 940	830, 840, 927, 930 935, 940	927, 930, 935, 940	830, 840, 927, 930 935, 940	830, 840, 927, 930 935, 940
Driver	Casambi, DALI, FO				
Driver position	Remote	Remote	Track adapter	Track adapter	Track adapter
Body colour	See the colour options below				
Inner colour	D Q	D Q	D Q	D Q	D Q



* The data refer to one spot. Multiply the number with the number of spots.

Standard: 1 2 3 9 Special colours:



Light source: High-power COB LED, CRI>80/90, MacAdam≤2, 50.000h L90 B10 at 35°C. **Optic:** Highly efficient with uniform distribution, metalized polycarbonate with lacquer finish / Highly efficient PMMA optical lenses / Acrylic high efficiency lens with adjustable beam angle. **Body:** Aluminium, powder coated. **Control gear:** Integrated highly-efficient driver with fixed output (FO) or dimmable (DALI-TD, Casambi). / Some versions require externally mounted driver - order separately. **Power supply:** 230V 50Hz / 350 - 700mA.

Sorgente: High-power COB LED, CRI>80/90, MacAdam≤2, 50.000h L90 B10 at 35°C. **Ottica:** Ottica ad alta efficienza con distribuzione uniforme, policarbonato metallizzato tramite laccatura (spot, medium, wide) / Lenti in PMMA ad alta efficienza / Lenti acriliche ad alta efficienza con fascio regolabile. **Corpo:** Alluminio, verniciatura a polvere. **Alimentazione:** Alimentatore integrato ad alta efficienza on-off (FO) o dimmerabile (DALI-TD, Casambi). / Alcune versioni richiedono il montaggio del driver esterno - ordinare separatamente. **Alimentatore:** 230V 50Hz / 350 - 700mA.

Svetlobni vir: Visoko učinkovit COB LED modul, CRI>80/90, barvno odstopanje MacAdam≤2, 50.000 h L90 B10 na 35 °C. **Optika:** Visoko učinkovit metaliziran in lakiran polikarbonat z enakomerno porazdelitvijo svetlobnega snopa (ozek, srednji, široki svetlobni snop) / Visoko učinkovite PMMA optične leče (ozek, srednji, eliptični svetlobni snop) / Visoko učinkovite akrilne optične leče z nastavljenim kotom svetlobnega snopa. **Ohišje:** Aluminij, pršeno barvan. **Napajalnik:** Integriran visoko učinkoviti LED konverter s konstantnim tokom (FO) ali regulacijskim izhodom (DALI-TD, Casambi). / Nekatere verzije zahtevajo zunanj LED konverter - naročiti ločeno. **Napajanje:** 230 V 50 Hz / 350 - 700 mA.



BY CHICAGO ATHENAEUM

reddot design award
winner

Pyrymyd

Ec(h)o friendly

No noise. No glare. No pollution.

Non ammette rumori. Non abbaglia. Non
inquina.Brez hrupa. Brez bleščanja. Brez
onesnaževanja.

You can finally forget about those unaesthetic acoustic ceilings. Here is Pyrymyd, an advanced all-in-one product, able to create various scenarios and personalized micro ambiances. Therefore, it is a perfect pick for offices and large open spaces.

Puoi finalmente dire addio agli antiestetici controsoffitti insonorizzati. Ora c'è Pyrymyd, un prodotto avanzato all-in-one, che sa creare nuovi scenari e microambienti personalizzati. La scelta perfetta per gli uffici e i grandi open space.

Končno lahko pozabite na neestetske akustične strope. Tukaj je Pyrymyd, napreden izdelek, ki združuje vse v enem in lahko ustvari različne scenarije in osebno prilagojene mikroambiente. Zato je odlična izbira za pisarne ter velike odprte prostore.

3D ecofriendly acoustic panels are made from 100 % recyclable fibre, in order to guarantee an echo friendly acoustic performance. And above all things, it provides efficient homogeneous light distribution.

I pannelli acustici stampati in 3D sono prodotti con fibra riciclabile al 100%, e assicurano performance acustiche davvero echo-friendly. Ma soprattutto una distribuzione della luce efficace ed omogenea.

3D okolju prijazne akustične plošče so izdelane iz 100 % recikliranih vlaken, da bi zagotovile prijazno akustiko brez odmevanja. Predvsem pa Pyrymyd zagotavlja učinkovito homogeno porazdelitev svetlobe.





115



Private office / Visualisation: Studio Spacer



116




Office with Deco and LFO optic / Visualisation: DSE visualisation







It's a luminaire. It's a ceiling. It improves the acoustics.

Acoustic ceiling with light or vice-versa? No matter how you define it, it solves three problems at once: improves the acoustics, offers high quality illumination with absolutely no glare and replaces the ceiling.



Maximum acoustic comfort

Pyrmyd enables effective soundproofing and sound absorbing in all areas with higher frequencies.




No, it's not off.

Are you wondering where the light comes from? With the Bartenbach LFO optic, Pyrmyd illuminates the space pleasantly with low glare and without seeing the light source. It looks like it is off, but the light will be there.

Three shades from black to grey

It's just a matter of taste and the feeling you want to create. Choose brighter tones for a more fresh, open appearance and optically higher ceilings.


The Grey (GR) Acoustic panel is made from 60% recycled material, while Light Grey (LG) and Black (BL) are made of 28% recycled material.





Pyrymyd

Technical Overview



Random patterns of light

No two layouts are the same, so each ceiling will be different, unique. Choose from different Deco versions or combine them with Pyrymyd Dark.



DECO VERSION




Deco 5



Deco 8



INSTALLATION TYPE



Click-in system with minimal distance between the panels and the ceiling.





Suspended installation with side profile.



LFO	DEC0	DARK
Glare control	UGR<19	-
Optics	LFO 32°	-
Luminaire luminous flux	660 lm	600 - 1600 lm
Nº of spots / panel	4	5, 8
LED colour	927, 930, 935, 940	927, 930, 935, 940
Driver	Casambi, DALI, FO	Casambi, DALI, FO
Driver position	Remote	Remote
Material	Thermoformed acoustic felt	Thermoformed acoustic felt
Sound absorbing surface	0,6 m ²	0,6 m ²
Reaction to fire classification	B – s2, d0	B – s2, d0

Dimensions



Colours:



Light source: High-power COB LED, CRI>90, MacAdam≤2, 50.000h L90 B10 at 35°C. **Optic:** Acrylic glare-free LFO lens / Satined prismatic lens dome for uniform light distribution. **Body:** Thermoformed acoustic felt. **Control gear:** Integrated highly-efficient driver with fixed output (FO) or dimmable (DALI-TD, Casambi).

Sorgente: COB LED High-power, CRI>90, MacAdam≤2, 50.000h L90 B10 a 35 °C.. **Optica:** Lente acrilica glare-free LFO / Lente prismatica satinata a cupola per una distribuzione uniforme della luce. **Corpo:** Feltro acustico termoformato. **Alimentazione:** Alimentatore ad alta efficienza on/off (FO) o dimmerabile (DALI-TD, Casambi) integrato.

Svetlobni vir: Visoko učinkovit COB LED modul, CRI>90, barvno odstopanje MacAdam≤2, 50.000 h L90 B10 na 35 °C. **Optika:** Akrilna LFO leča brez bleščanja / Satinirana prizmatična kupola za enakomerno osvetlitev. **Ohišje:** Termoformirani akustični flis. **Napajalnik:** Integriran visoko učinkoviti LED konverter s konstantnim tokom (FO) ali regulacijskim izhodom (DALI-TD, Casambi).

CONTACT US

Let's work together

Collaboration is the key to success. We have all you need: innovative high-quality products, knowLEDge, immense passion, more than 30-year tradition and experience, excellent staff, outstanding references and great partners. Let's create the future together and make it visible. All visible.

www.intra-lighting.com



Headquarters

Intra lighting d.o.o.
Vrtojvenska cesta 50
5290 Šempeter pri Gorici
Slovenia
T: +386 5 398 44 00
info@intra-lighting.com

Follow us on

Find us on


Sales point

Offices

Benelux
Intra lighting Benelux B.V.
Gildenstraat 26
4143 HS Leerdam
T: +31 345 623 678
E: sales@intra-lighting.nl

Italy
Intra lighting S.r.l.
Via Adelaide Bono Cairoli 30
20127 Milano
T: +39 02 9176 1234 / 42
E: info@intra-lighting.com

Slovenia
Intra lighting d.o.o.
BTC, PTC Diamant
Letališka 5
1000 Ljubljana
T: +386 1 547 65 30
E: info@intra-lighting.com

Follow us on

Bosna and Herzegovina

Intra lighting d.o.o.
Hasana Brkića 30
71000 Sarajevo
T: +387 33 642 841
E: info@intra-lighting.com

North America

Intra lighting US, LLC
227 W 29th Street, 12th Floor
New York, NY 10001
T: 215-918-4199
M: 215-388-1800
E: info.us@intra-lighting.com

United Arab Emirates

Intra lighting Middle East
Office 5WB 241, Building 5WB
Dubai Airport Freezone, Dubai
T: +971 42602089
E: info@intra-lighting.com

Imprint

Design: Intra lighting Text: Intra lighting & I&S Aladin

Intra lighting has the right to change, at any time, the technical aspects of its products or product data without prior notice. The data in this brochure is provided in good faith and only for your information. All information is without engagement, replacing preceding information and can always be modified. No part of this brochure may be copied without the written authorization of Intra lighting.

03/2023

© Intra lighting d.o.o.

