


Fiberdeck®

Never stop innovating





**Reliable products designed to last a long time and protect the environment.
As our natural resources are limited, we need to conserve and recycle them
for future generations.**

Our products are made from 95% recycled plastic waste.

**Forerunners in many fields, we are constantly on the lookout
for new products and solutions to advance sustainability.
products and simplify their use.**

**Fiberdeck®, is a young, dynamic team that shares the same values and favors
collaborative work. Respect for everyone involved is our condition for success.**



DECKING

EXOTICS BOARDS _____	08
VINTAGE BOARDS _____	10
VINTAGE BOARDS _____	12
MANHATTAN BOARDS _____	14
BROOKLYN BOARDS _____	16
COBRA CLIPS & SCREWS _____	18



FENCING

PREMIUM COMPOSITE BOARD _____	22
PREMIUM XL COMPOSITE BOARD _____	24
MODERN COMPOSITE BOARD _____	26
MODERN COMPOSITE VERTICAL BOARD _____	28
OPAL ALUMINUM BOARD _____	30
OPEN ALUMINUM BOARD _____	32
RHOMBUS ALUMINUM BOARD _____	34

HERA DECOR _____	36
PAXOS & LAMIA DECORS _____	38
CRIOS & CLARITY DECORS _____	40
GATES _____	42
CORNER KIT _____	44
POSTS _____	46
ACCESSORIES _____	48




CLADDING

WEO [®] ESSENTIAL _____	50
WEO [®] 35 _____	52
WEO [®] 60 _____	54
EXTERNAL CORNER TRIMS & CLADDING SCREWS _____	56
WEO [®] BRISE-SOLEIL _____	58
REALISATIONS _____	60



A QUALITY RECOGNIZED

Our range is fully compliant with the European Wood Regulations, EUTR. All our composite wood products are FSC-certified®, which you can recognize by the article text and the corresponding logo.



LONG LIFE SERVICE

A 20-year guarantee on products against fungal and insect attack, and on colorfastness and stain resistance.

Insect attack. Enhanced resistance to stains and fading.



EASE OF MAINTENANCE

Clean with a broom and detergent-free water. The protective polyethylene coating ensures the preservation of the natural color, look and feel of our products over time.



BIO-SOURCED PRODUCTS

Our products are made of 95% recycled waste—100% FSC®-certified wood sawdust and used plastics—thus contributing to resource conservation and environmental protection.

INNOVATIVE TOOLS



NEED SAMPLES?

Unsure about choosing between different colors or models?
Order the samples of your choice online, and you'll receive them at your
doorstep in less than 48 hours.

store.felixdistribution.com



ONLINE CONFIGURATORS

Discover our two online configurators to easily design your project,
estimate its cost, and generate a list of required materials.


User-friendly and efficient, they allow you to draw and visualize your future deck
or fence in just a few clicks. Practical tools for a flawless result!

en.mydeckplanner.com

en.myfenceplanner.com




DECKING



TECHNOLOGY IN THE SERVICE OF ELEGANCE

Fiberdeck's know-how is expressed through a range of technologies which, enable us to offer quality products that are unique on the market, both aesthetically pleasing and long-lasting.

Whether you are looking for the modernity of grained wood, the patina of aged wood or the warm nuances of Ipe, Fiberdeck deck boards offer the exceptional performance and durability of co-extruded composite wood.





20
YEARS
WARRANTY
LIMITED RESIDENTIAL


UV RESIST




60%
BIO SOURCED

EXOTICS

Sublimate your deck with EXOTICS boards and their faithful reproduction of the Ipe shades. Its subtle nuances of color are delicately recreated thanks to a unique manufacturing process. The board's fine polychromatic texture perfectly imitates the look of natural wood.


Coextrusion technology protects the board from stains and fading, and offers enhanced UV resistance. Each board is available in 2 faces a total of 3 colors: RED, YELLOW, BROWN. The random mix of these colors, together with the RED on each board, guarantees an effect faithful to IPE.

PLATING		RED/BROWN RED/YELLOW
	22,5 x 138 x 3900 mm	FD1960
FINISH		RED
	22,5 x 138 x 3000 mm	FD1832

BROWN / RED



YELLOW / RED



COBRA
 Clip Cobra® Hybrid 8-18
 1 bag for 4,5m2 FD0993



COBRA
 Cobra® Start/End
 FD0336





20 YEARS
WARRANTY
LIMITED RESIDENTIAL


UV RESIST




R12


HARMONY

HARMONY composite decking boards feature the new Hardcarp co-extrusion and protection technology to enhance the protection against impact and staining.

They imitate the texture of exotic woods as closely as possible, with 2 useful faces. One imitates the grain of the wood, the other is smoother like an exotic wood. Furthermore, the textured side scores 12 in the slipperiness test, depending on the defined orientation.

Installation is carried out using Cobra[®] 8-18 removable clips. Finishes can be with the fascia boards HARMONY.



		OCEAN GREY	INDIAN SUMMER	CEDAR
PLATING		FD1254	FD1255	FD2042
	22,5 x 138 x 4000 mm			
FINISH		FD2170	FD2171	FD2172
	22,5 x 138 x 3000 mm			

INDIAN SUMMER

OCEAN GREY

CEDAR



COBRA
 Clip Cobra[®] Hybrid 8-18
 1 bag for 4,5m2
 FD0993



COBRA
 Cobra[®] Start/End
 FD0336





20
YEARS
WARRANTY
LIMITED RESIDENTIAL


UV RESIST




60%
BIO SOURCED

VINTAGE

VINTAGE boards brilliantly reproduce the look of boards aged and patinated over time. The raised texture of the wood fibers creates a natural wood feel.

Available in 2 widths and 4 colors: Each board presents 2 different colors: Graphite/Wenge, Lunar Grey/Cedar. Finishing strips are available in each color. The coextrusion coating guarantees colorfastness for 20 years.

		GRAPHITE/WENGE		LUNAR GREY/CEDAR	
PLATING		FD1833		FD1834	
	22,5 x 138 x 4000 mm				
PLATING		FD1835		FD1836	
	22,5 x 210 x 4000 mm				
FINISH		FD1132	FD1131	FD1133	FD1890
	22,5 x 138 x 3000 mm				

GRAPHITE / WENGE



LUNAR GREY / CEDAR



COBRA
 Clip Cobra[®] Hybrid 8-18
 1 bag for 4,5m²
 FD0993



COBRA
 Cobra[®] Start/End
 FD0336





20 YEARS
WARRANTY
LIMITED RESIDENTIAL


UV RESIST







60%
BIO SOURCED

MANHATTAN

MANHATTAN boards offer a choice of smooth or grooved faces in 5 multi-chromatic colors. The colors are guaranteed for 20 years, and the decking requires very little maintenance. The grooves catch the light to give relief to the decking.

The screw-in strips associated with this range can be used to create all types of finishes, such as steps and skirting boards.

	LIGHT GREY	IPE	TEAK	DARK GREY	CEDAR
PLATING  22,5 x 145 x 3600 mm	FD1026	FD1027	FD1028	FD1025	FD1889
FINISH  22,5 x 138 x 3000 mm	FD1247	FD2111	FD1249	FD1246	FD1831
 10 x 84 x 2400 mm	FD0707	FD0708	FD0895	FD0706	-



COBRA
 Clip Cobra® Hybrid 8-18
 1 bag for 4,5m2
 FD0993



COBRA
 Cobra® Start/End
 FD0336





15 YEARS
WARRANTY
LIMITED RESIDENTIAL


UV RESIST




60%
BIO SOURCED

BROOKLYN

BROOKLYN boards offer a choice of smooth or textured wood grain in 5 multi-chromatic colors. The co-extrusion protective layer on both sides guarantees very low expansion and excellent color fastness over time.

The finishing boards associated with this range can be adapted to any configuration. Available in two widths.

	LIGHT GREY	IPE	TEAK	DARK GREY	CEDAR
PLATING  22,5 x 138 x 4000 mm	FD1239	FD1240	FD1241	FD1238	FD1827
 22,5 x 210 x 4000 mm	FD1243	FD1244	FD1245	FD1242	FD1829
FINISH  22,5 x 138 x 3000 mm	FD1247	FD1248	FD1249	FD1246	FD1831
 10 x 84 x 2400 mm	FD0707	FD0708	FD0895	FD0706	-



CLIPS & SCREWS

COMPOSITE DECKING



Fiberdeck® joins forces with Cobra Fastener® to offer reliable, long-lasting fastening solutions that are perfect for everyone range profiles.

CONCEALED FIXING

Cobra clips fit snugly between each board for secure, discreet fastening. Suitable for wood and aluminum joists.

LONGER SERVICE LIFE

The Cobra range allows you to use the fastener best suited to the deck board and structure, for better durability over time.

EASY DISASSEMBLY

With their unique design, Cobra clips allow easy removal of deck boards.



CLIP HYBRID 8-18

Set of 90 clips with AISI410 self-drilling screws for wood and aluminum.
Approx. 4-5 m²
FD0993



START/END CLIPS

AISI304 stainless steel clips (30 pcs). AISI304 stainless steel screws 4.5x25 mm (30 pcs)
FD0336



AIRSPACER

Set of 100 pieces + 4 board spacers 3-4-5-6 mm
FD1040



SCREWS FOR COMPOSITE WOOD DECKING

Set of 150 AISI304 stainless steel screws with end cap
FD0770 / FD0771



DISCOVER

ALL FASTENING AND STRUCTURAL SYSTEMS
FOR WOOD & COMPOSITE DECKING AT
WEBSITE www.cobrafastener.en




FENCING



BOARDS




DECORS



STRUCTURES



GATES



20 YEARS
WARRANTY
LIMITED RESIDENTIAL


UV RESIST



PREMIUM

PREMIUM boards are co-extruded. This means that the wood composite board is enveloped with a protective polymer layer that also carries the color in a randomly applied pattern. This layer is brushed for a warm and natural finish.

PREMIUM boards are impervious to insect and termite attack, and are guaranteed for 20 years against fading and staining.

To ensure their rigidity, the boards must be fitted with aluminum reinforcements.



CEDAR
FD1826



DARK GREY
FD1232



TEAK
FD1234



IPE
FD1233



LIGHT GREY
FD1235



REINFORCEMENTS
FD1388



21 x 150 x 1780 mm



20 YEARS
WARRANTY
LIMITED RESIDENTIAL

UV RESIST



PREMIUM XL

PREMIUM XL boards have all the technical properties and aesthetic qualities of PREMIUM boards. Than the premium range.

Thanks to a larger surface, the nuanced patterns are strongly expressed themselves for a remarkable effect.

Combined with standard PREMIUM boards, the result is striking and inimitable. To ensure rigidity, the boards must be fitted with aluminum reinforcements.



DARK GREY
FD2136




LIGHT GREY
FD2137




TEAK
FD2138



REINFORCEMENTS
FD1388



21 x 300 x 1780 mm



20 YEARS
WARRANTY
LIMITED RESIDENTIAL


UV RESIST



MODERN

MODERN boards offer an elegant imitation of slatted fence effect thanks to a carefully proportioned grooved surface expressed on both sides.

Thanks to co-extrusion, these wood composite boards are guaranteed against fading in the most extreme conditions. Available in three colors, they can be combined with OPALE aluminum boards.

To ensure their rigidity, the boards must be fitted with aluminum reinforcements.



TEAK
FD1121




DARK GREY
FD1118



CEDAR
FD1531



REINFORCEMENTS
FD1388



21 x 150 x 1780 mm



20 YEARS
WARRANTY
LIMITED RESIDENTIAL


UV RESIST





MODERN

VERTICAL POSE

Specially developed for vertical installation, the reinforced bottom rail guarantees long-lasting strength and stability.

It allows you to create a fence with an unique and timeless look.

In powder-coated aluminum, available in anthracite grey and black, it is finished to the highest standards to achieve the most beautiful effect.



TEAK
FD1121




DARK GREY
FD1118



CEDAR
FD1531



SMOOTH REINFORCED
GREY RAL7016 : FD2141
BLACK RAL9005 : FD2142



21 x 150 x 1780 mm



20 YEARS
WARRANTY
LIMITED RESIDENTIAL



OPALE

OPALE interlocking Aluminum are ideal for a modern and elegant Fence.

They can be combined with wood composite boards to create a warm contrast, or with OPEN boards for an airy effect.

OPALE boards are powder-coated with a textured effect and Qualicoat[®] and Qualimarine[®] certified.


They are available in anthracite grey RAL7016 and black RAL9005.




GREY RAL7016
FD0868



BLACK RAL9005
FD1927



21 x 150 x 1780 mm



20 YEARS
WARRANTY
LIMITED RESIDENTIAL



OPEN

OPEN boards are installed with spacers to create an openwork fence. They are available in two sections: 45mm and 100mm high.

These two heights allow you to choose between an airy or robust effect. The 15mm spacers can be stacked to finely manage the space left between the boards.

OPEN boards are powder-coated with a textured effect. Qualicoat[®] and Qualimarine[®] certified, they are available in anthracite grey RAL7016 and black RAL9005.





OPEN 45
 GREY RAL7016 : FD1198
 BLACK RAL9005 : FD1929



OPEN 100
 GREY RAL7016 : FD1197
 BLACK RAL9005 : FD1928



NYLON SPACERS 15MM
 GREY RAL7016 : FD1653
 BLACK RAL9005 : FD1925



21 x 100 x 1780 mm



21 x 45 x 1780 mm



20 YEARS
WARRANTY
LIMITED RESIDENTIAL



RHOMBUS

Unique in design, RHOMBUS boards are distinguished by their parallelepiped profile.

They offer a louvered effect, which allows to look out without being seen. They are installed with 15° angled spacers that can be stacked to manage the spacing between boards.

RHOMBUS boards are powder-coated with a textured effect. Qualicoat[®] and Qualimarine[®] certified, they are available in anthracite grey RAL7016 and black RAL9005.



GREY RAL7016
FD1564




BLACK RAL9005
FD1930



21 x 75 x 1780 mm



NYLON SPACERS 10MM
GREY RAL7016 : FD1643
BLACK RAL9005 : FD1924



20 YEARS
WARRANTY
LIMITED RESIDENTIAL



HERA

Laser-cut aluminum decors add personality to the fence.

They are supplied with the aluminum profiles that form their frame.

The whole assembly fits perfectly into the aluminum or composite boards.

Horizontal decors are positioned at the very top of the panel or between two fence boards. The HERA decor replaces exactly two fence boards.



HERA VERTICAL
GREY RAL 7016
FD1011



HERA VERTICAL
BLACK RAL 9005
FD1942



HERA HORIZONTAL
GREY RAL 7016 FD1010



HERA HORIZONTAL
BLACK RAL 9005 FD1941



20 YEARS
WARRANTY
LIMITED RESIDENTIAL



PAXOS

With a thickness of 2mm, the decors are delivered with an aluminum frame that fits over the aluminum or composite boards and into the posts.

Laser-cut aluminum decors add personality to the fence.

Horizontal decors are positioned at the very top of the panel or between two fence boards. They replace exactly three fence boards.



PAXOS VERTICAL
GREY RAL 7016
FD1009



PAXOS HORIZONTAL
GREY RAL 7016
FD1008

LAMIA

The LAMIA sets are designed in the same way as the HERA and PAXOS sets. They replace exactly two fence boards.



LAMIA VERTICAL
GREY RAL 7016
FD1216



LAMIA HORIZONTAL
GREY RAL 7016
FD1215



20 YEARS
WARRANTY
LIMITED RESIDENTIAL



CRIOS

CRIOS is a laser-cut aluminum backdrop with a pattern reminiscent of a giant set of bricks, allowing light and landscape to shine through while providing privacy.

CRIOS decors are designed in the same way as HERA and PAXOS decors. They replace exactly two fence boards.



CRIOS VERTICAL
GREY RAL 7016
FD1214



CRIOS HORIZONTAL
GREY RAL 7016
FD1213

CLARITY

The CLARITY frosted glass insert is 8mm thick and can be combined with composite or aluminum boards to create modern, and elegant filter panels.

It replaces three fence boards.



INSERT CLARITY
FD1219



GATES

The GATES can be easily matched to the style of your BOSTON fence, thanks to the fill-in-the-blank frames.

Two sizes are available, with maximum widths of 980mm and 1200mm, adjustable as required by cutting the horizontal crosspieces. Universal, these frames are suitable for left or right-hand opening, pull or push.

The lock is directly included in the frame amount on delivery.

For a perfect finish, we recommend an 1830mm battue. Installation can be free-standing within the fence, using 90x90mm posts, or on an existing wall or pillar with hinges.

The hardware includes a stop with adaptable strike, handles, cylinders and sashes.



FRAME 980 X 1830 MM
GREY RAL7016 FD1267
BLACK RAL9005 FD1935

FRAME 1200 X 1830 MM
GREY RAL7016 FD1430



HARDWARE
GREY RAL7016 FD1268
BLACK RAL9005 FD1962



POST 90 X 90 X 2750 MM
GREY RAL7016 FD1266
BLACK RAL9005 FD1945



HINGE FOR GATE
GREY RAL7016 FD1339
BLACK RAL9005 FD1963



BATTUE HEIGHT 1830 MM
GREY RAL7016 FD1985
BLACK RAL9005 FD1986




CORNER KIT FOR POST
Profiles and related hardware
GREY RAL7016 FD1338
BLACK RAL9005 FD1931

Fiberdeck®

ANGLE KIT FOR POSTS


The angle kit specially developed for the BOSTON concept allows you to give any angle from 10° to 170° to the design of your fence. It consists of a pivot pin that fits into one of the post's grooves, and a pivot that provides the desired angle.

The pivoting part holds the boards like a conventional post. The BOSTON fence adapts perfectly to any site configuration.





POSTS



SECTION	75x75mm
ALUMINUM THICKNESS	1,8 to 2,2mm
WIND RESISTANCE	120 km/h (fence height 1m80 sealed)
90° ANGLE MANAGEMENT	Includes
FINISHING PROFILE	Includes
COLORIS	Anthracite GREY RAL7016 & BLACK RAL9005, Textured powder coating
HEIGHT	124cm / 184 cm / 234cm / 300cm

ALU POST 75 X 75 X 1240 MM
 GREY RAL7016 FD1001
 BLACK RAL9005 FD1952

ALU POST 75 X 75 X 1840 MM
 GREY RAL7016 FD1002
 BLACK RAL9005 FD1922

ALU POST 75 X 75 X 2340 MM
 GREY RAL7016 FD1003
 BLACK RAL9005 FD1921

ALU POST 75 X 75 X 3000 MM
 GREY RAL7016 FD1122
 BLACK RAL9005 FD1920



FINISH PROFILE
 6 x 24 x 1840 mm
 GREY RAL7016 FD1715
 BLACK RAL9005 FD 1739



POST CAP
 75 x 75 mm
 GREY RAL 7016 FD1943
 BLACK RAL 9005 FD1944



CORNER KIT FOR POST
 Profiles and associated
 hardware
 GREY RAL 7016 FD1338
 BLACK RAL 9005 FD1931

ACCESSORIES

Fiberdeck[®]
POSTS & ACCESSORIES
FENCING



TOP/ BOTTOM PROFILE
25 x 30 x 1750 mm
GREY RAL 7016 FD1318
BLACK RAL 9005 FD1937



**REINFORCED
BOTTOM PROFILE**
25 x 35 x 1750 mm
GREY RAL 7016 FD2141
BLACK RAL 9005 FD2142




WALL PROFILE
28 x 24 x 1900 mm (2 pcs)
+ 12 SCREWS 4,8 x 16 mm + PLUGS
GREY RAL 7016 FD1278
BLACK RAL 9005 FD1953



STAINLESS STEEL ANCHOR
120 x 120 x 200 mm
GREY cover RAL 7016 FD1530
BLACK cover RAL 9005 FD1934



SET OF 4 CONNECTORS
FD1309



15MM NYLON SPACERS
66 pieces
GREY RAL 7016 FD1653
BLACK RAL 9005 FD1925



**NYLON SPACERS 10MM
FOR RHOMBUS** 44 pieces
GREY RAL 7016 FD1643
BLACK RAL 9005 FD1924



**SET OF 3 ALUMINUM
REINFORCEMENTS FOR
COMPOSITE FENCING**
FD1388



WALL ANCHOR SUPPORT
FD1340

CLADDING





WEO[®]

Bio-sourced cladding with outstanding performance

WEO[®] cladding boards have been developed using the latest co-extrusion technologies to ensure a product that is both weather-resistant and fade-resistant for 20 years, while utilizing 95% waste materials in its manufacturing. A waterproof polyethylene layer protects the wood from moisture absorption and stabilizes the material. Expansion is also minimized. Maintenance is limited to simple cleaning.



20 YEARS
WARRANTY
LIMITED RESIDENTIAL

UV RESIST



E



WEO[®] ESSENTIAL

Fiberdeck[®]
**COMPOSITE WALL
CLADDING**



WEO[®] ESSENTIAL cladding boards are available in 4 multi-chromatic shades that are resistant to fading and weathering, ensuring exceptional longevity. The brushed, matte surface provides a natural wood-like appearance, giving your façade a unique look.



TEAK
FD1995



IPE
FD1996




DARK GREY
FD1997



LIGHT GREY
FD1998

Coverage per board	0,596 m ²
Weight per sq/m	10,72 kg/m ²
Width	173 mm
Width (when lapped)	153 mm





20 YEARS
WARRANTY
LIMITED RESIDENTIAL


UV RESIST




E

WEO® 35

Fiberdeck® COMPOSITE SLATTED CLADDING



WEO35 boards feature a profile with a wood slat effect. The pronounced shape of the boards adds rhythm to façades, creating a modern and dynamic look. The matte brushed finish is resistant to fading and aging over time.

Also available in fire class D.



CEDAR
2.9M FD1536
3.9M FD1552



TEAK
2.9M FD1532
3.9M FD1549



IPE
2.9M FD1533
3.9M FD1550



DARK GREY
2.9M FD1535
3.9M FD1551




LIGHT GREY
2.9M FD1534
3.9M FD1954



EBONY BLACK
2.9M FD2101
3.9M FD2102

	Length 2.9M	Length 3.9M
Coverage per board	0,406 m2	0,546 m2
Weight per sq/m	15 kg/m2	15 kg/m2
Width	170 mm	170 mm
Width (when lapped)	140 mm	140 mm





20 YEARS
WARRANTY
LIMITED RESIDENTIAL

UV RESIST



D S1d0

WEO® 60

Fiberdeck® COMPOSITE SLATTED CLADDING



WEO60 cladding combines character and elegance with its wide wood slat effect. Its remarkable wood-like appearance enhances façades with harmony and style. Available in 4 colors with a matte brushed finish, it is resistant to fading and aging.

Also available in fire class D.




CEDAR
2.9M FD1567
3.9M FD1571

TEAK
2.9M FD1565
3.9M FD1569

IPE
2.9M FD1566
3.9M FD1570


DARK GREY
2.9M FD1568
3.9M FD1572

	Length 2.9M	Length 3.9M
Coverage per board	0,406 m ²	0,546 m ²
Weight per sq/m	14,5 kg/m ²	14,5 kg/m ²
Width	170 mm	170 mm
Width (when lapped)	140 mm	140 mm





EXTERNAL CORNER TRIMS




SNAP-FIT CORNER
50 x 50 mm x 3 m - WEO® 35 / WEO® 60

- CEDAR | FD2049
- TEAK | FD2047
- IPE | FD2048
- DARK GREY | FD2051
- EBONY BLACK | FD2052
- LIGHT GREY | FD2050

SNAP-FIT CORNER
35 x 41 mm x 3 m - WEO® 35 / WEO® 60
FD2046

WEO[®] - EDGING & SCREWING
CLADDING



ALUMINUM F PROFILE

65 x 80 mm x 3 m - WEO[®] 35 / WEO[®] 60

- | | |
|------------------|------------------------|
| ■ CEDAR FD1696 | ■ DARK GREY FD1695 |
| ■ TEAK FD1693 | ■ EBONY BLACK FD2105 |
| ■ IPE FD1694 | ■ LIGHT GREY FD1946 |

35 x 45 mm x 3 m - WEO[®] ESSENTIAL

- | | |
|-----------------|-----------------------|
| ■ TEAK FD1948 | ■ DARK GREY FD1949 |
| ■ IPE FD1951 | ■ LIGHT GREY FD1950 |

CLADDING SCREWS



COLOURED STAINLESS STEEL SCREWS A2 TORX

4.2 X 38 MM

100 units per box + bit
Visible screwing + Edging


- | | |
|------------------|------------------------|
| ■ CEDAR FD1451 | ■ DARK GREY FD1450 |
| ■ TEAK FD1447 | ■ LIGHT GREY FD1449 |
| ■ IPE FD1448 | ■ EBONY BLACK FD2103 |



STAINLESS STEEL SCREWS A2 TORX

4.2X32MM

200 units per box + bit
Hidden screwing
FD1940



20 YEARS
WARRANTY
LIMITED RESIDENTIAL



UV RESIST




50%
bio sourced

BRISE-SOLEIL

Fiberdeck[®]
BRISE-SOLEIL
 CLADDING



Composite wood sunshades are decorative elements for façades and various outdoor applications. They effectively shield buildings from sunlight, providing comfort for occupants. Their matte brushed finish gives buildings a contemporary look with a beautiful wood finish.



TEAK


CEDAR



BRISE-SOLEIL

42 X 60 mm x 3.90m
 42 x 145 mm x 3.90m

TEAK	CEDAR
FD1910	FD1947
FD2012	FD2013




Weight per m	1.25 kg
Width	60 mm
Height	42 mm
Length	3.90 m



END CAPS

42 x 60 mm
 42 x 145 mm

TEAK	CEDAR
FD1887	FD1888
FD2014	FD2015



Weight per m	2.90 kg
Width	145 mm
Height	42 mm
Length	3.90 m




Aluminum Tube

30 x 30 x 2 mm x 3.90 m
 FD1915

INSTALLATION



BRISE-SOLEIL



RAIL FASTENING



FASTENING WITH STAPLE



1 ALUMINUM CLIP NV3
FD1154

2 ALUMINUM RAIL
KX-3000 RAL9005
FD1156

3 SELF DRILLING A2 STAINLESS STEEL SCREWS


5,5 x 32 mm FD1155
5,5 x 50 mm FD1223

INSTALLATION




WEO® 35 / WEO® 60

INVISIBLE / HIDDEN SCREWING




VISIBLE SCREWING



BOARDS	BOARDS ORIENTATION	SCREWING
WEO® 35 / WEO® 60	VERTICAL	HIDDEN / VISIBLE
WEO® 35 / WEO® 60	HORIZONTAL	VISIBLE
	2M90	3M90
QTY OF SCREWS PER SQ/M (Span 600 mm)	12	12
QTY OF BOARDS PER SQ/M	2.46	1.83

WEO® ESSENTIAL

INVISIBLE / HIDDEN SCREWING



BOARDS	BOARDS ORIENTATION	SCREWING
WEO® ESSENTIAL	VERTICAL & HORIZONTAL	INVISIBLE
	3M90	
QTY OF SCREWS PER SQ/M (span 600 mm)	11	
QTY OF BOARDS PER SQ/M	1.68	





Fiberdeck[®]
Never stop innovating

Fiberdeck[®]
Never stop innovating

