FARO
BARCELONA

lighting&fan 2023

Check the current rates here
Consulta la tarifa vigente aquí



PRICES

For a sustainable future of forests.
Por un futuro sostenible de los bosques.

Edition
A2023

Art Director / Graphics
Faro Art

Printing
Jiménez Godoy

All Rights Reserved
Reproduction without written permission from the publisher is strictly prohibited.

Photographers
Guillem F-H
Andrés Fraga
Ricard Badía
Sergiy Kadulin
Stelios Kalisperis
Architectural Matter

Thanks to
Natalia Zubizarreta
Salto Proyectos
Vana Pernari Architecture
Estibaliz Martin Interiorismo
Colvin & Co.
Pía Capdevila
Erlantz Biderbost
Restaurant 3 Nusos
Pol&Grace Hotel
Elena Castells Poch
MIKMAX
Alfombras BSB
Bubes&Grabavska Design
Meritxell Ribé - The Room Studio

Headquarters
BARCELONA
Dinámica 1,
08755, Castellbisbal
Tel +34 937 723 949
info@faro.es

Showrooms
BARCELONA
Princesa
Calle Princesa, 52
08003, Barcelona
Tel +34 93 238 73 73
info@faro.es

MADRID
docontract MAD
Calle Velázquez, 35, 4ºD
28001, Madrid
Tel +34 689 583 571
showroom@docontractmad.com

PARIS
7 rue d'uzès
75002, Paris
Tel +34 687 845 758
hajar.chegri@faro.es

CONTENTS



portables / portátiles
42_61
indoor / hogar
64_147
Table&Floor / Mesa y suelo
148_221
Suspended / Suspensión
222_241
Ceiling / Techo
242_389
Surface / Superficie
390_405
Spotlights / Focos
406_433
Recessed / Empotrables
434_439
Track / Carril







outdoor / exterior

442_527

Floor / Suelo

528_555

Spike&Projector / Estaca y Proyector

556_571

Suspended / Suspensión

572_577

Ceiling / Techo

578_639

Surface / Superficie

640_665

Recessed / Empotrables

fan / ventilación

666_811

bulbs / bombillas

812_817





Faro Barcelona exists to contribute to the wellbeing and happiness of people through design and the relationship we establish with the objects that surround us in our daily lives. We believe in honest and accessible design. Design for everyone.

Nuestra razón de ser es contribuir al bienestar y la felicidad de las personas a través del diseño y la relación que establecemos con los objetos que nos acompañan en nuestro día a día. Creemos en el diseño honesto, cercano y accesible. Diseño para todos.

OUR PURPOSE

designed for happiness

Xavier Martin
CEO

Carlos López
Chairman



Faro Barcelona is a conscious and inspiring brand.
We believe in the power of enthusiasm to move forward and surf the waves the best way we know while enjoying the process and radiating light around us.
We celebrate 75 years of light.

Faro Barcelona es una marca consciente e inspiradora.
Creemos en el poder de la ilusión y el entusiasmo para avanzar y surfear las olas de la mejor forma que sabemos hacerlo, disfrutando del proceso e irradiando luz a nuestro alrededor. Celebramos 75 años de luz.

A BRAND WITH SOUL

Meet the Team
Conoce al equipo




BY ANDREU CARULLA
BUDDY

PEOPLE

The value of a great team
At Faro Barcelona, sustainability starts from the inside, taking care of the well-being and personal growth of our team.

Equality and diversity
At Faro Barcelona all people are great and equal, whatever their gender, age, religion or sexual orientation. Women, as well as men, play an important role: 76% of our team and 49% of our leaders are women.

Community support
For over a decade, we have been collaborating in social projects of foundations such as Caritas, providing our help to ensure a better qua-lity of life for the people helped by these organisations. Since 2008, we have had our own social project with Hook, each luminaire sold feeds a child in Africa for one year.

Supporting new talent
We collaborate with universities and design schools to help new talents emerge into their professional development. Projects such as Reborn, a second life for waste (La LLotja), Design Make It with 3D printing (CIM UPC), are some of the collaborations we have carried out.

Social innovation
We take part in disruptive social innovation research and develop products and services that solve social problems such as the ageing of the population. We have a positive impact on people's quality of life, contributing to their well-being and comfort through quality, accessible and sustainable lighting and design.



El valor de un gran equipo humano
En Faro Barcelona la sostenibilidad empieza en el interior, cuidando el bienestar y crecimiento personal de nuestro equipo.

Igualdad y diversidad
En Faro Barcelona todas las personas son grandes e iguales, sean del género, edad, religión u orientación sexual que sean. La mujer, igual que el hombre, desempeña un papel importante: el 76% de nuestro equipo y el 49% de nuestros líderes son mujeres.

Apoyo a la comunidad
Llevamos más de una década colaborando en proyectos sociales de fundaciones como Cáritas aportando nuestra ayuda para garantizar una mejor calidad de vida de las personas que ayudan estas organi-zaciones. Desde 2008, tenemos nuestro propio proyecto social con Hook, cada luminaria vendida alimenta durante una año a un niño en África.

Apoyo a los nuevos talentos
Colaboramos con universidades y centros de diseño para ayudar a los nuevos talentos en su desarrollo profesional. Proyectos como Reborn, una segunda vida para los desechos (La LLotja), Diseño Make It con impresión 3D (CIM UPC), son algunas de las colaboraciones que hemos realizado.

Innovación social
Participamos en investigaciones de innovación social disruptiva y desarrollamos productos y servicios que resuelven problemáticas sociales como el envejecimiento de la población.
Impactamos positivamente en la calidad de vida de las personas, contribuyendo a su bienestar y confort a través de la iluminación y el diseño de calidad, accesible y sostenible.



Our sustainability journey focuses on two main objectives: reducing our negative impact on the planet and maximising our positive social impact.
Nuestro camino hacia la sostenibilidad se centra en dos grandes objetivos: reducir nuestro impacto negativo en el planeta y maximizar nuestro impacto social positivo.

SUSTAINABILITY

TURN OFF THE LIGHT

Discover more
Descubre más

PLANET

Sustainable packaging
At Faro Barcelona, we have a sustainable packaging decalogue. Our packaging is made of recycled cardboard boxes printed in one ink and without staples to ease the disassembly and the right recycling. We have eliminated single-use plastics and replaced them with recyclable paper bags and we use recycled cardboard shavings to protect the product during transport in 60% of our shipments. All our packaging meets Drop Test ISTA-2C quality standards to ensure products arrive in perfect condition.



More sustainable logistics and transport
We have optimised the packaging size of each product to reduce the amount of packaging material and the carbon footprint of transport. FMCG products are transported in stacks, which means a greatly reduced carbon footprint. We have opened a new logistics centre in China to supply our Asia-Oceania market in a more sustainable way and reduce carbon emissions from transport.

Sustainable workspaces
We use green electricity in our offices. We produce 70% of the energy we consume with our own photovoltaic installation, ensuring that the energy is from renewable sources. In addition, our headquarters are designed to maximise the use of solar energy and natural light.

Supporting new talent Team committed to sustainability
At Faro Barcelona we have an internal sustainability committee that promotes different sustainability actions and monitors them.



Embalaje sostenible
En Faro Barcelona disponemos del decálogo de embalaje sostenible. Nuestros embalajes son cajas de cartón reciclado impresas a una sola tinta y sin grapas para facilitar así el desmontaje y su correcto reciclaje. Hemos eliminado los plásticos de un solo uso y sustituido por bolsas de papel reciclable y utilizamos virutas de cartón reciclado para la protección del producto durante el transporte en el 60% de nuestros envíos. Todos nuestros embalajes cumplen los estándares de calidad de Drop Test ISTA-2C para asegurar que los productos lleguen en perfecto estado.

Logística y transporte más sostenible
Hemos optimizado el tamaño del embalaje de cada producto para reducir la cantidad de material de embalaje y la emisión de carbono derivado del transporte. Los productos de gran consumo se transportan apilados, lo que implica una gran reducción de huella de carbono. Hemos abierto un nuevo centro logístico en China para abastecer a nuestro mercado Asia-Oceania de una forma más sostenible y reduciendo las emisiones de carbono derivadas del transporte.

Espacios de trabajo sostenibles
En nuestras oficinas utilizamos energía eléctrica verde. Producimos un 70% de la energía que consumimos con nuestra propia instalación fotovoltaica, asegurando que la energía es de fuente renovable. Además, nuestra sede cuenta con un diseño pensado para el máximo aprovechamiento de la energía solar y la luz natural.

Equipo comprometido con la sostenibilidad
En Faro Barcelona contamos con un comité de sostenibilidad interno que promueve diferentes acciones de sostenibilidad y realiza su seguimiento.



PRODUCT

Sustainability from conceptualisation
In our eco-design decalogue we set out the main guidelines we follow to make our designs more sustainable. We work with external consultants to reduce the environmental impact of our production processes, guaranteeing the quality and safety of our products. We are training our design team in circular design techniques for the more sustainable development of all our products.

A longer useful life
We work to design timeless, repairable and long-lasting products in order to reduce their environmental impact. We research new methods to ensure that our designs last longer,are easier to repair and recycle.

Standardisation and modularity
We work on the standardisation of components for a more efficient use of resources and more sustainable production. We develop modular collections that allow us greater versatility and more efficient logistics and transport.

More sustainable processes and materials
One of the major challenges towards a more sustainable production is the choice of materials as it represents more than 70% of the product's carbon footprint. The use of recycled materials or materials with a lower environmental impact, the implementation of new techniques and the reduction of the number of materials used, help us to achieve more sustainable manufacturing.Control of the supply chain

We share our sustainability vision and commitments with all our suppliers.
We, therefore have a supplier code of conduct to ensure a more sustainable supply chain.



Sostenibilidad desde la conceptualización
En nuestro decálogo de eco-diseño recogemos las principales directrices que seguimos para que nuestros diseños sean más sostenibles. Trabajamos con asesorías externas para reducir el impacto ambiental de nuestros procesos productivos, garantizando la calidad y seguridad de nuestros productos. Estamos formando a nuestro equipo de diseño en técnicas de diseño circular para el desarrollo más sostenible de todos nuestros productos.

Una mayor vida útil
Trabajamos en el diseño de productos atemporales, reparables y duraderos con el fin de reducir su impacto medioambiental.
Investigamos nuevos métodos para garantizar que nuestros diseños sean más duraderos, fáciles de reparar y de reciclar.

Estandarización y modularidad
Trabajamos en la estandarización de componentes para un uso más eficiente de los recursos y una producción más sostenible. Desarrollamos colecciones modulares que nos permiten mayor versatilidad y una logística y transporte más eficientes.

Procesos y materiales más sostenibles
Uno de los grandes retos hacia una producción más sostenible es la elección de los materiales ya que representa más del 70% de la huella de carbono del producto.
El uso de materiales reciclados o con menor impacto ambiental, la implementación de nuevas técnicas y la reducción del número de materiales usados, nos ayuda a conseguir una fabricación más sostenible.

Control de la cadena de suministro
Compartimos nuestra visión y compromisos de sostenibilidad con todos nuestros proveedores. Por ello, disponemos del código de conducta de proveedores para garantizar una cadena de suministro más sostenible.





This year we have achieved certification of our carbon footprint calculation in accordance with the ISO14064-1 international standard, a major milestone on our path to sustainability.
Thanks to this certification, we know the real volume of greenhouse gas emissions generated by our activity and it allows us to identify areas for improvement and implement compensation strategies through different programs. through different programs.
Este año hemos logrado la certificación del cálculo de la huella de carbono conforme al estándar internacional ISO14064-1, un gran hito en nuestro camino hacia la sostenibilidad.
Gracias a esta certificación conocemos el volumen real de emisiones de gas invernadero que genera nuestra actividad y nos permite identificar áreas de mejora e implementar estrategias de compensación a través de diferentes programas.



Certificación huella de carbono

CARBON FOOTPRINT CERTIFICATION



ISO 14064



Buddy
by Andreu Carulla

DESIGN AWARD 2022

GERMAN DESIGN AWARD WINNER 2022



Inviting
by Bohman&Folenius

reddot award 2019 winner

DESIGN AWARD 2019

GERMAN DESIGN AWARD SPECIAL 2019



Hook
by Oiko Design Office

reddot award 2018 winner

Green Product Award Winner 2018

GERMAN DESIGN AWARD WINNER 2020



Fuji
by Isaac Piñeiro

reddot winner 2021 lighting design

GERMAN DESIGN AWARD 2022



Brot
by Yembarastudio

reddot winner 2021 lighting design



Mine
by Nahtrang

Restaurant & Bar Product Design Awards Winner

GERMAN DESIGN AWARD WINNER 2018



Whizz
by Christoph F.W.

salone satellite 20years of new creativity



Bu-Oh
by Estudi Ribaudí

GERMAN DESIGN AWARD SPECIAL 2018



Lotus
by Estudi Ribaudí

DESIGN AWARD 2020



Mute
by Nahtrang

GERMAN DESIGN AWARD SPECIAL 2019



Han
by Goulafiguera

miaw DESIGN INNOVATION AWARDS



Maya
by Faro Lab

reddot winner 2023



Totem
by Roger Vancells

reddot winner 2023



AWARDS

Diseñadores, artistas, creadores. Ellos hacen de nuestro mundo un lugar mejor gracias a su ingenio, talento y creatividad.



Cristopher F. Wagner



Goula/Figuera



Marina Milà



Àlex & Manel Lluscà



Conillas



Jordi Llopis



Oiko Design Office



Lucid



Jordi Busquets



Jordi Blasi



Ernest Perera Studio



Adolfo Abejón



Aldanondoyfdez

Designers, artists, creators. They make our world a better place thanks to their ingenuity, talent and creativity.



Xjer Studio



Nutcreatives



Andreu Carulla



Alegre Design



Bohman&Folenius



Faro Lab



Isaac Piñeiro



Nahtrang



Pepe Llaudet



Estudi Ribaudí



Cristina Borràs



Yembarastudio



Roger Vancells



Héctor Serrano


IO



SHOWROOM

Barcelona · Madrid · Paris

Q-LAB

Quality & innovation
Calidad e innovación

At Faro Barcelona, we control the quality of our products and services from conception and design to functionality and reliability tests.
Our quality management system is based on ISO9001. Legislative compliance with safety regulations under EN60598 and ERP energy efficiency regulations.

En Faro Barcelona controlamos la calidad de nuestros productos y servicios desde la concepción y el diseño hasta los ensayos de funcionalidad y fiabilidad.
Nuestro sistema de gestión de calidad está basado en la ISO9001. Cumplimiento legislativo de las normativas de seguridad bajo la EN60598 y la normativa de eficiencia energética ERP.



Parametrical Lab

Specification Compliance

Electrical Safety Tests

Integrating Sphere

Climatic Chamber



Quality inspections Lab

Batch inspections

Functional Tests

Product Assembly Control

Product Finish Control

Technical Assistance Service (TAS)

Customer Returns Analysis

Customer Returns Repairs

TAS Spare Parts



Ceiling Fan Lab

Life Test

Customizations

Airflow measurements

Noise measurements

Goniophotometer Room




Assistance during installation
Acompañamiento
en instalación y obra
Consultancy and Advice
Consultoría y Asesoramiento
Product customisation
Personalización
de productos
Lighting projects
Lighting calculations
Cálculos
lumínicos
Digital documentation: Dialux (ULD, IES, LDT) Revit / BIM (RFA) 3D files, IGS (SketchUp)
Documentación digital: Dialux
(ULD, IES, LDT) Revit / BIM
(RFA) 3D files, IGS (SketchUp)
Advice on product selection
Asesoramiento en selección de productos
Lighting and fan projects department
Departamento de proyectos de iluminación y ventilación
Incident management
Gestión de incidencias
Technical service
Custom & Special developements
Technical support service
Servicio de atención técnica


Remote access to installations for configuration / changes
Acceso remoto a las instalaciones para configuración / cambios
Remote installation management
Gestión remota de instalaciones
Energy consumption monitoring
Monitorización de consumo energético
Scene and group definition
Definición de escenas y grupos
Scene and group definition
Definición de escenas y grupos
Control & Connectivity
Scalable installations
Instalaciones escalables
Turnkey project
Proyecto llave en mano
System Control design and planning
Diseño y planificación del sistema de control
Configuración de equipos para luminarias Plug&Play
Plug&Play equipment configuration for luminaires
Automation (sensors, timetables, circadian cycle)
Automatización (sensores, horarios, ciclo circadiano)
Solutions to connect to the control system (wired, wireless or remote devices)
Soluciones para conectarse al sistema de control (dispositivos cableados, inalámbricos o remotos)

SERVICES


ARCH



Download here
Descárgalo aquí

Portable
Portátil


Buddy
46


Candela
50


Hook
48


Lampanot
52


Take Away
45

Table
Mesa


1968
68


Academy
90


Akane
106

N


Anouk
78


Artis
122


Banker
82


Baobab
82

Berni
132


Bliss
76


Conga
114


Drum
108


Eterna
74


Gru
82


Guadalupe
94


Hoshi
70


Hotel
134


Inviting
66


Ito
78


Jellyfish
92


Lao
104


Lena
80


Levita
96


Linda
126


Link
102


Loop
98

N


Luang
828


Lula
74


Lupe
128


Mambo
110


Mine
73


Moma
144


Montreal
116


Nidia
76


Niko
72


Otto
80

Rem
120

Samba
112

Savoy
118

Snap
80

Stood
100

Sweet
145

Sumba
76

N

Tatawin
84

Ten
71

Tree
130

N

Venice
86

Vesper
124

Volta
136

Clip
Pinza



Inviting
66



Lena
334



Loop
98



Pepper
334



Stood
280



Studio
335

Floor
Suelo



Academy
90



Artis
122



Akane
106



Berni
132



Black
146



Conga
115



Drum
108



Guadalupe
94



Guest
142



Hotel
134



Jellyfish
92



Lao
104

Levita
96



Linda
126



Link
102



Loop
98

N



Luang
88



Lupe
128



Mambo
111



Moma
144



Montreal
116



Papua
146



Rem
120



Samba
113



Savoy
118



Stand Up
138



Stood
100



Sweet
145

N



Tatawin
84



Tree
130



Vesper
124



Volta
136

N



Venice
86



Whizz
140

Surface
Superficie


Academy 250


Board 370


Celia 364

Chera 376


Confetti 246


Costas 258

Cotton 356


Cove 378


Diula 381

Eaco 377

Elsa 378


Eres 350


Flash 254


Han 269


Homs 362


Hudson 363


Kamen 379

Kera 362


Levita 264


Linda 367


Liria 381

Lise 372


Loa 363


Loop 282


Luang 244


Luna 379


Magritte 380


Marina 363


Marlin 364


Maya 256


May 260


Moy 262


Nash 374


Noon 346


Olaf 374

Oslo 374


Otton 352


Ovo 350


Pure 271


Ras 366

Retro 367

Roda 324

Saba 324

Sahara 324

Sera 362

Slim 268

Snap 366

Snow 378

Stan 372

Stood 280

Tatawin 257

Ten 361

Tera 379

Tou 368

Venice 252

Volga 386

Whizz 266

Reader
Lector


Artis 296


Aurea 330


Bel 336


Berni 318


Blome 307


Boc 332


Boken 336


Conga 290


Corb 348


Duas 328


Essential 326


Eterna 298

Flin 333


Fold 308


Frame 302


Guadalupe 272


Guest 270


Handy 322


Hanna 326


Hotel 310


Joy 263


Juliet 334


Kale 337


Klee 274


Le Petit 331


Lead 337


Leser 336


Loke 333


Lupe 304


Magos 265


Mambo 294


Moma 327


Montreal 288


Mood 276


Niko 278


Nit 345


Orleans 402


Pixie 339


Press 338


Rem 300

Remake 366

N

Rob 332

Ron 306

Room 312

Samba 284

Sami 337

Savoy 286

Smile 347

Suau 340

Sumba 292

Sweet 320

Tila 344

Tira 327

Vesper 316

Volta 314

Well 348

Bath
Baño



Bianca
382



Brume
382



Danubio
388

Edge
384

N



Gala
384



Lago
384



Moy
262

Nilo
389



Perla
382

Ceiling
Techo

Ami
238

Bic
238



Cocotte
228



Dolme
228



Haru
234

Iris
237



Janet
234



Link
230

Mega
238



Natsu
234



Orleans
230



Pote
234



Rel
233



Seven
236

N



Shoku
224

Side
226



Stan
235



Sven
233



Tecto
232



Tender
228

Bath
Baño



Brume
240

Foro
238



Kao
239

Logos
239

Tola
240



Vuk
240

Zon
239

Suspended
Colgante


Aina 212


Art 204


Charlotte 200


Claire 206


Clara 204

Cocotte 176


Confetti 152


Conga 194


Cosmos 210


Costas 184


Crater 200

Danka 210

Dolme 176


Flash 150


Fusta 198


Haka 188


Halita 204


Hotel 198


Kombo 178


Lang 206


Levita 168


Liana 207


Linda 198


Liz 204


Loop 164


Lou 206


Magma 200


Mambo 192


Margot 200


Marina 205


Marlin 205


Mine 172


Mou 207


Naos 180


Nido 207


Ora 208


Pam 210


Plat 205


Pluma 182


Retro 166

Rose 202

Sabi 208

Saigon 160

Saipan 186

Samba 194

Savoy 196

Seven 212

Side 183

Slim 166

Stan 208

Stood 162

N

Tatawin 156

Sumba 186

Tree 198

Tupai 186

Venice 154

Vesper 196

Vico 158

Whizz 170

Winch 205

Bath
Baño

Brume 202

Spot
Foco


Coco 398


Lao 396


Link 404


Orleans 402


Ring 404


Stan 394


Stone 400

Recessed
Empotrable


Argón 419


Clear 422

N


Click 422


Croc 832


Domino 408


Ebba 424


Fox 426


Fresh 428

Gas 420


Hyde 414


Koi-2 421


Loke 333

Luan 433


Moist 427


Nais 421


Navi 411


Neon 420


Neu 410


Nord 410

Plas 412


Radón 418


Radón 418


Radón 418


Signal 410

Son 432


Stan 424


Suau 340


Ted 433

Tod 433


Wabi 424


Wet 422

Track
Carril


Link 436


Orleans 436

Plot 438

Stan 438

Portable
Portátil



Argus
58

Balda
60



Brot
460



Cage
58



Cat
458



Fuji
44



Kasp
54



Kerala
58



Task
60

Toc
56



Versus
456



Voila
60

Post
Sobremuro



Block
466



Blubs
482



Datna
472



Giza
478



Mauren
488



Mila
486



Mistu
482



Moon
482



Muffin
482



Muga
478



Nala
488



Naya
498



Rush
508



Screen
512



Spy-1
500



Twist
470



Wilma
479

Pole
Farola

Beret
520



Blubs
522



Bu-Oh
518



Datna
518

Grop
520



Mistu
522



Muffin
522



Nautica
526



Plaza
520



Rush
510



Screen
514

Tram
518

Floor
Suelo

Akane
452

N

Saigon
446

Toc
56

Bollard
Baliza


Agra
498


Alp
496

N

Balic
464


Bast
504


Beret
480

N

Bezel
504


Block
466


Brot
460


Blubs
484


Bu-Oh
494


Cast
468


Das
496


Datna
472


Gina
500


Grow
492


Giza
478


Kila
474


Klamp
502


Logar
481


Lotus
466


Mistu
484


Moon
484


Muga
478


Muffin
484


Nanda
480


Onze
479


Plim
476


Rush
508


Saura
502


Screen
512


Soleil
502


Shelby
470


Spy-2
500


Sticker
472

N

Totem
462


Tram
472


Twist
470


Wilma
479

Spike
Estaca


Andy
544


Balder
544

N

Bambou
538

N

Bezel
540

Flow
548

Foc
542

Leaf
530

Piccola
537

Plom
544

N

Saigon
534

Seth
542

Slot
546

Sobek
544

N

Spy-1
540

Toni
536

Tono
545

Voila
60

Suspended
Colgante



Blubs
570



Mistu
570



Moon
570



Muffin
570



Nautica
571

N



Saigon
558



Scuba
568



Wilma
571

Ceiling
Techo

N



Anga
574



Dakron
574



Goz
577



Kila
577



Mauren
488



Olot
576



Tami
576



Tasa
577



Yen
576

Recessed
Empotrable



Carter
648



Crosby
655



Curtis
655



Dang
643



Dart
646



Edel
662



Esca
645



Falls
664



Frol
644



Galo
642



Geiser
659



Gron
644



Grund
652



Kane
656



Led-18
661



Lio
662



Liso
645



Nase
642



Nat
650



Racing
648



Salt
661



Sedna
651



Soun
650

Spark-1
648

Stripe-1
645

Stripe-2
644

Suria
660

Taro
662

Tecno
662

Tras
657

Uve
643

Projector
Proyector



Alfa
550



Foc
555



Lit
555



Muur
552



Noboru
486



Oko
554



Plom
554



Project
550



Slot
546



Toran
554

Surface
Superficie



Aday
620



Alp
614



Ancora
612



Argot
597



Axel
614



Balic
583



Blind
624



Block
586



Blubs
594



Bonn
607



Borda
600



Bracket
614



Bronx
582



Brow
632



Bruc
623



Bu-Oh
610



Cabo
600



Canon
625



Cela
608



Dado
597



Datna
592



Derby
609



Doro
616



Dragma
612



Drak
632



Ele
626



Estay
609



Estoril
599



Fedón
608



Flow
548

Fred
606

Future
610

Gina
627

Grada
637

Grant
636

Half
586

Hikari
605

Kaula
620

Keenan
634

Kerala
590

Kila
592

Klamp
630

Kubick
605

Lace
623

Lacre
624

Lako
616

Ling
623


Log 624


Loth 633

Lotus 610


Lur 605


Mask 584


Mistu 594


Mol 606


Moon 594


Muffin 594


Must 638


Nahir 600


Nairobi 626


Nala 602


Natron 607


Nautica 598


Negus 607


Noray 600


Olan 625


Orwell 590


Oval 615


Pals 584


Pivot 602


Pol 606


Pomo 602


Proa 628


Path 636

Pill 632


Pill 632


Steps 628


Sticker 612


Suma 630


Sun 604


Sunset 625


Quart 615

Scuba 588


Tacana 617


Taima 627


Takua 615


Tamashi 602


Tane 622

Tejo 607

Thon 618

Timon 600

Tinia 626

Toc 596

Toluca 617

Tom 604

Tond 618

Tone 580

Tram 586

Twist 584

View 612

Wally 599

West 622

Wilma 596

Wood 627

XL



Andros
691



Aoba
695



Attos
689

Century
703

Cies
693



Just Fan
697



Kauai
687



Khios
683



Lantau
699



Manhattan
685



Tilos
701

L



Alo
705



Aloha
759

N



Amelia
723



Barth
727

Cocos
716



Cuba
760



Gotland
731

N



Heywood
719



Hydra
717

Ibiza
756



Icaria
755



Ice
745

Indus
714



Islot
735



Lama
713

N



Lantau
741



Lombok
758

Luzon
747



Mallorca
757



Malvinas
715

Meno
730



Milos
729



Morea
711



Nias
752



Palk
751

Pemba
750



Punt
763

Polaris
749



Poros
739

Polea
746

Rodas
737

Samos
733

Saona
734

Sioux
748

Siros
732

Tonic
709

Tonsay
753

Vulcano
707

M



Cooper
767



Deco Fan
775



Eco indus
788



Eterfan
771



Fraser
789



Izaro
761



Just Fan
773



Mini Eterfan
769

Mini Tube
777

Nassau
781



Panay
785

Tube
779

Typhoon
765



Winche
783



Yakarta
787

S



Cebu
798



Chicago
801



Easy
797



Feroe
792

N



Heywood
802



Hvar
799



Just Fan
805



Keiki
809



Lisboa
796

Mediterraneo
803



Mini Icaria
791

Mini Indus
800

N



Mini Lantau
795



Mini Mallorca
793



Palao
807



Vedra
808

portables
portátiles

Fuji by Isaac Piñeiro

reddot winner 2021

GERMAN DESIGN AWARD WINNER 2022





IN &OUT

Fuji

74465 ● Satin Black/Negro Satinado

Material	**Body** Aluminium+PC/Aluminio+PC **Diff** Opal White PC/PC Blanco Opal **Shade** Aluminium/Aluminio
Light Source	SMD LED 2W 2700K 90lm
Dimmable W	0.5w 25lm / 1w 45lm / 1.5w 90lm
CRI	>80
Class	III
Voltage (V/Hz)	5V DC
IP	44
IK	04
Battery incl.	Yes 6h Charge Max. 10h Worktime
USB	USB-C

DIM Hook ✔





25lm 45lm 90lm

PRICES

Take Away by Nahtrang



Accessories/Accesorios



Wall lamp/Aplique

01017 Beech/Haya

Material **Body** Wood/Madera



30lm 55lm 100lm

Take Away

01015 Matt White/Blanco Mate

01016 Matt Black/Negro Mate

Material	**Body** ABS+Wood/ABS+Madera
	Diff White TPU/TPU Blanco
Light Source	COB LED 2W 2700K 100lm
Dimmable W	0,5w 30lm / 1w 55lm / 1,5w 100lm
CRI	>80
Class	III
Voltage (V/Hz)	5V DC
IP	20
Battery incl.	Yes
	5h Charge Max. 5h Worktime
USB	MICRO USB

DIM



PRICES

Buddy by Andreu Carulla

reddot winner 2021

GERMAN DESIGN AWARD WINNER 2022









Buddy

20210	Opal White/Blanco Opal + Green/Verde
20209	Opal White/Blanco Opal + Blue/Azul
20208	Opal White/Blanco Opal + Dark Grey/Gris Oscuro

Material	**Body** PC
	Diff Opal PC/PC Opal
	Shade PC
Light Source	SMD LED 3W 2700K 260lm
CRI	>80
Class	III
Voltage (V/Hz)	5V DC
IP	20
Battery incl.	Yes
	9h Charge Max. Max. 10h Worktime
USB	PIN MAGNETICO

DIM





PRICES



Hook by Oiko Design

reddot award 2018 winner

GERMAN DESIGN AWARD WINNER 2020

Green Product Award Winner 2018





Hook

28369	Matt Black/Negro Mate
28365	Brown/Marrón

Material	**Body** Recycled PP/PP Reciclado
	Diff Opal PP/PP Opal
Light Source	1 E27 max. 5W
Bulb incl.	Yes
Recom. Bulb	17462
Class	II
IP	20
Cable	4.2 MT



Accessories/Accesorios

Magazine Rack/Revistero
28366

Shelve/Estantería
28367

Wall lamp/Aplique
28368

PRICES



Candela by Estudi Ribaudí



IN &OUT

Candela

70790 Terracotta/Terracota

Material	**Body** Polystone
	Diff Opal PC/PC Opal
Light Source	SMD LED 3W 3000K 290lm
CRI	=80
Class	III
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
Battery incl.	Yes
	8 a 10h Charge Max. 6h Worktime
USB	NO

DIM



PRICES



Lampanot by Cristina Borràs



Lampanot

70496 Matt White/Blanco Mate

Material	**Body** PEMD
	Diff Opal PEMD/PEMD Opal
Light Source	SMD LED 1W 3000K 80lm
CRI	>80
Class	III
Voltage (V/Hz)	5V DC/50-60Hz
IP	54
Battery incl.	Yes
	2h Charge Max. 4h Worktime
USB	MINI USB



PRICES



IN &OUT

SOLAR





2700K



3000K

Kasp 300

71912 ● Black/Negro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 2W 150lm
Dimmable K	2700 - 3000K
CRI	>80
Class	III
IP	65
Battery incl.	Yes
	20h Charge Max. 20h Worktime
USB	USB-C

DIM



IN &OUT

SOLAR





2700K



3000K

Kasp 500

71913 ● Black/Negro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 2W 150lm
Dimmable K	2700 - 3000K
CRI	>80
Class	III
IP	65
Battery incl.	Yes
	20h Charge Max. 20h Worktime
USB	USB-C

DIM





Wall accessory/Accesorio aplique

71914 ● Black/Negro

Material **Body** Aluminium/Aluminio

PRICES



Kasp wall Ref. 71912+71914

IN &OUT







Toc 380

70775	Matt White/Blanco Mate
70776	Matt Black/Negro Mate
70777	Grey/Gris

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 2W 3000K 180lm
Class	III
Voltage (V/Hz)	5V DC
IP	54
Battery incl.	Yes
	5h Charge Max. 9h Worktime
USB	MICRO USB

DIM



IN &OUT



Toc 1500

70786	Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 5W 3000K 468lm
Class	III
Voltage (V/Hz)	5V DC/50-60Hz
IP	54
Battery incl.	Yes
	9h Charge Max. 9h Worktime
USB	JACK

Wall
596



PRICES



Toc floor Ref. 70786

IN &OUT



Cage

75608 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 12W 2700K 990lm
CRI	>=80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Cable	2 MT



IN &OUT



Argus

70784 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	SMD LED 2W 3000K 220lm
CRI	>80
Class	III
Voltage (V/Hz)	5V DC
IP	54
Battery incl.	Yes
	5h Charge Max. 9h Worktime
USB	MICRO USB



IN &OUT




100lm


250lm


400lm

Kerala

74454 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 5W 3000K 400lm
Dimmable W	100lm / 250lm / 400lm
CRI	>80
Class	III
IP	54
Battery incl.	Yes
	8h Charge Max. 6h Worktime
USB	MICRO USB

DIM


Wall
590



PRICES



Cage portable Ref. 75608




16lm


103lm


263lm

Task

70914 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 2W 3000K 263lm
Dimmable W	16lm / 103lm / 263lm
CRI	>=80
Class	III
Voltage (V/Hz)	5V DC
IP	54
Battery incl.	Yes
	5h Charge Max. 6h Worktime
USB	USB-C

DIM





Balda 400

70498 Matt White/Blanco Mate

Material	**Body** PEMD
	Diff Opal PEMD/PEMD Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	55
Cable	1.8 MT





Balda 500

70499 Matt White/Blanco Mate

Material	**Body** PEMD
	Diff Opal PEMD/PEMD Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	55
Cable	1.8 MT













Voila

71565 Matt Black/Negro Mate

Material	**Body** ABS
	Diff Opal PEMD/PEMD Opal
Light Source	RGB LED 2W 3000K
Class	III
Voltage (V/Hz)	5V DC
IP	44
Battery incl.	Yes
	10h Charge Max. 7h Worktime
USB	MICRO USB



PRICES



Task portable Ref. 70914

indoor interior



Tatawin floor lamp Ref. 20336-119
designed by Adolfo Abejón

indoor interior

table & floor
mesa y suelo

Inviting by Bohman And Folenius

reddot award 2019
winner

DESIGN AWARD 2019

GERMAN DESIGN AWARD SPECIAL 2019







Inviting

57315	Matt White/Blanco Mate
57316	Matt Black/Negro Mate
57317	Yellow/Amarillo

Material	**Body** Aluminium/Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	SMD LED 6W 410lm
Dimmable K	2700 - 4800K
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	1.9 MT

DIM DIM 180º 90º Driver









Inviting

57312	Matt White/Blanco Mate
57313	Black/Negro
57314	Yellow/Amarillo

Material	**Body** Aluminium+Steel/Aluminio+Acero
	Diff Transparent/Transparente
Light Source	SMD LED 6W 410lm
Dimmable K	2700 - 4800K
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	1.9 MT

DIM DIM



Wall
248



PRICES



1968 by Jordi Busquets



1968

28372 Walnut/Nogal

Material	**Body** Wood/Madera
	Shade Textile/Textil
Light Source	SMD LED 8W 3000K 800lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	2.8 MT

DIM



PRICES



Hoshi by Xjer Studio







Hoshi

28387	Satin Gold/Oro Satinado + Matt Black/Negro Mate
28388	Black/Negro + Copper/Cobre

Material	**Body** Steel/Acero
	Diff Opal PC/PC Opal
Light Source	SMD LED 12W 3000K 930lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	2 MT

DIM



PRICES

Ten by Faro Lab











Ten

62156	Shiny Copper/Cobre Brillo
62157	Satin Gold/Oro Satinado
62168	Matt White/Blanco Mate
62169	Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.5 MT



Wall
361

PRICES



Niko by Nahtrang





1W 80lm



4W 250lm



7W 500lm



Niko Glass

01007A Matt White/Blanco Mate + Wood/Madera

Material	**Diff** Opal Glass/Cristal Opal

Niko PC

01025A Matt White/Blanco Mate + Wood/Madera

Material	**Body** Aluminium+Wood/Aluminio+Madera
	Diff Opal PC/PC Opal
Light Source	SMD LED 7W 3000K 500lm
Dimmable W	1w 80lm / 4w 250lm / 7w 500lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

DIM





Wall
278

PRICES

Mine by Nahtrang







Mine Glass

28378	Matt White/Blanco Mate + Wood/Madera
28379	Dark Grey/Gris Oscuro + Wood/Madera
Material	**Diff** Opal Glass/Cristal Opal

Mine PC

28211	Matt White/Blanco Mate + Wood/Madera
28212	Dark Grey/Gris Oscuro + Wood/Madera
Material	**Body** Aluminium+Wood/Aluminio+Madera
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2 MT

Suspended
172



PRICES







Eterna by Lucid Product Design

24008-13	Shiny Chrome/Cromo Brillo + White/Blanco
24008-14	Shiny Chrome/Cromo Brillo + Beige
24008-15	Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.8 MT



Wall
298



*Structures and shades also sold separately 822-824
Estructuras y pantallas también se venden por separado 822-824





Lula S by Marina Milà

28380	Matt White/Blanco Mate + White/Blanco
28382	Matt Black/Negro Mate + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.7 MT







Lula M by Marina Milà

28383	Matt White/Blanco Mate + White/Blanco
28385	Matt Black/Negro Mate + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.7 MT



PRICES



Eterna table lamp Ref. 24008-14
designed by Lucid



Sumba table S by Faro Lab

64317-71

Black/Negro + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	II
IP	20
Cable	1.5 MT



Suspended
186

Wall
292



Bliss

28401

Ash tree/Fresno + White/Blanco

Material	**Body** Wood/Madera
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.8 MT





Nidia

68423

Satin Nickel/Níquel Satinado + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.8 MT



PRICES



Sumba table lamp Ref. 64317-71
designed by Faro Lab



Anouk induction

53416 NEW Shiny White/Blanco Brillo

Material	**Body** ABS
	Diff Translucent/Translúcido
Light Source	SMD LED 8W
Dimmable K	2700K-6500K
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz

DIM DIM





Anouk

53415 Matt Black/Negro Mate

Material	**Body** ABS
	Diff Translucent/Translúcido
Light Source	SMD LED 8W 4000K 530lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	1.5 MT

DIM





Ito

52071 Matt Black/Negro Mate

Material	**Body** ABS+Aluminium/ABS+Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 5W 3000K 390lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	1.8 MT

DIM



PRICES



Anouk induction desk lamp Ref. 53416



Otto

52064	Matt Black/Negro Mate
52065	Matt White/Blanco Mate

Material	**Body** ABS+Silicone/ABS+Silicona
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 4000K 500lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	1.8 MT

DIM







Lena

52057	Shiny White/Blanco Brillo
52058	Shiny Black/Negro Brillo

Material	**Body** Aluminium+ABS+Silicone/Aluminio+ABS+Silicona
	Diff Translucent Glass/Cristal Translúcido
Light Source	SMD LED 3W 4000K 300lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	70°
Cable	1.8 MT







Snap

57400	White/Blanco
57401	Dark Grey/Gris Oscuro

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.8 MT



Wall
366



PRICES



Snap desk lamp Ref. 57400



Banker

68334 Old Gold/Oro Viejo + Green/Verde

Material	**Body** Steel/Acero
	Diff Glass/Cristal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.9 MT

180º







Gru

51916 Matt White/Blanco Mate

51917 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.7 MT









Baobab

51908 Matt White/Blanco Mate

51909 Matt Black/Negro Mate

51910 Grey/Gris

Material	**Body** Steel/Acero
Light Source	1 E14 max. 8W
Bulb incl.	No
Recom. Bulb	17461
Class	II
IP	20
Cable	1.7 MT



PRICES



Baobab desk lamp Ref. 51909

Tatawin by Adolfo Abejón NEW









Tatawin table

20337-116	Satin Black/Negro Satinado + Opal
20337-117	Satin Black/Negro Satinado + Shiny Black/Negro Brillo

Material	**Body** Steel/Acero
	Shade Glass/Cristal
Light Source	1 E27 G45 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	II
IP	20
Cable	1.5 MT

150º



Tatawin floor

20336-119	Satin Black/Negro Satinado + Opal
20336-120	Satin Black/Negro Satinado + Shiny Black/Negro Brillo

Material	**Body** Steel/Acero
	Shade Glass/Cristal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2 MT

150º

Suspended 156

Wall 257



PRICES



Tatawin floor lamp Ref. 20336-119
designed by Adolfo Abejón

Venice by Adolfo Abejón

NEW















Venice table

64276-115	Blue/Azul
64276-111	White/Blanco
64276-112	Shiny Black/Negro Brillo
64276-114	Black & White Gloss/Blanco y Negro Brillo
64276-113	Pink/Rosa

Material	**Body** Steel/Acero **Shade** Ceramic/Cerámica
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17063
Class	II
IP	20
Cable	1.5 MT

150º

PRICES



Venice floor

64275-115	Blue/Azul
64275-111	White/Blanco
64275-112	Shiny Black/Negro Brillo
64275-114	Black & White Gloss/Blanco y Negro Brillo
64275-113	Pink/Rosa

Material	**Body** Steel+Ceramic/Acero+Ceramica **Shade** Ceramic/Cerámica
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17063
Class	II
IP	20
Cable	2 MT

150º



Suspended
154



Wall
252





Venice table lamp Ref. 64276-111
designed by Adolfo Abejón

Luang by Faro Lab

NEW





Luang table S

23001-57	Black/Negro + Beige
23001-58	Black/Negro + Camel

Material	**Body** Steel/Acero
	Shade Papyrus/Papiro
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	II
IP	20
Cable	1.9 MT







Luang table M

23002-57	Black/Negro + Beige
23002-58	Black/Negro + Camel

Material	**Body** Steel/Acero
	Shade Papyrus/Papiro
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.9 MT







Luang floor

23003-59	Black/Negro + Beige
23003-60	Black/Negro + Camel

Material	**Body** Steel/Acero
	Shade Papyrus/Papiro
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.8 MT



Wall
244



PRICES



Luang floor lamp Ref. 23003-60
designed by Faro Lab

Academy by Nahtrang









Academy table

28202 Shiny Chrome/Cromo Brillo

Material	**Body** Aluminium+Steel/Aluminio+Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 4W 3000K 350lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	2 MT

DIM 350º



Academy floor

28205 Matt White/Blanco Mate

28204 Shiny Chrome/Cromo Brillo

Material	**Body** Aluminium+Steel/Aluminio+Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 3000K 550lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	2 MT

DIM 350º

Wall
250



PRICES



Academy floor lamp Ref. 28205
designed by Nahtrang

Jellyfish by Nahtrang





Jellyfish table

24522 Matt Black/Negro Mate + Matt Gold/Oro Mate

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 3000K 500lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	1.8 MT



Jellyfish floor

24521 Matt Black/Negro Mate + Matt Gold/Oro Mate

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 3000K 500lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	4.3 MT



PRICES



Jellyfish floor lamp Ref. 24521
designed by Nahtrang

Guadalupe by Faro Lab









Guadalupe table

20033-80	Matt Black/Negro Mate + Beige
20033-81	Matt Black/Negro Mate + Green/Verde

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT

360º



Guadalupe floor

20034-80	Matt Black/Negro Mate + Beige
20034-81	Matt Black/Negro Mate + Green/Verde

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	3.5 MT

360º



Wall
272



PRICES



Guadalupe floor lamp Ref. 20034-81
designed by Faro Lab

Levita by Nahtrang









Levita table

29692D Shiny Gold/Oro Brillo
29697 Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 6W 2700K 570lm
Dimmable W	1w 95lm / 4w 380lm / 6w 570lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	2 MT

DIM



Levita floor

29693D Shiny Gold/Oro Brillo
29698 Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 6W 2700K 570lm
Dimmable W	1w 95lm / 4w 380lm / 6w 570lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	2 MT

DIM



Suspended 168
Wall 264



PRICES



Levita floor lamp Ref. 29698
designed by Nahtrang

Loop by Estudi Ribaudí











1W 100lm



3W 300lm



6W 600lm

Loop table

29398 Matt Black/Negro Mate + Ash tree/Fresno
29568 Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Diff Translucent/Translúcido
	Shade Wood/Madera
Light Source	SMD LED 6W 2700K 600lm
Dimmable W	1w 100lm / 3w 300lm / 6w 600lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	2 MT

DIM 350º





Loop floor

29399 Matt Black/Negro Mate + Ash tree/Fresno
29569 Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Diff Translucent/Translúcido
	Shade Wood/Madera
Light Source	SMD LED 6W 2700K 600lm
Dimmable W	1w 100lm / 3w 300lm / 6w 600lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	2 MT

DIM 350º



Suspended
164



Wall
282



PRICES



Loop floor lamp Ref. 29569
designed by Estudi Ribaudí

Stood by Lucid Product Design





Stood table

29846 Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Shade Wood/Madera
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	2 MT



Stood floor

29847 Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Shade Wood/Madera
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	2 MT



Suspended 162

Wall 280



PRICES



Link by Estudi Ribaudí











Link table

29881	Matt White/Blanco Mate
29882	Matt Black/Negro Mate
29898	Bronze/Bronce

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	II
IP	20
Cable	1.9 MT



Link floor

29883	Matt White/Blanco Mate
29884	Matt Black/Negro Mate
29899	Bronze/Bronce

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	II
IP	20
Cable	1.9 MT





Ceiling
230

Spot
404

Track
436

Wall
404



PRICES



Link floor lamp Ref. 29899
designed by Estudi Ribaudí

Lao by Nahtrang









Lao table

29047	Matt Black/Negro Mate + Shiny Black/Negro Brillo
29048	Matt White/Blanco Mate + Shiny White/Blanco Brillo

Material	**Body** Aluminium+ABS/Aluminio+ABS
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 4W 3000K 400lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	2 MT





Lao floor

29049	Matt Black/Negro Mate + Shiny Black/Negro Brillo

Material	**Body** Aluminium+ABS/Aluminio+ABS
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 4W 3000K 400lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	2 MT



Spot
396



PRICES



Lao floor lamp Ref. 29049
designed by Nahtrang

Akane by Pepe Llaudet





Akane 350

28370 Matt Black/Negro Mate + Beige

Material	**Body** Steel/Acero
	Shade Papyrus/Papiro
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.7 MT



Akane 595

28371 Matt Black/Negro Mate + Beige

Material	**Body** Steel/Acero
	Shade Papyrus/Papiro
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.7 MT



PRICES



Akane floor lamp Ref. 28371
designed by Pepe Llaudet

Drum by Nahtrang









Drum table

24020-31	Matt Black/Negro Mate + Beige
24020-32	Matt Black/Negro Mate + Grey/Gris

Material	**Body** Steel/Acero **Diff** Opal PC/PC Opal **Shade** Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.8 MT



Drum floor

24023-33	Matt Black/Negro Mate + Beige
24023-34	Matt Black/Negro Mate + Grey/Gris

Material	**Body** Steel/Acero **Diff** Opal PC/PC Opal **Shade** Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	2.1 MT



PRICES



Drum table lamp Ref. 24020-31
designed by Nahtrang

Mambo by Faro Lab





Mambo table S

64317-47 Black/Negro + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



Mambo table

64311-48 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



Suspended
221



Wall
294



PRICES

*Structures and shades also sold separately 822-824 / *Estructuras y pantallas también se venden por separado* 822-824





Switch

Mambo floor

64313-49 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	I
IP	20
Cable	1.8 MT



PRICES

Samba by Faro Lab












Samba table S

64316-35	White/Blanco + Beige
64316-36	White/Blanco + Yellow/Amarillo
64316-37	White/Blanco + Green/Verde
64317-35	Black/Negro + Beige
64317-36	Black/Negro + Yellow/Amarillo
64317-37	Black/Negro + Green/Verde

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



Samba table

64310-38	Matt White/Blanco Mate + Beige
64310-39	Matt White/Blanco Mate + Yellow/Amarillo
64310-40	Matt White/Blanco Mate + Green/Verde
64311-38	Matt Black/Negro Mate + Beige
64311-39	Matt Black/Negro Mate + Yellow/Amarillo
64311-40	Matt Black/Negro Mate + Green/Verde

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



PRICES

*Structures and shades also sold separately 822-824 / *Estructuras y pantallas también se venden por separado* 822-824





Switch

Samba floor

64312-41	Matt White/Blanco Mate + Beige
64312-42	Matt White/Blanco Mate + Yellow/Amarillo
64312-43	Matt White/Blanco Mate + Green/Verde
64313-41	Matt Black/Negro Mate + Beige
64313-42	Matt Black/Negro Mate + Yellow/Amarillo
64313-43	Matt Black/Negro Mate + Green/Verde

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.8 MT





Suspended
194



Wall
284

PRICES

Conga by Faro Lab











Conga table S

64316-01	White/Blanco + White/Blanco
64316-02	White/Blanco + Beige
64317-03	Black/Negro + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



Conga table

64310-04	Matt White/Blanco Mate + White/Blanco
64310-05	Matt White/Blanco Mate + Beige
64311-06	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



PRICES

*Structures and shades also sold separately 822-824 / *Estructuras y pantallas también se venden por separado* 822-824





Switch

Conga floor

64312-07	Matt White/Blanco Mate + White/Blanco
64312-08	Matt White/Blanco Mate + Beige
64313-09	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.8 MT





Suspended
194



Wall
290

PRICES

Montreal by Nahtrang













Montreal table

24034-04	Matt White/Blanco Mate + White/Blanco
24034-05	Matt White/Blanco Mate + Beige
24035-04	Shiny Chrome/Cromo Brillo + White/Blanco
24035-05	Shiny Chrome/Cromo Brillo + Beige
24035-06	Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.8 MT



Montreal floor

24036-07	Matt White/Blanco Mate + White/Blanco
24036-08	Matt White/Blanco Mate + Beige
24037-07	Shiny Chrome/Cromo Brillo + White/Blanco
24037-08	Shiny Chrome/Cromo Brillo + Beige
24037-09	Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2.1 MT



Wall
288



PRICES

*Structures and shades also sold separately 822-824 / *Estructuras y pantallas también se venden por separado* 822-824



Montreal floor lamp Ref. 24036-07
designed by Nahtrang

Savoy by Isaac Piñeiro











Savoy table

20304-82	White/Blanco + White/Blanco
20305-83	Matt Black/Negro Mate + Black/Negro
20305-84	Matt Black/Negro Mate + Green/Verde

Material	**Body** Steel/Acero
	Diff White Steel/Acero Blanco
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2 MT



PRICES

Savoy floor

20306-85	Matt White/Blanco Mate + White/Blanco
20307-86	Matt Black/Negro Mate + Black/Negro
20307-87	Matt Black/Negro Mate + Green/Verde

Material	**Body** Steel/Acero
	Diff White Steel/Acero Blanco
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	2 MT



Suspended
196

Wall
286





Savoy table lamp Ref. 20305-84
designed by Isaac Piñeiro

Rem by Àlex & Manel Lluscà












Rem table

29684-04	Satin Nickel/Níquel Satinado + White/Blanco
29684-05	Satin Nickel/Níquel Satinado + Beige
29684-06	Satin Nickel/Níquel Satinado + Black/Negro
29685-04	Satin Bronze/Bronce Satinado + White/Blanco
29685-05	Satin Bronze/Bronce Satinado + Beige
29685-06	Satin Bronze/Bronce Satinado + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.6 MT



Rem floor

29686-07	Satin Nickel/Níquel Satinado + White/Blanco
29686-08	Satin Nickel/Níquel Satinado + Beige
29686-09	Satin Nickel/Níquel Satinado + Black/Negro
29687-07	Satin Bronze/Bronce Satinado + White/Blanco
29687-08	Satin Bronze/Bronce Satinado + Beige
29687-09	Satin Bronze/Bronce Satinado + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.9 MT



Wall
300



*Structures and shades also sold separately 822-824 / *Estructuras y pantallas también se venden por separado* 822-824



Rem floor lamp Ref. 29687-08
designed by Àlex & Manel Lluscà

Artis by Àlex & Manel Lluscà





Artis table

68488 Bronze/Bronce + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2.4 MT

350º



Artis floor

68489 Bronze/Bronce + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	3.2 MT

350º



Wall
296

PRICES



Artis floor lamp Ref. 68489
designed by Àlex & Manel Lluscà

Vesper by Nahtrang







Vesper table

29984 Matt White/Blanco Mate + Beige
29985 Brown/Marrón + Beige

Material	**Body** Steel/Acero
	Diff Beige Textile/Textil Beige
	Shade Textile/Textil
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.7 MT



Vesper floor

29979 Brown/Marrón + Beige

Material	**Body** Steel/Acero
	Diff Beige Textile/Textil Beige
	Shade Textile/Textil
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	II
IP	20
Cable	3.5 MT

Suspended
196



Wall
316



PRICES



Vesper floor lamp Ref. 29979
designed by Nahtrang

Linda by Estudi Ribaudí









Linda table

29307	Matt White/Blanco Mate + Beige
29311	Matt Black/Negro Mate + Beige

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2 MT



Linda floor

29312	Matt Black/Negro Mate + Beige

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	2.8 MT





Suspended 198 **Wall** 367

PRICES



Linda floor lamp Ref. 29312
designed by Estudi Ribaudí

Lupe by Jordi Busquets









Lupe table

29997 Shiny Chrome/Cromo Brillo + Beige

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.8 MT

360º



Lupe

20034-88 Matt Black/Negro Mate + Beige

29998 Shiny Chrome/Cromo Brillo + Beige

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	3.5 MT

360º



Wall
304



PRICES



Lupe floor lamp Ref. 20034-88
designed by Jordi Busquets

Tree by Estudi Ribaudí









Tree table

29866	Matt Black/Negro Mate + Black/Negro
29867	Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.8 MT



Tree floor

29868	Matt Black/Negro Mate + Black/Negro
29869	Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	2 MT

Suspended
198



PRICES



Tree floor lamp Ref. 29868
designed by Estudi Ribaudí

Berni by Nahtrang







Berni table

29332	Matt White/Blanco Mate + White/Blanco
29333	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Diff White Steel/Acero Blanco
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



Berni floor

29335	Matt White/Blanco Mate + White/Blanco
29336	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.5 MT





Wall
318

PRICES



Berni floor lamp Ref. 29335
designed by Nahtrang

Hotel by Àlex & Manel Lluscà









Hotel table

29942	Matt White/Blanco Mate + White/Blanco
29947	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Diff White/Blanco
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.9 MT





Hotel floor

29948	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Diff Black/Negro
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.9 MT



Suspended
198

Wall
310



PRICES



Hotel floor lamp Ref. 29948
designed by Alex & Manel Llusca

Volta by Estudi Ribaudí









Volta table

20025	Matt White/Blanco Mate + White/Blanco
20026	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2 MT



Volta floor

20029	Matt White/Blanco Mate + White/Blanco
20030	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2 MT



Wall
314

PRICES



Volta floor lamp Ref. 20030
designed by Estudi Ribaudí

Stand Up by Estudi Ribaudí











Stand Up

57211-01	Matt Black/Negro Mate + White/Blanco
57211-02	Matt Black/Negro Mate + Black/Negro
57211-03	Matt Black/Negro Mate + Grey/Gris

Material	**Body** Aluminium/Aluminio
	Shade Textilene
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2 MT

Driver



PRICES



Whizz by Christoph F.W.

salone satellite 20years of new creativity





Whizz

20164-95	Black/Negro + Satin Gold/Oro Satinado
20164-96	Satin Gold/Oro Satinado + Black/Negro

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17496
Class	II
IP	20
Cable	3.4 MT



Suspended
170

Wall
266



PRICES



Whizz floor lamp Ref. 20164-95
designed by Cristoph F.W.

Guest by Andreu Carulla



Guest

01046 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17429
Class	II
IP	20
Cable	1.8 MT

Wall
270



PRICES











Moma table

68500 Shiny Chrome/Cromo Brillo + White/Blanco
68501 Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Diff Opal PC/PC Opal
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.9 MT



Moma floor

68503 Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Diff Opal PC/PC Opal
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2.1 MT





Wall
327

PRICES

Sweet by Estudi Ribaudí





Sweet table

29955 Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Diff Black Textile/Textil Negro
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.9 MT



Sweet floor

29958 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Diff White Textile/Textil Blanco
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.7 MT





Wall
320

PRICES









Papua

68462	Matt White/Blanco Mate + White/Blanco
68463	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	2 MT



Black

29764	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	2.5 MT



PRICES



Black floor lamp Ref. 29764



Tatawin suspended Ref. 20339-116
designed by Adolfo Abejón

indoor interior

suspended
suspensión

Flash by Estudi Ribaudí



Flash

20201 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 10W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	1.5 MT

Driver ✔







Flash 4L

20203 Matt White/Blanco Mate

20207 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 38W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	1.5 MT

Driver ✔



PRICES



Flash suspended Ref. 20203
designed by Estudi Ribaudí

Confetti by Nutcreatives







Confetti 300

68600-50	White & Black/Blanco y Negro
68600-52	Multicolored shavings/Virutas multicolor
Material	**Body** Aluminium/Aluminio
	Shade Recycled PET/PET Reciclado
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT





Confetti 400

68600-51	White & Black/Blanco y Negro
Material	**Body** Aluminium/Aluminio
	Shade Recycled PET/PET Reciclado
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



Wall
246



PRICES



Venice by Adolfo Abejón










Venice

64255	Shiny White/Blanco Brillo
64256	Shiny Black/Negro Brillo
64258	Black & White Gloss/Blanco y Negro Brillo
64257	Gloss pink/Rosa brillante
64259 NEW	Blue/Azul

Material	**Body** Steel+Ceramic/Acero+Ceramica **Shade** Ceramic/Cerámica
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2.5 MT

Table&Floor
86

Wall
252



PRICES



Venice suspended Ref. 64256
designed by Adolfo Abejón

Tatawin by Adolfo Abejón

NEW





Tatawin lineal S

20338-116 Satin Black/Negro Satinado + Opal
20338-117 Satin Black/Negro Satinado + Shiny Black/Negro Brillo

Material	**Body** Steel/Acero
	Shade Glass/Cristal
Light Source	3 E27 G45 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	II
IP	20
Cable	2 MT







Tatawin S

20339-116 Satin Black/Negro Satinado + Opal
20339-117 Satin Black/Negro Satinado + Shiny Black/Negro Brillo

Material	**Body** Steel/Acero
	Shade Glass/Cristal
Light Source	1 E27 G45 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	II
IP	20
Cable	2 MT







Tatawin lineal M

20338-119 Satin Black/Negro Satinado + Opal
20338-120 Satin Black/Negro Satinado + Shiny Black/Negro Brillo

Material	**Body** Steel/Acero
	Shade Glass/Cristal
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2 MT







Tatawin M

20339-119 Satin Black/Negro Satinado + Opal
20339-120 Satin Black/Negro Satinado + Shiny Black/Negro Brillo

Material	**Body** Steel/Acero
	Shade Glass/Cristal
Light Source	1 E27 max. 15W
Bulb incl.	No
Class	II
IP	20
Cable	2 MT



Table&Floor 84



Wall 257



PRICES



Tatawin suspended Ref. 20338-119
designed by Adolfo Abejón

Vico by Faro Lab





Vico 600

61101 Matt Black/Negro Mate



Vico 600 canopy recessed

61105 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 15W 2700K 1500lm
CRI	>=90
Class	II
Voltage (V/Hz)	220V-240V/50Hz
IP	20
Cable	2 MT

TRIAC L DIM Driver



*More dimmable options under request/*Otras opciones de regulación bajo pedido*





Vico 1150

61103 Matt Black/Negro Mate

Vico 1150 canopy recessed

61104 Matt Black/Negro Mate



Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 30W 2700K 2800lm
CRI	>=90
Class	II
Voltage (V/Hz)	220V-240V/50Hz
IP	20
Cable	2 MT

TRIAC L DIM Driver



*More dimmable options under request/*Otras opciones de regulación bajo pedido*

Joint kit accessory/Accesorio kit unión



61117 Matt Black/Negro Mate

Material **Body** Steel/Acero

PRICES



Vico suspended Ref. 61104
designed by Faro Lab

Saigon by Nahtrang







Saigon in 700

20116	Matt Black/Negro Mate + Beige
20117	Matt Black/Negro Mate + White/Blanco
20118	Matt Black/Negro Mate + Terracotta/Terracota
20119	Matt Black/Negro Mate + Black/Negro
20120	Matt Black/Negro Mate + Yellow/Amarillo
20121	Matt Black/Negro Mate + Garnet/Granate
20122	Matt Black/Negro Mate + Green/Verde
20123	Matt Black/Negro Mate + Brown/Marrón

Material	**Body** Steel/Acero
	Diff Beige Papyrus/Papiro Beige
	Shade Textile ribbon/Cinta textil
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.6 MT





Saigon in 1300

20124	Matt Black/Negro Mate + Beige
20125	Matt Black/Negro Mate + White/Blanco
20126	Matt Black/Negro Mate + Terracotta/Terracota
20127	Matt Black/Negro Mate + Black/Negro
20128	Matt Black/Negro Mate + Yellow/Amarillo
20129	Matt Black/Negro Mate + Garnet/Granate
20130	Matt Black/Negro Mate + Green/Verde
20131	Matt Black/Negro Mate + Brown/Marrón

Material	**Body** Steel/Acero
	Diff Beige Papyrus/Papiro Beige
	Shade Textile ribbon/Cinta textil
Light Source	4 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.6 MT



PRICES



Saigon suspended Ref. 20128
designed by Nahtrang

Stood by Lucid Product Design



Stood

29848 Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Shade Wood/Madera
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	2 MT





Stood 5L

29849 Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Shade Wood/Madera
Light Source	5 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	2 MT



Table&Floor
100



Wall
280



PRICES



Stood suspended Ref. 29849
designed by Lucid Product Design

Loop by Estudi Ribaudí





Loop

29397	Matt Black/Negro Mate + Ash tree/Fresno
29567	Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Shade Wood/Madera
Light Source	SMD LED 18W 2700K 1050lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	1.2 MT
	Driver ✔



Table&Floor
98



Wall
282



PRICES



Loop suspended Ref. 29397
designed by Estudi Ribaudí



Slim

24504 Matt White/Blanco Mate

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 40W 3000K 1150lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	1.5 MT

Driver ✔

Wall
268







Retro

20046 Matt Copper/Cobre Mate + Matt Black/Negro Mate
20050 Matt Black/Negro Mate + Shiny Chrome/Cromo Brillo

Material	**Body** Steel/Acero
Light Source	1 E14 max. 8W
Bulb incl.	No
Recom. Bulb	17461
Class	I
IP	20
Cable	1.6 MT









Retro 12L

20047 Matt Copper/Cobre Mate + Matt Black/Negro Mate
20048 Matt Black/Negro Mate + Shiny Chrome/Cromo Brillo
20051 Matt Black/Negro Mate + Satin Gold/Oro Satinado

Material	**Body** Steel/Acero
Light Source	12 E14 max. 8W
Bulb incl.	No
Recom. Bulb	17461
Class	I
IP	20
Cable	3 MT

Wall
367



PRICES



Retro suspended Ref. 20051
designed by Alex & Manel Llusca

Levita by Nahtrang





Levita

29691	Shiny Gold/Oro Brillo
29696	Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 14W 2700K 530lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	1.5 MT

Driver ✔





Table&Floor
96



Wall
264





Levita pendant floor

29694	Shiny Gold/Oro Brillo
29699	Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 6W 2700K 250lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	1.5 MT

Driver ✔



*Max. ceiling height 3mts./*Altura max. techo 3mts.*

PRICES



Levita pendant floor Ref. 29699
designed by Nahtrang

Whizz by Christoph F.W.

salone satellite 20years of new creativity





Whizz

20160	Black/Negro + Satin Gold/Oro Satinado
20161	Satin Gold/Oro Satinado + Black/Negro

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17496
Class	II
IP	20
Cable	1.5 MT



Floor
140



Wall
266







Whizz pendant floor

20166-95	Black/Negro + Satin Gold/Oro Satinado
20166-96	Satin Gold/Oro Satinado + Black/Negro

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17496
Class	II
IP	20
Cable	3.4 MT





PRICES



Whizz suspended Ref. 20166-95
designed by Cristoph F.W.

Mine by Nahtrang

Restaurant & Bar Product Design Awards
Winner

GERMAN DESIGN AWARD SPECIAL 2018







Mine Glass

28375	Matt White/Blanco Mate
28376	Dark Grey/Gris Oscuro

Material	**Diff** Opal Glass/Cristal Opal

Mine PC

28209	Matt White/Blanco Mate
28210	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	4 MT

Table
73



PRICES



Thanks to DOS architects / Tavis Wright Photo by Tomeu Canyellas





Mine Glass Space

28375-1L	Matt White/Blanco Mate
28376-1L	Dark Grey/Gris Oscuro

Material **Diff** Opal Glass/Cristal Opal

Mine PC Space

28209-1L	Matt White/Blanco Mate
28210-1L	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2 MT





Mine Glass Space 2L

28375-2L	Matt White/Blanco Mate
28376-2L	Dark Grey/Gris Oscuro

Material **Diff** Opal Glass/Cristal Opal

Mine PC Space 2L

28209-2L	Matt White/Blanco Mate
28210-2L	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	4 MT





Mine Glass Space 3L

28375-3L	Matt White/Blanco Mate
28376-3L	Dark Grey/Gris Oscuro

Material **Diff** Opal Glass/Cristal Opal

Mine PC Space 3L

28209-3L	Matt White/Blanco Mate
28210-3L	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	6 MT

PRICES





Mine Glass Space 4L

28375-4L	Matt White/Blanco Mate
28376-4L	Dark Grey/Gris Oscuro

Material	**Diff** Opal Glass/Cristal Opal

Mine PC Space 4L

28209-4L	Matt White/Blanco Mate
28210-4L	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	4 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	8 MT





Mine Glass Space 5L

28375-5L	Matt White/Blanco Mate
28376-5L	Dark Grey/Gris Oscuro

Material	**Diff** Opal Glass/Cristal Opal

Mine PC Space 5L

28209-5L	Matt White/Blanco Mate
28210-5L	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	5 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	10 MT

Hook accessory/Accesorio gancho



28373 Matt White/Blanco Mate



28374 Dark Grey/Gris Oscuro

Tell us your needs and we will make it happen

Dinos tus necesidades y lo hacemos realidad

Send your demand on / *envíanos tu petición a* **customize@faro.es**

PRICES



Dolme by Xjer Studio

64099 Matt White/Blanco Mate

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 23W 3000K 1260lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	1.6 MT

Driver ✔



Ceiling
228







Cocotte 430 by Jordi Llopis

64262 Shiny White/Blanco Brillo

64263 Shiny Black/Negro Brillo

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 30W 3000K 1300lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔



Ceiling
228







Cocotte 550 by Jordi Llopis

64260 Shiny White/Blanco Brillo

64261 Shiny Black/Negro Brillo

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 36W 3000K 1700lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔



PRICES



Dolme suspended Ref. 64099
designed by Xjer Studio

Kombo by Nutcreatives





Kombo 120

68591-1L Grey/Gris
68592-1L Beige/Beige

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT







Kombo 200

68593-1L Grey/Gris
68594-1L Beige/Beige

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT









Kombo 400

68595-1L Grey/Gris
68596-1L Beige/Beige
68597-1L Terracotta/Terracotta

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



PRICES



Kombo suspended Ref. 68591-1L
designed by Nutcreatives

Naos by Àlex & Manel Lluscà



Naos 233

64500 Beige

Material	**Body** Steel+Glass/Acero+Cristal
	Diff Opal Glass/Cristal Opal
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	1.8 MT





Naos 400

64501 Beige

Material	**Body** Steel+Glass/Acero+Cristal
	Diff Opal Glass/Cristal Opal
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	1.8 MT



Two-colour ring accessory incl. / Accesorio anillo dos colores incl.



PRICES



Naos suspended Ref. 64501
designed by Àlex & Manel Ljuscà

Pluma by Nahtrang





Pluma

64172 Matt Black/Negro Mate + Matt Gold/Oro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 3000K 450lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	1.5 MT

Driver ✔



PRICES

Side by Àlex & Manel Lluscà







Side 200

62138	Matt Black/Negro Mate + Satin Gold/Oro Satinado
62139	Matt Black/Negro Mate + Satin Copper/Cobre Satinado

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	1 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17443
Class	II
IP	20
Cable	1.5 MT



Ceiling
226



PRICES

Costas by Àlex & Manel Lluscà



Costas 600

68590-69 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	II
IP	20
Cable	1.5 MT





Costas 1000

68590-70 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	II
IP	20
Cable	1.5 MT



Wall
258



Hook accessory incl. / Accesorio gancho incl.



PRICES



Costas suspended Ref. 68590-69
designed by Àlex & Manel Lluscà



Saipan

65134-76 Black/Negro + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	I
IP	20
Cable	2 MT





Tupai

65134-77 Black/Negro + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	I
IP	20
Cable	2 MT





Sumba by Faro Lab

65134-72 Black/Negro + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	I
IP	20
Cable	2 MT



Table
76



Wall
292



PRICES



Tupai suspended Ref. 65134-77



Haka 250

65134-73

Black/Negro + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	I
IP	20
Cable	2 MT





Haka 300

65134-74

Black/Negro + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	I
IP	20
Cable	2 MT





Haka 530

65134-75

Black/Negro + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	I
IP	20
Cable	2 MT



PRICES



Haka suspended Ref. 65134-73

Mambo by Faro Lab



Mambo 210

64315-47 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.7 MT





Mambo 320

64315-48 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.7 MT





Mambo 450

64315-49 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.7 MT



Table&Floor 110



Wall 294



PRICES

*Structures and shades also sold separately 821-824 / *Estructuras y pantallas también se venden por separado 821-824*



Mambo suspended Ref. 64315-49
designed by Faro Lab

Mambo by Faro Lab



Mambo 210 displaced canopy

64314-47 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT





Mambo 320 displaced canopy

64314-48 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT





Mambo 450 displaced canopy

64314-49 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



PRICES

*Structures and shades also sold separately 821-824 / *Estructuras y pantallas también se venden por separado 821-824*



Mambo suspended Ref. 64314-48
designed by Faro Lab





Samba by Faro Lab

64315-44	Matt Black/Negro Mate + Beige
64315-45	Matt Black/Negro Mate + Yellow/Amarillo
64315-46	Matt Black/Negro Mate + Green/Verde



Material	**Body** Steel/Acero
	Diff Papyrus/Papiro
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.7 MT







Samba displaced canopy by Faro Lab

64314-44	Matt Black/Negro Mate + Beige
64314-45	Matt Black/Negro Mate + Yellow/Amarillo
64314-46	Matt Black/Negro Mate + Green/Verde



Material	**Body** Steel/Acero
	Diff Papyrus/Papiro
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



Table&Floor
112



Wall
284







Conga by Faro Lab

64315-54	Matt Black/Negro Mate + White/Blanco
64315-55	Matt Black/Negro Mate + Beige
64315-56	Matt Black/Negro Mate + Black/Negro



Material	**Body** Steel/Acero
	Diff Papyrus/Papiro
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.7 MT



Table&Floor
115



Wall
290







Conga displaced canopy by Faro Lab

64314-54	Matt Black/Negro Mate + White/Blanco
64314-55	Matt Black/Negro Mate + Beige
64314-56	Matt Black/Negro Mate + Black/Negro



Material	**Body** Steel/Acero
	Diff Papyrus/Papiro
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT



PRICES

*Structures and shades also sold separately 821-824 / *Estructuras y pantallas también se venden por separado 821-824*



Samba suspended Ref. 64315-45
designed by Faro Lab





Savoy by Isaac Piñeiro

20308-89	White/Blanco + White/Blanco
20309-90	Black/Negro + Black/Negro
20309-91	Black/Negro + Green/Verde

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	0.8



Table&Floor
118



Wall
286





Vesper 400 by Nahtrang

29988	Matt White/Blanco Mate + Beige

Material	**Body** Steel/Acero
	Diff Opal PC/PC Opal
	Shade Textile/Textil
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	2 MT



Table&Floor
124



Wall
316







Vesper 600 by Nahtrang

29986	Matt White/Blanco Mate + Beige
29987	Brown/Marrón + Beige

Material	**Body** Steel/Acero
	Diff Opal PC/PC Opal
	Shade Textile/Textil
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	2 MT



PRICES



Savoy suspended Ref. 20308-89
designed by Isaac Piñeiro



Hotel by Àlex & Manel Lluscà

29944 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Diff White/Blanco
	Shade Textile/Textil
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	1 MT



Table&Floor
134



Wall
310





Fusta by Àlex & Manel Lluscà

28394 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel+Wood/Acero+Madera
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	I
IP	20
Cable	1.7 MT







Linda by Estudi Ribaudí

29309 Matt White/Blanco Mate + Beige

29313 Matt Black/Negro Mate + Beige

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	I
IP	20
Cable	1.2 MT



Table&Floor
126



Wall
367







Tree by Estudi Ribaudí

29864 Matt Black/Negro Mate + Black/Negro

29865 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	1.3 MT



Table&Floor
130



PRICES



Hotel suspended ref. 29944
designed by Àlex & Manel Lluscà



Crater

68461 Matt Black/Negro Mate + Matt Gold/Oro Mate

Material	**Body** Aluminium/Aluminio
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	1.5 MT









Magma

28398 Matt White/Blanco Mate + Matt Silver/Plata Mate
28399 Matt White/Blanco Mate + Matt Gold/Oro Mate
29468 Black/Negro + Matt Gold/Oro Mate

Material	**Body** Fiber glass/Fibra de vidrio
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	I
IP	20
Cable	2 MT







Margot

68561 Matt Black/Negro Mate + Wood/Madera
68564 Matt White/Blanco Mate + Wood/Madera

Material	**Body** Steel+Wood/Acero+Madera
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	I
IP	20
Cable	1.2 MT







Charlotte

68562 Dark Grey/Gris Oscuro
68563 Matt White/Blanco Mate

Material	**Body** Steel/Acero
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	I
IP	20
Cable	1.2 MT



PRICES



Crater suspended Ref. 68461
Project by Elena Castells Poch



Brume by Àlex & Manel Lluscà

40078 Anthracite/Antracita

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 3W 2700K 200lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44
Cable	1 MT

Driver ✔



Ceiling
240



Wall
382





Rose

65082 Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17429
Class	II
IP	20
Cable	1.5 MT





Rose 4L

65081 Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	4 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17429
Class	I
IP	20



PRICES



Brume suspended Ref. 40078
designed by Àlex & Manel Lluscà





Art

64137 Old Gold/Oro Viejo
65134 Black/Negro

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17425
Class	I
IP	20
Cable	1.5 MT





Liz

65080 Old Gold/Oro Viejo

Material	**Body** Steel+Glass/Acero+Cristal
	Diff Transparent/Transparente
	Shade Glass/Cristal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17428
Class	I
IP	20
Cable	1.3 MT





Clara

64128 Matt Black/Negro Mate + Transparent/Transparente

Material	**Body** Steel/Acero
	Shade Glass/Cristal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17428
Class	I
IP	20
Cable	2 MT





Halita

65071 Old Gold/Oro Viejo + Transparent/Transparente

Material	**Body** Steel+Glass/Acero+Cristal
	Shade Glass/Cristal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17428
Class	I
IP	20
Cable	1.5 MT



PRICES



Marlin

64133 Old Gold/Oro Viejo + Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17428
Class	I
IP	20
Cable	1.5 MT

Wall
364







Plat

68145 Matt Black/Negro Mate
68146 Matt White/Blanco Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17271
Class	II
IP	20
Cable	1.5 MT





Marina

60004 Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17428
Class	II
IP	20
Cable	1.5 MT

Wall
363





Winch polley by Àlex & Manel Lluscà

66205 Dark Brown/Marrón Oscuro

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	1.5 MT



PRICES





Lou

62800	Shiny Black/Negro Brillo
62801	Shiny Green/Verde Brillo

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	0.9 MT







Lang

62804	Shiny Black/Negro Brillo
62805	Shiny Green/Verde Brillo

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	I
IP	20
Cable	1.4 MT







Claire

62802	Shiny Black/Negro Brillo
62803	Shiny Green/Verde Brillo

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	I
IP	20
Cable	1.4 MT



PRICES



Mou

62806 Shiny Black/Negro Brillo

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	1.1 MT

350º





Liana

68569 Black/Negro + Natural Hemp/Cáñamo Natural

Material	**Body** Steel/Acero
	Shade Hemp/Cáñamo
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	I
IP	20
Cable	1.2 MT





Nido

68153 Matt Black/Negro Mate + Brown/Marrón

Material	**Body** Steel/Acero
	Shade Cane/Caña
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	I
IP	20
Cable	1.5 MT



PRICES





Ora

29894 Matt White/Blanco Mate
29895 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	SMD LED 4W 3000K 350lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	120°
Cable	1.5 MT

Driver ✔







Sabi

64320 Matt White/Blanco Mate
64321 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	SMD LED 3W 2700K 280lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°
Cable	1.2 MT

Driver ✔







Stan

43754 Matt White/Blanco Mate
43755 Matt Black/Negro Mate
43756 Satin Gold/Oro Satinado



Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20
Cable	1.2 MT


Ceiling 235


Recessed 424


Spot 392


Track 438


Wall 372



PRICES



Stan suspended Ref. 43756



Cosmos

64224 Bronze/Bronce

Material	**Body** Aluminium+Steel/Aluminio+Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 5W 3000K 360lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	180°
Cable	1.4 MT
	Driver ✔







Pam 165

64159 Matt White/Blanco Mate

64160 Black/Negro + Matt Gold/Oro Mate

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 11W 3000K 900lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	120°
Cable	1.5 MT
	Driver ✔





Pam 250

64162 Black/Negro + Matt Gold/Oro Mate

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 24W 3000K 1875lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	120°
Cable	1.5 MT
	Driver ✔





Danka

64223 Satin Gold/Oro Satinado + Matt Black/Negro Mate

Material	**Body** Steel+Aluminium/Acero+Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	COB LED 6W 3000K 530lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	60°
Cable	3 MT
	Driver ✔



PRICES



Pam 250 suspended Ref. 64162



Aina

64174 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Diff Opal PC/PC Opal
	Shade Textile/Textil
Light Source	SMD LED 40W 2700K 3000lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
Cable	1.3 MT

Driver ✔





Seven 400

68283 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Diff White Textile/Textil Blanco
	Shade Textile/Textil
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	0.9 MT



Ceiling
236





Seven 500

68284 White/Blanco + White/Blanco

Material	**Body** Steel/Acero
	Diff White Textile/Textil Blanco
	Shade Textile/Textil
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20
Cable	0.9 MT



PRICES



Aina suspended Ref. 64174

Soluciones de instalación

Installation solutions

Standard requests



See standard combination pages 215-219
Ver tabla combinaciones en páginas 215-219

Special requests



Send your demand on / envíanos tu petición a
customize@faro.es

	3 lights / *luces*	5 lights / *luces*	7 lights / *luces*
Kombo			
	68591-3L 68592-3L	68591-5L 68592-5L	68591-7L 68592-7L
	68593-3L 68594-3L	68593-5L 68594-5L	68593-7L 68594-7L
	68595-3L 68596-3L 68597-3L	68595-5L 68596-5L 68597-5L	68595-7L 68596-7L 68597-7L
Mambo			
	64314-47-3L	64314-47-5L	64314-47-7L
	64314-48-3L	64314-48-5L	64314-48-7L
	64314-49-3L	64314-49-5L	64314-49-7L

PRICES

		3 lights / *luces*	5 lights / *luces*	7 lights / *luces*
Conga				
		64314-54-3L 64314-55-3L 64314-56-3L	64314-54-5L 64314-55-5L 64314-56-5L	64314-54-7L 64314-55-7L 64314-56-7L
Samba				
		64314-44-3L 64314-45-3L 64314-46-3L	64314-44-5L 64314-45-5L 64314-46-5L	64314-44-7L 64314-45-7L 64314-46-7L
Retro				
		20046-3L 20050-3L	20046-5L 20050-5L	20046-7L 20050-7L
Plat				
		68145-3L 68146-3L	68145-5L 68146-5L	68145-7L 68146-7L

PRICES

		3 lights / *luces*	5 lights / *luces*	7 lights / *luces*
Art				
		64135-3L ● 64137-3L ◒	64135-5L ● 64137-5L ◒	64135-7L ● 64137-7L ◒
Liz				
		65080-3L ◒	65080-5L ◒	65080-7L ◒
Marlin				
		64133-3L ◒	64133-5L ◒	64133-7L ◒
Clara				
		64128-3L ◓	64128-5L ◓	64128-7L ◓

PRICES

		3 lights / *luces*	5 lights / *luces*	7 lights / *luces*
Claire				
		62802-3L ● 62803-3L ●	62802-5L ● 62803-5L ●	62802-7L ● 62803-7L ●
Lang				
		62804-3L ● 62805-3L ●	62804-5L ● 62805-5L ●	62804-7L ● 62805-7L ●
Whizz				
		20160-3L ● 20161-3L ●	20160-5L ● 20161-5L ●	20160-7L ● 20161-7L ●

PRICES

Tatawin S

NEW



3 lights / *luces*	5 lights / *luces*	7 lights / *luces*
		
20340-116-3L ●○	20340-116-5L ●○	20340-116-7L ●○
20340-117-3L ●●	20340-117-5L ●●	20340-117-7L ●●

Tatawin M

NEW



		
20340-119-3L ●○	20340-119-5L ●○	20340-119-7L ●○
20340-120-3L ●●	20340-120-5L ●●	20340-120-7L ●●

Venice

NEW



		
64255-115-3L NEW ●●	64255-115-5L NEW ●●	64255-115-7L NEW ●●
64255-111-3L NEW ●○	64255-111-5L NEW ●○	64255-111-7L NEW ●○
64255-112-3L NEW ●●	64255-112-5L NEW ●●	64255-112-7L NEW ●●
64255-113-3L NEW ●●	64255-113-5L NEW ●●	64255-113-7L NEW ●●
64255-114-3L NEW ●▥	64255-114-5L NEW ●▥	64255-114-7L NEW ●▥

PRICES

Canopy recessed
Florón empotrable

With frame
Con marco



64231



Trimless
Sin marco



64232



Compatible in these situations / *Compatibles en estas situaciones.*



Hook accessory for displaced light output.
Accesorio gancho para punto de luz desplazado.

Hook
Gancho



68602

***Track connector for suspension**
Conector carril para suspensión

Track
Carril



64231
64231

*Accessories compatible with all pendants with bulb and without turnbuckle.
Accesorios compatibles con todos los colgantes con bombilla y sin tensor/es

PRICES

Suspended 5 Mt. cable with plug (hook incl.)
Colgante con clavija 5 Mt. de cable (gancho incl.)

Conga



68604-54



68604-55



68604-56

Samba



68604-44



68604-45



68604-46

Kombo



68604-62
68604-63



68604-64
68604-65



68604-66
68604-67
68604-68

Mambo



68604-47



68604-48



68604-49

PRICES



Shoku 350 ceiling Ref. 64280
designed by Ernest Perera Studio

indoor interior

ceiling techo

Shoku by Ernest Perera Studio NEW









Shoku 350

64277	White/Blanco + White/Blanco
64278	White/Blanco + Black/Negro
64279	Black/Negro + Black/Negro
64280	Light Grey/Gris Claro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Diff Opal White PMMA/PMMA Blanco Opal
Light Source	SMD LED 24W 2700K
CRI	>90
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

TRIAC L DIM Driver







Shoku 600

64281	White/Blanco + White/Blanco
64282	Black/Negro + Black/Negro

Material	**Body** Aluminium/Aluminio
	Diff Opal White PMMA/PMMA Blanco Opal
Light Source	40W 2700K
CRI	>90
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

TRIAC L DIM Driver



PRICES



Shoku 350 ceiling Ref. 64278
designed by Ernest Perera Studio

Side by Àlex & Manel Lluscà







Side 200

62132	Matt White/Blanco Mate
62133	Matt White/Blanco Mate + Satin Nickel/Níquel Satinado
62134	Matt Black/Negro Mate + Satin Gold/Oro Satinado
62135	Matt Black/Negro Mate + Satin Copper/Cobre Satinado

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	1 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17443
Class	I
IP	20



Suspended
183











Side 390

62140	Matt White/Blanco Mate
62141	Matt White/Blanco Mate + Satin Nickel/Níquel Satinado
62142	Matt Black/Negro Mate + Satin Gold/Oro Satinado
62143	Matt Black/Negro Mate + Satin Copper/Cobre Satinado

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 15W 3000K 1200lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔











Side 450

62144	Matt White/Blanco Mate
62145	Matt White/Blanco Mate + Satin Nickel/Níquel Satinado
62146	Matt Black/Negro Mate + Satin Gold/Oro Satinado
62147	Matt Black/Negro Mate + Satin Copper/Cobre Satinado

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 17W 3000K 1600lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔



PRICES



Side 450 ceiling Ref. 62146
designed by Àlex & Manel Lluscà





Dolme by Xjer Studio

64096	Matt Black/Negro Mate
64097	Matt White/Blanco Mate

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 24W 3000K 1900lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

Driver ✔



Suspended
176







Tender

20094	Matt Black/Negro Mate + Oak/Roble
20095	Matt White/Blanco Mate + Oak/Roble

Material	**Body** Steel+Wood/Acero+Madera
	Diff Opal PC/PC Opal
Light Source	SMD LED 24W 3000K 1369lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔







Cocotte 430 by Jordi Llopis

64250	Shiny White/Blanco Brillo
64251	Shiny Black/Negro Brillo

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 30W 3000K 1300lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔







Cocotte 550 by Jordi Llopis

64182	Shiny White/Blanco Brillo
64183	Shiny Black/Negro Brillo

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 36W 3000K 1700lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔



Suspended
176



PRICES



Dolme ceiling Ref. 64097
designed by Xjer Studio





Link by Estudi Ribaudí

29877 Matt White/Blanco Mate
29878 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20




Spot
404


Track
436


Table&Floor
102

Wall
404







Orleans by Nahtrang

43529 Matt White/Blanco Mate
43531 Shiny Chrome/Cromo Brillo

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20









Orleans 2L by Nahtrang

43533 Matt Black/Negro Mate
43534 Shiny Chrome/Cromo Brillo

Material	**Body** Steel/Acero
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20




Spot
402


Track
436



PRICES



Orleans ceiling Ref. 43533
designed by Nahtrang





Tecto

63270 Matt White/Blanco Mate
63271 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	I
IP	20







Tecto 2L

63272 Matt White/Blanco Mate
63273 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	I
IP	20







Tecto AR111

63274 Matt White/Blanco Mate
63275 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 G53 AR111 max. 15W
Bulb incl.	No
Recom. Bulb	97411
Recom. Equip	98111020
Class	III
IP	20

180º







Tecto 2L AR111

63276 Matt White/Blanco Mate
63277 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	2 G53 AR111 max. 30W
Bulb incl.	No
Recom. Bulb	97411
Recom. Equip	98111020
Class	III
IP	20

180º



PRICES



Sven R

63268 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20





Sven SQ

63269 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20







Rel 100

64200 Matt White/Blanco Mate
64201 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 25W 2700K 2230lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	60°

Driver ✔







Rel 75

64198 Matt White/Blanco Mate
64199 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 15W 2700K 1340lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	60°

Driver ✔



PRICES





Haru

64206 Matt White/Blanco Mate
64207 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 3000K 350lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	120°

Driver ✔







Natsu

64204 Matt White/Blanco Mate
64205 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 30W 3000K 1500lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	120°

Driver ✔







Pote

63124 Matt White/Blanco Mate
63125 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Janet

65137 White/Blanco + Satin Gold/Oro Satinado

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	I
IP	20



PRICES









Stan

43746	Matt White/Blanco Mate
43747	Matt Black/Negro Mate
43758	Satin Gold/Oro Satinado

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	II
IP	20


Recessed
424


Spot
392

Suspended
208


Track
438


Wall
372



PRICES

*Accessories page 392/*Accesorios en página 392*





Seven 400

68323 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Diff White Textile/Textil Blanco
	Shade Textile/Textil
Light Source	SMD LED 20W 1313lm
Dimmable K	3000 - 4000 - 6000K
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

DIM DIM Driver





Seven 400

68298 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Diff White Textile/Textil Blanco
	Shade Textile/Textil
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Seven 500

68317 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Diff White Textile/Textil Blanco
	Shade Textile/Textil
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



Suspended
212



PRICES



Iris 225

63393 Satin Nickel/Níquel Satinado

Material	**Body** PS
	Diff Opal PC/PC Opal
Light Source	SMD LED 13W 3000K 1500lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔





Iris 295

63394 Satin Nickel/Níquel Satinado

Material	**Body** Aluminium/Aluminio
	Diff Opal PS/PS Opal
Light Source	SMD LED 20W 3000K 1600lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔





Iris 380

63395 Satin Nickel/Níquel Satinado

Material	**Body** Aluminium/Aluminio
	Diff Opal PS/PS Opal
Light Source	SMD LED 30W 3000K 2900lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔



PRICES



Bic

63408 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 60W 3000K 4000lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

TRIAC C DIM Driver



Mega

63410 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 52W 2700K 3600lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

TRIAC C DIM Driver







Ami

63397 Matt White/Blanco Mate

63398 Satin Nickel/Níquel Satinado

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 15W 2700K 1200lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

Driver





Foro

63404 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 24W 3000K 2000lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver



PRICES



Kao

63399 Shiny Chrome/Cromo Brillo

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 35W 3000K 2800lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔





Zon

63291 Matt White/Blanco Mate

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 18W 3000K 2000lm
CRI	85
Class	II
Voltage (V/Hz)	220V-240V/50Hz
IP	54

TRIAC C DIM Driver ✔







Logos 270

62965 Matt White/Blanco Mate

62980 Satin Nickel/Níquel Satinado

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	II
IP	44







Logos 350 2L

62966 Matt White/Blanco Mate

62981 Satin Nickel/Níquel Satinado

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	II
IP	44



PRICES





Vuk

64188 Matt White/Blanco Mate
64188N Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 40W 2700K 3000lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44

Driver ✔





Tola 270

62968 Matt White/Blanco Mate
62983 Satin Nickel/Níquel Satinado

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	II
IP	44





Tola 320

62969 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	II
IP	44





Brume by Àlex & Manel Lluscà

40077 Anthracite/Antracita

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 3W 2700K 200lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔



Suspended 202



Wall 382



PRICES



Brume ceiling Ref. 40077
designed by Àlex & Manel Lluscà



Tatawin wall lamp Ref. 20335-116
designed by Adolfo Abejón

indoor interior

Surface
Superficie

Luang by Faro Lab NEW







Luang

23004-57	Black/Negro + Beige
23004-58	Black/Negro + Camel

Material	**Body** Steel/Acero
	Shade Papyrus/Papiro
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	I
IP	20



PRICES



Confetti by Nutcreatives

NEW



Confetti 300 H70

62173-50 White & Black/Blanco y Negro
62173-52 Multicolored shavings/Virutas multicolor

Material	**Body** Aluminium/Aluminio
	Shade Recycled PET/PET Reciclado
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463E
Class	II
IP	20





Confetti 300 H140

62174-50 White & Black/Blanco y Negro
62174-52 Multicolored shavings/Virutas multicolor

Material	**Body** Aluminium/Aluminio
	Shade Recycled PET/PET Reciclado
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463E
Class	II
IP	20





Confetti 450 H70

62173-51 White & Black/Blanco y Negro

Material	**Body** Aluminium/Aluminio
	Shade Recycled PET/PET Reciclado
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464E
Class	II
IP	20





Confetti 450 H140

62174-51 White & Black/Blanco y Negro

Material	**Body** Aluminium/Aluminio
	Shade Recycled PET/PET Reciclado
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464E
Class	II
IP	20



PRICES



Inviting by Bohman And Folenius

reddot award 2019
winner

DESIGN AWARD 2019

GERMAN DESIGN AWARD SPECIAL 2019







Inviting

57318 NEW	Matt White/Blanco Mate
57319 NEW	Matt Black/Negro Mate
57320 NEW	Yellow/Amarillo

Material	**Body** Aluminium/Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	SMD LED 6W 410lm
Dimmable K	2700 - 4800K
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	1.9 MT

DIM DIM 180º 90º Driver









Inviting

57302	Yellow/Amarillo
57300	Matt White/Blanco Mate
57301	Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	SMD LED 6W 410lm
Dimmable K	2700 - 4800K
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cable	1.9 MT

DIM DIM 180º 90º Driver



PRICES



Academy by Nahtrang





Academy

28200 Shiny Chrome/Cromo Brillo

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 4W 3000K 350lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

DIM 350º Driver



PRICES

Desliz by Estudi Ribaudí





Desliz

28480	Satin Nickel/Níquel Satinado + White/Blanco
28481	Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
	Shade Textile/Textil
Light Source	SMD LED 11W 2700K 800lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

180º Driver ✔



PRICES

Venice by Adolfo Abejón NEW










Venice

64270	White/Blanco
64271	Black/Negro
64272	Pink/Rosa
64273	Black & White Gloss/Blanco y Negro Brillo
64274	Blue/Azul

Material	**Body** Aluminium/Aluminio
	Shade Ceramic/Cerámica
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20


Suspended 154


Table&Floor 86



PRICES



Venice wall lamp Ref. 64272
designed by Adolfo Abejón

Flash by Estudi Ribaudí





Flash

20204	Matt Black/Negro Mate
Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 10W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

350º 90º Driver



Suspended
150

PRICES



Maya by Faro Lab

NEW

reddot winner 2023













2 Installation Modes / 2 Modos de instalación



Maya

40102	Matt Black/Negro Mate + Shiny Black/Negro Brillo
40103	Matt White/Blanco Mate + Beige/Beige
40104	Matt Black/Negro Mate + Terracotta/Terracota

Material	**Body** Aluminium+Steel/Aluminio+Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 8W 2700K 580lm
CRI	>90
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cable	1.5 MT

DIM Driver



Tatawin by Adolfo Abejón

NEW









Tatawin

20335-116	Satin Black/Negro Satinado + Opal
20335-117	Satin Black/Negro Satinado + Shiny Black/Negro Brillo

Material	**Body** Aluminium/Aluminio
	Shade Glass/Cristal
Light Source	1 E27 G45 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	II
IP	20





Suspended 156



Table&Floor 84

PRICES

Costas by Àlex & Manel Lluscà

NEW



Costas 400 H70

62173-78 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Aluminium/Aluminio
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17071E
Class	II
IP	20





Costas 600 H70

62173-69 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Aluminium/Aluminio
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17071E
Class	II
IP	20





Costas 400 H140

62174-78 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Aluminium/Aluminio
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17072E
Class	II
IP	20





Costas 600 H140

62174-69 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Aluminium/Aluminio
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17072E
Class	II
IP	20



PRICES



May by Faro Lab












May

40095	White/Blanco
40096	Black/Negro
40097	Blue/Azul
40098	Coral
40099	Green/Verde

Material	**Body** Steel/Acero
	Diff Opal White Glass/Cristal Blanco Opal
Light Source	COB LED 4W 2700K 300lm
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔



PRICES



Moy by Nahtrang













Moy

40090		Satin Gold/Oro Satinado
40091		Shiny Chrome/Cromo Brillo
40092		Bronze/Bronce
40093		Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 4W 3000K 300lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔



PRICES

Joy by Nahtrang







Joy

64027	Matt Black/Negro Mate
64028	Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 3W 3000K 280lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver



PRICES

Levita by Nahtrang







Levita

29690	Shiny Gold/Oro Brillo
29695	Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 6W 2700K 570lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
	Driver ✔



Suspended 168



Table&Floor 96



PRICES

Magos by Faro Lab











Magos

20330	●	Black/Negro
20331	●	Maple/Arce
20332	●	Walnut/Nogal

Material	**Body** Aluminium+ABS/Aluminio+ABS
	Diff Opal PC/PC Opal
Light Source	SMD LED 14W 2700K 600lm
Bulb incl.	No
Reader	3W, 2700K, 160lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

DIM 360º 180º x2 Driver



PRICES

Whizz by Christoph F.W.

salone satellite 20years of new creativity





Whizz extensible

20167	Black/Negro + Satin Gold/Oro Satinado
20168	Satin Gold/Oro Satinado + Black/Negro

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17496
Class	II
IP	20
Cable	2 MT

180º







Whizz

20165-95	Black/Negro + Satin Gold/Oro Satinado
20165-96	Satin Gold/Oro Satinado + Black/Negro

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17496
Class	II
IP	20
Cable	3.4 MT



Floor
140



Suspended
170



PRICES



Whizz wall lamp Ref. 20165-95
designed by Cristoph F.W.

Slim by Àlex & Manel Lluscà





Slim

24502 Matt White/Blanco Mate

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 20W 3000K 1150lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

180º Driver ✔



PRICES

Han by Goulafiguera





Han

01001 Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 2700K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔



PRICES

Guest by Andreu Carulla





Guest

01045 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17429
Class	I
IP	20



Floor
142



PRICES

Pure by Nahtrang







Pure

24527	Matt White/Blanco Mate
24528	Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Transparent PMMA/PMMA Transparente
Light Source	SMD LED 6W 3000K 451lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

Driver ✔



PRICES

Guadalupe by Faro Lab





Guadalupe

20031-80	Black/Negro + Beige
20031-81	Black/Negro + Green/Verde

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20

360º



Table&Floor
94







Guadalupe reader

20032-80	Black/Negro + Beige
20032-81	Black/Negro + Green/Verde

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	1W, 3000K, 100lm
Driver incl.	Yes
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

360º x2 Driver ✔



PRICES



Guadalupe wall lamp Ref. 20031-80
designed by Faro Lab



Klee right

20065 Textured Grey/Gris Texturizado + Black/Negro

Material	**Body** Steel+Melamine/Acero+Melamina
	Diff Opal PMMA/PMMA Opal
Light Source	COB LED 10W 2700K 1021lm
Dimmable W	6w 690lm / 10w 1021lm
CRI	>=90
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	45°

DIM 350º 45º x2 Driver





Klee Left

20066 Textured Grey/Gris Texturizado + Black/Negro

Material	**Body** Steel+Melamine/Acero+Melamina
	Diff Opal PMMA/PMMA Opal
Light Source	COB LED 10W 2700K 1021lm
Dimmable W	6w 690lm / 10w 1021lm
CRI	>=90
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	45°

DIM 350º 45º x2 Driver



PRICES



Klee wall lamp Ref. 20065
designed by Isaac Piñeiro

Mood by Nahtrang



Mood SQ

20060 Oak/Roble + Black/Negro

Material	**Body** Steel+Wood/Acero+Madera
Light Source	SMD LED 2W 3000K 105lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Beam angle	45°

Driver





Mood RCT

20061 Oak/Roble + Black/Negro

Material	**Body** Steel+Wood/Acero+Madera
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 3000K 67lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver





Mood RCT reader

20062 Oak/Roble + Black/Negro

Material	**Body** Steel+Wood/Acero+Madera
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 3000K 67lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

x2 Driver



PRICES



Mood wall lamp Ref. 20061
designed by Nahtrang

Niko by Nahtrang


1W 80lm


4W 250lm


7W 500lm



Niko Glass right

01009A Matt White/Blanco Mate + Wood/Madera

Material	**Diff** Opal Glass/Cristal Opal

Niko PC right

01027A Matt White/Blanco Mate + Wood/Madera

Material	**Body** Aluminium+Wood/Aluminio+Madera
	Diff Opal PC/PC Opal
Light Source	SMD LED 7W 3000K 500lm
Dimmable W	1w 80lm / 4w 250lm / 7w 500lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

DIM Driver





Niko Glass left

01014A Matt White/Blanco Mate + Wood/Madera

Material	**Diff** Opal Glass/Cristal Opal

Niko PC left

01026A Matt White/Blanco Mate + Wood/Madera

Material	**Body** Aluminium+Wood/Aluminio+Madera
	Diff Opal PC/PC Opal
Light Source	SMD LED 7W 3000K 500lm
Dimmable W	1w 80lm / 4w 250lm / 7w 500lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

DIM Driver



Table
72

PRICES



Niko wall lamp Ref. 01009A
designed by Nahtrang

Stood by Lucid Product Design



Stood

29844 Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Shade Wood/Madera
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	II
IP	20

20º





Stood clip

29845 Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Shade Wood/Madera
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	II
IP	20
Cable	2.4 MT



Suspended 162



Table&Floor 100



PRICES



Stood wall lamp Ref. 29844
designed by Lucid Product Design

Loop by Estudi Ribaudí





Loop

29395	Matt Black/Negro Mate + Ash tree/Fresno
29565	Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Shade Wood/Madera
Light Source	SMD LED 6W 2700K 500lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

DIM 350º Driver







Loop Articulated

29396	Matt Black/Negro Mate + Ash tree/Fresno
29566	Matt Black/Negro Mate + Cherry/Cerezo

Material	**Body** Steel/Acero
	Shade Wood/Madera
Light Source	SMD LED 6W 2700K 500lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

DIM 150º 350º Driver




Suspended 164 **Table&Floor** 98



PRICES



Loop wall lamp Ref. 29395
designed by Estudi Ribaudí

Samba by Faro Lab



Samba

64306-35	White/Blanco + Beige
64306-36	White/Blanco + Yellow/Amarillo
64306-37	White/Blanco + Green/Verde
64307-35	Black/Negro + Beige
64307-36	Black/Negro + Yellow/Amarillo
64307-37	Black/Negro + Green/Verde

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Suspended 194



Table&Floor 112



Samba reader

64308-35	Matt White/Blanco Mate + Beige
64308-36	Matt White/Blanco Mate + Yellow/Amarillo
64308-37	Matt White/Blanco Mate + Green/Verde
64309-35	Matt Black/Negro Mate + Beige
64309-36	Matt Black/Negro Mate + Yellow/Amarillo
64309-37	Matt Black/Negro Mate + Green/Verde

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 280lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔



PRICES

Samba wall lamp Ref. 64306-35
designed by Faro Lab



*Structures and shades also sold separately 820-824 / *Estructuras y pantallas también se venden por separado* 820-824

Savoy by Isaac Piñeiro



Savoy

20300-92	Matt White/Blanco Mate + White/Blanco
20301-93	Matt Black/Negro Mate + Black/Negro
20301-94	Matt Black/Negro Mate + Green/Verde

Material	**Body** Steel/Acero
	Diff Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20





Suspended 196



Table&Floor 118



Savoy reader

20302-92	White/Blanco + White/Blanco
20303-93	Black/Negro + Black/Negro
20303-94	Black/Negro + Green/Verde

Material	**Body** Steel/Acero
	Diff Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 160lm
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔



PRICES

Savoy wall lamp Ref. 20301-94
designed by Isaac Piñeiro





*Structures and shades also sold separately 820-824 / *Estructuras y pantallas también se venden por separado* 820-824

Montreal by Nahtrang



Montreal

24030-01	Matt White/Blanco Mate + White/Blanco
24030-02	Matt White/Blanco Mate + Beige
24031-01	Shiny Chrome/Cromo Brillo + White/Blanco
24031-02	Shiny Chrome/Cromo Brillo + Beige
24031-03	Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20





Table&Floor
116



Montreal reader

24032-01	White/Blanco + White/Blanco
24032-02	White/Blanco + Beige
24033-01	Chrome/Cromo + White/Blanco
24033-02	Chrome/Cromo + Beige
24033-03	Chrome/Cromo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 2700K, 150lm
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔



PRICES

Montreal wall lamp Ref. 24032-01
designed by Nahtrang



*Structures and shades also sold separately 820-824 / *Estructuras y pantallas también se venden por separado* 820-824

Conga by Faro Lab



Conga

64306-01	White/Blanco + White/Blanco
64306-02	White/Blanco + Beige
64307-03	Black/Negro + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



Suspended 194



Table&Floor 115





Conga reader

64308-01	Matt White/Blanco Mate + White/Blanco
64308-02	Matt White/Blanco Mate + Beige
64309-03	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 280lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver



PRICES

Conga wall lamp Ref. 64309-03
designed by Faro Lab





*Structures and shades also sold separately 820-824 / *Estructuras y pantallas también se venden por separado* 820-824

Sumba by Faro Lab



Sumba

64307-71 Black/Negro + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	I
IP	20
	Driver ✗



Suspended
186



Table
76





Sumba reader

64309-71 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Reader	3W, 3000K, 280lm
Driver incl.	Yes
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
	Driver ✓



PRICES



Sumba wall lamp Ref. 64307-71
designed by Faro Lab

Mambo by Faro Lab



Mambo

64307-47 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



Suspended 221



Table&Floor 110





Mambo reader

64309-47 Matt Black/Negro Mate + Rattan/Ratán

Material	**Body** Steel/Acero
	Shade Rattan/Ratán
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 280lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔



PRICES

*Structures and shades also sold separately 820-824 / *Estructuras y pantallas también se venden por separado* 820-824



Mambo wall lamp Ref. 64309-47
designed by Faro Lab

Artis by Àlex & Manel Lluscà



Artis

68490-01	Old Bronze/Bronce Envejecido + White/Blanco
68490-02	Old Bronze/Bronce Envejecido + Beige
68490-03	Old Bronze/Bronce Envejecido + Black/Negro
68491-01	Shiny Chrome/Cromo Brillo + White/Blanco
68491-02	Shiny Chrome/Cromo Brillo + Beige
68491-03	Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Artis reader

68492-01	Old Bronze/Bronce Envejecido + White/Blanco
68492-02	Old Bronze/Bronce Envejecido + Beige
68492-03	Old Bronze/Bronce Envejecido + Black/Negro
68493-01	Shiny Chrome/Cromo Brillo + White/Blanco
68493-02	Shiny Chrome/Cromo Brillo + Beige
68493-03	Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	1W, 3000K, 140lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔





Artis articulated

68494-01	Bronze/Bronce + White/Blanco
68494-02	Bronze/Bronce + Beige
68494-03	Bronze/Bronce + Black/Negro
68495-01	Shiny Chrome/Cromo Brillo + White/Blanco
68495-02	Shiny Chrome/Cromo Brillo + Beige
68495-03	Shiny Chrome/Cromo Brillo

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



Table&Floor
122



PRICES

Artis wall lamp Ref. 68493-01
designed by Àlex & Manel Lluscà








*Structures and shades also sold separately 820-824 / *Estructuras y pantallas también se venden por separado* 820-824

Eterna by Lucid Product Design



Eterna

24005-10	Shiny Chrome/Cromo Brillo + White/Blanco
24005-11	Shiny Chrome/Cromo Brillo + Beige
24005-12	Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20





Eterna reader

24006-10	Chrome/Cromo + White/Blanco
24006-11	Chrome/Cromo + Beige
24006-12	Chrome/Cromo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	1W, 2700K, 90lm
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
	Driver ✔





Eterna reader

24007-10	Chrome/Cromo + White/Blanco
24007-11	Chrome/Cromo + Beige
24007-12	Chrome/Cromo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	1W, 2700K, 90lm
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
	Driver ✔



Table
74



PRICES

Eterna wall lamp Ref. 24007-10
designed by Lucid Product Design





*Structures and shades also sold separately 820-824 / *Estructuras y pantallas también se venden por separado* 820-824

Rem by Àlex & Manel Lluscà



Rem

29680-19	Matt Nickel/Níquel Mate + White/Blanco
29680-20	Matt Nickel/Níquel Mate + Beige
29680-21	Matt Nickel/Níquel Mate + Black/Negro
29681-19	Old Gold/Oro Viejo + White/Blanco
29681-20	Old Gold/Oro Viejo + Beige
29681-21	Old Gold/Oro Viejo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



Table&Floor
120





Rem reader

29682-19	Matt Nickel/Níquel Mate + White/Blanco
29682-20	Matt Nickel/Níquel Mate + Beige
29682-21	Matt Nickel/Níquel Mate + Black/Negro
29683-19	Old Gold/Oro Viejo + White/Blanco
29683-20	Old Gold/Oro Viejo + Beige
29683-21	Old Gold/Oro Viejo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	4W, 3000K, 120lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔



PRICES

Rem wall lamp Ref. 29683-20
designed by Àlex & Manel Lluscà



*Structures and shades also sold separately 820-824 / *Estructuras y pantallas también se venden por separado* 820-824



Frame

20170-01	Matt Nickel/Níquel Mate + White/Blanco
20170-02	Matt Nickel/Níquel Mate + Beige
20170-03	Matt Nickel/Níquel Mate + Black/Negro
20171-01	Old Gold/Oro Viejo + White/Blanco
20171-02	Old Gold/Oro Viejo + Beige
20171-03	Old Gold/Oro Viejo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Frame reader

20172-01	Matt Nickel/Níquel Mate + White/Blanco
20172-02	Matt Nickel/Níquel Mate + Beige
20172-03	Matt Nickel/Níquel Mate + Black/Negro
20173-01	Old Gold/Oro Viejo + White/Blanco
20173-02	Old Gold/Oro Viejo + Beige
20173-03	Old Gold/Oro Viejo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 100lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver



PRICES

Frame wall lamp Ref. 20170-03
designed by Nahtrang








*Structures and shades also sold separately 820-824 / *Estructuras y pantallas también se venden por separado* 820-824

Lupe by Jordi Busquets



Lupe

20031-88 Black/Negro + Beige

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20

360º



Table&Floor
128







Lupe reader

20032-88 Black/Negro + Beige

29996 Shiny Chrome/Cromo Brillo + White/Blanco

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	1W, 3000K, 100lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

360º Driver



PRICES



Lupe wall lamp Ref. 29996
designed by Jordi Busquets

Ron by Pepe Llaudet









Ron

64400-10	Dark Grey/Gris Oscuro + White/Blanco
64400-11	Dark Grey/Gris Oscuro + Beige
64400-12	Dark Grey/Gris Oscuro + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20

160º



PRICES

Blome by Estudi Ribaudí







Blome

62099	Matt White/Blanco Mate
62100	Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
	Shade Textilene
Light Source	SMD LED 3W 3000K 150lm
CRI	>90
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver



PRICES





Fold

64302 Matt White/Blanco Mate + White/Blanco
64303 Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20







Fold reader

64304 Matt White/Blanco Mate + White/Blanco
64305 Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 200lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver



PRICES



Fold wall lamp Ref. 64303
designed by Nutcreatives

Hotel by Àlex & Manel Lluscà





Hotel

29940	Shiny Chrome/Cromo Brillo + White/Blanco
29945	Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



Suspended 198 **Table&Floor** 134







Hotel reader

29941	Shiny Chrome/Cromo Brillo + White/Blanco
29946	Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	1W, 3500K, 80lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver



PRICES



Hotel wall lamp Ref. 29940
designed by Àlex & Manel Lluscà

Room by Àlex & Manel Lluscà





Room

29974	Satin Nickel/Níquel Satinado + White/Blanco
29975	Satin Nickel/Níquel Satinado + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Room reader

29976	Satin Nickel/Níquel Satinado + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 160lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔



PRICES



Room wall lamp Ref. 29976
designed by Àlex & Manel Lluscà

Volta by Estudi Ribaudí



Volta

20021 Satin Nickel/Níquel Satinado + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20







Volta reader

20023 Satin Nickel/Níquel Satinado + White/Blanco

20024 Satin Nickel/Níquel Satinado + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 200lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver



Table&Floor
136



PRICES



Volta wall lamp Ref. 20021
designed by Estudi Ribaudí





Vesper

29980	Matt White/Blanco Mate + Beige
29981	Brown/Marrón + Beige

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E14 max. 8W
Bulb incl.	No
Recom. Bulb	17461
Class	I
IP	20

Suspended 196



Table&Floor 124







Vesper reader

29982	Matt White/Blanco Mate + Beige
29983	Brown/Marrón + Beige

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E14 max. 8W
Bulb incl.	No
Recom. Bulb	17461
Reader	1W, 3000K, 120lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver



PRICES



Vesper wall lamp Ref. 29982
designed by Nahtrang





Berni

29326	Matt White/Blanco Mate + White/Blanco
29328	Satin Nickel/Níquel Satinado + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



Table&Floor
132









Berni reader

29329	Matt White/Blanco Mate + White/Blanco
29330	Matt Black/Negro Mate + Black/Negro
29331	Satin Nickel/Níquel Satinado + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 200lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔



PRICES



Berni wall lamp Ref. 29330
designed by Nahtrang
Project by Elena Castells Poch

Sweet by Estudi Ribaudí







Sweet

29936	Satin Nickel/Níquel Satinado + White/Blanco
29952	Matt White/Blanco Mate + White/Blanco
29953	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Diff White Textile/Textil Blanco
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



Table&Floor
145









Sweet reader

29935	Satin Nickel/Níquel Satinado + White/Blanco
29950	Matt White/Blanco Mate + White/Blanco
29951	Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel/Acero
	Diff White Textile/Textil Blanco
	Shade Textile/Textil
Light Source	1 E27 max. 2W
Bulb incl.	No
Recom. Bulb	17463
Reader	4W, 3000K, 120lm
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔



PRICES





Sweet wall lamp Ref. 29951
designed by Estudi Ribaudí

Handy by Jordi Blasi



Handy

28413 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Handy right

28414 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 40lm
Driver incl.	Yes
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver





Handy Left

28415 Matt White/Blanco Mate + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 40lm
Driver incl.	Yes
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver



PRICES



Handy wall lamp Ref. 28414
designed by Jordi Blasi





Sahara

62705 Shiny Chrome/Cromo Brillo + Beige
62706 Shiny Chrome/Cromo Brillo + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Saba

68544 Satin Nickel/Níquel Satinado + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Roda

62988 Satin Nickel/Níquel Satinado + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



PRICES



Sahara wall lamp Ref. 62705



Hanna

64301 Satin Nickel/Níquel Satinado + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Hanna reader

64300 Satin Nickel/Níquel Satinado + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 250lm
Driver incl.	Yes
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔





Essential

29341 Satin Nickel/Níquel Satinado + White/Blanco

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 2700K, 200lm
Driver incl.	Yes
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔



PRICES





Moma

68504 Shiny Chrome/Cromo Brillo + White/Blanco
68505 Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



Table&Floor
144







Moma reader

68506 Shiny Chrome/Cromo Brillo + White/Blanco
68507 Shiny Chrome/Cromo Brillo + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	1W, 6000K, 80lm
Driver incl.	Yes
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔







Tira

64322 Matt White/Blanco Mate + White/Blanco
64323 Matt Black/Negro Mate + Black/Negro

Material	**Body** Steel+Aluminium+Silicone/Acero+Aluminio+Silicona
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 280lm
Driver incl.	Yes
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

x2 Driver ✔



PRICES

Duas by Faro Lab









Duas

68467	Matt White/Blanco Mate + Shiny White/Blanco Brillo
68468	Matt Black/Negro Mate + Shiny Black/Negro Brillo

Material	**Body** Steel/Acero
Light Source	COB LED 3W 2700K 240 lm
CRI	>=80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Beam angle	45°

350º 90º Driver ✔



PRICES



Duas wall lamp Ref. 68467
designed by Faro Lab

Aurea by Estudi Ribaudí





Aurea

62115 Matt White/Blanco Mate

Material	**Body** Steel/Acero
	Diff Opal PC/PC Opal
Light Source	SMD LED 8W 2700K 300lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

350º 90º Driver



PRICES

Le Petit by Àlex & Manel Lluscà











Le Petit

62161	Matt White/Blanco Mate
62162	Matt Black/Negro Mate
62163	Satin Gold/Oro Satinado
62164	Bronze/Bronce

Material	**Body** Steel/Acero
Light Source	SMD LED 4W 3000K 130lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

60º 45º Driver ✔



PRICES











Boc

62707	Matt White/Blanco Mate
62708	Matt Black/Negro Mate
62709	Satin Nickel/Níquel Satinado
62710	Shiny Chrome/Cromo Brillo
62711	Bronze/Bronce

Material	**Body** Steel/Acero
Light Source	HIGH POWER LED 3W 3000K 130lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

350º 90º Driver ✔



NEW









Rob

68497	Bronze/Bronce
68499	Satin Nickel/Níquel Satinado
68508 NEW	White/Blanco
68509 NEW	Black/Negro

Material	**Body** Steel+Aluminium/Acero+Aluminio
Light Source	HIGH POWER LED 3W 3000K 160lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔







Rob Shade

68496	Bronze/Bronce + Opal
68498	Satin Nickel/Níquel Satinado + Opal

Material	**Body** Steel+Aluminium/Acero+Aluminio
	Shade PMMA
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Reader	3W, 3000K, 160lm
Driver incl.	Yes
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

350º 90º x2 Driver ✔



PRICES



Flin

64318 Matt White/Blanco Mate
64319 Matt Black/Negro Mate

Material	**Body** Steel+Aluminium+Silicone/Acero+Aluminio+Silicona
Light Source	HIGH POWER LED 3W 3000K 280lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°

350º 90º Driver









Loke

40994 Shiny Chrome/Cromo Brillo
41019 Matt White/Blanco Mate
41020 Matt Black/Negro Mate

Material	**Body** Aluminium+Steel/Aluminio+Acero
Light Source	HIGH POWER LED 3W 3000K 150lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°

350º 90º Driver





Loke recessed

40996 Shiny Chrome/Cromo Brillo

Material	**Body** Aluminium+Steel/Aluminio+Acero
Light Source	HIGH POWER LED 3W 3000K 150lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°
Cut out	ø60

350º 90º Driver



PRICES





Pepper

64168 Beige
64169 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	II
IP	20
Cable	1.7 MT

360º 180º







Lena clip

52059 Matt White/Blanco Mate
52061 Matt Black/Negro Mate

Material	**Body** PC+Aluminium+Silicone/PC+Aluminio+Silicona
Light Source	SMD LED 3W 4000K 300lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°
Cable	1.8 MT

360º 360º Driver





Juliet

41025N Shiny Chrome/Cromo Brillo

Material	**Body** Aluminium+Steel/Aluminio+Acero
Light Source	SMD LED 3W 3000K 150lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°

Driver



PRICES

Studio by Nahtrang









Studio

51133	●	Matt Black/Negro Mate
51134	◪	Shiny Chrome/Cromo Brillo
51135	○	Shiny White/Blanco Brillo

Material	**Body** Aluminium+ABS/Aluminio+ABS
Light Source	1 E14 max. 8W
Bulb incl.	No
Recom. Bulb	17461
Class	II
IP	20
Cable	1.6 MT



Accessories/Accesorios



Wall accessory/*Accesorio aplique*

51129 ● Black/Negro



PRICES







Bel

41028	Shiny Chrome/Cromo Brillo
41029	Matt White/Blanco Mate
41030	Matt Black/Negro Mate

Material	**Body** Aluminium+Steel/Aluminio+Acero
Light Source	HIGH POWER LED 3W 3000K 150lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°

Driver





Boken

41031	Matt White/Blanco Mate
41032	Matt Black/Negro Mate

Material	**Body** Aluminium+Steel+Silicone/Aluminio+Acero+Silicona
Light Source	HIGH POWER LED 3W 3000K 150lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°

Driver





Leser

41026	Matt Nickel/Níquel Mate + Matt Black/Negro Mate

Material	**Body** Aluminium+Steel+Silicone/Aluminio+Acero+Silicona
Light Source	COB LED 5W 3000K 300lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	36°

Driver



PRICES



Sami

41023 Matt White/Blanco Mate

Material	**Body** Aluminium+Steel+Silicone/Aluminio+Acero+Silicona
Light Source	HIGH POWER LED 3W 2700K 120lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°

Driver





Kale

62703 Matt Black/Negro Mate

Material	**Body** Aluminium+Steel+Silicone/Aluminio+Acero+Silicona
Light Source	HIGH POWER LED 3W 3000K 180lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Beam angle	45°

Driver





Lead

62704 Old Gold/Oro Viejo + Brown/Marrón

Material	**Body** Aluminium+Leather/Aluminio+Piel
Light Source	COB LED 3W 3000K 180lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Beam angle	45°

Driver



PRICES

Press by Jordi Blasi











Press

62350	Shiny White/Blanco Brillo + Matt Black/Negro Mate
62351	Matt Black/Negro Mate + Shiny Black/Negro Brillo
62352	Shiny Red/Rojo Brillo + Matt Black/Negro Mate
62353	Shiny Yellow/Amarillo Brillo + Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	SMD LED 3W 3000K 180lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

350º 90º Driver



PRICES

Pixie by Nahtrang







Pixie

24015	Matt White/Blanco Mate
24016	Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	HIGH POWER LED 2W 2700K 90lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	45°

Driver



PRICES

Suau by Nahtrang











Suau recessed

62111	Bronze/Bronce
62114	Satin Gold/Oro Satinado
62126	Satin Nickel/Níquel Satinado
62128	Matt Black/Negro Mate
62129	Matt White/Blanco Mate

Material	**Body** Steel/Acero
Light Source	HIGH POWER LED 3W 3000K 140lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°
Cut out	80x155x43

350º 90º Driver ✔







Suau USB

62116	Matt Black/Negro Mate
62117	Matt White/Blanco Mate

Material	**Body** Aluminium+Steel/Aluminio+Acero
Light Source	HIGH POWER LED 3W 3000K 140lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°

350º 90º Driver ✔











Suau

62104	Bronze/Bronce
62118	Matt Black/Negro Mate
62120	Matt White/Blanco Mate
62121	Grey/Gris

Material	**Body** Steel/Acero
Light Source	HIGH POWER LED 3W 3000K 140lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°

350º 90º Driver ✔



PRICES



Suau wall lamp/recessed Ref. 62111
designed by Nahtrang





Suau tray left

62124 Matt White/Blanco Mate
62125 Grey/Gris

Material	**Body** Aluminium+Steel/Aluminio+Acero
Light Source	HIGH POWER LED 3W 3000K 140lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°

350º 90º Driver







Suau tray right

62122 Matt White/Blanco Mate
62123 Grey/Gris

Material	**Body** Aluminium+Steel/Aluminio+Acero
Light Source	HIGH POWER LED 3W 3000K 140lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	30°

350º 90º Driver



PRICES



Suau wall lamp Ref. 62125
designed by Nahtrang

Tila by Estudi Ribaudí









2 Installation Modes / 2 Modos de instalación



Tila

62360		Ivory White/Blanco Marfil
62361		Black/Negro

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 G45 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	II
IP	20





PRICES

Nit by Goulafiguera











Nit Left

01003	Matt White/Blanco Mate
01004	Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.7 MT





Nit right

01005	Matt White/Blanco Mate
01006	Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20
Cable	1.7 MT





PRICES

Noon by Alegre Design





Noon

62355 Matt White/Blanco Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	I
IP	20





PRICES

Smile by Jordi Busquets







Smile

62130	Matt White/Blanco Mate
62131	Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20



PRICES



Well

64030 Matt White/Blanco Mate

Material	**Body** Aluminium+PP/Aluminio+PP
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 7W 2700K 340lm
CRI	>=90
Class	I
Voltage (V/Hz)	100V-240V/50Hz
IP	20

Driver







Corb

40135 Matt White/Blanco Mate

40136 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	I
IP	20



PRICES



Corb wall lamp Ref. 40135



Eres

64026 Matt White/Blanco Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Ovo 190 by Estudi Ribaudí

62105 Matt White/Blanco Mate

Material	**Body** Steel/Acero
Light Source	1 R7S 78mm max. 8W
Bulb incl.	No
Recom. Bulb	17499
Class	I
IP	20
	20º





Ovo 240 by Estudi Ribaudí

62108 Matt White/Blanco Mate

Material	**Body** Steel/Acero
Light Source	1 R7S 118mm max. 15W
Bulb incl.	No
Recom. Bulb	17497
Class	I
IP	20
	20º



PRICES



Eres wall lamp Ref. 64026

Thanks to Salto Proyectos de Arquitectura Photo by Architectural Matter

NEW





Otton RCT vertical

66400-97 Matt White/Blanco Mate + Linen/Lino

Material	**Shade** Linen/Lino

66400-98 Matt White/Blanco Mate + Jute/Yute

Material	**Shade** Jute/Yute
	Body Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



NEW





Otton R vertical

66400-101 Matt White/Blanco Mate + Linen/Lino

Material	**Shade** Linen/Lino

66400-102 Matt White/Blanco Mate + Jute/Yute

Material	**Shade** Jute/Yute
	Body Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



NEW





Otton SQ 200

66400-105 Matt White/Blanco Mate + Linen/Lino

Material	**Shade** Linen/Lino

66400-106 Matt White/Blanco Mate + Jute/Yute

Material	**Shade** Jute/Yute
	Body Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



PRICES



Otton wall lamp Ref. 66401-99

NEW





Otton RCT vertical 2L

66401-99 Matt White/Blanco Mate + Linen/Lino

Material	**Shade** Linen/Lino

66401-100 Matt White/Blanco Mate + Jute/Yute

Material	**Shade** Jute/Yute
	Body Steel/Acero
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



NEW





Otton R vertical 2L

66401-103 Matt White/Blanco Mate + Linen/Lino

Material	**Shade** Linen/Lino

66401-104 Matt White/Blanco Mate + Jute/Yute

Material	**Shade** Jute/Yute
	Body Steel/Acero
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



NEW





Otton RCT Horizontal 2L

66401-107 Matt White/Blanco Mate + Linen/Lino

Material	**Shade** Linen/Lino

66401-108 Matt White/Blanco Mate + Jute/Yute

Material	**Shade** Jute/Yute
	Body Steel/Acero
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



NEW





Otton R Horizontal 2L

66401-109 Matt White/Blanco Mate + Linen/Lino

Material	**Shade** Linen/Lino

66401-110 Matt White/Blanco Mate + Jute/Yute

Material	**Shade** Jute/Yute
	Body Steel/Acero
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



PRICES



Otton wall lamp Ref. 66401-108





Cotton RCT vertical 2L

66405 Matt White/Blanco Mate + Beige
66406 Matt White/Blanco Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Cotton R vertical

66407 Matt White/Blanco Mate + Beige
66408 Matt White/Blanco Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20







Cotton R vertical 2L

66409 Matt White/Blanco Mate + Beige
66410 Matt White/Blanco Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



PRICES



Cotton wall lamp Ref. 66405





Cotton RCT vertical

66403	Matt White/Blanco Mate + Beige
66404	Matt White/Blanco Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Cotton SQ 200

66411	Matt White/Blanco Mate + Beige
66412	Matt White/Blanco Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20







Cotton RCT Horizontal 2L

66413	Matt White/Blanco Mate + Beige
66414	Matt White/Blanco Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Cotton R Horizontal 2L

66415	Matt White/Blanco Mate + Beige
66416	Matt White/Blanco Mate + Black/Negro

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



PRICES



Cotton wall lamp Ref. 66403

Ten by Faro Lab









Ten 140

62170	Matt White/Blanco Mate
62171	Matt Black/Negro Mate
62172	Old Gold/Oro Viejo

Material	**Body** Aluminium/Aluminio
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20



PRICES


Thanks to LoCa Studio Photo by Pol Viladoms





Ten 70

62150		Matt White/Blanco Mate
62151		Matt Black/Negro Mate
62152		Old Gold/Oro Viejo
62153		Satin Gold/Oro Satinado
62154		Shiny Copper/Cobre Brillo
62155		Satin Nickel/Níquel Satinado

Material	**Body** Aluminium/Aluminio
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20


Table
71

PRICES





Homs

63167 Matt White/Blanco Mate

Material	**Body** Steel/Acero
Light Source	1 R7S 78mm max. 8W
Bulb incl.	No
Recom. Bulb	17499
Class	I
IP	20

20º







Kera

62300 Shiny White/Blanco Brillo

62301 Shiny Black/Negro Brillo

Material	**Body** Ceramic/Cerámica
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20







Sera

62302 Shiny White/Blanco Brillo

62303 Shiny Black/Negro Brillo

Material	**Body** Ceramic/Cerámica
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17464
Class	II
IP	20



PRICES



Loa

62809 Matt Black/Negro Mate + Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Shade Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Hudson

62810 Shiny Black/Negro Brillo

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Marina

60005 Matt Black/Negro Mate

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17428
Class	II
IP	20





Suspended
205



PRICES



Celia

40070 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E14 max. 8W
Bulb incl.	No
Recom. Bulb	17461
Class	II
IP	20
Cable	1.8 MT





Marlin

65133 Matt Black/Negro Mate + Old Gold/Oro Viejo

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17429
Class	I
IP	20



Suspended
205



PRICES



Celia wall lamp Ref. 40070



Ras

62807 Shiny Black/Negro Brillo

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20
Cable	2 MT

200º 90º







Snap

57402 BLANCO CREMA

57403 Dark Grey/Gris Oscuro

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20

350º 50º



Table
80





List

60000 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	20

350º 90º



PRICES





Linda by Estudi Ribaudí

29306 Matt White/Blanco Mate + Beige
29310 Matt Black/Negro Mate + Beige

Material	**Body** Steel/Acero
	Shade Textile/Textil
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20




Suspended 198


Table&Floor 126





Retro

20045 Matt Copper/Cobre Mate + Matt Black/Negro Mate
20049 Matt Black/Negro Mate + Shiny Chrome/Cromo Brillo

Material	**Body** Steel/Acero
Light Source	1 E14 max. 8W
Bulb incl.	No
Recom. Bulb	17461
Class	I
IP	20




Suspended 166



PRICES

Tou by Faro Lab







Tou 350

01205	Bordeaux/Burdeos
01207	Grey/Gris

Material	**Body** Aluminium+Foam/Aluminio+Espuma
	Diff Opal PMMA/PMMA Opal
	Shade Textile/Textil
Light Source	SMD LED 7W 2700K 450lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔







Tou 450

01206	Bordeaux/Burdeos
01208	Grey/Gris

Material	**Body** Aluminium+Foam/Aluminio+Espuma
	Diff Opal PMMA/PMMA Opal
	Shade Textile/Textil
Light Source	SMD LED 10W 2700K 750lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔



PRICES







Board 350

01040 ● Blackboard/Pizarra

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 7W 2700K 450lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔





Board 450

01041 ● Blackboard/Pizarra

Material	**Body** Steel/Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 10W 2700K 750lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

Driver ✔



PRICES





Lise

29888 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
Light Source	COB LED 2W 2700K 740lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Beam angle	80°

Driver









Stan

43748 Matt White/Blanco Mate
43749 Matt Black/Negro Mate
43759 Satin Gold/Oro Satinado

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20


Ceiling 235


Recessed 424


Spot 392

Suspended 208


Track 438









Stan 2L

43750 Matt White/Blanco Mate
43751 Matt Black/Negro Mate
43760 Satin Gold/Oro Satinado

Material	**Body** Aluminium/Aluminio
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20



PRICES



Stan wall lamp Ref. 43760





Nash 210

62819 Matt White/Blanco Mate
62821 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 8W 3000K 450lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

Driver ✔







Nash 370

62820 Matt White/Blanco Mate
62822 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 16W 3000K 990lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

Driver ✔





Oslo

63284 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	1 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17466
Class	I
IP	20





Olaf

63278 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
	Diff Opal PC/PC Opal
Light Source	2 E14 max. 8W
Bulb incl.	No
Recom. Bulb	17461
Class	I
IP	20



PRICES



Nash wall lamp Ref. 62820



Cheras 2

63173 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	1 R7S 78mm max. 8W
Bulb incl.	No
Recom. Bulb	17499
Class	I
IP	20





Cheras 3

63174 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	1 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17466
Class	I
IP	20





Cheras 4

63175 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	1 R7S 78mm max. 8W
Bulb incl.	No
Recom. Bulb	17499
Class	I
IP	20



PRICES



Eaco 1

63176 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	1 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17466
Class	I
IP	20





Eaco 2

63177 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	2 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17466
Class	I
IP	20





Eaco 3

63178 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	1 R7S 78mm max. 8W
Bulb incl.	No
Recom. Bulb	17499
Class	I
IP	20



PRICES



Snow

63285 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	1 E14 max. 8W
Bulb incl.	No
Recom. Bulb	17461
Class	I
IP	20





Elsa

63279 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
	Diff Opal PC/PC Opal
Light Source	SMD LED 8W 3000K 300lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
	Driver ✔





Cove

63480 White/Blanco

Material	**Body** Plaster/Yeso
Light Source	SMD LED 4W 3000K 270lm
CRI	>80
Class	I
Voltage (V/Hz)	230V/50-60Hz
IP	20
	Driver ✔



PRICES



Tera

63184 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	SMD LED 6W 2700K 530lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

Driver ✔





Luna

63225 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 5W 2700K 300lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

Driver ✔







Kamen

63311 Beige
63312 Grey/Gris

Material	**Body** Concrete/Cemento
Light Source	1 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17466
Class	I
IP	20



PRICES





Magritte 300

61080	Satin Nickel/Níquel Satinado
61083	Old Gold/Oro Viejo
61086	Matt Black/Negro Mate



Material	**Body** Aluminium+Steel/Aluminio+Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 3000K 380lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
	90º Driver ✔







Magritte 450

61081	Satin Nickel/Níquel Satinado
61084	Old Gold/Oro Viejo
61087	Matt Black/Negro Mate



Material	**Body** Aluminium+Steel/Aluminio+Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 8W 3000K 500lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
	90º Driver ✔







Magritte 600

61082	Satin Nickel/Níquel Satinado
61085	Old Gold/Oro Viejo
61088	Matt Black/Negro Mate



Material	**Body** Aluminium+Steel/Aluminio+Acero
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 12W 3000K 750lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
	90º Driver ✔



PRICES



Liria

63156 Satin Nickel/Níquel Satinado

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Diula 2L

62986 Satin Nickel/Níquel Satinado

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20





Diula

62987 Satin Nickel/Níquel Satinado + White/Blanco

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	20



PRICES









Perla by Àlex & Manel Lluscà

40085	Old Gold/Oro Viejo
40086	Shiny Chrome/Cromo Brillo
40087	Bronze/Bronce
40088	Black/Negro

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	1 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17443
Class	II
IP	44





Bianca by Àlex & Manel Lluscà

63510	Shiny Chrome/Cromo Brillo

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17443
Class	II
IP	44





Brume by Àlex & Manel Lluscà

40076	Anthracite/Antracita

Material	**Body** Steel/Acero
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 3W 2700K 200lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔



Ceiling
240



Suspended
202



PRICES



Perla wall lamp Ref. 40086
designed by Àlex & Manel Lluscà

NEW







Gala

63504	Shiny Chrome/Cromo Brillo
63505	Satin Gold/Oro Satinado
63506 NEW	Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17495
Class	II
IP	44





Lago

63503	Shiny Chrome/Cromo Brillo

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 G9 max. 6W
Bulb incl.	No
Recom. Bulb	17495
Class	II
IP	44





Edge 900

63502	Shiny Chrome/Cromo Brillo

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 18W 4000K 1300lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔



PRICES



Gala wall lamp Ref. 63506





Volga 310

63507 Shiny Chrome/Cromo Brillo
63512 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 5W 3000K 350lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔







Volga 600

63508 Shiny Chrome/Cromo Brillo
63513 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 12W 3000K 850lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔







Volga 900

63509 Shiny Chrome/Cromo Brillo
63514 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 18W 3000K 1300lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔



PRICES



Volga wall lamp Ref. 63512





Danubio 285

63600 Shiny Chrome/Cromo Brillo
63603 Bronze/Bronce

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 9W 2700K 600lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔







Danubio 395

63601 Shiny Chrome/Cromo Brillo
63604 Bronze/Bronce

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 12W 2700K 800lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔







Danubio 575

63602 Shiny Chrome/Cromo Brillo
63605 Bronze/Bronce

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 18W 2700K 1080lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔



PRICES





Nilo 600

63316 Matt Black/Negro Mate
63318 Shiny Chrome/Cromo Brillo

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 12W 3000K 950lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔







Nilo 900

63317 Matt Black/Negro Mate
63319 Shiny Chrome/Cromo Brillo

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 18W 3000K 1400lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔



PRICES



Stan spotlight Ref. 43762

indoor interior

Spotlights Focos





Stan LED

43726 Matt White/Blanco Mate + Matt Black/Negro Mate
43727 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	COB LED 12W 2700K 1200lm
CRI	>90
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

350º 90º Driver









Stan

43722 Matt White/Blanco Mate + Matt Black/Negro Mate
43723 Matt Black/Negro Mate + Matt Black/Negro Mate
43762 Satin Gold/Oro Satinado

Material	**Body** Aluminium+ABS/Aluminio+ABS
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º




Ceiling 235


Recessed 424

Suspended 208


Track 438


Wall 372

Accessories/Accesorios



Ring/Anillo

43728 Matt White/Blanco Mate
43729 Matt Gold/Oro Mate

Material **Body** ABS



Honey comb/Panel de abeja

43730

Material **Body** Aluminium/Aluminio

Linear spread lens/Lente difusor eliptica

43732

Material **Body** Glass/Cristal



Spread lens/Lente difusor

43731

Material **Body** Glass/Cristal

PRICES



Stan spotlight Ref. 43727





Stan

43740 Matt White/Blanco Mate
43741 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20









Stan 2L

43742 Matt White/Blanco Mate
43743 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20









Stan 3L

43744 Matt White/Blanco Mate
43745 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	3 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20





PRICES



Stan spotlight 2L Ref. 43743

Lao by Nahtrang





Lao

29039 Matt Black/Negro Mate + Shiny Black/Negro Brillo
29040 Matt White/Blanco Mate + Shiny White/Blanco Brillo

Material	**Body** Aluminium+ABS/Aluminio+ABS
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 4W 3000K 400lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

350º 90º Driver



Table&Floor
104





Lao 2L

29042 Matt White/Blanco Mate + Shiny White/Blanco Brillo

Material	**Body** Aluminium+ABS/Aluminio+ABS
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 9W 3000K 400lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

350º 90º Driver







Lao 3L

29043 Matt Black/Negro Mate + Shiny Black/Negro Brillo
29044 Matt White/Blanco Mate + Shiny White/Blanco Brillo

Material	**Body** Aluminium+ABS/Aluminio+ABS
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 13W 3000K 400lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20

350º 90º Driver



PRICES



Lao spotlight 3L Ref. 29043
designed by Nahtrang

Coco by Faro Lab









Coco

40660	Matt White/Blanco Mate
40661	Matt Black/Negro Mate
40662	Matt Black/Negro Mate + Green/Verde
40663	Matt Black/Negro Mate + Terracotta/Terracota

Material	**Body** ABS+Steel/ABS+Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º 45º







Coco 2L

40664	Matt White/Blanco Mate
40665	Matt Black/Negro Mate

Material	**Body** ABS+Steel/ABS+Acero
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º 45º







Coco 3L

40666	Matt White/Blanco Mate
40667	Matt Black/Negro Mate

Material	**Body** ABS+Steel/ABS+Acero
Light Source	3 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º 45º



PRICES



Coco spotlight 2L Ref. 40665
designed by Faro Lab

Stone by Àlex & Manel Lluscà



Stone

43500 Grey/Gris + Matt Black/Negro Mate

Material	**Body** Concrete+Steel/Cemento+Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º 90º





Stone 2L

43501 Grey/Gris + Matt Black/Negro Mate

Material	**Body** Concrete+Steel/Cemento+Acero
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º 90º





Stone 3L

43502 Grey/Gris + Matt Black/Negro Mate

Material	**Body** Concrete+Steel/Cemento+Acero
Light Source	3 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º 90º



PRICES



Stone spotlight Ref. 43500
designed by Àlex & Manel Lluscà

Orleans by Nahtrang





Orleans

43520	Matt White/Blanco Mate
43521	Matt Black/Negro Mate
43522	Shiny Chrome/Cromo Brillo + Matt Black/Negro Mate



Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20





Ceiling
230







Orleans 2L

43523	Matt White/Blanco Mate
43525	Shiny Chrome/Cromo Brillo + Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20









Orleans 3L

43527	Matt Black/Negro Mate
43528	Shiny Chrome/Cromo Brillo + Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	3 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20





PRICES



Orleans spotlight 2L Ref. 43523
designed by Nahtrang





Ring

40550 Matt White/Blanco Mate + Shiny Chrome/Cromo Brillo
40551 Dark Grey/Gris Oscuro + Shiny Chrome/Cromo Brillo

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º 90º







Link by Estudi Ribaudí

29873 Matt White/Blanco Mate
29874 Matt Black/Negro Mate
29897 Bronze/Bronce



Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º 90º

Ceiling 230


Table&Floor 102


Track 436

Wall 404







Link 2L by Estudi Ribaudí

29875 Matt White/Blanco Mate
29876 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º 90º





PRICES



Link spotlight Ref. 29874
designed by Estudi Ribaudí



Click recessed Ref. 43600

indoor interior

Recessed Empotrables

Domino by Aldanondoyfdez





Domino

63313 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 2700K 200lm
CRI	>=80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cut out	265x160

Driver ✔



PRICES





Neu

63286 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	1 GU5.3 MR16 max. 8W
Bulb incl.	No
Recom. Bulb	97686227
Socket incl.	Yes
Recom. Socket	
Class	III
IP	20
Cut out	ø160 30º



Nord

63290 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso **Diff** Opal PMMA/PMMA Opal
Light Source	SMD LED 18W 3000K 1400lm
CRI	>80
Recom. Driver	98310118LC
Class	III
IP	20
Cut out	ø305

Driver ⊗



*Drivers info pag. 818-819



Signal

02100101 Satin Nickel/Níquel Satinado

Material	**Body** Aluminium/Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 3W 3000K 102lm
CRI	>80
Recom. Driver	98310103
Class	III
IP	65
Beam angle	36°
Cut out	ø49

Driver ⊗

*Drivers info pag. 818-819

Recessed box/*Caja de empotrar*

02100101C Black/Negro

Material	**Body** PVC



PRICES





Navi

63481 White/Blanco

Material	**Body** Plaster/Yeso
Light Source	SMD LED 10W 3000K 630lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
Cut out	273x273
	Driver ✔



PRICES



*Drivers info pag. 818-819

Plas SQ

63283 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	HIGH POWER LED 1W 3000K 112lm
CRI	>80
Recom. Driver	98310103
Class	III
Voltage (V/Hz)	/50-60Hz
IP	20
Cut out	155x110

Driver ✗





*Drivers info pag. 818-819

Plas RCT

63490 White/Blanco

Material	**Body** Plaster/Yeso
Light Source	HIGH POWER LED 1W 2700K 200lm
CRI	>80
Driver incl.	Yes
Recom. Driver	98310103
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
Cut out	248x113

Driver ✓





*Drivers info pag. 818-819

Plas oval

63281 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	HIGH POWER LED 1W 3000K 112lm
CRI	>80
Recom. Driver	98310103
Class	III
Voltage (V/Hz)	/50-60Hz
IP	20
Cut out	175x110

Driver ✗



*Drivers info pag. 818-819

Plas linear

63282 Matt White/Blanco Mate

Material	**Body** Plaster/Yeso
Light Source	HIGH POWER LED 1W 3000K 112lm
CRI	>80
Recom. Driver	98310103
Class	III
Voltage (V/Hz)	/50-60Hz
IP	20
Cut out	231x85

Driver ✗



PRICES



Thanks to Lucia Buiza Photo by Pablo Gómez-Ogando Rodríguez
Plas recessed Ref. 63490





Hyde R Orientable

40118 Matt White/Blanco Mate
40119 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	ø83







Hyde R

40114 Matt White/Blanco Mate
40115 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	44
Cut out	ø83







Hyde R Orientable Trimless

40110 Matt White/Blanco Mate
40111 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	ø83



PRICES





Hyde SQ Orientable

40120 Matt White/Blanco Mate
40121 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	83x83

30º







Hyde SQ

40116 Matt White/Blanco Mate
40117 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	44
Cut out	83x83







Hyde SQ Orientable Trimless

40112 Matt White/Blanco Mate
40113 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	102x93

30º



PRICES





Hyde SQ Orientable 2L

40126 Matt White/Blanco Mate
40127 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	83x165
	30º







Hyde SQ 2L

40124 Matt White/Blanco Mate
40125 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	44
Cut out	83x165







Hyde SQ Orientable Trimless 2L

40122 Matt White/Blanco Mate
40123 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	182x93
	30º



PRICES



Hyde recessed Ref. 40126





Radon SQ

43396 Matt White/Blanco Mate
43406 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	ø80 30º







Radón RCT

43397 Matt White/Blanco Mate
43407 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	80x170 30º







Radon R

43398 Matt White/Blanco Mate
43408 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	ø80 30º



PRICES





Argon SQ

43402 Matt White/Blanco Mate
43412 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	100x100
	60º







Argon RCT

43403 Matt White/Blanco Mate
43413 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	220x102
	60º







Argon R

43401 Matt White/Blanco Mate
43411 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	ø100
	60º



PRICES





Neon SQ

43400 Matt White/Blanco Mate
43410 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	70x70







Neon R

43399 Matt White/Blanco Mate
43409 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	ø65







Gas

43404 Matt White/Blanco Mate
43405 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Socket incl.	No
Recom. Socket	43065
IP	20
Cut out	ø76



PRICES





Nais Orientable

02111001 White/Blanco
02111002 Black/Negro

Material	**Body** Aluminium+Steel/Aluminio+Acero
	Diff Transparent PMMA/PMMA Transparente
Light Source	COB LED 7W 2700K 625lm
CRI	>=90
Recom. Driver	98310620
Class	III
IP	23
Beam angle	36°
Cut out	ø76

15º Driver ✕



*Drivers info pag. 818-819





Nais

02121001 White/Blanco
02121002 Black/Negro

Material	**Body** Aluminium+Steel/Aluminio+Acero
	Diff Transparent PMMA/PMMA Transparente
Light Source	COB LED 7W 2700K 625lm
CRI	>=90
Class	III
IP	23
Beam angle	36°
Cut out	ø60

Driver ✕



*Drivers info pag. 818-819



Koi

42921 Matt White/Blanco Mate

Material	**Body** PC
	Diff Opal PC/PC Opal
Light Source	SMD LED 6W 3000K 400lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cut out	ø72

15º Driver ✓



PRICES





Click

43600 Matt White/Blanco Mate
43601 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 3W 2700K 252lm
CRI	85
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20
Cut out	80

90º 350º Driver ✓





Wet

02100801 Matt White/Blanco Mate

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
IP	44
Cut out	ø65





Clear

02100301 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 7W 3000K 403lm
CRI	>80
Recom. Driver	98310620
Class	III
IP	65
Beam angle	36°
Cut out	ø60

DIM Driver ✗



*Drivers info pag. 818-819

PRICES



Click recessed Ref. 43601





Stan recessed

43752	Matt White/Blanco Mate
43753	Matt Black/Negro Mate
43761	Satin Gold/Oro Satinado



Material	**Body** Aluminium+ABS/Aluminio+ABS
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20
Cut out	ø50




Ceiling 235


Spot 392

Suspended 208


Track 438


Wall 372



*Accessories page 392/*Accesorios en página 392*



Ebba

42919	Satin Nickel/Níquel Satinado

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 4W 3000K 304lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
Cut out	ø63

Driver ✔





Wabi

43900	Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	COB LED 10W 600lm
Dimmable K	1800 - 3200K
CRI	>=90
Class	III
IP	20
Beam angle	60°
Cut out	ø70

DIM Driver ✘



*Drivers info pag. 818-819

PRICES



Stan recessed Ref. 43753





Fox

02101001 Matt White/Blanco Mate
02101002 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 5W 2700K 500lm
CRI	>80
Class	III
IP	20
Beam angle	25°
Cut out	ø35

DIM Driver



*Drivers info pag. 818-819





Fox Trimless

02101101 Matt White/Blanco Mate
02101102 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 5W 2700K 500lm
CRI	>=90
Class	III
IP	20
Beam angle	25°
Cut out	ø45

DIM Driver



*Drivers info pag. 818-819





Fox 50 Orientable

02101301 Matt White/Blanco Mate
02101302 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 5W 2700K 500lm
CRI	>80
Class	III
IP	20
Beam angle	25°
Cut out	ø45

20º Driver



*Drivers info pag. 818-819

PRICES



Fox 50

02101501 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 7W 2700K 535lm
CRI	>80
Recom. Driver	98310620
Class	III
IP	20
Beam angle	36°
Cut out	ø40

DIM Driver ⊗



*Drivers info pag. 818-819



Fox 65

02101601 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 10W 2700K 680lm
CRI	>80
Recom. Driver	98310620
Class	III
IP	20
Beam angle	36°
Cut out	ø55

DIM Driver ⊗



*Drivers info pag. 818-819



Moist

02100901 Matt White/Blanco Mate

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	II
IP	44
Cut out	78x78



PRICES





Fresh IP44

02200501	Matt White/Blanco Mate
02200502	Matt Black/Negro Mate
02200503	Matt Gold/Oro Mate



Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	II
IP	44
Cut out	ø83







Fresh

02100501	Matt White/Blanco Mate
02100502	Matt Black/Negro Mate
02100503	Matt Gold/Oro Mate



Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	II
IP	20
Cut out	ø83







Fresh Trimless

02100701	Matt White/Blanco Mate
02100702	Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	II
IP	20
Cut out	ø90



PRICES



Fresh recessed Ref. 02100501



Fresh E27 Trimless

02300101 White/Blanco

Material	**Body** Aluminium/Aluminio
Light Source	1 E27 max. 8W
Bulb incl.	No
Recom. Bulb	17464
Class	I
IP	20
Cut out	ø90







Fresh Washer

02100601 Matt White/Blanco Mate
02100602 Matt Black/Negro Mate
02100603 Matt Gold/Oro Mate



Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	II
IP	20
Cut out	ø83







Fresh IP65

02101401 Matt White/Blanco Mate
02101402 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	I
IP	65
Cut out	ø83







Fresh IP65 Trimlees

02400101 Matt White/Blanco Mate
02400102 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	I
IP	65
Cut out	ø83



PRICES



Fresh recessed Ref. 02100601



Son 112

42928 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 8W 2700K 580lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cut out	ø100

Driver ✔





Son 220

42929 2700K Matt White/Blanco Mate

42930 4000K Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 24W 2000lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	20
Cut out	ø205

Driver ✔



PRICES



Ted

42926 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 15W 3000K 1200lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
Beam angle	160°
Cut out	ø150

Driver ✔





Tod

42927 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 20W 3000K 2000lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
Beam angle	160°
Cut out	ø160

Driver ✔





Luan

42931 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 40W 3000K 3200lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44
Cut out	ø375

Driver ✔



PRICES



Stan track Ref. 43724

indoor interior

Track
Carril



Orleans by Nahtrang

43536 Matt Black/Negro Mate

Material	**Body** Steel/Acero
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20



Ceiling
230



Spot
402









Link by Estudi Ribaudí

29871	Matt White/Blanco Mate
29872	Matt Black/Negro Mate
29896	Bronze/Bronce

Material	**Body** Steel+ABS/Acero+ABS
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20



Ceiling
230



Spot
404



Table&Floor
102

Wall
404



PRICES



Orleans track Ref. 43536
designed by Nahtrang





Stan LED

43724 Matt White/Blanco Mate
43725 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio **Diff** Transparent PC/PC Transparente
Light Source	COB LED 12W 2700K 1200lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	20

350º 90º Driver ✔







Stan

43720 Matt White/Blanco Mate
43721 Matt Black/Negro Mate
43757 Satin Gold/Oro Satinado



Material	**Body** Aluminium+ABS/Aluminio+ABS
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	20

350º



Ceiling 235 **Recessed** 424 **Spot** 392 **Suspended** 208 **Wall** 372



*Accessories page 392/*Accesorios en página 392*





Plot

64202 Matt White/Blanco Mate
64203 Matt Black/Negro Mate

Material	**Body** Steel+ABS/Acero+ABS
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17316
Class	I
IP	20

350º 90º



PRICES



Accessories/Accesorios



Surface track 1mt/Carril de superficie 1mt

64210A White/Blanco
64212A Black/Negro
64214A Grey/Gris

Material **Body** Aluminium/Aluminio





Surface track 2mts/Carril de superficie 2mts

64211A White/Blanco
64213A Black/Negro
64215A Grey/Gris

Material **Body** Aluminium/Aluminio



PRICES

outdoor exterior



Saigon floor lamp Ref. 71575-09
designed by Nahtrang

outdoor exterior

floor
suelo

Saigon by Nahtrang

NEW



Saigon out C100

71569-10 NEW Dark Grey/Gris Oscuro + Beige

Material	**Body** Aluminium+Concrete/Aluminio+Cemento
	Diff Opal PEMD/PEMD Opal
	Shade PP
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT



Portable
562

NEW



Saigon out 1950 C70

71569-09 NEW Dark Grey/Gris Oscuro + Beige

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PP
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT



Suspended
558

Portable
562

Spike
532

NEW



Saigon out 1200 C70

71575-09 NEW Dark Grey/Gris Oscuro + Beige

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PP
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT



PRICES



Saigon floor lamp Ref. 71569-10
designed by Nahtrang

Saigon by Nahtrang



Saigon out W100

71569-08 Dark Grey/Gris Oscuro + Brown/Marrón

Material	**Body** Aluminium+Concrete/Aluminio+Cemento
	Diff Opal PEMD/PEMD Opal
	Shade Synthetic wicker/Mimbre sintético
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Portable
564



Saigon out 1950 W70

71569-07 Dark Grey/Gris Oscuro + Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Synthetic wicker/Mimbre sintético
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Suspended
558



Portable
564



Spike
532



Saigon out 1200 W70

71575-07 Dark Grey/Gris Oscuro + Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Synthetic wicker/Mimbre sintético
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Suspended
558



Portable
564



Spike
532

PRICES



Saigon floor lamp Ref. 71569-08
designed by Nahtrang

Saigon by Nahtrang





Saigon out 1950 T70

71569-05 Dark Grey/Gris Oscuro + Cream/Crema
71569-06 Dark Grey/Gris Oscuro + Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Textilene
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT







Saigon out 1200 T70

71575-05 Dark Grey/Gris Oscuro + Cream/Crema
71575-06 Dark Grey/Gris Oscuro + Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Textilene
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT




Suspended
558


Portable
564


Spike
532

PRICES



Saigon floor lamp Ref. 71575-05
designed by Nahtrang

Saigon by Nahtrang



Saigon out 2100 R45

71569-04 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Saigon out 1300 R45

71575-04 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Saigon out 670 R45

71576-04 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT



Suspended 560 **Portable** 566 **Spike** 534



PRICES



Saigon out 2000 R55

71569-01 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Saigon out 1150 R55

71575-01 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Saigon out 500 R55

71576-01 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT


Suspended
560


Portable
566


Spike
534



PRICES

Akane by Pepe Llaudet









Akane

71262	Matt Black/Negro Mate + Green/Verde
71263	Matt Black/Negro Mate + Beige
71264	Matt Black/Negro Mate + Dark Brown/Marrón Oscuro

Material	**Body** Steel/Acero
	Shade PP
Light Source	E27 max. 12W
Bulb incl.	No
Recom. Bulb	17425
Class	II
IP	44
Cable	5 MT



PRICES

*Only for glass LED bulbs, models A60, ST64, G95 and G125
Sólo para bombillas LED de vidrio, modelos A60, ST64, G95 y G125



Akane floor Ref. 71264
designed by Pepe Llaudet

Cadaques by Faro Lab



2.5mts. cable extension accessory / *Accesorio extensión de cable 2.5mts.*

71244





Cadaques

71242	Dark Grey/Gris Oscuro + Beige
71243	Dark Grey/Gris Oscuro + Blue/Azul

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
	Shade Textilene
Light Source	SMD LED 18W 2700K 500lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44
Cable	3 MT

Driver ✔



PRICES



Cadaques floor Ref. 71242
designed by Faro Lab

Versus by Pepe Llaudet



Versus

74423 Matt White/Blanco Mate

Material	**Body** PEMD
	Diff Matt White/Blanco Mate
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT





Large strucure / *Estructura grande*

74424 Black/Negro

Material **Body** Steel/Acero





Small strucure / *Estructura pequeña*

74422 Black/Negro

Material **Body** Steel/Acero



PRICES



Versus floor Ref. 74423
designed by Pepe Llaudet



Saigon out R55 by Nahtrang

71584-02 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT









Cat by Nahtrang

71562 Matt Black/Negro Mate

71563 Matt White/Blanco Mate

71564 Red/Rojo

Material	**Body** Aluminium/Aluminio
	Diff Matt White PEMD/PEMD Blanco Mate
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	54
Cable	5 MT





Wall accessory/*Accesorio aplique*

71556 Black/Negro

Material **Body** Aluminium/Aluminio



PRICES



Cat floor Ref. 71563
designed by Nahtrang

Brot by Yembarastudio



reddot winner 2021

Standard/Estándar



71253 71254

Brot 900

71253 ● Black/Negro

Light Source	SMD LED 2W 2700K 620lm

Brot 1800

71254 ● Black/Negro

Material	**Body** Aluminium/Aluminio **Diff** Opal Glass/Cristal Opal
Light Source	SMD LED 3W 2700K 930lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔





Portable/*Portátil*



71256 71257

Brot 900 portable

71256 ● Black/Negro

Light Source	SMD LED 10W 2700K 620lm

Brot 1800 portable

71257 ● Black/Negro

Material	**Body** Aluminium/Aluminio **Diff** Opal Glass/Cristal Opal
Light Source	SMD LED 21W 2700K 930lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
Cable	1.8 MT

Driver ✔



PRICES



Totem by Roger Vancells

NEW

reddot winner 2023







Totem 285

75550 2700K — Grey Cement/Cemento Gris

75551 3000K — Grey Cement/Cemento Gris

Material	**Body** Concrete/Cemento
Light Source	SMD LED 6,5W370lm
CRI	>=80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	55
IK	06

Driver ✔









Totem 611

75552 2700K — Grey Cement/Cemento Gris

75553 3000K — Grey Cement/Cemento Gris

Material	**Body** Concrete/Cemento
Light Source	SMD LED 6,5W370lm
CRI	>=80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	55
IK	06

Driver ✔





Totem bollard Ref. 75553

Balic by Yembarastudio

NEW


2700K


3000K


4000K



Balic

70295 ● Black/Negro

Material	**Body** Aluminium/Aluminio
	Diff Prism Glass/Cristal Prismático
Light Source	SMD LED 8W 813/870/896lm
CRI	>=80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65

Driver ✔


Wall
583



PRICES





Lotus 350 by Estudi Ribaudí

71224 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 18W 3000K 1120lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08

Driver ✔



Wall
610





Lotus 650 by Estudi Ribaudí

71225 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 18W 3000K 1120lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08

Driver ✔





Block 350 by Àlex & Manel Lluscà

74141 Grey Cement/Cemento Gris

Material	**Body** Concrete/Cemento
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	65
IK	05

SEA SIDE SUITABLE



Wall
586





Block 700 by Àlex & Manel Lluscà

74142 Grey Cement/Cemento Gris

Material	**Body** Concrete/Cemento
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	I
IP	65
IK	06

SEA SIDE SUITABLE



PRICES



Lotus bollard Ref. 71224
designed by Estudi Ribaudí



Cast 300

74155 Dark Grey/Gris Oscuro

Material	**Body** Concrete/Cemento
	Diff Opal PC/PC Opal
Light Source	SMD LED 10W 3000K 550lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	06

Driver ✔





Cast 500

74156 Dark Grey/Gris Oscuro

Material	**Body** Concrete/Cemento
	Diff Opal PC/PC Opal
Light Source	SMD LED 10W 3000K 550lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	06

Driver ✔



PRICES



Cast 300 bollard Ref. 74155



Twist 300 by Estudi Ribaudí

71286 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 10W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔



Wall
584





Twist 500 by Estudi Ribaudí

71287 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 10W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔





Shelby 330 by Conillas

75537 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 10W 3000K 600lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔





Shelby 630 by Conillas

75538 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 10W 3000K 600lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔



PRICES



Twist post lamp Ref. 71286
designed by Estudi Ribaudí



Sticker by Lucid Product Design

75541 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 10W 3000K 623lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	55

Driver ✔

Wall
612





Tram 630 by Estudi Ribaudí

75531 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	E27 15W
Recom. Bulb	17463
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Pole
518

Wall
586





Datna 300 by Àlex & Manel Lluscà

74441 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44

Pole
518

Wall
592





Datna 600 by Àlex & Manel Lluscà

74442 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



PRICES



Sticker bollard Ref. 75541
designed by Lucid Product Design







Kila 400

71746	Dark Grey/Gris Oscuro +Transparent/Transparente
71747	Dark Grey/Gris Oscuro +Smoked/Fumé
71748	Dark Grey/Gris Oscuro +Amber/Ámbar

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	65



Ceiling
577



Wall
592









Kila 700

71749	Dark Grey/Gris Oscuro +Transparent/Transparente
71750	Dark Grey/Gris Oscuro +Smoked/Fumé
71751	Dark Grey/Gris Oscuro +Amber/Ámbar

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	65



PRICES



Kila bollard Ref. 71750



Plim 1

71299 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 10W 3000K 250lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08

Driver ✔





Plim 2

71300 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 10W 3000K 250lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08

Driver ✔





Plim 3

71301 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 10W 3000K 250lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08

Driver ✔



PRICES



Plim bollard Ref. 71299



Muga 295

75603 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 11W 3000K 810lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	55

Driver ✔





Muga 500

75604 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 11W 3000K 810lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	55

Driver ✔





Giza 265

70767 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	COB LED 15W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
IK	05

Driver ✔





Giza 650

70768 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	COB LED 15W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
IK	05

Driver ✔



PRICES



Onze

70761 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	54





Wilma 270

74997 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



Suspended
571



Wall
596





Wilma 340

75001 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44





Wilma 820

75003 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



PRICES



Beret 500

75522 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 8W 4000K 350lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54
IK	04

Driver ✔





Beret 900

75523 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 8W 4000K 350lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54
IK	04

Driver ✔





Nanda 500

71216 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 12W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver ✔



PRICES



Nanda 800

71217 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 12W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver ✔





Logar 650

75605 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 12W 3000K 580lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver ✔





Logar 900

75606 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 23W 3000K 1340lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver ✔



PRICES



Muffin 259 by Àlex & Manel Lluscà

74433S-04 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44



Bollard 484 **Pole** 522 **Suspended** 570 **Wall** 594





Mistu 310 by Faro Lab

74433S-02 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44



Bollard 484 **Pole** 522 **Suspended** 570 **Wall** 594





Blubs 240 by Estudi Ribaudí

74433S-03 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44



Bollard 484 **Pole** 524 **Suspended** 570 **Wall** 594





Moon 300 by Faro Lab

74433S-01 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44



Bollard 484 **Suspended** 570 **Wall** 594



PRICES



Moon post lamp Ref. 74433S-01
designed by Faro Lab



Muffin 559 by Àlex & Manel Lluscà

74434B-04 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Pole 522 | **Post** 482 | **Suspended** 570 | **Wall** 594





Mistu 600 by Faro Lab

74434B-02 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Pole 522 | **Post** 482 | **Suspended** 570 | **Wall** 594





Blubs 540 by Estudi Ribaudí

74434B-03 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Pole 522 | **Post** 482 | **Suspended** 570 | **Wall** 594





Moon 610 by Faro Lab

74434B-01 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Post 482 | **Suspended** 570 | **Wall** 594



PRICES



Muffin bollard Ref. 74434B-04
designed by Àlex & Manel Lluscà



Noboru

70576 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 16W 3000K 690lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50Hz
IP	65
IK	08
Beam angle	36°

Driver





Mila

70771 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 18W 4000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65

Driver





Sete

75521 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 6W 3000K 155lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver



PRICES



Noboru bollard Ref. 70576



Mauren

70993 Brass/Latón

Material	**Body** Brass/Latón
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44

SEA SIDE SUITABLE





Surat

72310 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	54





Nala

70772 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	54



Wall
602



PRICES



Mauren bollard Ref. 70993

Shadow by Àlex & Manel Lluscà



Shadow 250

72311 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 11W 3000K 800lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔





Shadow 450

72312 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 11W 3000K 800lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔



PRICES



Grow by Estudi Ribaudí



Grow

71206 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 9W 3500K 720lm
CRI	85
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔





Flowerpot/*Macetero*

71208 Dark Grey/Gris Oscuro



PRICES



Grow bollard flowerpot Ref. 71207+71208
designed by Estudi Ribaudí

Bu-Oh by Estudi Ribaudí

GERMAN DESIGN AWARD WINNER 2018



Bu-Oh 265

71213 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 12W 3000K 310lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔



Pole
518



Wall
610





Bu-Oh 560

71214 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 12W 3000K 310lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔



PRICES





Alp 500

74451 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 7W 3000K 350lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
Beam angle	180°
	Driver ✔





Alp 800

74452 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 7W 3000K 350lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
Beam angle	180°
	Driver ✔





Das 300

75519 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 8W 3000K 480lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
IK	06
Beam angle	180°
	Driver ✔





Das 650

75520 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 8W 3000K 480lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
IK	06
Beam angle	180°
	Driver ✔



PRICES



Alp 800 bollard Ref. 74452



Naya 200

71198 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 8W 3000K 180lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
Beam angle	120°

Driver ✔





Naya 500

71199 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 8W 3000K 180lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
Beam angle	120°

Driver ✔







Agra 200

70755 Dark Grey/Gris Oscuro
70756 Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 9W 3000K 420lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	55

Driver ✔







Agra 650

70753 Dark Grey/Gris Oscuro
70754 Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 9W 3000K 420lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	55

Driver ✔



PRICES



Naya 500 bollard Ref. 71199



Gina

71352 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 5W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	44



Wall
627





Chandra

72298 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 7W 3000K 195lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
Beam angle	30°
	Driver ✔





Spy 145

70782 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 6W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Beam angle	30°
	350º Driver ✔





Spy 435

70783 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 6W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Beam angle	30°
	350º Driver ✔



PRICES



Spy 435 bollard Ref. 70783



Klamp

74411 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



Wall
630





Soleil

70785 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 2W 3000K 140lm
CRI	>80
Class	III
IP	54
IK	07
	7h Charge Max. 3h Worktime

PIR Driver ✔





Saura

70774 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 2W 3000K 225lm
CRI	>80
Class	III
IP	54
Beam angle	180°
	8h Charge Max. 2,5h Worktime

PIR Driver ✔



PRICES



Saura solar bollard Ref. 70774



Bezel

70247 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 8W 2700K 349lm
CRI	>=90
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	06
Cable	1.2 MT

Driver ✔



Spike
540





Bast

70292 Dark Grey/Gris Oscuro

Material	**Body** Aluminium+PC/Aluminio+PC
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 25W 3000K 2100lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	10
Beam angle	360°

Driver ✔





180º Accessory / *Accesorio 180º*

70293 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio

PRICES



Bezel bollard Ref. 70247

Rush&Screen

by Estudi Ribaudí

Electronics and optics by *VOSSLOH-SCHWABE*

Optional drivers by *TCI*

Different optics to choose from



360º LENS
Optical efficiency 97%
Optimal installation ratio 2:1
(Pole distance to pole height)



360º WIDE LENS
Optical efficiency 96%
Optimal installation ratio 4,5:1
(Pole distance to pole height)



ASSYMETRICAL LENS
Optical efficiency 93%
Optimal installation ratio 4:1
(Pole distance to pole height)



Rush

Body Aluminium/Aluminio
Diff Transparent Polycarbonate/ Policarbonato transparente

COB LED	*VOSSLOH-SCHWABE*
MacAdam Steps	2
Risk Group	1
Lumen maintenance	L90 B10 up to 89.000h
Heat dissipation	Tested at high ambient temperature

IP65 | CRI90 | IK10 | 100-240V | 50-60Hz | Driver incl. | DALI optional | CASAMBI optional





Rush 14W	**CCT**	**FLUX**	**LENS**
750000	2700K	830lm	360°
750000C	2700K	830lm	360°
750000D	2700K	830lm	360°
750001	2700K	980lm	360° WIDE
750001C	2700K	980lm	360° WIDE
750001D	2700K	980lm	360° WIDE
750002	2700K	795lm	180°
750002C	2700K	795lm	180°
750002D	2700K	795lm	180°
750010	3000K	830lm	360°
750010C	3000K	830lm	360°
750010D	3000K	830lm	360°
750011	3000K	980lm	360° WIDE
750011C	3000K	980lm	360° WIDE
750011D	3000K	980lm	360° WIDE
750012	3000K	795lm	180°
750012C	3000K	795lm	180°
750012D	3000K	795lm	180°
750020	4000K	830lm	360°
750020C	4000K	830lm	360°
750020D	4000K	830lm	360°
750021	4000K	980lm	360° WIDE
750021C	4000K	980lm	360° WIDE
750021D	4000K	980lm	360° WIDE
750022	4000K	795lm	180°
750022C	4000K	795lm	180°
750022D	4000K	795lm	180°



Rush 20W	**CCT**	**FLUX**	**LENS**
750100	2700K	1147lm	360°
750100C	2700K	1147lm	360°
750100D	2700K	1147lm	360°
750101	2700K	1355lm	360° WIDE
750101C	2700K	1355lm	360° WIDE
750101D	2700K	1355lm	360° WIDE
750102	2700K	1103lm	180°
750102C	2700K	1103lm	180°
750102D	2700K	1103lm	180°
750110	3000K	1147lm	360°
750110C	3000K	1147lm	360°
750110D	3000K	1147lm	360°
750111	3000K	1355lm	360° WIDE
750111C	3000K	1355lm	360° WIDE
750111D	3000K	1355lm	360° WIDE
750112	3000K	1103lm	180°
750112C	3000K	1103lm	180°
750112D	3000K	1103lm	180°
750120	4000K	1147lm	360°
750120C	4000K	1147lm	360°
750120D	4000K	1147lm	360°
750121	4000K	1355lm	360° WIDE
750121C	4000K	1355lm	360° WIDE
750121D	4000K	1355lm	360° WIDE
750122	4000K	1103lm	180°
750122C	4000K	1103lm	180°
750122D	4000K	1103lm	180°

PRICES





STANDARD Driver incl. LIGHTING SOLUTIONS

VOSSLOH-SCHWABE

Beacon mA	350mA
Bollard mA	500mA
V	100-240V
Hz	50-60Hz
Power factor	0.90
Low ripple	<30%
Lifetime	50000h

Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

**DALI option* TCI LED professional led applications

TCI

Beacon mA	350mA
Bollard mA	500mA
V	220-240V
Hz	50-60Hz
Power factor	0.95
Low ripple	<3%
Lifetime	50000h

DALI-2 dimmable
PUSH SWITCH compatible
Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

**CASAMBI option* TCI LED professional led applications

TCI

Beacon mA	350mA
Bollard mA	500mA
V	220-240V
Hz	50-60Hz
Power factor	0.95
Low ripple	<3%
Lifetime	50000h

DALI-2 dimmable
PUSH SWITCH compatible
Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

Rush

Body Aluminium/Aluminio
Diff Transparent Polycarbonate/ Policarbonato transparente

COB LED	*VOSSLOH-SCHWABE*
MacAdam Steps	2
Risk Group	1
Lumen maintenance	L90 B10 up to 89.000h
Heat dissipation	Tested at high ambient temperature

IP65 | CRI90 | IK10 | 100-240V | 50-60Hz | Driver incl. | DALI optional | CASAMBI optional





Rush 38W	CCT	FLUX	LENS
750200	2700K	3322lm	360°
750200C	2700K	3322lm	360°
750200D	2700K	3322lm	360°
750201	2700K	3079lm	360° WIDE
750201C	2700K	3079lm	360° WIDE
750201D	2700K	3079lm	360° WIDE
750202	2700K	2397lm	180°
750202C	2700K	2397lm	180°
750202D	2700K	2397lm	180°
750210	3000K	3322lm	360°
750210C	3000K	3322lm	360°
750210D	3000K	3322lm	360°
750211	3000K	3079lm	360° WIDE
750211C	3000K	3079lm	360° WIDE
750211D	3000K	3079lm	360° WIDE
750212	3000K	2397lm	180°
750212C	3000K	2397lm	180°
750212D	3000K	2397lm	180°
750220	4000K	3322lm	360°
750220C	4000K	3322lm	360°
750220D	4000K	3322lm	360°
750221	4000K	3079lm	360° WIDE
750221C	4000K	3079lm	360° WIDE
750221D	4000K	3079lm	360° WIDE
750222	4000K	2397lm	180°
750222C	4000K	2397lm	180°
750222D	4000K	2397lm	180°



Rush 38W	CCT	FLUX	LENS
750300	2700K	2972lm	360°
750300C	2700K	2972lm	360°
750300D	2700K	2972lm	360°
750301	2700K	2921lm	360° WIDE
750301C	2700K	2921lm	360° WIDE
750301D	2700K	2921lm	360° WIDE
750302	2700K	2576lm	180°
750302C	2700K	2576lm	180°
750302D	2700K	2576lm	180°
750310	3000K	2972lm	360°
750310C	3000K	2972lm	360°
750310D	3000K	2972lm	360°
750311	3000K	2921lm	360° WIDE
750311C	3000K	2921lm	360° WIDE
750311D	3000K	2921lm	360° WIDE
750312	3000K	2576lm	180°
750312C	3000K	2576lm	180°
750312D	3000K	2576lm	180°
750320	4000K	2972lm	360°
750320C	4000K	2972lm	360°
750320D	4000K	2972lm	360°
750321	4000K	2921lm	360° WIDE
750321C	4000K	2921lm	360° WIDE
750321D	4000K	2921lm	360° WIDE
750322	4000K	2576lm	180°
750322C	4000K	2576lm	180°
750322D	4000K	2576lm	180°

PRICES





STANDARD Driver incl. LIGHTING SOLUTIONS

VOSSLOH-SCHWABE

mA	1050mA
V	100-240V
Hz	50-60Hz
Power factor	0.90
Low ripple	<30%
Lifetime	50000h

Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

**DALI option* TCI LED professional led applications

TCI

mA	1050mA
V	220-240V
Hz	50-60Hz
Power factor	0.95
Low ripple	<3%
Lifetime	50000h

DALI-2 dimmable
PUSH SWITCH compatible
Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

**CASAMBI option* TCI LED professional led applications

TCI

mA	1050mA
V	220-240V
Hz	50-60Hz
Power factor	0.95
Low ripple	<3%
Lifetime	50000h

DALI-2 dimmable
PUSH SWITCH compatible
Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

Screen

Body Aluminium/Aluminio
Diff Transparent Polycarbonate/ Policarbonato transparente

COB LED	*VOSSLOH-SCHWABE*
MacAdam Steps	2
Risk Group	1
Lumen maintenance	L90 B10 up to 89.000h
Heat dissipation	Tested at high ambient temperature

IP65 | CRI90 | IK10 | 100-240V | 50-60Hz | Driver incl. | DALI optional | CASAMBI optional





Screen 14W	CCT	FLUX	LENS
751000	2700K	712lm	360°
751000C	2700K	712lm	360°
751000D	2700K	712lm	360°
751001	2700K	856lm	360° WIDE
751001C	2700K	856lm	360° WIDE
751001D	2700K	856lm	360° WIDE
751002	2700K	695lm	180°
751002C	2700K	695lm	180°
751002D	2700K	695lm	180°
751010	3000K	712lm	360°
751010C	3000K	712lm	360°
751010D	3000K	712lm	360°
751011	3000K	856lm	360° WIDE
751011C	3000K	856lm	360° WIDE
751011D	3000K	856lm	360° WIDE
751012	3000K	695lm	180°
751012C	3000K	695lm	180°
751012D	3000K	695lm	180°
751020	4000K	712lm	360°
751020C	4000K	712lm	360°
751020D	4000K	712lm	360°
751021	4000K	856lm	360° WIDE
751021C	4000K	856lm	360° WIDE
751021D	4000K	856lm	360° WIDE
751022	4000K	695lm	180°
751022C	4000K	695lm	180°
751022D	4000K	695lm	180°



Screen 20W	CCT	FLUX	LENS
751100	2700K	990lm	360°
751100C	2700K	990lm	360°
751100D	2700K	990lm	360°
751101	2700K	1225lm	360° WIDE
751101C	2700K	1225lm	360° WIDE
751101D	2700K	1225lm	360° WIDE
751102	2700K	965lm	180°
751102C	2700K	965lm	180°
751102D	2700K	965lm	180°
751110	3000K	990lm	360°
751110C	3000K	990lm	360°
751110D	3000K	990lm	360°
751111	3000K	1225lm	360° WIDE
751111C	3000K	1225lm	360° WIDE
751111D	3000K	1225lm	360° WIDE
751112	3000K	965lm	180°
751112C	3000K	965lm	180°
751112D	3000K	965lm	180°
751120	4000K	990lm	360°
751120C	4000K	990lm	360°
751120D	4000K	990lm	360°
751121	4000K	1225lm	360° WIDE
751121C	4000K	1225lm	360° WIDE
751121D	4000K	1225lm	360° WIDE
751122	4000K	965lm	180°
751122C	4000K	965lm	180°
751122D	4000K	965lm	180°

PRICES





STANDARD Driver incl. LIGHTING SOLUTIONS

VOSSLOH-SCHWABE

Beacon mA	350mA
Bollard mA	500mA
V	100-240V
Hz	50-60Hz
Power factor	0.90
Low ripple	<30%
Lifetime	50000h

Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

**DALI option* TCI LED professional led applications

TCI

Beacon mA	350mA
Bollard mA	500mA
V	220-240V
Hz	50-60Hz
Power factor	0.95
Low ripple	<3%
Lifetime	50000h

DALI-2 dimmable
PUSH SWITCH compatible
Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

**CASAMBI option* TCI LED professional led applications

TCI

Beacon mA	350mA
Bollard mA	500mA
V	220-240V
Hz	50-60Hz
Power factor	0.95
Low ripple	<3%
Lifetime	50000h

DALI-2 dimmable
PUSH SWITCH compatible
Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

Screen

Body Aluminium/Aluminio
Diff Transparent Polycarbonate/ Policarbonato transparente

COB LED	*VOSSLOH-SCHWABE*
MacAdam Steps	2
Risk Group	1
Lumen maintenance	L90 B10 up to 89.000h
Heat dissipation	Tested at high ambient temperature

IP65 | CRI90 | IK10 | 100-240V | 50-60Hz | Driver incl. | DALI optional | CASAMBI optional





Screen 38W	CCT	FLUX	LENS
751200	2700K	2370lm	360°
751200C	2700K	2370lm	360°
751200D	2700K	2370lm	360°
751201	2700K	2692lm	360° WIDE
751201C	2700K	2692lm	360° WIDE
751201D	2700K	2692lm	360° WIDE
751202	2700K	1819lm	180°
751202C	2700K	1819lm	180°
751202D	2700K	1819lm	180°
751210	3000K	2370lm	360°
751210C	3000K	2370lm	360°
751210D	3000K	2370lm	360°
751211	3000K	2692lm	360° WIDE
751211C	3000K	2692lm	360° WIDE
751211D	3000K	2692lm	360° WIDE
751212	3000K	1819lm	180°
751212C	3000K	1819lm	180°
751212D	3000K	1819lm	180°
751220	4000K	2370lm	360°
751220C	4000K	2370lm	360°
751220D	4000K	2370lm	360°
751221	4000K	2692lm	360° WIDE
751221C	4000K	2692lm	360° WIDE
751221D	4000K	2692lm	360° WIDE
751222	4000K	1819lm	180°
751222C	4000K	1819lm	180°
751222D	4000K	1819lm	180°



Screen 38W	CCT	FLUX	LENS
751300	2700K	2661lm	360°
751300C	2700K	2661lm	360°
751300D	2700K	2661lm	360°
751301	2700K	2145lm	360° WIDE
751301C	2700K	2145lm	360° WIDE
751301D	2700K	2145lm	360° WIDE
751302	2700K	1656lm	180°
751302C	2700K	1656lm	180°
751302D	2700K	1656lm	180°
751310	3000K	2661lm	360°
751310C	3000K	2661lm	360°
751310D	3000K	2661lm	360°
751311	3000K	2145lm	360° WIDE
751311C	3000K	2145lm	360° WIDE
751311D	3000K	2145lm	360° WIDE
751312	3000K	1656lm	180°
751312C	3000K	1656lm	180°
751312D	3000K	1656lm	180°
751320	4000K	2661lm	360°
751320C	4000K	2661lm	360°
751320D	4000K	2661lm	360°
751321	4000K	2145lm	360° WIDE
751321C	4000K	2145lm	360° WIDE
751321D	4000K	2145lm	360° WIDE
751322	4000K	1656lm	180°
751322C	4000K	1656lm	180°
751322D	4000K	1656lm	180°

PRICES





STANDARD Driver incl. LIGHTING SOLUTIONS

VOSSLOH-SCHWABE

mA	1050mA
V	100-240V
Hz	50-60Hz
Power factor	0.90
Low ripple	<30%
Lifetime	50000h

Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

**DALI option* TCI LED professional led applications

TCI

mA	1050mA
V	220-240V
Hz	50-60Hz
Power factor	0.95
Low ripple	<3%
Lifetime	50000h

DALI-2 dimmable
PUSH SWITCH compatible
Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)

**CASAMBI option* TCI LED professional led applications

TCI

mA	1050mA
V	220-240V
Hz	50-60Hz
Power factor	0.95
Low ripple	<3%
Lifetime	50000h

DALI-2 dimmable
PUSH SWITCH compatible
Overload protection
Short-circuit protection
Overheating protection
SELV (Safety Extra Low Voltage)



Rush H.3700 mm
38W
3000K
Ref. 750210
Optics 360º
Luminaires interdistance/Interdistancia entre luminarias 10mt.



Rush H.3100 mm
38W
3000K
Ref. 750311
Optics 360º Wide
Luminaires interdistance/Interdistancia entre luminarias 12mt.



Screen H.3700 mm
38W
3000K
Ref. 751312
Optics 180º
Luminaires interdistance/Interdistancia entre luminarias 10mt.



Screen H.3100 mm
38W
3000K
Ref. 751311
Optics 360º Wide
Luminaires interdistance/Interdistancia entre luminarias 12mt.



Bu-Oh 2500 by Estudi Ribaudí

71209 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 42W 3000K 2700lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔



Bollard 494 **Wall** 610





Tram 2500 by Estudi Ribaudí

75532 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 43W 3000K 3000lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	55
IK	05

Driver ✔



Beacon 472 **Wall** 586





Datna 2500 by Àlex & Manel Lluscà

74444E Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 37W 3000K 2700lm
CRI	85
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔



Bollard 472 **Wall** 592



PRICES



Bu-oh pole lamp Ref. 71209
designed by Estudi Ribaudí



Grop 2000

75602 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 27W 3000K 1300lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver ✔





Beret 1800

75524 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 16W 4000K 625lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
IK	04

Driver ✔



Bollard
480





Plaza

75607 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 24W 3000K 1120lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
IK	08

Driver ✔



PRICES



Grop pole lamp Ref. 75602



Mistu 2L by Faro Lab

74435F2-02 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44



Bollard 484 **Post** 482 **Suspended** 570 **Wall** 594





Muffin 2L by Àlex & Manel Lluscà

74435F2-04 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44



Bollard 484 **Post** 482 **Suspended** 570 **Wall** 594





Blubs 2L by Estudi Ribaudí

74435F2-03 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44



Bollard 484 **Post** 482 **Suspended** 570 **Wall** 594



PRICES



Mistu pole lamp Ref. 74435F2-02
designed by Faro Lab



Mistu 3L by Faro Lab

74436F3-02 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44





Muffin 3L by Àlex & Manel Lluscà

74436F3-04 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44





Blubs 3L by Estudi Ribaudí

74436F3-03 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44



PRICES



Muffin pole lamp Ref. 74436F3-04
designed by Àlex & Manel Lluscà



Nautica 1L

71116 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	33



Suspended
571

Wall
598



Nautica 2L

71117 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	33





Nautica 3L

71118 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	3 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	33



PRICES



Nautica pole lamp Ref. 71118



Saigon spike Ref. 71575P-09
designed by Nahtrang

outdoor exterior

Spikes & Projectors Estacas y Proyectores

Leaf by Estudi Ribaudí





Leaf

70233 Grey/Gris

Material	**Body** Recycled ABS/ABS Reciclado **Diff** Opal PC/PC Opal
Light Source	GU10 8W
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44
IK	10
Cable	0.5 MT

SEA SIDE SUITABLE Driver



PRICES



Saigon by Nahtrang

NEW



Saigon out C70

71575P-09 NEW Dark Grey/Gris Oscuro + Beige

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PP
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT




Floor 444


Suspended 558


Portable 562



Saigon out W70

71575P-07 Dark Grey/Gris Oscuro + Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Synthetic wicker/Mimbre sintético
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT



Floor 446


Suspended 558


Portable 564





Saigon out T70

71575P-05 Dark Grey/Gris Oscuro + Cream/Crema

71575P-06 Dark Grey/Gris Oscuro + Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Textilene
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT




Floor 448


Suspended 558


Portable 564

PRICES



Saigon spike Ref. 71575P-09
designed by Nahtrang



Saigon out 1500 R45

71575P-04 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Saigon out 870 R45

71576P-04 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Saigon out 1350 R55

71575P-01 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Saigon out 730 R17

71576P-03 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT





Saigon out 1370 R17

71575P-03 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	2 MT



PRICES



Saigon spike Ref. 71575P-04
designed by Nahtrang

Toni by Alegre Design





Toni

71528 Matt Black/Negro Mate

Material	**Body** PC
	Diff Transparent PC/PC Transparente
Light Source	1 GU10 max. 5W
Bulb incl.	No
Recom. Bulb	97685327
Class	II
IP	65
Cable	2.5 MT

SEA SIDE SUITABLE



PRICES

Piccola by Faro Lab







Piccola

70245	Matt Black/Negro Mate
70246	Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 6W 2700K 360lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Cable	1.5 MT

Driver ✔



PRICES

NEW



Bambou 1068

75556 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	LIGHT MODULE 8W 2200K 606lm
CRI	>=80
Class	I
Voltage (V/Hz)	200V-250V/50-60Hz
IP	65
IK	06
Beam angle	360°
Cable	0.2 MT
	Driver ✔



Bambou 1268

75557 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	LIGHT MODULE 8W 2200K 606lm
CRI	>=80
Class	I
Voltage (V/Hz)	200V-250V/50-60Hz
IP	65
IK	06
Beam angle	360°
Cable	0.2 MT
	Driver ✔



PRICES



NEW



Bezel

70248 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 8W 2700K 349lm
CRI	>=90
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	06
Cable	1.2 MT

Driver ✔



Bollard
504



NEW



Spy 145

70787 Dark Grey/Gris Oscuro

Material	**Body** Aluminium+PC/Aluminio+PC
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 6W 3000K 495lm
Class	I
Voltage (V/Hz)	220V-240V/50Hz
IP	65
IK	05
Beam angle	30°
Cable	2 MT

350º

Driver ✔



NEW



Spy 435

70788 Dark Grey/Gris Oscuro

Material	**Body** Aluminium+PC/Aluminio+PC
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 6W 3000K 495lm
Class	I
Voltage (V/Hz)	220V-240V/50Hz
IP	65
IK	05
Beam angle	30°
Cable	2 MT

350º

Driver ✔



PRICES



Bezel spike Ref. 70248



Seth 280

70227 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	SMD LED 6W 2700K 450lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44
Beam angle	40°
Cable	2 MT
	Driver ✔





Seth 600

70226 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	SMD LED 6W 2700K 450lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44
Beam angle	40°
Cable	2 MT
	Driver ✔





Foc 210 spike

70158 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 16W 3000K 800lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50Hz
IP	65
Beam angle	36°
Cable	0.5 MT
	Driver ✔





Foc 520 spike

70159 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 16W 3000K 800lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50Hz
IP	65
Beam angle	36°
Cable	0.5 MT
	Driver ✔



Projector
555



PRICES



Seth spike Ref. 70226



Sobek

70151 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 7W 3000K 550lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	06
Beam angle	50°

Driver ✔





Balder

70469 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 3W 3000K 110lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
Beam angle	50°
Cable	2 MT

Driver ✔





Plom

70913 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	COB LED 9W 3000K 635lm
Dimmable W	200lm / 635lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	64
Cable	0.3 MT

90 Driver ✔



Projector
554





Andy

71613 Satin Gold/Oro Satinado

Material	**Body** Steel/Acero
	Diff Transparent PC/PC Transparente
Light Source	1 GU10 max. 5W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	65
Cable	2 MT



PRICES



Tono

73150 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	44
Cable	2 MT





Garten lampholder

73111 Matt Black/Negro Mate

Material	**Body** ABS
Light Source	1 E27 PAR38 max. 15W
Bulb incl.	No
Recom. Bulb	17400
Class	II
IP	54
Cable	2.5 MT





Garten plug

73100 Matt Black/Negro Mate

Material	**Body** ABS
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
Cable	2.5 MT



Accessories/Accesorios



Connection box T

75801

IP 68



Connection box

75800

IP 68

PRICES

Slot by Lucid Product Design



Slot 200

70035 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 13W 3000K 750lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Beam angle	28°
	Driver ✔





Slot 500

70036 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 13W 3000K 750lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Beam angle	28°
	Driver ✔





Slot 200 spike

70037 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 13W 3000K 750lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Beam angle	28°
Cable	1.5 MT
	Driver ✔





Slot 500 spike

70038 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 13W 3000K 750lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Beam angle	28°
Cable	1.5 MT
	Driver ✔



PRICES



Slot spike Ref. 70037
designed by Lucid Product Design

Flow by Alegre Design





Flow

71546	Matt Black/Negro Mate
71547	Beige

Material	**Body** PC
	Diff Opal PC/PC Opal
Light Source	1 GU10 max. 5W
Bulb incl.	No
Recom. Bulb	97685327
Class	II
IP	65
Cable	2.5 MT

SEA SIDE SUITABLE

360º 160º







Spike accessory 60cm / *Accesorio estaca 60cm*

71548	Matt Black/Negro Mate
71549	Beige

Material	**Body** Aluminium/Aluminio

PRICES



Flow spike Ref. 71547+71548
designed by Alegre Design



Alfa by Àlex & Manel Lluscà

70025 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 13W 3000K 845lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Beam angle	80°

Driver ✔







Project 73 by Àlex & Manel Lluscà

71383 Grey/Gris

71390 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 5W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	65







Project 165 by Àlex & Manel Lluscà

71389 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 PAR38 max. 15W
Bulb incl.	No
Recom. Bulb	17398
Class	I
IP	65





PRICES



Alfa projector Ref. 70025
designed by Àlex & Manel Lluscà



Muur 210

71770 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 21W 3000K 1337lm
CRI	>=80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	06
Beam angle	36°

SEA SIDE SUITABLE 30º 10 Driver



Visor accessory / *Accesorio visera*



71770V Dark Grey/Gris Oscuro







Muur 250

71771 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 29W 3000K 1877lm
CRI	>=80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	06
Beam angle	36°

SEA SIDE SUITABLE 30º 10 Driver



Visor accessory / *Accesorio visera*



71771V Dark Grey/Gris Oscuro





PRICES



Muur projector Ref. 71771+71771V



Oko

70161 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 20W 3000K 1400lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	08
Beam angle	30°

Driver ✔





Plom

70912 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	COB LED 9W 3000K 635lm
Dimmable W	200lm / 635lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	64

90 Driver ✔



Spike
544





Toran

70140 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 4W 4000K 345lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
IK	08
Beam angle	115°

Driver ✔



PRICES



Lit

70260 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 5W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	54
	45º





Foc 150

70156 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 16W 3000K 800lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Beam angle	36°
	45º Driver ✔



Spike
542





Foc 580

70157 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 16W 3000K 800lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Beam angle	36°
	45º 45 Driver ✔



PRICES



Saigon suspended lamp Ref. 71584-09
designed by Nahtrang

outdoor exterior

Suspended
Suspensión

Saigon by Nahtrang



Saigon out C70

Cone	**71579C-09 NEW**	Dark Grey/Gris Oscuro + Beige
Hole	**71579H-09 NEW**	Dark Grey/Gris Oscuro + Beige





Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PP
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT



Floor	**Portable**	**Spike**
444	562	532





Saigon out W70 cone cap

Cone	**71579C-07**	Dark Grey/Gris Oscuro + Brown/Marrón
Hole	**71579H-07**	Dark Grey/Gris Oscuro + Brown/Marrón





Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Synthetic wicker/Mimbre sintético
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT



Floor	**Portable**	**Spike**
446	564	532





Saigon out T70 Cone cap

Cone	**71579C-05**	Dark Grey/Gris Oscuro + Cream/Crema
Cone	**71579C-06**	Dark Grey/Gris Oscuro + Brown/Marrón
Hole	**71579H-05**	Dark Grey/Gris Oscuro + Cream/Crema
Hole	**71579H-06**	Dark Grey/Gris Oscuro + Brown/Marrón





Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Textilene
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT



Floor	**Portable**	**Spike**
448	564	532



PRICES



Saigon suspended lamp Ref. 71579H-05
designed by Nahtrang

Saigon by Nahtrang



Saigon out R45 Cone cap

Cone	**71579C-04**	Dark Grey/Gris Oscuro + White/Blanco
Hole	**71579H-04**	Dark Grey/Gris Oscuro + White/Blanco





Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT



Floor
450



Portable
566



Spike
534





Saigon out R55

71579-02	Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT



Floor
451



Portable
566



Spike
534





Saigon out R17 cone cap

Cone	**71579C-03**	Dark Grey/Gris Oscuro + White/Blanco
Hole	**71579H-03**	Dark Grey/Gris Oscuro + White/Blanco





Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT

Portable
566

Spike
534



PRICES



Saigon suspended lamp Ref. 71579-02
designed by Nahtrang

Saigon by Nahtrang NEW



Saigon out C100 portable

71584-10 NEW Dark Grey/Gris Oscuro + Beige

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PP
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT





Floor
444



Saigon out C70 portable

71584-09 NEW Dark Grey/Gris Oscuro + Beige

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade PP
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT





Floor
444

Suspended
558

Spike
532

PRICES



Saigon by Nahtrang



*Rope not included / Cuerda no incluida

Saigon out W100 portable

71584-08 Dark Grey/Gris Oscuro + Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Synthetic wicker/Mimbre sintético
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT





Floor
446



*Rope not included / Cuerda no incluida

Saigon out W70 portable

71584-07 Dark Grey/Gris Oscuro + Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Synthetic wicker/Mimbre sintético
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT





Floor
446



Suspended
558



Spike
532



*Rope not included / Cuerda no incluida



Saigon out T70 portable

71584-05 Dark Grey/Gris Oscuro + Cream/Crema

71584-06 Dark Grey/Gris Oscuro + Brown/Marrón

Material	**Body** Aluminium/Aluminio
	Diff Opal PEMD/PEMD Opal
	Shade Textilene
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT





Floor
448



Suspended
558



Spike
532

PRICES



Saigon portable Ref. 71584-08
designed by Nahtrang

Saigon by Nahtrang



*Rope not included / Cuerda no incluida

Saigon out R45 portable

71584-04 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT





Floor
450

Suspended
560



Spike
534



*Rope not included / Cuerda no incluida

Saigon out R55 portable

71584-01 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT





Floor
451



Suspended
560



Spike
534



*Rope not included / Cuerda no incluida

Saigon out R17 portatil

71584-03 Dark Grey/Gris Oscuro + White/Blanco

Material	**Body** Aluminium/Aluminio
	Shade PEMD
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	44
Cable	3 MT



Suspended
560

Spike
534

PRICES



Saigon portable Ref. 71584-01
designed by Nahtrang



Scuba 600

75753 Chrome/Cromo

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Opal PC/PC Opal
Light Source	SMD LED 20W 3000K 3200lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	66
IK	10
Beam angle	120°
Cable	3 MT

Driver ✔

Wall
588





Scuba 1200

75754 Chrome/Cromo

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Opal PC/PC Opal
Light Source	SMD LED 36W 3000K 5760lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	66
IK	10
Beam angle	120°
Cable	3 MT

Driver ✔



Canopy accessory for wall & suspension / Accesorio florón para aplique y suspensión



75755 Matt Black/Negro Mate

Material **Body** Aluminium/Aluminio

PRICES



Scuba suspended lamp Ref. 75754



Muffin by Àlex & Manel Lluscà

74427C-04 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Bollard 484 **Pole** 522 **Post** 482 **Wall** 594





Mistu by Faro Lab

74427C-02 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Bollard 484 **Pole** 522 **Post** 482 **Wall** 594





Blubs by Estudi Ribaudí

74427C-03 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Bollard 484 **Pole** 522 **Post** 482 **Wall** 594





Moon by Faro Lab

74427C-01 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Bollard 484 **Post** 482 **Wall** 594



PRICES





Nautica 260

71106 Matt White/Blanco Mate + Matt Copper/Cobre Mate
71138 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	33
Cable	1 MT





Nautica 340

71139 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	33
Cable	1 MT


Pole
526


Wall
598





Wilma 800

75002 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44
Cable	1.5 MT


Post
479


Wall
596



PRICES



Kila ceiling Ref. 71741

outdoor exterior

Ceiling
Techo

NEW







Anga 240

72352 White/Blanco
72353 Dark Grey/Gris Oscuro

Material	**Body** Concrete/Cemento
	Diff Opal White PMMA/PMMA Blanco Opal
Light Source	SMD LED 18W 2700K 1300lm
CRI	>=80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
IK	04

Driver ✔



NEW







Anga 295

72354 White/Blanco
72355 Dark Grey/Gris Oscuro

Material	**Body** Concrete/Cemento
	Diff Opal White PMMA/PMMA Blanco Opal
Light Source	SMD LED 24W 2700K 1794lm
CRI	>=80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
IK	04

Driver ✔





Dakron

70722 Matt White/Blanco Mate

Material	**Body** ABS
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	65
IK	10

SEA SIDE SUITABLE



PRICES



Anga ceiling Ref. 72354



Yen

70690 Grey/Gris

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	54







Olot

71372 Matt White/Blanco Mate

71374 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	44





Tami

70799 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 9W 3000K 600lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
Beam angle	40°
	20º Driver ✔



PRICES





Tasa

70806 Dark Grey/Gris Oscuro
70821 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	97687127
Class	I
IP	44









Kila 200

71740 Dark Grey/Gris Oscuro +Transparent/Transparente
71741 Dark Grey/Gris Oscuro +Smoked/Fumé
71742 Dark Grey/Gris Oscuro +Amber/Ámbar

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	65



Bollard
474



Wall
592





Goz

70575 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 9W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
Beam angle	40°

Driver ✔



PRICES



outdoor exterior

Surface
Superficie

Tone by Nahtrang







Tone

71538	Matt White/Blanco Mate
71539	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 20W 3000K 1200lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	07

Driver



PRICES



Tone wall lamp Ref. 71538
designed by Nahtrang

Bronx by Àlex & Manel Lluscà











Bronx

71194	●	Brown/Marrón
71195	○	White/Blanco
71196	●	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	44



PRICES

Balic by Yembarastudio

NEW





2700K 3000K 4000K



Balic

70294 ● Black/Negro

Material	**Body** Aluminium/Aluminio
	Diff Prism Glass/Cristal Prismático
Light Source	SMD LED 8W 813/870/896lm
CRI	>=80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65

Driver ✓ CCT OPTIONS 2700K 3000K 4000K



Bollard
464

PRICES



Mask by Lucid Product Design

71279 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 15W 3000K 550lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	06

SEA SIDE SUITABLE Driver







Pals by Faro Lab

70290 Matt White/Blanco Mate

70291 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	65
IK	06





Twist by Estudi Ribaudí

71285 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 10W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver



Beacon
468



PRICES



Mask wall lamp Ref. 71279
designed by Lucid Product Design



Block 135 by Àlex & Manel Lluscà

74139 Grey Cement/Cemento Gris

Material	**Body** Concrete/Cemento
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	I
IP	65
IK	06

SEA SIDE SUITABLE



Beacon
466





Tram by Estudi Ribaudí

75533 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



Beacon
470



Pole
518







Half by Nahtrang

71536 Matt White/Blanco Mate

71537 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 20W 3000K 1350lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	05

Driver ✔



PRICES



Block wall lamp Ref. 74139
designed by Àlex & Manel Lluscà



Scuba 600

75750 Chrome/Cromo

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Opal PC/PC Opal
Light Source	SMD LED 20W 3000K 3200lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	66
IK	10
Beam angle	120°
Cable	3 MT

Driver ✔

Suspended
568





Scuba 1200

75751 Chrome/Cromo

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Opal PC/PC Opal
Light Source	SMD LED 36W 3000K 5760lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	66
IK	10
Beam angle	120°
Cable	3 MT

Driver ✔



Canopy accessory for wall & suspension / Accesorio florón para aplique y suspensión



75755 Matt Black/Negro Mate

Material **Body** Aluminium/Aluminio

PRICES



Scuba wall lamp Ref. 75751



Kerala

74453 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 13W 3000K 600lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver ✔

Portable
58





Orwell

75700 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 8W 3000K 450lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54

Driver ✔





Orwell camera

75701 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 13W 480lm
Dimmable W	4w 95lm / 13w 480lm
Dimmable K	3000 - 6500K
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54

DIM DIM Driver ✔



PRICES



Kerala wall lamp Ref. 74453







Kila

71743	Dark Grey/Gris Oscuro +Transparent/Transparente
71744	Dark Grey/Gris Oscuro +Smoked/Fumé
71745	Dark Grey/Gris Oscuro +Amber/Ámbar

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	65



Ceiling
577



Bollard
472





Datna by Àlex & Manel Lluscà

74440	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



Bollard
470

Pole
518



PRICES



Kila wall lamp Ref. 71744



Muffin by Àlex & Manel Lluscà

74432A-04 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Bollard 482 **Pole** 522 **Post** 480 **Suspended** 570





Mistu by Faro Lab

74432A-02 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Bollard 482 **Pole** 522 **Post** 480 **Suspended** 570





Blubs by Estudi Ribaudí

74432A-03 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Bollard 482 **Pole** 522 **Post** 480 **Suspended** 570





Moon by Faro Lab

74432A-01 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	44

Bollard 482 **Post** 480 **Suspended** 570



PRICES



Blub's wall lamp Ref. 74432A-03
designed by Estudi Ribaudí



Toc

70780 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 8W 3000K 600lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65

Driver ✔

Portable
56





Wilma 280

74998 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



Post
477



Suspended
571





Wilma 320

75000 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



PRICES



Argot

71424 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44





Dado

71606 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	I
IP	23



PRICES



Nautica 310

71110 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	33



Pole
526



Suspended
571





Nautica 280

71128 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	33





Nautica 350

71129 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	33



PRICES



Estoril 260

71140 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17462
Class	I
IP	33
IK	06





Estoril 310

71141 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	33
IK	06





Wally

74261 Rust Brown/Marrón Oxido

Material	**Body** Steel/Acero
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



PRICES



Timon

70996 Brass/Latón

Material	**Body** Brass/Latón
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44

SEA SIDE SUITABLE





Noray

70999 Brass/Latón

Material	**Body** Brass/Latón
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	65
IK	03

SEA SIDE SUITABLE





Nahir

70992 Brass/Latón

Material	**Body** Brass/Latón
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44

SEA SIDE SUITABLE





Borda

70997 Brass/Latón

Material	**Body** Brass/Latón
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44

SEA SIDE SUITABLE





Cabo

70998 Brass/Latón

Material	**Body** Brass/Latón
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	65
IK	05

SEA SIDE SUITABLE



PRICES



Nahir wall lamp Ref. 70992



Nala

70773 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	54



Post
486





Tamashi

71303 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17428
Class	I
IP	65





Pomo

71306 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17426
Class	I
IP	65
IK	06







Pivot

71304 Matt White/Blanco Mate
71305 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 10W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	06

Driver ✔



PRICES



Nala wall lamp Ref. 70773



Sun

70823 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 4.4W 3000K 275lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver







Tom 190

70665 Matt White/Blanco Mate

70666 Dark Grey/Gris Oscuro

Material	**Body** ABS
	Diff Opal PC/PC Opal
Light Source	SMD LED 7W 3000K 400lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	10

SEA SIDE SUITABLE Driver







Tom 220

70682 Dark Grey/Gris Oscuro

70683 Matt White/Blanco Mate

Material	**Body** ABS
	Diff Opal PC/PC Opal
Light Source	SMD LED 11W 3000K 600lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	10

SEA SIDE SUITABLE Driver



PRICES



Hikari

71274 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 10W 3000K 400lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	10

Driver ✔







Kubick

70689 Dark Grey/Gris Oscuro
70715 Grey/Gris

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44





Lur

70827 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 12W 3000K 950lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver ✔



PRICES



Mol

70720 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44





Pol

70829 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 8W 3000K 550lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver ✔





Fred 200

70663 Dark Grey/Gris Oscuro
70664 Matt White/Blanco Mate

Material	**Body** ABS
	Diff Opal PC/PC Opal
Light Source	SMD LED 7W 3000K 400lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	10

SEA SIDE SUITABLE Driver ✔







Fred 245

70667 Dark Grey/Gris Oscuro
70668 Matt White/Blanco Mate

Material	**Body** ABS
	Diff Opal PC/PC Opal
Light Source	SMD LED 11W 3000K 600lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	10

SEA SIDE SUITABLE Driver ✔



PRICES



Natron

70887 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	54
IK	06







Tejo

70573 Dark Grey/Gris Oscuro

70573B Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	54
IK	06





Negus

70696 Grey/Gris

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	54
IK	10





Bonn

70697 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



PRICES



Cela

72280 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 304/Acero inoxidable 304
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	54





Cela stripped

72281 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 304/Acero inoxidable 304
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	54





Fedon

70714 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 304/Acero inoxidable 304
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	54



PRICES





Estay

72010 Matt White/Blanco Mate
72011 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44







Derby 200

72000 Matt White/Blanco Mate
72001 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44





Derby 283

72002 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



PRICES





Bu-Oh by Estudi Ribaudí

71212	Dark Grey/Gris Oscuro
71215	Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 12W 3000K 310lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔



Bollard
492



Pole
518







Lotus by Estudi Ribaudí

71222	Matt White/Blanco Mate
71223	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 18W 3000K 1700lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08

Driver ✔



Bollard
466







Future by Estudi Ribaudí

71516	Matt White/Blanco Mate
71517	Dark Grey/Gris Oscuro

Material	**Body** PC
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	II
IP	44

SEA SIDE SUITABLE



PRICES



Lotus wall lamp Ref. 71223
designed by Estudi Ribaudí



Sticker by Lucid Product Design

75540 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 13W 3000K 770lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	55

Driver ✔



Bollard
470





View by Estudi Ribaudí

71519 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	II
IP	54

SEA SIDE SUITABLE





Dragma by Àlex & Manel Lluscà

71362L Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 15W 3000K 500lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65

Driver ✔





Ancora by Àlex & Manel Lluscà

74401 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



PRICES



Sticker wall lamp Ref. 75540
designed by Lucid Product Design



Alp 130

74450 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 8W 3000K 350lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver ✔







Axel

71272 Matt White/Blanco Mate

71273 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 6W 3000K 360lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	07

Driver ✔





Bracket

72272 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 6W 3000K 270lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44

Driver ✔



PRICES



Quart

70579 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 30W 3000K 1200lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50Hz
IP	65

Driver ✔









Takua

71277 Dark Grey/Gris Oscuro
71308 Matt White/Blanco Mate
71309 Rust Brown/Marrón Oxido

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 10W 3000K 450lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	06

Driver ✔





Oval

71276 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 10W 3000K 450lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	06

Driver ✔



PRICES









Lako

71909	Matt White/Blanco Mate
71910	Dark Grey/Gris Oscuro
71911	Rust Brown/Marrón Oxido
71898	Teak/Teca + Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Prism Glass/Cristal Prismático
Light Source	SMD LED 8W 3000K 600lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Beam angle	90°

Driver ✔











Doro 220

71900	Matt White/Blanco Mate
71901	Dark Grey/Gris Oscuro
71902	Rust Brown/Marrón Oxido
71899	Teak/Teca + Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Prism Glass/Cristal Prismático
Light Source	SMD LED 2W 3000K 1000lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65

Driver ✔









Doro 380

71903	Matt White/Blanco Mate
71904	Dark Grey/Gris Oscuro
71905	Rust Brown/Marrón Oxido

Material	**Body** Aluminium/Aluminio
	Diff Prism Glass/Cristal Prismático
Light Source	SMD LED 20W 3000K 1800lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65

Driver ✔



PRICES







Doro 500

71906	Matt White/Blanco Mate
71907	Dark Grey/Gris Oscuro
71908	Rust Brown/Marrón Oxido

Material	**Body** Aluminium/Aluminio
	Diff Prism Glass/Cristal Prismático
Light Source	SMD LED 28W 3000K 2700lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65

Driver ✔





Toluca

71052	Satin Aluminium/Aluminio Satinado

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 16W 3000K 900lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	09

Driver ✔





Tacana

71049	Satin Aluminium/Aluminio Satinado

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 24W 3000K 1700lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	09

Driver ✔



PRICES







Tond 1L

71915 2700K — Dark Grey/Gris Oscuro
71916 3000K — Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 6W 195lm
CRI	>=80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54
IK	06
Beam angle	50°

Driver ✔









Tond 2L

71917 2700K — Dark Grey/Gris Oscuro
71918 3000K — Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 2x6W 542lm
CRI	>=80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54
IK	06
Beam angle	50°

Driver ✔





Thon 1L

70283 — Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 15W 3000K 825lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	55
Beam angle	18°

Driver ✔





Thon 2L

70284 — Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 30W 3000K 1538lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	55
Beam angle	18°

Driver ✔



PRICES



Tond wall lamp Ref. 71918



Kaula 100

70405 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 9W 3000K 800lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44

Driver ✔





Kaula 180

70406 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Opal PMMA/PMMA Opal
Light Source	SMD LED 16W 3000K 650lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44

Driver ✔







Aday 113

70644 Matt White/Blanco Mate

70645 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 6W 3000K 450lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54
IK	08

Driver ✔







Aday 175

70646 Matt White/Blanco Mate

70647 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 13W 3000K 787lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54
IK	08

Driver ✔



PRICES



Aday wall lamp Ref. 70647



Tane

72269 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 7W 3000K 280lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔





West 1

70888 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	54





West 2

70899 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17437
Class	I
IP	54



PRICES



Lace

70811 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 2x3W 4000K 315lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
Beam angle	110°

Driver ✔





Bruc

70828 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 13W 3000K 830lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
IK	06

Driver ✔







Ling

70812 Dark Grey/Gris Oscuro
70813 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 2x3W 4000K 630lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
Beam angle	110°

Driver ✔



PRICES



Lacre

70802 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	54





Log

70264 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 9W 3000K 600lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54

Driver ✔









Blind

70267 Matt White/Blanco Mate
70268 Rust Brown/Marrón Oxido
70634 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 6W 3000K 180lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65

Driver ✔



PRICES







Olan

70269	Matt White/Blanco Mate
70270	Rust Brown/Marrón Oxido
70637	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 6W 3000K 200lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	06

Driver ✔







Sunset

70686	Matt White/Blanco Mate
70687	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 6W 3000K 260lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54

Driver ✔







Canon

70566N	Dark Grey/Gris Oscuro
70567N	Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 4W 3000K 130lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44
Beam angle	120°

Driver ✔



PRICES





Nairobi

70830 Matt White/Blanco Mate
70832 Rust Brown/Marrón Oxido

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 6W 3000K 380lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver ✔





Tinia

71353 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44





Ele

74419 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 6W 3000K 450lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54
Beam angle	95°

Driver ✔



PRICES







Gina

71363	Dark Grey/Gris Oscuro
71366	Matt White/Blanco Mate
71367	Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	44



Bollard
500





Taima

71388	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 6W 3000K 310lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
Beam angle	180°

90° 90 Driver ✓





Wood

74455	Dark Grey/Gris Oscuro + Wood/Madera

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 11W 3000K 600lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
Beam angle	95°

90° Driver ✓



PRICES



Proa by Àlex & Manel Lluscà

74400 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	44







Steps 2L by Estudi Ribaudí

75500 Matt White/Blanco Mate

75501 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	44







Steps 4L by Estudi Ribaudí

75502 Matt White/Blanco Mate

75503 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	4 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	44



PRICES



Proa wall lamp Ref. 74400
designed by Àlex & Manel Lluscà



Klamp 1L by Àlex & Manel Lluscà

74407 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	44



Bollard
498





Klamp 2L by Àlex & Manel Lluscà

74408 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	2 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	44





Suma

70749 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	2 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44



PRICES



Klamp1 wall lamp Ref. 74407
designed by Àlex & Manel Lluscà







Pill

70824	Matt White/Blanco Mate
70825	Dark Grey/Gris Oscuro
70826	Rust Brown/Marrón Oxido

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 3,5W 3000K 110lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54

Driver





Drak

72330	Brass/Latón

Material	**Body** Aluminium/Aluminio
	Diff Transparent PMMA/PMMA Transparente
Light Source	SMD LED 4,5W 3000K 160lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44
IK	08

SEA SIDE SUITABLE Driver







Brow

70408	Matt White/Blanco Mate
70409	Dark Grey/Gris Oscuro

Material	**Body** PC
	Diff Opal PMMA/PMMA Opal
Light Source	COB LED 3W 3000K 100lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50Hz
IP	44

Driver



PRICES



Loth 1L

70285 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	COB LED 6W 3000K 165lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	67
IK	10

Driver ✔





Loth 2L

70286 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	COB LED 13W 3000K 235lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	67
IK	10

Driver ✔





Loth 4L

70287 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	COB LED 13W 3000K 400lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	67
IK	10

Driver ✔



PRICES



Keenan 1

70546 Matt Nickel/Níquel Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 1W 6500K 20lm
CRI	>80
Recom. Driver	98111020
Class	III
Voltage (V/Hz)	12V DC
IP	67
IK	08

SEA SIDE SUITABLE Driver





Keenan 2

70547 Matt Nickel/Níquel Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 1W 6500K 40lm
CRI	>80
Recom. Driver	98111020
Class	III
Voltage (V/Hz)	12V DC
IP	67
IK	08

SEA SIDE SUITABLE Driver





Keenan 4

70564 Matt Nickel/Níquel Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 1W 6500K 80lm
CRI	>80
Recom. Driver	98111020
Class	III
Voltage (V/Hz)	12V DC
IP	67
IK	08

SEA SIDE SUITABLE Driver



PRICES



Keenan surface Ref. 70564



Grant SQ

70655 Dark Grey/Gris Oscuro

Material	**Body** ABS
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 1W 3000K 65lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	10
Beam angle	120°

SEA SIDE SUITABLE Driver ✔





Grant R

70656 Dark Grey/Gris Oscuro

Material	**Body** ABS
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 1W 3000K 65lm
CRI	>80
Class	II
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	10
Beam angle	120°

SEA SIDE SUITABLE Driver ✔







Path

70501 Matt White/Blanco Mate

70508 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 9W 3000K 390lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	44

Driver ✔



PRICES





Grada 157

70906 Dark Grey/Gris Oscuro
70907 Rust Brown/Marrón Oxido

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 3W 3000K 86lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54

Driver ✔







Grada 250

70908 Dark Grey/Gris Oscuro
70909 Rust Brown/Marrón Oxido

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 6W 3000K 208lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54

Driver ✔







Grada 600

70910 Dark Grey/Gris Oscuro
70911 Rust Brown/Marrón Oxido

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	SMD LED 12W 3000K 443lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	54

Driver ✔



PRICES



Must 96

70657 Dark Grey/Gris Oscuro

Material	**Body** ABS
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 2W 3000K 80lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	10

SEA SIDE SUITABLE Driver





Must 158

70658 Dark Grey/Gris Oscuro

Material	**Body** ABS
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 3W 3000K 220lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	10

SEA SIDE SUITABLE Driver





Must 217

70659 Dark Grey/Gris Oscuro

Material	**Body** ABS
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 4W 3000K 240lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
IK	10

SEA SIDE SUITABLE Driver



PRICES



Must wall lamp Ref. 70567



outdoor exterior

Recessed Empotrables



Galo R

70265 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 3W 3000K 200lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
IK	05
Cut out	73x60

ASYMMETRIC ASIMÉTRICO Driver







Nase SQ

70395 Matt White/Blanco Mate

70398 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 3W 3000K 100lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
Beam angle	120°
Cut out	92x87

Driver







Nase RCT

70396 Matt White/Blanco Mate

70399 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 3W 3000K 100lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
Beam angle	120°
Cut out	132x90

ASYMMETRIC ASIMÉTRICO Driver



PRICES



*Drivers info pag. 818-819

Dang

70446 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Glass/Acero inoxidable 316L+Cristal **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 3W 3000K 80lm
CRI	>80
Recom. Driver	98324006
Class	III
Voltage (V/Hz)	24V DC/50-60Hz
IP	67
IK	05
Beam angle	40°
Cut out	ø88

SEA SIDE SUITABLE Driver





Uve

70397 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio **Diff** Transparent PC/PC Transparente
Light Source	SMD LED 2W 3000K 70lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
IK	08
Beam angle	120°
Cut out	ø78

Driver



PRICES



Frol

70135 Satin Nickel/Níquel Satinado

Material	**Body** Stainless steel 304/Acero inoxidable 304
	Diff Opal PC/PC Opal
Light Source	SMD LED 1W 3000K 55lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Cut out	92x92

Driver ✔





Gron

70134 Satin Nickel/Níquel Satinado

Material	**Body** Stainless steel 304/Acero inoxidable 304
	Diff Opal PC/PC Opal
Light Source	SMD LED 1W 3000K 70lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Cut out	105x66

Driver ✔







Stripe

72092	Dark Grey/Gris Oscuro
72093	Matt White/Blanco Mate
72094	Matt White/Blanco Mate
72095	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 5W 3000K 50lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
IK	07
Cut out	230x89

Driver ✔



PRICES





Liso

71490 Matt White/Blanco Mate
71491 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44
Cut out	230x89

Recessed box/*Caja de empotrar*
71482







Esca

71480 Matt White/Blanco Mate
71481 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal Glass/Cristal Opal
Light Source	1 E27 max. 15W
Bulb incl.	No
Recom. Bulb	17463
Class	I
IP	44
Cut out	230x89

Recessed box/*Caja de empotrar*
71482







Stripe grid

72094 Matt White/Blanco Mate
72095 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 5W 3000K 70lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	54
IK	07
Cut out	230x89x85

Driver ✔



PRICES





Dart SQ

70272 2700K	○	Matt White/Blanco Mate
70273 2700K	◐	Matt Black/Negro Mate
70272N NEW 3000K	○	Matt White/Blanco Mate
70273N NEW 3000K	◐	Matt Black/Negro Mate

Material	**Body** PC
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 2W 70lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Beam angle	100°
Cut out	ø68

Driver ✓ ✗



Choose required mounting accesory/Elija el accesorio de montaje necesario



Recessed box/*Caja de empotrar*

70276 ● Black/Negro



Surface box/*Caja de superficie*

70274 ○ White/Blanco
70275 ● Black/Negro





Dart RCT

70277 2700K	○	Matt White/Blanco Mate
70278 2700K	◐	Matt Black/Negro Mate
70277N NEW 3000K	○	Matt White/Blanco Mate
70278N NEW 3000K	◐	Matt Black/Negro Mate

Material	**Body** PC
	Diff Transparent Glass/Cristal Transparente
Light Source	COB LED 5W 275lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	65
Beam angle	100°
Cut out	160x68

Driver ✓ ✗



Choose required mounting accesory/Elija el accesorio de montaje necesario



Recessed box/*Caja de empotrar*

70281 ● Black/Negro



Surface box/*Caja de superficie*

70279 ○ White/Blanco
70280 ● Black/Negro

PRICES







Spark

70162 Dark Grey/Gris Oscuro
70163 Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 5W 3000K 230lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	10
Cut out	95x65

Driver





Racing

70403 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 1W 4000K 30lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
IK	08
Beam angle	45°
Cut out	ø76

ASYMMETRIC ASIMÉTRICO Driver





Carter

70402 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 1W 4000K 30lm
CRI	>80
Class	II
Voltage (V/Hz)	220V-240V/50-60Hz
IP	44
IK	08
Beam angle	45°
Cut out	ø76

ASYMMETRIC ASIMÉTRICO Driver



PRICES



Racing recessed Ref. 70403





Soun 105

70833	Dark Grey/Gris Oscuro
70834	Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 5W 3000K 280lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Beam angle	120°
Cut out	220x95

Driver







Soun 193

70900	Dark Grey/Gris Oscuro
70901	Matt White/Blanco Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 8W 3000K 630lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Beam angle	120°
Cut out	183x225

Driver







Nat

70271	Matt White/Blanco Mate
70638	Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Transparent PC/PC Transparente
Light Source	SMD LED 8W 3000K 330lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Cut out	215x65x70

ASYMMETRIC
ASIMÉTRICO
Driver



PRICES



Sedna SQ 90

70146 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 1W 3000K 30lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Beam angle	70°
Cut out	80x75

ASYMMETRIC ASIMÉTRICO Driver





Sedna RCT

70147 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 3W 3000K 90lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Beam angle	70°
Cut out	125x58

ASYMMETRIC ASIMÉTRICO Driver





Sedna SQ 140

70148 Dark Grey/Gris Oscuro

Material	**Body** Aluminium/Aluminio
	Diff Opal PC/PC Opal
Light Source	SMD LED 3W 3000K 90lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	65
IK	08
Beam angle	70°
Cut out	128x112

ASYMMETRIC ASIMÉTRICO Driver



PRICES





Grund 37

70726 Satin Stainless/Inoxidable Satinado
70730 Anodized Black/Negro Anodizado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	SMD LED 2W 3000K 152lm
CRI	>90
Recom. Driver	98310206E
Class	III
IP	67
IK	08
Beam angle	15°
Cut out	ø32

SEA SIDE SUITABLE Driver



*Drivers info pag. 818-819





Grund 80

70728 Satin Stainless/Inoxidable Satinado
70731 Anodized Black/Negro Anodizado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 7W 3000K 420lm
CRI	>90
Recom. Driver	98310620
Class	III
IP	67
IK	08
Beam angle	36°
Cut out	ø60

SEA SIDE SUITABLE Driver



*Drivers info pag. 818-819





Grund 92

70729 Satin Stainless/Inoxidable Satinado
70732 Anodized Black/Negro Anodizado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 13W 3000K 846lm
CRI	>90
Recom. Driver	98310620
Class	III
IP	67
IK	08
Beam angle	36°
Cut out	ø68

SEA SIDE SUITABLE Driver



*Drivers info pag. 818-819

PRICES



Grund recessed Ref. 70728





Grund 37

70733	Satin Aluminium/Aluminio Satinado
70735	Satin Black/Negro Satinado
Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	SMD LED 2W 2700K
CRI	>90
Recom. Driver	98310206E
Class	III
IP	67
IK	08
Beam angle	15°
Cut out	ø32

SEA SIDE SUITABLE Driver



*Drivers info pag. 818-819





Grund 80

70734	Satin Aluminium/Aluminio Satinado
70736	Satin Black/Negro Satinado
Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 7W 2700K
CRI	>90
Recom. Driver	98310620
Class	III
IP	67
IK	08
Beam angle	36°
Cut out	ø60

SEA SIDE SUITABLE Driver



*Drivers info pag. 818-819

PRICES



Crosby

70459N Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium+ABS/Acero inoxidable 316L+Aluminio+ABS **Diff** Opal Glass/Cristal Opal
Light Source	SMD LED 1W 3000K 13lm
CRI	>80
Class	I
Voltage (V/Hz)	120V-240V/50-60Hz
IP	67
IK	08
Beam angle	120°
Cut out	ø80

SEA SIDE SUITABLE Driver





Crosby 24V

70453 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium+ABS/Acero inoxidable 316L+Aluminio+ABS **Diff** Opal Glass/Cristal Opal
Light Source	SMD LED 2W 3000K 77lm
CRI	>80
Recom. Driver	98324006
Class	III
Voltage (V/Hz)	24V DC/50-60Hz
IP	67
IK	08
Beam angle	120°
Cut out	ø80

SEA SIDE SUITABLE Driver



*Drivers info pag. 818-819



Curtis

70462N Satin Stainless/Inoxidable Satinado

Material	**Body** Aluminium+ABS/Aluminio+ABS **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 2W 3000K 180lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
IK	08
Cut out	ø80

SEA SIDE SUITABLE ASYMMETRIC ASIMÉTRICO Driver



PRICES



*Drivers info pag. 818-819

Kane 1

70660 3000K — Satin Stainless/Inoxidable Satinado

70660W NEW 2700K — Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 3W 3000K 120lm
CRI	>80
Recom. Driver	98324006
Class	III
Voltage (V/Hz)	24V DC/50-60Hz
IP	67
IK	08
Beam angle	120°
Cut out	ø40

SEA SIDE SUITABLE

Driver





*Drivers info pag. 818-819

Kane 2

70661 3000K — Satin Stainless/Inoxidable Satinado

70661W NEW 2700K — Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 3W 3000K 120lm
CRI	>80
Recom. Driver	98324006
Class	III
Voltage (V/Hz)	24V DC/50-60Hz
IP	67
IK	08
Beam angle	120°
Cut out	ø40

SEA SIDE SUITABLE

Driver





*Drivers info pag. 818-819

Kane 3

70662 3000K — Satin Stainless/Inoxidable Satinado

70662W NEW 2700K — Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Opal Glass/Cristal Opal
Light Source	COB LED 3W 3000K 120lm
CRI	>80
Recom. Driver	98324006
Class	III
Voltage (V/Hz)	24V DC/50-60Hz
IP	67
IK	08
Beam angle	120°
Cut out	ø40

SEA SIDE SUITABLE

Driver



*Drivers info pag. 818-819

PRICES





Tras 2L Orientable

71701 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 4W 3000K 462lm
CRI	>=90
Class	III
Voltage (V/Hz)	24V DC
IP	67
IK	08
Beam angle	13°
Cut out	ø82

30º Driver





Recessed box/*Caja de empotrar*

71703





Tras 4L

71702 Matt Black/Negro Mate

Material	**Body** Aluminium/Aluminio
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 8W 3000K 924lm
CRI	>=90
Class	III
Voltage (V/Hz)	24V DC
IP	67
IK	09
Beam angle	13°
Cut out	ø82

Driver





Recessed box/*Caja de empotrar*

71703





Tras 12L

71716 13° Black/Negro
71717 40° Black/Negro

Material	**Body** Aluminium+ABS/Aluminio+ABS
	Diff Transparent Glass/Cristal Transparente
Light Source	SMD LED 25W 3000K 2580lm
CRI	>=90
Class	III
Voltage (V/Hz)	24V DC
IP	67
IK	10
Cut out	250x235

Driver





*Drivers info pag. 818-819

PRICES



Geiser 80 GU10

70304 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17324
Class	I
IP	67
IK	08
Cut out	ø116

SEA SIDE SUITABLE 40º





Geiser 80

70305 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 7W 3000K 400lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
IK	08
Beam angle	38°
Cut out	ø116

SEA SIDE SUITABLE Driver





Geiser 80 GU10

70310 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	97685327
Class	I
IP	67
IK	08
Cut out	ø120

SEA SIDE SUITABLE 25º 25º



PRICES



Geiser 130

70302 10° Satin Stainless/Inoxidable Satinado
70303 38° Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 7W 3000K 400lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	67
IK	08
Cut out	ø90

SEA SIDE SUITABLE 20º Driver





Geiser 180

70308 10° Satin Stainless/Inoxidable Satinado
70309 38° Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 15W 3000K 900lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
IK	08
Cut out	ø165

SEA SIDE SUITABLE 25º 25º Driver





Geiser 260

70306 10° Satin Stainless/Inoxidable Satinado
70307 38° Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 29W 3000K 1800lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
IK	08
Cut out	ø200

SEA SIDE SUITABLE 20º Driver



PRICES



Suria 120

70588 24° Satin Stainless/Inoxidable Satinado
70592N 60° Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 3W 3000K 175lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
IK	08
Cut out	ø100

SEA SIDE SUITABLE Driver





Suria 180

70589 24° Satin Stainless/Inoxidable Satinado
70593N 60° Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 12W 3000K 1280lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
IK	08
Cut out	ø165

SEA SIDE SUITABLE Driver





Suria 220

70586 24° Satin Stainless/Inoxidable Satinado
70587 60° Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 24W 3000K 1870lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
IK	08
Cut out	ø209

SEA SIDE SUITABLE Driver



PRICES



Led18 R

71496N 6000K — Satin Stainless/Inoxidable Satinado
71498N 3000K — Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Opal Glass/Cristal Opal
Light Source	SMD LED 3W 51lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	67
IK	08
Cut out	ø90

SEA SIDE SUITABLE Driver





Led18 SQ

71499N — Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Opal Glass/Cristal Opal
Light Source	SMD LED 3W 3000K 51.4lm
CRI	>80
Class	I
Voltage (V/Hz)	220V-240V/50-60Hz
IP	67
IK	08
Cut out	80x80

SEA SIDE SUITABLE Driver





Salt

70591 — Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 9W 3000K 500lm
CRI	>=90
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
IK	08
Beam angle	45°
Cut out	ø170

SEA SIDE SUITABLE ASYMMETRIC ASIMÉTRICO Driver



PRICES



Taro

70449 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	COB LED 7W 3000K 280lm
CRI	>80
Class	I
Voltage (V/Hz)	100V-240V/50-60Hz
IP	67
IK	08
Beam angle	30°
Cut out	ø90

SEA SIDE SUITABLE Driver





Tecno

71489N Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+Aluminium/Acero inoxidable 316L+Aluminio **Diff** Transparent Glass/Cristal Transparente
Light Source	1 GU10 max. 8W
Bulb incl.	No
Recom. Bulb	17324
Class	I
IP	67
IK	08
Cut out	ø100

SEA SIDE SUITABLE





Lio

71495 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel/Acero inoxidable **Diff** Opal Glass/Cristal Opal
Light Source	1 GX53 max. 6W
Bulb incl.	No
Recom. Bulb	17340
Class	I
IP	67
IK	10
Cut out	ø90

SEA SIDE SUITABLE





Edel

70455 Satin Stainless/Inoxidable Satinado

Material	**Body** Stainless steel 316L+ABS/Acero inoxidable 316L+ABS **Diff** Opal Glass/Cristal Opal
Light Source	SMD LED 18W 4000K 600lm
CRI	85
Class	III
Voltage (V/Hz)	24V DC/50-60Hz
IP	68
IK	08
Beam angle	25°
Cut out	ø156

SUBMERSIBLE SUMERGIBLE Driver



PRICES



Edel recessed Ref. 70455





Falls 290 Orientable

71730 Satin Stainless/Inoxidable Satinado

Light Source	SMD LED 8W 3000K 672lm
Beam angle	25°

Falls 290 Orientable

71731 Satin Stainless/Inoxidable Satinado

Light Source	SMD LED 8W 3000K 669lm
Beam angle	30x60°

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
CRI	>=90
Class	III
Voltage (V/Hz)	24V DC
IP	67
IK	09
Cut out	310x52

Driver



Falls 500 Orientable

71732 Satin Stainless/Inoxidable Satinado

Light Source	SMD LED 16W 3000K 1367lm
Beam angle	25°

Falls 500 Orientable

71733 Satin Stainless/Inoxidable Satinado

Light Source	SMD LED 16W 3000K 1413lm
Beam angle	30x60°

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
CRI	>=90
Class	III
Voltage (V/Hz)	24V DC
IP	67
IK	09
Cut out	520x53

Driver



PRICES





Falls 290

71734 Satin Stainless/Inoxidable Satinado

Light Source SMD LED 6W 2700K 190lm

Falls 290

71735 Satin Stainless/Inoxidable Satinado

Light Source SMD LED 6W 3000K 200lm

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Glass/Cristal
CRI	>=90
Class	III
Voltage (V/Hz)	24V DC
IP	67
IK	09
Cut out	310x52

Driver



Falls 500

71736 Satin Stainless/Inoxidable Satinado

Light Source SMD LED 12W 2700K 291lm

Falls 500

71737 Satin Stainless/Inoxidable Satinado

Light Source SMD LED 11W 3000K 316lm

Material	**Body** Stainless steel 316L/Acero inoxidable 316L
	Diff Glass/Cristal
CRI	>=90
Class	III
Voltage (V/Hz)	24V DC
IP	67
IK	09
Cut out	520x53

Driver



PRICES

fan
ventilación

Why a Fan?



The ceiling fan has become an essential element in the interior design of a space, providing style, functionality, efficiency and sustainability.

El ventilador de techo se ha convertido en un elemento imprescindible en el interiorismo de un espacio, aportando estilo, funcionalidad, eficiencia y sostenibilidad.





Healthy & environmental friendly
Saludable y sostenible

It improves the air quality and contributes to our well-being and health. It does not emit toxic gases dangerous to the environment.
Mejora la calidad del aire contribuyendo a nuestro bienestar y salud. No emite gases tóxicos.



Cost-effective
Eficiente

It ventilates and cool spaces with energy consumption 50% lower than other systems.
Ventila y refresca los espacios con un consumo energético un 50% más bajo que otros sistemas.



Summer and Winter use
Uso verano e invierno

The rotation of the blades creates a refreshing breeze in summer and eliminates air stratification in winter.
La rotación de las aspas crea una brisa refrescante en verano y elimina la estratificación del aire en invierno.



Best Choice

Over 40 years of experience in fan, we are your best choice.
Con más de 40 años de experiencia en la ventilación de techo, somos tu mejor elección.



Engine guaranteed for 15 years.

Motor con garantía de 15 años.



High performance.

Altas prestaciones.



Wide range. Over 80 designs.

Amplia gama. Más de 80 diseños.



DC motor. Better performance.

Motor DC. Un mejor rendimiento.

Smart fan connection guide
Guía conexión smart fan



Add a device.
In this case a ceiling fan.

Añade un dispositivo.
En este caso un ventilador de techo.



Enter your WIFI password.
Make sure you are connected to a 2.4 GHz network.

Introduce la contraseña de tu WIFI. Asegúrate de estar conectado a una red de 2.4 GHz.



Pair your fan.
Choose the option of new fan to make the connection.

Empareja tu ventilador.
Elige la opción de nuevo ventilador para realizar la conexión.



Configure the fan.
Select the mode you want to use your fan in.

Configura el ventilador.
Selecciona el modo en el que quieres usar tu ventilador.



Regulate the light on your fan.
You can modify the light emitted by your fan through the app.

Regula la luz de tu ventilador.
Podrás modificar la luz emitida por tu ventilador a través de la app.



Regulates fan speed.
You can modify the speed of your fan through the app.

Regula la velocidad del ventilador. Podrás modificar la velocidad de tu ventilador a través de la app.

Compatible con / Compatible with

GOOGLE ASSISTANT

SIRI

ALEXA


Smart
Fan
Download app
Descarga la app
WiZ
Available on the iPhone
App Store
ANDROID APP ON
Google play

Fan integration

in automation projects.

Compatible with:
Compatible con:

BACnet

KNX

LUTRON

CASAMBI

and other control systems with 0-10V/1-10V y otros sistemas de control con 0-10V/1-10V.



34162
Gateway 0-10V/1-10V fans
Pasarela 0-10V/1-10V fans

Integration gateway in automation systems for Faro WP fans by 0-10V / 1-10 V speed and light control.

Pasarela de integración en sistemas domóticos para ventiladores Faro WP por control 0-10V/1-10V en velocidad y luz.

up to 128 fans per gateway.
hasta 128 ventiladores por pasarela.



Size it to your space

Size is really important when selecting your ceiling fan. If a fan is too large, it can overwhelm the space. On the flip side, if the fan is too small, the airflow may be inadequate for that area.

El tamaño es realmente importante al seleccionar el ventilador de techo. Si un ventilador es demasiado grande, puede saturar el espacio. Por otro lado, si el ventilador es demasiado pequeño, el flujo de aire puede ser inadecuado para esa área.



XL

28 m2 o más/or more
300 SQ.FT or more



más/over ø165 CM.
over ø56 INCH.

L

17,6-28 m2
190-300 SQ.FT



ø 132-164CM.
ø50-54 INCH.

M

13-17,6 m2
140-190 SQ.FT



ø107-131 CM.
ø44-48 INCH.

S

13 m2 o menos/or less
140 SQ.FT or less



ø106 CM. o menos/or less
ø42 INCH. or less


TECHNOLOGY
SYSTEM

Custom Fans

We personalise and adapt fan functions to your project needs.
Personalizamos y adaptamos las funciones del ventilador a las necesidades de tu proyecto.



How you want to control your fan

Múltiples opciones de control



Our fans around the world

Adaptado a cualquier parte del mundo



We adapt fan speeds to your needs

Velocidad personalizada



We modify the memory of your fan

Memoria personalizada

Tell us your needs and we will make it happen
Dinos tus necesidades y lo hacemos realidad

Send your demand on / *envíanos tu petición a* **fanprojects@faro.es**

	S	M	L	XL	DC Motor	Smart Optional	IP44	Summer Winter	With light	Without light	LED	Optional	Control remote	Wall control	Chain	Ceiling mounted	Inclining roof
Alo (Light)			●					●	●		●		incl.				●
Alo			●					●		●			incl.				●
Aloha			●					●		●		●	incl.				●
Amelia (Light) NEW			●			●		●	●		●		incl.				●
Amelia NEW			●			●		●		●	●		incl.				●
Andros				●	●			●		●			incl.				●
Aoba				●				●		●			incl.				●
Attos				●	●	●		●	●		●		incl.				●
Barth			●		●			●	●		●		incl.				●
Cebu	●							●	●				incl.				●
Century				●	●			●	●		●		incl.				●
Chicago	●								●				incl.				●
Cies				●	●	●		●		●		●	incl.				●
Cocos			●		●	●		●	●		●		incl.				●
Cooper		●			●	●		●		●			incl.				
Cuba			●					●		●			optional		incl.	●	●
Decofan		●			●	●		●		●		●	incl.				
Easy	●							●	●				incl.			●	●
Eco Indus		●						●		●			optional	incl.			●
Eterfan		●			●	●		●		●		●	incl.				
Factory	●							●		●					incl.		●
Fraser		●			●	●		●	●		●		incl.				
Grid			●		●			●		●		●	incl.				
Gotland			●		●	●		●		●			incl.				●
Heywood S NEW	●					●		●		●			incl.				●
Heywood L NEW			●			●		●		●			incl.				●
Hvar	●				●	●		●	●		●		incl				●
Hydra			●		●			●	●			●	incl.				●
Ibiza			●					●		●			incl.				●
Icaria			●					●	●				incl.				●
Ice			●					●	●		●		incl.				●
Indus			●							●				incl.			
Islot			●		●	●		●		●			incl.				
Izaro			●		●	●		●	●		●		incl.				●
Just Fan S	●				●	●		●		●		●	incl.				●
Just Fan M		●			●	●		●		●		●	incl.				●
Just Fan XL				●	●	●		●		●		●	incl.				●
Kauai				●	●	●		●		●			incl.				●
Keiki	●							●		●				incl.			●
Khios XXL				●	●			●	●		●		incl.				
Komodo		●						●	●						incl.		●
Lama			●					●		●			incl.				
Lantau L			●		●	●		●		●			incl.				●
Lantau L (Light)			●		●	●		●	●		●		incl.				●
Lantau XL				●	●	●		●		●			incl.				●
Lantau XL (Light)				●	●	●		●	●		●		incl.				●
Lisboa	●							●	●				optional		incl.	●	●

	S	M	L	XL	DC Motor	Smart Optional	IP44	Summer Winter	With light	Without light	LED	Optional	Control remote	Wall control	Chain	Ceiling mounted	Inclining roof
Lombok			●					●	●				optional		incl.		●
Luzon			●							●			incl.				●
Mallorca			●					●		●			incl.				●
Malvinas			●		●			●		●				incl.			●
Manhattan				●	●			●	●		●		incl.				●
Mediterráneo	●								●						incl.		
Meno			●					●		●			incl.				●
Milos			●		●	●		●		●			incl.				●
Mini Eterfan		●			●	●		●		●		●	incl.				
Mini Icaria	●							●	●				incl.				●
Mini Indus	●									●				incl.			
Mini Lantau	●					●		●		●			incl.				●
Mini Mallorca	●							●		●			incl.				●
Mini Tube		●			●	●		●		●		●	incl.				
Mini Ufo	●							●	●				incl.				
Morea			●		●			●		●			incl.				●
Nassau		●			●	●		●		●			incl.				●
Nias			●		●			●		●			incl.			●	
Nuu			●		●	●		●		●			incl.				●
Nuu (Light)			●		●			●	●		●		incl.				●
Oboe	●							●		●							●
Palao	●							●	●				optional		incl.		●
Palk			●		●			●	●				incl.				●
Panay		●							●				incl.				●
Pemba			●		●			●		●		●	incl.				
Polaris			●		●	●		●	●		●		incl.				●
Polea			●		●	●		●		●			incl.				●
Poros			●		●	●		●	●		●		incl.				●
Punt		●			●	●			●		●		incl.				●
Samos			●		●	●		●		●			incl.				
Saona			●		●	●		●	●		●		incl.				●
Sioux			●		●	●	●	●		●			incl.				●
Siros			●		●	●		●		●			incl.				●
Rodas			●		●	●		●	●		●		incl.				●
Tabarca			●					●	●				incl.				●
Tilos				●	●			●	●				incl.				●
Tonic			●		●			●		●	●		incl.				●
Tonsay			●					●	●				incl.				
Tube		●				●		●		●		●	incl.				
Typhoon		●			●	●	●	●				●	incl.				●
Vanu				●				●	●				incl.			●	●
Vedra	●							●		●			optional	incl.			●
Vulcano			●					●	●		●		incl.				●
Winche		●			●	●	●	●				●	incl.				●
Yakarta		●						●		●			optional		incl.		●



Suitable for high ceilings
Ideal para techos altos



High airflow
Alto flujo de aire



Programmable from 1-4-8h
Programable de 1-4-8h



Light output. 1700lm 30w
Rendimiento lumínico.
1700lm 30w

KHIOS

PRICES

XXL SIZE | ø305 CM | > 28 M2 > 300 SQ.FT | DC MOTOR | SUMMER WINTER | REMOTE CONTROL



34250A
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate

Material Body	Steel/Acero	**Light**	SMD LED 32W 3000K 2200lm
Material Blades	Aluminium/Aluminio	**CRI**	>80
W	16-47-70-93-116-140	**Driver incl.**	Yes
RPM	38-56-64-70-74-77	**Diff**	PC
Airflow	m3 min		
V/Hz	220V-240V/50-60Hz		



A	A1
670/26.38"	630/24.8"
B	**C**
200/7.87"	300/11.81"
D	**E**
170/6.7"	240/9.45"
F	**G**
ø3050/120.1"	1400/55.12"





Suitable for high ceilings
Ideal para techos altos



Color temp. adjustable
Temp. de color regulable



High airflow
Alto flujo de aire

MANHATTAN

PRICES

ø244 CM | > 28 M2 > 300 SQ.FT | DC MOTOR | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33496
Body Satin Nickel/Níquel Satinado
Blades Satin Stainless/Inoxidable Satinado

Material Body	Steel/Acero	**Light**	SMD LED 20W 3000K
Material Blades	Aluminium/Aluminio	**Dimmable K**	2700 - 3300 - 4600K
W	15-20-25-30-35-56	**CRI**	>=90
RPM	50-55-60-65-70-78	**Driver incl.**	Yes
Airflow	269.12 m3 min	**Diff**	PC
V/Hz	220V-240V/50-60Hz		
Opt. downrod	Page 810		



A	A1
360/14.17"	325/12.8"
B	**C**
200/7.87"	130/5.12"
D	**E**
55/2.2"	130/5.12"
F	**G**
ø2440/96.1"	1160/45.67"



2 downrods incl. 4.9” / 9.8”
2 tijas incl. 125mm / 250mm



Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h



Natural wood
Madera natural

KAUAI

PRICES

ø240 CM | > 28 M2 > 300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



34200A
34200WPA *Smart Fan
Body Dark Brown/Marrón Oscuro
Blades Pine/Pino

Material Body	Steel/Acero
Material Blades	Wood/Madera
W	13.4-17-20.7-35.7-54.5
RPM	79-86-93-110-126
Airflow	254.85 m3 min
V/Hz	220V-240V/50-60Hz
Downrods	125-250mm



A	A1
480/18.9"	430/16.93"
B	**C**
170/6.69"	210/8.27"
D	**E**
65/2.6"	150/5.91"
F	**G**
ø2400/94.5"	1000/39.37"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-12 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-12 del receptor. El precio del receptor es con el descuento PRO35.





Suitable for high ceilings
Ideal para techos altos



Color temp. adjustable
Temp. de color regulable



Smart option
Opción inteligente

ATTOS

PRICES

ø213 CM | > 28 M2 > 300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33494
33494WP *Smart Fan
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate



33495
33495WP *Smart Fan
Body Dark Brown/Marrón Oscuro
Blades Dark Brown/Marrón Oscuro

Material Body	Steel/Acero
Material Blades	ABS
W	5-7-12-18-28-44
RPM	30-44-58-72-86-103
Airflow	155.81 m3 min
V/Hz	220V-240V/50-60Hz
Opt. downrod	Page 810

Light	SMD LED 18W 3000K 1200lm
Dimmable K	2700K/1000lm - 3300/1100lm - 4600K/1200lm
CRI	>=90
Driver incl.	Yes
Diff	PC



A	A1
340/13.39"	210/8.27"
B	**C**
120/4.72"	130/5.12"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø2130/83.9"	1020/40.16"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34151-28 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34151-28 del receptor. El precio del receptor es con el descuento PRO35.





Suitable for high ceilings
Ideal para techos altos



3 opt heights. 48" / 35" / 23"
3 opciones alturas 1220mm / 900mm / 600mm



High airflow
Alto flujo de aire

ANDROS

PRICES

ø213 CM | > 28 M2 > 300 SQ.FT | DC MOTOR | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33461A
Body White/Blanco
Blades White/Blanco



33462A
Body Brown/Marrón
Blades Brown/Marrón



33465A
Body Satin Nickel/Níquel Satinado
Blades Satin Nickel/Níquel Satinado

NEW



33414A NEW
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate

Optional downrod/Tijas opcionales ⊗







34002	1220/48”	Satin Nickel Níquel Satinado	**34001**	900/35.4”	Satin Nickel Níquel Satinado	**34000**	600/23.6”	Satin Nickel Níquel Satinado
34008	1220/48”	Dark Brown Marrón Oscuro	**34007**	900/35.4”	Dark Brown Marrón Oscuro	**34006**	600/23.6”	Dark Brown Marrón Oscuro
34011	1220/48”	Matt White Blanco Mate	**34010**	900/35.4”	Matt White Blanco Mate	**34009**	600/23.6”	Matt White Blanco Mate
34014	1220/48”	Matt Black Negro Mate	**34013**	900/35.4”	Matt Black Negro Mate	**34012**	600/23.6”	Matt Black Negro Mate

Material Body	Steel/Acero
Material Blades	Aluminium/Aluminio
W	4-6-10-15-22-35
RPM	30-41-53-64-74-88
Airflow	406.4 m3 min
V/Hz	220V-240V/50-60Hz
Downrods	600-900-1220mm
Opt. downrod	Page 810



A	A1
460/18.11”	425/16.73”
B	**C**
220/8.66”	240/9.45”
D	**E**
50/2”	150/5.91”
F	**G**
ø2130/83.9”	950/37.4”





Adjustable intensity
Intensidad regulable



Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h



High airflow
Alto flujo de aire

CIES

PRICES

ø210 CM | > 28 M2 > 300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



33512A
33512WPA *Smart Fan
Body Shiny White/Blanco Brillo
Blades Shiny White/Blanco Brillo



with light/con luz

SMD LED 15W 3000K 900lm >80 **Driver incl.** Yes
Diff ABS

33512WPA-1 *Smart Fan
33512A-1
Body Shiny White/Blanco Brillo
Blades Shiny White/Blanco Brillo

Material Body	Steel/Acero
Material Blades	ABS
W	6-9-15-28-44
RPM	54-67-79-98-112
Airflow	344.4 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
430/16.93"	380/14.96"
B	**C**
250/9.84"	230/9.06"
D	**E**
50/2"	148/5.83"
F	**G**
ø2108/83"	930/36.61"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34151-27 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34151-27 del receptor. El precio del receptor es con el descuento PRO35.





3 downrods incl. 8" / 12"/ 20"
3 tijas incl. 203mm / 305mm / 510mm



Wood
Madera

AOBA

PRICES

ø180 CM

> 28 M2
> 300 SQ.FT

REMOTE CONTROL



33349
Body Matt Black/Negro Mate
Blades Reddish Walnut/Nogal Rojizo

Material Body	Steel/Acero
Material Blades	Wood/Madera
W	30-70-88
RPM	74-125-152
Airflow	120 m3 min
V/Hz	220V-240V/50-60Hz
Accesories ⊗	33928 Wall Control 3 speeds
	33929 Remote Control/dimer-on-off
	33937 Remote Control/Programmer
Downrods	203-305-510mm



A	A1
520/20.47"	410/16.14"
B	**C**
200/7.87"	230/9.06"
D	**E**
145/5.7"	160/6.3"
F	**G**
ø1800/70.9"	780/30.71"



Smart option
Opción inteligente



3 downrods incl. 3.9” / 7.8”/ 17.7”
3 tijas incl. 101mm / 203mm / 457mm

JUSTFAN

— Conillas

PRICES

ø178 CM | > 28 M2 > 300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33430
33430WP ***Smart Fan***
Body Matt Black/Negro Mate
Blades Dark Walnut/Nogal Oscuro



33432
33432WP ***Smart Fan***
Body Matt Black/Negro Mate
Blades Black/Negro



ø1280
773



ø810
805

Material Body	Steel/Acero
Material Blades	ABS
W	4-6-9-12-17-31
RPM	48-64-82-98-114-145
Airflow	175.28 m3 min
V/Hz	220V-240V/50-60Hz
Downrods	101-203-457mm



A	A1
640/25.2"	630/24.8"
B	**C**
180/7.09"	130/5.12"
D	**E**
55/2.2"	130/5.12"
F	**G**
ø1780/70.1"	890/35.04"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-01 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-01 del receptor. El precio del receptor es con el descuento PRO35.





High airflow
Alto flujo de aire



Wood
Madera

LANTAU

PRICES

ø168 CM | > 28 M2 > 300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33464DC *DC Motor*
33464DCWP NEW **Smart Fan*
Body Satin Nickel/Níquel Satinado
Blades Dark Walnut/Nogal Oscuro



33504DC *DC Motor*
33504DCWP NEW **Smart Fan*
Body Matt Nickel/Níquel Mate
Blades Pine/Pino



with light/con luz

SMD LED 15W 3000K 900lm >80 **Driver incl.** Yes
Diff Glass/Cristal

33463
Body Satin Nickel/Níquel Satinado
Blades Dark Walnut/Nogal Oscuro

33505DC *DC Motor*
33505DCWP NEW **Smart Fan*
Body Matt Nickel/Níquel Mate
Blades Pine/Pino



ø1320
741



ø1070
795

Material Body	Steel/Acero
Material Blades	Wood/Madera
W	6-9-11-17-24-35
RPM	75-89-98-115-129-146
Airflow	261.6 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33974 DC Wall Control
Opt. downrod	Page 810



A	A1
410/16.14"	335/13.19"
B	**C**
180/7.09"	
D	**E**
70/2.8"	150/5.91"
F	**G**
ø1680/66.1"	840/33.07"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-36 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-36 del receptor. El precio del receptor es con el descuento PRO35.



Suitable for high cellings
Apto ideal para techos altos



3 optional downrod
Opcional 3 tjas

TILOS

PRICES

ø168 CM | > 28 M2 > 300 SQ.FT | DC MOTOR | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33466A
Body Dark Brown/Marrón Oscuro
Blades Dark Brown/Marrón Oscuro

Optional downrod/Tijas opcionales ⊗



34005 1220/48” Dark Brown Marrón Oscuro



34004 900/35.4” Dark Brown Marrón Oscuro



34003 600/23.6” Dark Brown Marrón Oscuro

Material Body	Steel/Acero
Material Blades	ABS
W	4-6-9-14-21-35
RPM	31-43-55-67-78-95
Airflow	264.05 m3 min
V/Hz	220V-240V/50-60Hz
Opt. downrod	Page 810

Light	2 E27 max. 15W
Bulb incl.	No
Rec. Bulb	17463
Diff	Glass/Cristal



A	A1
500/19.69”	440/17.32”
B	**C**
290/11.42”	220/8.66”
D	**E**
60/2.4”	140/5.51”
F	**G**
ø1685/66.3”	750/29.53”



Adjustable intensity
Intensidad regulable



Smart option
Opción inteligente

CENTURY

PRICES

ø165 CM | > 28 M2 > 300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33553A
33553WPA *Smart Fan*
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate



33554A
33554WPA *Smart Fan*
Body Satin Nickel/Níquel Satinado
Blades Grey/Gris

Material Body	Steel/Acero	**Light**	SMD LED 15W 3000K 1200lm
Material Blades	Plywood	**CRI**	>80
W	5-8-12-17-25-35	**Driver incl.**	Yes
RPM	60-80-95-110-125-140	**Diff**	PMMA
Airflow	233.41 m3 min		
V/Hz	220V-240V/50-60Hz		
Opt. downrod	Page 810		



A	A1
330/12.99"	250/9.84"
B	**C**
170/6.69"	150/5.91"
D	**E**
50/2"	130/5.12"
F	**G**
ø1650/65"	750/29.53"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-10 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-10 del receptor. El precio del receptor es con el descuento PRO35.

Thanks to Beti Guasch y Estudi Nou Arquitectes photo by Sara Adroer



Wood
Madera

ALO

PRICES

ø152 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33718
Body Matt Black/Negro Mate
Blades Pine/Pino



33728
Body Matt White/Blanco Mate
Blades Pine/Pino



with light/con luz

SMD LED 17W 3000K 600lm >80 **Driver incl.** Yes
Diff Glass/Cristal

33719
Body Matt Black/Negro Mate
Blades Pine/Pino

33727
Body Matt White/Blanco Mate
Blades Pine/Pino

Material Body	Steel/Acero
Material Blades	Wood/Madera
W	14-30-56
RPM	80-113-155
Airflow	129.29 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33928 Wall Control 3 speeds
	33929 Remote Control/dimer-on-off
	33937 Remote Control/Programmer
Opt. downrod	Page 810



A	A1
335/13.19"	320/12.6"
B	**C**
180/7.09"	160/6.3"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1520/59.8"	760/29.92"





Smart option
Opción inteligente



Glass diffuser
Difusor de cristal



Light performance 2000lm
Rendimiento lumínico 2000lm

VULCANO

PRICES

ø152 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33549
33549WP ***Smart Fan***
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero	**Light**	SMD LED 21W 3000K 2000lm
Material Blades	ABS	**CRI**	>80
W	5-8-10.5-14.7-16.9-21.4	**Driver incl.**	Yes
RPM	80-108-126-149-161-180	**Diff**	Glass/Cristal
Airflow	177.88 m3 min		
V/Hz	220V-240V/50-60Hz		
Opt. downrod	Page 810		



A	A1
330/12.99"	250/9.84"
B	**C**
123/4.84"	284/11.18"
D	**E**
55/2.2"	139/5.47"
F	**G**
ø1524/60"	645/25.39"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-20 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-20 del receptor. El precio del receptor es con el descuento PRO35.



Accessory cap
Tapa accesorio



Adjustable intensity
Intensidad regulable



Smart option
Opción inteligente

TONIC

PRICES

ø152 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33552
33552WP ***Smart Fan***
Body Dark Brown/Marrón Oscuro
Blades Dark Brown/Marrón Oscuro



33551
33551WP ***Smart Fan***
Body White/Blanco
Blades White/Blanco

Material Body	Steel/Acero	**Light**	SMD LED 15W 3000K 1200lm
Material Blades	ABS	**CRI**	>80
W	5-7-9-11-14-18	**Driver incl.**	Yes
RPM	100-120-140-160-180-200	**Diff**	PC
Airflow	180.57 m3 min		
V/Hz	220V-240V/50-60Hz		
Opt. downrod	Page 810		



A	A1
310/12.2"	250/9.84"
B	**C**
190/7.48"	180/7.09"
D	**E**
50/2"	130/5.12"
F	**G**
ø1520/59.8"	670/26.38"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-17 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-17 del receptor. El precio del receptor es con el descuento PRO35.



Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h

MOREA

PRICES

ø152 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



33511
33511WP *Smart Fan
Body Dark Brown/Marrón Oscuro
Blades Dark Walnut/Nogal Oscuro



33519
33519WP *Smart Fan
Body Dark Brown/Marrón Oscuro
Blades Pine/Pino

Material Body	Steel/Acero
Material Blades	ABS
W	3-7-12-17-38
RPM	58-105-131-148-195
Airflow	211.7 m3 min
V/Hz	220V-240V/50-60Hz
Opt. downrod	Page 810



A	A1
280/11.02"	215/8.46"
B	**C**
130/5.12"	170/6.69"
D	**E**
50/2"	148/5.83"
F	**G**
ø1520/59.8"	750/29.53"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-05 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-05 del receptor. El precio del receptor es con el descuento PRO35.





High airflow
Alto flujo de aire

LAMA

PRICES

ø143 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | REMOTE CONTROL



33506
Body Satin Nickel/Níquel Satinado
Blades Pine/Pino



33507
Body Matt Black/Negro Mate
Blades Reddish Walnut/Nogal Rojizo

Material Body	Steel/Acero
Material Blades	Wood/Madera
W	16-27-44
RPM	84-114-143
Airflow	178.83 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33928 Wall Control 3 speeds
	33929 Remote Control/dimer-on-off
	33937 Remote Control/Programmer



A	A1
272/10.71"	220/8.66"
B	**C**
120/4.72"	180/7.09"
D	**E**
25/1"	190/7.48"
F	**G**
ø1430/56.3"	610/24.02"

INDUS

PRICES

ø140 CM

> 17,6-28 M2
190-300 SQ.FT

WALL CONTROL





33001
Body White/Blanco
Blades White/Blanco



33002
Body Shiny Chrome/Cromo Brillo
Blades Shiny Chrome/Cromo Brillo



ø1200
788

ø920
800

Material Body	Steel/Acero
Material Blades	Steel/Acero
W	16-21-26-32-48
RPM	113-142-173-203-260
Airflow	155.52 m3 min
V/Hz	220V-240V/50Hz



A	A1
483/19.02"	440/17.32"
B	**C**
160/6.3"	180/7.09"
D	**E**
120/4.7"	145/5.71"
F	**G**
ø1400/55.1"	555/21.85"

MALVINAS

PRICES

ø140 CM

> 17,6-28 M2
190-300 SQ.FT

SUMMER
WINTER

WALL
CONTROL

INCLINING
ROOF





33110
Body Dark Grey/Gris Oscuro
Blades Walnut/Nogal
+Reddish Mahogany/Caoba Rojizo



33111
Body Brown/Marrón
Blades Mahogany/Caoba
+Reddish Mahogany/Caoba Rojizo

Material Body	Steel/Acero
Material Blades	MDF
W	24-37-48-57-80
RPM	111-145-170-187-229
Airflow	176.22 m3 min
V/Hz	220V-240V/50Hz



A	A1
600/23.62"	500/19.69"
B	**C**
160/6.3"	200/7.87"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1400/55.1"	590/23.23"

COCOS

PRICES

ø137 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



Smart option
Opción inteligente



33548
33548WP ***Smart Fan***
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero	**Light**	SMD LED 20W 3000K 1600lm
Material Blades	ABS	**CRI**	>80
W	7-10-13-17-24-29	**Driver incl.**	Yes
RPM	66-88-104-115-138-146	**Diff**	PC
Airflow	234 m3 min		
V/Hz	230V/50-60Hz		
Opt. downrod	Page 810		



A	A1
260/10.24"	200/7.87"
B	**C**
90/3.54"	200/7.87"
D	**E**
55/2.2"	140/5.51"
F	**G**
ø1370/53.9"	585/23.03"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-11 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-11 del receptor. El precio del receptor es con el descuento PRO35.

HYDRA

PRICES

ø133 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF





33725
Body Matt Black/Negro Mate
Blades Dark Walnut/Nogal Oscuro



33726
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate



Programmable from 1-4-8h
Programable de 1-4-8h

Material Body	Steel/Acero
Material Blades	Plywood
W	5-7-10-13-18-25
RPM	99-116-134-154-172-193
Airflow	175.99 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33974 DC Wall Control
Opt. downrod	Page 810

Light	SMD LED 22W 3000K 1200lm
CRI	>80
Driver incl.	Yes
Diff	ABS



A	A1
340/13.39"	300/11.81"
B	**C**
130/5.12"	250/9.84"
D	**E**
70/2.8"	130/5.12"
F	**G**
ø1330/52.4"	540/21.26"



Smart option
Opción inteligente

NEW **HEYWOOD**

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



33809
33809WP *Smart Fan
Body Matt Black/Negro Mate
Blades Dark Oak/Roble Oscuro



33810
33810WP *Smart Fan
Body Matt White/Blanco Mate
Blades Maple/Arce

Material Body	Steel/Acero
Material Blades	Wood/Madera
W	5.7-7.1-11.7-17.4-22.9-30.6
RPM	68-92-115-133-145-158
Airflow	128 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
268/10.55"	223/8.78"
B	**C**
82/3.23"	100/3.94"
D	**E**
59/2.3"	132/5.2"
F	**G**
ø1320/52"	

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-33 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-33 del receptor. El precio del receptor es con el descuento PRO35.



Smart option
Opción inteligente

NEW **AMELIA**

— Héctor Serrano 

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



33760
33760WP *Smart Fan
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate



33761
33761WP *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate



33762
33762WP *Smart Fan
Body Grey/Gris
Blades Grey/Gris

Material Body	Steel/Acero
Material Blades	ABS
W	5-7-10-15-19-28
RPM	69-99-123-143-162-189
Airflow	153 m3 min
V/Hz	50/60Hz/50-60Hz
Downrods	200



A	A1
320/12.6"	270/10.63"
B	**C**
100/3.94"	123/4.84"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1320/52"	635/25"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34151-31 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34151-31 del receptor. El precio del receptor es con el descuento PRO35.



Smart option
Opción inteligente

NEW

AMELIA

— Héctor Serrano

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



33760-22
33760WP-22 *Smart Fan
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate



33761-23
33761WP-23 *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate



33762-24
33762WP-24 *Smart Fan
Body Grey/Gris
Blades Grey/Gris

Material Body	Steel/Acero
Material Blades	ABS
W	5-7-10-15-19-28
RPM	69-99-123-143-162-189
Airflow	153 m3 min
V/Hz	50/60Hz/50-60Hz
Downrods	200

Light	SMD LED 20W 965lm
Dimmable K	2700K/796lm -3500K/965lm -5000K/915lm
CRI	>80
Driver incl.	Yes
Diff	PC



A	A1
430/16.93"	270/10.63"
B	**C**
219/8.62"	123/4.84"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1320/52"	635/25"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34151-37 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34151-37 del receptor. El precio del receptor es con el descuento PRO35.



Smart option
Opción inteligente

NEW

AMELIA

— Héctor Serrano



PRICES

ø132 CM

> 17,6-28 M2
190-300 SQ.FT

DC MOTOR

OPTION
SMART
100-240V
50-60Hz

SUMMER
WINTER

WITH
PROGRAMMER

INCLINING
ROOF



33760-25
33760WP-25 *Smart Fan
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate



33761-26
33761WP-26 *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate



33762-27
33762WP-27 *Smart Fan
Body Grey/Gris
Blades Grey/Gris

Material Body	Steel/Acero	**Light**	SMD LED 20W 2700K 1056lm
Material Blades	ABS	**CRI**	>80
W	5-7-10-15-19-28	**Driver incl.**	Yes
RPM	69-99-123-143-162-189	**Diff**	Glass/Cristal
Airflow	153 m3 min		
V/Hz	50/60Hz/50-60Hz		
Downrods	200		



A	A1
510/20.08"	270/10.63"
B	**C**
297/11.69"	123/4.84"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1320/52"	635/25"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34151-31 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34151-31 del receptor. El precio del receptor es con el descuento PRO35.





Adjustable intensity
Intensidad regulable



Programmable from 1-4-8h
Programable de 1-4-8h

BARTH

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | DIM | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



34260
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate



34261
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate

Material Body	Steel/Acero
Material Blades	Plywood
W	4-6-9.5-14-25
RPM	95-130-165-195-235
Airflow	240 m3 min
V/Hz	220V-240V/50-60Hz

Light	SMD LED 24W 6000K 2400lm
Dimmable K	2700 - 4350 - 6000K
CRI	>80
Driver incl.	Yes
Diff	PP



A	A1
291/11.46"	220/8.66"
B	**C**
136/5.35"	
D	**E**
60/2.4"	150/5.91"
F	**G**
ø1320/52"	542/21.34"



Smart option
Opción inteligente



Small and aesthetic motor
Motor pequeño y estético

MILOS

PRICES

ø132 CM

> 17,6-28 M2
190-300 SQ.FT

DC MOTOR

OPTION
SMART
100-240V
50-60Hz

SUMMER
WINTER

REMOTE
CONTROL

INCLINING
ROOF



34100
34100WP ***Smart Fan***
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate

Material Body	Steel/Acero
Material Blades	Plywood
W	4-6-10-16-28-34
RPM	50-73-96-118-143-188
Airflow	116.1 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
270/10.63"	260/10.24"
B	**C**
120/4.72"	70/2.76"
D	**E**
60/2.4"	140/5.51"
F	**G**
ø1320/52"	600/23.62"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-06 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-06 del receptor. El precio del receptor es con el descuento PRO35.

MENO

PRICES

ø135 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



Programmable from 1-2-4-8h
Programable de 1-2-4-8h



33782
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	ABS
Material Blades	ABS
W	22-43-85
RPM	108-162-235
Airflow	192 m3 min
V/Hz	220V-240V/50-60Hz
Accesories ⊗	33928 Wall Control 3 speeds
	33929 Remote Control/dimer-on-off
	33937 Remote Control/Programmer
Opt. downrod	Page 810



A	A1
320/12.6”	275/10.83”
B	**C**
160/6.3”	260/10.24”
D	**E**
60/2.4”	150/5.91”
F	**G**
ø1350/53.1”	540/21.26”

GOTLAND

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF





33446
33446WP *Smart Fan
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate



33447
33447WP *Smart Fan
Body Black/Negro
Blades Walnut/Nogal



Programmable from 1-4-8h
Programable de 1-4-8h

Material Body	Steel/Acero
Material Blades	ABS
W	4-6-10-17-23-30
RPM	95-121-148-177-198-214
Airflow	218.9 m3 min
V/Hz	220V-240V/50-60Hz
Accesories ⊗	33974 DC Wall Control
Opt. downrod	Page 810



A	A1
250/9.84”	250/9.84”
B	**C**
130/5.12”	170/6.69”
D	**E**
55/2.2”	130/5.12”
F	**G**
ø1320/52”	580/22.83”

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-03 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-03 del receptor. El precio del receptor es con el descuento PRO35.

SIROS

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



Small and aesthetic motor
Motor pequeño y estético



Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h



33804
33804WP ***Smart Fan***
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero
Material Blades	ABS
W	6-12-19-25-38
RPM	85-108-129-150-180
Airflow	188 m3 min
V/Hz	220V-240V/50-60Hz
Opt. downrod	Page 810



A	A1
250/9.84"	280/11.02"
B	**C**
80/3.15"	204/8.03"
D	**E**
60/2.4"	150/5.91"
F	**G**
ø1320/52"	580/22.83"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-16 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-16 del receptor. El precio del receptor es con el descuento PRO35.

SAMOS

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER





Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h

33729
33729WP *Smart Fan*
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero
Material Blades	ABS
W	4-6-10-17-23-31
RPM	104-130-160-196-214-236
Airflow	116.14 m3 min
V/Hz	220V-240V/50-60Hz
Accesories ⊗	33974 DC Wall Control
Downrods	152-254mm
Opt. downrod	Page 810



A	A1
355/13.98"	300/11.81"
B	**C**
170/6.69"	165/6.5"
D	**E**
70/2.8"	130/5.12"
F	**G**
ø1320/52"	570/22.44"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-14 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-14 del receptor. El precio del receptor es con el descuento PRO35.

SAONA

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | DIM | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



Adjustable intensity
Intensidad regulable



Smart option
Opción inteligente



Programmable from 1-3-6h
Programable de 1-3-6h



33803
33803WP *Smart Fan*
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero	**Light**	SMD LED 36W 2475lm
Material Blades	ABS	**Dimmable K**	3000 - 4000 - 6000K
W	5-8-14-21-38	**CRI**	>80
RPM	85-105-126-155-180	**Driver incl.**	Yes
Airflow	188 m3 min	**Diff**	PC
V/Hz	220V-240V/50-60Hz		



A	A1
330/12.99”	250/9.84”
B	**C**
150/5.91”	330/12.99”
D	**E**
58/2.3”	150/5.91”
F	**G**
ø1320/52”	490/19.29”

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-15 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-15 del receptor. El precio del receptor es con el descuento PRO35.

ISLOT

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF





Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h

33802
33802WP ***Smart Fan***
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero
Material Blades	ABS
W	6-9-15-23-38
RPM	109-140-168-200-235
Airflow	185 m3 min
V/Hz	220V-240V/50-60Hz
Opt. downrod	Page 810



A	A1
280/11.02"	230/9.06"
B	**C**
100/3.94"	300/11.81"
D	**E**
70/2.8"	150/5.91"
F	**G**
ø1320/52"	520/20.47"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-23 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-23 del receptor. El precio del receptor es con el descuento PRO35.





Adjustable intensity
Intensidad regulable



Smart option
Opción inteligente



Programmable from 2-6h
Programable de 2-6h



Glass diffuser
Difusor de cristal

RODAS

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | DIM | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



33522
33522WP *Smart Fan
Body Matt White/Blanco Mate
Blades Pine/Pino
+White/Blanco





33523
33523WP *Smart Fan
Body Dark Brown/Marrón Oscuro
Blades Dark Brown/Marrón Oscuro
+Dark Oak/Roble Oscuro



Material Body	Steel/Acero	**Light**	SMD LED 20W 3000K 1200lm
Material Blades	Plywood	**Dimmable W**	5-20w
W	7-9-12-16-21-26	**CRI**	>=90
RPM	130-145-160-178-194-210	**Driver incl.**	Yes
Airflow	246 m3 min	**Diff**	Glass/Cristal
V/Hz	220V-240V/50-60Hz		
Accesories ⊗	33974 DC Wall Control		
Opt. downrod	Page 810		



A	A1
370/14.57"	250/9.84"
B	**C**
230/9.06"	310/12.2"
D	**E**
70/2.8"	160/6.3"
F	**G**
ø1320/52"	580/22.83"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34151-29 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34151-29 del receptor. El precio del receptor es con el descuento PRO35.



Adjustable intensity
Intensidad regulable



High airflow
Alto flujo de aire



Smart option
Opción inteligente



Programmable from 2-6h
Programable de 2-6h



Glass diffuser
Difusor de cristal

POROS

PRICES

ø132 CM

> 17,6-28 M2
190-300 SQ.FT

DC MOTOR

OPTION
SMART
100-240V
50-60Hz

DIM

SUMMER WINTER

WITH PROGRAMMER

INCLINING ROOF



33524
33524WP ***Smart Fan***
Body Matt White/Blanco Mate
Blades Pine/Pino

Material Body	Steel/Acero	**Light**	SMD LED 15W 2700K 900lm
Material Blades	Wood/Madera	**Dimmable W**	5-15w
W	7-9-12-15-20-26	**CRI**	>80
RPM	120-132-145-160-174-185	**Driver incl.**	Yes
Airflow	240 m3 min	**Diff**	Glass/Cristal
V/Hz	220V-240V/50-60Hz		
Accesories ⊗	33974 DC Wall Control		
Opt. downrod	Page 810		



A	A1
370/14.57”	280/11.02”
B	**C**
160/6.3”	180/7.09”
D	**E**
70/2.8”	160/6.3”
F	**G**
ø1320/52”	560/22.05”

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34151-26 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34151-26 del receptor. El precio del receptor es con el descuento PRO35.

Thanks to María Villalón Studio Photo by Alberto Monteagudo



LANTAU

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33370DC *DC Motor*
33370DCWP NEW **Smart Fan*
Body Satin Nickel/Níquel Satinado
Blades Dark Walnut/Nogal Oscuro



33373DC *DC Motor*
33373DCWP NEW **Smart Fan*
Body Satin Nickel/Níquel Satinado
Blades Pine/Pino



33516DC *DC Motor*
33516DCWP NEW **Smart Fan*
Body Matt Black/Negro Mate
Blades Dark Walnut/Nogal Oscuro



33561DC NEW *DC Motor*
33561DCWP NEW **Smart Fan*
Body Matt White/Blanco Mate
Blades Pine/Pino



33562DC NEW *DC Motor*
33562DCWP NEW **Smart Fan*
Body Brown/Marrón
Blades Pine/Pino



with light/con luz

SMD LED 15W 3000K 900lm >80 **Driver incl.** Yes
Diff Glass/Cristal

33518DC *DC Motor*
33518DCWP NEW **Smart Fan*
Body Satin Nickel/Níquel Satinado
Blades Dark Walnut/Nogal Oscuro

33560DC *DC Motor*
33560DCWP NEW **Smart Fan*
Body Satin Nickel/Níquel Satinado
Blades Pine/Pino



ø1680
699



ø1070
795

Material Body	Steel/Acero
Material Blades	Wood/Madera
W	5-8-12-17-27-35
RPM	82-102-125-145-170-188
Airflow	147.56 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33974 DC Wall Control
Opt. downrod	Page 810



A	A1
330/12.99"	320/12.6"
B	**C**
165/6.5"	160/6.3"
D	**E**
70/2.8"	160/6.3"
F	**G**
ø1320/52"	660/25.98"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-35 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-35 del receptor. El precio del receptor es con el descuento PRO35.





Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h



Minimal design
Diseño minimal

NUU

— Estudi Ribaudí 

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



33721
33721WP **Smart Fan*
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate



with light/con luz

SMD LED 15W 3000K 600lm >80 **Driver incl.** Yes
Diff PC

33722
33722WP **Smart Fan*
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero
Material Blades	ABS
W	5-8-11-14-21-35
RPM	106-126-147-165-186-212
Airflow	104.58 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
330/12.99"	290/11.42"
B	**C**
160/6.3"	110/4.33"
D	**E**
55/2.2"	130/5.12"
F	**G**
ø1320/52"	600/23.62"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-13 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-13 del receptor. El precio del receptor es con el descuento PRO35.



Music player bluetooth
Altavoz bluetooth



Aesthetic light kit
Kit de luz estético

ICE

— Estudi Ribaudí

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33460
Body White/Blanco
Blades White/Blanco
+Maple/Arce



Material Body	Steel/Acero
Material Blades	MDF
W	13-25-55
RPM	75-135-180
Airflow	157.52 m3 min
V/Hz	220V-240V/50Hz
Opt. downrod	Page 810

Light	SMD LED 15W 3000K 800lm
CRI	>80
Driver incl.	Yes
Diff	Glass/Cristal



A	A1
385/15.16"	270/10.63"
B	**C**
210/8.27"	230/9.06"
D	**E**
65/2.6"	150/5.91"
F	**G**
ø1320/52"	555/21.85"

POLEA

— Conillas

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h



33724
33724WP *Smart Fan*
Body Brown/Marrón
Blades Walnut/Nogal
+Black/Negro



Material Body	Steel/Acero
Material Blades	Plywood
W	5-7-10-14-20-33
RPM	86-102-119-131-151-167
Airflow	111.3 m3 min
V/Hz	220V-240V/50-60Hz
Opt. downrod	Page 810



A	A1
372/14.65"	254/10"
B	**C**
118/4.65"	228/8.98"
D	**E**
56/2.2"	130/5.12"
F	**G**
ø1322/52"	547/21.54"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-21 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-21 del receptor. El precio del receptor es con el descuento PRO35.

LUZON

PRICES

ø132 CM

> 17,6-28 M2
190-300 SQ.FT

REMOTE CONTROL

INCLINING ROOF





2 downrods incl. 4.13" / 5.98"
2 tijas incl. 105mm / 152mm

33750
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero
Material Blades	ABS
W	23-42-65
RPM	90-120-155
Airflow	215.73 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33928 Wall Control 3 speeds
	33929 Remote Control/dimer-on-off
	33937 Remote Control/Programmer
Downrods	105-152mm
Opt. downrod	Page 810



A	A1
285/11.22"	235/9.25"
B	**C**
180/7.09"	160/6.3"
D	**E**
60/2.4"	140/5.51"
F	**G**
ø1320/52"	590/23.23"

SIOUX

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | IP44 OUTDOOR | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



2 downrods incl. 5" / 10"
2 tijas incl. 127mm / 254mm



IP44 outdoor
IP44 exterior



Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h



33770
33770WP *Smart Fan*
Body White/Blanco
Blades White/Blanco

Material Body	Steel/Acero
Material Blades	ABS
W	5-10-16-23-38
RPM	106-143-174-198-233
Airflow	164.32 m3 min
V/Hz	220V-240V/50-60Hz
Downrods	127-254mm
Opt. downrod	Page 810



A	A1
320/12.6"	260/10.24"
B	**C**
200/7.87"	220/8.66"
D	**E**
70/2.8"	170/6.69"
F	**G**
ø1320/52"	590/23.23"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-22 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-22 del receptor. El precio del receptor es con el descuento PRO35.

POLARIS

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF





Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h

33346
33346WP ***Smart Fan***
Body White/Blanco
Blades White/Blanco

Material Body	Steel/Acero	**Light**	SMD LED 18W 3000K 1500lm
Material Blades	ABS	**CRI**	>80
W	4-9-16-23-35	**Driver incl.**	Yes
RPM	86-108-130-145-175	**Diff**	PC
Airflow	163 m3 min		
V/Hz	220V-240V/50-60Hz		
Opt. downrod	Page 810		



A	A1
350/13.78"	275/10.83"
B	**C**
180/7.09"	170/6.69"
D	**E**
50/2"	130/5.12"
F	**G**
ø1320/52"	555/21.85"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-07 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-07 del receptor. El precio del receptor es con el descuento PRO35.

PEMBA

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | SUMMER WINTER | REMOTE CONTROL





Direct to the ceiling
Directo al techo



Suitable for low ceilings
Ideal techos bajos

with light/con luz

Light	SMD LED 15W 3000K 800lm
CRI	>95
Driver incl.	Yes
Diff	PC



33471N-3
Body Shiny White/Blanco Brillo
Blades Shiny White/Blanco Brillo

33471N
Body Shiny White/Blanco Brillo
Blades Shiny White/Blanco Brillo

Material Body	Steel+ABS/Acero+ABS
Material Blades	ABS
W	3-5-9-14-21-32
RPM	50-76-102-127-157-180
Airflow	191.14 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
215/8.46”	
B	**C**
250/9.84”	180/7.09”
D	**E**
	170/6.69”
F	**G**
ø1320/52”	570/22.44”

PALK

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33470
Body Satin Nickel/Níquel Satinado
Blades Maple/Arce

Material Body	Steel/Acero	**Light**	2 E14 max. 8W
Material Blades	Plywood	**Bulb incl.**	No
W	3-5-8-13-21-32	**Rec. Bulb**	17461
RPM	50-77-104-131-158-185	**Diff**	Glass/Cristal
Airflow	198.22 m3 min		
V/Hz	220V-240V/50-60Hz		
Opt. downrod	Page 810		



A	A1
390/15.35”	325/12.8”
B	**C**
140/5.51”	150/5.91”
D	**E**
60/2.4”	130/5.12”
F	**G**
ø1320/52”	570/22.44”

NIAS

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | SUMMER WINTER | REMOTE CONTROL





33472N
Body Satin Nickel/Níquel Satinado
Blades Dark Walnut/Nogal Oscuro

with light/con luz

Light	SMD LED 15W 3000K 800lm
CRI	>=90
Driver incl.	Yes
Diff	PC



33472N-6
Body Satin Nickel/Níquel Satinado
Blades Dark Walnut/Nogal Oscuro

Material Body	Steel/Acero
Material Blades	Plywood
W	2-7-9-14-21-32
RPM	50-82-114-146-178-210
Airflow	195.39 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
190/7.48”	
B	**C**
155/6.1”	140/5.51”
D	**E**
	170/6.69”
F	**G**
ø1320/52”	630/24.8”

TONSAY

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | REMOTE CONTROL





33385
Body Satin Nickel/Níquel Satinado
Blades Grey/Gris
+Mahogany/Caoba



33386
Body Dark Brown/Marrón Oscuro
Blades Cedro
+Wengue/Wengué

Material Body	Steel/Acero	**Light**	2 E27 max. 15W
Material Blades	Plywood	**Bulb incl.**	No
W	10-24-46	**Rec. Bulb**	17463
RPM	83-132-180	**Diff**	Glass/Cristal
Airflow	145.63 m3 min		
V/Hz	220V-240V/50Hz		
Accesories ⊗	33928 Wall Control 3 speeds		
	33929 Remote Control/dimer-on-off		
	33937 Remote Control/Programmer		



A	A1
305/12.01"	
B	**C**
300/11.81"	238/9.37"
D	**E**
	190/7.48"
F	**G**
ø1320/52"	535/21.06"



ICARIA

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33700
Body White/Blanco
Blades White/Blanco
+Maple/Arce





33701
Body Satin Nickel/Níquel Satinado
Blades Grey/Gris
+Maple/Arce





33702
Body Brown/Marrón
Blades Bleached Oak/Roble Emblanquecido
+Mahogany/Caoba





33705
Body Old Gold/Oro Viejo
Blades Brown/Marrón
+Oak/Roble





ø1070
791

Material Body	Steel/Acero	**Light**	2 E27 max. 15W
Material Blades	MDF	**Bulb incl.**	No
W	15-30-56	**Rec. Bulb**	17463
RPM	100-150-205	**Diff**	Glass/Cristal
Airflow	155.62 m3 min		
V/Hz	220V-240V/50Hz		
Accesories ⊗	33928 Wall Control 3 speeds		
	33929 Remote Control/dimer-on-off		
	33937 Remote Control/Programmer		
Opt. downrod	Page 810		



A	A1
415/16.34"	330/12.99"
B	**C**
280/11.02"	270/10.63"
D	**E**
50/2"	150/5.91"
F	**G**
ø1320/52"	520/20.47"

IBIZA

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33284
Body White/Blanco
Blades White/Blanco

Material Body	Steel/Acero
Material Blades	Plywood
W	16-29-49
RPM	113-162-212
Airflow	149.57 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33928 Wall Control 3 speeds
	33929 Remote Control/dimer-on-off
	33937 Remote Control/Programmer
Opt. downrod	Page 810



A	A1
330/12.99"	270/10.63"
B	**C**
170/6.69"	175/6.89"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1320/52"	570/22.44"

MALLORCA

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF





33350
Body White/Blanco
Blades White/Blanco
+Maple/Arce



33351
Body Dark Brown/Marrón Oscuro
Blades Mahogany/Caoba
+Bleached Oak/Roble Emblanquecido



ø1070
793

Material Body	Steel/Acero
Material Blades	MDF
W	15-30-56
RPM	100-150-205
Airflow	154.3 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33928 Wall Control 3 speeds
	33929 Remote Control/dimer-on-off
	33937 Remote Control/Programmer
Opt. downrod	Page 810



A	A1
380/14.96"	330/12.99"
B	**C**
180/7.09"	250/9.84"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1320/52"	520/20.47"

LOMBOK

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | INCLINING ROOF | CONTROLLED BY CHAINS



Glass diffuser
Difusor de cristal



33019
Body Dark Brown/Marrón Oscuro
Blades Pine/Pino

Material Body	Steel/Acero	**Light**	2 E27 max. 15W
Material Blades	Wood/Madera	**Bulb incl.**	No
W	14-29-58	**Rec. Bulb**	17463
RPM	85-135-185	**Diff**	Glass/Cristal
Airflow	123.72 m3 min		
V/Hz	220V-240V/50Hz		
Accesories ⊗	33928 Wall Control 3 speeds		
	33929 Remote Control/dimer-on-off		
	33937 Remote Control/Programmer		
Opt. downrod	Page 810		



A	A1
500/19.69"	246/9.69"
B	**C**
330/12.99"	285/11.22"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1320/52"	541/21.3"

ALOHA

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF





33710
Body Dark Brown/Marrón Oscuro
Blades Walnut/Nogal
+Dark Walnut/Nogal Oscuro

with light/con luz

Light	3 E27 max. 15W
Bulb incl.	No
Rec. Bulb	17426
Diff	Glass/Cristal



33710-13
Body Dark Brown/Marrón Oscuro
Blades Walnut/Nogal

Material Body	Steel/Acero
Material Blades	Plywood
W	15-32-58
RPM	80-125-180
Airflow	128.95 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33928 Wall Control 3 speeds
	33929 Remote Control/dimer-on-off
	33937 Remote Control/Programmer
Opt. downrod	Page 810



A	A1
350/13.78”	285/11.22”
B	**C**
130/5.12”	240/9.45”
D	**E**
60/2.4”	130/5.12”
F	**G**
ø1320/52”	530/20.87”

CUBA

PRICES

ø132 CM | > 17,6-28 M2 190-300 SQ.FT | SUMMER WINTER | INCLINING ROOF | CONTROLLED BY CHAINS





33352
Body Dark Brown/Marrón Oscuro
Blades Dark Brown/Marrón Oscuro



33352B
Body Old Gold/Oro Viejo
Blades Brown/Marrón

Material Body	Steel/Acero
Material Blades	ABS
W	20-34-65
RPM	73-99-145
Airflow	127.45 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33928 Wall Control 3 speeds
	33929 Remote Control/dimer-on-off
	33937 Remote Control/Programmer
Opt. downrod	Page 810



A	A1
510/20.08"	450/17.72"
B	**C**
350/13.78"	370/14.57"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1320/52"	600/23.62"

IZARO

PRICES

ø130 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF





Glass diffuser
Difusor de cristal



Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h

33514
33514WP *Smart Fan*
Body Shiny White/Blanco Brillo
Blades White/Blanco
+Maple/Arce



Material Body	Steel/Acero	**Light**	SMD LED 15W 2700K 850lm
Material Blades	Plywood	**CRI**	>80
W	5-10-16-25-37	**Driver incl.**	Yes
RPM	100-142-165-192-226	**Diff**	Glass/Cristal
Airflow	190.12 m3 min		
V/Hz	220V-240V/50-60Hz		
Opt. downrod	Page 810		



A	A1
420/16.54"	270/10.63"
B	**C**
260/10.24"	230/9.06"
D	**E**
70/2.8"	150/5.91"
F	**G**
ø1300/51.2"	540/21.26"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34151-30 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34151-30 del receptor. El precio del receptor es con el descuento PRO35.





Smart option
Opción inteligente



Programmable from 2-6h
Programable de 2-6h

PUNT

PRICES | ø130 CM | > 17,6-28 M2 190-300 SQ.FT | DC MOTOR | DIM | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



33814
33814WP *Smart Fan
Body White/Blanco
Blades Matt White/Blanco Mate



33815
33815WP *Smart Fan
Body Black/Negro
Blades Matt Black/Negro Mate



33816
33816WP *Smart Fan
Body White/Blanco
Blades Maple/Arce



33817
33817WP *Smart Fan
Body Black/Negro
Blades Walnut/Nogal



with light/con luz

SMD LED 18W 3000-4000-6500K1300lm **Driver incl.** Yes
Diff Glass/Cristal

33814-20
33814WP-20 *Smart Fan
Body White/Blanco
Blades Matt White/Blanco Mate

33815-21
33815WP-21 *Smart Fan
Body Black/Negro
Blades Matt Black/Negro Mate

33816-20
33816WP-20 *Smart Fan
Body White/Blanco
Blades Maple/Arce

33817-21
33817WP-21 *Smart Fan
Body Black/Negro
Blades Walnut/Nogal

Material Body	Steel/Acero
Material Blades	ABS
W	9-12-16-21-30-33
RPM	100-118-132-152-168-176
Airflow	173 m3 min
V/Hz	220V-240V/50-60Hz
Opt. downrod	Page 810



A	A1
285/11.22"	275/10.83"
B	**C**
66/2.6"	150/5.91"
D	**E**
59/2.3"	132/5.2"
F	**G**
ø1300/51.2"	578/22.76"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-24 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-24 del receptor. El precio del receptor es con el descuento PRO35.



IP44 outdoor
IP44 exterior



Smart option
Opción inteligente

TYPHOON

— Jordi Busquets 

PRICES | ø130 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | IP44 OUTDOOR | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33480
33480WP *Smart Fan
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate



33489
33489WP *Smart Fan
Body Grey/Gris
Blades Grey/Gris



33490
33490WP *Smart Fan
Body Dark Brown/Marrón Oscuro
Blades Dark Brown/Marrón Oscuro



with light/con luz

SMD LED 19W 3000K 900lm >80 **Driver incl.** Yes
Diff ABS

33480-14
33480WP-14 *Smart Fan
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

33489-15
33489WP-15 *Smart Fan
Body Grey/Gris
Blades Grey/Gris

33490-16
33490WP-16 *Smart Fan
Body Dark Brown/Marrón Oscuro
Blades Dark Brown/Marrón Oscuro

Material Body	Steel/Acero
Material Blades	ABS
W	3-5-8-12-21-31
RPM	50-71-93-115-138-162
Airflow	183.09 m3 min
V/Hz	220V-240V/50-60Hz
Opt. downrod	Page 810



A	A1
390/15.35"	370/14.57"
B	**C**
200/7.87"	200/7.87"
D	**E**
55/2.2"	130/5.12"
F	**G**
ø1300/51.2"	530/20.87"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-18 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-18 del receptor. El precio del receptor es con el descuento PRO35.



Aesthetic motor
Motor estético



Smart option
Opción inteligente



3 downrods incl. 3.9" / 7.8"/ 17.7"
3 tijas incl. 100mm / 200mm / 450mm

COPPER

— Conillas

PRICES

ø128 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33451
33451WP ***Smart Fan***
Body Matt Black/Negro Mate
Blades Walnut/Nogal

Material Body	Steel/Acero
Material Blades	PC
W	4-6-9-13-22-32
RPM	51-77-103-129-155-185
Airflow	145.66 m3 min
V/Hz	220V-240V/50-60Hz
Downrods	100-200-450mm



A	A1
640/25.2"	630/24.8"
B	**C**
180/7.09"	160/6.3"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1280/50.4"	555/21.85"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150 del receptor. El precio del receptor es con el descuento PRO35.





Additional kit
Kit adicional



Smart option
Opción inteligente

MINI ETERFAN

— Conillas

PRICES

ø128 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL



33382
33382WP *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente



32020
32020WP *Smart Fan
Body Shiny White/Blanco Brillo
Blades Transparent/Transparente



32025
32025WP *Smart Fan
Body Matt White/Blanco Mate
Blades Transparent/Transparente



32026
32026WP *Smart Fan
Body Shiny Black/Negro Brillo
Blades Transparent/Transparente



32027
32027WP *Smart Fan
Body Matt Black/Negro Mate
Blades Transparent/Transparente



32028
32028WP *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal



32029
32029WP *Smart Fan
Body Shiny Red/Rojo Brillo
Blades Transparent/Transparente



32030
32030WP *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate



with light/con luz

SMD LED 16W 3000K 709lm >80 **Driver incl.** Yes
Diff Glass/Cristal

33382-9
33382WP-9 *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente

32020-9
32020WP-9 *Smart Fan
Body Shiny White/Blanco Brillo
Blades Transparent/Transparente

32025-9
32025WP-9 *Smart Fan
Body Matt White/Blanco Mate
Blades Transparent/Transparente

32026-10
32026WP-10 *Smart Fan
Body Shiny Black/Negro Brillo
Blades Transparent/Transparente

32027-10
32027WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Transparent/Transparente

32028-10
32028WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal

32029-9
32029WP-9 *Smart Fan
Body Shiny Red/Rojo Brillo
Blades Transparent/Transparente

32030-10
32030WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate

Material Body	Steel+Glass/Acero+Cristal
Material Blades	PC
W	3-6-9-13-22-32
RPM	51-77-103-129-155-185
Airflow	145.66 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
450/17.72"	420/16.54"
B	**C**
420/16.54"	160/6.3"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1280/50.4"	555/21.85"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150 del receptor. El precio del receptor es con el descuento PRO35.



Additional kit
Kit adicional



Smart option
Opción inteligente

ETERFAN

— Conillas

PRICES

ø128 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL



33381
33381WP *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente



32000WP *Smart Fan
32000
Body Shiny White/Blanco Brillo
Blades Transparent/Transparente



32001
32001WP *Smart Fan
Body Matt White/Blanco Mate
Blades Transparent/Transparente



32002
32002WP *Smart Fan
Body Shiny Black/Negro Brillo
Blades Transparent/Transparente



32003
32003WP *Smart Fan
Body Matt Black/Negro Mate
Blades Transparent/Transparente



32004
32004WP *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal



32005
32005WP *Smart Fan
Body Shiny Red/Rojo Brillo
Blades Transparent/Transparente



32006
32006WP *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate



with light/con luz

SMD LED 16W 3000K 709lm >80 **Driver incl.** Yes
Diff Glass/Cristal

33381-9
33381WP-9 *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente

32000-9
32000WP-9 *Smart Fan
Body Shiny White/Blanco Brillo
Blades Transparent/Transparente

32001-9
32001WP-9 *Smart Fan
Body Matt White/Blanco Mate
Blades Transparent/Transparente

32002-10
32002WP-10 *Smart Fan
Body Shiny Black/Negro Brillo
Blades Transparent/Transparente

32003-10
32003WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Transparent/Transparente

32004-10
32004WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal

32005-9
32005WP-9 *Smart Fan
Body Shiny Red/Rojo Brillo
Blades Transparent/Transparente

32006-10
32006WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate

Material Body	Steel+Glass/Acero+Cristal
Material Blades	PC
W	3-6-9-13-22-32
RPM	51-77-103-129-155-185
Airflow	145.66 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
640/25.2"	760/29.92"
B	**C**
630/24.8"	160/6.3"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1280/50.4"	555/21.85"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150 del receptor. El precio del receptor es con el descuento PRO35.



Smart option
Opción inteligente



Additional kit
Kit adicional



3 downrods incl. 3.9" / 7.8"/ 17.7"
3 tijas incl. 100mm / 200mm / 450mm

JUSTFAN

— Conillas

PRICES

ø128 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33394
33394WP *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente



33395
33395WP *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal



33398
33398WP *Smart Fan
Body Old Gold/Oro Viejo
Blades Walnut/Nogal



33399
33399WP *Smart Fan
Body Copper/Cobre
Blades Walnut/Nogal



32100
32100WP *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate



33417
33417WP *Smart Fan
Body Old Gold/Oro Viejo
Blades Matt Black/Negro Mate



33418
33418WP *Smart Fan
Body Copper/Cobre
Blades Matt Black/Negro Mate



with light/con luz

SMD LED 16W 3000K 709lm >80 **Driver incl.** Yes
Diff Glass/Cristal

33394-9
33394WP-9 *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente

33395-10
33395WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal

33398-10
33398WP-10 *Smart Fan
Body Old Gold/Oro Viejo
Blades Walnut/Nogal

33399-10
33399WP-10 *Smart Fan
Body Copper/Cobre
Blades Walnut/Nogal

32100-10
32100WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate

33417-10
33417WP-10 *Smart Fan
Body Old Gold/Oro Viejo
Blades Matt Black/Negro Mate

33418-10
33418WP-10 *Smart Fan
Body Copper/Cobre
Blades Matt Black/Negro Mate



ø1780
697



ø810
805

Material Body	Steel/Acero
Material Blades	PC
W	4-6-9-13-22-32
RPM	51-77-103-129-155-185
Airflow	145.66 m3 min
V/Hz	220V-240V/50-60Hz
Downrods	100-200-450mm



A	A1
640/25.2"	630/24.8"
B	**C**
180/7.09"	160/6.3"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1280/50.4"	555/21.85"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150 del receptor. El precio del receptor es con el descuento PRO35.





Smart option
Opción inteligente



Aesthetic glass
Cristal estético



Additional kit
Kit adicional

DECOFAN

— Conillas

PRICES

ø128 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL



33394D
33394DWP *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente



33395D
33395DWP *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal



33398D
33398DWP *Smart Fan
Body Old Gold/Oro Viejo
Blades Walnut/Nogal



33399D
33399DWP *Smart Fan
Body Copper/Cobre
Blades Walnut/Nogal



with light/con luz

SMD LED 16W 3000K 709lm >80 **Driver incl.** Yes
Diff Glass/Cristal

33394D-9
33394DWP-9 *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente

33395D-10
33395DWP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal

33398D-10
33398DWP-10 *Smart Fan
Body Old Gold/Oro Viejo
Blades Walnut/Nogal

33399D-10
33399DWP-10 *Smart Fan
Body Copper/Cobre
Blades Walnut/Nogal

Material Body	Steel/Acero
Material Blades	PC
W	4-6-9-13-22-32
RPM	51-77-103-129-155-185
Airflow	145.66 m3 min
V/Hz	220V-240V/50-60Hz
Downrods	100-200-450mm



A	A1
450/17.72"	420/16.54"
B	**C**
	160/6.3"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1280/50.4"	555/21.85"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150 del receptor. El precio del receptor es con el descuento PRO35.



Additional kit
Kit adicional



Smart option
Opción inteligente

MINI TUBE

— Conillas

PRICES

ø128 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL



33393
33393WP *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente



32038
32038WP *Smart Fan
Body Shiny White/Blanco Brillo
Blades Transparent/Transparente



32039
32039WP *Smart Fan
Body Matt White/Blanco Mate
Blades Transparent/Transparente



32040
32040WP *Smart Fan
Body Shiny Black/Negro Brillo
Blades Transparent/Transparente



32041
32041WP *Smart Fan
Body Matt Black/Negro Mate
Blades Transparent/Transparente



32042
32042WP *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal



32043
32043WP *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate



with light/con luz

SMD LED 16W 3000K 709lm >80 **Driver incl.** Yes
Diff Glass/Cristal

33393-9
33393WP-9 *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente

32038-9
32038WP-9 *Smart Fan
Body Shiny White/Blanco Brillo
Blades Transparent/Transparente

32039-9
32039WP-9 *Smart Fan
Body Matt White/Blanco Mate
Blades Transparent/Transparente

32040-10
32040WP-10 *Smart Fan
Body Shiny Black/Negro Brillo
Blades Transparent/Transparente

32041-10
32041WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Transparent/Transparente

32042-10
32042WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal

32043-10
32043WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate

Material Body	Steel+Glass/Acero+Cristal
Material Blades	PC
W	4-6-9-13-22-32
RPM	51-77-103-129-155-185
Airflow	145.66 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
290/11.42"	250/9.84"
B	**C**
250/9.84"	160/6.3"
D	**E**
	130/5.12"
F	**G**
ø1280/50.4"	430/16.93"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150 del receptor. El precio del receptor es con el descuento PRO35.



Additional kit
Kit adicional



Smart option
Opción inteligente

TUBE

— Conillas

PRICES

ø128 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL



33374
33374WP *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente



32033
32033WP *Smart Fan
Body Shiny White/Blanco Brillo
Blades Transparent/Transparente



32034
32034WP *Smart Fan
Body Matt White/Blanco Mate
Blades Transparent/Transparente



32035
32035WP *Smart Fan
Body Shiny Black/Negro Brillo
Blades Transparent/Transparente



32036
32036WP *Smart Fan
Body Matt Black/Negro Mate
Blades Transparent/Transparente



32037
32037WP *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal



32060
32060WP *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate



with light/con luz

SMD LED 16W 3000K 709lm >80 **Driver incl.** Yes
Diff Glass/Cristal

33374-9
33374WP-9 *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente

32033-9
32033WP-9 *Smart Fan
Body Shiny White/Blanco Brillo
Blades Transparent/Transparente

32034-9
32034WP-9 *Smart Fan
Body Matt White/Blanco Mate
Blades Transparent/Transparente

32035-10
32035WP-10 *Smart Fan
Body Shiny Black/Negro Brillo
Blades Transparent/Transparente

32036-10
32036WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Transparent/Transparente

32037-10
32037WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal

32060-10
32060WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate

Material Body	Steel+Glass/Acero+Cristal
Material Blades	PC
W	3-6-9-13-22-32
RPM	51-77-103-129-155-185
Airflow	145.66 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
450/17.72"	420/16.54"
B	**C**
420/16.54"	160/6.3"
D	**E**
	130/5.12"
F	**G**
ø1280/50.4"	430/16.93"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150 del receptor. El precio del receptor es con el descuento PRO35.



Smart option
Opción inteligente



High airflow
Alto flujo de aire

NASSAU

PRICES

ø128 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33478
33478WP ***Smart Fan***
Body Dark Brown/Marrón Oscuro
Blades Dark Brown/Marrón Oscuro



33487
33487WP ***Smart Fan***
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Optional downrod/Tijas opcionales



33479
Body Dark Brown/Marrón Oscuro



33488
Body Matt White/Blanco Mate

Material Body	Steel/Acero
Material Blades	Plywood
W	4-6-10-16-24-37
RPM	50-87-125-162-199-237
Airflow	222.41 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
400/15.75"	370/14.57"
B	**C**
170/6.69"	120/4.72"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1280/50.4"	575/22.64"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-04 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-04 del receptor. El precio del receptor es con el descuento PRO35.



Ref.33481 IP44 outdoor
Ref.33481 IP44 exterior



Smart option
Opción inteligente

WINCHE

— Conillas

PRICES

ø127 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33481
33481WP *Smart Fan
Body Matt Black/Negro Mate
Blades Dark Brown/Marrón Oscuro



33482
33482WP *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Brown/Marrón



with light/con luz

SMD LED 15W 3000K 800lm >80 **Driver incl.** Yes
Diff ABS

33481-7
33481WP-7 *Smart Fan
Body Matt Black/Negro Mate
Blades Dark Walnut/Nogal Oscuro

33482-8
33482WP-8 *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Dark Walnut/Nogal Oscuro

Material Body	Steel/Acero
Material Blades	ABS
W	3-5-8-12-21-35
RPM	50-71-93-115-138-162
Airflow	183.01 m3 min
V/Hz	220V-240V/50-60Hz
Opt. downrod	Page 810



A	A1
390/15.35"	355/13.98"
B	**C**
210/8.27"	190/7.48"
D	**E**
55/2.2"	130/5.12"
F	**G**
ø1270/50"	530/20.87"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-08 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-08 del receptor. El precio del receptor es con el descuento PRO35.



PANAY

PRICES

ø122 CM | 13-17 M2 140-190 SQ.FT | REMOTE CONTROL | INCLINING ROOF



33607
Body White/Blanco
Blades White/Blanco
+Maple/Arce





33608
Body Matt Nickel/Níquel Mate
Blades Grey/Gris
+Mahogany/Caoba



Material Body	Steel/Acero
Material Blades	MDF
W	14-30-58
RPM	95-150-200
Airflow	116.2 m3 min
V/Hz	220V-240V/50Hz
Opt. downrod	Page 810

Light	2 E14 max. 8W
Bulb incl.	No
Rec. Bulb	17461
Diff	Glass/Cristal



A	A1
280/11.02"	180/7.09"
B	**C**
150/5.91"	210/8.27"
D	**E**
65/2.6"	130/5.12"
F	**G**
ø1220/48"	495/19.49"



YAKARTA

PRICES

ø121 CM | 13-17 M2 140-190 SQ.FT | SUMMER WINTER | INCLINING ROOF | DIRECT CEILING MOUNTING | CONTROLLED BY CHAINS



33711
Body Old Gold/Oro Viejo
Blades Dark Oak/Roble Oscuro
+Bleached Oak/Roble Emblanquecido





33712
Body White/Blanco
Blades White/Blanco
+Maple/Arce





33713
Body Brown/Marrón
Blades Mahogany/Caoba
+Dark Walnut/Nogal Oscuro





with light/con luz

3 E27 max. 60W **Bulb incl.** No **Rec. Bulb** 17463

33711-11
Body Old Gold/Oro Viejo
Blades Dark Oak/Roble Oscuro



33712-12
Body White/Blanco
Blades White/Blanco



33713-13
Body Brown/Marrón
Blades Mahogany/Caoba



Material Body	Steel/Acero
Material Blades	Plywood
W	14-23-51
RPM	115-150-205
Airflow	94.57 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33928 Wall Control 3 speeds
	33929 Remote Control/dimer-on-off
	33937 Remote Control/Programmer
Opt. downrod	Page 810



A	A1
350/13.78"	300/11.81"
B	**C**
130/5.12"	
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1210/47.6"	465/18.31"

ECO INDUS

PRICES

ø120 CM | 13-17 M2 140-190 SQ.FT | WALL CONTROL | INCLINING ROOF | EASY INSTALL



33005
Body Matt White/Blanco Mate
Blades White/Blanco



ø1400
714

ø920
800

Material Body	Steel/Acero
Material Blades	Steel/Acero
W	16-26-68
RPM	150-225-322
Airflow	189.47 m3 min
V/Hz	220V-240V/50Hz



A	A1
320/12.6”	270/10.63”
B	**C**
160/6.3”	190/7.48”
D	**E**
60/2.4”	130/5.12”
F	**G**
ø1200/47.2”	485/19.09”

FRASER

PRICES

ø120 CM | 13-17 M2 140-190 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER





Glass diffuser
Difusor de cristal



Smart option
Opción inteligente



Programmable from 1-4-8h
Programable de 1-4-8h

33756
33756WP ***Smart Fan***
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero	**Light**	16W 3000K 850lm
Material Blades	ABS	**CRI**	>=80
W	5-8-11-16-22-32	**Driver incl.**	Yes
RPM	103-126-145-166-182-209	**Diff**	Glass/Cristal
Airflow	212 m3 min		
V/Hz	220V-240V/50-60Hz		
Accesories ⊗	33928 Wall Control 3 speeds		



A	A1
310/12.2"	230/9.06"
B	**C**
190/7.48"	155/6.1"
D	**E**
	150/5.91"
F	**G**
ø1180/46.5"	530/20.87"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-09 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-09 del receptor. El precio del receptor es con el descuento PRO35.



Glass diffuser
Difusor de cristal

MINI ICARIA

PRICES

ø107 CM | < 13 M2 < 140 SQ.FT | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33695
Body Old Gold/Oro Viejo
Blades Brown/Marrón
+Oak/Roble





33696
Body Satin Nickel/Níquel Satinado
Blades Transparent/Transparente



33697
Body Dark Brown/Marrón Oscuro
Blades Mahogany/Caoba
+Oak/Roble





33698
Body White/Blanco
Blades White/Blanco
+Maple/Arce





33699
Body Matt Nickel/Níquel Mate
Blades Grey/Gris
+Maple/Arce





ø1320
755

Material Body	Steel/Acero	**Light**	2 E14 max. 8W
Material Blades	MDF	**Bulb incl.**	No
W	16-24-35	**Rec. Bulb**	17461
RPM	135-175-210	**Diff**	Glass/Cristal
Airflow	101.09 m3 min		
V/Hz	220V-240V/50Hz		
Accesories ⊗	33928 Wall Control 3 speeds		
	33929 Remote Control/dimer-on-off		
	33937 Remote Control/Programmer		
Opt. downrod	Page 810		



A	A1
405/15.94"	270/10.63"
B	**C**
280/11.02"	160/6.3"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1070/42.1"	425/16.73"

FEROE

PRICES

ø107 CM

< 13 M2
< 140 SQ.FT

REMOTE CONTROL

INCLINING ROOF



Glass diffuser
Difusor de cristal



33600
Body White/Blanco
Blades White/Blanco
+Maple/Arce



Material Body	Steel/Acero
Material Blades	MDF
W	10-21-41
RPM	80-145-180
Airflow	64.16 m3 min
V/Hz	220V-240V/50Hz
Opt. downrod	Page 810

Light	2 E14 max. 8W
Bulb incl.	No
Rec. Bulb	17461
Diff	Glass/Cristal



A	A1
320/12.6”	210/8.27”
B	**C**
160/6.3”	200/7.87”
D	**E**
60/2.4”	130/5.12”
F	**G**
ø1070/42.1”	420/16.54”

MINI MALLORCA

PRICES

ø107 CM

< 13 M2
< 140 SQ.FT

REMOTE CONTROL

INCLINING ROOF





33604
Body Matt Nickel/Níquel Mate
Blades Grey/Gris
+Black/Negro



ø1320
757

Material Body	Steel/Acero
Material Blades	MDF
W	10-21-41
RPM	80-145-180
Airflow	64.16 m3 min
V/Hz	220V-240V/50Hz
Opt. downrod	Page 810



A	A1
235/9.25"	200/7.87"
B	**C**
90/3.54"	220/8.66"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1070/42.1"	420/16.54"



MINI LANTAU

PRICES

ø107 CM | < 13 M2 < 140 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33508DC *DC Motor*
33508DCWP NEW **Smart Fan*
Body Matt Nickel/Níquel Mate
Blades Walnut/Nogal



33509DC *DC Motor*
33509DCWP NEW **Smart Fan*
Body Matt Nickel/Níquel Mate
Blades Pine/Pino



33517DC *DC Motor*
33517DCWP NEW **Smart Fan*
Body Matt Black/Negro Mate
Blades Walnut/Nogal



ø1680
699



ø1320
741

Material Body	Steel/Acero
Material Blades	Wood/Madera
W	3-5-7-10-15-21
RPM	72-104-131-164-193-224
Airflow	143.2 m3 min
V/Hz	220V-240V/50Hz
Accesories ⊗	33974 DC Wall Control
Opt. downrod	Page 810



A	A1
340/13.39"	300/11.81"
B	**C**
110/4.33"	
D	**E**
65/2.6"	150/5.91"
F	**G**
ø1070/42.1"	460/18.11"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-34 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-34 del receptor. El precio del receptor es con el descuento PRO35.

LISBOA

PRICES

ø107 CM | < 13 M2 < 140 SQ.FT | SUMMER WINTER | INCLINING ROOF | DIRECT CEILING MOUNTING | CONTROLLED BY CHAINS



33102
Body Dark Brown/Marrón Oscuro
Blades Mahogany/Caoba
+Dark Walnut/Nogal Oscuro



Material Body	Steel/Acero	**Light**	3 E27 max. 15W
Material Blades	MDF	**Bulb incl.**	No
W	27-35-47	**Rec. Bulb**	17462
RPM	130-185-235	**Diff**	Glass/Cristal
Airflow	99.96 m3 min		
V/Hz	220V-240V/50Hz		
Accesories ⊗	33928 Wall Control 3 speeds		
	33929 Remote Control/dimer-on-off		
	33937 Remote Control/Programmer		
Opt. downrod	Page 810		



A	A1
460/18.11"	240/9.45"
B	**C**
220/8.66"	300/11.81"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø1070/42.1"	420/16.54"

EASY

PRICES

ø105 CM | < 13 M2 < 140 SQ.FT | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF | EASY INSTALL





33415
Body White/Blanco
Blades White/Blanco



33416
Body Grey/Gris
Blades Grey/Gris



Programmable from 1-3-6-9h
Programable de 1-3-6-9h

Material Body	Steel+ABS/Acero+ABS	**Light**	2 E27 max. 15W
Material Blades	ABS	**Bulb incl.**	No
W	11-23-68	**Rec. Bulb**	17463
RPM	105-185-285	**Diff**	ABS
Airflow	159.76 m3 min		
V/Hz	220V-240V/50Hz		



A	A1
460/18.11”	320/12.6”
B	**C**
100/3.94”	210/8.27”
D	**E**
75/3”	140/5.51”
F	**G**
ø1050/41.3”	420/16.54”

CEBU

PRICES

ø102 CM | < 13 M2 < 140 SQ.FT | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33606
Body Shiny White/Blanco Brillo
Blades White/Blanco
+Maple/Arce



Material Body	Steel/Acero	**Light**	2 E14 max. 8W
Material Blades	MDF	**Bulb incl.**	No
W	8-22-38	**Rec. Bulb**	17461
RPM	84-140-180	**Diff**	Glass/Cristal
Airflow	109 m3 min		
V/Hz	220V-240V/50Hz		
Accesories ⊗	33928 Wall Control 3 speeds		
	33929 Remote Control/dimer-on-off		
	33937 Remote Control/Programmer		
Opt. downrod	Page 810		



A	A1
410/16.14"	270/10.63"
B	**C**
300/11.81"	180/7.09"
D	**E**
60/2.4"	140/5.51"
F	**G**
ø1020/40.2"	420/16.54"

HVAR

PRICES

ø97 CM | < 13 M2 < 140 SQ.FT | DC MOTOR | DIM | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



Adjustable intensity
Intensidad regulable



Programmable from 1-2-4-8h
Programable de 1-2-4-8h



Smart option
Opción inteligente



34300
34300WP *Smart Fan*
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero	**Light**	SMD LED 24W 6500K 1600lm
Material Blades	ABS	**Dimmable K**	3000 - 4500 - 6500K
W	5.5-8.8-14-20.6-27.5-34.8	**CRI**	>80
RPM	139-172-206-245-268-300	**Driver incl.**	Yes
Airflow	130 m3 min	**Diff**	PMMA
V/Hz	220V-240V/50Hz		
Downrods	127mm		



A	A1
549/21.61"	447/17.6"
B	**C**
295/11.61"	
D	**E**
80/3.1"	165/6.5"
F	**G**
ø914/36"	328/12.91"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-25 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-25 del receptor. El precio del receptor es con el descuento PRO35.

MINI INDUS

PRICES

ø92 CM

< 13 M2
< 140 SQ.FT

WALL CONTROL

EASY INSTALL



33011
Body White/Blanco
Blades White/Blanco

ø1400
714

ø1200
788

Material Body	Steel/Acero
Material Blades	Steel/Acero
W	10-13-17-22-43
RPM	183-225-272-299-330
Airflow	74.56 m3 min
V/Hz	220V-240V/50Hz



A	A1
483/19.02”	440/17.32”
B	**C**
160/6.3”	120/4.72”
D	**E**
120/4.7”	145/5.71”
F	**G**
ø920/36.2”	320/12.6”

CHICAGO

PRICES

ø91 CM

< 13 M2
< 140 SQ.FT

REMOTE CONTROL

INCLINING ROOF



33703
Body Matt Black/Negro Mate
Blades Walnut/Nogal

Material Body	Steel/Acero	**Light**	1 E27 max. 15W
Material Blades	MDF	**Bulb incl.**	No
W	15-26-49	**Rec. Bulb**	17463
RPM	136-192-225		
Airflow	96.71 m3 min		
V/Hz	220V-240V/50-60Hz		
Accesories ⊗	33928 Wall Control 3 speeds		
	33929 Remote Control/dimer-on-off		
	33937 Remote Control/Programmer		
Opt. downrod	Page 810		



A	A1
475/18.7”	295/11.61”
B	**C**
295/11.61”	140/5.51”
D	**E**
50/2”	150/5.91”
F	**G**
ø915/36”	380/14.96”

NEW

HEYWOOD

PRICES

ø90 CM | < 13 M2 < 140 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | WITH PROGRAMMER | INCLINING ROOF



Smart option
Opción inteligente



33806
33806WP *Smart Fan
Body Matt Black/Negro Mate
Blades Dark Oak/Roble Oscuro



33805
33805WP *Smart Fan
Body Matt White/Blanco Mate
Blades Maple/Arce



Material Body	Steel/Acero
Material Blades	Wood/Madera
W	5.2-7.3-12.2-17.4-23.2-31.6
RPM	123-166-204-242-267-300
Airflow	117 m3 min
V/Hz	220V-240V/50-60Hz



A	A1
268/10.55"	223/8.78"
B	**C**
82/3.23"	100/3.94"
D	**E**
59/2.3"	132/5.2"
F	**G**
ø900/35.4"	

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-33 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-33 del receptor. El precio del receptor es con el descuento PRO35.

MEDITERRÁNEO

PRICES

ø81 CM

< 13 M2
< 140 SQ.FT

SUMMER
WINTER

CONTROLLED
BY CHAINS





33704
Body White/Blanco
Blades White/Blanco
+Maple/Arce



33706
Body Matt Nickel/Níquel Mate
Blades Maple/Arce
+Mahogany/Caoba

Material Body	Steel/Acero	**Light**	1 E14 max. 8W
Material Blades	MDF	**Bulb incl.**	No
W	14-23-47	**Rec. Bulb**	17461
RPM	198-232-280	**Diff**	Glass/Cristal
Airflow	85.38 m3 min		
V/Hz	220V-240V/50Hz		
Accesories ⊗	33928 Wall Control 3 speeds		
	33929 Remote Control/dimer-on-off		
	33937 Remote Control/Programmer		



A	A1
385/15.16"	
B	**C**
260/10.24"	190/7.48"
D	**E**
110/4.3"	130/5.12"
F	**G**
ø815/32.1"	310/12.2"



Smart option
Opción inteligente



2 downrods incl. 3.9" / 7.8"
2 tijas incl. 100mm / 200mm

JUSTFAN

— Conillas

PRICES

ø81 CM | < 13 M2 < 140 SQ.FT | DC MOTOR | OPTION SMART 100-240V 50-60Hz | SUMMER WINTER | REMOTE CONTROL | INCLINING ROOF



33426
33426WP *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente



33425
33425WP *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal



33428
33428WP *Smart Fan
Body Old Gold/Oro Viejo
Blades Walnut/Nogal



33423
33423WP *Smart Fan
Body Copper/Cobre
Blades Walnut/Nogal



33424
33424WP *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate



33429
33429WP *Smart Fan
Body Old Gold/Oro Viejo
Blades Matt Black/Negro Mate



33427
33427WP *Smart Fan
Body Copper/Cobre
Blades Matt Black/Negro Mate



with light/con luz

SMD LED 16W 3000K 709lm >80 **Driver incl.** Yes
Diff Glass/Cristal

33426-9
33426WP-9 *Smart Fan
Body Shiny Chrome/Cromo Brillo
Blades Transparent/Transparente

33425-10
33425WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Walnut/Nogal

33428-10
33428WP-10 *Smart Fan
Body Old Gold/Oro Viejo
Blades Walnut/Nogal

33423-10
33423WP-10 *Smart Fan
Body Copper/Cobre
Blades Walnut/Nogal

33424-10
33424WP-10 *Smart Fan
Body Matt Black/Negro Mate
Blades Matt Black/Negro Mate

33429-10
33429WP-10 *Smart Fan
Body Old Gold/Oro Viejo
Blades Matt Black/Negro Mate

33427-10
33427WP-10 *Smart Fan
Body Copper/Cobre
Blades Matt Black/Negro Mate



ø1780
697



ø1280
775

Material Body	Steel/Acero
Material Blades	PC
W	2.8-3.2-4-5-6.7-9
RPM	51-86-122-158-195-235
Airflow	121.69 m3 min
V/Hz	220V-240V/50-60Hz
Downrods	100-200mm



A	A1
390/15.35"	380/14.96"
B	**C**
180/7.09"	160/6.3"
D	**E**
55/2.2"	130/5.12"
F	**G**
ø810/31.9"	358/14.09"

*Order your Smart Fan with the reference of the fan finished in WP and add the reference 34150-02 of the gear. The price of the gear is with PRO35 discount.
Solicita tu Smart Fan con la referencia del ventilador acabado en WP y añade la referencia 34150-02 del receptor. El precio del receptor es con el descuento PRO35.



PALAO

PRICES

ø81 CM | < 13 M2 < 140 SQ.FT | SUMMER WINTER | INCLINING ROOF | DIRECT CEILING MOUNTING | CONTROLLED BY CHAINS



33179
Body Matt White/Blanco Mate
Blades Multicolor



33180
Body White/Blanco
Blades White/Blanco



33183
Body Satin Nickel/Níquel Satinado
Blades Maple/Arce



33185
Body Dark Brown/Marrón Oscuro
Blades Mahogany/Caoba



33186
Body Grey/Gris
Blades Grey/Gris

Material Body	Steel/Acero	**Light**	1 E14 max. 8W
Material Blades	MDF	**Bulb incl.**	No
W	24-28-37	**Rec. Bulb**	17461
RPM	127-192-241	**Diff**	Glass/Cristal
Airflow	92.37 m3 min		
V/Hz	220V-240V/50Hz		
Accesories ⊗	33928 Wall Control 3 speeds		
	33929 Remote Control/dimer-on-off		
	33937 Remote Control/Programmer		
Opt. downrod	Page 810		



A	A1
390/15.35"	260/10.24"
B	**C**
190/7.48"	170/6.69"
D	**E**
60/2.4"	130/5.12"
F	**G**
ø810/31.9"	350/13.78"

VEDRA

PRICES

ø46 CM | < 13 M2 < 140 SQ.FT | WALL CONTROL | INCLINING ROOF



33450
Body Old Gold/Oro Viejo
Blades Dark Walnut/Nogal Oscuro



33525
Body Black/Negro
Blades Dark Walnut/Nogal Oscuro



Adjustable inclination
Inclinación regulable



Material Body	Steel/Acero
Material Blades	MDF
W	19-22-34-37
RPM	327-369-495-515
Airflow	58.11 m3 min
V/Hz	220V-240V/50Hz



A	A1
540/21.26"	450/17.72"
B	**C**
D	**E**
60/2.4"	145/5.71"
F	**G**
ø460/18.1"	200/7.87"

KEIKI

PRICES

ø43 CM | < 13 M2 < 140 SQ.FT | SUMMER WINTER | WALL CONTROL | INCLINING ROOF





33715
Body Dark Brown/Marrón Oscuro
Blades Dark Walnut/Nogal Oscuro



33720
Body Matt White/Blanco Mate
Blades Matt White/Blanco Mate

Material Body	Steel/Acero
Material Blades	Plywood
W	10-19-28
RPM	380-640-890
Airflow	38.61 m3 min
V/Hz	220V-240V/50Hz



A	A1
505/19.88"	440/17.32"
B	**C**
D	**E**
55/2.2"	150/5.91"
F	**G**
ø430/16.9"	150/5.91"

Downrods / Tijas

	**33904**	White/Blanco	Steel/Acero	/	ø21/0.8” / 300/11.81”
	**33944**	Matt White/Blanco Mate	Steel/Acero	/	ø21/0.8” / 400/15.75”
	**33948**	Satin Nickel/Níquel Satinado	Steel/Acero	/	ø21/0.8” / 400/15.75”
	**33954**	Matt White/Blanco Mate	Steel/Acero	/	ø21/0.8” / 500/19.69”
	**33957**	Old Gold/Oro Viejo	Steel/Acero	/	ø21/0.8” / 500/19.69”
	**33958**	Grey/Gris	Steel/Acero	/	ø21/0.8” / 500/19.69”
	**33959**	Grey/Gris	Steel/Acero	/	ø21/0.8” / 300/11.81”
	**33960**	Old Gold/Oro Viejo	Steel/Acero	/	ø21/0.8” / 300/11.81”
	**33962**	Dark Brown/Marrón Oscuro	Steel/Acero	/	ø21/0.8” / 300/11.81”
	**33964**	Dark Brown/Marrón Oscuro	Steel/Acero	/	ø21/0.8” / 500/19.69”
	**33965**	Satin Nickel/Níquel Satinado	Steel/Acero	/	ø21/0.8” / 300/11.81”
	**33971**	Satin Nickel/Níquel Satinado	Steel/Acero	/	ø21/0.8” / 500/19.69”

Remote control / Mando a distáncia

Remote control kit / Kit mando a distancia

	**33929**	/50/60Hz	/ 120/4.72”

Remote control kit with programmer / Kit mando a distancia con programador

	**33937**	/60Hz	/ 120/4.72”

PRICES

AC Wall control / Regulador de pared AC



33928 Steel/Acero 220V-240V/50/60Hz / 90/3.54”

3 speeds *The wall control is not compatible with the remote control at same time / El regulador de pared no se puede usar al mismo tiempo que el mando a distáncia

DC Wall control / Regulador de pared DC



33974 White/Blanco Steel/Acero 220V-240V/50Hz / 70/2.76”

6 speeds *Compatible with/con: GOTLAND/RODAS/HYDRA/SAMOS/POROS/LANTAU DC & All references ending in WP/Todas las referencias acabadas en WP

Light kits / Kits de luz

CIES



33513 white/blanco

JUSTFAN/ETERFAN/DECOFAN/TUBE



33390 chrome/cromo

33391 black/negro

NIAS



33472K matt nickel/níquel mate

YAKARTA



33714 dark brown/marrón oscuro

33716 white/blanco

33717 antique brass/oro envejecido

PEMBA



33471K white/blanco

33491K grey/gris

33492K brown/marrón

TYPHOON



33483 white/blanco **Indoor/Outdoor IP44**

33489K grey/gris **Indoor/Outdoor IP44**

33490K brown/marrón **Indoor/Outdoor IP44**

WINCHE



33484 black/negro **Indoor/Outdoor IP44**

33486 grey/gris

PRICES

Items with special discount conditions
Artículos con condiciones especiales de descuento

LED Bulb GU5.3		SOCKET	P	CRI		DIM	BEAM	FLUX	CCT
PARATHOM MR16									
	97686227	GU5.3	8W	92	40000 h	✓	24°	485lm	2700K
	97686230	GU5.3	8W	92	40000 h	✓	24°	500lm	3000K
	97686327	GU5.3	8W	92	40000 h	✓	36°	485lm	2700K
	97686330	GU5.3	8W	92	40000 h	✓	36°	500lm	3000K
LED bulb GU10									
MASTER LED Spot MV									
	97685327	SOCKET GU10	5W	90	25000 h	✓	36°	350lm	2700K
	97685330	SOCKET GU10	5W	90	25000 h	✓	36°	365lm	3000K
	97264	SOCKET GU10	5W	90	25000 h	✓	60°	355lm	2700K
	97404	SOCKET GU10	5W	90	25000 h	✓	60°	365lm	3000K
	97273	SOCKET GU10	5.5W	97	40000 h	✓	36°	355lm	2700K
	97402	SOCKET GU10	5.5W	97	40000 h	✓	36°	375lm	3000K
LED bulb GU10									
PARATHOM GU10									
	97166	SOCKET GU10	6.9W	80	15000 h		36°	575lm	2700K
	97291	SOCKET GU10	6.9W	80	15000 h		36°	575lm	3000K
	97403	SOCKET GU10	6.9W	80	15000 h		60°	575lm	2700K
	97292	SOCKET GU10	6.9W	80	15000 h		60°	575lm	3000K
QR111									
PARATHOM QR111									
	97411	SOCKET G53	15W	90	40000 h	✓	24°	800lm	2700K
	97412	SOCKET G53	15W	90	40000 h	✓	24°	800lm	3000K
	97413	SOCKET G53	15W	90	40000 h	✓	40°	800lm	2700K
	97414	SOCKET G53	15W	90	40000 h	✓	40°	800lm	3000K
PAR30									
PARATHOM PAR30									
	97687127	E27	10W	90	25000 h	✓	36°	633lm	2700K

SORAA

GU10		SOCKET	P	CRI	BEAM	FLUX	CCT	Compatible CCT Shifter	Compat. Linear Louver System
	97691327	SOCKET GU10	7.5W	95	25°	410lm	2700K	✓	✓
	97691127	SOCKET GU10	7.5W	95	10°	390lm	2700K	✓	✓
	97691227	SOCKET GU10	7.5W	95	36°	410lm	2700K	✓	✓
	97691330	SOCKET GU10	7.5W	95	25°	410lm	3000K	✓	✓
	97691130	SOCKET GU10	7.5W	95	10°	410lm	3000K	✓	✓
	97691230	SOCKET GU10	7.5W	95	36°	435lm	3000K	✓	✓
MR16 - GU5.3									
	97690127	SOCKET GU5.3	7.5W	95	10°	390lm	2700K		✓
	97690427	SOCKET GU5.3	7.5W	95	36°	410lm	2700K		✓
	97690130	SOCKET GU5.3	7.5W	95	10°	410lm	3000K	✓	✓
	97690430	SOCKET GU5.3	7.5W	95	36°	435lm	3000K	✓	✓
SNAP System - MR16 & PAR 20									
	97691695	CCT Shifter SNAP Lens - 2" Color Filter, ½ CTO, 3000K to 2400K							
	97691696	CCT Shifter SNAP Lens - 2" Color Filter, ¾ CTO, 3000K to 2200K							
	97691697	SNAP Lens - 2" Linear Beam Spreader 10°x25°							
	97691698	SNAP Lens - 2" Linear Beam Spreader 10°x36°							
	97691701	SNAP Lens - 2" Beam Spreader 17°							
	97691702	SNAP Lens - 2" Beam Spreader 25°							
	97691703	SNAP Lens - 2" Beam Spreader 36°							
	97691704	SNAP Lens - 2" Beam Spreader 60°							
	97691699	SNAP Lens - 2" Louver 40°							

QR111 - 12V		SOCKET	P	CRI	BEAM	FLUX	CCT
	97692327	SOCKET G53	12.5W	95	8°	575lm	2700K
	97692427	SOCKET G53	12.5W	95	36°	575lm	2700K
	97692330	SOCKET G53	12.5W	95	8°	620lm	3000K
	97692430	SOCKET G53	12.5W	95	36°	620lm	3000K
SNAP System - Large Lamps							
	97692595	CCT Shifter SNAP Lens - 4" Color Filter, ½ CTO, 3000K to 2700K					
	97692596	CCT Shifter SNAP Lens - 4" Color Filter, ¾ CTO, 3000K to 2200K					
	97692597	SNAP Lens - 4" Linear Beam Spreader 10°x36°					
	97692598	SNAP Lens - 4" Linear Beam Spreader 10°x60°					
	97692601	SNAP Lens - 4" Beam Spreader 17°					
	97692602	SNAP Lens - 4" Beam Spreader 25°					
	97692603	SNAP Lens - 4" Beam Spreader 36°					
	97692604	SNAP Lens - 4" Beam Spreader 60°					
	97692599	SNAP Lens - 4" Louver 40°					

LED Module	Ref	Socket	K	lm	CRI	I.E.E.	P	Beam	Dimm	DC Current	Hrs.	*Driver not incl.
	18030	—	2700	930	90	G	12W	12°	✓	350 mA	50.000	98310114C / 98310115
	18031	—	2700	1140	90	F	12W	36°	✓	350 mA	50.000	98310114C / 98310115
	18032	—	3000	1040	90	G	12W	12°	✓	350 mA	50.000	98310114C / 98310115
	18033	—	3000	1140	90	F	12W	36°	✓	350 mA	50.000	98310114C / 98310115
	18034	—	4000	1040	90	G	12W	12°	✓	350 mA	50.000	98310114C / 98310115
	18035	—	4000	1140	90	F	12W	36°	✓	350 mA	50.000	98310114C / 98310115

SMART	Ref	Socket	K	lm	CRI	I.E.E.	P	Beam	Dimm	V	Hz	Hrs.	Caract.	Size
	17498	E27	2700	806	≥80	E	7W	360°	APP	220-240	50/60	25.000	Filament	ø60/2,3” 102/4,5”

GU10	Ref	Socket	K	lm	CRI	I.E.E.	P	Beam	Dimm	V	Hz	Hrs.	Caract.	Size
	17328	GU10	2700	560	80	F	7W	120°	—	220-240	50/60	15.000	—	ø50/1,9” 55/2,3”
	17329	GU10	4000	560	80	F	7W	120°	—	220-240	50/60	15.000	—	ø50/1,9” 55/2,3”
	17330	GU10	3000	500	80	E	7W	38°	—	220-240	50/60	15.000	Glass	ø50/1,9” 55/2,3”
	17309	GU10	3000	545	>90	G	7W	40°	—	100-240	50/60	25.000	—	ø50/1,9” 54/2,1”
	17316	GU10	2700	632	80	F	8W	38°	—	100-240	50/60	25.000	—	ø50/1,9” 54/2,1”
	17317	GU10	4000	737	80	F	8W	38°	—	100-240	50/60	25.000	—	ø50/1,9” 54/2,1”
	17320	GU10	2700	604	80	G	8W	60°	—	100-240	50/60	25.000	—	ø50/1,9” 54/2,1”
	17321	GU10	4000	662	80	F	8W	60°	—	100-240	50/60	25.000	—	ø50/1,9” 54/2,1”
	17318	GU10	2700	563	80	G	8W	38°	✓	220-240	50/60	25.000	—	ø50/1,9” 54/2,1”
	17319	GU10	4000	717	80	G	8W	38°	✓	220-240	50/60	25.000	—	ø50/1,9” 54/2,1”
	17324	GU10	2700	629	80	G	8W	60°	—	100-240	50/60	25.000	—	ø50/1,9” 54/2,1”
	17325	GU10	4000	610	80	F	7W	60°	—	100-240	50/60	25.000	—	ø50/1,9” 54/2,1”
	17331	GU10	2700	482	80	G	7W	60°	✓	220-240	50/60	25.000	—	ø50/1,9” 54/2,1”
	17332	GU10	4000	671	80	G	8W	60°	✓	220-240	50/60	25.000	—	ø50/1,9” 54/2,1”

G45	Ref	Socket	K	lm	CRI	I.E.E.	P	Beam	Dimm	V	Hz	Hrs.	Caract.	Size
	17472	E27	—	30	—		1W	360°	—	220-240	50/60	25.000	Coloured glass	ø45/1,7” 66/2,6”
	17473	E27	—	30	—		1W	360°	—	220-240	50/60	25.000	Coloured glass	ø45/1,7” 66/2,6”
	17474	E27	—	30	—		1W	360°	—	220-240	50/60	25.000	Coloured glass	ø45/1,7” 66/2,6”
	17475	E27	—	30	—		1W	360°	—	220-240	50/60	25.000	Coloured glass	ø45/1,7” 66/2,6”

C35	Ref	Socket	K	lm	CRI	I.E.E.	P	Beam	Dimm	V	Hz	Hrs.	Caract.	Size
	17460	E14	2700	400	80	F	4W	360°	—	220-240	50/60	15.000	Matt glass	ø35/1,3" 100/4"
G45														
	17461	E14	2700	400	80	F	4W	360°	—	220-240	50/60	15.000	Matt glass	ø45/1,7" 78/3,1"
	17462	E27	2700	400	80	F	4W	360°	—	220-240	50/60	15.000	Matt glass	ø45/1,7" 75/2,9"
T45														
	17437	E27	3000	550	80	E	5W	360°	—	220-240	50/60	15.000	Matt glass	ø45/1,7" 112/4,4"
A60														
	17463	E27	2700	850	80	F	8W	360°	—	220-240	50/60	15.000	Matt glass	ø60/2,3" 102/4"
	17485	E27	2700	900	80	F	8W	360°	✓	220-240	50/60	15.000	Matt glass	ø60/2,3" 102/4"
	17486	E27	4000	950	80	F	8W	360°	✓	220-240	50/60	15.000	Matt glass	ø60/2,3" 102/4"
	17064	E27	5000	720	80	F	8W	270°	—	220-240	50/60	15.000	Polycar-bonate	ø60/2,3" 110/4,3"
	17067	E27	2700	850	80	F	9W	270°	✓	220-240	50/60	15.000	Polycar-bonate	ø60/2,3" 120/4,7"
	17070 NEW	E27	2700	820	80	F	9W	270°	✓	220-240	50/60	15.000	Polycar-bonate	ø60/2,3" 120/4,7"
G95														
	17464	E27	2700	800	80	F	8W	360°	—	220-240	50/60	15.000	Matt glass	ø95/3,7" 125/4,9"
	17482	E27	2700	900	80	F	8W	360°	✓	220-240	50/60	15.000	Matt glass	ø95/3,7" 130/5,1"
G120														
	17479	E27	2700	1600	80	F	18W	270°	✓	220-240	50/60	15.000	Polycar-bonate	ø120/4,7" 155/6,1"
G125														
	17465	E27	2700	800	80	F	8W	360°	—	220-240	50/60	15.000	Matt glass	ø125/4,9" 175/6,8"
G45														
	17417	E27	2700	220	80	E	2W	360°	—	220-240	50/60	15.000	Filament	ø45/1,7" 75/2,9"
A60														
	17420	E27	2700	470	80	E	4W	360°	—	220-240	50/60	15.000	Filament	ø60/2,3" 102/4,6"
ST64														
	17422	E27	2700	470	80	E	4W	360°	—	220-240	50/60	15.000	Filament	ø64/2,5" 146/5,7"
G95														
	17415	E27	2700	470	80	E	4W	360°	—	220-240	50/60	15.000	Filament	ø95/3,7" 125/4,9"
G125														
	17423	E27	2700	470	80	E	4W	360°	—	220-240	50/60	15.000	Filament	ø125/4,9" 175/6,8"

PRICES

T30	Ref	Socket	K	lm	CRI	I.E.E.	P	Beam	Dimm	V	Hz	Hrs.	Caract.	Size
	17445	E27	2200	550	80	F	6W	360°	—	220-240	50/60	15.000	Filament Amber	ø28/1,1” 300/11,8”
C35														
	17427	E14	2200	160	—	G	2W	360°	—	220-240	50/60	15.000	Filament Amber	ø36/1,4” 100/3,9”
G45														
	17413	E14	2200	160	—	G	2W	360°	—	220-240	50/60	15.000	Filament Amber	ø45/1,7” 78/3,1”
	17414	E27	2200	160	—	G	2W	360°	—	220-240	50/60	15.000	Filament Amber	ø45/1,7” 75/2,9”
	17493	E27	2200	300	—	G	4W	360°	✓	220-240	50/60	15.000	Filament Amber	ø45/1,7” 75/2,9”
A60														
	17426	E27	2200	400	—	F	4W	360°	—	220-240	50/60	15.000	Filament Amber	ø56/2,2” 102/4”
	17432	E27	2200	440	—	F	5W	360°	✓	220-240	50/60	15.000	Filament Amber	ø56/2,2” 102/4”
ST64														
	17428	E27	2200	400	—	F	4W	360°	—	220-240	50/60	15.000	Filament Amber	ø64/2,5” 146/5,7”
	17433	E27	2200	440	—	G	5W	360°	✓	220-240	50/60	15.000	Filament Amber	ø64/2,5” 146/5,7”
SP64														
	17409	E27	2000	380	—	F	5W	360°	—	220-240	50/60	15.000	Filament Amber	ø64/2,5” 146/5,7”
G95														
	17429	E27	2200	400	—	F	4W	360°	—	220-240	50/60	15.000	Filament Amber	ø95/3,7” 138/5,3”
G125														
	17425	E27	2200	400	—	F	4W	360°	—	220-240	50/60	15.000	Filament Amber	ø125/4,9” 175/6,8”
	17434	E27	2200	440	—	G	5W	360°	✓	220-240	50/60	15.000	Filament Amber	ø125/4,9” 175/6,8”
A160														
	17447	E27	2000	280	—	G	5W	360°	✓	220-240	50/60	25.000	Filament Amber	ø160/6,3” 300/11,8”
BT180														
	17449	E27	2000	400	—	G	8W	360°	✓	220-240	50/60	25.000	Filament Amber	ø160/6,3” 390/15,3”
A60														
	17496	E27	2700	450	80	E	4W	360°	—	220-240	50/60	25.000	Filament Gold	ø60/2.3” 102/4”
	17071 NEW	E27	2700	400	80	F	4W	360°	✓	220-240	50/60	15.000	Filament Black	ø60/2.3” 102/4”
	17073 NEW	E27	2700	400	80	F	4W	360°	✓	220-240	50/60	15.000	Mirror	ø60/2.3” 102/4”
G95														
	17271	E27	2700	450	80	E	4W	360°	—	220-240	50/60	15.000	Mirror	ø95/3,7” 125/4,9”
A95														
	17072 NEW	E27	2700	400	80	F	4W	180°	✓	220-240	50/60	15.000	Filament Black	ø95/3,7” 125/4,9”
T26														
	17446	E14	2700	120	80	E	1W	360°	—	220-240	50/60	15.000	LED	ø25/0,1” 58/2,3”

PRICES

R7S	Ref	Socket	K	lm	CRI	I.E.E.	P	Beam	Dimm	V	Hz	Hrs.	Caract.	Size
	17497	JP117	2700	800	80	A++	8W	360°	—	220-240	50/60	25.000	LED	ø13,5/0,5” 118/4,6”
G4														
	17487	G4	3000	155	80	F	1,6W	360°	—	12 AC	—	15.000	LED	ø11/0,4” 41/1,6”
	17494	G4	3000	90	80	G	1,5W	360°	—	12 AC	50/60	25.000	LED	ø11/0,5” 33/1,3”
G9														
	17443	G9	2700	350	80	F	3,5W	360°	—	220-240	50/60	15.000	—	ø16/0,7” 50/1,9”
	17444	G9	4000	350	80	F	3,5W	360°	—	220-240	50/60	15.000	—	ø16/0,7” 50/1,9”
	17466	G9	2700	450	80	F	5W	360°	—	220-240	50/60	15.000	—	ø16/0,7” 60/2,3”
	17467	G9	4000	450	80	F	5W	360°	—	220-240	50/60	15.000	—	ø16/0,7” 60/2,3”
	17468	G9	2700	350	80	F	3,5W	360°	✓	220-240	50/60	15.000	—	ø16/0,7” 50/1,9”
	17495	G9	3000	470	80	E	4W	360°	—	220-240	50/60	15.000	—	ø14/0,5” 65/2,5”
PAR38														
	17400	E27	4000	850	80	F	10W	60°	—	220-240	50/60	30.000	—	ø120/4,7” 140/5,5”
	17398	E27	3000	1052	80	F	11W	23°	—	100-240	50/60	25.000	IP65	ø120/4,7” 134/5,2”
	17399	E27	4000	400	—	—	10W	60°	—	220-240	50/60	30.000	—	ø120/4,7” 134/5,2”
R80														
	17477	E27	2700	1050	80	F	12W	120°	—	220-240	50/60	15.000	LED	ø80/3,1” 110/4,3”
JP118														
	17490	R7s	2700	1000	80	F	10W	—	—	220-240	50/60	15.000	LED	ø23/0,9” 118/4,6”
	17491	R7s	4000	1000	80	F	10W	—	—	220-240	50/60	15.000	LED	ø23/0,9” 118/4,6”
JP78														
	17488	R7s	2700	600	80	F	6W	—	—	220-240	50/60	15.000	LED	ø23/0,9” 78/3,07”
	17499	R7s	2700	450	80	F	5W	—	—	220-240	50/60	15.000	LED	ø14/0,5” 78/3,07”
GX53														
	17340	GX53	3000	530	80	F	6W	—	—	220-240	50/60	25.000	LED	ø76/2,9” 26/1,2”

PRICES

Drivers / Equipos

		mA	P	V	units		
FOX 3W	**02101001** **02101002**	350mA	3W	100/240V	1-4 units	on/off	**98310620**
				220/240V	2-3 units	triac	**98310110LC**
				220/240V	2-5 units	dali	**98310536**
				220/240V	2-5 units	casambi	**98310538**
FOX 5W	**02101001** **02101002**	500mA	5W	100/240V	only 1 unit	on/off	**98310306**
				220/240V	2-4 units	triac	**98310321LC**
				220/240V	1-5 units	dali	**98310536**
				220/240V	1-5 units	casambi	**98310538**
FOX TRIMLESS 3W	**02101101** **02101102**	350mA	3W	100/240V	1-4 units	on/off	**98310620**
				220/240V	2-3 units	triac	**98310110LC**
				220/240V	2-5 units	dali	**98310536**
				220/240V	2-5 units	casambi	**98310538**
FOX TRIMLESS 5W	**02101101** **02101102**	500mA	5W	100/240V	only 1 unit	on/off	**98310306**
				220/240V	2-4 units	triac	**98310321LC**
				220/240V	1-5 units	dali	**98310536**
				220/240V	1-5 units	casambi	**98310538**
FOX ORIENTABLE 3W	**02101301** **02101302**	350mA	3W	100/240V	1-4 units	on/off	**98310620**
				220/240V	2-3 units	triac	**98310110LC**
				220/240V	2-5 units	dali	**98310536**
				220/240V	2-5 units	casambi	**98310538**
FOX ORIENTABLE 5W	**02101301** **02101302**	500mA	5W	100/240V	only 1 unit	on/off	**98310306**
				220/240V	2-4 units	triac	**98310321LC**
				220/240V	1-5 units	dali	**98310536**
				220/240V	1-5 units	casambi	**98310538**
FOX 7W	**02101501**	350mA	7W	100/240V	1-2 units	on/off	**98310620**
				220/240V	2 units	triac	**98310118LC**
				220/240V	2 units	dali	**98310536**
				220/240V	2 units	casambi	**98310538**
FOX 10W	**02101601**	500mA	10W	100/240V	1-2 units	on/off	**98310620**
				220/240V	2 units	triac	**98310321LC**
				220/240V	2 units	dali	**98310536**
				220/240V	2 units	casambi	**98310538**
AIM 3W	**02100401**	350mA	3W	100/240V	1-4 units	on/off	**98310620**
				220/240V	2-3 units	triac	**98310110LC**
				220/240V	3-6 units	dali	**98310536**
				220/240V	3-6 units	casambi	**98310538**
CLEAR 7W	**02100301**	350mA	7W	100/240V	1-2 units	on/off	**98310620**
				220/240V	2 units	triac	**98310118LC**
				220/240V	1-2 units	dali	**98310536**
				220/240V	1-2 units	casambi	**98310538**
BOW 3W	**02150101**	350mA	3W	100/240V	1-2 units	on/off	**98310620**
				220/240V	2 units	triac	**98310118LC**
				220/240V	2 units	dali	**98310536**
				220/240V	2 units	casambi	**98310538**
BOW 10W	**02150201**	350mA	10W	100/240V	1-2 units	on/off	**98310620**
				220/240V	2 units	triac	**98310321LC**
				220/240V	2 units	dali	**98310536**
				220/240V	2 units	casambi	**98310538**
BOW 18W	**02150301**	350mA	18W	100/240V	only 1 unit	on/off	**98310620**
				220/240V	only 1 unit	triac	**98310321LC**
				220/240V	only 1 unit	dali	**98310536**
				220/240V	only 1 unit	casambi	**98310538**
PLAS 1W	**63281** **63282** **63283** **63490**	350mA	1W	100/240V	only 1 unit	on/off	**98310103**
				220/240V	2-3 units	triac	**98310110LC**
				220/240V	5-17 units	dali	**98310536**
				220/240V	5-17 units	casambi	**98310538**

		mA	P	V	units		
SIGNAL 3W	**02100101**		3W	100/240V	1-2 units	on/off	**98310110**
				220/240V	2-3 units	triac	**98310110LC**
				220/240V	2-6 units	dali	**98310536**
				220/240V	2-6 units	casambi	**98310538**
SIGNAL 3W	**02100101**		3W	100/240V	1-2 units	on/off	**98310110**
				220/240V	2-3 units	triac	**98310110LC**
				220/240V	2-6 units	dali	**98310536**
				220/240V	2-6 units	casambi	**98310538**
TRAS 4W	**71701**	24V DC	4W	100/240V	only 1 unit	on/off	**98324015U**
TRAS 8W	**71702**	24V DC	8W	100/240V	1-2 units	on/off	**98324015U**
TRAS 25W	**71716/71717**	24V DC	25W	100/240V	1-2 units	on/off	**98324030**
DANG 3W	**70446**		3W	100/240V	1-2 units	on/off	**98324006**
NAIS ORIENTABLE 7W	**02111001 02111002**		7W	100/240V	1-2 units	on/off	**98310620**
				220/240V	2 units	triac	**98310118LC**
				220/240V	1-2 units	dali	**98310536**
				220/240V	1-2 units	casambi	**98310538**
SIGNAL 3W	**02100101**		3W	100/240V	1-2 units	on/off	**98310110**
				220/240V	2-3 units	triac	**98310110LC**
				220/240V	2-6 units	dali	**98310536**
				220/240V	2-6 units	casambi	**98310538**
WABI 10W	**43900**		10W	100/240V	only 1 unit	on/off	**98310510C**
				220/240V	only 1 unit	triac	**98310510C**
NORD 18W	**63290**		18W	100/240V	only 1 unit	on/off	**98310118LC**
				220/240V	only 1 unit	triac	**98310118LC**
NAIS 7W	**02121001 02121002**		7W	100/240V	1-2 units	on/off	**98310620**
				220/240V	2 units	triac	**98310118LC**
				220/240V	1-2 units	dali	**98310536**
				220/240V	1-2 units	casambi	**98310538**
GRUND 2W	**70726 70730 70733 70735**	700mA	2W	100/240V	1-2 units	on/off	**98310206E**
				220/240V	2-4 units	triac	**98310210**
				220/240V	4-16 units	dali	**98310536**
				220/240V	4-16 units	casambi	**98310538**
GRUND 7W	**70728 70731 70734 70736**	350mA	7W	100/240V	1-2 units	on/off	**98310620**
				220/240V	2 units	triac	**98310118LC**
				220/240V	2 units	dali	**98310536**
				220/240V	2 units	casambi	**98310538**
GRUND 13W	**70729 70732**	350mA	13W	100/240V	1-2 units	on/off	**98310620**
				220/240V	only 1 unit	triac	**98310118LC**
				220/240V	only 1 unit	dali	**98310536**
				220/240V	only 1 unit	casambi	**98310538**
KANE 3W	**70660 70661 70662**	24V DC	3W	100/240V	1-2 units	on/off	**98324006**
				220/240V	1-3 units	triac	**98311315**
FALLS 6W	**71734 71735**		6W	100/240V	1-2 units	on/off	**98324020U**
				220/240V	5-23 units	triac	**97397**
				220/240V	1-14 units	dali	**97308**
				220/240V	1-14 units	casambi	**98324599**
FALLS 12W	**71736 71737**		12W	100/240V	only 1 unit	on/off	**98324020U**
				220/240V	2-14 units	triac	**97397**
				220/240V	1-6 units	dali	**97308**
				220/240V	1-6 units	casambi	**98324599**
FALLS ORIENTABLE 8W	**71730 71731**		8W	100/240V	1-2 units	on/off	**98324020U**
				220/240V	5-23 units	triac	**97397**
				220/240V	1-11 units	dali	**97308**
				220/240V	1-11 units	casambi	**98324599**
FALLS ORIENTABLE 16W	**71732 71733**		16W	100/240V	only 1 unit	on/off	**98324020U**
				220/240V	2-10 units	triac	**97397**
				220/240V	1-5 units	dali	**97308**
				220/240V	1-5 units	casambi	**98324599**
CROSBY 2W	**70453**		2W	100/240V	1-2 units	on/off	**98324006**

Shades / Pantallas

Wall lamps
Apliques



2P0111



2P0112





2P0113





2P0211





2P0212





2P0213





2P0411





2P0412





2P0413





2P0311





2P0312





2P0313





2P0615





2P0616





2P0617





2P0710





2P0763



Suspended
Suspensión



2P0141





2P0142





2P0143





2P0645





2P0646





2P0647





2P0710





2P0720





2P0730





2P0765





2P0766





2P0767





2P0768





2P0769





2P0764



Shades / Pantallas

Table lamps
Sobremesas



2P0121



2P0122





2P0123





2P0221





2P0222





2P0223





2P0421





2P0422





2P0423





2P0311





2P0312





2P0313





2P0625





2P0626





2P0627





2P0720





2P0763



Floor lamps
Luminarias de suelo



2P0131





2P0132





2P0133





2P0231





2P0232





2P0233





2P0431





2P0432





2P0433





2P0635





2P0636





2P0637





2P0730



Structures / Estructuras

ARTIS wall/*aplique*



68490 bronze/bronce

68491 chrome/cromo

ARTIS wall reader/*aplique con lector*



68492 bronze/bronce

68493 chrome/cromo

ARTIS wall extensible/*aplique extensible*



68494 bronze/bronce

68495 chrome/cromo

CONGA/MAMBO/SAMBA wall/*aplique*



64306 matt white/blanco mate

64307 matt black/negro mate

CONGA/MAMBO/SAMBA wall reader/*aplique con lector*



64308 matt white/blanco mate

64309 matt black/negro mate

CONGA/MAMBO/SAMBA suspended (turnbuckle)/*colgante (tensor)*



64314 matt black/negro mate

CONGA/MAMBO/SAMBA suspended/*colgante*

64315 matt black/negro mate

CONGA/MAMBO/SAMBA table (small)/*sobremesa (pequeña)*



64316 matt white/blanco mate

64317 matt black/negro mate

CONGA/MAMBO/SAMBA table/*sobremesa*



64310 matt white/blanco mate

64311 matt black/negro mate

CONGA/MAMBO/SAMBA floor/*suelo*



64312 matt white/blanco mate

64313 matt black/negro mate

ETERNA wall/*aplique*



24005 chrome/cromo

ETERNA wall reader/*aplique con lector*



24006 chrome/cromo (right)

24007 chrome/cromo (left)

ETERNA table/*sobremesa*



24008 chrome/cromo

FRAME wall/*aplique*



20170 matt nickel/níquel mate

20171 old gold/oro viejo

FRAME wall reader/*aplique con lector*



20172 matt nickel/níquel mate

20173 old gold/oro viejo

MONTREAL wall/*aplique*



24030 white/blanco

24031 chrome/cromo

MONTREAL wall reader/*aplique con lector*



24032 white/blanco

24033 chrome/cromo (left)

MONTREAL table/*sobremesa*



24034 white/blanco

24035 chrome/cromo

MONTREAL floor/*suelo*



24036 white/blanco

24037 chrome/cromo

REM wall/*aplique*



29680 matt nickel/níquel mate

29681 old gold/oro viejo

REM wall reader/*aplique con lector*



29682 matt nickel/níquel mate

29683 old gold/oro viejo

REM table/*sobremesa*



29684 matt nickel/níquel mate

29685 old gold/oro viejo

REM floor/*suelo*



29686 matt nickel/níquel mate

29687 old gold/oro viejo

RON wall/*aplique*



64400 dark grey/gris oscuro

General information / Información general

EN

The technical information detailed in our catalogue can be modified in order to improve the features or design of our products.
Faro Barcelona keeps the right to cancel or modify any model without prior notice and without any cause for complaints.
The conditions, technical characteristics and prices of the products that appear in this catalogue are the effective ones in the date of impression of the catalogue except for typographical error and are subject to possible changes.
The catalogue prices are public prices.
RATES DO NOT INCLUDE VAT.
Returned goods shall only be accepted, after prior notice being given to LOREFAR, on the grounds of being defective and never on the basis of broken glass or missing parts. In such cases, please contact us so that we can send you the required parts as a matter of urgency.
Exchanges or returns of goods in good condition will not be accepted. In the event of express acceptance by LOREFAR, a 20% charge shall be incurred, on receipt and checking, for depreciation and classification of the goods.

ES

La información referente a nuestros productos puede ser modificada con el fin de mejorar las características técnicas o de diseño.
Faro Barcelona se reserva el derecho de anular o modificar cualquier modelo sin previo aviso y sin que sea motivo de reclamaciones.
Las condiciones, características y precios de los productos que aparecen en este catálogo son los vigentes en la fecha de impresión del catálogo salvo error tipográfico y están sujetos a posibles modificaciones.
Los precios mostrados son precios de venta al público (PVP).
IVA NO INCLUIDO EN TARIFA
Previa comunicación a Lorefar sólo se aceptará la mercancía devuelta por defectuosa, nunca por cristales rotos o falta de algún componente. En estos casos rogamos se pongan en contacto con nosotros para enviarles urgentemente las piezas requeridas.
No se admitirán cambios ni devoluciones de mercancía en buen estado. En caso de aceptación explícita por parte de Lorefar, a su recepción y comprobación se emitirá un cargo del 20% en concepto de depreciación y clasificación de la mercancía.

FR

L'information qui se réfère à nos produits peut être modifiée afin d'améliorer les caractéristiques technique ou de design.
Faro Barcelona se réserve le droit d'annuler ou de modifier n'importe quel modèle sans préavis et sans que cela soit motif de réclamations.
Les conditions, caractéristiques et prix des produits qui apparaissent dans ce catalogue sont celles en vigueur à la date d'impression du catalogue sauf erreur typographique et sont susceptible d'être modifiées ultérieurement.
Les prix du catalogue son les prix de vente public .
IVA NON COMPRISE DANS LE TARIF.
Seule sera acceptée en retour la marchandise défectueuse, et ce après communication à LOREFAR. LOREFAR n'acceptera jamais de retour pour du verre brisé ou pour l'absence d'un composant quelconque. Dans ces derniers cas, nous vous prions de vous mettre en contact avec nous afin que nous vous fassions parvenir dans les plus brefs délais les pièces nécessaires. La marchandise en bon état ne sera ni reprise ni échangée. En cas d'acceptation explicite de sa part, LOREFAR retiendra 20% au titre de la dépréciation et de la classification du produit.

ITA

La informazione che si riferisce ai nostri articoli puó essere soggetta a modifiche con il fine du migliorare le caratteristiche, tecniche o di desgin, dei nostri prodotti. Faro Barcelona si reserva il diritto di annullare o modificare qualsiasi modello senza previo avviso e senza che sia motivo di reclami.
Le condizioni, caratteristiche e prezzi dei prodotti che compaiono in questo catalogo sono quelli vigenti alla data della stampa del catalogo ad eccezione di errori tipografici e sono soggetti a possibili modificazioni.
I prezzi indicati sono prezzi di vendita al pubblico.
IVA NON INCLUSA IN LISTINO.
LOREFAR accetta previa comunicazione, solo la merce restituita perché difettosa; in nessun caso accetterà la merce restituita per presenza di verti rotti o per mancanza di qualche componente. In questi casi vi preghiamo di contattarci per potervi mandare al più presto i pezzi richiesti.
Non si effettuano cambi né si ammettono restituzioni di merci in buono stato. In caso di accettazione esplicita da parte di LOREFAR, al momento del ricevimento e della verifica della merce si emetterà un addebito del 20% a titolo di deprezzamento e classificazione.

PT

A informação referente aos nossos produtos pode ser modificada com o fim de melhorar as características técnicas ou de desenho.
A Faro Barcelona reserva-se o direito de anular ou modificar qualquer modelo sem aviso prévio e sem que seja motivo de reclamações.
As condições, características e preços dos produtos que aparecem neste catálogo são os vigentes na data de impressão do catálogo salvo erro tipográfico e estão sujeitos a possíveis modificações. Os preços mostrados são preços de venda ao público (PVP).
IVA NÃO INCLUÍDO NA LISTA DE PREÇOS
Mediante comunicação prévia à Lorefar, apenas se aceitará a mercadoria devolvida por defeito, nunca por vidros partidos ou falta de algum componente. Nestes casos pedimos que entrem em contacto connosco para lhes enviarmos urgentemente as peças requeridas.
Não serão admitidas alterações nem devoluções de mercadoria em bom estado. Em caso de aceitação explícita por parte da Lorefar, na sua recepção e comprovação emitir-se-á um débito de 20% a título de depreciação e classificação da mercadoria.

GER

Die Information über unsere Produkte kann im Zusammenhang mit den Verbesserungen ihrer technischen Eigenschaften und ihres Designs jederzeit geändert werden.
Faro Barcelona behält sich das Recht vor, seine Modelle jederzeit und ohne vorherige Ankündigung vom Markt zu nehmen, ohne dass sich daraus ein Anrecht auf Beschwerden ableiten könnte.
Die Bedingungen, Eigenschaften und Preise der Produkte in diesem Katalog gelten zum Datum der Drucklegung des Katalogs vorbehaltlich Druckfehler und können jederzeit geändert werden. Diese Preise gelten für den Direktverkauf an den Kunden.
DIE MEHRWERTSTEUER IST NICHT IN DEN PREISEN EINGESCHLOSSEN
Nach vorheriger Kommunikation kann Lorefar die Rücklieferung von schadhafter Ware akzeptieren, jedoch niemals wegen beschädigten Glasteilen oder fehlenden Komponenten. In letzteren Fällen setzen Sie sich bitte zwecks schneller Zusendung der notwendigen Teile in Verbindung.
Wir tauschen keine Waren in gutem Zustand um oder nehmen sie zurück. Bei ausdrücklicher Annahme durch Lorefar nach Erhalt und Überprüfung stellen wir Ihnen 20% des Preises für Wertverminderung und Handhabung der Ware in Rechnung.

NL

De informatie over onze producten kan gewijzigd worden met als doel de technische eigenschappen of het design te verbeteren.
Faro Barcelona behoudt zich het recht voor onaangekondigd modellen te schrappen of te wijzigen en zonder dat dit aanleiding tot een klacht vormt.
De voorwaarden, eigenschappen en prijzen van de producten in deze catalogus zijn geldig op het moment van druk van de catalogus tenzij sprake is van een drukfout. Zij zijn onderhevig aan mogelijke wijzigingen. De getoonde prijzen betreffen verkoopprijzen.
Btw NIET BIJ DE PRIJS INBEGREPEN
Lorefar aanvaardt uitlsuitend defecte teruggezonden goederen nadat zij hierover van tevoren op de hoogte is gesteld. Dit geldt niet voor gebroken glas of het ontbreken van onderdelen. In deze gevallen wordt u verzocht met ons contact op te nemen zodat wij u zo snel mogelijk de gewenste onderdelen kunnen toezenden.
Ruilen of terugsturen van goederen in correcte staat is niet toegestaan. In geval van uitdrukkelijke aanvaarding door Lorefar wordt bij ontvangst en controle een heffing van 20% voor waardevermindering en classificatie van de goederen toegepast.

GRK

Οι πληροφορίες σχετικά με τα προϊόντα μας ενδέχεται να τροποποιηθούν με στόχο τη βελτίωση των τεχνικών χαρακτηριστικών ή του σχεδίου.
Η Faro Barcelona διατηρεί το δικαίωμα ακύρωσης ή τροποποίησης οποιουδήποτε μοντέλου χωρίς προηγούμενη προειδοποίηση και χωρίς αυτό να αποτελεί αιτία απαίτησης επιστροφής χρημάτων.
Οι όροι, τα χαρακτηριστικά και οι τιμές των προϊόντων που παρουσιάζονται σε αυτόν τον κατάλογο είναι αυτά που ισχύουν κατά την ημερομηνία της εκτύπωσης του καταλόγου, εκτός τυπογραφικών λαθών, και υπόκεινται σε αλλαγές.
Ο ΦΠΑ ΔΕΝ ΣΥΜΠΕΡΙΛΑΜΒΑΝΕΤΑΙ ΣΤΗΝ ΤΙΜΗ
Μετά από συνεννόηση με τη Lorefar, γίνονται αποδεκτές επιστροφές μόνο αν πρόκειται για ελαττωματικά εμπορεύματα και όχι για θραύση κρυστάλλων ή απουσία κάποιου στοιχείου. Στις περιπτώσεις αυτές, παρακαλούμε να έρθετε σε επαφή μαζί μας για να σας στείλουμε επειγόντως τα απαιτούμενα μέρη.

RUS

Информация относящаяся к нашей продукции может быть модифицирована с целью улучшить технические или внешние характеристики.
Faro Barcelona сохраняет за собой право анулировать или модифицировать любую модель без предупреждения и без того что это послужит причиной для жалоб.
Условия, характеристики и цены на изделия, указанные в данном каталоге, действительны на дату его выпуска, за исключением опечаток в каталоге, и могут быть изменены. В каталоге указаны розничные цены.
БЕЗ УЧЕТА НДС
В соответствии с правилами, компания Lorefar принимает возврат изделий только при наличии дефектов, но ни в коем случае не при разбитии стекла или отсутствии какой-либо детали. В таком случае, пожалуйста, свяжитесь с нами, чтобы мы отправили вам необходимые детали. Товар в рабочем состоянии не подлежит обмену или возврату. В случае подтверждения компанией Lorefar наличия дефектов, после возврата и проверки, начисляется 20% стоимости с учетом амортизации и классификации товаров.

CZ

Technické informace uvedené v katalogu mohou být modifikovány za účelem zdokonalování vlastností svítidel nebo jejich designu.
Producent Faro Barcelona si vyhrazuje právo konstrukčních změn nabízených modelů bez předcházejícího oznámení a tato skutečnost nemůže být předmětem jakékoliv stížnosti či reklamace.
Podmínky, technické specifikace a ceny produktů uvedené v katalogu jsou platné ke dni vydání katalogu. Producent si vyhrazuje právo konstrukčních změn nabízených modelů, pokud tyto nepovedou k zásadním změnám charakteru výrobků. Informace z tohoto katalogu postrádají platnosti v den vydání katalogu nového.
VŠECHNY CENY JSOU UVEDENY BEZ DPH.,
Zboží může být vráceno pouze po předchozím souhlasu od sPOLEčnosti PAXI, na základě poruchy nebo vady ovšem nikdy na základě poškozeného skla nebo chybějícího dílu. V takových případech nás, prosím, kontaktujte, abychom
Vám mohli požadované části svítidel urgentně zaslat. Výměny nebo vracení zboží v dobrém technickém stavu je nepřijatelné.

BL

Техническата информация, представена в нашият каталог , може да бъде променяна с цел да подобри представянето или дизайна на продуктите.
Фаро Барселона си запазва правото да отменя или променя всеки модел без предварително осведомяване и без това да се счита причина за оплаквания.
Условията, техническите характеристики и цените на продуктите показани в този каталог са ефективни към датата на отпечатването на каталога, с изключение на грешки при отпечатване и са обект на възможни промени.
Цените в каталога са публичните цени.
ЦЕНИТЕ НЕ ВКЛЮЧВАТ ДДС.
Връщане на закупена стока ще да бъдат приета единствено след писмено осведомяване на ЛОРЕФАР на основание дефекти и в никакъв случай на основание счупено стъкло или липсващи части. В такива случаи моля свържете те с нас, за да ви изпратим липсващите части по спешност.
Размяна или връщане на стока в добро състояние няма да бъде извършвана. В случай на спешно приемане от ЛОРЕФАР 20 % такса ще бъде наложена за приемане и проверка, за обезценяване и класификация на продуктите.

PL

Informacje techniczne wyszczególnione w naszym katalogu mogą być modyfikowane w celu poprawienia właściwości lub wzornictwa produktów.
Faro Barcelona ma prawo do anulowania i modyfikowania każdego z modeli bez uprzedniego infomowania i nie przyjmuje skarg z tego tytułu.
Warunki, opis techniczny oraz ceny artykułów , które pojawiają się w katalogu są aktualne do czasu przedruku katalogu za wyjątkiem pomyłek w druku, które podlegają ewentualnej zmianie. Ceny w katalogu są cenami publicznymi.
CENY NIE ZAWIERAJĄ STAWKI VAT.
Ewentualne zwroty mogą być zaakceptowane po uprzedniej zgodzie przez Lorefar na podstawie stwierdzenia , że są wadliwe, nigdy nie przyjmowane są zwroty artykułów, z powodu stłuczenia szkła czy brakujących części, w tym przypadku prosimy o kontakt w celu wysłania potrzebnych części w trybie natychmiastowym.
Wymiany lub zwroty artykułów w dobrym stanie nie będą zaakceptowane. W przypadku wyraźnej akceptacji przez Lorefar, 20% opłaty może być poniesione na otrzymanie i sprawdzenie, w celu sklasyfikowania uszkodzenia artykułu.

Materials / Materiales

EN	ES	FR	ITA
ABS	ABS	ABS	ABS
Acrylic	Acrílico	Acrylique	Acrilico
Aluminium	Aluminio	Aluminium	Alluminio
Beige Ribbon Shade	Tela encintada	Tissu adhésif	Tessuto registrato
Bubble Glass	Cristal Burbuja	Verre bullé	Vetro bolla
Brass	Latón	Laiton	Ottone
Die Cast Aluminium	Aluminio Inyectado	Fonte d'aluminium	Ghisa alluminio
Fiber Glass	Fibra de Vidrio	Fibre De Verre	Fibra Di Vetro
Glass	Cristal	Verre	Vetro
Leather	Piel	Peau	Pelle
Linen	Lino	Lin	Biancheria
Marble	Mármol	Marbre	Marmo
Opal Acrylic	Acrílico Opal	Acrylique opale	Acrilico opale
Opal Glass	Cristal Opal	Verre opale	Vetro opalino
Opal PMMA	PMMA Opal	PMMA opale	PMMA opale
Opal Polycarbonate	Policarbonato Opal	Polycarbonate opale	Policar-bonato opale
Opal PVC	PVC Opal	PVC opale	PVC opale
Papyrus	Papiro	Papyrus	Papiro
Parchment	Pergamino	Parchemin	Pergamena
PEMD	PEMD	PEMD	PEMD
PET Polyethylene Terephthalate	PET Polietileno tereftalato	PET Polyéthylène téréphtalate	PET polietilene tereftalato
Plaster	Yeso	Gypse	Gesso
PMMA	PMMA	PMMA	PMMA
Polycarbonate	Policarbonato	Polycarbonate	Policarbonato
Polyethylene	Polietileno	Polyéthylène	Polietilene
Polymer	Polímero	Polymères	Polimero
Polypropylene	Polipropileno	Polyéthylène	Polietilene
PVC	PVC	PVC	PVC
Rattan	Ratán	Rotin	Malacca
Resine	Resina	Résine	Resina
Rustic Glass	Cristal Rústico	Verre rustique	Vetro rustico
Silicone	Silicona	Silicone	Silicone
Stainless Steel	Acero Inoxidable	Acier inoxydable	Acciaio inossi.
Steel	Acero	Acier	Acciaio
Teflon	Teflón	Teflon	Teflon
Textile	Téxtil	Textile	Tessile
Translucent Glass	Cristal Translúcido	Verre translucide	Vetro traslucido
Translucent Polycarbonate	Policarbonato Translúcido	Polycarbonate translucide	Policar-bonato transl.
Transparent Glass	Cristal Transparente	Verre transparent	Vetro trasparente
Transparent PMMA	PMMA Transparente	PMMA transparent	PMMA trasparente
Wood	Madera	Bois	Legno
Zinc	Zinc	Zinc	Zinco

Symbology / Simbología

	EN	ES	FR	ITA
	Switch / Double Switch	Interruptor / Doble Interruptor	Interrupteur / Double Interrupteur	Interruttore / Doppio Interruttore
	USB Charger	Cargador USB	Chargeur USB	Caricatore USB
	Adjustable	Orientable	Orientable	Regolabile
	Dimmable	Dimable	Réglable	Regolabile
	Recessed box	Caja empotrar	Boîte encastrée	Incasso box
	Passive Infrared sensor (PIR)	Detector de movimineto pasivo (PIR)	Capteur infrarouge passif (PIR)	Sensore passivo a infrarossi (PIR)
	Leading & Trailing-edge dimming	Regulación con regulador de corte al inicio y/o al final de fase	Gradation avant et arrière	Dimmer iniziale e finale

Ref	Page
01001	269
01003	345
01004	345
01005	345
01006	345
01007A	72
01009A	278
01014A	278
01015	45
01016	45
01017	45
01025A	72
01026A	278
01027A	278
01040	370
01041	370
01045	270
01046	142
01205	368
01206	368
01207	368
01208	368
02100101	410
02100101C	410
02100301	422
02100501	428
02100502	428
02100503	428
02100601	430
02100602	430
02100603	430
02100701	428
02100702	428
02100801	422
02100901	427
02101001	426
02101002	426
02101101	426
02101102	426
02101301	426
02101302	426
02101401	430
02101402	430
02101501	427
02101601	427
02111001	421
02111002	421
02121001	421
02121002	421
02200501	428
02200502	428
02200503	428
02300101	430
02400101	430
02400102	430
17064	815
17067	815
17070	815
17071	816
17072	816
17073	816
17271	816
17309	814
17316	814
17317	814
17318	814
17319	814
17320	814
17321	814
17324	814
17325	814
17328	814
17329	814
17330	814
17331	814
17332	814
17340	817
17398	817
17399	817
17400	817
17409	816
17413	816
17414	816
17415	815
17417	815
17420	815
17422	815
17423	815
17425	816
17426	816
17427	816
17428	816
17429	816
17432	816
17433	816
17434	816
17437	815
17443	817
17444	817
17445	816
17446	816
17447	816
17449	816
17460	815
17461	815
17462	815
17463	815
17464	815
17465	815
17466	817
17467	817
17468	817
17472	814
17473	814
17474	814
17475	814
17477	817
17479	815
17482	815
17485	815
17486	815
17487	817
17488	817
17490	817
17491	817
17493	816
17494	817
17495	817
17496	816
17497	817
17498	814
17499	817
18030	814
18031	814
18032	814
18033	814
18034	814
18035	814
20021	314
20023	314
20024	314
20025	136
20026	136
20029	136
20030	136
20031-80	272
20031-81	272
20031-88	304
20032-80	272
20032-81	272
20032-88	304
20033-80	94
20033-81	94
20034-80	94
20034-81	94
20034-88	128
20045	367
20046	166
20046-3L	216
20046-5L	216
20046-7L	216
20047	166
20048	166
20049	367
20050	166
20050-3L	216
20050-5L	216
20050-7L	216
20051	166
20060	276
20061	276
20062	276
20065	274
20066	274
20094	228
20095	228
20116	160
20117	160
20118	160
20119	160
20120	160
20121	160
20122	160
20123	160
20124	160
20125	160
20126	160
20127	160
20128	160
20129	160
20130	160
20131	160
20160	170
20160-3L	218
20160-5L	218
20160-7L	218
20161	170
20161-3L	218
20161-5L	218
20161-7L	218
20164-95	140
20164-96	140
20165-95	266
20165-96	266
20166-95	170
20166-96	170
20167	266
20168	266
20170	824
20170-01	302
20170-02	302
20170-03	302
20171	824
20171-01	302
20171-02	302
20171-03	302
20172	824
20172-01	302
20172-02	302
20172-03	302
20173	824
20173-01	302
20173-02	302
20173-03	302
20201	150
20203	150
20204	254
20207	150
20208	46
20209	46
20210	46
20300-92	286
20301-93	286
20301-94	286
20302-92	286
20303-93	286
20303-94	286
20304-82	118
20305-83	118
20305-84	118
20306-85	118
20307-86	118
20307-87	118
20308-89	196
20309-90	196
20309-91	196
20330	265
20331	265
20332	265
20335-116	257
20335-117	257
20336-119	84
20336-120	84
20337-116	84
20337-117	84
20338-116	156
20338-117	156
20338-119	156
20338-120	156
20339-116	156
20339-117	156
20339-119	156
20339-120	156
20340-116-3L	219
20340-116-5L	219
20340-116-7L	219
20340-117-3L	219
20340-117-5L	219
20340-117-7L	219
20340-119-3L	219
20340-119-5L	219
20340-119-7L	219
20340-120-3L	219
20340-120-5L	219
20340-120-7L	219
23001-57	88
23001-58	88
23002-57	88
23002-58	88
23003-59	88
23003-60	88
23004-57	244
23004-58	244
24005	824
24005-10	298
24005-11	298
24005-12	298
24006	824
24006-10	298
24006-11	298
24006-12	298
24007	824
24007-10	298
24007-11	298
24007-12	298
24008	824
24008-13	74
24008-14	74
24008-15	74
24015	339
24016	339
24020-31	108
24020-32	108
24023-33	108
24023-34	108
24030	824
24030-01	288
24030-02	288
24031	824
24031-01	288
24031-02	288
24031-03	288
24032	824
24032-01	288
24032-02	288
24033	824
24033-01	288
24033-02	288
24033-03	288
24034	824
24034-04	116
24034-05	116
24035	824
24035-04	116
24035-05	116
24035-06	116
24036	824
24036-07	116
24036-08	116
24037	824
24037-07	116
24037-08	116
24037-09	116
24502	268
24504	166
24521	92
24522	92
24527	271
24528	271
28200	250
28202	90
28204	90
28205	90
28209	172
28209-1L	174
28209-2L	174
28209-3L	174
28209-4L	175
28209-5L	175
28210	172
28210-1L	174
28210-2L	174
28210-3L	174
28210-4L	175
28210-5L	175
28211	73
28212	73
28365	48
28366	48
28367	48
28368	48
28369	48
28370	106
28371	106
28372	68
28373	175
28374	175
28375	172
28375-1L	174
28375-2L	174
28375-3L	174
28375-4L	175
28375-5L	175
28376	172
28376-1L	174
28376-2L	174
28376-3L	174
28376-4L	175
28376-5L	175
28378	73
28379	73
28380	74
28382	74
28383	74
28385	74
28387	70
28388	70
28394	198
28398	200
28399	200
28401	76
28413	322
28414	322
28415	322
28480	251
28481	251

Ref	Page
29039	396
29040	396
29042	396
29043	396
29044	396
29047	104
29048	104
29049	104
29306	367
29307	126
29309	198
29310	367
29311	126
29312	126
29313	198
29326	318
29328	318
29329	318
29330	318
29331	318
29332	132
29333	132
29335	132
29336	132
29341	326
29395	282
29396	282
29397	164
29398	98
29399	98
29468	200
29565	282
29566	282
29567	164
29568	98
29569	98
29680	824
29680-19	300
29680-20	300
29680-21	300
29681	824
29681-19	300
29681-20	300
29681-21	300
29682	824
29682-19	300
29682-20	300
29682-21	300
29683	824
29683-19	300
29683-20	300
29683-21	300
29684	824
29684-04	120
29684-05	120
29684-06	120
29685	824
29685-04	120
29685-05	120
29685-06	120
29686	824
29686-07	120
29686-08	120
29686-09	120
29687	824
29687-07	120
29687-08	120
29687-09	120
29690	264
29691	168
29692D	96
29693D	96
29694	168
29695	264
29696	168
29697	96
29698	96
29699	168
29764	146
29844	280
29845	280
29846	100
29847	100
29848	162
29849	162
29864	198
29865	198
29866	130
29867	130
29868	130
29869	130
29871	436
29872	436
29873	404
29874	404
29875	404
29876	404
29877	230
29878	230
29881	102
29882	102
29883	102
29884	102
29888	372
29894	208
29895	208
29896	436
29897	404
29898	102
29899	102
29935	320
29936	320
29940	310
29941	310
29942	134
29944	198
29945	310
29946	310
29947	134
29948	134
29950	320
29951	320
29952	320
29953	320
29955	145
29958	145
29974	312
29975	312
29976	312
29979	124
29980	316
29981	316
29982	316
29983	316
29984	124
29985	124
29986	196
29987	196
29988	196
29996	304
29997	128
29998	128
2P0111	820
2P0112	820
2P0113	820
2P0121	822
2P0122	822
2P0123	822
2P0131	823
2P0132	823
2P0133	823
2P0141	821
2P0142	821
2P0143	821
2P0211	820
2P0212	820
2P0213	820
2P0221	822
2P0222	822
2P0223	822
2P0231	823
2P0232	823
2P0233	823
2P0311	820
2P0312	820
2P0313	820
2P0411	820
2P0412	820
2P0413	820
2P0421	822
2P0422	822
2P0423	822
2P0431	823
2P0432	823
2P0433	823
2P0615	820
2P0616	820
2P0617	820
2P0625	822
2P0626	822
2P0627	822
2P0635	823
2P0636	823
2P0637	823
2P0645	821
2P0646	821
2P0647	821
2P0710	820
2P0720	821
2P0730	821
2P0763	820
2P0764	821
2P0765	821
2P0766	821
2P0767	821
2P0768	821
2P0769	821
32000	771
32000-9	771
32000WP	771
32000WP-9	771
32001	771
32001-9	771
32001WP	771
32001WP-9	771
32002	771
32002-10	771
32002WP	771
32002WP-10	771
32003	771
32003-10	771
32003WP	771
32003WP-10	771
32004	771
32004-10	771
32004WP	771
32004WP-10	771
32005	771
32005-9	771
32005WP	771
32005WP-9	771
32006	771
32006-10	771
32006WP	771
32006WP-10	771
32020	769
32020-9	769
32020WP	769
32020WP-9	769
32025	769
32025-9	769
32025WP	769
32025WP-9	769
32026	769
32026-10	769
32026WP	769
32026WP-10	769
32027	769
32027-10	769
32027WP	769
32027WP-10	769
32028	769
32028-10	769
32028WP	769
32028WP-10	769
32029	769
32029-9	769
32029WP	769
32029WP-9	769
32030	769
32030-10	769
32030WP	769
32030WP-10	769
32033	779
32033-9	779
32033WP	779
32033WP-9	779
32034	779
32034-9	779
32034WP	779
32034WP-9	779
32035	779
32035-10	779
32035WP	779
32035WP-10	779
32036	779
32036-10	779
32036WP	779
32036WP-10	779
32037	779
32037-10	779
32037WP	779
32037WP-10	779
32038	777
32038-9	777
32038WP	777
32038WP-9	777
32039	777
32039-9	777
32039WP	777
32039WP-9	777
32040	777
32040-10	777
32040WP	777
32040WP-10	777
32041	777
32041-10	777
32041WP	777
32041WP-10	777
32042	777
32042-10	777
32042WP	777
32042WP-10	777
32043	777
32043-10	777
32043WP	777
32043WP-10	777
32060	779
32060-10	779
32060WP	779
32060WP-10	779
32100	773
32100-10	773
32100WP	773
32100WP-10	773
33001	714
33002	714
33005	788
33011	800
33019	758
33102	796
33110	715
33111	715
33179	807
33180	807
33183	807
33185	807
33186	807
33284	756
33346	749
33346WP	749
33349	695
33350	757
33351	757
33352	760
33352B	760
33370DC	741
33370DCWP	741
33373DC	741
33373DCWP	741
33374	779
33374-9	779
33374WP	779
33374WP-9	779
33381	771
33381-9	771
33381WP	771
33381WP-9	771
33382	769
33382-9	769
33382WP	769
33382WP-9	769
33385	753
33386	753
33390	811
33391	811
33393	777
33393-9	777
33393WP	777
33393WP-9	777
33394	773
33394-9	773
33394D	775
33394D-9	775
33394DWP	775
33394DWP-9	775
33394WP	773
33394WP-9	773
33395	773
33395-10	773
33395D	775
33395D-10	775
33395DWP	775
33395DWP-10	775
33395WP	773
33395WP-10	773
33398	773
33398-10	773
33398D	775
33398D-10	775
33398DWP	775
33398DWP-10	775
33398WP	773
33398WP-10	773
33399	773
33399-10	773
33399D	775
33399D-10	775
33399DWP	775
33399DWP-10	775
33399WP	773
33399WP-10	773
33414A	691
33415	797
33416	797
33417	773
33417-10	773
33417WP	773
33417WP-10	773
33418	773
33418-10	773
33418WP	773
33418WP-10	773
33423	805
33423-10	805
33423WP	805

Ref	Page
33423WP-10	805
33424	805
33424-10	805
33424WP	805
33424WP-10	805
33425	805
33425-10	805
33425WP	805
33425WP-10	805
33426	805
33426-9	805
33426WP	805
33426WP-9	805
33427	805
33427-10	805
33427WP	805
33427WP-10	805
33428	805
33428-10	805
33428WP	805
33428WP-10	805
33429	805
33429-10	805
33429WP	805
33429WP-10	805
33430	697
33430WP	697
33432	697
33432WP	697
33446	731
33446WP	731
33447	731
33447WP	731
33450	808
33451	767
33451WP	767
33460	745
33461A	691
33462A	691
33463	699
33464DC	699
33464DCWP	699
33465A	691
33466A	701
33470	751
33471K	811
33471N	750
33471N-3	750
33472K	811
33472N	752
33472N-6	752
33478	781
33478WP	781
33479	781
33480	765
33480-14	765
33480WP	765
33480WP-14	765
33481	783
33481-7	783
33481WP	783
33481WP-7	783
33482	783
33482-8	783
33482WP	783
33482WP-8	783
33483	811
33484	811
33486	811
33487	781
33487WP	781
33488	781
33489	765
33489-15	765
33489K	811
33489WP	765
33489WP-15	765
33490	765
33490-16	765
33490K	811
33490WP	765
33490WP-16	765
33491K	811
33492K	811
33494	689
33494WP	689
33495	689
33495WP	689
33496	685
33504DC	699
33504DCWP	699
33505DC	699
33505DCWP	699
33506	713
33507	713
33508DC	795
33508DCWP	795
33509DC	795
33509DCWP	795
33511	711
33511WP	711
33512A	693
33512A-1	693
33512WPA	693
33512WPA-1	693
33513	811
33514	761
33514WP	761
33516DC	741
33516DCWP	741
33517DC	795
33517DCWP	795
33518DC	741
33518DCWP	741
33519	711
33519WP	711
33522	737
33522WP	737
33523	737
33523WP	737
33524	739
33524WP	739
33525	808
33548	716
33548WP	716
33549	707
33549WP	707
33551	709
33551WP	709
33552	709
33552WP	709
33553A	703
33553WPA	703
33554A	703
33554WPA	703
33560DC	741
33560DCWP	741
33561DC	741
33561DCWP	741
33562DC	741
33562DCWP	741
33600	792
33604	793
33606	798
33607	785
33608	785
33695	791
33696	791
33697	791
33698	791
33699	791
33700	755
33701	755
33702	755
33703	801
33704	803
33705	755
33706	803
33710	759
33710-13	759
33711	787
33711-11	787
33712	787
33712-12	787
33713	787
33713-13	787
33714	811
33715	809
33716	811
33717	811
33718	705
33719	705
33720	809
33721	743
33721WP	743
33722	743
33722WP	743
33724	746
33724WP	746
33725	717
33726	717
33727	705
33728	705
33729	733
33729WP	733
33750	747
33756	789
33756WP	789
33760	721
33760-22	723
33760-25	725
33760WP	721
33760WP-22	723
33760WP-25	725
33761	721
33761-23	723
33761-26	725
33761WP	721
33761WP-23	723
33761WP-26	725
33762	721
33762-24	723
33762-27	725
33762WP	721
33762WP-24	723
33762WP-27	725
33770	748
33770WP	748
33782	730
33802	735
33802WP	735
33803	734
33803WP	734
33804	732
33804WP	732
33805	802
33805WP	802
33806	802
33806WP	802
33809	719
33809WP	719
33810	719
33810WP	719
33814	763
33814-20	763
33814WP	763
33814WP-20	763
33815	763
33815-21	763
33815WP	763
33815WP-21	763
33816	763
33816-20	763
33816WP	763
33816WP-20	763
33817	763
33817-21	763
33817WP	763
33817WP-21	763
33904	810
33928	811
33929	810
33937	810
33944	810
33948	810
33954	810
33957	810
33958	810
33959	810
33960	810
33962	810
33964	810
33965	810
33971	810
33974	811
34000	691
34001	691
34002	691
34003	701
34004	701
34005	701
34006	691
34007	691
34008	691
34009	691
34010	691
34011	691
34012	691
34013	691
34014	691
34100	729
34100WP	729
34200A	687
34200WPA	687
34250A	683
34260	727
34261	727
34300	799
34300WP	799
40070	364
40076	382
40077	240
40078	202
40085	382
40086	382
40087	382
40088	382
40090	262
40091	262
40092	262
40093	262
40095	260
40096	260
40097	260
40098	260
40099	260
40102	256
40103	256
40104	256
40110	414
40111	414
40112	415
40113	415
40114	414
40115	414
40116	415
40117	415
40118	414
40119	414
40120	415
40121	415
40122	416
40123	416
40124	416
40125	416
40126	416
40127	416
40135	348
40136	348
40550	404
40551	404
40660	398
40661	398
40662	398
40663	398
40664	398
40665	398
40666	398
40667	398
40994	333
40996	333
41019	333
41020	333
41023	337
41025N	334
41026	336
41028	336
41029	336
41030	336
41031	336
41032	336
42919	424
42921	421
42926	433
42927	433
42928	432
42929	432
42930	432
42931	433
43396	418
43397	418
43398	418
43399	420
43400	420
43401	419
43402	419
43403	419
43404	420
43405	420
43406	418
43407	418
43408	418
43409	420
43410	420
43411	419
43412	419
43413	419
43500	400
43501	400
43502	400
43520	402
43521	402
43522	402
43523	402
43525	402
43527	402
43528	402
43529	230
43531	230
43533	230
43534	230
43536	436
43600	422
43601	422
43720	438
43721	438
43722	392
43723	392
43724	438
43725	438
43726	392
43727	392
43728	392
43729	392
43730	392
43731	392

Ref	Page
43732	392
43740	394
43741	394
43742	394
43743	394
43744	394
43745	394
43746	235
43747	235
43748	372
43749	372
43750	372
43751	372
43752	424
43753	424
43754	208
43755	208
43756	208
43757	438
43758	235
43759	372
43760	372
43761	424
43762	392
43900	424
51129	335
51133	335
51134	335
51135	335
51908	82
51909	82
51910	82
51916	82
51917	82
52057	80
52058	80
52059	334
52061	334
52064	80
52065	80
52071	78
53415	78
53416	78
57211-01	138
57211-02	138
57211-03	138
57300	248
57301	248
57302	248
57312	66
57313	66
57314	66
57315	66
57316	66
57317	66
57318	248
57319	248
57320	248
57400	80
57401	80
57402	366
57403	366
60000	366
60004	205
60005	363
61080	380
61081	380
61082	380
61083	380
61084	380
61085	380
61086	380
61087	380
61088	380
61101	158
61103	158
61104	158
61105	158
61117	158
62099	307
62100	307
62104	340
62105	350
62108	350
62111	340
62114	340
62115	330
62116	340
62117	340
62118	340
62120	340
62121	340
62122	342
62123	342
62124	342
62125	342
62126	340
62128	340
62129	340
62130	347
62131	347
62132	226
62133	226
62134	226
62135	226
62138	183
62139	183
62140	226
62141	226
62142	226
62143	226
62144	226
62145	226
62146	226
62147	226
62150	361
62151	361
62152	361
62153	361
62154	361
62155	361
62156	71
62157	71
62161	331
62162	331
62163	331
62164	331
62168	71
62169	71
62170	360
62171	360
62172	360
62173-50	246
62173-51	246
62173-52	246
62173-69	258
62173-78	258
62174-50	246
62174-51	246
62174-52	246
62174-69	258
62174-78	258
62300	362
62301	362
62302	362
62303	362
62350	338
62351	338
62352	338
62353	338
62355	346
62360	344
62361	344
62703	337
62704	337
62705	324
62706	324
62707	332
62708	332
62709	332
62710	332
62711	332
62800	206
62801	206
62802	206
62802-3L	218
62802-5L	218
62802-7L	218
62803	206
62803-3L	218
62803-5L	218
62803-7L	218
62804	206
62804-3L	218
62804-5L	218
62804-7L	218
62805	206
62805-3L	218
62805-5L	218
62805-7L	218
62806	207
62807	366
62809	363
62810	363
62819	374
62820	374
62821	374
62822	374
62965	239
62966	239
62968	240
62969	240
62980	239
62981	239
62983	240
62986	381
62987	381
62988	324
63124	234
63125	234
63156	381
63167	362
63173	376
63174	376
63175	376
63176	377
63177	377
63178	377
63184	379
63225	379
63268	233
63269	233
63270	232
63271	232
63272	232
63273	232
63274	232
63275	232
63276	232
63277	232
63278	374
63279	378
63281	412
63282	412
63283	412
63284	374
63285	378
63286	410
63290	410
63291	239
63311	379
63312	379
63313	408
63316	389
63317	389
63318	389
63319	389
63393	237
63394	237
63395	237
63397	238
63398	238
63399	239
63404	238
63408	238
63410	238
63480	378
63481	411
63490	412
63502	384
63503	384
63504	384
63505	384
63506	384
63507	386
63508	386
63509	386
63510	382
63512	386
63513	386
63514	386
63600	388
63601	388
63602	388
63603	388
63604	388
63605	388
64026	350
64027	263
64028	263
64030	348
64096	228
64097	228
64099	176
64128	204
64128-3L	217
64128-5L	217
64128-7L	217
64133	205
64133-3L	217
64133-5L	217
64133-7L	217
64135-3L	217
64135-5L	217
64135-7L	217
64137	204
64137-3L	217
64137-5L	217
64137-7L	217
64159	210
64160	210
64162	210
64168	334
64169	334
64172	182
64174	212
64182	228
64183	228
64188	240
64188N	240
64198	233
64199	233
64200	233
64201	233
64202	438
64203	438
64204	234
64205	234
64206	234
64207	234
64210A	439
64211A	439
64212A	439
64213A	439
64214A	439
64215A	439
64223	210
64224	210
64231	220
64232	220
64250	228
64251	228
64255	154
64255-111-3L	219
64255-111-5L	219
64255-111-7L	219
64255-112-3L	219
64255-112-5L	219
64255-112-7L	219
64255-113-3L	219
64255-113-5L	219
64255-113-7L	219
64255-114-3L	219
64255-114-5L	219
64255-114-7L	219
64255-115-3L	219
64255-115-5L	219
64255-115-7L	219
64256	154
64257	154
64258	154
64259	154
64260	176
64261	176
64262	176
64263	176
64270	252
64271	252
64272	252
64273	252
64274	252
64275-111	86
64275-112	86
64275-113	86
64275-114	86
64275-115	86
64276-111	86
64276-112	86
64276-113	86
64276-114	86
64276-115	86
64277	224
64278	224
64279	224
64280	224
64281	224
64282	224
64300	326
64301	326
64302	308
64303	308
64304	308
64305	308
64306	824
64306-01	290
64306-02	290
64306-35	284
64306-36	284
64306-37	284
64307	824
64307-03	290
64307-35	284
64307-36	284
64307-37	284
64307-47	294
64307-71	292
64308	824
64308-01	290
64308-02	290
64308-35	284
64308-36	284
64308-37	284
64309	824
64309-03	290
64309-35	284
64309-36	284

Ref	Page
64309-37	284
64309-47	294
64309-71	292
64310	824
64310-04	114
64310-05	114
64310-38	112
64310-39	112
64310-40	112
64311	824
64311-06	114
64311-38	112
64311-39	112
64311-40	112
64311-48	110
64312	824
64312-07	115
64312-08	115
64312-41	113
64312-42	113
64312-43	113
64313	824
64313-09	115
64313-41	113
64313-42	113
64313-43	113
64313-49	111
64314	824
64314-44	194
64314-44-3L	216
64314-44-5L	216
64314-44-7L	216
64314-45	194
64314-45-3L	216
64314-45-5L	216
64314-45-7L	216
64314-46	194
64314-46-3L	216
64314-46-5L	216
64314-46-7L	216
64314-47	192
64314-47-3L	215
64314-47-5L	215
64314-47-7L	215
64314-48	192
64314-48-3L	215
64314-48-5L	215
64314-48-7L	215
64314-49	192
64314-49-3L	215
64314-49-5L	215
64314-49-7L	215
64314-54	194
64314-54-3L	216
64314-54-5L	216
64314-54-7L	216
64314-55	194
64314-55-3L	216
64314-55-5L	216
64314-55-7L	216
64314-56	194
64314-56-3L	216
64314-56-5L	216
64314-56-7L	216
64315	824
64315-44	194
64315-45	194
64315-46	194
64315-47	190
64315-48	190
64315-49	190
64315-54	194
64315-55	194
64315-56	194
64316	824
64316-01	114
64316-02	114
64316-35	112
64316-36	112
64316-37	112
64317	824
64317-03	114
64317-35	112
64317-36	112
64317-37	112
64317-47	110
64317-71	76
64318	333
64319	333
64320	208
64321	208
64322	327
64323	327
64400-10	306
64400-11	306
64400-12	306
64500	180
64501	180
65071	204
65080	204
65080-3L	217
65080-5L	217
65080-7L	217
65081	202
65082	202
65133	364
65134	204
65134-72	186
65134-73	188
65134-74	188
65134-75	188
65134-76	186
65134-77	186
65137	234
66205	205
66400	824
66400-101	352
66400-102	352
66400-105	352
66400-106	352
66400-97	352
66400-98	352
66401-100	354
66401-103	354
66401-104	354
66401-107	354
66401-108	354
66401-109	354
66401-110	354
66401-99	354
66403	358
66404	358
66405	356
66406	356
66407	356
66408	356
66409	356
66410	356
66411	358
66412	358
66413	358
66414	358
66415	358
66416	358
68145	205
68145-3L	216
68145-5L	216
68145-7L	216
68146	205
68146-3L	216
68146-5L	216
68146-7L	216
68153	207
68283	212
68284	212
68298	236
68317	236
68323	236
68334	82
68423	76
68461	200
68462	146
68463	146
68467	328
68468	328
68488	122
68489	122
68490	824
68490-01	296
68490-02	296
68490-03	296
68491	824
68491-01	296
68491-02	296
68491-03	296
68492	824
68492-01	296
68492-02	296
68492-03	296
68493	824
68493-01	296
68493-02	296
68493-03	296
68494	824
68494-01	296
68494-02	296
68494-03	296
68495	824
68495-01	296
68495-02	296
68495-03	296
68496	332
68497	332
68498	332
68499	332
68500	144
68501	144
68503	144
68504	327
68505	327
68506	327
68507	327
68508	332
68509	332
68544	324
68561	200
68562	200
68563	200
68564	200
68569	207
68590-69	184
68590-70	184
68591-1L	178
68591-3L	215
68591-5L	215
68591-7L	215
68592-1L	178
68592-3L	215
68592-5L	215
68592-7L	215
68593-1L	178
68593-3L	215
68593-5L	215
68593-7L	215
68594-1L	178
68594-3L	215
68594-5L	215
68594-7L	215
68595-1L	178
68595-3L	215
68595-5L	215
68595-7L	215
68596-1L	178
68596-3L	215
68596-5L	215
68596-7L	215
68597-1L	178
68597-3L	215
68597-5L	215
68597-7L	215
68600-50	152
68600-51	152
68600-52	152
68600-53	152
68602	220
68604-44	221
68604-45	221
68604-46	221
68604-47	221
68604-48	221
68604-49	221
68604-54	221
68604-55	221
68604-56	221
68604-62	221
68604-63	221
68604-64	221
68604-65	221
68604-66	221
68604-67	221
68604-68	221
70025	550
70035	546
70036	546
70037	546
70038	546
70134	644
70135	644
70140	554
70146	651
70147	651
70148	651
70151	544
70156	555
70157	555
70158	542
70159	542
70161	554
70162	648
70163	648
70226	542
70227	542
70233	530
70245	537
70246	537
70247	504
70248	540
70260	555
70264	624
70265	642
70267	624
70268	624
70269	625
70270	625
70271	650
70272	646
70272N	646
70273	646
70273N	646
70274	646
70275	646
70276	646
70277	646
70277N	646
70278	646
70278N	646
70279	646
70280	646
70281	646
70283	618
70284	618
70285	633
70286	633
70287	633
70290	584
70291	584
70292	504
70293	504
70294	583
70295	464
70302	659
70303	659
70304	658
70305	658
70306	659
70307	659
70308	659
70309	659
70310	658
70395	642
70396	642
70397	643
70398	642
70399	642
70402	648
70403	648
70405	620
70406	620
70408	632
70409	632
70446	643
70449	662
70453	655
70455	662
70459N	655
70462N	655
70469	544
70496	52
70498	60
70499	60
70501	636
70508	636
70546	634
70547	634
70564	634
70566N	625
70567N	625
70573	607
70573B	607
70575	577
70576	486
70579	615
70586	660
70587	660
70588	660
70589	660
70591	661
70592N	660
70593N	660
70634	624
70637	625
70638	650
70644	620
70645	620
70646	620
70647	620
70655	636
70656	636
70657	638
70658	638
70659	638
70660	656
70660W	656
70661	656
70661W	656
70662	656
70662W	656
70663	606
70664	606
70665	604
70666	604
70667	606
70668	606
70682	604
70683	604
70686	625

Ref	Page
70687	625
70689	605
70690	576
70696	607
70697	607
70714	608
70715	605
70720	606
70722	574
70726	652
70728	652
70729	652
70730	652
70731	652
70732	652
70733	654
70734	654
70735	654
70736	654
70749	630
70753	498
70754	498
70755	498
70756	498
70761	479
70767	478
70768	478
70771	486
70772	488
70773	602
70774	502
70775	56
70776	56
70777	56
70780	596
70782	500
70783	500
70784	58
70785	502
70786	56
70787	540
70788	540
70790	50
70799	576
70802	624
70806	577
70811	623
70812	623
70813	623
70821	577
70823	604
70824	632
70825	632
70826	632
70827	605
70828	623
70829	606
70830	626
70832	626
70833	650
70834	650
70887	607
70888	622
70899	622
70900	650
70901	650
70906	637
70907	637
70908	637
70909	637
70910	637
70911	637
70912	554
70913	544
70914	60
70992	600
70993	488
70996	600
70997	600
70998	600
70999	600
71049	617
71052	617
71106	571
71110	598
71116	526
71117	526
71118	526
71128	598
71129	598
71138	571
71139	571
71140	599
71141	599
71194	582
71195	582
71196	582
71198	498
71199	498
71206	492
71208	492
71209	518
71212	610
71213	494
71214	494
71215	610
71216	480
71217	481
71222	610
71223	610
71224	466
71225	466
71242	454
71243	454
71244	454
71253	460
71254	460
71256	460
71257	460
71262	452
71263	452
71264	452
71272	614
71273	614
71274	605
71276	615
71277	615
71279	584
71285	584
71286	470
71287	470
71299	476
71300	476
71301	476
71303	602
71304	602
71305	602
71306	602
71308	615
71309	615
71352	500
71353	626
71362L	612
71363	627
71366	627
71367	627
71372	576
71374	576
71383	550
71388	627
71389	550
71390	550
71424	597
71480	645
71481	645
71482	645
71489N	662
71490	645
71491	645
71495	662
71496N	661
71498N	661
71499N	661
71516	610
71517	610
71519	612
71528	536
71536	586
71537	586
71538	580
71539	580
71546	548
71547	548
71548	548
71549	548
71556	458
71562	458
71563	458
71564	458
71565	60
71569-01	451
71569-04	450
71569-05	448
71569-06	448
71569-07	446
71569-08	446
71569-09	444
71569-10	444
71575-01	451
71575-04	450
71575-05	448
71575-06	448
71575-07	446
71575-09	444
71575P-01	534
71575P-03	534
71575P-04	534
71575P-05	532
71575P-06	532
71575P-07	532
71575P-09	532
71576-01	451
71576-04	450
71576P-03	534
71576P-04	534
71579-02	560
71579C-03	560
71579C-04	560
71579C-05	558
71579C-06	558
71579C-07	558
71579C-09	558
71579H-03	560
71579H-04	560
71579H-05	558
71579H-06	558
71579H-07	558
71579H-09	558
71584-01	566
71584-02	458
71584-03	566
71584-04	566
71584-05	564
71584-06	564
71584-07	564
71584-08	564
71584-09	562
71584-10	562
71606	597
71613	544
71701	657
71702	657
71703	657
71716	657
71717	657
71730	664
71731	664
71732	664
71733	664
71734	665
71735	665
71736	665
71737	665
71740	577
71741	577
71742	577
71743	592
71744	592
71745	592
71746	474
71747	474
71748	474
71749	474
71750	474
71751	474
71770	552
71770V	552
71771	552
71771V	552
71898	616
71899	616
71900	616
71901	616
71902	616
71903	616
71904	616
71905	616
71906	617
71907	617
71908	617
71909	616
71910	616
71911	616
71912	54
71913	54
71914	54
71915	618
71916	618
71917	618
71918	618
72000	609
72001	609
72002	609
72010	609
72011	609
72092	644
72093	644
72094	645
72095	645
72269	622
72272	614
72280	608
72281	608
72298	500
72310	488
72311	490
72312	490
72330	632
72352	574
72353	574
72354	574
72355	574
73100	545
73111	545
73150	545
74139	586
74141	466
74142	466
74155	468
74156	468
74261	599
74400	628
74401	612
74407	630
74408	630
74411	502
74419	626
74422	456
74423	456
74424	456
74427C-01	570
74427C-02	570
74427C-03	570
74427C-04	570
74432A-01	594
74432A-02	594
74432A-03	594
74432A-04	594
74433S-01	482
74433S-02	482
74433S-03	482
74433S-04	482
74434B-01	484
74434B-02	484
74434B-03	484
74434B-04	484
74435F2-02	522
74435F2-03	522
74435F2-04	522
74436F3-02	524
74436F3-03	524
74436F3-04	524
74440	592
74441	472
74442	472
74444E	518
74450	614
74451	496
74452	496
74453	590
74454	58
74455	627
74465	44
74997	479
74998	596
75000	596
750000	508
750000C	508
750000D	508
750001	508
750001C	508
750001D	508
750002	508
750002C	508
750002D	508
75001	479
750010	508
750010C	508
750010D	508
750011	508
750011C	508
750011D	508
750012	508
750012C	508
750012D	508
75002	571
750020	508
750020C	508
750020D	508
750021	508
750021C	508
750021D	508
750022	508
750022C	508
750022D	508
75003	479
750100	508
750100C	508
750100D	508
750101	508
750101C	508
750101D	508
750102	508
750102C	508
750102D	508
750110	508

Ref	Page
750110C	508
750110D	508
750111	508
750111C	508
750111D	508
750112	508
750112C	508
750112D	508
750120	508
750120C	508
750120D	508
750121	508
750121C	508
750121D	508
750122	508
750122C	508
750122D	508
750200	510
750200C	510
750200D	510
750201	510
750201C	510
750201D	510
750202	510
750202C	510
750202D	510
750210	510
750210C	510
750210D	510
750211	510
750211C	510
750211D	510
750212	510
750212C	510
750212D	510
750220	510
750220C	510
750220D	510
750221	510
750221C	510
750221D	510
750222	510
750222C	510
750222D	510
750300	510
750300C	510
750300D	510
750301	510
750301C	510
750301D	510
750302	510
750302C	510
750302D	510
750310	510
750310C	510
750310D	510
750311	510
750311C	510
750311D	510
750312	510
750312C	510
750312D	510
750320	510
750320C	510
750320D	510
750321	510
750321C	510
750321D	510
750322	510
750322C	510
750322D	510
751000	512
751000C	512
751000D	512
751001	512
751001C	512
751001D	512
751002	512
751002C	512
751002D	512
751010	512
751010C	512
751010D	512
751011	512
751011C	512
751011D	512
751012	512
751012C	512
751012D	512
751020	512
751020C	512
751020D	512
751021	512
751021C	512
751021D	512
751022	512
751022C	512
751022D	512
751100	512
751100C	512
751100D	512
751101	512
751101C	512
751101D	512
751102	512
751102C	512
751102D	512
751110	512
751110C	512
751110D	512
751111	512
751111C	512
751111D	512
751112	512
751112C	512
751112D	512
751120	512
751120C	512
751120D	512
751121	512
751121C	512
751121D	512
751122	512
751122C	512
751122D	512
751200	514
751200C	514
751200D	514
751201	514
751201C	514
751201D	514
751202	514
751202C	514
751202D	514
751210	514
751210C	514
751210D	514
751211	514
751211C	514
751211D	514
751212	514
751212C	514
751212D	514
751220	514
751220C	514
751220D	514
751221	514
751221C	514
751221D	514
751222	514
751222C	514
751222D	514
751300	514
751300C	514
751300D	514
751301	514
751301C	514
751301D	514
751302	514
751302C	514
751302D	514
751310	514
751310C	514
751310D	514
751311	514
751311C	514
751311D	514
751312	514
751312C	514
751312D	514
751320	514
751320C	514
751320D	514
751321	514
751321C	514
751321D	514
751322	514
751322C	514
751322D	514
75500	628
75501	628
75502	628
75503	628
75519	496
75520	496
75521	486
75522	480
75523	480
75524	520
75531	472
75532	518
75533	586
75537	470
75538	470
75540	612
75541	472
75550	462
75551	462
75552	462
75553	462
75556	538
75557	538
75602	520
75603	478
75604	478
75605	481
75606	481
75607	520
75608	58
75700	590
75701	590
75750	588
75751	588
75753	568
75754	568
75755	568
75800	545
75801	545
97166	812
97264	812
97273	812
97291	812
97292	812
97402	812
97403	812
97404	812
97411	812
97412	812
97413	812
97414	812
97685327	812
97685330	812
97686227	812
97686230	812
97686327	812
97686330	812
97687127	812
97690127	813
97690130	813
97690427	813
97690430	813
97691127	813
97691130	813
97691227	813
97691230	813
97691327	813
97691330	813
97691695	813
97691696	813
97691697	813
97691698	813
97691699	813
97691701	813
97691702	813
97691703	813
97691704	813
97692327	813
97692330	813
97692427	813
97692430	813
97692595	813
97692596	813
97692597	813
97692598	813
97692599	813
97692601	813
97692602	813
97692603	813
97692604	813

1968	Indoor	Table	**68**
Academy	Indoor	Wall	**250**
Academy	Indoor	Floor	**90**
Academy	Indoor	Table	**90**
Aday	Outdoor	Wall	**620**
Agra	Outdoor	Floor	**498**
Agra	Outdoor	Post	**498**
Aina	Indoor	Suspended	**212**
Akane	Indoor	Table	**106**
Akane	Outdoor	Floor	**452**
Alfa	Outdoor	Projector	**550**
Alo	Fan		**705**
Aloha	Fan		**759**
Alp	Outdoor	Floor	**496**
Alp	Outdoor	Wall	**614**
Amelia	Fan		**721**
Amelia	Fan		**723**
Amelia	Fan		**725**
Ami	Indoor	Ceiling	**238**
Ancora	Outdoor	Wall	**612**
Andros	Fan		**691**
Andy	Outdoor	Spike	**544**
Anga	Outdoor	Ceiling	**574**
Anouk	Indoor	Table	**78**
Aoba	Fan		**695**
Argón	Indoor	Recessed	**419**
Argot	Outdoor	Wall	**597**
Argus	Portable	Portable	**58**
Art	Indoor	Suspended	**204**
Art	Indoor	Multiple	**217**
Artis	Indoor	Table	**122**
Artis	Indoor	Floor	**122**
Artis	Indoor	Wall	**296**
Attos	Fan		**689**
Aurea	Indoor	Wall	**330**
Axel	Outdoor	Wall	**614**
Balda	Portable	Portable	**60**
Balder	Outdoor	Spike	**544**
Balic	Outdoor	Floor	**464**
Balic	Outdoor	Wall	**583**
Bambou	Outdoor	Spike	**538**
Banker	Indoor	Table	**82**
Baobab	Indoor	Table	**82**
Barth	Fan		**727**
Bast	Outdoor	Post	**504**
Bel	Indoor	Wall	**336**
Beret	Outdoor	Floor	**480**
Beret	Outdoor	Pole	**520**
Berni	Indoor	Table	**132**
Berni	Indoor	Floor	**132**
Berni	Indoor	Wall	**318**
Bezel	Outdoor	Floor	**504**
Bezel	Outdoor	Spike	**540**
Bianca	Indoor	Wall	**382**
Bic	Indoor	Ceiling	**238**
Black	Indoor	Floor	**146**
Blind	Outdoor	Wall	**624**
Bliss	Indoor	Table	**76**
Block	Outdoor	Floor	**466**
Block	Outdoor	Wall	**586**
Blome	Indoor	Wall	**307**
Blubs	Outdoor	Post	**482**
Blubs	Outdoor	Floor	**484**
Blubs	Outdoor	Pole	**522**
Blubs	Outdoor	Pole	**524**
Blubs	Outdoor	Suspended	**570**
Blubs	Outdoor	Wall	**594**
Board	Indoor	Wall	**370**
Boc	Indoor	Wall	**332**
Boken	Indoor	Wall	**336**
Bonn	Outdoor	Wall	**607**
Borda	Outdoor	Wall	**600**
Bracket	Outdoor	Wall	**614**
Bronx	Outdoor	Wall	**582**
Brot	Outdoor	Floor	**460**
Brow	Outdoor	Wall	**632**
Bruc	Outdoor	Wall	**623**
Brume	Indoor	Suspended	**202**
Brume	Indoor	Ceiling	**240**
Brume	Indoor	Wall	**382**
Buddy	Portable	Portable	**46**
Bu-Oh	Outdoor	Floor	**494**
Bu-Oh	Outdoor	Pole	**518**
Bu-Oh	Outdoor	Wall	**610**
Cabo	Outdoor	Wall	**600**
Cadaques	Outdoor	Floor	**454**
Cage	Portable	Portable	**58**
Candela	Portable	Portable	**50**
Canon	Outdoor	Wall	**625**
Carter	Outdoor	Recessed	**648**
Cast	Outdoor	Floor	**468**
Cat	Outdoor	Table	**458**
Cebu	Fan		**798**
Cela	Outdoor	Wall	**608**
Celia	Indoor	Wall	**364**
Century	Fan		**703**
Chandra	Outdoor	Floor	**500**
Charlotte	Indoor	Suspended	**200**
Chera	Indoor	Wall	**376**
Chicago	Fan		**801**
Cies	Fan		**693**
Claire	Indoor	Suspended	**206**
Claire	Indoor	Multiple	**218**
Clara	Indoor	Suspended	**204**
Clara	Indoor	Multiple	**217**
Clear	Indoor	Recessed	**422**
Click	Indoor	Recessed	**422**
Coco	Indoor	Spot	**398**
Cocos	Fan		**716**
Cocotte	Indoor	Suspended	**176**
Cocotte	Indoor	Ceiling	**228**
Confetti	Indoor	Suspended	**152**
Confetti	Indoor	Wall	**246**
Conga	Indoor	Table	**114**
Conga	Indoor	Floor	**115**
Conga	Indoor	Suspended	**194**
Conga	Indoor	Multiple	**216**
Conga	Indoor	Multiple	**221**
Conga	Indoor	Wall	**290**
Cooper	Fan		**767**
Corb	Indoor	Wall	**348**
Cosmos	Indoor	Suspended	**210**
Costas	Indoor	Suspended	**184**
Costas	Indoor	Wall	**258**
Cotton	Indoor	Wall	**356**
Cotton	Indoor	Wall	**358**
Cove	Indoor	Wall	**378**
Crater	Indoor	Suspended	**200**
Crosby	Outdoor	Recessed	**655**
Cuba	Fan		**760**
Curtis	Outdoor	Recessed	**655**
Dado	Outdoor	Wall	**597**
Dakron	Outdoor	Ceiling	**574**
Dang	Outdoor	Recessed	**643**
Danka	Indoor	Suspended	**210**
Danubio	Indoor	Wall	**388**
Dart	Outdoor	Recessed	**646**
Das	Outdoor	Floor	**496**
Datna	Outdoor	Floor	**472**
Datna	Outdoor	Pole	**518**
Datna	Outdoor	Wall	**592**
Deco Fan	Fan		**775**
Derby	Outdoor	Wall	**609**
Desliz	Indoor	Wall	**251**
Diula	Indoor	Wall	**381**
Dolme	Indoor	Suspended	**176**
Dolme	Indoor	Ceiling	**228**
Domino	Indoor	Recessed	**408**

Doro	Outdoor	Wall	**616**
Doro	Outdoor	Wall	**617**
Dragma	Outdoor	Wall	**612**
Drak	Outdoor	Wall	**632**
Drum	Indoor	Table	**108**
Drum	Indoor	Floor	**108**
Duas	Indoor	Wall	**328**
Eaco	Indoor	Wall	**377**
Easy	Fan		**797**
Ebba	Indoor	Recessed	**424**
Eco indus	Fan		**788**
Edel	Outdoor	Recessed	**662**
Edge	Indoor	Wall	**384**
Ele	Outdoor	Wall	**626**
Elsa	Indoor	Wall	**378**
Eres	Indoor	Wall	**350**
Esca	Outdoor	Recessed	**645**
Essential	Indoor	Wall	**326**
Estay	Outdoor	Wall	**609**
Estoril	Outdoor	Wall	**599**
Eterfan	Fan		**771**
Eterna	Indoor	Wall	**298**
Eterna	Indoor	Table	**74**
Falls	Outdoor	Recessed	**664**
Falls	Outdoor	Recessed	**665**
Fedón	Outdoor	Wall	**608**
Feroe	Fan		**792**
Flash	Indoor	Suspended	**150**
Flash	Indoor	Wall	**254**
Flin	Indoor	Wall	**333**
Flow	Outdoor	Projector	**548**
Foc	Outdoor	Spike	**542**
Foc	Outdoor	Projector	**555**
Fold	Indoor	Wall	**308**
Foro	Indoor	Ceiling	**238**
Fox	Indoor	Recessed	**426**
Frame	Indoor	Wall	**302**
Fraser	Fan		**789**
Fred	Outdoor	Wall	**606**
Fred XL	Outdoor	Wall	**606**
Fresh	Indoor	Recessed	**428**
Fresh	Indoor	Recessed	**430**
Frol	Outdoor	Recessed	**644**
Fuji	Portable	Portable	**44**
Fusta	Indoor	Suspended	**198**
Future	Outdoor	Wall	**610**
Gala	Indoor	Wall	**384**
Galo	Outdoor	Recessed	**642**
Garten	Outdoor	Spike	**545**
Gas	Indoor	Recessed	**420**
Geiser	Outdoor	Recessed	**658**
Geiser	Outdoor	Recessed	**658**
Gina	Outdoor	Floor	**500**
Gina	Outdoor	Wall	**627**
Giza	Outdoor	Floor	**478**
Gotland	Fan		**731**
Goz	Outdoor	Ceiling	**577**
Grada	Outdoor	Wall	**637**
Grant	Outdoor	Wall	**636**
Gron	Outdoor	Recessed	**644**
Grop	Outdoor	Pole	**520**
Grow	Outdoor	Floor	**492**
Gru	Indoor	Table	**82**
Guadalupe	Indoor	Wall	**272**
Guadalupe	Indoor	Table	**94**
Guadalupe	Indoor	Floor	**94**
Guest	Indoor	Floor	**142**
Guest	Indoor	Wall	**270**
Haka	Indoor	Suspended	**188**
Half	Outdoor	Wall	**586**
Halita	Indoor	Suspended	**204**
Han	Indoor	Wall	**269**
Handy	Indoor	Wall	**322**
Hanna	Indoor	Wall	**326**
Haru	Indoor	Ceiling	**234**
Heywood	Fan		**719**
Heywood	Fan		**802**
Hikari	Outdoor	Wall	**605**
Homs	Indoor	Wall	**362**
Hook	Portable	Portable	**48**
Hoshi	Indoor	Table	**70**
Hotel	Indoor	Floor	**134**
Hotel	Indoor	Table	**134**
Hotel	Indoor	Suspended	**198**
Hotel	Indoor	Wall	**310**
Hudson	Indoor	Wall	**363**
Hvar	Fan		**799**
Hyde	Indoor	Recessed	**414**
Hydra	Fan		**717**
Ibiza	Fan		**756**
Icaria	Fan		**755**
Ice	Fan		**745**
Indus	Fan		**714**
Inviting	Indoor	Wall	**248**
Inviting	Indoor	Table	**66**
Iris	Indoor	Ceiling	**237**
Ito	Indoor	Table	**78**
Izaro	Fan		**761**
Janet	Indoor	Ceiling	**234**
Jellyfish	Indoor	Floor	**92**
Jellyfish	Indoor	Table	**92**
Joy	Indoor	Wall	**263**
Juliet	Indoor	Wall	**334**
Just Fan	Fan		**697**
Just Fan	Fan		**773**
Just Fan	Fan		**805**
Kale	Indoor	Wall	**337**
Kamen	Indoor	Wall	**379**
Kane	Outdoor	Recessed	**656**
Kao	Indoor	Ceiling	**239**
Kasp	Portable	Portable	**54**
Kasp	Portable	Portable	**54**
Kauai	Fan		**687**
Kaula	Outdoor	Wall	**620**
Keenan	Outdoor	Wall	**634**
Keiki	Fan		**809**
Kera	Indoor	Wall	**362**
Kerala	Portable	Portable	**58**
Kerala	Outdoor	Wall	**590**
Khios	Fan		**683**
Kila	Outdoor	Floor	**474**
Kila	Outdoor	Ceiling	**577**
Kila	Outdoor	Wall	**592**
Klamp	Outdoor	Floor	**502**
Klamp	Outdoor	Wall	**630**
Klee	Indoor	Wall	**274**
Koi-2	Indoor	Recessed	**421**
Kombo	Indoor	Suspended	**178**
Kombo	Indoor	Multiple	**215**
Kombo	Indoor	Multiple	**221**
Kubick	Outdoor	Wall	**605**
Lace	Outdoor	Wall	**623**
Lacre	Outdoor	Wall	**624**
Lago	Indoor	Wall	**384**
Lako	Outdoor	Wall	**616**
Lama	Fan		**713**
Lampanot	Portable	Portable	**52**
Lang	Indoor	Suspended	**206**
Lang	Indoor	Multiple	**218**
Lantau	Fan		**699**
Lantau	Fan		**741**
Lao	Indoor	Floor	**104**
Lao	Indoor	Table	**104**
Lao	Indoor	Spot	**396**
Le Petit	Indoor	Wall	**331**
Lead	Indoor	Wall	**337**
Leaf	Outdoor	Spike	**530**
Led-18	Outdoor	Recessed	**661**

Lena	Indoor	Clip	**334**
Lena	Indoor	Table	**80**
Leser	Indoor	Wall	**336**
Levita	Indoor	Suspended	**168**
Levita	Indoor	Wall	**264**
Levita	Indoor	Table	**96**
Levita	Indoor	Floor	**96**
Liana	Indoor	Suspended	**207**
Linda	Indoor	Floor	**126**
Linda	Indoor	Table	**126**
Linda	Indoor	Suspended	**198**
Linda	Indoor	Wall	**367**
Ling	Outdoor	Wall	**623**
Link	Indoor	Table	**102**
Link	Indoor	Floor	**102**
Link	Indoor	Ceiling	**230**
Link	Indoor	Spot	**404**
Link	Indoor	Track	**436**
Lio	Outdoor	Recessed	**662**
Liria	Indoor	Wall	**381**
Lisboa	Fan		**796**
Lise	Indoor	Wall	**372**
Liso	Outdoor	Recessed	**645**
List	Indoor	Wall	**366**
Lit	Outdoor	Projector	**555**
Liz	Indoor	Suspended	**204**
Liz	Indoor	Multiple	**217**
Loa	Indoor	Wall	**363**
Log	Outdoor	Wall	**624**
Logar	Outdoor	Floor	**481**
Logos	Indoor	Ceiling	**239**
Loke	Indoor	Wall	**333**
Lombok	Fan		**758**
Loop	Indoor	Suspended	**164**
Loop	Indoor	Wall	**282**
Loop	Indoor	Table	**98**
Loop	Indoor	Floor	**98**
Loth	Outdoor	Wall	**633**
Lotus	Outdoor	Floor	**466**
Lotus	Outdoor	Wall	**610**
Lou	Indoor	Suspended	**206**
Luan	Indoor	Recessed	**433**
Luang	Indoor	Wall	**244**
Luang	Indoor	Table	**88**
Luang	Indoor	Table	**88**
Luang	Indoor	Floor	**88**
Lula	Indoor	Table	**74**
Luna	Indoor	Wall	**379**
Lupe	Indoor	Table	**128**
Lupe	Indoor	Floor	**128**
Lupe	Indoor	Wall	**304**
Lur	Outdoor	Wall	**605**
Luzon	Fan		**747**
Magma	Indoor	Suspended	**200**
Magos	Indoor	Wall	**265**
Magritte	Indoor	Wall	**380**
Mallorca	Fan		**757**
Malvinas	Fan		**715**
Mambo	Indoor	Table	**110**
Mambo	Indoor	Floor	**111**
Mambo	Indoor	Suspended	**190**
Mambo	Indoor	Suspended	**192**
Mambo	Indoor	Multiple	**215**
Mambo	Indoor	Multiple	**221**
Mambo	Indoor	Wall	**294**
Manhattan	Fan		**685**
Margot	Indoor	Suspended	**200**
Marina	Indoor	Suspended	**205**
Marina	Indoor	Wall	**363**
Marlin	Indoor	Suspended	**205**
Marlin	Indoor	Multiple	**217**
Marlin	Indoor	Wall	**364**
Mask	Outdoor	Wall	**584**
Mauren	Outdoor	Ceiling	**488**
May	Indoor	Wall	**260**
Maya	Indoor	Wall	**256**
Mediterraneo	Fan		**803**
Mega	Indoor	Ceiling	**238**
Meno	Fan		**730**
Mila	Outdoor	Post	**486**
Milos	Fan		**729**
Mine	Indoor	Suspended	**172**
Mine	Indoor	Suspended	**174**
Mine	Indoor	Suspended	**175**
Mine	Indoor	Table	**73**
Mini Eterfan	Fan		**769**
Mini Icaria	Fan		**791**
Mini Indus	Fan		**800**
Mini Lantau	Fan		**795**
Mini Mallorca	Fan		**793**
Mini Tube	Fan		**777**
Mini-Project	Outdoor	Projector	**550**
Mistu	Outdoor	Post	**482**
Mistu	Outdoor	Floor	**484**
Mistu	Outdoor	Pole	**522**
Mistu	Outdoor	Pole	**524**
Mistu	Outdoor	Suspended	**570**
Mistu	Outdoor	Wall	**594**
Moist	Indoor	Recessed	**427**
Mol	Outdoor	Wall	**606**
Moma	Indoor	Table	**144**
Moma	Indoor	Floor	**144**
Moma	Indoor	Wall	**327**
Montreal	Indoor	Table	**116**
Montreal	Indoor	Floor	**116**
Montreal	Indoor	Wall	**288**
Mood	Indoor	Wall	**276**
Moon	Outdoor	Post	**482**
Moon	Outdoor	Floor	**484**
Moon	Outdoor	Suspended	**570**
Moon	Outdoor	Wall	**594**
Morea	Fan		**711**
Mou	Indoor	Suspended	**207**
Moy	Indoor	Wall	**262**
Muffin	Outdoor	Post	**482**
Muffin	Outdoor	Floor	**484**
Muffin	Outdoor	Pole	**522**
Muffin	Outdoor	Pole	**524**
Muffin	Outdoor	Suspended	**570**
Muffin	Outdoor	Wall	**594**
Muga	Outdoor	Floor	**478**
Must	Outdoor	Wall	**638**
Muur	Outdoor	Projector	**552**
Nahir	Outdoor	Wall	**600**
Nairobi	Outdoor	Wall	**626**
Nais	Indoor	Recessed	**421**
Nala	Outdoor	Post	**488**
Nala	Outdoor	Wall	**602**
Nanda	Outdoor	Floor	**480**
Nanda	Outdoor	Floor	**481**
Naos	Indoor	Suspended	**180**
Nase	Outdoor	Recessed	**642**
Nash	Indoor	Wall	**374**
Nassau	Fan		**781**
Nat	Outdoor	Recessed	**650**
Natron	Outdoor	Wall	**607**
Natsu	Indoor	Ceiling	**234**
Nautica	Outdoor	Pole	**526**
Nautica	Outdoor	Suspended	**571**
Nautica	Outdoor	Wall	**598**
Navi	Indoor	Recessed	**411**
Naya	Outdoor	Post	**498**
Naya	Outdoor	Floor	**498**
Negus	Outdoor	Wall	**607**
Neon	Indoor	Recessed	**420**
Neu	Indoor	Recessed	**410**
Nias	Fan		**752**
Nidia	Indoor	Table	**76**

Nido	Indoor	Suspended	**207**
Niko	Indoor	Wall	**278**
Niko	Indoor	Table	**72**
Nilo	Indoor	Wall	**389**
Nit	Indoor	Wall	**345**
Noboru	Outdoor	Floor	**486**
Noon	Indoor	Wall	**346**
Noray	Outdoor	Wall	**600**
Nord	Indoor	Recessed	**410**
Nuu	Fan		**743**
Oko	Outdoor	Projector	**554**
Olaf	Indoor	Wall	**374**
Olan	Outdoor	Wall	**625**
Olot	Outdoor	Ceiling	**576**
Onze	Outdoor	Floor	**479**
Ora	Indoor	Suspended	**208**
Orleans	Indoor	Ceiling	**230**
Orleans	Indoor	Spot	**402**
Orleans	Indoor	Track	**436**
Orwell	Outdoor	Wall	**590**
Oslo	Indoor	Wall	**374**
Otto	Indoor	Table	**80**
Otton	Indoor	Wall	**352**
Otton	Indoor	Wall	**354**
Oval	Outdoor	Wall	**615**
Ovo	Indoor	Wall	**350**
Palao	Fan		**807**
Palk	Fan		**751**
Pals	Outdoor	Wall	**584**
Pam	Indoor	Suspended	**210**
Panay	Fan		**785**
Papua	Indoor	Floor	**146**
Path	Outdoor	Wall	**636**
Pemba	Fan		**750**
Pepper	Indoor	Clip	**334**
Perla	Indoor	Wall	**382**
Piccola	Outdoor	Spike	**537**
Pill	Outdoor	Wall	**632**
Pivot	Outdoor	Wall	**602**
Pixie	Indoor	Wall	**339**
Plas	Indoor	Recessed	**412**
Plat	Indoor	Suspended	**205**
Plat	Indoor	Multiple	**216**
Plaza	Outdoor	Pole	**520**
Plim	Outdoor	Floor	**476**
Plom	Outdoor	Spike	**544**
Plom	Outdoor	Projector	**554**
Plot	Indoor	Track	**438**
Pluma	Indoor	Suspended	**182**
Pol	Outdoor	Wall	**606**
Polaris	Fan		**749**
Polea	Fan		**746**
Pomo	Outdoor	Wall	**602**
Poros	Fan		**739**
Pote	Indoor	Ceiling	**234**
Press	Indoor	Wall	**338**
Proa	Outdoor	Wall	**628**
Project	Outdoor	Projector	**550**
Punt	Fan		**763**
Pure	Indoor	Wall	**271**
Quart	Outdoor	Wall	**615**
Racing	Outdoor	Recessed	**648**
Radón	Indoor	Recessed	**418**
Ras	Indoor	Wall	**366**
Rel	Indoor	Ceiling	**233**
Rem	Indoor	Table	**120**
Rem	Indoor	Floor	**120**
Rem	Indoor	Wall	**300**
Retro	Indoor	Suspended	**166**
Retro	Indoor	Wall	**367**
Ring	Indoor	Spot	**404**
Rob	Indoor	Wall	**332**
Roda	Indoor	Wall	**324**
Rodas	Fan		**737**
Ron	Indoor	Wall	**306**
Room	Indoor	Wall	**312**
Rose	Indoor	Suspended	**202**
Rush	Outdoor	Post	**508**
Rush	Outdoor	Floor	**510**
Saba	Indoor	Wall	**324**
Sabi	Indoor	Suspended	**208**
Sahara	Indoor	Wall	**324**
Saigon	Indoor	Suspended	**160**
Saigon	Outdoor	Floor	**444**
Saigon	Outdoor	Floor	**446**
Saigon	Outdoor	Floor	**448**
Saigon	Outdoor	Floor	**450**
Saigon	Outdoor	Floor	**451**
Saigon	Outdoor	Ceiling	**458**
Saigon	Outdoor	Spike	**532**
Saigon	Outdoor	Spike	**534**
Saigon	Outdoor	Ceiling	**558**
Saigon	Outdoor	Suspended	**560**
Saigon	Outdoor	Suspended	**562**
Saigon	Outdoor	Suspended	**564**
Saigon	Outdoor	Suspended	**566**
Saipan	Indoor	Suspended	**186**
Salt	Outdoor	Recessed	**661**
Samba	Indoor	Table	**112**
Samba	Indoor	Floor	**113**
Samba	Indoor	Suspended	**194**
Samba	Indoor	Multiple	**216**
Samba	Indoor	Multiple	**221**
Samba	Indoor	Wall	**284**
Sami	Indoor	Wall	**337**
Samos	Fan		**733**
Saona	Fan		**734**
Saura	Outdoor	Floor	**502**
Savoy	Indoor	Table	**118**
Savoy	Indoor	Floor	**118**
Savoy	Indoor	Suspended	**196**
Savoy	Indoor	Wall	**286**
Screen	Outdoor	Post	**512**
Screen	Outdoor	Floor	**514**
Scuba	Outdoor	Suspended	**568**
Sedna	Outdoor	Recessed	**651**
Sera	Indoor	Wall	**362**
Sete	Outdoor	Post	**486**
Seth	Outdoor	Spike	**542**
Seven	Indoor	Suspended	**212**
Seven	Indoor	Ceiling	**236**
Shadow	Outdoor	Floor	**490**
Shelby	Outdoor	Floor	**470**
Shoku	Indoor	Ceiling	**224**
Side	Indoor	Suspended	**183**
Side	Indoor	Wall	**226**
Signal	Indoor	Recessed	**410**
Sioux	Fan		**748**
Siros	Fan		**732**
Slim	Indoor	Suspended	**166**
Slim	Indoor	Wall	**268**
Slot	Outdoor	Projector	**546**
Slot	Outdoor	Spike	**546**
Smile	Indoor	Wall	**347**
Snap	Indoor	Wall	**366**
Snap	Indoor	Table	**80**
Snow	Indoor	Wall	**378**
Sobek	Outdoor	Spike	**544**
Soleil	Outdoor	Floor	**502**
Son	Indoor	Recessed	**432**
Soun	Outdoor	Recessed	**650**
Spark-1	Outdoor	Recessed	**648**
Spy-1	Outdoor	Floor	**500**
Spy-1	Outdoor	Spike	**540**
Spy-2	Outdoor	Floor	**500**
Spy-2	Outdoor	Spike	**540**
Stan	Indoor	Suspended	**208**
Stan	Indoor	Ceiling	**235**

Stan	Indoor	Wall	**372**
Stan	Indoor	Spot	**392**
Stan	Indoor	Spot	**394**
Stan	Indoor	Recessed	**424**
Stand Up	Indoor	Floor	**138**
Steps	Outdoor	Wall	**628**
Sticker	Outdoor	Floor	**472**
Sticker	Outdoor	Wall	**612**
Stone	Indoor	Spot	**400**
Stood	Indoor	Table	**100**
Stood	Indoor	Floor	**100**
Stood	Indoor	Suspended	**162**
Stood	Indoor	Wall	**280**
Stood	Indoor	Table	**280**
Stripe-1	Outdoor	Recessed	**645**
Stripe-2	Outdoor	Recessed	**644**
Studio	Indoor	Clip	**335**
Suau	Indoor	Wall	**340**
Suau	Indoor	Wall	**342**
Suma	Outdoor	Wall	**630**
Sumba	Indoor	Suspended	**186**
Sumba	Indoor	Wall	**292**
Sumba	Indoor	Table	**76**
Sun	Outdoor	Wall	**604**
Sunset	Outdoor	Wall	**625**
Surat	Outdoor	Post	**488**
Suria	Outdoor	Recessed	**660**
Sven	Indoor	Ceiling	**233**
Sweet	Indoor	Floor	**145**
Sweet	Indoor	Wall	**320**
Tacana	Outdoor	Wall	**617**
Taima	Outdoor	Wall	**627**
Take Away	Portable	Portable	**45**
Takua	Outdoor	Wall	**615**
Tamashi	Outdoor	Wall	**602**
Tami	Outdoor	Ceiling	**576**
Tane	Outdoor	Wall	**622**
Taro	Outdoor	Recessed	**662**
Tasa	Outdoor	Ceiling	**577**
Task	Portable	Portable	**60**
Tatawin	Indoor	Suspended	**156**
Tatawin	Indoor	Multiple	**219**
Tatawin	Indoor	Wall	**257**
Tatawin	Indoor	Floor	**84**
Tecno	Outdoor	Recessed	**662**
Tecto	Indoor	Ceiling	**232**
Ted	Indoor	Recessed	**433**
Tejo	Outdoor	Wall	**607**
Ten	Indoor	Wall	**361**
Ten	Indoor	Table	**71**
Tender	Indoor	Ceiling	**228**
Tera	Indoor	Wall	**379**
Thon	Outdoor	Wall	**618**
Tila	Indoor	Wall	**344**
Tilos	Fan		**701**
Timon	Outdoor	Wall	**600**
Tinia	Outdoor	Wall	**626**
Tira	Indoor	Wall	**327**
Toc	Portable	Portable	**56**
Toc	Portable	Portable	**56**
Toc	Outdoor	Wall	**596**
Tod	Indoor	Recessed	**433**
Tola	Indoor	Ceiling	**240**
Toluca	Outdoor	Wall	**617**
Tom	Outdoor	Wall	**604**
Tond	Outdoor	Wall	**618**
Tone	Outdoor	Wall	**580**
Toni	Outdoor	Spike	**536**
Tonic	Fan		**709**
Tono	Outdoor	Spike	**545**
Tonsay	Fan		**753**
Toran	Outdoor	Projector	**554**
Totem	Outdoor	Floor	**462**
Tou	Indoor	Wall	**368**
Tram	Outdoor	Floor	**472**
Tram	Outdoor	Pole	**518**
Tram	Outdoor	Wall	**586**
Tras	Outdoor	Recessed	**657**
Tree	Indoor	Table	**130**
Tree	Indoor	Floor	**130**
Tree	Indoor	Suspended	**198**
Tube	Fan		**779**
Tupai	Indoor	Suspended	**186**
Twist	Outdoor	Floor	**470**
Twist	Outdoor	Wall	**584**
Typhoon	Fan		**765**
Uve	Outdoor	Recessed	**643**
Vedra	Fan		**808**
Venice	Indoor	Suspended	**154**
Venice	Indoor	Multiple	**219**
Venice	Indoor	Wall	**252**
Venice	Indoor	Floor	**86**
Venice	Indoor	Table	**86**
Versus	Outdoor	Floor	**456**
Vesper	Indoor	Floor	**124**
Vesper	Indoor	Table	**124**
Vesper	Indoor	Suspended	**196**
Vesper	Indoor	Wall	**316**
Vico	Indoor	Suspended	**158**
View	Outdoor	Wall	**612**
Voila	Portable	Portable	**60**
Volga	Indoor	Wall	**386**
Volta	Indoor	Table	**136**
Volta	Indoor	Floor	**136**
Volta	Indoor	Wall	**314**
Vuk	Indoor	Ceiling	**240**
Vulcano	Fan		**707**
Wabi	Indoor	Recessed	**424**
Wally	Outdoor	Wall	**599**
Well	Indoor	Wall	**348**
West	Outdoor	Wall	**622**
Wet	Indoor	Recessed	**422**
Whizz	Indoor	Floor	**140**
Whizz	Indoor	Suspended	**170**
Whizz	Indoor	Multiple	**218**
Whizz	Indoor	Wall	**266**
Wilma	Outdoor	Post	**479**
Wilma	Outdoor	Floor	**479**
Wilma	Outdoor	Suspended	**571**
Wilma	Outdoor	Wall	**596**
Winch	Indoor	Suspended	**205**
Winche	Fan		**783**
Wood	Outdoor	Wall	**627**
Yakarta	Fan		**787**
Yen	Outdoor	Ceiling	**576**
Zon	Indoor	Ceiling	**239**

Sustainability means implementing new models and behaviors that respect the delicate balance of the planet and its vital resources.

Xavier Martin, *CEO*





www.faro.es