

Hexalith® hexagonal tile for system floors in food production facilities


Made in Germany. Our hexagonal Hexalith® tile made of porcelain stoneware is ideal for heavy-duty wet and dry areas in industrial and commercial applications. Its shape facilitates installation, especially for gradients and drainage systems around floor inlets. The tile's joint design ensures particularly even surface finishes and thus minimizes rolling noise caused by dynamic loads. Durable, hygienic and sustainable – the Hexalith tile sets standards in functionality and hygiene standards.





durable. hygienic. sustainable


Hexalith® hexagonal tile


200 Light Grey


220 Titan Grey


230 Anthracite


300 Beige


400 Sand Yellow



510 Mars Red


Hexagonal 108 x 125 mm

Color	Thickness	Surface (slip resistance)					Require-ment Pie-ces/sqm	Content pieces/box	Content sqm/pallet	Weight kg/sqm	Weight kg/pallet
200 Light Grey	15 mm	–	R11	–	–	–	97.5	48	31.01	35.20	1,092
200 Light Grey	18 mm	R10	R11	R12	R12/V06	R13/V10 on request	96.5	40	26.11	41.30	1,079
220 Titan Grey	15 mm	–	R11	–	–	–	97.5	48	31.01	35.20	1,092
220 Titan Grey	18 mm	–	R11	–	–	–	96.5	40	26.11	41.30	1,079
230 Anthracite	15 mm	–	R11	–	–	–	97.5	48	31.01	35.20	1,092
230 Anthracite	18 mm	–	R11	–	–	–	96.5	40	26.11	41.30	1,079
300 Beige	15 mm	–	R11	–	–	–	97.5	48	31.01	35.20	1,092
300 Beige	18 mm	R10	R11	R12	R12/V06	R13/V10 on request	96.5	40	26.11	41.30	1,079
400 Sand Yellow	18 mm	–	R11	–	–	–	96.5	40	26.11	41.30	1,079
510 Mars Red	18 mm	–	R11	–	–	–	96.5	40	26.11	41.30	1,079

We offer other surfaces, thicknesses and special colors on request and from a certain order quantity. Thanks to our in-house processing and state-of-the-art digital printing technology, all colors and designs can be realized. Our current GTC (as of 03/2023) and accessories such as skirting boards, stair treads, coved plinths, internal/external mitre joints, internal/external external mitre joints, internal/external corners and Hexalith inserts can be found on our website: **www.argelith.com**


Surfaces


R10 Smooth


R11/R12 Profiled


R12/R13 with V06-V10

Finishing tiles


Point finishing tiles


Blunt finishing tiles

Finishing tile	Requirement pieces/lm (inl. joint)
Point	9.5
Blunt	4.5

Our service for your project.

Are you planning a project and need support with the selection and ordering of tiles? Do you have questions about technical requirements, patterns or local partners? Use our technical support:

+49 5472 402 651
export@argelith.com

Argelith Bodenkeramik
H. Bitter GmbH
Schledehauser Str. 133
D-49152 Bad Essen

Possible color deviations are due to printing technology.