



## Basics Reed Product Data Sheet

### Description

---

Basics Reed recreates the look, color, and feel of native natural thatching from many regions around the world. Designed for homeowners, our Basics line delivers the look of traditional thatch with the confidence of modern materials, creating outdoor structures that feel inviting and built to last.


### Features

---

- 10 Year Warranty
- No maintenance required
- Manufactured in the USA
- Fast and easy installation

### Components

---



**Field Shingle**



<u>Part Numbers</u>	<b>Sand Willow</b>	<b>Weathered Jute</b>
<b>Field Shingle</b>	SL-HD-GZ-1P-50-202-FS	SL-HD-GZ-1P-50-201-FS

## Specifications

---

Part	Size	Weight	Exposure	Coverage	Material
<b>Field Shingle</b>	42" x 16" (1067mm x 406mm)	3.00lb (1.36kg)	8.5" (215.9mm)	2.47 Sq ft (0.229 Sq M)	HDPE with galvaneal binder

## Packaging & Storage

---

	<b>Field Shingle</b>
<b>Quantity</b>	16 per box
<b>Weight</b>	51lbs (23kg)

\*Weights may vary



### Shipping Specifications

**Box Size:** 44" X 22" X 5" (1120 mm X 560 mm X 130 mm)

**Pallet:** 24 boxes per pallet

**Container:** 20' 10 pallets (240 boxes)    40' 20 pallets (480 boxes)

**Storage:** Store Basics Reed shingles in a dry, well-ventilated, weather tight, location.

Do not expose boxes to excessive moisture.

Overstacking boxes or excessive moisture may cause boxes to collapse.

Do not remove wrapping from the pallet until final placement at installation location.

### **Maintenance**

---

Basics Reed was designed so that no maintenance is required to ensure the best performance. However, it is recommended to do an annual inspection and brush off any loose debris to keep your roof looking its best.

### **Warranty**

---

Basics Reed has a 10 year limited warranty that covers faults in materials and workmanship in accordance with warranty terms.



## Application

---

Basics Reed is a universal system that can be installed on new construction or retrofit to existing structures. The versatile design allows it to be applied to a number of roofing substrates including the following: Plywood deck and Metal. Basics Reed synthetic thatch is suitable for use on any sloped roof with a pitch of 3:12 (14°) or greater. The total thickness of the roof system when installed is 1" (25.4mm).

### Plywood Deck:

- 15/32" (12mm) minimum plywood over rafters per local code
- Single Layer Tan Soprema Elastophene Stick HR FR+ GR Cap Sheet(#07066) adhered to plywood
- Basics Reed shingles installed at 8.5" (215.9mm) Exposure
- Fasten Basics Reed shingles with stainless steel 1.75" (45mm) 11ga. Ring shank roofing nails, 4 per shingle

### Metal:

- Existing corrugated metal roofing
- 15/32"(12mm) minimum plywood
- Single Layer Tan Soprema Elastophene Stick HR FR+ GR Cap Sheet(#07066) adhered to plywood
- Basics Reed shingles installed at 8.5" (215.9mm) Exposure
- Fasten Basics Reed shingles with stainless steel 1.25" (32mm) 11ga. Ring shank roofing nails, 4 per shingle.



Endureed Basics thatch manufactured by:  
Global Innovation LLC

313 SW Windswept Glen  
Lake City, Florida 32024

1-877-784-2824  
[endureed.com](http://endureed.com)