

**CHICAGO
FAUCETS®**
Geberit Group

HyTronic® With TempShield® Scald Protection

Durable, dependable, and now with **integrated scald protection.**



TempShield®
Available with integrated
ASSE 1070 Certified
scald protection.

HyTronic® with Integrated Scald Protection

A new solution for safe, touchless convenience.

Proven dependability and integrated **ASSE 1070 Certified Scald Protection** helps make HyTronic touchless faucets the very best solution for safety and hygiene. Above-deck components and the CF Connect App combine for easy adjustment and maintenance.

Benchmark for Durability

Heavy duty cast brass construction with a refined polished chrome finish.



Easy to Service

All components are above-deck for easy access and routine maintenance without shutting off water.

Best Sensor in the Industry

Twin-beam infrared system responds quickly, adjusts to environmental changes, and minimizes false activations.

User Adjustable

Available with user **adjustable temperature control** for improved user experience.



Easy to Adjust

The CF Connect App provides a secure and easy way to adjust and maintain the faucet with a smartphone.

- Hygiene Flush eliminates stagnant water from the plumbing system and removes harmful bacteria
- Six field-adjustable modes for metering, water savings, and detection ranges
- Track Usage



Integrated ASSE 1070 Certified Scald Protection



Built-in scald protection means:

- Faster installation and lower labor costs
- Fewer potential leak points
- Safer installation, every time

Pick a style to match your application.

We offer a choice of three distinct spout styles, including our popular gooseneck spout, to meet your needs.



Choice of advanced power options.

Also available in AC Plug-In or Hard-Wire and DC Lithium CRP2 Battery.



Maintenance-free power for 15 years or more.



Integrated backup power system for AC faucets.

Codes & Standards

Certified per ASSE 1070/ ASME A112.1070 / CSA B125.70
Certified to ASME A112.18.1/CSA B125.1 and NSF/ANSI 61, Section 9
NSF/ANSI 372 Low Lead Content



Complies with ADA requirements as specified in the Americans with Disabilities Act.

HyTronic® With TempShield® touchless faucets

- Choice of: AC, DC, Long Term Power Supply (LTPS)
- CF Connect App allows easy monitoring and adjustments with a smartphone or tablet



Traditional Spout

	Power Source			Mixer	
	AC	DC	LTPS	Concealed	User Adjustable
0.5 GPM Non-Aerating Laminar Spray Outlet					
H-T11H-43ABCPT	■	—	—	■	—
H-T11H-45ABCPT	■	—	—	—	■
H-T11H-13ABCPT	—	■	—	■	—
H-T11H-15ABCPT	—	■	—	—	■
H-T11H-63ABCPT	—	—	■	■	—
H-T11H-65ABCPT	—	—	■	—	■



Contemporary Spout

	Power Source			Mixer	
	AC	DC	LTPS	Concealed	User Adjustable
0.5 GPM Non-Aerating Laminar Spray Outlet					
H-C31H-43ABCPT	■	—	—	■	—
H-C31H-45ABCPT	■	—	—	—	■
H-C31H-13ABCPT	—	■	—	■	—
H-C31H-15ABCPT	—	■	—	—	■
H-C31H-63ABCPT	—	—	■	■	—
H-C31H-65ABCPT	—	—	■	—	■



Gooseneck Spout, 5-1/4" C-C

	Power Source			Mixer	
	AC	DC	LTPS	Concealed	User Adjustable
0.5 GPM Non-Aerating Laminar Spray Outlet					
H-G11H-43ABCPT	■	—	—	■	—
H-G11H-45ABCPT	■	—	—	—	■
H-G11H-13ABCPT	—	■	—	■	—
H-G11H-15ABCPT	—	■	—	—	■
H-G11H-63ABCPT	—	—	■	■	—
H-G11H-65ABCPT	—	—	■	—	■
Plain Spout End With 1.5 GPM Flow Control In The Spout Base					
H-G11K-43ABCPT	■	—	—	■	—
H-G11K-45ABCPT	■	—	—	—	■
H-G11K-13ABCPT	—	■	—	■	—
H-G11K-15ABCPT	—	■	—	—	■
H-G11K-63ABCPT	—	—	■	■	—
H-G11K-65ABCPT	—	—	■	—	■



Gooseneck Spout, 6" C-C

	Power Source				Mixer	
	AC	DC	LTPS	EBPS	Concealed	User Adjustable
Plain Spout End With 1.5 GPM Flow Control In The Spout Base						
H-G61K-43ABCPT	■	—	—	—	■	—
H-G61K-45ABCPT	■	—	—	—	—	■
H-G61K-13ABCPT	—	■	—	—	■	—
H-G61K-15ABCPT	—	■	—	—	—	■
H-G61K-63ABCPT	—	—	■	—	■	—
H-G61K-65ABCPT	—	—	■	—	—	■
H-G61K-75ABCPT	■	—	—	■	—	■

How to read the HyTronic® With TempShield® model number

Position	1	2	3	4	5	Finish
H-	XX	1	X	-	X	ABCPT

Model number example: H-T11H-15ABCPT

This is a HyTronic (H) with a traditional spout (T1), single hole mount (1), 0.5 GPM laminar outlet (H), battery power (1), with a user-adjustable mix (5), lead-free (AB), polished chrome finish (CP), and CF Connect compatible (T).

Model Number Reference Chart

Position	Feature	Code	Description
1	Spout Design	C3	Contemporary Spout
		T1	Traditional Spout
		G1	GN2 Gooseneck Spout
		G6	GN6 Gooseneck Spout
2	Mounting	1	Single Hole Mounting
3	Flow Control	H	0.5 GPM Laminar Flow Outlet
		K	1.5 GPM Internal Flow Control

Position	Feature	Code	Description
4	Power Source	1	Battery (DC) Power
		4	AC Power Less Transformer
		6	Long Term Power System (LTPS)
		7	Emergency Backup Power Supply (EBPS)
		3	Internal Mixer
5	Mixing	5	User Adjustable Mixer

The Smart Choice For Touchless Solutions.

We offer an extensive line of touchless solutions for every application. To learn more, visit chicagofaucets.com or contact us directly to discuss your requirements.

847/803-5000

customerservice.us@chicagofaucets.com

Visit chicagofaucets.com/support/where-to-buy to find a Sales Representative or plumbing distributor near you.



Scan to see our complete line of touchless products.

**CHICAGO
FAUCETS**
Geberit Group

Chicago Faucets, a member of the Geberit Group, is the leading brand of commercial faucets and fittings in the United States, offering a complete range of products for schools, laboratories, hospitals, office buildings, food service, airports, and sports facilities. Whatever your requirements may be, Chicago Faucets offers standard and made-to-order products that are designed to meet any commercial application.

© 2024 The Chicago Faucet Company. Product specifications subject to change without notice.

CF2188 10/24

2100 South Clearwater Drive, Des Plaines, IL 60018

Phone: 847/803-5000 | Fax: 847/849-1845 | Technical: 800/832-8783 | www.chicagofaucets.com

