

# TEAM collection



design by  
Marco Acerbis

Platek®

TEAM collection

item code: DOC\_TEAM

This document is available for  
download from our website  
[www.platek.eu](http://www.platek.eu)

The data in this document are valid  
on the print date indicated above.  
Any updates are available  
on our website [www.platek.eu](http://www.platek.eu)

THANKS TO


MARCO ACERBIS

# TEAM collection

design by  
Marco Acerbis

**Platek®**

# wall recessed step light bollard





TEAM bollard


ARCHITECTURAL OUTDOOR LIGHTING

Wall mounted step marker with great elegance and ability to play with the environment light when switched off, due to the side winglets that draw the profile. Available in three different shapes (square, rectangular and round) and with specifically engineered

optical system to have the widest opening beam. Team can be powered by a cable from the wall or can be composed in series by connecting elements with an external line. The product is available as a bollard, with single and double emission.

ARCHITECTURAL OUTDOOR LIGHTING



















TEAM  
wall recessed / step light




IP66  
round: IK 09  
other versions: IK 08

ø 160 mm  
140 x 140 mm  
260 x 140 mm

IP68 connector included

TEAM  
bollard



IP66  
IK 08

280 x 102 x h. 600 mm  
280 x 102 x h. 900 mm

IP68 connector included

on request finishes



standard finishes



TEAM wall recessed / step light

WHITE LED

3000K CRI>80  
220-240V 50/60Hz Ⓢ  
TRIAC dimmable

2700K / 4000K  
available on request

→ round



8W | 410 lm (\*)  
asymmetrical

→ square



8W | 395 lm (\*)  
asymmetrical

→ rectangular



17,5W | 890 lm (\*)  
asymmetrical

TEAM bollard

WHITE LED

3000K CRI>80  
220-240V 50/60Hz Ⓢ  
TRIAC dimmable

2700K / 4000K  
available on request

→ h. 600 mm single emission



8W | 410 lm (\*)  
asymmetrical

→ h. 600 mm double emission



8W | 395 lm (\*)  
asymmetrical

→ h. 900 mm single emission



17,5W | 890 lm (\*)  
asymmetrical

→ h. 900 mm double emission



35W | 1780 lm (\*)  
asymmetrical

(\*) Real Data

Platek Srl  
Registered Office: Via Paderno, 19  
Head Office: Via Marrocco, 4  
25050—Rodengo Saiano (BS),  
Italy  
P.Iva 03320290178  
C.F. 03007130176

T +39 030 68 18 201  
F +39 030 68 16 567  
info@platek.eu  
www.platek.eu

Art Direction  
Gusto IDS  
Platek  
  
Graphic design  
Gusto IDS  
Platek

Photo  
Metalli Photo Design  
Ottavio Tomasini  
Germano Borrelli  
Archivio Platek

© Platek 2020

Platek online  
[facebook.com/platek](https://facebook.com/platek)  
[twitter.com/platek](https://twitter.com/platek)  
[instagram.com/platek](https://instagram.com/platek)  
[youtube.com/platek](https://youtube.com/platek)  
[pinterest.it/platek](https://pinterest.it/platek)

