

$LAKECREST^{M}$

igner faucets

Beauty without compromise

Sophisticated design blends with commercial durability in the elegant LakeCrest line by T&S Brass. These stylish faucet designs bring a touch of refinement and legendary reliability to busy, modern facilities.

LakeCrest designer manual faucets are designed and built by T&S Brass and Bronze Works, a leading commercial-grade plumbing manufacturer with a history of unmatched reliability and durability for 75 years.



COMMERCIAL-GRADE CONSTRUCTION WITH LONG-TERM RELIABILITY

LakeCrest's durable elegance makes this new line ideal for modern, high-traffic facilities, such as:

- Contemporary office buildings
- Colleges & universities
- Hospitality & lodging
- Public facilities, such as airports and stadiums
- Communal areas in assisted living facilities
- Restaurant restrooms



LAKECREST[™]

COMMERCIAL FAUCETS with a modern aesthetic appeal

Gorgeous lines blend with commercial durability in tasteful, high-performance faucets.

MODELS



BP-0723 SINGLE HOLE METERING FAUCET

- Polished chrome finish
- Vandal resistant 0.5 GPM hidden non-aerated spray device^{*}
- Single temperature
- Push-button metering cartridge
- Can be paired with T&S universal deck plate

BP-2704

SINGLE HOLE DECK-MOUNT SINGLE LEVER FAUCET

- Polished chrome finish
- Ceramic cartridge
- Vandal resistant 0.5 GPM nonaerated spray device*
- Can be paired with T&S universal deck plate

BP-2704-BN

SINGLE HOLE DECK-MOUNT SINGLE LEVER FAUCET

- Brushed nickel finish
- Ceramic cartridge
- Vandal resistant 0.5 GPM nonaerated spray device*

BP-2704-MB

SINGLE HOLE DECK-MOUNT SINGLE LEVER FAUCET

- Matte black finish
- Ceramic cartridge
- Vandal resistant 0.5 GPM nonaerated spray device*

*Optional outlet devices available upon request:

- 0.35 GPM Non-Aerated Spray Device (V035 CALGreen)
- 1.0 GPM Concealed Aerator (V10 California CEC Title 20)
- 1.5 GPM Concealed Aerator (V15 EPA WaterSense)
- 1.5 GPM Concealed Laminar Flow Device (VL15 Healthcare/Medical)









BP-2712

4" CENTERSET DECK-MOUNT SINGLE LEVER FAUCET

- Polished chrome finish
- Ceramic cartridge
- Vandal resistant 0.5 GPM nonaerated spray device*

BP-2712-BN

4" CENTERSET DECK-MOUNT SINGLE LEVER FAUCET

- Brushed nickel finish
- Ceramic cartridge
- Vandal resistant 0.5 GPM nonaerated spray device^{*}

BP-2712-MB 4" CENTERSET DECK-MOUNT SINGLE LEVER FAUCET

- Matte black finish
- Ceramic cartridge
- Vandal resistant 0.5 GPM nonaerated spray device*

BP-2995

8" EASYINSTALL CONCEALED WIDESPREAD LAVATORY FAUCET

- Polished chrome finish
- Widespread lever handles
- Quarter-turn ceramic cartridges with check valves
- Lavatory spout with vandal resistant 0.5 GPM hidden nonaerated spray device*

S-2770

SEMI-PRO KITCHEN FAUCET

- Brushed stainless steel finish
- Deck-mount single lever faucet
- Ceramic cartridge
- 1.5 GPM Semi-Pro aerator and
 1.5 GPM Concentric spray device
- Detachable sprayer with magnetic latch
- Toggle for switching between aerator and sprayer
- 21" flexible stainless steel hose with spring









