



TABLE OF CONTENTS

Trimboard.....	06	VERSAWRAP®.....	20
Sheet.....	08	Soffit system.....	24
Tongue & groove profiles	10	Mouldings.....	26
XCEED Siding.....	12	Canvas Series®.....	28
Stealth Trim System	16	Finishing Systems.....	34
Corners	18		



VERSATEX Sheet, Corners, Trim Boards,
and VERSAWRAP Column Wraps



The PVC specialist

For more than 20 years, VERSATEX has been laser-focused on cellular PVC building materials, particularly trim. To meet our customers’ needs, we deliver the broadest PVC trim profile assortment in the industry. We are constantly improving to give our customers the highest quality products backed up with expert technical assistance. Engineering breakthroughs and manufacturing excellence deliver results like thickness tolerances that are half the industry norm and industry-first thicker products with the same tight tolerances.

Better material for your project

Compared to other siding and trim materials, PVC is a top choice. It’s virtually impervious to moisture, making it ideal for coastal, waterfront, or high-humidity environments. It’s as workable as wood, delivering outstanding aesthetics, but doesn’t need constant maintenance to try and stop wood’s inevitable decay and rot.

Better for contractors and homeowners

VERSATEX product development is bringing new designs to market, like XCEED Siding, streamlining the contractor’s job and delivering high quality, long-lasting options to homeowners. We work to make installing the best exterior solutions easy. Customers like the elevated look, low maintenance, and the industry-leading, fully transferrable, non-prorated Limited Lifetime Warranty.

Better for a sustainable world

We’re focused on manufacturing long-lasting PVC building materials that disrupt traditional materials’ repaint, repair, and replace cycle. We’ve installed new equipment that reduces our water consumption by 4 million gallons, and we reuse or recycle 99% of the scrap we produce. Constantly increasing our products’ recycled content – without compromising performance – further reduces our environmental impact.





PVC delivers superior performance to wood

On day one, VERSATEX exterior materials and wood will look essentially identical. But every week and month afterward, wood will likely move, start losing paint, and even deteriorate — cracking, swelling, and rotting — from moisture. PVC has no troublesome knots, grains, finger joints, or inconsistencies the way wood does. It's highly resistant to any tough weather condition, and it can be thermoformed, routed, laminated, or milled into curves and other architectural details.

VERSATEX delivers a superior PVC

Any other PVC is not VERSATEX PVC. We're proudly made in Aliquippa, Pennsylvania, supported by research, innovation, and customer service you won't find with imported, marginal quality PVC. Our manufacturing tolerances are 1/32" and our formulation has no cheap fillers like limestone dust, which grays over time and creates a more brittle board. Instead, our rich use of titanium dioxide keeps our products a bright white longer and protects against UV rays.



XCEED Siding in Stonewall Shade
VERSAWRAP Column Wrap Classic



XCEED Siding in Sequoia Green



**Class A Flame
Spread Rating**



**Moisture & Rot
Resistant**



**Color Fade &
Weather Resistant**



**Insect
Resistant**



**Easy to
Paint**



**Limited Lifetime
Warranty**



Trimboard



We started with trim and grew from there

VERSATEX specializes in cellular PVC building materials, so we take great pride in our first product, the nominal trimboard. And when it comes to dimensions, our selection is hard to beat: widths from 2" to 16", thicknesses from 5/8" to 1-1/2", and standard lengths up to 20'. We supply this extensive range of sizes to meet our customers' needs and to make their jobs just a bit easier.



Why VERSATEX is a better trim

- Moisture absorption is minimal, so there's no swelling or moving and no need to paint for protection
- PVC is not attractive to destructive insects and other pests
- Our Matte Bright White color is formulated to last for decades, both on smooth and Timber Ridge (woodgrain) textures
- Dimensions and angles are consistently precise, with true 90-degree angles +/- one degree
- Lightweight and easy to shape and form with routers and milling tools

		THICKNESS				
		5/8" (5/8" actual)	1" (3/4" actual)	5/4" (1" actual)	6/4" (1-1/4" actual)	8/4" (1-1/2" actual)
WIDTH						
Nominal	Actual					
2"	1-1/2"		•			
3"	2-1/2"		•			
4"	3-1/2"	•	•	•	•	•
5"	4-1/2"		•	•		
6"	5-1/2"	•	•	•	•	•
8"	7-1/4"	•	•	•	•	•
10"	9-1/4"	•	•	•	•	•
12"	11-1/4"	•	•	•	•	•
16"	15-1/4"	•	•	•		

- 5/8", 1", and 5/4" available in standard 12', 18', and 20' lengths; 6/4" and 8/4" available in standard 18' lengths
- 5/8", 1", and 5/4" boards come with protective film applied. 2" width boards are **not** offered with film
- Custom lengths and widths available in "Smartpack" quantities
- 8/4" thick trimboards and sheets as well as 6/4" sheets and special length Trimboards are subject to extended lead times
- 6/4" and 8/4" do not have sealed edges
- Most thicknesses can be ordered reversible - Smooth/Timber Ridge or Smooth/Smooth



Sheet



Innovating to make your jobs easier

For years, contractors, OEMs, and millwork houses have asked for a true 1-1/2" thick cellular PVC sheet – an ask more difficult than it seems. VERSATEX delivered a PVC sheet that was not only thicker but maintains the same industry-best 1/32" tolerance and core density of all sizes of our wide variety of sheet products. Now it's easier to create thick pergola rafters, window casings, panels, custom mouldings, and more.



Ready for your craftsmanship

VERSATEX features the most comprehensive sheet stock available, ranging from as thin as 1/4" to a full 1 1/2". We manufacture the most consistent sheet product in the industry, using high-tech extrusion technology to control sheet thickness. Our 1/32" tolerances are half that of competitors. Board and batten, accent walls, gables, and more are now a breeze, providing builders and fabricators high yields, less scrap, and a higher quality finished product.



		THICKNESS							
		¼"	3/8"	½"	5/8"	3/4"	1"	1-1/4"	1-1/2"
Width	Length								
4'	8'	●	●	●	●	●	●	●	●
4'	10'	●	●	●	●	●	●	●	●
4'	12'		●	●	●	●	●	●	●
4'	18'		●	●	●	●	●	●	●
4'	20'			●	●	●	●		

• Custom lengths and widths available in "Smartpack" quantities
• 5' wide sheets available in certain sizes and special quantities are subject to extended lead times
• 1-1/2" thickness are subject to extended lead times, All sizes except 1/4", 1-1/4", and 1-1/2" thickness available in Timber Ridge




Tongue & groove profiles



Stealth: faster install and better curb appeal

Stealth Beadboard profiles feature an extended nailing surface for a hidden fastening area, reducing blemishes, nail hole filling, and install time. It also means a more secure, wind-resistant install.



Beadboard Stealth Beadboard Piazza Blue Stealth Beadboard WP4/Nickel Gap



More options, greater flexibility

VERSATEX manufactures the widest range of PVC tongue & groove profiles in the industry, so customers have the materials they need to create their best projects. Each profile is optimized for design and installation flexibility. For example, WP4 profiles are reversible, offering a sleek and consistent Nickel Gap profile, and 1/2" and 3/4" beadboard thicknesses meet nearly every project requirement.

WIDTH		LENGTH		
		8'	10'	18'
Nominal	Actual			

BEADBOARD				
1/2 x 4	1/2" x 3-1/2"			●
1/2 x 6	1/2" x 5-1/2"			●
1 x 6	3/4" x 5-1/2"			●

STEALTH BEAD				
1/2 x 4	1/2" x 4"			●
1/2 x 6	1/2" x 6"			●

BEADED SHEET				
1/2 x 48	1/2" x 48"	●	●	

WP4/NICKEL GAP				
1 x 6	3/4" x 5-1/2"			●
1 x 8	3/4" x 7-1/4"			●

SHIPLAP/NICKEL GAP				
1 x 6	3/4" x 5-1/2"			●
1 x 8	3/4" x 7-1/4"			●

- Special 3/4" x 3-1/2" x 18' standard beadboard available in "UNIT" quantities
- End-matched WP4 available in 16' lengths via special order
- Shiplap/Nickel Gap is reversible





XCEED Siding



Traditional curb appeal with lifetime performance

XCEED Siding is a solid board made from a proprietary blend of VERSATEX cellular PVC, capped with a durable lifetime color that won't need repainting. It's naturally resistant to water and insects, and unlike hollow-back vinyl siding, XCEED also resists dents and temperature extremes.

Years down the road, you can expect your XCEED Siding job to look as good as when it was installed. It doesn't need regular maintenance beyond an occasional wash with a garden hose, and with a Limited Lifetime Warranty, homeowners get peace of mind.



PVC makes XCEED a superior siding

Cellular PVC delivers lasting beauty and protection you can trust, because unlike wood, it's not affected by moisture. XCEED performs even in moisture-prone areas, at or below grade, along rooflines, and around gutters, where wood breaks down. And the look is far superior to vinyl siding and its hollow-back, overlapping seams and tendency to fail in extreme weather.




Personalize with color and reveal choices

Select the traditional 4-1/2" reveal or the contemporary 7-1/2" to fit the home's design. Ten colors offer a variety of handsome options to choose from.



4-1/2" LAP SIDING

Gives a clean, classic style



7-1/2" LAP SIDING

Creates a bold, modern aesthetic



XCEED SIDING

Flawless parallel lines:
XCEED makes it easy

XCEED boards utilize a hidden nail hem butt joint bracket to keep joints tight and invisible. All you see is a continuous run of smooth, parallel beauty, worthy of the best house on the block.

Engineered for simple,
secure installs

- Once level is established with the starter strip and the first course, the following interlocking courses maintain established level.
- Each board interlocks into the course below, reducing installation time and labor, plus helping protect against wind lift.
- XCEED Siding and Stealth Trim are lightweight and easy to move without damage.






Stealth Trim System



The trim engineered for XCEED – or any other siding

VERSATEX had the builder in mind when designing the Stealth Trim System. Products are engineered with customizations that allow for faster and more aesthetically pleasing installations. Deep pockets (1-1/8" for 4", 1-1/2" for 6" up) accommodate any siding material such as fiber cement, cedar, and vinyl while the Stealth Skirtboard solves the issue of installing porous material at grade.



		LENGTH
THICKNESS		18'
Nominal	Actual	
STEALTH SKIRTBOARD		
1 x 8	3/4" x 7-1/4"	S T
STANDARD STEALTH, STEALTH W/ FLANGE, & TRIM W/ FLANGE		
5/4 x 4	1" x 3-1/2"	S T
STANDARD STEALTH, STEALTH W/ FLANGE, TRIM W/ FLANGE & STEALTH SKIRTBOARD		
5/4 x 6	1" x 5-1/2"	S T
STANDARD STEALTH & STEALTH SKIRTBOARD		
5/4 x 8	1" x 7-1/4"	S T
STEALTH CASING W/ J-CHANNEL		
	1-1/8" x 3-1/2"	S
	1-1/8" x 5-1/2"	S
Product Finish Key		
	Smooth S	Timber Ridge T



- Custom lengths and widths available in "Smartpack" quantities
- 5' wide Sheets available in certain sizes and special quantities are subject to extended lead times





Corners




No seams,
better performance

VERSATEX one-piece corners eliminate caulk, vulnerable seams, and onsite fabrication. The result is a crisp corner and an elevated appearance.



The original one-piece corner

Driven by innovation to help those on the job site, VERSATEX was the first PVC trim company to create a one-piece corner. We now offer a Standard Corner, Stealth Corner Inside Corner, and Stealth Hidden Fastener Corner. Jobsite-fabricated two-piece corners collect dust and dirt along their outside edges and seams, making it inevitable that projects will look unsightly over time. Our one-piece corners are easier to install and also require less maintenance, while offering a clean and bright, aesthetically superior solution. And now, Stealth Standard and Inside Corner have a 1-1/8" to 1-1/2" deep pocket compatible with virtually any siding product make VERSATEX corner options the best in the industry.



STANDARD & STEALTH CORNERS		LENGTH		
		10'	20'	22'
THICKNESS				
Nominal	Actual			
1" x 6"*	3/4" x 5-1/2"		S	
5/4" x 4"	1" x 3-1/2"	S T	S T	S
5/4" x 6"	1" x 5-1/2"	S T	S T	S
5/4" x 8"	1" x 7-1/4"		S	

*Stealth Corner not available in nominal 1" x 6"

- Special 12' and 22' Corners available in "UNIT" quantities
- Custom widths up to 10" available in "UNIT" quantities
- 10' and 20' Corners available in "Smartpack" quantities

STEALTH HIDDEN FASTENER CORNER		LENGTH	
		20'	
THICKNESS			
Nominal	Actual		
5/4" x 2"	1-1/8" x 1-1/2"	S	
5/4" x 4"	1-1/8" x 3-1/2"	S	
5/4" x 6"	1-1/8" x 5-1/2"	S	

Product Finish Key

Smooth

S

Timber Ridge

T



Stately columns with simplified installation

Covering a structural post is almost always a challenging task. The VERSATEX field-focused team set out to eliminate matching up four individual post cover pieces and create a way to deliver a higher aesthetic appearance with effortless, nearly zero onsite fabrication. For a lally column, support beams, front porch posts, or anything in between, wrapping posts with VERASAWRAP is a one-person install with a better final result than ever before.

The VERSAWRAP line includes one-piece Classic and Raised Panel designs with multiple crown and base accessories available. A pre-cut, Craftsman-style, four-piece tapered design completes the product offering.



Classic Wrap



Raised Panel



CLASSIC VERSAWRAP			LENGTH			RAISED PANEL VERSAWRAP			LENGTH	
			8'6"	10'	12'				8'6"	10'
THICKNESS						THICKNESS				
Nominal	Actual Inside	Actual Outside				Nominal	Actual Inside	Actual Outside		
4 x 4	3-3/4" x 3-3/4"	4-3/4" x 4-3/4"	●	●		6 x 6	5-3/4" x 5-3/4"	6-3/4" X 6-3/4"	●	●
6 x 6	5-3/4" x 5-3/4"	6-3/4" X 6-3/4"	●	●						
8 x 8	8-1/2" x 8-1/2"	9-1/2" X 9-1/2"	●	●						
12 x 12	9-3/4" x 9-3/4"	11-1/4" X 11-1/4"			●	8 x 8	8-1/2" x 8-1/2"	9-1/2" X 9-1/2"	●	●

- Special 10" Classic wraps available (minimum quantities apply)
- All 4", 6", and 8" VERSAWRAPs are made from actual 1/2" thick VERSATEX; 12" wraps are made from actual 3/4" thick VERSATEX
- Raised Panels start 16-1/2" from bottom with a railing gap from 30-3/4" to 38-1/2"; clearance above top panel measures 8-3/4"
- Painting of Raised Panel wraps is recommended for best aesthetic results and to prevent dirt accumulation where panels are milled into product



VERSAWRAP® Accent Wrap



Add architectural sophistication

VERSATEX offers all the accessories you need to take your project to the next level. Base Cap, Bed Moulding, and 4" Crown Moulding kits are all available, while Bed Moulding and 4" Crown Moulding XL kits are available to dress up accent wraps. They're pre-mitered, cut to length, and ready for an easy assembly and a snug fit around a 4", 6", or 8" VERSAWRAP. Post Caps are also available for 4", 6", and 8" VERSAWRAPs. All accessories are sold separately.

Nominal	Actual Inside Dimension
4 x 4 x 10	4-3/4" x 4-3/4" x 10"
6 x 6 x 10	6-3/4" x 6-3/4" x 10"
8 x 8 x 10	9-1/2" x 9-1/2" x 10"

- Nominal 10 x 10 x 10' Accent Wraps are available in "UNIT" quantities
- Add 1" to inside dimensions to calculate outside measurements




VERSAWRAP® Tapered Wrap



Fine woodwork details made easy

Our four-piece tapered column wrap provides the same convenience of the one-piece VERSAWRAP for Craftsman-style projects. Four pre-cut panels each have a friction-fit miter lock joint to eliminate calculations and cuts. The correct angle for each panel is ensured. Fastening angles and 3-1/2" decorative accent wrap pieces are included with the wrap for the cap and base of each tapered column to fasten and accessorize as the project requires. There is no quicker and easier way to deliver a Craftsman aesthetic.

	5'	6'
12" base – 8" cap	●	●
16" base – 12" cap	●	●





Soffit system



Airflow made easy

VERSATEX continually looks for new ways to help reduce labor time and improve aesthetics during installation. We introduced the first-ever Vented Cellular PVC Soffit System to create a one-stop shop for easy ventilation. The Vented Soffit features 10 square inches of free airspace per linear foot, making it one of the most superior airflow systems in the market. The vents are cut to prevent nesting insect infiltration while still being able to be screened when required by code. Notched fascia and frieze boards have a pre-mitered 9/16" pocket to accept 1/2" solid or vented VERSATEX Soffit.

SOFFIT BOARDS	18' Vented	18' Solid
	Actual	
1/2" x 12"		
1/2" x 16"		
1/2" x 24"		

NOTCHED FASCIA	18'	
	Nominal	Actual
1 x 8	3/4" x 7-1/4"	

FRIEZE BOARD	18'	
	Nominal	Actual
5/4 x 6	1" x 5-1/2"	

Product Finish Key

Smooth

Timber Ridge



Mouldings

VERSATEX Exterior Moulding delivers more profiles and more choices to add detailed beauty to any job. Plus, its low-gloss, matte finish and durable extruded PVC material* gives you the performance you depend on.

Crown Profiles

3" Crown
PCB3"CROWN

4" Crown
PCB4"CROWN

5" Crown
PCB5"CROWN

6" Crown
PCB6"CROWN

8" Crown
PAB8CROWN

Solid Crown
PCBSOLIDCROWN

Rams Crown
PCBRAMSCROWN

Imperial Rake
PCBIMPERIALRAKEMOUL

Pediment Crown
PCBPEDIMENT - 12'

Bed Mould
PCBBEDMOUL

Sill Profiles

Sill
PCBSILL

Historic Sill
PCBHISTORICSILL

Heavy Sill Nose
PCBHEAVYSILLNOSE

Double Hung Sill
PSCDOUBLEHUNGSILL - 18'

Sill Nose
PCBSILLNOSE

Sub Sill Nose
PCBSUBSILLNOSE

Casing Profiles

Brick Mould
PCBBRICKMOUL - 18'

Brick w/ Flange
PCBBRICKMOULDW/F - 18'

J-Channel Brick
PCBJBRICK - 18'

Adams Casing
PCBADAMSCASING

Crosshead Pediment
PAPEDIMENT - 18'

Base Cap
PCBBASECAP

Rake Mould
PCBRAKEMOUL

Backband
PCBBACKBAND

Cove Profiles

Baluster
PCBBALUSTER

Scotia
PCBSCOTIACOVE

Quarter Round
PCBQTRROUND

Nose Cove
PCBNOSECOVE

Additional Profiles

Water Table
PCBWATERTABLE - 18'

Panel Mould
PCBPANEL

T-Mould
BBTMOUL - 12'

Shingle Mould
PCBSHINGLEBAND

Beadboard Cap
PABEADCAP

Drip Cap
PCBDRIPC

Louver Blades
PCBLOUVER175 - 12'

Garage Seal
PCBGARAGEDOORSEAL



Canvas Series®



Weathered Grey

Finished hardwood look with VERSATEX PVC durability

The Canvas Series® by VERSATEX delivers the rich look of premium stained wood and the ultra-low maintenance of cellular PVC. Exterior-grade, realistic wood-tone laminates are bonded to our WP4, Stealth Beadboard, 4" Crown and Bed Mould, and now VERSAWRAP® column wraps and dimensional trimboard profiles. Projects go faster without the need for labor-intensive staining and last longer with the moisture- and insect-resistance that is synonymous with VERSATEX PVC.



Turner Oak

*Versatex is recommended for exterior applications. Consult your local jurisdictional official or design professional for use in other locations.



Walnut



Kitami

Worry-free woodgrain finish choices

Offered in a wide variety of lightly textured, low-gloss finishes, the Canvas Series is the solution to any project's porch ceiling, soffit, wainscoting, and other exterior applications.



Natural Amber




Driftwood



Turner Oak




Copper



Natural Macore



Walnut



Champagne Oak



Weathered Grey



Kitami

Due to print resolution limitations, product colors may not appear exactly as shown. Refer to a product sample before final selection; please check with your dealer.



Walnut



Weathered Grey



Driftwood




Natural Amber



Kitami

Hidden fastening for a flawless look

Traditionally, face nailing is used for installing WP4 or beadboard profiles. Unfortunately, even the best craftsman can leave blemishes and an unsightly finished product. The VZclip works with VERSATEX WP4 profiles to fasten boards securely and speed up installation times, with no face nailing. The recommended fastener for the VZclip is a #8 x 1-5/8" coarse thread construction screw.



For invisible top-down fastening, we offer the STARBORN PRO PLUG® system with matching plugs.

Installation tip: To minimize pattern repeating, install the boards by rows, not by columns.

Profile	Actual
WP4	3/4" x 5-1/2"
Stealth Bead	1/2" x 6"
4" Crown	9/16" x 3-5/8"
Bed Mould	9/16" x 3-5/4"

LENGTH	
16'	18'
	•
	•
•	
•	



Canvas Series® Trim Boards

To answer the overwhelming demand from our customers, we created Canvas Series Trim Boards. Their woodgrain laminate covers three sides of the board and wrap slightly onto the fourth side, minimizing the need for touch ups. They are great for beam wraps, accent walls, or other areas where you need a beautiful wood look with near-zero maintenance. Boards can be cut or ripped down to custom size and edges finished with Canvas Series markers or daubers to conceal the exposed white core.

Available in all 9 colors

	18'
Actual	
1" x 8"	•
1" X 12"	•



Canvas Series® VERSAWRAP®

Wrap beams and posts with the rich look of premium stained wood with the low-maintenance convenience of VERSATEX. Natural wood-tone laminates are bonded onto 4-piece VERSAWRAP PVC profiles, eliminating the need for labor intensive re-staining and adding the durability, moisture- and insect-resistance of cellular PVC.

Available in Natural Amber,
Turner Oak, and Kitami

Accessories

- 10" 4-piece accent wrap
- Base moulding kits (cut to size with Hofmann Dovetail connectors)

	10'
Actual	
6" x 6"	•





Finishing Systems



XCEED Siding Nail Hem Bracket



VZClip



#20 Biscuits

Products to streamline any job

VERSATEX ensures builders have everything they need to make installation as trouble-free as possible. #20 biscuits are specifically made for VERSATEX PVC in any edge-to-edge biscuit joint application. VZClips allow for quicker and stronger install of WP4 & Nickel Gap profiles, and Weld-On 705 is our adhesive of choice, having an approximate 3-5 minute set time and closely matching board color.


Quantity	
Product	
#20 Biscuits	25/box; Cases contain 10 boxes
VZClip	Boxes contain approx. 315 clips
Stainless Steel VZClip	Boxes contain approx. 315 clips
Weld-On Can - Clear	4 oz8 oz
Weld-On Can - White	16 oz32 oz
Weld-On Squeeze Tube	5 oz (white only)
Canvas End Cut Coating	Cases contain 10 daubers



#20 BISCUITS



VZCLIP



WELD-ON 705



CANVAS END CUT COATING

Where we're from is who we are



Aliquippa, Pennsylvania, is the heart of where the U.S. built the 20th century, making steel, bridges, glass, and machinery. Today, VERSATEX's two factories on the banks of the Ohio River produce the exterior siding, trim, and moulding that are revolutionizing home construction in the 21st century. Our people share the grit and determination of the workers who were here before us, and we proudly carry on the tradition of one town serving an entire nation.



400 Steel Street, Aliquippa, PA 1500
(724) 857-1111 | [VERSATEX.com](https://www.versatex.com)

© 2026 Versatex Building Products, LLC and its affiliates. All rights reserved.

VERSATEX®
BUILDING PRODUCTS