

ETEREA collection



design by
Danesi & Buzzoni

Platek®

ETEREA collection

item code: DOC_ETEREA
This document is available for
download from our website
www.platek.eu

The data in this document are valid
on the print date indicated above.
Any updates are available
on our website www.platek.eu

THANKS TO

DANESI & BUZZONI

ETEREA collection

design by
Danesi & Buzzoni

Platek®

battery lamp
applique
pendant
portable
product





ETEREA large

DECORATIVE OUTDOOR LIGHTING

Eterea takes inspiration from the classic lantern, proposed in its essential forms. Ancient memories are constituted by pure and geometric lines, able to create an incorporeal volume, made up only of light. By its diffused light, it perfectly fits on terraces, gardens and arcades. Eterea just like the classic

lanterns, can be placed directly on the ground or fixed to a wall by means of its bracket. A touch of functional design is given by a transparent clip to secure the cable to the vertical uprights. Eterea is now also available in small, medium and large battery-powered version.

DECORATIVE OUTDOOR LIGHTING


















DECORATIVE OUTDOOR LIGHTING

DECORATIVE OUTDOOR LIGHTING

ETEREA medium pendant




ETEREA large battery




DECORATIVE OUTDOOR LIGHTING

ETEREA large battery




DECORATIVE OUTDOOR LIGHTING







ETEREA battery lamp




IP65
IK 07

2,5 mm Photo-etched
methacrylate

100 x 100 x h. 200 mm
150 x 150 x h. 300 mm
215 x 215 x h. 455 mm

ETEREA pendant




IP65
IK 08

4 / 6 mm thick white
tempered glass

150 x 150 x h. 300 mm
215 x 215 x h. 455 mm

ETEREA portable product




IP65
IK 08

4 / 6 mm thick white
tempered glass

150 x 150 x h. 300 mm
215 x 215 x h. 455 mm

ETEREA applique



IP65

small: IK 05
2,5 mm Photo-etched
methacrylate

medium and large: IK08
4 / 6 mm thick white
tempered glass

100 x 100 x h. 200 mm
150 x 150 x h. 300 mm
215 x 215 x h. 455 mm

standard finishes



.02 white



.07 corten



.08 anthracite

ETEREA battery lamp

WHITE LED

→ h. 200 mm

→ h. 300 mm

3000K CRI>80
battery charged ⬢



1W | 75 lm (*)
diffuse



2,8W | 275 lm (*)
diffuse

2700K
available on request

→ h. 455 mm



2,8W | 275 lm (*)
diffuse

ETEREA portable product

WHITE LED

→ h. 300 mm

→ h. 455 mm

3000K CRI>80
220-240V 50/60Hz ⊕



9,6W | 385 lm (*)
diffuse



17,5W | 735 lm (*)
diffuse

2700K / 4000K
available on request

(*) Real Data



Lighting data

ETHEREA applique

WHITE LED

3000K CRI>80
220-240V 50/60Hz ⊕

2700K / 4000K
available on request

→ h. 200 mm



4W | 180 lm (*)
diffuse

→ h. 300 mm



9,6W | 385 lm (*)
diffuse

→ h. 455 mm



17,5W | 735 lm (*)
diffuse

ETHEREA pendant

WHITE LED

3000K CRI>80
220-240V 50/60Hz ⊕

2700K / 4000K
available on request

→ h. 300 mm



9,6W | 385 lm (*)
diffuse

→ h. 455 mm



17,5W | 735 lm (*)
diffuse

(*) Real Data

Platek Srl
Registered Office: Via Paderno, 19
Head Office: Via Marrocco, 4
25050—Rodengo Saiano (BS),
Italy
P.Iva 03320290178
C.F. 03007130176

T +39 030 68 18 201
F +39 030 68 16 567
info@platek.eu
www.platek.eu

Art Direction
Gusto IDS
Platek

Graphic design
Gusto IDS
Platek

Photo
Germano Borrelli
Metalli Photo Design
Ottavio Tomasini

© Platek 2020

Platek online
facebook.com/platek
twitter.com/platek
instagram.com/platek
youtube.com/platek

