



WAVECREST™

BY T&S

designer faucets

Hands-free elegance

Contemporary style meets durability in the touchless WaveCrest line by T&S Brass and Bronze Works, a leading commercial-grade plumbing manufacturer with a history of unmatched reliability and durability for 75 years.



**SOPHISTICATED AESTHETIC APPEAL
WITH LONG-TERM RELIABILITY**

WaveCrest's sleek, minimalistic lines make it ideal for modern, high-traffic facilities, such as:

- ◆ Contemporary office buildings
- ◆ Colleges & universities
- ◆ Hospitality & lodging
- ◆ Public facilities, such as airports and stadiums
- ◆ Communal areas in assisted living facilities
- ◆ Restaurant restrooms



WAVECREST™

BY T&S

TIMELESS ELEGANCE
with commercial durability

WaveCrest models are available in lavatory and medical heights in a variety of styles with brushed nickel or chrome finish options. Featuring below-deck electronics, WaveCrest products offer a sleek look with more intuitive sensor activation and auto-flush capabilities.

MODELS All WaveCrest models include a hidden sensor and a recessed 0.5 GPM non-aerated spray device.*



ECW-3150
CHROME
FINISH



ECW-3150-BN
BRUSHED NICKEL
FINISH



ECW-3150-MB
MATTE BLACK
FINISH



ECW-3152
CHROME
FINISH



ECW-3152-BN
BRUSHED NICKEL
FINISH



ECW-3152-MB
MATTE BLACK
FINISH



ECW-3153
CHROME
FINISH



ECW-3153-BN
BRUSHED NICKEL
FINISH



ECW-3153-MB
MATTE BLACK
FINISH



ECW-3158
CHROME
FINISH



ECW-3158-BN
BRUSHED NICKEL
FINISH



ECW-3158-MB
MATTE BLACK
FINISH



ECW-3162
CHROME
FINISH



ECW-3162-BN
BRUSHED NICKEL
FINISH



ECW-3162-MB
MATTE BLACK
FINISH



ECW-3163
CHROME
FINISH



ECW-3163-BN
BRUSHED NICKEL
FINISH



ECW-3163-MB
MATTE BLACK
FINISH



ECW-3172
CHROME
FINISH



ECW-3172-BN
BRUSHED NICKEL
FINISH



ECW-3172-MB
MATTE BLACK
FINISH

*Optional outlet devices available upon request:

0.35 GPM Non-Aerated Spray Device (V035 - CALGreen)

1.0 GPM Concealed Aerator (V10 - California CEC Title 20)

1.5 GPM Concealed Aerator (V15 - EPA WaterSense)

1.5 GPM Concealed Laminar Flow Device (VL15 - Healthcare/Medical)



RELIABILITY BUILT IN™
www.tsbrass.com

800-020908-45