



VERSATEX™

Instant curb appeal
with lifetime performance

A better approach to a beautiful home

Xceed Siding combines modern style and durability, delivering the look of natural wood in a product built to last for decades. With rich, fade-resistant colors, high-resistance to the elements, and perfectly matched trim options, it offers a complete, low-maintenance solution that elevates curb appeal and peace of mind.



**Class A Flame
Spread Rating**



**Moisture & Rot
Resistant**



**Color Fade &
Weather Resistant**



**Insect
Resistant**



**Easy to
Paint**



**Limited Lifetime
Warranty**

Colorful choices

Choose from 10 contemporary colors that last the life of the product and two reveal heights that offer a high-end appearance to satisfy any homeowner or designer.



Durable

Xceed Siding is made from a proprietary blend of cellular PVC and is thicker than traditional vinyl siding. Xceed is resistant to water, dents, temperature extremes, and insects. Expect your Xceed Siding job to look as good as the day it was installed, years down the road.



Painted wood

Worry-free

Xceed Siding doesn't need repainting or any maintenance beyond an occasional wash with a garden hose. With a robust Limited Lifetime Warranty, homeowners get beauty without upkeep hassles.



Xceed Siding

Due to screen/print resolution limitations, product colors may not appear exactly as shown. It's always best to refer to a product sample before final selection. Please check with your dealer.



Xceed Siding
in Sequoia Green

Classic looks, solid feel

Welcome the timeless look of wood lap siding, with distinct shadow lines and a timeless look both from the curb and up close. Unlike flimsy vinyl siding, Xceed Siding is more rigid and durable, allowing for easier handling and installation.



Xceed Siding
in Vail White

Siding, not seams

Prominent vertical seams in the facade's smooth, horizontal lines are a visual interruption that makes the job seem imperfect. Xceed Siding has 16-foot long board lengths, which means fewer butt joints. The innovative nail hem bracket system makes those joints practically invisible. The result is a smooth, coordinated aesthetic that complements the home's architecture.

Parallel runs, unseen joints


Xceed Siding boards utilize a hidden nail hem butt joint bracket to keep joints tight and invisible. All you see is a continuous run of smooth beauty, worthy of the best house on the block.

Two reveals

Xceed Siding offers a choice of board heights that work with many architectural styles.



4 1/2" Lap Siding

Gives a clean, classic style



7 1/2" Lap Siding

Creates a bold, modern aesthetic




Xceed Siding
in Quick Silver



PVC makes Xceed a superior siding

Cellular PVC delivers lasting protection you can trust. Unlike wood, it's not affected by moisture or rot. Use Xceed with confidence in moisture-prone areas, even below grade. While vinyl offers water resistance, overlapping seams, lack of rigidity, and tendency to crack mean poor aesthetics.



Xceed Siding



Painted wood



Vinyl siding

Ultra-low maintenance

Xceed Siding performs with minimal upkeep. The lightly grained surface texture adds to the realistic wood look. Unlike wood, it doesn't need painting, sealing, or special treatments. The surface resists dirt, mold, and mildew, so cleaning is as simple as a quick rinse with a garden hose.



Assured performance

Xceed Siding leads with a Limited Lifetime Warranty* against moisture-caused swelling, warping, peeling, flaking, cracking, rusting, blistering, and splintering coupled with a Limited Hail Warranty and Limited Color Fade Warranty. The product and fade warranties are transferrable for residential subsequent owners; coverage periods and commercial coverage vary, so check the warranty documents for specific details.

	XCEED Siding	Cedar	Vinyl
Highest insulation r-value	✓		
Virtually impervious to moisture	✓		✓
Class A Flame Spread Rating	✓		
No painting or staining required	✓		✓
Impact resistant	✓	✓	

*Versatex.com/warranty-support/

Engineered for builders




Fast, level & secure

- Once level is established with the starter strip and the first course, the following interlocking courses maintain established level
- Each board interlocks into the course below, reducing installation time and labor, plus helping protect against wind lift
- Xceed Siding and Stealth Trim are lightweight and easy to move without damage



VIEW XCEED
INSTALL GUIDE



Innovative design

Built with market-leading technology that reduces heat build-up (HBU) issues, a bonded UV-protected color cap that ends routine painting for a lifetime, and the VZ DropLock™ system that helps eliminate tedious chalk line-snapping, Xceed Siding brings innovative thinking to your next job.

Simple installation

A heavy duty nailing flange features wide slot openings every eight inches to allow you to hit framing, while allowing for the expansion and contraction movement of a floating system. 16-foot lengths mean boards go up quicker, either with a nail gun or by hand.

Fewer & tighter seams

16-foot boards mean fewer butt joints, and nail hem brackets keep those joints tight and practically invisible, ensuring beautiful performance without caulk, adhesives, and flashing.





Complete protection & an elevated finish

Versatex® Stealth Trim and Xceed Trim complement Xceed Siding with precise fits and coordinating aesthetics. Beyond these options, a wide portfolio of rot- and moisture-resistant accessories deliver performance, protection, and architectural detail.



Xceed Siding in Vail White



BEFORE



AFTER

A complete system

From roofline to grade, Versatex® Trim portfolio and accessories add crisp lines, protects siding ends and wall penetrations, and reduces onsite fabrication. Accessories use the same durable PVC material and design as siding and trim, for lifetime durability and cohesive aesthetics.



Stealth Corner

One-piece cornerboard conceals siding ends without messy caulk and seams to collect dirt.



Stealth Window Surround

The perfect transition from siding to window, adding crisp beauty and effective water management.



2-Piece Stealth Inside Corner

Flawless inside corner conceals siding ends while tucking behind for moisture protection.



Watertable

Completely rot-proof watertable directs water away from vulnerable window sills, for effective, good-looking water management.



Versatex® accessories



Mounting block

Available in a variety of sizes and colors from fixture mounting to dryer vents and cable access, these accessories are engineered to integrate seamlessly.



Mounting block



Vent cover

Round, octagonal, and specialty vents come in a range of sizes to add vital ventilation to attics, fans, and appliances while enhancing the aesthetics of a home's facade.



Gable vent



EXPLORE MORE
TRIM & ACCESSORIES

Innovation, dedication & service



Improvement never stops

We listen to our customers and develop solutions, like the new mounting block and vent components for Xceed Siding. With our PVC expertise, we simplify installation, elevate design, and reduce maintenance, all while maintaining the highest quality standards.

Versatex® support

Get the tools and guidance you need for a flawless installation. Versatex is here to back you up with:

- Detailed install guides
- Factory support team
- How-to videos
- In-person training
- Field support reps
- Jobsite “first nail” support



Made in the USA

Xceed products are proudly manufactured in the USA at our two state-of-the-art facilities in Aliquippa, Pennsylvania, creating jobs, opportunities, and better homes in our region and beyond.

A complete system for outstanding results

XCEED PREMIUM LAP SIDING

COLOR	4 1/2" REVEAL	4 1/2" PCS/SQUARE	7 1/2" REVEAL	7 1/2" PCS/SQUARE
Simple Sage	EXSD4516SISA	16.67	EXSD7516SISA	10
Sequoia Green	EXSD4516SEGR	16.67	EXSD7516SEGR	10
Heritage Blue	EXSD4516HEBL	16.67	EXSD7516HEBL	10
Sand Castle	EXSD4516SACA	16.67	EXSD7516SACA	10
Mojave Tan	EXSD4516MOTA	16.67	EXSD7516MOTA	10
Stonewall Shade	EXSD4516STSH	16.67	EXSD7516STSH	10
Monument Gray	EXSD4516MOGR	16.67	EXSD7516MOGR	10
Quick Silver	EXSD4516QUSI	16.67	EXSD7516QUSI	10
Centennial Stone	EXSD4516CEST	16.67	EXSD7516CEST	10
Vail White	EXSD4516VAWH	16.67	EXSD7516VAWH	10

	PCS/BOX	WEIGHT/BOX	BOXES/PALLET	BOXES/SQUARE
4 1/2" XCEED SIDING	4 PCS	32.5 LBS	60	4 BOXES
7 1/2" XCEED SIDING	4 PCS	47.2 LBS	40	2.5 BOXES


	Quantity
Product	
Xceed Nail Hem Bracket & Screw Set	50 Pre-drilled stainless steel brackets 220 Stainless steel mounting screws




**XCEED NAIL HEM
BRACKET & SCREW SET**
SKU# EXSEAMBRACKET

- 6 sq/box for the 4.5" profile
- 10 sq/box for the 7.5" profile
- Failure to use the bracket system voids the warranty

XCEED SIDING TRIM PROFILES			SMOOTH	TIMBER RIDGE
ITEM	NOMINAL	ACTUAL	18'	18'
Xceed Band Board	1 x 6"	3/4" x 5 1/2"	EXBBSM010618	EXBBTR010618
Xceed Band Board	1 x 8"	3/4" x 7 1/4"	EXBBSM010818	EXBBTR010818
Xceed Frieze Board	5/4 x 4"	1" x 3 1/2"	EXFBSM540418	EXFBTR540418
Xceed Frieze Board	5/4 x 6"	1" x 5 1/2"	EXFBSM540618	EXFBTR540618




Xceed Band Board




Xceed Frieze Board

STEALTH WINDOW TRIM PROFILES			SMOOTH	TIMBER RIDGE
ITEM	NOMINAL	ACTUAL	18'	18'
Standard Stealth	5/4 x 4"	1" x 3 1/2"	STBSM540418	STBTR540418
Standard Stealth	5/4 x 6"	1" x 5 1/2"	STBSM540618	STBTR540618
Standard Stealth	5/4 x 8"	1"x 7 1/4"	STBSM540818	STBTR540818
Stealth w/ Flange	5/4 x 4"	1" x 3 1/2"	SNFTBSM540418	SNFTBTR540418
Stealth w/ Flange	5/4 x 6"	1" x 5 1/2"	SNFTBSM540618	SNFTBTR540618




Standard Stealth



Stealth w/ Flange

STEALTH CORNER PROFILES			SMOOTH		TIMBER RIDGE	
ITEM	NOMINAL	ACTUAL	10'	20'	10'	20'
Stealth Corner	5/4 x 4"	1 x 3 1/2"	SCRSM540410	SCRSM540420	SCRTR540410	SCRTR540420
Stealth Corner	5/4 x 6"	1 x 5 1/2"	SCRSM540610	SCRSM540620	SCRTR540610	SCRTR540620
Stealth Corner	5/4 x 8"	1 x 7 1/4"		SCRSM540820		
2-Piece Stealth Inside Corner*	5/4 x 4"		INCRSM540410	INCRSM540420	INCRTR540410	INCRTR540420


*2-Piece Stealth Inside Corner has a 2.5" reveal




Stealth Corner

XCEED SIDING STARTER PROFILES


ITEM	ACTUAL		METAL STARTER	
Galvanized metal starter	3/4" x 4 1/2" x 10' (28 Gauge)		EXGMSTARTER	
Stainless steel metal starter	3/4" x 4 1/2" x 10' (28 Gauge)		EXSSSTARTER	
ITEM	ACTUAL		SMOOTH	TIMBER RIDGE
Xceed Tapered PVC Starter	3/4" x 4 1/2" x 18'		EXTSSM0104518	EXTSTR0104518
Xceed Tapered PVC Starter	3/4" x 7 1/2" x 18'		EXTSSM0107518	EXTSTR0107518
ITEM	NOMINAL	ACTUAL	SMOOTH	TIMBER RIDGE
Xceed Skirtboard	1 x 4 x 18'	3/4" x 3 1/2" x 18'	EXSBSM010418	EXSBTR010418
Xceed Skirtboard	1 x 6 x 18'	3/4" x 5 1/2" x 18'	EXSBSM010618	EXSBTR010618



Galvanized &
stainless steel metal
starter



Xceed Tapered
PVC Starter



Xceed Skirtboard

Stealth Trim pockets increased to 1-1/8" for 4" nominal and 1-½" for 6" nominal and greater

*For additional profiles, visit website.



ORDER
FREE SAMPLES

“

Xceed Siding
was a pleasure
to work with ...
it's engineered
properly and
looks fantastic.

- William Rivera
Two Brothers Contracting

Xceed Siding in Heritage Blue



400 Steel Street, Aliquippa, PA 1500
(724) 857-1111 | [VERSATEX.com](https://www.versatex.com)

© 2026 Versatex Building Products, LLC and its affiliates. All rights reserved. The TM and (R) symbols denote trademarks or registered trademarks of James Hardie Technology Limited or its affiliates.



JamesHardie™

The home of resilient beauty™