

# OMEGA SAFARI

NEW





The **OMEGA SAFARI** fence system perfectly blends natural aesthetics with modern durability. Inspired by the elegant look of bamboo, it brings a lush, organic feel to any setting. Its unique design features diagonally welded, crisscrossed bars that provide a stylish, nature-themed appearance while delivering strength and reliability.

Constructed with vertical aluminum solid rods and horizontal flat supports, protected by a durable polyester powder-coated finish, the OMEGA SAFARI fence offers security, longevity, and visual appeal. It integrates seamlessly into various environments: Private gardens, schools, parks, zoos, trails, bridges, warehouses, residential areas, and more where both protection and design matter.

OMEGA II has been the original welded-wire fence company since 1992 and this new exceptional product is the perfect addition to our product offerings.


## TECHNICAL SPECIFICATIONS

SPACING BETWEEN VERTICAL RODS	Maximum 3 <sup>13</sup> / <sub>16</sub> " (97.5 mm)
VERTICAL INCLINED SOLID RODS	Diameter <sup>11</sup> / <sub>16</sub> " (18 mm)
HORIZONTAL FLATS SUPPORTS	Rectangular 1 <sup>1</sup> / <sub>4</sub> " x <sup>1</sup> / <sub>4</sub> " (31.75 mm x 6.35 mm)
MOUNTING ANGLE SUPPORT	U-shape bracket adjustable from 0° to 180°
STRUCTURE	Diagonally welded, crisscrossed rods and flats
FINISH	Polyester Powder-coated
MATERIAL	Aluminum 6061-T6



# OMEGA SAFARI

**NEW**



## PANEL

STANDARD HEIGHT	46", 70", 94" (1168 mm, 1778 mm, 2388 mm)
STANDARD LENGTH	91 1/2" (2324 mm)
FINISH	Polyester powder coated

## MESH

HORIZONTAL FLAT	1 1/4" x 1/4" (31.75 mm x 6.35 mm)
VERTICAL ROD	1 1/16" (18 mm)
OPENINGS	Maximum 3 13/16" (97.5 mm) between vertical rods

## SQUARE POST

DIMENSIONS	2" x 2" (50.8 x 50.8 mm)
BRACKETS	U-shaped bracket
CAP	Standard square cap

## AVAILABLE SWING GATES

WIDTH	36", 42", 48", 60", 72" or 96" (914 mm, 1067 mm, 1219 mm, 1524 mm, 1829 mm or 2438 mm)
HEIGHT	48", 72" or 96" (1219 mm, 1829 mm or 2438 mm)

Choose from our 18 standard gate sizes, designed to meet most needs. For specific requests, custom sizes are also available.

