JamesHardie™

Hardie® Artisan® Siding & Trim

Distinctive Design, Engineered to Last™

Offering gorgeous, deep shadow lines and extra thick boards, Hardie® Artisan® Siding and Trim will set your home apart. The 5/8-inch thickness and unique features of Hardie® Artisan® siding provide precise fit and finish as well as the freedom to miter corners for attractive, streamlined styling.







LOCK JOINT SYSTEM

Hardie® Artisan® siding flat wall profiles have a lock joint system that helps enable faster, cleaner installation.



DESIGN FLEXIBILITY

Hardie® Artisan® siding flat wall profiles can be oriented vertically, horizontally or used as soffit.



MITERED CORNERS

Add sophistication to your design with mitered corners that can be crafted on-site with any Hardie® Artisan® profile.

2024 GREEN BUILDER SUSTAINABLE PRODUCT OF THE YEAR

Hardie® Artisan® Lap Siding has been named one of **Green Builder Media's** 2024 Sustainable Products of the Year.


2025 GREEN BUILDER SUSTAINABLE PRODUCT OF THE YEAR

Hardie® Artisan® Trim has been named one of **Green Builder Media's** 2025 Sustainable Products of the Year.

MOST VALUABLE PRODUCT AWARDS — SILVER — PROBUILDER — 7TH ANNUAL AWARDS

Hardie® Artisan® Lap Siding has been named a Silver Award Winner in **Pro Builder's** 2025 Most Valuable Products Awards

Hardie® Artisan® Siding & Trim



Lap Siding

Lap Siding

Thickness 5/8 in.

Width	7.25 in. (6 in. exposure)	8.25 in. (7 in. exposure)
Length	12 ft.	12 ft.
Pcs/Pallet	144	125
Finish	Primed	Primed





Trim

Trim

Thickness 1.5 in.

Width	3.5 in.	5.5 in.
Length	12 ft.	12 ft.
Pcs/Pallet	192	120
Finish	Primed	Primed

FLAT WALL PROFILES




Shiplap

Shiplap

Thickness 5/8 in.

Width	10.25 in. (9 in. exposure)
Length	12 ft.
Channel Size	.15 in.
Pcs/Pallet	105
Finish	Primed







V-Groove

V-Groove

Thickness 5/8 in.

Width	8.25 in. (7 in. exposure)
Length	12 ft.
Channel Size	.5 in.
Pcs/Pallet	126
Finish	Primed





Square Channel

Square Channel

Thickness 5/8 in.

Width	10.25 in. (9 in. exposure)
Length	12 ft.
Channel Size	1 in.
Pcs/Pallet	105
Finish	Primed



© 2025 James Hardie Building Products Inc. All rights reserved. Unless otherwise noted, ™ and ® denote a trademark or registered trademark owned by James Hardie Technology Ltd. The Green Builder Media logo and the Pro Builder logo are trademarks of their respective owners. **HAC2402-MF 3/25**