

SIMES



Bell

Outdoor decorative collection

Ornamental and minimal

Bell is the decorative collection of Simes developed with precious solid bronze inserts designed to enrich the architecture.

With its elegant and minimal silhouette, Bell reinterprets in a contemporary way an object from the past. An outdoor product characterized by the combination of noble materials and warm colors, designed for prestigious properties, historic homes and elegant villas.

Bell and Minibell are available as wall mounted applique, ceiling and bollard version.

Ceiling



Applique



Bollard


Prestigious materials

Bell is an outdoor range of products enriched with refined inserts in solid satin bronze.

The elegance of the Bell family is dictated from a harmonious merge of colors and materials. The product differentiate for the shape of the aluminum body enriched by bronze inserts characterizing the whole family in a decisive way.

The reflector that embraces the inner part of the lamp warmth the light beam and the tapered cone slims the silhouette.

These decorative elements in solid bronze are treated with a transparent protective layer that maintains the color and ensures quality and durability.



Protection class
IP65

Insulation class
CLASS I ⚡

Mechanical resistance of glass
IK 06



Applique

Two sizes for the wall.

Bell and Minibell wall lamps enhance the classic facades with a warm and welcoming light. These versions are characterized by a curved arm, which orients the light beam downwards. Thanks to the position of the lamp and the reeded microglass, the light effect is homogeneous and not glaring.



Ceiling

Rigid support and cable suspension.

Bell ceiling is available with rigid support or with adjustable cable. Due to its stability to the wind, the Bell Ceiling with rigid support is particularly suitable for outdoor exposed environments. In the cable suspension version Bell is expressed in a very elegant silhouette particularly suitable for porches and lodge.




Bollard


**Tilted to 20° for
an embracing light.**

Bell is an elegant garden lamp, thin and refined, inspired by the shape of the bell. This beautiful bollard discreetly stands out in the landscape to illuminate walkways, bushes and decorative elements of private gardens. The light wraps the stake from the stem to the ground, resting evenly all around.







MINIBELL APPLIQUE




S.8000W
 MID-POWER LED 3000K CRI90
 Rated luminaire luminous flux 669lm
 Rated input power 10,3W
 220V-240V AC 50/60Hz / DC
 ON/OFF not dimmable
 Pre-wired with 1,5m cable




BELL APPLIQUE



S.8020W
 MID-POWER LED 3000K CRI90
 Rated luminaire luminous flux 1079lm
 Rated input power 20,4W
 220V-240V AC 50/60Hz / DC
 ON/OFF not dimmable
 Pre-wired with 1,5m cable




MINIBELL BOLLARD 70




S.8005W
 MID-POWER LED 3000K CRI90
 Rated luminaire luminous flux 669lm
 Rated input power 10,3W
 220V-240V AC 50/60Hz / DC
 ON/OFF not dimmable
 Pre-wired with 4,0m cable


With flange to be fixed in concrete with stainless steel screws for fixing in the ground.




BELL CEILING



S.8035W
 MID-POWER LED 3000K CRI90
 Rated luminaire luminous flux 1079lm
 Rated input power 20,4W
 220V-240V AC 50/60Hz / DC
 ON/OFF not dimmable
 Pre-wired with 1,5m cable




MINIBELL BOLLARD 90




S.8006W
 MID-POWER LED 3000K CRI90
 Rated luminaire luminous flux 669lm
 Rated input power 10,3W
 220V-240V AC 50/60Hz / DC
 ON/OFF not dimmable
 Pre-wired with 4,0m cable

With flange to be fixed in concrete with stainless steel screws for fixing in the ground.



BELL SUSPENSION



S.8030W
 MID-POWER LED 3000K CRI90
 Rated luminaire luminous flux 1079lm
 Rated input power 20,4W
 220V-240V AC 50/60Hz / DC
 ON/OFF not dimmable
 Pre-wired with 4,0m cable

Colors:

- White (cod. 01)
- Burnished bronze (cod. 20)





SIMES

luce per l'architettura

SIMES S.p.A. VIA G. PASTORE 2/4 - 25040 CORTE FRANCA (BRESCIA) - ITALY
Tel. (+39) 030 9860411 - Fax (+39) 030 9828308
simes@simes.com - www.simes.com