



KCLASS



KLASS

Elegance, Exclusivity, No Limits Integration


Klass is a prestigious device, a super-stylish video intercom featuring ultra-slim design and 3mm glass finish

LCD IPS 7" display, with 1.024 × 600 px resolution, offers a **wide and sharp view of video streams** and available functions.

Capacitive touch screen monitor **includes a high-resolution front camera** up to 1080p, enabled during intercommunication with another Klass monitor.

Handset available

Klass is full-duplex hands-free assuring a high-level phonic performance and – for those wishing for more privacy – an additional handset is available, **featuring plug & play quick-connect and magnetic cradle**



No Limits Integration

Klass is built on IPure technology, supporting standard protocols used for integration with third party systems, **with no additional license fees.**

- ✓ **RTSP** protocol for integration with IP video surveillance systems.
- ✓ **SIP** protocol for interfacing with VoIP switchboards and with Public Address systems.
- ✓ **HTTP** to manage all outdoor and indoor station commands and services on third-party platforms.

Klass uses embedded Linux for maximum reliability and includes a built-in browser for full interoperability with third parties.


A Wi-Fi dongle module is available for alternative connection to the local network.



Security for your Spaces

Klass manages up to **64 IP camera streams** and **camera switching** function is available: during conversation, by a simple touch on the screen or on the button, you can choose the **camera you want to view** - in addition to the door station's.

Moreover, you can **prioritize the stream** you prefer during a conversation.



4 preset buttons: conversation and auto power on, door opener, menu, privacy.

4 numbered buttons for additional services.

KLASSE

Reliable and Complete

Klass features **8 soft touch buttons**.

All buttons – including the preset ones – are **freely configurable** to manage the functions you prefer.

2 inputs and 2 outputs are included to **manage services**, both locally and through the Videx App.



KLASS

Smart & Comfort

Built-in sensors can be integrated with third party systems and devices to trigger many automations

- ✓ **Ambient light sensor** for automatic brightness and theme adjustment.
- ✓ **Proximity sensor** allowing automatic screen power-on as the user gets closer.
- ✓ **Temperature and humidity sensor** to manage room temperature.

All the available functions can be remotely managed through the Vindex app: no configuration is needed and in a snap you can have everything under control when you're not home



Answer calls



Open the gate



Manage room temperature



Custom access to services



Camera switch to view other camera streams



Manage all other additional services integrated with other systems and devices

Ultra-slim design

3mm glass finish

LCD IPS 7" display, 1.024 x 600 px resolution

Up to 1080p high-res front camera

Surface mounting

Full-duplex handsfree, handset available as optional

Capacitive touch screen

PoE or 12 Vdc power

Optional Wi-Fi dongle module for connection to local network

Managing up to 64 IP camera streams

Camera switching available both locally and remotely



Be Smart, Be Klass





KL7VXIPW



KL7VXIPB


Klass Series 7" Connected video intercom, hands-free full-duplex audio speaker for IPure System

Klass Series videointercom, Embedded Linux operating system, 7" 16/9 high resolution (1024x600 pixels IPS) LCD TFT full touch capacitive touchscreen, 3mm glass cover lens, full-duplex audio speaker, temperature/humidity sensor, ambient light sensor, proximity sensor, 2 active/low inputs, 2 relay outputs that can be activated locally (C, NO - max 35Vdc 50mA), 8 soft-touch buttons that can be configured or dedicated to preset functions: conversation/auto power on, door opener, intercom call, video camera/privacy service switching, etc. Contrast adjustment, brightness and call volume.


Local call input, video-intercom function configurable through GUI menu (up to 1080p). Features: privacy programmable through GUI menu, weather widget, switching outdoor audio/video stations or CCTV video cameras implemented with RTSP protocol, event log available locally or through the Videx APP, CCTV implementation with PiP feature.

Smart chronothermostat function that can be managed locally or through the Videx APP. Integrated browser, Multi-compatibility with protocols: SIP 2.0, RTSP, HTTP. Optional Wi-Fi Dongle module Cod. DNGL. Bracket Cod. KLBRW or Cod. KLBRB. is included.


White or black glass and ABS material. RJ-45 port 10/100 Mbps. IEEE 802.3af (Class 0) PoE power or 12V dc - 650mA. Dimensions: 195x165x30mm. Wall-mounted, optional table stand Cod. KLHFTS or Cod. KLHSTS.



Induction coil for hearing aid users




KLBRW



KLBRB

Klass Series Mounting Bracket

Klass Series mounting bracket with connectors. White or black ABS material. Dimension 97x122x5mm.



DNGL

Wi-Fi Dongle


Optional device that can be inserted inside the video intercom for connection to the local Wi-Fi network. An alternative connection type to the standard Ethernet connection. Allows connectivity to the VIDEX Cloud or through integrated browser the possibility of integration with third-party devices.



KLHFTS

Klass Series, hands-free, table stand


Klass Series, hands-free, table stand. Satin finish stainless steel material. Dimension 154x185x116mm.



KLHSTS

Klass Series, with handset, table stand

Klass Series, with handset, table stand. Satin finish stainless steel material. Dimension 212x185x116mm.




KLHSW



KLHSB

Klass Series Handset with magnetic cradle and cord

Klass Series handset with magnetic cradle and cord. White or black ABS material. Dimensions 42x165x30mm.



Videx worldwide

Videx Electronics S.p.A.
Via del Lavoro, 1
63846 - Monte Giberto (FM) - Italy
T. +39 0734 631 669
F. +39 0734 632 475
E. info@videx.it
www.videx.it

Videx Security Ltd
1 Osprey Trinity Park Trinity Way
London E4 8TD
T. (+44) 0370 300 1240
E. marketing@videxuk.com
www.videxuk.com

VX Ibéria Unipessoal Lda
Rua Tenente Mário Grilo, 26 D, E, F
4200-397 Porto
T. (+351) 221 124 531
E. comercial@videx.it
www.videx.it

Videx Asia Pacific Pte Ltd
31 Woodlands Close #06-37
Woodlands Horizon Singapore 737855
T. (+65) 81898912
E. commercial@videx.it
www.videx.it

Videx Danmark
Hammershusgade 15 DK-2100
Copenhagen
T. (+45) 39 29 80 00
F. (+45) 39 27 77 75
E. videx@videx.dk
www.videx.dk

Videx Benelux
E3 laan, 93 B-9800 Deinze
T. (+32) 9 380 40 20
F. (+32) 9 380 40 25
E. info@nestorcompany.be
www.nestorcompany.be

Videx Hellas Electronics
48 Filolaou Str.
11633 Athens
T. (+30) 210 7521028
T. (+30) 210 7521998
F. (+30) 210 7560712
E. videx@videx.gr
www.videx.gr



KLASS

Videx Electronics S.p.A.

Via del Lavoro, 1 | 63846 - Monte Giberto (FM) - Italy
T. +39 0734 631 669 | F. +39 0734 632 475 | info@videx.it

www.videx.it

EN