

# Gyrofocus


1968

---

DESIGN: DOMINIQUE IMBERT

*With its singular style and hearth that rotates 360°, the Gyrofocus has earned its place as an icon of contemporary design alongside the most legendary names in furniture and interior design.*

*Focus's flagship model, the Gyrofocus was voted the "Most Beautiful Object in the World" in an Italian design competition and has been exhibited at the Guggenheim Museum in New York.*



**focus**®

CREATE BEYOND CONVENTION


# Gyrofocus

wood-burning (Ecodesign)



## 2021 WOOD ECODESIGN

*The wood-burning Gyrofocus was reissued in 2021 in a closed glass-fronted version with excellent energy and environmental performance. Its two sliding glass panels offer an unobstructed view of the fire. Winner of a number of international awards, this model has also received a mention for sustainability at the "Archiproducts Design Awards".*



# Gyrofocus

wood-burning (Ecodesign)



## DIMENSIONS / WEIGHT

HEIGHT (mm)	WIDTH (mm)	DEPTH (mm)	FIREPLACE WEIGHT (kg)	FLUE WEIGHT (kg/linear metre)
610	1250	1250	200	16

## SAFETY DISTANCE FROM COMBUSTIBLE MATERIALS

FRONT (mm)	BACK (mm)	SIDE (mm)	FLOOR (mm)
800	500	500	400

## SAFETY DISTANCE FROM GLASS SURFACES (mm)

1000
------

## TECHNICAL SPECIFICATIONS


HEAT OUTPUT (kW)	EFFICIENCY (%)	MINIMUM ROOM VOLUME (m <sup>3</sup> )
18	81	80

## FINISH

Black
-------

# Gyrofocus

wood-burning (Ecodesign)



# Gyrofocus

gas



## 2020 GAS

*The Gyrofocus is now also available in a gas version, operated by remote control. At the touch of a button, the fire can be lit, the flame intensity and heat adjusted, or a programme set for controlled, constant, comfortable heat.*



# Gyrofocus

gas



## DIMENSIONS / WEIGHT

HEIGHT (mm)	WIDTH (mm)	DEPTH (mm)	FIREPLACE WEIGHT (kg)	FLUE WEIGHT (kg/linear metre)
610	1250	1250	153	16

## DISTANCE FROM COMBUSTIBLE MATERIALS

FRONT (mm)	BACK (mm)	SIDE (mm)	FLOOR (mm)
300	300	300	0

## SAFETY DISTANCE FROM GLASS SURFACES (mm)

500
-----

## TECHNICAL SPECIFICATIONS

NATURAL GAS HEAT OUTPUT (kW)	PROPANE HEAT OUTPUT (kW)	NATURAL GAS CONSUMPTION (m <sup>3</sup> /h)	PROPANE CONSUMPTION (m <sup>3</sup> /h)
13.5	13	1.26	0.373

## ELECTRICAL POWER SUPPLY


Batteries
-----------

## FINISH

Black	White
-------	-------

# Gyrofocus

gas



# Gyrofocus

bioethanol



## 2024 BIOETHANOL

***Smokeless, with no external flue: the installation possibilities are endless!***

*Fuelled with bioethanol and fitted with a fully electronic, safe burner (made in France), this fireplace is operated by remote control. It is smokeless and does not require an external flue outlet, allowing unprecedented freedom of installation on any floor.*



# Gyrofocus

bioethanol



## DIMENSIONS / WEIGHT

HEIGHT (mm)	WIDTH (mm)	DEPTH (mm)	FIREPLACE WEIGHT (kg)	FLUE WEIGHT (kg/linear metre)
610	1250	1250	125	16

## SAFETY DISTANCE FROM COMBUSTIBLE MATERIALS

FRONT (mm)	BACK (mm)	SIDE (mm)	FLOOR (mm)
800	300	300	0

## SAFETY DISTANCE FROM GLASS SURFACES (mm)

500
-----

## WITH EXTERNAL OUTLET

HEAT OUTPUT (kW)	TANK CAPACITY (L)	AUTONOMY (h)	MIN. CEILING VOLUME (m <sup>3</sup> )
9.5	10	6.5	0

## WITHOUT EXTERNAL OUTLET

HEAT OUTPUT (kW)	TANK CAPACITY (L)	AUTONOMY (h)	MIN. CEILING HEIGHT (m)	MIN. ROOM VOLUME (m <sup>3</sup> )
7.5	10	8	2.50	150

## ELECTRICAL POWER SUPPLY

Batteries
-----------

## FINISH


Black	White
-------	-------

# Gyrofocus

bioethanol



2490 minimum\*



\*if not connected to an external outlet

# Gyrofocus

outdoor (wood-burning)



*The outdoor models are available with a black anti-corrosion finish or a rusted finish, both developed by Focus for exterior use. The rusted surface gradually changes, so the patina gains character over time.*



# Gyrofocus

outdoor (wood-burning)



## DIMENSIONS / WEIGHT

HEIGHT (mm)	WIDTH (mm)	DEPTH (mm)	FIREPLACE WEIGHT (kg)	FLUE WEIGHT (kg/linear metre)
610	1250	1250	90	16

## SAFETY DISTANCE FROM COMBUSTIBLE MATERIALS

FRONT (mm)	BACK (mm)	SIDE (mm)	FLOOR (mm)
800	500	500	400

## SAFETY DISTANCE FROM GLASS SURFACES (mm)


500
-----

## FINISH

Outdoor black	Rusted steel
---------------	--------------

# Gyrofocus

outdoor (wood-burning)





CREATE BEYOND CONVENTION

