

# TOTO®

## NEW COMMERCIAL TOILETS & ECOPOWER® FLUSH VALVES

### HIGH-PERFORMANCE MEETS EASY MAINTENANCE

TOTO's revolutionary new commercial toilet features its market-leading **TORNADO FLUSH®** system, which provides a powerful nozzle to create a forceful centrifugal, cyclonic rinsing action that reduces waste buildup and keeps the bowl cleaner. Using only 1.28 gallons per flush, this high-efficiency flushing system is more effective in one flush than most commercial toilets with multiple flushes. Its modern hole-free concave rim design means that TOTO's new water-efficient toilet delivers consistent high performance; its hole-free, concave rim design ensures easy maintenance.



SCAN CODE  
TO PLAY VIDEO



**Product Shown:**

Commercial Flushometer High-Efficiency Wall-Hung Toilet; CT728CUG  
ECOPOWER Exposed Flush Valve; TET1UB32#CP

# Commercial Toilets & Flush Valve Line-Up



**Commercial Flushometer  
Top Spud Wall-Hung**



**Commercial Flushometer  
Back Spud Wall-Hung**



**Commercial Flushometer  
Floor-Mounted Toilet**



**Commercial Flushometer  
ADA Floor-Mounted Toilet**

## COMMERCIAL TOILET FEATURES INCLUDE:

- TORNADO FLUSH® is a sustainable, high-performance system that effectively removes waste, utilizing 360° of cleaning power to scour the bowl and rim
- Floor-mounted or Wall-Hung option
- ADA compliant and UNIVERSAL HEIGHT option
- Elongated front bowl
- Optional CEFIONTECT ceramic glaze minimizes waste from sticking to porous ceramic surfaces
- Clear glazed trapway coating
- 10"-12" rough-in
- Designed for reclaimed water use
- Maximum static load rating of 1000 lbs when used with appropriate wall carrier




**ECOPOWER Exposed  
Flush Valve**



**ECOPOWER Exposed  
Flush Valve**



**ECOPOWER Concealed  
Flush Valve (14" x 12")**



**ECOPOWER Concealed  
Flush Valve (4" x 4")**

## FLUSH VALVE FEATURES INCLUDE:

- Self-powered hydroelectric flush valve system
- No minimum daily usage requirement
- Neutral rough-in and adjustable tail piece connection
- Durable chrome plated body with tamper-proof screws and solid bronze valve body
- Self-cleaning piston valve with 360° filter screen
- Smart sensor with self-adjusting detection range and fuzzy logic control to reduce water usage
- 6-second detection time to prevent ghost flushing
- ADA compliant

## PERFECTLY CLEAN IN ONE POWERFUL FLUSH



### SENSOR DETECTION

6-second detection time prevents ghost flushing.



### TORNADO FLUSH®

Our flushing system generates 360-degrees of cleaning power that reaches every spot.



### CEFIONTECT®

Our ceramic glaze minimizes waste from sticking to porous ceramic surfaces.

# Commercial Toilets

## Commercial Flushometer Top Spud Wall-Hung Toilet



SKU	GPF	Bowl Shape	Bowl Height	CEFIONTECT
CT728CU	1.0/1.28/1.6	Elongated	Regular Height	Not Included
*CT728CUX	1.0/1.28/1.6	Elongated	Regular Height	Not Included

Available in #01 Cotton only  
\* Reclaimed Water model

SC534 and SC134 seats  
are available

*Seat not included*

## Commercial Flushometer Back Spud Wall-Hung Toilet



SKU	GPF	Bowl Shape	Bowl Height	CEFIONTECT
CT728CUV	1.0/1.28/1.6	Elongated	Regular Height	Not Included
CT728CUG	1.0/1.28/1.6	Elongated	Regular Height	Included
CT728CUVG	1.0/1.28/1.6	Elongated	Regular Height	Included

Available in #01 Cotton only

SC534 and SC134 seats  
are available

*Seat not included*

## Commercial Flushometer Floor-Mounted Toilet



SKU	GPF	Bowl Shape	Bowl Height	Rough-In	CEFIONTECT
CT725CU	1.0/1.28/1.6	Elongated	Regular Height	12" ***	Not Included
CT725CUF	1.0/1.28/1.6	Elongated	Universal Height	12" ***	Not Included
CT725CUX	1.0/1.28/1.6	Elongated	Regular Height	12" ***	Not Included
*CT725CUFX	1.0/1.28/1.6	Elongated	Universal Height	12" ***	Not Included
CT725CUG	1.0/1.28/1.6	Elongated	Regular Height	12" ***	Included
CT725CUFG	1.0/1.28/1.6	Elongated	Universal Height	12" ***	Included
*CT725CUGX	1.0/1.28/1.6	Elongated	Regular Height	12" ***	Included
*CT725CUFGX	1.0/1.28/1.6	Elongated	Universal Height	12" ***	Included

Available in #01 Cotton only

\* Reclaimed Water model

\*\*\*10" Rough-ins are available

Universal Height meets ADA height compliance with the commercial seats

SC534 and SC134 seats  
are available

*Seat not included*

# ECOPOWER® Flush Valves

## ECOPOWER Exposed Toilet Flush Valve



SKU	GPF	Flush Valve	1-1/2" Vacuum Breaker Tube, 1" angle stop
TET1UB32	1.0	TET1UB	VB0932B
*TET1UBX32	1.0	*TET1UBX	*VB0932XB
TET1LB32	1.28	TET1LB	VB0932B
*TET1LBX32	1.28	*TET1LBX	*VB0932XB
TET1GB32	1.6	TET1GB	VB0932B

Available in #CP Polished Chrome  
\* Reclaimed Water model



SKU	GPF	Flush Valve	1-1/2" Vacuum Breaker Tube, 1" angle stop
TET6UB32	1.0	TET6UB	VB0932B#CP
*TET6UBX32	1.0	*TET6UBX	*VB0932XB#CP
TET6LB32	1.28	TET6LB	VB0932B#CP
*TET6LBX32	1.28	*TET6LBX	*VB0932XB#CP
TET6GB32	1.6	TET6GB	VB0932B#CP


All models required 24-1/2" Vacuum Breaker Tube THP3291B#CP  
\* Reclaimed Water model

## ECOPOWER Concealed Toilet Flush Valve - 14" x 12"



SKU	GPF	Flush Valve	1-1/2" Vacuum Breaker Tube, 1" angle stop
TET2UB31	1.0	TET2UB	VB1331#RB
TET2UB32	1.0	TET2UB	VB0932#RB
TET2UB33	1.0	TET2UB	VB1333#RB
TET2LB31	1.28	TET2LB	VB1331#RB
TET2LB32	1.28	TET2LB	VB0932#RB
TET2LB33	1.28	TET2LB	VB1333#RB
TET2GB31	1.6	TET2GB	VB1331#RB
TET2GB32	1.6	TET2GB	VB0932#RB
TET2GB33	1.6	TET2GB	VB1333#RB

## ECOPOWER Concealed Toilet Flush Valve - 4" x 4"



SKU	GPF	Flush Valve	1-1/2" Vacuum Breaker Tube, 1" angle stop
TET3UB31	1.0	TET3UB	VB1331#RB
TET3UB32	1.0	TET3UB	VB0932#RB
TET3UB33	1.0	TET3UB	VB1333#RB
TET3LB31	1.28	TET3LB	VB1331#RB
TET3LB32	1.28	TET3LB	VB0932#RB
TET3LB33	1.28	TET3LB	VB1333#RB
TET3GB31	1.6	TET3GB	VB1331#RB
TET3GB32	1.6	TET3GB	VB0932#RB
TET3GB33	1.6	TET3GB	VB1333#RB