



# FULL ACCESS FRAMELESS KITCHEN & BATH CABINETS



[www.cosmocabinets.com](http://www.cosmocabinets.com)  
January 2025



## Standard Cabinet Dimensions:


Wall Cabinets	12" Deep
Base Cabinets	24" Deep x 34 1/2"
Handicap Base Cabinets	24" Deep x 32 1/2"
Vanity Cabinets	21" Deep x 34 1/2"
Handicap Vanity Base Cabinets	21" Deep x 32 1/2"
Oven / Utility Cabinets	24" Deep x 84/90/96"
Linen Cabinets	21" Deep x 84/90/96" High
Drawer Depth	Vanity-18" ; Kitchen cabinet - 20"

## Construction Details:

- Cabinet Box** Particle Board (5/8") Or Plywood (3/4") Box With White Coated Foil
- Cabinet Back** 1/4" Back with 3 Runners in Particle Board (5/8") or Plywood (3/4")
- Cabinet End Panel** Matching Color Ends As Doors
- Box Assembly** Glued Bore And Dowel Construction
- Cabinet Fronts** Door And Drawer Front 3/4" Thick
- Edge Banding** PVC In Matching Color To Doors
- Hinges** Soft Close 6 Way Adjustable
- Shelves** 3/4" Thick White Coated Foil
- Toe Kick** Removable Toe Kick With Clip-On System
- Folding Plastic Legs** Waterproof Plastic Leg Levelers with 3 1/2" - 6" H adjustment range
- Drawer Box Options**
  - A White 5/8" Particle Board Box With Epoxy Coated Self Close Slide \*
  - B White 5/8" Particle Board Box With Undermount Soft Close Full Extension Slide
  - C Blum Meta Box With 5/8" Thick Bottom With Soft-Close
  - D Double Wall Meta Box with 5/8" Thick Bottom With Undermount Soft Close Full Extension Slide
  - E Dovetail 5/8" Solid Wood Box With Undermount Soft Close Full Extension Slide




\* Options A is also available in Plywood Box when ordering a plywood cabinet



## Standard Cabinet Dimensions:

Wall Cabinets	12" Deep
Base Cabinets	24" Deep x 34 1/2"
Handicap Base Cabinets	24" Deep x 32 1/2"
Vanity Cabinets	21" Deep x 34 1/2"
Handicap Vanity Base Cabinets	21" Deep x 32 1/2"
Oven / Utility Cabinets	24" Deep x 84/90/96"
Linen Cabinets	21" Deep x 84/90/96" High
Drawer Depth	Vanity-18" ; Kitchen cabinet - 20"



## Construction Details:

- |    |                           |  |
|----|---------------------------|--|
| 1  | <b>Cabinet Box</b>        | Particle Board (5/8") Or Plywood (3/4") Box With White Coated Foil   |
| 2  | <b>Cabinet Back</b>       | 1/4" Back with 3 Runners in Particle Board (5/8") or Plywood ( 3/4")   |
| 3  | <b>Cabinet End Panel</b>  | Matching Color Ends As Doors   |
| 4  | <b>Box Assembly</b>       | Glued Bore And Dowel Construction  |
| 5  | <b>Cabinet Fronts</b>     | Door And Drawer Front 3/4" Thick   |
| 6  | <b>Edge Banding</b>       | PVC In Matching Color To Doors   |
| 7  | <b>Hinges</b>             | Soft Close 6 Way Adjustable  |
| 8  | <b>Shelves</b>            | 3/4" Thick White Coated Foil   |
| 9  | <b>Toe Kick</b>           | Traditional Integrated Toe Kick  |
| 10 | <b>Drawer Box Options</b> | A White 5/8" Particle Board Box With Epoxy Coated Self Close Slide *<br>B White 5/8" Particle Board Box With Undermount Soft Close Full Extension Slide<br>C Blum Meta Box With 5/8" Thick Bottom With Soft-Close<br>D Double Wall Meta Box with 5/8" Thick Bottom With Undermount Soft Close Full Extension Slide<br>E Dovetail 5/8" Solid Wood Box With Undermount Soft Close Full Extension Slide |




\* Options A is also available in Plywood Box when ordering a plywood cabinet






# DELTA (Group 1)

The Delta Value Line combines affordability with quality. The slab door design brings a touch of modern elegance to any space, while the solid and wood grain look gives you the aesthetic appeal of natural wood without the cost. Built with a  $\frac{3}{4}$ " engineered wood core and Thermofused Laminate (TFL), this product ensures durability and longevity.



**Perfect White**




**Fossil Grey**




**Slate**



**Dune**



**Somerset**




**Licorice**





## SIERRA (GROUP 2)

Featuring a textured wood grain look, this door adds depth and character to any room. The Thermofused Laminate (TFL) surface is not only visually appealing but also durable. Its  $\frac{3}{4}$ " engineered wood core provides the ideal stability for long-term use.




**Breezewood**

**Carmel**

## SANTA FE (Group 2)

Santa Fe is a beautifully crafted DuraTek™ slab door and drawer front designed in solid colors or a textured wood grain. More than just a pretty face, it offers unmatched durability with its scratch-resistant vinyl finish. Its superior coating keeps it impeccably clean and resists fingerprints, creating a pristine look that really lasts.



**Dolphin**

**Charleston Grey**


**Velvet Blue**

**Spring Green**






**Slate**




**Velvet Black**



**White Haven**



**Ivory**




**Dark Knight**



**Natural Oak**



**Cinnamon**



**Cacao**



**Aspen Grey**



**Heritage Grey**





# YOSEMITE (Group 3)

Yosemite is a DuraTek™ Shaker door with 2 ½" rail width that combines classic elegance with modern durability. Available in solid color or a textured wood grain, the fully sealed design with a superior coating offers excellent scratch resistance and resists fingerprints. It's ideal for those who appreciate timeless design with low maintenance.



**Perfect White**



**Dolphin**



**Fossil Grey**



**Charleston Grey**



**Velvet Blue**



**Spring Green**



**Slate**



**Velvet Black**






**White Haven**



**Ivory**



**Dark Knight**



**Natural Oak**



**Cinnamon**



**Cacao**



**Aspen Grey**



**Heritage Grey**





# SUPERIOR (Group 3)

Superior is a DuraTek™ Shaker door with 2 ½" rail width constructed with a 45° mitered joint that combines classic elegance with modern durability. Available in solid color or a textured wood grain, the fully sealed design with a superior coating offers excellent scratch resistance and resists fingerprints. It's ideal for those who appreciate timeless design with low maintenance.



**Dolphin**



**Fossil Grey**



**Charleston Grey**



**Velvet Blue**



**Spring Green**




**Slate**



**Velvet Black**



**Ivory**



**Dark Knight**



**Natural Oak**



**Cinnamon**



**Cacao**



**Aspen Grey**



**Heritage Grey**





# OLYMPIC (Group 3)

Olympic is a DuraTek™ Thin Shaker door with 1/2" rail width constructed with a 45° mitered joint that combines classic elegance with modern durability. Available in solid color or a textured wood grain, the fully sealed design with an superior coating offers excellent scratch resistance and resists fingerprints. It's ideal for those who appreciate timeless design with low maintenance.



**Perfect White**



**Dolphin**



**Fossil Grey**



**Charleston Grey**



**Velvet Blue**



**Spring Green**



**Slate**



**Velvet Black**



**White Haven**



**Ivory**



**Dark Knight**



**Natural Oak**



**Cinnamon**



**Cacao**



**Aspen Grey**



**Heritage Grey**





## OCONEE (Group 4)

The Ocone range caters to those who seek luxury and sophistication. Choose between the premium slab high gloss door for a sleek, modern look or the painted shaker door with 2  $\frac{3}{4}$ " rail width for a timeless appeal. Both options are constructed with a  $\frac{3}{4}$ " MDF core, offering superior durability.




**Fossil Grey**



**Perfect White**



**Velvet Blue**



**High Gloss  
Perfect White**

**Cosmo Cabinets** commits to consistently deliver value with a high-quality product using innovative technology and exceptional service in every cabinet.



Our cabinets are made in Eatonton, GA with locally sourced materials offering a quality product with a short lead time. Our manufacturing facility is spread over 350,000 Sft in Eatonton, GA. The plant is set up with high speed state-of-the-art equipment capable of handling small and large orders.

**CONTACT US TODAY TO LEARN  
MORE ABOUT OUR SERVICES AND  
HOW WE CAN BEST SERVE YOUR  
PROJECT NEEDS.**

-  110 Industrial Blvd., Eatonton, GA 31024
-  (770) 934 4044
-  [sales@cosmocabinets.com](mailto:sales@cosmocabinets.com)
-  [WWW.COSMOCABINETS.COM](http://WWW.COSMOCABINETS.COM)

