





**FRESCO DI CALCE®**  
ANTIQUE  
EFFECT FINISH




1600/41 - Polvere + Metallo Blue



1600/41 - Polvere + Metallo Flash Gold



1600/13 - Estate + Metallo Flash Gold



1600/44 - Specchio + Metallo Blue



1600/44 - Specchio + Metallo Flash Gold



1600/16 - Pietra + Metallo Flash Gold

**ENG** Fresco Di Calce®

Fresco Di Calce® is a water-based decorative paint designed to create deep and pronounced antique effects on interior and exterior walls.

**Technical Name**  
Antique Effect Paint.

**Key Properties**

- Unleaded
- Provides life, depth and translucency
- Water based
- Washable (after full curing)
- Non-flammable
- Easy to apply
- Wide range of color combination
- Odorless
- 1 base color 1600/00-Suolo
- Very low VOC content in compliance with:
  - EU directive 2010/79/EU
  - French decree No: 2011-321

**Pack Size**

- 1 US Quart - (0.87kg)
- 1 US Gallon - (3.48 kg)

**Recommended Uses**

Internal and external applications.

**Type of Substrate**

Plaster, embossed wall coverings, gypsum board, concrete, cement rendering, brick work and block work.

**Finish**

Eggshell finish.

**Coverage**

20-25 m<sup>2</sup> per kg.

**Drying Time**


2-4 hours depending on ambient temperature and humidity.

**Thinner**

No thinning required.

**Preparation**

All surfaces to be painted should be clean, dry and free from loose & flaking material. Rub down & rinse. Prime the substrate with COLORTEK® Fresco Di Calce® primer.



**Instructions**

Prime the surface with two coats of Fresco Di Calce® primer. Once the surface has completely dried, apply Fresco Di Calce® using the Fresco brush in rotational movements with uneven pressure. A second coat can be applied if desired. To achieve the metallic effect, apply 1 coat of Metallo by adding 40% of Classic Color.

Tip: Only dip approximately 1mm of the brush into the paint. **Do not apply at temperatures below 5°C or when rain is expected.**

**Cleaning**

Remove as much product as possible from application equipment before cleaning. Clean equipment immediately after use with warm soapy water & rinse thoroughly.

**Do not empty product into drains or watercourses.**

**Additional Info**

Product batches are tested using a quality control system and are ISO 9001:2008 certified.

**Transportation & Storage**

Care should be taken to avoid spillage. Protect from frost & humidity.

**FR** Fresco Di Calce®

Fresco Di Calce® est une peinture décorative à l'eau spécifiquement formulée pour créer des effets rustique sur murs intérieurs et extérieurs.

**Nom Technique**

Peinture à effet antique.

**Propriétés**

- Ne contient pas de plomb
- Produit en base eau
- Lavable
- Facile à appliquer
- Large sélection de couleurs
- Inodore
- 1 couleur de base 1600/00-Suolo
- Faible teneur en COV conformément aux:
  - Directive EU directive 2010/79/EU
  - Decret Français No: 2011-321

**Emballage**

- 1US Quart – (0.85kg)
- 1US Gallon – (3.48 kg)



**Usage Recommandé**

Application en intérieur et extérieur.

**Types de Support**

Enduit, ciment, plâtre et plaque de plâtre, anciennes peintures usuelles absorbantes, etc.

**Finition**

Coquille d'œuf.

**Rendement**

20 à 25 m<sup>2</sup> par kg.

**Temps de Séchage**

Environ 2 à 4 heures en fonction des conditions climatiques et de la température ambiante.

**Diluant**

Aucune dilution requise.

**Préparation du Support**

Le support doit être dur, propre, sain, sec, cohésif et libre de toute matière telle que salpêtre, mousse, lichen ou autres microorganismes pouvant empêcher l'adhérence du produit sur le support.

**Application**

Appliquez deux couches du primaire Fresco Di Calce® et laissez la surface sécher. Appliquez par la suite une couche de Fresco Di Calce® à l'aide d'une brosse en suivant un mouvement circulaire et en variant la pression sur la surface. Appliquez une deuxième couche si nécessaire. Pour obtenir l'effet métallique, appliquez une couche de Metallo en ajoutant 40% de Classic Color. Conseil: Ne pas tromper la brosse plus 1mm dans la peinture.

**Nettoyage des Outils**

Éliminer autant que possible le reste du produit de la surface des outils. Nettoyer ces derniers en les frottant vigoureusement avec de l'eau et du savon. Ne pas vider les restes du produit dans égouts ou les voies d'eau.

**Information Additionnelle**

Le processus de fabrication de Fresco Di Calce® est soumis au plus stricts contrôles de qualité certifiés conformes au standard ISO 9001:2008

**Transport et Stockage**

Stocker le produit à l'abri de l'humidité et des températures de gel.



Synergy, Added Value, Continuous Improvement, Diversity, Integrity, Social Responsibility.

www.colortek.eu  
info@colortek.eu







1600/01 - Aura



1600/05 - Burro




1600/09 - Morbido



1600/13 - Estate



1600/17 - Faro



1600/21 - Tramonto




1600/25 - Rosa



1600/29 - Vero




1600/33 - Noce




1600/37 - Nebbia



1600/41 - Polvere



1600/45 - Nube




1600/49 - Menta




1600/53 - Foglia



1600/57 - Cielo




1600/61 - Segreto




1600/02 - Sole



1600/06 - Pesca



1600/10 - Duna



1600/14 - Fiore



1600/18 - Dolce



1600/22 - Sognare




1600/26 - Amore



1600/30 - Battere



1600/34 - Marrone



1600/38 - Foschia




1600/42 - Vapore




1600/46 - Notte



1600/50 - Verde



1600/54 - Cedro



1600/58 - Marina



1600/62 - Violetta



1600/03 - Oro



1600/07 - Terra



1600/11 - Frutta




1600/15 - Fuoco



1600/19 - Argilla



1600/23 - Picante



1600/27 - Rosso



1600/31 - Cuore



1600/35 - Sabbia




1600/39 - Tempesta



1600/43 - Anima



1600/47 - Grigio



1600/51 - Ombra




1600/55 - Mela



1600/59 - Profondo




1600/63 - Lavanda




1600/04 - Limone



1600/08 - Fusione




1600/12 - Arancia



1600/16 - Pietra




1600/20 - Spezia




1600/24 - Fluo



1600/28 - Caldo



1600/32 - Passione



1600/36 - Vecchio




1600/40 - Carta




1600/44 - Specchio




1600/48 - Onice




1600/52 - Fiume



1600/56 - Foresta



1600/60 - Zingaro



1600/64 - Camelot