

**acoupanel®**  
acoustic wall & ceiling

3D Wall-Perspective  
a new choice of room decoration  
material

# PERSPECTIVE

acoustic panels



**Feltech**

Feltech Manufacturing Co.,Ltd

info@feltech.co.th  
www.feltech.co.th





# PERSPECTIVE

acoustic panels

3D features of the collection designs are available in tile form. For easy to fit spaces and smaller areas where panel sizes are less economical.

3D Wall-Perspective, a new choice of room decoration material.

Product Name **acoupanel® Perspective (APD12)**  
 Product Category Wall and ceiling  
 Composition Polyester fibers with >60% recycled content  
 Weight 2,400 gram/sq.m +/-10%  
 Density 200 kgs/Cubic.m +/-10%  
 Thickness 12 mm with depth to 7.50 mm +/-10%  
 Size 600mm x 600mm +/-10%  
 1,200mm x 2,800 mm +/-10%

Performance  
 Sound Transmission Class STC 5, ISO 717 Part 1  
 Sound Absorption NRC 0.45 with no air gap, ISO 354

**Sound Absorption Coefficients(α<sub>s</sub>)**

(Hz)	125	250	500	1000	2000	4000
Frequency f	0.06	0.02	0.23	0.61	0.89	0.95

Color Fastness to Light > 6, ISO 105 B02-1994  
 Reaction to Fire EN 13501-1, Class B-s1, d0  
 Indoor Air Quality Low VOCs emission, formaldehyde and Phenol-free  
 Moisture Content <0.10% by weight

The specifications are subject to normal manufacturing variations. Due to continued product and performance development, the manufacturer reserves all right to vary specification without prior notice.

Due to the fine, fibrous and textural nature of the product, slight visual imperfections or dye lot variations may be seen when viewing.



PP\_01 Parallel, Celery color  
(Panel 1.20 x 2.80 m)



PT\_01 Curvature, Piano Black color  
(Tile 0.60 x 0.60 m)




PP\_02 Column, AP12 Ivory color  
(Panel 1.20 x 2.80 m)



PT\_05 Diamond edge, AP12 Metal color  
(Tiles 0.60 x 0.60 m)



PP\_03 Serene, Pearl color  
(Panel 1.20 x 2.80 m)



PT\_03 Ripple, AP12 Pitachio color  
(Tiles 0.60 x 0.60 m)



PP\_03 Serene, Pearl color Printed  
(Panel 1.20 x 2.80 m)




PT\_02 Post, AP12 Sencha color  
(Tiles 0.60 x 0.60 m)



PP\_04 Facet, Metal color  
(Tile 1.20 x 2.40 m)


■ Perspective Tiles



PT 01 Curvature , Tile 0.60 x 0.60 m



PT 02 Post, Tile 0.60 x 0.60 m  
(Bevel edge around)



PT 03 Ripple, Tile 0.60 x 0.60 m  
(Bevel edge around)



PT 04 Loft, Tile 0.60 x 0.60 m



PT 05 Diamond edge, Tile 0.60 x 0.60 m

# PERSPECTIVE

acoustic panels


3D Wall-Perspective, a new choice of room decoration material.

feltech.acoustic



PP 01 Parallel, Panel 1.20 x 2.80 m


■ Perspective Panels



PP 02 Column, Panel 1.20 x 2.80 m



PP 03 Serene, Panel 1.20 x 2.80 m



PP 04 Facet, Panel 1.20 x 2.80 m



PP 03 Serene, W100 Printing  
Panel 1.20 x 2.80 m