





Lounge furniture

PRODUCT INFORMATION



ASSMANN

Contents



[A] SYNEO SOFT

The Syneo Soft lounge furniture offers stylish and inviting furnishing solutions – ideal for meetings, confidential conversations, or creative idea exchanges. Syneo Soft impresses with sound-absorbing materials, low-noise ventilation systems, and integrated motion sensors for lighting and ventilation.



Learn more
ass.al/8rxrgsj

Syneo Soft | Lounge

Communication zones reimagined and designed with an appealing design language: Syneo Soft lounge furniture focuses on stylish and acoustically effective furnishing solutions.



Lounge Work & Seat



Lounge Seat



Lounge Conference



Meeting Room | Retreat | Co-Learning-Space

Whether in open space offices, reception and waiting areas, or as a stylish learning and working environment – Syneo Soft lounge furniture can be used flexibly and provides space for meetings, quiet conversations, and creative idea exchange.



Syneo Soft | Lounge

In the midst of it all yet pleasantly secluded: The various seating elements and partition walls of the Syneo Soft Lounge series offer a wide range of design and combination options for configuring and creating personalized lounge and communication zones.



Lounge Conference with Partition Wall



Lounge Conference with Partition Wall



With well-thought-out furnishing concepts, office spaces can be used flexibly. The sound-absorbing Syneo Soft lounge furniture can also function as a temporary workstation where employees can work undisturbed. Thanks to the integrated Netbox Mini Pix, electronic devices can be conveniently charged at the workstation.

Accessories for Syneo Soft | Lounge



Netbox Mini Pix



Syneo Soft | Meeting

The open or closed room-in-room solutions offer the ideal retreat for meetings or creative discussions. The meeting boxes are equipped with electrical components and feature a lighting and ventilation system controlled by a motion sensor.

Accessories for Syneo Soft | Meeting closed




Button



Dimmer



Touchscreen



Sliding door guide with or without floor mounting



Ideal working atmosphere

The elegantly designed lounge systems can be customized with a wide selection of fabrics, colors, and built-in components. By using high-quality materials, our lounge furniture contributes to improved room acoustics, creating a relaxed environment for conversations.



Syneo Soft | Freestyle

New possibilities for the flexible office: The Syneo Soft Freestyle with integrated sofas and table is available either with a stylish slatted roof or a closed roof, and optionally with dimmable LED lighting.



Maximum flexibility in space utilization

The meeting box can be easily moved to wherever it is needed depending on the work situation, offers the utmost seating comfort, and is available with either gliders or casters.

Accessories for Syneo Soft | Freestyle



Individual power supply for autonomous use

For flexible use in the office, the Syneo Soft Freestyle is optionally available with a power plug or integrated battery technology, allowing smartphones or tablets to be charged directly via a power outlet or USB-C and USB-A ports on the table.



Power feed cable with socket available




Battery available with USB-C and USB-A ports

Syneo Soft | Phone

Loud on the outside, quiet on the inside. Syneo Soft Phone is a closed and space-saving retreat for phone calls. The cabins are equipped with a motion sensor that controls the integrated lighting and ventilation system.

Accessories for Syneo Soft | Phone



Button

Dimmer

Touchscreen




Optional with soundproof floor seal




System


Syneo Soft | Lounge



Lounge Work
Height 1,400 mm | Width 1,540 mm




Lounge Conference
Height 1,400 mm | Width 2,540 mm




Lounge Work + Seat
Height 1,400 mm | Width 1,540 mm


Syneo Soft | Lounge




Lounge Seat
Height 1,400 mm | Depth 820 mm



Double Seat Element
Height 1,400 mm | Depth 1,570 mm



Quad Lounge Element
Height 1,400 mm | Depth 1,570 mm



Partition walls
Height 1,400 mm | Depth 70 mm



TV wall mount




Cushion



Netbox Pix



Adapter clamp set
(2 pieces)




(4 pieces)





Table (optional)
Depth 950 mm | 1,150 mm
1,350 mm | 1,550 mm


Syneo Soft | Lounge



Double seat element (left)
Height 1,400 mm | Depth 1,570 mm







Double seat element (right)
Height 1,400 mm | Depth 1,570 mm



Syneo Soft | Meeting | open


Height 2,360 mm



Tables



Cushions






TV wall mount



Power outlet

Syneo Soft | Meeting | closed

Height 2,300 / 2,450 mm | Width 2,840 mm



Power outlet




Touchscreen
(ventilation + light)



Button
(light)



Dimmer
(ventilation + light)




Tables



TV wall mount

Syneo Soft | Freestyle

Height 1,960 mm



Netbox Pix



Remote control



Battery




Netbox Juke



Battery charger

Syneo Soft | Phone



Side table



Side table



Button
(light)



Dimmer
(ventilation + light)



Touchscreen
(ventilation + light)

[A] SYNEO LINE

In the midst of it all, yet pleasantly secluded. The sound-absorbing and clean-lined Syneo Line lounge furniture creates quiet retreats in open office landscapes, providing spaces for undisturbed conversations or focused individual work.



Learn more
ass.al/wtudc5h

Syneo Line | Lounge

Modern solutions for open space offices or waiting areas. The Syneo Line Lounge impresses with its effective acoustic properties and creates a quiet and comfortable retreat.




Syneo Line | Lounge

The stylish Syneo Line lounge furniture combines appealing design and high functionality – from temporary workstations to practical coat storage solutions.




System


Lounge




Seating lounge
Height 930 mm | Depth 800 mm




Lounge elements
Height 1,560 mm | Depth 800 mm




Wall elements
Height 1,560 mm | Depth 800 mm



Temporary workstations
Height 1,560 mm | Depth 800 mm



Seating elements
Height 505 mm | Depth 395 mm



Tables
Depth 600 mm



Partition wall element*



Wall with table*
Table elements integrated
(Connection element)



Coat rails



Magazine holder



Netbox Point

*Only available for order in combination with at least one seating element.

[A] SYNEO SILENCE

Bye-bye office noise! Syneo Silence offers the perfect solution for undisturbed work and improved acoustics. A simple yet convincing solution: temporary retreats that are much more than just phone booths. Spaces for undisturbed meetings, focused moments alone, one-on-one conversations, or small groups.



Learn more
ass.al/711wfy2

Syneo Silence

Whether for individual work, collaborative projects for two, or focused team meetings – with six different variants, the Syneo Silence room systems flexibly adapt to your needs.



Space for quiet

The sound-absorbing surfaces and dark carpet flooring noticeably and effectively improve room acoustics by up to 25 dB*. Various ventilation and lighting options ensure a pleasant working environment and enhance well-being.

Accessories for Syneo Silence



Button



Dimmer



Touchscreen



*Values for Syneo Silence Meeting S



Details that make the difference


It is the combination of design and function that makes Syneo Silence the new favorite spot in the office. A wide range of trendy color and material options ensures that the booths blend seamlessly into the work environment. The booths can be designed in nine selected decors. Optional fabric side walls complete the modern appearance.



High-quality multiplex board with HPL decor coating and optional fabric side walls




Delicate handle strip on the glass door with magnetic closure




Dark carpet flooring for improved acoustics

System


Meetingbox




Single S (with standing table)
Single M (with standing table)
Single M (with seating table and benches)
Single L (with standing table)
Single L (with seating table)



Duo Pod (with standing table)
Duo Pod (with seating table and benches)



Meeting S (with standing table)
Meeting S (with seating table and benches)
Meeting S (with seating table and media wall)
Meeting S (with seating table, media wall, and benches)




Meeting M (with standing table)
Meeting M (with seating table and benches)
Meeting M (with seating table and media wall)
Meeting M (with seating table, media wall, and benches)

Accessories




Side table




Benches

Height 840 mm
 Depth 530 mm



[A] SYNEO PART

The clean design of the Syneo Part elements, combined with high-quality materials and appealing colors, creates a pleasant atmosphere and offers optimal comfort. The movable seating elements enable spontaneous informal exchanges, while the flexible partition walls provide a variety of uses and diverse functionalities.



Learn more
ass.al/5r5sp75

Syneo Part | Diner Module

The Syneo Part Diner Modules can be connected to each other or additionally expanded with a storage element. The comfortable backrests are available in two different heights.



Syneo Part | Seating Elements

The stylish and flexible Syneo Part seating elements are available in three different sizes, are easy to move, and are an ideal complement to all Syneo Lounge or Meeting furnishing solutions.



Syneo Part | Coat Rack

Everything finds its place with the Syneo Part coat rack. Depending on individual needs, individual elements can be connected. In addition to the seating option with backrests of varying heights, combinations with storage and shelving modules are also possible.



Syneo Part | Mobile Pedestal | Bistro Table

The practical Syneo Part mobile pedestals provide ample storage space for important documents and feature a soft seat cushion. The bistro table is the ideal complement to all Syneo Soft and Syneo Part models.



Syneo Part | Wondawall

The Syneo Part Wondawall offers high mobility thanks to its practical casters and can be flexibly used anywhere desired, whether as a privacy screen, room divider, or presentation surface. Depending on needs, it can be customized as a shelf, decoratively upholstered fabric wall, or with acoustic panels. The Syneo Part Wondawall allows the use of sound-absorbing materials to reduce noise levels in the office and improve privacy.



For dynamic space design and increased focus

Its versatility makes it the perfect solution for various requirements and allows easy room reconfiguration. The Syneo Part Wondawall offers flexible room division without permanent walls, making it ideal for open floor plans and large spaces. It enables the separation of work areas to enhance privacy and concentration.



The Syneo Part Wondawall as a planted design element



Mobile privacy screen with acoustic function

Syneo Part | Mobile Partition Walls

Whether as a flipchart, mobile partition wall with screen mount, whiteboard, or lacquered wall panel usable as a magnetic board – the flexible Syneo Part partition walls offer a wide range of possibilities for various requirements.





System

Syneo Part | Wondawall

Width 800/1,200 mm | Height 1,425/1,910 mm

Caster options




*Execution depending on equipment variant
Specifications subject to change. Information on variants and dimensions can be found in the electronic planning data. All dimensions in mm.




System

Syneo Part | Mobile Partition Walls




Mobile partition walls
 Mobile partition walls with rail
 Mobile partition wall with 2 flipchart holders
 Mobile partition wall whiteboard holders
 Mobile partition wall with metal panels, usable as a magnetic surface
 Mobile partition wall prepared for TV

Syneo Part | Diner



Diner
 Width 800/1,000/1,200 mm





Seating elements
 Height 505 mm
 Width 395 mm




Cabinet elements
 Height 3 or 4 levels
 Width 400 mm
 Depth 340 / 360 mm

Syneo Part | Coat Rack



Sliding door cabinet with coat rack element
 Height 1,710 mm



Mobile pedestal
 Width 400 / 800 / 1,200 mm
 Depth 440 mm



Bistro table with magazine compartment
 W / H / D 600 mm

Covers

Fabrics

STEP



STEP MELANGE



Step/Step Melange:

Gabriel

Covers

Fabrics

REPLAY



BLAZER



ERA



Note on wrinkling

The wrinkling on upholstered surfaces can vary depending on the model, upholstery construction, and fabric of our furniture. It is a natural characteristic of high-quality, soft upholstery and emphasizes the special seating comfort and relaxed appearance of our furniture. | Information subject to change


RePlay + Era + Blazer + Rivet + Penta:

camira

Covers

Fabrics

RIVET



Wire | EGL03 Resin | EGL04 Molten | EGL09 Forge | EGL12 Copper | EGL14 Ferrous | EGL15




Chromoly | EGL19 Crucible | EGL24 Woodrose | EGL33 Hemlock | EGL34 Otter | EGL36 Charcoal | EGL37




Deep Sea | EGL48 Twig | EGL49 Grey Brindle | EGL50

PENTA



Gamut | PEN01 Intensity | PEN07 Newton | PEN10 Goethe | PEN11 Dark | PEN12 Shade | PEN13




Tincture | PEN14 Hint | PEN16 Render | PEN17 Glow | PEN19 Light | PEN20 Hue Pen | PEN21



Purity | PEN23 Radiance | PEN28 Marbel | PEN29

Faux leather

SKAI® PAROTEGA NF



Chocolate | F6461656 Lime | F6461657 Black | F6461659 Smoke | F6461660 Birch | F6461661 Cherry | F6461665



Royal | F6461710 Slate | F646173

Note on wrinkling

The wrinkling on upholstered surfaces can vary depending on the model, upholstery construction, and fabric of our furniture. It is a natural characteristic of high-quality, soft upholstery and emphasizes the special seating comfort and relaxed appearance of our furniture. | Information subject to change

Surfaces

BASIC UNI Available for all wooden components



Signal white Grey-white Light grey Cashmere Mist grey Basalt



Graphite grey Terra brown Black

BASIC WOOD Available for all wooden components



Acacia Crema oak Honey oak Oak nougat Walnut Maple



Beech

BASIC + TREND For Syneo Silence HPL decors



Signal white Black Stone green Fjord green Baltic blue Denim blue



Sand yellow Rust red Antique pink

PREMIUM Available for all wooden components



Tobacco oak Oak natura Polar oak Light grey exposed concrete Anthracite exposed concrete

Optimal room acoustics for NEW WORK

Open office structures promote quick exchange among users and emphasize greater flexibility. However, these advantages come with higher noise levels, where even relatively low noise can lead to stress and impair performance. For optimal room acoustics, a short reverberation time and a quiet working environment are crucial – both of which are positively influenced by Syneo room-in-room solutions and sound-absorbing surfaces.



Voices and sounds neither escape from the cabin to the outside nor enter from outside. Conversations can be held undisturbed and confidentially.*



A reduction of just 10 dB(A) corresponds to a subjectively perceived halving of the noise level.

Noise level reduction


	Syneo Soft Phone	Syneo Soft Meeting	Syneo Silence Single S	Syneo Silence Single M
	17 dB(A)	14 dB(A)	26,3 dB(A)	24,9 dB(A)
	Syneo Silence Single L	Syneo Silence DuoPod	Syneo Silence Meeting S	Syneo Silence Meeting M
	25,3 dB(A)	25,1 dB(A)	25,1 dB(A)	25,1 dB(A)

Noise level reduction in the speech frequency range

*Ambient noise levels of 40 dB must be present to prevent sounds from inside the box from escaping outside.

It's all about tone

Acoustics are an often underestimated productivity factor. In addition to new retreat options and the reduction of noise levels in the office, the Syneo furnishing systems equally impress with their modern design, combining both visual and acoustic aspects of space optimization into a smart overall concept. This promotes employee performance and well-being while creating the best conditions for focused work.



The Syneo room systems create both acoustic and visual privacy for conversations and phone calls.



The stress factor of noise is blocked out wherever it hinders productivity. This way, employees can enjoy undisturbed quiet while working inside the box.

ALL YOUR WORKPLACE NEEDS

More information
[assmann.de/en/
 company/awards/](https://assmann.de/en/company/awards/)



Whether flexible desk and storage systems or reception, seminar, and lounge furniture – we offer you not just a wide range of furnishing solutions, but also support you with holistic concepts from a single source: from space planning with **ASSMANN 4ROOMS**, through intelligent work solutions with **ASSMANN SMART**, to personalized home office design with **ASSMANN HOME**.



Awards for our products



Awards for our company





ASSMANN BÜROMÖBEL GMBH & CO. KG

Heinrich-Assmann-Straße 11
D-49324 Melle

Postfach 1222
D-49304 Melle

Fon +49 (0) 5422 706-0

info@assmann.de
www.assmann.de

