

TEKNOFLOR™

HIGH PERFORMANCE FLOORING



SYMPHONY HPD™

COMMERCIAL RESILIENT SHEET FLOORING

TEKNOFLOR™ SYMPHONY HPD™ is a masterfully composed collection that blends abstract visuals into a harmonious whole, offering 24 designs across three distinct styles. Each element of the collection is specifically engineered to meet the rigorous demands of Healthcare, Senior Living, Corporate, and Educational environments. Backed by a 12-Year non-prorated commercial warranty, Symphony™ HPD delivers high-performance durability with a sophisticated aesthetic, allowing you to orchestrate a space that is as resilient as it is inspired.

WOODWIND DESIGN SERIES

Offering a tight, classic look inspired by cross-weave textiles, the Woodwind series provides a stable and refined foundation for interior spaces. Its intricate pattern delivers a professional aesthetic that is both understated and sophisticated, perfect for environments that require a clean, timeless backdrop with a touch of textile-inspired warmth.




STRINGS DESIGN SERIES

Strings offers a subtle yet dynamic take on an open-weave textile. This series provides a melodic, flowing visual that adds quiet movement and texture to a floor. Its light and airy pattern is ideal for creating a sense of openness and tranquility, allowing for effortless coordination with other materials throughout a facility.




BRASS DESIGN SERIES

The Brass series rounds out the collection as a strong abstract with unique, natural movement. Designed to be bold and powerful, these visuals add a sense of organic energy to a room. The natural shifts in the pattern create a dynamic surface that hides wear beautifully while making a confident design statement in high-traffic areas.



SYMPHONY

BENEATH THE DESIGN



1. SURFACE PERFORMANCE ENHANCEMENTS

A UV cured urethane coating for extra wear & stain resistance, and easy care & maintenance.

2. WEAR LAYER

The transparent vinyl wear layer provides exceptional durability against scuffs and abrasions.

3. HIGH RESOLUTION PRINTED FILM

High-resolution printed film delivers the beauty and realism of natural wood with vivid clarity.

4. FIBERGLASS STABILIZER

A fiberglass mesh provides structural integrity, minimizes dimensional movement, and ensures that the floor remains flat.

5. SOLID VINYL CORE WITH SHOCK ABSORBING LAYER

The solid vinyl core consists of two amalgamated layers that provide enhanced dimensional stability and shock absorption for comfort underfoot.

6. NON-WOVEN FIBER BACKING LAYER

The non-woven polyethylene fiber backing improves tensile strength, enhances the product's tear resistance, and increases flexibility. *Appearance may vary by collection.*

FEATURE

BENEFITS

DURABLE AND LOW MAINTENANCE

- No Wax, No Buff; Easily cleaned by damp mopping or auto-scrubbing
- Thicker, 2.3mm gauge for enhanced performance in heavy traffic areas
- Easy maintenance results in savings and investment payback

ENVIRONMENTALLY CONSCIOUS

- No odors from floor finish or strippers; no wax flushed into sewer system
- No antimicrobial agents added
- Floorscore® Certified

DESIGN FLEXIBILITY


- Digital imaging and high resolution offset printing process
- Embossed texture for heightened realism
- Ideal for Healthcare, Senior Living, Corporate/Office, Retail, Hospitality, Academic and Educational Environments

HEAT WELD & COVE


- Coordinating weld rods designed for each SKU creating a seamless installation
- Increased infection control
- Does not promote bacterial growth
- Does not attract debris




SYMPHONY HPD™



ALLEGRO
91105
WOODWIND



MELODY
91108
WOODWIND



OBOE
91104
WOODWIND



PICCOLO
91103
WOODWIND



SONATA
91305
STRINGS




GUITAR
91308
STRINGS




VIOLIN
91304
STRINGS




SOFT SUITE
91303
STRINGS



TRUMPET
91205
BRASS



ACAPPELLA
91208
BRASS



BALLAD
91204
BRASS



TUNE
91203
BRASS




MINUET
91102
WOODWIND



TEMPO
91101
WOODWIND



CONCERTO
91106
WOODWIND



HARMONY
91107
WOODWIND




HARP
91302
STRINGS



CELLO
91301
STRINGS




PHILHARMONIC
91306
STRINGS




RHYTHM
91307
STRINGS




MEASURE
91202
BRASS



FRENCH HORN
91201
BRASS



CRESCENDO
91206
BRASS



ALTO
91207
BRASS

SPECIFICATIONS

PRODUCT DATA

CONSTRUCTION	Heterogeneous Resilient Sheet Flooring
COMPOSITION	Virgin PVC
FINISH	Urethane
OVERALL THICKNESS	2.3 mm (0.091 in.)
WEAR LAYER THICKNESS	20 mil (0.50 mm)
ROLL DIMENSIONS	6.00 ft. x 75.00 ft. (1.83 m x 22.86 m)
ROLL COVERAGE	50.00 sq.yd/Roll (41.81 sq.m)
PATTERN REPEAT	70.86 in. x 39.37 in. (1800 mm x 1000 mm)
COMMERCIAL WARRANTY	12-Year

TECHNICAL DETAILS - SPECIFICATION STANDARD (ASTM F1303)

TEST STANDARDS	REQUIREMENTS	RESULTS
ASTM F1303 - Classification	Refer to Standard	Type 1, Grade 1, Class B
ASTM F410 - Wear Layer Thickness	Min 0.020 in. (0.51 mm)	Passes Requirements
ASTM F137 - Flexibility	0.25-in. (6.4-mm) Mandrel, No Crack or Break	Passes Requirements
ASTM F1914 - Residual Indentation	Max 0.012-in. (0.31-mm) Residual Indent	Passes Requirements
ASTM F970 - Static Load	Max 0.005-in. (0.13-mm) Residual Indent	Passes Requirements
ASTM F925 - Chemical Resistance	No More Than a Slight Change in Surface Dulling, Surface Attack, or Staining	Passes Requirements
ASTM F1514 - Resistance To Heat	Average $\Delta E \leq 8.0$	Passes Requirements
ASTM F1514 - Resistance To Light	Average $\Delta E \leq 8.0$	Passes Requirements

For full list of test results visit [teknofloor.com](https://www.teknofloor.com).

SUSTAINABILITY



FloorScore® is one of the most recognized and stringent indoor air quality standards in the United States and Canada for hard surface flooring materials, adhesives and underlayments. Products that are FloorScore certified contribute to good indoor air quality and comply with CDPH Standard Method v1.2-2017 / CA Section 01350.



The Health Product Declaration® Open Standard provides manufacturers with a standardized, deep-dive methodology of reporting material contents of building products. The contents of such products are scored per GreenScreen for Safer Chemicals and screened against over 70 priority hazard lists, including California Proposition 65 and REACH SVHC.



Environmental Product Declarations (EPD) signal a manufacturer's commitment to measure and reduce the environmental impacts of its products and to report the impacts in a hyper-transparent way. EPDs are standardized, third-party verified documents that allow for the proper comparison of the environmental impacts of goods within the same product category.



"Nutrition labels" for building products, Declare® labels allow manufacturers to clearly and concisely answer three key questions about their products: 1) Where are they made? 2) What end-of-life options are available? 3) What ingredients are present? Ingredients are screened and reported against the International Living Future Institute's Red List.



JUSTSM is a program that provides an innovative platform for organizations to be transparent about operations, including employee benefits and financial and community investments. The program highlights companies that have transparency in social justice and equity policies. HMTX Industries has earned the Just label for all US operations and employees.



A GSA Schedule is a long-term, government-wide contract that simplifies the process of selling products and services to federal, state, and local government agencies.

TEKNOFLOR™

Teknoflor is an HMTX brand.

119 Thomas Street
Calhoun, GA 30701
800.522.9166
teknoflor.com

Please visit teknoflor.com for the most up to date product & technical information.

Product images shown are for reference only and may not reflect final product color match.

March 1, 2026