



Kona Product Data Sheet

Description


Kona synthetic thatch is an innovative roofing system simulating the appearance and texture of natural East Asian grass thatch. Whether installing on a new commercial project or retrofitting a traditionally framed tiki hut, Kona is an easy-to-install system that gives decades of maintenance free performance.

Features

- 30 Year Warranty*
- Manufactured in the USA
- Fire and Wind Resistant
- No maintenance required
- Fast and easy installation
- Life-like design

*See supplemental warranty document

Specifications




Field Shingle

Product Number: 734504
Size: 42"x 16" (1067 x 406 mm)
Weight: 4.27lb (1.94 kg)
Exposure: 8" (203 mm)
Coverage: 2.33 Sq Ft (0.22 Sq M)
Material: PVC with stainless steel binder




ENDUREED[®]

PREMIUM



2" Eave Bend

Product Number: 734505
Size: 42"x 16" (1067 x 406 mm)
Weight: 4.27lb (1.94 kg)
Exposure: 2" (51 mm)
Coverage: 2.33 Sq Ft (0.22 Sq M)
Material: PVC with stainless steel binder



5" Eave Bend

Product Number: 734506
Size: 42"x 16" (1067 x 406 mm)
Weight: 4.27lb (1.94 kg)
Exposure: 5" (127 mm)
Coverage: 2.33 Sq Ft (0.22 Sq M)
Material: PVC with stainless steel binder



Ceiling Shingle

Product Number: 734599
Size: 42"x 14" (1067 x 356 mm)
Weight: 5.76lb (2.61 kg)
Exposure: 12" (305 mm)
Coverage: 3.5 Sq Ft (0.33 Sq M)
Material: PVC with stainless steel binder



Hip/Ridge Shingle

Product Number: 734507
Size: 14" (356 mm)
Weight: 1.42lb (0.64 kg)
Exposure: 4" (102 mm)
Coverage: 0"
Material: PVC with stainless steel binder



Shipping & Storage

	Field shingle	Ceiling shingle	2" eave bend	5" eave bend	Starter shingle	Reverse bend	Hip/ Ridge
Quantity	14 per box	12 per box	8 per box	8 per box	25 per box	5 per box	30 per box
Weight	70lbs	72lbs	36lbs	36lbs	65lbs	24lbs	45lbs

*Weights may vary

Shipping Specifications

Box Size: 44" X 22" X 5" (1120 X 560 X 130 mm)

Pallet: 24 boxes per pallet

Container: 20' 10 pallets (200 boxes) 40' 20 pallets (400 boxes)

Storage: Store Kona shingles in a dry, well-ventilated, weather tight, location..

Do not expose boxes to excessive moisture.

Overstacking boxes or excessive moisture may cause boxes to collapse.

Do not remove wrapping from bulk stack pallet until final placement at installation location.



Testing & Approval

- Florida Product Approval FL-21047-R2

Test Standard	Result
(Fire) ASTM E-108	Class A
(Fire) ASTM E-84	Flame Spread 12.5
(Fire) ASTM E-84	SDI 225
(Wind) ASTM D-3161	Class F (110 MPH Maximum test speed)
(Wind) TAS 107-95	110 MPH (Maximum test speed)
(Wind + Rain) TAS 100-95	Pass
(Wind Uplift) UL 1897	Design Pressure 82.5 PSF (up to 200 mph)
(Impact) UL 2218	Class 4
(Fire) Bs 476 (part 3) (British Standards)	Ext.S.AA
(Fire) BS 476 (part 7) (British Standards)	Class 2
(Fungi) ASTM G 21-96	No Fungi Growth (pass)
(Fire)GB 8624-2012 (China)	Class B1

Maintenance



Kona synthetic thatch was designed so that no maintenance is required to ensure the best performance. However, it is recommended to do an annual inspection and brush off any loose debris to keep your roof looking its best.

Warranty

Kona synthetic thatch has a 30-year limited warranty that covers faults in materials and workmanship in accordance with current warranty terms.

Application

Kona synthetic thatch is a universal system that can be installed on new construction or retrofit to existing structures. The versatile design allows it to be applied to a number of roofing substrates including the following: Plywood deck, Concrete, and Metal. Kona synthetic thatch is suitable for use on any sloped roof with a pitch of 3:12 (14°) or greater. The total thickness of the roof system when installed is 1" (25.4mm).

Plywood Deck:

- 15/32" (12mm) minimum plywood over rafters per local code
- Single Layer Tan Soprema Elastophene Stick HR FR+ GR Cap Sheet (#07066) adhered to plywood
- Kona shingles installed at 8" (203mm) Exposure
- Fasten Kona shingles with stainless steel 1.75" (45mm) 11 ga. Ring shank roofing nails, 4 per shingle
- System weight: 3.10 lbs / sq ft.(15.12 kg / M2)

Plywood Deck, Class A Fire Rated:

- 15/32"(12mm) minimum plywood over rafters per local code
- ½" DensDeck gypsum, fastened 12" O.C. fastened to plywood
- Single Layer Tan Soprema Elastophene Stick HR FR+ GR Cap Sheet(#07066) adhered to DensDeck
- Kona shingles installed at 8" (203mm) Exposure



- Fasten Kona shingles with Stainless steel 2.50" (64mm) 10ga. Ring shank Roofing nails, 4 per shingle
- System weight: 5.10 lbs / sq ft.(24.92 kg / M2)

Metal:

- Existing corrugated metal roofing
- 15/32"(12mm) minimum plywood
- Single Layer Tan Soprema Elastophene Stick HR FR+ GR Cap Sheet(#07066) adhered to plywood
- Kona shingles installed at 8" (203mm) Exposure
- Fasten Kona shingles with stainless steel 1.25" (32mm) 11ga. Ring shank roofing nails, 4 per shingle
- System weight: 4.38 lbs / sq ft.(21.37 kg / M2) using 15/32" (12mm) Plywood

Concrete:

- Structural concrete substrate
- Single Layer Tan Soprema Elastophene Stick HR FR+ GR Cap Sheet(#07066) adhered to concrete
- Kona shingles installed at 8" (203mm) Exposure
- Fasten Kona shingles with 410 stainless steel 1.75" (45mm) 3/16"Tapcon® screws, 3 per shingle
- System weight: 3.10 lbs / sq ft.(15.12 kg / M2)

Premium thatch manufactured by:
Global Innovation LLC

313 SW Windswept Glen
Lake City, Florida 32024



ENDUREED®

1-877-784-2824
www.endureed.com