

However, for the purpose of facilitating to the customer the latest novelties, FIGUERAS reserves the right to introduce the modifications and variations that it considers most appropriate and suitable for marketing its products.



Flex RT 2314

## Technical specifications

### › Structure

- Made of tube and steel plate arc welding with continuous wire.

### › Paint

- Electrostatic powder polyester paint.
- Paint Thickness: 70-80 microns.
- Grid adhesion according to UNE-EN ISO 2409 : 100%.

### › Upholstery

- Reaction to fire standards:
  - Spain: UNE-EN 1021 Parts 1 and 2.
  - France: NF D 60-013.
  - Italy: UNI 9175 Class 1.IM.
  - Germany: DIN 66084.
  - USA: CAL TB117.

### › Polyurethane foam

- Seat density: 60-65 Kg/m<sup>3</sup>.
- Backrest density: 50-55 Kg/m<sup>3</sup>.

### › Aluminium

- Die cast aluminium alloy.
- Tensile strength (Rm)=240 Mpa.
- Elongation <1%.

### › Fire resistance

- BS 5852. Clause 12. Ignition sources 0, 1 and 5. (with approved fabric).
- USA:CAL T.B. 133 (with approved fabric).


### › Resistance and durability classification

- UNE-EN 12727 Level 4 (Severe use).

### › Ergonomics and Comfort

- Seat tested in official laboratory - IBV - Instituto de Biomecánica de Valencia.

## General dimensions



Flex RT 2314

## General description

› A revolutionary concept in seating. It combines the comfort and safety of a floor-mounted seat with total freedom of movement allowing it to rotate 360° and slide horizontally by 17 cm. It automatically returns to its position, leaving the place clean and tidy. It has all the features of the Flex 6040 seat.

· This system is specially designed for parliamentary or boardroom designs, but is also ideal for any other space that requires mobility (lounges, meeting points, etc.).



· Thanks to its easy movement, the seat is always in an ideal working position. The seat rotates enabling the user to talk to the person sitting in front or behind.

· Once unoccupied, the seats always return to their original position in silence, ensuring that the place always looks tidy and is easy to clean.

· The seat return system ensures that the aisles are always clear in the event of an emergency evacuation.

· These seats are made of a compact block of cold molded polyurethane foam that completely covers a metal structure composed of a curved tube frame. The block has an upholstered cover that can be easily interchanged via a zipper system. The backrest shares the same features. The armrest consists of a compact upholstered block that extends to the middle of the leg.

· The seat and backrest assembly rests on a painted die-cast aluminium centre leg which also houses the RT mechanism and is attached to the floor with four anchor points.

· Fire Response: This product complies with international standards.

However, for the purpose of facilitating to the customer the latest novelties, FIGUERAS reserves the right to introduce the modifications and variations that it considers most appropriate and suitable for marketing its products.

## Materials and finishes

### › Metal Parts Features

- The steel complies with the following European standards:
  - Tube up to 2mm thick: Alloy designation according to UNE-EN 10305 part 3: E-220.
  - Tube more than 2 mm thick: Alloy designation S275JR.
  - Plate: alloy designation according to EN 10111: DD12.

### › Protection and Paint of Metal Parts

- Prior to powder coating, metal parts are treated with a three stage, non-acidic cleaning process to achieve superior finish adhesion. The finishing of the thermosetting polyester powder coating must be applied by electrostatic means with a minimum thickness of 70-80microns.
- After coating, the parts must be oven cured to create a durable finishing that meets the following requirements:
  - Composition: Polyester powder suitable for outdoor use.
  - Cross Cut Test Adhesion according to UNE-EN ISO 2409 classification GT 0-1.
  - Scratch resistance according to ISO 15184:98 Level HB-H.
  - Total thickness: 70-80Microns.
  - Rust resistance (NSS), according to ISO 9220: 200 h.
  - Resistance to MEK 50 double rubs without paint stripping.

### › Seat and Backrest Cushions Features

- The seat and backrest cushions are made of cold moulded polyurethane foam.
- In the inside, both include metallic tube structures and steel plates, with springs. This system guarantees great comfort and avoids the appearance of deformations in the foams, even after an intensive use.
- The upholstery of the cushions and the headrest is handcrafted, allowing all types of upholstery: fabrics, similar leather or natural leather. Within the range of products approved by Figueras.
- This allows the seat to be customized according to each project's requirements.
- Optionally, a fire barrier can be incorporated between the upholstery and the PUR foam.
- They comply with all international fire behaviour requirements.
- Seat foam density: 60-65 kg/m<sup>3</sup>.
- Backrest foam density: 50-55kg/m<sup>3</sup>.

### › Upholstery

• Group A:  
Figueras Fabrics ®



• Group B:



(\*) Fabric sample / printed by collection. Check colours available.

### › Pigments for metal parts

