

# Townships Collection

**CONSTRUCTION** Steel doors with PVC overlays

**THICKNESS** 1 3/4" door + 5/8" overlays

**INSULATION** R-16 Polyurethane



# Princeton doors




PRINCETON P-23, 10' X 8', BLACK DOOR AND OVERLAYS, PANORAMIC WINDOWS WITH WHITE SANDBLASTED GLASS



PRINCETON P-23, 8' X 7', DESERT SAND DOORS AND OVERLAYS, 8 LITE PANORAMIC WINDOWS WITH CLEAR GLASS

## Available designs



The Princeton is only manufactured with a 30" high Panoramic section.



PRINCETON P-11, 9' X 8', ICE WHITE DOORS AND OVERLAYS, 8 LITE PANORAMIC WINDOWS WITH CLEAR GLASS



PRINCETON P-31, 9' X 8', CHOCOLATE WALNUT DOORS AND OVERLAYS, 4 LITES PANORAMIC WINDOWS WITH CLEAR GLASS

# Eastman doors




EASTMAN E-23, 10' X 7', ICE WHITE DOORS AND OVERLAYS, 8 LITE PANORAMIC WINDOWS



EASTMAN E-13, 9' X 7', BLACK DOORS AND OVERLAYS, 4 VERTICAL LITE PANORAMIC WINDOWS

## Available designs



The top section of the Eastman can have a 24" high Panoramic section, regular windows, or no windows.

## Enhance with decorative hardware

Available for Princeton and Eastman. To find the perfect ones for you, build your door at [garaga.com/designcentre](https://garaga.com/designcentre).



EASTMAN E-11, 16' X 8', ICE WHITE DOOR AND OVERLAYS, CLEAR WINDOWS

# Cambridge doors




CAMBRIDGE CM, 9' X 7', CLAYSTONE DOOR AND OVERLAYS, 4 LITE PANORAMIC WINDOWS WITH CLEAR GLASS




CAMBRIDGE CS, 9' X 7', CHOCOLATE WALNUT FAUX WOOD DOOR AND OVERLAYS, PANORAMIC WINDOWS WITH CLEAR GLASS

## Available designs



Due to the architecture, section heights are not identical.



CAMBRIDGE CL, 9' X 8', BLACK DOORS AND OVERLAYS



CAMBRIDGE CL, 16' X 8', BLACK DOOR AND OVERLAYS, PANORAMIC WINDOWS WITH CLEAR GLASS



PRINCETON P-31, 18' X 8', ICE WHITE DOOR AND OVERLAYS, PANORAMIC WINDOWS WITH CLEAR GLASS

# Luxurious and elegant overlays

Elevate your home's exterior with our exclusive Townships Collection. Combine steel doors with refined PVC overlays that merge timeless charm with modern strength. Designed to enhance any home's style, these doors add lasting value and create an inviting, sophisticated look that will make every arrival feel special.



PRINCETON P-11, 9' X 8', DARK WALNUT FAUX WOOD DOORS AND BLACK OVERLAYS, 4 VERTICAL LITE PANORAMIC WINDOWS WITH CLEAR GLASS



PRINCETON P-22, 9' X 7', ICE WHITE DOORS AND OVERLAYS, ARCH OVERLAY WITH PANORAMIC WINDOWS, CLEAR GLASS

## Arch overlay

Always installed in the top section and only available with Panoramic windows or without windows. Available for Princeton and Eastman. Arch Overlay is available in Ice White, Desert Sand, Claystone and Black.



## Panel colors



## Overlay colors






EASTMAN E-11, 10' X 7', DESERT SAND DOOR AND OVERLAYS, 8 LITE PANORAMIC WINDOWS

## Windows

### Panoramic




### Standard³



### Orion



### Types of glass



(1/5 = clear, 5/5 = opaque)

## Novatech®

Match your garage door glass with your entry door glass. More than 20 options. Scan to see all glass choices.




## Window size comparison

### Panoramic

#### Princeton



#### Eastman and Cambridge



### Standard

#### Eastman



The squares widths vary depending on the design and size of the chosen door.

Panoramic, Orion and Types of Glass windows can only be installed in the top section. Panoramic window frames are not insulated and are made from extruded aluminum that is always finished in white on the interior of the section. From the outside, the extrusion will be hidden by the decorative overlays.


¹ Only available for Princeton P-31 layout.

² Not available for Cambridge CM and CS layouts.

³ Not available for Cambridge and Princeton layouts.

⁴ Clear 40" x 13" thermopane glass is also available with the Low-E Argon energy option.

## Construction details

Insulation level	Best (R-16)
Energy efficiency	● ● ● ● ●
Soundproofing	● ● ● ● ●
Rigidity	● ● ● ● ●
Construction	<p>1 ¼" door + 5/8" overlays</p> <p>3 layers with polyurethane insulation</p>  <p><b>InterLok™ joints</b> block air infiltration for superior thermal insulation</p> <p><b>Polyurethane insulation</b> acts as a thermal break to prevent transfer of cold or heat</p> <p><b>Wood end blocks</b> are one of the most effective thermal breaks</p>



EASTMAN E-11, 16' X 8', BLACK DOOR AND OVERLAYS, 4 VERTICAL LITE PANORAMIC WINDOWS

**Garage door sizes:** Widths from 8' to 18', in 1" increments. Heights in 3" increments: Princeton from 7' to 8', Eastman and Cambridge from 6'6" to 8'. See your garage door dealer for more details on oversized doors available.

## Warranty

Door sections: limited lifetime. Dura+ hardware: 2 years. Weatherstripping: 1 year. Windows: 10 years against seal defects and 1 year for thermal break. Decorative PVC moldings: 10 years (discoloration) and 5 years (delamination).

# LiftMaster®

## Smart and quiet openers

POWERED BY myQ®

### ELITE SERIES®



- Ultra quiet
- Belt or chain drive
- ¾ HP, AC or DC power
- Integrated camera for some models



- Ultra quiet
- Jackshaft
- DC power

### PREMIUM SERIES®



- Quiet
- Belt or chain drive
- ½ HP, AC or DC power

### CONTRACTOR SERIES®



- Belt or chain drive
- ½ HP, AC or DC power



# GARAGA®

1 800 464-2724  
info@garaga.com  
garaga.com

logo FSC

**YOUR  
GARAGA  
DISTRIBUTOR**