

SMART-CAPS™



Features & Benefits

- Works with standard strut
- 14" and 24" available
- Ready-to-use with Dakota Smart-Clamps™
- Double-sided top and bottom row capability
- Optional receiver available for easy installation to strut*
- Clean and organized appearance



bimobject®

Product Details


Material: 12 Gauge Structural Steel, Grade 50

Finish: Pre-galvanized Zinc


Applications: Electrical



Side view
of Smart-Cap™




Place one side of
locking tab into strut



Push down until
you hear a click

PART#	DESCRIPTION	LENGTH	GAUGE	HEIGHT
DS-CAP12-14-PG	14" Dakota Smart-Cap w/o receiver	1' 2" (14")	12 GA.	13/16"
DS-CAP12-24-PG	24" Dakota Smart-Cap w/o receiver	2' (24")		
DS-CAPTR12-14-PG	14" Dakota Smart-Cap w/ threaded receiver	1' 2" (14")		
DS-CAPTR12-24-PG	24" Dakota Smart-Cap w/ threaded receiver	2' (24")		

SMART-CAP™ SPECIFICATIONS



A HOLE TO HOLE CENTER DISTANCE	B DISTANCE BETWEEN SLOTS	C SLOT LENGTH	D OVERALL LENGTH	E HOLE DIAMETER	F OVERALL WIDTH	G INSIDE WIDTH	H INSIDE HEIGHT
22" Centers (55.8mm)	31.5" (8mm)	0.787" (20mm)	1'2" (14")	13/32" (11.1mm)	1.91" (48.5mm)	1.7" (43.2mm)	13/16" (20.6mm)
			2' (24")				
			10' (120")				
			1'2" (14")				
			2' (24")				

DOUBLE THE CAPACITY OF YOUR SUPPORT SYSTEM

