

VIVREAU TOP 50/ 85

COUNTERTOP AND FLOORSTANDING



INSTALLATION REQUIREMENTS

V. Technical data

	VIVREAU Top 50 VIVREAU Top 50 HygienePlus	VIVREAU Top 85 VIVREAU Top 85 HygienePlus
Cooling capacity (l/h)	50	85
Minimum cupboard height (mm)	700	700
Dimensions Countertop (W x H x D mm)	277 x 530 x 518	277 x 530 x 518
Dimensions Floorstanding (W x H x D mm)	277 x 1430 x 518	277 x 1430 x 518
Dispensing height (mm)	330	330
Weight Countertop (kg)	35	40
Weight Base cabinet (kg)	7	7
Max. flow rate (l/min)	2	2
Drip tray	Part of the appliance, movable	Part of the appliance, movable
Water types	Ambient, chilled still & chilled sparkling (medium & classic)	Ambient, chilled still & chilled sparkling (medium & classic)
Hygiene configuration	ThermalGate™(Standard) HygienePlus (Optional)	ThermalGate™(Standard) HygienePlus (Optional)
Waste water connection	Waste water pipe (optional) Waste water container (optional)	Waste water pipe (optional) Waste water container (optional)
Voltage (V)	230	230
Frequency (Hz)	50	50
Max. current (A)	2.0	2.4
Max. power consumption (W)	440	540
Min. fuse (A)	10	10
Protection class	I	I
CO ₂ operating pressure (MPa)	0.45	0.45
Max. inlet water pressure (MPa)	0.6	0.6
System operating inlet water pressure (MPa / psi)	0.4 / 58 (at 2 l/min water flow)	0.4 / 58 (at 2 l/min water flow)
Inlet water temperature (°C)	5 - 25	5 - 25
Temperature range (°C)	16 - 32	16 - 32
Max. relative humidity (%)	60	60
Noise emission (dbA)	< 58	< 62
Refrigerant	Type	R290
	g	54
Height above sea level (m)	< 2000	< 2000

BRITA GmbH
Heinrich-Hertz-Str. 4
65232 Taunusstein
Germany

www.brita.net

BRITA Vivreau Ltd
1st Floor
Beaufort House
Cricket Field Road
Uxbridge UB8 1QG
United Kingdom

www.vivreau.com